


+ ProKIT - WHEEL BEARING KIT



# Our most important product: Our customers' satisfaction

We are among the leading manufacturers for rolling bearings, linear technology components and steering systems worldwide. We can be found on almost every continent – with production facilities, sales offices and technology centres – because our customers appreciate short decision-making channels, prompt deliveries and local service.



## The NSK Company

NSK commenced operations as the first Japanese manufacturer of rolling bearings back in 1916. Ever since, we have been continuously expanding and improving not only our product portfolio but also our range of services for various industrial sectors. In this context our worldwide research and production facilities are linked together in a global network. Here we concentrate not only on the development of new technologies, but also on

the continuous optimisation of quality – at every process stage. Among other things, our research activities include product design, simulation applications using a variety of analytical systems and the development of different steels and lubricants for rolling bearings.

More about NSK under: [www.nskeurope.com](http://www.nskeurope.com)

# Automotive Aftermarket

---

## Products

NSK manufactures 100% genuine parts as specified and used by the OE car manufacturers and first tier suppliers. The quality of all parts is tested and approved by the our OE customers. This is extremely important as NSK's overall aim is to always strive for the absolute best in quality.

### Country of Origin

We manufacture our products in the vicinity of the most important international automobile manufacturers and suppliers. The short distances promote regular communication and coordination and guarantee optimum service. For common high volume vehicles, bearings are made at multiple NSK factories to support local supply.

### Global standards apply to NSK Automotive products

NSK products comply with the technical specifications and quality standards defined by the group headquarters in Japan in conjunction with our OEM customers. Uniform process flows, global production standards and our staff's high level of expertise also guarantee that our bearings are always a constant high quality.

NSK wheel bearings are compact and, due to their low weight, guarantee efficient fuel consumption. What's more, they also contribute to the vehicle's and the passengers' active and passive safety, through integrated ABS sensors and other technology. For this reason, NSK never compromises on quality or manufacturing processes.

### Approved by automobile manufacturers and suppliers

Only approved sources of steel, lubricants and seal components are used to further ensure the same performance of our products no matter which factory is producing for our customers. Due to the approval of the OEMs, spare-parts distributors can also be sure of receiving only high-quality and precision-fit wheel bearings – from every NSK factory.

## Automotive Aftermarket


### Nothing beats OE Quality

NSK, as a worldwide strategic partner to the top automobile manufacturers and suppliers in the automotive industry, provide solutions that offer greater performance while taking up less space. Intelligent steering systems, engine and transmission bearings, bearings for ancillaries – our products not only ensure more efficient use of fuel, but also increase active and passive safety for vehicles.



# Automotive Business

Our innovative solutions contribute to increase the performance of the next generation of vehicles and support our position as strategic partner to the top automakers and suppliers around the world: ultra-high-speed bearings for electric motors, new ball screw units for advanced braking systems, proprietary traction reducer technology or force feedback actuators for steer-by-wire. A few examples of our products which improve fuel economy, vehicle range, safety and user comfort in modern vehicles.



# ProKIT - Wheel Bearing Kit



## What is ProKIT?

**ProKIT** is NSK's new range for the **Independent Automotive Aftermarket**. ProKIT packages consist of all the necessary **components** needed to mount the product concerned.

QR-codes are included on the packaging, providing detailed information about the product, its applications and traceability.

ProKIT packages for the AAM contain only 100% genuine wheel bearings, as tested and approved by the OEM. Moreover, ProKIT comprises all components necessary to mount the product concerned, including snap rings, seals and fasteners. This is extremely important as NSK's overall aim is to always strive for the absolute best in quality. All ProKITs are produced in an ISO accredited environment.

As well as producing the highest quality automotive car parts, the ProKIT packaging itself is designed to meet the highest NSK quality standards and the boxes have been designed to stack easily without damage, thus protecting the contents.

## Simple 7 Digit Reference Number:

KH0....  
Taper Roller Bearings



KH1....  
Generation 1



KH2....  
Generation 2



KH3....  
Generation 3


























# Pictograms and Abbreviations

	EN	JA	DE	FR	IT	ES	PL	TR
	Front Axle	フロントアクスル	Vorderachse	Essieu avant	Assale anteriore	Eje delantero	Oś przednia	Ön aks
	Front Axle Left	フロントアクスル 左	Vorderachse Links	Essieu avant gauche	Assale anteriore Sx	Eje delantero, izquierda	oś przednia, z lewej	Ön aksın solu
	Front Axle Right	フロントアクスル 右	Vorderachse Rechts	Essieu avant droit	Assale anteriore Dx	Eje delantero, derecha	os przednia, z prawej	Ön aksın sağı
	Rear Axle	リアアクスル	Hinterachse	Essieu arrière	Assale posteriore	Eje trasero	Oś tylna	Arka aks
	Rear Axle Left	リアアクスル 左	Hinterachse Links	Essieu arrière gauche	Assale posteriore Sx	Eje trasero izquierda	Oś tylna strona lewa	Sol arka aks
	Rear Axle Right	リアアクスル 右	Hinterachse Rechts	Essieu arrière droit	Assale posteriore Dx	Eje trasero, derecha	Oś tylna strona prawa	Sağ arka aks
... ->	Construction year from	次の製造年 から	Baujahr ab	Année à partir de	Anno da	Año con strucción desde	Rok prod. Do	Yapı serisi ...'ye kadar
-> ...	Construction year to	次の製造年まで	Baujahr bis	Année jusqu'à	Anno fino a	Año construcción hasta	Rok prod. Od	Yapı serisi ...'dan itibaren
VIN: ... -> VIN: -> ...	Vehicle Ident. No: from Vehicle Ident. No: to	次の車両識別番号から 次の車両識別番号まで 車両識別番号	Fahrgestell-Nr.: ab Fahrgestell-Nr.: bis Fahrgestell-Nr.:	N° de châssis à partir de N° de châssis jusqu'à N° de châssis:	N° telaio: da N° telaio: fino a N° telaio:	N° de chasis: desde N° de chasis: hasta N° de chasis:	Numer podwozia: od Numer podwozia: do Numer podwozia:	Yürür şasi numarasından itibaren Yürür şasi numarasına kadar Şasi numarası
	For PR number	PR 番号用	Für PR-Nummer	Pour numéro PR	Per N° PR	Número de PR	dla numeru PR	PR numarası için
	Not for PR number	PR 番号には適していません	Nicht für PR-Nummer	Pas pour numéro PR	Non per N° PR	no para el numero PR	nie dla numeru PR	PR numarası için değil
	for OE number	OE 番号用	für OE-Nummer	pour numéro OE	per N° OE	para OE N°	dla numeru OE	OE numarası için
Orga -> ...	for RPO number (vehicle manufacturing date) up to	次の組織番号まで	für Organisationsnr. bis	pour numéro OPR (date de fabrication du véhicule) jusqu'à	per numero organizzazione fino a	para n.º de org. hasta	dla numeru organizacyjnego do	...e kadar organizasyon numarası için
	Engine Code	エンジンコード	Motorcode	Code moteur	Codice motore	Código de motor	Kod silnika	Motor kodu
	For vehicle prod. country: GB	車両製造国: 英国	Für Fahrzeugprod. Land: GB	Pays constructeur du véhicule: Grande-Bretagne	Paese produzione veicolo: Gran Bretagna	País producción vehículo: Gran Bretaña	Kraj producenta pojazdu: Wielka Brytania	Aracın üretildiği ülke: Büyük Britanya
	For vehicle prod. country: Hungary	車両製造国: ハンガリー	Für Fahrzeugprod. Land: Ungarn	Pays constructeur du véhicule: Hongrie	Paese produzione veicolo: Ungheria	País producción vehículo: Hungría	Kraj producenta pojazdu: Węgry	Aracın üretildiği ülke: Macaristan
	Not for vehicle prod. Country: China	車両製造国には適していません 中国	Nicht für Fahrzeugprod. Land: China	Pas pour pays constructeur du véhicule Chine	Non per paese produzione veicolo Cina	No para país producción vehículos China	Nie dla kraju produkcji pojazdu Chiny	Aracın üretildiği ülke için değil Çin
	For country-spec. model: Australia	国別の仕様: オーストラリア	Länderausf.: Australien	Type de pays: Australie	Modello p. paesi: Australia	Modelo por país: Australia	Wersja na kraj: Australia	Ülke versiyonu: Avustralya
	For country-spec. model: Switzerland	国別の仕様: スイス	Länderausf.: Schweiz	Type de pays: Suisse	Modello p. paesi: Svizzera	Modelo por país: Suiza	Wersja na kraj: Szwajcaria	Ülke versiyonu: İsviçre
	For country-spec. model: Europe	国別の仕様: ヨーロッパ	Länderausf.: Europa	Type de pays: Europe	Modello p. paesi: Europa	Modelo por país: Europa	Wersja na kraj: Europa	Ülke versiyonu: Avrupa
	For country-spec. model: Japan	国別の仕様: 日本	Länderausf.: Japan	Type de pays: Japon	Modello p. paesi: Giappone	Modelo por país: Japón	Wersja na kraj: Japonia	Ülke versiyonu: Japonya
	For country-spec. model: Sweden	国別の仕様: スウェーデン	Länderausf.: Schweden	Type de pays: Suède	Modello p. paesi: Svezia	Modelo por país: Suecia	Wersja na kraj: Szwecja	Ülke versiyonu: İsveç
	For country-spec. model: Thailand	国別の仕様: タイ	Länderausf.: Thailand	Type de pays: Thaïlande	Modello p. paesi: Thailandia	Modelo por país: Tailandia	Wersja na kraj: Tajlandia	Ülke versiyonu: Tayland
	For country-spec. model: Türkiye	国別の仕様: トルコ	Länderausf.: Türkei	Type de pays: Turquie	Modello p. paesi: Turchia	Modelo por país: Turquía	Wersja na kraj: Turcja	Ülke versiyonu: Türkiye
	Not for country-spec. model: Brazil	国仕様には適しません: ブラジル	Nicht für Länderausf.: Brasilien	pas pour version-pays: Brésil	Non per versione per paese: Brasile	No para modelo país: Brasil	Nie dla wersji dla kraju: Brazylia	Ülke versiyonu için geçerli değildir: Brezilya
	Not for country-spec. model: Türkiye	国仕様には適しません: トルコ	Nicht für Länderausf.: Türkei	pas pour version-pays: Turquie	Non per versione per paese: Turchia	No para modelo país: Turquía	Nie dla wersji dla kraju: Turcja	Ülke versiyonu için geçerli değildir: Türkiye

## Pictograms and Abbreviations

	EN	JA	DE	FR	IT	ES	PL	TR
	Special Purpose Vehicle: for government vehicles	特殊用途車両: 公用車用	Sondereinsatz-Fzg: für Behördenfzg	Véhicule à usage spécial: pour véhicules d'administration	Autoveicolo uso speciali: per veicoli dell'amministrazione pubblica	Vehículo especial: para vehículos admon. Pública	Pojazd specjalnego przeznaczenia: dla pojazdów administracyjnych	Özel kullanım amaçlı araç: Resmi araçlar için
	Special Purpose Vehicle: for ambulances	特殊用途車両: 救急車用	Sondereinsatz-Fzg: für Krankenwagen	Véhicule à usage spécial: pour ambulances	Autoveicolo uso speciali: per ambulanza	Vehículo especial: para ambulancias	Pojazd specjalnego przeznaczenia: dla karettek	Özel kullanım amaçlı araç: Hastane arabası için
	Special Purpose Vehicle: for armoured vehicles	特殊用途車両: 装甲車両用	Sondereinsatz-Fzg: für gepanzerte Fzg	Véhicule à usage spécial: pour véhicules blindés	Autoveicolo uso speciali: per veicoli corazzati	Vehículo especial: para vehículos blindados	Pojazd specjalnego przeznaczenia: dla pojazdów uzbrojonych	Özel kullanım amaçlı araç: Zırhlı araçlar için
	Special Purpose Vehicle: for motor home	特殊用途車両: キャンピングカー用	Sondereinsatz-Fzg: für Wohnmobile	Véhicule à usage spécial: pour camping-cars	Autoveicolo uso speciali: per camper	Vehículo especial: para autocaravana	Pojazd specjalnego przeznaczenia: dla pojazdów kempingowych	Özel kullanım amaçlı araç: Karavanlar için
	Special Purpose Vehicle: for campers	特殊用途車両: キャンピングカー用	Sondereinsatz-Fzg: für Campingfzg	Véhicule à usage spécial: pour véhicule de camping	Autoveicolo uso speciali: per autoroulotte	Vehículo especial: para vehículos de camping	Pojazd specjalnego przeznaczenia: dla samochodów kempingowych	Özel kullanım amaçlı araç: Kamp araçları için
	Special Purpose Vehicle: not for government vehicles	特殊用途車両: 公用車には適していません	Sondereinsatz-Fzg: nicht für Behördenfzg	Véhicule à usage spécial: pas pour véhicules de l'administration	Autoveicolo uso speciali: Non per veicoli dell'amministrazione pubbl.	Vehículo especial: no para veh. admon. Pública	Pojazd specjalnego przeznaczenia: nie dla pojazdów administracyjnych	Özel kullanım amaçlı araç: Resmi araçlar için değil
	Special Purpose Vehicle: not for ambulances	特殊用途車両: 救急車には適していません	Sondereinsatz-Fzg: nicht für Krankenwagen	Véhicule à usage spécial: pas pour ambulances	Autoveicolo uso speciali: Non per ambulanze	Vehículo especial: no para ambulancias	Pojazd specjalnego przeznaczenia: nie dla karettek	Özel kullanım amaçlı araç: Hastane arabası için değil
	Special Purpose Vehicle: not for armoured vehicles	特殊用途車両: 装甲車両には適していません	Sondereinsatz-Fzg: nicht für gepanzerte Fzg	Véhicule à usage spécial: pas pour véhicules blindés	Autoveicolo uso speciali: Non per veicoli corazzati	Vehículo especial: no para vehículos blindados	Pojazd specjalnego przeznaczenia: nie dla pojazdów uzbrojonych	Özel kullanım amaçlı araç: Zırhlı araçlar için değil
	Special Purpose Vehicle: not for motor home	特殊用途車両: キャンピングカーには適していません	Sondereinsatz-Fzg: nicht für Wohnmobile	Véhicule à usage spécial: pas pour camping-cars	Autoveicolo uso speciali: Non per camper	Vehículo especial: no para autocaravana	Pojazd specjalnego przeznaczenia: nie dla pojazdów kempingowych	Özel kullanım amaçlı araç: Karavanlar için değil
	Special Purpose Vehicle: not for campers	特殊用途車両: キャンピングカーには適しません	Sondereinsatz-Fzg: nicht für Campingfzg	Véhicule à usage spécial: pas pour véhicules de camping	Autoveicolo uso speciali: Non per autoroulotte	Vehículo especial: no para ve. Camping	Pojazd specjalnego przeznaczenia: nie dla samochodów kempingowych	Özel kullanım amaçlı araç: Kamp aracı için değil
<b>MT</b>	Transmission Type: Manual Transmission	トランスミッションの方式: マニュアルトランスミッション	Getriebeart: Schaltgetriebe	Type d'entraînement: boîte de vitesses manuelle	Modalità di trasmissione: Cambio manuale	Clase de caja de cambios: Caja de cambios manual	Rodzaj skrzyni biegów: Skrzynia biegów manualna	Şanzıman türü: Mekanik şanzıman
<b>MT</b> <sup>⑤</sup>	Transmission Type: 5-Speed Manual Transmission	トランスミッションの方式: 5速トランスミッション	Getriebeart: Schaltgetriebe 5 Gang	Type d'entraînement: Boîte de vitesses manuelle à 5 vitesses	Modalità di trasmissione: Cambio manuale a 5 marce	Clase de caja de cambios: Caja de cambios manual, 5 marchas	Rodzaj skrzyni biegów: Przekładnia manualna 5-biegowa	Şanzıman türü: Mekanik şanzıman 5 vites
<del><b>MT</b></del>	Transmission Type: not for manual transmission	トランスミッションの方式: マニュアルトランスミッションには適していません	Getriebeart: nicht für Schaltgetriebe	Type d'entraînement: pas pour boîte à vitesse manuelle	Modalità di trasmissione: non per cambio manuale	Clase de caja de cambios: no para caja de cambios manual	Rodzaj skrzyni biegów: nie dla mechanicznej skrzyni biegów	Şanzıman türü: Mekanik şanzıman için değil
<del><b>MT</b></del> <sup>⑤</sup>	Transmission Type: not for 5-speed manual transmission	トランスミッションの方式: マニュアルトランスミッション 5速には適していません	Getriebeart: nicht für Schaltgetriebe 5 Gang	Type d'entraînement: pas pour boîte de vitesses manuelle 5 vitesses	Modalità di trasmissione: non per cambio manuale a 5 marce	Clase de caja de cambios: no para caja de cambios manual 5 marchas	Rodzaj skrzyni biegów: nie dla 5-biegowej mech. skrzyni biegów	Şanzıman türü: Mekanik şanzıman 5 vites için değil
<del><b>MT</b></del> <sup>⑥</sup>	Transmission Type: not for 6-speed manual transmission	トランスミッションの方式: マニュアルトランスミッション 6速には適していません	Getriebeart: nicht für Schaltgetriebe 6 Gang	Type d'entraînement: pas pour boîte de vitesses manuelle 6 vitesses	Modalità di trasmissione: non per cambio manuale a 6 marce	Clase de caja de cambios: no para caja de cambios manual 6 marchas	Rodzaj skrzyni biegów: nie dla 6-biegowej mech. skrzyni biegów	Şanzıman türü: Mekanik şanzıman 6 vites için değil
<b>AT</b>	Transmission Type: not for automatic transmission	トランスミッションの方式: オートマチックトランスミッションには適していません	Getriebeart: nicht für Automatikgetriebe	Type d'entraînement: pas pour boîte de vitesses automatique	Modalità di trasmissione: Non per trasmissione automatica	Clase de caja de cambios: no para transmisión automática	Rodzaj skrzyni biegów: nie dla automatycznej skrzyni biegów	Şanzıman türü: Otomatik şanzıman için değil
<b>AT</b> <sup>④</sup>	Transmission Type: 4-Speed Automatic Transmission	トランスミッションの方式: 4速オートマチックトランスミッション	Getriebeart: Getriebeautomatik 4 Gang	Type d'entraînement: Boîte automatique à 4 vitesses	Modalità di trasmissione: Cambio automatico a 4 marce	Clase de caja de cambios: Automática, 4 vel.	Rodzaj skrzyni biegów: Przekładnia automatyczna 4-biegowa	Şanzıman türü: Şanzıman otomatikli 4 vites
<b>AT</b> <sup>⑤</sup>	Transmission Type: for 5-speed automatic transmission	トランスミッションの方式: オートマチックトランスミッション5速用	Getriebeart: für Getriebeautomatik 5 Gang	Type d'entraînement: pour boîte automatique 5 vitesses	Modalità di trasmissione: per cambio automatico a 5 marce	Clase de caja de cambios: para caja automática 5 vel.	Rodzaj skrzyni biegów: dla automatyki skrzyni 5-biegowej	Şanzıman türü: 5 vitesli otomatik şanzıman için
<del><b>AT</b></del>	Transmission Type: not for automatic transmission	トランスミッションの方式: オートマチックトランスミッションには適していません	Getriebeart: nicht für Automatikgetriebe	Type d'entraînement: pas pour boîte de vitesses automatique	Modalità di trasmissione: Non per trasmissione automatica	Clase de caja de cambios: no para transmisión automática	Rodzaj skrzyni biegów: nie dla automatycznej skrzyni biegów	Şanzıman türü: Otomatik şanzıman için değil

## Pictograms and Abbreviations

	EN	JA	DE	FR	IT	ES	PL	TR
	Transmission Type: not for 4-speed automatic transmission	トランスミッションの方式: オートマチックトランスミッション4速には適していません	Getriebeart: nicht für Getriebeautomatik 4 Gang	Type d'entraînement: pas pour boîte automatique 4 vitesses	Modalità di trasmissione: non per cambio automatico a 4 marce	Clase de caja de cambios: no para cambio automático a 4 marcha	Rodzaj skrzyni biegów: nie dla 4-biegowej autom. skrzyni biegów	Şanzıman türü: Şanzıman otomatığı 4 vites için değil
	Transmission Type: not for 5-speed automatic transmission	トランスミッションの方式: オートマチックトランスミッション5速には適していません	Getriebeart: nicht für Getriebeautomatik 5 Gang	Type d'entraînement: pas pour boîte automatique 5 vitesses	Modalità di trasmissione: non per cambio automatico a 5 marce	Clase de caja de cambios: no para cambio automático a 5 marcha	Rodzaj skrzyni biegów: nie dla 5-biegowej autom. skrzyni biegów	Şanzıman türü: Şanzıman otomatığı 5 vites için değil
	Number of Teeth, ABS ring	歯数 ABSリング	Zähnezahl ABS-Ring	Nombre de dents, anneau ABS	N° denti anello ABS	Número de dientes, anillo ABS	Ilość zębów, pierścień ABS	ABS halkası diş sayısı
	Brake Type: Disc Brake	ブレーキのタイプ: ディスクブレーキ	Bremsenart: Scheibenbremse	Type de freinage: Frein à disque	Tipo freno: Freno a disco	Tipo de freno: Discos	Typ układu hamulcowego: Hamulce tarczowe	Fren türü: Diskli fren
	Brake Type: Drum Brake	ブレーキのタイプ: ドラムブレーキ	Bremsenart: Trommelbremse	Type de freinage: Frein à tambour	Tipo freno: Freno a tamburo	Tipo de freno: Tambor	Typ układu hamulcowego: Hamulec bębnowy	Fren türü: Kampanalı fren
	Rim Size [in]	リムサイズ [インチ]	Felgenreöße [Zoll]	Dimension de la jante [pouces]	Misura cerchione [pollici]	Tamaño de llanta [in]	Rozmiar felgi [cal]	Jant büyüklüğü [inç]
	not for rim size [in]	ホイールサイズ [インチ] には適しません	nicht für Felgenreöße [Zoll]	pas pour dimension de jante [pouce]	non per misura cerchione [pollici]	no para dimensión de llantas [in]	nie dla felgi o rozmiarze [cal]	Jant boyutu için geçerli değildir [Inç]
	Spring Type: for coil-spring suspension vehicles	スプリングタイプ: コイルスプリング付き車両用	Federungsart: für Fahrzeuge mit Schraubenfederung	Type de suspension: pour véhicules avec suspension hélicoïdale	Tipo sospensione: per veicoli con sospensioni con molla elicoidale	Tipo de suspensión: para vehículos con suspensión de muelle helicoidal	Rodzaj resorowania: dla pojazdów z zawieszeniem ze sprężynami śrubowymi	Süspansiyon türü: Helezonik süspansiyonlu araçlar için
	Spring Type: for vehicles with pneumatic suspension	スプリングタイプ: エアスプリング付き車両用	Federungsart: für Fahrzeuge mit Luftfederung	Type de suspension: pour véhicules avec suspension pneumatique	Tipo sospensione: per veicoli con sospensioni pneumatiche	Tipo de suspensión: para vehículos con suspensión neumática	Rodzaj resorowania: dla pojazdów z zawieszeniem pneumatycznym	Süspansiyon türü: Havalı süspansiyona sahip araçlar için
	Braking / Drive Dynamics: for vehicles with ABS	ブレーキ/走行性能: ABS付き車両用	Brems-/Fahrndynamik: für Fahrzeuge mit ABS	Dynamique de mouvement et de freinage: pour véhicules avec système antiblocage	Dinamica frenata/guida: per veicoli con ABS	Dinámica de frenado / conducción: para vehículos con ABS	Dynamika hamowania/jazdy: dla pojazdów z ABS	Fren /Sürüş dinamiği: ABS'li araçlar için
	Braking / Drive Dynamics: for vehicles with EDS	ブレーキ/走行性能: EDS付き車両用	Brems-/Fahrndynamik: für Fahrzeuge mit EDS	Dynamique de mouvement et de freinage: pour véhicules avec EDS	Dinamica frenata/guida: per veicoli con EDS	Dinámica de frenado / conducción: para vehículos con EDS	Dynamika hamowania/jazdy: dla pojazdów z EDS	Fren /Sürüş dinamiği: EDS'li araçlar için
	Braking / Drive Dynamics: for vehicles with ESP	ブレーキ/走行性能: ESP付き車両用	Brems-/Fahrndynamik: für Fahrzeuge mit ESP	Dynamique de mouvement et de freinage: pour véhicules avec ESP	Dinamica frenata/guida: per veicoli con ESP	Dinámica de frenado / conducción: para vehículos con ESP	Dynamika hamowania/jazdy: dla pojazdów z ESP	Fren /Sürüş dinamiği: ESP'li araçlar için
	Braking / Drive Dynamics: for vehicles without ABS	ブレーキ/走行性能: ABS無しの車両用	Brems-/Fahrndynamik: für Fahrzeuge ohne ABS	Dynamique de mouvement et de freinage: pour véhicules sans système antiblocage	Dinamica frenata/guida: per veicoli senza ABS	Dinámica de frenado / conducción: para vehículos sin ABS	Dynamika hamowania/jazdy: dla pojazdów bez ABS	Fren /Sürüş dinamiği: ABS'siz araçlar için
	Braking / Drive Dynamics: for vehicles without ESP	ブレーキ/走行性能: ESP無しの車両用	Brems-/Fahrndynamik: für Fahrzeuge ohne ESP	Dynamique de mouvement et de freinage: pour véhicules sans ESP	Dinamica frenata/guida: per veicoli senza ESP	Dinámica de frenado / conducción: para vehículos sin ESP	Dynamika hamowania/jazdy: dla pojazdów bez ESP	Fren /Sürüş dinamiği: ESP'siz araçlar için
	Tyres: with single tyres	タイヤ: シングルタイヤ付き	Bereifung: mit Einfachbereifung	Pneus: avec pneus simples	Pneumatici: con pneumatici singoli	Neumáticos: con neumáticos sencillos	Opony: z pojedynczymi oponami	Lastik donanımı: Tekli tekerlek donanımı ile
	Tyres: with dual tyres	タイヤ: ダブルタイヤ付き	Bereifung: mit Doppelbereifung	Pneus: avec pneus doubles	Pneumatici: con pneumatici gemellati	Neumáticos: con neumáticos gemelos	Opony: z podwójnymi oponami	Lastik donanımı: Çift tekerlek donanımı ile
	For extended wheelbase	延長されたホイールベース用	Für verlängerten Radstand	Pour empattement rallongé	per passo allungato	para distancia entre ejes prolongada	dla rozszerzonego rozstawu osi	Uzatılmış tekerlek mesafesi için
	Short wheelbase	短いホイールベース	Kurzer Radstand	Empattement court	Passo ruote corto	distancia corta entre ejes	krótki rozstaw kół	Kısa tekerlek mesafesi için
	Centre wheelbase	中程度のホイールベース	Mittlerer Radstand	Empattement moyen	Passo ruote medio	distancia media entre ejes	Średni rozstaw kół	Orta tekerlek mesafesi için
	Not for extended wheelbase	延長されたホイールベースには適していません	Nicht für verlängerten Radstand	Pas pour empattement rallongé	Non per passo allungato	no para distancia entre ejes prolongada	nie dla rozszerzonego rozstawu osi	Uzatılmış tekerlek mesafesi için değil
	Suspension: for vehicles with sports suspension	サスペンション: スポーツサスペンション付き車両用	Fahrwerk: für Fahrzeuge mit Sportfahrwerk	Châssis: pour véhicules avec châssis sportif	Autotelaio: per veicoli con autotelaio sportivo	Suspensión: para vehículos con chasis deportivo	Podwozie: dla pojazdów z zawieszeniem sportowym	Yürüyüş takımı: Spor şasiye sahip araçlar için
	Suspension: for vehicles with heavy duty suspension	サスペンション: 強化型サスペンション付き車両用	Fahrwerk: für Fahrzeuge mit verstärktem Fahrwerk	Châssis: pour véhicules avec châssis renforcé	Autotelaio: per veicoli con autotelaio rinforzato	Suspensión: para vehículos con chasis reforzado	Podwozie: dla pojazdów z zawieszeniem wzmocnionym	Yürüyüş takımı: Güçlendirilmiş şasiye sahip araçlar için
	Suspension: for vehicles with IDS suspension	サスペンション: IDSサスペンション搭載車両用	Fahrwerk: für Fahrzeuge mit IDS-Fahrwerk	Châssis: pour véhicules avec châssis intégré IDS	Autotelaio: per veicoli con autotelaio IDS (dinamico interattivo)	Suspensión: para vehículos con suspensión IDS	Podwozie: dla pojazdów z zawieszeniem IDS	Yürüyüş takımı: IDS (Interaktif Sürüş Sistemi) şasiye sahip araçlar için







## Productdetails

---



## Passenger Car applications

---



## Cross references

---



## Overview of order numbers





---

---

## Wheel Suspension


### Bearing Kit

Wheel Bearing Kit.....	12
------------------------	----





Part Number	Pk.	Description																								
<p>KH00002</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661039106</td> </tr> <tr> <td>Fitting Position</td> <td>Rear Axle</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>29</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>19</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.3</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45.2</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.2</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A</td> </tr> <tr> <td>SEAT</td> <td>211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A</td> </tr> <tr> <td>VW</td> <td>211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A</td> </tr> </table>	EAN	192661039106	Fitting Position	Rear Axle	Inner diameter 1 [mm]	29	Inner diameter 2 [mm]	19	Outer diameter 1 [mm]	50.3	Outer diameter 2 [mm]	45.2	Width 1 [mm]	14.2	Width 2 [mm]	15.5	<b>OE No.</b>		AUDI	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A	SEAT	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A	VW	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A
EAN	192661039106																									
Fitting Position	Rear Axle																									
Inner diameter 1 [mm]	29																									
Inner diameter 2 [mm]	19																									
Outer diameter 1 [mm]	50.3																									
Outer diameter 2 [mm]	45.2																									
Width 1 [mm]	14.2																									
Width 2 [mm]	15.5																									
<b>OE No.</b>																										
AUDI	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A																									
SEAT	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A																									
VW	211 405 645, 211 405 645 D, 311 405 625 F, 443 505 509, 4A0 598 625, 4A0 598 625 A																									
<p>KH00003</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661037577</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>14.2</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.3</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50.3</td> </tr> <tr> <td>Width 1 [mm]</td> <td>13.9</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.2</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B</td> </tr> <tr> <td>SEAT</td> <td>191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B</td> </tr> <tr> <td>SKODA</td> <td>191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B</td> </tr> <tr> <td>VW</td> <td>191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B</td> </tr> </table>	EAN	192661037577	Inner diameter 1 [mm]	17.5	Inner diameter 2 [mm]	14.2	Outer diameter 1 [mm]	50.3	Outer diameter 2 [mm]	50.3	Width 1 [mm]	13.9	Width 2 [mm]	14.2	<b>OE No.</b>		AUDI	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B	SEAT	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B	SKODA	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B	VW	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B
EAN	192661037577																									
Inner diameter 1 [mm]	17.5																									
Inner diameter 2 [mm]	14.2																									
Outer diameter 1 [mm]	50.3																									
Outer diameter 2 [mm]	50.3																									
Width 1 [mm]	13.9																									
Width 2 [mm]	14.2																									
<b>OE No.</b>																										
AUDI	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B																									
SEAT	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B																									
SKODA	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B																									
VW	191 598 625, 311 405 625 F, 311 405 625 N, 311 405 645, 311 405 645 B																									
<p>KH00004</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661023785</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>50.3</td> </tr> <tr> <td>Width [mm]</td> <td>17.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1137830, 1375743, 5U7J-1A049-AA, 7220658, 89FB-1238-AD, 96FX-1A049-AB</td> </tr> </table>	EAN	192661023785	Inner diameter [mm]	29	Outer diameter [mm]	50.3	Width [mm]	17.5	<b>OE No.</b>		FORD	1137830, 1375743, 5U7J-1A049-AA, 7220658, 89FB-1238-AD, 96FX-1A049-AB												
EAN	192661023785																									
Inner diameter [mm]	29																									
Outer diameter [mm]	50.3																									
Width [mm]	17.5																									
<b>OE No.</b>																										
FORD	1137830, 1375743, 5U7J-1A049-AA, 7220658, 89FB-1238-AD, 96FX-1A049-AB																									
<p>KH00005</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661041604</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 03 065, 16 03 193, 90005147, 90486463</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 065, 16 03 193, 90005147, 90486463</td> </tr> </table>	EAN	192661041604	Inner diameter 1 [mm]	17	Inner diameter 2 [mm]	29	Outer diameter 1 [mm]	40	Outer diameter 2 [mm]	50	Width 1 [mm]	14	Width 2 [mm]	15	<b>OE No.</b>		OPEL	16 03 065, 16 03 193, 90005147, 90486463	VAUXHALL	16 03 065, 16 03 193, 90005147, 90486463				
EAN	192661041604																									
Inner diameter 1 [mm]	17																									
Inner diameter 2 [mm]	29																									
Outer diameter 1 [mm]	40																									
Outer diameter 2 [mm]	50																									
Width 1 [mm]	14																									
Width 2 [mm]	15																									
<b>OE No.</b>																										
OPEL	16 03 065, 16 03 193, 90005147, 90486463																									
VAUXHALL	16 03 065, 16 03 193, 90005147, 90486463																									



Part Number	Pk.	Description														
<p>KH00007</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048528</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18</td> </tr> </table> <p><b>OE No.</b></p> <p>MERCEDES-BENZ 203 330 00 51, A 002 980 30 02, A 002 980 31 02</p>	EAN	192661048528	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	50	Outer diameter 2 [mm]	62	Width 1 [mm]	18	Width 2 [mm]	18
EAN	192661048528															
Inner diameter 1 [mm]	20															
Inner diameter 2 [mm]	35															
Outer diameter 1 [mm]	50															
Outer diameter 2 [mm]	62															
Width 1 [mm]	18															
Width 2 [mm]	18															
<p>KH00008</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048535</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>28.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>19</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>57</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> </table> <p><b>OE No.</b></p> <p>FORD 109E1200A2, 1516151, 1583567, 70EB-1200-AA, 81AB1238AA</p>	EAN	192661048535	Inner diameter 1 [mm]	28.5	Inner diameter 2 [mm]	19	Outer diameter 1 [mm]	57	Outer diameter 2 [mm]	45	Width 1 [mm]	20	Width 2 [mm]	17
EAN	192661048535															
Inner diameter 1 [mm]	28.5															
Inner diameter 2 [mm]	19															
Outer diameter 1 [mm]	57															
Outer diameter 2 [mm]	45															
Width 1 [mm]	20															
Width 2 [mm]	17															
<p>KH00009</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048542</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18</td> </tr> </table> <p><b>OE No.</b></p> <p>FORD 1591389, 5007040, 81AB-1215-AB</p>	EAN	192661048542	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	18	Width 2 [mm]	18
EAN	192661048542															
Inner diameter 1 [mm]	35															
Inner diameter 2 [mm]	35															
Outer diameter 1 [mm]	60															
Outer diameter 2 [mm]	60															
Width 1 [mm]	18															
Width 2 [mm]	18															
<p>KH00010</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661045930</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>41</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>73</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>22</td> </tr> </table> <p><b>OE No.</b></p> <p>MERCEDES-BENZ A 006 981 58 05, A 007 981 13 05, A 901 330 10 25 VW 2D0 498 625</p>	EAN	192661045930	Inner diameter 1 [mm]	41	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	73	Outer diameter 2 [mm]	52	Width 1 [mm]	20	Width 2 [mm]	22
EAN	192661045930															
Inner diameter 1 [mm]	41															
Inner diameter 2 [mm]	25															
Outer diameter 1 [mm]	73															
Outer diameter 2 [mm]	52															
Width 1 [mm]	20															
Width 2 [mm]	22															
<p>KH00011</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048559</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>74</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>74</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> </table> <p><b>OE No.</b></p> <p>HYUNDAI 52701-44120 MITSUBISHI MB9322726</p>	EAN	192661048559	Inner diameter 1 [mm]	45	Inner diameter 2 [mm]	45	Outer diameter 1 [mm]	74	Outer diameter 2 [mm]	74	Width 1 [mm]	20	Width 2 [mm]	20
EAN	192661048559															
Inner diameter 1 [mm]	45															
Inner diameter 2 [mm]	45															
Outer diameter 1 [mm]	74															
Outer diameter 2 [mm]	74															
Width 1 [mm]	20															
Width 2 [mm]	20															

Part Number	Pk.	Description																				
KH00013 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048573</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>12</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1053115, 1583567, 5025899, 6197791, 97VX-1K018-AA</td> </tr> </table>	EAN	192661048573	Inner diameter 1 [mm]	19	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	45	Outer diameter 2 [mm]	62	Width 1 [mm]	12	Width 2 [mm]	18	<b>OE No.</b>		FORD	1053115, 1583567, 5025899, 6197791, 97VX-1K018-AA		
EAN	192661048573																					
Inner diameter 1 [mm]	19																					
Inner diameter 2 [mm]	35																					
Outer diameter 1 [mm]	45																					
Outer diameter 2 [mm]	62																					
Width 1 [mm]	12																					
Width 2 [mm]	18																					
<b>OE No.</b>																						
FORD	1053115, 1583567, 5025899, 6197791, 97VX-1K018-AA																					
KH00014 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048580</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>96285525</td> </tr> <tr> <td>DAEWOO</td> <td>96285525</td> </tr> </table>	EAN	192661048580	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	15	Width 2 [mm]	15	<b>OE No.</b>		CHEVROLET	96285525	DAEWOO	96285525
EAN	192661048580																					
Inner diameter 1 [mm]	35																					
Inner diameter 2 [mm]	35																					
Outer diameter 1 [mm]	60																					
Outer diameter 2 [mm]	60																					
Width 1 [mm]	15																					
Width 2 [mm]	15																					
<b>OE No.</b>																						
CHEVROLET	96285525																					
DAEWOO	96285525																					
KH00015 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048597</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>22</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>46</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>140 981 03 05, 212 330 00 25, 218 330 01 25, 230 330 03 25, A 002 980 65 02, A 140 981 03 05</td> </tr> </table>	EAN	192661048597	Inner diameter 1 [mm]	22	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	46	Outer diameter 2 [mm]	68	Width 1 [mm]	15.5	Width 2 [mm]	20	<b>OE No.</b>		MERCEDES-BENZ	140 981 03 05, 212 330 00 25, 218 330 01 25, 230 330 03 25, A 002 980 65 02, A 140 981 03 05		
EAN	192661048597																					
Inner diameter 1 [mm]	22																					
Inner diameter 2 [mm]	40																					
Outer diameter 1 [mm]	46																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	15.5																					
Width 2 [mm]	20																					
<b>OE No.</b>																						
MERCEDES-BENZ	140 981 03 05, 212 330 00 25, 218 330 01 25, 230 330 03 25, A 002 980 65 02, A 140 981 03 05																					
KH00017 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048603</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.6</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-11000, 51720-11100, 51730-11000, 51730-11100</td> </tr> <tr> <td>MITSUBISHI</td> <td>MA125842, MA125843</td> </tr> </table>	EAN	192661048603	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	50.25	Outer diameter 2 [mm]	40	Width 1 [mm]	14.75	Width 2 [mm]	14.6	<b>OE No.</b>		HYUNDAI	51720-11000, 51720-11100, 51730-11000, 51730-11100	MITSUBISHI	MA125842, MA125843
EAN	192661048603																					
Inner diameter 1 [mm]	27																					
Inner diameter 2 [mm]	17.5																					
Outer diameter 1 [mm]	50.25																					
Outer diameter 2 [mm]	40																					
Width 1 [mm]	14.75																					
Width 2 [mm]	14.6																					
<b>OE No.</b>																						
HYUNDAI	51720-11000, 51720-11100, 51730-11000, 51730-11100																					
MITSUBISHI	MA125842, MA125843																					
KH00018 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048610</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>41</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>09265-41001</td> </tr> </table>	EAN	192661048610	Inner diameter 1 [mm]	41	Inner diameter 2 [mm]	41	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	18	Width 2 [mm]	18	<b>OE No.</b>		SUZUKI	09265-41001		
EAN	192661048610																					
Inner diameter 1 [mm]	41																					
Inner diameter 2 [mm]	41																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	18																					
Width 2 [mm]	18																					
<b>OE No.</b>																						
SUZUKI	09265-41001																					



Part Number	Pk.	Description																						
<p>KH00019</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048627</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>75</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>27.85</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21.65</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 26, 3730 22, 3735 18</td> </tr> <tr> <td>FIAT</td> <td>5996248, 5996253, 71714452</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 26, 3730 22, 3735 18</td> </tr> </table>	EAN	192661048627	Inner diameter 1 [mm]	40	Inner diameter 2 [mm]	30	Outer diameter 1 [mm]	75	Outer diameter 2 [mm]	62	Width 1 [mm]	27.85	Width 2 [mm]	21.65	<b>OE No.</b>		CITROËN	3350 26, 3730 22, 3735 18	FIAT	5996248, 5996253, 71714452	PEUGEOT	3350 26, 3730 22, 3735 18
EAN	192661048627																							
Inner diameter 1 [mm]	40																							
Inner diameter 2 [mm]	30																							
Outer diameter 1 [mm]	75																							
Outer diameter 2 [mm]	62																							
Width 1 [mm]	27.85																							
Width 2 [mm]	21.65																							
<b>OE No.</b>																								
CITROËN	3350 26, 3730 22, 3735 18																							
FIAT	5996248, 5996253, 71714452																							
PEUGEOT	3350 26, 3730 22, 3735 18																							
<p>KH00020</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048634</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>22</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 002 980 65 02, A 140 981 03 05</td> </tr> </table>	EAN	192661048634	Inner diameter 1 [mm]	22	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	45	Outer diameter 2 [mm]	68	Width 1 [mm]	17	Width 2 [mm]	20	<b>OE No.</b>		MERCEDES-BENZ	A 002 980 65 02, A 140 981 03 05				
EAN	192661048634																							
Inner diameter 1 [mm]	22																							
Inner diameter 2 [mm]	40																							
Outer diameter 1 [mm]	45																							
Outer diameter 2 [mm]	68																							
Width 1 [mm]	17																							
Width 2 [mm]	20																							
<b>OE No.</b>																								
MERCEDES-BENZ	A 002 980 65 02, A 140 981 03 05																							
<p>KH00021</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048641</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1492160, 1565443</td> </tr> </table>	EAN	192661048641	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	50	Outer diameter 2 [mm]	40	Width 1 [mm]	14.25	Width 2 [mm]	14	<b>OE No.</b>		FORD	1492160, 1565443				
EAN	192661048641																							
Inner diameter 1 [mm]	27																							
Inner diameter 2 [mm]	17.5																							
Outer diameter 1 [mm]	50																							
Outer diameter 2 [mm]	40																							
Width 1 [mm]	14.25																							
Width 2 [mm]	14																							
<b>OE No.</b>																								
FORD	1492160, 1565443																							
<p>KH00022</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048658</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1583567, 5007029, 6077541, 81AB-1238-AA, 81AB-1238-BA, A800X-1K028-CA</td> </tr> </table>	EAN	192661048658	Inner diameter 1 [mm]	19	Inner diameter 2 [mm]	32	Outer diameter 1 [mm]	45	Outer diameter 2 [mm]	59	Width 1 [mm]	16.75	Width 2 [mm]	16.7	<b>OE No.</b>		FORD	1583567, 5007029, 6077541, 81AB-1238-AA, 81AB-1238-BA, A800X-1K028-CA				
EAN	192661048658																							
Inner diameter 1 [mm]	19																							
Inner diameter 2 [mm]	32																							
Outer diameter 1 [mm]	45																							
Outer diameter 2 [mm]	59																							
Width 1 [mm]	16.75																							
Width 2 [mm]	16.7																							
<b>OE No.</b>																								
FORD	1583567, 5007029, 6077541, 81AB-1238-AA, 81AB-1238-BA, A800X-1K028-CA																							
<p>KH00023</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048665</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.6</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1492160, 1565444, 5007028, 72GB-1200-AA, 72GB-1215-AA, A800X-1K028-BA</td> </tr> </table>	EAN	192661048665	Inner diameter 1 [mm]	17.5	Inner diameter 2 [mm]	29	Outer diameter 1 [mm]	40	Outer diameter 2 [mm]	50	Width 1 [mm]	14.6	Width 2 [mm]	14.7	<b>OE No.</b>		FORD	1492160, 1565444, 5007028, 72GB-1200-AA, 72GB-1215-AA, A800X-1K028-BA				
EAN	192661048665																							
Inner diameter 1 [mm]	17.5																							
Inner diameter 2 [mm]	29																							
Outer diameter 1 [mm]	40																							
Outer diameter 2 [mm]	50																							
Width 1 [mm]	14.6																							
Width 2 [mm]	14.7																							
<b>OE No.</b>																								
FORD	1492160, 1565444, 5007028, 72GB-1200-AA, 72GB-1215-AA, A800X-1K028-BA																							

Part Number	Pk.	Description																						
KH00024	1	<table border="1"> <tr> <td>EAN</td> <td>192661048672</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>43</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1954435, 1954437</td> </tr> <tr> <td>NISSAN</td> <td>40210-2S600, 40210-50W00, 40215-0F000, 40215-50W00</td> </tr> </table>	EAN	192661048672	Inner diameter 1 [mm]	43	Inner diameter 2 [mm]	45	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	17	Width 2 [mm]	20	<b>OE No.</b>		FORD	1954435, 1954437	NISSAN	40210-2S600, 40210-50W00, 40215-0F000, 40215-50W00		
EAN	192661048672																							
Inner diameter 1 [mm]	43																							
Inner diameter 2 [mm]	45																							
Outer diameter 1 [mm]	68																							
Outer diameter 2 [mm]	68																							
Width 1 [mm]	17																							
Width 2 [mm]	20																							
<b>OE No.</b>																								
FORD	1954435, 1954437																							
NISSAN	40210-2S600, 40210-50W00, 40215-0F000, 40215-50W00																							
KH00025	1	<table border="1"> <tr> <td>EAN</td> <td>192661048689</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>51</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>57</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>85</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>97</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17.4</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>0634048, 0634049, 11-634048, 11-634049, 5015650, 86VX-1A049-CA</td> </tr> </table>	EAN	192661048689	Inner diameter 1 [mm]	51	Inner diameter 2 [mm]	57	Outer diameter 1 [mm]	85	Outer diameter 2 [mm]	97	Width 1 [mm]	17.4	Width 2 [mm]	21	<b>OE No.</b>		FORD	0634048, 0634049, 11-634048, 11-634049, 5015650, 86VX-1A049-CA				
EAN	192661048689																							
Inner diameter 1 [mm]	51																							
Inner diameter 2 [mm]	57																							
Outer diameter 1 [mm]	85																							
Outer diameter 2 [mm]	97																							
Width 1 [mm]	17.4																							
Width 2 [mm]	21																							
<b>OE No.</b>																								
FORD	0634048, 0634049, 11-634048, 11-634049, 5015650, 86VX-1A049-CA																							
KH00026	1	<table border="1"> <tr> <td>EAN</td> <td>192661048696</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>75</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ISUZU</td> <td>8-94227-041-01, 8-94258-819-0</td> </tr> <tr> <td>OPEL</td> <td>3 28 109, 3 30 019, 3 30 023, 94227041, 94258819</td> </tr> <tr> <td>VAUXHALL</td> <td>3 28 109, 3 30 019, 3 30 023, 94227041, 94258819</td> </tr> </table>	EAN	192661048696	Inner diameter 1 [mm]	45	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	75	Outer diameter 2 [mm]	68	Width 1 [mm]	21	Width 2 [mm]	19	<b>OE No.</b>		ISUZU	8-94227-041-01, 8-94258-819-0	OPEL	3 28 109, 3 30 019, 3 30 023, 94227041, 94258819	VAUXHALL	3 28 109, 3 30 019, 3 30 023, 94227041, 94258819
EAN	192661048696																							
Inner diameter 1 [mm]	45																							
Inner diameter 2 [mm]	40																							
Outer diameter 1 [mm]	75																							
Outer diameter 2 [mm]	68																							
Width 1 [mm]	21																							
Width 2 [mm]	19																							
<b>OE No.</b>																								
ISUZU	8-94227-041-01, 8-94258-819-0																							
OPEL	3 28 109, 3 30 019, 3 30 023, 94227041, 94258819																							
VAUXHALL	3 28 109, 3 30 019, 3 30 023, 94227041, 94258819																							
KH00027	1	<table border="1"> <tr> <td>EAN</td> <td>192661048702</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90366-17010, 90366-27001, 90368-17017</td> </tr> </table>	EAN	192661048702	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	47	Outer diameter 2 [mm]	40	Width 1 [mm]	15	Width 2 [mm]	15	<b>OE No.</b>		TOYOTA	90366-17010, 90366-27001, 90368-17017				
EAN	192661048702																							
Inner diameter 1 [mm]	25																							
Inner diameter 2 [mm]	17.5																							
Outer diameter 1 [mm]	47																							
Outer diameter 2 [mm]	40																							
Width 1 [mm]	15																							
Width 2 [mm]	15																							
<b>OE No.</b>																								
TOYOTA	90366-17010, 90366-27001, 90368-17017																							
KH00028	1	<table border="1"> <tr> <td>EAN</td> <td>192661051900</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>96316634, 96316635</td> </tr> <tr> <td>DAEWOO</td> <td>96316634, 96316635</td> </tr> </table>	EAN	192661051900	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	47	Outer diameter 2 [mm]	52	Width 1 [mm]	15.25	Width 2 [mm]	16.25	<b>OE No.</b>		CHEVROLET	96316634, 96316635	DAEWOO	96316634, 96316635		
EAN	192661051900																							
Inner diameter 1 [mm]	20																							
Inner diameter 2 [mm]	25																							
Outer diameter 1 [mm]	47																							
Outer diameter 2 [mm]	52																							
Width 1 [mm]	15.25																							
Width 2 [mm]	16.25																							
<b>OE No.</b>																								
CHEVROLET	96316634, 96316635																							
DAEWOO	96316634, 96316635																							










Part Number	Pk.	Description																				
<p>KH00029</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051917</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>23</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>3C11-1A049-AA, 4479002</td> </tr> </table>	EAN	192661051917	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	23	<b>OE No.</b>		FORD	3C11-1A049-AA, 4479002								
EAN	192661051917																					
Inner diameter [mm]	55																					
Outer diameter [mm]	90																					
Width [mm]	23																					
<b>OE No.</b>																						
FORD	3C11-1A049-AA, 4479002																					
<p>KH00030</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048719</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>23</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90363-40020</td> </tr> </table>	EAN	192661048719	Inner diameter [mm]	40	Outer diameter [mm]	90	Width [mm]	23	<b>OE No.</b>		TOYOTA	90363-40020								
EAN	192661048719																					
Inner diameter [mm]	40																					
Outer diameter [mm]	90																					
Width [mm]	23																					
<b>OE No.</b>																						
TOYOTA	90363-40020																					
<p>KH00031</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051924</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>18.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.3</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.7</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 000 981 58 05, A 000 981 59 05, A 107 330 00 51</td> </tr> <tr> <td>PORSCHE</td> <td>999 059 065 00, 999 059 098 00</td> </tr> </table>	EAN	192661051924	Inner diameter 1 [mm]	18.9	Inner diameter 2 [mm]	31.8	Outer diameter 1 [mm]	45.3	Outer diameter 2 [mm]	59	Width 1 [mm]	16.7	Width 2 [mm]	16.7	<b>OE No.</b>		MERCEDES-BENZ	A 000 981 58 05, A 000 981 59 05, A 107 330 00 51	PORSCHE	999 059 065 00, 999 059 098 00
EAN	192661051924																					
Inner diameter 1 [mm]	18.9																					
Inner diameter 2 [mm]	31.8																					
Outer diameter 1 [mm]	45.3																					
Outer diameter 2 [mm]	59																					
Width 1 [mm]	16.7																					
Width 2 [mm]	16.7																					
<b>OE No.</b>																						
MERCEDES-BENZ	A 000 981 58 05, A 000 981 59 05, A 107 330 00 51																					
PORSCHE	999 059 065 00, 999 059 098 00																					
<p>KH00032</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051931</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>20</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>42</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.3</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15.2</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>77 03 090 266, 77 03 090 267</td> </tr> <tr> <td>RENAULT</td> <td>77 03 090 266, 77 03 090 267</td> </tr> </table>	EAN	192661051931	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	20	Outer diameter 1 [mm]	47	Outer diameter 2 [mm]	42	Width 1 [mm]	15.3	Width 2 [mm]	15.2	<b>OE No.</b>		DACIA	77 03 090 266, 77 03 090 267	RENAULT	77 03 090 266, 77 03 090 267
EAN	192661051931																					
Inner diameter 1 [mm]	25																					
Inner diameter 2 [mm]	20																					
Outer diameter 1 [mm]	47																					
Outer diameter 2 [mm]	42																					
Width 1 [mm]	15.3																					
Width 2 [mm]	15.2																					
<b>OE No.</b>																						
DACIA	77 03 090 266, 77 03 090 267																					
RENAULT	77 03 090 266, 77 03 090 267																					
<p>KH00033</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051948</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>65.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>3666951, 4488728, XM34-1215-AA, XM34-1216-CA</td> </tr> <tr> <td>MAZDA</td> <td>S08-33-047, S08-333-075, UH71-33-061B</td> </tr> </table>	EAN	192661051948	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	65.25	Outer diameter 2 [mm]	52	Width 1 [mm]	18.75	Width 2 [mm]	16	<b>OE No.</b>		FORD	3666951, 4488728, XM34-1215-AA, XM34-1216-CA	MAZDA	S08-33-047, S08-333-075, UH71-33-061B
EAN	192661051948																					
Inner diameter 1 [mm]	35																					
Inner diameter 2 [mm]	25																					
Outer diameter 1 [mm]	65.25																					
Outer diameter 2 [mm]	52																					
Width 1 [mm]	18.75																					
Width 2 [mm]	16																					
<b>OE No.</b>																						
FORD	3666951, 4488728, XM34-1215-AA, XM34-1216-CA																					
MAZDA	S08-33-047, S08-333-075, UH71-33-061B																					






Part Number	Pk.	Description																						
<p>KH00034</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051955</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>29</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>1 137 830, 96FX-1A049-AB</td> </tr> </table>	EAN	192661051955	Inner diameter 1 [mm]	29	Inner diameter 2 [mm]	29	Outer diameter 1 [mm]	50	Outer diameter 2 [mm]	50	Width 1 [mm]	17.5	Width 2 [mm]	17.5	<b>OE No.</b>		FORD	1 137 830, 96FX-1A049-AB				
EAN	192661051955																							
Inner diameter 1 [mm]	29																							
Inner diameter 2 [mm]	29																							
Outer diameter 1 [mm]	50																							
Outer diameter 2 [mm]	50																							
Width 1 [mm]	17.5																							
Width 2 [mm]	17.5																							
<b>OE No.</b>																								
FORD	1 137 830, 96FX-1A049-AB																							
<p>KH00035</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051962</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>80</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CITROËN</td> <td>3326 27, 3350 29</td> </tr> <tr> <td>FIAT</td> <td>4330647, 71714450</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 27, 3350 29</td> </tr> </table>	EAN	192661051962	Inner diameter 1 [mm]	50	Inner diameter 2 [mm]	50	Outer diameter 1 [mm]	80	Outer diameter 2 [mm]	80	Width 1 [mm]	21	Width 2 [mm]	21	<b>OE No.</b>		CITROËN	3326 27, 3350 29	FIAT	4330647, 71714450	PEUGEOT	3326 27, 3350 29
EAN	192661051962																							
Inner diameter 1 [mm]	50																							
Inner diameter 2 [mm]	50																							
Outer diameter 1 [mm]	80																							
Outer diameter 2 [mm]	80																							
Width 1 [mm]	21																							
Width 2 [mm]	21																							
<b>OE No.</b>																								
CITROËN	3326 27, 3350 29																							
FIAT	4330647, 71714450																							
PEUGEOT	3326 27, 3350 29																							
<p>KH00036</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051979</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>41.3</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>73.4</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>85</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>26</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>NISSAN</td> <td>40215-C6000, 43210-C9300</td> </tr> </table>	EAN	192661051979	Inner diameter 1 [mm]	41.3	Inner diameter 2 [mm]	50	Outer diameter 1 [mm]	73.4	Outer diameter 2 [mm]	85	Width 1 [mm]	19.5	Width 2 [mm]	26	<b>OE No.</b>		NISSAN	40215-C6000, 43210-C9300				
EAN	192661051979																							
Inner diameter 1 [mm]	41.3																							
Inner diameter 2 [mm]	50																							
Outer diameter 1 [mm]	73.4																							
Outer diameter 2 [mm]	85																							
Width 1 [mm]	19.5																							
Width 2 [mm]	26																							
<b>OE No.</b>																								
NISSAN	40215-C6000, 43210-C9300																							
<p>KH00037</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051986</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45.2</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77.8</td> </tr> <tr> <td>Width [mm]</td> <td>19.8</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>LAND ROVER</td> <td>STC3482</td> </tr> </table>	EAN	192661051986	Inner diameter [mm]	45.2	Outer diameter [mm]	77.8	Width [mm]	19.8	<b>OE No.</b>		LAND ROVER	STC3482										
EAN	192661051986																							
Inner diameter [mm]	45.2																							
Outer diameter [mm]	77.8																							
Width [mm]	19.8																							
<b>OE No.</b>																								
LAND ROVER	STC3482																							
<p>KH00038</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077344</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>29</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>19.1</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.3</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45.2</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.7</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.6</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>AUDI</td> <td>211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625</td> </tr> <tr> <td>SEAT</td> <td>211 405 645 D, 311 405 625 F, 443 505 509</td> </tr> <tr> <td>VW</td> <td>211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625</td> </tr> </table>	EAN	192661077344	Inner diameter 1 [mm]	29	Inner diameter 2 [mm]	19.1	Outer diameter 1 [mm]	50.3	Outer diameter 2 [mm]	45.2	Width 1 [mm]	14.7	Width 2 [mm]	16.6	<b>OE No.</b>		AUDI	211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625	SEAT	211 405 645 D, 311 405 625 F, 443 505 509	VW	211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625
EAN	192661077344																							
Inner diameter 1 [mm]	29																							
Inner diameter 2 [mm]	19.1																							
Outer diameter 1 [mm]	50.3																							
Outer diameter 2 [mm]	45.2																							
Width 1 [mm]	14.7																							
Width 2 [mm]	16.6																							
<b>OE No.</b>																								
AUDI	211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625																							
SEAT	211 405 645 D, 311 405 625 F, 443 505 509																							
VW	211 405 645 D, 311 405 625 F, 443 505 509, 8D0 598 625																							



Part Number	Pk.	Description																						
<p>KH00039</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661051993</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 21 1 107 456, 31 21 6 634 103, 31 21 6 634 106</td> </tr> </table>	EAN	192661051993	Inner diameter 1 [mm]	19	Inner diameter 2 [mm]	32	Outer diameter 1 [mm]	45.25	Outer diameter 2 [mm]	59	Width 1 [mm]	16.75	Width 2 [mm]	16.7	<b>OE No.</b>		BMW	31 21 1 107 456, 31 21 6 634 103, 31 21 6 634 106				
EAN	192661051993																							
Inner diameter 1 [mm]	19																							
Inner diameter 2 [mm]	32																							
Outer diameter 1 [mm]	45.25																							
Outer diameter 2 [mm]	59																							
Width 1 [mm]	16.75																							
Width 2 [mm]	16.7																							
<b>OE No.</b>																								
BMW	31 21 1 107 456, 31 21 6 634 103, 31 21 6 634 106																							
<p>KH00040</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052006</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 000 981 58 05, A 000 981 59 05, A 115 330 00 51</td> </tr> </table>	EAN	192661052006	Inner diameter 1 [mm]	19	Inner diameter 2 [mm]	31.8	Outer diameter 1 [mm]	45.25	Outer diameter 2 [mm]	59	Width 1 [mm]	16.75	Width 2 [mm]	16.7	<b>OE No.</b>		MERCEDES-BENZ	A 000 981 58 05, A 000 981 59 05, A 115 330 00 51				
EAN	192661052006																							
Inner diameter 1 [mm]	19																							
Inner diameter 2 [mm]	31.8																							
Outer diameter 1 [mm]	45.25																							
Outer diameter 2 [mm]	59																							
Width 1 [mm]	16.75																							
Width 2 [mm]	16.7																							
<b>OE No.</b>																								
MERCEDES-BENZ	A 000 981 58 05, A 000 981 59 05, A 115 330 00 51																							
<p>KH00041</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052013</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>34.75</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>21.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>59.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45.25</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 21 1 106 032, 31 21 1 106 033, 31 21 1 119 571</td> </tr> </table>	EAN	192661052013	Inner diameter 1 [mm]	34.75	Inner diameter 2 [mm]	21.8	Outer diameter 1 [mm]	59.25	Outer diameter 2 [mm]	45.25	Width 1 [mm]	16.75	Width 2 [mm]	16.5	<b>OE No.</b>		BMW	31 21 1 106 032, 31 21 1 106 033, 31 21 1 119 571				
EAN	192661052013																							
Inner diameter 1 [mm]	34.75																							
Inner diameter 2 [mm]	21.8																							
Outer diameter 1 [mm]	59.25																							
Outer diameter 2 [mm]	45.25																							
Width 1 [mm]	16.75																							
Width 2 [mm]	16.5																							
<b>OE No.</b>																								
BMW	31 21 1 106 032, 31 21 1 106 033, 31 21 1 119 571																							
<p>KH00042</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052020</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>21</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>65</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>04421-35010, 04421-35020, 90368-21065, 90368-34001</td> </tr> <tr> <td>VW</td> <td>008 311 123 A</td> </tr> </table>	EAN	192661052020	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	21	Outer diameter 1 [mm]	65	Outer diameter 2 [mm]	50	Width 1 [mm]	18.75	Width 2 [mm]	18.5	<b>OE No.</b>		TOYOTA	04421-35010, 04421-35020, 90368-21065, 90368-34001	VW	008 311 123 A		
EAN	192661052020																							
Inner diameter 1 [mm]	35																							
Inner diameter 2 [mm]	21																							
Outer diameter 1 [mm]	65																							
Outer diameter 2 [mm]	50																							
Width 1 [mm]	18.75																							
Width 2 [mm]	18.5																							
<b>OE No.</b>																								
TOYOTA	04421-35010, 04421-35020, 90368-21065, 90368-34001																							
VW	008 311 123 A																							
<p>KH00043</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052037</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>55</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 25, 3735 15</td> </tr> <tr> <td>FIAT</td> <td>4470127, 71714454, 7667784</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 25, 3735 15</td> </tr> </table>	EAN	192661052037	Inner diameter 1 [mm]	40	Inner diameter 2 [mm]	30	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	55	Width 1 [mm]	20	Width 2 [mm]	17	<b>OE No.</b>		CITROËN	3350 25, 3735 15	FIAT	4470127, 71714454, 7667784	PEUGEOT	3350 25, 3735 15
EAN	192661052037																							
Inner diameter 1 [mm]	40																							
Inner diameter 2 [mm]	30																							
Outer diameter 1 [mm]	68																							
Outer diameter 2 [mm]	55																							
Width 1 [mm]	20																							
Width 2 [mm]	17																							
<b>OE No.</b>																								
CITROËN	3350 25, 3735 15																							
FIAT	4470127, 71714454, 7667784																							
PEUGEOT	3350 25, 3735 15																							

Part Number	Pk.	Description																						
KH00044	1	<table border="1"> <tr> <td>EAN</td> <td>192661052044</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>73.5</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>63</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>KIA</td> <td>0K01A-33-047, 0K01A-33-075</td> </tr> </table>	EAN	192661052044	Inner diameter 1 [mm]	45	Inner diameter 2 [mm]	38	Outer diameter 1 [mm]	73.5	Outer diameter 2 [mm]	63	Width 1 [mm]	19.5	Width 2 [mm]	17	<b>OE No.</b>		KIA	0K01A-33-047, 0K01A-33-075				
EAN	192661052044																							
Inner diameter 1 [mm]	45																							
Inner diameter 2 [mm]	38																							
Outer diameter 1 [mm]	73.5																							
Outer diameter 2 [mm]	63																							
Width 1 [mm]	19.5																							
Width 2 [mm]	17																							
<b>OE No.</b>																								
KIA	0K01A-33-047, 0K01A-33-075																							
KH00045	1	<table border="1"> <tr> <td>EAN</td> <td>192661066034</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.6</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>1492160, 1565443, 3024E-1200A, 72GB-1215-AA</td> </tr> </table>	EAN	192661066034	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	50.25	Outer diameter 2 [mm]	40	Width 1 [mm]	14.75	Width 2 [mm]	14.6	<b>OE No.</b>		FORD	1492160, 1565443, 3024E-1200A, 72GB-1215-AA				
EAN	192661066034																							
Inner diameter 1 [mm]	27																							
Inner diameter 2 [mm]	17.5																							
Outer diameter 1 [mm]	50.25																							
Outer diameter 2 [mm]	40																							
Width 1 [mm]	14.75																							
Width 2 [mm]	14.6																							
<b>OE No.</b>																								
FORD	1492160, 1565443, 3024E-1200A, 72GB-1215-AA																							
KH00046	1	<table border="1"> <tr> <td>EAN</td> <td>192661066041</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>22</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.8</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50.8</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20.2</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20.2</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>AUSTIN</td> <td>GHB377</td> </tr> <tr> <td>MG</td> <td>GHB377</td> </tr> <tr> <td>ROVER</td> <td>GHB377</td> </tr> </table>	EAN	192661066041	Inner diameter 1 [mm]	22	Inner diameter 2 [mm]	22	Outer diameter 1 [mm]	50.8	Outer diameter 2 [mm]	50.8	Width 1 [mm]	20.2	Width 2 [mm]	20.2	<b>OE No.</b>		AUSTIN	GHB377	MG	GHB377	ROVER	GHB377
EAN	192661066041																							
Inner diameter 1 [mm]	22																							
Inner diameter 2 [mm]	22																							
Outer diameter 1 [mm]	50.8																							
Outer diameter 2 [mm]	50.8																							
Width 1 [mm]	20.2																							
Width 2 [mm]	20.2																							
<b>OE No.</b>																								
AUSTIN	GHB377																							
MG	GHB377																							
ROVER	GHB377																							
KH00047	1	<table border="1"> <tr> <td>EAN</td> <td>192661066058</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>16.9</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09262-350031, 09262-35007</td> </tr> </table>	EAN	192661066058	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	16.9	<b>OE No.</b>		SUZUKI	09262-350031, 09262-35007										
EAN	192661066058																							
Inner diameter [mm]	35																							
Outer diameter [mm]	72																							
Width [mm]	16.9																							
<b>OE No.</b>																								
SUZUKI	09262-350031, 09262-35007																							
KH00048	1	<table border="1"> <tr> <td>EAN</td> <td>192661066065</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>20</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>47</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09262-25061, 09262-30069</td> </tr> </table>	EAN	192661066065	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	20	Outer diameter 1 [mm]	52	Outer diameter 2 [mm]	47	Width 1 [mm]	15	Width 2 [mm]	14	<b>OE No.</b>		SUZUKI	09262-25061, 09262-30069				
EAN	192661066065																							
Inner diameter 1 [mm]	25																							
Inner diameter 2 [mm]	20																							
Outer diameter 1 [mm]	52																							
Outer diameter 2 [mm]	47																							
Width 1 [mm]	15																							
Width 2 [mm]	14																							
<b>OE No.</b>																								
SUZUKI	09262-25061, 09262-30069																							








Part Number	Pk.	Description																				
<p>KH00049</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066072</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>23</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>43591-65D00</td> </tr> </table>	EAN	192661066072	Inner diameter [mm]	40	Outer diameter [mm]	80	Width 1 [mm]	18	Width 2 [mm]	23	<b>OE No.</b>		SUZUKI	43591-65D00						
EAN	192661066072																					
Inner diameter [mm]	40																					
Outer diameter [mm]	80																					
Width 1 [mm]	18																					
Width 2 [mm]	23																					
<b>OE No.</b>																						
SUZUKI	43591-65D00																					
<p>KH00050</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066089</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>72</td> </tr> <tr> <td>Width 1 [mm]</td> <td>22.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>24.25</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>NISSAN</td> <td>40210-9X50A, 40210-F3900, 40215-9X50A, 40215-F3901</td> </tr> </table>	EAN	192661066089	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	52	Outer diameter 2 [mm]	72	Width 1 [mm]	22.25	Width 2 [mm]	24.25	<b>OE No.</b>		NISSAN	40210-9X50A, 40210-F3900, 40215-9X50A, 40215-F3901		
EAN	192661066089																					
Inner diameter 1 [mm]	20																					
Inner diameter 2 [mm]	35																					
Outer diameter 1 [mm]	52																					
Outer diameter 2 [mm]	72																					
Width 1 [mm]	22.25																					
Width 2 [mm]	24.25																					
<b>OE No.</b>																						
NISSAN	40210-9X50A, 40210-F3900, 40215-9X50A, 40215-F3901																					
<p>KH00051</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066096</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>31.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>62</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.75</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>AUSTIN</td> <td>GHK1140</td> </tr> <tr> <td>ROVER</td> <td>GHK1140</td> </tr> </table>	EAN	192661066096	Inner diameter 1 [mm]	31.5	Inner diameter 2 [mm]	31.5	Outer diameter 1 [mm]	62	Outer diameter 2 [mm]	62	Width 1 [mm]	16.75	Width 2 [mm]	16.75	<b>OE No.</b>		AUSTIN	GHK1140	ROVER	GHK1140
EAN	192661066096																					
Inner diameter 1 [mm]	31.5																					
Inner diameter 2 [mm]	31.5																					
Outer diameter 1 [mm]	62																					
Outer diameter 2 [mm]	62																					
Width 1 [mm]	16.75																					
Width 2 [mm]	16.75																					
<b>OE No.</b>																						
AUSTIN	GHK1140																					
ROVER	GHK1140																					
<p>KH00052</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066102</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25.4</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>57.15</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.8</td> </tr> <tr> <td>Width 2 [mm]</td> <td>12.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TRIUMPH</td> <td>117853, GHB117</td> </tr> </table>	EAN	192661066102	Inner diameter 1 [mm]	25.4	Inner diameter 2 [mm]	25.8	Outer diameter 1 [mm]	57.15	Outer diameter 2 [mm]	31.8	Width 1 [mm]	15.8	Width 2 [mm]	12.5	<b>OE No.</b>		TRIUMPH	117853, GHB117		
EAN	192661066102																					
Inner diameter 1 [mm]	25.4																					
Inner diameter 2 [mm]	25.8																					
Outer diameter 1 [mm]	57.15																					
Outer diameter 2 [mm]	31.8																					
Width 1 [mm]	15.8																					
Width 2 [mm]	12.5																					
<b>OE No.</b>																						
TRIUMPH	117853, GHB117																					
<p>KH00053</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066119</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>34.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>15.75</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>41.25</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.6</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CATERHAM</td> <td>GHB110, GHB111</td> </tr> <tr> <td>TRIUMPH</td> <td>GHB110, GHB111</td> </tr> </table>	EAN	192661066119	Inner diameter 1 [mm]	34.9	Inner diameter 2 [mm]	15.75	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	41.25	Width 1 [mm]	16.75	Width 2 [mm]	14.6	<b>OE No.</b>		CATERHAM	GHB110, GHB111	TRIUMPH	GHB110, GHB111
EAN	192661066119																					
Inner diameter 1 [mm]	34.9																					
Inner diameter 2 [mm]	15.75																					
Outer diameter 1 [mm]	60																					
Outer diameter 2 [mm]	41.25																					
Width 1 [mm]	16.75																					
Width 2 [mm]	14.6																					
<b>OE No.</b>																						
CATERHAM	GHB110, GHB111																					
TRIUMPH	GHB110, GHB111																					

Part Number	Pk.	Description																				
<p>KH00054</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066126</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>26</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>04421-30011, 04421-30012</td> </tr> </table>	EAN	192661066126	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	26	<b>OE No.</b>		TOYOTA	04421-30011, 04421-30012								
EAN	192661066126																					
Inner diameter [mm]	35																					
Outer diameter [mm]	72																					
Width [mm]	26																					
<b>OE No.</b>																						
TOYOTA	04421-30011, 04421-30012																					
<p>KH00055</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066133</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>21</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>65</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 000 981 63 05, A 001 980 29 02, A 116 330 00 51</td> </tr> </table>	EAN	192661066133	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	21	Outer diameter 1 [mm]	65	Outer diameter 2 [mm]	50	Width 1 [mm]	18.75	Width 2 [mm]	18.5	<b>OE No.</b>		MERCEDES-BENZ	A 000 981 63 05, A 001 980 29 02, A 116 330 00 51		
EAN	192661066133																					
Inner diameter 1 [mm]	35																					
Inner diameter 2 [mm]	21																					
Outer diameter 1 [mm]	65																					
Outer diameter 2 [mm]	50																					
Width 1 [mm]	18.75																					
Width 2 [mm]	18.5																					
<b>OE No.</b>																						
MERCEDES-BENZ	A 000 981 63 05, A 001 980 29 02, A 116 330 00 51																					
<p>KH00056</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066140</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>39.9</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.6</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>ALFA ROMEO</td> <td>60535941</td> </tr> <tr> <td>TOYOTA</td> <td>90368-17017, 90368-26027</td> </tr> </table>	EAN	192661066140	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	50.25	Outer diameter 2 [mm]	39.9	Width 1 [mm]	14.75	Width 2 [mm]	14.6	<b>OE No.</b>		ALFA ROMEO	60535941	TOYOTA	90368-17017, 90368-26027
EAN	192661066140																					
Inner diameter 1 [mm]	27																					
Inner diameter 2 [mm]	17.5																					
Outer diameter 1 [mm]	50.25																					
Outer diameter 2 [mm]	39.9																					
Width 1 [mm]	14.75																					
Width 2 [mm]	14.6																					
<b>OE No.</b>																						
ALFA ROMEO	60535941																					
TOYOTA	90368-17017, 90368-26027																					
<p>KH00057</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066157</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21.25</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>5013161, 6140418, 85GB-1238-AA, A850X-4K018-AA</td> </tr> </table>	EAN	192661066157	Inner diameter 1 [mm]	40.5	Inner diameter 2 [mm]	40.5	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	21.25	Width 2 [mm]	21.25	<b>OE No.</b>		FORD	5013161, 6140418, 85GB-1238-AA, A850X-4K018-AA		
EAN	192661066157																					
Inner diameter 1 [mm]	40.5																					
Inner diameter 2 [mm]	40.5																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	21.25																					
Width 2 [mm]	21.25																					
<b>OE No.</b>																						
FORD	5013161, 6140418, 85GB-1238-AA, A850X-4K018-AA																					
<p>KH00058</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066164</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>41</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45.25</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>VW</td> <td>113 517 185 C, 251 405 645 B</td> </tr> </table>	EAN	192661066164	Inner diameter 1 [mm]	41	Inner diameter 2 [mm]	22	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	45.25	Width 1 [mm]	18	Width 2 [mm]	16.5	<b>OE No.</b>		VW	113 517 185 C, 251 405 645 B		
EAN	192661066164																					
Inner diameter 1 [mm]	41																					
Inner diameter 2 [mm]	22																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	45.25																					
Width 1 [mm]	18																					
Width 2 [mm]	16.5																					
<b>OE No.</b>																						
VW	113 517 185 C, 251 405 645 B																					








Part Number	Pk.	Description																						
<p>KH00059</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066171</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>39.9</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59.1</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.6</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> </table> <p><b>OE No.</b></p> <p>MERCEDES-BENZ A 000 981 58 05, A 006 981 16 05, A 201 220 01 51, A 201 330 01 51</p>	EAN	192661066171	Inner diameter 1 [mm]	17.5	Inner diameter 2 [mm]	31.8	Outer diameter 1 [mm]	39.9	Outer diameter 2 [mm]	59.1	Width 1 [mm]	14.6	Width 2 [mm]	16.7								
EAN	192661066171																							
Inner diameter 1 [mm]	17.5																							
Inner diameter 2 [mm]	31.8																							
Outer diameter 1 [mm]	39.9																							
Outer diameter 2 [mm]	59.1																							
Width 1 [mm]	14.6																							
Width 2 [mm]	16.7																							
<p>KH00060</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066188</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>59</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>51</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> </table> <p><b>OE No.</b></p> <p>LDV RTC3427</p>	EAN	192661066188	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	22	Outer diameter 1 [mm]	59	Outer diameter 2 [mm]	51	Width 1 [mm]	17	Width 2 [mm]	15								
EAN	192661066188																							
Inner diameter 1 [mm]	35																							
Inner diameter 2 [mm]	22																							
Outer diameter 1 [mm]	59																							
Outer diameter 2 [mm]	51																							
Width 1 [mm]	17																							
Width 2 [mm]	15																							
<p>KH00061</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066195</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>49.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>49.9</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>80</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>ALFA ROMEO</td> <td>4330647</td> </tr> <tr> <td>CITROËN</td> <td>3326 27</td> </tr> <tr> <td>FIAT</td> <td>4330647</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 27</td> </tr> </table>	EAN	192661066195	Inner diameter 1 [mm]	49.9	Inner diameter 2 [mm]	49.9	Outer diameter 1 [mm]	80	Outer diameter 2 [mm]	80	Width 1 [mm]	21	Width 2 [mm]	21	ALFA ROMEO	4330647	CITROËN	3326 27	FIAT	4330647	PEUGEOT	3326 27
EAN	192661066195																							
Inner diameter 1 [mm]	49.9																							
Inner diameter 2 [mm]	49.9																							
Outer diameter 1 [mm]	80																							
Outer diameter 2 [mm]	80																							
Width 1 [mm]	21																							
Width 2 [mm]	21																							
ALFA ROMEO	4330647																							
CITROËN	3326 27																							
FIAT	4330647																							
PEUGEOT	3326 27																							
<p>KH00062</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066201</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> </table> <p><b>OE No.</b></p> <p>FORD 5024195, 91AX-1K028-AA</p>	EAN	192661066201	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	19	Width 2 [mm]	19								
EAN	192661066201																							
Inner diameter 1 [mm]	35																							
Inner diameter 2 [mm]	35																							
Outer diameter 1 [mm]	60																							
Outer diameter 2 [mm]	60																							
Width 1 [mm]	19																							
Width 2 [mm]	19																							
<p>KH00063</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066218</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.5</td> </tr> </table> <p><b>OE No.</b></p> <p>FORD 5024251, 91AX-1A049-AA</p>	EAN	192661066218	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	18.5	Width 2 [mm]	18.5								
EAN	192661066218																							
Inner diameter 1 [mm]	35																							
Inner diameter 2 [mm]	35																							
Outer diameter 1 [mm]	60																							
Outer diameter 2 [mm]	60																							
Width 1 [mm]	18.5																							
Width 2 [mm]	18.5																							

Part Number	Pk.	Description																				
<p>KH00064</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066225</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>26</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>09269-35010</td> </tr> </table>	EAN	192661066225	Inner diameter [mm]	35	Outer diameter [mm]	80	Width [mm]	26	<b>OE No.</b>		SUZUKI	09269-35010								
EAN	192661066225																					
Inner diameter [mm]	35																					
Outer diameter [mm]	80																					
Width [mm]	26																					
<b>OE No.</b>																						
SUZUKI	09269-35010																					
<p>KH00065</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066232</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>31.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>4 14 301, 91149606</td> </tr> <tr> <td>VAUXHALL</td> <td>4 14 301, 91149606</td> </tr> </table>	EAN	192661066232	Inner diameter [mm]	40	Outer diameter [mm]	90	Width [mm]	31.5	<b>OE No.</b>		OPEL	4 14 301, 91149606	VAUXHALL	4 14 301, 91149606						
EAN	192661066232																					
Inner diameter [mm]	40																					
Outer diameter [mm]	90																					
Width [mm]	31.5																					
<b>OE No.</b>																						
OPEL	4 14 301, 91149606																					
VAUXHALL	4 14 301, 91149606																					
<p>KH00066</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066249</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>23</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>3C11-1A049-AA, 4479002</td> </tr> </table>	EAN	192661066249	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	23	<b>OE No.</b>		FORD	3C11-1A049-AA, 4479002								
EAN	192661066249																					
Inner diameter [mm]	55																					
Outer diameter [mm]	90																					
Width [mm]	23																					
<b>OE No.</b>																						
FORD	3C11-1A049-AA, 4479002																					
<p>KH00067</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068823</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>39.9</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50.3</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.6</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>PORSCHE</td> <td>311 405 625 F, 311 405 645</td> </tr> <tr> <td>VW</td> <td>311 405 625 F, 311 405 645</td> </tr> </table>	EAN	192661068823	Inner diameter 1 [mm]	17.5	Inner diameter 2 [mm]	29	Outer diameter 1 [mm]	39.9	Outer diameter 2 [mm]	50.3	Width 1 [mm]	14.6	Width 2 [mm]	14.7	<b>OE No.</b>		PORSCHE	311 405 625 F, 311 405 645	VW	311 405 625 F, 311 405 645
EAN	192661068823																					
Inner diameter 1 [mm]	17.5																					
Inner diameter 2 [mm]	29																					
Outer diameter 1 [mm]	39.9																					
Outer diameter 2 [mm]	50.3																					
Width 1 [mm]	14.6																					
Width 2 [mm]	14.7																					
<b>OE No.</b>																						
PORSCHE	311 405 625 F, 311 405 645																					
VW	311 405 625 F, 311 405 645																					
<p>KH00068</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068830</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>30</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>62</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>PORSCHE</td> <td>113 501 277 A, 113 501 283</td> </tr> <tr> <td>VW</td> <td>113 501 277 A, 113 501 283</td> </tr> </table>	EAN	192661068830	Inner diameter 1 [mm]	30	Inner diameter 2 [mm]	30	Outer diameter 1 [mm]	62	Outer diameter 2 [mm]	62	Width 1 [mm]	16	Width 2 [mm]	19	<b>OE No.</b>		PORSCHE	113 501 277 A, 113 501 283	VW	113 501 277 A, 113 501 283
EAN	192661068830																					
Inner diameter 1 [mm]	30																					
Inner diameter 2 [mm]	30																					
Outer diameter 1 [mm]	62																					
Outer diameter 2 [mm]	62																					
Width 1 [mm]	16																					
Width 2 [mm]	19																					
<b>OE No.</b>																						
PORSCHE	113 501 277 A, 113 501 283																					
VW	113 501 277 A, 113 501 283																					










Part Number	Pk.	Description																				
<p>KH00069</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068847</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72.1</td> </tr> <tr> <td>Width [mm]</td> <td>22</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09269-35009</td> </tr> </table>	EAN	192661068847	Inner diameter [mm]	35	Outer diameter [mm]	72.1	Width [mm]	22	<b>OE No.</b>		SUZUKI	09269-35009								
EAN	192661068847																					
Inner diameter [mm]	35																					
Outer diameter [mm]	72.1																					
Width [mm]	22																					
<b>OE No.</b>																						
SUZUKI	09269-35009																					
<p>KH00070</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068854</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>26</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>30</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>1201302, 1C1J-1A049-CA, 3897275, 4552765, 5L3W-1225-AA, F75W-1225-BA</td> </tr> </table>	EAN	192661068854	Inner diameter [mm]	26	Outer diameter [mm]	76	Width [mm]	30	<b>OE No.</b>		FORD	1201302, 1C1J-1A049-CA, 3897275, 4552765, 5L3W-1225-AA, F75W-1225-BA								
EAN	192661068854																					
Inner diameter [mm]	26																					
Outer diameter [mm]	76																					
Width [mm]	30																					
<b>OE No.</b>																						
FORD	1201302, 1C1J-1A049-CA, 3897275, 4552765, 5L3W-1225-AA, F75W-1225-BA																					
<p>KH00071</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068861</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width 1 [mm]</td> <td>23</td> </tr> <tr> <td>Width 2 [mm]</td> <td>28</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>90363-40072</td> </tr> </table>	EAN	192661068861	Inner diameter [mm]	40	Outer diameter [mm]	90	Width 1 [mm]	23	Width 2 [mm]	28	<b>OE No.</b>		TOYOTA	90363-40072						
EAN	192661068861																					
Inner diameter [mm]	40																					
Outer diameter [mm]	90																					
Width 1 [mm]	23																					
Width 2 [mm]	28																					
<b>OE No.</b>																						
TOYOTA	90363-40072																					
<p>KH00072</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068878</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 221 330 02 25</td> </tr> </table>	EAN	192661068878	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	52	Outer diameter 2 [mm]	68	Width 1 [mm]	19	Width 2 [mm]	20	<b>OE No.</b>		MERCEDES-BENZ	A 221 330 02 25		
EAN	192661068878																					
Inner diameter 1 [mm]	25																					
Inner diameter 2 [mm]	40																					
Outer diameter 1 [mm]	52																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	19																					
Width 2 [mm]	20																					
<b>OE No.</b>																						
MERCEDES-BENZ	A 221 330 02 25																					
<p>KH00073</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071731</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>19</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>KIA</td> <td>00317 33075, MB002-33-047</td> </tr> <tr> <td>MAZDA</td> <td>0317-33-075, B002-33-047</td> </tr> </table>	EAN	192661071731	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	19	Outer diameter 1 [mm]	50	Outer diameter 2 [mm]	45	Width 1 [mm]	17	Width 2 [mm]	15	<b>OE No.</b>		KIA	00317 33075, MB002-33-047	MAZDA	0317-33-075, B002-33-047
EAN	192661071731																					
Inner diameter 1 [mm]	27																					
Inner diameter 2 [mm]	19																					
Outer diameter 1 [mm]	50																					
Outer diameter 2 [mm]	45																					
Width 1 [mm]	17																					
Width 2 [mm]	15																					
<b>OE No.</b>																						
KIA	00317 33075, MB002-33-047																					
MAZDA	0317-33-075, B002-33-047																					






Part Number	Pk.	Description																				
<p>KH00074</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071748</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>22</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09269-35009</td> </tr> </table>	EAN	192661071748	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	22	<b>OE No.</b>		SUZUKI	09269-35009								
EAN	192661071748																					
Inner diameter [mm]	35																					
Outer diameter [mm]	72																					
Width [mm]	22																					
<b>OE No.</b>																						
SUZUKI	09269-35009																					
<p>KH00075</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072929</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>27</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>27</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15.75</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FIAT</td> <td>46576148</td> </tr> </table>	EAN	192661072929	Inner diameter 1 [mm]	27	Inner diameter 2 [mm]	27	Outer diameter 1 [mm]	52	Outer diameter 2 [mm]	52	Width 1 [mm]	15.75	Width 2 [mm]	15.75	<b>OE No.</b>		FIAT	46576148		
EAN	192661072929																					
Inner diameter 1 [mm]	27																					
Inner diameter 2 [mm]	27																					
Outer diameter 1 [mm]	52																					
Outer diameter 2 [mm]	52																					
Width 1 [mm]	15.75																					
Width 2 [mm]	15.75																					
<b>OE No.</b>																						
FIAT	46576148																					
<p>KH00076</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072936</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40.75</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40.75</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>2012478, 5012347, 6140418, 85GB-1238-AA, A840X-1A049-BA, A840X-1A049-DA</td> </tr> </table>	EAN	192661072936	Inner diameter 1 [mm]	40.75	Inner diameter 2 [mm]	40.75	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	21	Width 2 [mm]	21	<b>OE No.</b>		FORD	2012478, 5012347, 6140418, 85GB-1238-AA, A840X-1A049-BA, A840X-1A049-DA		
EAN	192661072936																					
Inner diameter 1 [mm]	40.75																					
Inner diameter 2 [mm]	40.75																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	21																					
Width 2 [mm]	21																					
<b>OE No.</b>																						
FORD	2012478, 5012347, 6140418, 85GB-1238-AA, A840X-1A049-BA, A840X-1A049-DA																					
<p>KH00077</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072943</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>38</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>65</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>65</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-21100</td> </tr> <tr> <td>MITSUBISHI</td> <td>MB349416</td> </tr> </table>	EAN	192661072943	Inner diameter 1 [mm]	38	Inner diameter 2 [mm]	38	Outer diameter 1 [mm]	65	Outer diameter 2 [mm]	65	Width 1 [mm]	21	Width 2 [mm]	21	<b>OE No.</b>		HYUNDAI	51720-21100	MITSUBISHI	MB349416
EAN	192661072943																					
Inner diameter 1 [mm]	38																					
Inner diameter 2 [mm]	38																					
Outer diameter 1 [mm]	65																					
Outer diameter 2 [mm]	65																					
Width 1 [mm]	21																					
Width 2 [mm]	21																					
<b>OE No.</b>																						
HYUNDAI	51720-21100																					
MITSUBISHI	MB349416																					
<p>KH00078</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072950</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>34.75</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>34.75</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FORD</td> <td>1591389, 5010762, 81AB-1215-AB, A820X-1K018-RA</td> </tr> </table>	EAN	192661072950	Inner diameter 1 [mm]	34.75	Inner diameter 2 [mm]	34.75	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	18.5	Width 2 [mm]	18.5	<b>OE No.</b>		FORD	1591389, 5010762, 81AB-1215-AB, A820X-1K018-RA		
EAN	192661072950																					
Inner diameter 1 [mm]	34.75																					
Inner diameter 2 [mm]	34.75																					
Outer diameter 1 [mm]	60																					
Outer diameter 2 [mm]	60																					
Width 1 [mm]	18.5																					
Width 2 [mm]	18.5																					
<b>OE No.</b>																						
FORD	1591389, 5010762, 81AB-1215-AB, A820X-1K018-RA																					








Part Number	Pk.	Description																						
<p>KH00079</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072967</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>37.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>37.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>63</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>63</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17.25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>KK15033047</td> </tr> <tr> <td>MAZDA</td> <td>B001-33-047</td> </tr> </table>	EAN	192661072967	Inner diameter 1 [mm]	37.5	Inner diameter 2 [mm]	37.5	Outer diameter 1 [mm]	63	Outer diameter 2 [mm]	63	Width 1 [mm]	17.25	Width 2 [mm]	17.25	<b>OE No.</b>		KIA	KK15033047	MAZDA	B001-33-047		
EAN	192661072967																							
Inner diameter 1 [mm]	37.5																							
Inner diameter 2 [mm]	37.5																							
Outer diameter 1 [mm]	63																							
Outer diameter 2 [mm]	63																							
Width 1 [mm]	17.25																							
Width 2 [mm]	17.25																							
<b>OE No.</b>																								
KIA	KK15033047																							
MAZDA	B001-33-047																							
<p>KH00080</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072974</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>55</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>90</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>90</td> </tr> <tr> <td>Width 1 [mm]</td> <td>23</td> </tr> <tr> <td>Width 2 [mm]</td> <td>23</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 30</td> </tr> <tr> <td>FIAT</td> <td>1300535080</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 30</td> </tr> </table>	EAN	192661072974	Inner diameter 1 [mm]	55	Inner diameter 2 [mm]	55	Outer diameter 1 [mm]	90	Outer diameter 2 [mm]	90	Width 1 [mm]	23	Width 2 [mm]	23	<b>OE No.</b>		CITROËN	3350 30	FIAT	1300535080	PEUGEOT	3350 30
EAN	192661072974																							
Inner diameter 1 [mm]	55																							
Inner diameter 2 [mm]	55																							
Outer diameter 1 [mm]	90																							
Outer diameter 2 [mm]	90																							
Width 1 [mm]	23																							
Width 2 [mm]	23																							
<b>OE No.</b>																								
CITROËN	3350 30																							
FIAT	1300535080																							
PEUGEOT	3350 30																							
<p>KH00081</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072981</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>36</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>57</td> </tr> <tr> <td>Width [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JEEP</td> <td>J8134586</td> </tr> </table>	EAN	192661072981	Inner diameter [mm]	36	Outer diameter [mm]	57	Width [mm]	17	<b>OE No.</b>		JEEP	J8134586										
EAN	192661072981																							
Inner diameter [mm]	36																							
Outer diameter [mm]	57																							
Width [mm]	17																							
<b>OE No.</b>																								
JEEP	J8134586																							
<p>KH00082</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072998</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>63</td> </tr> <tr> <td>Width [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>51720-FD000, KK150-33-047</td> </tr> <tr> <td>MAZDA</td> <td>B001-33-047</td> </tr> </table>	EAN	192661072998	Inner diameter [mm]	38	Outer diameter [mm]	63	Width [mm]	17	<b>OE No.</b>		KIA	51720-FD000, KK150-33-047	MAZDA	B001-33-047								
EAN	192661072998																							
Inner diameter [mm]	38																							
Outer diameter [mm]	63																							
Width [mm]	17																							
<b>OE No.</b>																								
KIA	51720-FD000, KK150-33-047																							
MAZDA	B001-33-047																							
<p>KH00083</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073001</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>62</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SSANGYONG</td> <td>4143103210, 4143103210X, 4143203210, 4143203210X</td> </tr> </table>	EAN	192661073001	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	62	Outer diameter 2 [mm]	68	Width 1 [mm]	18	Width 2 [mm]	19	<b>OE No.</b>		SSANGYONG	4143103210, 4143103210X, 4143203210, 4143203210X				
EAN	192661073001																							
Inner diameter 1 [mm]	35																							
Inner diameter 2 [mm]	40																							
Outer diameter 1 [mm]	62																							
Outer diameter 2 [mm]	68																							
Width 1 [mm]	18																							
Width 2 [mm]	19																							
<b>OE No.</b>																								
SSANGYONG	4143103210, 4143103210X, 4143203210, 4143203210X																							

Part Number	Pk.	Description																																				
KH00084	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661073018</td> </tr> <tr> <td colspan="2">Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td colspan="2">Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td colspan="2">Outer diameter 1 [mm]</td> <td>57</td> </tr> <tr> <td colspan="2">Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td colspan="2">Width 1 [mm]</td> <td>18</td> </tr> <tr> <td colspan="2">Width 2 [mm]</td> <td>21</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td colspan="2">0K72A-33-047, 0K72A-33-075</td> </tr> </table>	EAN		192661073018	Inner diameter 1 [mm]		25	Inner diameter 2 [mm]		35	Outer diameter 1 [mm]		57	Outer diameter 2 [mm]		68	Width 1 [mm]		18	Width 2 [mm]		21	<b>OE No.</b>			KIA	0K72A-33-047, 0K72A-33-075										
EAN		192661073018																																				
Inner diameter 1 [mm]		25																																				
Inner diameter 2 [mm]		35																																				
Outer diameter 1 [mm]		57																																				
Outer diameter 2 [mm]		68																																				
Width 1 [mm]		18																																				
Width 2 [mm]		21																																				
<b>OE No.</b>																																						
KIA	0K72A-33-047, 0K72A-33-075																																					
KH00085	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661073025</td> </tr> <tr> <td colspan="2">Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td colspan="2">Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td colspan="2">Outer diameter 1 [mm]</td> <td>59</td> </tr> <tr> <td colspan="2">Outer diameter 2 [mm]</td> <td>45.2</td> </tr> <tr> <td colspan="2">Width 1 [mm]</td> <td>16.8</td> </tr> <tr> <td colspan="2">Width 2 [mm]</td> <td>15.5</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td colspan="2">A 002 980 19 02, A 002 980 65 02, A 129 330 03 51</td> </tr> </table>	EAN		192661073025	Inner diameter 1 [mm]		35	Inner diameter 2 [mm]		22	Outer diameter 1 [mm]		59	Outer diameter 2 [mm]		45.2	Width 1 [mm]		16.8	Width 2 [mm]		15.5	<b>OE No.</b>			MERCEDES-BENZ	A 002 980 19 02, A 002 980 65 02, A 129 330 03 51										
EAN		192661073025																																				
Inner diameter 1 [mm]		35																																				
Inner diameter 2 [mm]		22																																				
Outer diameter 1 [mm]		59																																				
Outer diameter 2 [mm]		45.2																																				
Width 1 [mm]		16.8																																				
Width 2 [mm]		15.5																																				
<b>OE No.</b>																																						
MERCEDES-BENZ	A 002 980 19 02, A 002 980 65 02, A 129 330 03 51																																					
KH00086	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661073032</td> </tr> <tr> <td colspan="2">Inner diameter 1 [mm]</td> <td>65</td> </tr> <tr> <td colspan="2">Inner diameter 2 [mm]</td> <td>55</td> </tr> <tr> <td colspan="2">Outer diameter 1 [mm]</td> <td>100</td> </tr> <tr> <td colspan="2">Outer diameter 2 [mm]</td> <td>90</td> </tr> <tr> <td colspan="2">Width 1 [mm]</td> <td>23</td> </tr> <tr> <td colspan="2">Width 2 [mm]</td> <td>23</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td colspan="2">43210-00Q0C, 43215-00Q0A</td> </tr> <tr> <td>OPEL</td> <td colspan="2">44 21 370, 44 213 78, 95507285</td> </tr> <tr> <td>RENAULT</td> <td colspan="2">43 21 051 62R, 43 21 098 18R</td> </tr> <tr> <td>VAUXHALL</td> <td colspan="2">44 213 78, 95507285, 95507286</td> </tr> </table>	EAN		192661073032	Inner diameter 1 [mm]		65	Inner diameter 2 [mm]		55	Outer diameter 1 [mm]		100	Outer diameter 2 [mm]		90	Width 1 [mm]		23	Width 2 [mm]		23	<b>OE No.</b>			NISSAN	43210-00Q0C, 43215-00Q0A		OPEL	44 21 370, 44 213 78, 95507285		RENAULT	43 21 051 62R, 43 21 098 18R		VAUXHALL	44 213 78, 95507285, 95507286	
EAN		192661073032																																				
Inner diameter 1 [mm]		65																																				
Inner diameter 2 [mm]		55																																				
Outer diameter 1 [mm]		100																																				
Outer diameter 2 [mm]		90																																				
Width 1 [mm]		23																																				
Width 2 [mm]		23																																				
<b>OE No.</b>																																						
NISSAN	43210-00Q0C, 43215-00Q0A																																					
OPEL	44 21 370, 44 213 78, 95507285																																					
RENAULT	43 21 051 62R, 43 21 098 18R																																					
VAUXHALL	44 213 78, 95507285, 95507286																																					
KH00087	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661073049</td> </tr> <tr> <td colspan="2">Inner diameter 1 [mm]</td> <td>21</td> </tr> <tr> <td colspan="2">Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td colspan="2">Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td colspan="2">Outer diameter 2 [mm]</td> <td>65</td> </tr> <tr> <td colspan="2">Width 1 [mm]</td> <td>18</td> </tr> <tr> <td colspan="2">Width 2 [mm]</td> <td>18</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>ISUZU</td> <td colspan="2">8-84242-683-0, 8-94242-913-0</td> </tr> </table>	EAN		192661073049	Inner diameter 1 [mm]		21	Inner diameter 2 [mm]		35	Outer diameter 1 [mm]		50	Outer diameter 2 [mm]		65	Width 1 [mm]		18	Width 2 [mm]		18	<b>OE No.</b>			ISUZU	8-84242-683-0, 8-94242-913-0										
EAN		192661073049																																				
Inner diameter 1 [mm]		21																																				
Inner diameter 2 [mm]		35																																				
Outer diameter 1 [mm]		50																																				
Outer diameter 2 [mm]		65																																				
Width 1 [mm]		18																																				
Width 2 [mm]		18																																				
<b>OE No.</b>																																						
ISUZU	8-84242-683-0, 8-94242-913-0																																					
KH00088	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661073056</td> </tr> <tr> <td colspan="2">Inner diameter 1 [mm]</td> <td>26.9</td> </tr> <tr> <td colspan="2">Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td colspan="2">Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td colspan="2">Outer diameter 2 [mm]</td> <td>39.9</td> </tr> <tr> <td colspan="2">Width 1 [mm]</td> <td>14.75</td> </tr> <tr> <td colspan="2">Width 2 [mm]</td> <td>14.6</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td colspan="2">16 03 025, 16 03 049, 9005147</td> </tr> <tr> <td>VAUXHALL</td> <td colspan="2">16 03 025, 16 03 049, 9005147</td> </tr> </table>	EAN		192661073056	Inner diameter 1 [mm]		26.9	Inner diameter 2 [mm]		17.5	Outer diameter 1 [mm]		50.25	Outer diameter 2 [mm]		39.9	Width 1 [mm]		14.75	Width 2 [mm]		14.6	<b>OE No.</b>			OPEL	16 03 025, 16 03 049, 9005147		VAUXHALL	16 03 025, 16 03 049, 9005147							
EAN		192661073056																																				
Inner diameter 1 [mm]		26.9																																				
Inner diameter 2 [mm]		17.5																																				
Outer diameter 1 [mm]		50.25																																				
Outer diameter 2 [mm]		39.9																																				
Width 1 [mm]		14.75																																				
Width 2 [mm]		14.6																																				
<b>OE No.</b>																																						
OPEL	16 03 025, 16 03 049, 9005147																																					
VAUXHALL	16 03 025, 16 03 049, 9005147																																					



Part Number	Pk.	Description																				
<p>KH00089</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073063</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15</td> </tr> <tr> <td>Width 2 [mm]</td> <td>13.2</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 460 640</td> </tr> </table>	EAN	192661073063	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	17	Outer diameter 1 [mm]	42	Outer diameter 2 [mm]	40	Width 1 [mm]	15	Width 2 [mm]	13.2	<b>OE No.</b>		RENAULT	77 01 460 640		
EAN	192661073063																					
Inner diameter 1 [mm]	20																					
Inner diameter 2 [mm]	17																					
Outer diameter 1 [mm]	42																					
Outer diameter 2 [mm]	40																					
Width 1 [mm]	15																					
Width 2 [mm]	13.2																					
<b>OE No.</b>																						
RENAULT	77 01 460 640																					
<p>KH00090</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073070</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>34</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>72</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>72</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>60 01 544 851, 77 01 450 639, 77 01 460 639</td> </tr> </table>	EAN	192661073070	Inner diameter 1 [mm]	34	Inner diameter 2 [mm]	34	Outer diameter 1 [mm]	72	Outer diameter 2 [mm]	72	Width 1 [mm]	17	Width 2 [mm]	17	<b>OE No.</b>		RENAULT	60 01 544 851, 77 01 450 639, 77 01 460 639		
EAN	192661073070																					
Inner diameter 1 [mm]	34																					
Inner diameter 2 [mm]	34																					
Outer diameter 1 [mm]	72																					
Outer diameter 2 [mm]	72																					
Width 1 [mm]	17																					
Width 2 [mm]	17																					
<b>OE No.</b>																						
RENAULT	60 01 544 851, 77 01 450 639, 77 01 460 639																					
<p>KH00091</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073087</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>28.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 11</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 11</td> </tr> </table>	EAN	192661073087	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	28.5	<b>OE No.</b>		CITROËN	3350 11	PEUGEOT	3350 11						
EAN	192661073087																					
Inner diameter [mm]	35																					
Outer diameter [mm]	72																					
Width [mm]	28.5																					
<b>OE No.</b>																						
CITROËN	3350 11																					
PEUGEOT	3350 11																					
<p>KH00092</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073094</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>30</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>62</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 460 637, 77 03 090 270, 77 03 090 271</td> </tr> </table>	EAN	192661073094	Inner diameter 1 [mm]	30	Inner diameter 2 [mm]	30	Outer diameter 1 [mm]	62	Outer diameter 2 [mm]	62	Width 1 [mm]	16	Width 2 [mm]	16	<b>OE No.</b>		RENAULT	77 01 460 637, 77 03 090 270, 77 03 090 271		
EAN	192661073094																					
Inner diameter 1 [mm]	30																					
Inner diameter 2 [mm]	30																					
Outer diameter 1 [mm]	62																					
Outer diameter 2 [mm]	62																					
Width 1 [mm]	16																					
Width 2 [mm]	16																					
<b>OE No.</b>																						
RENAULT	77 01 460 637, 77 03 090 270, 77 03 090 271																					
<p>KH00093</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073100</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59.1</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>11055109, 11055119, 3 28 018, 3 30 012</td> </tr> <tr> <td>VAUXHALL</td> <td>11055109, 11055119, 3 28 018, 3 30 012</td> </tr> </table>	EAN	192661073100	Inner diameter 1 [mm]	19.9	Inner diameter 2 [mm]	31.8	Outer diameter 1 [mm]	45.25	Outer diameter 2 [mm]	59.1	Width 1 [mm]	16.75	Width 2 [mm]	16.7	<b>OE No.</b>		OPEL	11055109, 11055119, 3 28 018, 3 30 012	VAUXHALL	11055109, 11055119, 3 28 018, 3 30 012
EAN	192661073100																					
Inner diameter 1 [mm]	19.9																					
Inner diameter 2 [mm]	31.8																					
Outer diameter 1 [mm]	45.25																					
Outer diameter 2 [mm]	59.1																					
Width 1 [mm]	16.75																					
Width 2 [mm]	16.7																					
<b>OE No.</b>																						
OPEL	11055109, 11055119, 3 28 018, 3 30 012																					
VAUXHALL	11055109, 11055119, 3 28 018, 3 30 012																					

Part Number	Pk.	Description																				
<p>KH00094</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073117</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>20</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>42</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>2358 17, 3730 15, 3748 13</td> </tr> <tr> <td>PEUGEOT</td> <td>2358 17, 3730 15, 3748 13</td> </tr> </table>	EAN	192661073117	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	20	Outer diameter 1 [mm]	47	Outer diameter 2 [mm]	42	Width 1 [mm]	15	Width 2 [mm]	15	<b>OE No.</b>		CITROËN	2358 17, 3730 15, 3748 13	PEUGEOT	2358 17, 3730 15, 3748 13
EAN	192661073117																					
Inner diameter 1 [mm]	25																					
Inner diameter 2 [mm]	20																					
Outer diameter 1 [mm]	47																					
Outer diameter 2 [mm]	42																					
Width 1 [mm]	15																					
Width 2 [mm]	15																					
<b>OE No.</b>																						
CITROËN	2358 17, 3730 15, 3748 13																					
PEUGEOT	2358 17, 3730 15, 3748 13																					
<p>KH00095</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073124</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>82</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>82</td> </tr> <tr> <td>Width 1 [mm]</td> <td>28.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>28.75</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 468 409</td> </tr> </table>	EAN	192661073124	Inner diameter 1 [mm]	50	Inner diameter 2 [mm]	50	Outer diameter 1 [mm]	82	Outer diameter 2 [mm]	82	Width 1 [mm]	28.75	Width 2 [mm]	28.75	<b>OE No.</b>		RENAULT	77 01 468 409		
EAN	192661073124																					
Inner diameter 1 [mm]	50																					
Inner diameter 2 [mm]	50																					
Outer diameter 1 [mm]	82																					
Outer diameter 2 [mm]	82																					
Width 1 [mm]	28.75																					
Width 2 [mm]	28.75																					
<b>OE No.</b>																						
RENAULT	77 01 468 409																					
<p>KH00096</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073131</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>72</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>24</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19.3</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 465 647</td> </tr> </table>	EAN	192661073131	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	72	Outer diameter 2 [mm]	52	Width 1 [mm]	24	Width 2 [mm]	19.3	<b>OE No.</b>		RENAULT	77 01 465 647		
EAN	192661073131																					
Inner diameter 1 [mm]	35																					
Inner diameter 2 [mm]	25																					
Outer diameter 1 [mm]	72																					
Outer diameter 2 [mm]	52																					
Width 1 [mm]	24																					
Width 2 [mm]	19.3																					
<b>OE No.</b>																						
RENAULT	77 01 465 647																					
<p>KH00097</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073148</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>29</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59.9</td> </tr> <tr> <td>Width 1 [mm]</td> <td>10.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>11.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JAGUAR</td> <td>CAC 4306, CAC 4999</td> </tr> </table>	EAN	192661073148	Inner diameter 1 [mm]	29	Inner diameter 2 [mm]	34	Outer diameter 1 [mm]	50.25	Outer diameter 2 [mm]	59.9	Width 1 [mm]	10.75	Width 2 [mm]	11.7	<b>OE No.</b>		JAGUAR	CAC 4306, CAC 4999		
EAN	192661073148																					
Inner diameter 1 [mm]	29																					
Inner diameter 2 [mm]	34																					
Outer diameter 1 [mm]	50.25																					
Outer diameter 2 [mm]	59.9																					
Width 1 [mm]	10.75																					
Width 2 [mm]	11.7																					
<b>OE No.</b>																						
JAGUAR	CAC 4306, CAC 4999																					
<p>KH00098</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073155</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LADA</td> <td>2121-3103020-10</td> </tr> </table>	EAN	192661073155	Inner diameter 1 [mm]	40	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	20	Width 2 [mm]	20	<b>OE No.</b>		LADA	2121-3103020-10		
EAN	192661073155																					
Inner diameter 1 [mm]	40																					
Inner diameter 2 [mm]	40																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	20																					
Width 2 [mm]	20																					
<b>OE No.</b>																						
LADA	2121-3103020-10																					








Part Number	Pk.	Description														
<p>KH00099</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073162</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>0.75</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.75</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>1.78</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59.131</td> </tr> <tr> <td>Width 1 [mm]</td> <td>0.47</td> </tr> <tr> <td>Width 2 [mm]</td> <td>11.81</td> </tr> </table> <p><b>OE No.</b> MERCEDES-BENZ    A 000 981 58 05, A 000 981 59 05, A 201 330 02 51</p>	EAN	192661073162	Inner diameter 1 [mm]	0.75	Inner diameter 2 [mm]	31.75	Outer diameter 1 [mm]	1.78	Outer diameter 2 [mm]	59.131	Width 1 [mm]	0.47	Width 2 [mm]	11.81
EAN	192661073162															
Inner diameter 1 [mm]	0.75															
Inner diameter 2 [mm]	31.75															
Outer diameter 1 [mm]	1.78															
Outer diameter 2 [mm]	59.131															
Width 1 [mm]	0.47															
Width 2 [mm]	11.81															
<p>KH00100</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073179</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>26.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>17.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>39.9</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.6</td> </tr> </table> <p><b>OE No.</b> KIA                    KKY01-33047, KKY01-33075, MB002-033-47, MB002-33-075 MAZDA              B002-33-047, B002-33-075</p>	EAN	192661073179	Inner diameter 1 [mm]	26.9	Inner diameter 2 [mm]	17.5	Outer diameter 1 [mm]	50.25	Outer diameter 2 [mm]	39.9	Width 1 [mm]	14.75	Width 2 [mm]	14.6
EAN	192661073179															
Inner diameter 1 [mm]	26.9															
Inner diameter 2 [mm]	17.5															
Outer diameter 1 [mm]	50.25															
Outer diameter 2 [mm]	39.9															
Width 1 [mm]	14.75															
Width 2 [mm]	14.6															
<p>KH00101</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073186</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>17</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>20</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>12</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15</td> </tr> </table> <p><b>OE No.</b> DAIHATSU            90043-63010, 90043-63012</p>	EAN	192661073186	Inner diameter 1 [mm]	17	Inner diameter 2 [mm]	20	Outer diameter 1 [mm]	40	Outer diameter 2 [mm]	52	Width 1 [mm]	12	Width 2 [mm]	15
EAN	192661073186															
Inner diameter 1 [mm]	17															
Inner diameter 2 [mm]	20															
Outer diameter 1 [mm]	40															
Outer diameter 2 [mm]	52															
Width 1 [mm]	12															
Width 2 [mm]	15															
<p>KH00102</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073193</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>39.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>80</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>24</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.25</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO        26800140, 26800330 IVECO                93813627</p>	EAN	192661073193	Inner diameter 1 [mm]	39.5	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	80	Outer diameter 2 [mm]	62	Width 1 [mm]	24	Width 2 [mm]	18.25
EAN	192661073193															
Inner diameter 1 [mm]	39.5															
Inner diameter 2 [mm]	25															
Outer diameter 1 [mm]	80															
Outer diameter 2 [mm]	62															
Width 1 [mm]	24															
Width 2 [mm]	18.25															
<p>KH00103</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073209</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>80</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>33.3</td> </tr> <tr> <td>Width 2 [mm]</td> <td>26.6</td> </tr> </table> <p><b>OE No.</b> IVECO                8582739, 8582740</p>	EAN	192661073209	Inner diameter 1 [mm]	40	Inner diameter 2 [mm]	30	Outer diameter 1 [mm]	80	Outer diameter 2 [mm]	62	Width 1 [mm]	33.3	Width 2 [mm]	26.6
EAN	192661073209															
Inner diameter 1 [mm]	40															
Inner diameter 2 [mm]	30															
Outer diameter 1 [mm]	80															
Outer diameter 2 [mm]	62															
Width 1 [mm]	33.3															
Width 2 [mm]	26.6															

Part Number	Pk.	Description																								
<p>KH00104</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073216</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>62</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19.4</td> </tr> <tr> <td>Width 2 [mm]</td> <td>24</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>44 03 942, 9111942</td> </tr> <tr> <td>VAUXHALL</td> <td>44 03 942, 9111942</td> </tr> </table>	EAN	192661073216	Inner diameter 1 [mm]	25	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	62	Outer diameter 2 [mm]	52	Width 1 [mm]	19.4	Width 2 [mm]	24	<b>OE No.</b>		OPEL	44 03 942, 9111942	VAUXHALL	44 03 942, 9111942				
EAN	192661073216																									
Inner diameter 1 [mm]	25																									
Inner diameter 2 [mm]	35																									
Outer diameter 1 [mm]	62																									
Outer diameter 2 [mm]	52																									
Width 1 [mm]	19.4																									
Width 2 [mm]	24																									
<b>OE No.</b>																										
OPEL	44 03 942, 9111942																									
VAUXHALL	44 03 942, 9111942																									
<p>KH00105</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073223</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>40</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>52</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.6</td> </tr> <tr> <td>Width 2 [mm]</td> <td>22</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 140 330 02 51, A 140 981 03 05, A 140 981 05 05</td> </tr> </table>	EAN	192661073223	Inner diameter 1 [mm]	40	Inner diameter 2 [mm]	25	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	52	Width 1 [mm]	14.6	Width 2 [mm]	22	<b>OE No.</b>		MERCEDES-BENZ	A 140 330 02 51, A 140 981 03 05, A 140 981 05 05						
EAN	192661073223																									
Inner diameter 1 [mm]	40																									
Inner diameter 2 [mm]	25																									
Outer diameter 1 [mm]	68																									
Outer diameter 2 [mm]	52																									
Width 1 [mm]	14.6																									
Width 2 [mm]	22																									
<b>OE No.</b>																										
MERCEDES-BENZ	A 140 330 02 51, A 140 981 03 05, A 140 981 05 05																									
<p>KH00106</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073230</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45.2</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77.8</td> </tr> <tr> <td>Width [mm]</td> <td>19.8</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>STC 4382</td> </tr> </table>	EAN	192661073230	Inner diameter [mm]	45.2	Outer diameter [mm]	77.8	Width [mm]	19.8	<b>OE No.</b>		LAND ROVER	STC 4382												
EAN	192661073230																									
Inner diameter [mm]	45.2																									
Outer diameter [mm]	77.8																									
Width [mm]	19.8																									
<b>OE No.</b>																										
LAND ROVER	STC 4382																									
<p>KH00107</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073247</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>30</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>4470124, 71714453</td> </tr> <tr> <td>CITROËN</td> <td>3730 20, 3735 15</td> </tr> <tr> <td>FIAT</td> <td>4470124, 71714453</td> </tr> <tr> <td>PEUGEOT</td> <td>3730 20, 3735 15</td> </tr> </table>	EAN	192661073247	Inner diameter 1 [mm]	30	Inner diameter 2 [mm]	40	Outer diameter 1 [mm]	55	Outer diameter 2 [mm]	68	Width 1 [mm]	17	Width 2 [mm]	19	<b>OE No.</b>		ALFA ROMEO	4470124, 71714453	CITROËN	3730 20, 3735 15	FIAT	4470124, 71714453	PEUGEOT	3730 20, 3735 15
EAN	192661073247																									
Inner diameter 1 [mm]	30																									
Inner diameter 2 [mm]	40																									
Outer diameter 1 [mm]	55																									
Outer diameter 2 [mm]	68																									
Width 1 [mm]	17																									
Width 2 [mm]	19																									
<b>OE No.</b>																										
ALFA ROMEO	4470124, 71714453																									
CITROËN	3730 20, 3735 15																									
FIAT	4470124, 71714453																									
PEUGEOT	3730 20, 3735 15																									
<p>KH00108</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073254</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAIHATSU</td> <td>90043-63248-000</td> </tr> </table>	EAN	192661073254	Inner diameter [mm]	32	Outer diameter [mm]	72	Width [mm]	25	<b>OE No.</b>		DAIHATSU	90043-63248-000												
EAN	192661073254																									
Inner diameter [mm]	32																									
Outer diameter [mm]	72																									
Width [mm]	25																									
<b>OE No.</b>																										
DAIHATSU	90043-63248-000																									















Part Number	Pk.	Description																				
<p>KH00109</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074060</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>19.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>14.9</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Width 1 [mm]</td> <td>13.25</td> </tr> <tr> <td>Width 2 [mm]</td> <td>11.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46576155, 60055388</td> </tr> </table>	EAN	192661074060	Inner diameter 1 [mm]	19.9	Inner diameter 2 [mm]	14.9	Outer diameter 1 [mm]	43	Outer diameter 2 [mm]	35	Width 1 [mm]	13.25	Width 2 [mm]	11.5	<b>OE No.</b>		FIAT	46576155, 60055388		
EAN	192661074060																					
Inner diameter 1 [mm]	19.9																					
Inner diameter 2 [mm]	14.9																					
Outer diameter 1 [mm]	43																					
Outer diameter 2 [mm]	35																					
Width 1 [mm]	13.25																					
Width 2 [mm]	11.5																					
<b>OE No.</b>																						
FIAT	46576155, 60055388																					
<p>KH00110</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074077</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>60547722</td> </tr> </table>	EAN	192661074077	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	25	<b>OE No.</b>		ALFA ROMEO	60547722								
EAN	192661074077																					
Inner diameter [mm]	35																					
Outer diameter [mm]	72																					
Width [mm]	25																					
<b>OE No.</b>																						
ALFA ROMEO	60547722																					
<p>KH00111</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074084</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>18.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50.3</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>14.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>60523333, 60523334</td> </tr> </table>	EAN	192661074084	Inner diameter 1 [mm]	18.9	Inner diameter 2 [mm]	29	Outer diameter 1 [mm]	45.25	Outer diameter 2 [mm]	50.3	Width 1 [mm]	16.75	Width 2 [mm]	14.7	<b>OE No.</b>		ALFA ROMEO	60523333, 60523334		
EAN	192661074084																					
Inner diameter 1 [mm]	18.9																					
Inner diameter 2 [mm]	29																					
Outer diameter 1 [mm]	45.25																					
Outer diameter 2 [mm]	50.3																					
Width 1 [mm]	16.75																					
Width 2 [mm]	14.7																					
<b>OE No.</b>																						
ALFA ROMEO	60523333, 60523334																					
<p>KH00112</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074091</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>73</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>63</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>3666957, 3666963, XM34-1215-BA, XM34-1216-BA</td> </tr> <tr> <td>MAZDA</td> <td>S231-33-047, S321-3375</td> </tr> </table>	EAN	192661074091	Inner diameter 1 [mm]	45	Inner diameter 2 [mm]	37	Outer diameter 1 [mm]	73	Outer diameter 2 [mm]	63	Width 1 [mm]	20	Width 2 [mm]	17	<b>OE No.</b>		FORD	3666957, 3666963, XM34-1215-BA, XM34-1216-BA	MAZDA	S231-33-047, S321-3375
EAN	192661074091																					
Inner diameter 1 [mm]	45																					
Inner diameter 2 [mm]	37																					
Outer diameter 1 [mm]	73																					
Outer diameter 2 [mm]	63																					
Width 1 [mm]	20																					
Width 2 [mm]	17																					
<b>OE No.</b>																						
FORD	3666957, 3666963, XM34-1215-BA, XM34-1216-BA																					
MAZDA	S231-33-047, S321-3375																					
<p>KH00113</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074107</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>41</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>68</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>21</td> </tr> <tr> <td>Width 2 [mm]</td> <td>21</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>6140418, 85GB-1238-AA</td> </tr> </table>	EAN	192661074107	Inner diameter 1 [mm]	41	Inner diameter 2 [mm]	41	Outer diameter 1 [mm]	68	Outer diameter 2 [mm]	68	Width 1 [mm]	21	Width 2 [mm]	21	<b>OE No.</b>		FORD	6140418, 85GB-1238-AA		
EAN	192661074107																					
Inner diameter 1 [mm]	41																					
Inner diameter 2 [mm]	41																					
Outer diameter 1 [mm]	68																					
Outer diameter 2 [mm]	68																					
Width 1 [mm]	21																					
Width 2 [mm]	21																					
<b>OE No.</b>																						
FORD	6140418, 85GB-1238-AA																					






Part Number	Pk.	Description																				
<p>KH00115</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074121</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>16</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09262-30103</td> </tr> </table>	EAN	192661074121	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	16	<b>OE No.</b>		SUZUKI	09262-30103								
EAN	192661074121																					
Inner diameter [mm]	30																					
Outer diameter [mm]	62																					
Width [mm]	16																					
<b>OE No.</b>																						
SUZUKI	09262-30103																					
<p>KH00116</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074138</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>23</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>90363-40068, 90363-40072</td> </tr> </table>	EAN	192661074138	Inner diameter [mm]	40	Outer diameter [mm]	90	Width [mm]	23	<b>OE No.</b>		TOYOTA	90363-40068, 90363-40072								
EAN	192661074138																					
Inner diameter [mm]	40																					
Outer diameter [mm]	90																					
Width [mm]	23																					
<b>OE No.</b>																						
TOYOTA	90363-40068, 90363-40072																					
<p>KH00117</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077351</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>21</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>65</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>NISSAN</td> <td>039-05923, 19802902, 40210-F1700, 40215-F1700</td> </tr> </table>	EAN	192661077351	Inner diameter 1 [mm]	21	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	50	Outer diameter 2 [mm]	65	Width 1 [mm]	18	Width 2 [mm]	18	<b>OE No.</b>		NISSAN	039-05923, 19802902, 40210-F1700, 40215-F1700		
EAN	192661077351																					
Inner diameter 1 [mm]	21																					
Inner diameter 2 [mm]	35																					
Outer diameter 1 [mm]	50																					
Outer diameter 2 [mm]	65																					
Width 1 [mm]	18																					
Width 2 [mm]	18																					
<b>OE No.</b>																						
NISSAN	039-05923, 19802902, 40210-F1700, 40215-F1700																					
<p>KH00118</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077368</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>55</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>90</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>90</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>25</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 001 981 89 05, A 002 981 13 05, A 002 981 19 05, A 002 981 66 05, A 005 981 53 05, A 006 981 56 05, A 007 981 04 05, A 007 981 55 05</td> </tr> <tr> <td>VW</td> <td>291 501 319 B, 2D0 501 319 A, 2D0 501 319 B</td> </tr> </table>	EAN	192661077368	Inner diameter 1 [mm]	55	Inner diameter 2 [mm]	50	Outer diameter 1 [mm]	90	Outer diameter 2 [mm]	90	Width 1 [mm]	34	Width 2 [mm]	25	<b>OE No.</b>		MERCEDES-BENZ	A 001 981 89 05, A 002 981 13 05, A 002 981 19 05, A 002 981 66 05, A 005 981 53 05, A 006 981 56 05, A 007 981 04 05, A 007 981 55 05	VW	291 501 319 B, 2D0 501 319 A, 2D0 501 319 B
EAN	192661077368																					
Inner diameter 1 [mm]	55																					
Inner diameter 2 [mm]	50																					
Outer diameter 1 [mm]	90																					
Outer diameter 2 [mm]	90																					
Width 1 [mm]	34																					
Width 2 [mm]	25																					
<b>OE No.</b>																						
MERCEDES-BENZ	A 001 981 89 05, A 002 981 13 05, A 002 981 19 05, A 002 981 66 05, A 005 981 53 05, A 006 981 56 05, A 007 981 04 05, A 007 981 55 05																					
VW	291 501 319 B, 2D0 501 319 A, 2D0 501 319 B																					
<p>KH00119</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077375</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>73</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>63</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MAZDA</td> <td>S083-33-047, S231-33-047, S231-33-075, UH71-33-047</td> </tr> </table>	EAN	192661077375	Inner diameter 1 [mm]	45	Inner diameter 2 [mm]	38	Outer diameter 1 [mm]	73	Outer diameter 2 [mm]	63	Width 1 [mm]	20	Width 2 [mm]	17	<b>OE No.</b>		MAZDA	S083-33-047, S231-33-047, S231-33-075, UH71-33-047		
EAN	192661077375																					
Inner diameter 1 [mm]	45																					
Inner diameter 2 [mm]	38																					
Outer diameter 1 [mm]	73																					
Outer diameter 2 [mm]	63																					
Width 1 [mm]	20																					
Width 2 [mm]	17																					
<b>OE No.</b>																						
MAZDA	S083-33-047, S231-33-047, S231-33-075, UH71-33-047																					








Part Number	Pk.	Description																						
<p>KH00120</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077382</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>20.5</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>65</td> </tr> <tr> <td>Width [mm]</td> <td>31</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JEEP</td> <td>05012825AA</td> </tr> </table>	EAN	192661077382	Inner diameter [mm]	20.5	Outer diameter [mm]	65	Width [mm]	31	<b>OE No.</b>		JEEP	05012825AA										
EAN	192661077382																							
Inner diameter [mm]	20.5																							
Outer diameter [mm]	65																							
Width [mm]	31																							
<b>OE No.</b>																								
JEEP	05012825AA																							
<p>KH00121</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080207</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>23</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>GHB127</td> </tr> <tr> <td>ROVER</td> <td>GHB127</td> </tr> </table>	EAN	192661080207	Inner diameter [mm]	40	Outer diameter [mm]	80	Width [mm]	23	<b>OE No.</b>		MG	GHB127	ROVER	GHB127								
EAN	192661080207																							
Inner diameter [mm]	40																							
Outer diameter [mm]	80																							
Width [mm]	23																							
<b>OE No.</b>																								
MG	GHB127																							
ROVER	GHB127																							
<p>KH00122</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080214</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>17</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>GHB130</td> </tr> </table>	EAN	192661080214	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	17	<b>OE No.</b>		MG	GHB130										
EAN	192661080214																							
Inner diameter [mm]	35																							
Outer diameter [mm]	72																							
Width [mm]	17																							
<b>OE No.</b>																								
MG	GHB130																							
<p>KH00123</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080221</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>25.4</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>15.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.8</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>41.2</td> </tr> <tr> <td>Width 1 [mm]</td> <td>14.3</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17.2</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BOND</td> <td>GHB110, GHB111</td> </tr> <tr> <td>TRIUMPH</td> <td>GHB110, GHB111</td> </tr> <tr> <td>TVR</td> <td>GHB110, GHB111</td> </tr> </table>	EAN	192661080221	Inner diameter 1 [mm]	25.4	Inner diameter 2 [mm]	15.8	Outer diameter 1 [mm]	50.8	Outer diameter 2 [mm]	41.2	Width 1 [mm]	14.3	Width 2 [mm]	17.2	<b>OE No.</b>		BOND	GHB110, GHB111	TRIUMPH	GHB110, GHB111	TVR	GHB110, GHB111
EAN	192661080221																							
Inner diameter 1 [mm]	25.4																							
Inner diameter 2 [mm]	15.8																							
Outer diameter 1 [mm]	50.8																							
Outer diameter 2 [mm]	41.2																							
Width 1 [mm]	14.3																							
Width 2 [mm]	17.2																							
<b>OE No.</b>																								
BOND	GHB110, GHB111																							
TRIUMPH	GHB110, GHB111																							
TVR	GHB110, GHB111																							
<p>KH00124</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080238</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>26.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>18.9</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.2</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>45.25</td> </tr> <tr> <td>Width 1 [mm]</td> <td>10.6</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.75</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LOTUS</td> <td>A036C6041Z, A036C6042Z</td> </tr> </table>	EAN	192661080238	Inner diameter 1 [mm]	26.9	Inner diameter 2 [mm]	18.9	Outer diameter 1 [mm]	50.2	Outer diameter 2 [mm]	45.25	Width 1 [mm]	10.6	Width 2 [mm]	16.75	<b>OE No.</b>		LOTUS	A036C6041Z, A036C6042Z				
EAN	192661080238																							
Inner diameter 1 [mm]	26.9																							
Inner diameter 2 [mm]	18.9																							
Outer diameter 1 [mm]	50.2																							
Outer diameter 2 [mm]	45.25																							
Width 1 [mm]	10.6																							
Width 2 [mm]	16.75																							
<b>OE No.</b>																								
LOTUS	A036C6041Z, A036C6042Z																							






Part Number	Pk.	Description																				
<p>KH00125</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080245</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>46.1</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>41.3</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>85</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>76.2</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17.69</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>RTC3416, RTC3426</td> </tr> </table>	EAN	192661080245	Inner diameter 1 [mm]	46.1	Inner diameter 2 [mm]	41.3	Outer diameter 1 [mm]	85	Outer diameter 2 [mm]	76.2	Width 1 [mm]	17.69	Width 2 [mm]	18.5	<b>OE No.</b>		LAND ROVER	RTC3416, RTC3426		
EAN	192661080245																					
Inner diameter 1 [mm]	46.1																					
Inner diameter 2 [mm]	41.3																					
Outer diameter 1 [mm]	85																					
Outer diameter 2 [mm]	76.2																					
Width 1 [mm]	17.69																					
Width 2 [mm]	18.5																					
<b>OE No.</b>																						
LAND ROVER	RTC3416, RTC3426																					
<p>KH00126</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080252</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>18.9</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>31.8</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>45.25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>59.1</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16.75</td> </tr> <tr> <td>Width 2 [mm]</td> <td>16.7</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>GHB102, GHB105</td> </tr> <tr> <td>ROVER</td> <td>GHB102, GHB105</td> </tr> </table>	EAN	192661080252	Inner diameter 1 [mm]	18.9	Inner diameter 2 [mm]	31.8	Outer diameter 1 [mm]	45.25	Outer diameter 2 [mm]	59.1	Width 1 [mm]	16.75	Width 2 [mm]	16.7	<b>OE No.</b>		MG	GHB102, GHB105	ROVER	GHB102, GHB105
EAN	192661080252																					
Inner diameter 1 [mm]	18.9																					
Inner diameter 2 [mm]	31.8																					
Outer diameter 1 [mm]	45.25																					
Outer diameter 2 [mm]	59.1																					
Width 1 [mm]	16.75																					
Width 2 [mm]	16.7																					
<b>OE No.</b>																						
MG	GHB102, GHB105																					
ROVER	GHB102, GHB105																					
<p>KH00127</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080269</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>46</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>41.3</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>79.4</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>73</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.1</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAIMLER</td> <td>C15230, C19066</td> </tr> <tr> <td>JAGUAR</td> <td>C15230, C19066</td> </tr> </table>	EAN	192661080269	Inner diameter 1 [mm]	46	Inner diameter 2 [mm]	41.3	Outer diameter 1 [mm]	79.4	Outer diameter 2 [mm]	73	Width 1 [mm]	18.5	Width 2 [mm]	18.1	<b>OE No.</b>		DAIMLER	C15230, C19066	JAGUAR	C15230, C19066
EAN	192661080269																					
Inner diameter 1 [mm]	46																					
Inner diameter 2 [mm]	41.3																					
Outer diameter 1 [mm]	79.4																					
Outer diameter 2 [mm]	73																					
Width 1 [mm]	18.5																					
Width 2 [mm]	18.1																					
<b>OE No.</b>																						
DAIMLER	C15230, C19066																					
JAGUAR	C15230, C19066																					
<p>KH00128</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080276</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>37.5</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>37.5</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>63</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>63</td> </tr> <tr> <td>Width 1 [mm]</td> <td>19</td> </tr> <tr> <td>Width 2 [mm]</td> <td>19</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>5012346, 5012477, A840X-1K018-AA, A840X-1K018-BA</td> </tr> </table>	EAN	192661080276	Inner diameter 1 [mm]	37.5	Inner diameter 2 [mm]	37.5	Outer diameter 1 [mm]	63	Outer diameter 2 [mm]	63	Width 1 [mm]	19	Width 2 [mm]	19	<b>OE No.</b>		FORD	5012346, 5012477, A840X-1K018-AA, A840X-1K018-BA		
EAN	192661080276																					
Inner diameter 1 [mm]	37.5																					
Inner diameter 2 [mm]	37.5																					
Outer diameter 1 [mm]	63																					
Outer diameter 2 [mm]	63																					
Width 1 [mm]	19																					
Width 2 [mm]	19																					
<b>OE No.</b>																						
FORD	5012346, 5012477, A840X-1K018-AA, A840X-1K018-BA																					
<p>KH00129</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080283</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>29.9</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>62</td> </tr> <tr> <td>Width 1 [mm]</td> <td>15.3</td> </tr> <tr> <td>Width 2 [mm]</td> <td>17.4</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 03 090 203, 77 03 090 269</td> </tr> </table>	EAN	192661080283	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	29.9	Outer diameter 1 [mm]	47	Outer diameter 2 [mm]	62	Width 1 [mm]	15.3	Width 2 [mm]	17.4	<b>OE No.</b>		RENAULT	77 03 090 203, 77 03 090 269		
EAN	192661080283																					
Inner diameter 1 [mm]	20																					
Inner diameter 2 [mm]	29.9																					
Outer diameter 1 [mm]	47																					
Outer diameter 2 [mm]	62																					
Width 1 [mm]	15.3																					
Width 2 [mm]	17.4																					
<b>OE No.</b>																						
RENAULT	77 03 090 203, 77 03 090 269																					








Part Number	Pk.	Description																		
<p>KH00130</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080290</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>50.8</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>46</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>85</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>79</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17.5</td> </tr> <tr> <td>Width 2 [mm]</td> <td>18.6</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LDV</td> <td>RTC3412, RTC3436</td> </tr> </table>	EAN	192661080290	Inner diameter 1 [mm]	50.8	Inner diameter 2 [mm]	46	Outer diameter 1 [mm]	85	Outer diameter 2 [mm]	79	Width 1 [mm]	17.5	Width 2 [mm]	18.6	<b>OE No.</b>		LDV	RTC3412, RTC3436
EAN	192661080290																			
Inner diameter 1 [mm]	50.8																			
Inner diameter 2 [mm]	46																			
Outer diameter 1 [mm]	85																			
Outer diameter 2 [mm]	79																			
Width 1 [mm]	17.5																			
Width 2 [mm]	18.6																			
<b>OE No.</b>																				
LDV	RTC3412, RTC3436																			
<p>KH00131</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080306</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>45.7</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>75</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>73.5</td> </tr> <tr> <td>Width 1 [mm]</td> <td>18.7</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JAGUAR</td> <td>CAC6333, JLM1708, JLM21053</td> </tr> </table>	EAN	192661080306	Inner diameter 1 [mm]	45.7	Inner diameter 2 [mm]	41	Outer diameter 1 [mm]	75	Outer diameter 2 [mm]	73.5	Width 1 [mm]	18.7	Width 2 [mm]	20	<b>OE No.</b>		JAGUAR	CAC6333, JLM1708, JLM21053
EAN	192661080306																			
Inner diameter 1 [mm]	45.7																			
Inner diameter 2 [mm]	41																			
Outer diameter 1 [mm]	75																			
Outer diameter 2 [mm]	73.5																			
Width 1 [mm]	18.7																			
Width 2 [mm]	20																			
<b>OE No.</b>																				
JAGUAR	CAC6333, JLM1708, JLM21053																			
<p>KH00132</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080313</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>35</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>60</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>60</td> </tr> <tr> <td>Width 1 [mm]</td> <td>11.39</td> </tr> <tr> <td>Width 2 [mm]</td> <td>11.39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1591389, 5011392, 5911391, 81AB-1215-AB, A830X-1A049-FA, A830X-1A049-GA</td> </tr> </table>	EAN	192661080313	Inner diameter 1 [mm]	35	Inner diameter 2 [mm]	35	Outer diameter 1 [mm]	60	Outer diameter 2 [mm]	60	Width 1 [mm]	11.39	Width 2 [mm]	11.39	<b>OE No.</b>		FORD	1591389, 5011392, 5911391, 81AB-1215-AB, A830X-1A049-FA, A830X-1A049-GA
EAN	192661080313																			
Inner diameter 1 [mm]	35																			
Inner diameter 2 [mm]	35																			
Outer diameter 1 [mm]	60																			
Outer diameter 2 [mm]	60																			
Width 1 [mm]	11.39																			
Width 2 [mm]	11.39																			
<b>OE No.</b>																				
FORD	1591389, 5011392, 5911391, 81AB-1215-AB, A830X-1A049-FA, A830X-1A049-GA																			
<p>KH00133</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080320</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>20</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>46</td> </tr> <tr> <td>Width 1 [mm]</td> <td>16</td> </tr> <tr> <td>Width 2 [mm]</td> <td>15.9</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>PORSCHE</td> <td>999 059 089 01, 999 059 090 00</td> </tr> </table>	EAN	192661080320	Inner diameter 1 [mm]	20	Inner diameter 2 [mm]	22	Outer diameter 1 [mm]	52	Outer diameter 2 [mm]	46	Width 1 [mm]	16	Width 2 [mm]	15.9	<b>OE No.</b>		PORSCHE	999 059 089 01, 999 059 090 00
EAN	192661080320																			
Inner diameter 1 [mm]	20																			
Inner diameter 2 [mm]	22																			
Outer diameter 1 [mm]	52																			
Outer diameter 2 [mm]	46																			
Width 1 [mm]	16																			
Width 2 [mm]	15.9																			
<b>OE No.</b>																				
PORSCHE	999 059 089 01, 999 059 090 00																			
<p>KH00134</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080337</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>50</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>82</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>73</td> </tr> <tr> <td>Width 1 [mm]</td> <td>17</td> </tr> <tr> <td>Width 2 [mm]</td> <td>22</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90080-36064, 90080-36067, 90368-45087, 90368-49084</td> </tr> </table>	EAN	192661080337	Inner diameter 1 [mm]	50	Inner diameter 2 [mm]	45	Outer diameter 1 [mm]	82	Outer diameter 2 [mm]	73	Width 1 [mm]	17	Width 2 [mm]	22	<b>OE No.</b>		TOYOTA	90080-36064, 90080-36067, 90368-45087, 90368-49084
EAN	192661080337																			
Inner diameter 1 [mm]	50																			
Inner diameter 2 [mm]	45																			
Outer diameter 1 [mm]	82																			
Outer diameter 2 [mm]	73																			
Width 1 [mm]	17																			
Width 2 [mm]	22																			
<b>OE No.</b>																				
TOYOTA	90080-36064, 90080-36067, 90368-45087, 90368-49084																			

Part Number	Pk.	Description																		
KH00135 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080344</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>22</td> </tr> <tr> <td>Inner diameter 2 [mm]</td> <td>22</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>50.8</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>50.8</td> </tr> <tr> <td>Width 1 [mm]</td> <td>20.2</td> </tr> <tr> <td>Width 2 [mm]</td> <td>20.2</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>ROVER</td> <td>GHB213, GHB377, GHK1548, GHK1549, GHK1550</td> </tr> </table>	EAN	192661080344	Inner diameter 1 [mm]	22	Inner diameter 2 [mm]	22	Outer diameter 1 [mm]	50.8	Outer diameter 2 [mm]	50.8	Width 1 [mm]	20.2	Width 2 [mm]	20.2	<b>OE No.</b>		ROVER	GHB213, GHB377, GHK1548, GHK1549, GHK1550
EAN	192661080344																			
Inner diameter 1 [mm]	22																			
Inner diameter 2 [mm]	22																			
Outer diameter 1 [mm]	50.8																			
Outer diameter 2 [mm]	50.8																			
Width 1 [mm]	20.2																			
Width 2 [mm]	20.2																			
<b>OE No.</b>																				
ROVER	GHB213, GHB377, GHK1548, GHK1549, GHK1550																			
KH00136 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080351</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45.2</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77.8</td> </tr> <tr> <td>Width [mm]</td> <td>19.8</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>LAND ROVER</td> <td>RTC 3429, STC 4382</td> </tr> </table>	EAN	192661080351	Inner diameter [mm]	45.2	Outer diameter [mm]	77.8	Width [mm]	19.8	<b>OE No.</b>		LAND ROVER	RTC 3429, STC 4382						
EAN	192661080351																			
Inner diameter [mm]	45.2																			
Outer diameter [mm]	77.8																			
Width [mm]	19.8																			
<b>OE No.</b>																				
LAND ROVER	RTC 3429, STC 4382																			
KH00137 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080368</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>10</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MAZDA</td> <td>9960-30-208</td> </tr> </table>	EAN	192661080368	Inner diameter [mm]	40	Outer diameter [mm]	80	Width [mm]	10	<b>OE No.</b>		MAZDA	9960-30-208						
EAN	192661080368																			
Inner diameter [mm]	40																			
Outer diameter [mm]	80																			
Width [mm]	10																			
<b>OE No.</b>																				
MAZDA	9960-30-208																			
KH00138 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>22</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09269-35009</td> </tr> </table>	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	22	<b>OE No.</b>		SUZUKI	09269-35009								
Inner diameter [mm]	35																			
Outer diameter [mm]	72																			
Width [mm]	22																			
<b>OE No.</b>																				
SUZUKI	09269-35009																			
KH00139 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080900</td> </tr> <tr> <td>Fitting Position</td> <td>Rear Axle</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>16</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUZUKI</td> <td>09262-30103</td> </tr> </table>	EAN	192661080900	Fitting Position	Rear Axle	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	16	<b>OE No.</b>		SUZUKI	09262-30103				
EAN	192661080900																			
Fitting Position	Rear Axle																			
Inner diameter [mm]	30																			
Outer diameter [mm]	62																			
Width [mm]	16																			
<b>OE No.</b>																				
SUZUKI	09262-30103																			







Part Number	Pk.	Description
<p>KH00140</p> 	1	<p>EAN   192661080917</p> <p>Fitting Position   Front Axle</p> <p>Inner diameter 1 [mm]   1.78</p> <p>Inner diameter 2 [mm]   55</p> <p>Outer diameter 1 [mm]   2.89</p> <p>Outer diameter 2 [mm]   90</p> <p>Width 1 [mm]   1.62</p> <p>Width 2 [mm]   22</p> <p><b>OE No.</b></p> <p>TOYOTA   90080-36067, 90080-36098</p>
<p>KH10001</p> 	1	<p>EAN   29176971891</p> <p>Inner diameter [mm]   40</p> <p>Outer diameter [mm]   74</p> <p>Width [mm]   40</p> <p><b>OE No.</b></p> <p>AUDI   1J0 498 625, 1J0 598 625</p> <p>SEAT   1J0 498 625, 1J0 598 625</p> <p>SKODA   1J0 498 625, 1J0 598 625</p> <p>VAG   1J0 498 625, 1J0 598 625</p> <p>VW   1J0 407 625 C, 1J0 498 625, 1J0 598 625</p>
<p>KH10002</p> 	1	<p>EAN   29176973420</p> <p>Inner diameter [mm]   40</p> <p>Outer diameter [mm]   74</p> <p>Width [mm]   42</p> <p><b>OE No.</b></p> <p>TOYOTA   90080-36087, 90080-36137, 90363-40066, 90363-40067</p>
<p>KH10003</p> 	1	<p>EAN   29176974526</p> <p>Inner diameter [mm]   40</p> <p>Outer diameter [mm]   74</p> <p>Width [mm]   36</p> <p><b>OE No.</b></p> <p>NISSAN   40210-4M400, 40210-4Z000</p>
<p>KH10004</p> 	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   29176974533</p> <p>Inner diameter [mm]   49</p> <p>Outer diameter [mm]   88</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   48</p> <p><b>OE No.</b></p> <p>VW   2H0 407 627 A, 2H0 498 627, 2H0 498 627 A</p>

Part Number	Pk.	Description																		
<p>KH10005</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176975141</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90369-43008</td> </tr> </table>	EAN	29176975141	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	45	<b>OE No.</b>		TOYOTA	90369-43008						
EAN	29176975141																			
Inner diameter [mm]	43																			
Outer diameter [mm]	82																			
Width [mm]	45																			
<b>OE No.</b>																				
TOYOTA	90369-43008																			
<p>KH10006</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176978104</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>83</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350.82</td> </tr> <tr> <td>DS</td> <td>3350.82</td> </tr> <tr> <td>PEUGEOT</td> <td>3350.82, 3350.98</td> </tr> </table>	EAN	29176978104	Inner diameter [mm]	45	Outer diameter [mm]	83	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	44	<b>OE No.</b>		CITROËN	3350.82	DS	3350.82	PEUGEOT	3350.82, 3350.98
EAN	29176978104																			
Inner diameter [mm]	45																			
Outer diameter [mm]	83																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	44																			
<b>OE No.</b>																				
CITROËN	3350.82																			
DS	3350.82																			
PEUGEOT	3350.82, 3350.98																			
<p>KH10007</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013038</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 1 130 617, 33 41 2 220 987</td> </tr> </table>	EAN	192661013038	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		BMW	33 41 1 130 617, 33 41 2 220 987						
EAN	192661013038																			
Inner diameter [mm]	42																			
Outer diameter [mm]	75																			
Width [mm]	37																			
<b>OE No.</b>																				
BMW	33 41 1 130 617, 33 41 2 220 987																			
<p>KH10008</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176974540</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>85</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 6 762 321, 33 41 6 775 842</td> </tr> </table>	EAN	29176974540	Inner diameter [mm]	45	Outer diameter [mm]	85	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41	<b>OE No.</b>		BMW	33 41 6 762 321, 33 41 6 775 842				
EAN	29176974540																			
Inner diameter [mm]	45																			
Outer diameter [mm]	85																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	41																			
<b>OE No.</b>																				
BMW	33 41 6 762 321, 33 41 6 775 842																			
<p>KH10009</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176974557</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width 1 [mm]</td> <td>35</td> </tr> <tr> <td>Width 2 [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40210-30R01, 40210-30R06, 40210-32R01, 40210-32R06, 40210-90J00</td> </tr> </table>	EAN	29176974557	Inner diameter [mm]	42	Outer diameter [mm]	79	Width 1 [mm]	35	Width 2 [mm]	38	<b>OE No.</b>		NISSAN	40210-30R01, 40210-30R06, 40210-32R01, 40210-32R06, 40210-90J00				
EAN	29176974557																			
Inner diameter [mm]	42																			
Outer diameter [mm]	79																			
Width 1 [mm]	35																			
Width 2 [mm]	38																			
<b>OE No.</b>																				
NISSAN	40210-30R01, 40210-30R06, 40210-32R01, 40210-32R06, 40210-90J00																			










Part Number	Pk.	Description																
<p>KH10010</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975158</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SEAT</td> <td>1S0 498 625, 1S0 498 625A</td> </tr> <tr> <td>SKODA</td> <td>1S0 498 625, 1S0 498 625A</td> </tr> <tr> <td>VW</td> <td>1S0 407 625, 1S0 498 625, 1S0 498 625A</td> </tr> </table>	EAN	29176975158	Inner diameter [mm]	35	Outer diameter [mm]	66	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	SEAT	1S0 498 625, 1S0 498 625A	SKODA	1S0 498 625, 1S0 498 625A	VW	1S0 407 625, 1S0 498 625, 1S0 498 625A
EAN	29176975158																	
Inner diameter [mm]	35																	
Outer diameter [mm]	66																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	37																	
SEAT	1S0 498 625, 1S0 498 625A																	
SKODA	1S0 498 625, 1S0 498 625A																	
VW	1S0 407 625, 1S0 498 625, 1S0 498 625A																	
<p>KH10011</p>	1	<table border="1"> <tr> <td>EAN</td> <td>29176975165</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>3M34 1215 AA, 4432022</td> </tr> <tr> <td>MAZDA</td> <td>UM51 33 047</td> </tr> </table>	EAN	29176975165	Inner diameter [mm]	47	Outer diameter [mm]	88	Width [mm]	55	FORD	3M34 1215 AA, 4432022	MAZDA	UM51 33 047				
EAN	29176975165																	
Inner diameter [mm]	47																	
Outer diameter [mm]	88																	
Width [mm]	55																	
FORD	3M34 1215 AA, 4432022																	
MAZDA	UM51 33 047																	
<p>KH10013</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176989834</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>RENAULT</td> <td>40030-3865R, 40210-5733R</td> </tr> </table>	EAN	29176989834	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	RENAULT	40030-3865R, 40210-5733R				
EAN	29176989834																	
Inner diameter [mm]	37																	
Outer diameter [mm]	72																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	37																	
RENAULT	40030-3865R, 40210-5733R																	
<p>KH10014</p>	1	<table border="1"> <tr> <td>EAN</td> <td>29176975936</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>71</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>TOYOTA</td> <td>90369-38021, 90369-38022</td> </tr> </table>	EAN	29176975936	Inner diameter [mm]	38	Outer diameter [mm]	71	Width [mm]	39	TOYOTA	90369-38021, 90369-38022						
EAN	29176975936																	
Inner diameter [mm]	38																	
Outer diameter [mm]	71																	
Width [mm]	39																	
TOYOTA	90369-38021, 90369-38022																	
<p>KH10016</p>	1	<table border="1"> <tr> <td>EAN</td> <td>29176980978</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>KIA</td> <td>0K2 JT 33047, 0K9 A2 33047, KGA 2A 33047</td> </tr> <tr> <td>MAZDA</td> <td>FB01 26 151 A, FB01 26 151 B, FB01 26 151 C, FB01 26 151 D, FB01 26 151 E, FB01 26 151 F, GA2A 33047</td> </tr> </table>	EAN	29176980978	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	45	KIA	0K2 JT 33047, 0K9 A2 33047, KGA 2A 33047	MAZDA	FB01 26 151 A, FB01 26 151 B, FB01 26 151 C, FB01 26 151 D, FB01 26 151 E, FB01 26 151 F, GA2A 33047				
EAN	29176980978																	
Inner diameter [mm]	42																	
Outer diameter [mm]	80																	
Width [mm]	45																	
KIA	0K2 JT 33047, 0K9 A2 33047, KGA 2A 33047																	
MAZDA	FB01 26 151 A, FB01 26 151 B, FB01 26 151 C, FB01 26 151 D, FB01 26 151 E, FB01 26 151 F, GA2A 33047																	






Part Number	Pk.	Description														
<p>KH10017</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176989476</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>B 4553 3047 C, B 4553 3047 D</td> </tr> </table>	EAN	29176989476	Inner diameter [mm]	40	Outer diameter [mm]	74	Width [mm]	40	<b>OE No.</b>		MAZDA	B 4553 3047 C, B 4553 3047 D		
EAN	29176989476															
Inner diameter [mm]	40															
Outer diameter [mm]	74															
Width [mm]	40															
<b>OE No.</b>																
MAZDA	B 4553 3047 C, B 4553 3047 D															
<p>KH10018</p> 	1	<p><b>Safety information</b>  This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176989841</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>73</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>44300-SAA-003, 44300-SCA-E51</td> </tr> </table>	EAN	29176989841	Inner diameter [mm]	38	Outer diameter [mm]	73	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	40	<b>OE No.</b>		HONDA	44300-SAA-003, 44300-SCA-E51
EAN	29176989841															
Inner diameter [mm]	38															
Outer diameter [mm]	73															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	40															
<b>OE No.</b>																
HONDA	44300-SAA-003, 44300-SCA-E51															
<p>KH10019</p> 	1	<p><b>Safety information</b>  This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176980831</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90363-40079</td> </tr> </table>	EAN	29176980831	Inner diameter [mm]	40	Outer diameter [mm]	75	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	<b>OE No.</b>		TOYOTA	90363-40079
EAN	29176980831															
Inner diameter [mm]	40															
Outer diameter [mm]	75															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	39															
<b>OE No.</b>																
TOYOTA	90363-40079															
<p>KH10021</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176978111</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90363-W0001, 90369-T0004, 90369-T0007</td> </tr> </table>	EAN	29176978111	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	45	<b>OE No.</b>		TOYOTA	90363-W0001, 90369-T0004, 90369-T0007		
EAN	29176978111															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Width [mm]	45															
<b>OE No.</b>																
TOYOTA	90363-W0001, 90369-T0004, 90369-T0007															








Part Number	Pk.	Description												
<p>KH10022</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176980848</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>• 45 • 84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>71742699</td> </tr> <tr> <td>SUZUKI</td> <td>43440-56K00, 43440-79J00, 43440-80J00</td> </tr> </table>	EAN	29176980848	Inner diameter [mm]	• 45 • 84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	FIAT	71742699	SUZUKI	43440-56K00, 43440-79J00, 43440-80J00
EAN	29176980848													
Inner diameter [mm]	• 45 • 84													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	39													
FIAT	71742699													
SUZUKI	43440-56K00, 43440-79J00, 43440-80J00													
<p>KH10023</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176994104</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LEXUS</td> <td>90369-38019</td> </tr> </table>	EAN	29176994104	Inner diameter [mm]	38	Outer diameter [mm]	74	Width [mm]	33	LEXUS	90369-38019		
EAN	29176994104													
Inner diameter [mm]	38													
Outer diameter [mm]	74													
Width [mm]	33													
LEXUS	90369-38019													
<p>KH10024</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176994111</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>44300-S5A-008, 44300-S6D-E01, 44300-S6D-E011, 44300-S6D-E012-M1, 44300-SR3-A01, 44300-ST3-E01</td> </tr> </table>	EAN	29176994111	Inner diameter [mm]	43	Outer diameter [mm]	79	Width [mm]	38	HONDA	44300-S5A-008, 44300-S6D-E01, 44300-S6D-E011, 44300-S6D-E012-M1, 44300-SR3-A01, 44300-ST3-E01		
EAN	29176994111													
Inner diameter [mm]	43													
Outer diameter [mm]	79													
Width [mm]	38													
HONDA	44300-S5A-008, 44300-S6D-E01, 44300-S6D-E011, 44300-S6D-E012-M1, 44300-SR3-A01, 44300-ST3-E01													
<p>KH10025</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010327</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LEXUS</td> <td>90369-45006, 90369-A0002</td> </tr> <tr> <td>TOYOTA</td> <td>90369-A0002</td> </tr> </table>	EAN	192661010327	Inner diameter [mm]	45	Outer diameter [mm]	86	Width [mm]	45	LEXUS	90369-45006, 90369-A0002	TOYOTA	90369-A0002
EAN	192661010327													
Inner diameter [mm]	45													
Outer diameter [mm]	86													
Width [mm]	45													
LEXUS	90369-45006, 90369-A0002													
TOYOTA	90369-A0002													
<p>KH10026</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176994142</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>43210 AG000</td> </tr> </table>	EAN	29176994142	Inner diameter [mm]	43	Outer diameter [mm]	79	Width [mm]	45	NISSAN	43210 AG000		
EAN	29176994142													
Inner diameter [mm]	43													
Outer diameter [mm]	79													
Width [mm]	45													
NISSAN	43210 AG000													





Part Number	Pk.	Description														
KH10027	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010334</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>16 101 376 80</td> </tr> <tr> <td>PEUGEOT</td> <td>16 101 376 80</td> </tr> </table>	EAN	192661010334	Inner diameter [mm]	42	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	44	CITROËN	16 101 376 80	PEUGEOT	16 101 376 80
EAN	192661010334															
Inner diameter [mm]	42															
Outer diameter [mm]	80															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	44															
CITROËN	16 101 376 80															
PEUGEOT	16 101 376 80															
KH10028	1	<table border="1"> <tr> <td>EAN</td> <td>192661010341</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>44300-S1A-E01</td> </tr> </table>	EAN	192661010341	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	40	HONDA	44300-S1A-E01				
EAN	192661010341															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Width [mm]	40															
HONDA	44300-S1A-E01															
KH10029	1	<table border="1"> <tr> <td>EAN</td> <td>192661010358</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>44300-S1A-E01</td> </tr> </table>	EAN	192661010358	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	40	HONDA	44300-S1A-E01				
EAN	192661010358															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Width [mm]	40															
HONDA	44300-S1A-E01															
KH10030	1	<table border="1"> <tr> <td>EAN</td> <td>192661010365</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>58</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>47 11 556, 95507796</td> </tr> <tr> <td>SUZUKI</td> <td>46860 62J00, 46860 62J01, 46860 63J00, 46860 63J01</td> </tr> <tr> <td>VAUXHALL</td> <td>47 11 556, 95507796</td> </tr> </table>	EAN	192661010365	Inner diameter [mm]	28	Outer diameter [mm]	58	Width [mm]	44	OPEL	47 11 556, 95507796	SUZUKI	46860 62J00, 46860 62J01, 46860 63J00, 46860 63J01	VAUXHALL	47 11 556, 95507796
EAN	192661010365															
Inner diameter [mm]	28															
Outer diameter [mm]	58															
Width [mm]	44															
OPEL	47 11 556, 95507796															
SUZUKI	46860 62J00, 46860 62J01, 46860 63J00, 46860 63J01															
VAUXHALL	47 11 556, 95507796															
KH10031	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661041611</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>44300-TF0-951</td> </tr> </table>	EAN	192661041611	Inner diameter [mm]	38	Outer diameter [mm]	74	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	40	HONDA	44300-TF0-951		
EAN	192661041611															
Inner diameter [mm]	38															
Outer diameter [mm]	74															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	40															
HONDA	44300-TF0-951															








Part Number	Pk.	Description																
KH10032 	1	<table border="1"> <tr> <td>EAN</td> <td>192661043363</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>58</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>3785-A024</td> </tr> </table>	EAN	192661043363	Inner diameter [mm]	28	Outer diameter [mm]	58	Width [mm]	48	<b>OE No.</b>		MITSUBISHI	3785-A024				
EAN	192661043363																	
Inner diameter [mm]	28																	
Outer diameter [mm]	58																	
Width [mm]	48																	
<b>OE No.</b>																		
MITSUBISHI	3785-A024																	
KH10033 	1	<table border="1"> <tr> <td>EAN</td> <td>192661024034</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-4A00A, 43210-4A00D</td> </tr> <tr> <td>SUZUKI</td> <td>46860-M68K00, 46860-M68K01, 46860-M68K10</td> </tr> </table>	EAN	192661024034	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	42	<b>OE No.</b>		NISSAN	43210-4A00A, 43210-4A00D	SUZUKI	46860-M68K00, 46860-M68K01, 46860-M68K10		
EAN	192661024034																	
Inner diameter [mm]	25																	
Outer diameter [mm]	52																	
Width [mm]	42																	
<b>OE No.</b>																		
NISSAN	43210-4A00A, 43210-4A00D																	
SUZUKI	46860-M68K00, 46860-M68K01, 46860-M68K10																	
KH10034 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010372</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40210-2Y000</td> </tr> </table>	EAN	192661010372	Inner diameter [mm]	43	Outer diameter [mm]	76	Width [mm]	43	<b>OE No.</b>		NISSAN	40210-2Y000				
EAN	192661010372																	
Inner diameter [mm]	43																	
Outer diameter [mm]	76																	
Width [mm]	43																	
<b>OE No.</b>																		
NISSAN	40210-2Y000																	
KH10035 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176994159</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width 1 [mm]</td> <td>40</td> </tr> <tr> <td>Width 2 [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>44300-S9A-003</td> </tr> </table>	EAN	29176994159	Inner diameter [mm]	45	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width 1 [mm]	40	Width 2 [mm]	42	<b>OE No.</b>		HONDA	44300-S9A-003
EAN	29176994159																	
Inner diameter [mm]	45																	
Outer diameter [mm]	84																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width 1 [mm]	40																	
Width 2 [mm]	42																	
<b>OE No.</b>																		
HONDA	44300-S9A-003																	
KH10037 	1	<table border="1"> <tr> <td>EAN</td> <td>192661012161</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>53</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1201568, 2SJ-1A049-AA</td> </tr> </table>	EAN	192661012161	Inner diameter [mm]	29	Outer diameter [mm]	53	Width [mm]	37	<b>OE No.</b>		FORD	1201568, 2SJ-1A049-AA				
EAN	192661012161																	
Inner diameter [mm]	29																	
Outer diameter [mm]	53																	
Width [mm]	37																	
<b>OE No.</b>																		
FORD	1201568, 2SJ-1A049-AA																	

Part Number	Pk.	Description																
<p>KH10038</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661012178</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1133023, 1S7-1K018-AA</td> </tr> <tr> <td>JAGUAR</td> <td>C2S8276</td> </tr> </table>	EAN	192661012178	Inner diameter [mm]	40	Outer diameter [mm]	75	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	FORD	1133023, 1S7-1K018-AA	JAGUAR	C2S8276		
EAN	192661012178																	
Inner diameter [mm]	40																	
Outer diameter [mm]	75																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	37																	
FORD	1133023, 1S7-1K018-AA																	
JAGUAR	C2S8276																	
<p>KH10039</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661012185</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44.98</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MERCEDES-BENZ</td> <td>A 129 980 02 16, A 129 980 03 16, A 202 980 00 16, A 202 980 01 16, A 202 981 01 27, A 203 980 00 16, A 209 980 00 16</td> </tr> </table>	EAN	192661012185	Inner diameter [mm]	44.98	Outer diameter [mm]	84	Width [mm]	39	MERCEDES-BENZ	A 129 980 02 16, A 129 980 03 16, A 202 980 00 16, A 202 980 01 16, A 202 981 01 27, A 203 980 00 16, A 209 980 00 16						
EAN	192661012185																	
Inner diameter [mm]	44.98																	
Outer diameter [mm]	84																	
Width [mm]	39																	
MERCEDES-BENZ	A 129 980 02 16, A 129 980 03 16, A 202 980 00 16, A 202 980 01 16, A 202 981 01 27, A 203 980 00 16, A 209 980 00 16																	
<p>KH10040</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661014561</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>51</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3748 94</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 94</td> </tr> <tr> <td>DS</td> <td>3748 94</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 94</td> </tr> </table>	EAN	192661014561	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	51	CITROËN	3748 94	CITROËN/PEUGEOT	3748 94	DS	3748 94	PEUGEOT	3748 94
EAN	192661014561																	
Inner diameter [mm]	30																	
Outer diameter [mm]	62																	
Width [mm]	51																	
CITROËN	3748 94																	
CITROËN/PEUGEOT	3748 94																	
DS	3748 94																	
PEUGEOT	3748 94																	
<p>KH10041</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661012192</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>5027620, 93BX-1K018-AA</td> </tr> </table>	EAN	192661012192	Inner diameter [mm]	40	Outer diameter [mm]	75	Width [mm]	37	FORD	5027620, 93BX-1K018-AA						
EAN	192661012192																	
Inner diameter [mm]	40																	
Outer diameter [mm]	75																	
Width [mm]	37																	
FORD	5027620, 93BX-1K018-AA																	
<p>KH10042</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661012208</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72.04</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 03 337, 93188889</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 337, 93188889</td> </tr> </table>	EAN	192661012208	Inner diameter [mm]	35	Outer diameter [mm]	72.04	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	33	OPEL	16 03 337, 93188889	VAUXHALL	16 03 337, 93188889		
EAN	192661012208																	
Inner diameter [mm]	35																	
Outer diameter [mm]	72.04																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	33																	
OPEL	16 03 337, 93188889																	
VAUXHALL	16 03 337, 93188889																	













Part Number	Pk.	Description																		
<p>KH10043</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010389</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3326 72, 3326 76</td> </tr> <tr> <td>FIAT</td> <td>46773660, 51753790, 71714459, 71745046, 71753062</td> </tr> <tr> <td>LANCIA</td> <td>46773660, 51753790, 71714459, 71745046, 71753062</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 72, 3326 76</td> </tr> </table>	EAN	192661010389	Inner diameter [mm]	35	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	33	CITROËN	3326 72, 3326 76	FIAT	46773660, 51753790, 71714459, 71745046, 71753062	LANCIA	46773660, 51753790, 71714459, 71745046, 71753062	PEUGEOT	3326 72, 3326 76
EAN	192661010389																			
Inner diameter [mm]	35																			
Outer diameter [mm]	72																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	33																			
CITROËN	3326 72, 3326 76																			
FIAT	46773660, 51753790, 71714459, 71745046, 71753062																			
LANCIA	46773660, 51753790, 71714459, 71745046, 71753062																			
PEUGEOT	3326 72, 3326 76																			
<p>KH10044</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661011638</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>46528566, 46773659, 5890990, 71714468, 7555466</td> </tr> <tr> <td>LANCIA</td> <td>46528566, 46773659, 5890990, 71714468, 7555466</td> </tr> </table>	EAN	192661011638	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	33	FIAT	46528566, 46773659, 5890990, 71714468, 7555466	LANCIA	46528566, 46773659, 5890990, 71714468, 7555466						
EAN	192661011638																			
Inner diameter [mm]	35																			
Outer diameter [mm]	72																			
Width [mm]	33																			
FIAT	46528566, 46773659, 5890990, 71714468, 7555466																			
LANCIA	46528566, 46773659, 5890990, 71714468, 7555466																			
<p>KH10046</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661013571</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1085569, 1112547, 1201569, 1513043, 2S6J-1K018-BA, 8V51-1215-AB, 98AX-1K018-BA, 98AX-1K018-BB</td> </tr> </table>	EAN	192661013571	Inner diameter [mm]	39	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	FORD	1085569, 1112547, 1201569, 1513043, 2S6J-1K018-BA, 8V51-1215-AB, 98AX-1K018-BA, 98AX-1K018-BB						
EAN	192661013571																			
Inner diameter [mm]	39																			
Outer diameter [mm]	72																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	37																			
FORD	1085569, 1112547, 1201569, 1513043, 2S6J-1K018-BA, 8V51-1215-AB, 98AX-1K018-BA, 98AX-1K018-BB																			
<p>KH10047</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661011645</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>16 066 235 80, 3350.69, 3350.84, 3350.97</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>16 066 235 80, 3350.69, 3350.84, 3350.97</td> </tr> <tr> <td>DS</td> <td>16 066 235 80, 3350.69, 3350.84, 3350.97</td> </tr> <tr> <td>PEUGEOT</td> <td>16 066 235 80, 3350.69, 3350.84, 3350.97</td> </tr> </table>	EAN	192661011645	Inner diameter [mm]	42	Outer diameter [mm]	82	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	36	CITROËN	16 066 235 80, 3350.69, 3350.84, 3350.97	CITROËN/PEUGEOT	16 066 235 80, 3350.69, 3350.84, 3350.97	DS	16 066 235 80, 3350.69, 3350.84, 3350.97	PEUGEOT	16 066 235 80, 3350.69, 3350.84, 3350.97
EAN	192661011645																			
Inner diameter [mm]	42																			
Outer diameter [mm]	82																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	36																			
CITROËN	16 066 235 80, 3350.69, 3350.84, 3350.97																			
CITROËN/PEUGEOT	16 066 235 80, 3350.69, 3350.84, 3350.97																			
DS	16 066 235 80, 3350.69, 3350.84, 3350.97																			
PEUGEOT	16 066 235 80, 3350.69, 3350.84, 3350.97																			

Part Number	Pk.	Description																		
KH10048 	1	<table border="1"> <tr> <td>EAN</td> <td>192661011652</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 90</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 90</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 90</td> </tr> </table>	EAN	192661011652	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	48	<b>OE No.</b>		CITROËN	3748 90	CITROËN/PEUGEOT	3748 90	PEUGEOT	3748 90		
EAN	192661011652																			
Inner diameter [mm]	30																			
Outer diameter [mm]	62																			
Width [mm]	48																			
<b>OE No.</b>																				
CITROËN	3748 90																			
CITROËN/PEUGEOT	3748 90																			
PEUGEOT	3748 90																			
KH10049 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661013045</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 169 981 00 06, A 169 981 01 27</td> </tr> </table>	EAN	192661013045	Inner diameter [mm]	45	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 169 981 00 06, A 169 981 01 27				
EAN	192661013045																			
Inner diameter [mm]	45																			
Outer diameter [mm]	84																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	39																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 169 981 00 06, A 169 981 01 27																			
KH10050 	1	<table border="1"> <tr> <td>EAN</td> <td>192661016954</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>37</td> </tr> <tr> <td>Width [mm]</td> <td>72</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1061596, 98-AB1215-AB</td> </tr> </table>	EAN	192661016954	Inner diameter [mm]	39	Outer diameter [mm]	37	Width [mm]	72	<b>OE No.</b>		FORD	1061596, 98-AB1215-AB						
EAN	192661016954																			
Inner diameter [mm]	39																			
Outer diameter [mm]	37																			
Width [mm]	72																			
<b>OE No.</b>																				
FORD	1061596, 98-AB1215-AB																			
KH10051 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013052</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3326 31, 3350 17, 95 654 076</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3326 31, 3350 17, 95 654 076</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 31, 3350 17, 95 654 076</td> </tr> </table>	EAN	192661013052	Inner diameter [mm]	35	Outer diameter [mm]	72	Rim Hole Number	4	Width [mm]	33	<b>OE No.</b>		CITROËN	3326 31, 3350 17, 95 654 076	CITROËN/PEUGEOT	3326 31, 3350 17, 95 654 076	PEUGEOT	3326 31, 3350 17, 95 654 076
EAN	192661013052																			
Inner diameter [mm]	35																			
Outer diameter [mm]	72																			
Rim Hole Number	4																			
Width [mm]	33																			
<b>OE No.</b>																				
CITROËN	3326 31, 3350 17, 95 654 076																			
CITROËN/PEUGEOT	3326 31, 3350 17, 95 654 076																			
PEUGEOT	3326 31, 3350 17, 95 654 076																			
KH10052 	1	<table border="1"> <tr> <td>EAN</td> <td>192661011669</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 16, 3350 33, 95 619 160</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3350 16, 3350 33, 95 619 160</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 16, 3350 33, 95 619 160</td> </tr> </table>	EAN	192661011669	Inner diameter [mm]	42	Outer diameter [mm]	82	Width [mm]	36	<b>OE No.</b>		CITROËN	3350 16, 3350 33, 95 619 160	CITROËN/PEUGEOT	3350 16, 3350 33, 95 619 160	PEUGEOT	3350 16, 3350 33, 95 619 160		
EAN	192661011669																			
Inner diameter [mm]	42																			
Outer diameter [mm]	82																			
Width [mm]	36																			
<b>OE No.</b>																				
CITROËN	3350 16, 3350 33, 95 619 160																			
CITROËN/PEUGEOT	3350 16, 3350 33, 95 619 160																			
PEUGEOT	3350 16, 3350 33, 95 619 160																			














Part Number	Pk.	Description																				
<p>KH10053</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661011676</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 32</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3350 32</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 32</td> </tr> </table>	EAN	192661011676	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	33	<b>OE No.</b>		CITROËN	3350 32	CITROËN/PEUGEOT	3350 32	PEUGEOT	3350 32				
EAN	192661011676																					
Inner diameter [mm]	37																					
Outer diameter [mm]	72																					
Width [mm]	33																					
<b>OE No.</b>																						
CITROËN	3350 32																					
CITROËN/PEUGEOT	3350 32																					
PEUGEOT	3350 32																					
<p>KH10054</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661011683</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 72, 3350 86, 3350 92</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3350 72, 3350 86, 3350 92</td> </tr> <tr> <td>DS</td> <td>3350 72, 3350 86, 3350 92</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 72, 3350 86, 3350 92</td> </tr> </table>	EAN	192661011683	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	33	<b>OE No.</b>		CITROËN	3350 72, 3350 86, 3350 92	CITROËN/PEUGEOT	3350 72, 3350 86, 3350 92	DS	3350 72, 3350 86, 3350 92	PEUGEOT	3350 72, 3350 86, 3350 92
EAN	192661011683																					
Inner diameter [mm]	37																					
Outer diameter [mm]	72																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	33																					
<b>OE No.</b>																						
CITROËN	3350 72, 3350 86, 3350 92																					
CITROËN/PEUGEOT	3350 72, 3350 86, 3350 92																					
DS	3350 72, 3350 86, 3350 92																					
PEUGEOT	3350 72, 3350 86, 3350 92																					
<p>KH10055</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661011690</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C</td> </tr> <tr> <td>SEAT</td> <td>191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C</td> </tr> <tr> <td>VW</td> <td>191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C</td> </tr> </table>	EAN	192661011690	Inner diameter [mm]	40	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		AUDI	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C	SEAT	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C	VW	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C				
EAN	192661011690																					
Inner diameter [mm]	40																					
Outer diameter [mm]	72																					
Width [mm]	37																					
<b>OE No.</b>																						
AUDI	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C																					
SEAT	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C																					
VW	191 498 625 A, 357 407 625, 357 498 625 B, 357 498 625 C																					
<p>KH10056</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013069</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 39, 3748 77</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 39, 3748 77</td> </tr> </table>	EAN	192661013069	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	37	<b>OE No.</b>		CITROËN	3748 39, 3748 77	PEUGEOT	3748 39, 3748 77						
EAN	192661013069																					
Inner diameter [mm]	25																					
Outer diameter [mm]	52																					
Width [mm]	37																					
<b>OE No.</b>																						
CITROËN	3748 39, 3748 77																					
PEUGEOT	3748 39, 3748 77																					
<p>KH10057</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013076</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40210-00QAA</td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 779</td> </tr> </table>	EAN	192661013076	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		NISSAN	40210-00QAA	RENAULT	77 01 205 779						
EAN	192661013076																					
Inner diameter [mm]	37																					
Outer diameter [mm]	72																					
Width [mm]	37																					
<b>OE No.</b>																						
NISSAN	40210-00QAA																					
RENAULT	77 01 205 779																					

Part Number	Pk.	Description														
KH10058 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013083</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>60 01 547 696</td> </tr> <tr> <td>RENAULT</td> <td>60 01 547 696</td> </tr> </table>	EAN	192661013083	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		DACIA	60 01 547 696	RENAULT	60 01 547 696
EAN	192661013083															
Inner diameter [mm]	37															
Outer diameter [mm]	72															
Width [mm]	37															
<b>OE No.</b>																
DACIA	60 01 547 696															
RENAULT	60 01 547 696															
KH10060 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013090</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VW</td> <td>191 498 625</td> </tr> </table>	EAN	192661013090	Inner diameter [mm]	35	Outer diameter [mm]	66	Width [mm]	37	<b>OE No.</b>		VW	191 498 625		
EAN	192661013090															
Inner diameter [mm]	35															
Outer diameter [mm]	66															
Width [mm]	37															
<b>OE No.</b>																
VW	191 498 625															
KH10061 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013809</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 6 762 317, 6762317</td> </tr> </table>	EAN	192661013809	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		BMW	33 41 6 762 317, 6762317		
EAN	192661013809															
Inner diameter [mm]	42															
Outer diameter [mm]	75															
Width [mm]	37															
<b>OE No.</b>																
BMW	33 41 6 762 317, 6762317															
KH10062 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013595</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>32</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 18, 95603182</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 18, 95603182</td> </tr> </table>	EAN	192661013595	Inner diameter [mm]	35	Outer diameter [mm]	66	Width [mm]	32	<b>OE No.</b>		CITROËN	3350 18, 95603182	PEUGEOT	3350 18, 95603182
EAN	192661013595															
Inner diameter [mm]	35															
Outer diameter [mm]	66															
Width [mm]	32															
<b>OE No.</b>																
CITROËN	3350 18, 95603182															
PEUGEOT	3350 18, 95603182															
KH10063 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013601</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>67</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>328980, 9195608</td> </tr> <tr> <td>VAUXHALL</td> <td>328980, 9195608</td> </tr> </table>	EAN	192661013601	Inner diameter [mm]	34	Outer diameter [mm]	67	Width [mm]	37	<b>OE No.</b>		OPEL	328980, 9195608	VAUXHALL	328980, 9195608
EAN	192661013601															
Inner diameter [mm]	34															
Outer diameter [mm]	67															
Width [mm]	37															
<b>OE No.</b>																
OPEL	328980, 9195608															
VAUXHALL	328980, 9195608															








Part Number	Pk.	Description																												
<p>KH10064</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661014684</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45.3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-00QAB</td> </tr> <tr> <td>OPEL</td> <td>44 030 44, 9111044</td> </tr> <tr> <td>RENAULT</td> <td>77 01 206 742</td> </tr> <tr> <td>VAUXHALL</td> <td>44 030 44, 9111044</td> </tr> </table>	EAN	192661014684	Inner diameter [mm]	45.3	Outer diameter [mm]	80	Width [mm]	48	<b>OE No.</b>		NISSAN	43210-00QAB	OPEL	44 030 44, 9111044	RENAULT	77 01 206 742	VAUXHALL	44 030 44, 9111044										
EAN	192661014684																													
Inner diameter [mm]	45.3																													
Outer diameter [mm]	80																													
Width [mm]	48																													
<b>OE No.</b>																														
NISSAN	43210-00QAB																													
OPEL	44 030 44, 9111044																													
RENAULT	77 01 206 742																													
VAUXHALL	44 030 44, 9111044																													
<p>KH10065</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013618</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ABARTH</td> <td>46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047</td> </tr> <tr> <td>ALFA ROMEO</td> <td>46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047</td> </tr> <tr> <td>CITROËN</td> <td>3326 75, 3326 77</td> </tr> <tr> <td>FIAT</td> <td>46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047</td> </tr> <tr> <td>FORD</td> <td>9S51J-1K018-BA</td> </tr> <tr> <td>LANCIA</td> <td>46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047</td> </tr> <tr> <td>OPEL</td> <td>16 03 338, 93188890</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 75, 3326 77</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 338, 93188890</td> </tr> </table>	EAN	192661013618	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		ABARTH	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047	ALFA ROMEO	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047	CITROËN	3326 75, 3326 77	FIAT	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047	FORD	9S51J-1K018-BA	LANCIA	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047	OPEL	16 03 338, 93188890	PEUGEOT	3326 75, 3326 77	VAUXHALL	16 03 338, 93188890
EAN	192661013618																													
Inner diameter [mm]	37																													
Outer diameter [mm]	72																													
Width [mm]	37																													
<b>OE No.</b>																														
ABARTH	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047																													
ALFA ROMEO	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047																													
CITROËN	3326 75, 3326 77																													
FIAT	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047																													
FORD	9S51J-1K018-BA																													
LANCIA	46512970, 46773662, 51753791, 55703171, 60815375, 60815492, 71745047																													
OPEL	16 03 338, 93188890																													
PEUGEOT	3326 75, 3326 77																													
VAUXHALL	16 03 338, 93188890																													
<p>KH10066</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661016961</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>4B0 498 625</td> </tr> <tr> <td>SKODA</td> <td>4B0 498 625</td> </tr> <tr> <td>VW</td> <td>4B0 498 625</td> </tr> </table>	EAN	192661016961	Inner diameter [mm]	39	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		AUDI	4B0 498 625	SKODA	4B0 498 625	VW	4B0 498 625												
EAN	192661016961																													
Inner diameter [mm]	39																													
Outer diameter [mm]	75																													
Width [mm]	37																													
<b>OE No.</b>																														
AUDI	4B0 498 625																													
SKODA	4B0 498 625																													
VW	4B0 498 625																													
<p>KH10069</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661023204</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>4A0 498 625, 4B0 498 625 A</td> </tr> <tr> <td>SKODA</td> <td>4A0 498 625, 4B0 498 625 A</td> </tr> <tr> <td>VW</td> <td>4A0 498 625, 4B0 498 625 A</td> </tr> </table>	EAN	192661023204	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	37	<b>OE No.</b>		AUDI	4A0 498 625, 4B0 498 625 A	SKODA	4A0 498 625, 4B0 498 625 A	VW	4A0 498 625, 4B0 498 625 A												
EAN	192661023204																													
Inner diameter [mm]	43																													
Outer diameter [mm]	82																													
Width [mm]	37																													
<b>OE No.</b>																														
AUDI	4A0 498 625, 4B0 498 625 A																													
SKODA	4A0 498 625, 4B0 498 625 A																													
VW	4A0 498 625, 4B0 498 625 A																													

Part Number	Pk.	Description														
<p>KH10070</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661019320</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1513043, 1582282, 1699368, 1746588, 2356115, 8V51-1215-AB, 8V5J-1K018-AA, ACP1-1215-AFA, ACP1-1215-AFB, HCPC-1K018-AA</td> </tr> <tr> <td>MAZDA</td> <td>D651-33-047A, D651-33-047B</td> </tr> </table>	EAN	192661019320	Inner diameter [mm]	39	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	FORD	1513043, 1582282, 1699368, 1746588, 2356115, 8V51-1215-AB, 8V5J-1K018-AA, ACP1-1215-AFA, ACP1-1215-AFB, HCPC-1K018-AA	MAZDA	D651-33-047A, D651-33-047B
EAN	192661019320															
Inner diameter [mm]	39															
Outer diameter [mm]	72															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	37															
FORD	1513043, 1582282, 1699368, 1746588, 2356115, 8V51-1215-AB, 8V5J-1K018-AA, ACP1-1215-AFA, ACP1-1215-AFB, HCPC-1K018-AA															
MAZDA	D651-33-047A, D651-33-047B															
<p>KH10072</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661023792</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>35</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SANTANA</td> <td>09269-41001, 43462-85C00</td> </tr> <tr> <td>SUZUKI</td> <td>09269-41001, 43462-85C00</td> </tr> </table>	EAN	192661023792	Inner diameter [mm]	41	Outer diameter [mm]	68	Width [mm]	35	SANTANA	09269-41001, 43462-85C00	SUZUKI	09269-41001, 43462-85C00		
EAN	192661023792															
Inner diameter [mm]	41															
Outer diameter [mm]	68															
Width [mm]	35															
SANTANA	09269-41001, 43462-85C00															
SUZUKI	09269-41001, 43462-85C00															
<p>KH10073</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661036693</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>DACIA</td> <td>77 01 205 812, 77 01 208 767, 77 01 465 735</td> </tr> <tr> <td>NISSAN</td> <td>43210-AX000, 43210-AZ300</td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 812, 77 01 208 767, 77 01 465 735</td> </tr> </table>	EAN	192661036693	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	37	DACIA	77 01 205 812, 77 01 208 767, 77 01 465 735	NISSAN	43210-AX000, 43210-AZ300	RENAULT	77 01 205 812, 77 01 208 767, 77 01 465 735
EAN	192661036693															
Inner diameter [mm]	25															
Outer diameter [mm]	52															
Width [mm]	37															
DACIA	77 01 205 812, 77 01 208 767, 77 01 465 735															
NISSAN	43210-AX000, 43210-AZ300															
RENAULT	77 01 205 812, 77 01 208 767, 77 01 465 735															
<p>KH10074</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661036709</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>RENAULT</td> <td>77 01 463 523, 77 03 090 313</td> </tr> </table>	EAN	192661036709	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	37	RENAULT	77 01 463 523, 77 03 090 313				
EAN	192661036709															
Inner diameter [mm]	25															
Outer diameter [mm]	52															
Width [mm]	37															
RENAULT	77 01 463 523, 77 03 090 313															
<p>KH10075</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661041628</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>65</td> </tr> <tr> <td>Width [mm]</td> <td>35</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>DACIA</td> <td>60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181</td> </tr> <tr> <td>RENAULT</td> <td>60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181</td> </tr> </table>	EAN	192661041628	Inner diameter [mm]	35	Outer diameter [mm]	65	Width [mm]	35	DACIA	60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181	RENAULT	60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181		
EAN	192661041628															
Inner diameter [mm]	35															
Outer diameter [mm]	65															
Width [mm]	35															
DACIA	60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181															
RENAULT	60 01 543 344, 77 01 205 778, 77 01 462 469, 77 01 465 181															








Part Number	Pk.	Description
<p>KH10076</p>	1	<p>EAN   192661036716</p> <p>Inner diameter [mm]   25</p> <p>Outer diameter [mm]   55</p> <p>Width [mm]   45</p> <p><b>OE No.</b></p> <p>DACIA   77 01 208 058</p> <p>RENAULT   77 01 208 058</p>
<p>KH10077</p>	1	<p>EAN   192661041635</p> <p>Inner diameter [mm]   25</p> <p>Outer diameter [mm]   55</p> <p>Width [mm]   43</p> <p><b>OE No.</b></p> <p>DACIA   77 01 210 004</p> <p>RENAULT   77 01 210 004</p>
<p>KH10078</p>	1	<p>EAN   192661036778</p> <p>Inner diameter [mm]   49</p> <p>Outer diameter [mm]   84</p> <p>Width [mm]   48</p> <p><b>OE No.</b></p> <p>CITROËN   3326 62</p> <p>FIAT   1328046080</p> <p>PEUGEOT   3326 62</p>
<p>KH10079</p>	1	<p>EAN   192661037584</p> <p>Inner diameter [mm]   25</p> <p>Outer diameter [mm]   60</p> <p>Width [mm]   45</p> <p><b>OE No.</b></p> <p>CITROËN   3748 83</p> <p>PEUGEOT   3748 83</p>
<p>KH10080</p>	1	<p>EAN   192661045176</p> <p>Inner diameter [mm]   42</p> <p>Outer diameter [mm]   80</p> <p>Width [mm]   39</p> <p><b>OE No.</b></p> <p>DACIA   40 21 070 49R, 40 21 080 22R</p> <p>RENAULT   40 21 070 49R, 40 21 080 22R</p>

Part Number	Pk.	Description																
KH10081 	1	<table border="1"> <tr> <td>EAN</td> <td>192661036785</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>56</td> </tr> <tr> <td>Width [mm]</td> <td>32</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 19, 95 654 077</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 19, 95 654 077</td> </tr> </table>	EAN	192661036785	Inner diameter [mm]	25	Outer diameter [mm]	56	Width [mm]	32	<b>OE No.</b>		CITROËN	3350 19, 95 654 077	PEUGEOT	3350 19, 95 654 077		
EAN	192661036785																	
Inner diameter [mm]	25																	
Outer diameter [mm]	56																	
Width [mm]	32																	
<b>OE No.</b>																		
CITROËN	3350 19, 95 654 077																	
PEUGEOT	3350 19, 95 654 077																	
KH10082 	1	<table border="1"> <tr> <td>EAN</td> <td>192661036792</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>55</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-00QAD</td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 596, 77 01 463 987</td> </tr> </table>	EAN	192661036792	Inner diameter [mm]	25	Outer diameter [mm]	55	Width [mm]	43	<b>OE No.</b>		NISSAN	43210-00QAD	RENAULT	77 01 205 596, 77 01 463 987		
EAN	192661036792																	
Inner diameter [mm]	25																	
Outer diameter [mm]	55																	
Width [mm]	43																	
<b>OE No.</b>																		
NISSAN	43210-00QAD																	
RENAULT	77 01 205 596, 77 01 463 987																	
KH10083 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052051</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 17</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 17</td> </tr> </table>	EAN	192661052051	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	37	<b>OE No.</b>		CITROËN	3748 17	PEUGEOT	3748 17		
EAN	192661052051																	
Inner diameter [mm]	25																	
Outer diameter [mm]	52																	
Width [mm]	37																	
<b>OE No.</b>																		
CITROËN	3748 17																	
PEUGEOT	3748 17																	
KH10084 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052068</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1001718, 1497386, 6M21-1A047-AA, 95VW-1A047-AA</td> </tr> <tr> <td>SEAT</td> <td>7M3 498 625, 7M3 498 625 A</td> </tr> <tr> <td>VW</td> <td>7M3 498 625, 7M3 498 625 A</td> </tr> </table>	EAN	192661052068	Inner diameter [mm]	43	Outer diameter [mm]	80	Width [mm]	38	<b>OE No.</b>		FORD	1001718, 1497386, 6M21-1A047-AA, 95VW-1A047-AA	SEAT	7M3 498 625, 7M3 498 625 A	VW	7M3 498 625, 7M3 498 625 A
EAN	192661052068																	
Inner diameter [mm]	43																	
Outer diameter [mm]	80																	
Width [mm]	38																	
<b>OE No.</b>																		
FORD	1001718, 1497386, 6M21-1A047-AA, 95VW-1A047-AA																	
SEAT	7M3 498 625, 7M3 498 625 A																	
VW	7M3 498 625, 7M3 498 625 A																	
KH10085 	1	<table border="1"> <tr> <td>EAN</td> <td>192661043370</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 780, 77 01 466 803, 77 01 467 860</td> </tr> </table>	EAN	192661043370	Inner diameter [mm]	40	Outer diameter [mm]	84	Width [mm]	38	<b>OE No.</b>		RENAULT	77 01 205 780, 77 01 466 803, 77 01 467 860				
EAN	192661043370																	
Inner diameter [mm]	40																	
Outer diameter [mm]	84																	
Width [mm]	38																	
<b>OE No.</b>																		
RENAULT	77 01 205 780, 77 01 466 803, 77 01 467 860																	













Part Number	Pk.	Description																		
<p>KH10086</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661037591</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 A1</td> </tr> <tr> <td>DS</td> <td>3748 A1</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 A1</td> </tr> </table>	EAN	192661037591	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	42	<b>OE No.</b>		CITROËN	3748 A1	DS	3748 A1	PEUGEOT	3748 A1		
EAN	192661037591																			
Inner diameter [mm]	25																			
Outer diameter [mm]	52																			
Width [mm]	42																			
<b>OE No.</b>																				
CITROËN	3748 A1																			
DS	3748 A1																			
PEUGEOT	3748 A1																			
<p>KH10089</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661041642</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82.5</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3326 40, 3350 27, 3350 91</td> </tr> <tr> <td>FIAT</td> <td>1330512080, 71714473, 9567217680</td> </tr> <tr> <td>LANCIA</td> <td>1330512080, 71714473, 9567217680</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 40, 3350 27, 3350 91</td> </tr> </table>	EAN	192661041642	Inner diameter [mm]	44	Outer diameter [mm]	82.5	Width [mm]	37	<b>OE No.</b>		CITROËN	3326 40, 3350 27, 3350 91	FIAT	1330512080, 71714473, 9567217680	LANCIA	1330512080, 71714473, 9567217680	PEUGEOT	3326 40, 3350 27, 3350 91
EAN	192661041642																			
Inner diameter [mm]	44																			
Outer diameter [mm]	82.5																			
Width [mm]	37																			
<b>OE No.</b>																				
CITROËN	3326 40, 3350 27, 3350 91																			
FIAT	1330512080, 71714473, 9567217680																			
LANCIA	1330512080, 71714473, 9567217680																			
PEUGEOT	3326 40, 3350 27, 3350 91																			
<p>KH10090</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661041659</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-00Q0M, 43210-00QAC</td> </tr> <tr> <td>OPEL</td> <td>44 08 277, 91159917</td> </tr> <tr> <td>RENAULT</td> <td>77 01 206 849</td> </tr> <tr> <td>VAUXHALL</td> <td>44 08 277, 91159917</td> </tr> </table>	EAN	192661041659	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	48	<b>OE No.</b>		NISSAN	43210-00Q0M, 43210-00QAC	OPEL	44 08 277, 91159917	RENAULT	77 01 206 849	VAUXHALL	44 08 277, 91159917
EAN	192661041659																			
Inner diameter [mm]	35																			
Outer diameter [mm]	68																			
Width [mm]	48																			
<b>OE No.</b>																				
NISSAN	43210-00Q0M, 43210-00QAC																			
OPEL	44 08 277, 91159917																			
RENAULT	77 01 206 849																			
VAUXHALL	44 08 277, 91159917																			
<p>KH10091</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661041666</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3730 32</td> </tr> <tr> <td>FIAT</td> <td>1328029080, 71753818</td> </tr> <tr> <td>PEUGEOT</td> <td>3730 32</td> </tr> </table>	EAN	192661041666	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	60	<b>OE No.</b>		CITROËN	3730 32	FIAT	1328029080, 71753818	PEUGEOT	3730 32		
EAN	192661041666																			
Inner diameter [mm]	42																			
Outer diameter [mm]	75																			
Width [mm]	60																			
<b>OE No.</b>																				
CITROËN	3730 32																			
FIAT	1328029080, 71753818																			
PEUGEOT	3730 32																			
<p>KH10092</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661039779</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45.3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>45 01 155, 9161455</td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 417</td> </tr> <tr> <td>VAUXHALL</td> <td>45 01 155, 9161455</td> </tr> </table>	EAN	192661039779	Inner diameter [mm]	45.3	Outer diameter [mm]	80	Width [mm]	48	<b>OE No.</b>		OPEL	45 01 155, 9161455	RENAULT	77 01 205 417	VAUXHALL	45 01 155, 9161455		
EAN	192661039779																			
Inner diameter [mm]	45.3																			
Outer diameter [mm]	80																			
Width [mm]	48																			
<b>OE No.</b>																				
OPEL	45 01 155, 9161455																			
RENAULT	77 01 205 417																			
VAUXHALL	45 01 155, 9161455																			

Part Number	Pk.	Description
<p>KH10093</p> 	1	<p>EAN 192661052075</p> <p>Inner diameter [mm] 29</p> <p>Outer diameter [mm] 53</p> <p>Width [mm] 37</p> <p><b>OE No.</b></p> <p>FORD 1085565, 1135043, 1201568, 1212541, 1212546, 2S41-1A154-AA, 2S41-1A154-BA, 2S6J-1A049-AA, 98AX-1A049-AA, 98AX-1A049-AB</p> <p>MAZDA D350-26-151B, D350-26-151C</p>
<p>KH10097</p> 	1	<p>EAN 192661041673</p> <p>Inner diameter [mm] 39</p> <p>Outer diameter [mm] 72</p> <p>Width [mm] 37</p> <p><b>OE No.</b></p> <p>FORD 1141771, 2S6J-1K018-AA</p>
<p>KH10100</p> 	1	<p>EAN 192661045183</p> <p>Inner diameter [mm] 49</p> <p>Outer diameter [mm] 84</p> <p>Width [mm] 48</p> <p><b>OE No.</b></p> <p>NISSAN 40210-00QAC</p> <p>OPEL 44 03 023, 9111023</p> <p>RENAULT 77 01 206 740</p> <p>VAUXHALL 44 03 023, 9111023</p>
<p>KH10101</p> 	1	<p>EAN 192661052082</p> <p>Inner diameter [mm] 55</p> <p>Outer diameter [mm] 90</p> <p>Width [mm] 60</p> <p><b>OE No.</b></p> <p>CITROËN 3326 63</p> <p>FIAT 1328054080</p> <p>PEUGEOT 3326 63</p>
<p>KH10104</p> 	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661048726</p> <p>Inner diameter [mm] 25</p> <p>Outer diameter [mm] 55</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 48</p> <p><b>OE No.</b></p> <p>RENAULT 77 01 208 059</p>









Part Number	Pk.	Description																				
<p>KH10105</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048733</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1484266, 2T14-1K018-AA, 2T14-1K018-AB, 4410218</td> </tr> </table>	EAN	192661048733	Inner diameter [mm]	39	Outer diameter [mm]	74	Width [mm]	39	<b>OE No.</b>		FORD	1484266, 2T14-1K018-AA, 2T14-1K018-AB, 4410218								
EAN	192661048733																					
Inner diameter [mm]	39																					
Outer diameter [mm]	74																					
Width [mm]	39																					
<b>OE No.</b>																						
FORD	1484266, 2T14-1K018-AA, 2T14-1K018-AB, 4410218																					
<p>KH10106</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048740</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>69</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>6822JL</td> </tr> <tr> <td>PEUGEOT</td> <td>6822JL</td> </tr> <tr> <td>TOYOTA</td> <td>90369-W0001</td> </tr> </table>	EAN	192661048740	Inner diameter [mm]	38	Outer diameter [mm]	69	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width 1 [mm]	34	Width 2 [mm]	39	<b>OE No.</b>		CITROËN	6822JL	PEUGEOT	6822JL	TOYOTA	90369-W0001
EAN	192661048740																					
Inner diameter [mm]	38																					
Outer diameter [mm]	69																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width 1 [mm]	34																					
Width 2 [mm]	39																					
<b>OE No.</b>																						
CITROËN	6822JL																					
PEUGEOT	6822JL																					
TOYOTA	90369-W0001																					
<p>KH10107</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048757</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>64</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>90065431</td> </tr> <tr> <td>VAUXHALL</td> <td>90065431</td> </tr> </table>	EAN	192661048757	Inner diameter [mm]	34	Outer diameter [mm]	64	Width [mm]	37	<b>OE No.</b>		OPEL	90065431	VAUXHALL	90065431						
EAN	192661048757																					
Inner diameter [mm]	34																					
Outer diameter [mm]	64																					
Width [mm]	37																					
<b>OE No.</b>																						
OPEL	90065431																					
VAUXHALL	90065431																					
<p>KH10108</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048764</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAEWOO</td> <td>90279332</td> </tr> <tr> <td>OPEL</td> <td>16 03 191, 3 28 103, 904486460</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 191, 3 28 103, 904486460</td> </tr> </table>	EAN	192661048764	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		DAEWOO	90279332	OPEL	16 03 191, 3 28 103, 904486460	VAUXHALL	16 03 191, 3 28 103, 904486460				
EAN	192661048764																					
Inner diameter [mm]	39																					
Outer diameter [mm]	72																					
Width [mm]	37																					
<b>OE No.</b>																						
DAEWOO	90279332																					
OPEL	16 03 191, 3 28 103, 904486460																					
VAUXHALL	16 03 191, 3 28 103, 904486460																					
<p>KH10109</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048771</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>85</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 22 1 095 702, 33 41 1 090 505</td> </tr> </table>	EAN	192661048771	Inner diameter [mm]	45	Outer diameter [mm]	85	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41	<b>OE No.</b>		BMW	31 22 1 095 702, 33 41 1 090 505						
EAN	192661048771																					
Inner diameter [mm]	45																					
Outer diameter [mm]	85																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	41																					
<b>OE No.</b>																						
BMW	31 22 1 095 702, 33 41 1 090 505																					






Part Number	Pk.	Description																
KH10110 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048788</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>70</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-02000, 51720-1C000, 51720-25000, 51720-29100, 51720-29150, 51720-29300, 51720-29400</td> </tr> <tr> <td>KIA</td> <td>51720-02000</td> </tr> </table>	EAN	192661048788	Inner diameter [mm]	38	Outer diameter [mm]	70	Width [mm]	37	<b>OE No.</b>		HYUNDAI	51720-02000, 51720-1C000, 51720-25000, 51720-29100, 51720-29150, 51720-29300, 51720-29400	KIA	51720-02000		
EAN	192661048788																	
Inner diameter [mm]	38																	
Outer diameter [mm]	70																	
Width [mm]	37																	
<b>OE No.</b>																		
HYUNDAI	51720-02000, 51720-1C000, 51720-25000, 51720-29100, 51720-29150, 51720-29300, 51720-29400																	
KIA	51720-02000																	
KH10111 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048795</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46531160, 71714458</td> </tr> <tr> <td>FORD</td> <td>1587548</td> </tr> </table>	EAN	192661048795	Inner diameter [mm]	35	Outer diameter [mm]	66	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	33	<b>OE No.</b>		FIAT	46531160, 71714458	FORD	1587548
EAN	192661048795																	
Inner diameter [mm]	35																	
Outer diameter [mm]	66																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	33																	
<b>OE No.</b>																		
FIAT	46531160, 71714458																	
FORD	1587548																	
KH10112 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048801</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>83</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 415 334 06 00</td> </tr> <tr> <td>RENAULT</td> <td>77 01 208 950, 77 01 209 838</td> </tr> </table>	EAN	192661048801	Inner diameter [mm]	45	Outer diameter [mm]	83	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 415 334 06 00	RENAULT	77 01 208 950, 77 01 209 838
EAN	192661048801																	
Inner diameter [mm]	45																	
Outer diameter [mm]	83																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	39																	
<b>OE No.</b>																		
MERCEDES-BENZ	A 415 334 06 00																	
RENAULT	77 01 208 950, 77 01 209 838																	
KH10113 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048818</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>27</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>53</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 04 007, 9196286</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 007, 9196286</td> </tr> </table>	EAN	192661048818	Inner diameter [mm]	27	Outer diameter [mm]	53	Width [mm]	43	<b>OE No.</b>		OPEL	16 04 007, 9196286	VAUXHALL	16 04 007, 9196286		
EAN	192661048818																	
Inner diameter [mm]	27																	
Outer diameter [mm]	53																	
Width [mm]	43																	
<b>OE No.</b>																		
OPEL	16 04 007, 9196286																	
VAUXHALL	16 04 007, 9196286																	
KH10114 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048825</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>0K552-33047, 51720-FL047</td> </tr> </table>	EAN	192661048825	Inner diameter [mm]	42	Outer diameter [mm]	76	Width [mm]	39	<b>OE No.</b>		KIA	0K552-33047, 51720-FL047				
EAN	192661048825																	
Inner diameter [mm]	42																	
Outer diameter [mm]	76																	
Width [mm]	39																	
<b>OE No.</b>																		
KIA	0K552-33047, 51720-FL047																	








Part Number	Pk.	Description																		
<p>KH10115</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048832</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40210-00Q0E, 40210-00QAG, 40210-00QAK</td> </tr> <tr> <td>OPEL</td> <td>4412598, 4430305, 93161059, 93161376</td> </tr> <tr> <td>RENAULT</td> <td>40 21 096 97R, 77 01 207 358, 77 01 207 966, 77 01 208 427</td> </tr> <tr> <td>VAUXHALL</td> <td>4412598, 4430305, 93161059, 93161376</td> </tr> </table>	EAN	192661048832	Inner diameter [mm]	45	Outer diameter [mm]	88	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	NISSAN	40210-00Q0E, 40210-00QAG, 40210-00QAK	OPEL	4412598, 4430305, 93161059, 93161376	RENAULT	40 21 096 97R, 77 01 207 358, 77 01 207 966, 77 01 208 427	VAUXHALL	4412598, 4430305, 93161059, 93161376
EAN	192661048832																			
Inner diameter [mm]	45																			
Outer diameter [mm]	88																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	39																			
NISSAN	40210-00Q0E, 40210-00QAG, 40210-00QAK																			
OPEL	4412598, 4430305, 93161059, 93161376																			
RENAULT	40 21 096 97R, 77 01 207 358, 77 01 207 966, 77 01 208 427																			
VAUXHALL	4412598, 4430305, 93161059, 93161376																			
<p>KH10116</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048849</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1484269, 2T14-1K018-BA, 2T14-1K018-BB, 4410219</td> </tr> </table>	EAN	192661048849	Inner diameter [mm]	39	Outer diameter [mm]	74	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	FORD	1484269, 2T14-1K018-BA, 2T14-1K018-BB, 4410219						
EAN	192661048849																			
Inner diameter [mm]	39																			
Outer diameter [mm]	74																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	39																			
FORD	1484269, 2T14-1K018-BA, 2T14-1K018-BB, 4410219																			
<p>KH10117</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048856</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>8L0 498 625, 8L0 498 625 B</td> </tr> <tr> <td>SEAT</td> <td>8L0 498 625, 8L0 498 625 B</td> </tr> <tr> <td>VW</td> <td>8L0 498 625, 8L0 498 625 B</td> </tr> </table>	EAN	192661048856	Inner diameter [mm]	40	Outer diameter [mm]	74	Width [mm]	40	AUDI	8L0 498 625, 8L0 498 625 B	SEAT	8L0 498 625, 8L0 498 625 B	VW	8L0 498 625, 8L0 498 625 B				
EAN	192661048856																			
Inner diameter [mm]	40																			
Outer diameter [mm]	74																			
Width [mm]	40																			
AUDI	8L0 498 625, 8L0 498 625 B																			
SEAT	8L0 498 625, 8L0 498 625 B																			
VW	8L0 498 625, 8L0 498 625 B																			
<p>KH10118</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048863</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width 1 [mm]</td> <td>35</td> </tr> <tr> <td>Width 2 [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUZUKI</td> <td>43462-84A00</td> </tr> </table>	EAN	192661048863	Inner diameter [mm]	41	Outer diameter [mm]	68	Width 1 [mm]	35	Width 2 [mm]	40	SUZUKI	43462-84A00						
EAN	192661048863																			
Inner diameter [mm]	41																			
Outer diameter [mm]	68																			
Width 1 [mm]	35																			
Width 2 [mm]	40																			
SUZUKI	43462-84A00																			






Part Number	Pk.	Description																		
KH10119	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048870</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3350.93</td> </tr> <tr> <td>FIAT</td> <td>71748673, 9403350889</td> </tr> <tr> <td>PEUGEOT</td> <td>3350.93</td> </tr> <tr> <td>TOYOTA</td> <td>SU001-A0982</td> </tr> </table>	EAN	192661048870	Inner diameter [mm]	45	Outer diameter [mm]	86	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	44	CITROËN	3350.93	FIAT	71748673, 9403350889	PEUGEOT	3350.93	TOYOTA	SU001-A0982
EAN	192661048870																			
Inner diameter [mm]	45																			
Outer diameter [mm]	86																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	44																			
CITROËN	3350.93																			
FIAT	71748673, 9403350889																			
PEUGEOT	3350.93																			
TOYOTA	SU001-A0982																			
KH10120	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048887</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3326.71</td> </tr> <tr> <td>FIAT</td> <td>51745702</td> </tr> <tr> <td>PEUGEOT</td> <td>3326.71</td> </tr> </table>	EAN	192661048887	Inner diameter [mm]	55	Outer diameter [mm]	90	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	54	CITROËN	3326.71	FIAT	51745702	PEUGEOT	3326.71		
EAN	192661048887																			
Inner diameter [mm]	55																			
Outer diameter [mm]	90																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	54																			
CITROËN	3326.71																			
FIAT	51745702																			
PEUGEOT	3326.71																			
KH10121	1	<table border="1"> <tr> <td>EAN</td> <td>192661048894</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>92 14 025</td> </tr> <tr> <td>SUZUKI</td> <td>43440-86G00</td> </tr> <tr> <td>VAUXHALL</td> <td>92 14 025</td> </tr> </table>	EAN	192661048894	Inner diameter [mm]	40	Outer diameter [mm]	72	Width [mm]	36	OPEL	92 14 025	SUZUKI	43440-86G00	VAUXHALL	92 14 025				
EAN	192661048894																			
Inner diameter [mm]	40																			
Outer diameter [mm]	72																			
Width [mm]	36																			
OPEL	92 14 025																			
SUZUKI	43440-86G00																			
VAUXHALL	92 14 025																			
KH10122	1	<table border="1"> <tr> <td>EAN</td> <td>192661048900</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>47 06 538, 9213602</td> </tr> <tr> <td>VAUXHALL</td> <td>47 06 538, 9213602</td> </tr> </table>	EAN	192661048900	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	42	OPEL	47 06 538, 9213602	VAUXHALL	47 06 538, 9213602						
EAN	192661048900																			
Inner diameter [mm]	25																			
Outer diameter [mm]	52																			
Width [mm]	42																			
OPEL	47 06 538, 9213602																			
VAUXHALL	47 06 538, 9213602																			



Part Number	Pk.	Description														
KH10123 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048917</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-38110, 51720-3A101</td> </tr> <tr> <td>KIA</td> <td>51720-38110, 51720-3A101</td> </tr> </table>	EAN	192661048917	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	41	<b>OE No.</b>		HYUNDAI	51720-38110, 51720-3A101	KIA	51720-38110, 51720-3A101
EAN	192661048917															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Width [mm]	41															
<b>OE No.</b>																
HYUNDAI	51720-38110, 51720-3A101															
KIA	51720-38110, 51720-3A101															
KH10124 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048924</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>46860-76G01</td> </tr> </table>	EAN	192661048924	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	42	<b>OE No.</b>		SUZUKI	46860-76G01		
EAN	192661048924															
Inner diameter [mm]	25															
Outer diameter [mm]	52															
Width [mm]	42															
<b>OE No.</b>																
SUZUKI	46860-76G01															
KH10125 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048931</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1501642, 1668557, 2215574, 8V41-1215-BA, 8V41-1215-BB, 8V41-1215-BC</td> </tr> </table>	EAN	192661048931	Inner diameter [mm]	45	Outer diameter [mm]	82	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42	<b>OE No.</b>		FORD	1501642, 1668557, 2215574, 8V41-1215-BA, 8V41-1215-BB, 8V41-1215-BC
EAN	192661048931															
Inner diameter [mm]	45															
Outer diameter [mm]	82															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	42															
<b>OE No.</b>																
FORD	1501642, 1668557, 2215574, 8V41-1215-BA, 8V41-1215-BB, 8V41-1215-BC															
KH10126 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048948</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1501642, 1668557, 1796001, 8V41-1215-BA, 8V41-1215-BB, 8V41-1K018-AA</td> </tr> </table>	EAN	192661048948	Inner diameter [mm]	45	Outer diameter [mm]	82	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42	<b>OE No.</b>		FORD	1501642, 1668557, 1796001, 8V41-1215-BA, 8V41-1215-BB, 8V41-1K018-AA
EAN	192661048948															
Inner diameter [mm]	45															
Outer diameter [mm]	82															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	42															
<b>OE No.</b>																
FORD	1501642, 1668557, 1796001, 8V41-1215-BA, 8V41-1215-BB, 8V41-1K018-AA															
KH10127 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048955</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>85</td> </tr> <tr> <td>Width [mm]</td> <td>30</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>5025900, 6765406, 92VB-1225-BA, 92VX-1A049-AA</td> </tr> </table>	EAN	192661048955	Inner diameter [mm]	45	Outer diameter [mm]	85	Width [mm]	30	<b>OE No.</b>		FORD	5025900, 6765406, 92VB-1225-BA, 92VX-1A049-AA		
EAN	192661048955															
Inner diameter [mm]	45															
Outer diameter [mm]	85															
Width [mm]	30															
<b>OE No.</b>																
FORD	5025900, 6765406, 92VB-1225-BA, 92VX-1A049-AA															

Part Number	Pk.	Description																				
<p>KH10128</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>90363-32035, 90369-32003</td> </tr> </table>	Inner diameter [mm]	32	Outer diameter [mm]	72	Width [mm]	45	<b>OE No.</b>		LEXUS	90363-32035, 90369-32003										
Inner diameter [mm]	32																					
Outer diameter [mm]	72																					
Width [mm]	45																					
<b>OE No.</b>																						
LEXUS	90363-32035, 90369-32003																					
<p>KH10129</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048962</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 011 981 89 05, A 017 981 46 05, A 902 350 00 68, A 902 350 14 10</td> </tr> </table>	EAN	192661048962	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	48	<b>OE No.</b>		MERCEDES-BENZ	A 011 981 89 05, A 017 981 46 05, A 902 350 00 68, A 902 350 14 10								
EAN	192661048962																					
Inner diameter [mm]	49																					
Outer diameter [mm]	84																					
Width [mm]	48																					
<b>OE No.</b>																						
MERCEDES-BENZ	A 011 981 89 05, A 017 981 46 05, A 902 350 00 68, A 902 350 14 10																					
<p>KH10130</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048979</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>83</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>ANR5861</td> </tr> </table>	EAN	192661048979	Inner diameter [mm]	44	Outer diameter [mm]	83	Width [mm]	37	<b>OE No.</b>		LAND ROVER	ANR5861								
EAN	192661048979																					
Inner diameter [mm]	44																					
Outer diameter [mm]	83																					
Width [mm]	37																					
<b>OE No.</b>																						
LAND ROVER	ANR5861																					
<p>KH10132</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661048986</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82.5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 70, 3350 81, 3350 87</td> </tr> <tr> <td>FIAT</td> <td>1326188080, 71731547</td> </tr> <tr> <td>LANCIA</td> <td>1326188080, 71731547</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 70, 3350 81, 3350 87</td> </tr> </table>	EAN	192661048986	Inner diameter [mm]	44	Outer diameter [mm]	82.5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		CITROËN	3350 70, 3350 81, 3350 87	FIAT	1326188080, 71731547	LANCIA	1326188080, 71731547	PEUGEOT	3350 70, 3350 81, 3350 87
EAN	192661048986																					
Inner diameter [mm]	44																					
Outer diameter [mm]	82.5																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	37																					
<b>OE No.</b>																						
CITROËN	3350 70, 3350 81, 3350 87																					
FIAT	1326188080, 71731547																					
LANCIA	1326188080, 71731547																					
PEUGEOT	3350 70, 3350 81, 3350 87																					
<p>KH10133</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052099</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-2D200, 51720-38000</td> </tr> <tr> <td>KIA</td> <td>51720-2D200, 51720-38000</td> </tr> </table>	EAN	192661052099	Inner diameter [mm]	42	Outer diameter [mm]	80	Width 1 [mm]	34	Width 2 [mm]	36	<b>OE No.</b>		HYUNDAI	51720-2D200, 51720-38000	KIA	51720-2D200, 51720-38000				
EAN	192661052099																					
Inner diameter [mm]	42																					
Outer diameter [mm]	80																					
Width 1 [mm]	34																					
Width 2 [mm]	36																					
<b>OE No.</b>																						
HYUNDAI	51720-2D200, 51720-38000																					
KIA	51720-2D200, 51720-38000																					








Part Number	Pk.	Description																		
<p>KH10134</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661048993</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>4B0 598 625 B</td> </tr> </table>	EAN	192661048993	Inner diameter [mm]	39	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		AUDI	4B0 598 625 B						
EAN	192661048993																			
Inner diameter [mm]	39																			
Outer diameter [mm]	75																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	4B0 598 625 B																			
<p>KH10135</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049006</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>57.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90369-47001</td> </tr> </table>	EAN	192661049006	Inner diameter [mm]	47	Outer diameter [mm]	88	Width [mm]	57.5	<b>OE No.</b>		TOYOTA	90369-47001						
EAN	192661049006																			
Inner diameter [mm]	47																			
Outer diameter [mm]	88																			
Width [mm]	57.5																			
<b>OE No.</b>																				
TOYOTA	90369-47001																			
<p>KH10136</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049013</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>4A0 407 625 A, 4D0 407 625 E, 8E0 598 625</td> </tr> </table>	EAN	192661049013	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	37	<b>OE No.</b>		AUDI	4A0 407 625 A, 4D0 407 625 E, 8E0 598 625						
EAN	192661049013																			
Inner diameter [mm]	43																			
Outer diameter [mm]	82																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	4A0 407 625 A, 4D0 407 625 E, 8E0 598 625																			
<p>KH10137</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052105</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>47 09 078, 93193920</td> </tr> <tr> <td>SUZUKI</td> <td>43440-51K00, 43440-71L00</td> </tr> <tr> <td>VAUXHALL</td> <td>47 09 078, 93193920</td> </tr> </table>	EAN	192661052105	Inner diameter [mm]	40	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	36	<b>OE No.</b>		OPEL	47 09 078, 93193920	SUZUKI	43440-51K00, 43440-71L00	VAUXHALL	47 09 078, 93193920
EAN	192661052105																			
Inner diameter [mm]	40																			
Outer diameter [mm]	72																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	36																			
<b>OE No.</b>																				
OPEL	47 09 078, 93193920																			
SUZUKI	43440-51K00, 43440-71L00																			
VAUXHALL	47 09 078, 93193920																			
<p>KH10138</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049020</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-00Q0A, 43210-00Q1B</td> </tr> <tr> <td>OPEL</td> <td>44 19 184, 93197150</td> </tr> <tr> <td>RENAULT</td> <td>43 21 041 77R, 43 21 070 45R</td> </tr> <tr> <td>VAUXHALL</td> <td>44 19 184, 93197150</td> </tr> </table>	EAN	192661049020	Inner diameter [mm]	45	Outer diameter [mm]	80	Width [mm]	60	<b>OE No.</b>		NISSAN	43210-00Q0A, 43210-00Q1B	OPEL	44 19 184, 93197150	RENAULT	43 21 041 77R, 43 21 070 45R	VAUXHALL	44 19 184, 93197150
EAN	192661049020																			
Inner diameter [mm]	45																			
Outer diameter [mm]	80																			
Width [mm]	60																			
<b>OE No.</b>																				
NISSAN	43210-00Q0A, 43210-00Q1B																			
OPEL	44 19 184, 93197150																			
RENAULT	43 21 041 77R, 43 21 070 45R																			
VAUXHALL	44 19 184, 93197150																			



Part Number	Pk.	Description																		
KH10139 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049037</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40210-00Q0H</td> </tr> <tr> <td>OPEL</td> <td>44 19 183, 93197149</td> </tr> <tr> <td>RENAULT</td> <td>40 21 037 08R</td> </tr> <tr> <td>VAUXHALL</td> <td>44 19 183, 93197149</td> </tr> </table>	EAN	192661049037	Inner diameter [mm]	55	Outer diameter [mm]	90	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	54	NISSAN	40210-00Q0H	OPEL	44 19 183, 93197149	RENAULT	40 21 037 08R	VAUXHALL	44 19 183, 93197149
EAN	192661049037																			
Inner diameter [mm]	55																			
Outer diameter [mm]	90																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	54																			
NISSAN	40210-00Q0H																			
OPEL	44 19 183, 93197149																			
RENAULT	40 21 037 08R																			
VAUXHALL	44 19 183, 93197149																			
KH10140 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049044</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MERCEDES-BENZ</td> <td>A 164 981 01 06, A 164 981 04 06</td> </tr> </table>	EAN	192661049044	Inner diameter [mm]	54	Outer diameter [mm]	90	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	MERCEDES-BENZ	A 164 981 01 06, A 164 981 04 06						
EAN	192661049044																			
Inner diameter [mm]	54																			
Outer diameter [mm]	90																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	50																			
MERCEDES-BENZ	A 164 981 01 06, A 164 981 04 06																			
KH10141 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049051</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>64</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHEVROLET</td> <td>94535247, 94535249</td> </tr> <tr> <td>DAEWOO</td> <td>94535247, 94535249</td> </tr> </table>	EAN	192661049051	Inner diameter [mm]	34	Outer diameter [mm]	64	Width [mm]	37	CHEVROLET	94535247, 94535249	DAEWOO	94535247, 94535249						
EAN	192661049051																			
Inner diameter [mm]	34																			
Outer diameter [mm]	64																			
Width [mm]	37																			
CHEVROLET	94535247, 94535249																			
DAEWOO	94535247, 94535249																			
KH10142 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049068</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>DACIA</td> <td>43 21 020 69R, 43 21 031 06R</td> </tr> <tr> <td>RENAULT</td> <td>43 21 020 69R, 43 21 031 06R</td> </tr> </table>	EAN	192661049068	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	48	DACIA	43 21 020 69R, 43 21 031 06R	RENAULT	43 21 020 69R, 43 21 031 06R						
EAN	192661049068																			
Inner diameter [mm]	30																			
Outer diameter [mm]	62																			
Width [mm]	48																			
DACIA	43 21 020 69R, 43 21 031 06R																			
RENAULT	43 21 020 69R, 43 21 031 06R																			





Part Number	Pk.	Description																		
KH10143 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049075</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-00Q0B</td> </tr> <tr> <td>OPEL</td> <td>44 21 076, 931168843</td> </tr> <tr> <td>RENAULT</td> <td>43 21 048 99R</td> </tr> <tr> <td>VAUXHALL</td> <td>44 21 076, 931168843</td> </tr> </table>	EAN	192661049075	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	60	<b>OE No.</b>		NISSAN	43210-00Q0B	OPEL	44 21 076, 931168843	RENAULT	43 21 048 99R	VAUXHALL	44 21 076, 931168843
EAN	192661049075																			
Inner diameter [mm]	55																			
Outer diameter [mm]	90																			
Width [mm]	60																			
<b>OE No.</b>																				
NISSAN	43210-00Q0B																			
OPEL	44 21 076, 931168843																			
RENAULT	43 21 048 99R																			
VAUXHALL	44 21 076, 931168843																			
KH10144 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049082</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>43 21 021 03R</td> </tr> </table>	EAN	192661049082	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	48	<b>OE No.</b>		RENAULT	43 21 021 03R						
EAN	192661049082																			
Inner diameter [mm]	30																			
Outer diameter [mm]	62																			
Width [mm]	48																			
<b>OE No.</b>																				
RENAULT	43 21 021 03R																			
KH10145 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049099</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 638 981 00 27</td> </tr> </table>	EAN	192661049099	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 638 981 00 27						
EAN	192661049099																			
Inner diameter [mm]	45																			
Outer diameter [mm]	84																			
Width [mm]	39																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 638 981 00 27																			
KH10146 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049105</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>30818024, 30884539</td> </tr> </table>	EAN	192661049105	Inner diameter [mm]	40	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		VOLVO	30818024, 30884539						
EAN	192661049105																			
Inner diameter [mm]	40																			
Outer diameter [mm]	75																			
Width [mm]	37																			
<b>OE No.</b>																				
VOLVO	30818024, 30884539																			
KH10147 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049112</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 168 981 06 27, A 414 981 01 27</td> </tr> </table>	EAN	192661049112	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		MERCEDES-BENZ	A 168 981 06 27, A 414 981 01 27						
EAN	192661049112																			
Inner diameter [mm]	42																			
Outer diameter [mm]	75																			
Width [mm]	37																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 168 981 06 27, A 414 981 01 27																			

Part Number	Pk.	Description																		
KH10148	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049129</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LAND ROVER</td> <td>LR041425, RFC 000010</td> </tr> <tr> <td>MG</td> <td>GHK 1692, RUD100150</td> </tr> <tr> <td>ROVER</td> <td>GHK 1692, RUD100150</td> </tr> </table>	EAN	192661049129	Inner diameter [mm]	44	Outer diameter [mm]	82	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	LAND ROVER	LR041425, RFC 000010	MG	GHK 1692, RUD100150	ROVER	GHK 1692, RUD100150		
EAN	192661049129																			
Inner diameter [mm]	44																			
Outer diameter [mm]	82																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	37																			
LAND ROVER	LR041425, RFC 000010																			
MG	GHK 1692, RUD100150																			
ROVER	GHK 1692, RUD100150																			
KH10149	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049136</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40210-00QAE</td> </tr> <tr> <td>OPEL</td> <td>4408668, 91160086</td> </tr> <tr> <td>RENAULT</td> <td>40 21 065 66R, 77 01 206 847</td> </tr> <tr> <td>VAUXHALL</td> <td>4408668, 91160086</td> </tr> </table>	EAN	192661049136	Inner diameter [mm]	45	Outer diameter [mm]	86	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	NISSAN	40210-00QAE	OPEL	4408668, 91160086	RENAULT	40 21 065 66R, 77 01 206 847	VAUXHALL	4408668, 91160086
EAN	192661049136																			
Inner diameter [mm]	45																			
Outer diameter [mm]	86																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	39																			
NISSAN	40210-00QAE																			
OPEL	4408668, 91160086																			
RENAULT	40 21 065 66R, 77 01 206 847																			
VAUXHALL	4408668, 91160086																			
KH10150	1	<table border="1"> <tr> <td>EAN</td> <td>192661052112</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>RENAULT</td> <td>77 01 206 771</td> </tr> </table>	EAN	192661052112	Inner diameter [mm]	40	Outer diameter [mm]	84	Width [mm]	38	RENAULT	77 01 206 771								
EAN	192661052112																			
Inner diameter [mm]	40																			
Outer diameter [mm]	84																			
Width [mm]	38																			
RENAULT	77 01 206 771																			
KH10151	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049143</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>46836196, 46836198, 71729125, 71753820, 92403013</td> </tr> <tr> <td>LANCIA</td> <td>46836196, 46836198, 71729125, 71753820, 92403013</td> </tr> <tr> <td>OPEL</td> <td>3 28 011, 3 28 023, 95511623, 95513921</td> </tr> <tr> <td>VAUXHALL</td> <td>3 28 011, 3 28 023, 95511623, 95513921</td> </tr> </table>	EAN	192661049143	Inner diameter [mm]	37	Outer diameter [mm]	74	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	FIAT	46836196, 46836198, 71729125, 71753820, 92403013	LANCIA	46836196, 46836198, 71729125, 71753820, 92403013	OPEL	3 28 011, 3 28 023, 95511623, 95513921	VAUXHALL	3 28 011, 3 28 023, 95511623, 95513921
EAN	192661049143																			
Inner diameter [mm]	37																			
Outer diameter [mm]	74																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	37																			
FIAT	46836196, 46836198, 71729125, 71753820, 92403013																			
LANCIA	46836196, 46836198, 71729125, 71753820, 92403013																			
OPEL	3 28 011, 3 28 023, 95511623, 95513921																			
VAUXHALL	3 28 011, 3 28 023, 95511623, 95513921																			








Part Number	Pk.	Description																
KH10152	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052129</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>51</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>7L0498287</td> </tr> <tr> <td>PORSCHE</td> <td>7L0498287</td> </tr> <tr> <td>VW</td> <td>7L0498287</td> </tr> </table>	EAN	192661052129	Inner diameter [mm]	51	Outer diameter [mm]	96	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	AUDI	7L0498287	PORSCHE	7L0498287	VW	7L0498287
EAN	192661052129																	
Inner diameter [mm]	51																	
Outer diameter [mm]	96																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	50																	
AUDI	7L0498287																	
PORSCHE	7L0498287																	
VW	7L0498287																	
KH10153	1	<table border="1"> <tr> <td>EAN</td> <td>192661066256</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>BMW</td> <td>31 22 6 751 978, 31 22 6 783 913</td> </tr> </table>	EAN	192661066256	Inner diameter [mm]	49	Outer diameter [mm]	90	Width [mm]	45	BMW	31 22 6 751 978, 31 22 6 783 913						
EAN	192661066256																	
Inner diameter [mm]	49																	
Outer diameter [mm]	90																	
Width [mm]	45																	
BMW	31 22 6 751 978, 31 22 6 783 913																	
KH10154	1	<table border="1"> <tr> <td>EAN</td> <td>192661049150</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>KIA</td> <td>50310-3E101, 50310-3E200, 50310-3E201</td> </tr> </table>	EAN	192661049150	Inner diameter [mm]	42	Outer diameter [mm]	76	Width [mm]	39	KIA	50310-3E101, 50310-3E200, 50310-3E201						
EAN	192661049150																	
Inner diameter [mm]	42																	
Outer diameter [mm]	76																	
Width [mm]	39																	
KIA	50310-3E101, 50310-3E200, 50310-3E201																	
KH10155	1	<table border="1"> <tr> <td>EAN</td> <td>192661049167</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>1346651080</td> </tr> </table>	EAN	192661049167	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	48	FIAT	1346651080						
EAN	192661049167																	
Inner diameter [mm]	49																	
Outer diameter [mm]	84																	
Width [mm]	48																	
FIAT	1346651080																	
KH10156	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052136</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MAZDA</td> <td>BP4L-33-047, BP4L-33-047A, BP4L-33-047B</td> </tr> </table>	EAN	192661052136	Inner diameter [mm]	42	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	45	MAZDA	BP4L-33-047, BP4L-33-047A, BP4L-33-047B				
EAN	192661052136																	
Inner diameter [mm]	42																	
Outer diameter [mm]	80																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	45																	
MAZDA	BP4L-33-047, BP4L-33-047A, BP4L-33-047B																	





Part Number	Pk.	Description														
KH10157 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049174</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-0Q000, 51720-2H000, 51720-2K000</td> </tr> <tr> <td>KIA</td> <td>51720-0Q000, 51720-2H000, 51720-2K000</td> </tr> </table>	EAN	192661049174	Inner diameter [mm]	42	Outer diameter [mm]	78	Width [mm]	40	<b>OE No.</b>		HYUNDAI	51720-0Q000, 51720-2H000, 51720-2K000	KIA	51720-0Q000, 51720-2H000, 51720-2K000
EAN	192661049174															
Inner diameter [mm]	42															
Outer diameter [mm]	78															
Width [mm]	40															
<b>OE No.</b>																
HYUNDAI	51720-0Q000, 51720-2H000, 51720-2K000															
KIA	51720-0Q000, 51720-2H000, 51720-2K000															
KH10158 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049181</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR519097</td> </tr> </table>	EAN	192661049181	Inner diameter [mm]	40	Outer diameter [mm]	74	Width [mm]	36	<b>OE No.</b>		MITSUBISHI	MR519097		
EAN	192661049181															
Inner diameter [mm]	40															
Outer diameter [mm]	74															
Width [mm]	36															
<b>OE No.</b>																
MITSUBISHI	MR519097															
KH10159 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049198</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>89</td> </tr> <tr> <td>Width [mm]</td> <td>51</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>RFM500020, RLB100042</td> </tr> </table>	EAN	192661049198	Inner diameter [mm]	50	Outer diameter [mm]	89	Width [mm]	51	<b>OE No.</b>		LAND ROVER	RFM500020, RLB100042		
EAN	192661049198															
Inner diameter [mm]	50															
Outer diameter [mm]	89															
Width [mm]	51															
<b>OE No.</b>																
LAND ROVER	RFM500020, RLB100042															
KH10160 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049204</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>51</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>RLB000011</td> </tr> </table>	EAN	192661049204	Inner diameter [mm]	51	Outer diameter [mm]	96	Width [mm]	50	<b>OE No.</b>		LAND ROVER	RLB000011		
EAN	192661049204															
Inner diameter [mm]	51															
Outer diameter [mm]	96															
Width [mm]	50															
<b>OE No.</b>																
LAND ROVER	RLB000011															
KH10161 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049211</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>GAM6-33-047, GAM6-33-047A, GAM6-33-047B</td> </tr> </table>	EAN	192661049211	Inner diameter [mm]	45	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	45	<b>OE No.</b>		MAZDA	GAM6-33-047, GAM6-33-047A, GAM6-33-047B
EAN	192661049211															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	45															
<b>OE No.</b>																
MAZDA	GAM6-33-047, GAM6-33-047A, GAM6-33-047B															








Part Number	Pk.	Description																		
KH10162	1	<table border="1"> <tr> <td>EAN</td> <td>192661052143</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SKODA</td> <td>6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801</td> </tr> <tr> <td>VW</td> <td>6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801</td> </tr> </table>	EAN	192661052143	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	37	<b>OE No.</b>		SKODA	6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801	VW	6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801				
EAN	192661052143																			
Inner diameter [mm]	35																			
Outer diameter [mm]	68																			
Width [mm]	37																			
<b>OE No.</b>																				
SKODA	6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801																			
VW	6U0 407 625 A, 6U0 498 002, 6U0 498 003, 969106801																			
KH10163	1	<table border="1"> <tr> <td>EAN</td> <td>192661052150</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46539970, 51754191, 71714480, 82374669, 82390273</td> </tr> </table>	EAN	192661052150	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		FIAT	46539970, 51754191, 71714480, 82374669, 82390273						
EAN	192661052150																			
Inner diameter [mm]	37																			
Outer diameter [mm]	72																			
Width [mm]	37																			
<b>OE No.</b>																				
FIAT	46539970, 51754191, 71714480, 82374669, 82390273																			
KH10164	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052167</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3326 74</td> </tr> <tr> <td>MITSUBISHI</td> <td>3885A017, MN101347</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 74</td> </tr> </table>	EAN	192661052167	Inner diameter [mm]	43	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	40	<b>OE No.</b>		CITROËN	3326 74	MITSUBISHI	3885A017, MN101347	PEUGEOT	3326 74
EAN	192661052167																			
Inner diameter [mm]	43																			
Outer diameter [mm]	80																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	40																			
<b>OE No.</b>																				
CITROËN	3326 74																			
MITSUBISHI	3885A017, MN101347																			
PEUGEOT	3326 74																			
KH10165	1	<table border="1"> <tr> <td>EAN</td> <td>192661052174</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 31</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 31</td> </tr> </table>	EAN	192661052174	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	39	<b>OE No.</b>		CITROËN	3350 31	PEUGEOT	3350 31				
EAN	192661052174																			
Inner diameter [mm]	45																			
Outer diameter [mm]	84																			
Width [mm]	39																			
<b>OE No.</b>																				
CITROËN	3350 31																			
PEUGEOT	3350 31																			
KH10166	1	<table border="1"> <tr> <td>EAN</td> <td>192661066263</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>46</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 163 330 0051</td> </tr> </table>	EAN	192661066263	Inner diameter [mm]	49	Outer diameter [mm]	88	Width [mm]	46	<b>OE No.</b>		MERCEDES-BENZ	A 163 330 0051						
EAN	192661066263																			
Inner diameter [mm]	49																			
Outer diameter [mm]	88																			
Width [mm]	46																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 163 330 0051																			

Part Number	Pk.	Description										
<p>KH10167</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052181</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39.7</td> </tr> </table> <p><b>OE No.</b>            RENAULT 77 01 205 972, 77 01 470 552</p>	EAN	192661052181	Inner diameter [mm]	40	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39.7
EAN	192661052181											
Inner diameter [mm]	40											
Outer diameter [mm]	84											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	39.7											
<p>KH10168</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052198</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>46</td> </tr> </table> <p><b>OE No.</b>            JAGUAR XR81723</p>	EAN	192661052198	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	46		
EAN	192661052198											
Inner diameter [mm]	42											
Outer diameter [mm]	80											
Width [mm]	46											
<p>KH10169</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052204</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b>            JAGUAR MJA1830AD, MJA1830AE</p>	EAN	192661052204	Inner diameter [mm]	42	Outer diameter [mm]	76	Width [mm]	39		
EAN	192661052204											
Inner diameter [mm]	42											
Outer diameter [mm]	76											
Width [mm]	39											
<p>KH10170</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052211</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>73</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> </table> <p><b>OE No.</b>            IVECO 42470840, 42470845</p>	EAN	192661052211	Inner diameter [mm]	40	Outer diameter [mm]	73	Width [mm]	55		
EAN	192661052211											
Inner diameter [mm]	40											
Outer diameter [mm]	73											
Width [mm]	55											
<p>KH10171</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052228</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> </table> <p><b>OE No.</b>            IVECO 42558516, 46393024, 7180066, 7187566</p>	EAN	192661052228	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	60		
EAN	192661052228											
Inner diameter [mm]	55											
Outer diameter [mm]	90											
Width [mm]	60											













Part Number	Pk.	Description																				
<p>KH10172</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052235</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JAGUAR</td> <td>MNC1830AA</td> </tr> </table>	EAN	192661052235	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	45	<b>OE No.</b>		JAGUAR	MNC1830AA								
EAN	192661052235																					
Inner diameter [mm]	42																					
Outer diameter [mm]	80																					
Width [mm]	45																					
<b>OE No.</b>																						
JAGUAR	MNC1830AA																					
<p>KH10173</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052242</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>47 06 538, 9213602</td> </tr> <tr> <td>VAUXHALL</td> <td>47 06 538, 9213602</td> </tr> </table>	EAN	192661052242	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	42	<b>OE No.</b>		OPEL	47 06 538, 9213602	VAUXHALL	47 06 538, 9213602						
EAN	192661052242																					
Inner diameter [mm]	25																					
Outer diameter [mm]	52																					
Width [mm]	42																					
<b>OE No.</b>																						
OPEL	47 06 538, 9213602																					
VAUXHALL	47 06 538, 9213602																					
<p>KH10174</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052259</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40210-00Q0L</td> </tr> <tr> <td>OPEL</td> <td>44 22 229, 95516872</td> </tr> <tr> <td>RENAULT</td> <td>40 21 074 35R</td> </tr> <tr> <td>VAUXHALL</td> <td>44 22 229, 95516872</td> </tr> </table>	EAN	192661052259	Inner diameter [mm]	55	Outer diameter [mm]	90	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	54	<b>OE No.</b>		NISSAN	40210-00Q0L	OPEL	44 22 229, 95516872	RENAULT	40 21 074 35R	VAUXHALL	44 22 229, 95516872
EAN	192661052259																					
Inner diameter [mm]	55																					
Outer diameter [mm]	90																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	54																					
<b>OE No.</b>																						
NISSAN	40210-00Q0L																					
OPEL	44 22 229, 95516872																					
RENAULT	40 21 074 35R																					
VAUXHALL	44 22 229, 95516872																					
<p>KH10175</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066270</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>55</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-1HA1A, 43210-1HA9D, 43210-1HM0A</td> </tr> </table>	EAN	192661066270	Inner diameter [mm]	25	Outer diameter [mm]	55	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	48	<b>OE No.</b>		NISSAN	43210-1HA1A, 43210-1HA9D, 43210-1HM0A						
EAN	192661066270																					
Inner diameter [mm]	25																					
Outer diameter [mm]	55																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	48																					
<b>OE No.</b>																						
NISSAN	43210-1HA1A, 43210-1HA9D, 43210-1HM0A																					

Part Number	Pk.	Description										
KH10176 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052266</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b>            NISSAN 40210-1HA1A, 40210-1HA9D</p>	EAN	192661052266	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37
EAN	192661052266											
Inner diameter [mm]	37											
Outer diameter [mm]	72											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	37											
KH10177 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052273</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> </table> <p><b>OE No.</b>            DACIA 60 01 548 986, 82 00 381 151            RENAULT 60 01 548 986, 82 00 381 151</p>	EAN	192661052273	Inner diameter [mm]	30	Outer diameter [mm]	62	Width [mm]	48		
EAN	192661052273											
Inner diameter [mm]	30											
Outer diameter [mm]	62											
Width [mm]	48											
KH10178 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052280</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b>            VOLVO 3454197</p>	EAN	192661052280	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	37		
EAN	192661052280											
Inner diameter [mm]	35											
Outer diameter [mm]	68											
Width [mm]	37											
KH10179 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052297</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> </table> <p><b>OE No.</b>            TOYOTA 90369-35029</p>	EAN	192661052297	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	33		
EAN	192661052297											
Inner diameter [mm]	35											
Outer diameter [mm]	68											
Width [mm]	33											
KH10180 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052303</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b>            NISSAN 40210-99B00</p>	EAN	192661052303	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	39		
EAN	192661052303											
Inner diameter [mm]	35											
Outer diameter [mm]	68											
Width [mm]	39											










Part Number	Pk.	Description																
<p>KH10181</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052310</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46529970, 5890987, 60815880, 71714460</td> </tr> <tr> <td>FIAT</td> <td>46529970, 5890987, 60815880, 71714460</td> </tr> <tr> <td>LANCIA</td> <td>46529970, 5890987, 60815880, 71714460</td> </tr> </table>	EAN	192661052310	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		ALFA ROMEO	46529970, 5890987, 60815880, 71714460	FIAT	46529970, 5890987, 60815880, 71714460	LANCIA	46529970, 5890987, 60815880, 71714460
EAN	192661052310																	
Inner diameter [mm]	37																	
Outer diameter [mm]	72																	
Width [mm]	37																	
<b>OE No.</b>																		
ALFA ROMEO	46529970, 5890987, 60815880, 71714460																	
FIAT	46529970, 5890987, 60815880, 71714460																	
LANCIA	46529970, 5890987, 60815880, 71714460																	
<p>KH10182</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052327</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>90369-43008, 90369-43009</td> </tr> <tr> <td>TOYOTA</td> <td>90369-43008, 90369-43009</td> </tr> </table>	EAN	192661052327	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	45	<b>OE No.</b>		LEXUS	90369-43008, 90369-43009	TOYOTA	90369-43008, 90369-43009		
EAN	192661052327																	
Inner diameter [mm]	43																	
Outer diameter [mm]	82																	
Width [mm]	45																	
<b>OE No.</b>																		
LEXUS	90369-43008, 90369-43009																	
TOYOTA	90369-43008, 90369-43009																	
<p>KH10183</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052334</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>55</td> </tr> <tr> <td>Width [mm]</td> <td>53.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 168 981 07 27</td> </tr> </table>	EAN	192661052334	Inner diameter [mm]	25	Outer diameter [mm]	55	Width [mm]	53.5	<b>OE No.</b>		MERCEDES-BENZ	A 168 981 07 27				
EAN	192661052334																	
Inner diameter [mm]	25																	
Outer diameter [mm]	55																	
Width [mm]	53.5																	
<b>OE No.</b>																		
MERCEDES-BENZ	A 168 981 07 27																	
<p>KH10184</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052341</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>40 21 073 14R</td> </tr> <tr> <td>RENAULT</td> <td>40 21 073 14R</td> </tr> </table>	EAN	192661052341	Inner diameter [mm]	42	Outer diameter [mm]	77	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	<b>OE No.</b>		DACIA	40 21 073 14R	RENAULT	40 21 073 14R
EAN	192661052341																	
Inner diameter [mm]	42																	
Outer diameter [mm]	77																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	39																	
<b>OE No.</b>																		
DACIA	40 21 073 14R																	
RENAULT	40 21 073 14R																	
<p>KH10185</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066287</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>27</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>5451859, 75523458</td> </tr> <tr> <td>PEUGEOT</td> <td>5451859, 75523458</td> </tr> </table>	EAN	192661066287	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	27	<b>OE No.</b>		CITROËN	5451859, 75523458	PEUGEOT	5451859, 75523458		
EAN	192661066287																	
Inner diameter [mm]	35																	
Outer diameter [mm]	72																	
Width [mm]	27																	
<b>OE No.</b>																		
CITROËN	5451859, 75523458																	
PEUGEOT	5451859, 75523458																	






Part Number	Pk.	Description																		
<p>KH10186</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066294</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>64</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D</td> </tr> <tr> <td>SEAT</td> <td>171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D</td> </tr> <tr> <td>SKODA</td> <td>171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D</td> </tr> <tr> <td>VW</td> <td>171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D</td> </tr> </table>	EAN	192661066294	Inner diameter [mm]	34	Outer diameter [mm]	64	Width [mm]	37	<b>OE No.</b>		AUDI	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D	SEAT	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D	SKODA	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D	VW	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D
EAN	192661066294																			
Inner diameter [mm]	34																			
Outer diameter [mm]	64																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D																			
SEAT	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D																			
SKODA	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D																			
VW	171 498 625A, 171 498 625B, 171 498 625C, 171 498 625D																			
<p>KH10187</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066300</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>861 498 625, 871 498 625 A</td> </tr> <tr> <td>VW</td> <td>861 498 625, 871 498 625A</td> </tr> </table>	EAN	192661066300	Inner diameter [mm]	34	Outer diameter [mm]	62	Width [mm]	37	<b>OE No.</b>		AUDI	861 498 625, 871 498 625 A	VW	861 498 625, 871 498 625A				
EAN	192661066300																			
Inner diameter [mm]	34																			
Outer diameter [mm]	62																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	861 498 625, 871 498 625 A																			
VW	861 498 625, 871 498 625A																			
<p>KH10188</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066317</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 1 134 549</td> </tr> </table>	EAN	192661066317	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	42	<b>OE No.</b>		BMW	33 41 1 134 549						
EAN	192661066317																			
Inner diameter [mm]	42																			
Outer diameter [mm]	80																			
Width [mm]	42																			
<b>OE No.</b>																				
BMW	33 41 1 134 549																			
<p>KH10189</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066324</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>GHK 1366, RFM000050</td> </tr> <tr> <td>ROVER</td> <td>GHK 1366, RFM000050</td> </tr> </table>	EAN	192661066324	Inner diameter [mm]	38	Outer diameter [mm]	68	Width [mm]	37	<b>OE No.</b>		MG	GHK 1366, RFM000050	ROVER	GHK 1366, RFM000050				
EAN	192661066324																			
Inner diameter [mm]	38																			
Outer diameter [mm]	68																			
Width [mm]	37																			
<b>OE No.</b>																				
MG	GHK 1366, RFM000050																			
ROVER	GHK 1366, RFM000050																			
<p>KH10190</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066331</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46421951, 71714472</td> </tr> <tr> <td>FIAT</td> <td>46421951, 71714472</td> </tr> <tr> <td>LANCIA</td> <td>46421951, 71714472</td> </tr> </table>	EAN	192661066331	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	37	<b>OE No.</b>		ALFA ROMEO	46421951, 71714472	FIAT	46421951, 71714472	LANCIA	46421951, 71714472		
EAN	192661066331																			
Inner diameter [mm]	42																			
Outer diameter [mm]	80																			
Width [mm]	37																			
<b>OE No.</b>																				
ALFA ROMEO	46421951, 71714472																			
FIAT	46421951, 71714472																			
LANCIA	46421951, 71714472																			








Part Number	Pk.	Description																		
<p>KH10191</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066348</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>49</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 124 980 05 16</td> </tr> </table>	EAN	192661066348	Inner diameter [mm]	43	Outer diameter [mm]	49	Width [mm]	84	<b>OE No.</b>		MERCEDES-BENZ	A 124 980 05 16						
EAN	192661066348																			
Inner diameter [mm]	43																			
Outer diameter [mm]	49																			
Width [mm]	84																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 124 980 05 16																			
<p>KH10192</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066355</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 15</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 15</td> </tr> </table>	EAN	192661066355	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	39	<b>OE No.</b>		CITROËN	3350 15	PEUGEOT	3350 15				
EAN	192661066355																			
Inner diameter [mm]	45																			
Outer diameter [mm]	84																			
Width [mm]	39																			
<b>OE No.</b>																				
CITROËN	3350 15																			
PEUGEOT	3350 15																			
<p>KH10193</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066362</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>1H0 498 625, 357 407 625 A</td> </tr> <tr> <td>SEAT</td> <td>1H0 498 625, 357 407 625 A</td> </tr> <tr> <td>SKODA</td> <td>1H0 498 625, 357 407 625 A</td> </tr> <tr> <td>VW</td> <td>1H0 498 625, 357 407 625 A</td> </tr> </table>	EAN	192661066362	Inner diameter [mm]	40	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		AUDI	1H0 498 625, 357 407 625 A	SEAT	1H0 498 625, 357 407 625 A	SKODA	1H0 498 625, 357 407 625 A	VW	1H0 498 625, 357 407 625 A
EAN	192661066362																			
Inner diameter [mm]	40																			
Outer diameter [mm]	72																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	1H0 498 625, 357 407 625 A																			
SEAT	1H0 498 625, 357 407 625 A																			
SKODA	1H0 498 625, 357 407 625 A																			
VW	1H0 498 625, 357 407 625 A																			
<p>KH10194</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066379</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>321 498 625 E, 331 598 625</td> </tr> <tr> <td>VW</td> <td>321 498 625 E, 331 598 625</td> </tr> </table>	EAN	192661066379	Inner diameter [mm]	39	Outer diameter [mm]	68	Width [mm]	37	<b>OE No.</b>		AUDI	321 498 625 E, 331 598 625	VW	321 498 625 E, 331 598 625				
EAN	192661066379																			
Inner diameter [mm]	39																			
Outer diameter [mm]	68																			
Width [mm]	37																			
<b>OE No.</b>																				
AUDI	321 498 625 E, 331 598 625																			
VW	321 498 625 E, 331 598 625																			
<p>KH10195</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066386</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>45 01 154, 9161454</td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 416</td> </tr> <tr> <td>VAUXHALL</td> <td>45 01 154, 9161454</td> </tr> </table>	EAN	192661066386	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	48	<b>OE No.</b>		OPEL	45 01 154, 9161454	RENAULT	77 01 205 416	VAUXHALL	45 01 154, 9161454		
EAN	192661066386																			
Inner diameter [mm]	49																			
Outer diameter [mm]	84																			
Width [mm]	48																			
<b>OE No.</b>																				
OPEL	45 01 154, 9161454																			
RENAULT	77 01 205 416																			
VAUXHALL	45 01 154, 9161454																			

Part Number	Pk.	Description																						
KH10196 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066393</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40210-00QAF</td> </tr> <tr> <td>OPEL</td> <td>44 08 669, 91160087</td> </tr> <tr> <td>RENAULT</td> <td>77 01 206 848</td> </tr> <tr> <td>VAUXHALL</td> <td>44 08 699, 91160087</td> </tr> </table>	EAN	192661066393	Inner diameter [mm]	45	Outer diameter [mm]	86	Width [mm]	39	<b>OE No.</b>		NISSAN	40210-00QAF	OPEL	44 08 669, 91160087	RENAULT	77 01 206 848	VAUXHALL	44 08 699, 91160087				
EAN	192661066393																							
Inner diameter [mm]	45																							
Outer diameter [mm]	86																							
Width [mm]	39																							
<b>OE No.</b>																								
NISSAN	40210-00QAF																							
OPEL	44 08 669, 91160087																							
RENAULT	77 01 206 848																							
VAUXHALL	44 08 699, 91160087																							
KH10197 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066409</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>34</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-2D000, 51720-2D100</td> </tr> <tr> <td>KIA</td> <td>51720-2D000, 51720-2D100</td> </tr> </table>	EAN	192661066409	Inner diameter [mm]	39	Outer diameter [mm]	74	Width [mm]	34	<b>OE No.</b>		HYUNDAI	51720-2D000, 51720-2D100	KIA	51720-2D000, 51720-2D100								
EAN	192661066409																							
Inner diameter [mm]	39																							
Outer diameter [mm]	74																							
Width [mm]	34																							
<b>OE No.</b>																								
HYUNDAI	51720-2D000, 51720-2D100																							
KIA	51720-2D000, 51720-2D100																							
KH10198 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066416</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82.5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46836200, 50700495, 71753821</td> </tr> <tr> <td>FIAT</td> <td>46836200, 50700495, 71753821</td> </tr> <tr> <td>LANCIA</td> <td>46836200, 50700495, 71753821</td> </tr> <tr> <td>OPEL</td> <td>3 28 012, 95511624</td> </tr> <tr> <td>VAUXHALL</td> <td>3 28 012, 95511624</td> </tr> </table>	EAN	192661066416	Inner diameter [mm]	42	Outer diameter [mm]	82.5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		ALFA ROMEO	46836200, 50700495, 71753821	FIAT	46836200, 50700495, 71753821	LANCIA	46836200, 50700495, 71753821	OPEL	3 28 012, 95511624	VAUXHALL	3 28 012, 95511624
EAN	192661066416																							
Inner diameter [mm]	42																							
Outer diameter [mm]	82.5																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
Width [mm]	37																							
<b>OE No.</b>																								
ALFA ROMEO	46836200, 50700495, 71753821																							
FIAT	46836200, 50700495, 71753821																							
LANCIA	46836200, 50700495, 71753821																							
OPEL	3 28 012, 95511624																							
VAUXHALL	3 28 012, 95511624																							
KH10199 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066423</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>60 01 547 686</td> </tr> <tr> <td>RENAULT</td> <td>60 01 547 686</td> </tr> </table>	EAN	192661066423	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		DACIA	60 01 547 686	RENAULT	60 01 547 686						
EAN	192661066423																							
Inner diameter [mm]	37																							
Outer diameter [mm]	72																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
Width [mm]	37																							
<b>OE No.</b>																								
DACIA	60 01 547 686																							
RENAULT	60 01 547 686																							








Part Number	Pk.	Description										
KH10200 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066430</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>83</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b> RENAULT 40 21 018 77R, 82 00 351 777</p>	EAN	192661066430	Inner diameter [mm]	45	Outer diameter [mm]	83	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39
EAN	192661066430											
Inner diameter [mm]	45											
Outer diameter [mm]	83											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	39											
KH10201 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066447</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b> HYUNDAI 51720-2J001, 52710-26500, 52710-26510, 52710-26530 KIA 51720-2J001, 52710-26500, 52710-26510, 52710-26530</p>	EAN	192661066447	Inner diameter [mm]	42	Outer diameter [mm]	76	Width [mm]	39		
EAN	192661066447											
Inner diameter [mm]	42											
Outer diameter [mm]	76											
Width [mm]	39											
KH10202 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066454</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b> ROVER ADU9475EVA, GHK1285</p>	EAN	192661066454	Inner diameter [mm]	42	Outer diameter [mm]	78	Width [mm]	38		
EAN	192661066454											
Inner diameter [mm]	42											
Outer diameter [mm]	78											
Width [mm]	38											
KH10203 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066461</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b> BMW 33 41 6 762 317</p>	EAN	192661066461	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37		
EAN	192661066461											
Inner diameter [mm]	42											
Outer diameter [mm]	75											
Width [mm]	37											
KH10204 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066478</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>36</td> </tr> </table> <p><b>OE No.</b> TOYOTA 90080-36043</p>	EAN	192661066478	Inner diameter [mm]	38	Outer diameter [mm]	74	Width [mm]	36		
EAN	192661066478											
Inner diameter [mm]	38											
Outer diameter [mm]	74											
Width [mm]	36											

Part Number	Pk.	Description																
KH10205 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066485</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VW</td> <td>701498625</td> </tr> </table>	EAN	192661066485	Inner diameter [mm]	45	Outer diameter [mm]	80	Width [mm]	45	<b>OE No.</b>		VW	701498625				
EAN	192661066485																	
Inner diameter [mm]	45																	
Outer diameter [mm]	80																	
Width [mm]	45																	
<b>OE No.</b>																		
VW	701498625																	
KH10206 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066492</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>GENERAL MOTORS</td> <td>90510542</td> </tr> <tr> <td>OPEL</td> <td>16 03 196, 90510542</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 196, 90510542</td> </tr> </table>	EAN	192661066492	Inner diameter [mm]	39	Outer diameter [mm]	74	Width [mm]	39	<b>OE No.</b>		GENERAL MOTORS	90510542	OPEL	16 03 196, 90510542	VAUXHALL	16 03 196, 90510542
EAN	192661066492																	
Inner diameter [mm]	39																	
Outer diameter [mm]	74																	
Width [mm]	39																	
<b>OE No.</b>																		
GENERAL MOTORS	90510542																	
OPEL	16 03 196, 90510542																	
VAUXHALL	16 03 196, 90510542																	
KH10207 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066508</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>90369-43005</td> </tr> <tr> <td>TOYOTA</td> <td>90369-43005</td> </tr> </table>	EAN	192661066508	Inner diameter [mm]	43	Outer diameter [mm]	80	Width [mm]	50	<b>OE No.</b>		LEXUS	90369-43005	TOYOTA	90369-43005		
EAN	192661066508																	
Inner diameter [mm]	43																	
Outer diameter [mm]	80																	
Width [mm]	50																	
<b>OE No.</b>																		
LEXUS	90369-43005																	
TOYOTA	90369-43005																	
KH10208 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066515</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1497388</td> </tr> <tr> <td>SEAT</td> <td>7M0 598 625 A, 7M3 598 625</td> </tr> <tr> <td>VW</td> <td>7M0 598 625 A, 7M3 598 625</td> </tr> </table>	EAN	192661066515	Inner diameter [mm]	43	Outer diameter [mm]	80	Width [mm]	38	<b>OE No.</b>		FORD	1497388	SEAT	7M0 598 625 A, 7M3 598 625	VW	7M0 598 625 A, 7M3 598 625
EAN	192661066515																	
Inner diameter [mm]	43																	
Outer diameter [mm]	80																	
Width [mm]	38																	
<b>OE No.</b>																		
FORD	1497388																	
SEAT	7M0 598 625 A, 7M3 598 625																	
VW	7M0 598 625 A, 7M3 598 625																	
KH10209 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066522</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>55</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 168 981 03 27</td> </tr> </table>	EAN	192661066522	Inner diameter [mm]	25	Outer diameter [mm]	55	Width [mm]	43	<b>OE No.</b>		MERCEDES-BENZ	A 168 981 03 27				
EAN	192661066522																	
Inner diameter [mm]	25																	
Outer diameter [mm]	55																	
Width [mm]	43																	
<b>OE No.</b>																		
MERCEDES-BENZ	A 168 981 03 27																	












Part Number	Pk.	Description														
<p>KH10210</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066539</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1333562, 3S6J-1K018-AA</td> </tr> </table>	EAN	192661066539	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		FORD	1333562, 3S6J-1K018-AA		
EAN	192661066539															
Inner diameter [mm]	39															
Outer diameter [mm]	72															
Width [mm]	37															
<b>OE No.</b>																
FORD	1333562, 3S6J-1K018-AA															
<p>KH10211</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066546</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>44</td> </tr> <tr> <td>Width 2 [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>52371-3E000</td> </tr> </table>	EAN	192661066546	Inner diameter [mm]	40	Outer diameter [mm]	80	Width 1 [mm]	44	Width 2 [mm]	45	<b>OE No.</b>		KIA	52371-3E000
EAN	192661066546															
Inner diameter [mm]	40															
Outer diameter [mm]	80															
Width 1 [mm]	44															
Width 2 [mm]	45															
<b>OE No.</b>																
KIA	52371-3E000															
<p>KH10212</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066553</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>30870319</td> </tr> </table>	EAN	192661066553	Inner diameter [mm]	40	Outer diameter [mm]	80	Width 1 [mm]	34	Width 2 [mm]	36	<b>OE No.</b>		VOLVO	30870319
EAN	192661066553															
Inner diameter [mm]	40															
Outer diameter [mm]	80															
Width 1 [mm]	34															
Width 2 [mm]	36															
<b>OE No.</b>																
VOLVO	30870319															
<p>KH10213</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066560</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>96471775, 96471776</td> </tr> <tr> <td>DAEWOO</td> <td>96471775, 96471776</td> </tr> </table>	EAN	192661066560	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	37	<b>OE No.</b>		CHEVROLET	96471775, 96471776	DAEWOO	96471775, 96471776
EAN	192661066560															
Inner diameter [mm]	25															
Outer diameter [mm]	52															
Width [mm]	37															
<b>OE No.</b>																
CHEVROLET	96471775, 96471776															
DAEWOO	96471775, 96471776															
<p>KH10214</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066577</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>40 21 095 33R</td> </tr> <tr> <td>RENAULT</td> <td>40 21 095 33R</td> </tr> </table>	EAN	192661066577	Inner diameter [mm]	42	Outer diameter [mm]	77	Width [mm]	39	<b>OE No.</b>		DACIA	40 21 095 33R	RENAULT	40 21 095 33R
EAN	192661066577															
Inner diameter [mm]	42															
Outer diameter [mm]	77															
Width [mm]	39															
<b>OE No.</b>																
DACIA	40 21 095 33R															
RENAULT	40 21 095 33R															

Part Number	Pk.	Description																
KH10215 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066584</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>61.8</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>47 00 322, 9203934</td> </tr> <tr> <td>SUZUKI</td> <td>43440-74F00, 43440-78A00</td> </tr> <tr> <td>VAUXHALL</td> <td>47 00 322, 9203934</td> </tr> </table>	EAN	192661066584	Inner diameter [mm]	35	Outer diameter [mm]	61.8	Width [mm]	40	<b>OE No.</b>		OPEL	47 00 322, 9203934	SUZUKI	43440-74F00, 43440-78A00	VAUXHALL	47 00 322, 9203934
EAN	192661066584																	
Inner diameter [mm]	35																	
Outer diameter [mm]	61.8																	
Width [mm]	40																	
<b>OE No.</b>																		
OPEL	47 00 322, 9203934																	
SUZUKI	43440-74F00, 43440-78A00																	
VAUXHALL	47 00 322, 9203934																	
KH10216 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068885</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54.75</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>99.25</td> </tr> <tr> <td>Width [mm]</td> <td>56.25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3326 14</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 14</td> </tr> </table>	EAN	192661068885	Inner diameter [mm]	54.75	Outer diameter [mm]	99.25	Width [mm]	56.25	<b>OE No.</b>		CITROËN	3326 14	PEUGEOT	3326 14		
EAN	192661068885																	
Inner diameter [mm]	54.75																	
Outer diameter [mm]	99.25																	
Width [mm]	56.25																	
<b>OE No.</b>																		
CITROËN	3326 14																	
PEUGEOT	3326 14																	
KH10217 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068892</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>51753789, 5890991, 71714466</td> </tr> </table>	EAN	192661068892	Inner diameter [mm]	35	Outer diameter [mm]	66	Width [mm]	33	<b>OE No.</b>		FIAT	51753789, 5890991, 71714466				
EAN	192661068892																	
Inner diameter [mm]	35																	
Outer diameter [mm]	66																	
Width [mm]	33																	
<b>OE No.</b>																		
FIAT	51753789, 5890991, 71714466																	
KH10218 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068908</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 04 287, 3 28 103, 90279332, 90486461</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 287, 3 28 103, 90279332, 90486461</td> </tr> </table>	EAN	192661068908	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		OPEL	16 04 287, 3 28 103, 90279332, 90486461	VAUXHALL	16 04 287, 3 28 103, 90279332, 90486461		
EAN	192661068908																	
Inner diameter [mm]	39																	
Outer diameter [mm]	72																	
Width [mm]	37																	
<b>OE No.</b>																		
OPEL	16 04 287, 3 28 103, 90279332, 90486461																	
VAUXHALL	16 04 287, 3 28 103, 90279332, 90486461																	
KH10219 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068915</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 04 292, 4 15 203, 90235281, 90486468</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 292, 4 15 203, 90235281, 90486468</td> </tr> </table>	EAN	192661068915	Inner diameter [mm]	37	Outer diameter [mm]	74	Width [mm]	45	<b>OE No.</b>		OPEL	16 04 292, 4 15 203, 90235281, 90486468	VAUXHALL	16 04 292, 4 15 203, 90235281, 90486468		
EAN	192661068915																	
Inner diameter [mm]	37																	
Outer diameter [mm]	74																	
Width [mm]	45																	
<b>OE No.</b>																		
OPEL	16 04 292, 4 15 203, 90235281, 90486468																	
VAUXHALL	16 04 292, 4 15 203, 90235281, 90486468																	









Part Number	Pk.	Description														
KH10220 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068922</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>60</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>VOLVO</td> <td>3411886</td> </tr> </table>	EAN	192661068922	Inner diameter [mm]	30	Outer diameter [mm]	60	Width [mm]	37	<b>OE No.</b>		VOLVO	3411886		
EAN	192661068922															
Inner diameter [mm]	30															
Outer diameter [mm]	60															
Width [mm]	37															
<b>OE No.</b>																
VOLVO	3411886															
KH10221 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068939</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>36</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MITSUBISHI</td> <td>MB808442, MR449797</td> </tr> </table>	EAN	192661068939	Inner diameter [mm]	40	Outer diameter [mm]	74	Width 1 [mm]	34	Width 2 [mm]	36	<b>OE No.</b>		MITSUBISHI	MB808442, MR449797
EAN	192661068939															
Inner diameter [mm]	40															
Outer diameter [mm]	74															
Width 1 [mm]	34															
Width 2 [mm]	36															
<b>OE No.</b>																
MITSUBISHI	MB808442, MR449797															
KH10222 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068946</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SAAB</td> <td>4689923</td> </tr> </table>	EAN	192661068946	Inner diameter [mm]	39	Outer diameter [mm]	74	Width [mm]	39	<b>OE No.</b>		SAAB	4689923		
EAN	192661068946															
Inner diameter [mm]	39															
Outer diameter [mm]	74															
Width [mm]	39															
<b>OE No.</b>																
SAAB	4689923															
KH10223 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068953</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>IVECO</td> <td>42470834, 42470839</td> </tr> </table>	EAN	192661068953	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	50	<b>OE No.</b>		IVECO	42470834, 42470839		
EAN	192661068953															
Inner diameter [mm]	35															
Outer diameter [mm]	68															
Width [mm]	50															
<b>OE No.</b>																
IVECO	42470834, 42470839															
KH10224 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068960</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>IVECO</td> <td>42471033</td> </tr> </table>	EAN	192661068960	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	48	<b>OE No.</b>		IVECO	42471033		
EAN	192661068960															
Inner diameter [mm]	49															
Outer diameter [mm]	84															
Width [mm]	48															
<b>OE No.</b>																
IVECO	42471033															





Part Number	Pk.	Description														
KH10225 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068977</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>64</td> </tr> <tr> <td>Width [mm]</td> <td>37.25</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAIHATSU</td> <td>90043-63253</td> </tr> </table>	EAN	192661068977	Inner diameter [mm]	35	Outer diameter [mm]	64	Width [mm]	37.25	<b>OE No.</b>		DAIHATSU	90043-63253		
EAN	192661068977															
Inner diameter [mm]	35															
Outer diameter [mm]	64															
Width [mm]	37.25															
<b>OE No.</b>																
DAIHATSU	90043-63253															
KH10226 	1	<table border="1"> <tr> <td>EAN</td> <td>192661068984</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>94535259, 94535982, 96995000</td> </tr> <tr> <td>DAEWOO</td> <td>94535259, 94535982, 96995000</td> </tr> </table>	EAN	192661068984	Inner diameter [mm]	39	Outer diameter [mm]	74	Width [mm]	39	<b>OE No.</b>		CHEVROLET	94535259, 94535982, 96995000	DAEWOO	94535259, 94535982, 96995000
EAN	192661068984															
Inner diameter [mm]	39															
Outer diameter [mm]	74															
Width [mm]	39															
<b>OE No.</b>																
CHEVROLET	94535259, 94535982, 96995000															
DAEWOO	94535259, 94535982, 96995000															
KH10227 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661068991</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>71745047</td> </tr> </table>	EAN	192661068991	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		FIAT	71745047
EAN	192661068991															
Inner diameter [mm]	37															
Outer diameter [mm]	72															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	37															
<b>OE No.</b>																
FIAT	71745047															
KH10228 	1	<p><b>General Information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069004</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 169 981 00 06, A 169 981 01 27</td> </tr> </table>	EAN	192661069004	Inner diameter [mm]	45	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 169 981 00 06, A 169 981 01 27
EAN	192661069004															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	39															
<b>OE No.</b>																
MERCEDES-BENZ	A 169 981 00 06, A 169 981 01 27															







Part Number	Pk.	Description												
<p>KH10229</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1" data-bbox="507 412 1469 555"> <tr> <td>EAN</td> <td>192661069011</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>51</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>91</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> </table> <p><b>OE No.</b> HONDA 44300-SJK-01, 44300-SWW-E01</p>	EAN	192661069011	Inner diameter [mm]	51	Outer diameter [mm]	91	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	44		
EAN	192661069011													
Inner diameter [mm]	51													
Outer diameter [mm]	91													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	44													
<p>KH10230</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1" data-bbox="507 828 1469 999"> <tr> <td>EAN</td> <td>192661069028</td> </tr> <tr> <td>Fitting Position</td> <td>Front Axle</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b> MAZDA GD1D-33-047, GS1D-33-047C</p>	EAN	192661069028	Fitting Position	Front Axle	Inner diameter [mm]	42	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	45
EAN	192661069028													
Fitting Position	Front Axle													
Inner diameter [mm]	42													
Outer diameter [mm]	80													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	45													
<p>KH10231</p> 	1	<table border="1" data-bbox="507 1151 1469 1263"> <tr> <td>EAN</td> <td>192661069035</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44.8</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> </table> <p><b>OE No.</b> LAND ROVER FTC1507</p>	EAN	192661069035	Inner diameter [mm]	44.8	Outer diameter [mm]	84	Width [mm]	53				
EAN	192661069035													
Inner diameter [mm]	44.8													
Outer diameter [mm]	84													
Width [mm]	53													
<p>KH10232</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1" data-bbox="507 1590 1469 1733"> <tr> <td>EAN</td> <td>192661069042</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>70</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b> DAIHATSU 90043-63315, 90043-63369</p>	EAN	192661069042	Inner diameter [mm]	38	Outer diameter [mm]	70	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	38		
EAN	192661069042													
Inner diameter [mm]	38													
Outer diameter [mm]	70													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	38													






Part Number	Pk.	Description														
KH10233	1	<p><b>General Information</b></p> <p>This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069059</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>JAGUAR</td> <td>C2P12624</td> </tr> <tr> <td>LAND ROVER</td> <td>LR024508</td> </tr> </table>	EAN	192661069059	Inner diameter [mm]	48	Outer diameter [mm]	86	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42	JAGUAR	C2P12624	LAND ROVER	LR024508
EAN	192661069059															
Inner diameter [mm]	48															
Outer diameter [mm]	86															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	42															
JAGUAR	C2P12624															
LAND ROVER	LR024508															
KH10234	1	<table border="1"> <tr> <td>EAN</td> <td>192661069066</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3326 69</td> </tr> <tr> <td>FIAT</td> <td>1346650080</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 69</td> </tr> </table>	EAN	192661069066	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	60	CITROËN	3326 69	FIAT	1346650080	PEUGEOT	3326 69
EAN	192661069066															
Inner diameter [mm]	55															
Outer diameter [mm]	90															
Width [mm]	60															
CITROËN	3326 69															
FIAT	1346650080															
PEUGEOT	3326 69															
KH10345	1	<table border="1"> <tr> <td>EAN</td> <td>192661071755</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>65</td> </tr> <tr> <td>Width 1 [mm]</td> <td>48</td> </tr> <tr> <td>Width 2 [mm]</td> <td>52</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUBARU</td> <td>28016-AA020, 28016-AA030</td> </tr> </table>	EAN	192661071755	Inner diameter [mm]	38	Outer diameter [mm]	65	Width 1 [mm]	48	Width 2 [mm]	52	SUBARU	28016-AA020, 28016-AA030		
EAN	192661071755															
Inner diameter [mm]	38															
Outer diameter [mm]	65															
Width 1 [mm]	48															
Width 2 [mm]	52															
SUBARU	28016-AA020, 28016-AA030															
KH10346	1	<table border="1"> <tr> <td>EAN</td> <td>192661071762</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>70</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HYUNDAI</td> <td>51720-02000</td> </tr> <tr> <td>KIA</td> <td>51720-02000</td> </tr> </table>	EAN	192661071762	Inner diameter [mm]	38	Outer diameter [mm]	70	Width [mm]	37	HYUNDAI	51720-02000	KIA	51720-02000		
EAN	192661071762															
Inner diameter [mm]	38															
Outer diameter [mm]	70															
Width [mm]	37															
HYUNDAI	51720-02000															
KIA	51720-02000															
KH10347	1	<table border="1"> <tr> <td>EAN</td> <td>192661071779</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LEXUS</td> <td>90369-49001, 90369-49002</td> </tr> <tr> <td>TOYOTA</td> <td>90369-49001, 90369-49002</td> </tr> </table>	EAN	192661071779	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	50	LEXUS	90369-49001, 90369-49002	TOYOTA	90369-49001, 90369-49002		
EAN	192661071779															
Inner diameter [mm]	49															
Outer diameter [mm]	84															
Width [mm]	50															
LEXUS	90369-49001, 90369-49002															
TOYOTA	90369-49001, 90369-49002															








Part Number	Pk.	Description														
<p>KH10348</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071786</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 03 022, 93168535</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 022, 93168535</td> </tr> </table>	EAN	192661071786	Inner diameter [mm]	40	Outer diameter [mm]	78	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	40	OPEL	16 03 022, 93168535	VAUXHALL	16 03 022, 93168535
EAN	192661071786															
Inner diameter [mm]	40															
Outer diameter [mm]	78															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	40															
OPEL	16 03 022, 93168535															
VAUXHALL	16 03 022, 93168535															
<p>KH10349</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071793</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>PORSCHE</td> <td>999 053 042 10, 999 053 054 05</td> </tr> </table>	EAN	192661071793	Inner diameter [mm]	42	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42	PORSCHE	999 053 042 10, 999 053 054 05		
EAN	192661071793															
Inner diameter [mm]	42															
Outer diameter [mm]	80															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	42															
PORSCHE	999 053 042 10, 999 053 054 05															
<p>KH10350</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071809</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>PORSCHE</td> <td>999 053 054 05</td> </tr> </table>	EAN	192661071809	Inner diameter [mm]	42	Outer diameter [mm]	80	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42	PORSCHE	999 053 054 05		
EAN	192661071809															
Inner diameter [mm]	42															
Outer diameter [mm]	80															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	42															
PORSCHE	999 053 054 05															
<p>KH10351</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071816</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44.8</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LAND ROVER</td> <td>FTC1507</td> </tr> </table>	EAN	192661071816	Inner diameter [mm]	44.8	Outer diameter [mm]	84	Width [mm]	53	LAND ROVER	FTC1507				
EAN	192661071816															
Inner diameter [mm]	44.8															
Outer diameter [mm]	84															
Width [mm]	53															
LAND ROVER	FTC1507															

Part Number	Pk.	Description														
<p>KH10352</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071823</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>51720-0Q000, 51720-2K000</td> </tr> </table>	EAN	192661071823	Inner diameter [mm]	42	Outer diameter [mm]	78	Width [mm]	40	<b>OE No.</b>		KIA	51720-0Q000, 51720-2K000		
EAN	192661071823															
Inner diameter [mm]	42															
Outer diameter [mm]	78															
Width [mm]	40															
<b>OE No.</b>																
KIA	51720-0Q000, 51720-2K000															
<p>KH10353</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071830</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAEWOO</td> <td>94535254</td> </tr> </table>	EAN	192661071830	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		DAEWOO	94535254		
EAN	192661071830															
Inner diameter [mm]	39															
Outer diameter [mm]	72															
Width [mm]	37															
<b>OE No.</b>																
DAEWOO	94535254															
<p>KH10354</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071847</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 6 792 356</td> </tr> </table>	EAN	192661071847	Inner diameter [mm]	42	Outer diameter [mm]	75	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		BMW	33 41 6 792 356
EAN	192661071847															
Inner diameter [mm]	42															
Outer diameter [mm]	75															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	37															
<b>OE No.</b>																
BMW	33 41 6 792 356															
<p>KH10355</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071854</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>51</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>LR024267, LR070453</td> </tr> </table>	EAN	192661071854	Inner diameter [mm]	51	Outer diameter [mm]	96	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	<b>OE No.</b>		LAND ROVER	LR024267, LR070453
EAN	192661071854															
Inner diameter [mm]	51															
Outer diameter [mm]	96															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	50															
<b>OE No.</b>																
LAND ROVER	LR024267, LR070453															













Part Number	Pk.	Description										
<p>KH10356</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071861</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> </table> <p><b>OE No.</b> BMW 33 41 6 792 361, 6 792 361</p>	EAN	192661071861	Inner diameter [mm]	45	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41		
EAN	192661071861											
Inner diameter [mm]	45											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	41											
<p>KH10357</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073261</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width 1 [mm]</td> <td>38</td> </tr> <tr> <td>Width 2 [mm]</td> <td>41</td> </tr> </table> <p><b>OE No.</b> ROVER GHK1559, RUD100070</p>	EAN	192661073261	Inner diameter [mm]	43	Outer diameter [mm]	79	Width 1 [mm]	38	Width 2 [mm]	41
EAN	192661073261											
Inner diameter [mm]	43											
Outer diameter [mm]	79											
Width 1 [mm]	38											
Width 2 [mm]	41											
<p>KH10358</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073278</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b> SEAT 6N0 407 625, 6N0 498 625 VW 6N0 407 625, 6N0 498 625</p>	EAN	192661073278	Inner diameter [mm]	35	Outer diameter [mm]	66	Width [mm]	37		
EAN	192661073278											
Inner diameter [mm]	35											
Outer diameter [mm]	66											
Width [mm]	37											
<p>KH10359</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073285</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b> SUBARU 28016-AA011, 28316-FE000</p>	EAN	192661073285	Inner diameter [mm]	42	Outer diameter [mm]	72	Width [mm]	38		
EAN	192661073285											
Inner diameter [mm]	42											
Outer diameter [mm]	72											
Width [mm]	38											
<p>KH10360</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073292</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>73</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b> HONDA 44300-SR3-004, 44300-SR3-008, 44300-SR3-015</p>	EAN	192661073292	Inner diameter [mm]	38	Outer diameter [mm]	73	Width [mm]	40		
EAN	192661073292											
Inner diameter [mm]	38											
Outer diameter [mm]	73											
Width [mm]	40											

Part Number	Pk.	Description														
KH10361 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073308</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>90369-43008</td> </tr> </table>	EAN	192661073308	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	45	<b>OE No.</b>		TOYOTA	90369-43008		
EAN	192661073308															
Inner diameter [mm]	43															
Outer diameter [mm]	82															
Width [mm]	45															
<b>OE No.</b>																
TOYOTA	90369-43008															
KH10362 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073315</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>BMW</td> <td>33 41 6 762 317</td> </tr> </table>	EAN	192661073315	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		BMW	33 41 6 762 317		
EAN	192661073315															
Inner diameter [mm]	42															
Outer diameter [mm]	75															
Width [mm]	37															
<b>OE No.</b>																
BMW	33 41 6 762 317															
KH10363 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073322</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width 1 [mm]</td> <td>48</td> </tr> <tr> <td>Width 2 [mm]</td> <td>53</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUBARU</td> <td>28016-PA010</td> </tr> </table>	EAN	192661073322	Inner diameter [mm]	42	Outer diameter [mm]	72	Width 1 [mm]	48	Width 2 [mm]	53	<b>OE No.</b>		SUBARU	28016-PA010
EAN	192661073322															
Inner diameter [mm]	42															
Outer diameter [mm]	72															
Width 1 [mm]	48															
Width 2 [mm]	53															
<b>OE No.</b>																
SUBARU	28016-PA010															
KH10364 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073339</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>92</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 639 330 13 32, A 639 981 04 27</td> </tr> </table>	EAN	192661073339	Inner diameter [mm]	50	Outer diameter [mm]	92	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	<b>OE No.</b>		MERCEDES-BENZ	A 639 330 13 32, A 639 981 04 27
EAN	192661073339															
Inner diameter [mm]	50															
Outer diameter [mm]	92															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	50															
<b>OE No.</b>																
MERCEDES-BENZ	A 639 330 13 32, A 639 981 04 27															
KH10365 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073346</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR491449</td> </tr> </table>	EAN	192661073346	Inner diameter [mm]	40	Outer diameter [mm]	80	Width [mm]	40	<b>OE No.</b>		MITSUBISHI	MR491449		
EAN	192661073346															
Inner diameter [mm]	40															
Outer diameter [mm]	80															
Width [mm]	40															
<b>OE No.</b>																
MITSUBISHI	MR491449															















Part Number	Pk.	Description														
<p>KH10366</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073353</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>55</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 414 981 02 05</td> </tr> </table>	EAN	192661073353	Inner diameter [mm]	30	Outer diameter [mm]	55	Width [mm]	56	<b>OE No.</b>		MERCEDES-BENZ	A 414 981 02 05		
EAN	192661073353															
Inner diameter [mm]	30															
Outer diameter [mm]	55															
Width [mm]	56															
<b>OE No.</b>																
MERCEDES-BENZ	A 414 981 02 05															
<p>KH10367</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073360</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>46</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Width [mm]</td> <td>57</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VW</td> <td>2H0 501 171, 2H0 501 172</td> </tr> </table>	EAN	192661073360	Inner diameter [mm]	46	Outer diameter [mm]	78	Width [mm]	57	<b>OE No.</b>		VW	2H0 501 171, 2H0 501 172		
EAN	192661073360															
Inner diameter [mm]	46															
Outer diameter [mm]	78															
Width [mm]	57															
<b>OE No.</b>																
VW	2H0 501 171, 2H0 501 172															
<p>KH10368</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073377</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 246 981 00 06</td> </tr> </table>	EAN	192661073377	Inner diameter [mm]	45	Outer diameter [mm]	84	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41	<b>OE No.</b>		MERCEDES-BENZ	A 246 981 00 06
EAN	192661073377															
Inner diameter [mm]	45															
Outer diameter [mm]	84															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	41															
<b>OE No.</b>																
MERCEDES-BENZ	A 246 981 00 06															
<p>KH10369</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073384</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>60.3</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>71714455, 7364573</td> </tr> </table>	EAN	192661073384	Inner diameter [mm]	30	Outer diameter [mm]	60.3	Width [mm]	37	<b>OE No.</b>		FIAT	71714455, 7364573		
EAN	192661073384															
Inner diameter [mm]	30															
Outer diameter [mm]	60.3															
Width [mm]	37															
<b>OE No.</b>																
FIAT	71714455, 7364573															
<p>KH10370</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073391</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>52</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 463 986, 77 03 090 325, 77 03 090 434</td> </tr> </table>	EAN	192661073391	Inner diameter [mm]	25	Outer diameter [mm]	52	Width [mm]	43	<b>OE No.</b>		RENAULT	77 01 463 986, 77 03 090 325, 77 03 090 434		
EAN	192661073391															
Inner diameter [mm]	25															
Outer diameter [mm]	52															
Width [mm]	43															
<b>OE No.</b>																
RENAULT	77 01 463 986, 77 03 090 325, 77 03 090 434															

Part Number	Pk.	Description																
<p>KH10371</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073407</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273</td> </tr> <tr> <td>FIAT</td> <td>46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273</td> </tr> <tr> <td>LANCIA</td> <td>46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273</td> </tr> </table>	EAN	192661073407	Inner diameter [mm]	37	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		ALFA ROMEO	46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273	FIAT	46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273	LANCIA	46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273
EAN	192661073407																	
Inner diameter [mm]	37																	
Outer diameter [mm]	72																	
Width [mm]	37																	
<b>OE No.</b>																		
ALFA ROMEO	46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273																	
FIAT	46423869, 46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273																	
LANCIA	46474537, 46529970, 51754191, 60811546, 60813089, 60814780, 82374669, 82390273																	
<p>KH10372</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073414</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>44300-SE0-003, 44300-SE0-018</td> </tr> </table>	EAN	192661073414	Inner diameter [mm]	40	Outer diameter [mm]	76	Width [mm]	41	<b>OE No.</b>		HONDA	44300-SE0-003, 44300-SE0-018				
EAN	192661073414																	
Inner diameter [mm]	40																	
Outer diameter [mm]	76																	
Width [mm]	41																	
<b>OE No.</b>																		
HONDA	44300-SE0-003, 44300-SE0-018																	
<p>KH10373</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073421</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46773659</td> </tr> <tr> <td>LANCIA</td> <td>46773659</td> </tr> </table>	EAN	192661073421	Inner diameter [mm]	35	Outer diameter [mm]	72	Width [mm]	33	<b>OE No.</b>		FIAT	46773659	LANCIA	46773659		
EAN	192661073421																	
Inner diameter [mm]	35																	
Outer diameter [mm]	72																	
Width [mm]	33																	
<b>OE No.</b>																		
FIAT	46773659																	
LANCIA	46773659																	
<p>KH10374</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073438</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 1 124 358, 33 41 6 762 317</td> </tr> </table>	EAN	192661073438	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		BMW	33 41 1 124 358, 33 41 6 762 317				
EAN	192661073438																	
Inner diameter [mm]	39																	
Outer diameter [mm]	72																	
Width [mm]	37																	
<b>OE No.</b>																		
BMW	33 41 1 124 358, 33 41 6 762 317																	
<p>KH10375</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073445</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>36</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>09267-36002</td> </tr> </table>	EAN	192661073445	Inner diameter [mm]	36	Outer diameter [mm]	68	Width [mm]	33	<b>OE No.</b>		SUZUKI	09267-36002				
EAN	192661073445																	
Inner diameter [mm]	36																	
Outer diameter [mm]	68																	
Width [mm]	33																	
<b>OE No.</b>																		
SUZUKI	09267-36002																	








Part Number	Pk.	Description																				
KH10376 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073452</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 03 195, 3 28 106, 90447280, 90510544</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 195, 3 28 106, 90447280, 90510544</td> </tr> </table>	EAN	192661073452	Inner diameter [mm]	34	Outer diameter [mm]	66	Width [mm]	37	<b>OE No.</b>		OPEL	16 03 195, 3 28 106, 90447280, 90510544	VAUXHALL	16 03 195, 3 28 106, 90447280, 90510544						
EAN	192661073452																					
Inner diameter [mm]	34																					
Outer diameter [mm]	66																					
Width [mm]	37																					
<b>OE No.</b>																						
OPEL	16 03 195, 3 28 106, 90447280, 90510544																					
VAUXHALL	16 03 195, 3 28 106, 90447280, 90510544																					
KH10377 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073469</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>210 980 01 16, 210 980 05 16, 220 330 00 51, 220 980 00 16, 220 980 01 16, 220 981 00 27, A 000 980 05 16, A 140 980 06 16, A 140 981 04 27</td> </tr> </table>	EAN	192661073469	Inner diameter [mm]	49	Outer diameter [mm]	88	Width [mm]	43	<b>OE No.</b>		MERCEDES-BENZ	210 980 01 16, 210 980 05 16, 220 330 00 51, 220 980 00 16, 220 980 01 16, 220 981 00 27, A 000 980 05 16, A 140 980 06 16, A 140 981 04 27								
EAN	192661073469																					
Inner diameter [mm]	49																					
Outer diameter [mm]	88																					
Width [mm]	43																					
<b>OE No.</b>																						
MERCEDES-BENZ	210 980 01 16, 210 980 05 16, 220 330 00 51, 220 980 00 16, 220 980 01 16, 220 981 00 27, A 000 980 05 16, A 140 980 06 16, A 140 981 04 27																					
KH10378 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073476</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46532573, 71714464, 71740076</td> </tr> </table>	EAN	192661073476	Inner diameter [mm]	34	Outer diameter [mm]	68	Width [mm]	37	<b>OE No.</b>		FIAT	46532573, 71714464, 71740076								
EAN	192661073476																					
Inner diameter [mm]	34																					
Outer diameter [mm]	68																					
Width [mm]	37																					
<b>OE No.</b>																						
FIAT	46532573, 71714464, 71740076																					
KH10379 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073483</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77</td> </tr> <tr> <td>Width [mm]</td> <td>41.45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90366-T0007</td> </tr> </table>	EAN	192661073483	Inner diameter [mm]	43	Outer diameter [mm]	77	Width [mm]	41.45	<b>OE No.</b>		TOYOTA	90366-T0007								
EAN	192661073483																					
Inner diameter [mm]	43																					
Outer diameter [mm]	77																					
Width [mm]	41.45																					
<b>OE No.</b>																						
TOYOTA	90366-T0007																					
KH10380 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073490</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DACIA</td> <td>40 21 015 54 R, 60 01 550 915, 77 01 207 677</td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>415 334 07 00</td> </tr> <tr> <td>NISSAN</td> <td>40210-AX000</td> </tr> <tr> <td>RENAULT</td> <td>40 21 015 54 R, 60 01 550 915, 77 01 207 677</td> </tr> </table>	EAN	192661073490	Inner diameter [mm]	37	Outer diameter [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		DACIA	40 21 015 54 R, 60 01 550 915, 77 01 207 677	MERCEDES-BENZ	415 334 07 00	NISSAN	40210-AX000	RENAULT	40 21 015 54 R, 60 01 550 915, 77 01 207 677
EAN	192661073490																					
Inner diameter [mm]	37																					
Outer diameter [mm]	72																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	37																					
<b>OE No.</b>																						
DACIA	40 21 015 54 R, 60 01 550 915, 77 01 207 677																					
MERCEDES-BENZ	415 334 07 00																					
NISSAN	40210-AX000																					
RENAULT	40 21 015 54 R, 60 01 550 915, 77 01 207 677																					

Part Number	Pk.	Description																
KH10381 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073506</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>77</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>90369-35034, 90903-63006</td> </tr> <tr> <td>TOYOTA</td> <td>90369-35034, 90903-63006</td> </tr> </table>	EAN	192661073506	Inner diameter [mm]	35	Outer diameter [mm]	77	Width [mm]	42	<b>OE No.</b>		LEXUS	90369-35034, 90903-63006	TOYOTA	90369-35034, 90903-63006		
EAN	192661073506																	
Inner diameter [mm]	35																	
Outer diameter [mm]	77																	
Width [mm]	42																	
<b>OE No.</b>																		
LEXUS	90369-35034, 90903-63006																	
TOYOTA	90369-35034, 90903-63006																	
KH10383 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074152</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1954476</td> </tr> <tr> <td>NISSAN</td> <td>43210-42G10</td> </tr> </table>	EAN	192661074152	Inner diameter [mm]	40	Outer diameter [mm]	80	Width [mm]	38	<b>OE No.</b>		FORD	1954476	NISSAN	43210-42G10		
EAN	192661074152																	
Inner diameter [mm]	40																	
Outer diameter [mm]	80																	
Width [mm]	38																	
<b>OE No.</b>																		
FORD	1954476																	
NISSAN	43210-42G10																	
KH10384 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074169</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1959350</td> </tr> <tr> <td>NISSAN</td> <td>43210-0VV00</td> </tr> </table>	EAN	192661074169	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	38	<b>OE No.</b>		FORD	1959350	NISSAN	43210-0VV00		
EAN	192661074169																	
Inner diameter [mm]	42																	
Outer diameter [mm]	80																	
Width [mm]	38																	
<b>OE No.</b>																		
FORD	1959350																	
NISSAN	43210-0VV00																	
KH10385 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074176</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46512972, 46783975, 60815378</td> </tr> <tr> <td>FIAT</td> <td>46512972, 46783975, 60815378</td> </tr> <tr> <td>LANCIA</td> <td>46512972, 46783975, 60815378</td> </tr> </table>	EAN	192661074176	Inner diameter [mm]	42	Outer diameter [mm]	80	Width [mm]	37	<b>OE No.</b>		ALFA ROMEO	46512972, 46783975, 60815378	FIAT	46512972, 46783975, 60815378	LANCIA	46512972, 46783975, 60815378
EAN	192661074176																	
Inner diameter [mm]	42																	
Outer diameter [mm]	80																	
Width [mm]	37																	
<b>OE No.</b>																		
ALFA ROMEO	46512972, 46783975, 60815378																	
FIAT	46512972, 46783975, 60815378																	
LANCIA	46512972, 46783975, 60815378																	
KH10386 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074183</td> </tr> <tr> <td>Fitting Position</td> <td>Front Axle</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>IVECO</td> <td>42471216</td> </tr> </table>	EAN	192661074183	Fitting Position	Front Axle	Inner diameter [mm]	45	Outer diameter [mm]	88	Width [mm]	55	<b>OE No.</b>		IVECO	42471216		
EAN	192661074183																	
Fitting Position	Front Axle																	
Inner diameter [mm]	45																	
Outer diameter [mm]	88																	
Width [mm]	55																	
<b>OE No.</b>																		
IVECO	42471216																	








Part Number	Pk.	Description																
<p>KH10387</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661074190</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>71714464, 71740076</td> </tr> </table>	EAN	192661074190	Inner diameter [mm]	35	Outer diameter [mm]	68	Width [mm]	37	<b>OE No.</b>		FIAT	71714464, 71740076				
EAN	192661074190																	
Inner diameter [mm]	35																	
Outer diameter [mm]	68																	
Width [mm]	37																	
<b>OE No.</b>																		
FIAT	71714464, 71740076																	
<p>KH10388</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074206</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width 1 [mm]</td> <td>40</td> </tr> <tr> <td>Width 2 [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>44300-SDA-A51, 44300-SDA-A52</td> </tr> </table>	EAN	192661074206	Inner diameter [mm]	48	Outer diameter [mm]	86	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width 1 [mm]	40	Width 2 [mm]	42	<b>OE No.</b>		HONDA	44300-SDA-A51, 44300-SDA-A52
EAN	192661074206																	
Inner diameter [mm]	48																	
Outer diameter [mm]	86																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width 1 [mm]	40																	
Width 2 [mm]	42																	
<b>OE No.</b>																		
HONDA	44300-SDA-A51, 44300-SDA-A52																	
<p>KH10389</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661074213</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90369-48001</td> </tr> </table>	EAN	192661074213	Inner diameter [mm]	43	Outer diameter [mm]	80	Width [mm]	45	<b>OE No.</b>		TOYOTA	90369-48001				
EAN	192661074213																	
Inner diameter [mm]	43																	
Outer diameter [mm]	80																	
Width [mm]	45																	
<b>OE No.</b>																		
TOYOTA	90369-48001																	
<p>KH10390</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661074220</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>70</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>DAIHATSU</td> <td>90043-63314</td> </tr> </table>	EAN	192661074220	Inner diameter [mm]	38	Outer diameter [mm]	70	Width [mm]	38	<b>OE No.</b>		DAIHATSU	90043-63314				
EAN	192661074220																	
Inner diameter [mm]	38																	
Outer diameter [mm]	70																	
Width [mm]	38																	
<b>OE No.</b>																		
DAIHATSU	90043-63314																	
<p>KH10391</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661074237</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>48</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3326 66</td> </tr> <tr> <td>FIAT</td> <td>71728975</td> </tr> <tr> <td>PEUGEOT</td> <td>3326 66</td> </tr> </table>	EAN	192661074237	Inner diameter [mm]	49	Outer diameter [mm]	84	Width [mm]	48	<b>OE No.</b>		CITROËN	3326 66	FIAT	71728975	PEUGEOT	3326 66
EAN	192661074237																	
Inner diameter [mm]	49																	
Outer diameter [mm]	84																	
Width [mm]	48																	
<b>OE No.</b>																		
CITROËN	3326 66																	
FIAT	71728975																	
PEUGEOT	3326 66																	

Part Number	Pk.	Description												
<p>KH10392</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074244</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>55</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>IVECO</td> <td>2996026, 500054867, 7188164</td> </tr> </table>	EAN	192661074244	Inner diameter [mm]	55	Outer diameter [mm]	90	Width [mm]	55	<b>OE No.</b>		IVECO	2996026, 500054867, 7188164
EAN	192661074244													
Inner diameter [mm]	55													
Outer diameter [mm]	90													
Width [mm]	55													
<b>OE No.</b>														
IVECO	2996026, 500054867, 7188164													
<p>KH10393</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077399</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>RENAULT</td> <td>60 25 370 536, 60 25 371 670, 77 01 469 682</td> </tr> </table>	EAN	192661077399	Inner diameter [mm]	45	Outer diameter [mm]	88	Width [mm]	39	<b>OE No.</b>		RENAULT	60 25 370 536, 60 25 371 670, 77 01 469 682
EAN	192661077399													
Inner diameter [mm]	45													
Outer diameter [mm]	88													
Width [mm]	39													
<b>OE No.</b>														
RENAULT	60 25 370 536, 60 25 371 670, 77 01 469 682													
<p>KH10394</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077405</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 210 330 01 51</td> </tr> </table>	EAN	192661077405	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 210 330 01 51
EAN	192661077405													
Inner diameter [mm]	45													
Outer diameter [mm]	84													
Width [mm]	39													
<b>OE No.</b>														
MERCEDES-BENZ	A 210 330 01 51													
<p>KH10395</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077412</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Width [mm]</td> <td>51</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>90369-54001, 90369-54002</td> </tr> </table>	EAN	192661077412	Inner diameter [mm]	54	Outer diameter [mm]	96	Width [mm]	51	<b>OE No.</b>		TOYOTA	90369-54001, 90369-54002
EAN	192661077412													
Inner diameter [mm]	54													
Outer diameter [mm]	96													
Width [mm]	51													
<b>OE No.</b>														
TOYOTA	90369-54001, 90369-54002													
<p>KH10396</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CHRYSLER</td> <td>5272447AA, 5272448AA</td> </tr> <tr> <td>DODGE</td> <td>5272447AA, 5272448AA</td> </tr> </table>	Inner diameter [mm]	42	Outer diameter [mm]	76	Width [mm]	39	<b>OE No.</b>		CHRYSLER	5272447AA, 5272448AA	DODGE	5272447AA, 5272448AA
Inner diameter [mm]	42													
Outer diameter [mm]	76													
Width [mm]	39													
<b>OE No.</b>														
CHRYSLER	5272447AA, 5272448AA													
DODGE	5272447AA, 5272448AA													








Part Number	Pk.	Description										
<p>KH10397</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661077436</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>44</td> </tr> </table> <p><b>OE No.</b> HONDA 44300-SMG-G01, 44300-SNA-951, 44300-SNA-952</p>	EAN	192661077436	Inner diameter [mm]	43	Outer diameter [mm]	78	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	44
EAN	192661077436											
Inner diameter [mm]	43											
Outer diameter [mm]	78											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	44											
<p>KH10398</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661077443</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>36</td> </tr> </table> <p><b>OE No.</b> MITSUBISHI MB303865</p>	EAN	192661077443	Inner diameter [mm]	40	Outer diameter [mm]	80	Width 1 [mm]	34	Width 2 [mm]	36
EAN	192661077443											
Inner diameter [mm]	40											
Outer diameter [mm]	80											
Width 1 [mm]	34											
Width 2 [mm]	36											
<p>KH10399</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661077450</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>76</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b> MITSUBISHI MR594080</p>	EAN	192661077450	Inner diameter [mm]	40	Outer diameter [mm]	76	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	38
EAN	192661077450											
Inner diameter [mm]	40											
Outer diameter [mm]	76											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	38											
<p>KH10400</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661077467</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b> NISSAN 43210-8H300</p>	EAN	192661077467	Inner diameter [mm]	38	Outer diameter [mm]	79	Width [mm]	45		
EAN	192661077467											
Inner diameter [mm]	38											
Outer diameter [mm]	79											
Width [mm]	45											
<p>KH10401</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661077474</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>62</td> </tr> <tr> <td>Width [mm]</td> <td>31</td> </tr> </table> <p><b>OE No.</b> SUZUKI 09267-35003</p>	EAN	192661077474	Inner diameter [mm]	35	Outer diameter [mm]	62	Width [mm]	31		
EAN	192661077474											
Inner diameter [mm]	35											
Outer diameter [mm]	62											
Width [mm]	31											

Part Number	Pk.	Description												
KH10402 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077481</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>74</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>90080-36087</td> </tr> </table>	EAN	192661077481	Inner diameter [mm]	40	Outer diameter [mm]	74	Width [mm]	42	<b>OE No.</b>		TOYOTA	90080-36087
EAN	192661077481													
Inner diameter [mm]	40													
Outer diameter [mm]	74													
Width [mm]	42													
<b>OE No.</b>														
TOYOTA	90080-36087													
KH10403 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077498</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MAZDA</td> <td>GP9A33047A, GP9A33047B, GP9A33047C, GP9A33047D</td> </tr> </table>	EAN	192661077498	Inner diameter [mm]	45	Outer diameter [mm]	84	Width [mm]	45	<b>OE No.</b>		MAZDA	GP9A33047A, GP9A33047B, GP9A33047C, GP9A33047D
EAN	192661077498													
Inner diameter [mm]	45													
Outer diameter [mm]	84													
Width [mm]	45													
<b>OE No.</b>														
MAZDA	GP9A33047A, GP9A33047B, GP9A33047C, GP9A33047D													
KH10404 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080375</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>36.9</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>LANCIA</td> <td>82289841</td> </tr> </table>	EAN	192661080375	Inner diameter [mm]	36.9	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		LANCIA	82289841
EAN	192661080375													
Inner diameter [mm]	36.9													
Outer diameter [mm]	72													
Width [mm]	37													
<b>OE No.</b>														
LANCIA	82289841													
KH10405 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080924</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>RENAULT</td> <td>7701205692</td> </tr> </table>	EAN	192661080924	Inner diameter [mm]	42	Outer diameter [mm]	84	Width [mm]	39	<b>OE No.</b>		RENAULT	7701205692
EAN	192661080924													
Inner diameter [mm]	42													
Outer diameter [mm]	84													
Width [mm]	39													
<b>OE No.</b>														
RENAULT	7701205692													
KH10406 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080382</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>38</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>70</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>DAIHATSU</td> <td>90043-61387</td> </tr> </table>	EAN	192661080382	Inner diameter [mm]	38	Outer diameter [mm]	70	Width [mm]	38	<b>OE No.</b>		DAIHATSU	90043-61387
EAN	192661080382													
Inner diameter [mm]	38													
Outer diameter [mm]	70													
Width [mm]	38													
<b>OE No.</b>														
DAIHATSU	90043-61387													















Part Number	Pk.	Description														
<p>KH10407</p>	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>66</td> </tr> <tr> <td>Width [mm]</td> <td>33</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ALFA ROMEO</td> <td>46423870, 51753789, 71714466</td> </tr> <tr> <td>FIAT</td> <td>46423870, 51753789, 71714466</td> </tr> <tr> <td>LANCIA</td> <td>46423870, 51753789, 71714466</td> </tr> </table>	Inner diameter [mm]	35	Outer diameter [mm]	66	Width [mm]	33	<b>OE No.</b>		ALFA ROMEO	46423870, 51753789, 71714466	FIAT	46423870, 51753789, 71714466	LANCIA	46423870, 51753789, 71714466
Inner diameter [mm]	35															
Outer diameter [mm]	66															
Width [mm]	33															
<b>OE No.</b>																
ALFA ROMEO	46423870, 51753789, 71714466															
FIAT	46423870, 51753789, 71714466															
LANCIA	46423870, 51753789, 71714466															
<p>KH10408</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661080399</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>39</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 1 124 358</td> </tr> </table>	EAN	192661080399	Inner diameter [mm]	39	Outer diameter [mm]	72	Width [mm]	37	<b>OE No.</b>		BMW	33 41 1 124 358		
EAN	192661080399															
Inner diameter [mm]	39															
Outer diameter [mm]	72															
Width [mm]	37															
<b>OE No.</b>																
BMW	33 41 1 124 358															
<p>KH10409</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661080405</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>75</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>PORSCHE</td> <td>999 053 041 03</td> </tr> </table>	EAN	192661080405	Inner diameter [mm]	42	Outer diameter [mm]	75	Width [mm]	37	<b>OE No.</b>		PORSCHE	999 053 041 03		
EAN	192661080405															
Inner diameter [mm]	42															
Outer diameter [mm]	75															
Width [mm]	37															
<b>OE No.</b>																
PORSCHE	999 053 041 03															
<p>KH10410</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661080412</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>67</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42300-S2L-004, 42300-S2L-008</td> </tr> </table>	EAN	192661080412	Inner diameter [mm]	32	Outer diameter [mm]	67	Width [mm]	40	<b>OE No.</b>		HONDA	42300-S2L-004, 42300-S2L-008		
EAN	192661080412															
Inner diameter [mm]	32															
Outer diameter [mm]	67															
Width [mm]	40															
<b>OE No.</b>																
HONDA	42300-S2L-004, 42300-S2L-008															
<p>KH10411</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder in one of the seals. Use a Magnetic Encoder Detector to verify ABS side before mounting! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Inner diameter [mm]</td> <td>47</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>83</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1225764, 1S7J-1K018-AA</td> </tr> </table>	Inner diameter [mm]	47	Outer diameter [mm]	83	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37	<b>OE No.</b>		FORD	1225764, 1S7J-1K018-AA		
Inner diameter [mm]	47															
Outer diameter [mm]	83															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	37															
<b>OE No.</b>																
FORD	1225764, 1S7J-1K018-AA															






Part Number	Pk.	Description																
<p>KH10412</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width [mm]</td> <td>47</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>90369-35060</td> </tr> </table>	Inner diameter [mm]	35	Outer diameter [mm]	80	Width [mm]	47	<b>OE No.</b>		TOYOTA	90369-35060						
Inner diameter [mm]	35																	
Outer diameter [mm]	80																	
Width [mm]	47																	
<b>OE No.</b>																		
TOYOTA	90369-35060																	
<p>KH10413</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Width 1 [mm]</td> <td>33</td> </tr> <tr> <td>Width 2 [mm]</td> <td>36</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>09267-40001</td> </tr> </table>	Inner diameter [mm]	40	Outer diameter [mm]	72	Width 1 [mm]	33	Width 2 [mm]	36	<b>OE No.</b>		SUZUKI	09267-40001				
Inner diameter [mm]	40																	
Outer diameter [mm]	72																	
Width 1 [mm]	33																	
Width 2 [mm]	36																	
<b>OE No.</b>																		
SUZUKI	09267-40001																	
<p>KH10414</p> 	1	<table border="1"> <tr> <td>Fitting Position</td> <td>Front Axle</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>80</td> </tr> <tr> <td>Width 1 [mm]</td> <td>34</td> </tr> <tr> <td>Width 2 [mm]</td> <td>40</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51720-38000</td> </tr> </table>	Fitting Position	Front Axle	Inner diameter [mm]	42	Outer diameter [mm]	80	Width 1 [mm]	34	Width 2 [mm]	40	<b>OE No.</b>		HYUNDAI	51720-38000		
Fitting Position	Front Axle																	
Inner diameter [mm]	42																	
Outer diameter [mm]	80																	
Width 1 [mm]	34																	
Width 2 [mm]	40																	
<b>OE No.</b>																		
HYUNDAI	51720-38000																	
<p>KH10415</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79.7</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 210 981 02 27</td> </tr> </table>	Inner diameter [mm]	45	Outer diameter [mm]	79.7	Width [mm]	39	<b>OE No.</b>		MERCEDES-BENZ	A 210 981 02 27						
Inner diameter [mm]	45																	
Outer diameter [mm]	79.7																	
Width [mm]	39																	
<b>OE No.</b>																		
MERCEDES-BENZ	A 210 981 02 27																	
<p>KH20001</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176971716</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748.82, 3748.86, 3748.87</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748-82, 3748-86, 3748-87, 96 418 876 80</td> </tr> <tr> <td>PEUGEOT</td> <td>3748.82, 3748.86, 3748.87</td> </tr> </table>	EAN	29176971716	Outer diameter [mm]	128	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	<b>OE No.</b>		CITROËN	3748.82, 3748.86, 3748.87	CITROËN/PEUGEOT	3748-82, 3748-86, 3748-87, 96 418 876 80	PEUGEOT	3748.82, 3748.86, 3748.87
EAN	29176971716																	
Outer diameter [mm]	128																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
<b>OE No.</b>																		
CITROËN	3748.82, 3748.86, 3748.87																	
CITROËN/PEUGEOT	3748-82, 3748-86, 3748-87, 96 418 876 80																	
PEUGEOT	3748.82, 3748.86, 3748.87																	







Part Number	Pk.	Description										
<p>KH20002</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975943</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> PEUGEOT 3748.A6, 96 858 633 80</p>	EAN	29176975943	Outer diameter [mm]	128	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring		
EAN	29176975943											
Outer diameter [mm]	128											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH20003</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176976032</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> AUDI 1K0 501 611 G, 1K0 598 611, 8V0 598 611 A SEAT 1K0 501 611 G, 1K0 598 611, 8V0 598 611 A SKODA 8V0 598 611 A VW 1K0 501 611 G, 1K0 598 611, 8V0 598 611 A</p>	EAN	29176976032	Inner diameter [mm]	30	Outer diameter [mm]	136.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176976032											
Inner diameter [mm]	30											
Outer diameter [mm]	136.5											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH20004</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661041680</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> AUDI 1T0 598 611, 1T0 598 611 B, 3G0 598 611, 3G0 598 611 A, 5QF 598 611, 8S0 598 611 SEAT 1T0 598 611, 1T0 598 611 B, 3G0 598 611, 3G0 598 611 A, 5QF 598 611, 8S0 598 611 SKODA 1T0 598 611, 1T0 598 611 B, 3G0 598 611, 3G0 598 611 A, 5QF 598 611, 8S0 598 611 VW 1T0 598 611, 1T0 598 611 B, 3G0 598 611, 3G0 598 611 A, 5QF 598 611, 8S0 598 611</p>	EAN	192661041680	Inner diameter [mm]	32	Outer diameter [mm]	136.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661041680											
Inner diameter [mm]	32											
Outer diameter [mm]	136.5											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH20005</p> 	1	<table border="1"> <tr> <td>Axle Stub Diameter [mm]</td> <td>35</td> </tr> <tr> <td>EAN</td> <td>29176980855</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>52.7</td> </tr> </table> <p><b>OE No.</b> CITROËN 160 812 83 80, 3748 A7 MITSUBISHI 3785 A002, 3785 A026 PEUGEOT 160 812 83 80, 3748 A7</p>	Axle Stub Diameter [mm]	35	EAN	29176980855	Rim Hole Number	4	Width [mm]	52.7		
Axle Stub Diameter [mm]	35											
EAN	29176980855											
Rim Hole Number	4											
Width [mm]	52.7											
<p>KH20006</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176994128</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> HONDA 42200-SAA-003, 42200-SAA-G01, 42200-SAA-G02</p>	EAN	29176994128	Outer diameter [mm]	134	Supplementary Article/Info 2	with integrated magnetic sensor ring				
EAN	29176994128											
Outer diameter [mm]	134											
Supplementary Article/Info 2	with integrated magnetic sensor ring											

Part Number	Pk.	Description										
<p>KH20007</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176994135</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> HONDA 42200-SAA-G51, 42200-SAH-G51</p>	EAN	29176994135	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated magnetic sensor ring				
EAN	29176994135											
Outer diameter [mm]	136											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH20008</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661043387</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> AUDI 4H0 498 625, 4H0 498 625 A, 4H0 498 625 B, 4H0 498 625 C, 4H0 498 625 D, 4H0 498 625 E, 8K0 407 625, 8K0 407 625 A, 8K0 407 625 G, 8K0 407 625 J, 8K0 598 625 PORSCHE 8K0 704 625 B</p>	EAN	192661043387	Outer diameter [mm]	126	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring		
EAN	192661043387											
Outer diameter [mm]	126											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH20009</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013816</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>121</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width 1 [mm]</td> <td>63</td> </tr> </table> <p><b>OE No.</b> AUDI 6Q0 598 611, 6Q0 598 611 F, 8X0 598 611 SEAT 6Q0 598 611, 6Q0 598 611 F, 8X0 598 611 SKODA 6Q0 598 611, 6Q0 598 611 F, 8X0 598 611 VW 6Q0 598 611, 6Q0 598 611 F, 8X0 598 611</p>	EAN	192661013816	Outer diameter [mm]	121	Rim Hole Number	5	Width 1 [mm]	63		
EAN	192661013816											
Outer diameter [mm]	121											
Rim Hole Number	5											
Width 1 [mm]	63											
<p>KH20010</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661016978</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> </table> <p><b>OE No.</b> AUDI 1J0 598 477 SEAT 1J0 598 477 SKODA 1J0 598 477 VW 1J0 598 477</p>	EAN	192661016978	Inner diameter [mm]	30	Outer diameter [mm]	120	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring
EAN	192661016978											
Inner diameter [mm]	30											
Outer diameter [mm]	120											
Rim Hole Number	5											
Supplementary Article/Info 2	with ABS sensor ring											
<p>KH20011</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661012215</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> </table> <p><b>OE No.</b> FORD 1377907, 6C11-1K018-AA</p>	EAN	192661012215	Inner diameter [mm]	45	Outer diameter [mm]	117	Rim Hole Number	5		
EAN	192661012215											
Inner diameter [mm]	45											
Outer diameter [mm]	117											
Rim Hole Number	5											







Part Number	Pk.	Description																		
<p>KH20012</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010396</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.1</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 68</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 68</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 68</td> </tr> </table>	EAN	192661010396	Inner diameter [mm]	32	Outer diameter [mm]	129.1	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	<b>OE No.</b>		CITROËN	3748 68	CITROËN/PEUGEOT	3748 68	PEUGEOT	3748 68
EAN	192661010396																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129.1																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
<b>OE No.</b>																				
CITROËN	3748 68																			
CITROËN/PEUGEOT	3748 68																			
PEUGEOT	3748 68																			
<p>KH20013</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010402</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.1</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 80</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 80</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 80</td> </tr> </table>	EAN	192661010402	Inner diameter [mm]	32	Outer diameter [mm]	129.1	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	<b>OE No.</b>		CITROËN	3748 80	CITROËN/PEUGEOT	3748 80	PEUGEOT	3748 80
EAN	192661010402																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129.1																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
<b>OE No.</b>																				
CITROËN	3748 80																			
CITROËN/PEUGEOT	3748 80																			
PEUGEOT	3748 80																			
<p>KH20014</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010419</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.1</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 43</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 43</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 43</td> </tr> </table>	EAN	192661010419	Inner diameter [mm]	32	Outer diameter [mm]	129.1	Rim Hole Number	4	<b>OE No.</b>		CITROËN	3748 43	CITROËN/PEUGEOT	3748 43	PEUGEOT	3748 43		
EAN	192661010419																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129.1																			
Rim Hole Number	4																			
<b>OE No.</b>																				
CITROËN	3748 43																			
CITROËN/PEUGEOT	3748 43																			
PEUGEOT	3748 43																			
<p>KH20015</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661010426</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.1</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 28</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 28</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 28</td> </tr> </table>	EAN	192661010426	Inner diameter [mm]	32	Outer diameter [mm]	129.1	Rim Hole Number	4	<b>OE No.</b>		CITROËN	3748 28	CITROËN/PEUGEOT	3748 28	PEUGEOT	3748 28		
EAN	192661010426																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129.1																			
Rim Hole Number	4																			
<b>OE No.</b>																				
CITROËN	3748 28																			
CITROËN/PEUGEOT	3748 28																			
PEUGEOT	3748 28																			
<p>KH20016</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010433</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.1</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 88</td> </tr> <tr> <td>CITROËN/PEUGEOT</td> <td>3748 88</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 88</td> </tr> </table>	EAN	192661010433	Inner diameter [mm]	32	Outer diameter [mm]	129.1	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	<b>OE No.</b>		CITROËN	3748 88	CITROËN/PEUGEOT	3748 88	PEUGEOT	3748 88
EAN	192661010433																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129.1																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
<b>OE No.</b>																				
CITROËN	3748 88																			
CITROËN/PEUGEOT	3748 88																			
PEUGEOT	3748 88																			

Part Number	Pk.	Description																
<p>KH20017</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661013106</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150</td> </tr> </table>	EAN	192661013106	Inner diameter [mm]	30	Outer diameter [mm]	120	Supplementary Article/Info 2	with integrated magnetic sensor ring	OPEL	16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150	VAUXHALL	16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150				
EAN	192661013106																	
Inner diameter [mm]	30																	
Outer diameter [mm]	120																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
OPEL	16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150																	
VAUXHALL	16 04 017, 16 04 018, 16 04 358, 4 20 004, 93168760, 93190215, 95512288, 95517150																	
<p>KH20018</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661012222</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1377908, 6C11-1K018-BA</td> </tr> </table>	EAN	192661012222	Inner diameter [mm]	49	Outer diameter [mm]	125.5	Rim Hole Number	5	FORD	1377908, 6C11-1K018-BA						
EAN	192661012222																	
Inner diameter [mm]	49																	
Outer diameter [mm]	125.5																	
Rim Hole Number	5																	
FORD	1377908, 6C11-1K018-BA																	
<p>KH20020</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661013113</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>131.25</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1223640, 1326487, 1336139, 1471854, 3M51-2C300-CA, 3M51-2C300-CF, 3M51-2C300-CG, 3M51-2C300-CH</td> </tr> </table>	EAN	192661013113	Outer diameter [mm]	131.25	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	FORD	1223640, 1326487, 1336139, 1471854, 3M51-2C300-CA, 3M51-2C300-CF, 3M51-2C300-CG, 3M51-2C300-CH						
EAN	192661013113																	
Outer diameter [mm]	131.25																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
FORD	1223640, 1326487, 1336139, 1471854, 3M51-2C300-CA, 3M51-2C300-CF, 3M51-2C300-CG, 3M51-2C300-CH																	
<p>KH20021</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661013625</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>121</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SEAT</td> <td>1S0 598 611</td> </tr> <tr> <td>SKODA</td> <td>1S0 598 611</td> </tr> <tr> <td>VW</td> <td>1S0 598 611</td> </tr> </table>	EAN	192661013625	Inner diameter [mm]	28	Outer diameter [mm]	121	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	SEAT	1S0 598 611	SKODA	1S0 598 611	VW	1S0 598 611
EAN	192661013625																	
Inner diameter [mm]	28																	
Outer diameter [mm]	121																	
Rim Hole Number	4																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
SEAT	1S0 598 611																	
SKODA	1S0 598 611																	
VW	1S0 598 611																	



Part Number	Pk.	Description																								
<p>KH20022</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661013823</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>ABARTH</td> <td>46512973, 46519901, 51754193, 60815429</td> </tr> <tr> <td>ALFA ROMEO</td> <td>46512973, 46519901, 51754193, 60815429</td> </tr> <tr> <td>CITROËN</td> <td>16 066 353 80, 3701 84</td> </tr> <tr> <td>FIAT</td> <td>46512973, 46519901, 51754193, 60815429</td> </tr> <tr> <td>FORD</td> <td>1730689, BS51-1A034-AA</td> </tr> <tr> <td>LANCIA</td> <td>46512973, 46519901, 51754193, 60815429</td> </tr> <tr> <td>PEUGEOT</td> <td>16 066 353 80, 3701 84</td> </tr> </table>	EAN	192661013823	Inner diameter [mm]	30	Outer diameter [mm]	117	Rim Hole Number	4	<b>OE No.</b>		ABARTH	46512973, 46519901, 51754193, 60815429	ALFA ROMEO	46512973, 46519901, 51754193, 60815429	CITROËN	16 066 353 80, 3701 84	FIAT	46512973, 46519901, 51754193, 60815429	FORD	1730689, BS51-1A034-AA	LANCIA	46512973, 46519901, 51754193, 60815429	PEUGEOT	16 066 353 80, 3701 84
EAN	192661013823																									
Inner diameter [mm]	30																									
Outer diameter [mm]	117																									
Rim Hole Number	4																									
<b>OE No.</b>																										
ABARTH	46512973, 46519901, 51754193, 60815429																									
ALFA ROMEO	46512973, 46519901, 51754193, 60815429																									
CITROËN	16 066 353 80, 3701 84																									
FIAT	46512973, 46519901, 51754193, 60815429																									
FORD	1730689, BS51-1A034-AA																									
LANCIA	46512973, 46519901, 51754193, 60815429																									
PEUGEOT	16 066 353 80, 3701 84																									
<p>KH20023</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661024041</td> </tr> <tr> <td>Inner diameter 1 [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>193</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1377911, 6C11-1A049-BA</td> </tr> </table>	EAN	192661024041	Inner diameter 1 [mm]	37	Outer diameter [mm]	193	Rim Hole Number	5	<b>OE No.</b>		FORD	1377911, 6C11-1A049-BA												
EAN	192661024041																									
Inner diameter 1 [mm]	37																									
Outer diameter [mm]	193																									
Rim Hole Number	5																									
<b>OE No.</b>																										
FORD	1377911, 6C11-1A049-BA																									
<p>KH20024</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661016985</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120.6</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>72</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SKODA</td> <td>6Q0 407 621 BG, 6Q0 407 621 BH, 6Q0 407 621 CA, 6Q0 407 621 CB, 6R0 407 621 F, 6R0 407 621 G</td> </tr> </table>	EAN	192661016985	Outer diameter [mm]	120.6	Outer diameter 2 [mm]	72	Supplementary Article/Info 2	with integrated magnetic sensor ring	<b>OE No.</b>		SKODA	6Q0 407 621 BG, 6Q0 407 621 BH, 6Q0 407 621 CA, 6Q0 407 621 CB, 6R0 407 621 F, 6R0 407 621 G												
EAN	192661016985																									
Outer diameter [mm]	120.6																									
Outer diameter 2 [mm]	72																									
Supplementary Article/Info 2	with integrated magnetic sensor ring																									
<b>OE No.</b>																										
SKODA	6Q0 407 621 BG, 6Q0 407 621 BH, 6Q0 407 621 CA, 6Q0 407 621 CB, 6R0 407 621 F, 6R0 407 621 G																									
<p>KH20025</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661014691</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>149.4</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VW</td> <td>7H0 401 611 D, 7H0 401 611 E, 7H0 401 611 H, 7L0 498 611</td> </tr> </table>	EAN	192661014691	Outer diameter [mm]	149.4	Rim Hole Number	5	<b>OE No.</b>		VW	7H0 401 611 D, 7H0 401 611 E, 7H0 401 611 H, 7L0 498 611														
EAN	192661014691																									
Outer diameter [mm]	149.4																									
Rim Hole Number	5																									
<b>OE No.</b>																										
VW	7H0 401 611 D, 7H0 401 611 E, 7H0 401 611 H, 7L0 498 611																									
<p>KH20026</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661014707</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>149.4</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VW</td> <td>7H0 498 611</td> </tr> </table>	EAN	192661014707	Outer diameter [mm]	149.4	Rim Hole Number	5	<b>OE No.</b>		VW	7H0 498 611														
EAN	192661014707																									
Outer diameter [mm]	149.4																									
Rim Hole Number	5																									
<b>OE No.</b>																										
VW	7H0 498 611																									






Part Number	Pk.	Description														
<p>KH20027</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661016992</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>120.7</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>66</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>82.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SKODA</td> <td>6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C</td> </tr> <tr> <td>VW</td> <td>6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C</td> </tr> </table>	EAN	192661016992	Outer diameter 1 [mm]	120.7	Outer diameter 2 [mm]	66	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	82.5	SKODA	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C	VW	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C
EAN	192661016992															
Outer diameter 1 [mm]	120.7															
Outer diameter 2 [mm]	66															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	82.5															
SKODA	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C															
VW	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C															
<p>KH20028</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661017005</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>120.7</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>66</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>82.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SKODA</td> <td>6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C</td> </tr> <tr> <td>VW</td> <td>6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C</td> </tr> </table>	EAN	192661017005	Outer diameter 1 [mm]	120.7	Outer diameter 2 [mm]	66	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	82.5	SKODA	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C	VW	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C
EAN	192661017005															
Outer diameter 1 [mm]	120.7															
Outer diameter 2 [mm]	66															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	82.5															
SKODA	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C															
VW	6Q0 407 621 AB, 6Q0 407 621 AF, 6Q0 407 621 AL, 6Q0 407 621 BK, 6Q0 407 621 BP, 6R0 407 621 C															
<p>KH20029</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661023808</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>193</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1377912, 6C11-1A049-DA</td> </tr> </table>	EAN	192661023808	Outer diameter [mm]	193	Rim Hole Number	5	FORD	1377912, 6C11-1A049-DA						
EAN	192661023808															
Outer diameter [mm]	193															
Rim Hole Number	5															
FORD	1377912, 6C11-1A049-DA															
<p>KH20030</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661019337</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>1604020, 1604360, 93190216, 95517093</td> </tr> <tr> <td>VAUXHALL</td> <td>1604020, 1604360, 93190216, 95517093</td> </tr> </table>	EAN	192661019337	Inner diameter [mm]	30	Outer diameter [mm]	120	Supplementary Article/Info 2	with integrated magnetic sensor ring	OPEL	1604020, 1604360, 93190216, 95517093	VAUXHALL	1604020, 1604360, 93190216, 95517093		
EAN	192661019337															
Inner diameter [mm]	30															
Outer diameter [mm]	120															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
OPEL	1604020, 1604360, 93190216, 95517093															
VAUXHALL	1604020, 1604360, 93190216, 95517093															














Part Number	Pk.	Description																
<p>KH20031</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661037607</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42.25</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A</td> </tr> <tr> <td>VW</td> <td>3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A</td> </tr> </table>	EAN	192661037607	Inner diameter [mm]	45	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	42.25	AUDI	3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A	VW	3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A				
EAN	192661037607																	
Inner diameter [mm]	45																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	42.25																	
AUDI	3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A																	
VW	3D0 498 607, 3D0 498 607 A, 4E0 498 625 B, 4F0 498 625 A, 4F0 598 625 A																	
<p>KH20032</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661045190</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>82</td> </tr> <tr> <td>Width [mm]</td> <td>40.25</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>8E0 498 625 B</td> </tr> <tr> <td>SEAT</td> <td>8E0 498 625 B</td> </tr> <tr> <td>SKODA</td> <td>8E0 498 625 B</td> </tr> <tr> <td>VW</td> <td>8E0 498 625 B</td> </tr> </table>	EAN	192661045190	Inner diameter [mm]	43	Outer diameter [mm]	82	Width [mm]	40.25	AUDI	8E0 498 625 B	SEAT	8E0 498 625 B	SKODA	8E0 498 625 B	VW	8E0 498 625 B
EAN	192661045190																	
Inner diameter [mm]	43																	
Outer diameter [mm]	82																	
Width [mm]	40.25																	
AUDI	8E0 498 625 B																	
SEAT	8E0 498 625 B																	
SKODA	8E0 498 625 B																	
VW	8E0 498 625 B																	
<p>KH20033</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661043394</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>143</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>BMW</td> <td>31 22 6 757 024, 6 757 024</td> </tr> </table>	EAN	192661043394	Outer diameter [mm]	143	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	BMW	31 22 6 757 024, 6 757 024						
EAN	192661043394																	
Outer diameter [mm]	143																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with ABS sensor ring																	
BMW	31 22 6 757 024, 6 757 024																	
<p>KH20034</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661043400</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>ALFA ROMEO</td> <td>51754192, 71737612, 71737613</td> </tr> <tr> <td>FIAT</td> <td>51754192, 71737612, 71737613</td> </tr> <tr> <td>LANCIA</td> <td>51754192, 71737612, 71737613</td> </tr> </table>	EAN	192661043400	Outer diameter [mm]	117	Rim Hole Number	4	ALFA ROMEO	51754192, 71737612, 71737613	FIAT	51754192, 71737612, 71737613	LANCIA	51754192, 71737612, 71737613				
EAN	192661043400																	
Outer diameter [mm]	117																	
Rim Hole Number	4																	
ALFA ROMEO	51754192, 71737612, 71737613																	
FIAT	51754192, 71737612, 71737613																	
LANCIA	51754192, 71737612, 71737613																	
<p>KH20035</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661043417</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>129</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>91</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>65</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3748 72</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 72</td> </tr> </table>	EAN	192661043417	Inner diameter [mm]	25	Outer diameter 1 [mm]	129	Outer diameter 2 [mm]	91	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	65	CITROËN	3748 72	PEUGEOT	3748 72
EAN	192661043417																	
Inner diameter [mm]	25																	
Outer diameter 1 [mm]	129																	
Outer diameter 2 [mm]	91																	
Supplementary Article/Info 2	with ABS sensor ring																	
Width [mm]	65																	
CITROËN	3748 72																	
PEUGEOT	3748 72																	





Part Number	Pk.	Description																				
KH20036 	1	<table border="1"> <tr> <td>EAN</td> <td>192661043424</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>133</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>70</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>73.4</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 204 667, 77 04 002 263</td> </tr> </table>	EAN	192661043424	Inner diameter [mm]	25	Outer diameter 1 [mm]	133	Outer diameter 2 [mm]	70	Rim Hole Number	4	Width [mm]	73.4	<b>OE No.</b>		RENAULT	77 01 204 667, 77 04 002 263				
EAN	192661043424																					
Inner diameter [mm]	25																					
Outer diameter 1 [mm]	133																					
Outer diameter 2 [mm]	70																					
Rim Hole Number	4																					
Width [mm]	73.4																					
<b>OE No.</b>																						
RENAULT	77 01 204 667, 77 04 002 263																					
KH20037 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052358</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>71747713</td> </tr> </table>	EAN	192661052358	Outer diameter [mm]	120	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	<b>OE No.</b>		FIAT	71747713								
EAN	192661052358																					
Outer diameter [mm]	120																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
<b>OE No.</b>																						
FIAT	71747713																					
KH20038 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049228</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>31</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748.69</td> </tr> <tr> <td>PEUGEOT</td> <td>3748.69</td> </tr> </table>	EAN	192661049228	Inner diameter [mm]	31	Number of Teeth, ABS ring	48	Outer diameter [mm]	128	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	59	<b>OE No.</b>		CITROËN	3748.69	PEUGEOT	3748.69
EAN	192661049228																					
Inner diameter [mm]	31																					
Number of Teeth, ABS ring	48																					
Outer diameter [mm]	128																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	59																					
<b>OE No.</b>																						
CITROËN	3748.69																					
PEUGEOT	3748.69																					
KH20039 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049235</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>78</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1201300, 1C1J-1K018-AA, 4052783</td> </tr> </table>	EAN	192661049235	Inner diameter [mm]	45	Outer diameter [mm]	78	Rim Hole Number	5	Width [mm]	53	<b>OE No.</b>		FORD	1201300, 1C1J-1K018-AA, 4052783						
EAN	192661049235																					
Inner diameter [mm]	45																					
Outer diameter [mm]	78																					
Rim Hole Number	5																					
Width [mm]	53																					
<b>OE No.</b>																						
FORD	1201300, 1C1J-1K018-AA, 4052783																					
KH20040 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049242</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>130</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>8E0598611</td> </tr> <tr> <td>SEAT</td> <td>8E0598611</td> </tr> </table>	EAN	192661049242	Inner diameter [mm]	32	Number of Teeth, ABS ring	44	Outer diameter [mm]	130	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	49	<b>OE No.</b>		AUDI	8E0598611	SEAT	8E0598611
EAN	192661049242																					
Inner diameter [mm]	32																					
Number of Teeth, ABS ring	44																					
Outer diameter [mm]	130																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	49																					
<b>OE No.</b>																						
AUDI	8E0598611																					
SEAT	8E0598611																					

Part Number	Pk.	Description																		
<p>KH20041</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049259</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>86</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="1"> <tr> <td> <table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661049259	Inner diameter [mm]	50	Outer diameter [mm]	86	Rim Hole Number	4	Width [mm]	55	<b>OE No.</b>		<table border="1"> <tr> <td> <table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table>	MITSUBISHI	3885A013		
EAN	192661049259																			
Inner diameter [mm]	50																			
Outer diameter [mm]	86																			
Rim Hole Number	4																			
Width [mm]	55																			
<b>OE No.</b>																				
<table border="1"> <tr> <td> <table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table>	MITSUBISHI	3885A013																	
<table border="1"> <tr> <td>MITSUBISHI</td> <td>3885A013</td> </tr> </table>	MITSUBISHI	3885A013																		
MITSUBISHI	3885A013																			
<p>KH20042</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049266</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>69.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="1"> <tr> <td>VW</td> <td>1T0 598 611 A</td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661049266	Inner diameter [mm]	32	Outer diameter [mm]	137	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	69.5	<b>OE No.</b>		<table border="1"> <tr> <td>VW</td> <td>1T0 598 611 A</td> </tr> </table>	VW	1T0 598 611 A	
EAN	192661049266																			
Inner diameter [mm]	32																			
Outer diameter [mm]	137																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	69.5																			
<b>OE No.</b>																				
<table border="1"> <tr> <td>VW</td> <td>1T0 598 611 A</td> </tr> </table>	VW	1T0 598 611 A																		
VW	1T0 598 611 A																			
<p>KH20044</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049273</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>88</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="1"> <tr> <td>FIAT</td> <td>6000609410</td> </tr> <tr> <td>MITSUBISHI</td> <td>MB992372, MR992374</td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661049273	Inner diameter [mm]	50	Outer diameter [mm]	88	Width [mm]	55	<b>OE No.</b>		<table border="1"> <tr> <td>FIAT</td> <td>6000609410</td> </tr> <tr> <td>MITSUBISHI</td> <td>MB992372, MR992374</td> </tr> </table>	FIAT	6000609410	MITSUBISHI	MB992372, MR992374			
EAN	192661049273																			
Inner diameter [mm]	50																			
Outer diameter [mm]	88																			
Width [mm]	55																			
<b>OE No.</b>																				
<table border="1"> <tr> <td>FIAT</td> <td>6000609410</td> </tr> <tr> <td>MITSUBISHI</td> <td>MB992372, MR992374</td> </tr> </table>	FIAT	6000609410	MITSUBISHI	MB992372, MR992374																
FIAT	6000609410																			
MITSUBISHI	MB992372, MR992374																			
<p>KH20045</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049280</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="1"> <tr> <td>FORD</td> <td>1437643, 6G91-2C300-AAB</td> </tr> <tr> <td>LAND ROVER</td> <td>LR003157</td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661049280	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	<b>OE No.</b>		<table border="1"> <tr> <td>FORD</td> <td>1437643, 6G91-2C300-AAB</td> </tr> <tr> <td>LAND ROVER</td> <td>LR003157</td> </tr> </table>	FORD	1437643, 6G91-2C300-AAB	LAND ROVER	LR003157			
EAN	192661049280																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
<b>OE No.</b>																				
<table border="1"> <tr> <td>FORD</td> <td>1437643, 6G91-2C300-AAB</td> </tr> <tr> <td>LAND ROVER</td> <td>LR003157</td> </tr> </table>	FORD	1437643, 6G91-2C300-AAB	LAND ROVER	LR003157																
FORD	1437643, 6G91-2C300-AAB																			
LAND ROVER	LR003157																			
<p>KH20046</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049297</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>58</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="1"> <tr> <td>CITROËN</td> <td>3701 42, 95619162</td> </tr> <tr> <td>PEUGEOT</td> <td>3701 42, 95619162</td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661049297	Inner diameter [mm]	32	Outer diameter [mm]	128	Rim Hole Number	4	Width [mm]	58	<b>OE No.</b>		<table border="1"> <tr> <td>CITROËN</td> <td>3701 42, 95619162</td> </tr> <tr> <td>PEUGEOT</td> <td>3701 42, 95619162</td> </tr> </table>	CITROËN	3701 42, 95619162	PEUGEOT	3701 42, 95619162	
EAN	192661049297																			
Inner diameter [mm]	32																			
Outer diameter [mm]	128																			
Rim Hole Number	4																			
Width [mm]	58																			
<b>OE No.</b>																				
<table border="1"> <tr> <td>CITROËN</td> <td>3701 42, 95619162</td> </tr> <tr> <td>PEUGEOT</td> <td>3701 42, 95619162</td> </tr> </table>	CITROËN	3701 42, 95619162	PEUGEOT	3701 42, 95619162																
CITROËN	3701 42, 95619162																			
PEUGEOT	3701 42, 95619162																			






Part Number	Pk.	Description
KH20047 	1	EAN   192661049303
		Inner diameter [mm]   30
		Number of Teeth, ABS ring   44
		Outer diameter [mm]   119
		Rim Hole Number   4
		Supplementary Article/Info 2   with ABS sensor ring
		Width [mm]   61
		<b>OE No.</b>
		ALFA ROMEO   60812057, 7769902
		FIAT   60812057, 7769902
		LANCIA   60812057, 7769902
KH20048 	1	EAN   192661049310
		Inner diameter [mm]   25
		Number of Teeth, ABS ring   29
		Outer diameter [mm]   128
		Rim Hole Number   4
		Supplementary Article/Info 2   with ABS sensor ring
		Width [mm]   71
		<b>OE No.</b>
		CITROËN   3748 31
		PEUGEOT   3748 31
KH20049 	1	EAN   192661052365
		Inner diameter [mm]   35
		Outer diameter [mm]   116
		Rim Hole Number   5
		Width [mm]   63.5
		<b>OE No.</b>
		ALFA ROMEO   60652014
KH20050 	1	EAN   192661049327
		Inner diameter [mm]   25
		Outer diameter [mm]   133
		Rim Hole Number   4
		Supplementary Article/Info 2   with ABS sensor ring
		Width [mm]   54
		<b>OE No.</b>
		RENAULT   77 01 205 499
KH20051 	1	<b>Safety information</b>
		This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!
		EAN   192661049334
		Inner diameter [mm]   35
		Outer diameter [mm]   128
		Rim Hole Number   5
		Supplementary Article/Info 2   with integrated magnetic sensor ring
		Width [mm]   69
		<b>OE No.</b>
		ALFA ROMEO   51754195, 60652720



Part Number	Pk.	Description																						
<p>KH20052</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052372</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>63</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SEAT</td> <td>6K9 501 477</td> </tr> <tr> <td>VW</td> <td>6K9 501 477</td> </tr> </table>	EAN	192661052372	Inner diameter [mm]	29	Outer diameter [mm]	120	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	63	<b>OE No.</b>		SEAT	6K9 501 477	VW	6K9 501 477				
EAN	192661052372																							
Inner diameter [mm]	29																							
Outer diameter [mm]	120																							
Rim Hole Number	4																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	63																							
<b>OE No.</b>																								
SEAT	6K9 501 477																							
VW	6K9 501 477																							
<p>KH20053</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049341</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 70</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 70</td> </tr> </table>	EAN	192661049341	Inner diameter [mm]	32	Outer diameter [mm]	129	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	38	<b>OE No.</b>		CITROËN	3748 70	PEUGEOT	3748 70				
EAN	192661049341																							
Inner diameter [mm]	32																							
Outer diameter [mm]	129																							
Rim Hole Number	4																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
Width [mm]	38																							
<b>OE No.</b>																								
CITROËN	3748 70																							
PEUGEOT	3748 70																							
<p>KH20054</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049358</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>20</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>47</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SMART</td> <td>0001870V023000000</td> </tr> </table>	EAN	192661049358	Inner diameter [mm]	20	Number of Teeth, ABS ring	42	Outer diameter [mm]	134	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	47	<b>OE No.</b>		SMART	0001870V023000000						
EAN	192661049358																							
Inner diameter [mm]	20																							
Number of Teeth, ABS ring	42																							
Outer diameter [mm]	134																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	47																							
<b>OE No.</b>																								
SMART	0001870V023000000																							
<p>KH20055</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049365</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>69</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3350 71</td> </tr> <tr> <td>FIAT</td> <td>9403350718</td> </tr> <tr> <td>LANCIA</td> <td>9403350718</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 71</td> </tr> </table>	EAN	192661049365	Inner diameter [mm]	30	Outer diameter [mm]	120	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	69	<b>OE No.</b>		CITROËN	3350 71	FIAT	9403350718	LANCIA	9403350718	PEUGEOT	3350 71
EAN	192661049365																							
Inner diameter [mm]	30																							
Outer diameter [mm]	120																							
Rim Hole Number	5																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
Width [mm]	69																							
<b>OE No.</b>																								
CITROËN	3350 71																							
FIAT	9403350718																							
LANCIA	9403350718																							
PEUGEOT	3350 71																							

Part Number	Pk.	Description
<p>KH20056</p> 	1	<p>EAN   192661049372</p> <p>Inner diameter [mm]   25</p> <p>Number of Teeth, ABS ring   48</p> <p>Outer diameter [mm]   129</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   59</p> <p><b>OE No.</b></p> <p>CITROËN   3748 41</p> <p>PEUGEOT   3748 41</p>
<p>KH20057</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049389</p> <p>Inner diameter [mm]   43</p> <p>Outer diameter [mm]   85</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   40</p> <p><b>OE No.</b></p> <p>AUDI   4E0 598 625</p>
<p>KH20058</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049396</p> <p>Inner diameter [mm]   30</p> <p>Outer diameter [mm]   116</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   45</p> <p><b>OE No.</b></p> <p>ALFA ROMEO   51757885</p>
<p>KH20059</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049402</p> <p>Inner diameter [mm]   42</p> <p>Outer diameter [mm]   160</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   103</p> <p><b>OE No.</b></p> <p>CITROËN   3701 83</p> <p>FIAT   517549410, 71753810</p> <p>PEUGEOT   3701 83</p>













Part Number	Pk.	Description																		
<p>KH20060</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049419</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>31</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 21 1 128 569, 31 21 1 129 576, 31 21 1 131 297</td> </tr> </table>	EAN	192661049419	Inner diameter [mm]	31	Number of Teeth, ABS ring	48	Outer diameter [mm]	120	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	61	<b>OE No.</b>		BMW	31 21 1 128 569, 31 21 1 129 576, 31 21 1 131 297
EAN	192661049419																			
Inner diameter [mm]	31																			
Number of Teeth, ABS ring	48																			
Outer diameter [mm]	120																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	61																			
<b>OE No.</b>																				
BMW	31 21 1 128 569, 31 21 1 129 576, 31 21 1 131 297																			
<p>KH20061</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049426</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>74</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 89</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 89</td> </tr> </table>	EAN	192661049426	Inner diameter [mm]	32	Outer diameter [mm]	129	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	74	<b>OE No.</b>		CITROËN	3748 89	PEUGEOT	3748 89
EAN	192661049426																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	74																			
<b>OE No.</b>																				
CITROËN	3748 89																			
PEUGEOT	3748 89																			
<p>KH20062</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049433</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A 230 981 01 27</td> </tr> </table>	EAN	192661049433	Inner diameter [mm]	49	Outer diameter [mm]	126	Rim Hole Number	4	Width [mm]	42	<b>OE No.</b>		MERCEDES-BENZ	A 230 981 01 27				
EAN	192661049433																			
Inner diameter [mm]	49																			
Outer diameter [mm]	126																			
Rim Hole Number	4																			
Width [mm]	42																			
<b>OE No.</b>																				
MERCEDES-BENZ	A 230 981 01 27																			
<p>KH20063</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052389</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>51.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>43570-60010, 43570-60011</td> </tr> </table>	EAN	192661052389	Inner diameter [mm]	54	Outer diameter [mm]	96	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	51.5	<b>OE No.</b>		TOYOTA	43570-60010, 43570-60011				
EAN	192661052389																			
Inner diameter [mm]	54																			
Outer diameter [mm]	96																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	51.5																			
<b>OE No.</b>																				
TOYOTA	43570-60010, 43570-60011																			
<p>KH20064</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049440</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>142</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>8K0 598 611 A</td> </tr> </table>	EAN	192661049440	Inner diameter [mm]	32	Outer diameter [mm]	142	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	<b>OE No.</b>		AUDI	8K0 598 611 A		
EAN	192661049440																			
Inner diameter [mm]	32																			
Outer diameter [mm]	142																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	50																			
<b>OE No.</b>																				
AUDI	8K0 598 611 A																			

Part Number	Pk.	Description												
KH20065	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049457</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67.5</td> </tr> </table> <p><b>OE No.</b> HONDA 42200-TF0-N51</p>	EAN	192661049457	Inner diameter [mm]	30	Outer diameter [mm]	139	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67.5		
EAN	192661049457													
Inner diameter [mm]	30													
Outer diameter [mm]	139													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	67.5													
KH20066	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049464</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>107</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>40</td> </tr> </table> <p><b>OE No.</b> RENAULT 77 01 208 966, 82 00 416 590</p>	EAN	192661049464	Inner diameter [mm]	45	Outer diameter [mm]	107	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	40
EAN	192661049464													
Inner diameter [mm]	45													
Outer diameter [mm]	107													
Rim Hole Number	4													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	40													
KH20067	1	<table border="1"> <tr> <td>EAN</td> <td>192661049471</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>124</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> </table> <p><b>OE No.</b> BMW 33 41 1 095 238, 33 41 1 095 652, 33 41 1 095 654</p>	EAN	192661049471	Inner diameter [mm]	45	Outer diameter [mm]	124	Rim Hole Number	4	Width [mm]	41		
EAN	192661049471													
Inner diameter [mm]	45													
Outer diameter [mm]	124													
Rim Hole Number	4													
Width [mm]	41													
KH20068	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049488</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO 51813925, 60652011, 60671437, 71714478 LANCIA 51813925, 60652011, 60671437, 71714478</p>	EAN	192661049488	Inner diameter [mm]	42	Outer diameter [mm]	126	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37
EAN	192661049488													
Inner diameter [mm]	42													
Outer diameter [mm]	126													
Rim Hole Number	4													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	37													
KH20069	1	<table border="1"> <tr> <td>EAN</td> <td>192661049495</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> </table> <p><b>OE No.</b> HONDA 42200-S5A-J01</p>	EAN	192661049495	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	139	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	67
EAN	192661049495													
Inner diameter [mm]	30													
Number of Teeth, ABS ring	50													
Outer diameter [mm]	139													
Supplementary Article/Info 2	with ABS sensor ring													
Width [mm]	67													













Part Number	Pk.	Description
<p>KH20070</p> 	1	<p>EAN 192661049501</p> <p>Inner diameter [mm] 30</p> <p>Number of Teeth, ABS ring 50</p> <p>Outer diameter [mm] 152</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with ABS sensor ring</p> <p>Width [mm] 69</p> <p><b>OE No.</b></p> <p>HONDA 42200-S7A-008</p>
<p>KH20071</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661052396</p> <p>Inner diameter [mm] 43</p> <p>Outer diameter [mm] 85</p> <p>Rim Hole Number 4</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 40</p> <p><b>OE No.</b></p> <p>AUDI 4F0 498 625, 4F0 498 625 B</p>
<p>KH20072</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661049518</p> <p>Outer diameter [mm] 137</p> <p>Rim Hole Number 4</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 59</p> <p><b>OE No.</b></p> <p>mitsubishi MN102067, MN102068 SMART 4543300059</p>
<p>KH20073</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661052402</p> <p>Outer diameter [mm] 136</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 92</p> <p><b>OE No.</b></p> <p>VOLVO 30736501, 31476395, 32246153</p>
<p>KH20074</p> 	1	<p>EAN 192661052419</p> <p>Inner diameter [mm] 37</p> <p>Number of Teeth, ABS ring 48</p> <p>Outer diameter [mm] 190</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with ABS sensor ring</p> <p>Width [mm] 90</p> <p><b>OE No.</b></p> <p>FORD 1201303, 1C1J-1A049-BA</p>






Part Number	Pk.	Description																				
<p>KH20075</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052426</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>108</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 462 020</td> </tr> </table>	EAN	192661052426	Inner diameter [mm]	40	Outer diameter [mm]	108	Width [mm]	49	<b>OE No.</b>		RENAULT	77 01 462 020								
EAN	192661052426																					
Inner diameter [mm]	40																					
Outer diameter [mm]	108																					
Width [mm]	49																					
<b>OE No.</b>																						
RENAULT	77 01 462 020																					
<p>KH20076</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052433</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>110</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3307 67, 3748 30</td> </tr> <tr> <td>PEUGEOT</td> <td>3307 67, 3748 30</td> </tr> </table>	EAN	192661052433	Inner diameter [mm]	40	Outer diameter [mm]	110	Width [mm]	38	<b>OE No.</b>		CITROËN	3307 67, 3748 30	PEUGEOT	3307 67, 3748 30						
EAN	192661052433																					
Inner diameter [mm]	40																					
Outer diameter [mm]	110																					
Width [mm]	38																					
<b>OE No.</b>																						
CITROËN	3307 67, 3748 30																					
PEUGEOT	3307 67, 3748 30																					
<p>KH20077</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052440</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>132</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>74</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 00 820 849, 77 01 204 689</td> </tr> </table>	EAN	192661052440	Inner diameter [mm]	25	Number of Teeth, ABS ring	44	Outer diameter [mm]	132	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	74	<b>OE No.</b>		RENAULT	77 00 820 849, 77 01 204 689		
EAN	192661052440																					
Inner diameter [mm]	25																					
Number of Teeth, ABS ring	44																					
Outer diameter [mm]	132																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	74																					
<b>OE No.</b>																						
RENAULT	77 00 820 849, 77 01 204 689																					
<p>KH20078</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052457</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>74</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 477</td> </tr> </table>	EAN	192661052457	Inner diameter [mm]	25	Number of Teeth, ABS ring	44	Outer diameter [mm]	133	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	74	<b>OE No.</b>		RENAULT	77 01 205 477		
EAN	192661052457																					
Inner diameter [mm]	25																					
Number of Teeth, ABS ring	44																					
Outer diameter [mm]	133																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	74																					
<b>OE No.</b>																						
RENAULT	77 01 205 477																					
<p>KH20079</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052464</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 35</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 35</td> </tr> </table>	EAN	192661052464	Inner diameter [mm]	32	Number of Teeth, ABS ring	29	Outer diameter [mm]	129	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	59	<b>OE No.</b>		CITROËN	3748 35	PEUGEOT	3748 35
EAN	192661052464																					
Inner diameter [mm]	32																					
Number of Teeth, ABS ring	29																					
Outer diameter [mm]	129																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	59																					
<b>OE No.</b>																						
CITROËN	3748 35																					
PEUGEOT	3748 35																					








Part Number	Pk.	Description												
<p>KH20080</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052471</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> </table> <p><b>OE No.</b> RENAULT 77 01 205 471</p>	EAN	192661052471	Inner diameter [mm]	25	Outer diameter 2 [mm]	133	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	43
EAN	192661052471													
Inner diameter [mm]	25													
Outer diameter 2 [mm]	133													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	43													
<p>KH20081</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052488</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> </table> <p><b>OE No.</b> RENAULT 77 01 206 353</p>	EAN	192661052488	Inner diameter [mm]	25	Outer diameter [mm]	133	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	54		
EAN	192661052488													
Inner diameter [mm]	25													
Outer diameter [mm]	133													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	54													
<p>KH20082</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052495</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>118</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>62</td> </tr> </table> <p><b>OE No.</b> FIAT 46554135, 51759727, 51965295, 71753819, 71769492</p>	EAN	192661052495	Inner diameter [mm]	30	Outer diameter [mm]	118	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	62		
EAN	192661052495													
Inner diameter [mm]	30													
Outer diameter [mm]	118													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	62													
<p>KH20083</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052501</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>37</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO 46739139, 71753817</p>	EAN	192661052501	Inner diameter [mm]	37	Outer diameter [mm]	125	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	37		
EAN	192661052501													
Inner diameter [mm]	37													
Outer diameter [mm]	125													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	37													





Part Number	Pk.	Description																		
<p>KH20084</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066591</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1334289, 1334291, 1362870, 1362872, 1458701, 1458702, 1462160, 1469186 7, 1469189, 2T14-2C299-CA, 2T14-2C299-CB, 2T14-2C299-CC, 2T14-2C299-CD, 2T14-2C299-CE, 2T14-2C299-DA, 2T14-2C299-DB, 2T14-2C299-DD, 7T16-2C99-BB</td> </tr> </table>	EAN	192661066591	Inner diameter [mm]	37	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	FORD	1334289, 1334291, 1362870, 1362872, 1458701, 1458702, 1462160, 1469186 7, 1469189, 2T14-2C299-CA, 2T14-2C299-CB, 2T14-2C299-CC, 2T14-2C299-CD, 2T14-2C299-CE, 2T14-2C299-DA, 2T14-2C299-DB, 2T14-2C299-DD, 7T16-2C99-BB				
EAN	192661066591																			
Inner diameter [mm]	37																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	67																			
FORD	1334289, 1334291, 1362870, 1362872, 1458701, 1458702, 1462160, 1469186 7, 1469189, 2T14-2C299-CA, 2T14-2C299-CB, 2T14-2C299-CC, 2T14-2C299-CD, 2T14-2C299-CE, 2T14-2C299-DA, 2T14-2C299-DB, 2T14-2C299-DD, 7T16-2C99-BB																			
<p>KH20085</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052518</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>35.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>BMW</td> <td>33 41 1 095 238</td> </tr> </table>	EAN	192661052518	Inner diameter [mm]	45	Outer diameter [mm]	126	Rim Hole Number	4	Width [mm]	35.5	BMW	33 41 1 095 238						
EAN	192661052518																			
Inner diameter [mm]	45																			
Outer diameter [mm]	126																			
Rim Hole Number	4																			
Width [mm]	35.5																			
BMW	33 41 1 095 238																			
<p>KH20086</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052525</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>143</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>103</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>16 063 747 80, 3701 82</td> </tr> <tr> <td>FIAT</td> <td>5175492, 71753811</td> </tr> <tr> <td>PEUGEOT</td> <td>16 063 747 80, 3701 82</td> </tr> </table>	EAN	192661052525	Inner diameter [mm]	42	Outer diameter [mm]	143	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	103	CITROËN	16 063 747 80, 3701 82	FIAT	5175492, 71753811	PEUGEOT	16 063 747 80, 3701 82
EAN	192661052525																			
Inner diameter [mm]	42																			
Outer diameter [mm]	143																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	103																			
CITROËN	16 063 747 80, 3701 82																			
FIAT	5175492, 71753811																			
PEUGEOT	16 063 747 80, 3701 82																			
<p>KH20087</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052532</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>92</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1463833, 1496721, 6G91-2C300-GAB, 6G91-2C300-GAC</td> </tr> </table>	EAN	192661052532	Outer diameter [mm]	137	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	92	FORD	1463833, 1496721, 6G91-2C300-GAB, 6G91-2C300-GAC						
EAN	192661052532																			
Outer diameter [mm]	137																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	92																			
FORD	1463833, 1496721, 6G91-2C300-GAB, 6G91-2C300-GAC																			








Part Number	Pk.	Description														
<p>KH20088</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052549</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>131</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>92</td> </tr> </table> <p><b>OE No.</b> VOLVO 30714730, 31340604</p>	EAN	192661052549	Inner diameter [mm]	30	Outer diameter [mm]	131	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	92		
EAN	192661052549															
Inner diameter [mm]	30															
Outer diameter [mm]	131															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	92															
<p>KH20089</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066607</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>96</td> </tr> <tr> <td>Width [mm]</td> <td>51.5</td> </tr> </table> <p><b>OE No.</b> TOYOTA 43560-60010, 90080-37030, 90369-T0003</p>	EAN	192661066607	Inner diameter [mm]	54	Outer diameter [mm]	96	Width [mm]	51.5						
EAN	192661066607															
Inner diameter [mm]	54															
Outer diameter [mm]	96															
Width [mm]	51.5															
<p>KH20090</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052556</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>130</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO 51832400</p>	EAN	192661052556	Inner diameter [mm]	30	Outer diameter [mm]	130	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	45		
EAN	192661052556															
Inner diameter [mm]	30															
Outer diameter [mm]	130															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	45															
<p>KH20091</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052563</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>118</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> </table> <p><b>OE No.</b> FIAT 7603485 LANCIA 7603485</p>	EAN	192661052563	Inner diameter [mm]	30	Outer diameter [mm]	118	Rim Hole Number	4	Width [mm]	61				
EAN	192661052563															
Inner diameter [mm]	30															
Outer diameter [mm]	118															
Rim Hole Number	4															
Width [mm]	61															
<p>KH20092</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052570</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> </table> <p><b>OE No.</b> CITROËN 95 666 965 PEUGEOT 95 666 965</p>	EAN	192661052570	Inner diameter [mm]	32	Number of Teeth, ABS ring	48	Outer diameter [mm]	129	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	53
EAN	192661052570															
Inner diameter [mm]	32															
Number of Teeth, ABS ring	48															
Outer diameter [mm]	129															
Rim Hole Number	4															
Supplementary Article/Info 2	with ABS sensor ring															
Width [mm]	53															

Part Number	Pk.	Description																						
<p>KH20093</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661052587</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>70</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>51810087</td> </tr> <tr> <td>OPEL</td> <td>328014, 95511660</td> </tr> <tr> <td>VAUXHALL</td> <td>328014, 95511660</td> </tr> </table>	EAN	192661052587	Inner diameter [mm]	30	Outer diameter [mm]	120	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	70	FIAT	51810087	OPEL	328014, 95511660	VAUXHALL	328014, 95511660				
EAN	192661052587																							
Inner diameter [mm]	30																							
Outer diameter [mm]	120																							
Rim Hole Number	5																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
Width [mm]	70																							
FIAT	51810087																							
OPEL	328014, 95511660																							
VAUXHALL	328014, 95511660																							
<p>KH20094</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066614</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>89</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MAZDA</td> <td>B455-26-15XA, B455-26-15XB</td> </tr> </table>	EAN	192661066614	Inner diameter [mm]	30	Outer diameter [mm]	122	Rim Hole Number	4	Width [mm]	89	MAZDA	B455-26-15XA, B455-26-15XB										
EAN	192661066614																							
Inner diameter [mm]	30																							
Outer diameter [mm]	122																							
Rim Hole Number	4																							
Width [mm]	89																							
MAZDA	B455-26-15XA, B455-26-15XB																							
<p>KH20095</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066621</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>52</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3350 28, 3701 61</td> </tr> <tr> <td>FIAT</td> <td>7174474, 9567217780</td> </tr> <tr> <td>LANCIA</td> <td>7174474, 9567217780</td> </tr> <tr> <td>PEUGEOT</td> <td>3350 28, 3701 61</td> </tr> </table>	EAN	192661066621	Inner diameter [mm]	30	Number of Teeth, ABS ring	48	Outer diameter [mm]	120	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	52	CITROËN	3350 28, 3701 61	FIAT	7174474, 9567217780	LANCIA	7174474, 9567217780	PEUGEOT	3350 28, 3701 61
EAN	192661066621																							
Inner diameter [mm]	30																							
Number of Teeth, ABS ring	48																							
Outer diameter [mm]	120																							
Rim Hole Number	5																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	52																							
CITROËN	3350 28, 3701 61																							
FIAT	7174474, 9567217780																							
LANCIA	7174474, 9567217780																							
PEUGEOT	3350 28, 3701 61																							
<p>KH20096</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066638</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>47</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MITSUBISHI</td> <td>MR369518, MR47533</td> </tr> </table>	EAN	192661066638	Inner diameter [mm]	40	Outer diameter [mm]	140	Rim Hole Number	4	Width [mm]	47	MITSUBISHI	MR369518, MR47533										
EAN	192661066638																							
Inner diameter [mm]	40																							
Outer diameter [mm]	140																							
Rim Hole Number	4																							
Width [mm]	47																							
MITSUBISHI	MR369518, MR47533																							
<p>KH20097</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066645</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>62</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>ALFA ROMEO</td> <td>60613615</td> </tr> </table>	EAN	192661066645	Inner diameter [mm]	30	Outer diameter [mm]	117	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	62	ALFA ROMEO	60613615										
EAN	192661066645																							
Inner diameter [mm]	30																							
Outer diameter [mm]	117																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	62																							
ALFA ROMEO	60613615																							








Part Number	Pk.	Description																
<p>KH20098</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066652</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>46</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MG</td> <td>GHK 1693, RLB 100292</td> </tr> <tr> <td>ROVER</td> <td>GHK 1693, RLB 100292</td> </tr> </table>	EAN	192661066652	Inner diameter [mm]	32	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	46	MG	GHK 1693, RLB 100292	ROVER	GHK 1693, RLB 100292
EAN	192661066652																	
Inner diameter [mm]	32																	
Outer diameter [mm]	140																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	46																	
MG	GHK 1693, RLB 100292																	
ROVER	GHK 1693, RLB 100292																	
<p>KH20099</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066669</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>76</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>46</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>RENAULT</td> <td>77 01 205 472</td> </tr> </table>	EAN	192661066669	Inner diameter [mm]	25	Outer diameter 1 [mm]	76	Outer diameter 2 [mm]	133	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	46	RENAULT	77 01 205 472
EAN	192661066669																	
Inner diameter [mm]	25																	
Outer diameter 1 [mm]	76																	
Outer diameter 2 [mm]	133																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	46																	
RENAULT	77 01 205 472																	
<p>KH20100</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066676</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3748 76, 3748 79</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 76, 3748 79</td> </tr> </table>	EAN	192661066676	Inner diameter [mm]	25	Outer diameter [mm]	129	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	60	CITROËN	3748 76, 3748 79	PEUGEOT	3748 76, 3748 79		
EAN	192661066676																	
Inner diameter [mm]	25																	
Outer diameter [mm]	129																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	60																	
CITROËN	3748 76, 3748 79																	
PEUGEOT	3748 76, 3748 79																	
<p>KH20101</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066683</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>73</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>43210-00Q0D, 43210-00QAC</td> </tr> <tr> <td>RENAULT</td> <td>77 01 208 075</td> </tr> </table>	EAN	192661066683	Inner diameter [mm]	25	Outer diameter [mm]	133	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	73	NISSAN	43210-00Q0D, 43210-00QAC	RENAULT	77 01 208 075		
EAN	192661066683																	
Inner diameter [mm]	25																	
Outer diameter [mm]	133																	
Supplementary Article/Info 2	with ABS sensor ring																	
Width [mm]	73																	
NISSAN	43210-00Q0D, 43210-00QAC																	
RENAULT	77 01 208 075																	

Part Number	Pk.	Description																		
<p>KH20102</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066690</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>46</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 22 2 229 501</td> </tr> </table>	EAN	192661066690	Inner diameter [mm]	37	Number of Teeth, ABS ring	48	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	46	<b>OE No.</b>		BMW	31 22 2 229 501
EAN	192661066690																			
Inner diameter [mm]	37																			
Number of Teeth, ABS ring	48																			
Outer diameter [mm]	139																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	46																			
<b>OE No.</b>																				
BMW	31 22 2 229 501																			
<p>KH20103</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066706</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>4220-S5A-008</td> </tr> </table>	EAN	192661066706	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	139	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	56	<b>OE No.</b>		HONDA	4220-S5A-008
EAN	192661066706																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	56																			
<b>OE No.</b>																				
HONDA	4220-S5A-008																			
<p>KH20104</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066713</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>49</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MERCEDES-BENZ</td> <td>A2119810227</td> </tr> </table>	EAN	192661066713	Inner diameter [mm]	49	Outer diameter [mm]	126	Rim Hole Number	4	Width [mm]	50	<b>OE No.</b>		MERCEDES-BENZ	A2119810227				
EAN	192661066713																			
Inner diameter [mm]	49																			
Outer diameter [mm]	126																			
Rim Hole Number	4																			
Width [mm]	50																			
<b>OE No.</b>																				
MERCEDES-BENZ	A2119810227																			
<p>KH20105</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066720</td> </tr> <tr> <td>Fitting Position</td> <td>Rear Axle</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>63</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>7746191</td> </tr> </table>	EAN	192661066720	Fitting Position	Rear Axle	Inner diameter [mm]	30	Outer diameter [mm]	117	Rim Hole Number	4	Width [mm]	63	<b>OE No.</b>		FIAT	7746191		
EAN	192661066720																			
Fitting Position	Rear Axle																			
Inner diameter [mm]	30																			
Outer diameter [mm]	117																			
Rim Hole Number	4																			
Width [mm]	63																			
<b>OE No.</b>																				
FIAT	7746191																			
<p>KH20106</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066737</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>138</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>90</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>BP4K-33-15XB</td> </tr> </table>	EAN	192661066737	Inner diameter [mm]	28	Outer diameter [mm]	138	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	90	<b>OE No.</b>		MAZDA	BP4K-33-15XB		
EAN	192661066737																			
Inner diameter [mm]	28																			
Outer diameter [mm]	138																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	90																			
<b>OE No.</b>																				
MAZDA	BP4K-33-15XB																			










Part Number	Pk.	Description																				
<p>KH20107</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066744</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>41</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>84</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>43401-65D10</td> </tr> </table>	EAN	192661066744	Inner diameter [mm]	41	Outer diameter [mm]	84	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	55	<b>OE No.</b>		SUZUKI	43401-65D10						
EAN	192661066744																					
Inner diameter [mm]	41																					
Outer diameter [mm]	84																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	55																					
<b>OE No.</b>																						
SUZUKI	43401-65D10																					
<p>KH20108</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066751</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 44</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 44</td> </tr> </table>	EAN	192661066751	Inner diameter [mm]	32	Outer diameter [mm]	129	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	59	<b>OE No.</b>		CITROËN	3748 44	PEUGEOT	3748 44		
EAN	192661066751																					
Inner diameter [mm]	32																					
Outer diameter [mm]	129																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	59																					
<b>OE No.</b>																						
CITROËN	3748 44																					
PEUGEOT	3748 44																					
<p>KH20109</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661066768</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>51810086, 52056182</td> </tr> <tr> <td>OPEL</td> <td>328013, 95511659</td> </tr> <tr> <td>VAUXHALL</td> <td>328013, 95511659</td> </tr> </table>	EAN	192661066768	Inner diameter [mm]	30	Outer diameter [mm]	117	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	61	<b>OE No.</b>		FIAT	51810086, 52056182	OPEL	328013, 95511659	VAUXHALL	328013, 95511659
EAN	192661066768																					
Inner diameter [mm]	30																					
Outer diameter [mm]	117																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	61																					
<b>OE No.</b>																						
FIAT	51810086, 52056182																					
OPEL	328013, 95511659																					
VAUXHALL	328013, 95511659																					
<p>KH20110</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066775</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>69.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-2C101, 52710-2C105</td> </tr> </table>	EAN	192661066775	Inner diameter [mm]	32	Number of Teeth, ABS ring	44	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	69.5	<b>OE No.</b>		HYUNDAI	52710-2C101, 52710-2C105		
EAN	192661066775																					
Inner diameter [mm]	32																					
Number of Teeth, ABS ring	44																					
Outer diameter [mm]	139																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	69.5																					
<b>OE No.</b>																						
HYUNDAI	52710-2C101, 52710-2C105																					
<p>KH20111</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661066782</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>31</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 21 1 128 157, 31 21 1 128 569, 31 21 1 131 297</td> </tr> </table>	EAN	192661066782	Inner diameter [mm]	31	Number of Teeth, ABS ring	48	Outer diameter [mm]	120	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	61	<b>OE No.</b>		BMW	31 21 1 128 157, 31 21 1 128 569, 31 21 1 131 297		
EAN	192661066782																					
Inner diameter [mm]	31																					
Number of Teeth, ABS ring	48																					
Outer diameter [mm]	120																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	61																					
<b>OE No.</b>																						
BMW	31 21 1 128 157, 31 21 1 128 569, 31 21 1 131 297																					






Part Number	Pk.	Description																		
<p>KH20112</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066799</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>90</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>64</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 21 1 131 298</td> </tr> </table>	EAN	192661066799	Inner diameter [mm]	37	Number of Teeth, ABS ring	90	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	64	<b>OE No.</b>		BMW	31 21 1 131 298
EAN	192661066799																			
Inner diameter [mm]	37																			
Number of Teeth, ABS ring	90																			
Outer diameter [mm]	139																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	64																			
<b>OE No.</b>																				
BMW	31 21 1 131 298																			
<p>KH20113</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066805</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 00 803 924, 77 01 204 693</td> </tr> </table>	EAN	192661066805	Inner diameter [mm]	25	Number of Teeth, ABS ring	30	Outer diameter [mm]	133	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	54	<b>OE No.</b>		RENAULT	77 00 803 924, 77 01 204 693
EAN	192661066805																			
Inner diameter [mm]	25																			
Number of Teeth, ABS ring	30																			
Outer diameter [mm]	133																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	54																			
<b>OE No.</b>																				
RENAULT	77 00 803 924, 77 01 204 693																			
<p>KH20114</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066812</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>121</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>NA23-33-04XA</td> </tr> </table>	EAN	192661066812	Inner diameter [mm]	28	Number of Teeth, ABS ring	44	Outer diameter [mm]	121	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	67	<b>OE No.</b>		MAZDA	NA23-33-04XA
EAN	192661066812																			
Inner diameter [mm]	28																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	121																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	67																			
<b>OE No.</b>																				
MAZDA	NA23-33-04XA																			
<p>KH20115</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066829</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>64</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>31 22 1 092 519</td> </tr> </table>	EAN	192661066829	Inner diameter [mm]	37	Number of Teeth, ABS ring	48	Outer diameter [mm]	139	Rim Hole Number	4	Width [mm]	64	<b>OE No.</b>		BMW	31 22 1 092 519		
EAN	192661066829																			
Inner diameter [mm]	37																			
Number of Teeth, ABS ring	48																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Width [mm]	64																			
<b>OE No.</b>																				
BMW	31 22 1 092 519																			
<p>KH20116</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066836</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>42</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>60 25 370 612</td> </tr> </table>	EAN	192661066836	Inner diameter [mm]	30	Number of Teeth, ABS ring	44	Outer diameter [mm]	133	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	42	<b>OE No.</b>		RENAULT	60 25 370 612		
EAN	192661066836																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	133																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	42																			
<b>OE No.</b>																				
RENAULT	60 25 370 612																			








Part Number	Pk.	Description
<p>KH20117</p>	1	<p>EAN   192661066843</p> <p>Inner diameter [mm]   28</p> <p>Number of Teeth, ABS ring   43</p> <p>Outer diameter [mm]   120</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   61.5</p> <p><b>OE No.</b></p> <p>SEAT   6X0 501 477, 6X0 598 477</p> <p>VW   6X0 501 477, 6X0 598 477</p>
<p>KH20118</p>	1	<p>EAN   192661066850</p> <p>Inner diameter [mm]   27</p> <p>Outer diameter [mm]   123</p> <p>Rim Hole Number   4</p> <p>Width [mm]   53</p> <p><b>OE No.</b></p> <p>OPEL   4 20 240, 9196298</p> <p>VAUXHALL   4 20 240, 9196298</p>
<p>KH20119</p>	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <p>EAN   192661066867</p> <p>Inner diameter [mm]   25</p> <p>Outer diameter [mm]   120</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   62</p> <p><b>OE No.</b></p> <p>AUDI   6E0 598 611</p> <p>VW   6E0 598 611, 6E0 598 611A</p>
<p>KH20120</p>	1	<p>EAN   192661066874</p> <p>Number of Teeth, ABS ring   48</p> <p>Outer diameter [mm]   187</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   45</p> <p><b>OE No.</b></p> <p>FORD   1318154, 3C1J-1A049BA</p>
<p>KH20121</p>	1	<p>EAN   192661066881</p> <p>Inner diameter [mm]   25</p> <p>Number of Teeth, ABS ring   48</p> <p>Outer diameter [mm]   129</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   42</p> <p><b>OE No.</b></p> <p>CITROËN   3748 78</p> <p>PEUGEOT   3748 78</p>






Part Number	Pk.	Description																		
<p>KH20122</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066898</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>65</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUZUKI</td> <td>43402-54G22, 43402-60G20, 43402-60G21</td> </tr> </table>	EAN	192661066898	Inner diameter [mm]	28	Number of Teeth, ABS ring	42	Outer diameter [mm]	129.5	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	65	<b>OE No.</b>		SUZUKI	43402-54G22, 43402-60G20, 43402-60G21
EAN	192661066898																			
Inner diameter [mm]	28																			
Number of Teeth, ABS ring	42																			
Outer diameter [mm]	129.5																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	65																			
<b>OE No.</b>																				
SUZUKI	43402-54G22, 43402-60G20, 43402-60G21																			
<p>KH20123</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066904</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SMART</td> <td>A 451 330 00 59, A 451 330 01 59</td> </tr> </table>	EAN	192661066904	Outer diameter [mm]	134	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	56	<b>OE No.</b>		SMART	A 451 330 00 59, A 451 330 01 59						
EAN	192661066904																			
Outer diameter [mm]	134																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	56																			
<b>OE No.</b>																				
SMART	A 451 330 00 59, A 451 330 01 59																			
<p>KH20124</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066911</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>48.3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>108.5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>45.3</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 40 6 850 156, 33 40 6 850 159, 33 41 6 775 021</td> </tr> </table>	EAN	192661066911	Inner diameter [mm]	48.3	Outer diameter [mm]	108.5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	45.3	<b>OE No.</b>		BMW	33 40 6 850 156, 33 40 6 850 159, 33 41 6 775 021				
EAN	192661066911																			
Inner diameter [mm]	48.3																			
Outer diameter [mm]	108.5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	45.3																			
<b>OE No.</b>																				
BMW	33 40 6 850 156, 33 40 6 850 159, 33 41 6 775 021																			
<p>KH20125</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066928</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>89</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>42450-60050</td> </tr> <tr> <td>TOYOTA</td> <td>42450-60050</td> </tr> </table>	EAN	192661066928	Inner diameter [mm]	44	Outer diameter [mm]	89	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	<b>OE No.</b>		LEXUS	42450-60050	TOYOTA	42450-60050		
EAN	192661066928																			
Inner diameter [mm]	44																			
Outer diameter [mm]	89																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	67																			
<b>OE No.</b>																				
LEXUS	42450-60050																			
TOYOTA	42450-60050																			
<p>KH20126</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069073</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 36</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 36</td> </tr> </table>	EAN	192661069073	Inner diameter [mm]	32	Outer diameter [mm]	129	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	59	<b>OE No.</b>		CITROËN	3748 36	PEUGEOT	3748 36		
EAN	192661069073																			
Inner diameter [mm]	32																			
Outer diameter [mm]	129																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	59																			
<b>OE No.</b>																				
CITROËN	3748 36																			
PEUGEOT	3748 36																			








Part Number	Pk.	Description																		
<p>KH20127</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069080</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>37</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>190</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>90</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1 201 304, 1 377 910, 1 417 338, 1C1J-1A049-AA, 6C11-2C229-AA</td> </tr> </table>	EAN	192661069080	Inner diameter [mm]	37	Outer diameter [mm]	190	Rim Hole Number	5	Width [mm]	90	<b>OE No.</b>		FORD	1 201 304, 1 377 910, 1 417 338, 1C1J-1A049-AA, 6C11-2C229-AA				
EAN	192661069080																			
Inner diameter [mm]	37																			
Outer diameter [mm]	190																			
Rim Hole Number	5																			
Width [mm]	90																			
<b>OE No.</b>																				
FORD	1 201 304, 1 377 910, 1 417 338, 1C1J-1A049-AA, 6C11-2C229-AA																			
<p>KH20128</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069097</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>96264600, 96280244</td> </tr> <tr> <td>DAEWOO</td> <td>96264600, 96280244</td> </tr> </table>	EAN	192661069097	Inner diameter [mm]	42	Number of Teeth, ABS ring	34	Outer diameter [mm]	72	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	<b>OE No.</b>		CHEVROLET	96264600, 96280244	DAEWOO	96264600, 96280244
EAN	192661069097																			
Inner diameter [mm]	42																			
Number of Teeth, ABS ring	34																			
Outer diameter [mm]	72																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
<b>OE No.</b>																				
CHEVROLET	96264600, 96280244																			
DAEWOO	96264600, 96280244																			
<p>KH20129</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069103</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>72</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>G14V-26-15X, G14V-26-15XA, G14V-26-15XB</td> </tr> </table>	EAN	192661069103	Inner diameter [mm]	42	Outer diameter [mm]	72	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	<b>OE No.</b>		MAZDA	G14V-26-15X, G14V-26-15XA, G14V-26-15XB				
EAN	192661069103																			
Inner diameter [mm]	42																			
Outer diameter [mm]	72																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
<b>OE No.</b>																				
MAZDA	G14V-26-15X, G14V-26-15XA, G14V-26-15XB																			
<p>KH20130</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069110</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>112</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>62</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>FIAT</td> <td>46519901, 50701247, 50704683</td> </tr> </table>	EAN	192661069110	Inner diameter [mm]	30	Outer diameter [mm]	112	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	62	<b>OE No.</b>		FIAT	46519901, 50701247, 50704683				
EAN	192661069110																			
Inner diameter [mm]	30																			
Outer diameter [mm]	112																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	62																			
<b>OE No.</b>																				
FIAT	46519901, 50701247, 50704683																			
<p>KH20131</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069127</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>89</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>42460-60010</td> </tr> <tr> <td>TOYOTA</td> <td>42460-60010</td> </tr> </table>	EAN	192661069127	Inner diameter [mm]	44	Outer diameter [mm]	89	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	<b>OE No.</b>		LEXUS	42460-60010	TOYOTA	42460-60010		
EAN	192661069127																			
Inner diameter [mm]	44																			
Outer diameter [mm]	89																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	67																			
<b>OE No.</b>																				
LEXUS	42460-60010																			
TOYOTA	42460-60010																			

Part Number	Pk.	Description																						
<p>KH20132</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069134</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661069134	Inner diameter [mm]	30	Number of Teeth, ABS ring	43	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	56.5	<b>OE No.</b>		<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table>	MITSUBISHI	MR527452		
EAN	192661069134																							
Inner diameter [mm]	30																							
Number of Teeth, ABS ring	43																							
Outer diameter [mm]	137.5																							
Rim Hole Number	4																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	56.5																							
<b>OE No.</b>																								
<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table>	MITSUBISHI	MR527452																					
<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR527452</td> </tr> </table>	MITSUBISHI	MR527452																						
MITSUBISHI	MR527452																							
<p>KH20133</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069141</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>53</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>91</td> </tr> <tr> <td>Width [mm]</td> <td>62</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661069141	Inner diameter [mm]	53	Outer diameter [mm]	91	Width [mm]	62	<b>OE No.</b>		<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table>	MITSUBISHI	MR418068, MR418524								
EAN	192661069141																							
Inner diameter [mm]	53																							
Outer diameter [mm]	91																							
Width [mm]	62																							
<b>OE No.</b>																								
<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table>	MITSUBISHI	MR418068, MR418524																					
<table border="0"> <tr> <td>MITSUBISHI</td> <td>MR418068, MR418524</td> </tr> </table>	MITSUBISHI	MR418068, MR418524																						
MITSUBISHI	MR418068, MR418524																							
<p>KH20134</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069158</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>54</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>92</td> </tr> <tr> <td>Width [mm]</td> <td>62</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661069158	Inner diameter [mm]	54	Outer diameter [mm]	92	Width [mm]	62	<b>OE No.</b>		<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table>	MITSUBISHI	3758A004								
EAN	192661069158																							
Inner diameter [mm]	54																							
Outer diameter [mm]	92																							
Width [mm]	62																							
<b>OE No.</b>																								
<table border="0"> <tr> <td> <table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table>	MITSUBISHI	3758A004																					
<table border="0"> <tr> <td>MITSUBISHI</td> <td>3758A004</td> </tr> </table>	MITSUBISHI	3758A004																						
MITSUBISHI	3758A004																							
<p>KH20135</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071878</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>36</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>79</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661071878	Inner diameter [mm]	36	Outer diameter [mm]	140	Rim Hole Number	5	Width [mm]	79	<b>OE No.</b>		<table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table>	MAZDA	GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB						
EAN	192661071878																							
Inner diameter [mm]	36																							
Outer diameter [mm]	140																							
Rim Hole Number	5																							
Width [mm]	79																							
<b>OE No.</b>																								
<table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table>	MAZDA	GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB																					
<table border="0"> <tr> <td>MAZDA</td> <td>GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB</td> </tr> </table>	MAZDA	GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB																						
MAZDA	GF4K-26-15X, GF4K-26-15XA, GF4K-26-15XB																							
<p>KH20136</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071885</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67.3</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td> <table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table> </td> <td></td> </tr> </table> </td> <td></td> </tr> </table>	EAN	192661071885	Inner diameter [mm]	28	Outer diameter [mm]	122	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	67.3	<b>OE No.</b>		<table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table>	MAZDA	NA23-33-04XC				
EAN	192661071885																							
Inner diameter [mm]	28																							
Outer diameter [mm]	122																							
Rim Hole Number	4																							
Supplementary Article/Info 2	with ABS sensor ring																							
Width [mm]	67.3																							
<b>OE No.</b>																								
<table border="0"> <tr> <td> <table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table> </td> <td></td> </tr> </table>	<table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table>	MAZDA	NA23-33-04XC																					
<table border="0"> <tr> <td>MAZDA</td> <td>NA23-33-04XC</td> </tr> </table>	MAZDA	NA23-33-04XC																						
MAZDA	NA23-33-04XC																							








Part Number	Pk.	Description																				
<p>KH20137</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071892</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>146</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>75</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-SED-952</td> </tr> </table>	EAN	192661071892	Inner diameter [mm]	34	Outer diameter [mm]	146	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	75	<b>OE No.</b>		HONDA	42200-SED-952				
EAN	192661071892																					
Inner diameter [mm]	34																					
Outer diameter [mm]	146																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	75																					
<b>OE No.</b>																						
HONDA	42200-SED-952																					
<p>KH20138</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071908</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>58</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3748 A5</td> </tr> <tr> <td>PEUGEOT</td> <td>3748 A5</td> </tr> <tr> <td>RENAULT</td> <td>3748 A5</td> </tr> </table>	EAN	192661071908	Inner diameter [mm]	32	Outer diameter [mm]	129	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	58	<b>OE No.</b>		CITROËN	3748 A5	PEUGEOT	3748 A5	RENAULT	3748 A5
EAN	192661071908																					
Inner diameter [mm]	32																					
Outer diameter [mm]	129																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	58																					
<b>OE No.</b>																						
CITROËN	3748 A5																					
PEUGEOT	3748 A5																					
RENAULT	3748 A5																					
<p>KH20139</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071915</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>42</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>73</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43200-BM500</td> </tr> </table>	EAN	192661071915	Inner diameter [mm]	30	Number of Teeth, ABS ring	42	Outer diameter [mm]	148	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	73	<b>OE No.</b>		NISSAN	43200-BM500				
EAN	192661071915																					
Inner diameter [mm]	30																					
Number of Teeth, ABS ring	42																					
Outer diameter [mm]	148																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	73																					
<b>OE No.</b>																						
NISSAN	43200-BM500																					
<p>KH20140</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071922</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR527453</td> </tr> </table>	EAN	192661071922	Inner diameter [mm]	30	Number of Teeth, ABS ring	43	Outer diameter [mm]	137.5	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	56.5	<b>OE No.</b>		MITSUBISHI	MR527453		
EAN	192661071922																					
Inner diameter [mm]	30																					
Number of Teeth, ABS ring	43																					
Outer diameter [mm]	137.5																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	56.5																					
<b>OE No.</b>																						
MITSUBISHI	MR527453																					
<p>KH20141</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071939</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>142</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>50</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>AUDI</td> <td>4G0 598 611, 6G0 501 611</td> </tr> </table>	EAN	192661071939	Inner diameter [mm]	32	Outer diameter [mm]	142	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	50	<b>OE No.</b>		AUDI	4G0 598 611, 6G0 501 611						
EAN	192661071939																					
Inner diameter [mm]	32																					
Outer diameter [mm]	142																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	50																					
<b>OE No.</b>																						
AUDI	4G0 598 611, 6G0 501 611																					

Part Number	Pk.	Description																				
<p>KH20142</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661071946</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43200-AV700</td> </tr> </table>	EAN	192661071946	Inner diameter [mm]	30	Outer diameter [mm]	148	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	49	<b>OE No.</b>		NISSAN	43200-AV700				
EAN	192661071946																					
Inner diameter [mm]	30																					
Outer diameter [mm]	148																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	49																					
<b>OE No.</b>																						
NISSAN	43200-AV700																					
<p>KH20143</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073513</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>27</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>60.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43202-34B00, 43202-72B00</td> </tr> </table>	EAN	192661073513	Inner diameter [mm]	27	Outer diameter [mm]	134	Rim Hole Number	4	Width [mm]	60.5	<b>OE No.</b>		NISSAN	43202-34B00, 43202-72B00						
EAN	192661073513																					
Inner diameter [mm]	27																					
Outer diameter [mm]	134																					
Rim Hole Number	4																					
Width [mm]	60.5																					
<b>OE No.</b>																						
NISSAN	43202-34B00, 43202-72B00																					
<p>KH20144</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073520</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>68</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>GHK1596, RLB000050</td> </tr> <tr> <td>ROVER</td> <td>GHK1596, RLB000050</td> </tr> </table>	EAN	192661073520	Inner diameter [mm]	30	Outer diameter [mm]	136	Rim Hole Number	4	Width [mm]	68	<b>OE No.</b>		MG	GHK1596, RLB000050	ROVER	GHK1596, RLB000050				
EAN	192661073520																					
Inner diameter [mm]	30																					
Outer diameter [mm]	136																					
Rim Hole Number	4																					
Width [mm]	68																					
<b>OE No.</b>																						
MG	GHK1596, RLB000050																					
ROVER	GHK1596, RLB000050																					
<p>KH20145</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073537</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>66</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MG</td> <td>RLB000060</td> </tr> <tr> <td>ROVER</td> <td>RLB000060</td> </tr> </table>	EAN	192661073537	Inner diameter [mm]	30	Number of Teeth, ABS ring	43	Outer diameter [mm]	136	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	66	<b>OE No.</b>		MG	RLB000060	ROVER	RLB000060
EAN	192661073537																					
Inner diameter [mm]	30																					
Number of Teeth, ABS ring	43																					
Outer diameter [mm]	136																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	66																					
<b>OE No.</b>																						
MG	RLB000060																					
ROVER	RLB000060																					
<p>KH20146</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073544</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>72</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>30812651, 30889072</td> </tr> </table>	EAN	192661073544	Inner diameter [mm]	30	Outer diameter [mm]	140	Rim Hole Number	4	Width [mm]	72	<b>OE No.</b>		VOLVO	30812651, 30889072						
EAN	192661073544																					
Inner diameter [mm]	30																					
Outer diameter [mm]	140																					
Rim Hole Number	4																					
Width [mm]	72																					
<b>OE No.</b>																						
VOLVO	30812651, 30889072																					










Part Number	Pk.	Description																		
<p>KH20147</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073551</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>73</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>RENAULT</td> <td>77 01 205 170</td> </tr> </table>	EAN	192661073551	Inner diameter [mm]	25	Number of Teeth, ABS ring	44	Outer diameter [mm]	133	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	73	<b>OE No.</b>		RENAULT	77 01 205 170
EAN	192661073551																			
Inner diameter [mm]	25																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	133																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	73																			
<b>OE No.</b>																				
RENAULT	77 01 205 170																			
<p>KH20148</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073568</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Width [mm]</td> <td>66</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42201-S10-A01</td> </tr> </table>	EAN	192661073568	Inner diameter [mm]	43	Outer diameter [mm]	148	Width [mm]	66	<b>OE No.</b>		HONDA	42201-S10-A01						
EAN	192661073568																			
Inner diameter [mm]	43																			
Outer diameter [mm]	148																			
Width [mm]	66																			
<b>OE No.</b>																				
HONDA	42201-S10-A01																			
<p>KH20149</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073575</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>70</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-S1A-E02</td> </tr> </table>	EAN	192661073575	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	152	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	70	<b>OE No.</b>		HONDA	42200-S1A-E02
EAN	192661073575																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	152																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	70																			
<b>OE No.</b>																				
HONDA	42200-S1A-E02																			
<p>KH20150</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073582</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>66</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52750-26100</td> </tr> </table>	EAN	192661073582	Inner diameter [mm]	35	Outer diameter [mm]	148	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	66	<b>OE No.</b>		HYUNDAI	52750-26100				
EAN	192661073582																			
Inner diameter [mm]	35																			
Outer diameter [mm]	148																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	66																			
<b>OE No.</b>																				
HYUNDAI	52750-26100																			
<p>KH20151</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073599</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>35</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>47</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>71.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>32710-3A100, 52710-3A101</td> </tr> </table>	EAN	192661073599	Inner diameter [mm]	35	Number of Teeth, ABS ring	47	Outer diameter [mm]	148	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	71.5	<b>OE No.</b>		HYUNDAI	32710-3A100, 52710-3A101		
EAN	192661073599																			
Inner diameter [mm]	35																			
Number of Teeth, ABS ring	47																			
Outer diameter [mm]	148																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	71.5																			
<b>OE No.</b>																				
HYUNDAI	32710-3A100, 52710-3A101																			






Part Number	Pk.	Description														
<p>KH20152</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073605</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>27</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Width [mm]</td> <td>74</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>NISSAN</td> <td>43200-BM400</td> </tr> </table>	EAN	192661073605	Inner diameter [mm]	27	Outer diameter [mm]	148	Width [mm]	74	<b>OE No.</b>		NISSAN	43200-BM400		
EAN	192661073605															
Inner diameter [mm]	27															
Outer diameter [mm]	148															
Width [mm]	74															
<b>OE No.</b>																
NISSAN	43200-BM400															
<p>KH20153</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073612</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HONDA</td> <td>42200-SEL-T01</td> </tr> </table>	EAN	192661073612	Inner diameter [mm]	28	Outer diameter [mm]	133	Rim Hole Number	4	Width [mm]	55	<b>OE No.</b>		HONDA	42200-SEL-T01
EAN	192661073612															
Inner diameter [mm]	28															
Outer diameter [mm]	133															
Rim Hole Number	4															
Width [mm]	55															
<b>OE No.</b>																
HONDA	42200-SEL-T01															
<p>KH20154</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073629</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>127</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUBARU</td> <td>28474-AE000</td> </tr> </table>	EAN	192661073629	Inner diameter [mm]	40	Outer diameter [mm]	127	Width [mm]	56	<b>OE No.</b>		SUBARU	28474-AE000		
EAN	192661073629															
Inner diameter [mm]	40															
Outer diameter [mm]	127															
Width [mm]	56															
<b>OE No.</b>																
SUBARU	28474-AE000															
<p>KH20155</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073636</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>90</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>BMW</td> <td>33 40 6 789 970</td> </tr> </table>	EAN	192661073636	Inner diameter [mm]	45	Outer diameter [mm]	90	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41	<b>OE No.</b>		BMW	33 40 6 789 970
EAN	192661073636															
Inner diameter [mm]	45															
Outer diameter [mm]	90															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	41															
<b>OE No.</b>																
BMW	33 40 6 789 970															
<p>KH20156</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073643</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>52</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>91</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MITSUBISHI</td> <td>3555A015, 3885A014</td> </tr> </table>	EAN	192661073643	Inner diameter [mm]	52	Outer diameter [mm]	91	Width [mm]	56	<b>OE No.</b>		MITSUBISHI	3555A015, 3885A014		
EAN	192661073643															
Inner diameter [mm]	52															
Outer diameter [mm]	91															
Width [mm]	56															
<b>OE No.</b>																
MITSUBISHI	3555A015, 3885A014															








Part Number	Pk.	Description
<p>KH20157</p>	1	<p>EAN   192661073650</p> <p>Inner diameter [mm]   45</p> <p>Outer diameter [mm]   161</p> <p>Rim Hole Number   6</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   60</p> <p><b>OE No.</b></p> <p>HYUNDAI   51750-4H050</p>
<p>KH20158</p>	1	<p>EAN   192661073667</p> <p>Inner diameter [mm]   27</p> <p>Outer diameter [mm]   134</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   52.5</p> <p><b>OE No.</b></p> <p>NISSAN   43200-0M800, 4320-0M801</p>
<p>KH20159</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661073674</p> <p>Inner diameter 1 [mm]   43</p> <p>Inner diameter 2 [mm]   45</p> <p>Outer diameter [mm]   92</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   42</p> <p><b>OE No.</b></p> <p>AUDI   420 598 625, 420 598 625 A, 420 598 625 D</p>
<p>KH20160</p>	1	<p>EAN   192661073681</p> <p>Inner diameter [mm]   30</p> <p>Number of Teeth, ABS ring   48</p> <p>Outer diameter [mm]   139.2</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   86</p> <p><b>OE No.</b></p> <p>HONDA   42200-SMG-G51</p>
<p>KH20161</p>	1	<p>EAN   192661073698</p> <p>Inner diameter [mm]   30</p> <p>Number of Teeth, ABS ring   44</p> <p>Outer diameter [mm]   116.5</p> <p>Rim Hole Number   4</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   61</p> <p><b>OE No.</b></p> <p>ALFA ROMEO   46425959, 60809721, 60811481, 7613514</p> <p>FIAT   46425959, 60809721, 60811481, 7613514</p> <p>LANCIA   46425959, 60809721, 60811481, 7613514</p>






Part Number	Pk.	Description																		
<p>KH20162</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073704</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>111</td> </tr> <tr> <td>Width [mm]</td> <td>52</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>42409-05010, 42409-20010, 42450-05030</td> </tr> </table>	EAN	192661073704	Inner diameter [mm]	30	Outer diameter [mm]	111	Width [mm]	52	<b>OE No.</b>		TOYOTA	42409-05010, 42409-20010, 42450-05030						
EAN	192661073704																			
Inner diameter [mm]	30																			
Outer diameter [mm]	111																			
Width [mm]	52																			
<b>OE No.</b>																				
TOYOTA	42409-05010, 42409-20010, 42450-05030																			
<p>KH20163</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073711</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>47</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MAZDA</td> <td>NA01-33-04X, NA01-33-04XA</td> </tr> </table>	EAN	192661073711	Inner diameter [mm]	28	Outer diameter [mm]	122	Rim Hole Number	4	Width [mm]	47	<b>OE No.</b>		MAZDA	NA01-33-04X, NA01-33-04XA				
EAN	192661073711																			
Inner diameter [mm]	28																			
Outer diameter [mm]	122																			
Rim Hole Number	4																			
Width [mm]	47																			
<b>OE No.</b>																				
MAZDA	NA01-33-04X, NA01-33-04XA																			
<p>KH20164</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073728</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>70</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>VOLVO</td> <td>271585, 271795</td> </tr> </table>	EAN	192661073728	Inner diameter [mm]	30	Number of Teeth, ABS ring	48	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	70	<b>OE No.</b>		VOLVO	271585, 271795
EAN	192661073728																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	48																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	70																			
<b>OE No.</b>																				
VOLVO	271585, 271795																			
<p>KH20166</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073735</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>121</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>89</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MAZDA</td> <td>B603-26-15XA, B603-26-15XB, B603-26-15XC</td> </tr> </table>	EAN	192661073735	Inner diameter [mm]	30	Number of Teeth, ABS ring	44	Outer diameter [mm]	121	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	89	<b>OE No.</b>		MAZDA	B603-26-15XA, B603-26-15XB, B603-26-15XC
EAN	192661073735																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	121																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	89																			
<b>OE No.</b>																				
MAZDA	B603-26-15XA, B603-26-15XB, B603-26-15XC																			
<p>KH20167</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073742</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>118</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>80</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>AUDI</td> <td>6E0 407 621 C, 6E0 407 621 D</td> </tr> <tr> <td>VW</td> <td>6E0 407 621 C, 6E0 407 621 D</td> </tr> </table>	EAN	192661073742	Outer diameter [mm]	118	Rim Hole Number	4	Width [mm]	80	<b>OE No.</b>		AUDI	6E0 407 621 C, 6E0 407 621 D	VW	6E0 407 621 C, 6E0 407 621 D				
EAN	192661073742																			
Outer diameter [mm]	118																			
Rim Hole Number	4																			
Width [mm]	80																			
<b>OE No.</b>																				
AUDI	6E0 407 621 C, 6E0 407 621 D																			
VW	6E0 407 621 C, 6E0 407 621 D																			








Part Number	Pk.	Description																		
<p><b>KH20168</b></p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073759</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-2D010, 52710-2D011</td> </tr> </table>	EAN	192661073759	Inner diameter [mm]	32	Outer diameter [mm]	139	Rim Hole Number	4	Width [mm]	53	<b>OE No.</b>		HYUNDAI	52710-2D010, 52710-2D011				
EAN	192661073759																			
Inner diameter [mm]	32																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Width [mm]	53																			
<b>OE No.</b>																				
HYUNDAI	52710-2D010, 52710-2D011																			
<p><b>KH20169</b></p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074251</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>85</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HONDA</td> <td>42200-SK7-A01, 42200-ST3-E51</td> </tr> </table>	EAN	192661074251	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	136	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	85	<b>OE No.</b>		HONDA	42200-SK7-A01, 42200-ST3-E51
EAN	192661074251																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	136																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	85																			
<b>OE No.</b>																				
HONDA	42200-SK7-A01, 42200-ST3-E51																			
<p><b>KH20170</b></p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074268</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>64</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-22400</td> </tr> </table>	EAN	192661074268	Inner diameter [mm]	28	Outer diameter [mm]	139	Rim Hole Number	4	Width [mm]	64	<b>OE No.</b>		HYUNDAI	52710-22400				
EAN	192661074268																			
Inner diameter [mm]	28																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Width [mm]	64																			
<b>OE No.</b>																				
HYUNDAI	52710-22400																			
<p><b>KH20171</b></p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074688</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>129</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CITROËN</td> <td>3701 67, 3748 75</td> </tr> <tr> <td>PEUGEOT</td> <td>3701 67, 3748 75</td> </tr> </table>	EAN	192661074688	Inner diameter [mm]	25	Outer diameter [mm]	129	Rim Hole Number	4	Width [mm]	59	<b>OE No.</b>		CITROËN	3701 67, 3748 75	PEUGEOT	3701 67, 3748 75		
EAN	192661074688																			
Inner diameter [mm]	25																			
Outer diameter [mm]	129																			
Rim Hole Number	4																			
Width [mm]	59																			
<b>OE No.</b>																				
CITROËN	3701 67, 3748 75																			
PEUGEOT	3701 67, 3748 75																			
<p><b>KH20172</b></p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074275</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>40</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>79</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>42409-42010</td> </tr> </table>	EAN	192661074275	Inner diameter [mm]	40	Outer diameter [mm]	79	Width [mm]	60	<b>OE No.</b>		TOYOTA	42409-42010						
EAN	192661074275																			
Inner diameter [mm]	40																			
Outer diameter [mm]	79																			
Width [mm]	60																			
<b>OE No.</b>																				
TOYOTA	42409-42010																			

Part Number	Pk.	Description																		
<p>KH20173</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074282</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HONDA</td> <td>42200-S10-A01</td> </tr> </table>	EAN	192661074282	Inner diameter [mm]	43	Outer diameter [mm]	148	Width [mm]	60	<b>OE No.</b>		HONDA	42200-S10-A01						
EAN	192661074282																			
Inner diameter [mm]	43																			
Outer diameter [mm]	148																			
Width [mm]	60																			
<b>OE No.</b>																				
HONDA	42200-S10-A01																			
<p>KH20174</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074299</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>108</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>52</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>TOYOTA</td> <td>42409-19015, 42450-12030</td> </tr> </table>	EAN	192661074299	Inner diameter [mm]	28	Outer diameter [mm]	108	Rim Hole Number	4	Width [mm]	52	<b>OE No.</b>		TOYOTA	42409-19015, 42450-12030				
EAN	192661074299																			
Inner diameter [mm]	28																			
Outer diameter [mm]	108																			
Rim Hole Number	4																			
Width [mm]	52																			
<b>OE No.</b>																				
TOYOTA	42409-19015, 42450-12030																			
<p>KH20175</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074305</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>147</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>68</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HONDA</td> <td>42200-S30-C51, 42200-S30-J51</td> </tr> </table>	EAN	192661074305	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	147	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	68	<b>OE No.</b>		HONDA	42200-S30-C51, 42200-S30-J51
EAN	192661074305																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	147																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	68																			
<b>OE No.</b>																				
HONDA	42200-S30-C51, 42200-S30-J51																			
<p>KH20176</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074312</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>123</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HONDA</td> <td>44200-SXO-008</td> </tr> </table>	EAN	192661074312	Inner diameter [mm]	45	Outer diameter [mm]	123	Rim Hole Number	4	Width [mm]	49	<b>OE No.</b>		HONDA	44200-SXO-008				
EAN	192661074312																			
Inner diameter [mm]	45																			
Outer diameter [mm]	123																			
Rim Hole Number	4																			
Width [mm]	49																			
<b>OE No.</b>																				
HONDA	44200-SXO-008																			
<p>KH20177</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074329</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>126</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>79</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>SUBARU</td> <td>28063-AA-010, 28063-AC-000</td> </tr> </table>	EAN	192661074329	Inner diameter [mm]	30	Outer diameter [mm]	126	Rim Hole Number	5	Width [mm]	79	<b>OE No.</b>		SUBARU	28063-AA-010, 28063-AC-000				
EAN	192661074329																			
Inner diameter [mm]	30																			
Outer diameter [mm]	126																			
Rim Hole Number	5																			
Width [mm]	79																			
<b>OE No.</b>																				
SUBARU	28063-AA-010, 28063-AC-000																			













Part Number	Pk.	Description																		
<p>KH20178</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074336</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>68</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-S30-951</td> </tr> </table>	EAN	192661074336	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	152	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	68	<b>OE No.</b>		HONDA	42200-S30-951
EAN	192661074336																			
Inner diameter [mm]	30																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	152																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	68																			
<b>OE No.</b>																				
HONDA	42200-S30-951																			
<p>KH20179</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074343</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>120</td> </tr> <tr> <td>Width [mm]</td> <td>85</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>IVECO</td> <td>93810034</td> </tr> </table>	EAN	192661074343	Inner diameter [mm]	45	Outer diameter [mm]	120	Width [mm]	85	<b>OE No.</b>		IVECO	93810034						
EAN	192661074343																			
Inner diameter [mm]	45																			
Outer diameter [mm]	120																			
Width [mm]	85																			
<b>OE No.</b>																				
IVECO	93810034																			
<p>KH20180</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074350</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>65</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-17100, 52710-2D100</td> </tr> </table>	EAN	192661074350	Inner diameter [mm]	32	Number of Teeth, ABS ring	44	Outer diameter [mm]	139	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	65	<b>OE No.</b>		HYUNDAI	52710-17100, 52710-2D100
EAN	192661074350																			
Inner diameter [mm]	32																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	65																			
<b>OE No.</b>																				
HYUNDAI	52710-17100, 52710-2D100																			
<p>KH20181</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074367</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>46</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>57.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHRYSLER</td> <td>4860074AA</td> </tr> </table>	EAN	192661074367	Number of Teeth, ABS ring	46	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	57.5	<b>OE No.</b>		CHRYSLER	4860074AA		
EAN	192661074367																			
Number of Teeth, ABS ring	46																			
Outer diameter [mm]	135																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	57.5																			
<b>OE No.</b>																				
CHRYSLER	4860074AA																			
<p>KH20182</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074374</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>46</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>57.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHRYSLER</td> <td>4509766, 4509767</td> </tr> <tr> <td>DODGE</td> <td>4509766, 4509767</td> </tr> </table>	EAN	192661074374	Number of Teeth, ABS ring	46	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	57.5	<b>OE No.</b>		CHRYSLER	4509766, 4509767	DODGE	4509766, 4509767
EAN	192661074374																			
Number of Teeth, ABS ring	46																			
Outer diameter [mm]	135																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	57.5																			
<b>OE No.</b>																				
CHRYSLER	4509766, 4509767																			
DODGE	4509766, 4509767																			

Part Number	Pk.	Description																		
<p>KH20183</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074381</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43202-0L710</td> </tr> </table>	EAN	192661074381	Inner diameter [mm]	30	Outer diameter [mm]	148	Rim Hole Number	5	Width [mm]	49	<b>OE No.</b>		NISSAN	43202-0L710				
EAN	192661074381																			
Inner diameter [mm]	30																			
Outer diameter [mm]	148																			
Rim Hole Number	5																			
Width [mm]	49																			
<b>OE No.</b>																				
NISSAN	43202-0L710																			
<p>KH20184</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074398</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>47</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-29670, 52710-29671</td> </tr> </table>	EAN	192661074398	Inner diameter [mm]	28	Number of Teeth, ABS ring	44	Outer diameter [mm]	139	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	47	<b>OE No.</b>		HYUNDAI	52710-29670, 52710-29671
EAN	192661074398																			
Inner diameter [mm]	28																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	47																			
<b>OE No.</b>																				
HYUNDAI	52710-29670, 52710-29671																			
<p>KH20185</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074404</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-2D111</td> </tr> <tr> <td>KIA</td> <td>52710-2D111</td> </tr> </table>	EAN	192661074404	Inner diameter [mm]	32	Number of Teeth, ABS ring	45	Outer diameter [mm]	139	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	53	<b>OE No.</b>		HYUNDAI	52710-2D111	KIA	52710-2D111
EAN	192661074404																			
Inner diameter [mm]	32																			
Number of Teeth, ABS ring	45																			
Outer diameter [mm]	139																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	53																			
<b>OE No.</b>																				
HYUNDAI	52710-2D111																			
KIA	52710-2D111																			
<p>KH20186</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT!</b> Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074411</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-SJF-951</td> </tr> </table>	EAN	192661074411	Inner diameter [mm]	30	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	<b>OE No.</b>		HONDA	42200-SJF-951		
EAN	192661074411																			
Inner diameter [mm]	30																			
Outer diameter [mm]	139																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	67																			
<b>OE No.</b>																				
HONDA	42200-SJF-951																			
<p>KH20187</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074428</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR403558</td> </tr> </table>	EAN	192661074428	Inner diameter [mm]	30	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	56.5	<b>OE No.</b>		MITSUBISHI	MR403558		
EAN	192661074428																			
Inner diameter [mm]	30																			
Outer diameter [mm]	140																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	56.5																			
<b>OE No.</b>																				
MITSUBISHI	MR403558																			










Part Number	Pk.	Description																				
<p>KH20188</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074435</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>56.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR316631</td> </tr> </table>	EAN	192661074435	Inner diameter [mm]	30	Outer diameter [mm]	140	Rim Hole Number	5	Width [mm]	56.5	<b>OE No.</b>		MITSUBISHI	MR316631						
EAN	192661074435																					
Inner diameter [mm]	30																					
Outer diameter [mm]	140																					
Rim Hole Number	5																					
Width [mm]	56.5																					
<b>OE No.</b>																						
MITSUBISHI	MR316631																					
<p>KH20189</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT!</b> Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074442</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>45</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>89.9</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>41</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>BMW</td> <td>33 41 2 282 675</td> </tr> </table>	EAN	192661074442	Inner diameter [mm]	45	Outer diameter [mm]	89.9	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	41	<b>OE No.</b>		BMW	33 41 2 282 675						
EAN	192661074442																					
Inner diameter [mm]	45																					
Outer diameter [mm]	89.9																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	41																					
<b>OE No.</b>																						
BMW	33 41 2 282 675																					
<p>KH20190</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077504</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>56</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-S87-C51, 42200-S87-C52</td> </tr> </table>	EAN	192661077504	Inner diameter [mm]	30	Number of Teeth, ABS ring	50	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	56	<b>OE No.</b>		HONDA	42200-S87-C51, 42200-S87-C52		
EAN	192661077504																					
Inner diameter [mm]	30																					
Number of Teeth, ABS ring	50																					
Outer diameter [mm]	152																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	56																					
<b>OE No.</b>																						
HONDA	42200-S87-C51, 42200-S87-C52																					
<p>KH20191</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661077511</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>58</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>3701 58</td> </tr> <tr> <td>PEUGEOT</td> <td>3701 58</td> </tr> </table>	EAN	192661077511	Inner diameter [mm]	32	Number of Teeth, ABS ring	29	Outer diameter [mm]	128	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	58	<b>OE No.</b>		CITROËN	3701 58	PEUGEOT	3701 58
EAN	192661077511																					
Inner diameter [mm]	32																					
Number of Teeth, ABS ring	29																					
Outer diameter [mm]	128																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with ABS sensor ring																					
Width [mm]	58																					
<b>OE No.</b>																						
CITROËN	3701 58																					
PEUGEOT	3701 58																					
<p>KH20192</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>79</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43200-30R06, 43200-30R07</td> </tr> </table>	Inner diameter [mm]	30	Outer diameter [mm]	148	Rim Hole Number	4	Width [mm]	79	<b>OE No.</b>		NISSAN	43200-30R06, 43200-30R07								
Inner diameter [mm]	30																					
Outer diameter [mm]	148																					
Rim Hole Number	4																					
Width [mm]	79																					
<b>OE No.</b>																						
NISSAN	43200-30R06, 43200-30R07																					

Part Number	Pk.	Description																		
<p>KH20193</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080931</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>68</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MITSUBISHI</td> <td>MB316451, MB864967, MB864968</td> </tr> </table>	EAN	192661080931	Inner diameter [mm]	29	Outer diameter [mm]	68	Rim Hole Number	4	Width [mm]	53	<b>OE No.</b>		MITSUBISHI	MB316451, MB864967, MB864968				
EAN	192661080931																			
Inner diameter [mm]	29																			
Outer diameter [mm]	68																			
Rim Hole Number	4																			
Width [mm]	53																			
<b>OE No.</b>																				
MITSUBISHI	MB316451, MB864967, MB864968																			
<p>KH20194</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>70</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>MITSUBISHI</td> <td>MB844919</td> </tr> </table>	Inner diameter [mm]	28	Outer diameter [mm]	125	Rim Hole Number	4	Width [mm]	70	<b>OE No.</b>		MITSUBISHI	MB844919						
Inner diameter [mm]	28																			
Outer diameter [mm]	125																			
Rim Hole Number	4																			
Width [mm]	70																			
<b>OE No.</b>																				
MITSUBISHI	MB844919																			
<p>KH20195</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661080948</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>26</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Width [mm]</td> <td>50.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-02500</td> </tr> </table>	EAN	192661080948	Inner diameter [mm]	26	Outer diameter [mm]	140	Width [mm]	50.5	<b>OE No.</b>		HYUNDAI	52710-02500						
EAN	192661080948																			
Inner diameter [mm]	26																			
Outer diameter [mm]	140																			
Width [mm]	50.5																			
<b>OE No.</b>																				
HYUNDAI	52710-02500																			
<p>KH20196</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>44</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>64.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-25100, 52710-25101</td> </tr> <tr> <td>KIA</td> <td>52710-25100, 52710-25101</td> </tr> </table>	Inner diameter [mm]	28	Number of Teeth, ABS ring	44	Outer diameter [mm]	140	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	64.5	<b>OE No.</b>		HYUNDAI	52710-25100, 52710-25101	KIA	52710-25100, 52710-25101
Inner diameter [mm]	28																			
Number of Teeth, ABS ring	44																			
Outer diameter [mm]	140																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	64.5																			
<b>OE No.</b>																				
HYUNDAI	52710-25100, 52710-25101																			
KIA	52710-25100, 52710-25101																			
<p>KH20197</p> 	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>32</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>79</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52710-29100, 52710-2D000</td> </tr> <tr> <td>KIA</td> <td>52710-29100, 52710-2D000</td> </tr> </table>	Inner diameter [mm]	32	Outer diameter [mm]	139	Rim Hole Number	4	Width [mm]	79	<b>OE No.</b>		HYUNDAI	52710-29100, 52710-2D000	KIA	52710-29100, 52710-2D000				
Inner diameter [mm]	32																			
Outer diameter [mm]	139																			
Rim Hole Number	4																			
Width [mm]	79																			
<b>OE No.</b>																				
HYUNDAI	52710-29100, 52710-2D000																			
KIA	52710-29100, 52710-2D000																			







Part Number	Pk.	Description																		
<p>KH20198</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661080955</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>33</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>46</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>KIA</td> <td>0K9A5-26-150</td> </tr> </table>	EAN	192661080955	Inner diameter [mm]	33	Number of Teeth, ABS ring	46	Outer diameter [mm]	140	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	59	<b>OE No.</b>		KIA	0K9A5-26-150
EAN	192661080955																			
Inner diameter [mm]	33																			
Number of Teeth, ABS ring	46																			
Outer diameter [mm]	140																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	59																			
<b>OE No.</b>																				
KIA	0K9A5-26-150																			
<p>KH20199</p>	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>49</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-S04-951</td> </tr> </table>	Inner diameter [mm]	28	Number of Teeth, ABS ring	50	Outer diameter [mm]	134	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	49	<b>OE No.</b>		HONDA	42200-S04-951		
Inner diameter [mm]	28																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	134																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	49																			
<b>OE No.</b>																				
HONDA	42200-S04-951																			
<p>KH20200</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661080962</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>34</td> </tr> <tr> <td>Number of Teeth, ABS ring</td> <td>50</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67.5</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-SV2-N51, 42200-SV4-N51</td> </tr> </table>	EAN	192661080962	Inner diameter [mm]	34	Number of Teeth, ABS ring	50	Outer diameter [mm]	152	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	67.5	<b>OE No.</b>		HONDA	42200-SV2-N51, 42200-SV4-N51
EAN	192661080962																			
Inner diameter [mm]	34																			
Number of Teeth, ABS ring	50																			
Outer diameter [mm]	152																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	67.5																			
<b>OE No.</b>																				
HONDA	42200-SV2-N51, 42200-SV4-N51																			
<p>KH20201</p>	1	<table border="1"> <tr> <td>Inner diameter [mm]</td> <td>43</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>127</td> </tr> <tr> <td>Width [mm]</td> <td>45</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>43210-AL500, 43210-AL505</td> </tr> </table>	Inner diameter [mm]	43	Outer diameter [mm]	127	Width [mm]	45	<b>OE No.</b>		NISSAN	43210-AL500, 43210-AL505								
Inner diameter [mm]	43																			
Outer diameter [mm]	127																			
Width [mm]	45																			
<b>OE No.</b>																				
NISSAN	43210-AL500, 43210-AL505																			
<p>KH20202</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>53</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MITSUBISHI</td> <td>MR223284</td> </tr> </table>	Inner diameter [mm]	28	Outer diameter [mm]	125	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	53	<b>OE No.</b>		MITSUBISHI	MR223284						
Inner diameter [mm]	28																			
Outer diameter [mm]	125																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	53																			
<b>OE No.</b>																				
MITSUBISHI	MR223284																			





Part Number	Pk.	Description																		
<p>KH30002</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176951145</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>136.5</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>85</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A, 8X0 498 625</td> </tr> <tr> <td>SEAT</td> <td>1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A</td> </tr> <tr> <td>SKODA</td> <td>1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A</td> </tr> <tr> <td>VW</td> <td>1K0 407 621 C, 1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A</td> </tr> </table>	EAN	29176951145	Outer diameter 1 [mm]	136.5	Outer diameter 2 [mm]	85	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	AUDI	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A, 8X0 498 625	SEAT	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A	SKODA	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A	VW	1K0 407 621 C, 1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A
EAN	29176951145																			
Outer diameter 1 [mm]	136.5																			
Outer diameter 2 [mm]	85																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
AUDI	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A, 8X0 498 625																			
SEAT	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A																			
SKODA	1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A																			
VW	1K0 407 621 C, 1T0 498 621, 3C0 498 621, 5K0 498 621, 8J0 598 625, 8J0 598 625A																			
<p>KH30003</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>42200-T3V-A51</td> </tr> </table>	Number of mounting bores	4	Outer diameter [mm]	139.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	HONDA	42200-T3V-A51								
Number of mounting bores	4																			
Outer diameter [mm]	139.5																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
HONDA	42200-T3V-A51																			
<p>KH30004</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176989858</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>134</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>43202-1J60A</td> </tr> </table>	EAN	29176989858	Number of mounting bores	4	Outer diameter [mm]	134	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	NISSAN	43202-1J60A						
EAN	29176989858																			
Number of mounting bores	4																			
Outer diameter [mm]	134																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
NISSAN	43202-1J60A																			
<p>KH30005</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>29176975950</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HONDA</td> <td>42200-TA0A-51, 42200-TA0A-A511-M1</td> </tr> </table>	EAN	29176975950	Number of mounting bores	4	Outer diameter [mm]	139.5	Rim Hole Number	5	HONDA	42200-TA0A-51, 42200-TA0A-A511-M1								
EAN	29176975950																			
Number of mounting bores	4																			
Outer diameter [mm]	139.5																			
Rim Hole Number	5																			
HONDA	42200-TA0A-51, 42200-TA0A-A511-M1																			
<p>KH30006</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176970863</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MINI</td> <td>31 22 6 756 889</td> </tr> </table>	EAN	29176970863	Number of mounting bores	4	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	MINI	31 22 6 756 889						
EAN	29176970863																			
Number of mounting bores	4																			
Outer diameter [mm]	137.5																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
MINI	31 22 6 756 889																			







Part Number	Pk.	Description										
<p>KH30007</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176974564</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MINI 31 22 6 776 162, 31 22 6 776 671</p>	EAN	29176974564	Number of mounting bores	4	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176974564											
Number of mounting bores	4											
Outer diameter [mm]	137.5											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30008</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176973437</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MINI 33 41 6 756 830</p>	EAN	29176973437	Number of mounting bores	4	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176973437											
Number of mounting bores	4											
Outer diameter [mm]	137.5											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30010</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176971907</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MINI 33 41 6 786 552</p>	EAN	29176971907	Number of mounting bores	4	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176971907											
Number of mounting bores	4											
Outer diameter [mm]	137.5											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30011</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975172</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> NISSAN 40202-ED000, 40202-ED00A, 40202-ED02A, 40202-ED05A</p>	EAN	29176975172	Number of mounting bores	3	Outer diameter [mm]	122	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176975172											
Number of mounting bores	3											
Outer diameter [mm]	122											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30012</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176990250</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> HONDA 42200-TL0-G51</p>	EAN	29176990250	Number of mounting bores	4	Outer diameter [mm]	152.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176990250											
Number of mounting bores	4											
Outer diameter [mm]	152.5											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											

Part Number	Pk.	Description																						
<p>KH30013</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975578</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>TOYOTA</td> <td>42410-42040</td> </tr> <tr> <td>TOYOTA (FAW)</td> <td>42410-42040</td> </tr> </table>	EAN	29176975578	Number of mounting bores	4	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	TOYOTA	42410-42040	TOYOTA (FAW)	42410-42040								
EAN	29176975578																							
Number of mounting bores	4																							
Outer diameter [mm]	152																							
Rim Hole Number	5																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
TOYOTA	42410-42040																							
TOYOTA (FAW)	42410-42040																							
<p>KH30014</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176973444</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter 1 [mm]</td> <td>136.5</td> </tr> <tr> <td>Outer diameter 2 [mm]</td> <td>85</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>5Q0 407 621 A, 8V0 498 625 A</td> </tr> <tr> <td>SEAT</td> <td>8V0 498 625 A</td> </tr> <tr> <td>SKODA</td> <td>8V0 498 625 A</td> </tr> <tr> <td>VAG</td> <td>8V0 498 625 A</td> </tr> <tr> <td>VW</td> <td>8V0 498 625 A</td> </tr> </table>	EAN	29176973444	Number of mounting bores	3	Outer diameter 1 [mm]	136.5	Outer diameter 2 [mm]	85	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	AUDI	5Q0 407 621 A, 8V0 498 625 A	SEAT	8V0 498 625 A	SKODA	8V0 498 625 A	VAG	8V0 498 625 A	VW	8V0 498 625 A
EAN	29176973444																							
Number of mounting bores	3																							
Outer diameter 1 [mm]	136.5																							
Outer diameter 2 [mm]	85																							
Rim Hole Number	5																							
Supplementary Article/Info 2	with integrated magnetic sensor ring																							
AUDI	5Q0 407 621 A, 8V0 498 625 A																							
SEAT	8V0 498 625 A																							
SKODA	8V0 498 625 A																							
VAG	8V0 498 625 A																							
VW	8V0 498 625 A																							
<p>KH30015</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975585</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>3748 A0, 3748.96</td> </tr> <tr> <td>FIAT</td> <td>140 139 34 80, 940 374 89 69</td> </tr> <tr> <td>PEUGEOT</td> <td>140 139 34 80, 3748 A0</td> </tr> <tr> <td>TOYOTA</td> <td>SU 001A 1005</td> </tr> </table>	EAN	29176975585	Number of mounting bores	4	Outer diameter [mm]	128	Supplementary Article/Info 2	with integrated ABS sensor	CITROËN	3748 A0, 3748.96	FIAT	140 139 34 80, 940 374 89 69	PEUGEOT	140 139 34 80, 3748 A0	TOYOTA	SU 001A 1005						
EAN	29176975585																							
Number of mounting bores	4																							
Outer diameter [mm]	128																							
Supplementary Article/Info 2	with integrated ABS sensor																							
CITROËN	3748 A0, 3748.96																							
FIAT	140 139 34 80, 940 374 89 69																							
PEUGEOT	140 139 34 80, 3748 A0																							
TOYOTA	SU 001A 1005																							
<p>KH30016</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176971914</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>128</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>144 008 82 80, 3448.A3, 3748 99, 3748.95, 3748.A3</td> </tr> <tr> <td>FIAT</td> <td>1401393280, 1440088280, 940 374 89 59</td> </tr> <tr> <td>PEUGEOT</td> <td>144 008 82 80, 3748 99, 3748.A3</td> </tr> <tr> <td>TOYOTA</td> <td>SU 001A 1006</td> </tr> </table>	EAN	29176971914	Number of mounting bores	4	Outer diameter [mm]	128	Supplementary Article/Info 2	with integrated ABS sensor	CITROËN	144 008 82 80, 3448.A3, 3748 99, 3748.95, 3748.A3	FIAT	1401393280, 1440088280, 940 374 89 59	PEUGEOT	144 008 82 80, 3748 99, 3748.A3	TOYOTA	SU 001A 1006						
EAN	29176971914																							
Number of mounting bores	4																							
Outer diameter [mm]	128																							
Supplementary Article/Info 2	with integrated ABS sensor																							
CITROËN	144 008 82 80, 3448.A3, 3748 99, 3748.95, 3748.A3																							
FIAT	1401393280, 1440088280, 940 374 89 59																							
PEUGEOT	144 008 82 80, 3748 99, 3748.A3																							
TOYOTA	SU 001A 1006																							












Part Number	Pk.	Description												
<p>KH30017</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176990267</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> TOYOTA 43550-02010, 43550-02070, 43550-12010, 43550-42010</p>	EAN	29176990267	Number of mounting bores	4	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring		
EAN	29176990267													
Number of mounting bores	4													
Outer diameter [mm]	139													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
<p>KH30018</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Axle Stub Diameter [mm]</td> <td>30</td> </tr> <tr> <td>EAN</td> <td>29176978128</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> TOYOTA 43350-42020, 43550-02020, 43550-02080</p>	Axle Stub Diameter [mm]	30	EAN	29176978128	Number of mounting bores	4	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
Axle Stub Diameter [mm]	30													
EAN	29176978128													
Number of mounting bores	4													
Outer diameter [mm]	139													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
<p>KH30021</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176976049</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>143</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MITSUBISHI MR 594443</p>	EAN	29176976049	Number of mounting bores	4	Outer diameter [mm]	143	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring		
EAN	29176976049													
Number of mounting bores	4													
Outer diameter [mm]	143													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
<p>KH30023</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176976056</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> NISSAN 43202 1KA0A, 43202 BA60A</p>	EAN	29176976056	Number of mounting bores	4	Outer diameter [mm]	148	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring		
EAN	29176976056													
Number of mounting bores	4													
Outer diameter [mm]	148													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													

Part Number	Pk.	Description																
<p>KH30024</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176978135</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHEVROLET</td> <td>19316545, 19318302, 19318306</td> </tr> <tr> <td>NISSAN</td> <td>40202-1KA0A, 40202-3DA0A, 40202-3PU0A, 40202-3RA0A, 40202-3SH0A, 40202-3SH1A, 40202-4AFOA, 40202-5SK0A, 40202-BA60A, 40202-EN010, 40202-JG000, 40202-JG01A, 40202-JG01B</td> </tr> <tr> <td>RENAULT</td> <td>40202 2560R, 40202 JY00A</td> </tr> </table>	EAN	29176978135	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	CHEVROLET	19316545, 19318302, 19318306	NISSAN	40202-1KA0A, 40202-3DA0A, 40202-3PU0A, 40202-3RA0A, 40202-3SH0A, 40202-3SH1A, 40202-4AFOA, 40202-5SK0A, 40202-BA60A, 40202-EN010, 40202-JG000, 40202-JG01A, 40202-JG01B	RENAULT	40202 2560R, 40202 JY00A
EAN	29176978135																	
Number of mounting bores	4																	
Outer diameter [mm]	136																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
CHEVROLET	19316545, 19318302, 19318306																	
NISSAN	40202-1KA0A, 40202-3DA0A, 40202-3PU0A, 40202-3RA0A, 40202-3SH0A, 40202-3SH1A, 40202-4AFOA, 40202-5SK0A, 40202-BA60A, 40202-EN010, 40202-JG000, 40202-JG01A, 40202-JG01B																	
RENAULT	40202 2560R, 40202 JY00A																	
<p>KH30025</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176976063</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>INFINITI</td> <td>40202 1EA0B, 40202 4GA0A, 40202 CG010, 40202 CG01A, 40202 CG01B, 40202 EG000, 40202 EG06C, 40202 EJ70A</td> </tr> <tr> <td>NISSAN</td> <td>40202 1EA0B, 40202 4GA0A, 40202 EG000, 40202 EG06C, 40202 EJ70A</td> </tr> </table>	EAN	29176976063	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	INFINITI	40202 1EA0B, 40202 4GA0A, 40202 CG010, 40202 CG01A, 40202 CG01B, 40202 EG000, 40202 EG06C, 40202 EJ70A	NISSAN	40202 1EA0B, 40202 4GA0A, 40202 EG000, 40202 EG06C, 40202 EJ70A		
EAN	29176976063																	
Number of mounting bores	4																	
Outer diameter [mm]	136																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
INFINITI	40202 1EA0B, 40202 4GA0A, 40202 CG010, 40202 CG01A, 40202 CG01B, 40202 EG000, 40202 EG06C, 40202 EJ70A																	
NISSAN	40202 1EA0B, 40202 4GA0A, 40202 EG000, 40202 EG06C, 40202 EJ70A																	
<p>KH30026</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176976070</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>INFINITI</td> <td>40202-EJ70B</td> </tr> </table>	EAN	29176976070	Number of mounting bores	4	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated magnetic sensor ring	INFINITI	40202-EJ70B						
EAN	29176976070																	
Number of mounting bores	4																	
Outer diameter [mm]	136																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
INFINITI	40202-EJ70B																	
<p>KH30027</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176975967</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40202-CA06C, 40202-ZM70A</td> </tr> </table>	EAN	29176975967	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	NISSAN	40202-CA06C, 40202-ZM70A				
EAN	29176975967																	
Number of mounting bores	4																	
Outer diameter [mm]	136																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
NISSAN	40202-CA06C, 40202-ZM70A																	













Part Number	Pk.	Description										
<p>KH30028</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176978586</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-12090, 42450-12140</p>	EAN	29176978586	Number of mounting bores	4	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor
EAN	29176978586											
Number of mounting bores	4											
Outer diameter [mm]	152											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated ABS sensor											
<p>KH30029</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176980862</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>121</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> RENAULT 43206 7636R SMART A 453 356 00 00</p>	EAN	29176980862	Number of mounting bores	4	Outer diameter [mm]	121	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176980862											
Number of mounting bores	4											
Outer diameter [mm]	121											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30032</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176990274</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MINI 33 41 6 786 552</p>	EAN	29176990274	Number of mounting bores	4	Outer diameter [mm]	137.5	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	29176990274											
Number of mounting bores	4											
Outer diameter [mm]	137.5											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30033</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010440</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> LEXUS 43550-30030, 43550-30031</p>	EAN	192661010440	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661010440											
Number of mounting bores	4											
Outer diameter [mm]	140											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											

Part Number	Pk.	Description										
<p>KH30034</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010457</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> LEXUS 43560-30030, 43560-30031</p>	EAN	192661010457	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661010457											
Number of mounting bores	4											
Outer diameter [mm]	140											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30035</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661010464</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-02120, 42450-12100</p>	EAN	192661010464	Number of mounting bores	4	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor
EAN	192661010464											
Number of mounting bores	4											
Outer diameter [mm]	152											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated ABS sensor											
<p>KH30036</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661012727</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>124</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> SUBARU 28473-AG000, 28473-AG001, 28474-AG000</p>	EAN	192661012727	Number of mounting bores	4	Outer diameter [mm]	124	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661012727											
Number of mounting bores	4											
Outer diameter [mm]	124											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30040</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>29176994197</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-47040</p>	EAN	29176994197	Number of mounting bores	4	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor
EAN	29176994197											
Number of mounting bores	4											
Outer diameter [mm]	135											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated ABS sensor											
<p>KH30041</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661012239</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> OPEL 16 04 315, 93178625 VAUXHALL 16 04 315, 93178625</p>	EAN	192661012239	Number of mounting bores	4	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated ABS sensor		
EAN	192661012239											
Number of mounting bores	4											
Outer diameter [mm]	136											
Supplementary Article/Info 2	with integrated ABS sensor											







Part Number	Pk.	Description																		
<p>KH30042</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661012246</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1471852, 1481197, 1491957, 1506577, 1508112, 1766628, 3M51-2C299-RBC, 7M51-2C299-AA, 7M51-2C299-AB, 7M51-2C299-AC, 7M51-2C299-AD, 7M51-2C299-BC</td> </tr> </table>	EAN	192661012246	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	FORD	1471852, 1481197, 1491957, 1506577, 1508112, 1766628, 3M51-2C299-RBC, 7M51-2C299-AA, 7M51-2C299-AB, 7M51-2C299-AC, 7M51-2C299-AD, 7M51-2C299-BC						
EAN	192661012246																			
Number of mounting bores	4																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
FORD	1471852, 1481197, 1491957, 1506577, 1508112, 1766628, 3M51-2C299-RBC, 7M51-2C299-AA, 7M51-2C299-AB, 7M51-2C299-AC, 7M51-2C299-AD, 7M51-2C299-BC																			
<p>KH30043</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661013632</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1115019, 1124904, 1146689, 1332888, 1383427, 1S71-2C299-AC, 1S71-2C299-AD, 1S71-2C299-AF, 1S71-2C299-AG, 1S71-2C299-AH, 1S71-2C299-AJ, 4858822</td> </tr> <tr> <td>JAGUAR</td> <td>C2S46771</td> </tr> </table>	EAN	192661013632	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated ABS sensor	FORD	1115019, 1124904, 1146689, 1332888, 1383427, 1S71-2C299-AC, 1S71-2C299-AD, 1S71-2C299-AF, 1S71-2C299-AG, 1S71-2C299-AH, 1S71-2C299-AJ, 4858822	JAGUAR	C2S46771								
EAN	192661013632																			
Outer diameter [mm]	136																			
Supplementary Article/Info 2	with integrated ABS sensor																			
FORD	1115019, 1124904, 1146689, 1332888, 1383427, 1S71-2C299-AC, 1S71-2C299-AD, 1S71-2C299-AF, 1S71-2C299-AG, 1S71-2C299-AH, 1S71-2C299-AJ, 4858822																			
JAGUAR	C2S46771																			
<p>KH30044</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661013649</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 04 316, 93178626</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 316, 93178626</td> </tr> </table>	EAN	192661013649	Outer diameter [mm]	140	Supplementary Article/Info 2	with integrated ABS sensor	OPEL	16 04 316, 93178626	VAUXHALL	16 04 316, 93178626								
EAN	192661013649																			
Outer diameter [mm]	140																			
Supplementary Article/Info 2	with integrated ABS sensor																			
OPEL	16 04 316, 93178626																			
VAUXHALL	16 04 316, 93178626																			
<p>KH30045</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661011706</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>127</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>82</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E</td> </tr> <tr> <td>SEAT</td> <td>6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E</td> </tr> <tr> <td>SKODA</td> <td>6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E</td> </tr> <tr> <td>VW</td> <td>6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E</td> </tr> </table>	EAN	192661011706	Outer diameter [mm]	127	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	82	AUDI	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E	SEAT	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E	SKODA	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E	VW	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E
EAN	192661011706																			
Outer diameter [mm]	127																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	82																			
AUDI	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E																			
SEAT	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E																			
SKODA	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E																			
VW	6C0 407 621, 6Q0 407 621 AD, 6Q0 407 621 AH, 6Q0 407 621 AJ, 6Q0 407 621 BR, 6R0 407 621 A, 6R0 407 621 E																			





Part Number	Pk.	Description																
<p>KH30046</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661023211</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 03 254, 93178652</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 254, 93178652</td> </tr> </table>	EAN	192661023211	Outer diameter [mm]	137	Supplementary Article/Info 2	with integrated ABS sensor	OPEL	16 03 254, 93178652	VAUXHALL	16 03 254, 93178652						
EAN	192661023211																	
Outer diameter [mm]	137																	
Supplementary Article/Info 2	with integrated ABS sensor																	
OPEL	16 03 254, 93178652																	
VAUXHALL	16 03 254, 93178652																	
<p>KH30048</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661037614</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B</td> </tr> <tr> <td>SEAT</td> <td>1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B</td> </tr> <tr> <td>SKODA</td> <td>1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B</td> </tr> <tr> <td>VW</td> <td>1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B</td> </tr> </table>	EAN	192661037614	Outer diameter [mm]	136.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	AUDI	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B	SEAT	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B	SKODA	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B	VW	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B
EAN	192661037614																	
Outer diameter [mm]	136.5																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
AUDI	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B																	
SEAT	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B																	
SKODA	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B																	
VW	1K0 407 621 E, 1K0 498 621, 5K0 498 621 A, 5WA 407 621, 8V0 498 625, 8V0 498 625 B, 8V0 598 625, 8V0 598 625 B																	
<p>KH30049</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661037621</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136.5</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C</td> </tr> <tr> <td>SEAT</td> <td>5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C</td> </tr> <tr> <td>SKODA</td> <td>5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C</td> </tr> <tr> <td>VW</td> <td>5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C</td> </tr> </table>	EAN	192661037621	Outer diameter [mm]	136.5	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	AUDI	5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C	SEAT	5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C	SKODA	5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C	VW	5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C
EAN	192661037621																	
Outer diameter [mm]	136.5																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
AUDI	5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C																	
SEAT	5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C																	
SKODA	5Q0 407 621 A, 5WA 407 621 A, 8V0 598 625C																	
VW	5Q0 407 621 A, 5WA 407 621 A, 8S0 498 625, 8V0 598 625C																	
<p>KH30050</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661023815</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MAZDA</td> <td>N243-26-15X</td> </tr> </table>	EAN	192661023815	Number of mounting bores	3	Outer diameter [mm]	122	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	MAZDA	N243-26-15X				
EAN	192661023815																	
Number of mounting bores	3																	
Outer diameter [mm]	122																	
Rim Hole Number	4																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
MAZDA	N243-26-15X																	



Part Number	Pk.	Description										
<p>KH30051</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661039786</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> MAZDA                    D10H-26-15X</p>	EAN	192661039786	Number of mounting bores	4	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661039786											
Number of mounting bores	4											
Outer diameter [mm]	139											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30054</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661043431</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> OPEL                    16 04 003, 16 04 302, 16 04 306, 90510629, 90540069, 9120128 VAUXHALL            16 04 003, 16 04 302, 16 04 306, 90510629, 90540069, 9120128</p>	EAN	192661043431	Number of mounting bores	4	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated ABS sensor		
EAN	192661043431											
Number of mounting bores	4											
Outer diameter [mm]	136											
Supplementary Article/Info 2	with integrated ABS sensor											
<p>KH30055</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661049525</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> </table> <p><b>OE No.</b> OPEL                    16 04 004, 16 04 307, 4 21 000, 90511494, 90540262, 9120129 VAUXHALL            16 04 004, 16 04 307, 4 21 000, 90511494, 90540262, 9120129</p>	EAN	192661049525	Number of mounting bores	4	Outer diameter [mm]	136				
EAN	192661049525											
Number of mounting bores	4											
Outer diameter [mm]	136											
<p>KH30057</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661049532</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>119.4</td> </tr> <tr> <td>Width [mm]</td> <td>85</td> </tr> </table> <p><b>OE No.</b> OPEL                    1603208, 9117619 VAUXHALL            1603208, 9117619</p>	EAN	192661049532	Inner diameter [mm]	25	Number of mounting bores	3	Outer diameter [mm]	119.4	Width [mm]	85
EAN	192661049532											
Inner diameter [mm]	25											
Number of mounting bores	3											
Outer diameter [mm]	119.4											
Width [mm]	85											
<p>KH30058</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049549</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>119.2</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> OPEL                    1603209, 9117620 VAUXHALL            1603209, 9117620</p>	EAN	192661049549	Number of mounting bores	3	Outer diameter [mm]	119.2	Supplementary Article/Info 2	with integrated ABS sensor		
EAN	192661049549											
Number of mounting bores	3											
Outer diameter [mm]	119.2											
Supplementary Article/Info 2	with integrated ABS sensor											

Part Number	Pk.	Description																				
<p>KH30059</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049556</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>25.4</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>1603211, 9117622</td> </tr> <tr> <td>VAUXHALL</td> <td>1603211, 9117622</td> </tr> </table>	EAN	192661049556	Inner diameter [mm]	25.4	Number of mounting bores	3	Outer diameter [mm]	137	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	84	OPEL	1603211, 9117622	VAUXHALL	1603211, 9117622				
EAN	192661049556																					
Inner diameter [mm]	25.4																					
Number of mounting bores	3																					
Outer diameter [mm]	137																					
Supplementary Article/Info 2	with integrated ABS sensor																					
Width [mm]	84																					
OPEL	1603211, 9117622																					
VAUXHALL	1603211, 9117622																					
<p>KH30060</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049563</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>89</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>VOLVO</td> <td>31201011, 31340099, 31340100</td> </tr> </table>	EAN	192661049563	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	89	VOLVO	31201011, 31340099, 31340100						
EAN	192661049563																					
Number of mounting bores	4																					
Outer diameter [mm]	136																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	89																					
VOLVO	31201011, 31340099, 31340100																					
<p>KH30061</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049570</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>51748680</td> </tr> <tr> <td>OPEL</td> <td>16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387</td> </tr> <tr> <td>SAAB</td> <td>93175327, 93186387</td> </tr> <tr> <td>VAUXHALL</td> <td>16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387</td> </tr> </table>	EAN	192661049570	Number of mounting bores	3	Outer diameter [mm]	137	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	39	FIAT	51748680	OPEL	16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387	SAAB	93175327, 93186387	VAUXHALL	16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387
EAN	192661049570																					
Number of mounting bores	3																					
Outer diameter [mm]	137																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with integrated ABS sensor																					
Width [mm]	39																					
FIAT	51748680																					
OPEL	16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387																					
SAAB	93175327, 93186387																					
VAUXHALL	16 03 143, 16 03 243, 16 03 294, 93171495, 93175327, 93186387																					
<p>KH30062</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049587</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>117</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HYUNDAI</td> <td>52750-1G100, 52750-1G101</td> </tr> <tr> <td>KIA</td> <td>52750-1G100, 52750-1G101</td> </tr> </table>	EAN	192661049587	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	4	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	117	HYUNDAI	52750-1G100, 52750-1G101	KIA	52750-1G100, 52750-1G101				
EAN	192661049587																					
Number of mounting bores	4																					
Outer diameter [mm]	140																					
Rim Hole Number	4																					
Supplementary Article/Info 2	with integrated ABS sensor																					
Width [mm]	117																					
HYUNDAI	52750-1G100, 52750-1G101																					
KIA	52750-1G100, 52750-1G101																					







Part Number	Pk.	Description
<p>KH30063</p> 	1	<p>EAN 192661049594</p> <p>Outer diameter [mm] 143</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with ABS sensor ring</p> <p>Width [mm] 51</p> <p><b>OE No.</b></p> <p>BMW 31 22 6 765 601</p>
<p>KH30064</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661049600</p> <p>Number of mounting bores 4</p> <p>Outer diameter [mm] 135</p> <p>Rim Hole Number 4</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 56</p> <p><b>OE No.</b></p> <p>CITROËN 3748.85</p> <p>PEUGEOT 3748.85</p> <p>TOYOTA 42450-0H010</p>
<p>KH30065</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661049617</p> <p>Inner diameter [mm] 33</p> <p>Number of mounting bores 3</p> <p>Outer diameter [mm] 137</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with integrated ABS sensor</p> <p>Width [mm] 39</p> <p><b>OE No.</b></p> <p>OPEL 16 03 255, 16 03 295, 93178661, 93186388</p> <p>VAUXHALL 16 03 255, 16 03 295, 93178661, 93186388</p>
<p>KH30066</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661049624</p> <p>Number of mounting bores 4</p> <p>Outer diameter [mm] 136</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with integrated ABS sensor</p> <p>Width [mm] 99</p> <p><b>OE No.</b></p> <p>VOLVO 31201642, 31280051</p>

Part Number	Pk.	Description																																	
KH30067	1	<table border="1"> <tr> <td colspan="2">EAN</td> <td>192661049631</td> </tr> <tr> <td colspan="2">Number of Teeth, ABS ring</td> <td>46</td> </tr> <tr> <td colspan="2">Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td colspan="2">Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2">Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>52730-2H000</td> <td></td> </tr> <tr> <td>KIA</td> <td>52730-2H000</td> <td></td> </tr> </table>	EAN		192661049631	Number of Teeth, ABS ring		46	Outer diameter [mm]		148	Rim Hole Number		5	Supplementary Article/Info 2		with ABS sensor ring	<b>OE No.</b>			HYUNDAI	52730-2H000		KIA	52730-2H000										
EAN		192661049631																																	
Number of Teeth, ABS ring		46																																	
Outer diameter [mm]		148																																	
Rim Hole Number		5																																	
Supplementary Article/Info 2		with ABS sensor ring																																	
<b>OE No.</b>																																			
HYUNDAI	52730-2H000																																		
KIA	52730-2H000																																		
KH30068	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td colspan="2">EAN</td> <td>192661049648</td> </tr> <tr> <td colspan="2">Number of mounting bores</td> <td>3</td> </tr> <tr> <td colspan="2">Outer diameter [mm]</td> <td>151</td> </tr> <tr> <td colspan="2">Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2">Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td colspan="2">Width [mm]</td> <td>88</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>25903358, 48 09 314, 48 14 304, 96626339</td> <td></td> </tr> <tr> <td>OPEL</td> <td>25903358, 48 09 314, 48 14 304, 96626339</td> <td></td> </tr> <tr> <td>VAUXHALL</td> <td>25903358, 48 09 314, 48 14 304, 96626339</td> <td></td> </tr> </table>	EAN		192661049648	Number of mounting bores		3	Outer diameter [mm]		151	Rim Hole Number		5	Supplementary Article/Info 2		with integrated ABS sensor	Width [mm]		88	<b>OE No.</b>			CHEVROLET	25903358, 48 09 314, 48 14 304, 96626339		OPEL	25903358, 48 09 314, 48 14 304, 96626339		VAUXHALL	25903358, 48 09 314, 48 14 304, 96626339				
EAN		192661049648																																	
Number of mounting bores		3																																	
Outer diameter [mm]		151																																	
Rim Hole Number		5																																	
Supplementary Article/Info 2		with integrated ABS sensor																																	
Width [mm]		88																																	
<b>OE No.</b>																																			
CHEVROLET	25903358, 48 09 314, 48 14 304, 96626339																																		
OPEL	25903358, 48 09 314, 48 14 304, 96626339																																		
VAUXHALL	25903358, 48 09 314, 48 14 304, 96626339																																		
KH30069	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td colspan="2">EAN</td> <td>192661049655</td> </tr> <tr> <td colspan="2">Number of mounting bores</td> <td>4</td> </tr> <tr> <td colspan="2">Outer diameter [mm]</td> <td>131.25</td> </tr> <tr> <td colspan="2">Rim Hole Number</td> <td>4</td> </tr> <tr> <td colspan="2">Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2">Width [mm]</td> <td>68.5</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>FORD</td> <td>1699196, 1896739, 1899042, DCP1-2C299-A1C, DCP1-2C299-B6A</td> <td></td> </tr> </table>	EAN		192661049655	Number of mounting bores		4	Outer diameter [mm]		131.25	Rim Hole Number		4	Supplementary Article/Info 2		with integrated magnetic sensor ring	Width [mm]		68.5	<b>OE No.</b>			FORD	1699196, 1896739, 1899042, DCP1-2C299-A1C, DCP1-2C299-B6A										
EAN		192661049655																																	
Number of mounting bores		4																																	
Outer diameter [mm]		131.25																																	
Rim Hole Number		4																																	
Supplementary Article/Info 2		with integrated magnetic sensor ring																																	
Width [mm]		68.5																																	
<b>OE No.</b>																																			
FORD	1699196, 1896739, 1899042, DCP1-2C299-A1C, DCP1-2C299-B6A																																		
KH30070	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td colspan="2">EAN</td> <td>192661049662</td> </tr> <tr> <td colspan="2">Number of mounting bores</td> <td>3</td> </tr> <tr> <td colspan="2">Outer diameter [mm]</td> <td>157</td> </tr> <tr> <td colspan="2">Rim Hole Number</td> <td>5</td> </tr> <tr> <td colspan="2">Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td colspan="2">Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="3"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>13502785, 13580135, 328292</td> <td></td> </tr> <tr> <td>OPEL</td> <td>13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292</td> <td></td> </tr> <tr> <td>SAAB</td> <td>13502785, 328292</td> <td></td> </tr> <tr> <td>VAUXHALL</td> <td>13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292</td> <td></td> </tr> </table>	EAN		192661049662	Number of mounting bores		3	Outer diameter [mm]		157	Rim Hole Number		5	Supplementary Article/Info 2		with integrated magnetic sensor ring	Width [mm]		67	<b>OE No.</b>			CHEVROLET	13502785, 13580135, 328292		OPEL	13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292		SAAB	13502785, 328292		VAUXHALL	13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292	
EAN		192661049662																																	
Number of mounting bores		3																																	
Outer diameter [mm]		157																																	
Rim Hole Number		5																																	
Supplementary Article/Info 2		with integrated magnetic sensor ring																																	
Width [mm]		67																																	
<b>OE No.</b>																																			
CHEVROLET	13502785, 13580135, 328292																																		
OPEL	13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292																																		
SAAB	13502785, 328292																																		
VAUXHALL	13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292																																		









Part Number	Pk.	Description
<p>KH30071</p> 	1	<p>EAN   192661049679</p> <p>Number of mounting bores   4</p> <p>Outer diameter [mm]   140</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   68</p> <p><b>OE No.</b></p> <p>OPEL   16 04 314, 93170611</p> <p>SAAB   24 421 906, 93 170 611</p> <p>VAUXHALL   16 04 314, 93170611</p>
<p>KH30072</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049686</p> <p>Number of mounting bores   3</p> <p>Outer diameter [mm]   120</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   39</p> <p><b>OE No.</b></p> <p>OPEL   16 03 253, 93178651</p> <p>VAUXHALL   16 03 253, 93178651</p>
<p>KH30073</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049693</p> <p>Outer diameter [mm]   135</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   38</p> <p><b>OE No.</b></p> <p>ALFA ROMEO   50707555, 71753815</p>
<p>KH30074</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661049709</p> <p>Inner diameter [mm]   30</p> <p>Number of mounting bores   3</p> <p>Outer diameter [mm]   137</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   85</p> <p><b>OE No.</b></p> <p>OPEL   16 03 282, 16 03 296, 93182913, 93186389</p> <p>VAUXHALL   16 03 282, 16 03 296, 93182913, 93186389</p>

Part Number	Pk.	Description																
<p>KH30075</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052594</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>68</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>71742696, 71768040, 71768165</td> </tr> <tr> <td>SUZUKI</td> <td>43402-79J50, 43402-79J51, 43402-79J52</td> </tr> </table>	EAN	192661052594	Number of mounting bores	4	Outer diameter [mm]	125	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	68	FIAT	71742696, 71768040, 71768165	SUZUKI	43402-79J50, 43402-79J51, 43402-79J52
EAN	192661052594																	
Number of mounting bores	4																	
Outer diameter [mm]	125																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated ABS sensor																	
Width [mm]	68																	
FIAT	71742696, 71768040, 71768165																	
SUZUKI	43402-79J50, 43402-79J51, 43402-79J52																	
<p>KH30076</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049716</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>153</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>JEEP</td> <td>52128692AC, 52128692AD, 52128692AE, 52128692AF</td> </tr> </table>	EAN	192661049716	Number of mounting bores	3	Outer diameter [mm]	153	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	84	JEEP	52128692AC, 52128692AD, 52128692AE, 52128692AF		
EAN	192661049716																	
Number of mounting bores	3																	
Outer diameter [mm]	153																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated ABS sensor																	
Width [mm]	84																	
JEEP	52128692AC, 52128692AD, 52128692AE, 52128692AF																	
<p>KH30077</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049723</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHRYSLER</td> <td>4641517AD</td> </tr> </table>	EAN	192661049723	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	60	CHRYSLER	4641517AD		
EAN	192661049723																	
Number of mounting bores	4																	
Outer diameter [mm]	140																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	60																	
CHRYSLER	4641517AD																	
<p>KH30078</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052600</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>83</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>BMW</td> <td>31 20 1 095 616, 31 22 1 093 427</td> </tr> </table>	EAN	192661052600	Number of mounting bores	4	Outer diameter [mm]	139	Rim Hole Number	5	Width [mm]	83	BMW	31 20 1 095 616, 31 22 1 093 427				
EAN	192661052600																	
Number of mounting bores	4																	
Outer diameter [mm]	139																	
Rim Hole Number	5																	
Width [mm]	83																	
BMW	31 20 1 095 616, 31 22 1 093 427																	






Part Number	Pk.	Description												
<p>KH30080</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052624</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>147</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>51</td> </tr> </table> <p><b>OE No.</b> BMW 31 21 6 765 157</p>	EAN	192661052624	Number of mounting bores	4	Outer diameter [mm]	147	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	51
EAN	192661052624													
Number of mounting bores	4													
Outer diameter [mm]	147													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	51													
<p>KH30081</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052631</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>93</td> </tr> </table> <p><b>OE No.</b> FORD 1769848, 1776845, AG9C-2B664-FAA, AG9J-2B664-FAE</p>	EAN	192661052631	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	93
EAN	192661052631													
Number of mounting bores	4													
Outer diameter [mm]	136													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	93													
<p>KH30082</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049730</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>69</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-0D050, 42450-52060, 42450-74020</p>	EAN	192661049730	Number of mounting bores	4	Outer diameter [mm]	135	Rim Hole Number	4	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	69
EAN	192661049730													
Number of mounting bores	4													
Outer diameter [mm]	135													
Rim Hole Number	4													
Supplementary Article/Info 2	with integrated ABS sensor													
Width [mm]	69													
<p>KH30084</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049747</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> </table> <p><b>OE No.</b> OPEL 16 03 841, 93188477 VAUXHALL 16 03 841, 93188477</p>	EAN	192661049747	Number of mounting bores	3	Outer diameter [mm]	137	Supplementary Article/Info 2	with integrated ABS sensor				
EAN	192661049747													
Number of mounting bores	3													
Outer diameter [mm]	137													
Supplementary Article/Info 2	with integrated ABS sensor													






Part Number	Pk.	Description																				
KH30085 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052648</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>159</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>78</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LAND ROVER</td> <td>LR014147, RFM500010</td> </tr> </table>	EAN	192661052648	Number of mounting bores	4	Outer diameter [mm]	159	Rim Hole Number	5	Width [mm]	78	<b>OE No.</b>		LAND ROVER	LR014147, RFM500010						
EAN	192661052648																					
Number of mounting bores	4																					
Outer diameter [mm]	159																					
Rim Hole Number	5																					
Width [mm]	78																					
<b>OE No.</b>																						
LAND ROVER	LR014147, RFM500010																					
KH30086 	1	<table border="1"> <tr> <td>EAN</td> <td>192661049754</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HYUNDAI</td> <td>51750-3J000</td> </tr> <tr> <td>KIA</td> <td>51750-3J000</td> </tr> </table>	EAN	192661049754	Number of mounting bores	4	Outer diameter [mm]	137	Rim Hole Number	5	Width [mm]	67	<b>OE No.</b>		HYUNDAI	51750-3J000	KIA	51750-3J000				
EAN	192661049754																					
Number of mounting bores	4																					
Outer diameter [mm]	137																					
Rim Hole Number	5																					
Width [mm]	67																					
<b>OE No.</b>																						
HYUNDAI	51750-3J000																					
KIA	51750-3J000																					
KH30087 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049761</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>151</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>82</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>25903295, 96626439</td> </tr> <tr> <td>OPEL</td> <td>25903295, 48 04 658, 48 14 139, 96626439</td> </tr> <tr> <td>VAUXHALL</td> <td>25903295, 48 04 658, 48 14 139, 96626439</td> </tr> </table>	EAN	192661049761	Number of mounting bores	4	Outer diameter [mm]	151	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	82	<b>OE No.</b>		CHEVROLET	25903295, 96626439	OPEL	25903295, 48 04 658, 48 14 139, 96626439	VAUXHALL	25903295, 48 04 658, 48 14 139, 96626439
EAN	192661049761																					
Number of mounting bores	4																					
Outer diameter [mm]	151																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with integrated ABS sensor																					
Width [mm]	82																					
<b>OE No.</b>																						
CHEVROLET	25903295, 96626439																					
OPEL	25903295, 48 04 658, 48 14 139, 96626439																					
VAUXHALL	25903295, 48 04 658, 48 14 139, 96626439																					
KH30088 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052655</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>87</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>HONDA</td> <td>42200-STK-951</td> </tr> </table>	EAN	192661052655	Number of mounting bores	4	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	87	<b>OE No.</b>		HONDA	42200-STK-951				
EAN	192661052655																					
Number of mounting bores	4																					
Outer diameter [mm]	152																					
Rim Hole Number	5																					
Supplementary Article/Info 2	with integrated magnetic sensor ring																					
Width [mm]	87																					
<b>OE No.</b>																						
HONDA	42200-STK-951																					








Part Number	Pk.	Description																		
<p>KH30089</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049778</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>146</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>87</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHEVROLET</td> <td>13502829, 13583479, 13590795</td> </tr> <tr> <td>OPEL</td> <td>13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038</td> </tr> <tr> <td>VAUXHALL</td> <td>13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038</td> </tr> </table>	EAN	192661049778	Number of mounting bores	3	Outer diameter [mm]	146	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	87	CHEVROLET	13502829, 13583479, 13590795	OPEL	13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038	VAUXHALL	13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038
EAN	192661049778																			
Number of mounting bores	3																			
Outer diameter [mm]	146																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	87																			
CHEVROLET	13502829, 13583479, 13590795																			
OPEL	13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038																			
VAUXHALL	13502829, 13583479, 13590795, 3 28 001, 3 28 021, 3 28 038																			
<p>KH30090</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049785</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>27</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>78.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUZUKI</td> <td>43401-65J01, 43401-65J02, 43402-57L50, 43402-57L51</td> </tr> </table>	EAN	192661049785	Inner diameter [mm]	27	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	78.5	SUZUKI	43401-65J01, 43401-65J02, 43402-57L50, 43402-57L51		
EAN	192661049785																			
Inner diameter [mm]	27																			
Number of mounting bores	4																			
Outer diameter [mm]	140																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	78.5																			
SUZUKI	43401-65J01, 43401-65J02, 43402-57L50, 43402-57L51																			
<p>KH30091</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661049792</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>102</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1538604, 8V41-1A049-AA</td> </tr> </table>	EAN	192661049792	Outer diameter [mm]	136	Rim Hole Number	5	Width [mm]	102	FORD	1538604, 8V41-1A049-AA								
EAN	192661049792																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Width [mm]	102																			
FORD	1538604, 8V41-1A049-AA																			
<p>KH30092</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661049808</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>124</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUBARU</td> <td>28373-AG000, 28373-AG001, 28373-FG000</td> </tr> </table>	EAN	192661049808	Number of mounting bores	4	Outer diameter [mm]	124	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	61	SUBARU	28373-AG000, 28373-AG001, 28373-FG000				
EAN	192661049808																			
Number of mounting bores	4																			
Outer diameter [mm]	124																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	61																			
SUBARU	28373-AG000, 28373-AG001, 28373-FG000																			

Part Number	Pk.	Description												
<p>KH30093</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661049815</td> </tr> <tr> <td>Number of mounting bores</td> <td>3</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>153</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> </table> <p><b>OE No.</b>            JEEP 52128693AA, 52128693AB, 52128693AE, 52128693AF</p>	EAN	192661049815	Number of mounting bores	3	Outer diameter [mm]	153	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	84
EAN	192661049815													
Number of mounting bores	3													
Outer diameter [mm]	153													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated ABS sensor													
Width [mm]	84													
<p>KH30094</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661049822</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>175</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95</td> </tr> </table> <p><b>OE No.</b>            MERCEDES-BENZ A 906 350 01 49            VW A 906 350 01 49</p>	EAN	192661049822	Number of mounting bores	4	Outer diameter [mm]	175	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95		
EAN	192661049822													
Number of mounting bores	4													
Outer diameter [mm]	175													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	95													
<p>KH30095</p> 	1	<p><b>Safety information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661052662</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>131</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>128</td> </tr> </table> <p><b>OE No.</b>            AUDI 8E0 501 611, 8E0 501 611 J            SKODA 8E0 501 611, 8E0 501 611 J            VW 8E0 501 611, 8E0 501 611 J</p>	EAN	192661052662	Outer diameter [mm]	131	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	128		
EAN	192661052662													
Outer diameter [mm]	131													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	128													
<p>KH30096</p> 	1	<p><b>Technical Information</b>            This bearing has an integrated magnetic encoder!  <b>IMPORTANT! Keep away from strong magnetic sources!</b></p> <table border="1"> <tr> <td>EAN</td> <td>192661052679</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>44.5</td> </tr> </table> <p><b>OE No.</b>            JAGUAR C2C19585, XR825194</p>	EAN	192661052679	Outer diameter [mm]	139	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	44.5		
EAN	192661052679													
Outer diameter [mm]	139													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated ABS sensor													
Width [mm]	44.5													












Part Number	Pk.	Description														
<p>KH30097</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066935</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>54.5</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-0D010, 42450-52020, 42450-52021</p>	EAN	192661066935	Outer diameter [mm]	135	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	54.5						
EAN	192661066935															
Outer diameter [mm]	135															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	54.5															
<p>KH30098</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066942</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>137</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b> SAAB 5392493</p>	EAN	192661066942	Outer diameter [mm]	137	Rim Hole Number	5	Width [mm]	39						
EAN	192661066942															
Outer diameter [mm]	137															
Rim Hole Number	5															
Width [mm]	39															
<p>KH30099</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052686</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> </table> <p><b>OE No.</b> VOLVO 31658085</p>	EAN	192661052686	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	59		
EAN	192661052686															
Number of mounting bores	4															
Outer diameter [mm]	136															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	59															
<p>KH30100</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052693</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>39</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO 50707556, 71753816</p>	EAN	192661052693	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	39				
EAN	192661052693															
Outer diameter [mm]	135															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	39															
<p>KH30101</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052709</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>30</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>143</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95</td> </tr> </table> <p><b>OE No.</b> RENAULT 40 21 000 06R, 40 21 046 30R, 40 21 046 87R, 40 21 050 19R, 40 21 056 62R</p>	EAN	192661052709	Inner diameter [mm]	30	Number of mounting bores	4	Outer diameter [mm]	143	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95
EAN	192661052709															
Inner diameter [mm]	30															
Number of mounting bores	4															
Outer diameter [mm]	143															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	95															

Part Number	Pk.	Description												
<p>KH30102</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066959</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>144</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>64</td> </tr> </table> <p><b>OE No.</b> BMW 31 20 6 773 207, 31 20 6 779 735, 31 22 6 867 808</p>	EAN	192661066959	Outer diameter [mm]	144	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	64		
EAN	192661066959													
Outer diameter [mm]	144													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	64													
<p>KH30103</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661066966</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>161</td> </tr> </table> <p><b>OE No.</b> KIA 51750-4D000</p>	EAN	192661066966	Outer diameter [mm]	161								
EAN	192661066966													
Outer diameter [mm]	161													
<p>KH30104</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052716</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>60</td> </tr> </table> <p><b>OE No.</b> VOLVO 30748989, 31340119, 31340120</p>	EAN	192661052716	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	60		
EAN	192661052716													
Outer diameter [mm]	136													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	60													
<p>KH30105</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661066973</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>157</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> </table> <p><b>OE No.</b> CHEVROLET 13502785, 13507374, 13580135 OPEL 13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292 VAUXHALL 13502785, 13507374, 13580135, 3 28 006, 3 28 042, 3 28 292</p>	EAN	192661066973	Outer diameter [mm]	157	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67		
EAN	192661066973													
Outer diameter [mm]	157													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	67													
<p>KH30106</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052723</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>28</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>82</td> </tr> </table> <p><b>OE No.</b> VOLVO 272456</p>	EAN	192661052723	Inner diameter [mm]	28	Number of mounting bores	4	Outer diameter [mm]	135	Rim Hole Number	5	Width [mm]	82
EAN	192661052723													
Inner diameter [mm]	28													
Number of mounting bores	4													
Outer diameter [mm]	135													
Rim Hole Number	5													
Width [mm]	82													















Part Number	Pk.	Description																		
<p>KH30107</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052730</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>101</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>JAGUAR</td> <td>C2S3301, C2S46772</td> </tr> </table>	EAN	192661052730	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Width [mm]	101	<b>OE No.</b>		JAGUAR	C2S3301, C2S46772				
EAN	192661052730																			
Number of mounting bores	4																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Width [mm]	101																			
<b>OE No.</b>																				
JAGUAR	C2S3301, C2S46772																			
<p>KH30108</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052747</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>FIAT</td> <td>71747068, 71768167</td> </tr> <tr> <td>SUZUKI</td> <td>43402-79J00, 43402-79J01, 43402-79J02</td> </tr> </table>	EAN	192661052747	Number of mounting bores	4	Outer diameter [mm]	140	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	84	<b>OE No.</b>		FIAT	71747068, 71768167	SUZUKI	43402-79J00, 43402-79J01, 43402-79J02		
EAN	192661052747																			
Number of mounting bores	4																			
Outer diameter [mm]	140																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	84																			
<b>OE No.</b>																				
FIAT	71747068, 71768167																			
SUZUKI	43402-79J00, 43402-79J01, 43402-79J02																			
<p>KH30109</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661052754</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>90</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>VOLVO</td> <td>30794650, 31406300</td> </tr> </table>	EAN	192661052754	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Width [mm]	90	<b>OE No.</b>		VOLVO	30794650, 31406300				
EAN	192661052754																			
Number of mounting bores	4																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Width [mm]	90																			
<b>OE No.</b>																				
VOLVO	30794650, 31406300																			
<p>KH30110</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052761</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>145</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>57</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>BMW</td> <td>31 20 6 867 087, 31 20 6 872 888, 6 867 087, 6 872 888</td> </tr> </table>	EAN	192661052761	Number of mounting bores	4	Outer diameter [mm]	145	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	57	<b>OE No.</b>		BMW	31 20 6 867 087, 31 20 6 872 888, 6 867 087, 6 872 888		
EAN	192661052761																			
Number of mounting bores	4																			
Outer diameter [mm]	145																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	57																			
<b>OE No.</b>																				
BMW	31 20 6 867 087, 31 20 6 872 888, 6 867 087, 6 872 888																			
<p>KH30111</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661052778</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>130</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>96.4</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CITROËN</td> <td>96 713 260 80, 98 037 361 80</td> </tr> <tr> <td>PEUGEOT</td> <td>96 713 260 80, 98 037 361 80</td> </tr> </table>	EAN	192661052778	Number of mounting bores	4	Outer diameter [mm]	130	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	96.4	<b>OE No.</b>		CITROËN	96 713 260 80, 98 037 361 80	PEUGEOT	96 713 260 80, 98 037 361 80
EAN	192661052778																			
Number of mounting bores	4																			
Outer diameter [mm]	130																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	96.4																			
<b>OE No.</b>																				
CITROËN	96 713 260 80, 98 037 361 80																			
PEUGEOT	96 713 260 80, 98 037 361 80																			






Part Number	Pk.	Description																		
KH30112	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p>  <table border="1"> <tr> <td>EAN</td> <td>192661052785</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>130</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>96.4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CITROËN</td> <td>96 743 752 80, 98 037 361 80</td> </tr> <tr> <td>PEUGEOT</td> <td>96 743 752 80, 98 037 361 80</td> </tr> </table>	EAN	192661052785	Number of mounting bores	4	Outer diameter [mm]	130	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	96.4	CITROËN	96 743 752 80, 98 037 361 80	PEUGEOT	96 743 752 80, 98 037 361 80		
EAN	192661052785																			
Number of mounting bores	4																			
Outer diameter [mm]	130																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	96.4																			
CITROËN	96 743 752 80, 98 037 361 80																			
PEUGEOT	96 743 752 80, 98 037 361 80																			
KH30113	1	 <table border="1"> <tr> <td>EAN</td> <td>192661066980</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>20</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>117</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>69</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>ALFA ROMEO</td> <td>4400918, 5890994, 5963034, 71747857</td> </tr> <tr> <td>FIAT</td> <td>4400918, 5890994, 5963034, 71747857</td> </tr> <tr> <td>LANCIA</td> <td>4400918, 5890994, 5963034, 71747857</td> </tr> </table>	EAN	192661066980	Inner diameter [mm]	20	Outer diameter [mm]	117	Rim Hole Number	4	Width [mm]	69	ALFA ROMEO	4400918, 5890994, 5963034, 71747857	FIAT	4400918, 5890994, 5963034, 71747857	LANCIA	4400918, 5890994, 5963034, 71747857		
EAN	192661066980																			
Inner diameter [mm]	20																			
Outer diameter [mm]	117																			
Rim Hole Number	4																			
Width [mm]	69																			
ALFA ROMEO	4400918, 5890994, 5963034, 71747857																			
FIAT	4400918, 5890994, 5963034, 71747857																			
LANCIA	4400918, 5890994, 5963034, 71747857																			
KH30114	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p>  <table border="1"> <tr> <td>EAN</td> <td>192661066997</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>155</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>16 04 002, 16 04 301, 90510543, 9119931</td> </tr> <tr> <td>SAAB</td> <td>43 98 046, 47 78 494, 48 39 122</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 002, 16 04 301, 90510543, 9119931</td> </tr> </table>	EAN	192661066997	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	155	OPEL	16 04 002, 16 04 301, 90510543, 9119931	SAAB	43 98 046, 47 78 494, 48 39 122	VAUXHALL	16 04 002, 16 04 301, 90510543, 9119931
EAN	192661066997																			
Number of mounting bores	4																			
Outer diameter [mm]	140																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated ABS sensor																			
Width [mm]	155																			
OPEL	16 04 002, 16 04 301, 90510543, 9119931																			
SAAB	43 98 046, 47 78 494, 48 39 122																			
VAUXHALL	16 04 002, 16 04 301, 90510543, 9119931																			
KH30115	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p>  <table border="1"> <tr> <td>EAN</td> <td>192661067000</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>VOLVO</td> <td>31329980, 9173991</td> </tr> </table>	EAN	192661067000	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	43	VOLVO	31329980, 9173991				
EAN	192661067000																			
Number of mounting bores	4																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	43																			
VOLVO	31329980, 9173991																			



Part Number	Pk.	Description																		
<p>KH30116</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661067017</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>164</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>54</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>JEEP</td> <td>52098679AD</td> </tr> </table>	EAN	192661067017	Outer diameter [mm]	164	Rim Hole Number	5	Width [mm]	54	<b>OE No.</b>		JEEP	52098679AD						
EAN	192661067017																			
Outer diameter [mm]	164																			
Rim Hole Number	5																			
Width [mm]	54																			
<b>OE No.</b>																				
JEEP	52098679AD																			
<p>KH30117</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067024</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>55</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>42450-05040, 42450-47030, 42450-63011</td> </tr> </table>	EAN	192661067024	Outer diameter [mm]	135	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	55	<b>OE No.</b>		TOYOTA	42450-05040, 42450-47030, 42450-63011						
EAN	192661067024																			
Outer diameter [mm]	135																			
Supplementary Article/Info 2	with integrated ABS sensor																			
Width [mm]	55																			
<b>OE No.</b>																				
TOYOTA	42450-05040, 42450-47030, 42450-63011																			
<p>KH30118</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661067031</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>85</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>LEXUS</td> <td>42410-0E050</td> </tr> <tr> <td>TOYOTA</td> <td>42410-0E050</td> </tr> </table>	EAN	192661067031	Outer diameter [mm]	152	Rim Hole Number	5	Width [mm]	85	<b>OE No.</b>		LEXUS	42410-0E050	TOYOTA	42410-0E050				
EAN	192661067031																			
Outer diameter [mm]	152																			
Rim Hole Number	5																			
Width [mm]	85																			
<b>OE No.</b>																				
LEXUS	42410-0E050																			
TOYOTA	42410-0E050																			
<p>KH30119</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067048</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>83</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>13502828, 13583478, 3 028 016, 3 28 000</td> </tr> <tr> <td>OPEL</td> <td>13502828, 13583478, 3 28 000, 3 28 016</td> </tr> <tr> <td>VAUXHALL</td> <td>13502828, 13583478, 3 28 000, 3 28 016</td> </tr> </table>	EAN	192661067048	Outer diameter [mm]	136	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	83	<b>OE No.</b>		CHEVROLET	13502828, 13583478, 3 028 016, 3 28 000	OPEL	13502828, 13583478, 3 28 000, 3 28 016	VAUXHALL	13502828, 13583478, 3 28 000, 3 28 016
EAN	192661067048																			
Outer diameter [mm]	136																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	83																			
<b>OE No.</b>																				
CHEVROLET	13502828, 13583478, 3 028 016, 3 28 000																			
OPEL	13502828, 13583478, 3 28 000, 3 28 016																			
VAUXHALL	13502828, 13583478, 3 28 000, 3 28 016																			
<p>KH30120</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067055</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>122</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>82</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>MAZDA</td> <td>D651-25-15XD, D651-26-15XA, D651-26-15XB, D651-26-15XC, D651-26-15XE</td> </tr> </table>	EAN	192661067055	Outer diameter [mm]	122	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	82	<b>OE No.</b>		MAZDA	D651-25-15XD, D651-26-15XA, D651-26-15XB, D651-26-15XC, D651-26-15XE				
EAN	192661067055																			
Outer diameter [mm]	122																			
Rim Hole Number	4																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	82																			
<b>OE No.</b>																				
MAZDA	D651-25-15XD, D651-26-15XA, D651-26-15XB, D651-26-15XC, D651-26-15XE																			






Part Number	Pk.	Description														
<p>KH30121</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067062</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>61</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>LEXUS</td> <td>43550-47010, 43550-47011</td> </tr> <tr> <td>TOYOTA</td> <td>43550-47010, 43550-47011</td> </tr> </table>	EAN	192661067062	Outer diameter [mm]	125	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	61	LEXUS	43550-47010, 43550-47011	TOYOTA	43550-47010, 43550-47011
EAN	192661067062															
Outer diameter [mm]	125															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	61															
LEXUS	43550-47010, 43550-47011															
TOYOTA	43550-47010, 43550-47011															
<p>KH30122</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067079</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>79</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SAAB</td> <td>5058185</td> </tr> </table>	EAN	192661067079	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	79	SAAB	5058185		
EAN	192661067079															
Outer diameter [mm]	140															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	79															
SAAB	5058185															
<p>KH30123</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661067086</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Width [mm]</td> <td>89</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>VOLVO</td> <td>30639875</td> </tr> </table>	EAN	192661067086	Outer diameter [mm]	136	Width [mm]	89	VOLVO	30639875						
EAN	192661067086															
Outer diameter [mm]	136															
Width [mm]	89															
VOLVO	30639875															
<p>KH30124</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661067093</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>68</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>TOYOTA</td> <td>43510-47010, 43510-47011</td> </tr> </table>	EAN	192661067093	Outer diameter [mm]	125	Rim Hole Number	5	Width [mm]	68	TOYOTA	43510-47010, 43510-47011				
EAN	192661067093															
Outer diameter [mm]	125															
Rim Hole Number	5															
Width [mm]	68															
TOYOTA	43510-47010, 43510-47011															
<p>KH30125</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067109</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>131</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>AUDI</td> <td>4F0 598 611 A, 4F0 598 611 B</td> </tr> </table>	EAN	192661067109	Outer diameter [mm]	131	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95.5	AUDI	4F0 598 611 A, 4F0 598 611 B		
EAN	192661067109															
Outer diameter [mm]	131															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	95.5															
AUDI	4F0 598 611 A, 4F0 598 611 B															








Part Number	Pk.	Description																		
<p>KH30126</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661067116</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Width [mm]</td> <td>75</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>31262356, 31360027</td> </tr> </table>	EAN	192661067116	Outer diameter [mm]	136	Width [mm]	75	<b>OE No.</b>		VOLVO	31262356, 31360027								
EAN	192661067116																			
Outer diameter [mm]	136																			
Width [mm]	75																			
<b>OE No.</b>																				
VOLVO	31262356, 31360027																			
<p>KH30127</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661067123</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95.6</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CITROËN</td> <td>1606291880</td> </tr> <tr> <td>MITSUBISHI</td> <td>3785A009, MB101397</td> </tr> <tr> <td>PEUGEOT</td> <td>1606291880</td> </tr> </table>	EAN	192661067123	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95.6	<b>OE No.</b>		CITROËN	1606291880	MITSUBISHI	3785A009, MB101397	PEUGEOT	1606291880
EAN	192661067123																			
Outer diameter [mm]	140																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	95.6																			
<b>OE No.</b>																				
CITROËN	1606291880																			
MITSUBISHI	3785A009, MB101397																			
PEUGEOT	1606291880																			
<p>KH30128</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069165</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>29</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Width [mm]</td> <td>76</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>274378</td> </tr> </table>	EAN	192661069165	Inner diameter [mm]	29	Outer diameter [mm]	136	Width [mm]	76	<b>OE No.</b>		VOLVO	274378						
EAN	192661069165																			
Inner diameter [mm]	29																			
Outer diameter [mm]	136																			
Width [mm]	76																			
<b>OE No.</b>																				
VOLVO	274378																			
<p>KH30129</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069172</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>59</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>VOLVO</td> <td>9173872</td> </tr> </table>	EAN	192661069172	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Width [mm]	59	<b>OE No.</b>		VOLVO	9173872				
EAN	192661069172																			
Number of mounting bores	4																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Width [mm]	59																			
<b>OE No.</b>																				
VOLVO	9173872																			
<p>KH30130</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661069189</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>110</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>OPEL</td> <td>16 04 005, 9120273</td> </tr> <tr> <td>VAUXHALL</td> <td>16 04 005, 9120273</td> </tr> </table>	EAN	192661069189	Number of mounting bores	4	Outer diameter [mm]	140	Rim Hole Number	5	Width [mm]	110	<b>OE No.</b>		OPEL	16 04 005, 9120273	VAUXHALL	16 04 005, 9120273		
EAN	192661069189																			
Number of mounting bores	4																			
Outer diameter [mm]	140																			
Rim Hole Number	5																			
Width [mm]	110																			
<b>OE No.</b>																				
OPEL	16 04 005, 9120273																			
VAUXHALL	16 04 005, 9120273																			

Part Number	Pk.	Description																		
KH30131	1	<table border="1"> <tr> <td>EAN</td> <td>192661069196</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>26</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Width [mm]</td> <td>95</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>NISSAN</td> <td>40 20 275 85 R, 43 20 2JY 30A, 43202-EN100, 43202-EN11A, 43202-JG200, 43202-JG21B</td> </tr> </table>	EAN	192661069196	Inner diameter [mm]	26	Outer diameter [mm]	148	Width [mm]	95	<b>OE No.</b>		NISSAN	40 20 275 85 R, 43 20 2JY 30A, 43202-EN100, 43202-EN11A, 43202-JG200, 43202-JG21B						
EAN	192661069196																			
Inner diameter [mm]	26																			
Outer diameter [mm]	148																			
Width [mm]	95																			
<b>OE No.</b>																				
NISSAN	40 20 275 85 R, 43 20 2JY 30A, 43202-EN100, 43202-EN11A, 43202-JG200, 43202-JG21B																			
KH30133	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069202</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>78.26</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>13502872</td> </tr> <tr> <td>OPEL</td> <td>13502872, 3 28 002</td> </tr> <tr> <td>VAUXHALL</td> <td>13502872, 3 28 002</td> </tr> </table>	EAN	192661069202	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	78.26	<b>OE No.</b>		CHEVROLET	13502872	OPEL	13502872, 3 28 002	VAUXHALL	13502872, 3 28 002
EAN	192661069202																			
Outer diameter [mm]	136																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	78.26																			
<b>OE No.</b>																				
CHEVROLET	13502872																			
OPEL	13502872, 3 28 002																			
VAUXHALL	13502872, 3 28 002																			
KH30134	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069219</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>146</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>78.26</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>CHEVROLET</td> <td>13502873, 13591999</td> </tr> <tr> <td>OPEL</td> <td>13502873, 13591999, 3 28 003, 3 28 037</td> </tr> <tr> <td>VAUXHALL</td> <td>13502873, 13591999, 3 28 003, 3 28 0037</td> </tr> </table>	EAN	192661069219	Outer diameter [mm]	146	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	78.26	<b>OE No.</b>		CHEVROLET	13502873, 13591999	OPEL	13502873, 13591999, 3 28 003, 3 28 037	VAUXHALL	13502873, 13591999, 3 28 003, 3 28 0037
EAN	192661069219																			
Outer diameter [mm]	146																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	78.26																			
<b>OE No.</b>																				
CHEVROLET	13502873, 13591999																			
OPEL	13502873, 13591999, 3 28 003, 3 28 037																			
VAUXHALL	13502873, 13591999, 3 28 003, 3 28 0037																			
KH30135	1	<table border="1"> <tr> <td>EAN</td> <td>192661069226</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>152</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>85</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>TOYOTA</td> <td>42410-42020</td> </tr> </table>	EAN	192661069226	Outer diameter [mm]	152	Rim Hole Number	5	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	85	<b>OE No.</b>		TOYOTA	42410-42020				
EAN	192661069226																			
Outer diameter [mm]	152																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with ABS sensor ring																			
Width [mm]	85																			
<b>OE No.</b>																				
TOYOTA	42410-42020																			
KH30136	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069233</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>124</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>104.3</td> </tr> <tr> <td colspan="2"><b>OE No.</b></td> </tr> <tr> <td>SUBARU</td> <td>28473-FG000, 28473-SC000</td> </tr> </table>	EAN	192661069233	Outer diameter [mm]	124	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	104.3	<b>OE No.</b>		SUBARU	28473-FG000, 28473-SC000				
EAN	192661069233																			
Outer diameter [mm]	124																			
Rim Hole Number	5																			
Supplementary Article/Info 2	with integrated magnetic sensor ring																			
Width [mm]	104.3																			
<b>OE No.</b>																				
SUBARU	28473-FG000, 28473-SC000																			








Part Number	Pk.	Description
<p>KH30137</p> 	1	<p>EAN   192661069240</p> <p>Outer diameter [mm]   147.8</p> <p>Width [mm]   75</p> <p><b>OE No.</b></p> <p>NISSAN   43202-4X00A, 43202-ZP80A</p>
<p>KH30138</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661069257</p> <p>Outer diameter [mm]   140</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   93.4</p> <p><b>OE No.</b></p> <p>LEXUS   435500-30010</p> <p>TOYOTA   435500-30010</p>
<p>KH30139</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661069264</p> <p>Outer diameter [mm]   136</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   63</p> <p><b>OE No.</b></p> <p>VOLVO   31262040, 31277808, 31329968</p>
<p>KH30140</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661069271</p> <p>Outer diameter [mm]   175</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   94.5</p> <p><b>OE No.</b></p> <p>MERCEDES-BENZ   A 903 350 02 49</p>
<p>KH30141</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661069288</p> <p>Outer diameter [mm]   152</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   64</p> <p><b>OE No.</b></p> <p>TOYOTA   42450-0F020, 42450-0F021</p>

Part Number	Pk.	Description										
<p>KH30142</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069295</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>164.75</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>74.95</td> </tr> </table> <p><b>OE No.</b> JEEP 52089434AB, 52089434AC</p>	EAN	192661069295	Outer diameter [mm]	164.75	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	74.95		
EAN	192661069295											
Outer diameter [mm]	164.75											
Supplementary Article/Info 2	with integrated ABS sensor											
Width [mm]	74.95											
<p>KH30143</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069301</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>96.05</td> </tr> </table> <p><b>OE No.</b> FORD 1702973, 1703150, 1706172, 1706173, 1760855, 1785690, 1814090, 1815483, 1851452, BV61-2C299-AAB, BV61-2C299-AAC, BV61-2C299-AAD, BV61-2C299-AAE, BV61-2C299-AAF, BV61-2C299-BAA, BV61-2C299-BAB, BV61-2C299-BAC</p>	EAN	192661069301	Outer diameter [mm]	136	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	96.05		
EAN	192661069301											
Outer diameter [mm]	136											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	96.05											
<p>KH30144</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661069318</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95</td> </tr> </table> <p><b>OE No.</b> MERCEDES-BENZ A 169 981 00 27</p>	EAN	192661069318	Outer diameter [mm]	148	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95		
EAN	192661069318											
Outer diameter [mm]	148											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	95											
<p>KH30145</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071953</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>120</td> </tr> </table> <p><b>OE No.</b> NISSAN 43202-1YPDA, 43202-EE500</p>	EAN	192661071953	Outer diameter [mm]	148	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	120
EAN	192661071953											
Outer diameter [mm]	148											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	120											
<p>KH30146</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661071960</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>95.5</td> </tr> </table> <p><b>OE No.</b> NISSAN 43202-CA000</p>	EAN	192661071960	Outer diameter [mm]	148	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	95.5
EAN	192661071960											
Outer diameter [mm]	148											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	95.5											










Part Number	Pk.	Description
<p>KH30147</p>	1	<p>EAN   192661071977</p> <p>Number of Teeth, ABS ring   47</p> <p>Outer diameter [mm]   148</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   94.2</p> <p><b>OE No.</b></p> <p>HYUNDAI   52730-3S200</p> <p>KIA   52730-3S200</p>
<p>KH30148</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661071984</p> <p>Outer diameter [mm]   135</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   69</p> <p><b>OE No.</b></p> <p>TOYOTA   42450-74010</p>
<p>KH30149</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661071991</p> <p>Outer diameter [mm]   136</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   70</p> <p><b>OE No.</b></p> <p>NISSAN   40202-AL510, 40202-AL56C</p>
<p>KH30150</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661072004</p> <p>Outer diameter [mm]   152</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   70</p> <p><b>OE No.</b></p> <p>TOYOTA   42450-05080, 42450-05081, 42450-12110</p>
<p>KH30151</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661072011</p> <p>Outer diameter [mm]   154</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   88</p> <p><b>OE No.</b></p> <p>LEXUS   42410-30020, 42410-30021</p> <p>TOYOTA   42410-30020, 42410-30021</p>






Part Number	Pk.	Description														
<p>KH30152</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661072028</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>154.3</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>69.7</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>DODGE</td> <td>52109947AF</td> </tr> <tr> <td>JEEP</td> <td>52109947AF</td> </tr> </table>	EAN	192661072028	Outer diameter [mm]	154.3	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	69.7	DODGE	52109947AF	JEEP	52109947AF
EAN	192661072028															
Outer diameter [mm]	154.3															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	69.7															
DODGE	52109947AF															
JEEP	52109947AF															
<p>KH30153</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661072035</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>142</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>102.65</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MAZDA</td> <td>BB2M-26-15XA, BB2M-26-15XB, BP4K-26-15XA, BP4K-26-15XB, BP4K-26-15XC</td> </tr> </table>	EAN	192661072035	Outer diameter [mm]	142	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	102.65	MAZDA	BB2M-26-15XA, BB2M-26-15XB, BP4K-26-15XA, BP4K-26-15XB, BP4K-26-15XC				
EAN	192661072035															
Outer diameter [mm]	142															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	102.65															
MAZDA	BB2M-26-15XA, BB2M-26-15XB, BP4K-26-15XA, BP4K-26-15XB, BP4K-26-15XC															
<p>KH30154</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661072042</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>138</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>90.4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUBARU</td> <td>28473-FG010, 28473-Va000, 28473-ZR000</td> </tr> </table>	EAN	192661072042	Outer diameter [mm]	138	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	90.4	SUBARU	28473-FG010, 28473-Va000, 28473-ZR000		
EAN	192661072042															
Outer diameter [mm]	138															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	90.4															
SUBARU	28473-FG010, 28473-Va000, 28473-ZR000															
<p>KH30155</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661072059</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>150</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>73.4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHRYSLER</td> <td>04779218AB</td> </tr> </table>	EAN	192661072059	Outer diameter [mm]	150	Rim Hole Number	5	Width [mm]	73.4	CHRYSLER	04779218AB				
EAN	192661072059															
Outer diameter [mm]	150															
Rim Hole Number	5															
Width [mm]	73.4															
CHRYSLER	04779218AB															
<p>KH30158</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073766</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>90</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHRYSLER</td> <td>4641196, BCA513074</td> </tr> </table>	EAN	192661073766	Outer diameter [mm]	139	Rim Hole Number	5	Width [mm]	90	CHRYSLER	4641196, BCA513074				
EAN	192661073766															
Outer diameter [mm]	139															
Rim Hole Number	5															
Width [mm]	90															
CHRYSLER	4641196, BCA513074															








Part Number	Pk.	Description
<p>KH30159</p>	1	<p>EAN   192661073773</p> <p>Inner diameter [mm]   31</p> <p>Outer diameter [mm]   153</p> <p>Rim Hole Number   5</p> <p>Width [mm]   88</p> <p><b>OE No.</b></p> <p>JEEP   53007449</p>
<p>KH30160</p>	1	<p>EAN   192661073780</p> <p>Inner diameter [mm]   26</p> <p>Outer diameter [mm]   133</p> <p>Width [mm]   73</p> <p><b>OE No.</b></p> <p>SMART   0002072V01000000</p>
<p>KH30161</p>	1	<p>EAN   192661073797</p> <p>Number of Teeth, ABS ring   47</p> <p>Outer diameter [mm]   148</p> <p>Supplementary Article/Info 2   with ABS sensor ring</p> <p>Width [mm]   100.5</p> <p><b>OE No.</b></p> <p>HYUNDAI   52730-3K200</p> <p>KIA   52730-3K200</p>
<p>KH30162</p>	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661073803</p> <p>Outer diameter [mm]   139</p> <p>Rim Hole Number   5</p> <p>Supplementary Article/Info 2   with integrated ABS sensor</p> <p>Width [mm]   113</p> <p><b>OE No.</b></p> <p>HYUNDAI   52750-2K000</p> <p>KIA   52750-2K000</p>
<p>KH30163</p>	1	<p><b>Safety information</b></p> <p>This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN   192661073810</p> <p>Inner diameter [mm]   27</p> <p>Outer diameter [mm]   140</p> <p>Supplementary Article/Info 2   with integrated magnetic sensor ring</p> <p>Width [mm]   83.2</p> <p><b>OE No.</b></p> <p>CITROËN   3730 36</p> <p>MINIBUS   3785A015, 3785A019</p> <p>PEUGEOT   3730 36</p>

Part Number	Pk.	Description														
<p>KH30164</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073827</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>80.6</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHRYSLER</td> <td>5105770AC, 5105770AD</td> </tr> <tr> <td>JEEP</td> <td>5105770AD, 5105770AE</td> </tr> </table>	EAN	192661073827	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	80.6	CHRYSLER	5105770AC, 5105770AD	JEEP	5105770AD, 5105770AE
EAN	192661073827															
Outer diameter [mm]	140															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	80.6															
CHRYSLER	5105770AC, 5105770AD															
JEEP	5105770AD, 5105770AE															
<p>KH30165</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073834</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>67.45</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40202-3LH0A, 40202-JX00A</td> </tr> </table>	EAN	192661073834	Outer diameter [mm]	136	Rim Hole Number	4	Width [mm]	67.45	NISSAN	40202-3LH0A, 40202-JX00A				
EAN	192661073834															
Outer diameter [mm]	136															
Rim Hole Number	4															
Width [mm]	67.45															
NISSAN	40202-3LH0A, 40202-JX00A															
<p>KH30166</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073841</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>79.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>NISSAN</td> <td>40202-4AE0A, 40202-4Ea1A</td> </tr> <tr> <td>RENAULT</td> <td>40 20 24E A0A</td> </tr> </table>	EAN	192661073841	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	79.5	NISSAN	40202-4AE0A, 40202-4Ea1A	RENAULT	40 20 24E A0A
EAN	192661073841															
Outer diameter [mm]	136															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	79.5															
NISSAN	40202-4AE0A, 40202-4Ea1A															
RENAULT	40 20 24E A0A															
<p>KH30167</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073858</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>66.4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHEVROLET</td> <td>96636585</td> </tr> <tr> <td>DAEWOO</td> <td>96636585</td> </tr> </table>	EAN	192661073858	Outer diameter [mm]	139	Rim Hole Number	4	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	66.4	CHEVROLET	96636585	DAEWOO	96636585
EAN	192661073858															
Outer diameter [mm]	139															
Rim Hole Number	4															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	66.4															
CHEVROLET	96636585															
DAEWOO	96636585															
<p>KH30168</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073865</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Width [mm]</td> <td>58</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HYUNDAI</td> <td>52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001</td> </tr> <tr> <td>KIA</td> <td>52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001</td> </tr> </table>	EAN	192661073865	Outer diameter [mm]	140	Rim Hole Number	4	Width [mm]	58	HYUNDAI	52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001	KIA	52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001		
EAN	192661073865															
Outer diameter [mm]	140															
Rim Hole Number	4															
Width [mm]	58															
HYUNDAI	52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001															
KIA	52750-1C000, 52750-1C002, 52750-1G000, 52750-1G001															








Part Number	Pk.	Description										
<p>KH30169</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073872</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-02060, 42450-12070</p>	EAN	192661073872	Number of mounting bores	4	Outer diameter [mm]	135	Rim Hole Number	4	Supplementary Article/Info 2	with integrated magnetic sensor ring
EAN	192661073872											
Number of mounting bores	4											
Outer diameter [mm]	135											
Rim Hole Number	4											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
<p>KH30170</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073889</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>38</td> </tr> </table> <p><b>OE No.</b> ALFA ROMEO 50702890, 50706067, 71753813</p>	EAN	192661073889	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	38
EAN	192661073889											
Outer diameter [mm]	135											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	38											
<p>KH30171</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073896</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>100.5</td> </tr> </table> <p><b>OE No.</b> HYUNDAI 52730-3K100 KIA 52730-3K100</p>	EAN	192661073896	Outer diameter [mm]	148	Rim Hole Number	5	Width [mm]	100.5		
EAN	192661073896											
Outer diameter [mm]	148											
Rim Hole Number	5											
Width [mm]	100.5											
<p>KH30172</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661073902</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>133</td> </tr> <tr> <td>Rim Hole Number</td> <td>3</td> </tr> <tr> <td>Width [mm]</td> <td>58.8</td> </tr> </table> <p><b>OE No.</b> SMART A 451 350 01 35, A 451 350 02 35</p>	EAN	192661073902	Outer diameter [mm]	133	Rim Hole Number	3	Width [mm]	58.8		
EAN	192661073902											
Outer diameter [mm]	133											
Rim Hole Number	3											
Width [mm]	58.8											
<p>KH30173</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661073919</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>96</td> </tr> </table> <p><b>OE No.</b> TOYOTA 42450-0F010</p>	EAN	192661073919	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	96
EAN	192661073919											
Outer diameter [mm]	140											
Rim Hole Number	5											
Supplementary Article/Info 2	with integrated ABS sensor											
Width [mm]	96											

Part Number	Pk.	Description																
<p>KH30174</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074459</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>125</td> </tr> <tr> <td>Width [mm]</td> <td>58.3</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>CHRYSLER</td> <td>4397498, 5141067</td> </tr> </table>	EAN	192661074459	Outer diameter [mm]	125	Width [mm]	58.3	<b>OE No.</b>		CHRYSLER	4397498, 5141067						
EAN	192661074459																	
Outer diameter [mm]	125																	
Width [mm]	58.3																	
<b>OE No.</b>																		
CHRYSLER	4397498, 5141067																	
<p>KH30175</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074466</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>145</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>155</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>BMW</td> <td>31 22 6 750 217, 6 750 217</td> </tr> </table>	EAN	192661074466	Outer diameter [mm]	145	Rim Hole Number	5	Width [mm]	155	<b>OE No.</b>		BMW	31 22 6 750 217, 6 750 217				
EAN	192661074466																	
Outer diameter [mm]	145																	
Rim Hole Number	5																	
Width [mm]	155																	
<b>OE No.</b>																		
BMW	31 22 6 750 217, 6 750 217																	
<p>KH30176</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074473</td> </tr> <tr> <td>Inner diameter [mm]</td> <td>73</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>100.5</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>HYUNDAI</td> <td>52730-2G200, 52730-3K000</td> </tr> <tr> <td>KIA</td> <td>52730-2G200, 52730-3K000</td> </tr> </table>	EAN	192661074473	Inner diameter [mm]	73	Outer diameter [mm]	148	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	100.5	<b>OE No.</b>		HYUNDAI	52730-2G200, 52730-3K000	KIA	52730-2G200, 52730-3K000
EAN	192661074473																	
Inner diameter [mm]	73																	
Outer diameter [mm]	148																	
Supplementary Article/Info 2	with ABS sensor ring																	
Width [mm]	100.5																	
<b>OE No.</b>																		
HYUNDAI	52730-2G200, 52730-3K000																	
KIA	52730-2G200, 52730-3K000																	
<p>KH30177</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074480</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>93</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>LEXUS</td> <td>43560-30010, 43560-30011</td> </tr> </table>	EAN	192661074480	Outer diameter [mm]	140	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	93	<b>OE No.</b>		LEXUS	43560-30010, 43560-30011		
EAN	192661074480																	
Outer diameter [mm]	140																	
Rim Hole Number	5																	
Supplementary Article/Info 2	with integrated magnetic sensor ring																	
Width [mm]	93																	
<b>OE No.</b>																		
LEXUS	43560-30010, 43560-30011																	
<p>KH30178</p> 	1	<table border="1"> <tr> <td>EAN</td> <td>192661074497</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Width [mm]</td> <td>106</td> </tr> <tr> <td><b>OE No.</b></td> <td></td> </tr> <tr> <td>NISSAN</td> <td>43202-JX00A</td> </tr> </table>	EAN	192661074497	Outer diameter [mm]	148	Width [mm]	106	<b>OE No.</b>		NISSAN	43202-JX00A						
EAN	192661074497																	
Outer diameter [mm]	148																	
Width [mm]	106																	
<b>OE No.</b>																		
NISSAN	43202-JX00A																	











Part Number	Pk.	Description												
<p>KH30179</p>	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074503</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>142.95</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>BMW</td> <td>31 22 2 282 670</td> </tr> </table>	EAN	192661074503	Outer diameter [mm]	142.95	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	84	BMW	31 22 2 282 670		
EAN	192661074503													
Outer diameter [mm]	142.95													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	84													
BMW	31 22 2 282 670													
<p>KH30181</p>	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074510</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>65</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>CHEVROLET</td> <td>95459540, 95951600</td> </tr> </table>	EAN	192661074510	Outer diameter [mm]	139	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	65	CHEVROLET	95459540, 95951600		
EAN	192661074510													
Outer diameter [mm]	139													
Supplementary Article/Info 2	with integrated ABS sensor													
Width [mm]	65													
CHEVROLET	95459540, 95951600													
<p>KH30182</p>	1	<table border="1"> <tr> <td>EAN</td> <td>192661074527</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Width [mm]</td> <td>77</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>MAZDA</td> <td>G331-26-15X, G33S-26-15XA, G33S-26-15XB, G33S-26-15XC</td> </tr> </table>	EAN	192661074527	Outer diameter [mm]	140	Rim Hole Number	5	Width [mm]	77	MAZDA	G331-26-15X, G33S-26-15XA, G33S-26-15XB, G33S-26-15XC		
EAN	192661074527													
Outer diameter [mm]	140													
Rim Hole Number	5													
Width [mm]	77													
MAZDA	G331-26-15X, G33S-26-15XA, G33S-26-15XB, G33S-26-15XC													
<p>KH30183</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074534</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>157</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>13502785, 13507374, 3 28 042, 3 28 292</td> </tr> <tr> <td>VAUXHALL</td> <td>13502785, 13507374, 3 28 042, 3 28 292</td> </tr> </table>	EAN	192661074534	Outer diameter [mm]	157	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	OPEL	13502785, 13507374, 3 28 042, 3 28 292	VAUXHALL	13502785, 13507374, 3 28 042, 3 28 292
EAN	192661074534													
Outer diameter [mm]	157													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
Width [mm]	67													
OPEL	13502785, 13507374, 3 28 042, 3 28 292													
VAUXHALL	13502785, 13507374, 3 28 042, 3 28 292													
<p>KH30184</p>	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661074541</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>51943307</td> </tr> <tr> <td>JEEP</td> <td>51943307</td> </tr> </table>	EAN	192661074541	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	FIAT	51943307	JEEP	51943307
EAN	192661074541													
Outer diameter [mm]	135													
Rim Hole Number	5													
Supplementary Article/Info 2	with integrated magnetic sensor ring													
FIAT	51943307													
JEEP	51943307													

Part Number	Pk.	Description
<p>KH30185</p> 	1	<p>EAN 192661077528</p> <p>Outer diameter [mm] 148</p> <p>Rim Hole Number 4</p> <p>Width [mm] 116</p> <p><b>OE No.</b></p> <p>HYUNDAI 52730-38000, 52730-38001, 52730-38002, 52730-38003</p>
<p>KH30186</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661077535</p> <p>Outer diameter [mm] 137</p> <p>Rim Hole Number 4</p> <p>Supplementary Article/Info 2 with integrated ABS sensor</p> <p>Width [mm] 60</p> <p><b>OE No.</b></p> <p>MITSUBISHI MR594142</p> <p>SMART A 454 350 01 35</p>
<p>KH30187</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661077542</p> <p>Outer diameter [mm] 139</p> <p>Rim Hole Number 4</p> <p>Supplementary Article/Info 2 with integrated ABS sensor</p> <p>Width [mm] 130.6</p> <p><b>OE No.</b></p> <p>CHEVROLET 96639607</p> <p>DAEWOO 96639607</p>
<p>KH30188</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661077559</p> <p>Number of mounting bores 4</p> <p>Outer diameter [mm] 152</p> <p>Rim Hole Number 5</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p><b>OE No.</b></p> <p>HONDA 42200-TOB-951</p>
<p>KH30189</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <p>EAN 192661077566</p> <p>Outer diameter [mm] 143</p> <p>Supplementary Article/Info 2 with integrated magnetic sensor ring</p> <p>Width [mm] 95.8</p> <p><b>OE No.</b></p> <p>MERCEDES-BENZ A 246 334 00 06</p>














Part Number	Pk.	Description														
<p>KH30190</p> 	1	<p><b>Technical Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661077573</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>135</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FIAT</td> <td>51952935</td> </tr> <tr> <td>JEEP</td> <td>51952935</td> </tr> </table>	EAN	192661077573	Outer diameter [mm]	135	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	FIAT	51952935	JEEP	51952935		
EAN	192661077573															
Outer diameter [mm]	135															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
FIAT	51952935															
JEEP	51952935															
<p>KH30191</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>149</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>FORD</td> <td>1118054, 98BG-2C299-DC</td> </tr> </table>	Outer diameter [mm]	136	Rim Hole Number	4	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	149	FORD	1118054, 98BG-2C299-DC				
Outer diameter [mm]	136															
Rim Hole Number	4															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	149															
FORD	1118054, 98BG-2C299-DC															
<p>KH30192</p> 	1	<table border="1"> <tr> <td>Number of Teeth, ABS ring</td> <td>48</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>148</td> </tr> <tr> <td>Rim Hole Number</td> <td>4</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with ABS sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>116</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HYUNDAI</td> <td>52730-38100, 52730-38102</td> </tr> <tr> <td>KIA</td> <td>52730-38100, 52730-38102</td> </tr> </table>	Number of Teeth, ABS ring	48	Outer diameter [mm]	148	Rim Hole Number	4	Supplementary Article/Info 2	with ABS sensor ring	Width [mm]	116	HYUNDAI	52730-38100, 52730-38102	KIA	52730-38100, 52730-38102
Number of Teeth, ABS ring	48															
Outer diameter [mm]	148															
Rim Hole Number	4															
Supplementary Article/Info 2	with ABS sensor ring															
Width [mm]	116															
HYUNDAI	52730-38100, 52730-38102															
KIA	52730-38100, 52730-38102															
<p>KH30193</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>EAN</td> <td>192661080979</td> </tr> <tr> <td>Number of mounting bores</td> <td>4</td> </tr> <tr> <td>Outer diameter [mm]</td> <td>136</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>43</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>VOLVO</td> <td>31329980</td> </tr> </table>	EAN	192661080979	Number of mounting bores	4	Outer diameter [mm]	136	Rim Hole Number	5	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	43	VOLVO	31329980
EAN	192661080979															
Number of mounting bores	4															
Outer diameter [mm]	136															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated magnetic sensor ring															
Width [mm]	43															
VOLVO	31329980															
<p>KH30194</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Outer diameter [mm]</td> <td>112</td> </tr> <tr> <td>Rim Hole Number</td> <td>5</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>84</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>TOYOTA</td> <td>42450-42030</td> </tr> </table>	Outer diameter [mm]	112	Rim Hole Number	5	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	84	TOYOTA	42450-42030				
Outer diameter [mm]	112															
Rim Hole Number	5															
Supplementary Article/Info 2	with integrated ABS sensor															
Width [mm]	84															
TOYOTA	42450-42030															

Part Number	Pk.	Description										
<p>KH30195</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Outer diameter [mm]</td> <td>139</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>110.4</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>HYUNDAI</td> <td>52750-2B100</td> </tr> <tr> <td>KIA</td> <td>52750-2B100</td> </tr> </table>	Outer diameter [mm]	139	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	110.4	HYUNDAI	52750-2B100	KIA	52750-2B100
Outer diameter [mm]	139											
Supplementary Article/Info 2	with integrated ABS sensor											
Width [mm]	110.4											
HYUNDAI	52750-2B100											
KIA	52750-2B100											
<p>KH30196</p> 	1	<p><b>General Information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Outer diameter [mm]</td> <td>157</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated magnetic sensor ring</td> </tr> <tr> <td>Width [mm]</td> <td>67</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>OPEL</td> <td>13502785, 13507374, 3 28 042, 3 28 292</td> </tr> <tr> <td>VAUXHALL</td> <td>13502785, 13507374, 3 28 042, 3 28 292</td> </tr> </table>	Outer diameter [mm]	157	Supplementary Article/Info 2	with integrated magnetic sensor ring	Width [mm]	67	OPEL	13502785, 13507374, 3 28 042, 3 28 292	VAUXHALL	13502785, 13507374, 3 28 042, 3 28 292
Outer diameter [mm]	157											
Supplementary Article/Info 2	with integrated magnetic sensor ring											
Width [mm]	67											
OPEL	13502785, 13507374, 3 28 042, 3 28 292											
VAUXHALL	13502785, 13507374, 3 28 042, 3 28 292											
<p>KH30197</p> 	1	<p><b>Safety information</b> This bearing has an integrated magnetic encoder! IMPORTANT! Keep away from strong magnetic sources!</p> <table border="1"> <tr> <td>Outer diameter [mm]</td> <td>140</td> </tr> <tr> <td>Supplementary Article/Info 2</td> <td>with integrated ABS sensor</td> </tr> <tr> <td>Width [mm]</td> <td>88.5</td> </tr> </table> <p><b>OE No.</b></p> <table border="1"> <tr> <td>SUZUKI</td> <td>43402-80J50, 43402-80J51, 43402-80J52</td> </tr> </table>	Outer diameter [mm]	140	Supplementary Article/Info 2	with integrated ABS sensor	Width [mm]	88.5	SUZUKI	43402-80J50, 43402-80J51, 43402-80J52		
Outer diameter [mm]	140											
Supplementary Article/Info 2	with integrated ABS sensor											
Width [mm]	88.5											
SUZUKI	43402-80J50, 43402-80J51, 43402-80J52											







ABARTH.....	180	MINI.....	386
ALFA ROMEO.....	181	MITSUBISHI.....	388
AUDI.....	189	NISSAN.....	395
AUSTIN.....	209	OPEL.....	403
AUTOBIANCHI.....	210	PEUGEOT.....	428
BMW.....	211	PORSCHE.....	450
BOND.....	231	PROTON.....	454
CADILLAC.....	232	RELIANT.....	455
CATERHAM.....	233	RENAULT.....	456
CHEVROLET.....	234	ROVER.....	482
CHRYSLER.....	236	SAAB.....	485
CITROËN.....	238	SANTANA.....	487
CUPRA.....	260	SEAT.....	488
DACIA.....	261	SKODA.....	497
DAEWOO.....	265	SMART.....	503
DAIHATSU.....	267	SSANGYONG.....	505
DAIMLER.....	269	SUBARU.....	506
DODGE.....	270	SUZUKI.....	509
DS.....	271	TALBOT.....	513
FIAT.....	272	TOYOTA.....	514
FORD.....	295	TOYOTA (FAW).....	526
FSO.....	318	TRIUMPH.....	527
HINDUSTAN.....	319	TVR.....	528
HONDA.....	320	VAUXHALL.....	529
HYUNDAI.....	324	VOLVO.....	547
INFINITI.....	331	VW.....	556
ISUZU.....	333	YUGO.....	584
IVECO.....	334	ZASTAVA.....	585
JAGUAR.....	336		
JEEP.....	338		
KIA.....	340		
LADA.....	344		
LANCIA.....	345		
LAND ROVER.....	350		
LDV.....	353		
LEXUS.....	354		
LOTUS.....	356		
MAZDA.....	357		
MERCEDES-BENZ.....	364		
MG.....	385		

    				
<b>ABARTH - 500 / 595 / 695</b>				<b>08/08</b> →
1.4 (312.AXD1A)	99 kW	1.4 l	08/08→	 <b>KH10065</b> ProKIT  <b>KH20022</b> ProKIT
1.4 (312.AXF11, 312.AXF1A, 312.AXD1A)	118 kW	1.4 l	08/08→	
1.4 (312.AXF11, 312.AXF1A)	132 kW	1.4 l	08/08→	
1.4 (312.AXF1A, 312.AXD1A)	103 kW	1.4 l	05/10→	
1.4 (312.AXT1A)	140 kW	1.4 l	08/08→	
<b>ABARTH - 500C / 595C / 695C</b>				<b>05/08</b> →
1.4 (312.AXD1A)	99 kW	1.4 l	05/08→	 <b>KH10065</b> ProKIT  <b>KH20022</b> ProKIT
1.4 (312.AXF11, 312.AXF1A)	132 kW	1.4 l	06/10→	
1.4 (312.AXF1A, 312.AXD1A)	118 kW	1.4 l	05/11→	
1.4 (312.AXF1A, 312.AXF11, 312.AXD1A)	103 kW	1.4 l	09/09→	



				13	i		
<b>ALFA ROMEO - 75 Sedan (162_)</b>						<b>05/85→09/92</b>	
1.6 (162.B2B, 162.B2C)	81 kW	1.6 l	05/85→09/89			KH00111 ProKIT	
1.8 (162.B1A, 162.B1B)	85 kW	1.8 l	09/85→06/89				
1.8 (162.B1H)	95 kW	1.8 l	08/89→02/92				
1.8 (162.B1L, 162.B1F)	88 kW	1.8 l	09/88→02/92				
1.8 Turbo (162.B1C, 162.B1D, 162.B1G)	110 kW	1.8 l	09/86→02/92				
1.8 Turbo i.e. (162.B1E)	114 kW	1.8 l	02/86→01/90				
2.4 TD (162.B5)	82 kW	2.4 l	01/89→02/92				
2.5 V6 (162.B3)	110 kW	2.5 l	05/85→08/86				
3.0 V6 (162.B6C)	141 kW	3 l	02/90→02/92				
1.6 Cat (162.B2B, 162.B2C)	81 kW	1.6 l	05/89→02/92	; 09/89 ->		KH00111 ProKIT	
1.8 (162.B1H)	90 kW	1.8 l	08/89→02/92				
2.0 (162.BA)	94 kW	2 l	05/85→10/88	; -> 07/87		KH00111 ProKIT	
2.0 T.S. (162.4CB, 162.B4, 162.B4A)	107 kW	2 l	01/87→02/92	;		KH00111 ProKIT	
2.0 T.S Cat (162.B4A)	109 kW	2 l	05/85→02/92	; 09/88 ->;		KH00111 ProKIT	
2.0 TD (162.BD, 162.BG)	70 kW	2 l	05/85→09/92	; 02/86 ->		KH00111 ProKIT	
3.0 V6 Cat (162.B6A)	136 kW	3 l	01/87→02/92	; 09/88 ->		KH00111 ProKIT	
<b>ALFA ROMEO - 90 (162_)</b>						<b>10/84→07/87</b>	
1.8 (162.A1A)	85 kW	1.8 l	10/84→07/87			KH00111 ProKIT	
2.0 i.e. (162.A2A, 162.A2E)	94 kW	2 l	10/84→07/87				
2.4 TD (162.B5)	81 kW	2.4 l	10/84→07/87				
2.5 i.e. V6 (162.A, 162.AA)	110 kW	2.5 l	10/84→07/87				
1.8 (162A1)	89 kW	1.8 l	10/84→07/87	; 06/86 ->		KH00111 ProKIT	
<b>ALFA ROMEO - 145 (930_)</b>						<b>07/94→01/01</b>	
1.4 i.e. (930.A3)	66 kW	1.4 l	07/94→12/96	; 09/94 ->; ;		KH10181 ProKIT	
				; 02/96 ->;		KH20047 ProKIT	
				; -> 01/96;		KH20161 ProKIT	
						KH20034 ProKIT	
1.4 i.e. 16V T.S. (930.A3A)	76 kW	1.4 l	12/96→01/01	; 10/98 ->; VIN 3180591 ->;		KH10065 ProKIT	
1.6 i.e. 16V T.S. (930.A2)	88 kW	1.6 l	12/96→01/01	; VIN -> 3180591; ;		KH10181 ProKIT	
				; -> 12/98;		KH20047 ProKIT	
						KH20034 ProKIT	
				; VIN 3180592 ->;		KH20022 ProKIT	
1.6 16V T.S. (930.A2C)	82 kW	1.6 l	09/97→12/00	; 10/98 ->; VIN 3180591 ->;		KH10065 ProKIT	
						KH20034 ProKIT	
				; VIN 3180592 ->;		KH20022 ProKIT	
1.6 i.e. (930.A2)	76 kW	1.6 l	10/94→12/96	;		KH10181 ProKIT	
1.7 i.e. 16V (930.A1)	95 kW	1.7 l	10/94→12/96	; 02/96 ->;		KH20047 ProKIT	
				; -> 01/96;		KH20161 ProKIT	
						KH20034 ProKIT	
1.8 i.e. 16V (930.A1A)	106 kW	1.8 l	03/98→01/01	; 06/98 ->; VIN -> 3180591		KH10181 ProKIT	
2.0 16V (930.A5)	114 kW	2 l	03/98→01/01	; 10/98 ->; VIN 3180591 ->;		KH10065 ProKIT	
				; -> 12/98;		KH20047 ProKIT	
						KH20034 ProKIT	
				; VIN 3180592 ->;		KH20022 ProKIT	
1.8 i.e. 16V T.S. (930.A1A)	103 kW	1.8 l	12/96→12/98	; 10/98 ->; VIN 3180591 ->;		KH10065 ProKIT	
				; VIN -> 3180591		KH10181 ProKIT	
						KH20034 ProKIT	
						KH20047 ProKIT	
				; VIN 3180592 ->		KH20022 ProKIT	
1.9 JTD (930.A4B)	77 kW	1.9 l	02/99→01/01	;		KH10190 ProKIT	
						KH10385 ProKIT	
						KH20034 ProKIT	
				; VIN 3180592 ->;		KH20022 ProKIT	
1.9 TD (930.A4)	66 kW	1.9 l	10/94→02/99	; VIN -> 3180591		KH10181 ProKIT	
				; VIN 3180591 ->;			
				; 10/98 ->; VIN 3180591 ->;		KH10065 ProKIT	
				; 01/97 ->; VIN -> 3180590;		KH20047 ProKIT	
				; -> 01/96;		KH20161 ProKIT	
						KH20034 ProKIT	
				; VIN 3180592 ->;		KH20022 ProKIT	

				13		i			
<b>ALFA ROMEO - 145 (930_)</b>								<b>07/94→01/01</b>	
2.0 16V T.S. (930.A5)	110 kW	2 l	10/95→01/01		11/95 ->; VIN -> 3180591; ABS, ABS			KH10181 ProKIT	
					10/98 ->; VIN 3180591 ->; ABS			KH10065 ProKIT	
					-> 01/96; ABS			KH20161 ProKIT	
					-> 12/98; ABS			KH20047 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 3180592 ->; ABS			KH20022 ProKIT	
<b>ALFA ROMEO - 146 (930_)</b>								<b>12/94→10/01</b>	
1.4 i.e. (930.B3)	66 kW	1.4 l	12/94→12/96		ABS, ABS			KH10181 ProKIT	
1.7 i.e. 16V (930.B1)	95 kW	1.7 l	12/94→12/96		02/96 ->; ABS			KH20047 ProKIT	
					-> 01/96; ABS			KH20161 ProKIT	
					ABS			KH20034 ProKIT	
1.4 i.e. 16V T.S. (930.B3A)	76 kW	1.4 l	11/96→01/01		10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
1.6 i.e. 16V T.S. (930.B2B, 930.B2C)	88 kW	1.6 l	11/96→10/01		ABS			KH10181 ProKIT	
1.8 i.e. 16V T.S. (930.B1A)	103 kW	1.8 l	11/96→01/01		-> 09/98; ABS			KH20047 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
1.6 16V T.S. (930.B2C)	82 kW	1.6 l	09/97→12/00		10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
1.6 i.e. (930.B2)	76 kW	1.6 l	12/94→12/96					KH10181 ProKIT	
					02/96 ->; ABS			KH20047 ProKIT	
					-> 01/96; ABS			KH20161 ProKIT	
					ABS			KH20034 ProKIT	
1.8 i.e. 16V T.S. (930.B1A)	106 kW	1.8 l	03/98→01/01		06/98 ->; VIN -> 0173864			KH10181 ProKIT	
					10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
					-> 12/98; ABS			KH20047 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
1.9 JTD (930.B4B)	77 kW	1.9 l	02/99→01/01		ABS			KH10190 ProKIT	
					ABS			KH10385 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
1.9 TD (930.B4A)	66 kW	1.9 l	12/94→02/99		VIN -> 0173864			KH10181 ProKIT	
					VIN 0173864 ->; ABS				
					10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
					01/97 ->; VIN -> 3180590; ABS			KH20047 ProKIT	
					-> 01/96; ABS			KH20161 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
2.0 16V (930.B5)	114 kW	2 l	03/97→10/01		06/98 ->; VIN -> 0173864			KH10181 ProKIT	
					10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
					-> 09/98; ABS			KH20047 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
2.0 16V T.S. (930.B5)	110 kW	2 l	10/95→01/01		10/98 ->; VIN 0173864 ->; ABS			KH10065 ProKIT	
					VIN 0173864 ->; ABS			KH10181 ProKIT	
					02/96 -> 07/98; ABS			KH20047 ProKIT	
					-> 01/96; ABS			KH20161 ProKIT	
					ABS			KH20034 ProKIT	
					VIN 0173865 ->; ABS			KH20022 ProKIT	
<b>ALFA ROMEO - 147 (937_)</b>								<b>01/01→03/10</b>	
1.6 16V T.SPARK (937.AXA1A, 937.AXB1A, 937.BXB1A)	88 kW	1.6 l	01/01→03/10					KH20083 ProKIT	
1.6 16V T.SPARK ECO (937.AXA1A, 937.BXA1A)	77 kW	1.6 l	01/01→03/10		10/04 ->; VIN 3402368 ->			KH20058 ProKIT	
					-> 10/04; VIN -> 3402367			KH20049 ProKIT	
					-> 10/04; VIN -> 3402367			KH20051 ProKIT	
1.9 JTD (937.AXD1A, 937.BXD1A)	85 kW	1.9 l	04/01→03/10					KH20083 ProKIT	
					10/04 -> 09/05; VIN 3402368 ->			KH20058 ProKIT	
					VIN -> 3402367			KH20049 ProKIT	
					VIN -> 3402367			KH20051 ProKIT	









































    					
<b>ALFA ROMEO - 147 (937_)</b>				<b>01/01→03/10</b>	
1.9 JTD (937.AXF1A, 937.BXF1A)	74 kW	1.9 l	06/03→03/10		KH20083 ProKIT
				; 10/04 -> 09/05; VIN 3402368 ->	KH20058 ProKIT
1.9 JTD 16V (937.AXG1B, 937.BXG1B)	93 kW	1.9 l	09/03→09/04		KH20083 ProKIT
1.9 JTD 16V (937.AXG1B, 937.BXG1B)	103 kW	1.9 l	11/02→03/10		KH20083 ProKIT
				; 07/05 -> 09/06; VIN 3402368 ->	KH20058 ProKIT
				; VIN -> 3402367	KH20049 ProKIT
				; VIN -> 3402367	KH20051 ProKIT
1.9 JTD 16V (937.AXM1B, 937.AXS1B)	100 kW	1.9 l	10/04→03/10		KH20083 ProKIT
1.9 JTD 8V (937.AXD1A, 937.AXU1A, 937.BXU1A)	88 kW	1.9 l	07/05→03/10	; VIN 3402368 ->	KH20058 ProKIT
1.9 JTD 8V (937.AXD1A, 937.AXV1A, 937.BXB1A)	85 kW	1.9 l	10/04→03/10		KH20083 ProKIT
				; -> 09/05; VIN 3402368 ->	KH20058 ProKIT
1.9 JTD 16V (937.AXN1B, 937.BXN1B)	110 kW	1.9 l	09/04→03/10		KH20083 ProKIT
				; VIN -> 3402367	KH20049 ProKIT
				; VIN -> 3402367	KH20051 ProKIT
				; VIN 3402368 ->	KH20058 ProKIT
2.0 16V T.SPARK (937.AXA1, 937.AXC1, 937.BXC1)	110 kW	2 l	01/01→03/10		KH20083 ProKIT
				; 10/04 -> 11/08; VIN 3402368 ->	KH20058 ProKIT
				; VIN -> 3402367	KH20049 ProKIT
				; VIN -> 3402367	KH20051 ProKIT
				; VIN 3402368 ->	KH20058 ProKIT
3.2 GTA (937.AXL1)	184 kW	3.2 l	02/03→03/10	; -> 01/06	KH20068 ProKIT
				; 10/04 -> 01/06; VIN 3402368 ->	KH20058 ProKIT
<b>ALFA ROMEO - 155 (167_)</b>				<b>01/92→12/97</b>	
1.6 16V T.S. (167.A6A)	88 kW	1.6 l	05/96→12/97	; -> 08/97	KH10181 ProKIT
1.7 T.S. 16V (167.A4N)	103 kW	1.7 l	05/96→12/97	; ABS	KH20034 ProKIT
2.0 T.S. 16V (167.A2G)	110 kW	2 l	03/95→12/97	; ABS	KH20161 ProKIT
1.7 T.S. (167.A4D, 167.A4H)	85 kW	1.7 l	04/93→04/96	; -> 03/95	KH10181 ProKIT
1.8 T.S. Sport (167.A4A, 167.A4C, 167.A4E)	93 kW	1.8 l	03/92→12/96	; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
1.7 T.S. (167.A4G)	83 kW	1.7 l	04/93→04/96		KH10181 ProKIT
1.8 T.S. (167.A4A, 167.A4C, 167.A4E)	95 kW	1.8 l	02/92→05/94	; ABS	KH20034 ProKIT
2.0 T.S. (167.A2A, 167.A2D)	104 kW	2 l	02/92→05/95	; ABS	KH20161 ProKIT
2.0 T.S. (167.A2D)	106 kW	2 l	02/92→01/95		
1.8 T.S. (167.A4C, 167.A)	77 kW	1.8 l	02/92→12/97	; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
1.9 TD (167.A3B, 167.A3)	66 kW	1.9 l	04/93→12/97	; 07/93 -> 08/97	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
2.0 16V Turbo Q4 (167.A2B, 167.A2C, 167.A2E)	137 kW	2 l	01/92→12/97		KH10190 ProKIT
2.0 16V Turbo Q4 (167.A2B, 167.A2C, 167.A2E)	140 kW	2 l	03/92→12/97		
2.5 TD (167.A1A, 167.A1G)	92 kW	2.5 l	04/93→12/97		KH10190 ProKIT
2.5 V6 (167.A1C, 167.A1)	121 kW	2.5 l	03/92→05/95	; ABS	KH20034 ProKIT
2.5 V6 (167.A1C, 167.A1E)	120 kW	2.5 l	09/92→12/97	; ABS	KH20161 ProKIT
<b>ALFA ROMEO - 156 / 156 Sportwagon (932_)</b>				<b>02/97→05/06</b>	
1.6 16V T.SPARK. (932B4100)	88 kW	1.6 l	05/00→05/06	; -> 06/04	KH20068 ProKIT
				; -> 01/06; VIN 0644570 ->	KH20058 ProKIT
				; ABS	KH20049 ProKIT
				; ABS	KH20051 ProKIT
1.6 16V T.SPARK (932.A4, 932.A4100)	88 kW	1.6 l	09/97→09/05	; -> 06/04	KH20068 ProKIT
				; 01/99 ->; ABS	KH20049 ProKIT
				; 01/99 ->; ABS	KH20051 ProKIT
				; VIN 0644570 ->	KH20058 ProKIT
1.8 16V T.SPARK (932.A3)	106 kW	1.8 l	09/97→10/00		KH20068 ProKIT
1.9 JTD (932B2)	77 kW	1.9 l	09/97→10/00		
2.0 16V T.SPARK (932A2)	114 kW	2 l	09/97→06/02	; 01/99 ->; ABS	KH20049 ProKIT
2.4 JTD (932B1)	100 kW	2.4 l	09/97→09/03	; 01/99 ->; ABS	KH20051 ProKIT
2.5 V6 24V (932A1)	140 kW	2.5 l	09/97→09/02		


















































































ALFA ROMEO - 156 / 156 Sportwagon (932_)				02/97→05/06	
1.8 16V T.SPARK (932.A3100)	103 kW	1.8 l	09/97→09/05		KH20068 ProKIT
2.0 JTS (932AXA)	122 kW	2 l	03/02→09/05		KH20049 ProKIT
2.4 JTD (932AXF00)	129 kW	2.4 l	10/03→09/05		KH20051 ProKIT
2.5 V6 24V (932A11_)	141 kW	2.5 l	10/00→09/05		KH20058 ProKIT
				VIN 0644570 ->	
1.8 16V T.SPARK (932A3)	106 kW	1.8 l	05/00→10/00		KH20068 ProKIT
1.9 JTD (932.A2B00)	81 kW	1.9 l	10/00→05/01		KH20049 ProKIT
1.9 JTD (932.B2B00)	81 kW	1.9 l	10/00→05/01		KH20051 ProKIT
1.9 JTD (932B2)	77 kW	1.9 l	05/00→10/00		
2.0 16V T.SPARK (932A2)	114 kW	2 l	05/00→06/02		
2.0 16V T.SPARK (932A21_)	110 kW	2 l	10/00→03/02		
2.0 16V T.SPARK (932B21_)	110 kW	2 l	10/00→03/02		
2.4 JTD (932B1)	100 kW	2.4 l	05/00→09/03		
2.5 V6 24V (932A1)	140 kW	2.5 l	02/97→08/03		
1.8 16V T.SPARK (932B31_)	103 kW	1.8 l	02/97→05/06	-> 01/06	KH20068 ProKIT
2.0 JTS (932BXA)	122 kW	2 l	03/02→05/06	-> 01/06; VIN 0644570 ->	KH20058 ProKIT
2.4 JTD (932BXF00)	129 kW	2.4 l	10/03→05/06		KH20049 ProKIT
					KH20051 ProKIT
1.9 JTD (932.A2B00, 932.A2C00)	85 kW	1.9 l	05/01→09/05	-> 01/05	KH20068 ProKIT
1.9 JTD (932B2B, 932B2C)	85 kW	1.9 l	05/01→05/06	-> 01/05; VIN 0644570 ->	KH20058 ProKIT
					KH20049 ProKIT
					KH20051 ProKIT
1.9 JTD 16V (932AXE00)	103 kW	1.9 l	11/02→09/05	04/03 -> 01/05	KH20068 ProKIT
1.9 JTD 16V (932BXE00)	103 kW	1.9 l	11/02→05/06	-> 01/05; VIN 0644570 ->	KH20058 ProKIT
					KH20049 ProKIT
					KH20051 ProKIT
1.9 JTD 16V Q4 (932BXN20)	110 kW	1.9 l	07/04→05/06	09/04 ->	KH20068 ProKIT
					KH10198 ProKIT
2.4 JTD (932.B1B00)	103 kW	2.4 l	10/00→05/06	-> 03/03	KH20068 ProKIT
2.4 JTD (932A1B_)	103 kW	2.4 l	10/00→09/05		KH20049 ProKIT
					KH20051 ProKIT
2.4 JTD (932.BXC00)	110 kW	2.4 l	03/02→05/06	-> 07/03	KH20068 ProKIT
2.4 JTD (932AXC)	110 kW	2.4 l	03/02→09/05	-> 07/03; VIN 0644570 ->	KH20058 ProKIT
					KH20049 ProKIT
					KH20051 ProKIT
2.5 V6 24V (932B1100)	141 kW	2.5 l	02/97→05/06	-> 09/05	KH20068 ProKIT
				-> 09/05; VIN 0644570 ->	KH20058 ProKIT
					KH20049 ProKIT
					KH20051 ProKIT
3.2 GTA (932.BXB00)	184 kW	3.2 l	03/02→05/06	-> 02/06	KH20068 ProKIT
				-> 02/06; VIN 0644570 ->	KH20058 ProKIT
					KH20049 ProKIT
					KH20051 ProKIT
3.2 GTA (932AXB)	184 kW	3.2 l	03/02→09/05		KH20068 ProKIT
				VIN 0644570 ->	KH20058 ProKIT
ALFA ROMEO - 159 Sedan / 159 Sportwagon (939_)				06/05→12/12	
1.8 MPI (939AXL1A)	103 kW	1.8 l	06/05→11/11		KH30073 ProKIT
1.8 MPI (939BXL1A)	103 kW	1.8 l	06/05→11/11	VIN -> 7026205	KH30170 ProKIT
1.8 Tbi (939.AXN1B)	147 kW	1.8 l	05/09→12/12		
1.8 Tbi (939BXN1B)	147 kW	1.8 l	07/09→11/11	-> 07/10	KH30100 ProKIT
1.9 JTDm 16V (939BXC1B, 939BXC12)	110 kW	1.9 l	03/06→11/11		
1.9 JTDm 8V (939BXE1B)	88 kW	1.9 l	03/06→11/11		
2.0 JTDm (939AXP1B)	125 kW	2 l	05/09→11/11		
2.0 JTDm (939BXP1B)	125 kW	2 l	07/09→11/11		
2.4 JTDm (939AXD)	154 kW	2.4 l	07/07→11/11		
2.4 JTDm (939BXD1B, 939BXD12)	147 kW	2.4 l	03/06→11/11		
3.2 JTS (939AXG2B)	191 kW	3.2 l	01/08→11/11		
3.2 JTS (939BXH1B)	191 kW	3.2 l	02/08→11/11		
1.9 JTDm 16V (939AXC1B, 939AXC12)	110 kW	1.9 l	09/05→11/11	VIN -> 7026205	KH30170 ProKIT
1.9 JTDm 16V (939AXF1B, 939AXC1B)	100 kW	1.9 l	09/05→11/11	VIN 7026206 ->	KH30073 ProKIT
				02/06 -> 07/10	KH30100 ProKIT
1.9 JTS (939AXA1B)	118 kW	1.9 l	09/05→11/11		
2.2 JTS (939AXB1B, 939AXB11)	136 kW	2.2 l	09/05→11/11		
2.4 JTDm (939AXD12, 939AXD11)	147 kW	2.4 l	09/05→11/11		

































				13	i		
<b>ALFA ROMEO - 159 Sedan / 159 Sportwagon (939_)</b>						<b>06/05→12/12</b>	
1.9 JTDM 16V (939BXC1B)	100 kW	1.9 l	03/06→11/11		VIN → 7026205	KH30170 ProKIT	
1.9 JTS (939BXA1B)	118 kW	1.9 l	03/06→11/11		VIN 7026206 →	KH30073 ProKIT	
2.2 JTS (939BXB1B, 939BXB11)	136 kW	2.2 l	03/06→11/11			KH30100 ProKIT	
2.4 JTDM (939.BXM1B)	154 kW	2.4 l	05/07→12/12		→ 07/10	KH30100 ProKIT	
1.9 JTDM 8V (939AXE1B)	88 kW	1.9 l	09/05→11/11			KH30073 ProKIT	
					VIN → 7026205	KH30170 ProKIT	
					02/06 → 07/10	KH30100 ProKIT	
2.0 JTDM (939AXQ1B)	120 kW	2 l	05/09→11/11			KH30073 ProKIT	
2.0 JTDM (939BXQ1B)	120 kW	2 l	05/09→11/11			KH30100 ProKIT	
2.4 JTDM Q4 (939AXMB2)	154 kW	2.4 l	05/07→11/11			KH30100 ProKIT	
2.4 JTDM Q4 (939BXM2B)	154 kW	2.4 l	05/07→11/11			KH30100 ProKIT	
2.0 JTDM (939AXR1B)	100 kW	2 l	06/10→11/11			KH30073 ProKIT	
2.0 JTDM (939BXR1B)	100 kW	2 l	06/10→11/11		→ 07/10	KH30100 ProKIT	
3.2 JTS Q4 (939AXH1B, 939AXG22)	191 kW	3.2 l	12/05→11/11		VIN → 7026205	KH30170 ProKIT	
					VIN 7026206 →	KH30073 ProKIT	
3.2 JTS Q4 (939BXG2B, 939BXG22)	191 kW	3.2 l	03/06→11/11			KH30073 ProKIT	
<b>ALFA ROMEO - 164 Sedan (164_)</b>						<b>06/87→09/98</b>	
2.0 T.S. (164.A2C, 164.A2L)	105 kW	2 l	06/87→09/92			KH10190 ProKIT	
2.0 T.S. (164.A2H)	109 kW	2 l	06/87→09/92			KH10371 ProKIT	
2.0 T.S. (164.H3)	106 kW	2 l	09/92→09/98		→ 11/93;	KH10190 ProKIT	
					12/93 →; VIN 0014992 →;	KH10371 ProKIT	
					→ 11/93; VIN → 0014991;	KH10371 ProKIT	
2.0 Turbo (164A2B)	128 kW	2 l	10/87→09/98			KH10190 ProKIT	
2.0 Turbo (164A2B)	129 kW	2 l	02/88→10/92			KH10190 ProKIT	
2.0 V6 Turbo (164.A2G, 164.A2F)	150 kW	2 l	03/91→09/92			KH10190 ProKIT	
2.0 V6 Turbo (164.K3)	148 kW	2 l	09/92→09/98			KH10190 ProKIT	
2.5 TD (164.A1A)	84 kW	2.5 l	06/87→09/92			KH10190 ProKIT	
2.5 TD (164.K2A, 164.K2B)	92 kW	2.5 l	09/92→09/98			KH10190 ProKIT	
3.0 (164A)	138 kW	3 l	11/87→09/91			KH10190 ProKIT	
3.0 (164H1)	168 kW	3 l	04/93→02/95			KH10190 ProKIT	
3.0 24V (164.K1)	155 kW	3 l	09/92→09/98			KH10190 ProKIT	
3.0 24V QV (164.H1)	171 kW	3 l	09/92→09/98			KH10190 ProKIT	
3.0 i.e. QV (164.AG)	147 kW	3 l	09/90→09/92			KH10190 ProKIT	
3.0 V6 (164.A)	141 kW	3 l	06/87→09/92			KH10190 ProKIT	
3.0 V6 (164.AD, 164.AH, 164.AB)	135 kW	3 l	06/87→09/92			KH10190 ProKIT	
3.0 V6 (164.H1A, 164.H1B, 164.K1P)	132 kW	3 l	09/92→09/98			KH10190 ProKIT	
3.0 24V Q4 (164.K1M, 164.K1C)	170 kW	3 l	02/94→09/98			KH10190 ProKIT	
3.0 24V QV All-wheel Drive (164K1H)	171 kW	3 l	11/92→10/97			KH10190 ProKIT	
<b>ALFA ROMEO - 166 Sedan (936_)</b>						<b>09/98→06/07</b>	
2.0 T.Spark (936A3A_)	114 kW	2 l	09/98→10/00		10/98 →	KH20068 ProKIT	
2.0 V6 (936A3_)	151 kW	2 l	09/98→10/00			KH20049 ProKIT	
2.4 JTD (936A2A_)	100 kW	2.4 l	09/98→10/00		ABS	KH20051 ProKIT	
2.5 V6 24V (936A2_)	140 kW	2.5 l	09/98→12/06		ABS	KH20051 ProKIT	
3.0 V6 24V (936A1000, 936A1001)	166 kW	3 l	09/98→06/07			KH20051 ProKIT	
2.0 T.Spark (936A3B00)	110 kW	2 l	10/00→06/07		→ 04/06	KH20068 ProKIT	
2.4 JTD (936AXA00, 936A3B00)	110 kW	2.4 l	04/02→06/07		ABS	KH20049 ProKIT	
					ABS	KH20051 ProKIT	
2.4 JTD (936A2B_)	103 kW	2.4 l	10/00→06/07		→ 09/03	KH20068 ProKIT	
					ABS	KH20049 ProKIT	
					ABS	KH20051 ProKIT	
2.4 JTD (936AXC00, 936AXD01)	129 kW	2.4 l	10/03→06/07			KH20068 ProKIT	
3.2 V6 24V (936AXB00, 936AXA00)	176 kW	3.2 l	10/03→06/07		ABS	KH20049 ProKIT	
					ABS	KH20051 ProKIT	
2.4 JTD (936AXC00, 936AXG00)	136 kW	2.4 l	07/05→06/07			KH20068 ProKIT	
2.4 JTD (936AXC00)	132 kW	2.4 l	07/06→06/07			KH20068 ProKIT	
2.5 V6 24V (936A21_)	138 kW	2.5 l	10/00→06/07		→ 01/05	KH20068 ProKIT	
					ABS	KH20049 ProKIT	
					ABS	KH20051 ProKIT	
3.0 V6 24V (936A11_)	162 kW	3 l	10/00→06/07		→ 01/06	KH20068 ProKIT	
					ABS	KH20049 ProKIT	
					ABS	KH20051 ProKIT	
<b>ALFA ROMEO - 1750-2000 Saloon (105_)</b>						<b>03/68→07/75</b>	
1750 (105.48)	83 kW	1.8 l	03/68→10/72		ABS	KH00110 ProKIT	
2000 (105)	97 kW	2 l	10/71→07/75			KH00110 ProKIT	

















				     	
<b>ALFA ROMEO - ALFETTA GT / ALFETTA Sedan (116_)</b>				<b>01/74→01/86</b>	
1.6 (116.B1A)	79 kW	1.6 l	01/75→12/84	 ; 03/80 ->	KH00111 ProKIT
				 ; -> 11/80	KH00056 ProKIT
1.6 (11604)	79 kW	1.6 l	01/76→09/82	 ; -> 11/80	KH00056 ProKIT
1.8 (116.B2)	90 kW	1.8 l	10/79→12/84	 ; 07/81 ->	KH00111 ProKIT
				 ; -> 11/80	KH00056 ProKIT
1.8 (11608, 11642)	85 kW	1.8 l	07/74→04/82		KH00056 ProKIT
1.8 (11610, 11654)	89 kW	1.8 l	06/74→12/76		
1.8 (11610)	85 kW	1.8 l	01/74→12/76		
1.8 (11608)	89 kW	1.8 l	10/79→12/84	 ; 02/81 -> 12/82	KH00111 ProKIT
				 ; -> 11/80	KH00056 ProKIT
2.0 (116.55F, 116.56F, 116.55N, 116.56N)	97 kW	2 l	07/78→12/84	 ; -> 11/80	KH00056 ProKIT
					KH00111 ProKIT
2.0 (116.55G, 116.56G)	89 kW	2 l	03/77→02/80	 ; 02/80 ->	KH00111 ProKIT
					KH00056 ProKIT
2.0 (11610)	89 kW	2 l	07/78→01/86	 ; 03/80 -> 12/85	KH00111 ProKIT
				 ; -> 11/80	KH00056 ProKIT
2.0 (11636, 11610)	96 kW	2 l	06/77→12/84	 ; 02/80 -> 12/80	KH00111 ProKIT
				 ; -> 11/80	KH00056 ProKIT
2.0 TD (116.BA)	60 kW	2 l	10/79→03/83	 ; 03/80 ->	KH00111 ProKIT
2.4 TD (116.B3)	70 kW	2.4 l	04/83→12/84		KH00111 ProKIT
<b>ALFA ROMEO - AR 6 Bus / AR 6 Van / AR 8 Platform/Chassis / AR 8 Van (280_)</b>				<b>04/78→12/89</b>	
1.9 D (280)	51 kW	1.9 l	04/85→12/89	 ; VIN -> 604496	KH00061 ProKIT
2.4 D (280)	53 kW	2.4 l	04/85→02/86		KH00107 ProKIT
2.5 D (280)	55 kW	2.5 l	03/86→12/89		
2.4 D (280)	53 kW	2.4 l	04/78→08/86	 ; Axle: Iveco Axle	KH00102 ProKIT
				 ; Trim Level: 35AR8, 40AR8; Axle: Iveco Axle; Manufacturer Restriction: SALISBURY-1	
				 ; VIN -> 604496	KH00061 ProKIT
2.4 TD (280)	68 kW	2.4 l	04/85→12/88	 ; VIN -> 604496	KH00061 ProKIT
2.4 TD (280)	68 kW	2.4 l	04/85→12/89		
2.4 TD (280)	68 kW	2.4 l	09/86→12/89		
2.5 D (280)	55 kW	2.5 l	09/86→12/89		
<b>ALFA ROMEO - BRERA (939_)</b>				<b>01/06→05/11</b>	
1.8 Tbi (939DXN1B)	147 kW	1.8 l	05/09→06/10		KH30073 ProKIT
2.0 JTDM (939DXP1B)	125 kW	2 l	05/09→06/10	 ; -> 03/10	KH30100 ProKIT
2.0 JTDM (939DXQ1B)	120 kW	2 l	03/08→06/10		
2.4 JTDM 20V (939DXD1B, 939DXM1B)	154 kW	2.4 l	05/07→03/11		
3.2 JTS (939DXG2B, 939DXG1B)	191 kW	3.2 l	03/08→06/10		
2.2 JTS (939.DXB11)	136 kW	2.2 l	01/06→05/11		KH30073 ProKIT
2.4 JTDM 20V (939DXD1B, 939DXD12)	147 kW	2.4 l	01/06→03/11	 ; 02/06 -> 03/10	KH30100 ProKIT
3.2 JTS Q4 (939.DXG22)	191 kW	3.2 l	01/06→05/11		KH30073 ProKIT
<b>ALFA ROMEO - GIULIA GT / GIULIA Sedan (105_)</b>				<b>06/64→12/78</b>	
1.8 D	38 kW	1.8 l	06/76→12/78		KH00110 ProKIT
1300 Super	64 kW	1.3 l	01/74→12/78		
1300 Super (115)	64 kW	1.3 l	01/74→12/78		
1600 Super	76 kW	1.6 l	01/74→12/78		
1600 Super (105,14)	71 kW	1.6 l	06/64→08/69		
1600 Super (115)	76 kW	1.6 l	01/74→12/78		
1300 TI (105,39)	62 kW	1.3 l	04/69→07/75	 ; 01/73 ->	KH00110 ProKIT
<b>ALFA ROMEO - GIULIETTA (940_)</b>				<b>04/10→12/20</b>	
1.4 TB (940FXA1A, 940FXT1A)	88 kW	1.4 l	04/10→12/20		KH20090 ProKIT
1.4 TB (940FXB1A, 940FXB11)	125 kW	1.4 l	04/10→10/18		
1.4 TB (940FXN1A, 940FXU1A)	77 kW	1.4 l	04/11→02/17		
1.6 JTDM (940FXD1A)	77 kW	1.6 l	04/10→02/16		
1.8 Tbi (940FXC1A)	173 kW	1.8 l	04/10→02/16		
2.0 JTDM (940.FXL1A)	103 kW	2 l	04/10→12/20		
2.0 JTDM (940FXE1A, 940FXG11)	125 kW	2 l	04/10→12/20		
<b>ALFA ROMEO - GIULIETTA Sedan (116_)</b>				<b>10/77→12/85</b>	
1.3 (116.44A)	66 kW	1.3 l	10/77→06/83	 ; 03/80 ->	KH00111 ProKIT
1.6 (116.50B)	79 kW	1.6 l	10/77→04/85	 ; -> 11/80	KH00056 ProKIT
1.8 (116.AA, 116.AB)	90 kW	1.8 l	04/79→04/85		





























										
<b>ALFA ROMEO - GIULIETTA Sedan (116_)</b>										<b>10/77→12/85</b>
2.0 (116.A1A)	96 kW	2 l	06/80→04/85		-> 11/80					KH00056 ProKIT
										KH00111 ProKIT
2.0 TD (116A2)	61 kW	2 l	01/83→12/85							KH00111 ProKIT
2.0 Turbo (116)	125 kW	2 l	04/83→06/85							
<b>ALFA ROMEO - GT (105_)</b>										<b>03/63→12/77</b>
1300 Junior (105)	64 kW	1.3 l	01/66→12/77		-> 01/73					KH00110 ProKIT
1600 (115)	76 kW	1.6 l	09/72→12/77							
1600 (115)	80 kW	1.6 l	06/71→12/77							
V 2000 (105)	96 kW	1.9 l	01/71→12/77							
1600 (105)	75 kW	1.6 l	03/63→12/66							KH00110 ProKIT
1600 (105)	80 kW	1.6 l	01/66→12/68							
A 1600 (105)	83 kW	1.6 l	01/65→12/70							
V 1750 (105)	83 kW	1.8 l	01/67→12/72							
<b>ALFA ROMEO - GT (937_)</b>										<b>11/03→09/10</b>
1.8 TS (937CXR1A)	103 kW	1.8 l	11/03→09/10		01/04 ->					KH20068 ProKIT
					01/04 ->; VIN 0023784 ->					KH20058 ProKIT
					(ABS)					KH20049 ProKIT
					(ABS)					KH20051 ProKIT
1.9 JTD (937CXN1B, 937CXZ1B)	125 kW	1.9 l	05/08→09/10							KH20068 ProKIT
2.0 JTS (937CXH11, 937CXH1A, 937CXT1A)	119 kW	2 l	12/06→09/10							KH20058 ProKIT
1.9 JTD (937CXN1B)	110 kW	1.9 l	11/03→09/10							KH20068 ProKIT
					(ABS)					KH20049 ProKIT
					(ABS)					KH20051 ProKIT
					VIN 0023784 ->					KH20058 ProKIT
2.0 JTS (937CXH1A, 937CXH11)	121 kW	2 l	11/03→09/10		-> 11/06					KH20068 ProKIT
					-> 11/06; VIN 0023784 ->					KH20058 ProKIT
					(ABS)					KH20049 ProKIT
					(ABS)					KH20051 ProKIT
3.2 GTA (937CXP1B)	176 kW	3.2 l	11/03→09/10		-> 01/08					KH20068 ProKIT
					-> 01/08; VIN 0023784 ->					KH20058 ProKIT
					(ABS)					KH20049 ProKIT
					(ABS)					KH20051 ProKIT
<b>ALFA ROMEO - GTA Coupe (113_)</b>										<b>05/68→12/76</b>
1.3 Junior	81 kW	1.3 l	05/68→12/76		01/73 ->					KH00110 ProKIT
1.3 Junior	117 kW	1.3 l	05/68→12/76							
<b>ALFA ROMEO - GTV (116_)</b>										<b>07/78→02/87</b>
2.0 (11636)	96 kW	2 l	07/78→01/86		12/80 ->					KH00111 ProKIT
6 2.5 (116.CA)	116 kW	2.5 l	11/80→02/87							
<b>ALFA ROMEO - GTV (916_)</b>										<b>06/95→10/05</b>
1.8 16V (916C3)	106 kW	1.8 l	05/98→10/05		04/00 ->; VIN 6063041 ->					KH10065 ProKIT
					VIN -> 6060340					KH20097 ProKIT
2.0 JTS (916CXA00)	121 kW	2 l	04/03→10/05							KH10065 ProKIT
					VIN -> 6060340					KH20097 ProKIT
2.0 T.SPARK 16V (916.C2_, 916C2C00)	110 kW	2 l	06/95→10/05		04/00 ->; VIN 6063041 ->					KH10065 ProKIT
2.0 T.SPARK 16V (916C2C)	114 kW	2 l	09/97→03/03		-> 04/00; VIN -> 6063041					KH10181 ProKIT
					VIN -> 6060340					KH20097 ProKIT
2.0 V6 Turbo (916.C2A)	148 kW	2 l	06/95→09/98		VIN -> 6063040					KH10190 ProKIT
					VIN -> 6060340					KH20097 ProKIT
3.0 V6 24V (916.C1)	162 kW	3 l	10/96→10/00		04/00 ->; VIN 6063041 ->					KH10385 ProKIT
					-> 04/00; VIN -> 6063040					KH10190 ProKIT
					VIN -> 6060340					KH20097 ProKIT
3.0 V6 24V (916.C1B_)	160 kW	3 l	10/00→10/05		VIN 6063041 ->					KH10385 ProKIT
					VIN -> 6060340					KH20097 ProKIT
3.2 V6 24V (916CXB00)	176 kW	3.2 l	04/03→10/05							KH10385 ProKIT
					VIN -> 6060340					KH20097 ProKIT

											
<b>ALFA ROMEO - MITO (955_)</b>										<b>08/08→10/18</b>	
0.9 (955AXY1B, 955AXZ1B)	74 kW	0.9 l	12/13→08/18								<b>KH20022</b> ProKIT
0.9 TwinAir (955.AXW1B)	63 kW	0.9 l	07/11→12/13								
0.9 TwinAir (955AXY1B)	77 kW	0.9 l	04/13→08/18								
1.4 (955.AXB1B, 955.AXU1A)	57 kW	1.4 l	03/11→10/18								
1.4 (955AXB1B)	58 kW	1.4 l	08/08→08/13								
1.4 (955AXV1A)	51 kW	1.4 l	05/11→10/18								
1.4 Bifuel (955.AXG1A)	88 kW	1.4 l	04/16→10/18								
1.4 MultiAir (955AXL1B)	77 kW	1.4 l	09/09→08/13								
1.6 JTDM (955AXE1B)	85 kW	1.6 l	08/08→08/15								
1.3 MultiJet (955AXH1B, 955AXT1A)	66 kW	1.3 l	08/08→08/10								<b>KH10065</b> ProKIT
1.3 MultiJet (955AXP1A, 955AYC1A)	70 kW	1.3 l	09/09→10/18								<b>KH20022</b> ProKIT
1.3 MultiJet (955AXT1A, 955AYA1A)	59 kW	1.3 l	12/13→12/15								
1.3 MultiJet (955AXT1A)	62 kW	1.3 l	01/11→12/15								
1.4 (955AXB1B, 955.AXF1B)	70 kW	1.4 l	09/08→08/13								
1.4 Bifuel (955AXG1A)	88 kW	1.4 l	01/09→08/16								
1.4 MultiAir (955AXN1B)	125 kW	1.4 l	09/09→10/18								
1.4 TB (955.AYB11, 955.AXB1B)	103 kW	1.4 l	12/13→10/18								
1.4 TJet (955AXA1B)	114 kW	1.4 l	08/08→06/11								
1.4 TJet (955AXD1B)	110 kW	1.4 l	09/08→06/11								
1.4 TJet (955AXG1A)	88 kW	1.4 l	08/08→08/13								
1.4 Turbo MultiAir (955AXM1A, 955AXR11)	99 kW	1.4 l	10/09→12/14								
1.4 Turbo MultiAir (955AXS1B, 955AXS11)	120 kW	1.4 l	10/09→10/18								
1.6 JTDM (955AXC1B)	88 kW	1.6 l	08/08→08/15								
<b>ALFA ROMEO - MONTREAL (105_)</b>										<b>12/72→03/79</b>	
2.6 (105.64)	143 kW	2.6 l	12/72→03/79								<b>KH00110</b> ProKIT
<b>ALFA ROMEO - SPIDER (105_, 115_)</b>										<b>03/66→12/93</b>	
1300 (10591)	64 kW	1.3 l	01/68→12/77								<b>KH00110</b> ProKIT
1600 (10503)	80 kW	1.6 l	03/66→12/68								
1600 (11507)	80 kW	1.6 l	03/71→12/79								
1600 (11535)	76 kW	1.6 l	03/76→12/90								
1600 (115A2)	79 kW	1.6 l	01/90→12/93								
1750 (10557)	83 kW	1.8 l	01/67→12/71								
2000 (10512, 10524)	96 kW	2 l	01/71→12/77								
2000 (11538, 115661)	92 kW	2 l	08/86→12/90								
2000 (11538, 115A1)	93 kW	2 l	01/77→12/93								
2000 (115680, 115681)	85 kW	2 l	08/86→12/90								
2000 (115A1A)	88 kW	2 l	01/90→12/93								
<b>ALFA ROMEO - SPIDER (916_)</b>										<b>09/94→04/05</b>	
1.8 16V (916S3)	106 kW	1.8 l	05/98→04/05		04/00 ->	VIN	6063041 ->				<b>KH10065</b> ProKIT
2.0 T.SPARK 16V (916S2B)	114 kW	2 l	05/98→08/00		VIN ->	6063041					<b>KH10181</b> ProKIT
2.0 T.SPARK 16V (916S2C00)	110 kW	2 l	06/95→04/05		VIN ->	6060340					<b>KH20097</b> ProKIT
2.0 JTS (916SXA00)	121 kW	2 l	04/03→04/05		VIN ->	6063041					<b>KH10181</b> ProKIT
					VIN	6063041 ->					<b>KH10065</b> ProKIT
					VIN ->	6060340					<b>KH20097</b> ProKIT
2.0 V6 Turbo (916S2A)	148 kW	2 l	05/98→04/05		04/00 ->	VIN	6063041 ->				<b>KH10385</b> ProKIT
3.0 V6 (916S1)	141 kW	3 l	06/95→04/05		-> 04/00;	VIN ->	6063040				<b>KH10190</b> ProKIT
					VIN ->	6063041					<b>KH10181</b> ProKIT
					VIN ->	6060340					<b>KH20097</b> ProKIT
3.0 V6 (916S1B00)	160 kW	3 l	09/94→04/05		VIN	6063041 ->					<b>KH10385</b> ProKIT
					VIN ->	6060340					<b>KH20097</b> ProKIT
3.0 V6 24V (916S1)	162 kW	3 l	01/99→10/03		04/00 ->	VIN	6063041 ->				<b>KH10385</b> ProKIT
					-> 04/00;	VIN ->	6063040				<b>KH10190</b> ProKIT
					VIN ->	6060340					<b>KH20097</b> ProKIT
3.2 V6 24V (916SXB00)	176 kW	3.2 l	04/03→04/05		VIN ->	6060340					<b>KH10385</b> ProKIT
					VIN ->	6060340					<b>KH20097</b> ProKIT
<b>ALFA ROMEO - SPIDER (939_)</b>										<b>03/06→03/11</b>	
1.8 Tbi (939DXN1B)	147 kW	1.8 l	05/09→03/11								<b>KH30073</b> ProKIT
2.0 JTDM (939DXP1B, 939EXP1B)	125 kW	2 l	05/09→06/10		->	03/10					<b>KH30100</b> ProKIT
2.0 JTDM (939DXQ1B)	120 kW	2 l	04/09→03/11								
2.2 JTS (939EXB1B, 939EXB11)	136 kW	2.2 l	03/06→03/11								
2.4 JTDM (939DXM1B, 939EXM1B)	154 kW	2.4 l	03/08→03/11								
2.4 JTDM (939EXD1B, 939EXD12)	147 kW	2.4 l	03/06→03/11								
3.2 JTS (939EXG2B)	191 kW	3.2 l	03/08→03/11								
3.2 JTS Q4 (939EXG2B, 939EXG22)	191 kW	3.2 l	03/06→03/11								<b>KH30073</b> ProKIT

										
<b>AUDI - 50 (863)</b>										<b>08/74→07/78</b>
0.8	25 kW	0.8 l	01/76→07/78							KH00003 ProKIT
1.1	44 kW	1.1 l	08/74→07/77							
1.3	43 kW	1.3 l	01/77→07/78							
1.1	37 kW	1.1 l	08/74→07/78							KH10187 ProKIT
1.3	44 kW	1.3 l	08/77→07/78							KH00003 ProKIT
<b>AUDI - 80 B2 Saloon (811, 813, 814, 819, 853)</b>										<b>08/78→03/87</b>
1.3	40 kW	1.3 l	09/78→07/81		VIN 8242072774 ->					KH10194 ProKIT
1.3	44 kW	1.3 l	09/78→07/81							KH00002 ProKIT
1.3	44 kW	1.3 l	09/78→07/86							KH00003 ProKIT
1.6	51 kW	1.6 l	08/78→07/81							KH00002 ProKIT
2.2	85 kW	2.2 l	10/80→07/83							KH00003 ProKIT
1.6	54 kW	1.6 l	02/86→07/86							KH10194 ProKIT
1.6	55 kW	1.6 l	08/78→07/86							KH00002 ProKIT
1.6	55 kW	1.6 l	08/78→03/87							
1.6	63 kW	1.6 l	08/78→02/83							KH00003 ProKIT
1.6 D	40 kW	1.6 l	08/80→08/86							
1.6 GLE	81 kW	1.6 l	08/78→07/82							
1.6 TD	51 kW	1.6 l	08/81→05/86							
1.8	65 kW	1.8 l	02/86→07/86							
1.8	66 kW	1.8 l	01/83→08/86							
1.8	68 kW	1.8 l	08/83→08/86							
1.8 GTE	81 kW	1.8 l	08/85→07/86							
1.8 GTE	82 kW	1.8 l	10/84→08/86							
1.9 CD-5S	85 kW	1.9 l	09/81→07/83							
2.0	85 kW	2 l	10/83→09/84							
<b>AUDI - 80 B3 Saloon (893, 894, 8A2)</b>										<b>06/86→10/91</b>
1.4	48 kW	1.4 l	08/86→07/88		-> 04/88; VIN -> 89J373598					KH10194 ProKIT
1.6	51 kW	1.6 l	08/87→09/91							KH00002 ProKIT
1.6	55 kW	1.6 l	09/86→08/91							
1.6 D	40 kW	1.6 l	02/87→07/89							
1.6 TD	59 kW	1.6 l	09/86→08/91							
1.8	55 kW	1.8 l	10/86→01/90							
1.8	83 kW	1.8 l	09/86→07/88							
1.8 E	82 kW	1.8 l	06/86→08/91							
1.8 S	65 kW	1.8 l	08/86→01/90							
1.8 S	66 kW	1.8 l	09/86→10/91							
1.6	75 kW	1.6 l	08/90→10/91							KH00002 ProKIT
1.9 D	50 kW	1.9 l	08/89→08/91							
2.0	82 kW	2 l	10/90→08/91							
2.0 E	83 kW	2 l	08/88→10/90							
2.0 E 16V	101 kW	2 l	03/90→09/91							
<b>AUDI - 80 B4 Avant / 80 B4 Saloon (8C5, 8C2)</b>										<b>09/91→01/96</b>
1.6	52 kW	1.6 l	09/91→12/94		VIN -> 8G-V-004 799					KH00002 ProKIT
1.6 E	74 kW	1.6 l	06/93→12/94							
1.6 E	74 kW	1.6 l	06/93→01/96							
1.9 TD	55 kW	1.9 l	09/91→12/94							
1.9 TDI	66 kW	1.9 l	09/91→12/94							
1.9 TDI	66 kW	1.9 l	07/92→01/96							
2.0	66 kW	2 l	09/91→12/94							
2.0	66 kW	2 l	07/92→01/96							
2.0 E	85 kW	2 l	09/91→12/94							
2.0 E	85 kW	2 l	07/92→01/96							
2.0 E 16V	101 kW	2 l	09/91→07/92							
2.0 E 16V	103 kW	2 l	08/92→12/94							
2.0 E 16V	103 kW	2 l	02/93→01/96							
2.3 E	98 kW	2.3 l	09/91→12/94							
2.3 E	98 kW	2.3 l	07/92→01/96							
2.6	110 kW	2.6 l	07/92→01/96							
2.8	128 kW	2.8 l	09/91→12/94							
2.8	128 kW	2.8 l	09/91→01/96							
2.6	110 kW	2.6 l	07/92→12/94							KH00002 ProKIT
<b>AUDI - 90 B2 Sedan / 90 B3 Sedan (813, 814, 853, 893, 894, 8A2)</b>										<b>10/84→09/91</b>
1.6 TD	51 kW	1.6 l	10/85→01/87							KH00002 ProKIT
2.0	85 kW	2 l	07/88→09/91							KH00003 ProKIT
2.0 20 V	118 kW	2 l	08/89→07/91							
1.6 TD	59 kW	1.6 l	04/87→09/91		-> 04/88; VIN -> 89J373598					KH10194 ProKIT
2.2 E	100 kW	2.2 l	04/87→07/91							KH00002 ProKIT
										KH00003 ProKIT



											
<b>AUDI - 90 B2 Sedan / 90 B3 Sedan (813, 814, 853, 893, 894, 8A2)</b>										<b>10/84→09/91</b>	
2.0	83 kW	2 l	03/86→03/87		-> 12/86						<b>KH10194</b> ProKIT
2.0	85 kW	2 l	10/84→03/87		01/87 -> ; AC						
2.2	85 kW	2.2 l	01/85→03/87								<b>KH00002</b> ProKIT
2.2	100 kW	2.2 l	10/84→03/87								<b>KH00003</b> ProKIT
2.3 E	98 kW	2.3 l	04/87→09/91		-> 04/88; VIN -> 89J373598						<b>KH10194</b> ProKIT
2.3 E	100 kW	2.3 l	04/87→07/91								<b>KH00002</b> ProKIT
2.3 E 20V	123 kW	2.3 l	04/90→07/91								<b>KH00002</b> ProKIT
2.3 E 20V	125 kW	2.3 l	08/88→07/91								
<b>AUDI - 100 C1 Coupe / 100 C1 Saloon (817, 801, 803, 805, 807, 811, 813, F104)</b>										<b>11/68→12/76</b>	
1.6	63 kW	1.6 l	01/75→07/76								<b>KH00003</b> ProKIT
1.8	59 kW	1.8 l	11/68→11/71								
1.8	63 kW	1.8 l	09/71→07/74								
1.8	66 kW	1.8 l	11/68→11/71								
1.8	74 kW	1.8 l	10/70→07/76								
1.9	82 kW	1.9 l	08/71→12/76								
1.9	82 kW	1.9 l	09/71→07/76								
1.9	85 kW	1.9 l	07/70→07/71								
<b>AUDI - 100 C2 Avant / 100 C2 Saloon / 100 C3 Avant / 100 C3 Saloon / 100 C4 Avant / 100 C4 Saloon (435, 436, 431, 433, 434, 445, 446, 443, 444, 4A5, 4A2)</b>										<b>06/76→07/94</b>	
1.6	63 kW	1.6 l	08/76→07/82								<b>KH00002</b> ProKIT
1.6	63 kW	1.6 l	07/77→02/83								
1.8	55 kW	1.8 l	08/82→12/87								
1.8	65 kW	1.8 l	02/86→07/88								
1.8	65 kW	1.8 l	02/86→07/90								
1.8	66 kW	1.8 l	08/83→07/89								
1.8 Cat	66 kW	1.8 l	03/85→11/90								
1.9	74 kW	1.9 l	08/80→07/82								
1.9	74 kW	1.9 l	08/80→08/84								
1.9	74 kW	1.9 l	08/82→07/84								
1.9	74 kW	1.9 l	02/83→07/84								
2.0	74 kW	2 l	12/90→07/94								
2.0	83 kW	2 l	08/86→11/87								
2.0	83 kW	2 l	09/86→11/87								
2.0	85 kW	2 l	06/76→08/78								
2.0	85 kW	2 l	08/77→07/80								
2.0	85 kW	2 l	08/84→12/87								
2.0 Cat	85 kW	2 l	01/88→11/90								
2.0 D	51 kW	2 l	08/78→07/82								
2.0 D	51 kW	2 l	08/78→02/83								
2.0 D	51 kW	2 l	08/82→07/88								
2.0 D	51 kW	2 l	03/83→11/90								
2.0 D Turbo	64 kW	2 l	08/82→02/88								
2.0 D Turbo	74 kW	2 l	03/88→11/90								
2.0 E	74 kW	2 l	09/91→07/94								
2.0 E	85 kW	2 l	01/85→12/87								
2.0 E	85 kW	2 l	12/90→07/94								
2.0 E	85 kW	2 l	09/91→07/94								
2.0 E 16V	103 kW	2 l	01/92→07/94								
2.0 E 16V	103 kW	2 l	07/92→07/94								
2.0 E Cat	85 kW	2 l	01/88→11/90								
2.0 TD	64 kW	2 l	03/83→10/87								
2.0 TD	74 kW	2 l	03/88→11/90								
2.1	85 kW	2.1 l	07/77→02/83								
2.1	85 kW	2.1 l	10/77→07/82								
2.1	96 kW	2.1 l	08/82→07/84								
2.1	100 kW	2.1 l	03/77→07/82								
2.1	100 kW	2.1 l	07/77→02/83								
2.1	100 kW	2.1 l	08/82→07/84								
2.2	79 kW	2.2 l	08/82→07/84								
2.2	85 kW	2.2 l	10/84→09/86								
2.2	96 kW	2.2 l	08/82→07/84								
2.2	101 kW	2.2 l	08/84→12/88								
2.2 Cat	101 kW	2.2 l	06/89→11/90								
2.2 Turbo	121 kW	2.2 l	08/86→11/90								
2.3	98 kW	2.3 l	03/90→11/90								
2.3	100 kW	2.3 l	08/86→11/90								
2.3 E	98 kW	2.3 l	01/90→11/90								
2.3 E	98 kW	2.3 l	12/90→07/94								
2.3 E	98 kW	2.3 l	09/91→07/94								
2.3 E	100 kW	2.3 l	10/86→11/90								
2.4 D	60 kW	2.4 l	08/89→11/90								
2.4 D	60 kW	2.4 l	08/89→07/91								
2.4 D	60 kW	2.4 l	12/90→07/94								

     				
<b>AUDI - 100 C2 Avant / 100 C2 Saloon / 100 C3 Avant / 100 C3 Saloon / 100 C4 Avant / 100 C4 Saloon (435, 436, 431, 433, 434, 445, 446, 443, 444, 4A5, 4A2)</b>				
2.5 TDI	85 kW	2.5 l	12/90→07/94	 KH00002 ProKIT
2.5 TDI	88 kW	2.5 l	01/90→11/90	
2.6	102 kW	2.6 l	07/93→07/94	
2.6	110 kW	2.6 l	03/92→07/94	
2.8 E	128 kW	2.8 l	12/90→07/94	
2.8 E	128 kW	2.8 l	09/91→07/94	
<b>AUDI - 200 C2 Saloon / 200 C3 Avant / 200 C3 Saloon (437, 438, 447, 448)</b>				
2.1 5E	100 kW	2.1 l	10/79→09/82	 KH00002 ProKIT
2.1 5E	100 kW	2.1 l	08/83→07/84	
2.1 5T	125 kW	2.1 l	10/79→08/82	
2.1 Turbo	134 kW	2.1 l	08/83→01/88	
2.2	101 kW	2.2 l	08/84→07/85	
2.2 Turbo	121 kW	2.2 l	08/85→09/91	
2.2 Turbo	140 kW	2.2 l	02/88→12/90	
2.2 Turbo	147 kW	2.2 l	02/88→12/90	
2.3	100 kW	2.3 l	11/86→09/91	
<b>AUDI - A1 / A1 Sportback (8X1, 8XK, 8XA, 8XF)</b>				
1.0 TFSI	60 kW	1 l	01/16→10/18	 PR 1LJ KH30045 ProKIT
S1 quattro	170 kW	2 l	03/14→10/18	
1.0 TFSI	70 kW	1 l	03/15→10/18	 PR 1LJ KH30045 ProKIT
1.4 TDI	66 kW	1.4 l	11/14→10/18	 KH20009 ProKIT
1.4 TFSI	92 kW	1.4 l	11/14→10/18	
1.4 TFSI	110 kW	1.4 l	11/14→10/18	
1.6 TDI	85 kW	1.6 l	11/14→10/18	
1.8 TFSI	141 kW	1.8 l	02/15→10/18	
1.2 TFSI	63 kW	1.2 l	05/10→04/15	 PR 1LJ KH30045 ProKIT
1.2 TFSI	63 kW	1.2 l	01/12→04/15	 PR 1LJ KH30002 ProKIT
1.4 TFSI	90 kW	1.4 l	05/10→04/15	 KH20009 ProKIT
1.4 TFSI	90 kW	1.4 l	11/11→04/15	
1.4 TFSI	103 kW	1.4 l	04/12→04/15	
1.4 TFSI	136 kW	1.4 l	01/11→04/15	
1.4 TFSI	136 kW	1.4 l	11/11→04/15	
1.6 TDI	66 kW	1.6 l	03/11→04/15	
1.6 TDI	66 kW	1.6 l	11/11→04/15	
1.6 TDI	77 kW	1.6 l	05/10→04/15	
1.6 TDI	77 kW	1.6 l	11/11→04/15	
2.0 TDI	100 kW	2 l	05/12→04/15	
2.0 TDI	105 kW	2 l	09/11→04/15	
2.0 TFSI quattro	188 kW	2 l	03/12→11/12	 PR 1LJ KH30045 ProKIT
				 PR 1LJ KH30002 ProKIT
<b>AUDI - A1 Sportback (GBA)</b>				
25 TFSI	70 kW	1 l	11/18→	 PR 1ZG KH30045 ProKIT
30 TFSI	85 kW	1 l	07/18→	
35 TFSI	110 kW	1.5 l	09/18→	
40 TFSI	147 kW	2 l	09/18→	
<b>AUDI - A2 (8Z0)</b>				
1.2 TDI	45 kW	1.2 l	03/01→08/05	 KH20167 ProKIT
1.4	55 kW	1.4 l	02/00→08/05	 KH30045 ProKIT
1.4 TDI	55 kW	1.4 l	02/00→08/05	 KH20009 ProKIT
1.4 TDI	66 kW	1.4 l	11/03→08/05	
1.6 FSI	81 kW	1.6 l	05/02→08/05	
<b>AUDI - A3 (8L1)</b>				
1.6	74 kW	1.6 l	09/96→05/03	 KH10001 ProKIT
1.6	75 kW	1.6 l	08/00→05/03	
1.8	92 kW	1.8 l	09/96→05/03	 ABS KH20010 ProKIT
1.8 T	110 kW	1.8 l	12/96→05/03	
1.8 T	132 kW	1.8 l	12/98→05/03	
1.9 TDI	66 kW	1.9 l	09/96→07/01	
1.9 TDI	74 kW	1.9 l	10/00→05/03	
1.9 TDI	81 kW	1.9 l	08/97→07/01	
1.9 TDI	96 kW	1.9 l	08/00→05/03	
1.8 T quattro	110 kW	1.8 l	12/96→05/03	 KH10001 ProKIT
1.8 T quattro	132 kW	1.8 l	10/98→05/03	
1.9 TDI quattro	96 kW	1.9 l	08/00→05/03	
S3 quattro	154 kW	1.8 l	03/99→04/02	 KH10001 ProKIT
			 VIN 8L-1-180 001 ->  AMK KH10117 ProKIT	
S3 quattro	165 kW	1.8 l	10/01→05/03	 KH10001 ProKIT
			 VIN 8L-1-180 001 -> KH10117 ProKIT	





**AUDI - A3 (8P1)**

**05/03→08/12**

1.2 TSI	77 kW	1.2 l	04/10→08/12	; Number of mounting bores: 4	KH30002 ProKIT
1.4 TFSI	92 kW	1.4 l	09/07→08/12	; Number of mounting bores: 3	KH30048 ProKIT
1.6	75 kW	1.6 l	05/03→08/12	; VIN -> 8P-4-162 000; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.6 E-Power	75 kW	1.6 l	01/11→08/12	; VIN 8P-4-162 001 ->; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.6 FSI	85 kW	1.6 l	08/03→09/07		
1.6 TDI	66 kW	1.6 l	05/09→08/12		
1.6 TDI	77 kW	1.6 l	05/09→08/12		
1.8 T	110 kW	1.8 l	08/06→08/12		
1.8 TFSI	118 kW	1.8 l	11/06→08/12		
1.9 TDI	77 kW	1.9 l	05/03→05/10		
2.0 FSI	110 kW	2 l	05/03→06/08		
2.0 TDI	100 kW	2 l	05/03→08/12		
2.0 TDI	103 kW	2 l	06/05→06/08		
2.0 TDI	120 kW	2 l	06/06→06/08		
2.0 TDI	125 kW	2 l	03/06→08/12		
2.0 TDI 16V	103 kW	2 l	05/03→08/12		
2.0 TFSI	147 kW	2 l	09/04→08/12		
1.8 TFSI quattro	118 kW	1.8 l	07/08→08/12	;	KH30002 ProKIT
2.0 TDI 16V quattro	103 kW	2 l	08/04→08/12		
2.0 TDI quattro	100 kW	2 l	05/03→06/08		
2.0 TDI quattro	103 kW	2 l	01/06→06/08		
2.0 TDI quattro	125 kW	2 l	03/06→08/12		
2.0 TFSI quattro	147 kW	2 l	09/04→08/12		
3.2 V6 quattro	184 kW	3.2 l	07/03→05/09		
S3 quattro	188 kW	2 l	02/07→08/12		
S3 quattro	195 kW	2 l	11/06→08/12		

**AUDI - A3 (8V1, 8VK)**

**04/12→10/20**

1.0 TFSI	85 kW	1 l	07/16→12/17	; PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
1.2 TFSI	77 kW	1.2 l	02/13→05/15	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.2 TFSI	81 kW	1.2 l	05/14→08/16		KH20003 ProKIT
1.4 TFSI	90 kW	1.4 l	04/12→05/14		
1.4 TFSI	92 kW	1.4 l	05/14→08/16		
1.4 TFSI	103 kW	1.4 l	03/13→08/16		
1.4 TSI	110 kW	1.4 l	05/14→12/17		
1.5 TFSI	110 kW	1.5 l	05/17→12/17		
1.6 TDI	77 kW	1.6 l	10/12→05/15		
1.6 TDI	81 kW	1.6 l	09/13→12/17		
1.6 TDI	85 kW	1.6 l	02/17→10/20		
1.8 TFSI	132 kW	1.8 l	04/12→08/16		
2.0 TDI	81 kW	2 l	01/13→08/16		
2.0 TDI	100 kW	2 l	05/13→08/16		
2.0 TDI	105 kW	2 l	09/12→10/20		
2.0 TDI	110 kW	2 l	04/12→12/17		
2.0 TDI	135 kW	2 l	05/13→08/16		
2.0 TFSI	140 kW	2 l	05/16→12/17		
1.8 TFSI quattro	132 kW	1.8 l	08/12→08/16	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
2.0 TDI quattro	110 kW	2 l	10/12→12/17		
2.0 TDI quattro	135 kW	2 l	12/12→12/17		
2.0 TFSI quattro	140 kW	2 l	05/16→12/17	; PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
S3 quattro	206 kW	2 l	02/13→07/14		
S3 quattro	210 kW	2 l	05/14→08/16		
S3 quattro	213 kW	2 l	07/16→12/17		
S3 quattro	221 kW	2 l	11/12→08/16		
S3 quattro	228 kW	2 l	06/16→12/17		

**AUDI - A3 Convertible (8P7)**

**04/08→05/13**

1.2 TFSI	77 kW	1.2 l	03/10→05/13	; Number of mounting bores: 4	KH30002 ProKIT
1.4 TFSI	92 kW	1.4 l	02/11→05/13	; Number of mounting bores: 3	KH30048 ProKIT
1.6	75 kW	1.6 l	09/08→05/10	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.6 TDI	77 kW	1.6 l	05/09→05/13		
1.8 TFSI	118 kW	1.8 l	04/08→05/13		
1.9 TDI	77 kW	1.9 l	04/08→10/09		
2.0 TDI	100 kW	2 l	04/08→05/13		
2.0 TDI	103 kW	2 l	04/08→05/13		
2.0 TFSI	147 kW	2 l	04/08→05/13		

**AUDI - A3 Convertible / A3 Limousine (8V7, 8VE, 8VS, 8VM)**

**05/13→10/20**

1.0 TFSI	85 kW	1 l	07/16→10/20	; PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
1.2 TFSI	77 kW	1.2 l	10/13→	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.2 TFSI	81 kW	1.2 l	05/14→		KH20003 ProKIT
1.4 TFSI	85 kW	1.4 l	02/16→10/20		
1.4 TFSI	90 kW	1.4 l	09/13→10/20		
1.4 TFSI	92 kW	1.4 l	09/13→		
1.4 TFSI	92 kW	1.4 l	02/14→		
1.4 TFSI	103 kW	1.4 l	05/13→		
1.4 TFSI	103 kW	1.4 l	10/13→		
1.4 TSI	110 kW	1.4 l	05/14→10/20		
1.5 TFSI	110 kW	1.5 l	05/17→10/18		
1.6 TDI	77 kW	1.6 l	09/13→		



AUDI - A3 Convertible / A3 Limousine (8V7, 8VE, 8VS, 8VM)				05/13→10/20	
1.6 TDI	81 kW	1.6 l	02/14→10/20	PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
1.6 TDI	81 kW	1.6 l	05/14→10/20		
1.6 TDI	85 kW	1.6 l	03/17→10/20	PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.6 TDI	85 kW	1.6 l	04/17→10/20		
1.8 TFSI	125 kW	1.8 l	11/13→10/20	PR 1ZE, 1ZF, 1ZP	KH20003 ProKIT
1.8 TFSI	125 kW	1.8 l	05/14→10/20		
1.8 TFSI	132 kW	1.8 l	05/13→		
1.8 TFSI	132 kW	1.8 l	10/13→07/16		
2.0 TDI	81 kW	2 l	05/13→10/20		
2.0 TDI	100 kW	2 l	09/13→		
2.0 TDI	100 kW	2 l	10/13→		
2.0 TDI	105 kW	2 l	10/13→10/20		
2.0 TDI	110 kW	2 l	05/13→10/20		
2.0 TDI	110 kW	2 l	10/13→10/20		
2.0 TDI	135 kW	2 l	05/14→		
2.0 TDI	135 kW	2 l	05/14→10/20		
2.0 TFSI	140 kW	2 l	05/16→10/20		
2.0 TFSI	162 kW	2 l	11/15→10/20		
30 TDI	85 kW	1.6 l	07/18→10/20		
30 TFSI	85 kW	1 l	07/18→10/20		
35 TDI	110 kW	2 l	07/18→10/20		
35 TFSI	110 kW	1.5 l	10/18→10/20		
40 TFSI	140 kW	2 l	07/18→10/20		
40 TFSI	140 kW	2 l	11/18→10/20		
1.6 TDI quattro	81 kW	1.6 l	05/15→	PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.8 TFSI quattro	132 kW	1.8 l	11/13→		
1.8 TFSI quattro	132 kW	1.8 l	03/14→	PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
2.0 TDI quattro	110 kW	2 l	10/13→10/20		
2.0 TDI quattro	110 kW	2 l	03/14→10/20		
2.0 TDI quattro	135 kW	2 l	05/14→07/18		
2.0 TDI quattro	135 kW	2 l	05/14→10/20		
2.0 TFSI quattro	140 kW	2 l	05/16→10/20		
2.0 TFSI quattro	162 kW	2 l	05/14→10/20		
40 TDI quattro	135 kW	2 l	07/18→07/19		
40 TFSI quattro	140 kW	2 l	07/18→10/20		
S3 quattro	206 kW	2 l	10/13→		
S3 quattro	210 kW	2 l	03/14→		
S3 quattro	210 kW	2 l	05/14→		
S3 quattro	213 kW	2 l	07/16→10/20		
S3 quattro	213 kW	2 l	08/16→10/20		
S3 quattro	215 kW	2 l	05/14→10/20		
S3 quattro	221 kW	2 l	10/13→10/20		
S3 quattro	221 kW	2 l	04/14→10/20		
S3 quattro	228 kW	2 l	06/16→10/20		
S3 quattro	228 kW	2 l	07/16→10/20		
2.0 TFSI quattro	162 kW	2 l	11/13→10/20	PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
RS3 quattro	294 kW	2.5 l	04/17→10/20		
2.0 TFSI quattro	170 kW	2 l	07/18→10/20		KH30048 ProKIT
40 TFSI quattro	140 kW	2 l	11/18→10/20		
AUDI - A3 Limousine (8YS)				04/20→	
30 TDI	85 kW	2 l	06/20→	Centering Diameter [mm]: 85	KH30049 ProKIT
30 TFSI	81 kW	1 l	06/20→		
30 TFSI Mild Hybrid	81 kW	1 l	06/20→		
35 TDI	110 kW	2 l	04/20→		
35 TFSI	110 kW	1.5 l	04/20→		
35 TFSI Mild Hybrid	110 kW	1.5 l	04/20→		
40 TDI quattro	147 kW	2 l	12/20→	Centering Diameter [mm]: 85	KH30049 ProKIT
S3 quattro	228 kW	2 l	06/20→		
AUDI - A3 Sportback (8PA)				09/04→03/13	
1.2 TSI	77 kW	1.2 l	04/10→03/13	Number of mounting bores: 4	KH30002 ProKIT
1.4 TFSI	92 kW	1.4 l	09/07→03/13		
1.6	75 kW	1.6 l	09/04→03/13	Number of mounting bores: 3	KH30048 ProKIT
1.6 E-Power	75 kW	1.6 l	01/11→03/13		
1.6 FSI	85 kW	1.6 l	09/04→09/07	VIN -> 8P-4-162 000; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.6 TDI	66 kW	1.6 l	05/09→03/13		
1.6 TDI	77 kW	1.6 l	05/09→03/13	VIN 8P-4-162 001 ->; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.8 TFSI	118 kW	1.8 l	11/06→03/13		
1.9 TDI	77 kW	1.9 l	09/04→05/10		
2.0 FSI	110 kW	2 l	09/04→06/08		
2.0 TDI	100 kW	2 l	09/04→03/13		
2.0 TDI	103 kW	2 l	06/05→06/08		
2.0 TDI	120 kW	2 l	06/06→06/08		
2.0 TDI	125 kW	2 l	03/06→03/13		
2.0 TDI 16V	103 kW	2 l	09/04→03/13		
2.0 TFSI	147 kW	2 l	09/04→03/13		





**AUDI - A3 Sportback (8PA)**

09/04→03/13

1.8 FSI	110 kW	1.8 l	08/06→06/08	; Number of mounting bores: 4	KH30002 ProKIT
2.0 TDI	104 kW	2 l	01/10→03/13	; Number of mounting bores: 3	KH30048 ProKIT
				; Inner diameter 1 [mm]: 30	KH20003 ProKIT
				; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.8 TFSI quattro	118 kW	1.8 l	07/08→03/13	; Number of mounting bores: 4	KH30002 ProKIT
2.0 TDI 16V quattro	103 kW	2 l	11/05→03/13		
2.0 TDI quattro	103 kW	2 l	01/06→06/08		
2.0 TDI quattro	125 kW	2 l	03/06→03/13		
2.0 TFSI quattro	147 kW	2 l	09/04→03/13		
3.2 V6 quattro	184 kW	3.2 l	09/04→05/09		
RS3 quattro	250 kW	2.5 l	01/11→12/12		
S3 quattro	188 kW	2 l	07/08→03/13		
S3 quattro	195 kW	2 l	06/08→03/13		

**AUDI - A3 Sportback (8VA, 8VF)**

09/12→

1.0 TFSI	85 kW	1 l	07/16→10/20	; PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
1.2 TFSI	77 kW	1.2 l	05/13→	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.2 TFSI	81 kW	1.2 l	05/14→08/16		KH20003 ProKIT
1.4 TFSI	90 kW	1.4 l	09/12→10/20		
1.4 TFSI	92 kW	1.4 l	05/14→08/16		
1.4 TFSI	103 kW	1.4 l	03/13→		
1.4 TFSI g-tron	81 kW	1.4 l	11/13→10/20		
1.4 TFSI	110 kW	1.4 l	05/14→10/20		
1.5 TFSI	110 kW	1.5 l	05/17→10/18		
1.6 TDI	77 kW	1.6 l	10/12→		
1.6 TDI	81 kW	1.6 l	09/13→10/20		
1.6 TDI	85 kW	1.6 l	02/17→10/20		
1.8 TFSI	132 kW	1.8 l	09/12→		
2.0 TDI	81 kW	2 l	05/13→10/20		
2.0 TDI	100 kW	2 l	05/13→08/16		
2.0 TDI	105 kW	2 l	03/13→10/20		
2.0 TDI	110 kW	2 l	09/12→10/20		
2.0 TDI	135 kW	2 l	05/13→08/16		
2.0 TFSI	140 kW	2 l	05/16→10/20		
30 g-tron	96 kW	1.5 l	11/18→10/20		
30 TDI	85 kW	1.6 l	07/18→10/20		
30 TFSI	85 kW	1 l	07/18→10/20		
35 TDI	110 kW	2 l	07/18→10/20		
35 TFSI	110 kW	1.5 l	10/18→10/20		
40 TFSI	140 kW	2 l	07/18→10/20		
1.6 TDI quattro	81 kW	1.6 l	05/15→08/16	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.8 TFSI quattro	132 kW	1.8 l	05/13→		
2.0 TDI quattro	110 kW	2 l	02/13→10/20	; PR 1LC, 1LJ, 1ZA, 1ZD	KH30014 ProKIT
2.0 TDI quattro	135 kW	2 l	05/13→07/18		
2.0 TFSI quattro	140 kW	2 l	05/16→10/20		
40 TDI quattro	135 kW	2 l	07/18→10/20		
40 TFSI quattro	140 kW	2 l	07/18→10/20		
S3 quattro	206 kW	2 l	05/13→		
S3 quattro	210 kW	2 l	05/14→08/16		
S3 quattro	213 kW	2 l	07/16→10/20		
S3 quattro	221 kW	2 l	11/12→10/20		
S3 quattro	228 kW	2 l	06/16→10/20		
RS3 quattro	270 kW	2.5 l	03/15→	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
RS3 quattro	294 kW	2.5 l	04/17→10/20		

**AUDI - A3 Sportback (8YA)**

11/19→



30 g-tron	96 kW	1.5 l	07/20→	; Centering Diameter [mm]: 85	KH30049 ProKIT
30 TDI	85 kW	2 l	11/19→		
30 TFSI	81 kW	1 l	06/20→		
30 TFSI Mild Hybrid	81 kW	1 l	06/20→		
35 TDI	110 kW	2 l	11/19→		
35 TFSI	110 kW	1.5 l	11/19→		
35 TFSI Mild Hybrid	110 kW	1.5 l	04/20→		
40 TFSIe	110 kW	1.4 l	06/20→		
40 TDI quattro	147 kW	2 l	12/20→	; Centering Diameter [mm]: 85	KH30049 ProKIT
S3 quattro	228 kW	2 l	06/20→		















































**AUDI - A4 Allroad B8 Avant (8KH)** 04/09→05/16

2.0 TDI quattro	100 kW	2 l	09/09→05/16	 	KH20008 ProKIT
2.0 TDI quattro	105 kW	2 l	09/09→05/16		
2.0 TDI quattro	110 kW	2 l	05/13→05/16		
2.0 TDI quattro	120 kW	2 l	04/09→05/16		
2.0 TDI quattro	125 kW	2 l	04/09→05/16		
2.0 TDI quattro	130 kW	2 l	11/11→05/16		
2.0 TDI quattro	140 kW	2 l	09/13→05/16		
2.0 TFSI quattro	155 kW	2 l	04/09→05/16		
2.0 TFSI quattro	162 kW	2 l	05/13→05/16		
2.0 TFSI quattro	165 kW	2 l	05/13→05/16		
3.0 TDI quattro	176 kW	3 l	04/09→01/12		
3.0 TDI quattro	180 kW	3 l	01/12→05/16		

**AUDI - A4 B5 Avant / A4 B5 Sedan (8D5, 8D2)** 11/94→09/01

1.6	74 kW	1.6 l	11/94→10/00		KH10066 ProKIT
1.6	74 kW	1.6 l	11/94→09/01		
1.6	75 kW	1.6 l	07/00→11/00		KH10069 ProKIT
1.6	75 kW	1.6 l	07/00→09/01	 VIN -> 8G-V-152 676	KH00002 ProKIT
1.8	85 kW	1.8 l	04/95→11/00	 VIN 8D-V-152 677 ->	KH00038 ProKIT
1.8	85 kW	1.8 l	07/95→09/01		
1.8	92 kW	1.8 l	11/94→11/00		
1.8	92 kW	1.8 l	02/96→09/01		
1.8 T	110 kW	1.8 l	01/95→11/00		
1.8 T	110 kW	1.8 l	03/96→09/01		
1.8 T	132 kW	1.8 l	12/97→11/00		
1.8 T	132 kW	1.8 l	12/97→09/01		
1.9 Hybrid	66 kW	1.9 l	03/98→06/00		
1.9 TDI	55 kW	1.9 l	12/95→11/00		
1.9 TDI	55 kW	1.9 l	03/96→09/01		
1.9 TDI	66 kW	1.9 l	01/95→11/00		
1.9 TDI	66 kW	1.9 l	02/96→09/01		
1.9 TDI	81 kW	1.9 l	10/95→11/00		
1.9 TDI	81 kW	1.9 l	02/96→09/01		
1.9 TDI	85 kW	1.9 l	03/00→11/00		
1.9 TDI	85 kW	1.9 l	03/00→09/01		
2.4	120 kW	2.4 l	08/97→11/00		
2.4	120 kW	2.4 l	08/97→09/01		
2.5 TDI	110 kW	2.5 l	09/97→11/00		
2.5 TDI	110 kW	2.5 l	09/97→09/01		
2.8	140 kW	2.8 l	09/99→10/00		
1.8 quattro	85 kW	1.8 l	07/95→11/00		KH10066 ProKIT
1.8 quattro	85 kW	1.8 l	07/95→09/01		KH10069 ProKIT
1.8 quattro	92 kW	1.8 l	01/95→11/00		
1.8 quattro	92 kW	1.8 l	01/96→09/01		
1.8 T quattro	110 kW	1.8 l	01/95→11/00		
1.8 T quattro	110 kW	1.8 l	01/96→09/01		
1.8 T quattro	132 kW	1.8 l	12/97→11/00		
1.8 T quattro	132 kW	1.8 l	12/97→09/01		
1.9 TDI quattro	81 kW	1.9 l	09/96→11/00		
1.9 TDI quattro	81 kW	1.9 l	09/96→09/01		
1.9 TDI quattro	85 kW	1.9 l	03/00→11/00		
1.9 TDI quattro	85 kW	1.9 l	03/00→09/01		
2.4 quattro	120 kW	2.4 l	08/97→11/00		
2.4 quattro	120 kW	2.4 l	08/97→09/01		
2.5 TDI quattro	110 kW	2.5 l	09/97→11/00		
2.5 TDI quattro	110 kW	2.5 l	09/97→09/01		
2.8 quattro	140 kW	2.8 l	03/99→09/00		
2.8 quattro	140 kW	2.8 l	09/99→10/00		
2.4	121 kW	2.4 l	03/97→11/00		KH10066 ProKIT
2.4	121 kW	2.4 l	03/97→09/01	 VIN 8D-T-160 956 ->	KH10069 ProKIT
2.6	110 kW	2.6 l	01/95→11/00		
2.6	110 kW	2.6 l	02/96→09/01	 VIN -> 8G-V-152 676	KH00002 ProKIT
2.8	128 kW	2.8 l	09/95→07/97	 VIN 8D-V-152 677 ->	KH00038 ProKIT
2.8	142 kW	2.8 l	10/96→11/00		
2.8	142 kW	2.8 l	10/96→09/01		
2.4 quattro	121 kW	2.4 l	03/97→11/00		KH10066 ProKIT
2.4 quattro	121 kW	2.4 l	03/97→09/01	 VIN 8D-T-160 956 ->	KH10069 ProKIT
2.6 quattro	110 kW	2.6 l	01/95→11/00		
2.6 quattro	110 kW	2.6 l	01/96→09/01		
2.8 quattro	128 kW	2.8 l	01/95→07/97		
2.8 quattro	128 kW	2.8 l	01/96→09/96		
2.8 quattro	142 kW	2.8 l	10/96→08/01		
2.8 quattro	142 kW	2.8 l	10/96→09/01		
2.8	128 kW	2.8 l	03/96→09/96		KH10066 ProKIT
				 VIN 8D-T-160 956 ->	KH10069 ProKIT
				 VIN 8D-V-152 677 ->	KH00038 ProKIT



     					
AUDI - A4 B5 Avant / A4 B5 Sedan (8D5, 8D2)				11/94→09/01	
2.8	140 kW	2.8 l	03/99→09/00		KH10066 ProKIT
					KH10069 ProKIT
				 VIN 8D-V-152 677 ->	KH00038 ProKIT
RS4 quattro	280 kW	2.7 l	05/00→09/01		KH10066 ProKIT
					KH20032 ProKIT
S4 quattro	195 kW	2.7 l	09/97→09/01		KH10066 ProKIT
AUDI - A4 B6 / A4 B6 Avant / A4 B6 Convertible / A4 B7 Avant / A4 B7 Con- vertible / A4 B7 Sedan (8E2, 8E5, 8H7, 8ED, 8HE, 8EC)				11/00→03/09	
1.6	75 kW	1.6 l	11/00→12/04		KH20032 ProKIT
1.6	75 kW	1.6 l	09/01→12/04		KH20040 ProKIT
1.6	75 kW	1.6 l	11/04→06/08		
1.8 T	110 kW	1.8 l	11/00→07/02		
1.8 T	110 kW	1.8 l	09/01→07/02		
1.8 T	120 kW	1.8 l	07/02→12/04		
1.8 T	120 kW	1.8 l	07/02→12/05		
1.8 T	120 kW	1.8 l	11/04→06/08		
1.8 T	140 kW	1.8 l	11/02→12/04		
1.9 TDI	74 kW	1.9 l	05/01→12/04		
1.9 TDI	74 kW	1.9 l	11/01→12/04		
1.9 TDI	85 kW	1.9 l	06/04→12/04		
1.9 TDI	85 kW	1.9 l	11/04→06/08		
1.9 TDI	96 kW	1.9 l	11/00→12/04		
1.9 TDI	96 kW	1.9 l	09/01→12/04		
2.0	96 kW	2 l	11/00→12/04		
2.0	96 kW	2 l	09/01→12/04		
2.0	96 kW	2 l	09/04→12/05		
2.0	96 kW	2 l	11/04→06/08		
2.0 FSI	110 kW	2 l	07/02→12/04		
2.0 TDI	100 kW	2 l	11/04→06/08		
2.0 TDI	100 kW	2 l	01/06→03/09		
2.0 TDI	103 kW	2 l	11/04→06/08		
2.0 TDI	103 kW	2 l	01/06→03/09		
2.0 TDI	125 kW	2 l	06/06→06/08		
2.0 TDI 16V	103 kW	2 l	11/04→06/08		
2.0 TFSI	125 kW	2 l	10/06→06/08		
2.0 TFSI	147 kW	2 l	11/04→06/08		
2.0 TFSI	162 kW	2 l	06/05→06/08		
2.0 TFSI 16V	147 kW	2 l	01/06→03/09		
2.4	120 kW	2.4 l	09/01→12/04		
2.4	120 kW	2.4 l	04/02→12/05		
2.4	125 kW	2.4 l	09/01→12/04		
2.4	125 kW	2.4 l	04/02→12/05		
2.5 TDI	114 kW	2.5 l	08/01→07/02		
2.5 TDI	114 kW	2.5 l	09/01→07/02		
2.5 TDI	120 kW	2.5 l	07/02→12/04		
2.5 TDI	120 kW	2.5 l	08/02→12/05		
2.5 TDI	120 kW	2.5 l	11/04→05/06		
2.7 TDi	120 kW	2.7 l	11/05→03/08		
2.7 TDI	120 kW	2.7 l	11/05→06/08		
2.7 TDI	132 kW	2.7 l	01/06→06/08		
2.7 TDI	132 kW	2.7 l	06/06→03/09		
3.0	160 kW	3 l	04/01→12/04		
3.0	160 kW	3 l	11/04→05/06		
3.0	162 kW	3 l	11/00→12/04		
3.0	162 kW	3 l	09/01→12/04		
3.0	162 kW	3 l	04/02→12/05		
3.2 FSI	188 kW	3.2 l	01/05→06/08		
3.2 FSI	188 kW	3.2 l	01/06→03/09		
1.8 T	125 kW	1.8 l	07/01→12/04		KH20032 ProKIT
1.8 T	125 kW	1.8 l	10/02→10/05		
2.0 TDI	89 kW	2 l	09/05→09/06		
2.0 TDI	93 kW	2 l	11/05→11/06		
2.0 TDI	120 kW	2 l	06/06→06/08		
3.0	160 kW	3 l	04/02→12/05		
3.0	160 kW	3 l	11/04→05/06		
1.8 T quattro	110 kW	1.8 l	11/00→07/02		KH20032 ProKIT
				 Code: 1BD	
				 12/00 -> 06/02; for vehicles without track widening	KH10136 ProKIT
1.8 T quattro	110 kW	1.8 l	09/01→07/02		KH20032 ProKIT
				 Code: 1BD	
				 -> 06/02; for vehicles without track widening	KH10136 ProKIT
1.8 T quattro	120 kW	1.8 l	07/02→12/04		KH20032 ProKIT
1.8 T quattro	120 kW	1.8 l	11/04→06/08		
1.8 T quattro	140 kW	1.8 l	11/02→12/04	 for vehicles without track widening	KH10136 ProKIT



**AUDI - A4 B6 / A4 B6 Avant / A4 B6 Convertible / A4 B7 Avant / A4 B7 Con- 11/00→03/09**  
**vertible / A4 B7 Sedan (8E2, 8E5, 8H7, 8ED, 8HE, 8EC)**

1.9 TDI quattro	96 kW	1.9 l	11/01→12/04		KH20032 ProKIT
2.0 TDI quattro	103 kW	2 l	01/06→06/08		
2.0 TDI quattro	125 kW	2 l	06/06→06/08	; Code: 1BD	
2.0 TFSI quattro	147 kW	2 l	11/04→06/08	; for vehicles without track widening	KH10136 ProKIT
2.0 TFSI quattro	162 kW	2 l	06/05→06/08		
2.5 TDI quattro	132 kW	2.5 l	09/01→12/04		
3.0 quattro	160 kW	3 l	04/01→12/04		
3.0 quattro	162 kW	3 l	09/01→12/04		
3.0 TDI quattro	150 kW	3 l	01/06→03/09		
3.0 TDI quattro	171 kW	3 l	01/06→06/08		
3.0 TDI quattro	171 kW	3 l	01/06→03/09		
3.2 FSI quattro	188 kW	3.2 l	01/05→06/08		
3.2 FSI quattro	188 kW	3.2 l	01/06→03/09		
1.8 T quattro	120 kW	1.8 l	05/03→12/05		KH20032 ProKIT
3.0 quattro	162 kW	3 l	05/03→12/05	; Code: 1BD	
				; 06/03 ->	KH10136 ProKIT
1.8 T quattro	125 kW	1.8 l	07/01→12/04		KH20032 ProKIT
1.8 T quattro	125 kW	1.8 l	09/01→12/04	; Code: 1BD	
2.0 TDI quattro	120 kW	2 l	06/06→06/08		
2.0 TFSI quattro	162 kW	2 l	06/05→06/08		KH20032 ProKIT
				; Code: 1BD	
				; 02/06 ->; for vehicles without track widening	KH10136 ProKIT
2.5 TDI quattro	132 kW	2.5 l	11/00→12/04		KH20032 ProKIT
3.0 quattro	162 kW	3 l	11/00→12/04	; Code: 1BD	
				; 12/00 ->; for vehicles without track widening	KH10136 ProKIT
3.0 quattro	160 kW	3 l	04/01→12/04		KH20032 ProKIT
				; Code: 1BD	
				; 09/01 ->; for vehicles without track widening	KH10136 ProKIT
3.0 quattro	160 kW	3 l	11/04→07/06		KH20032 ProKIT
3.0 TDI quattro	150 kW	3 l	11/04→06/08	; Code: 1BD	
				; -> 05/06; for vehicles without track widening	KH10136 ProKIT
S4 quattro	253 kW	4.2 l	03/03→12/04		KH10136 ProKIT
S4 quattro	253 kW	4.2 l	03/04→12/05		
S4 quattro	253 kW	4.2 l	11/04→06/08		

**AUDI - A4 B8 / A4 B8 Avant (8K2, 8K5) 11/07→12/15**

1.8 TFSI	88 kW	1.8 l	01/08→12/15		KH20008 ProKIT
1.8 TFSI	118 kW	1.8 l	11/07→03/12		KH20064 ProKIT
1.8 TFSI	125 kW	1.8 l	11/11→12/15		
2.0 TDI	88 kW	2 l	06/08→12/15		
2.0 TDI	100 kW	2 l	11/07→12/15		
2.0 TDI	100 kW	2 l	04/08→12/15		
2.0 TDI	105 kW	2 l	11/07→12/15		
2.0 TDI	105 kW	2 l	04/08→12/15		
2.0 TDI	110 kW	2 l	05/13→12/15		
2.0 TDI	120 kW	2 l	08/08→12/15		
2.0 TDI	125 kW	2 l	01/08→03/12		
2.0 TDI	125 kW	2 l	04/08→03/12		
2.0 TDI	130 kW	2 l	11/11→12/15		
2.0 TDI	140 kW	2 l	09/13→12/15		
2.0 TFSI	132 kW	2 l	06/08→12/15		
2.0 TFSI	155 kW	2 l	06/08→05/13		
2.0 TFSI	165 kW	2 l	05/13→12/15		
2.0 TFSI flexible fuel	132 kW	2 l	11/09→12/15		
2.7 TDI	120 kW	2.7 l	06/08→03/12		
2.7 TDI	140 kW	2.7 l	11/07→03/12		
2.7 TDI	140 kW	2.7 l	04/08→03/12		
3.0 TDI	150 kW	3 l	11/11→12/15		
3.2 FSI	195 kW	3.2 l	09/08→03/12		
1.8 TFSI	88 kW	1.8 l	04/08→12/15		KH20008 ProKIT
				; 06/08 ->	KH20064 ProKIT
1.8 TFSI quattro	118 kW	1.8 l	09/08→03/12		KH20008 ProKIT
1.8 TFSI quattro	125 kW	1.8 l	11/11→12/15		
2.0 TDI quattro	105 kW	2 l	04/08→12/15		
2.0 TDI quattro	105 kW	2 l	11/08→12/15		
2.0 TDI quattro	110 kW	2 l	05/13→12/15		
2.0 TDI quattro	125 kW	2 l	01/08→03/12		
2.0 TDI quattro	125 kW	2 l	08/08→03/12		
2.0 TDI quattro	130 kW	2 l	11/11→12/15		
2.0 TDI quattro	140 kW	2 l	09/13→12/15		
2.0 TFSI flexible fuel quattro	132 kW	2 l	11/09→12/15		
2.0 TFSI quattro	132 kW	2 l	11/09→03/12		
2.0 TFSI quattro	155 kW	2 l	06/08→12/15		
2.0 TFSI quattro	162 kW	2 l	05/13→12/15		



**AUDI - A4 B8 / A4 B8 Avant (8K2, 8K5)**







**11/07→12/15**

2.0 TFSI quattro	165 kW	2 l	05/13→12/15		KH20008 ProKIT
3.0 TDI quattro	155 kW	3 l	06/08→05/10		
3.0 TDI quattro	176 kW	3 l	11/07→03/12		
3.0 TDI quattro	176 kW	3 l	04/08→03/12		
3.0 TDI quattro	180 kW	3 l	11/11→12/15		
3.0 TFSI quattro	200 kW	3 l	02/12→12/15		
3.2 FSI quattro	195 kW	3.2 l	11/07→03/12		
3.2 FSI quattro	195 kW	3.2 l	04/08→03/12		
RS4 quattro	331 kW	4.2 l	05/12→08/15		
S4 quattro	245 kW	3 l	11/08→12/15		
2.7 TDI	120 kW	2.7 l	11/07→03/12		KH20008 ProKIT

**AUDI - A5 / A5 Convertible / A5 Sportback (8T3, 8F7, 8TA)**

**06/07→01/17**

1.8 TFSI	106 kW	1.8 l	09/14→01/17		KH20008 ProKIT
1.8 TFSI	118 kW	1.8 l	09/09→03/12		KH20064 ProKIT
1.8 TFSI	118 kW	1.8 l	11/09→09/11		
1.8 TFSI	125 kW	1.8 l	10/07→01/17		
1.8 TFSI	125 kW	1.8 l	08/11→01/17		
1.8 TFSI	125 kW	1.8 l	09/11→03/16		
2.0 TDI	100 kW	2 l	09/09→01/17		
2.0 TDI	105 kW	2 l	09/09→01/17		
2.0 TDI	105 kW	2 l	10/11→05/15		
2.0 TDI	110 kW	2 l	05/13→01/17		
2.0 TDI	120 kW	2 l	08/08→01/17		
2.0 TDI	120 kW	2 l	09/09→01/17		
2.0 TDI	125 kW	2 l	08/08→03/12		
2.0 TDI	125 kW	2 l	05/09→03/12		
2.0 TDI	125 kW	2 l	09/09→03/12		
2.0 TDI	130 kW	2 l	10/11→01/17		
2.0 TDI	140 kW	2 l	09/13→01/17		
2.0 TFSI	132 kW	2 l	03/09→03/12		
2.0 TFSI	155 kW	2 l	06/08→11/13		
2.0 TFSI	155 kW	2 l	03/09→06/14		
2.0 TFSI	162 kW	2 l	05/13→12/14		
2.0 TFSI	165 kW	2 l	05/13→05/16		
2.7 TDI	140 kW	2.7 l	03/09→03/12		
2.7 TDI	140 kW	2.7 l	09/09→03/12		
3.0 TDI	150 kW	3 l	10/11→01/17		
3.2 FSI	195 kW	3.2 l	06/07→03/12		
3.2 FSI	195 kW	3.2 l	03/09→03/12		
1.8 TFSI	118 kW	1.8 l	05/09→09/11		KH20008 ProKIT
2.0 TFSI	132 kW	2 l	11/08→03/12		KH20064 ProKIT
2.0 TFSI	132 kW	2 l	09/09→06/14	; 11/09 ->	
2.0 TFSI	155 kW	2 l	09/09→11/13		
1.8 TFSI	130 kW	1.8 l	05/15→01/17		KH20008 ProKIT
2.0 TDI	120 kW	2 l	05/09→06/14		
2.0 TFSI	169 kW	2 l	08/15→01/17		
2.7 TDI	120 kW	2.7 l	05/09→03/12		
2.7 TDI	120 kW	2.7 l	09/09→03/12		
2.0 TDI quattro	125 kW	2 l	08/08→03/12		KH20008 ProKIT
2.0 TDI quattro	125 kW	2 l	09/09→03/12		
2.0 TDI quattro	130 kW	2 l	12/11→01/17		
2.0 TDI quattro	130 kW	2 l	01/12→05/15		
2.0 TDI quattro	140 kW	2 l	09/13→01/17		
2.0 TFSI quattro	155 kW	2 l	06/08→01/17		
2.0 TFSI quattro	155 kW	2 l	03/09→01/17		
2.0 TFSI quattro	155 kW	2 l	09/09→01/17		
2.0 TFSI quattro	162 kW	2 l	03/12→01/17		
2.0 TFSI quattro	165 kW	2 l	05/13→05/16		
2.0 TFSI quattro	169 kW	2 l	08/15→01/17		
3.0 TDI quattro	155 kW	3 l	03/08→05/10		
3.0 TDI quattro	160 kW	3 l	05/15→01/17		
3.0 TDI quattro	176 kW	3 l	06/07→03/12		
3.0 TDI quattro	176 kW	3 l	03/09→03/12		
3.0 TDI quattro	176 kW	3 l	09/09→03/12		
3.0 TDI quattro	180 kW	3 l	10/11→01/17		
3.0 TFSI quattro	200 kW	3 l	11/11→01/17		
3.0 TFSI quattro	200 kW	3 l	12/11→01/17		
3.2 FSI quattro	195 kW	3.2 l	06/07→03/12		
3.2 FSI quattro	195 kW	3.2 l	03/09→03/12		
3.2 FSI quattro	195 kW	3.2 l	09/09→03/12		
RS5 quattro	331 kW	4.2 l	03/10→01/17		
RS5 quattro	331 kW	4.2 l	11/12→08/15		
S5 quattro	245 kW	3 l	06/09→01/17		
S5 quattro	245 kW	3 l	01/10→01/17		
S5 quattro	245 kW	3 l	10/11→01/17		
S5 quattro	260 kW	4.2 l	06/07→03/12		
2.0 TFSI quattro	165 kW	2 l	05/13→05/16		KH20008 ProKIT
3.0 TDI quattro	180 kW	3 l	10/11→01/17		KH20064 ProKIT

     					
<b>AUDI - A5 / A5 Convertible / A5 Sportback (8T3, 8F7, 8TA)</b>					<b>06/07→01/17</b>
2.7 TDI	120 kW	2.7 l	09/07→03/12		KH20008 ProKIT
				; 06/08 ->	KH20064 ProKIT
2.7 TDI	140 kW	2.7 l	06/07→03/12		KH20008 ProKIT
				; 07/07 ->	KH20064 ProKIT
<b>AUDI - A6 Allroad C6 Avant (4FH)</b>					<b>03/06→08/11</b>
2.7 TDI quattro	120 kW	2.7 l	05/06→08/11		KH20031 ProKIT
2.7 TDI quattro	132 kW	2.7 l	03/06→10/08		
2.7 TDI quattro	140 kW	2.7 l	10/08→08/11		
3.0 TDI quattro	155 kW	3 l	05/06→08/11		
3.0 TDI quattro	171 kW	3 l	05/06→10/08		
3.0 TDI quattro	176 kW	3 l	10/08→08/11		
4.2 FSI quattro	257 kW	4.2 l	05/06→12/10		
3.0 TFSI quattro	213 kW	3 l	10/08→08/11	; -> 05/10	KH20071 ProKIT
					KH20031 ProKIT
3.2 FSI quattro	188 kW	3.2 l	05/06→10/08		KH20071 ProKIT
					KH20031 ProKIT
<b>AUDI - A6 Allroad C7 (4GH, 4GJ)</b>					<b>01/12→09/18</b>
3.0 TDI quattro	140 kW	3 l	11/15→09/18		KH20008 ProKIT
3.0 TDI quattro	150 kW	3 l	01/12→12/14		
3.0 TDI quattro	155 kW	3 l	09/14→09/18		
3.0 TDI quattro	160 kW	3 l	09/14→09/18		
3.0 TDI quattro	180 kW	3 l	01/12→06/16		
3.0 TDI quattro	200 kW	3 l	09/14→09/18		
3.0 TDI quattro	230 kW	3 l	01/12→12/14		
3.0 TDI quattro	235 kW	3 l	01/12→09/18		
3.0 TFSI quattro	228 kW	3 l	01/12→12/14		
3.0 TFSI quattro	245 kW	3 l	09/14→09/18		
<b>AUDI - A6 C4 Avant / A6 C4 Sedan (4A5, 4A2)</b>					<b>06/94→12/97</b>
1.8	92 kW	1.8 l	12/95→10/97		KH10069 ProKIT
1.8	92 kW	1.8 l	12/95→12/97		KH00002 ProKIT
1.9 TDI	66 kW	1.9 l	06/94→10/97		
1.9 TDI	66 kW	1.9 l	06/94→12/97		
2.0	74 kW	2 l	06/94→10/97		
2.0	74 kW	2 l	06/94→12/97		
2.0	79 kW	2 l	06/94→07/95		
2.0	85 kW	2 l	06/94→10/97		
2.0	85 kW	2 l	06/94→12/97		
2.0 16V	103 kW	2 l	06/94→10/97		
2.0 16V	103 kW	2 l	06/94→12/97		
2.3	98 kW	2.3 l	06/94→12/95		
2.4	110 kW	2.4 l	07/95→06/96		
2.5 TDI	85 kW	2.5 l	06/94→10/97		
2.5 TDI	85 kW	2.5 l	06/94→12/97		
2.5 TDI	103 kW	2.5 l	08/94→10/97		
2.5 TDI	103 kW	2.5 l	08/94→12/97		
2.6	102 kW	2.6 l	06/94→02/97		
2.6	102 kW	2.6 l	06/94→10/97		
2.6	110 kW	2.6 l	06/94→10/97		
2.6	110 kW	2.6 l	06/94→12/97		
2.8	120 kW	2.8 l	06/94→07/95		
2.8	120 kW	2.8 l	08/95→07/96		
2.8	128 kW	2.8 l	06/94→10/97		
2.8	128 kW	2.8 l	06/94→12/97		
2.8	142 kW	2.8 l	12/95→10/97		
2.8	142 kW	2.8 l	12/95→12/97		
1.8 quattro	92 kW	1.8 l	12/95→10/97		KH10069 ProKIT
1.8 quattro	92 kW	1.8 l	12/95→12/97		
2.0 16V quattro	103 kW	2 l	06/94→10/97		
2.0 16V quattro	103 kW	2 l	06/94→12/97		
2.3 quattro	98 kW	2.3 l	06/94→12/95		
2.5 TDI quattro	103 kW	2.5 l	07/95→12/97		
2.5 TDI quattro	103 kW	2.5 l	10/95→10/97		
2.6 quattro	110 kW	2.6 l	06/94→10/97		
2.6 quattro	110 kW	2.6 l	06/94→12/97		
2.8 quattro	128 kW	2.8 l	06/94→10/97		
2.8 quattro	128 kW	2.8 l	06/94→12/97		
2.8 quattro	142 kW	2.8 l	12/95→10/97		
2.8 quattro	142 kW	2.8 l	12/95→12/97		
S6 4.2 quattro	213 kW	4.2 l	06/94→10/97		
S6 4.2 quattro	213 kW	4.2 l	06/94→12/97		
S6 Plus quattro	240 kW	4.2 l	04/96→10/97		
S6 Plus quattro	240 kW	4.2 l	04/96→12/97		
S6 Turbo quattro	169 kW	2.2 l	06/94→10/97		
S6 Turbo quattro	169 kW	2.2 l	06/94→12/97		































				13		i		
AUDI - A6 C5 Avant / A6 C5 Sedan (4B5, 4B2)							01/97→01/05	
1.8	85 kW	1.8 l	05/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
1.8	85 kW	1.8 l	02/98→01/05		VIN 4B-2-031-501 ->			
1.8 T quattro	110 kW	1.8 l	12/97→01/05			KH10066 ProKIT		
1.8 T quattro	132 kW	1.8 l	12/97→01/05					
1.8	92 kW	1.8 l	07/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
1.8	92 kW	1.8 l	12/97→01/05		VIN 4B-2-031-501 ->			
1.9 TDI	81 kW	1.9 l	04/97→10/00					
1.9 TDI	81 kW	1.9 l	02/98→04/01			KH10066 ProKIT		
1.9 TDI	85 kW	1.9 l	07/00→01/05			KH30095 ProKIT		
1.9 TDI	96 kW	1.9 l	08/01→01/05					
2.0	96 kW	2 l	08/01→01/05					
1.8 T	110 kW	1.8 l	01/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
1.8 T	110 kW	1.8 l	12/97→01/05		VIN 4B-2-031-501 ->			
						KH10066 ProKIT		
					AT	KH10069 ProKIT		
						KH30095 ProKIT		
1.8 T	132 kW	1.8 l	12/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
1.8 T	132 kW	1.8 l	04/99→01/05		VIN 4B-2-031-501 ->			
						KH10066 ProKIT		
					VIN -> 4B-2-031 500	KH10069 ProKIT		
						KH30095 ProKIT		
1.8 T quattro	110 kW	1.8 l	02/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
					VIN 4B-2-031-501 ->			
						KH10066 ProKIT		
					04/97 -> 06/99	KH10134 ProKIT		
1.8 T quattro	132 kW	1.8 l	12/97→01/05		VIN -> 4B-2-031-500;  17, 18 Inch	KH20032 ProKIT		
					VIN 4B-2-031-501 ->			
						KH10066 ProKIT		
					-> 06/99	KH10134 ProKIT		
2.4	100 kW	2.4 l	07/98→01/05		VIN -> 4B-2-031 500;  17, 18 Inch	KH20032 ProKIT		
2.4	115 kW	2.4 l	02/97→01/05		VIN 4B-2-031 501 ->			
2.4	115 kW	2.4 l	12/97→01/05					
2.4	120 kW	2.4 l	02/97→01/05			KH10066 ProKIT		
2.4	120 kW	2.4 l	12/97→01/05					
2.4	121 kW	2.4 l	02/97→01/05		VIN -> 4B-2-031 500	KH10069 ProKIT		
2.4	121 kW	2.4 l	12/97→01/05			KH30095 ProKIT		
2.5 TDI	110 kW	2.5 l	07/97→01/05					
2.5 TDI	110 kW	2.5 l	12/97→01/05					
2.5 TDI	132 kW	2.5 l	02/00→01/05					
2.7 T	169 kW	2.7 l	02/99→01/05					
2.8	132 kW	2.8 l	12/97→05/00					
2.8	140 kW	2.8 l	07/99→01/05					
2.8	142 kW	2.8 l	02/97→01/05					
2.8	142 kW	2.8 l	12/97→01/05					
2.4	125 kW	2.4 l	08/01→01/05		VIN -> 4B-2-031 500;  17, 18 Inch	KH20032 ProKIT		
2.5 TDI	114 kW	2.5 l	08/01→01/05		VIN 4B-2-031 501 ->			
2.5 TDI	120 kW	2.5 l	07/02→01/05					
3.0	162 kW	3 l	08/01→01/05					
						KH10066 ProKIT		
						KH30095 ProKIT		
2.4 quattro	115 kW	2.4 l	08/98→07/99		VIN -> 4B-2-031 500;  17, 18 Inch	KH20032 ProKIT		
					VIN 4B-2-031 501 ->			
						KH10066 ProKIT		
						KH10134 ProKIT		
2.4 quattro	115 kW	2.4 l	08/98→05/01		VIN -> 4B-2-031 500;  17, 18 Inch	KH20032 ProKIT		
2.4 quattro	120 kW	2.4 l	12/97→01/05		VIN 4B-2-031 501 ->			
2.4 quattro	121 kW	2.4 l	12/97→01/05					
2.4 quattro	125 kW	2.4 l	08/01→01/05			KH10066 ProKIT		
2.5 TDI quattro	110 kW	2.5 l	12/97→01/05					
2.5 TDI quattro	132 kW	2.5 l	02/00→01/05					
2.7 T quattro	169 kW	2.7 l	12/97→01/05					
2.7 T quattro	184 kW	2.7 l	08/01→01/05					
2.8 quattro	132 kW	2.8 l	01/98→04/00					
2.8 quattro	140 kW	2.8 l	07/99→05/01					
2.8 quattro	142 kW	2.8 l	12/97→01/05					
3.0 quattro	160 kW	3 l	06/01→07/04					
3.0 quattro	160 kW	3 l	06/01→01/05					
3.0 quattro	162 kW	3 l	08/01→01/05					



















































				13		i		
<b>AUDI - A6 C5 Avant / A6 C5 Sedan (4B5, 4B2)</b>							<b>01/97→01/05</b>	
2.4 quattro	120 kW	2.4 l	02/97→01/05		VIN -> 4B-2-031 500;  17, 18 Inch		KH20032 ProKIT	
					VIN 4B-2-031 501 ->			
							KH10066 ProKIT	
					05/97 -> 05/01		KH10134 ProKIT	
2.4 quattro	121 kW	2.4 l	02/97→01/05		VIN -> 4B-2-031 500;  17, 18 Inch		KH20032 ProKIT	
2.8 quattro	142 kW	2.8 l	02/97→01/05		VIN 4B-2-031 501 ->			
							KH10066 ProKIT	
					04/97 -> 05/01		KH10134 ProKIT	
2.5 TDI quattro	110 kW	2.5 l	07/97→01/05		VIN -> 4B-2-031 500;  17, 18 Inch		KH20032 ProKIT	
					VIN 4B-2-031 501 ->			
							KH10066 ProKIT	
					-> 05/01		KH10134 ProKIT	
2.7 quattro	187 kW	2.7 l	05/01→07/04				KH10066 ProKIT	
3.7 quattro	191 kW	3.7 l	03/99→01/05					
2.8	132 kW	2.8 l	10/97→05/00		VIN -> 4B-2-031 500;  17, 18 Inch		KH20032 ProKIT	
					VIN 4B-2-031 501 ->			
							KH10066 ProKIT	
					VIN -> 4B-2-031 500		KH10069 ProKIT	
					04/98 ->		KH10134 ProKIT	
							KH30095 ProKIT	
3.0	160 kW	3 l	06/01→01/05		VIN -> 4B-2-031 500;  17, 18 Inch		KH20032 ProKIT	
					VIN 4B-2-031 501 ->			
							KH10066 ProKIT	
3.7	191 kW	3.7 l	03/99→01/05				KH10066 ProKIT	
							KH30095 ProKIT	
4.2 quattro	220 kW	4.2 l	11/98→01/05				KH10066 ProKIT	
							KH20032 ProKIT	
RS6 plus quattro	353 kW	4.2 l	04/04→01/05				KH10066 ProKIT	
RS6 quattro	331 kW	4.2 l	07/02→01/05				KH20032 ProKIT	
S6 quattro	250 kW	4.2 l	09/99→01/05				KH10066 ProKIT	
							KH20032 ProKIT	
					-> 05/04		KH10134 ProKIT	
S6 quattro	250 kW	4.2 l	09/99→01/05				KH10066 ProKIT	
							KH20032 ProKIT	
							KH10134 ProKIT	
<b>AUDI - A6 C6 Avant / A6 C6 Sedan (4F5, 4F2)</b>							<b>05/04→08/11</b>	
2.0 TDI	89 kW	2 l	09/05→06/06				KH20071 ProKIT	
2.0 TDI	103 kW	2 l	07/04→10/08				KH30125 ProKIT	
2.0 TDI	103 kW	2 l	06/05→10/08					
2.0 TDI	100 kW	2 l	07/04→03/11		-> 05/10		KH20071 ProKIT	
2.0 TDI	100 kW	2 l	06/05→08/11		-> 05/10		KH30125 ProKIT	
2.0 TDI	125 kW	2 l	10/08→08/11					
2.0 TDI	125 kW	2 l	11/08→03/11					
2.0 TFSI	125 kW	2 l	06/05→03/11		-> 05/10		KH20071 ProKIT	
2.0 TFSI	125 kW	2 l	06/05→08/11				KH20031 ProKIT	
2.8 FSI	140 kW	2.8 l	10/08→03/11					
2.8 FSI	140 kW	2.8 l	10/08→08/11		-> 05/10		KH30125 ProKIT	
2.8 FSI	162 kW	2.8 l	10/08→03/11					
2.8 FSI	162 kW	2.8 l	10/08→08/11					
2.4	130 kW	2.4 l	05/04→10/08				KH20031 ProKIT	
2.4	130 kW	2.4 l	03/05→10/08				KH20071 ProKIT	
2.8 FSI	154 kW	2.8 l	11/06→10/08					
3.0	160 kW	3 l	03/05→05/06				KH30125 ProKIT	
3.2 FSI	188 kW	3.2 l	05/04→05/09					
3.2 FSI	188 kW	3.2 l	03/05→10/08					
2.4 quattro	130 kW	2.4 l	01/05→10/08				KH20031 ProKIT	
2.4 quattro	130 kW	2.4 l	03/05→10/08				KH20071 ProKIT	
2.8 FSI quattro	154 kW	2.8 l	06/07→10/08					
3.0 quattro	160 kW	3 l	05/04→05/06					
3.2 FSI quattro	188 kW	3.2 l	05/04→10/08					
3.2 FSI quattro	188 kW	3.2 l	03/05→10/08					



AUDI - A6 C6 Avant / A6 C6 Sedan (4F5, 4F2)				05/04→08/11	
2.7 TDI	120 kW	2.7 l	11/04→03/11		KH20031 ProKIT
2.7 TDI	120 kW	2.7 l	03/05→08/11		KH30125 ProKIT
2.7 TDI	140 kW	2.7 l	10/08→03/11	; -> 05/10	
2.7 TDI	140 kW	2.7 l	10/08→08/11		
2.7 TDI	132 kW	2.7 l	11/04→10/08		KH20031 ProKIT
2.7 TDI	132 kW	2.7 l	03/05→10/08		KH30125 ProKIT
2.7 TDI quattro	120 kW	2.7 l	06/05→03/11	;	KH20031 ProKIT
2.7 TDI quattro	120 kW	2.7 l	06/05→08/11		
2.7 TDI quattro	132 kW	2.7 l	11/04→10/08		
2.7 TDI quattro	140 kW	2.7 l	10/08→03/11		
2.7 TDI quattro	140 kW	2.7 l	10/08→08/11		
3.0 quattro	160 kW	3 l	03/05→05/06		
3.0 TDI quattro	155 kW	3 l	05/04→03/11		
3.0 TDI quattro	155 kW	3 l	03/05→08/11		
3.0 TDI quattro	165 kW	3 l	05/04→05/06		
3.0 TDI quattro	165 kW	3 l	03/05→05/06		
3.0 TDI quattro	171 kW	3 l	06/06→10/08		
3.0 TDI quattro	176 kW	3 l	10/08→03/11		
3.0 TDI quattro	176 kW	3 l	10/08→08/11		
3.0 TFSI quattro	213 kW	3 l	10/08→03/11		
3.0 TFSI quattro	213 kW	3 l	10/08→08/11		
3.0 TFSI quattro	220 kW	3 l	10/08→03/11		
3.0 TFSI quattro	220 kW	3 l	10/08→08/11		
3.2 FSI quattro	183 kW	3.2 l	09/06→10/08		
4.2 FSI quattro	257 kW	4.2 l	06/06→03/11		
4.2 FSI quattro	257 kW	4.2 l	06/06→08/11		
4.2 quattro	246 kW	4.2 l	05/04→05/06		
4.2 quattro	246 kW	4.2 l	03/05→05/06		
RS6 quattro	426 kW	5 l	04/08→08/10		
RS6 quattro	426 kW	5 l	09/08→08/10		
S6 quattro	320 kW	5.2 l	03/06→03/11		
S6 quattro	320 kW	5.2 l	03/06→08/11		
2.8 FSI quattro	140 kW	2.8 l	10/08→03/11	; -> 05/10	KH20071 ProKIT
2.8 FSI quattro	140 kW	2.8 l	10/08→08/11	;	KH20031 ProKIT
2.8 FSI quattro	162 kW	2.8 l	10/08→03/11		
2.8 FSI quattro	162 kW	2.8 l	10/08→08/11		
3.0	160 kW	3 l	08/04→05/06		KH20031 ProKIT
3.2 FSI	195 kW	3.2 l	05/09→03/11		
AUDI - A6 C7 / A6 C7 Avant (4G2, 4GC, 4G5, 4GD)				11/10→09/18	
1.8 TFSI	140 kW	1.8 l	09/14→09/18		KH20008 ProKIT
2.0 TDI	110 kW	2 l	09/14→09/18	; Trim Level: 1BA, 1BE, 1BR, 1BV;	KH20064 ProKIT
2.0 TFSI	185 kW	2 l	09/14→09/18		
3.0 TDI	155 kW	3 l	09/14→09/18		
3.0 TDI	160 kW	3 l	09/14→09/18		
1.8 TFSI	140 kW	1.8 l	09/14→09/18		KH20008 ProKIT
2.0 TDI	100 kW	2 l	01/12→09/18		
2.0 TDI	110 kW	2 l	09/14→09/18		
2.0 TFSI	185 kW	2 l	09/14→09/18		
3.0 TDI	150 kW	3 l	05/11→09/18		
3.0 TDI	155 kW	3 l	09/14→09/18		
3.0 TDI	160 kW	3 l	09/14→09/18		
2.0 TDI	120 kW	2 l	03/11→09/18		KH20008 ProKIT
2.0 TDI	130 kW	2 l	03/11→09/18		
2.0 TFSI	132 kW	2 l	05/11→09/18	; Trim Level: 1BA, 1BE, 1BR, 1BV;	KH20064 ProKIT
2.0 TFSI	155 kW	2 l	03/11→05/13	;	KH20141 ProKIT
2.0 TFSI Hybrid	155 kW	2 l	11/11→04/15		
2.8 FSI	150 kW	2.8 l	11/10→04/15		
3.0 TDI	150 kW	3 l	11/10→09/18		
2.0 TDI	120 kW	2 l	05/11→09/18		KH20008 ProKIT
2.0 TDI	130 kW	2 l	05/11→09/18		KH20141 ProKIT
2.0 TDI	140 kW	2 l	11/13→09/18		
2.0 TFSI	132 kW	2 l	06/11→09/18		
2.8 FSI	150 kW	2.8 l	05/11→04/15		
2.0 TDI	140 kW	2 l	11/13→09/18		KH20008 ProKIT
				; Trim Level: 1BA, 1BE, 1BR, 1BV;	KH20064 ProKIT
					KH20141 ProKIT
2.0 TDI quattro	140 kW	2 l	04/15→09/18	;	KH20008 ProKIT
2.0 TFSI quattro	155 kW	2 l	05/12→04/15		
2.0 TFSI quattro	162 kW	2 l	05/13→09/18		
2.0 TFSI quattro	183 kW	2 l	05/15→09/18		
2.0 TFSI quattro	185 kW	2 l	05/14→09/18		
2.0 TFSI quattro	185 kW	2 l	05/15→09/18		
2.8 FSI quattro	150 kW	2.8 l	11/10→04/15		
2.8 FSI quattro	150 kW	2.8 l	05/11→04/15		
2.8 FSI quattro	162 kW	2.8 l	09/14→09/18		
3.0 TDI quattro	150 kW	3 l	03/11→09/18		

				     	
<b>AUDI - A6 C7 / A6 C7 Avant (4G2, 4GC, 4G5, 4GD)</b>				<b>11/10→09/18</b>	
3.0 TDI quattro	150 kW	3 l	05/11→09/18	 	KH20008 ProKIT
3.0 TDI quattro	155 kW	3 l	09/14→09/18		
3.0 TDI quattro	160 kW	3 l	09/14→09/18		
3.0 TDI quattro	180 kW	3 l	03/11→09/18		
3.0 TDI quattro	180 kW	3 l	05/11→09/18		
3.0 TDI quattro	200 kW	3 l	09/14→09/18		
3.0 TDI quattro	230 kW	3 l	11/11→09/18		
3.0 TDI quattro	235 kW	3 l	09/14→09/18		
3.0 TDI quattro	240 kW	3 l	09/14→09/18		
3.0 TFSI quattro	220 kW	3 l	11/10→05/12		
3.0 TFSI quattro	220 kW	3 l	05/11→05/12		
3.0 TFSI quattro	228 kW	3 l	03/11→09/18		
3.0 TFSI quattro	228 kW	3 l	11/11→09/18		
3.0 TFSI quattro	245 kW	3 l	09/14→09/18		
RS6 performance quattro	445 kW	4 l	11/15→09/18		
RS6 quattro	412 kW	4 l	01/13→09/18		
S6 quattro	309 kW	4 l	02/12→09/18		
S6 quattro	331 kW	4 l	10/14→09/18		
2.0 TFSI	162 kW	2 l	05/13→09/18	 ; Trim Level: 1BA, 1BE, 1BR, 1BV; 	KH20064 ProKIT
					KH20141 ProKIT
<b>AUDI - A7 Sportback (4GA, 4GF)</b>				<b>10/10→05/18</b>	
1.8 TFSI	140 kW	1.8 l	04/15→05/18		KH20008 ProKIT
2.0 TFSI	185 kW	2 l	09/14→05/18		
3.0 TDI	140 kW	3 l	11/15→05/18		
3.0 TDI	155 kW	3 l	11/15→05/18		
3.0 TDI	160 kW	3 l	07/14→05/18		
2.0 TFSI quattro	183 kW	2 l	05/15→05/18	 	KH20008 ProKIT
2.0 TFSI quattro	185 kW	2 l	05/15→05/18		
2.8 FSI quattro	150 kW	2.8 l	10/10→03/15		
2.8 FSI quattro	162 kW	2.8 l	09/14→05/18		
3.0 TDI quattro	140 kW	3 l	11/15→05/18		
3.0 TDI quattro	150 kW	3 l	12/10→03/15		
3.0 TDI quattro	155 kW	3 l	07/14→05/18		
3.0 TDI quattro	160 kW	3 l	07/14→05/18		
3.0 TDI quattro	176 kW	3 l	05/13→06/17		
3.0 TDI quattro	180 kW	3 l	10/10→06/16		
3.0 TDI quattro	200 kW	3 l	05/14→05/18		
3.0 TDI quattro	230 kW	3 l	11/11→03/15		
3.0 TDI quattro	235 kW	3 l	05/14→05/18		
3.0 TDI quattro	240 kW	3 l	09/14→05/18		
3.0 TFSI quattro	220 kW	3 l	10/10→05/12		
3.0 TFSI quattro	228 kW	3 l	01/11→03/15		
3.0 TFSI quattro	245 kW	3 l	05/14→05/18		
RS7 performance quattro	445 kW	4 l	11/15→04/18		
RS7 quattro	412 kW	4 l	10/13→04/18		
S7 quattro	309 kW	4 l	02/12→03/15		
S7 quattro	331 kW	4 l	07/14→05/18		
2.8 FSI	150 kW	2.8 l	02/11→03/15		KH20008 ProKIT
					KH20141 ProKIT
3.0 TDI	150 kW	3 l	11/10→03/15		KH20008 ProKIT
				 	KH20141 ProKIT
<b>AUDI - A8 D2 (4D2, 4D8)</b>				<b>03/94→09/02</b>	
2.5 TDI	110 kW	2.5 l	01/97→04/00	 VIN 4D-X-005 501 ->  20 Inch	KH20032 ProKIT
2.5 TDI	132 kW	2.5 l	09/00→09/02	 VIN 4D-X-005 001 ->	
2.5 TDI quattro	110 kW	2.5 l	07/97→04/00	 VIN 4D-T-007 001 -> VIN 4D-X-005 500	KH10069 ProKIT
2.5 TDI quattro	132 kW	2.5 l	09/00→09/02		
2.8	142 kW	2.8 l	04/96→09/02		
2.8 quattro	142 kW	2.8 l	04/96→09/02		
3.3 TDI quattro	165 kW	3.3 l	06/00→09/02		
3.7	169 kW	3.7 l	07/95→12/98		
3.7	191 kW	3.7 l	11/98→09/02		
3.7 quattro	169 kW	3.7 l	07/95→11/98		
3.7 quattro	191 kW	3.7 l	11/98→09/02		
4.2 quattro	175 kW	4.2 l	02/99→04/00		
4.2 quattro	180 kW	4.2 l	03/94→07/96		
4.2 quattro	220 kW	4.2 l	03/94→11/98		
4.2 quattro	228 kW	4.2 l	11/98→09/02		
S8 quattro	250 kW	4.2 l	07/96→06/99		
S8 quattro	265 kW	4.2 l	06/99→09/02		
2.8	120 kW	2.8 l	07/95→03/96	 VIN 4D-X-005 501 ->  20 Inch	KH20032 ProKIT
2.8	128 kW	2.8 l	03/94→03/96	 VIN 4D-X-005 001 ->	
2.8 quattro	120 kW	2.8 l	07/95→03/96		
2.8 quattro	128 kW	2.8 l	03/94→03/96		
6.0 W12 quattro	309 kW	6 l	01/01→09/02	 VIN 4D-T-007 001 -> VIN 4D-X-005 500	KH10069 ProKIT
				 VIN 4D-X-005 001 ->	KH20032 ProKIT



				      13 	
<b>AUDI - A8 D3 (4E2, 4E8)</b>				<b>10/02→07/10</b>	
2.8 FSI	154 kW	2.8 l	08/07→07/10		KH20031 ProKIT
3.0	160 kW	3 l	07/03→05/06	 	KH20057 ProKIT
3.0	162 kW	3 l	07/03→05/05		
3.2 FSI	191 kW	3.2 l	06/05→07/10		
4.0 TDI quattro	202 kW	4 l	05/03→07/05		
S8 quattro	331 kW	5.2 l	06/06→07/10		
3.0 quattro	160 kW	3 l	11/03→05/04		KH20031 ProKIT
4.2 TDI quattro	235 kW	4.2 l	01/05→06/05		
S8 quattro	324 kW	5.2 l	09/06→07/10		
3.0 TDI quattro	155 kW	3 l	11/03→07/10	  	KH10134 ProKIT
3.2 FSI quattro	191 kW	3.2 l	06/05→07/10		KH20031 ProKIT
4.2 FSI quattro	257 kW	4.2 l	06/06→07/10	 	KH20057 ProKIT
4.2 TDI quattro	240 kW	4.2 l	07/05→07/10		
3.0 TDI quattro	171 kW	3 l	08/03→07/10	  	KH10134 ProKIT
					KH20031 ProKIT
				 	KH20057 ProKIT
3.7 quattro	206 kW	3.7 l	10/02→05/06		KH20031 ProKIT
				 	KH20057 ProKIT
4.2 quattro	246 kW	4.2 l	10/02→07/10		KH20031 ProKIT
				  	KH20057 ProKIT
6.0 W12 quattro	331 kW	6 l	12/03→07/10	  	KH10134 ProKIT
					KH20031 ProKIT
				 	KH20057 ProKIT
<b>AUDI - A8 D4 (4H2, 4H8, 4HC, 4HL)</b>				<b>11/09→01/18</b>	
2.0 TFSI hybrid	155 kW	2 l	02/12→11/15	 	KH20008 ProKIT
3.0 TDI	150 kW	3 l	09/11→09/13		
3.0 TDI quattro	155 kW	3 l	08/10→11/15	  	KH20008 ProKIT
3.0 TDI quattro	176 kW	3 l	11/12→06/16		
3.0 TDI quattro	184 kW	3 l	07/10→01/18		
3.0 TDI quattro	190 kW	3 l	10/13→01/18		
3.0 TDI quattro	193 kW	3 l	05/15→01/18		
3.0 TFSI quattro	213 kW	3 l	07/10→04/14		
3.0 TFSI quattro	228 kW	3 l	11/11→01/18		
3.0 TFSI quattro	245 kW	3 l	06/10→01/18		
4.0 TFSI quattro	309 kW	4 l	03/12→12/14		
4.0 TFSI quattro	320 kW	4 l	10/13→12/15		
4.2 FSI quattro	273 kW	4.2 l	11/09→12/12		
4.2 TDI quattro	258 kW	4.2 l	11/09→04/14		
4.2 TDI quattro	283 kW	4.2 l	10/13→01/18		
6.3 W12 quattro	368 kW	6.3 l	01/11→01/18		
S8 plus quattro	445 kW	4 l	11/15→01/18		
S8 quattro	382 kW	4 l	04/12→01/18		
<b>AUDI - ALLROAD C5 Avant (4BH)</b>				<b>05/00→08/05</b>	
2.5 TDI quattro	120 kW	2.5 l	05/03→08/05		KH10066 ProKIT
2.5 TDI quattro	132 kW	2.5 l	05/00→08/05		KH10069 ProKIT
2.7 quattro	187 kW	2.7 l	09/00→08/05		
2.7 T quattro	184 kW	2.7 l	05/00→08/05		
4.2 V8 quattro	220 kW	4.2 l	07/02→08/05		
<b>AUDI - CABRIOLET B3 (8G7)</b>				<b>05/91→08/00</b>	
1.8	92 kW	1.8 l	01/97→08/00	 VIN -> 8G-V-004 799	KH00002 ProKIT
1.9 TDI	66 kW	1.9 l	06/95→08/00	 VIN 8G-V-004 800 ->	KH00038 ProKIT
2.0 16V	103 kW	2 l	06/95→07/96		
2.0 E	85 kW	2 l	01/93→07/98		
2.3 E	98 kW	2.3 l	05/91→07/94		
2.6	110 kW	2.6 l	06/93→08/00		
2.8	128 kW	2.8 l	11/92→08/00		
<b>AUDI - COUPE B2 / COUPE B3 (81, 855, 856, 89, 8B3)</b>				<b>07/80→12/96</b>	
1.6	55 kW	1.6 l	07/80→08/81		KH10194 ProKIT
1.8	55 kW	1.8 l	08/81→07/83		KH00002 ProKIT
1.8 GT	65 kW	1.8 l	04/86→10/88		
1.8 GT	66 kW	1.8 l	09/82→10/88		
1.8 GT	68 kW	1.8 l	01/85→07/88		
1.8 GT	79 kW	1.8 l	08/86→10/87		
1.8 GT	82 kW	1.8 l	08/86→10/88		
1.9	85 kW	1.9 l	08/80→07/83		
2.0	83 kW	2 l	03/86→04/88		
2.0	85 kW	2 l	09/83→07/86		
2.1 GT	96 kW	2.1 l	09/82→10/87		
2.2 GT	85 kW	2.2 l	07/81→10/87		
2.2 GT	100 kW	2.2 l	09/84→10/88		
2.3	98 kW	2.3 l	08/86→07/87		

AUDI - COUPE B2 / COUPE B3 (81, 855, 856, 89, 8B3)					07/80→12/96
1.8	82 kW	1.8 l	08/89→07/91		KH00002 ProKIT
2.0	82 kW	2 l	03/90→07/90		
2.0	83 kW	2 l	05/89→03/90		
2.0	85 kW	2 l	05/89→12/96		
2.0 16 V	101 kW	2 l	01/92→07/92		
2.0 16 V	103 kW	2 l	08/92→12/96		
2.0 20 V	118 kW	2 l	08/89→07/91		
2.1 GT	79 kW	2.1 l	01/81→07/83		
2.3	98 kW	2.3 l	03/90→12/96		
2.3	100 kW	2.3 l	10/88→07/94		
2.3 20V	123 kW	2.3 l	08/90→07/91		
2.3 20V	125 kW	2.3 l	08/89→07/91		
2.6	110 kW	2.6 l	08/92→12/96		
2.8	128 kW	2.8 l	09/91→12/96		
AUDI - FOX B1 Saloon (80, 82)					05/72→07/78
1.3	40 kW	1.3 l	05/72→07/78	; 01/74 ->; VIN 8242072774 ->	KH10194 ProKIT
1.3	44 kW	1.3 l	05/72→07/78		KH00003 ProKIT
1.5	55 kW	1.5 l	05/72→08/75		
1.5	63 kW	1.5 l	05/72→07/76		
1.6 GT	74 kW	1.6 l	09/73→07/76		
1.6	53 kW	1.6 l	01/76→07/78		KH10194 ProKIT
1.6	55 kW	1.6 l	09/75→07/78		
1.6	61 kW	1.6 l	08/76→07/78		KH00003 ProKIT
1.6	63 kW	1.6 l	09/75→07/78		
1.6 GTE	81 kW	1.6 l	01/76→07/78		
AUDI - Q2 (GAB, GAG)					06/16→
1.0 TFSI	85 kW	1 l	10/16→10/20		KH30014 ProKIT
1.4 TFSI	110 kW	1.4 l	06/16→08/18		KH20003 ProKIT
1.6 TDI	85 kW	1.6 l	06/16→10/18		
2.0 TDI	105 kW	2 l	11/16→10/20		
2.0 TDI	110 kW	2 l	09/16→		
30 TDI	85 kW	1.6 l	07/18→		
30 TFSI	85 kW	1 l	07/18→10/20		
35 TDI	110 kW	2 l	09/16→		
35 TFSI	110 kW	1.5 l	07/18→		
2.0 TDI quattro	110 kW	2 l	09/16→		KH30014 ProKIT
2.0 TDI quattro	140 kW	2 l	07/16→08/18		KH30049 ProKIT
2.0 TFSI quattro	140 kW	2 l	05/17→		
35 TDI quattro	110 kW	2 l	09/18→		
40 TFSI quattro	140 kW	2 l	09/18→		
SQ2 TFSI quattro	221 kW	2 l	08/18→		
30 TFSI	81 kW	1 l	08/20→		KH20003 ProKIT
AUDI - Q3 (8UB, 8UG)					06/11→10/18
1.4 TFSI	92 kW	1.4 l	07/16→10/18		KH30002 ProKIT
1.4 TFSi Flex	110 kW	1.4 l	02/16→10/18		
1.4 TSI	110 kW	1.4 l	10/13→10/18	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TDI	88 kW	2 l	03/15→10/18		
2.0 TDI	100 kW	2 l	09/11→10/18		
2.0 TDI	103 kW	2 l	09/11→10/18		
2.0 TDI	110 kW	2 l	11/14→10/18		
2.0 TDI	130 kW	2 l	06/11→04/15		
2.0 TDI	135 kW	2 l	05/15→10/18		
2.0 TFSI	132 kW	2 l	05/15→10/18		
2.0 TFSI	147 kW	2 l	09/14→10/18		
2.0 TDI quattro	103 kW	2 l	01/12→10/18		KH30002 ProKIT
2.0 TDI quattro	110 kW	2 l	11/14→10/18		
2.0 TDI quattro	120 kW	2 l	06/11→04/15		
2.0 TDI quattro	130 kW	2 l	06/11→10/18		
2.0 TDI quattro	135 kW	2 l	11/14→10/18		
2.0 TFSI quattro	125 kW	2 l	06/11→04/15		
2.0 TFSI quattro	132 kW	2 l	11/14→10/18		
2.0 TFSI quattro	147 kW	2 l	09/14→10/18		
2.0 TFSI quattro	155 kW	2 l	06/11→04/15		
2.0 TFSI quattro	162 kW	2 l	11/14→10/18		
RS 2.5 quattro	228 kW	2.5 l	10/13→10/18		
RS 2.5 quattro	250 kW	2.5 l	05/13→10/18		
RS performance 2.5 quattro	270 kW	2.5 l	01/15→10/18		





**AUDI - Q3 / Q3 Sportback (F3B, F3N)**

07/18→

2.5 RS quattro	294 kW	2.5 l	10/19→		KH30049 ProKIT
35 TDI quattro	110 kW	2 l	09/18→		
35 TDI quattro	110 kW	2 l	09/19→		
40 TDI quattro	140 kW	2 l	10/18→		
40 TDI quattro	140 kW	2 l	07/19→		
40 TDI quattro	147 kW	2 l	09/20→		
40 TFSI quattro	132 kW	2 l	06/19→		
40 TFSI quattro	140 kW	2 l	07/18→		
40 TFSI quattro	140 kW	2 l	11/19→		
45 TFSI	180 kW	2 l	01/21→		
45 TFSI quattro	169 kW	2 l	07/18→		
45 TFSI quattro	169 kW	2 l	06/19→		
35 TDI	110 kW	2 l	09/18→		KH20004 ProKIT
35 TDI	110 kW	2 l	11/19→		
35 TFSI	110 kW	1.4 l	11/18→		
35 TFSI	110 kW	1.4 l	10/19→		
35 TFSI	110 kW	1.5 l	08/18→		
35 TFSI	110 kW	1.5 l	09/19→		
35 TFSI Mild Hybrid	110 kW	1.5 l	11/19→		

**AUDI - Q5 (8RB)**

11/08→05/17

2.0 TDI	100 kW	2 l	11/10→05/17		KH20008 ProKIT
2.0 TDI	105 kW	2 l	11/10→05/13		KH20141 ProKIT
2.0 TDI	110 kW	2 l	05/13→05/17		KH20008 ProKIT
					KH20141 ProKIT
2.0 TDI	140 kW	2 l	09/15→05/17		KH20008 ProKIT
2.0 TDI quattro	100 kW	2 l	08/09→05/17		KH20008 ProKIT
2.0 TDI quattro	105 kW	2 l	08/09→05/13		
2.0 TDI quattro	110 kW	2 l	05/13→05/17		
2.0 TDI quattro	120 kW	2 l	11/08→05/17		
2.0 TDI quattro	125 kW	2 l	11/08→09/12		
2.0 TDI quattro	130 kW	2 l	06/12→05/17		
2.0 TDI quattro	140 kW	2 l	11/13→05/17		
2.0 TFSI Hybrid quattro	155 kW	2 l	06/11→06/16		
2.0 TFSI quattro	132 kW	2 l	08/09→05/17		
2.0 TFSI quattro	155 kW	2 l	11/08→09/12		
2.0 TFSI quattro	162 kW	2 l	05/13→05/17		
2.0 TFSI quattro	165 kW	2 l	06/12→05/16		
2.0 TFSI quattro	169 kW	2 l	08/15→05/17		
3.0 TDI quattro	155 kW	3 l	11/08→09/12		
3.0 TDI quattro	176 kW	3 l	11/08→05/17		
3.0 TDI quattro	180 kW	3 l	06/12→05/17		
3.0 TDI quattro	184 kW	3 l	06/12→05/17		
3.0 TDI quattro	190 kW	3 l	11/13→05/17		
3.0 TFSI quattro	200 kW	3 l	06/12→05/17		
3.2 FSI quattro	199 kW	3.2 l	11/08→12/12		
SQ5 TDI quattro	230 kW	3 l	12/12→11/15		
SQ5 TDI quattro	240 kW	3 l	04/15→05/17		
SQ5 TDI quattro	250 kW	3 l	11/15→05/17		
SQ5 TFSI quattro	260 kW	3 l	05/13→05/17		

**AUDI - Q7 (4LB)**

03/06→08/15

3.0 TDI quattro	155 kW	3 l	03/06→05/10		KH10152 ProKIT
3.0 TDI quattro	171 kW	3 l	03/06→05/08		
3.6 FSI quattro	206 kW	3.6 l	08/06→05/10		
4.2 FSI quattro	257 kW	4.2 l	03/06→05/10		
4.2 TDI quattro	240 kW	4.2 l	03/07→06/09		
3.0 TDI quattro	176 kW	3 l	11/07→08/15		KH10152 ProKIT
3.0 TFSI quattro	200 kW	3 l	05/10→08/15		
3.0 TFSI quattro	245 kW	3 l	05/10→08/15		
4.2 TDI quattro	250 kW	4.2 l	05/09→08/15		
6.0 TDI quattro	368 kW	6 l	09/08→05/14		

**AUDI - R8 / R8 Spyder (422, 423, 427, 429)**

04/07→07/15

4.2 FSI quattro	309 kW	4.2 l	04/07→09/10		KH20071 ProKIT
4.2 FSI quattro	316 kW	4.2 l	07/10→07/15		KH20031 ProKIT
4.2 FSI quattro	316 kW	4.2 l	09/10→07/15		KH20071 ProKIT
5.2 FSI quattro	386 kW	5.2 l	04/09→07/15		KH20071 ProKIT
5.2 FSI quattro	386 kW	5.2 l	02/10→07/15		KH20159 ProKIT
5.2 FSI quattro	404 kW	5.2 l	05/12→07/15		KH20071 ProKIT
5.2 FSI quattro	412 kW	5.2 l	11/10→07/15		KH20159 ProKIT
5.2 FSI quattro	412 kW	5.2 l	11/11→07/15		KH20159 ProKIT
5.2 FSI quattro	419 kW	5.2 l	07/14→07/15		KH20159 ProKIT



**AUDI - TT (8J3)** **08/06→06/14**

1.8 TFSI	118 kW	1.8 l	06/08→06/14		KH30002 ProKIT
2.0 TFSI	147 kW	2 l	08/06→06/10	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TFSI	149 kW	2 l	01/08→06/10		
2.0 TFSI	155 kW	2 l	05/10→06/14		
2.0 TDI quattro	125 kW	2 l	06/08→06/14		
2.0 TFSI quattro	147 kW	2 l	06/08→06/10		KH30002 ProKIT
2.0 TFSI quattro	155 kW	2 l	05/10→06/14		
2.0 TTS quattro	195 kW	2 l	05/08→06/14		
2.0 TTS quattro	200 kW	2 l	05/08→06/14		
2.5 RS quattro	250 kW	2.5 l	07/09→06/14		
2.5 RS quattro	265 kW	2.5 l	05/11→06/14		
3.2 V6 quattro	184 kW	3.2 l	08/06→06/10		

**AUDI - TT (8N3)** **10/98→06/06**

1.8 T	110 kW	1.8 l	09/02→06/06	; 01/03 ->; MT's;	KH10117 ProKIT
					KH10001 ProKIT
				(ABS)	KH20010 ProKIT
1.8 T	120 kW	1.8 l	09/05→06/06		KH10001 ProKIT
				; MT's;	KH10117 ProKIT
1.8 T	140 kW	1.8 l	09/05→06/06	(ABS)	KH20010 ProKIT
				; 01/03 ->;  AUQ; MT's;	KH10117 ProKIT
					KH10001 ProKIT
1.8 T	132 kW	1.8 l	10/98→06/06	(ABS)	KH20010 ProKIT
					KH10001 ProKIT
					KH10117 ProKIT
1.8 T	134 kW	1.8 l	09/99→06/06	(ABS)	KH20010 ProKIT
					KH10001 ProKIT
1.8 T quattro	132 kW	1.8 l	10/98→06/06	; 01/01 ->; VIN 8N-1-046 001 ->;  ARY	KH10117 ProKIT
					KH10001 ProKIT
1.8 T quattro	140 kW	1.8 l	09/05→06/06		KH10001 ProKIT
1.8 T quattro	180 kW	1.8 l	03/05→06/06	; VIN 8N-1-046 001 ->	KH10117 ProKIT
3.2 VR6 quattro	184 kW	3.2 l	07/03→06/06		KH10117 ProKIT
1.8 T quattro	165 kW	1.8 l	10/98→06/06	; 01/01 ->; VIN 8N-1-046 001 ->;  APX	KH10117 ProKIT
					KH10001 ProKIT

**AUDI - TT (FV3, FVP)** **07/14→**

1.8 TFSI	132 kW	1.8 l	07/15→08/18		KH30049 ProKIT
2.0 TDI	135 kW	2 l	07/14→	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TFSI	169 kW	2 l	07/14→		
40 TFSI	145 kW	2 l	07/18→		
45 TFSI	180 kW	2 l	07/18→		
2.0 TDI quattro	135 kW	2 l	01/17→		
2.0 TFSI quattro	162 kW	2 l	04/15→		KH30049 ProKIT
2.0 TFSI quattro	169 kW	2 l	07/14→		
2.0 TTS quattro	210 kW	2 l	02/15→		
2.0 TTS quattro	228 kW	2 l	11/14→		
2.5 RS quattro	294 kW	2.5 l	10/16→		
2.0 TFSI quattro	170 kW	2 l	09/18→		
2.0 TTS quattro	215 kW	2 l	07/15→		
2.0 TTS quattro	225 kW	2 l	08/18→		
45 TFSI quattro	180 kW	2 l	07/18→		

**AUDI - TT Roadster (8J9)** **03/07→06/14**

























1.8 TFSI	118 kW	1.8 l	06/08→06/14		KH30002 ProKIT
2.0 TFSI	147 kW	2 l	03/07→06/10	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TFSI	155 kW	2 l	05/10→06/14		
2.0 TDI quattro	125 kW	2 l	06/08→06/14		
2.0 TFSI quattro	147 kW	2 l	06/08→06/10		KH30002 ProKIT
2.0 TFSI quattro	155 kW	2 l	05/10→06/14		
2.0 TTS quattro	195 kW	2 l	05/08→06/14		
2.0 TTS quattro	200 kW	2 l	05/08→06/14		
2.5 RS quattro	250 kW	2.5 l	07/09→06/14		
2.5 RS quattro	265 kW	2.5 l	03/12→06/14		
3.2 V6 quattro	184 kW	3.2 l	03/07→06/10		

**AUDI - TT Roadster (8N9)** **10/99→06/06**

















1.8 T	110 kW	1.8 l	01/01→06/06	; 01/03 ->; MT's;	KH10117 ProKIT
					KH10001 ProKIT
				(ABS)	KH20010 ProKIT
1.8 T	120 kW	1.8 l	09/05→06/06		KH10001 ProKIT
				(ABS)	KH20010 ProKIT

<b>AUDI - TT Roadster (8N9)</b>				<b>10/99→06/06</b>	
1.8 T	132 kW	1.8 l	10/99→06/06	; 01/03 →;  AUQ;  MT S;  Sport	KH10117 ProKIT
					KH10001 ProKIT
				(ABS)	KH20010 ProKIT
1.8 T	140 kW	1.8 l	09/05→06/06		KH10001 ProKIT
				;  MT S;  Sport	KH10117 ProKIT
				(ABS)	KH20010 ProKIT
1.8 T quattro	132 kW	1.8 l	02/00→06/06	; 01/01 →; VIN 8N-1-046 001 →;  ARY	KH10117 ProKIT
				;	KH10001 ProKIT
1.8 T quattro	140 kW	1.8 l	09/05→06/06	;	KH10001 ProKIT
3.2 VR6 quattro	184 kW	3.2 l	07/03→06/06	; VIN 8N-1-046 001 →	KH10117 ProKIT
1.8 T quattro	165 kW	1.8 l	10/99→06/06	; 01/01 →; VIN 8N-1-046 001 →;  APX	KH10117 ProKIT
				;	KH10001 ProKIT
<b>AUDI - TT Roadster (FV9, FVR)</b>				<b>11/14→</b>	
1.8 TFSI	132 kW	1.8 l	07/15→08/18		KH30049 ProKIT
2.0 TDI	135 kW	2 l	11/14→	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TFSI	169 kW	2 l	11/14→		
40 TFSI	145 kW	2 l	07/18→		
45 TFSI	180 kW	2 l	07/18→		
2.0 TDI quattro	135 kW	2 l	01/17→		KH30049 ProKIT
2.0 TFSI quattro	162 kW	2 l	04/15→		
2.0 TFSI quattro	169 kW	2 l	11/14→		
2.0 TTS quattro	210 kW	2 l	02/15→		
2.0 TTS quattro	228 kW	2 l	11/14→		
2.5 RS quattro	294 kW	2.5 l	10/16→		
2.0 TFSI quattro	170 kW	2 l	09/18→	;	KH30049 ProKIT
2.0 TTS quattro	225 kW	2 l	08/18→		
45 TFSI quattro	180 kW	2 l	07/18→		
TTS quattro	235 kW	2 l	11/20→		



				     	
<b>AUSTIN - METRO I Fastback (XF)</b>				<b>10/80→04/90</b>	
1.0	30 kW	1 l	10/80→04/90	 ; -> 09/84	<b>KH00046</b> ProKIT
1.0	33 kW	1 l	10/80→04/90		
1.0 Surf HLE	35 kW	1 l	10/80→04/90		
1.3 Turbo	66 kW	1.3 l	10/83→04/90		
1.3	51 kW	1.3 l	10/80→04/90	 ; 02/81 -> 09/84	<b>KH00046</b> ProKIT
1.3	52 kW	1.3 l	10/80→12/85		
1.3 L, HLE, S	44 kW	1.3 l	10/80→04/90	 ; 05/82 -> 09/84	<b>KH00046</b> ProKIT
<b>AUSTIN - MINI II</b>				<b>10/67→06/93</b>	
1000	26 kW	1 l	10/67→09/84	 ; 01/84 ->; VIN 239251 ->; MT	<b>KH00051</b> ProKIT
				 ; 01/84 ->; VIN 234914 ->; AT	
				 ; 09/73 -> 09/82	<b>KH00046</b> ProKIT
1000	29 kW	1 l	10/67→09/84	 ; 12/82 ->; VIN -> 234913	<b>KH00046</b> ProKIT
				 ; VIN 239249 -> VIN 239250	
				 ; 01/84 ->; VIN 239251 ->; MT	<b>KH00051</b> ProKIT
				 ; 01/84 ->; VIN 234914 ->; AT	
1000 Mayfair	31 kW	1 l	08/82→06/93	 ; 12/82 ->; VIN -> 234913	<b>KH00046</b> ProKIT
				 ; VIN 239249 -> VIN 239250	
				 ; 01/84 -> 12/90; VIN 239251 ->; MT	<b>KH00051</b> ProKIT
				 ; 01/84 -> 12/90; VIN 234914 ->; AT	
1000 Mayfair Sport	30 kW	1 l	09/88→06/93	 ; -> 12/90; VIN 239251 ->; MT	<b>KH00051</b> ProKIT
				 ; -> 12/90; VIN 234914 ->; AT	
				 ; -> 08/90	<b>KH00046</b> ProKIT
1275 GT	39 kW	1.3 l	10/69→08/80		<b>KH00051</b> ProKIT



     				
<b>AUTOBIANCHI - A 112</b>				<b>10/69→12/85</b>
0.9	32 kW	0.9 l	10/69→12/72	 KH10369 ProKIT
0.9	33 kW	0.9 l	01/76→12/78	
0.9 Junior	31 kW	0.9 l	07/75→12/85	 ; 06/84 -> KH20091 ProKIT
1.0 Abarth	43 kW	1 l	09/71→12/75	 ; VIN 006077, 526703 -> VIN 526702 KH10369 ProKIT
				 KH20091 ProKIT
1.0 Abarth	51 kW	1 l	01/74→12/84	 ; 09/76 -> 09/76; VIN 006077, 526703 -> VIN 526702 KH10369 ProKIT
				 KH20091 ProKIT
1.0 E,Elite,LX	35 kW	1 l	11/77→12/85	 KH20091 ProKIT
<b>AUTOBIANCHI - Y10</b>				<b>03/85→10/95</b>
1.0	33 kW	1 l	03/85→10/95	 KH30113 ProKIT
1.0	41 kW	1 l	03/85→10/95	
1.0 Cat	33 kW	1 l	10/87→10/95	 KH20091 ProKIT
1.0 Turbo	63 kW	1 l	03/85→10/95	
1.1 i.e. Cat	42 kW	1.1 l	09/90→10/95	
1.3 i.e. GT	54 kW	1.3 l	06/89→10/95	
1.3 i.e. GT	57 kW	1.3 l	06/89→10/95	
1.0 4WD	37 kW	1 l	12/86→10/95	 KH30113 ProKIT
1.1	42 kW	1.1 l	06/89→10/95	
1.1 4WD	42 kW	1.1 l	06/89→10/95	



**BMW - 1 (E81, E87)**

**06/04→09/12**

116 d	66 kW	2 l	01/11→12/11		KH30080 ProKIT
116 d	85 kW	2 l	11/08→12/11		KH10061 ProKIT
116 d	85 kW	2 l	03/09→06/11		
116 i	85 kW	1.6 l	06/04→06/11		
116 i	85 kW	1.6 l	09/07→12/11		
116 i	90 kW	1.6 l	03/07→12/11		
116 i	90 kW	1.6 l	09/07→06/11		
116 i	90 kW	2 l	11/08→12/11		
116 i	90 kW	2 l	01/09→06/11		
118 d	90 kW	2 l	06/04→02/07		
118 d	100 kW	2 l	09/06→12/11		
118 d	100 kW	2 l	03/07→06/11		
118 d	105 kW	2 l	09/06→12/11		
118 d	105 kW	2 l	03/07→06/11		
118 i	95 kW	2 l	07/04→02/07		
118 i	100 kW	2 l	10/06→06/11		
118 i	105 kW	2 l	09/06→06/11		
118 i	105 kW	2 l	09/06→12/11		
118 i	125 kW	2 l	03/07→12/07		
120 d	120 kW	2 l	06/04→06/11		
120 d	120 kW	2 l	03/07→12/11		
120 d	130 kW	2 l	03/07→06/11		
120 d	130 kW	2 l	03/07→12/11		
120 i	110 kW	2 l	06/04→02/07		
120 i	115 kW	2 l	03/07→06/11		
120 i	115 kW	2 l	03/07→12/11		
120 i	120 kW	2 l	03/07→06/11		
120 i	120 kW	2 l	03/07→12/11		
120 i	125 kW	2 l	03/07→06/11		
120 i	125 kW	2 l	03/07→09/12		
118 i	100 kW	2 l	09/06→12/11		KH30080 ProKIT
120 d	110 kW	2 l	06/04→02/07		
120 d	145 kW	2 l	03/07→12/11		
123 d	150 kW	2 l	03/07→06/11		KH30080 ProKIT
123 d	150 kW	2 l	03/07→12/11		KH10008 ProKIT
130 i	190 kW	3 l	09/06→12/11		
130 i	190 kW	3 l	03/07→06/11		
130 i	195 kW	3 l	09/05→02/07		
130 i	195 kW	3 l	09/06→12/11		

**BMW - 1 (F20, F21)**

**07/11→**

114 d	70 kW	1.5 l	06/15→		KH10354 ProKIT
114 d	70 kW	1.5 l	07/15→06/19		
114 d	70 kW	1.6 l	07/12→		
114 d	70 kW	1.6 l	11/12→06/15		
114 i	75 kW	1.6 l	12/11→		
114 i	75 kW	1.6 l	07/12→02/15		
116 d	85 kW	1.5 l	03/15→		
116 d	85 kW	1.5 l	03/15→06/19		
116 d	85 kW	1.6 l	12/11→		
116 d	85 kW	1.6 l	03/12→02/15		
116 d	85 kW	2 l	07/11→02/15		
116 d	85 kW	2 l	01/12→		
116 i	80 kW	1.5 l	03/15→		
116 i	80 kW	1.5 l	03/15→06/19		
116 i	100 kW	1.6 l	07/11→02/15		
116 i	100 kW	1.6 l	12/11→		
118 d	100 kW	2 l	07/11→06/19		
118 d	100 kW	2 l	12/11→02/15		
118 d	105 kW	2 l	07/11→02/15		
118 d	105 kW	2 l	12/11→		
118 d	110 kW	2 l	03/15→		
118 d	110 kW	2 l	03/15→06/19		
118 d xDrive	105 kW	2 l	05/13→		
118 d xDrive	105 kW	2 l	07/13→02/15		
118 d xDrive	110 kW	2 l	03/15→		
118 d xDrive	110 kW	2 l	03/15→06/19		
118 i	100 kW	1.5 l	07/15→06/19		
118 i	100 kW	1.6 l	03/15→		
118 i	100 kW	1.6 l	03/15→06/15		
118 i	125 kW	1.6 l	07/11→02/15		
118 i	125 kW	1.6 l	07/12→		
120 d	120 kW	2 l	07/11→06/19		
120 d	120 kW	2 l	07/12→		
120 d	135 kW	2 l	07/11→02/15		
120 d	135 kW	2 l	07/12→		
120 d	140 kW	2 l	03/15→		
120 d	140 kW	2 l	03/15→06/19		
120 d	147 kW	2 l	07/11→02/15		
120 d	147 kW	2 l	01/12→02/15		


**BMW - 1 (F20, F21)**
**07/11→**

120 d xDrive	135 kW	2 l	02/12→02/15
120 d xDrive	135 kW	2 l	11/12→02/15
120 d xDrive	140 kW	2 l	03/15→
120 d xDrive	140 kW	2 l	03/15→06/19
120 d xDrive	147 kW	2 l	01/12→
120 d xDrive	147 kW	2 l	11/12→02/15
120 i	130 kW	1.6 l	03/15→
120 i	130 kW	1.6 l	03/15→06/16
120 i	135 kW	2 l	07/16→
120 i	135 kW	2 l	07/16→06/19
125 d	155 kW	2 l	12/11→02/15
125 d	155 kW	2 l	03/12→06/19
125 d	160 kW	2 l	12/11→
125 d	160 kW	2 l	03/12→02/15
125 d	165 kW	2 l	03/15→
125 d	165 kW	2 l	03/15→06/19
125 i	160 kW	2 l	12/11→12/19
125 i	160 kW	2 l	03/12→11/17
125 i	165 kW	2 l	10/15→
125 i	165 kW	2 l	07/16→06/19
125 i	175 kW	2 l	03/12→11/17
125 i	175 kW	2 l	03/13→
M 135 i	235 kW	3 l	12/11→
M 135 i	235 kW	3 l	07/12→02/15
M 135 i	240 kW	3 l	03/15→
M 135 i	240 kW	3 l	03/15→06/16
M 135 i xDrive	235 kW	3 l	02/12→
M 135 i xDrive	235 kW	3 l	11/12→02/15
M 135 i xDrive	240 kW	3 l	03/15→
M 135 i xDrive	240 kW	3 l	03/15→06/16
M 140 i	250 kW	3 l	10/15→
M 140 i	250 kW	3 l	07/16→06/19
M 140 i xDrive	250 kW	3 l	09/15→
M 140 i xDrive	250 kW	3 l	07/16→06/19

KH10354 ProKIT

**BMW - 1 Convertible / 1 Coupe (E88, E82)**
**09/07→12/13**

118 d	100 kW	2 l	09/08→12/13
118 d	100 kW	2 l	09/09→10/13
118 d	105 kW	2 l	09/08→12/13
118 d	105 kW	2 l	09/09→10/13
118 i	100 kW	2 l	09/08→12/13
118 i	105 kW	2 l	03/08→12/13
120 d	120 kW	2 l	09/07→10/13
120 d	120 kW	2 l	03/08→12/13
120 d	130 kW	2 l	09/07→10/13
120 d	130 kW	2 l	03/08→12/13
120 d	145 kW	2 l	03/08→12/13
120 i	115 kW	2 l	03/08→12/13
120 i	115 kW	2 l	09/09→10/13
120 i	120 kW	2 l	03/08→12/13
120 i	125 kW	2 l	10/07→10/13
120 i	125 kW	2 l	12/07→10/13
125 i	160 kW	3 l	12/07→10/13
125 i	160 kW	3 l	03/08→10/13
120 d	145 kW	2 l	09/07→10/13
123 d	150 kW	2 l	10/07→10/13
123 d	150 kW	2 l	09/08→12/13
128 i	172 kW	3 l	12/07→10/13
135 i	225 kW	3 l	10/07→10/13
135 i	225 kW	3 l	03/08→10/13
135 i	240 kW	3 l	10/07→10/13
135 i	240 kW	3 l	03/08→12/13
M	250 kW	3 l	03/11→06/12

KH30080 ProKIT

KH10061 ProKIT

KH30080 ProKIT

KH30080 ProKIT

KH10008 ProKIT

KH10008 ProKIT

**BMW - 2.5-3.2 Coupe (E9)**
**01/69→03/76**













2.5 CS	110 kW	2.5 l	09/74→03/76
2800 CS	125 kW	2.8 l	01/69→04/71
3.0 CS	132 kW	3 l	05/71→03/76
3.0 CSi	147 kW	3 l	07/71→03/76
3.0 CSiL	152 kW	3.2 l	01/74→11/75

KH00039 ProKIT

**BMW - 2 Convertible / 2 Coupe (F23, F22, F87)**
**10/12→**

218 d	100 kW	2 l	03/14→06/15
218 d	100 kW	2 l	07/15→
218 d	105 kW	2 l	03/14→06/15
218 d	110 kW	2 l	07/15→
218 i	100 kW	1.5 l	03/15→
220 d	120 kW	2 l	03/14→
220 d	120 kW	2 l	11/14→

KH10354 ProKIT

     					
<b>BMW - 2 Convertible / 2 Coupe (F23, F22, F87)</b>				<b>10/12→</b>	
220 d	135 kW	2 l	10/12→11/14	 <b>KH10354 ProKIT</b>	
220 d	140 kW	2 l	03/14→		
220 d	147 kW	2 l	10/12→11/14		
220 d xDrive	120 kW	2 l	03/15→		
220 d xDrive	140 kW	2 l	06/14→		
220 i	135 kW	2 l	10/13→		
220 i	135 kW	2 l	04/14→07/16		
220 i	135 kW	2 l	09/15→		
225 d	160 kW	2 l	01/14→		
225 d	165 kW	2 l	07/15→		
228 i	180 kW	2 l	07/14→		
228 i	180 kW	2 l	11/14→		
230 i	185 kW	2 l	07/16→		
M2	272 kW	3 l	11/15→06/18		
M 235 i	240 kW	3 l	10/13→		
M 235 i	240 kW	3 l	11/14→		
M 235 i xDrive	240 kW	3 l	07/14→		
M 235 i xDrive	240 kW	3 l	07/15→		
M 240 i	250 kW	3 l	09/15→		
M 240 i xDrive	250 kW	3 l	09/15→		
<b>BMW - 3 (F30, F80)</b>				<b>11/11→10/18</b>	
316 d	85 kW	2 l	03/12→10/18	 <b>KH10354 ProKIT</b>	
316 i	100 kW	1.6 l	07/12→08/16		
318 d	100 kW	2 l	03/12→10/18		 <b>Outer diameter [mm]: 85</b> <b>KH10356 ProKIT</b>
318 d	105 kW	2 l	03/12→06/15		
318 d	110 kW	2 l	07/15→10/18		
318 i	100 kW	1.5 l	07/15→10/18		
320 d	120 kW	2 l	11/11→10/18		
320 d	135 kW	2 l	11/11→03/16		
320 d	140 kW	2 l	07/15→10/18		
320 d	147 kW	2 l	11/11→03/16		
320 i	125 kW	1.6 l	11/12→06/16		
320 i	135 kW	2 l	03/12→10/18		
320 i	135 kW	2 l	07/15→10/18		
325 d	155 kW	2 l	03/13→02/16		
325 d	160 kW	2 l	03/13→02/16		
325 d	165 kW	2 l	03/16→02/18		
328 i	180 kW	2 l	11/11→10/18		
330 d	190 kW	3 l	07/12→10/18		
330 d	210 kW	3 l	07/12→10/18		
330 e	185 kW	2 l	11/15→10/18		
330 i	185 kW	2 l	07/15→10/18		
335 i	225 kW	3 l	11/11→07/15		
335 i	240 kW	3 l	11/11→06/13		
335 i	250 kW	3 l	07/13→07/15		
340 i	240 kW	3 l	07/15→10/18		
340 i	265 kW	3 l	07/15→10/18		
ActiveHybrid	250 kW	3 l	07/12→06/15		
M3	317 kW	3 l	03/14→10/18		
M3 Competition	331 kW	3 l	03/16→10/18		
M3 CS	338 kW	3 l	01/18→10/18		
318 d xDrive	105 kW	2 l	07/13→06/15	 <b>Outer diameter [mm]: 85</b> <b>KH10356 ProKIT</b>	
318 d xDrive	110 kW	2 l	07/15→02/18		
320 d xDrive	120 kW	2 l	08/12→10/18		
320 d xDrive	135 kW	2 l	08/12→06/15		
320 d xDrive	140 kW	2 l	07/15→10/18		
320 d xDrive	147 kW	2 l	08/12→06/15		
320 i xDrive	135 kW	2 l	07/12→10/18		
320 i xDrive	135 kW	2 l	07/15→10/18		
328 i xDrive	180 kW	2 l	07/12→08/16		
330 d xDrive	190 kW	3 l	03/13→10/18		
330 d xDrive	210 kW	3 l	03/13→10/18		
330 i xDrive	185 kW	2 l	07/15→10/18		
335 d xDrive	230 kW	3 l	07/13→10/18		
335 i xDrive	225 kW	3 l	07/12→07/15		
335 i xDrive	240 kW	3 l	07/12→06/13		
335 i xDrive	250 kW	3 l	07/13→07/15		
340 i xDrive	240 kW	3 l	07/15→10/18		
340 i xDrive	265 kW	3 l	07/15→10/18		
<b>BMW - 3 Compact (E36)</b>					<b>01/94→08/00</b>
316 g	75 kW	1.6 l	02/96→08/00		 <b>KH10408 ProKIT</b>
316 i	75 kW	1.6 l	01/94→08/00		
318 tds	66 kW	1.7 l	06/95→08/00		
318 ti	103 kW	1.8 l	09/94→12/95		
318 ti	103 kW	1.9 l	01/96→08/99	 <b>KH10203 ProKIT</b>	
323 ti	125 kW	2.5 l	09/97→08/00		





**BMW - 3 Compact (E46)**

03/01→02/05

316 ti	77 kW	1.6 l	06/02→02/05
316 ti	85 kW	1.6 l	06/02→02/05
316 ti	85 kW	1.8 l	06/01→02/05
318 td	85 kW	2 l	03/03→02/05
318 ti	100 kW	2 l	03/01→12/04
318 ti	105 kW	2 l	03/01→12/04
320 td	110 kW	2 l	09/01→02/05
325 ti	141 kW	2.5 l	04/01→12/04

	KH10007 ProKIT
--	----------------

**BMW - 3 Convertible (E30)**

12/85→11/93

316 i Baur TC	73 kW	1.6 l	09/87→12/89
M3 2.3	143 kW	2.3 l	06/88→06/91
M3 2.3	147 kW	2.3 l	06/88→07/89
M3 2.3	158 kW	2.3 l	06/88→10/93

	KH10203 ProKIT
--	----------------

318 i	83 kW	1.8 l	09/90→10/93
-------	-------	-------	-------------

; 01/91 ->	KH20111 ProKIT
------------	----------------

; -> 04/93	KH20060 ProKIT
------------	----------------

	KH10203 ProKIT
--	----------------

320 i	95 kW	2 l	05/86→11/93
-------	-------	-----	-------------

; 07/86 -> 05/91	KH20060 ProKIT
------------------	----------------

; 10/87 -> 01/93; ABS	KH20111 ProKIT
-----------------------	----------------

	KH10203 ProKIT
--	----------------

325 i	125 kW	2.5 l	08/87→11/93
-------	--------	-------	-------------

; -> 12/92	KH20060 ProKIT
------------	----------------

; -> 01/93; ABS	KH20111 ProKIT
-----------------	----------------

	KH10203 ProKIT
--	----------------

325 i	126 kW	2.5 l	12/85→12/87
-------	--------	-------	-------------

; 02/86 ->	KH20060 ProKIT
------------	----------------

; 09/86 -> ABS	KH20111 ProKIT
----------------	----------------

	KH10203 ProKIT
--	----------------

**BMW - 3 Convertible (E36)**

03/93→11/99

318 i	85 kW	1.8 l	03/94→11/99
318 i	103 kW	1.8 l	01/94→12/95
320 i	110 kW	2 l	12/93→11/99
323 i	125 kW	2.5 l	05/95→11/99
325 i	141 kW	2.5 l	03/93→08/95

;	KH10007 ProKIT
;	KH10374 ProKIT

328 i	142 kW	2.8 l	01/95→11/99
-------	--------	-------	-------------

;	KH10007 ProKIT
---	----------------

M3 3.0	210 kW	3 l	04/94→07/95
--------	--------	-----	-------------

	KH10109 ProKIT
--	----------------

M3 3.2	236 kW	3.2 l	03/96→09/99
--------	--------	-------	-------------

**BMW - 3 Convertible (E46)**

04/00→12/07

318 Ci	100 kW	2 l	12/00→08/06
318 Ci	105 kW	2 l	09/01→12/07
318 Ci	110 kW	2 l	03/04→08/06
320 Cd	110 kW	2 l	02/05→12/07
320 Ci	120 kW	2.2 l	01/06→12/07
320 Ci	125 kW	2.2 l	09/00→12/07
323 Ci	120 kW	2.5 l	04/00→09/00
323 Ci	125 kW	2.5 l	04/00→09/00
325 Ci	141 kW	2.5 l	09/00→08/06

	KH20033 ProKIT
	KH10007 ProKIT

330 Cd	150 kW	3 l	08/05→12/07
--------	--------	-----	-------------

	KH20033 ProKIT
--	----------------

330 Ci	170 kW	3 l	06/00→08/06
--------	--------	-----	-------------

	KH10109 ProKIT
--	----------------

M3	252 kW	3.2 l	03/01→08/06
----	--------	-------	-------------

	KH20102 ProKIT
--	----------------






































	KH10109 ProKIT
--	----------------

**BMW - 3 Convertible (E93)**
























05/06→12/13

318 i	105 kW	2 l	03/10→12/13
320 d	120 kW	2 l	01/08→12/13
320 d	130 kW	2 l	03/08→02/10
320 d	135 kW	2 l	03/10→10/13
320 i	115 kW	2 l	01/07→08/13
320 i	120 kW	2 l	09/06→10/13
320 i	125 kW	2 l	03/07→10/13
325 d	145 kW	3 l	03/07→12/10
325 d	150 kW	3 l	09/09→09/13
325 d	155 kW	3 l	03/07→12/10
325 i	160 kW	2.5 l	12/06→02/10
325 i	155 kW	3 l	10/06→12/13
325 i	160 kW	3 l	03/07→12/13
330 d	170 kW	3 l	03/07→12/13
330 d	180 kW	3 l	01/09→12/13
330 i	190 kW	3 l	03/10→10/13
330 i	200 kW	3 l	03/07→02/10
330 i	200 kW	3 l	03/07→10/13
335 i	225 kW	3 l	12/06→10/13

	KH30080 ProKIT
	KH30080 ProKIT
	KH10008 ProKIT

												
<b>BMW - 3 Convertible (E93)</b>										<b>05/06→12/13</b>		
320 d	145 kW	2 l	09/07→02/10									<b>KH10008</b> ProKIT
320 d	147 kW	2 l	03/10→10/13									
335 i	240 kW	3 l	05/06→10/13									
M3	309 kW	4 l	03/08→10/13									<b>KH30179</b> ProKIT
												<b>KH10008</b> ProKIT
<b>BMW - 3 Coupe (E36, E46)</b>										<b>10/91→07/06</b>		
316 Ci	77 kW	1.6 l	04/00→07/06									<b>KH20033</b> ProKIT
316 Ci	85 kW	1.6 l	06/02→07/06								<b>KH10007</b> ProKIT	
318 Ci	85 kW	1.9 l	12/99→08/01									
318 Ci	87 kW	1.9 l	12/99→08/01									
318 Ci	100 kW	2 l	12/00→05/06									
318 Ci	105 kW	2 l	09/01→02/04									
318 Ci	110 kW	2 l	03/04→05/06									
320 Cd	110 kW	2 l	11/03→07/06									
320 Ci	110 kW	2 l	02/99→08/01									
320 Ci	120 kW	2.2 l	01/00→05/06									
320 Ci	125 kW	2.2 l	01/00→05/06									
323 Ci	120 kW	2.5 l	04/99→09/00									
323 Ci	125 kW	2.5 l	04/99→09/00									
325 Ci	141 kW	2.5 l	09/00→05/06									
328 Ci	142 kW	2.8 l	12/98→05/00									
328 i	142 kW	2.8 l	01/95→04/99									
316 i	75 kW	1.6 l	09/93→11/98									<b>KH20033</b> ProKIT
318 is	103 kW	1.8 l	01/92→12/95								<b>KH10007</b> ProKIT	
318 is	103 kW	1.9 l	09/95→04/99									
320 i	110 kW	2 l	12/91→11/98								<b>KH10374</b> ProKIT	
323 i	125 kW	2.5 l	05/95→04/99									
325 i	141 kW	2.5 l	10/91→02/95									
330 Cd	150 kW	3 l	03/03→07/06									<b>KH20033</b> ProKIT
330 Ci	170 kW	3 l	06/00→05/06									<b>KH10109</b> ProKIT
M3 3.0	217 kW	3 l	09/93→05/95									
M3 3.2	236 kW	3.2 l	10/95→11/98									
330 xi	170 kW	3 l	06/00→07/06								<b>KH10109</b> ProKIT	
M3	252 kW	3.2 l	07/00→05/06									<b>KH20102</b> ProKIT
M3 CSL	265 kW	3.2 l	05/03→12/03									<b>KH10109</b> ProKIT
M3 3.0	210 kW	3 l	11/92→07/95									<b>KH10109</b> ProKIT
<b>BMW - 3 Coupe (E92)</b>										<b>03/06→12/13</b>		
316 i	90 kW	1.6 l	09/07→06/13									<b>KH30080</b> ProKIT
318 i	105 kW	2 l	03/10→12/13								<b>KH10061</b> ProKIT	
320 d	120 kW	2 l	03/07→06/13									
320 d	130 kW	2 l	09/06→02/10									
320 d	135 kW	2 l	03/10→06/13									
320 i	115 kW	2 l	06/07→12/13									
320 i	120 kW	2 l	01/07→12/13									
320 i	125 kW	2 l	03/07→12/13									
320 d xDrive	120 kW	2 l	09/08→06/13									<b>KH10008</b> ProKIT
320 d xDrive	145 kW	2 l	09/08→02/10									
320 d xDrive	147 kW	2 l	03/10→06/13									
325 i xDrive	150 kW	2.5 l	03/10→04/13									
335 i	240 kW	3 l	06/06→06/13									
335 i xDrive	224 kW	3 l	01/09→06/13									
335 i xDrive	240 kW	3 l	11/08→06/13									
335 xi	240 kW	3 l	03/07→02/10									
M3 GTS	331 kW	4.4 l	03/07→12/13									
320 d xDrive	130 kW	2 l	09/08→02/10									<b>KH10153</b> ProKIT
325 xi	160 kW	2.5 l	09/06→02/10								<b>KH10008</b> ProKIT	
325 xi	160 kW	3 l	09/07→08/08									
330 xd	170 kW	3 l	03/06→08/08									
330 xd	180 kW	3 l	03/08→02/10									
330 xi	200 kW	3 l	09/06→08/07									
335 xi	225 kW	3 l	03/07→02/10									
320 d xDrive	135 kW	2 l	03/10→06/13			-> 02/11					<b>KH10153</b> ProKIT	
325 i xDrive	160 kW	3 l	09/08→12/13								<b>KH10008</b> ProKIT	
330 d xDrive	180 kW	3 l	02/10→06/13									
330 i xDrive	200 kW	3 l	03/10→06/13									
335 i xDrive	225 kW	3 l	11/08→12/13									



				     	
<b>BMW - 3 Coupe (E92)</b>				<b>03/06→12/13</b>	
325 d	145 kW	3 l	02/07→02/10		KH30080 ProKIT
325 d	150 kW	3 l	09/09→12/13		KH10008 ProKIT
325 d	155 kW	3 l	02/07→02/10		
330 d	170 kW	3 l	03/06→08/08		
330 d	180 kW	3 l	01/09→12/13		
330 i	190 kW	3 l	03/10→06/13		
330 i	200 kW	3 l	09/06→02/10		
330 i	200 kW	3 l	09/07→06/13		
335 d	210 kW	3 l	03/06→03/13		
335 i	225 kW	3 l	06/06→06/13		
325 i	155 kW	2.5 l	03/10→06/13		KH30080 ProKIT
325 i	160 kW	2.5 l	06/06→02/10		
325 i	160 kW	3 l	09/07→06/13		
328 i	172 kW	3 l	06/06→06/13		
M3	309 kW	4 l	06/07→06/13		KH30179 ProKIT
					KH10008 ProKIT
<b>BMW - 3 Gran Turismo (F34)</b>				<b>11/12→</b>	
318 d	100 kW	2 l	03/13→06/15	 Outer diameter [mm]: 85	KH10356 ProKIT
318 d	105 kW	2 l	03/13→06/15		
318 d	110 kW	2 l	07/15→		
320 d	120 kW	2 l	03/13→06/15		
320 d	135 kW	2 l	03/13→06/15		
320 d	140 kW	2 l	07/15→		
320 d	147 kW	2 l	03/13→06/15		
320 d xDrive	120 kW	2 l	07/13→06/15		
320 d xDrive	135 kW	2 l	07/13→06/15		
320 d xDrive	140 kW	2 l	07/15→		
320 d xDrive	147 kW	2 l	07/13→06/15		
320 i	120 kW	2 l	03/13→06/16		
320 i	135 kW	2 l	03/13→06/16		
320 i	135 kW	2 l	07/16→		
320 i xDrive	120 kW	2 l	07/13→06/16		
320 i xDrive	135 kW	2 l	11/12→06/16		
320 i xDrive	135 kW	2 l	07/16→		
325 d	155 kW	2 l	07/13→06/16		
325 d	160 kW	2 l	07/13→06/16		
325 d	165 kW	2 l	07/16→02/18		
328 i	180 kW	2 l	03/13→06/16		
328 i xDrive	180 kW	2 l	07/13→06/16		
330 d	190 kW	3 l	03/14→		
330 d	210 kW	3 l	03/14→		
330 d xDrive	190 kW	3 l	03/14→		
330 d xDrive	210 kW	3 l	03/14→		
330 i	185 kW	2 l	07/16→		
330 i xDrive	185 kW	2 l	07/16→		
335 d xDrive	230 kW	3 l	03/14→		
335 i	225 kW	3 l	03/13→06/16		
335 i	240 kW	3 l	03/13→03/14		
335 i	250 kW	3 l	04/14→06/16		
335 i xDrive	225 kW	3 l	07/13→06/16		
335 i xDrive	240 kW	3 l	03/13→03/14		
335 i xDrive	250 kW	3 l	04/14→06/16		
340 i	240 kW	3 l	07/16→		
340 i	265 kW	3 l	07/16→		
340 i xDrive	240 kW	3 l	07/16→		
340 i xDrive	265 kW	3 l	07/16→		
<b>BMW - 3 Sedan (E21)</b>				<b>06/75→10/82</b>	
320/6	90 kW	2 l	08/77→10/82		KH00039 ProKIT
320 i	92 kW	2 l	06/75→08/82		
323 i	105 kW	2.3 l	01/78→10/82		
<b>BMW - 3 Sedan (E30)</b>				<b>09/82→01/92</b>	
315	55 kW	1.6 l	09/82→12/91	 ; 09/85 ->; ABS	KH10203 ProKIT
316	66 kW	1.8 l	09/83→06/88		KH20060 ProKIT
				 ; ABS	KH20111 ProKIT
				 ; 09/85 ->; ABS	KH10203 ProKIT
316 (Ecotronic)	66 kW	1.8 l	09/83→06/88	 ; 10/83 ->	KH20060 ProKIT
				 ; ABS	KH20111 ProKIT
				 ; 09/85 ->; ABS	KH10203 ProKIT
316 i	73 kW	1.6 l	09/87→06/91	 ; 09/88 -> 12/90; ABS	KH20111 ProKIT
				 ; 09/88 ->	KH20060 ProKIT
				 ; 09/88 ->; ABS	KH10203 ProKIT



				13	i		
BMW - 3 Sedan (E30)						09/82→01/92	
316 i	75 kW	1.6 l	07/88→06/91		09/88 -> 12/90; ABS	KH2011 ProKIT	
					09/88 ->	KH20060 ProKIT	
					ABS	KH10203 ProKIT	
316 i	75 kW	1.8 l	08/87→08/88		ABS	KH10203 ProKIT	
325 i X	125 kW	2.5 l	09/86→08/91				
325 i X	126 kW	2.5 l	03/86→12/87				
M3 2.3	143 kW	2.3 l	07/86→06/91				
M3 2.3	147 kW	2.3 l	02/87→05/89				
M3 2.3	158 kW	2.3 l	01/86→12/90				
M3 EVO I 2.3	162 kW	2.3 l	10/88→10/90				
M3 EVO II 2.5	175 kW	2.5 l	01/90→01/92				
318 i	75 kW	1.8 l	12/84→08/88			KH20060 ProKIT	
318 i	77 kW	1.8 l	09/82→08/87		09/85 -> ABS	KH10203 ProKIT	
318 i	83 kW	1.8 l	06/87→12/91		10/87 -> 04/91; ABS	KH20111 ProKIT	
318 i	85 kW	1.8 l	09/87→06/91			KH20060 ProKIT	
					ABS	KH10203 ProKIT	
318 is	100 kW	1.8 l	09/89→08/91		11/89 ->	KH20060 ProKIT	
					02/90 -> 04/91; ABS	KH20111 ProKIT	
					ABS	KH10203 ProKIT	
320 i	92 kW	2 l	09/82→12/91		03/83 -> ABS	KH20111 ProKIT	
					09/85 -> ABS	KH10203 ProKIT	
320 i	95 kW	2 l	10/86→04/91		-> 12/90; ABS	KH20111 ProKIT	
						KH20060 ProKIT	
					ABS	KH10203 ProKIT	
323 i	102 kW	2.3 l	09/82→08/83		03/83 -> ABS	KH20111 ProKIT	
						KH20060 ProKIT	
323 i	110 kW	2.3 l	09/83→09/86		-> 07/85; ABS	KH20111 ProKIT	
					-> 05/86	KH20060 ProKIT	
					09/85 -> ABS	KH10203 ProKIT	
324 d	63 kW	2.4 l	09/85→12/90			KH20060 ProKIT	
324 td	85 kW	2.4 l	09/87→08/91		ABS	KH20111 ProKIT	
					ABS	KH10203 ProKIT	
325 e 2.7	90 kW	2.7 l	10/83→12/88		02/85 -> 08/87	KH20060 ProKIT	
					09/85 -> ABS	KH10203 ProKIT	
325 e 2.7	95 kW	2.7 l	01/85→08/87		02/85 ->	KH20060 ProKIT	
					09/85 -> ABS	KH10203 ProKIT	
325 i	125 kW	2.5 l	12/86→06/91		-> 12/90; ABS	KH20111 ProKIT	
					-> 03/91	KH20060 ProKIT	
					ABS	KH10203 ProKIT	
325 i	126 kW	2.5 l	09/83→11/89		09/85 -> 09/89	KH20060 ProKIT	
					10/85 -> ABS	KH20111 ProKIT	
					09/85 -> ABS	KH10203 ProKIT	
BMW - 3 Sedan (E36)						09/90→11/98	
316 i	73 kW	1.6 l	03/91→08/93			KH10007 ProKIT	
316 i	75 kW	1.6 l	09/93→05/98			KH10374 ProKIT	
318 i	83 kW	1.8 l	09/90→08/93				
318 i	85 kW	1.8 l	09/93→11/98				
318 is	103 kW	1.8 l	09/93→12/95				
318 is	103 kW	1.9 l	01/96→05/98				
318 tds	66 kW	1.7 l	01/95→02/98				
320 i	110 kW	2 l	01/91→02/98				
323 i	125 kW	2.5 l	05/95→11/98				
325 i	141 kW	2.5 l	09/90→12/95				
325 td	85 kW	2.5 l	09/91→02/98				
325 tds	105 kW	2.5 l	05/93→02/98				
328 i	142 kW	2.8 l	01/95→04/98			KH10007 ProKIT	
BMW - 3 Sedan (E46)						12/97→05/05	
316 i	77 kW	1.6 l	04/00→02/05			KH10007 ProKIT	
316 i	85 kW	1.6 l	06/02→02/05				
316 i	85 kW	1.8 l	02/02→02/05				
316 i	77 kW	1.9 l	12/98→02/02				
318 d	85 kW	2 l	09/01→03/03				
318 d	85 kW	2 l	03/03→02/05				
318 i	87 kW	1.9 l	12/97→09/01				
318 i	100 kW	2 l	09/01→02/05				
318 i	105 kW	2 l	09/01→02/05				





**BMW - 3 Sedan (E46)**
















































**12/97→05/05**

320 d	95 kW	2 l	02/98→08/01		KH10007 ProKIT
320 d	100 kW	2 l	04/98→09/01		
320 d	110 kW	2 l	09/01→05/05		
320 i	110 kW	2 l	03/98→09/00		
320 i	120 kW	2.2 l	09/00→02/05		
320 i	125 kW	2.2 l	09/00→02/05		
323 i	120 kW	2.5 l	03/98→09/00		
323 i	125 kW	2.5 l	03/98→09/00		
325 i	141 kW	2.5 l	09/00→02/05		
328 i	142 kW	2.8 l	02/98→06/00		
325 xi	141 kW	2.5 l	09/00→02/05		KH10109 ProKIT
330 xd	135 kW	3 l	01/00→02/03		
330 xd	150 kW	3 l	09/02→12/04		
330 xi	170 kW	3 l	06/00→02/05		KH10109 ProKIT
330 d	135 kW	3 l	10/99→02/05		
330 d	150 kW	3 l	03/03→02/05		
330 i	168 kW	3 l	01/01→04/05		
330 i	170 kW	3 l	06/00→02/05		

**BMW - 3 Sedan (E90)**

**12/04→12/11**

316 d	85 kW	2 l	07/09→12/11		KH30080 ProKIT	
316 i	85 kW	1.6 l	09/05→10/11		KH10061 ProKIT	
316 i	90 kW	1.6 l	09/07→10/11			
318 d	90 kW	2 l	03/05→08/07		KH10008 ProKIT	
318 d	100 kW	2 l	09/07→10/11			
318 d	105 kW	2 l	02/07→10/11			
318 i	95 kW	2 l	09/05→08/07			
318 i	100 kW	2 l	09/07→10/11			
318 i	105 kW	2 l	09/07→10/11			
320 i	110 kW	2 l	12/04→08/07			
320 i	115 kW	2 l	02/07→12/11			
320 i	120 kW	2 l	03/07→12/11			
320 i	125 kW	2 l	09/07→10/11			
323 i	130 kW	2.5 l	09/05→02/07			
323 i	140 kW	2.5 l	03/07→12/11			
328 i	172 kW	3 l	09/06→12/11			
320 d	110 kW	2 l	12/04→09/07			KH30080 ProKIT
320 d	120 kW	2 l	12/04→10/11			
320 d	130 kW	2 l	09/07→02/10	<b>for government vehicles</b>		KH10008 ProKIT
320 d	135 kW	2 l	03/10→10/11			
325 i	155 kW	2.5 l	01/06→12/11		KH10061 ProKIT	
325 i	160 kW	2.5 l	12/04→12/11			
325 i	155 kW	3 l	03/07→12/11			
325 i	160 kW	3 l	03/07→12/11			
320 d	115 kW	2 l	12/04→09/07	<b>for government vehicles</b>	KH10008 ProKIT	
320 d xDrive	120 kW	2 l	09/08→10/11			
325 i xDrive	155 kW	3 l	09/08→10/11		KH10061 ProKIT	
320 d xDrive	130 kW	2 l	09/08→02/10			
325 xi	160 kW	2.5 l	09/05→08/08	<b>for government vehicles</b>	KH10008 ProKIT	
325 xi	160 kW	3 l	09/07→08/08			
320 d xDrive	135 kW	2 l	03/10→10/11	<b>-&gt; 02/11</b>	KH10153 ProKIT	
				<b>for government vehicles</b>		
320 si	127 kW	2 l	09/05→08/06		KH30080 ProKIT	
					KH10061 ProKIT	
325 d	145 kW	3 l	09/06→02/10		KH30080 ProKIT	
325 d	150 kW	3 l	03/10→10/11			
330 d	155 kW	3 l	09/05→12/11		KH10008 ProKIT	
330 d	170 kW	3 l	09/05→09/08			
330 d	180 kW	3 l	09/08→10/11			
330 i	190 kW	3 l	12/04→10/11			
330 i	200 kW	3 l	03/07→12/11			
330 i	200 kW	3 l	09/07→10/11			
335 d	210 kW	3 l	09/06→12/11			
335 i	220 kW	3 l	03/06→12/11			
335 i	224 kW	3 l	03/06→12/11			
335 i	225 kW	3 l	09/06→12/11			
335 i	240 kW	3 l	03/06→12/11			
325 i xDrive	160 kW	3 l	09/08→10/11	<b>-&gt; 02/10</b>		KH10153 ProKIT
				<b>for government vehicles</b>		
						KH10061 ProKIT
330 d xDrive	180 kW	3 l	09/08→10/11	<b>-&gt; 02/11</b>		KH10153 ProKIT
330 i xDrive	200 kW	3 l	09/08→10/11			
335 i xDrive	225 kW	3 l	09/08→10/11		KH10008 ProKIT	

				   	 13		
<b>BMW - 3 Sedan (E90)</b>							<b>12/04→12/11</b>
330 xd	170 kW	3 l	09/05→08/08				KH10153 ProKIT
330 xi	190 kW	3 l	09/05→08/07				KH10008 ProKIT
330 xi	200 kW	3 l	09/07→08/08				
335 xi	225 kW	3 l	03/07→08/08				
335 i xDrive	240 kW	3 l	05/08→10/11				KH10008 ProKIT
335 xi	224 kW	3 l	09/06→06/08				
335 xi	240 kW	3 l	09/06→06/08				
M3 CRT	331 kW	4.4 l	03/11→12/11				
M3	309 kW	4 l	12/07→10/11				KH30179 ProKIT
							KH10008 ProKIT
<b>BMW - 3 Touring (E30)</b>							<b>07/87→06/94</b>
316 i	73 kW	1.6 l	09/91→06/94	 ; 10/91 -> 02/94; ABS			KH20111 ProKIT
				 ; -> 09/93			KH20060 ProKIT
							KH10203 ProKIT
316 i	75 kW	1.6 l	09/91→06/94	 ; 10/91 -> 02/94; ABS			KH20111 ProKIT
							KH10203 ProKIT
318 i	83 kW	1.8 l	04/89→06/94	 ; -> 09/93			KH20060 ProKIT
				 ; -> 02/94; ABS			KH20111 ProKIT
							KH10203 ProKIT
318 i	85 kW	1.8 l	09/87→06/91	 ; 09/88 ->			KH20060 ProKIT
				 ; 04/89 ->; ABS			KH20111 ProKIT
							KH10203 ProKIT
320 i	95 kW	2 l	01/88→12/91	 ; 09/88 -> 04/91; ABS			KH20111 ProKIT
				 ; 09/88 ->			KH20060 ProKIT
							KH10203 ProKIT
324 td	85 kW	2.4 l	01/88→06/93	 ; 06/88 ->			KH20060 ProKIT
				 ; ABS			KH20111 ProKIT
							KH10203 ProKIT
325 i	125 kW	2.5 l	07/87→03/93	 ; 02/88 ->			KH20060 ProKIT
				 ; 04/88 -> 01/93; ABS			KH20111 ProKIT
							KH10203 ProKIT
325 i X	125 kW	2.5 l	06/88→10/93				KH10203 ProKIT
<b>BMW - 3 Touring (E36)</b>							<b>01/95→05/99</b>
316 i	75 kW	1.6 l	03/97→05/99				KH20033 ProKIT
318 i	85 kW	1.8 l	09/95→04/99				KH10007 ProKIT
318 tds	66 kW	1.7 l	03/95→04/99	 ; 			KH10374 ProKIT
320 i	110 kW	2 l	01/95→04/99	 ; 			
323 i	125 kW	2.5 l	12/95→04/99				
325 tds	105 kW	2.5 l	03/95→04/99				
328 i	142 kW	2.8 l	02/95→04/99				KH20033 ProKIT
				 ; 			KH10007 ProKIT
<b>BMW - 3 Touring (E46)</b>							<b>06/99→07/05</b>
316 i	85 kW	1.8 l	03/02→02/05				KH20033 ProKIT
318 d	85 kW	2 l	10/02→03/03				KH10007 ProKIT
318 d	85 kW	2 l	03/03→02/05				
318 i	85 kW	1.9 l	10/99→09/01				
318 i	87 kW	1.9 l	10/99→09/01				
318 i	105 kW	2 l	09/01→07/05				
320 d	100 kW	2 l	03/00→09/01				
320 d	110 kW	2 l	09/01→02/05				
320 i	110 kW	2 l	10/99→09/00				
320 i	120 kW	2.2 l	09/00→02/05				
320 i	125 kW	2.2 l	09/00→02/05				
325 i	141 kW	2.5 l	09/00→02/05				
328 i	142 kW	2.8 l	06/99→05/00				
325 xi	141 kW	2.5 l	09/00→02/05	 ; 			KH10109 ProKIT
330 xd	135 kW	3 l	01/00→03/03				
330 xd	150 kW	3 l	08/02→05/05				
330 xi	170 kW	3 l	06/00→02/05				
330 d	135 kW	3 l	10/99→02/05				KH20033 ProKIT
330 d	150 kW	3 l	03/03→02/05				KH10109 ProKIT
330 i	170 kW	3 l	06/00→02/05				





**BMW - 3 Touring (E91)**

**12/04→12/12**

316 d	85 kW	2 l	09/09→06/12		<b>KH30080</b> ProKIT
316 i	90 kW	1.6 l	09/08→06/12		
318 d	90 kW	2 l	09/05→08/07	; for government vehicles	<b>KH10008</b> ProKIT
318 d	100 kW	2 l	07/07→06/12	;	<b>KH10061</b> ProKIT
318 d	105 kW	2 l	09/07→06/12		
318 i	95 kW	2 l	01/06→08/07		
318 i	100 kW	2 l	09/07→03/12		
318 i	105 kW	2 l	05/07→05/12		
320 d	120 kW	2 l	06/05→06/12		
320 i	110 kW	2 l	09/05→06/12		
320 i	125 kW	2 l	02/07→12/12		
320 d	110 kW	2 l	12/04→08/07		<b>KH30080</b> ProKIT
320 d	130 kW	2 l	02/07→12/10		<b>KH10008</b> ProKIT
320 d	135 kW	2 l	03/10→05/12	;	<b>KH10061</b> ProKIT
320 d	145 kW	2 l	02/07→02/10		<b>KH10008</b> ProKIT
320 d	147 kW	2 l	03/10→05/12		
320 d xDrive	120 kW	2 l	07/09→06/12		
320 d xDrive	145 kW	2 l	02/08→02/10		
320 d xDrive	147 kW	2 l	03/10→05/12		
320 i	120 kW	2 l	02/07→05/12		
325 i xDrive	155 kW	3 l	09/08→06/12		
325 xi	155 kW	3 l	09/07→08/08		
335 i xDrive	240 kW	3 l	09/08→06/12		
335 xi	240 kW	3 l	03/07→08/08		
320 d xDrive	130 kW	2 l	09/08→02/10		<b>KH10153</b> ProKIT
325 xi	160 kW	2.5 l	08/05→08/08		
325 xi	160 kW	3 l	09/07→08/08		<b>KH10008</b> ProKIT
330 xi	190 kW	3 l	09/05→08/07		
335 xi	225 kW	3 l	03/07→08/08		
320 d xDrive	135 kW	2 l	03/10→06/12	; -> 02/11	<b>KH10153</b> ProKIT
325 i xDrive	160 kW	3 l	09/08→06/12		<b>KH10008</b> ProKIT
330 d xDrive	180 kW	3 l	01/09→06/12		
330 i xDrive	200 kW	3 l	09/07→06/12		
330 xd	170 kW	3 l	09/05→06/12		
330 xi	200 kW	3 l	09/07→06/12		
335 i xDrive	225 kW	3 l	09/08→06/12		
320 i	115 kW	2 l	09/05→06/12		<b>KH10008</b> ProKIT
				;	<b>KH10061</b> ProKIT
323 i	130 kW	2.5 l	04/06→06/07		<b>KH30080</b> ProKIT
323 i	140 kW	2.5 l	09/06→07/08		<b>KH10008</b> ProKIT
325 d	145 kW	3 l	09/06→06/12		
325 d	150 kW	3 l	02/10→06/12		
325 i	155 kW	2.5 l	12/04→12/10		
325 i	160 kW	2.5 l	12/04→08/08		
325 i	155 kW	3 l	09/07→06/12		
325 i	160 kW	3 l	09/07→06/12		
330 d	155 kW	3 l	06/05→05/12		
330 d	170 kW	3 l	12/04→08/08		
330 d	180 kW	3 l	02/08→05/12		
330 i	190 kW	3 l	08/05→08/07		
330 i	200 kW	3 l	09/07→06/12		
335 d	210 kW	3 l	09/06→06/12		
335 i	225 kW	3 l	09/06→06/12		
335 i	240 kW	3 l	09/06→06/12		

**BMW - 3 Touring (F31)**

**07/12→06/19**

316 d	85 kW	2 l	11/12→06/19		<b>KH10354</b> ProKIT
316 i	100 kW	1.6 l	03/13→06/15		
318 d	100 kW	2 l	11/12→06/19	; Outer diameter [mm]: 85	<b>KH10356</b> ProKIT
318 d	105 kW	2 l	11/12→06/15		
318 d	110 kW	2 l	07/15→06/19		
318 i	100 kW	1.5 l	07/15→06/19		
320 d	120 kW	2 l	07/12→06/19		
320 d	135 kW	2 l	07/12→02/16		
320 d	140 kW	2 l	07/15→06/19		
320 d	147 kW	2 l	07/12→02/16		
320 i	120 kW	2 l	11/12→06/15		
320 i	135 kW	2 l	11/12→06/15		
320 i	135 kW	2 l	07/15→06/19		
325 d	155 kW	2 l	03/13→02/16		
325 d	160 kW	2 l	03/13→02/16		
325 d	165 kW	2 l	03/16→02/18		
328 i	180 kW	2 l	07/12→06/15		
330 d	190 kW	3 l	07/12→06/19		
330 d	210 kW	3 l	07/12→06/19		
330 i	185 kW	2 l	07/15→06/19		
335 i	225 kW	3 l	03/13→06/15		
335 i	240 kW	3 l	03/13→06/13		



**BMW - 3 Touring (F31)** **07/12→06/19**

335 i	250 kW	3 l	07/13→06/15		KH10354 ProKIT
340 i	240 kW	3 l	07/15→06/19		KH10356 ProKIT
340 i	265 kW	3 l	07/15→06/19	Outer diameter [mm]: 85	KH10356 ProKIT
318 d xDrive	105 kW	2 l	07/13→06/15	Outer diameter [mm]: 85	KH10356 ProKIT
318 d xDrive	110 kW	2 l	07/15→02/18		
320 d xDrive	120 kW	2 l	03/13→06/19		
320 d xDrive	135 kW	2 l	03/13→06/15		
320 d xDrive	140 kW	2 l	07/15→06/19		
320 d xDrive	147 kW	2 l	03/13→06/15		
320 i xDrive	120 kW	2 l	03/13→06/15		
320 i xDrive	135 kW	2 l	03/13→06/15		
320 i xDrive	135 kW	2 l	07/15→06/19		
328 i xDrive	180 kW	2 l	03/13→06/16		
330 d xDrive	190 kW	3 l	03/13→06/19		
330 d xDrive	210 kW	3 l	03/13→06/19		
330 i xDrive	185 kW	2 l	07/15→06/19		
335 d xDrive	230 kW	3 l	11/13→06/19		
335 i xDrive	225 kW	3 l	03/13→06/15		
335 i xDrive	240 kW	3 l	03/13→06/13		
335 i xDrive	250 kW	3 l	07/13→06/15		
340 i xDrive	240 kW	3 l	07/15→06/19		
340 i xDrive	265 kW	3 l	07/15→06/19		

**BMW - 4 Convertible / 4 Coupe / 4 Gran Coupe (F33, F83, F32, F82, F36)** **07/13→**

418 d	100 kW	2 l	03/14→12/20		KH10354 ProKIT
418 d	100 kW	2 l	03/15→10/17		KH10356 ProKIT
418 d	105 kW	2 l	03/14→06/15	Outer diameter [mm]: 85	KH10356 ProKIT
418 d	110 kW	2 l	03/15→10/17		
418 d	110 kW	2 l	07/15→12/20		
418 i	100 kW	1.5 l	07/15→		
418 i	100 kW	1.5 l	03/16→		
420 d	120 kW	2 l	07/13→02/15		
420 d	120 kW	2 l	11/13→		
420 d	120 kW	2 l	03/14→12/20		
420 d	135 kW	2 l	07/13→02/15		
420 d	135 kW	2 l	10/13→06/15		
420 d	135 kW	2 l	03/14→02/15		
420 d	140 kW	2 l	03/15→		
420 d	140 kW	2 l	07/15→		
420 d	147 kW	2 l	07/13→03/15		
420 d	147 kW	2 l	10/13→06/15		
420 d	147 kW	2 l	03/14→02/15		
420 i	120 kW	2 l	11/13→02/17		
420 i	120 kW	2 l	03/14→02/17		
420 i	120 kW	2 l	07/14→02/16		
420 i	120 kW	2 l	03/16→		
420 i	135 kW	2 l	11/13→02/17		
420 i	135 kW	2 l	03/14→02/17		
420 i	135 kW	2 l	07/14→02/16		
420 i	135 kW	2 l	03/16→		
425 d	155 kW	2 l	03/14→02/16		
425 d	155 kW	2 l	07/14→02/16		
425 d	155 kW	2 l	03/16→02/18		
425 d	160 kW	2 l	03/14→02/16		
425 d	160 kW	2 l	07/14→02/16		
425 d	165 kW	2 l	03/16→10/17		
425 d	165 kW	2 l	03/16→02/18		
428 i	180 kW	2 l	07/13→02/17		
428 i	180 kW	2 l	11/13→02/17		
428 i	180 kW	2 l	03/14→06/16		
430 d	190 kW	3 l	11/13→		
430 d	190 kW	3 l	07/14→		
430 d	210 kW	3 l	11/13→		
430 d	210 kW	3 l	07/14→		
430 i	185 kW	2 l	03/16→		
435 i	225 kW	3 l	07/13→02/16		
435 i	225 kW	3 l	11/13→02/16		
435 i	225 kW	3 l	03/14→02/16		
435 i	250 kW	3 l	07/13→02/16		
435 i	250 kW	3 l	11/13→02/16		
435 i	250 kW	3 l	03/14→02/16		
440 i	240 kW	3 l	03/16→		
440 i	265 kW	3 l	03/16→		
M4	317 kW	3 l	03/14→		
M4	317 kW	3 l	07/14→		
M4 Competition	331 kW	3 l	03/16→		
M4 CS	338 kW	3 l	07/17→06/19		
M4 GTS	368 kW	3 l	03/16→02/17		
420 d xDrive	120 kW	2 l	11/13→	Outer diameter [mm]: 85	KH10356 ProKIT
420 d xDrive	120 kW	2 l	03/14→12/20		
420 d xDrive	135 kW	2 l	11/13→02/15		





**BMW - 4 Convertible / 4 Coupe / 4 Gran Coupe (F33, F83, F32, F82, F36)**

07/13→

420 d xDrive	135 kW	2 l	03/14→02/15
420 d xDrive	140 kW	2 l	03/15→
420 d xDrive	147 kW	2 l	11/13→03/15
420 d xDrive	147 kW	2 l	03/14→02/15
420 i xDrive	120 kW	2 l	11/13→02/16
420 i xDrive	120 kW	2 l	07/14→02/16
420 i xDrive	120 kW	2 l	03/16→
420 i xDrive	135 kW	2 l	11/13→02/16
420 i xDrive	135 kW	2 l	07/14→02/16
420 i xDrive	135 kW	2 l	03/16→
428 i xDrive	180 kW	2 l	07/13→02/16
428 i xDrive	180 kW	2 l	03/14→02/16
430 d xDrive	190 kW	3 l	03/14→
430 d xDrive	190 kW	3 l	07/14→
430 d xDrive	210 kW	3 l	03/14→
430 d xDrive	210 kW	3 l	07/14→
430 i xDrive	185 kW	2 l	03/16→
435 d xDrive	230 kW	3 l	11/13→12/20
435 d xDrive	230 kW	3 l	07/14→
435 i xDrive	225 kW	3 l	07/13→02/16
435 i xDrive	225 kW	3 l	07/14→02/16
435 i xDrive	250 kW	3 l	07/13→02/16
435 i xDrive	250 kW	3 l	07/14→02/16
440 i xDrive	240 kW	3 l	03/16→
440 i xDrive	265 kW	3 l	03/16→

; Outer diameter [mm]: 85	KH10356 ProKIT
---------------------------	----------------

**BMW - 5 / 5 Gran Turismo (F10, F07)**



















































01/09→02/17

518 d	100 kW	2 l	07/13→10/16
518 d	105 kW	2 l	07/13→06/14
518 d	110 kW	2 l	07/14→10/16
520 d	120 kW	2 l	06/10→10/16
520 d	120 kW	2 l	07/12→06/13
520 d	135 kW	2 l	06/10→06/14
520 d	135 kW	2 l	04/11→02/17
520 d	140 kW	2 l	07/14→10/16
520 i	125 kW	1.6 l	07/13→10/16
520 i	120 kW	2 l	09/11→10/16
520 i	135 kW	2 l	09/11→10/16
523 i	150 kW	3 l	06/09→08/11
525 d	155 kW	2 l	09/11→10/16
525 d	160 kW	2 l	09/11→10/16
525 d	150 kW	3 l	03/10→08/11
528 i	180 kW	2 l	09/11→10/16
528 i	180 kW	2 l	07/13→02/17
528 i	190 kW	3 l	03/10→08/11
530 d	155 kW	3 l	09/10→02/17
530 d	180 kW	3 l	08/09→06/12
530 d	180 kW	3 l	01/10→08/11
530 d	190 kW	3 l	09/11→10/16
530 d	190 kW	3 l	07/12→02/17
530 d	210 kW	3 l	09/10→10/16
530 i	200 kW	3 l	05/11→06/13
535 d	220 kW	3 l	03/10→06/12
535 d	220 kW	3 l	09/10→08/11
535 d	230 kW	3 l	09/11→10/16
535 d	230 kW	3 l	07/12→02/17
535 i	225 kW	3 l	01/09→02/17
535 i	225 kW	3 l	01/10→10/16
535 i	240 kW	3 l	07/13→10/16
550 i	300 kW	4.4 l	08/09→06/12
550 i	300 kW	4.4 l	03/10→06/13
550 i	330 kW	4.4 l	07/12→02/17
550 i	330 kW	4.4 l	07/13→10/16
ActiveHybrid	250 kW	3 l	12/11→10/16







; Thread Size: M12x1.25	KH30110 ProKIT
	KH20124 ProKIT

520 d xDrive	120 kW	2 l	10/13→10/16
520 d xDrive	135 kW	2 l	07/13→06/14
520 d xDrive	140 kW	2 l	07/14→10/16
523 i	150 kW	2.5 l	01/10→08/11
525 d xDrive	155 kW	2 l	09/11→10/16
525 d xDrive	160 kW	2 l	09/11→10/16
528 i xDrive	180 kW	2 l	09/11→10/16
530 d xDrive	180 kW	3 l	06/10→06/12
530 d xDrive	190 kW	3 l	03/11→10/16
530 d xDrive	190 kW	3 l	07/12→02/17
530 d xDrive	210 kW	3 l	03/11→10/16
535 d xDrive	220 kW	3 l	03/10→06/12
535 d xDrive	230 kW	3 l	09/11→10/16
535 d xDrive	230 kW	3 l	07/12→02/17
535 i xDrive	225 kW	3 l	09/10→02/17
535 i xDrive	225 kW	3 l	03/11→10/16
535 i xDrive	240 kW	3 l	07/13→10/16

	KH20124 ProKIT
--	----------------

     					
BMW - 5 / 5 Gran Turismo (F10, F07)				01/09→02/17	
550 i xDrive	300 kW	4.4 l	06/10→06/12		KH20124 ProKIT
550 i xDrive	300 kW	4.4 l	08/10→06/13		
550 i xDrive	330 kW	4.4 l	07/12→02/17		
550 i xDrive	330 kW	4.4 l	07/13→10/16		
BMW - 5 Sedan (E12)				03/72→06/81	
518	66 kW	1.8 l	07/74→05/81		KH00039 ProKIT
520	85 kW	2 l	06/72→01/79		
520/6	90 kW	2 l	03/77→06/81		
520 i	92 kW	2 l	03/72→07/79		
520 i	96 kW	2 l	08/72→10/75		
525	107 kW	2.5 l	10/73→08/76		
525	110 kW	2.5 l	08/75→06/81		
528	121 kW	2.8 l	01/75→08/76		
528	125 kW	2.8 l	08/75→07/77		
528 i	130 kW	2.8 l	03/77→09/79		
528 i	135 kW	2.8 l	08/79→06/81		
M535 i	160 kW	3.5 l	04/80→05/81	 ; 09/80 ->	KH00041 ProKIT
BMW - 5 Sedan (E28, E34)				05/81→12/95	
518	66 kW	1.8 l	06/81→09/84	 ; 10/81 ->; 	KH20112 ProKIT
518 i	77 kW	1.8 l	05/81→12/87	 ; 01/85 ->; 	KH20112 ProKIT
518 i	83 kW	1.8 l	09/89→04/94		KH10188 ProKIT
518 i	85 kW	1.8 l	05/94→08/95		
520 i	95 kW	2 l	06/87→09/90		
520 i 24V	110 kW	2 l	04/90→08/95		
525 i	125 kW	2.5 l	02/88→08/90		
525 i 24V	141 kW	2.5 l	03/90→08/95		
525 iX 24V	141 kW	2.5 l	10/91→08/95		
525 td	85 kW	2.5 l	03/93→08/95		
525 tds	105 kW	2.5 l	09/91→08/95		
530 i	138 kW	3 l	01/88→04/90		
530 i V8	160 kW	3 l	09/92→12/95		
535 i, M 535 i	136 kW	3.4 l	01/85→12/87		
535 i, M 535 i	141 kW	3.4 l	01/85→12/87		
540 i V8	210 kW	4 l	09/92→12/95		
M5	232 kW	3.6 l	09/88→03/92		
M5	250 kW	3.8 l	01/92→07/95		
520 i	92 kW	2 l	06/81→12/87	 ; 10/81 ->; 	KH20112 ProKIT
				 -> 09/86; 	KH10188 ProKIT
520 i	95 kW	2 l	08/85→12/87		KH20112 ProKIT
524 td	85 kW	2.4 l	09/83→12/87	 -> 09/86; 	KH10188 ProKIT
524 d	63 kW	2.4 l	03/86→12/87		KH20112 ProKIT
535 i	162 kW	3.4 l	01/85→12/87		KH10188 ProKIT
525 e	90 kW	2.7 l	09/81→12/87	 -> 09/86	KH10188 ProKIT
525 e	92 kW	2.7 l	03/83→12/87	 ; 06/83 ->; 	KH20112 ProKIT
				 -> 09/86	KH10188 ProKIT
525 e	95 kW	2.7 l	09/85→12/87	 ; 	KH20112 ProKIT
				 -> 09/86	KH10188 ProKIT
525 i	110 kW	2.5 l	06/81→12/87	 ; 10/81 -> 10/87; 	KH20112 ProKIT
				 -> 04/86	KH10188 ProKIT
528 i	135 kW	2.8 l	06/81→12/87	 ; 10/81 ->; 	KH20112 ProKIT
					KH10188 ProKIT
M5	210 kW	3.5 l	08/85→12/87	 ; 07/86 ->; 	KH20112 ProKIT
					KH10188 ProKIT
BMW - 5 Sedan (E39)				09/95→06/03	
520 d	100 kW	2 l	02/00→06/03	 -> 04/03	KH20067 ProKIT
525 td	85 kW	2.5 l	01/97→06/03		
520 i	100 kW	2 l	01/96→06/03	 ; 07/99 -> 04/03	KH20067 ProKIT
535 i	180 kW	3.5 l	09/98→06/03		
520 i	110 kW	2 l	01/96→06/03	 ; 04/96 -> 08/00	KH30078 ProKIT
				 ; 07/96 ->	KH20067 ProKIT
520 i	125 kW	2.2 l	09/00→06/03		KH30078 ProKIT
525 i	141 kW	2.5 l	09/00→06/03		KH20067 ProKIT
530 i	170 kW	3 l	09/00→06/03	 -> 04/03	KH20067 ProKIT
523 i	125 kW	2.5 l	09/95→08/00	 ; 04/96 ->	KH30078 ProKIT
528 i	142 kW	2.8 l	09/95→08/00		KH20067 ProKIT
525 d	120 kW	2.5 l	02/00→06/03	 ; 09/00 ->	KH30078 ProKIT
				 -> 04/03	KH20067 ProKIT



     					
<b>BMW - 5 Sedan (E39)</b>				<b>09/95→06/03</b>	
530 d	135 kW	3 l	08/98→09/00	; 09/98 ->	KH30078 ProKIT
				; 09/98 ->	KH20067 ProKIT
530 d	142 kW	3 l	09/98→06/03	; 03/01 ->	KH30078 ProKIT
				; -> 04/03	KH20067 ProKIT
535 i	173 kW	3.5 l	06/96→08/98	; 09/96 ->	KH30078 ProKIT
				; 07/96 ->	KH20067 ProKIT
540 i	210 kW	4.4 l	03/96→06/03	; 06/96 ->	KH30078 ProKIT
M5	294 kW	4.9 l	10/98→06/03	; 07/99 ->	KH20067 ProKIT
<b>BMW - 5 Sedan (E60)</b>				<b>12/01→03/10</b>	
520 d	110 kW	2 l	09/05→02/07		KH30063 ProKIT
525 d	120 kW	2.5 l	12/04→03/10		
535 d	210 kW	3 l	01/07→03/10		
520 d	120 kW	2 l	09/05→12/09		KH30063 ProKIT
				; -> 08/07	KH20067 ProKIT
520 d	130 kW	2 l	09/07→12/09		KH30063 ProKIT
520 i	125 kW	2 l	09/07→12/09		KH20067 ProKIT
523 i	140 kW	2.5 l	03/07→12/09		
525 d	145 kW	3 l	01/07→03/10		
525 i	141 kW	2.5 l	09/03→02/05		
525 i	160 kW	3 l	01/07→03/10		
530 d	160 kW	3 l	09/02→09/05		
530 d	173 kW	3 l	02/07→12/09		
540 i	225 kW	4 l	03/07→12/09		
545 i	245 kW	4.4 l	09/03→08/05		
520 i	125 kW	2.2 l	07/03→03/10		KH30063 ProKIT
				; -> 03/05	KH20067 ProKIT
523 i	130 kW	2.5 l	10/04→02/07		KH30063 ProKIT
525 d	130 kW	2.5 l	06/04→03/10		
525 i	160 kW	2.5 l	03/05→12/09	; -> 12/06	KH20067 ProKIT
530 d	170 kW	3 l	09/05→03/07		
535 d	200 kW	3 l	09/04→03/10		
525 d xDrive	145 kW	3 l	09/07→12/09		KH10153 ProKIT
					KH20067 ProKIT
525 i xDrive	160 kW	3 l	09/08→03/10		KH10153 ProKIT
525 xd	145 kW	3 l	11/06→08/07		
525 xi	160 kW	3 l	03/07→12/09		
530 d xDrive	173 kW	3 l	09/07→12/09		
530 i xDrive	200 kW	3 l	09/08→12/09		
530 xd	173 kW	3 l	03/07→08/07		
530 xi	200 kW	3 l	02/07→08/08		
525 xi	160 kW	2.5 l	04/05→02/07		KH10153 ProKIT
530 xi	190 kW	3 l	09/04→02/07	; -> 12/06	KH20067 ProKIT
530 i	170 kW	3 l	12/01→02/05		KH30063 ProKIT
530 i	200 kW	3 l	03/07→12/09		KH20067 ProKIT
550 i	270 kW	4.8 l	09/05→12/09		
530 i	190 kW	3 l	03/05→03/07		KH30063 ProKIT
				; -> 12/06;	KH20067 ProKIT
530 xd	170 kW	3 l	02/05→02/07		KH10153 ProKIT
				; 09/05 -> 12/06	KH20067 ProKIT
M5	373 kW	5 l	09/04→12/09		KH20189 ProKIT
<b>BMW - 5 Touring (E34)</b>				<b>07/91→07/96</b>	
518 i	83 kW	1.8 l	04/93→04/94		KH10188 ProKIT
518 i	85 kW	1.8 l	05/94→07/96		
520 i	110 kW	2 l	07/91→07/96		
525 i	141 kW	2.5 l	07/91→07/96		
525 ix	141 kW	2.5 l	01/92→03/96		
525 td	85 kW	2.5 l	03/93→07/96		
525 tds	105 kW	2.5 l	12/91→07/96		
530 i	160 kW	3 l	09/92→07/96		
540 i	210 kW	4 l	09/93→07/96		
M5	250 kW	3.8 l	04/92→07/95		
<b>BMW - 5 Touring (E39)</b>				<b>11/96→05/04</b>	
520 d	100 kW	2 l	02/00→09/03		KH20067 ProKIT
520 i	100 kW	2 l	03/97→08/01	; 07/99 ->	KH20067 ProKIT
520 i	110 kW	2 l	03/97→08/01	; 04/97 -> 08/00	KH30078 ProKIT
					KH20067 ProKIT

































































BMW - 5 Touring (E39)					11/96→05/04
520 i	125 kW	2.2 l	09/00→12/03	; 05/03 ->	KH30078 ProKIT
					KH20067 ProKIT
523 i	125 kW	2.5 l	03/97→08/00		KH30078 ProKIT
528 i	142 kW	2.8 l	11/96→08/00		KH20067 ProKIT
530 i	170 kW	3 l	09/00→12/03		
525 d	120 kW	2.5 l	02/00→05/04	; 09/00 -> 02/04	KH30078 ProKIT
				-> 04/04	KH20067 ProKIT
525 i	141 kW	2.5 l	09/00→05/04	; -> 02/04	KH30078 ProKIT
				; -> 04/04	KH20067 ProKIT
525 tds	105 kW	2.5 l	03/97→05/04	; -> 09/98	KH30078 ProKIT
				; -> 04/04	KH20067 ProKIT
530 d	135 kW	3 l	08/98→09/00	; 09/98 ->	KH30078 ProKIT
				; 09/98 ->	KH20067 ProKIT
530 d	142 kW	3 l	09/00→05/04	; 04/01 -> 02/04	KH30078 ProKIT
				; -> 04/04	KH20067 ProKIT
540 i	210 kW	4.4 l	04/97→12/03	; 09/97 ->	KH30078 ProKIT
					KH20067 ProKIT

BMW - 5 Touring (E61)					03/04→12/10
520 d	110 kW	2 l	09/05→02/07		KH30063 ProKIT
520 d	120 kW	2 l	04/05→05/10		KH20085 ProKIT
523 i	130 kW	2.5 l	10/04→02/07		
523 i	140 kW	2.5 l	03/07→01/10		
525 d	120 kW	2.5 l	03/04→03/07		
525 d	130 kW	2.5 l	03/04→03/07		
525 d	145 kW	3 l	03/07→05/10		
525 i	141 kW	2.5 l	06/04→12/10		
525 i	160 kW	2.5 l	03/05→05/10		
525 i	160 kW	3 l	01/07→12/10		
530 d	160 kW	3 l	03/04→09/05		
530 d	170 kW	3 l	02/05→02/07		
530 d	173 kW	3 l	02/07→05/10		
530 i	190 kW	3 l	09/04→02/07		
530 i	200 kW	3 l	01/07→12/10		
535 d	200 kW	3 l	09/04→12/10		
535 d	210 kW	3 l	01/07→12/10		
550 i	270 kW	4.8 l	07/05→12/10		
520 d	130 kW	2 l	09/07→05/10		KH30063 ProKIT
520 i	125 kW	2 l	09/07→12/10		KH20067 ProKIT
					KH20085 ProKIT
525 d xDrive	145 kW	3 l	09/08→05/10		KH10153 ProKIT
					KH20067 ProKIT
					KH20085 ProKIT
525 i xDrive	160 kW	3 l	09/08→12/10		KH10153 ProKIT
525 xd	145 kW	3 l	09/07→09/08		KH20085 ProKIT
525 xi	160 kW	2.5 l	07/05→12/10		
525 xi	160 kW	3 l	01/07→12/10		
530 d xDrive	173 kW	3 l	09/07→05/10		
530 i xDrive	200 kW	3 l	09/08→05/10		
530 xd	170 kW	3 l	02/05→02/07		
530 xd	173 kW	3 l	03/07→08/07		
530 xi	190 kW	3 l	04/05→02/07		
530 xi	200 kW	3 l	03/07→05/10		
545 i	245 kW	4.4 l	06/04→12/10		KH30063 ProKIT
				; -> 02/10	KH20085 ProKIT
M5	373 kW	5 l	02/07→12/10		KH20189 ProKIT

BMW - 5 Touring (F11)					11/09→02/17
518 d	100 kW	2 l	07/13→02/17	; Thread Size: M12x1.25	KH30110 ProKIT
518 d	105 kW	2 l	07/13→06/14		KH20124 ProKIT
518 d	110 kW	2 l	07/14→02/17		
520 d	120 kW	2 l	06/10→02/17		
520 d	135 kW	2 l	06/10→06/14		
520 d	140 kW	2 l	07/14→02/17		
520 i	120 kW	2 l	09/11→02/17		
520 i	135 kW	2 l	10/10→02/17		
523 i	150 kW	3 l	11/09→08/11		
525 d	155 kW	2 l	09/11→02/17		
525 d	160 kW	2 l	09/11→02/17		
525 d	150 kW	3 l	09/10→08/11		
528 i	180 kW	2 l	09/11→02/17		
528 i	190 kW	3 l	11/09→08/11		



				     13 	
<b>BMW - 5 Touring (F11)</b>					<b>11/09→02/17</b>
530 d	180 kW	3 l	06/10→08/11	 ; Thread Size: M12x1.25	KH30110 ProKIT
530 d	190 kW	3 l	09/11→02/17		KH20124 ProKIT
530 d	210 kW	3 l	09/11→02/17		
530 i	200 kW	3 l	07/11→06/13		
535 d	220 kW	3 l	09/10→08/11		
535 d	230 kW	3 l	09/11→02/17		
535 i	225 kW	3 l	06/10→02/17		
535 i	240 kW	3 l	07/13→02/17		
550 i	300 kW	4.4 l	09/10→06/13		
550 i	330 kW	4.4 l	07/13→02/17		
520 d xDrive	120 kW	2 l	07/14→02/17		KH20124 ProKIT
520 d xDrive	135 kW	2 l	07/13→06/14		
520 d xDrive	140 kW	2 l	07/14→02/17		
525 d xDrive	155 kW	2 l	07/13→02/17		
525 d xDrive	160 kW	2 l	07/13→02/17		
528 i xDrive	180 kW	2 l	09/11→02/17		
530 d xDrive	190 kW	3 l	03/11→02/17		
530 d xDrive	210 kW	3 l	03/11→02/17		
535 d xDrive	230 kW	3 l	09/11→02/17		
535 i xDrive	225 kW	3 l	09/11→02/17		
535 i xDrive	240 kW	3 l	07/13→02/17		
<b>BMW - 6 (E24)</b>					<b>10/75→04/89</b>
628 CSi	135 kW	2.8 l	09/79→08/87	 ; 09/80 -> 05/82	KH00041 ProKIT
				 ; 05/82 -> 05/87; (ABS)	KH20112 ProKIT
				 ; 05/82 ->	KH10188 ProKIT
630 CS	135 kW	3 l	04/76→08/79	 ; -> 06/78	KH00039 ProKIT
630 CS	136 kW	3 l	04/76→08/79		
633 CSi	147 kW	3.2 l	10/75→12/81	 ; 06/78 ->	KH00041 ProKIT
				 ; -> 06/78	KH00039 ProKIT
635 CSi	136 kW	3.4 l	12/84→12/86		KH10188 ProKIT
635 CSi	160 kW	3.4 l	05/82→06/87		
635 CSi	162 kW	3.4 l	07/87→04/89		
M 635 CSi	191 kW	3.5 l	04/86→02/89		
635 CSi	141 kW	3.4 l	12/77→04/89	 ; 05/82 ->	KH10188 ProKIT
635 CSi	155 kW	3.4 l	07/87→04/89	 ; (ABS)	KH20112 ProKIT
					KH10188 ProKIT
635 CSi	160 kW	3.5 l	06/78→04/82	 ; 10/78 ->	KH00041 ProKIT
M 635 CSi	210 kW	3.5 l	04/84→12/88	 ; 01/85 ->; (ABS)	KH20112 ProKIT
					KH10188 ProKIT
<b>BMW - 6 / 6 Convertible (E63, E64)</b>					<b>09/03→08/10</b>
630 i	190 kW	3 l	09/04→08/07		KH30063 ProKIT
645 Ci	245 kW	4.4 l	09/03→08/05		KH20085 ProKIT
645 Ci	245 kW	4.4 l	04/04→08/05		
630 i	200 kW	3 l	09/07→08/10	-> 02/10; 	KH30063 ProKIT
635 d	210 kW	3 l	07/07→07/10	 ; -> 02/10	KH20085 ProKIT
650 i	270 kW	4.8 l	09/05→08/10		
M	373 kW	5 l	09/05→07/10		KH20189 ProKIT
M6	373 kW	5 l	09/06→08/10		
<b>BMW - 6 Convertible / 6 Coupe / 6 Gran Coupe (F12, F13, F06)</b>					<b>12/10→10/18</b>
640 d	230 kW	3 l	09/11→10/17	 ; Thread Size: M12x1.25	KH30110 ProKIT
640 d	230 kW	3 l	09/11→06/18		KH20124 ProKIT
640 d	230 kW	3 l	03/12→10/18		
640 i	235 kW	3 l	07/11→10/17		
640 i	235 kW	3 l	09/11→06/18		
640 i	235 kW	3 l	03/12→10/18		
650 i	298 kW	4.4 l	09/11→12/12		
650 i	300 kW	4.4 l	12/10→06/12		
650 i	300 kW	4.4 l	07/11→06/12		
650 i	330 kW	4.4 l	07/12→10/17		
650 i	330 kW	4.4 l	07/12→06/18		
650 i	330 kW	4.4 l	07/12→10/18		
640 d xDrive	230 kW	3 l	03/12→10/17		KH20124 ProKIT
640 d xDrive	230 kW	3 l	03/12→06/18		
640 d xDrive	230 kW	3 l	03/13→10/18		
640 i xDrive	235 kW	3 l	03/13→10/17		
640 i xDrive	235 kW	3 l	03/13→06/18		
640 i xDrive	235 kW	3 l	03/13→10/18		
650 i xDrive	300 kW	4.4 l	09/11→06/12		
650 i xDrive	300 kW	4.4 l	09/11→02/15		
650 i xDrive	330 kW	4.4 l	07/12→10/17		
650 i xDrive	330 kW	4.4 l	07/12→06/18		
650 i xDrive	330 kW	4.4 l	07/12→10/18		

				     13 	
<b>BMW - 7 Sedan (E23, E32)</b>					<b>05/77→09/94</b>
728	125 kW	2.8 l	05/77→08/79	 ; 06/77 ->	KH00041 ProKIT
730	135 kW	3 l	05/77→08/79		
733 i	145 kW	3.2 l	05/77→08/86		
728 i	135 kW	2.8 l	09/77→08/86	 ; 12/79 -> 05/86	KH00041 ProKIT
				 ; 09/81 ->	KH10188 ProKIT
730 i, iL	138 kW	3 l	03/87→03/94		KH10188 ProKIT
730 i, iL	145 kW	3 l	03/85→01/89		
730 i, iL V8	160 kW	3 l	04/92→09/94		
735 i	160 kW	3.4 l	09/82→09/86		
735 i, iL	155 kW	3.4 l	06/86→07/92		
735 i, iL	162 kW	3.4 l	07/86→01/89		
740 i, iL V8	210 kW	4 l	05/92→03/94		
745 i	185 kW	3.2 l	04/80→04/83		
745 i	185 kW	3.4 l	05/83→08/86		
750 i, iL V12	220 kW	5 l	09/87→09/94		
732 i	145 kW	3.2 l	09/79→08/86	 ; 09/81 ->	KH10188 ProKIT
735 i	160 kW	3.5 l	09/79→09/82		
735 i	136 kW	3.4 l	05/84→09/86	 ; -> 04/86	KH00041 ProKIT
735 i	141 kW	3.4 l	04/85→08/86		KH10188 ProKIT
<b>BMW - 7 Sedan (E38)</b>					<b>03/94→11/01</b>
725 tds	105 kW	2.5 l	04/96→11/01		KH10109 ProKIT
728i X	142 kW	2.8 l	11/95→09/01		
730 d	135 kW	3 l	08/98→04/00		
730 d	142 kW	3 l	04/00→11/01		
730 i, iL	155 kW	3 l	10/94→11/01		
735 i, iL	175 kW	3.5 l	09/98→07/01		
740 d	180 kW	3.9 l	05/99→11/01		
728 i, iL	142 kW	2.8 l	08/95→11/01	 ; 01/96 ->	KH20115 ProKIT
					KH10109 ProKIT
730 i, iL	160 kW	3 l	03/94→02/96		KH20115 ProKIT
735 i, iL	173 kW	3.5 l	03/96→08/98		KH10109 ProKIT
740 i, iL	210 kW	4 l	03/94→02/96		
750 i, iL	240 kW	5.4 l	11/94→07/01		
740 i, iL	210 kW	4.4 l	02/96→07/01	 ; 03/96 ->	KH20115 ProKIT
					KH10109 ProKIT
<b>BMW - 7 Sedan (E65, E66, E67)</b>					<b>07/01→08/08</b>
730 d	160 kW	3 l	06/02→02/05	 ; 03/03 -> 01/05	KH30175 ProKIT
					KH20085 ProKIT
730 i, Li	170 kW	3 l	03/03→07/08	 ; -> 01/05	KH30175 ProKIT
					KH20085 ProKIT
730 i, Li	190 kW	3 l	03/05→08/08		KH30175 ProKIT
730 Ld	170 kW	3 l	07/05→08/08		KH20085 ProKIT
735 i, Li	200 kW	3.6 l	11/01→02/05		
740 i, Li	225 kW	4 l	03/05→08/08		
745 i, Li	245 kW	4.4 l	07/01→03/05		
750 i, Li	270 kW	4.8 l	03/05→08/08		
760 i, Li	327 kW	6 l	01/03→08/08		
740 d	190 kW	3.9 l	10/02→02/05		KH20085 ProKIT
745 d	220 kW	4.4 l	03/05→08/05		
745 d	242 kW	4.4 l	07/05→07/08		
<b>BMW - 7 Sedan (F01, F02, F03, F04)</b>					<b>02/08→12/15</b>
730 d	155 kW	3 l	02/08→05/15	 ; Thread Size: M12x1.25	KH30110 ProKIT
730 d	180 kW	3 l	09/08→06/12		KH20124 ProKIT
730 d	190 kW	3 l	07/12→05/15		
730 i, Li	190 kW	3 l	09/09→06/15		
740 d	225 kW	3 l	09/09→06/12		
740 d	230 kW	3 l	07/12→06/15		
740 i, Li	235 kW	3 l	07/12→12/15		
740 i, Li	240 kW	3 l	09/08→06/12		
750 i, Li	300 kW	4.4 l	09/08→06/12		
750 i, Li	330 kW	4.4 l	07/12→06/15		
760 i, Li	400 kW	6 l	09/09→12/15		
ActiveHybrid 7	260 kW	3 l	08/12→06/15		
ActiveHybrid 7	342 kW	4.4 l	04/10→06/12		
730 d xDrive	190 kW	3 l	11/11→05/15		KH20124 ProKIT
740 d xDrive	225 kW	3 l	09/10→12/12		
740 d xDrive	230 kW	3 l	07/12→06/15		
740 i, Li xDrive	235 kW	3 l	07/12→12/15		
750 d xDrive	280 kW	3 l	07/12→12/15		
750 i, Li xDrive	300 kW	4.4 l	09/09→06/12		
750 i, Li xDrive	330 kW	4.4 l	07/12→06/15		





**BMW - 8 (E31) 01/90→12/99**

840 Ci	210 kW	4.4 l	03/96→06/99		KH10109 ProKIT
840 i	210 kW	4 l	03/93→02/96		
850 Ci	240 kW	5.4 l	09/94→12/99		
850 CSi	277 kW	5.6 l	09/93→12/95		
850 Si	280 kW	5.6 l	11/92→12/96		
850 i, Ci	220 kW	5 l	01/90→08/94		

**BMW - 1500-2000 Sedan (115, 116, 118, 121) 08/63→11/72**

1800	66 kW	1.8 l	08/63→09/69	; 01/66 ->; VIN 1272610 ->	KH00039 ProKIT
1800	66 kW	1.8 l	07/69→09/71		
1800 Ti (TISA)	96 kW	1.8 l	10/63→04/68		KH00039 ProKIT
2000	66 kW	1.8 l	01/70→11/72		
2000	74 kW	2 l	09/68→07/72		
2000 Ti / Tilux	88 kW	2 l	01/66→07/72		
2000 Tii	96 kW	2 l	12/69→07/72		
1800 Ti	81 kW	1.8 l	10/63→04/68	; 01/66 ->; VIN 1417851 ->	

**BMW - 1502-2002 Sedan / 1502-2002 Touring (E10, E6) 06/68→07/75**

2002 Ti	88 kW	2 l	06/68→04/72		KH00039 ProKIT
2002 Tii	96 kW	2 l	01/71→07/75		
2002 Tii	96 kW	2 l	04/71→06/75		
2002 Turbo	125 kW	2 l	01/74→07/75		

**BMW - 2000 Coupe (120) 10/65→06/70**

C/CA	74 kW	2 l	10/65→06/70		KH00039 ProKIT
CS	88 kW	2 l	10/65→06/70		

**BMW - 2500-3.3 Sedan (E3) 10/68→04/77**

2.8 L	125 kW	2.8 l	02/75→04/77		KH00039 ProKIT
2500	110 kW	2.5 l	10/68→04/77		
2800	125 kW	2.8 l	10/68→07/75		
3.0 L	132 kW	3 l	02/75→04/77		
3.0 S	132 kW	3 l	05/71→04/77		
3.0 Si	143 kW	3 l	10/75→04/77		
3.0 Si	147 kW	3 l	07/71→09/75		
3.2 Li	147 kW	3.2 l	10/75→04/77		
3.3 L	140 kW	3.3 l	01/74→09/76		

**BMW - V8 Coupe (502) 10/58→07/66**






















2.6	81 kW	2.6 l	10/58→11/61		KH00039 ProKIT
2600	81 kW	2.6 l	09/61→12/64		
3.2	88 kW	3.2 l	11/58→11/61		
3.2 Super	103 kW	3.2 l	11/58→11/61		
3200 CS	118 kW	3.2 l	07/62→07/66		
3200 L	103 kW	3.2 l	09/61→12/64		
3200 S	118 kW	3.2 l	09/61→12/64		

**BMW - X1 SUV (E84) 03/09→06/15**

sDrive 16 d	85 kW	2 l	04/12→06/15		KH20155 ProKIT
sDrive 18 d	100 kW	2 l	03/09→06/15		
sDrive 18 d	105 kW	2 l	12/09→06/15		KH10153 ProKIT
sDrive 18 i	100 kW	2 l	03/10→06/15		
sDrive 18 i	110 kW	2 l	03/10→06/15		
sDrive 20 d	120 kW	2 l	03/10→06/15		
sDrive 20 d	130 kW	2 l	10/09→06/15		
sDrive 20 d	135 kW	2 l	07/12→06/15		
sDrive 20 i	135 kW	2 l	09/11→06/15		
xDrive 18 d	100 kW	2 l	03/09→06/15		
xDrive 18 d	105 kW	2 l	10/09→06/15		
xDrive 20 d	120 kW	2 l	03/10→06/15		
xDrive 20 d	130 kW	2 l	09/09→06/12		
xDrive 20 d	135 kW	2 l	07/12→06/15		
xDrive 20 i	135 kW	2 l	09/11→06/15		
xDrive 23 d	150 kW	2 l	10/09→06/15		
xDrive 25 d	160 kW	2 l	10/09→06/15		
xDrive 25 i	160 kW	3 l	03/10→08/11		
xDrive 28 i	180 kW	2 l	03/11→06/15		
xDrive 28 i	190 kW	3 l	09/09→08/11		

**BMW - X3 (E83) 09/03→12/11**

2.0 d	110 kW	2 l	09/04→08/07		KH10153 ProKIT
2.0 i	110 kW	2 l	07/05→08/08		
2.0 sd	130 kW	2 l	09/07→08/08		KH10109 ProKIT
2.5 i	141 kW	2.5 l	03/04→07/06		
2.5 si	160 kW	2.5 l	08/06→08/08		
3.0 d	150 kW	3 l	01/04→08/05		
3.0 d	160 kW	3 l	09/05→08/08		
3.0 i xDrive	170 kW	3 l	09/03→07/06		

									
<b>BMW - X3 (E83)</b>				<b>09/03→12/11</b>					
3.0 sd	210 kW	3 l	09/06→08/08						KH10153 ProKIT
3.0 si	200 kW	3 l	08/06→08/08						KH10109 ProKIT
xDrive 20 d	130 kW	2 l	09/08→08/10						
xDrive 25 i	160 kW	2.5 l	09/08→08/10						
xDrive 30 d	160 kW	3 l	09/08→08/10						
2.5 si xDrive	155 kW	2.5 l	08/06→08/08						KH10109 ProKIT
xDrive 18 d	100 kW	2 l	04/09→12/11						
xDrive 20 d	120 kW	2 l	09/08→08/10						
xDrive 30 d	155 kW	3 l	09/08→08/10						
xDrive 35 d	210 kW	3 l	09/08→08/11						
xDrive 18 d	105 kW	2 l	09/08→12/11		-> 02/11				KH10153 ProKIT
xDrive 20 i	110 kW	2 l	09/08→08/11						KH10109 ProKIT
xDrive 30 i	200 kW	3 l	09/08→08/10		-> 02/10				KH10153 ProKIT
									KH10109 ProKIT
<b>BMW - X3 (F25)</b>				<b>10/12→08/17</b>					
sDrive 18 d	100 kW	2 l	10/12→03/14		; Thread Size: M12x1.25				KH30110 ProKIT
sDrive 18 d	105 kW	2 l	10/12→03/14						
sDrive 18 d	110 kW	2 l	04/14→08/17						
sDrive 20 i	125 kW	1.6 l	04/14→08/17						
sDrive 20 i	135 kW	2 l	04/14→08/17						
<b>BMW - X5 (E53)</b>				<b>01/00→10/06</b>					
3.0 d	135 kW	3 l	04/01→09/03						KH10153 ProKIT
4.4 i	210 kW	4.4 l	01/00→09/03						KH20085 ProKIT
4.6 is	255 kW	4.6 l	10/01→09/03						
3.0 d	160 kW	3 l	10/03→09/06						KH10153 ProKIT
4.4 i	235 kW	4.4 l	10/03→10/06						
4.8 is	265 kW	4.8 l	04/04→09/06						
3.0 i	170 kW	3 l	04/00→10/06						KH10153 ProKIT
					-> 09/03				KH20085 ProKIT
<b>BMW - X5 (E70, F15, F85)</b>				<b>10/06→07/18</b>					
3.0 3.0d	155 kW	3 l	02/07→09/08						KH30102 ProKIT
3.0 d	173 kW	3 l	12/06→09/08						
3.0 sd	210 kW	3 l	10/07→09/08						
3.0 si	200 kW	3 l	10/06→09/08						
M	423 kW	4.4 l	12/14→07/18						
M 50 d	280 kW	3 l	08/11→06/13						
M 50 d	280 kW	3 l	12/13→07/18						
xDrive 25 d	155 kW	2 l	12/13→07/15						
xDrive 25 d	160 kW	2 l	12/13→07/15						
xDrive 25 d	170 kW	2 l	08/15→07/18						
xDrive 25 d	160 kW	3 l	04/14→07/18						
xDrive 30 d	155 kW	3 l	10/08→07/13						
xDrive 30 d	173 kW	3 l	10/08→03/10						
xDrive 30 d	180 kW	3 l	04/10→07/13						
xDrive 30 d	183 kW	3 l	12/13→07/18						
xDrive 30 d	190 kW	3 l	08/13→07/18						
xDrive 30 d	204 kW	3 l	08/13→07/18						
xDrive 30 d	210 kW	3 l	08/13→07/18						
xDrive 30 i	200 kW	3 l	10/08→03/10						
xDrive 35 d	210 kW	3 l	10/08→07/13						
xDrive 35 i	225 kW	3 l	04/10→07/13						
xDrive 35 i	225 kW	3 l	12/13→07/18						
xDrive 35 i	235 kW	3 l	02/12→06/13						
xDrive 35 i	240 kW	3 l	12/13→07/18						
xDrive 40 d	225 kW	3 l	09/10→06/13						
xDrive 40 d	230 kW	3 l	12/13→07/18						
xDrive 40e	205 kW	2 l	08/15→07/18						
xDrive 40e	230 kW	2 l	08/15→07/18						
xDrive 40 i	225 kW	3 l	01/12→06/13						
xDrive 48 i	261 kW	4.8 l	10/08→03/10						
<b>BMW - X6 (E71, E72, F16, F86)</b>				<b>06/07→07/19</b>					
M 50 d	280 kW	3 l	08/11→06/14						KH30102 ProKIT
xDrive 30 d	155 kW	3 l	04/10→07/14						
xDrive 30 d	155 kW	3 l	08/14→07/19						
xDrive 30 d	173 kW	3 l	04/08→03/10						
xDrive 30 d	180 kW	3 l	04/10→07/14						
xDrive 30 d	183 kW	3 l	12/14→07/19						
xDrive 30 d	190 kW	3 l	08/14→07/19						
xDrive 30 d	204 kW	3 l	08/14→07/19						
xDrive 35 d	210 kW	3 l	01/08→03/10						
xDrive 35 i	224 kW	3 l	01/08→06/14						
xDrive 35 i	225 kW	3 l	01/08→07/14						
xDrive 35 i	225 kW	3 l	08/14→07/19						





**BMW - X6 (E71, E72, F16, F86) 06/07→07/19**

xDrive 35 i	235 kW	3 l	07/09→06/14		KH30102 ProKIT
xDrive 35 i	240 kW	3 l	06/07→03/10		
xDrive 35 i	240 kW	3 l	08/14→07/19		
xDrive 40 d	225 kW	3 l	07/09→06/14		
xDrive 40 d	230 kW	3 l	12/14→07/19		
xDrive 50 i	300 kW	4.4 l	07/08→07/14		
xDrive 50 i	330 kW	4.4 l	10/07→06/14		
xDrive 50 i	330 kW	4.4 l	08/14→07/19		

**BMW - Z1 Roadster 06/88→06/91**

2.5	125 kW	2.5 l	06/88→06/91	; 03/89 ->	KH20060 ProKIT
				; 03/89 -> 09/90	KH10362 ProKIT

**BMW - Z3 Coupe / Z3 Roadster (E36) 10/95→06/03**

1.8 i	85 kW	1.8 l	10/95→10/98		KH20033 ProKIT
1.9 i	103 kW	1.9 l	11/95→03/99		KH10408 ProKIT
1.9 i	85 kW	1.9 l	01/99→01/03		KH20033 ProKIT
1.9 i	87 kW	1.9 l	07/98→01/03	; 04/99 ->	KH10362 ProKIT
				; -> 04/99	KH10408 ProKIT
2.0 i	110 kW	2 l	04/99→01/03		KH20033 ProKIT
2.2 i	120 kW	2.2 l	08/00→01/03		KH10362 ProKIT
2.2 i	125 kW	2.2 l	10/00→06/02		
2.8 i	142 kW	2.8 l	11/96→05/00		
3.0 i	170 kW	3 l	06/00→01/03		
2.8 i	142 kW	2.8 l	01/98→05/00		KH20033 ProKIT
				; 07/98 ->	KH10362 ProKIT
2.8 i	143 kW	2.8 l	01/96→07/00		KH20033 ProKIT
3.0 i	170 kW	3 l	06/00→06/03		KH20033 ProKIT
				; -> 06/02	KH10362 ProKIT
M	236 kW	3.2 l	02/98→06/01		KH20033 ProKIT
M	239 kW	3.2 l	06/01→06/03		KH10109 ProKIT
M 3.2	236 kW	3.2 l	01/97→06/00		
M 3.2	239 kW	3.2 l	06/01→01/03		
M 3.2	179 kW	3.2 l	02/98→06/00		KH10109 ProKIT

**BMW - Z4 Coupe / Z4 Roadster (E86, E85) 12/02→02/09**




2.0 i	110 kW	2 l	03/05→02/09		KH20033 ProKIT
2.2 i	125 kW	2.2 l	10/03→10/05		KH10061 ProKIT
2.5 i	130 kW	2.5 l	09/05→02/09		
2.5 i	141 kW	2.5 l	12/02→12/05		
2.5 si	160 kW	2.5 l	01/06→08/08		
3.0 i	170 kW	3 l	12/02→12/05		
3.0 si	195 kW	3 l	01/06→08/08		
3.0 si	195 kW	3 l	04/06→08/08		
2.5 si	155 kW	2.5 l	09/05→02/09		KH20033 ProKIT
M	252 kW	3.2 l	01/06→08/08		KH20102 ProKIT
M	252 kW	3.2 l	04/06→08/08		KH10109 ProKIT

**BMW - Z4 Roadster (E89) 02/09→08/16**


sDrive 18 i	115 kW	2 l	04/13→08/16		KH30080 ProKIT
sDrive 20 i	120 kW	2 l	09/11→08/16		KH10061 ProKIT
sDrive 20 i	135 kW	2 l	09/11→08/16		
sDrive 23 i	150 kW	2.5 l	03/09→08/11		
sDrive 28 i	180 kW	2 l	09/11→08/16		
sDrive 30 i	190 kW	3 l	02/09→08/11		
sDrive 35 i	225 kW	3 l	02/09→08/16		
sDrive 35 is	250 kW	3 l	03/10→08/16		

**BMW - Z8 Roadster (E52) 01/00→12/03**

4.9	294 kW	4.9 l	01/00→12/03		KH30078 ProKIT
					KH10109 ProKIT

					
<b>BOND - EQUIPE Coupe</b>					<b>01/67→12/70</b>
1300 GT	56 kW	1.3 l	01/67→12/70		<b>KH00123</b> ProKIT
<b>BOND - EQUIPE Mk. II Convertible / EQUIPE Mk. II Coupe</b>					<b>01/68→12/71</b>
2.0 GT	77 kW	2 l	01/68→12/71		<b>KH00124</b> ProKIT



CADILLAC - BLS				04/06→
1.9 D	110 kW	1.9 l	04/06→	 <b>KH30071 ProKIT</b>
2.0 T	129 kW	2 l	04/06→12/10	
2.0 T	154 kW	2 l	04/06→	
2.8 T	188 kW	2.8 l	04/06→	







**CATERHAM - 21 (C2)** **01/94**→

1.6 i	86 kW	1.6 l	01/94→12/02	; 01/98 ->	KH00053 ProKIT
1.6 i Supersport	103 kW	1.6 l	01/96→12/98		
1.8 i	140 kW	1.8 l	01/97→		

**CATERHAM - SEVEN (CF)** **06/86**→

1.4 i	97 kW	1.4 l	01/92→09/95		KH00053 ProKIT
1.6	74 kW	1.6 l	01/90→09/95		
1.6 i	103 kW	1.6 l	09/95→10/97		
1.8 16 V	171 kW	1.8 l	10/99→		
1.8 i	112 kW	1.8 l	01/98→12/01		
1700 Super Sprint	99 kW	1.7 l	01/90→12/95		
2.0 i	121 kW	2 l	01/90→09/95		
Cosworth 1600	110 kW	1.6 l	06/86→12/92		





**CHEVROLET - AVEO / KALOS Hatchback / AVEO / KALOS Saloon (T200, T250, T255) 05/03→**

1.2	53 kW	1.2 l	03/05→12/07		KH10141 ProKIT		
1.2	62 kW	1.2 l	01/08→		KH10213 ProKIT		
1.2	62 kW	1.2 l	04/08→				
1.2 LPG	62 kW	1.2 l	01/09→				
1.4	61 kW	1.4 l	03/05→05/08				
1.4	69 kW	1.4 l	03/05→05/13				
1.4	74 kW	1.4 l	04/08→				
1.4	74 kW	1.4 l	09/08→				
1.4 16V	69 kW	1.4 l	05/03→05/08				
1.2	55 kW	1.2 l	01/08→				KH10213 ProKIT
1.2 LPG	62 kW	1.2 l	04/08→12/11				
1.4	61 kW	1.4 l	03/05→				

**CHEVROLET - CAPTIVA (C100, C140) 06/06→12/09**









2.0 D	93 kW	2 l	10/06→12/09		KH30068 ProKIT		
2.0 D	110 kW	2 l	09/07→	; ;	KH30068 ProKIT		
2.0 D 4WD	110 kW	2 l	10/06→				
2.4	100 kW	2.4 l	06/06→				
2.4 4WD	100 kW	2.4 l	06/06→02/11				
2.4 LPG	100 kW	2.4 l	01/07→				
2.4 LPG 4WD	100 kW	2.4 l	01/07→02/11				
3.2 4WD	169 kW	3.2 l	06/06→				
2.0 D	120 kW	2 l	01/11→				KH30087 ProKIT
2.0 D 4WD	120 kW	2 l	01/11→				
2.2 D	135 kW	2.2 l	07/14→				
2.4	126 kW	2.4 l	11/12→				
2.4 4WD	126 kW	2.4 l	11/12→				
3.0 4WD	190 kW	3 l	11/10→09/18				
3.0 4WD	197 kW	3 l	01/12→				
2.0 D 4WD	93 kW	2 l	10/06→12/09		KH30068 ProKIT		
				;	KH30087 ProKIT		
				;	KH30087 ProKIT		
2.2 D	120 kW	2.2 l	03/11→				
2.2 D 4WD	120 kW	2.2 l	03/11→				
2.2 D 4WD	135 kW	2.2 l	03/11→				
2.4	123 kW	2.4 l	03/11→				
2.4 4WD	123 kW	2.4 l	03/11→				

**CHEVROLET - CITY EXPRESS Mini Cargo Van 07/14→**








































2.0	98 kW	2 l	07/14→		KH30024 ProKIT
-----	-------	-----	--------	--	----------------
























**CHEVROLET - CRUZE / CRUZE Hatchback / CRUZE Station Wagon (J300, J305, J308) 05/09→05/11**

1.4	74 kW	1.4 l	07/13→	;	KH30089 ProKIT
1.4	74 kW	1.4 l	07/13→12/15	;	KH30119 ProKIT
1.4	103 kW	1.4 l	08/12→		
1.6	86 kW	1.6 l	12/12→		
1.6	86 kW	1.6 l	12/12→12/15		
1.6	91 kW	1.6 l	08/12→12/15		
1.7 D	96 kW	1.7 l	01/12→		
1.7 TD	81 kW	1.7 l	08/13→12/15		
1.7 TD	96 kW	1.7 l	08/12→		
1.8	104 kW	1.8 l	08/12→		
2.0 TD	120 kW	2 l	08/12→		
1.4	103 kW	1.4 l	09/10→	; ;	KH30133 ProKIT
1.6	80 kW	1.6 l	01/12→	; ;	KH30134 ProKIT
1.8 LPG	104 kW	1.8 l	06/11→		
1.4	103 kW	1.4 l	06/12→	;	KH30089 ProKIT
1.6	80 kW	1.6 l	05/09→	;	KH30119 ProKIT
1.6	83 kW	1.6 l	05/09→		
1.6	91 kW	1.6 l	05/09→	; ;	KH30133 ProKIT
1.6	91 kW	1.6 l	06/11→	; ;	KH30134 ProKIT
1.7 D	96 kW	1.7 l	01/12→12/15		
1.8	103 kW	1.8 l	11/09→		
1.8	103 kW	1.8 l	10/11→		
1.8	104 kW	1.8 l	05/09→		
1.8	104 kW	1.8 l	06/11→		
1.8 LPG	104 kW	1.8 l	06/11→12/15		
2.0 CDI	110 kW	2 l	05/09→		
2.0 CDI	120 kW	2 l	08/10→		
2.0 CDI	120 kW	2 l	06/11→		
1.7 TD	81 kW	1.7 l	11/13→	;	KH30119 ProKIT
1.7 TD	81 kW	1.7 l	11/13→12/15		
































											
<b>CHEVROLET - CRUZE / CRUZE Hatchback / CRUZE Station Wagon (J300, J305, J308)</b> <span style="float: right;">05/09→05/11</span>											
2.0 CDI	92 kW	2 l	05/09→05/11			16 Inch					KH30089 ProKIT
						15 Inch					KH30119 ProKIT
						15 Inch					KH30133 ProKIT
						16 Inch					KH30134 ProKIT
<b>CHEVROLET - EPICA (KL1_)</b> <span style="float: right;">01/05→12/11</span>											
2.0	94 kW	2 l	01/05→12/06								KH30167 ProKIT
2.0	98 kW	2 l	01/05→12/06								
2.0	105 kW	2 l	06/06→12/11		01/08 ->						KH30181 ProKIT
2.0 D	110 kW	2 l	01/07→12/11		-> 06/10;						KH30167 ProKIT
											KH30187 ProKIT
											KH10226 ProKIT
2.5	115 kW	2.5 l	06/06→12/11		01/08 ->						KH30181 ProKIT
											KH30187 ProKIT
<b>CHEVROLET - EVANDA Sedan</b> <span style="float: right;">03/05→12/06</span>											
2.0	96 kW	2 l	03/05→12/06								KH30167 ProKIT
<b>CHEVROLET - LACETTI (J200)</b> <span style="float: right;">03/05→</span>											
1.4 16V	70 kW	1.4 l	03/05→03/13								KH10226 ProKIT
1.6	80 kW	1.6 l	03/05→								KH30187 ProKIT
1.8	89 kW	1.8 l	08/05→12/11								
1.8	90 kW	1.8 l	03/05→								KH30187 ProKIT
2.0 D	89 kW	2 l	01/07→								
<b>CHEVROLET - MALIBU (V300)</b> <span style="float: right;">01/12→</span>											
2.0 D	118 kW	2 l	04/12→								KH30070 ProKIT
2.4	123 kW	2.4 l	01/12→								KH30105 ProKIT
3.0	196 kW	3 l	04/13→								KH30105 ProKIT
<b>CHEVROLET - MATIZ (M200, M250)</b> <span style="float: right;">03/05→12/07</span>											
0.8	38 kW	0.8 l	03/05→12/13		-> 06/10						KH00014 ProKIT
1.0	49 kW	1 l	03/05→		-> 06/10						KH00028 ProKIT
1.0	47 kW	1 l	03/05→12/07								KH00014 ProKIT
											KH00028 ProKIT
<b>CHEVROLET - NUBIRA Estate / NUBIRA Saloon</b> <span style="float: right;">01/05→12/11</span>											
1.6	80 kW	1.6 l	03/05→12/11								KH10226 ProKIT
1.8	89 kW	1.8 l	08/05→12/11								KH30187 ProKIT
1.8	90 kW	1.8 l	03/05→12/09								
2.0 D	89 kW	2 l	01/05→12/11			02/07 ->					KH10226 ProKIT
2.0 D	89 kW	2 l	01/07→12/11								
<b>CHEVROLET - ORLANDO (J309)</b> <span style="float: right;">02/11→</span>											
1.4	103 kW	1.4 l	06/12→			16 Inch					KH30089 ProKIT
1.8	104 kW	1.8 l	02/11→								
2.0 D	96 kW	2 l	02/11→12/15								
2.0 D	120 kW	2 l	02/11→								
<b>CHEVROLET - REZZO MPV (U100)</b> <span style="float: right;">03/05→</span>											
1.6	77 kW	1.6 l	03/05→		-> 06/08						KH10226 ProKIT
1.6	79 kW	1.6 l	08/05→		-> 06/08;						KH20128 ProKIT
2.0	89 kW	2 l	03/05→								
2.0	90 kW	2 l	08/05→09/09								
<b>CHEVROLET - SPARK</b> <span style="float: right;">05/05→02/10</span>											
0.8	37 kW	0.8 l	05/05→02/10		01/06 ->						KH00014 ProKIT
					01/06 ->						KH00028 ProKIT
1.0 SX	46 kW	1 l	05/05→		01/06 -> 06/10						KH00014 ProKIT
					01/06 -> 06/10						KH00028 ProKIT
<b>CHEVROLET - SPARK (M300)</b> <span style="float: right;">03/10→</span>											
1.0	50 kW	1 l	03/10→								KH10141 ProKIT
1.2	60 kW	1.2 l	03/10→								KH10213 ProKIT
1.0 LPG	50 kW	1 l	03/10→								KH10213 ProKIT
1.2 LPG	60 kW	1.2 l	03/10→								



				      	
<b>CHRYSLER - 300C Sedan / 300C Touring (LX, LE)</b>				<b>09/04→11/12</b>	
2.7	130 kW	2.7 l	01/07→12/10		KH30155 ProKIT
2.7	130 kW	2.7 l	01/07→11/12		
2.7	142 kW	2.7 l	09/04→12/10		
2.7	142 kW	2.7 l	09/04→11/12		
3.0 CRD	160 kW	3 l	09/05→12/10		
3.0 CRD	160 kW	3 l	09/05→11/12		
3.0 V6 CRD	155 kW	3 l	11/10→11/12		
3.5	183 kW	3.5 l	09/04→12/10		
3.5	183 kW	3.5 l	09/04→11/12		
5.7	250 kW	5.7 l	09/04→12/08		
5.7	250 kW	5.7 l	09/04→12/10		
6.1 SRT8	317 kW	6.1 l	06/05→12/10		
6.1 SRT8	317 kW	6.1 l	06/05→11/12		
<b>CHRYSLER - LE BARON Convertible / LE BARON Saloon</b>				<b>09/86→12/96</b>	
2.2 i Turbo	109 kW	2.2 l	09/86→12/90	 ;  14, 15, 16 Inch	KH30174 ProKIT
2.2 i Turbo	130 kW	2.2 l	09/86→12/90		
2.2 i Turbo	130 kW	2.2 l	09/89→01/91		
2.5 i	75 kW	2.5 l	09/86→12/93		
2.5 i	75 kW	2.5 l	01/89→12/94		
2.5 i Turbo	112 kW	2.5 l	01/89→12/93		
2.5 i Turbo	112 kW	2.5 l	01/89→12/94		
3.0 i V6	105 kW	3 l	01/90→12/94		
3.0 i V6	105 kW	3 l	01/90→12/96		
<b>CHRYSLER - NEON II Sedan</b>				<b>08/99→12/06</b>	
1.6	85 kW	1.6 l	11/01→12/06		KH10396 ProKIT
1.8	91 kW	1.8 l	01/00→12/01		
2.0 16V	97 kW	2 l	10/02→12/06		
2.0 16V R/T	110 kW	2 l	10/01→12/06		
2.0 16V R/T	112 kW	2 l	10/01→12/04		
2.0 16V	98 kW	2 l	08/99→12/06	 ; (ABS); -> 12/99	KH20182 ProKIT
					KH10396 ProKIT
<b>CHRYSLER - NEON Sedan (PL)</b>				<b>05/94→08/99</b>	
1.8 16V	85 kW	1.8 l	09/97→08/99	 ; (ABS);  14 Inch	KH20182 ProKIT
2.0 16V	98 kW	2 l	05/94→08/99		
2.0 16V	107 kW	2 l	06/94→08/99		
2.0 16V	109 kW	2 l	04/96→08/99		
<b>CHRYSLER - PT CRUISER Combi Van / PT CRUISER Convertible / PT CRUISER Wagon (PT_)</b>				<b>06/00→12/10</b>	
1.6	85 kW	1.6 l	11/01→12/10	 ; 01/02 ->	KH10396 ProKIT
2.4	110 kW	2.4 l	06/00→12/10		
1.6	85 kW	1.6 l	10/02→09/07		KH10396 ProKIT
2.0	104 kW	2 l	10/02→03/04		
2.2 CRD	89 kW	2.2 l	10/02→08/08		
2.4	169 kW	2.4 l	09/04→12/10		
2.4 GT	164 kW	2.4 l	03/04→03/08		
GT 2.4	164 kW	2.4 l	08/03→12/10		
2.0	100 kW	2 l	10/04→12/10		KH10396 ProKIT
2.2 CRD	89 kW	2.2 l	03/02→12/10		KH20181 ProKIT
2.2 CRD	110 kW	2.2 l	08/05→12/10		
2.4	105 kW	2.4 l	08/05→12/10		
2.0	104 kW	2 l	06/00→09/04	 ; 07/00 ->	KH20181 ProKIT
				 ; 01/02 ->	KH10396 ProKIT
2.4	105 kW	2.4 l	03/04→03/08	 ; 11/04 ->	KH20181 ProKIT
					KH10396 ProKIT
<b>CHRYSLER - VOYAGER / GRAND VOYAGER III (GS_, NS_)</b>				<b>01/95→03/01</b>	
2.0 i	98 kW	2 l	01/95→03/01	 ; 10/96 ->;  14 Inch	KH30077 ProKIT
3.8 i AWD	122 kW	3.8 l	01/95→03/01	 ;  14 Inch	KH30174 ProKIT
2.4 i	111 kW	2.4 l	01/95→03/01	 ; 01/96 ->;  14 Inch	KH30077 ProKIT
3.0	112 kW	3 l	01/95→03/01		
3.3 i	116 kW	3.3 l	01/95→03/01	 ;  14 Inch	KH30174 ProKIT
3.8 i AWD	131 kW	3.8 l	01/95→03/01		
2.5 TD	85 kW	2.5 l	01/95→03/01	 ; 10/95 ->;  15 Inch	KH30158 ProKIT
				 ;  14 Inch	KH30174 ProKIT
<b>CHRYSLER - VOYAGER I / VOYAGER II (AS, ES)</b>				<b>10/87→09/95</b>	
2.5 i	72 kW	2.5 l	01/91→09/95	 ;  15 Inch	KH30158 ProKIT
2.5 i	74 kW	2.5 l	08/90→09/95	 ;  14 Inch	KH30174 ProKIT

											
<b>CHRYSLER - VOYAGER I / VOYAGER II (AS, ES)</b>										<b>10/87→09/95</b>	
2.5 TD	87 kW	2.5 l	01/92→09/95							01/93 ->; 15 Inch	KH30158 ProKIT
										14 Inch	KH30174 ProKIT
3.0	100 kW	3 l	10/87→09/90							01/89 ->; 15 Inch	KH30158 ProKIT
3.0	101 kW	3 l	10/87→09/90								
3.0	104 kW	3 l	10/90→09/95							15 Inch	KH30158 ProKIT
3.3	112 kW	3.3 l	10/89→09/90								
3.0 i	108 kW	3 l	01/91→09/95							-> 02/91; 15 Inch	KH30158 ProKIT
										14 Inch	KH30174 ProKIT
3.3 i	110 kW	3.3 l	08/90→09/95							04/92 ->; 15 Inch	KH30158 ProKIT
3.3 i	120 kW	3.3 l	08/90→09/95							14 Inch	KH30174 ProKIT
3.3 i AWD	110 kW	3.3 l	08/90→09/95								
3.3 i AWD	120 kW	3.3 l	08/90→09/95								
<b>CHRYSLER - VOYAGER IV (RG, RS)</b>										<b>02/00→12/08</b>	
2.4	108 kW	2.4 l	02/00→12/08								KH30077 ProKIT
2.5 CRD	88 kW	2.5 l	08/05→12/08								
2.5 CRD	105 kW	2.5 l	02/00→12/08								
2.8 CRD	110 kW	2.8 l	06/04→12/08								
3.3	128 kW	3.3 l	02/00→12/08								
3.3 AWD	128 kW	3.3 l	02/00→12/08								
3.8	160 kW	3.8 l	02/00→12/08								
3.8 AWD	160 kW	3.8 l	02/00→12/08								



									
<b>CITROËN - 2 CV</b>				<b>03/63→07/90</b>					
4	12 kW	0.4 l	03/63→02/70						<b>KH10185</b> ProKIT
4	17 kW	0.4 l	01/70→12/75						
6	18 kW	0.6 l	09/75→06/81						
6	20 kW	0.6 l	08/79→07/90						
6	21 kW	0.6 l	02/70→10/85						
<b>CITROËN - AX (ZA-)</b>				<b>07/86→12/98</b>					
1.3 Sport	70 kW	1.3 l	04/87→12/88						<b>KH10062</b> ProKIT
10	32 kW	1 l	09/86→06/92						
10	33 kW	1 l	07/86→12/98						<b>KH10081</b> ProKIT
10	37 kW	1 l	02/87→12/98						
10 E	30 kW	1 l	12/86→12/88						
11	40 kW	1.1 l	12/86→04/94						
11	44 kW	1.1 l	09/86→12/97						
11 Cat (ZA_)	40 kW	1.1 l	09/88→12/89						
14	44 kW	1.4 l	12/86→12/88						
14	49 kW	1.4 l	06/88→12/89						
1.4 Allure	48 kW	1.4 l	08/92→04/94						<b>KH10081</b> ProKIT
14	51 kW	1.4 l	01/89→12/91						
14	61 kW	1.4 l	01/88→12/92						
14 GT	59 kW	1.4 l	01/89→12/91						
15 D	43 kW	1.5 l	08/94→12/97						
1.4 GTi	66 kW	1.4 l	08/91→12/96						<b>KH10083</b> ProKIT
1.4 GTi	69 kW	1.4 l	06/91→12/96						
1.4 GTi	74 kW	1.4 l	06/91→12/92						
14	62 kW	1.4 l	01/88→12/92		05/91 ->				<b>KH10051</b> ProKIT
14 (ZA)	55 kW	1.4 l	04/87→04/97		-> 04/91				<b>KH10062</b> ProKIT
14 D	38 kW	1.4 l	09/88→06/92						<b>KH10081</b> ProKIT
14 4x4	55 kW	1.4 l	08/91→12/96						<b>KH10051</b> ProKIT
14 D	37 kW	1.4 l	08/91→12/97						<b>KH10051</b> ProKIT
15 D	40 kW	1.5 l	08/94→12/97						<b>KH10081</b> ProKIT
<b>CITROËN - BERLINGO Box Body/MPV (B9)</b>				<b>04/08→</b>					
1.6	66 kW	1.6 l	04/08→		ABS				<b>KH10047</b> ProKIT
1.6	80 kW	1.6 l	04/08→		ABS				<b>KH10040</b> ProKIT
1.6 BlueHDi 100	73 kW	1.6 l	12/14→						
1.6 BlueHDi 120	88 kW	1.6 l	12/14→						
1.6 HDi / BlueHDi 75	55 kW	1.6 l	07/10→						
1.6 HDi 110	80 kW	1.6 l	04/08→						
1.6 HDi 110	82 kW	1.6 l	07/10→						
1.6 HDi 115	84 kW	1.6 l	07/10→						
1.6 HDi 75	55 kW	1.6 l	04/08→						
1.6 HDi 90	66 kW	1.6 l	07/10→12/17						
1.6 HDi 90	68 kW	1.6 l	07/10→						
1.6 HDi 90 16V	66 kW	1.6 l	04/08→						
1.6 VTi 120	88 kW	1.6 l	11/09→						
1.6 VTi 95	72 kW	1.6 l	07/10→						
Electric	35 kW		01/13→						
Electric	49 kW		01/13→						
<b>CITROËN - BERLINGO Box Body/MPV / BERLINGO MPV (M_, MF_, GJK_, GFK_)</b>				<b>07/96→12/11</b>					
1.1 i (MAHDZ, MBHDZ, MBHFX)	44 kW	1.1 l	07/96→03/08						<b>KH10052</b> ProKIT
1.4 i (MBKFX, MBKFW)	55 kW	1.4 l	07/96→12/11		01/99 -> 10/04; ABS; 29				<b>KH20108</b> ProKIT
					01/99 -> ABS				<b>KH20014</b> ProKIT
					11/04 -> ABS				<b>KH20016</b> ProKIT
					-> 11/04; ESP; ABS				<b>KH20013</b> ProKIT
					ABS				<b>KH20126</b> ProKIT
1.1 i (MFHDZ, MFHFX)	44 kW	1.1 l	07/96→05/08						<b>KH10052</b> ProKIT
1.4 i (MFKFX, MFKFW, GJKFWB, GJKFWC, GFKFWC)	55 kW	1.4 l	07/96→12/11		01/99 -> 10/04; ABS; 29				<b>KH20108</b> ProKIT
1.9 D (MFWJZ)	51 kW	1.9 l	07/98→10/05		01/99 -> ABS				<b>KH20014</b> ProKIT
					11/04 -> ABS				<b>KH20016</b> ProKIT
					-> 01/99; ABS				<b>KH20015</b> ProKIT
					-> 11/04; ESP; ABS				<b>KH20013</b> ProKIT
					ABS				<b>KH20126</b> ProKIT



**CITROËN - BERLINGO Box Body/MPV / BERLINGO MPV (M\_, MF\_, GJK\_, GFK\_) 07/96→12/11**

1.4	53 kW	1.4 l	11/02→10/05			KH10052 ProKIT
1.4 bivalent	48 kW	1.4 l	11/02→12/11			KH10052 ProKIT
1.4 i bivalent (MBKFW)	55 kW	1.4 l	04/03→10/05		11/04 ->; ABS	KH20016 ProKIT
1.4 i bivalent (MFKFW)	55 kW	1.4 l	04/03→10/08		-> 10/04; ABS, ESP, 29	KH20108 ProKIT
1.6 16V (MBNFU)	80 kW	1.6 l	10/00→03/08		-> 11/04; ESP, ABS	KH20013 ProKIT
1.6 16V (MFNFU)	80 kW	1.6 l	10/00→12/11		ABS	KH20014 ProKIT
1.6 16V (MFNFU)	81 kW	1.6 l	11/02→10/08		ABS	KH20014 ProKIT
1.9 D 70 (MBWJZ, MCWJZ)	51 kW	1.9 l	04/99→12/11			
2.0 HDI 90 (MBRHY, MCRHY)	66 kW	2 l	12/99→12/11			
2.0 HDI 90 (MFRHY)	66 kW	2 l	12/99→10/05			
2.0 HDI 90 4WD (MBRHY, MCRHY)	66 kW	2 l	11/00→10/05			
1.6 16V	81 kW	1.6 l	08/05→12/07		ABS	KH20016 ProKIT
1.6 HDI 75 (MB9HW)	55 kW	1.6 l	07/05→12/11			KH10052 ProKIT
1.6 HDI 75 (MF9HW, GJ9HWC, GF9HWC, GN9HWC)	55 kW	1.6 l	07/05→12/11		ABS	KH20014 ProKIT
1.6 HDI 90 (MB9HX, MC9HX)	66 kW	1.6 l	07/05→12/11		ABS	KH20016 ProKIT
1.6 HDI 90 (MF9HX)	66 kW	1.6 l	07/05→05/08			
1.8 D (MBA9A, MCA9A)	43 kW	1.8 l	07/96→10/02			KH10052 ProKIT
1.8 i 4WD (MFLFX)	66 kW	1.8 l	04/97→10/01		01/99 ->; ABS	KH20014 ProKIT
1.9 D (MBDJY)	51 kW	1.9 l	07/96→12/03		01/99 ->; ABS, ESP, 29	KH20108 ProKIT
					ESP, ABS	KH20013 ProKIT
					ABS	KH20126 ProKIT
1.8 D (MFA9A)	43 kW	1.8 l	07/98→10/02			KH10052 ProKIT
1.8 i (MFLFX)	66 kW	1.8 l	05/97→10/02		01/99 ->; ABS	KH20014 ProKIT
1.9 D (MFDJY)	50 kW	1.9 l	07/96→12/03		01/99 ->; ABS, ESP, 29	KH20108 ProKIT
					-> 01/99; ABS	KH20015 ProKIT
					ESP, ABS	KH20013 ProKIT
					ABS	KH20126 ProKIT
1.8 i électrique	66 kW 16 kW	1.8 l	05/98→10/02 01/00→10/02		ESP, ABS	KH10052 ProKIT
					ABS	KH20014 ProKIT
					ABS, ESP, 29	KH20108 ProKIT
1.9 D 4WD (MFWJZ)	51 kW	1.9 l	07/98→10/05			KH10052 ProKIT
					01/99 -> 10/04; ABS, ESP, 29	KH20108 ProKIT
					01/99 ->; ABS	KH20014 ProKIT
					-> 11/04; ESP, ABS	KH20013 ProKIT
1.9 D 70 4WD (MBWJZ, MCWJZ) Electric	51 kW 28 kW	1.9 l	07/98→03/06 01/98→12/05			KH10052 ProKIT
					01/99 -> 10/04; ABS, ESP, 29	KH20108 ProKIT
					01/99 ->; ABS	KH20014 ProKIT
					11/04 ->; ABS	KH20016 ProKIT
					-> 11/04; ESP, ABS	KH20013 ProKIT
2.0 HDi 4x4 (MFRHY) Electric	66 kW 28 kW	2 l	11/02→10/05 07/03→12/05		-> 10/04; ABS, ESP, 29	KH20108 ProKIT
					11/04 ->; ABS	KH20016 ProKIT
					-> 11/04; ESP, ABS	KH20013 ProKIT
					ABS	KH20014 ProKIT
Electric	42 kW		01/11→12/11		ABS	KH10040 ProKIT

**CITROËN - BERLINGO MULTISPACE / BERLINGO Platform/Chassis (B9) 04/08→**

1.2 PureTech 110	81 kW	1.2 l	02/16→		ABS	KH10047 ProKIT
1.4 i	55 kW	1.4 l	07/11→			
1.6 HDi 90	66 kW	1.6 l	07/10→			
1.6	66 kW	1.6 l	04/08→		ABS	KH10047 ProKIT
1.6	80 kW	1.6 l	04/08→		ABS	KH10040 ProKIT
1.6	81 kW	1.6 l	11/08→		ABS	KH10040 ProKIT
1.6 BlueHDi 100	73 kW	1.6 l	12/14→			
1.6 BlueHDi 120	88 kW	1.6 l	12/14→			
1.6 HDi 110	80 kW	1.6 l	04/08→			
1.6 HDi 110	82 kW	1.6 l	07/10→			
1.6 HDi 115	84 kW	1.6 l	07/10→			
1.6 HDi 75 / BlueHDi 75	55 kW	1.6 l	04/08→			
1.6 HDi 75 16V	55 kW	1.6 l	04/08→			
1.6 HDi 90	66 kW	1.6 l	04/08→			
1.6 HDi 90	68 kW	1.6 l	07/10→			
1.6 HDi 90 16V	66 kW	1.6 l	04/08→			
1.6 HDi 92	68 kW	1.6 l	07/10→12/17			
1.6 VTi 120	88 kW	1.6 l	11/09→			
1.6 VTi 95	72 kW	1.6 l	07/10→			










**CITROËN - BX / BX Break (XB-)**

**10/82→12/94**







1.4	40 kW	1.4 l	01/87→01/92		KH10052 ProKIT
1.6	85 kW	1.6 l	01/87→01/92		
1.9 DT TXD	66 kW	1.9 l	02/92→12/94		
11	35 kW	1.1 l	10/82→01/92		
11	42 kW	1.1 l	10/86→06/92		
14	40 kW	1.4 l	10/82→01/92		
14	47 kW	1.4 l	01/89→12/89		
14	53 kW	1.4 l	01/86→02/93		
14 E	59 kW	1.4 l	10/85→05/89		
15	59 kW	1.6 l	10/87→05/92		
16	55 kW	1.6 l	09/88→12/94		
16	58 kW	1.6 l	09/87→02/93		
16	70 kW	1.6 l	02/92→12/92		
16	70 kW	1.6 l	02/92→06/94		
19	80 kW	1.9 l	06/88→12/94		
19	90 kW	1.9 l	07/86→01/92		
19 4x4	78 kW	1.9 l	06/89→05/91		
19 4x4	80 kW	1.9 l	10/90→05/91		
19 E 4x4	80 kW	1.9 l	04/89→02/93		
19 GTi	90 kW	1.9 l	10/84→06/94		
19 GTi 4x4	88 kW	1.9 l	06/88→02/93		
1.4	44 kW	1.4 l	01/87→01/92		KH10052 ProKIT
				; -> 04/88;	KH20046 ProKIT
1.4	52 kW	1.4 l	01/87→01/92		KH10052 ProKIT
				; -> 11/89;	KH20046 ProKIT
1.8 D	44 kW	1.8 l	10/85→09/93		KH10052 ProKIT
14	55 kW	1.4 l	01/89→02/93		
14 E	45 kW	1.4 l	10/82→06/88		KH20046 ProKIT
14 E	52 kW	1.4 l	04/83→07/89		
15	59 kW	1.6 l	10/87→05/92		
16	65 kW	1.6 l	05/89→12/94		
16	66 kW	1.6 l	10/82→06/88		
18 D	44 kW	1.8 l	10/85→09/93		
19	75 kW	1.9 l	07/86→05/89		
19	77 kW	1.9 l	07/86→05/89		
19 D	51 kW	1.9 l	03/87→02/93		
19 GTi 16V	108 kW	1.9 l	03/88→02/93		
19 GTi 16V	116 kW	1.9 l	09/87→12/88		
1.9 D	52 kW	1.9 l	01/87→01/92		KH10052 ProKIT
19 D	51 kW	1.9 l	03/87→12/94	; 04/87 ->;	KH20046 ProKIT
11	40 kW	1.1 l	10/88→06/92		KH10052 ProKIT
				; -> 06/91;	KH20046 ProKIT
14	47 kW	1.4 l	01/89→12/89		KH10052 ProKIT
				; 12/89 ->;	KH20046 ProKIT
14	55 kW	1.4 l	01/89→02/93		KH10052 ProKIT
				; 07/90 ->;	KH20046 ProKIT
14 E	49 kW	1.4 l	09/85→02/93		KH10052 ProKIT
16	53 kW	1.6 l	01/87→02/93		
16	68 kW	1.6 l	10/82→12/92	07/88 ->; ;	KH20046 ProKIT
19 E	80 kW	1.9 l	06/88→02/93		
14 E	53 kW	1.4 l	04/83→02/93		KH10052 ProKIT
				-> 06/88; ;	KH20046 ProKIT
16	53 kW	1.6 l	09/88→12/94		KH10052 ProKIT
16	76 kW	1.6 l	03/86→02/93	; -> 09/89;	KH20046 ProKIT
16	55 kW	1.6 l	09/88→02/93		KH10052 ProKIT
				; -> 06/90;	KH20046 ProKIT
16	64 kW	1.6 l	07/85→02/93		KH10052 ProKIT
				; -> 06/89;	KH20046 ProKIT
16	64 kW	1.6 l	07/85→12/94		KH10052 ProKIT
				; 07/86 -> 06/88;	KH20046 ProKIT
16	66 kW	1.6 l	06/85→06/88		KH10052 ProKIT
19 D	47 kW	1.9 l	09/83→11/94	; 07/85 ->;	KH20046 ProKIT
16	68 kW	1.6 l	04/83→01/92		KH10052 ProKIT
				; 07/85 -> 06/88;	KH20046 ProKIT
16	76 kW	1.6 l	03/86→12/94		KH10052 ProKIT
				; -> 09/91;	KH20046 ProKIT
16 E	65 kW	1.6 l	05/89→02/93		KH10052 ProKIT
				; 09/89 ->;	KH20046 ProKIT



				  	 	 13			
<b>CITROËN - BX / BX Break (XB-_)</b>								<b>10/82→12/94</b>	
19	70 kW	1.9 l	09/86→11/89						KH10052 ProKIT
					01/88 -> 09/89;				KH20046 ProKIT
19	70 kW	1.9 l	12/87→12/89						KH10052 ProKIT
19 Cat (AZE151)	75 kW	1.9 l	07/86→12/94		03/89 -> ;				KH20046 ProKIT
19	75 kW	1.9 l	07/86→12/94						KH10052 ProKIT
					-> 01/92;				KH20046 ProKIT
19	88 kW	1.9 l	06/88→12/94						KH10052 ProKIT
					01/92 -> 02/93;				KH20046 ProKIT
19 D	47 kW	1.9 l	09/83→09/93						KH10052 ProKIT
					-> 04/87;				KH20046 ProKIT
19 GTi	88 kW	1.9 l	06/88→02/93						KH10052 ProKIT
					01/92 -> ;				KH20046 ProKIT
19 GTi	90 kW	1.9 l	07/86→02/93						KH10052 ProKIT
					09/86 -> ;				KH20046 ProKIT
TRD Turbo	66 kW	1.8 l	03/88→02/93						KH10052 ProKIT
					07/89 -> ;				KH20046 ProKIT
TRD Turbo	66 kW	1.8 l	03/88→12/94						KH10052 ProKIT
					-> 02/93;				KH20046 ProKIT
<b>CITROËN - C1 / C1 II (PM_, PN_, PA_, PS_)</b>								<b>06/05→</b>	
1.0	50 kW	1 l	06/05→09/14						KH10106 ProKIT
1.0 VTi 68	51 kW	1 l	04/14→						KH30064 ProKIT
1.2 VTi 82	60 kW	1.2 l	04/14→						
1.4 HDi	40 kW	1.4 l	06/05→09/14						
<b>CITROËN - C2 / C2 ENTERPRISE (JM_, JG_)</b>								<b>07/03→09/12</b>	
1.1	44 kW	1.1 l	09/03→09/12						KH10053 ProKIT
1.4	54 kW	1.4 l	09/03→12/09						KH10054 ProKIT
1.4	55 kW	1.4 l	10/06→12/09						
1.4 16V	65 kW	1.4 l	04/05→12/09						KH10056 ProKIT
1.4 HDi	50 kW	1.4 l	09/06→12/09						KH20100 ProKIT
1.6	80 kW	1.6 l	07/03→10/10						
1.6 HDi	80 kW	1.6 l	09/05→12/09						
1.6 VTS	90 kW	1.6 l	10/04→12/09						
1.1	44 kW	1.1 l	11/03→12/09						KH10053 ProKIT
									KH10054 ProKIT
1.4 HDi	50 kW	1.4 l	07/03→12/09						KH10053 ProKIT
									KH10054 ProKIT
									KH10056 ProKIT
									KH20100 ProKIT
1.4 HDi	51 kW	1.4 l	09/03→04/05						KH10053 ProKIT
1.4 HDi	51 kW	1.4 l	11/03→04/05						KH10054 ProKIT
									KH20100 ProKIT
<b>CITROËN - C3 I (FC_, FN_)</b>								<b>02/02→07/12</b>	
1.1 i	44 kW	1.1 l	02/02→						KH10053 ProKIT
1.4 16V	65 kW	1.4 l	12/03→						KH10054 ProKIT
1.4 16V HDi	66 kW	1.4 l	02/02→						KH10056 ProKIT
1.4 HDi	50 kW	1.4 l	02/02→						KH20100 ProKIT
1.4 HDi	55 kW	1.4 l	05/05→						
1.4 i	54 kW	1.4 l	02/02→11/10						
1.4 i Bivalent	54 kW	1.4 l	02/02→						
1.6 16V	80 kW	1.6 l	02/02→08/10						
1.6 16V	81 kW	1.6 l	05/03→09/05						
1.6 16V HDi	66 kW	1.6 l	10/05→						
1.6 16V HDi	80 kW	1.6 l	09/05→						
1.6 Bioflex	83 kW	1.6 l	06/05→12/13						
1.1 LPG	44 kW	1.1 l	06/06→12/09						KH10053 ProKIT
1.4 BiFuel	54 kW	1.4 l	09/08→12/09						KH10054 ProKIT
1.4 Flex	59 kW	1.4 l	12/05→07/12						
1.4	58 kW	1.4 l	12/05→07/12						KH10053 ProKIT
1.4 HDi	52 kW	1.4 l	07/03→02/11						KH10053 ProKIT
1.4 i Bivalent	49 kW	1.4 l	01/08→12/09						KH10054 ProKIT
									KH20100 ProKIT



<b>CITROËN - C3 II (SC_)</b>				<b>09/09</b> →	
1.0 VTi 68	50 kW	1 l	08/12→	; <b>Outer diameter 1 [mm]: 82;</b>	<b>KH10047</b> ProKIT
1.2 THP 110	81 kW	1.2 l	10/14→	; ; <b>Outer diameter 1 [mm]: 72</b>	<b>KH10054</b> ProKIT
1.2 VTi 82	60 kW	1.2 l	06/12→09/16	;	<b>KH10048</b> ProKIT
1.4	54 kW	1.4 l	11/09→09/16	;	<b>KH10048</b> ProKIT
1.6 BlueHDi 100	73 kW	1.6 l	07/14→	;	<b>KH10086</b> ProKIT
1.6 BlueHDi 75	55 kW	1.6 l	04/15→		
1.6 HDi	68 kW	1.6 l	11/09→09/16		
1.6 HDi 110	82 kW	1.6 l	11/09→		
1.6 HDi 115	84 kW	1.6 l	09/12→		
1.6 HDi 90	66 kW	1.6 l	11/09→		
1.1 BiFuel	44 kW	1.1 l	11/10→	; <b>Outer diameter 1 [mm]: 82;</b>	<b>KH10047</b> ProKIT
1.1 i	44 kW	1.1 l	09/09→01/13	; <b>Outer diameter 1 [mm]: 72;</b>	<b>KH10053</b> ProKIT
1.4 HDi 70 (SC8HZC, SC8HR0, SC8HP4)	50 kW	1.4 l	11/09→	; ; <b>Outer diameter 1 [mm]: 72</b>	<b>KH10054</b> ProKIT
				;	<b>KH10048</b> ProKIT
				;	<b>KH10086</b> ProKIT
1.4 LPG	54 kW	1.4 l	07/10→	;	<b>KH10086</b> ProKIT
1.4 LPG	70 kW	1.4 l	06/13→	; <b>Outer diameter 1 [mm]: 82;</b>	<b>KH10047</b> ProKIT
1.4 VTi	72 kW	1.4 l	11/09→	; ; <b>Outer diameter 1 [mm]: 72</b>	<b>KH10054</b> ProKIT
1.4 VTi 95	70 kW	1.4 l	11/09→	;	<b>KH10048</b> ProKIT
1.6 VTi 120	88 kW	1.6 l	11/09→	;	<b>KH10048</b> ProKIT
<b>CITROËN - C3 III (SX)</b>				<b>07/16</b> →	
1.2 THP 110	81 kW	1.2 l	07/16→	;	<b>KH10048</b> ProKIT
1.2 VTi 68	50 kW	1.2 l	07/16→	; ; <b>ø 228 mm;</b>	
1.2 VTi 82	60 kW	1.2 l	07/16→		
1.6 BlueHDi 100	73 kW	1.6 l	07/16→		
1.6 BlueHDi 75	55 kW	1.6 l	07/16→		
<b>CITROËN - C3 PICASSO (SH_)</b>				<b>02/09</b> →	
1.2 THP 110	81 kW	1.2 l	01/15→	; <b>Outer diameter 1 [mm]: 82</b>	<b>KH10047</b> ProKIT
1.4 VTi 95	70 kW	1.4 l	02/09→	;	<b>KH10048</b> ProKIT
1.4 VTi 95 LPG	70 kW	1.4 l	01/12→		
1.6 BlueHDi 100	73 kW	1.6 l	01/15→		
1.6 HDi	66 kW	1.6 l	02/09→		
1.6 HDi	80 kW	1.6 l	02/09→		
1.6 HDi 110	82 kW	1.6 l	05/10→		
1.6 HDi 115	84 kW	1.6 l	01/13→		
1.6 HDi 90	68 kW	1.6 l	07/10→		
1.6 VTi 120	88 kW	1.6 l	02/09→		
1.5 Flex	68 kW	1.5 l	06/12→12/16	; <b>Outer diameter 1 [mm]: 82</b>	<b>KH10047</b> ProKIT
1.5 i	66 kW	1.5 l	06/13→		
1.6	81 kW	1.6 l	04/11→06/13		
1.6	85 kW	1.6 l	06/13→		
1.6 Flex	83 kW	1.6 l	05/11→06/12		
1.6 Flex	90 kW	1.6 l	07/11→12/16		
1.6 VTi	84 kW	1.6 l	07/09→		
<b>CITROËN - C3 Pluriel (HB_)</b>				<b>05/03</b> →	
1.4	54 kW	1.4 l	05/03→	;	<b>KH10053</b> ProKIT
1.4 HDi	50 kW	1.4 l	04/04→	;	<b>KH10054</b> ProKIT
1.6	80 kW	1.6 l	05/03→	;	<b>KH10056</b> ProKIT
				;	<b>KH20100</b> ProKIT
1.4	55 kW	1.4 l	07/03→	;	<b>KH10053</b> ProKIT
				;	<b>KH10054</b> ProKIT
				;	<b>KH20100</b> ProKIT
<b>CITROËN - C4 I / C4 I Saloon / C4 II (LC_, NC_)</b>				<b>11/04</b> → <b>12/16</b>	
1.2 THP 110	81 kW	1.2 l	02/15→12/17	; <b>Outer diameter 1 [mm]: 82;</b> <b>19 Inch</b>	<b>KH10047</b> ProKIT
1.2 THP 130	96 kW	1.2 l	04/14→	;	<b>KH10040</b> ProKIT
1.4 VTi 95	70 kW	1.4 l	11/09→		
1.6 BlueHDi 100	73 kW	1.6 l	07/14→		
1.6 BlueHDi 115	85 kW	1.6 l	08/14→		
1.6 BlueHDi 120	88 kW	1.6 l	02/15→		
1.6 HDi 110	82 kW	1.6 l	11/09→		
1.6 HDi 115	84 kW	1.6 l	07/12→		
1.6 HDi 90	68 kW	1.6 l	11/09→		
1.6 VTi 120	88 kW	1.6 l	11/09→12/16		
1.6 VTi 120 LPG	88 kW	1.6 l	09/11→		
2.0 HDi / BlueHDi 150	110 kW	2 l	11/09→		

     						
CITROËN - C4 I / C4 I Saloon / C4 II (LC_, NC_)				11/04→12/16		
1.4 16V	65 kW	1.4 l	11/04→07/11	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6 16V	80 kW	1.6 l	11/04→07/11	; 09/06 ->;	KH10048 ProKIT	
1.6 16V	80 kW	1.6 l	07/06→07/11			
1.6 HDi	66 kW	1.6 l	11/04→07/11	; -> 09/06	KH10079 ProKIT	
1.6 HDi	80 kW	1.6 l	11/04→07/11			
1.6 HDi	80 kW	1.6 l	07/06→07/11			
2.0 16V	100 kW	2 l	11/04→07/07			
2.0 16V	103 kW	2 l	11/04→07/11			
2.0 16V	103 kW	2 l	07/06→07/11			
2.0 16V	130 kW	2 l	11/04→07/08			
2.0 HDi	100 kW	2 l	11/04→07/11			
1.6	81 kW	1.6 l	01/10→	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6	81 kW	1.6 l	03/11→			
1.6 Flex	83 kW	1.6 l	09/07→09/10			
1.6 Flex	83 kW	1.6 l	02/09→12/15			
1.6 HDi	85 kW	1.6 l	07/06→07/11			
1.6 HDi	85 kW	1.6 l	07/06→08/13			
2.0 Exclusive 16V	105 kW	2 l	07/07→12/08			
2.0 Flex	109 kW	2 l	10/08→07/13			
2.0 Flex	109 kW	2 l	02/09→07/13			
2.0 Flex	111 kW	2 l	07/06→08/13			
2.0 Flex	111 kW	2 l	01/12→12/15			
2.0 HDi	81 kW	2 l	04/07→12/11			
2.0 HDi	103 kW	2 l	06/07→12/10			
2.0 HDi / BlueHDi 160	120 kW	2 l	10/10→			
1.6 16V Bio-Flex	80 kW	1.6 l	09/07→07/08	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6 THP 140	103 kW	1.6 l	07/08→07/11			
1.6 THP 150	110 kW	1.6 l	07/08→07/11	;	KH10048 ProKIT	
1.6 VTi 120	88 kW	1.6 l	07/08→07/11			
2.0 16V	105 kW	2 l	09/06→07/09			
2.0 HDi	81 kW	2 l	04/07→07/08			
2.0 HDi	103 kW	2 l	07/08→07/11			
1.6 THP 155	115 kW	1.6 l	11/09→12/16	; Outer diameter 1 [mm]: 83	KH10006 ProKIT	
					; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT
						;
<b>CITROËN - C4 AIRCROSS Wagon</b>				<b>04/12→</b>		
1.6 HDi 115 AWC	84 kW	1.6 l	05/12→		KH30127 ProKIT	
1.8 HDi 150 AWC	110 kW	1.8 l	04/12→			
<b>CITROËN - C4 CACTUS</b>				<b>09/14→</b>		
1.2 PureTech 130	96 kW	1.2 l	11/17→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT	
					; Outer diameter 1 [mm]: 72	KH10054 ProKIT
						;
1.2 THP 110	81 kW	1.2 l	09/14→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT	
1.2 VTi 75 / PureTech 75	55 kW	1.2 l	09/14→			
1.2 VTi 82	60 kW	1.2 l	09/14→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT	
1.6 BlueHDi 100	73 kW	1.6 l	09/14→			
1.6 HDi 90	68 kW	1.6 l	09/14→	;	KH10048 ProKIT	
					;	KH10086 ProKIT
1.5 BlueHDi 100	73 kW	1.5 l	06/18→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT	
1.5 BlueHDi 100	75 kW	1.5 l	06/18→			
1.5 BlueHDi 120	88 kW	1.5 l	09/18→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT	
1.6 THP 173 Flex	127 kW	1.6 l	09/18→			
1.6 VTi 115	85 kW	1.6 l	01/19→			
1.6 VTi 120 Flex	87 kW	1.6 l	09/18→			
1.6 VTi 120 Flex	90 kW	1.6 l	09/18→			
THP 165	121 kW	1.6 l	01/19→			
<b>CITROËN - C4 Coupe (LA_)</b>				<b>11/04→12/13</b>		
1.4 16V	65 kW	1.4 l	11/04→07/11	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6 16V	80 kW	1.6 l	11/04→07/11			
1.6 HDi	66 kW	1.6 l	11/04→07/11	; 09/06 ->;	KH10048 ProKIT	
1.6 HDi	80 kW	1.6 l	11/04→07/11			
2.0 16V	100 kW	2 l	11/04→07/07	; -> 09/06	KH10079 ProKIT	
2.0 16V	130 kW	2 l	11/04→12/10			
2.0 HDi	100 kW	2 l	11/04→12/10			
1.6 16V	81 kW	1.6 l	03/11→12/13	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6 THP	103 kW	1.6 l	06/08→07/11			
1.6 THP 150	110 kW	1.6 l	07/08→07/11	; Outer diameter 1 [mm]: 82;  19 Inch	KH10047 ProKIT	
1.6 VTi 120	88 kW	1.6 l	07/08→07/11			
2.0 HDi	103 kW	2 l	07/08→07/11	;	KH10048 ProKIT	
2.0 VTR	103 kW	2 l	10/06→12/07			
<b>CITROËN - C4 GRAND PICASSO I (UA_)</b>				<b>10/06→12/13</b>		
1.6 16V	103 kW	1.6 l	07/08→12/10		KH10047 ProKIT	
1.6 16V	110 kW	1.6 l	10/08→08/13			





**CITROËN - C4 GRAND PICASSO I (UA\_)**

10/06→12/13

1.6 HDi	80 kW	1.6 l	10/06→06/11
1.6 HDi 110	82 kW	1.6 l	09/10→08/13
1.6 THP 155	115 kW	1.6 l	09/10→08/13
1.6 VTi 120	88 kW	1.6 l	07/08→08/13
1.8 i 16V	92 kW	1.8 l	10/06→12/10
1.8 i 16V CNG	86 kW	1.8 l	03/09→12/11
1.8 i 16V Flex	86 kW	1.8 l	06/09→01/13
2.0 HDi 138	100 kW	2 l	10/06→12/13
2.0 HDi 150	110 kW	2 l	07/09→08/13
2.0 HDi 165	120 kW	2 l	09/10→08/13
2.0 i 16V	103 kW	2 l	10/06→08/13
2.0 i 16V	105 kW	2 l	01/10→08/13

	KH10047 ProKIT
--	----------------

**CITROËN - C4 GRAND PICASSO II (DA\_, DE\_)**

06/13→

1.2 THP 130	96 kW	1.2 l	04/14→
1.6 BlueHDi 100	73 kW	1.6 l	01/15→
1.6 BlueHDi 120	88 kW	1.6 l	07/14→
1.6 HDi / BlueHDi 115	85 kW	1.6 l	09/13→
1.6 HDi 90	68 kW	1.6 l	09/13→
1.6 THP 155	115 kW	1.6 l	09/13→
1.6 THP 165	121 kW	1.6 l	07/14→
1.6 VTi 120	88 kW	1.6 l	09/13→
2.0 BlueHDi 150	110 kW	2 l	06/13→
1.6 THP 150	110 kW	1.6 l	09/14→
2.0 BlueHDi 135	100 kW	2 l	09/13→

	KH10027 ProKIT
	KH30111 ProKIT
	KH10027 ProKIT

**CITROËN - C4 PICASSO I MPV (UD\_)**

10/06→08/13

1.6 16V	110 kW	1.6 l	07/08→08/13
1.6 HDi	80 kW	1.6 l	02/07→08/13
1.6 HDi 110	82 kW	1.6 l	09/10→08/13
1.6 THP 140	103 kW	1.6 l	07/08→08/13
1.6 THP 155	115 kW	1.6 l	09/10→08/13
1.6 VTi 120	88 kW	1.6 l	07/08→08/13
1.8 Bifuel	92 kW	1.8 l	01/09→10/12
1.8 i 16V	92 kW	1.8 l	02/07→12/11
2.0 HDi 138	100 kW	2 l	10/06→08/13
2.0 HDi 150	110 kW	2 l	07/09→08/13
2.0 HDi 165	120 kW	2 l	09/10→08/13
2.0 i 16V	103 kW	2 l	09/07→08/13
2.0 i 16V	105 kW	2 l	05/08→05/13

	KH10047 ProKIT
	KH10040 ProKIT

**CITROËN - C4 PICASSO II**

02/13→

1.2 THP 130	96 kW	1.2 l	04/14→
1.6 BlueHDi 100	73 kW	1.6 l	12/14→
1.6 BlueHDi 120	88 kW	1.6 l	07/14→
1.6 HDi / BlueHDi 115	85 kW	1.6 l	02/13→
1.6 HDi 90	68 kW	1.6 l	02/13→
1.6 THP 155	115 kW	1.6 l	02/13→
1.6 THP 165	121 kW	1.6 l	07/14→
1.6 VTi 120	88 kW	1.6 l	02/13→
2.0 BlueHDi 135	100 kW	2 l	09/13→
2.0 BlueHDi 150	110 kW	2 l	09/13→
1.6 THP 150	110 kW	1.6 l	09/14→

























	KH10027 ProKIT
	KH30111 ProKIT
	KH10027 ProKIT

**CITROËN - C5 I / C5 I Break / C5 II / C5 II Break (DC\_, DE\_, RC\_, RE\_)**

03/01→01/08







































1.6 HDi (RC8HZB)	80 kW	1.6 l	09/04→01/08
1.6 HDi (RE9HZC, RE9HYB)	80 kW	1.6 l	09/04→01/08
1.8 16V	92 kW	1.8 l	09/05→01/08
1.8 16V (DC6FZB, DC6FZE)	85 kW	1.8 l	03/01→08/04
1.8 16V (DE6FZB, DE6FZE)	85 kW	1.8 l	06/01→08/04
1.8 16V (RC6FZB)	85 kW	1.8 l	09/04→08/05
1.8 16V (RE6FYB)	92 kW	1.8 l	09/05→01/08
1.8 16V (RE6FZB)	85 kW	1.8 l	09/04→08/05
2.0 16V (DCRFNC, DCRFNF)	100 kW	2 l	03/01→08/04
2.0 16V (DERFNF, DERFNC, RERFNC)	100 kW	2 l	06/01→08/04
2.0 16V (RCRFJB, RCRFJC)	103 kW	2 l	09/04→08/08
2.0 16V (RERFJB, RERFJC)	103 kW	2 l	09/04→
2.0 16V HPI (DCRLZB)	103 kW	2 l	03/01→08/04
2.0 16V HPI (DERLZB)	103 kW	2 l	06/01→08/04
2.0 HDi	79 kW	2 l	03/01→08/04
2.0 HDi (DCRHYP)	66 kW	2 l	03/01→08/04
2.0 HDi (DCRHZB, DCRHZE)	80 kW	2 l	03/01→08/04
2.0 HDi (DERHSB, DERHSE)	79 kW	2 l	06/01→08/04
2.0 HDi (DERHYB)	66 kW	2 l	06/01→08/04
2.0 HDi (DERHZB, DERHZE)	80 kW	2 l	06/01→08/04
2.0 HDi (RCRHRH)	100 kW	2 l	09/04→01/08
2.0 HDi (RERHRH)	100 kW	2 l	09/04→
2.2 HDi	125 kW	2.2 l	04/06→08/08

	KH10047 ProKIT
	KH20053 ProKIT

      			
<b>CITROËN - C5 I / C5 I Break / C5 II / C5 II Break (DC_, DE_, RC_, RE_) 03/01→01/08</b>			
2.2 HDi (DC4HXB, DC4HXE)	98 kW	2.2 l	03/01→08/04 
2.2 HDi (DE4HXB, DE4HXE)	98 kW	2.2 l	06/01→08/04 
2.2 HDi (RC4HXE)	98 kW	2.2 l	09/04→08/08
2.2 HDi (RE4HTE, RE4HT2)	125 kW	2.2 l	04/06→08/08
2.2 HDi (RE4HXE)	98 kW	2.2 l	09/04→
3.0 Carlsson	173 kW	3 l	09/03→08/04
3.0 V6 (DCXFXC, DCXFXF)	152 kW	3 l	03/01→08/04
3.0 V6 (DEXFXC, DEXFXF)	152 kW	3 l	06/01→08/04
3.0 V6 (RCXFUF)	152 kW	3 l	09/04→09/08
3.0 V6 (REXFUF)	152 kW	3 l	09/04→01/08
2.2 HDi	120 kW	2.2 l	05/06→01/08 
2.2 HDi (RE4HPE, RE4HP2, RE4HRE, RE4HR2)	120 kW	2.2 l	05/06→01/08
3.0 (REXFUJ)	173 kW	3 l	09/04→01/08
3.0 Carlsson HP	173 kW	3 l	08/01→08/04
3.0 V6 (REXFUJ)	155 kW	3 l	10/04→04/07
<b>CITROËN - C5 III Break / C5 III Sedan (RW_, RD_) 02/08→</b>			
1.6 HDi 110	80 kW	1.6 l	02/08→ 
1.6 HDi 110	82 kW	1.6 l	07/10→ 
1.6 HDi 115	84 kW	1.6 l	01/12→
1.6 THP 150	110 kW	1.6 l	04/09→
1.6 THP 150	110 kW	1.6 l	07/10→
1.6 THP 155	115 kW	1.6 l	04/09→
1.6 VTi 120	88 kW	1.6 l	07/10→
1.6 VTi 120	88 kW	1.6 l	07/10→
1.8 16V	92 kW	1.8 l	02/08→
1.8 16V (RW6FYC)	92 kW	1.8 l	02/08→12/09
2.0 16V	103 kW	2 l	02/08→
2.0 16V (RWRFJC, RWRFJF)	103 kW	2 l	02/08→12/11
2.0 16V BioFlex	103 kW	2 l	02/08→
2.0 16V BioFlex (RDRFJF)	103 kW	2 l	02/08→12/12
2.0 HDi	100 kW	2 l	02/08→
2.0 HDi (RDRHDA)	100 kW	2 l	02/08→
2.0 HDi 140	103 kW	2 l	11/08→
2.0 HDi 140	103 kW	2 l	04/09→
2.0 HDi 150 / BlueHdi 150 (RWRHEJ, RWRHE8)	110 kW	2 l	04/09→02/15
2.0 HDi 165	120 kW	2 l	04/09→
2.2 HDi (RD4HTH)	125 kW	2.2 l	02/08→12/11
2.2 HDi (RW4HTH)	125 kW	2.2 l	02/08→12/11
2.2 HDi 165	120 kW	2.2 l	02/08→
2.2 HDi 200	150 kW	2.2 l	07/10→
2.7 HDi	150 kW	2.7 l	02/08→
3.0 HDi 240 (RDx8CA)	177 kW	3 l	04/09→10/14
3.0 HDi 240 (RWx8CA)	177 kW	3 l	04/09→10/14
3.0 V6	155 kW	3 l	02/08→
3.0 V6 (RWXFVA, RWXFUA)	155 kW	3 l	02/08→12/10
2.0 HDi 150 / BlueHdi 150 (RDRHEA, RDRHE8)	110 kW	2 l	04/09→02/15 
2.0 HDi 180	133 kW	2 l	03/15→
<b>CITROËN - C5 Estate Van (DE_, RE_) 06/02→01/08</b>			
1.6 HDi	80 kW	1.6 l	09/04→01/08 
1.8	85 kW	1.8 l	09/04→08/05
2.0	103 kW	2 l	11/04→01/08
2.0 HDi	66 kW	2 l	06/02→08/04
2.0 HDi	80 kW	2 l	06/02→08/04
2.0 HDi	100 kW	2 l	09/04→01/08
2.2 HDi	98 kW	2.2 l	06/02→08/04
<b>CITROËN - C6 Sedan (TD_) 09/05→12/12</b>			
2.2 HDi	120 kW	2.2 l	06/06→12/10 
2.2 HDi	125 kW	2.2 l	06/06→12/12 
2.7 HDi	150 kW	2.7 l	09/05→12/11
3.0 HDi	177 kW	3 l	04/09→12/12
3.0 V6	155 kW	3 l	09/05→12/12
<b>CITROËN - C8 (EA_, EB_) 07/02→12/12</b>			
2.0	100 kW	2 l	07/02→ 
2.0 16V	103 kW	2 l	09/05→ 
2.0 HDi	79 kW	2 l	07/02→ 
2.0 HDi	88 kW	2 l	07/06→
2.0 HDi 135	100 kW	2 l	03/06→
2.0 HDi 165	120 kW	2 l	03/06→ 
3.0 V6	150 kW	3 l	07/02→
2.2	116 kW	2.2 l	07/02→ 
			 -> 03/11;  3FZ (EW12J4)
			 -> 03/11



<b>CITROËN - C8 (EA_, EB_)</b>					<b>07/02→12/12</b>	
2.2 HDi	94 kW	2.2 l	07/02→	; -> 03/11;  4HW (DW12TED4) ; -> 03/11	KH10132 ProKIT KH20055 ProKIT	
2.2 HDi	125 kW	2.2 l	06/06→12/12	; -> 03/11;  4HT (DW12BTED4) ; -> 03/11	KH10132 ProKIT KH20055 ProKIT	
<b>CITROËN - C15 Box Body/MPV (VD_)</b>					<b>10/84→12/05</b>	
1.0	33 kW	1 l	10/84→12/97	; Orga -> 03978 ; 07/88 -> 06/95	KH00091 ProKIT KH20046 ProKIT	
1.0 E	37 kW	1 l	11/92→07/96		KH10051 ProKIT	
1.1	40 kW	1.1 l	11/88→07/96			
1.9 D	51 kW	1.9 l	01/00→07/05			
1.1	35 kW	1.1 l	10/84→12/96	; Orga -> 03978 ; 07/87 -> 07/88	KH00091 ProKIT KH20046 ProKIT	
1.1	40 kW	1.1 l	10/84→07/87	; 07/87 ->	KH20046 ProKIT	
1.1 i	44 kW	1.1 l	07/88→12/96	; Orga -> 03978	KH00091 ProKIT	
1.4 i	55 kW	1.4 l	05/91→12/96		KH10051 ProKIT	
1.8 D	44 kW	1.8 l	07/86→12/00		KH20046 ProKIT	
1.3	47 kW	1.3 l	07/87→05/88	; Orga -> 03978 	KH00091 ProKIT KH20046 ProKIT	
1.4	49 kW	1.4 l	07/87→12/96	; Orga -> 03978  ; 07/88 ->	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
1.4 E	44 kW	1.4 l	05/87→12/96	; Orga -> 03978 ; 05/88 -> 07/89	KH00091 ProKIT KH20046 ProKIT	
1.9 D	44 kW	1.9 l	12/00→12/05	; Orga -> 03978  ; 09/01 ->	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
<b>CITROËN - C15 Estate</b>					<b>04/87→08/00</b>	
1.1	40 kW	1.1 l	10/88→10/92	  ; -> 07/92	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
1.1	44 kW	1.1 l	08/88→07/96	  ; 09/89 ->	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
1.4	44 kW	1.4 l	05/87→10/92	 ; 05/88 -> 07/88	KH00091 ProKIT KH20046 ProKIT	
1.4	49 kW	1.4 l	05/87→09/92	; 05/88 ->  ; 07/88 ->	KH10051 ProKIT KH00091 ProKIT KH20046 ProKIT	
1.4	55 kW	1.4 l	05/91→07/96	  	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
1.8 D	44 kW	1.8 l	04/87→08/00	  ; -> 07/96	KH00091 ProKIT KH10051 ProKIT KH20046 ProKIT	
<b>CITROËN - C25 Bus / C25 Platform/Chassis / C25 Van (280_, 290_)</b>					<b>09/81→07/94</b>	
1.8	50 kW	1.8 l	11/81→01/94	; 01/89 ->; VIN 604497 ->	KH00035 ProKIT	
1.8 E	51 kW	1.8 l	07/87→02/94			
1.9 D	51 kW	1.9 l	07/87→02/94	; -> 12/89; VIN -> 604496	KH00061 ProKIT	
1.9 D 1400	51 kW	1.9 l	01/88→01/94			
2.0	62 kW	2 l	01/87→03/94			
2.5 D	54 kW	2.5 l	02/85→07/94			
2.5 D	55 kW	2.5 l	11/81→01/94			
2.5 D	55 kW	2.5 l	11/83→01/94			
2.5 DT	70 kW	2.5 l	01/87→01/94			
1.9 DT	60 kW	1.9 l	10/91→01/94	; VIN 604497 ->	KH00035 ProKIT	
1.9 TD	60 kW	1.9 l	04/92→02/94			
2.0	62 kW	2 l	02/91→02/94			
2.0	62 kW	2 l	02/91→03/94			
2.0 4x4	62 kW	2 l	01/90→01/94			
2.5 DT	70 kW	2.5 l	08/91→01/94			
2.5 DT 4x4	70 kW	2.5 l	08/91→01/94			
2.0	57 kW	2 l	11/81→12/86	; VIN -> 604496	KH00061 ProKIT	
2.5 D 4x4	55 kW	2.5 l	11/83→12/86			

										
<b>CITROËN - C25 Bus / C25 Platform/Chassis / C25 Van (280_, 290_)</b>									<b>09/81→07/94</b>	
2.0 E	58 kW	2 l	09/81→02/94		; 01/89 ->	VIN 604497 ->				KH00035 ProKIT
2.0 E	58 kW	2 l	09/81→03/94		; > 12/89;	VIN -> 604496				KH00061 ProKIT
2.5 D	54 kW	2.5 l	10/85→02/94							KH00107 ProKIT
2.5 D Turbo	70 kW	2.5 l	08/87→02/94		; > 08/90;	VIN 289711 ->				KH00107 ProKIT
2.5 D 4x4	54 kW	2.5 l	01/87→02/94		; 01/89 ->	VIN 604497 ->				KH00035 ProKIT
2.5 D Turbo 4x4	70 kW	2.5 l	08/87→02/94		; > 12/89;	VIN -> 604496				KH00061 ProKIT
					; 09/90 ->					KH00107 ProKIT
<b>CITROËN - C-CROSSER (VU_, VV_)</b>									<b>02/07→12/12</b>	
2.2 HDi	115 kW	2.2 l	02/07→12/12		; > 02/10					KH10164 ProKIT
2.4 16V	125 kW	2.4 l	08/08→12/12							
<b>CITROËN - C-ELYSEE (DD_)</b>									<b>11/12→01/17</b>	
1.2 VTi 72 (DDHMY0)	53 kW	1.2 l	11/12→01/17		; Outer diameter 1 [mm]: 82					KH10047 ProKIT
					; Outer diameter 1 [mm]: 72					KH10054 ProKIT
										KH10086 ProKIT
1.2 VTi 82	60 kW	1.2 l	12/14→							KH10086 ProKIT
1.6 BlueHDi 100	73 kW	1.6 l	11/14→		; 02/17 ->	Brake diameter, outer [mm]: 203				
1.6 HDi 92	68 kW	1.6 l	11/12→		; Outer diameter 1 [mm]: 82					KH10047 ProKIT
1.6 VTi 115 (DDNFP0, DDNFP6, DDNFP9)	85 kW	1.6 l	11/12→		; Outer diameter 1 [mm]: 72					KH10054 ProKIT
1.5 BlueHDi 100	75 kW	1.5 l	05/18→		; Outer diameter 1 [mm]: 82					KH10047 ProKIT
					; Outer diameter 1 [mm]: 72					KH10054 ProKIT
<b>CITROËN - C-ZERO</b>									<b>10/10→</b>	
C-Zero	35 kW		10/10→							KH20005 ProKIT
C-Zero	47 kW		10/10→							
C-Zero	49 kW		10/14→							
<b>CITROËN - DISPATCH Platform/Chassis</b>									<b>07/11→</b>	
2.0 HDi 125	94 kW	2 l	07/11→							KH10119 ProKIT
<b>CITROËN - DISPATCH Van</b>									<b>01/07→03/16</b>	
1.6 HDi 90 16V	66 kW	1.6 l	01/07→03/16							KH10119 ProKIT
1.6 HDi 90 8V	66 kW	1.6 l	01/07→03/16							KH30015 ProKIT
2.0 HDi 120	88 kW	2 l	01/07→03/16							KH30016 ProKIT
2.0 HDi 125	94 kW	2 l	07/11→03/16							
2.0 HDi 140	100 kW	2 l	01/07→03/16							
2.0 HDi 165	120 kW	2 l	07/10→03/16							
2.0 HDi 95	72 kW	2 l	07/11→03/16							
2.0 i	103 kW	2 l	01/07→03/16							
<b>CITROËN - DISPATCH Van (V_)</b>									<b>04/16→</b>	
1.6 BlueHDi 115	85 kW	1.6 l	04/16→							KH10119 ProKIT
1.6 BlueHDi 95	70 kW	1.6 l	04/16→							
2.0 BlueHDi 120	90 kW	2 l	04/16→							
2.0 BlueHDi 150	110 kW	2 l	04/16→							
2.0 BlueHDi 180	130 kW	2 l	04/16→							
<b>CITROËN - DS3 / DS3 Convertible (SA_)</b>									<b>11/09→07/15</b>	
1.2 THP 110	81 kW	1.2 l	10/14→03/15		; Outer diameter 1 [mm]: 82					KH10047 ProKIT
1.2 THP 110	81 kW	1.2 l	10/14→07/15		; Outer diameter 1 [mm]: 72					KH10054 ProKIT
1.2 VTi 82	60 kW	1.2 l	01/13→03/15							KH10048 ProKIT
1.2 VTi 82	60 kW	1.2 l	01/13→07/15							KH10048 ProKIT
1.4 HDi 70 (SA8HP4)	50 kW	1.4 l	04/10→07/15							KH10086 ProKIT
1.6 BlueHDi 100	73 kW	1.6 l	07/14→07/15							
1.6 BlueHDi 115	85 kW	1.6 l	10/13→07/15							
1.6 BlueHDi 120	88 kW	1.6 l	10/13→07/15							
1.6 BlueHDi 120	88 kW	1.6 l	07/14→07/15							
1.6 BlueHDi 75	55 kW	1.6 l	03/15→07/15							
1.6 HDi 110	82 kW	1.6 l	11/09→07/15							
1.6 HDi 115	84 kW	1.6 l	08/12→07/15							
1.6 HDi 115	85 kW	1.6 l	10/13→07/15							
1.6 HDi 90	68 kW	1.6 l	01/13→07/15							
1.4 VTi 95	70 kW	1.4 l	04/10→07/15		; Outer diameter 1 [mm]: 82					KH10047 ProKIT
1.4 VTi 95 LPG	70 kW	1.4 l	08/12→07/15		; Outer diameter 1 [mm]: 72					KH10054 ProKIT
1.4 VTi 98	72 kW	1.4 l	11/09→07/15							KH10048 ProKIT
1.6 Racing	149 kW	1.6 l	02/11→07/15							KH10048 ProKIT
1.6 Racing	152 kW	1.6 l	02/11→07/15							
1.6 Racing	152 kW	1.6 l	03/14→07/15							
1.6 THP 150	110 kW	1.6 l	01/10→07/15							
1.6 THP 150	110 kW	1.6 l	01/13→07/15							
1.6 THP 155	115 kW	1.6 l	04/10→07/15							
1.6 THP 155	115 kW	1.6 l	01/13→07/15							
1.6 THP160	120 kW	1.6 l	01/12→07/15							





**CITROËN - DS3 / DS3 Convertible (SA\_) 11/09→07/15**

1.6 THP 165	121 kW	1.6 l	10/14→06/15	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 THP 165	121 kW	1.6 l	10/14→07/15	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.6 VTi 120	88 kW	1.6 l	04/10→07/15	;	KH10048 ProKIT
1.6 VTi 120	88 kW	1.6 l	01/13→07/15	;	KH10048 ProKIT
1.6 BlueHDi 100	75 kW	1.6 l	07/14→07/15	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 Racing	149 kW	1.6 l	03/14→07/15	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.6 THP 165	120 kW	1.6 l	02/15→07/15	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.6 HDi 90	68 kW	1.6 l	11/09→07/15	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
				; Outer diameter 1 [mm]: 72	KH10054 ProKIT
				;	KH10048 ProKIT
					KH10086 ProKIT

**CITROËN - DS4 (NX\_) 04/11→07/15**

1.2 THP 130	96 kW	1.2 l	07/14→07/15	; Outer diameter 1 [mm]: 83;	KH10006 ProKIT
1.6 BlueHDi 120	88 kW	1.6 l	07/14→07/15	; Outer diameter 1 [mm]: 82;	KH10047 ProKIT
1.6 HDi 110	82 kW	1.6 l	04/11→07/15	; ;	KH10040 ProKIT
1.6 HDi 115	84 kW	1.6 l	08/12→07/15	; ;	KH10040 ProKIT
1.6 HDi 90	68 kW	1.6 l	05/11→07/15	;	KH20138 ProKIT
1.6 THP 155	115 kW	1.6 l	04/11→07/15		
1.6 THP 160	120 kW	1.6 l	04/12→07/15		
1.6 VTi 120	88 kW	1.6 l	04/11→07/15		
2.0 BlueHDi 150	110 kW	2 l	07/14→07/15		
2.0 BlueHDi 180	133 kW	2 l	07/14→07/15		
2.0 HDi / BlueHDi 135	100 kW	2 l	09/11→07/15		
2.0 HDi 165	120 kW	2 l	04/11→07/15		
1.6 BlueHDi 115	85 kW	1.6 l	07/14→07/15	; Outer diameter 1 [mm]: 83;	KH10006 ProKIT
1.6 THP 150	110 kW	1.6 l	04/11→07/15	; Outer diameter 1 [mm]: 82;	KH10047 ProKIT
1.6 THP 165	121 kW	1.6 l	01/12→07/15	; ;	KH10040 ProKIT
1.6 THP 200	147 kW	1.6 l	04/11→07/15	; Outer diameter 1 [mm]: 83;	KH10006 ProKIT
				; Outer diameter 1 [mm]: 82;	KH10047 ProKIT
				;	KH20138 ProKIT

**CITROËN - DS5 11/11→07/15**

1.6 BlueHDi 120	88 kW	1.6 l	07/14→07/15	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
1.6 HDi	85 kW	1.6 l	11/13→07/15	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 HDi 110	82 kW	1.6 l	11/11→07/15	;	KH10040 ProKIT
1.6 HDi 115	84 kW	1.6 l	06/12→07/15	;	KH10040 ProKIT
1.6 THP 150	110 kW	1.6 l	11/11→07/15		
1.6 THP 155	115 kW	1.6 l	11/11→07/15		
1.6 THP 165	121 kW	1.6 l	01/12→07/15		
2.0 BlueHDi 150	110 kW	2 l	07/14→07/15		
2.0 HDi 135	100 kW	2 l	11/11→07/15		
2.0 HDi 165	120 kW	2 l	11/11→07/15		
1.6 THP 165 Hybrid	121 kW	1.6 l	06/12→07/15	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
				; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 THP 200	147 kW	1.6 l	11/11→07/15	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
				; Outer diameter 1 [mm]: 82	KH10047 ProKIT
				;	KH20138 ProKIT
2.0 BlueHDi 180	133 kW	2 l	08/13→07/15	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
				; Outer diameter 1 [mm]: 82	KH10047 ProKIT
				;	KH10040 ProKIT
				;	KH20138 ProKIT
2.0 HDi 200 Hybrid4 All-wheel Drive	147 kW	2 l	12/11→07/15	; Outer diameter 1 [mm]: 83	KH10006 ProKIT




































































**CITROËN - DYANE 08/67→10/84**

4	13 kW	0.4 l	08/67→03/68		KH10185 ProKIT
4	17 kW	0.4 l	04/68→07/75		
6	21 kW	0.6 l	12/68→10/84		
6	24 kW	0.6 l	05/72→12/80		

**CITROËN - EVASION MPV (22, U6) 06/94→07/02**

1.8	73 kW	1.8 l	05/97→07/02	; -> 05/02	KH20095 ProKIT
1.9 TD	66 kW	1.9 l	11/94→07/02		KH10089 ProKIT
2.0 HDI	80 kW	2 l	08/99→07/02		KH20095 ProKIT
2.1 TD	80 kW	2.1 l	05/96→07/02	; -> 05/02	KH20095 ProKIT
1.9 TD	68 kW	1.9 l	10/95→12/98		KH10089 ProKIT
				; -> 09/98	KH20095 ProKIT
2.0	89 kW	2 l	06/94→07/02		KH10089 ProKIT
2.0 Turbo C.T.	108 kW	2 l	06/94→07/02	; 07/94 -> 05/02	KH20095 ProKIT



    						
<b>CITROËN - EVASION MPV (22, U6)</b>				<b>06/94→07/02</b>		
2.0 16V	97 kW	2 l	05/98→04/00		KH10089 ProKIT	
				 ; 10/98 ->	KH20095 ProKIT	
2.0 16V	100 kW	2 l	05/00→07/02		KH10089 ProKIT	
				 ; 07/00 -> 05/02	KH20095 ProKIT	
2.0 HDi 16V	80 kW	2 l	09/99→07/02		KH10089 ProKIT	
				 ; 01/01 -> 05/02	KH20095 ProKIT	
<b>CITROËN - JUMPER Bus</b>				<b>04/06→</b>		
2.0 BlueHdi 110	81 kW	2 l	07/15→09/19		KH10120 ProKIT	
2.0 BlueHdi 130	96 kW	2 l	07/15→09/19		KH20059 ProKIT	
2.0 BlueHdi 160	120 kW	2 l	07/15→09/19	 ; Payload [kg]: 1,600;  ; Payload [kg]: 2,000		
2.2 HDi 100	74 kW	2.2 l	04/06→		KH20086 ProKIT	
2.2 HDi 110	81 kW	2.2 l	07/11→			
2.2 HDi 120	88 kW	2.2 l	04/06→			
2.2 HDi 130	96 kW	2.2 l	07/11→			
2.2 HDi 150	110 kW	2.2 l	07/11→			
3.0 HDi 155	115 kW	3 l	07/10→			
3.0 HDi 160	116 kW	3 l	09/06→			
3.0 HDi 180	130 kW	3 l	07/11→			
2.2 BlueHdi 120	88 kW	2.2 l	08/19→			KH10120 ProKIT
2.2 BlueHdi 140	103 kW	2.2 l	08/19→			
2.2 BlueHdi 165	121 kW	2.2 l	08/19→			
<b>CITROËN - JUMPER Bus (230P)</b>				<b>02/94→04/02</b>		
1.9 D	51 kW	1.9 l	01/99→04/02	 ; VIN -> 16205754;  ;  ; Payload from [kg]:	KH00035 ProKIT	
1.9 TD	66 kW	1.9 l	08/94→04/02	1,000 → Payload to [kg]: 1,400		
1.9 TD	68 kW	1.9 l	02/94→04/02	 ; VIN -> 1620653;  ;  ; Payload from [kg]:	KH10078 ProKIT	
2.0	80 kW	2 l	02/94→04/02	1,000 → Payload to [kg]: 1,400		
2.5 D	63 kW	2.5 l	08/94→04/02	 ; VIN 16205754 ->;  ;  ; Payload from [kg]:	KH10078 ProKIT	
2.5 TD	76 kW	2.5 l	08/94→04/02	1,000 → Payload to [kg]: 1,400		
2.5 TDi	79 kW	2.5 l	12/96→11/00	 ; VIN 16205755 ->;  ;  ; Payload from [kg]:	KH10078 ProKIT	
2.8 HDi	94 kW	2.8 l	09/00→04/02	1,000 → Payload to [kg]: 1,400		
				 ;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00080 ProKIT	
				 ; VIN -> 16194399; Payload [kg]: 1,800		
				 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT	
				 ; VIN -> 16194399; Payload [kg]: 1,800	KH00019 ProKIT	
				 ; VIN -> 16194399; Payload [kg]: 1,000, 1,400	KH00043 ProKIT	
				 ; VIN 16194400 ->	KH10091 ProKIT	
1.9 TD 4x4	68 kW	1.9 l	08/96→04/02	 ; VIN -> 16205754;  ;  ; Payload from [kg]:	KH00035 ProKIT	
2.0 4x4	80 kW	2 l	08/96→04/02	1,000 → Payload to [kg]: 1,400		
2.5 D 4x4	63 kW	2.5 l	08/96→04/02	 ; VIN -> 1620653;  ;  ; Payload from [kg]:	KH10078 ProKIT	
2.5 TD 4x4	76 kW	2.5 l	08/96→04/02	1,000 → Payload to [kg]: 1,400		
2.5 TDi 4x4	79 kW	2.5 l	12/96→11/00	 ; 	KH10078 ProKIT	
2.8 HDi 4x4	94 kW	2.8 l	09/00→04/02	1,000 → Payload to [kg]: 1,400		
				 ;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00080 ProKIT	
				 ; VIN -> 16194399; Payload [kg]: 1,800		
				 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT	
					KH10391 ProKIT	
2.8 D	64 kW	2.8 l	01/99→02/02	 ; VIN -> 16205754;  ;  ; Payload from [kg]:	KH00035 ProKIT	
				1,000 → Payload to [kg]: 1,400		
				 ; VIN -> 1620653;  ;  ; Payload from [kg]:	KH10078 ProKIT	
				1,000 → Payload to [kg]: 1,400		
				 ; VIN 16205754 ->;  ;  ; Payload from [kg]:	KH10078 ProKIT	
				1,000 → Payload to [kg]: 1,400		
				 ; VIN 16205755 ->;  ;  ; Payload from [kg]:	KH00080 ProKIT	
				1,000 → Payload to [kg]: 1,400		
				 ;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00080 ProKIT	
				 ; VIN -> 16194399; Payload [kg]: 1,800		
				 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT	
				 ; VIN 16194400 ->	KH10091 ProKIT	





**CITROËN - JUMPER Bus (244, Z\_)** **04/02→06/06**

2.0	81 kW	2 l	04/02→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
2.0 bivalent	81 kW	2 l	02/03→06/06	; not for vehicle identification number: 936...	KH10101 ProKIT
2.0 HDi	62 kW	2 l	04/02→06/06	Payload [kg]: 1,800	
2.2 HDi	74 kW	2.2 l	04/02→06/06	; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
2.8 HDi	94 kW	2.8 l	04/02→06/06		KH10091 ProKIT
2.3 HDi	93 kW	2.3 l	08/08→	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
2.8 HDi	77 kW	2.8 l	06/03→06/06	; not for vehicle identification number: 936...	KH10101 ProKIT
2.8 HDi All-wheel Drive	94 kW	2.8 l	04/02→06/06	; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT

**CITROËN - JUMPER Platform/Chassis** **04/06→**

2.0 BlueHDi 110	81 kW	2 l	11/15→09/19		KH10120 ProKIT
2.0 BlueHDi 130	96 kW	2 l	11/15→09/19	; Payload [kg]: 1,600; ; Payload [kg]: 2,000	KH20059 ProKIT
2.0 BlueHDi 160	120 kW	2 l	11/15→09/19		
2.2 HDi 100	74 kW	2.2 l	04/06→	; Payload [kg]: 1,200, 1,400, 1,600;	KH20086 ProKIT
2.2 HDi 110	81 kW	2.2 l	07/11→		
2.2 HDi 120	88 kW	2.2 l	04/06→		
2.2 HDi 130	96 kW	2.2 l	07/11→		
2.2 HDi 150	110 kW	2.2 l	07/11→		
3.0 HDi 145	107 kW	3 l	07/10→		
3.0 HDi 160	116 kW	3 l	09/06→		
3.0 HDi 180	130 kW	3 l	07/11→		
2.0 BlueHDi 130 4x4	96 kW	2 l	11/15→09/19		KH10120 ProKIT
2.0 BlueHDi 160 4x4	120 kW	2 l	11/15→09/19		
2.2 BlueHDi 120	88 kW	2.2 l	08/19→		
2.2 BlueHDi 140	103 kW	2.2 l	08/19→		
2.2 BlueHDi 165	121 kW	2.2 l	08/19→		

**CITROËN - JUMPER Platform/Chassis (230)** **03/94→04/02**






1.9 TD	66 kW	1.9 l	03/94→04/02	; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
1.9 TD	68 kW	1.9 l	03/94→04/02	; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.0	80 kW	2 l	03/94→04/02	; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.5 D	63 kW	2.5 l	03/94→04/02	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.5 TD	76 kW	2.5 l	03/94→04/02	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.5 TDi	79 kW	2.5 l	12/96→04/02	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.8 HDi	94 kW	2.8 l	09/00→04/02	; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,800	KH00019 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,000, 1,400	KH00043 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT
2.5 D 4x4	63 kW	2.5 l	03/00→04/02	; VIN -> 16205754; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
2.5 TDi 4x4	79 kW	2.5 l	03/00→04/02	; VIN -> 1620653; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				;	
				; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
				; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				;	KH10391 ProKIT
2.8 D	64 kW	2.8 l	01/99→02/02	; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
				; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT







**CITROËN - JUMPER Platform/Chassis (244)** **02/02→06/06**










































2.0 HDi	62 kW	2 l	04/02→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
2.2 HDi	74 kW	2.2 l	04/02→06/06	; not for vehicle identification number: 936...	KH10101 ProKIT
2.8 HDi	94 kW	2.8 l	04/02→06/06	Payload [kg]: 1,800	
2.8 HDi	107 kW	2.8 l	05/04→06/06	; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
					KH10091 ProKIT
























































CITROËN - JUMPER Platform/Chassis (244)				02/02→06/06	
2.8 HDi 4x4	94 kW	2.8 l	02/02→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
				; not for vehicle identification number: 936...;	KH10101 ProKIT
				Payload [kg]: 1,800	
				; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
CITROËN - JUMPER Van				04/06→	
2.0 BlueHDi 110	81 kW	2 l	11/15→09/19		KH10120 ProKIT
2.0 BlueHDi 130	96 kW	2 l	11/15→09/19	; Payload [kg]: 1,600; ; Payload [kg]: 2,000	KH20059 ProKIT
2.0 BlueHDi 160	120 kW	2 l	11/15→09/19	; Payload [kg]: 1,200, 1,400, 1,600;	KH20086 ProKIT
2.2 HDi 100	74 kW	2.2 l	04/06→12/12		
2.2 HDi 110	81 kW	2.2 l	07/11→		
2.2 HDi 120	88 kW	2.2 l	04/06→		
2.2 HDi 130	96 kW	2.2 l	07/11→		
2.2 HDi 150	110 kW	2.2 l	07/11→		
3.0 HDi 145	107 kW	3 l	07/10→		
3.0 HDi 155	115 kW	3 l	07/10→		
3.0 HDi 160	116 kW	3 l	09/06→		
3.0 HDi 180	130 kW	3 l	07/11→		
2.0 BlueHDi 130 4x4	96 kW	2 l	11/15→09/19		KH10120 ProKIT
2.0 BlueHDi 160 4x4	120 kW	2 l	11/15→09/19		
2.2 BlueHDi 120	88 kW	2.2 l	08/19→		
2.2 BlueHDi 140	103 kW	2.2 l	08/19→		
2.2 BlueHDi 165	121 kW	2.2 l	08/19→		
2.2 HDi 130 4x4	96 kW	2.2 l	01/12→05/16		
CITROËN - JUMPER Van (230L)				02/94→04/02	
1.9 D	50 kW	1.9 l	07/99→04/02	; VIN -> 16205754; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
1.9 D	51 kW	1.9 l	02/94→04/02		
1.9 TD	66 kW	1.9 l	03/94→04/02	; VIN -> 1620653; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
1.9 TD	68 kW	1.9 l	03/94→04/02		
2.0	80 kW	2 l	03/94→04/02	; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
2.0 HDI	62 kW	2 l	11/01→04/02		
2.5 D	63 kW	2.5 l	03/94→04/02	; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.5 TD	76 kW	2.5 l	03/94→04/02		
2.5 TDi	79 kW	2.5 l	12/96→11/00	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.8 HDi	94 kW	2.8 l	09/00→04/02	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,800	KH00019 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,000, 1,400	KH00043 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT
2.0 4x4	80 kW	2 l	10/96→01/02	; VIN -> 16205754; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
2.5 D 4x4	63 kW	2.5 l	03/00→04/02		
2.5 DT 4x4	76 kW	2.5 l	10/96→08/97	; VIN -> 1620653; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
2.5 TDi 4x4	79 kW	2.5 l	03/00→11/00		
2.8 HDi 4x4	94 kW	2.8 l	09/00→04/02	;	
				; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
				; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				;	KH10391 ProKIT
2.8 D	64 kW	2.8 l	01/99→02/02	; VIN -> 16205754; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
				; VIN -> 1620653; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN 16205754 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
				; VIN 16205755 ->; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
CITROËN - JUMPER Van (244)				04/02→10/10	
2.0	81 kW	2 l	04/02→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
2.0 bivalent	81 kW	2 l	02/03→06/06		
2.0 HDi	62 kW	2 l	04/02→06/06	; not for vehicle identification number: 936...;	KH10101 ProKIT
2.2 HDi	74 kW	2.2 l	04/02→06/06	Payload [kg]: 1,800	
2.8 HDi	94 kW	2.8 l	04/02→06/06	; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
2.8 HDi	107 kW	2.8 l	04/04→06/06		KH10091 ProKIT



    				
<b>CITROËN - JUMPER Van (244)</b>				<b>04/02→10/10</b>
2.3 HDi	93 kW	2.3 l	08/08→	KH10120 ProKIT
2.8 HDi	77 kW	2.8 l	06/03→06/06	; Payload [kg]: 800, 1,000, 1,400 KH10078 ProKIT
2.8 HDi	89 kW	2.8 l	07/05→10/10	; not for vehicle identification number: 936...; Payload [kg]: 1,800 KH10101 ProKIT
				; VIN 936...; Payload [kg]: 1,800 KH10234 ProKIT
2.8 HDi 4x4	94 kW	2.8 l	04/02→06/06	; Payload [kg]: 800, 1,000, 1,400 KH10078 ProKIT
				; not for vehicle identification number: 936...; Payload [kg]: 1,800 KH10101 ProKIT
				; VIN 936...; Payload [kg]: 1,800 KH10234 ProKIT
				KH10391 ProKIT
<b>CITROËN - JUMPY (U6U_)</b>				<b>10/95→12/06</b>
1.6	58 kW	1.6 l	10/95→08/00	KH10089 ProKIT
1.9 D	51 kW	1.9 l	10/95→08/98	KH20095 ProKIT
1.9 TD	66 kW	1.9 l	10/95→08/00	KH10089 ProKIT
1.9 D 70	51 kW	1.9 l	04/98→11/03	KH20095 ProKIT
				; 05/98 -> KH20095 ProKIT
1.9 TD	68 kW	1.9 l	04/96→11/03	; -> 12/01 KH20095 ProKIT
2.0	100 kW	2 l	04/00→12/06	KH10089 ProKIT
				; 09/00 -> 12/03 KH20095 ProKIT
2.0 HDi 110	80 kW	2 l	03/00→10/06	KH10089 ProKIT
2.0 HDi 95	69 kW	2 l	10/99→10/06	; 09/00 -> KH20095 ProKIT
2.0 i 16V	102 kW	2 l	03/00→10/06	KH10089 ProKIT
				; 01/04 -> KH20095 ProKIT
<b>CITROËN - JUMPY (VF7)</b>				<b>01/07→03/16</b>
1.6 HDi 90 16V	66 kW	1.6 l	01/07→03/16	KH10119 ProKIT
1.6 HDi 90 8V	66 kW	1.6 l	01/07→03/16	;  KH30015 ProKIT
2.0 HDi 120	88 kW	2 l	01/07→03/16	;  KH30016 ProKIT
2.0 HDi 125	94 kW	2 l	07/11→03/16	;  KH30016 ProKIT
2.0 HDi 140	100 kW	2 l	01/07→03/16	KH30016 ProKIT
2.0 HDi 165	120 kW	2 l	07/10→03/16	KH30016 ProKIT
2.0 HDi 95	72 kW	2 l	07/11→03/16	KH30016 ProKIT
2.0 i	103 kW	2 l	01/07→03/16	KH30016 ProKIT
<b>CITROËN - JUMPY Bus (V_)</b>				<b>04/16→</b>
1.6 BlueHDi 115	85 kW	1.6 l	04/16→	KH10119 ProKIT
1.6 BlueHDi 95	70 kW	1.6 l	04/16→	KH10119 ProKIT
2.0 BlueHDi 150	110 kW	2 l	04/16→	KH10119 ProKIT
2.0 BlueHDi 180	130 kW	2 l	04/16→	KH10119 ProKIT
<b>CITROËN - JUMPY Platform/Chassis (BU_, BV_, BW_, BX_)</b>				<b>10/99→10/06</b>
1.9 TD	68 kW	1.9 l	10/99→10/06	KH10089 ProKIT
				; -> 12/03 KH20095 ProKIT
2.0	100 kW	2 l	12/03→10/06	KH10089 ProKIT
2.0 HDi 110	80 kW	2 l	12/03→10/06	KH10089 ProKIT
2.0 HDi 95	69 kW	2 l	10/99→10/06	KH10089 ProKIT
				; 09/00 -> KH20095 ProKIT
<b>CITROËN - JUMPY Platform/Chassis (V_)</b>				<b>09/16→</b>
1.6 BlueHDi 95	70 kW	1.6 l	09/16→	KH10119 ProKIT
2.0 BlueHDi 120	90 kW	2 l	09/16→	KH10119 ProKIT
2.0 BlueHDi 150	110 kW	2 l	09/16→	KH10119 ProKIT
<b>CITROËN - JUMPY Van (BS_, BT_, BY_, BZ_)</b>				<b>10/95→10/06</b>
1.6 i	58 kW	1.6 l	10/95→08/00	KH10089 ProKIT
2.0 HDi 110	80 kW	2 l	10/01→10/06	KH20095 ProKIT
1.9 D	51 kW	1.9 l	10/95→08/98	KH10089 ProKIT
1.9 DT	65 kW	1.9 l	10/95→08/00	KH10089 ProKIT
2.0 HDi 110	80 kW	2 l	01/02→10/06	KH10089 ProKIT
1.9 D 70	51 kW	1.9 l	04/98→10/06	KH10089 ProKIT
				; 05/98 -> KH20095 ProKIT
1.9 TD	66 kW	1.9 l	10/95→08/00	KH10089 ProKIT
				; 06/98 -> KH20095 ProKIT
2.0 HDi 95	69 kW	2 l	10/99→10/06	KH10089 ProKIT
2.0 i 16V	102 kW	2 l	03/00→10/06	; 09/00 -> KH20095 ProKIT
<b>CITROËN - LNA</b>				<b>11/76→10/86</b>
0.6	24 kW	0.6 l	11/76→07/79	KH00091 ProKIT

     				11/76→10/86	
<b>CITROËN - LNA</b>					
0.6	25 kW	0.6 l	07/82→04/85		KH00091 ProKIT
1.0	33 kW	1 l	07/84→10/86		KH00094 ProKIT
1.1	37 kW	1.1 l	07/82→04/85		
0.6	26 kW	0.6 l	11/78→07/86		KH00091 ProKIT
				; 08/80 ->	KH00094 ProKIT
<b>CITROËN - MEHARI</b>					
05/68→10/87					
0.6	19 kW	0.6 l	05/68→10/79		KH10185 ProKIT
0.6	21 kW	0.6 l	10/79→10/87		
4x4	21 kW	0.6 l	10/79→10/87	; 12/83 ->	KH10185 ProKIT
<b>CITROËN - NEMO Box Body/MPV / NEMO MPV (AA_)</b>					
02/08→					
1.3 HDi 75	55 kW	1.3 l	10/10→		KH10065 ProKIT
1.4 HDi	50 kW	1.4 l	02/08→		KH20022 ProKIT
1.4 HDi	50 kW	1.4 l	04/09→		
1.3 HDi 80	59 kW	1.3 l	10/15→		KH20022 ProKIT
1.4	54 kW	1.4 l	02/08→	; ABS	KH10043 ProKIT
1.4	54 kW	1.4 l	04/09→		KH20022 ProKIT
<b>CITROËN - SAXO (S0, S1)</b>					
02/96→04/04					
1.0 X	33 kW	1 l	05/96→11/98		KH10062 ProKIT
				;	KH10081 ProKIT
				;	KH10083 ProKIT
1.0 X	37 kW	1 l	05/98→06/03	; -> 08/99	KH10062 ProKIT
				; ABS	KH10053 ProKIT
				; 08/99 ->;	KH10056 ProKIT
				; -> 01/99;	KH10081 ProKIT
				; -> 01/99;	KH10083 ProKIT
1.1 BiFuel	44 kW	1.1 l	07/00→06/03	; ABS	KH10053 ProKIT
				; ABS;	KH10062 ProKIT
1.1 X, SX	40 kW	1.1 l	05/96→09/03	; -> 08/99; ABS;	KH10062 ProKIT
				; ABS	KH10053 ProKIT
				; 01/99 -> 08/99; ABS;	KH10056 ProKIT
				; -> 01/99; Outer diameter 1 [mm]: 56	KH10081 ProKIT
				; -> 01/99; Outer diameter 1 [mm]: 52	KH10083 ProKIT
1.1 X, SX	44 kW	1.1 l	05/96→09/03	; -> 08/99; ABS;	KH10062 ProKIT
				; ABS	KH10053 ProKIT
				; 08/99 ->	KH10056 ProKIT
				; -> 01/99; HDZ (TU1M); Outer diameter 1 [mm]: 56	KH10081 ProKIT
				; -> 01/99; Outer diameter 1 [mm]: 52	KH10083 ProKIT
1.4 VTS	55 kW	1.4 l	05/96→06/03	; -> 01/99	KH10051 ProKIT
				; ABS	KH10053 ProKIT
				; 12/00 ->	KH10056 ProKIT
				; -> 01/99	KH10083 ProKIT
1.5 D	40 kW	1.5 l	09/96→09/03	; -> 01/99	KH10051 ProKIT
1.5 D	42 kW	1.5 l	09/96→06/01	; ABS	KH10053 ProKIT
				; 01/99 ->	KH10056 ProKIT
				; -> 01/99	KH10083 ProKIT
1.5 D	43 kW	1.5 l	07/01→04/04	; ABS	KH10053 ProKIT
					KH10056 ProKIT
1.6	66 kW	1.6 l	02/96→06/03	; -> 01/99	KH10051 ProKIT
				; ABS	KH10053 ProKIT
				; 01/99 ->;	KH10056 ProKIT
				; 10/99 ->; ABS	KH20171 ProKIT
				; -> 01/99	KH10083 ProKIT
1.6	74 kW	1.6 l	02/01→04/04	; ABS	KH10053 ProKIT
1.6 VTS	72 kW	1.6 l	09/00→09/03		
1.6	88 kW	1.6 l	02/96→04/04	; -> 01/99	KH10051 ProKIT
				; ABS	KH10053 ProKIT
				; 01/99 ->;	KH10056 ProKIT

     						
<b>CITROËN - SAXO (S0, S1)</b>				<b>02/96→04/04</b>		
1.6 VTL, VTR	65 kW	1.6 l	05/96→06/03	 ; -> 01/99	KH10051 ProKIT	
				 ; ABS	KH10053 ProKIT	
				 ; 01/99 ->; 	KH10056 ProKIT	
				 ; -> 01/99	KH10083 ProKIT	
1.6 VTS	87 kW	1.6 l	06/96→09/03	 ; -> 01/99	KH10051 ProKIT	
				 ; ABS	KH10053 ProKIT	
Electric	20 kW		11/96→06/03	 ; -> 01/99	KH10051 ProKIT	
				 ; ABS	KH10053 ProKIT	
				 ; 01/99 ->	KH10056 ProKIT	
<b>CITROËN - SPACETOURER Bus (V_)</b>				<b>04/16→</b>		
1.6 BlueHDi 115	85 kW	1.6 l	04/16→		KH10119 ProKIT	
1.6 BlueHDi 95	70 kW	1.6 l	04/16→			
2.0 BlueHDi 120	90 kW	2 l	12/19→			
2.0 BlueHDi 150	110 kW	2 l	04/16→			
2.0 BlueHDi 180	130 kW	2 l	04/16→			
<b>CITROËN - VISA / VISA Convertible</b>				<b>09/78→03/91</b>		
0.6	24 kW	0.6 l	07/82→03/91		KH00091 ProKIT	
0.6	25 kW	0.6 l	09/78→06/88		KH00094 ProKIT	
1.0	33 kW	1 l	09/84→06/88			
11 E	35 kW	1.1 l	09/78→06/88			
11 E	37 kW	1.1 l	07/82→03/91			
11 E	42 kW	1.1 l	09/78→03/91			
11 RE	37 kW	1.1 l	03/83→10/88			
14	44 kW	1.4 l	07/84→03/91			
14 GT	58 kW	1.4 l	03/82→03/91			
II Super X	47 kW	1.2 l	07/80→06/82			
<b>CITROËN - XANTIA / XANTIA Break (X1_, X2_)</b>				<b>03/93→04/03</b>		
1.6 i	65 kW	1.6 l	03/93→03/01		KH10052 ProKIT	
				 ; 07/93 -> 05/95; ABS	KH20092 ProKIT	
				 ; 08/93 -> 05/95; ABS	KH20046 ProKIT	
				 ; 06/95 ->; ABS	KH20015 ProKIT	
1.8 i	66 kW	1.8 l	04/97→04/03		KH10052 ProKIT	
1.8 i	74 kW	1.8 l	06/95→01/98			
1.8 i 16V	81 kW	1.8 l	06/95→04/03			
1.9 SD	55 kW	1.9 l	04/97→04/03			
1.9 Turbo D	66 kW	1.9 l	06/95→04/03			
2.0 i	89 kW	2 l	06/95→04/03			
2.0 i 16V	97 kW	2 l	06/95→04/03			
2.0 Turbo	108 kW	2 l	06/95→04/03			
2.1 Turbo D 12V	80 kW	2.1 l	06/96→02/99			
1.8 i	66 kW	1.8 l	04/97→04/03		KH10052 ProKIT	
1.8 i 16V	81 kW	1.8 l	06/95→12/01	 ; ABS	KH20015 ProKIT	
1.9 SD	55 kW	1.9 l	02/96→04/03			
2.0 i 16V	97 kW	2 l	06/95→04/03			
2.0 Turbo	108 kW	2 l	06/95→04/03			
2.1 Turbo D 12V	80 kW	2.1 l	06/95→02/99			
3.0 i 24V	140 kW	3 l	01/97→04/03			
1.8 i	74 kW	1.8 l	03/93→01/98		KH10052 ProKIT	
				 ; 07/93 -> 05/95; ABS	KH20092 ProKIT	
				 ; 06/95 ->; ABS	KH20015 ProKIT	
				 ; -> 05/95; ABS	KH20046 ProKIT	
1.9 D	50 kW	1.9 l	06/94→01/98		KH10052 ProKIT	
				 ; 07/94 -> 05/95; ABS	KH20046 ProKIT	
				 ; 06/95 ->; ABS	KH20015 ProKIT	
1.9 D	51 kW	1.9 l	06/94→01/98		KH10052 ProKIT	
1.9 Turbo D	66 kW	1.9 l	05/93→04/03	 ; 06/95 ->; ABS	KH20015 ProKIT	
2.0 i 16V	110 kW	2 l	06/94→01/98			
2.0 HDI 109	80 kW	2 l	02/99→04/03		KH10052 ProKIT	
				 ; 09/99 ->; ABS	KH20014 ProKIT	
				 ; -> 05/95; ABS	KH20092 ProKIT	
2.0 HDI 90	66 kW	2 l	03/99→04/03	 ; 05/93 -> 05/95; ABS	KH20092 ProKIT	
3.0 V6	140 kW	3 l	01/98→04/03		 ; 06/95 ->; ABS	KH20015 ProKIT
2.0 i	89 kW	2 l	03/93→04/03		 ; -> 05/95; ABS	KH20046 ProKIT











































































										
<b>CITROËN - XANTIA / XANTIA Break (X1_, X2_) 03/93→04/03</b>										
2.0 i 16V	112 kW	2 l	03/93→01/98							KH10052 ProKIT
					05/93 ->	05/95;	ABS			KH20092 ProKIT
					06/95 ->		ABS			KH20015 ProKIT
					->	12/94;	ABS			KH20046 ProKIT
<b>CITROËN - XM (Y3) 05/89→06/94</b>										
2.0 i	79 kW	2 l	05/89→04/94							KH10192 ProKIT
2.1 D 12V	60 kW	2.1 l	05/89→06/94							
3.0 V6	123 kW	3 l	05/89→06/94							
2.0 i	89 kW	2 l	05/89→06/94							KH10192 ProKIT
					10/89 ->					KH20076 ProKIT
2.0 i Turbo	104 kW	2 l	09/92→06/94							KH10192 ProKIT
					01/93 ->	03/94				KH20076 ProKIT
2.1 TD 12V	80 kW	2.1 l	05/89→06/94							KH10192 ProKIT
					03/90 ->	03/94				KH20076 ProKIT
3.0 V6 24V	147 kW	3 l	07/90→06/94							KH10192 ProKIT
					->	06/93				KH20076 ProKIT
<b>CITROËN - XM (Y4) 05/94→10/00</b>										
2.0 i 16V	97 kW	2 l	05/94→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
2.0 Turbo	108 kW	2 l	05/94→10/00		->	04/97;	VIN ->	7477		KH10192 ProKIT
2.1 TD 12V	80 kW	2.1 l	05/94→10/00		07/94 ->					KH20076 ProKIT
2.5 TD	95 kW	2.5 l	05/94→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
3.0 V6	123 kW	3 l	05/94→10/00		->	04/97;	VIN ->	7477		KH10192 ProKIT
					07/94 ->	04/97				KH20076 ProKIT
3.0 V6	140 kW	3 l	04/97→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
					->	04/97;	VIN ->	7477		KH10192 ProKIT
										KH20076 ProKIT
3.0 V6 24V	147 kW	3 l	05/94→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
					->	04/97;	VIN ->	7477		KH10192 ProKIT
<b>CITROËN - XM Break (Y3, Y4) 11/91→10/00</b>										
2.0 i	89 kW	2 l	11/91→04/94							KH10192 ProKIT
										KH20076 ProKIT
2.0 i (Y3A)	79 kW	2 l	11/91→04/94							KH10192 ProKIT
2.1 D12	60 kW	2.1 l	07/94→06/96							
2.1 D 12V	60 kW	2.1 l	11/91→04/94							
3.0 V6	123 kW	3 l	11/91→04/94							
2.0 i 16V	97 kW	2 l	05/94→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
2.0 Turbo	108 kW	2 l	05/94→10/00		->	04/97;	VIN ->	7477		KH10192 ProKIT
2.5 TD	95 kW	2.5 l	05/94→10/00		07/94 ->					KH20076 ProKIT
2.0 Turbo	104 kW	2 l	09/92→04/94							KH10192 ProKIT
					01/93 ->	03/94				KH20076 ProKIT
2.1 TD 12V	80 kW	2.1 l	11/91→04/94							KH10192 ProKIT
					->	03/94				KH20076 ProKIT
2.1 TD 12V	80 kW	2.1 l	05/94→10/00		04/97 ->	VIN 7478 ->				KH10165 ProKIT
					->	03/97;	VIN ->	7477		KH10192 ProKIT
					07/94 ->					KH20076 ProKIT
3.0 V6	123 kW	3 l	05/94→10/00		04/97 ->	VIN 7478 ->				KH10165 ProKIT
					->	03/97;	VIN ->	7477		KH10192 ProKIT
					07/94 ->	04/97				KH20076 ProKIT
3.0 V6	140 kW	3 l	04/97→10/00		05/97 ->	VIN 7478 ->				KH10165 ProKIT
					->	04/97;	VIN ->	7477		KH10192 ProKIT
										KH20076 ProKIT
<b>CITROËN - XSARA / XSARA Break (N1, N2) 04/97→08/05</b>										
1.4 HDi	50 kW	1.4 l	01/03→03/05		ABS					KH10052 ProKIT
					ESP					KH20035 ProKIT
					ESP					KH20121 ProKIT
1.4 HDi	50 kW	1.4 l	01/03→08/05		ESP					KH20035 ProKIT
1.6 16V	80 kW	1.6 l	09/00→08/05		ESP					KH20121 ProKIT
2.0 HDi 109	80 kW	2 l	05/01→08/05		ESP					KH20121 ProKIT












CITROËN - XSARA / XSARA Break (N1, N2)				04/97→08/05	
1.4 i	55 kW	1.4 l	04/97→03/05	04/98 ->	KH20035 ProKIT
1.5 D	42 kW	1.5 l	04/97→09/00	09/98 ->	KH10056 ProKIT
1.6 i	65 kW	1.6 l	04/97→09/00	-> 09/98;	KH10083 ProKIT
1.4 i	55 kW	1.4 l	10/97→08/05	-> 09/98;	KH20048 ProKIT
1.6 i	65 kW	1.6 l	10/97→09/00	-> 01/00; Code: ENTERPRISE;	
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.4 LPG	55 kW	1.4 l	05/98→08/00	09/98 ->	KH10056 ProKIT
				-> 09/98;	KH10083 ProKIT
					KH20035 ProKIT
1.5 D	42 kW	1.5 l	10/97→09/00	-> 09/98;	KH20048 ProKIT
				-> 01/00; Code: ENTERPRISE;	
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.6 16V	80 kW	1.6 l	09/00→03/05		KH10056 ProKIT
					KH20035 ProKIT
1.8 BiFuel	82 kW	1.8 l	07/97→08/00	04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				-> 09/98;	KH10083 ProKIT
1.8 D	43 kW	1.8 l	04/97→09/00	04/98 ->	KH20035 ProKIT
1.8 i	66 kW	1.8 l	04/97→09/00	09/98 ->	KH10056 ProKIT
1.9 D	50 kW	1.9 l	04/97→09/00	09/98 ->	KH20121 ProKIT
1.9 SD	55 kW	1.9 l	01/98→09/00	-> 09/98;	KH10083 ProKIT
1.9 TD	66 kW	1.9 l	04/97→09/00	-> 09/98;	KH20048 ProKIT
1.8 D	43 kW	1.8 l	10/97→09/00	-> 09/98;	
1.8 i	66 kW	1.8 l	10/97→09/00	-> 01/00; Code: ENTERPRISE;	
1.9 D	50 kW	1.9 l	10/97→09/00	04/98 ->	KH20035 ProKIT
1.9 D	55 kW	1.9 l	01/98→09/00	09/98 ->	KH10056 ProKIT
1.9 TD	66 kW	1.9 l	10/97→09/00	-> 09/98;	KH10083 ProKIT
1.8 i 16V	81 kW	1.8 l	04/97→09/00	11/97 -> 04/99;	KH20171 ProKIT
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.8 i 16V	81 kW	1.8 l	10/97→09/00	-> 09/98;	KH20048 ProKIT
				-> 01/00; Code: ENTERPRISE;	
				11/97 -> 04/99;	KH20171 ProKIT
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.8 i Aut.	74 kW	1.8 l	04/97→09/00	11/97 -> 04/99	KH20171 ProKIT
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.8 i Aut.	74 kW	1.8 l	10/97→09/00	-> 09/98;	KH20048 ProKIT
				-> 01/00; Code: ENTERPRISE;	
				04/98 -> 04/99	KH20171 ProKIT
				04/98 ->	KH20035 ProKIT
				09/98 ->	KH10056 ProKIT
				09/98 ->	KH20121 ProKIT
				-> 09/98;	KH10083 ProKIT
1.8 LPG	81 kW	1.8 l	05/98→08/00	09/98 ->	KH10056 ProKIT
				-> 09/98;	KH10083 ProKIT
					KH20035 ProKIT
1.8 VTS	85 kW	1.8 l	08/98→10/04		KH20035 ProKIT
1.9 D	52 kW	1.9 l	04/00→04/05		KH20035 ProKIT

















CITROËN - XSARA / XSARA Break (N1, N2)				04/97→08/05					
1.9 D	51 kW	1.9 l	07/98→03/05	; 09/98 ->; ;	KH20121 ProKIT				
				; -> 09/98; ;	KH10083 ProKIT				
				;	KH10056 ProKIT				
				;	KH20035 ProKIT				
1.9 D	51 kW	1.9 l	07/98→08/05	; -> 09/98;	KH20048 ProKIT				
				; -> 01/00; Code: ENTERPRISE;					
				; 09/98 ->; ;	KH20121 ProKIT				
				; -> 09/98; ;	KH10083 ProKIT				
2.0 16V	97 kW	2 l	07/98→09/00	; -> 09/98;  RFV (XU10J4R);	KH20048 ProKIT				
				; -> 01/00;  RFV (XU10J4R); Code: ENTERPRISE;					
				; 09/98 ->;	KH10056 ProKIT				
				; 09/98 ->;  RFV (XU10J4R); ;	KH20121 ProKIT				
2.0 16V	97 kW	2 l	07/98→09/00	; -> 09/98; ;	KH10083 ProKIT				
				;	KH20035 ProKIT				
				; 09/98 ->;	KH10056 ProKIT				
				; 09/98 ->; ;	KH20121 ProKIT				
2.0 16V	100 kW	2 l	09/00→03/05	;	KH20035 ProKIT				
				2.0 16V	100 kW	2 l	09/00→08/05	RFN (EW10J4); ;	KH20121 ProKIT
2.0 HDi 109	80 kW	2 l	05/01→03/05						KH10056 ProKIT
				2.0 HDi 90	66 kW	2 l	02/99→03/05	;	KH20035 ProKIT
								2.0 HDi 90	66 kW
CITROËN - XSARA Coupe (N0)				01/98→03/05					
1.4 HDi	50 kW	1.4 l	01/03→03/05		KH10052 ProKIT				
				; ;	KH20121 ProKIT				
1.4 i	55 kW	1.4 l	03/98→03/05		KH10052 ProKIT				
				OE 335016;					
				; -> 01/99	KH10051 ProKIT				
					KH10053 ProKIT				
				; 09/98 ->	KH10056 ProKIT				
1.6 16V	80 kW	1.6 l	09/00→03/05	;	KH10083 ProKIT				
				OE 3350 16;					
					KH10052 ProKIT				
1.6 i	65 kW	1.6 l	02/98→09/00	; -> 01/99	KH10051 ProKIT				
				OE 335016; ;	KH10052 ProKIT				
					KH10053 ProKIT				
				; 09/98 ->	KH10056 ProKIT				
				; -> 09/98; ;	KH10083 ProKIT				
1.8 i	66 kW	1.8 l	02/98→09/00		KH10052 ProKIT				
				; 09/98 ->;	KH10056 ProKIT				
1.9 D	50 kW	1.9 l	02/98→09/00	; 09/98 ->; ;	KH20121 ProKIT				
				; 09/98 ->; ;	KH10083 ProKIT				
1.8 i 16V	81 kW	1.8 l	02/98→09/00		KH10052 ProKIT				
				; 03/98 -> 04/99; ;	KH20171 ProKIT				
				; 09/98 ->;	KH10056 ProKIT				
				; 09/98 ->; ;	KH20121 ProKIT				
1.8 LPG	82 kW	1.8 l	01/98→08/00		KH10052 ProKIT				
				1.9 D	55 kW	1.9 l	02/98→05/99	; 09/98 ->;	KH10056 ProKIT
; -> 09/98; ;	KH10083 ProKIT								
1.9 D	51 kW	1.9 l	02/99→03/05		KH10052 ProKIT				
				2.0 HDi 109	80 kW	2 l	05/01→03/05		KH10056 ProKIT
2.0 HDi 90	66 kW	2 l	02/99→03/05					;	KH20121 ProKIT
				2.0 16V	100 kW	2 l	09/00→03/05		KH10052 ProKIT
RFN (EW10J4); ;	KH20121 ProKIT								









				     	
<b>CITROËN - XSARA Estate Van</b>				<b>09/00→03/05</b>	
2.0 HDi	66 kW	2 l	09/00→03/05		KH10052 ProKIT
				 	KH10056 ProKIT
<b>CITROËN - XSARA PICASSO (N68)</b>				<b>12/99→06/12</b>	
1.6	65 kW	1.6 l	12/99→09/01		KH10052 ProKIT
1.6 Chrono	74 kW	1.6 l	04/01→10/04	 <b>OE 335016;</b> 	
				  <b>48;</b> 	KH20013 ProKIT
					KH20014 ProKIT
				   <b>29</b>	KH20108 ProKIT
1.6	67 kW	1.6 l	06/02→08/05		KH10052 ProKIT
				 <b>OE 335016;</b> 	
				 <b>11/04 -&gt;;</b> 	KH20016 ProKIT
				 <b>-&gt; 10/04;</b>  <b>48;</b> 	KH20013 ProKIT
				 <b>-&gt; 10/04;</b>   <b>29</b>	KH20108 ProKIT
					KH20014 ProKIT
1.6	70 kW	1.6 l	12/99→12/10		KH10052 ProKIT
					
				 <b>11/04 -&gt;;</b> 	KH20016 ProKIT
				 <b>-&gt; 10/04;</b>  <b>48;</b> 	KH20013 ProKIT
				 <b>-&gt; 10/04;</b>   <b>29</b>	KH20108 ProKIT
					KH20014 ProKIT
1.6 16V	80 kW	1.6 l	09/05→12/11		KH10052 ProKIT
1.6 16V	81 kW	1.6 l	06/05→09/06	 <b>OE 335016;</b> 	
					KH20014 ProKIT
1.6 HDi	66 kW	1.6 l	09/05→12/11		KH10052 ProKIT
					KH20014 ProKIT
					KH20016 ProKIT
1.6 HDi	80 kW	1.6 l	05/04→12/11		KH10052 ProKIT
1.8 16V	85 kW	1.8 l	02/00→08/05	 <b>11/04 -&gt;;</b> 	KH20016 ProKIT
1.8 SX	76 kW	1.8 l	06/00→08/05		
2.0 16V	100 kW	2 l	01/03→06/12	 <b>-&gt; 10/04;</b>  <b>48;</b> 	KH20013 ProKIT
2.0 HDi	66 kW	2 l	12/99→12/11	 <b>-&gt; 10/04;</b>   <b>29</b>	KH20108 ProKIT
					KH20014 ProKIT
2.0 16V	101 kW	2 l	12/99→11/11	 <b>11/04 -&gt;;</b> 	KH20016 ProKIT
					KH20013 ProKIT
<b>CITROËN - ZX (N2)</b>				<b>03/91→07/99</b>	
1.1	40 kW	1.1 l	03/91→08/93		KH10051 ProKIT
1.1	44 kW	1.1 l	03/91→06/97		KH10052 ProKIT
1.4	55 kW	1.4 l	03/91→06/97	 	KH10083 ProKIT
1.4 i	55 kW	1.4 l	03/91→06/97		
1.4 D	37 kW	1.4 l	07/94→10/97		KH10051 ProKIT
				 	KH10083 ProKIT
1.6	66 kW	1.6 l	07/94→10/97		KH10052 ProKIT
1.6 i	65 kW	1.6 l	03/91→06/97	 	KH10083 ProKIT
1.8	76 kW	1.8 l	03/91→10/97		
1.8	82 kW	1.8 l	04/96→10/97		
1.8 D	44 kW	1.8 l	06/93→06/97		
1.8 i	74 kW	1.8 l	07/92→06/97		
1.8 i 16V	81 kW	1.8 l	01/96→06/97		
1.9	96 kW	1.9 l	03/91→09/93		
1.9 D	47 kW	1.9 l	03/91→06/97		
1.9 D	50 kW	1.9 l	07/93→06/97		
1.9 DT	65 kW	1.9 l	07/94→10/97		
1.9 DT	68 kW	1.9 l	06/92→06/94		
1.9 i	88 kW	1.9 l	03/91→06/97		
1.9 TD	66 kW	1.9 l	07/92→06/97		
2.0	90 kW	2 l	07/94→10/97		
2.0	122 kW	2 l	09/96→10/97		
2.0 i	89 kW	2 l	07/92→06/97		
2.0 i 16V	110 kW	2 l	06/94→06/97		
2.0 i 16V	112 kW	2 l	07/92→10/94		
2.0 i 16V	120 kW	2 l	05/96→06/97		
1.9	93 kW	1.9 l	03/91→06/97	 	KH10083 ProKIT
1.9 D	52 kW	1.9 l	10/93→07/99		
2.0 i 16V	114 kW	2 l	07/92→10/97		

     				10/93→02/98	
CITROËN - ZX Break (N2)					
1.4 i	55 kW	1.4 l	10/93→10/97		<b>KH10051</b> ProKIT
				 ABS	<b>KH10052</b> ProKIT
				 ABS	<b>KH20048</b> ProKIT
1.6 i	65 kW	1.6 l	10/93→10/97		<b>KH10052</b> ProKIT
1.8 D	44 kW	1.8 l	10/93→10/97	 ABS	<b>KH20048</b> ProKIT
1.8 i	74 kW	1.8 l	10/93→10/97		
1.8 i 16V	81 kW	1.8 l	01/96→02/98		
1.9 D	47 kW	1.9 l	10/93→10/97		
1.9 D	50 kW	1.9 l	06/94→10/97		
1.9 TD	66 kW	1.9 l	10/93→10/97		









    					
<b>CUPRA - ATECA (KH7, KHP)</b>					<b>09/18→</b>
2.0 TSI 4Drive	221 kW	2 l	09/18→		<b>KH30014</b> ProKIT
2.0 TSI 4Drive	257 kW	2 l	05/20→		<b>KH30049</b> ProKIT
<b>CUPRA - FORMENTOR (KM7)</b>					<b>07/20→</b>
1.5 TSI	110 kW	1.5 l	11/20→		<b>KH30049</b> ProKIT
2.0 TSI 4Drive	228 kW	2 l	07/20→	 	<b>KH30049</b> ProKIT
<b>CUPRA - LEON (KL1)</b>					<b>09/20→</b>
VZ 1.4 e-HYBRID	180 kW	1.4 l	09/20→		<b>KH20003</b> ProKIT
<b>CUPRA - LEON Sportstourer (KL8)</b>					<b>09/20→</b>
VZ 1.4 e-HYBRID	180 kW	1.4 l	09/20→	 : Centering Diameter [mm]: 80	<b>KH30048</b> ProKIT
				 : Centering Diameter [mm]: 85	<b>KH30049</b> ProKIT
					<b>KH20003</b> ProKIT

     					
<b>DACIA - 1300</b>					<b>12/72→05/83</b>
1.3	40 kW	1.3 l	12/72→05/83	; 01/77 →	KH00032 ProKIT
<b>DACIA - 1310 Saloon (U, X)</b>					<b>05/83→07/04</b>
1.3	40 kW	1.3 l	05/83→07/04		KH00032 ProKIT
<b>DACIA - DOKKER Express Box Body/MPV / DOKKER MPV (KE_)</b>					<b>11/12→</b>
1.2 TCe (KEM0, KEAY)	85 kW	1.2 l	11/12→		KH10184 ProKIT
1.2 TCe 115 (FEM0)	84 kW	1.2 l	12/12→		
1.5 dCi / Blue dCi 75 (KEAJ, KEAH, KEJW)	55 kW	1.5 l	11/12→		KH10142 ProKIT
1.5 dCi (FEAJ)	66 kW	1.5 l	12/12→		
1.5 dCi (KEAJ, KEAH)	66 kW	1.5 l	11/12→		
1.5 dCi 75 / Blue dCi 75 (FEJW, FEAH)	55 kW	1.5 l	12/12→		
1.6	61 kW	1.6 l	11/12→		
1.6	61 kW	1.6 l	12/12→		
1.2 TCe 115 (FEAY)	85 kW	1.2 l	07/15→		KH10184 ProKIT
1.6	75 kW	1.6 l	04/15→		
1.6 LPG	61 kW	1.6 l	11/13→		
1.6 LPG	75 kW	1.6 l	04/15→		
<b>DACIA - DUSTER / DUSTER SUV Van (HM_, HS_)</b>					<b>04/10→01/18</b>
1.2 TCe 125	92 kW	1.2 l	10/13→01/18		KH10080 ProKIT
1.5 dCi	80 kW	1.5 l	08/13→01/18		KH10142 ProKIT
1.2 TCe 125 (HMMA)	92 kW	1.2 l	10/17→		KH10080 ProKIT
1.2 TCe 125 4x4	92 kW	1.2 l	06/15→01/18		
1.2 TCe 125 4x4 (HMMA)	92 kW	1.2 l	10/17→		
1.2 TCe 125 4x4 (HSAU)	92 kW	1.2 l	10/13→		
1.5 dCi	66 kW	1.5 l	04/11→		
1.5 dCi	80 kW	1.5 l	04/13→		
1.5 dCi	81 kW	1.5 l	08/13→01/18		
1.5 dCi 110 (HMAB)	80 kW	1.5 l	10/17→		
1.5 dCi 110 4x4 (HMAB)	80 kW	1.5 l	10/17→		
1.5 dCi 4x4	66 kW	1.5 l	04/11→		
1.5 dCi 4x4	80 kW	1.5 l	04/13→		
1.5 dCi 90 (HMAA)	66 kW	1.5 l	10/17→		
1.6 16V 4x4	77 kW	1.6 l	04/11→		
1.6 16V Hi-Flex	77 kW	1.6 l	04/11→		
1.6 16V LPG	77 kW	1.6 l	04/11→01/18		
1.6 SCe 115	84 kW	1.6 l	06/15→		
1.6 SCe 115	84 kW	1.6 l	06/15→01/18		
1.6 SCe 115 (HMM1)	84 kW	1.6 l	10/17→		
1.6 SCe 115 4x4	84 kW	1.6 l	06/15→01/18		
1.6 SCe 115 4x4 (HMM1)	84 kW	1.6 l	10/17→		
1.6 SCe 115 LPG	84 kW	1.6 l	06/15→01/18		
1.6 SCe 115 LPG (HMM1)	80 kW	1.6 l	10/17→		
1.5 dCi	63 kW	1.5 l	04/10→01/18		KH10080 ProKIT
1.5 dCi (HSMC)	79 kW	1.5 l	06/10→01/18		KH10177 ProKIT
1.6 16V Hi-Flex	77 kW	1.6 l	08/10→01/18		
1.5 dCi (HSAJ)	66 kW	1.5 l	10/10→01/18		KH10080 ProKIT
1.6 16V	77 kW	1.6 l	04/10→01/18	; 12/10 →	KH10142 ProKIT
				; → 11/10	KH10177 ProKIT
1.5 dCi 4x4	66 kW	1.5 l	10/10→01/18		KH10080 ProKIT
1.5 dCi 4x4	80 kW	1.5 l	08/13→01/18		
1.5 dCi 4x4 (HSMC, HSMD)	81 kW	1.5 l	10/10→01/18		KH10214 ProKIT
1.6 16V 4x4	77 kW	1.6 l	06/10→01/18		
<b>DACIA - LODGY (JS_)</b>					<b>03/12→</b>
1.2 TCe (JSAY, JSM0)	85 kW	1.2 l	03/12→		KH10184 ProKIT
1.5 dCi	80 kW	1.5 l	06/15→		
1.6 LPG	61 kW	1.6 l	11/13→		
1.6 LPG	75 kW	1.6 l	04/15→		
1.6 SCe 100	75 kW	1.6 l	06/15→		
1.5 dCi	66 kW	1.5 l	03/12→		KH10184 ProKIT
1.5 dCi	79 kW	1.5 l	01/13→		KH10142 ProKIT
1.6	61 kW	1.6 l	03/12→		
<b>DACIA - LOGAN (LS_)</b>					<b>09/04→12/12</b>
1.0 Hi-Flex (LS0R, LS1G)	56 kW	1 l	01/11→10/12	; ABS	KH10058 ProKIT
					KH10073 ProKIT
					KH10077 ProKIT

























































				13		i		
<b>DACIA - LOGAN (LS_)</b>							<b>09/04→12/12</b>	
1.2 16V (LS1N, LS02, BS02)	55 kW	1.2 l	02/06→		ABS		KH10058 ProKIT	
1.2 16V LPG	55 kW	1.2 l	02/06→		ABS		KH10380 ProKIT	
1.6 16V Flexifuel	77 kW	1.6 l	07/10→				KH10073 ProKIT	
1.6 Bifuel	62 kW	1.6 l	05/10→				KH10077 ProKIT	
1.6 MPI 85	62 kW	1.6 l	05/10→				KH10077 ProKIT	
1.4 (LS0A, LS0C, LS0E, LS0G)	55 kW	1.4 l	09/04→		06/08 ->; ABS		KH10380 ProKIT	
					-> 03/08; Code: LS0A, LS0C, LS0E, LS0G; ABS		KH10199 ProKIT	
					ABS		KH10058 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
1.4 MPI LPG (LS0C)	55 kW	1.4 l	02/06→12/12		06/08 ->; ABS		KH10380 ProKIT	
					ABS		KH10058 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
1.5 dCi (LS04)	55 kW	1.5 l	05/10→12/12		-> 04/11; Code: LS00, LS0J, LS0K, LS0Y; ABS		KH10199 ProKIT	
1.5 dCi (LS04)	65 kW	1.5 l	05/10→		ABS		KH10058 ProKIT	
					ABS		KH10380 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
1.5 dCi (LS0J, LS0Y)	48 kW	1.5 l	09/05→		06/08 ->; ABS		KH10380 ProKIT	
1.5 dCi (LS0K)	50 kW	1.5 l	01/06→12/12		-> 03/08; Code: LS00, LS0J, LS0K, LS0Y; ABS		KH10199 ProKIT	
1.5 dCi (LS0W)	63 kW	1.5 l	09/07→12/11		ABS		KH10058 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
1.6 (LS0B, LS0D, LS0F, LS0H)	64 kW	1.6 l	09/04→		06/08 ->; ABS		KH10380 ProKIT	
					-> 03/08; Code: LS0B, LS0D, LS0F, LS0H; ABS		KH10199 ProKIT	
					ABS		KH10058 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
1.6 16V (LS09, LS0L, LS0M, LS0P, LS0V, LS18, LS1S, LS1V,...)	77 kW	1.6 l	02/06→		06/08 ->; ABS		KH10380 ProKIT	
					-> 03/08; Code: LS0L, LS0M, LS0P, LS0V; ABS		KH10199 ProKIT	
					ABS		KH10058 ProKIT	
							KH10073 ProKIT	
							KH10077 ProKIT	
<b>DACIA - LOGAN II</b>							<b>10/12→</b>	
1.0 SCe 75	54 kW	1 l	01/17→		ABS		KH10058 ProKIT	
1.6	59 kW	1.6 l	09/16→				KH10077 ProKIT	
TCe 90 LPG	66 kW	0.9 l	09/15→				KH10077 ProKIT	
1.2	54 kW	1.2 l	05/15→		-> 04/17; ABS		KH10380 ProKIT	
1.2	55 kW	1.2 l	10/12→		ABS		KH10058 ProKIT	
1.2 LPG	55 kW	1.2 l	10/12→				KH10077 ProKIT	
1.5 dCi	63 kW	1.5 l	01/13→				KH10077 ProKIT	
1.5 dCi	66 kW	1.5 l	10/12→					
1.5 dCi / Blue dCi 75	55 kW	1.5 l	10/12→					
1.6 16V	77 kW	1.6 l	01/13→					
TCe 90	66 kW	0.9 l	10/12→					
1.2 LPG	53 kW	1.2 l	02/13→		-> 04/17; ABS		KH10380 ProKIT	
<b>DACIA - LOGAN EXPRESS / LOGAN MCV (FS_, KS_)</b>							<b>02/07→06/13</b>	
1.4	55 kW	1.4 l	02/07→		04/07 ->; ABS		KH10380 ProKIT	
					-> 03/08; Code: FS0A, FS0E, KS0A, KS0E;		KH10199 ProKIT	
					Body Type: Estate; ABS			
					ABS		KH10058 ProKIT	
							KH10177 ProKIT	
1.4	55 kW	1.4 l	03/09→		ABS		KH10058 ProKIT	
1.5 dCi	55 kW	1.5 l	05/10→		ABS		KH10380 ProKIT	
1.5 dCi	65 kW	1.5 l	05/10→					
1.5 dCi (FS0K)	50 kW	1.5 l	03/09→					
1.5 dCi (FS0W)	63 kW	1.5 l	03/09→					
1.6	64 kW	1.6 l	03/09→					
1.6 16V Hi-Flex	77 kW	1.6 l	11/09→					
1.6 Bifuel	62 kW	1.6 l	05/10→					
1.6 MPI 85	62 kW	1.6 l	05/10→					
1.5 dCi	48 kW	1.5 l	04/08→06/13		ABS		KH10380 ProKIT	

     					
DACIA - LOGAN EXPRESS / LOGAN MCV (FS_, KS_)				02/07→06/13	
1.5 dCi (KS04)	55 kW	1.5 l	05/10→06/13	; -> 04/11; Code: FS0J, FS0K, KS0J, KS0K;	KH10199 ProKIT
1.5 dCi (KS04)	65 kW	1.5 l	05/10→	; ; Body Type: Estate;	KH10058 ProKIT
				;	KH10380 ProKIT
1.5 dCi (KS0K)	50 kW	1.5 l	02/07→	; 04/07 ->;	KH10380 ProKIT
				; -> 03/08; Code: FS0J, FS0K, KS0J, KS0K;	KH10199 ProKIT
				; ; Body Type: Estate;	KH10058 ProKIT
					KH10177 ProKIT
1.5 dCi (KS0W)	63 kW	1.5 l	09/07→12/12	; -> 03/08; Code: FS0J, FS0K, KS0J, KS0K;	KH10199 ProKIT
				; ; Body Type: Estate;	KH10058 ProKIT
				;	KH10380 ProKIT
1.6 (KS0B, KS0D, KS0F)	64 kW	1.6 l	02/07→06/13	; 04/07 ->;	KH10380 ProKIT
				; -> 03/08; Code: FS0B, FS0F, KS0B, KS0F;	KH10199 ProKIT
				; ; Body Type: Estate;	KH10058 ProKIT
					KH10177 ProKIT
1.6 16V (KS0L, KS0M, KS0P, KS1S)	77 kW	1.6 l	02/07→	; 04/07 ->;	KH10380 ProKIT
				; -> 03/08; Code: KS0M, KS0P; Body Type: Estate;	KH10199 ProKIT
					KH10058 ProKIT
				;	KH10177 ProKIT
1.6 Bifuel	64 kW	1.6 l	11/08→	; -> 04/11; Code: KS0M, KS0P; Body Type: Estate;	KH10199 ProKIT
					KH10058 ProKIT
				;	KH10380 ProKIT
				;	KH10380 ProKIT
DACIA - LOGAN MCV II / LOGAN Pickup (US_)				03/08→	
1.0 SCe 75	54 kW	1 l	12/16→	;	KH10058 ProKIT
1.4	55 kW	1.4 l	01/09→		
1.6	62 kW	1.6 l	06/13→		
1.6 16V (US1Y)	77 kW	1.6 l	01/10→08/13		
1.2	54 kW	1.2 l	05/15→	; -> 04/17;	KH10380 ProKIT
1.2	55 kW	1.2 l	02/13→	;	KH10058 ProKIT
1.2 LPG	55 kW	1.2 l	02/13→		
1.5 dCi	55 kW	1.5 l	02/13→		
1.5 dCi	60 kW	1.5 l	09/16→		
1.5 dCi	63 kW	1.5 l	02/13→		
1.5 dCi	66 kW	1.5 l	02/13→		
TCe 90 (K8M1)	66 kW	0.9 l	02/13→		
TCe 90 LPG	66 kW	0.9 l	09/15→		
1.2 LPG	53 kW	1.2 l	02/13→	; -> 04/17;	KH10380 ProKIT
1.5 dCi	55 kW	1.5 l	05/10→	;	KH10058 ProKIT
1.5 dCi	65 kW	1.5 l	05/10→	;	KH10380 ProKIT
1.5 dCi (US00, US0J, US0Y)	48 kW	1.5 l	04/08→12/12	;	
1.5 dCi (US0K)	50 kW	1.5 l	03/08→		
1.5 dCi (US0W)	63 kW	1.5 l	03/08→		
1.6	64 kW	1.6 l	03/08→		
1.6 Bifuel	62 kW	1.6 l	05/10→		
1.6 MPI 85	62 kW	1.6 l	05/10→		
DACIA - NOVA				04/96→03/03	
1.4	48 kW	1.4 l	04/96→03/01		KH10075 ProKIT
1.6	53 kW	1.6 l	04/96→03/03		
DACIA - SANDERO				06/08→12/12	
1.0 Hi-Flex	56 kW	1 l	01/11→12/12	;	KH10058 ProKIT
1.6 Hi-Flex (BS1H)	64 kW	1.6 l	06/08→12/12		KH10073 ProKIT
					KH10077 ProKIT
1.2 16V	55 kW	1.2 l	11/08→	;	KH10058 ProKIT
1.4 (BS0C, BS0A, BS0G, BS1F, BS0E)	55 kW	1.4 l	06/08→	;	KH10380 ProKIT
1.4 MPI LPG	53 kW	1.4 l	01/09→		KH10073 ProKIT
1.5 dCi	48 kW	1.5 l	11/08→		KH10077 ProKIT
1.5 dCi	50 kW	1.5 l	11/08→		
1.5 dCi	55 kW	1.5 l	05/10→		
1.5 dCi	63 kW	1.5 l	11/08→		
1.5 dCi	65 kW	1.5 l	05/10→		
1.6 (BS0D, BS0B, BS0F, BS0H)	64 kW	1.6 l	06/08→		

















<b>DACIA - SANDERO</b>				<b>06/08→12/12</b>	
1.6 16V	77 kW	1.6 l	07/11→	; ABS	<b>KH10058</b> ProKIT
1.6 16V Bifuel	77 kW	1.6 l	01/11→	; ABS	<b>KH10380</b> ProKIT
1.6 LPG	62 kW	1.6 l	05/10→10/12	; ABS	<b>KH10073</b> ProKIT
1.6 LPG (BS03)	60 kW	1.6 l	01/11→12/12		<b>KH10073</b> ProKIT
1.6 MPI 85 (BS03)	62 kW	1.6 l	05/10→06/13		<b>KH10077</b> ProKIT
1.2 16V LPG	55 kW	1.2 l	11/08→		<b>KH10058</b> ProKIT
				; ABS	<b>KH10380</b> ProKIT
					<b>KH10073</b> ProKIT
					<b>KH10077</b> ProKIT
1.6 LPG	64 kW	1.6 l	06/08→12/12	; ABS	<b>KH10380</b> ProKIT
<b>DACIA - SANDERO II</b>				<b>10/12→</b>	
1.0 SCe 75 (B8JC, B8JD)	54 kW	1 l	12/16→	; ABS	<b>KH10058</b> ProKIT
1.2	54 kW	1.2 l	05/15→	; → 04/17; ABS	<b>KH10380</b> ProKIT
1.2	55 kW	1.2 l	10/12→	; ABS	<b>KH10058</b> ProKIT
1.2 LPG	55 kW	1.2 l	10/12→		
1.5 dCi	63 kW	1.5 l	01/13→		
1.5 dCi	66 kW	1.5 l	10/12→		
1.5 dCi 75 / Blue dCi 75 (B8JW, B8M4, B8AH, B8M7, B8M6)	55 kW	1.5 l	10/12→		
1.6	59 kW	1.6 l	09/16→		
1.6	63 kW	1.6 l	11/12→		
TCe 90 (B8M1, B8MA)	66 kW	0.9 l	10/12→		
TCe 90 LPG (B8M1)	66 kW	0.9 l	09/15→		
<b>DACIA - SOLENZA (B41_)</b>				<b>02/03→</b>	
1.4 (B41A, B41B, B41C)	55 kW	1.4 l	02/03→10/05		<b>KH10075</b> ProKIT
1.9 D (B41E, B41F, B41G)	46 kW	1.9 l	02/03→		
<b>DACIA - SUPERNOVA</b>				<b>04/00→03/03</b>	
1.4	55 kW	1.4 l	04/00→03/03		<b>KH10075</b> ProKIT





































































										
<b>DAEWOO - CIELO / CIELO Saloon</b>										<b>02/95→08/97</b>
1.5 (08, 68)	55 kW	1.5 l	02/95→08/97		03/95 →					KH10107 ProKIT
1.5 (19)	55 kW	1.5 l	02/95→08/97							
1.5 16V (08, 68)	66 kW	1.5 l	02/95→08/97		03/95 →					KH10108 ProKIT
1.5 16V (19)	66 kW	1.5 l	02/95→08/97							
<b>DAEWOO - ESPERO Sedan (KLEJ)</b>										<b>02/95→09/99</b>
1.5 16V	66 kW	1.5 l	02/95→06/99		-> 05/99					KH10108 ProKIT
1.8	66 kW	1.8 l	02/95→09/99							
1.8	70 kW	1.8 l	02/95→06/99							
2.0	77 kW	2 l	02/95→06/99							
<b>DAEWOO - EVANDA (KLAL)</b>										<b>08/02→</b>
2.0	96 kW	2 l	08/02→		-> 12/06; ABS					KH30167 ProKIT
<b>DAEWOO - KALOS (KLAS)</b>										<b>09/02→</b>
1.2	53 kW	1.2 l	04/03→							KH10141 ProKIT
1.4	61 kW	1.4 l	09/02→							KH10213 ProKIT
1.4 16V	69 kW	1.4 l	04/03→							
<b>DAEWOO - KALOS Saloon (KLAS)</b>										<b>11/02→12/04</b>
1.4	61 kW	1.4 l	11/02→12/04							KH10213 ProKIT
1.4	69 kW	1.4 l	05/03→12/04							
<b>DAEWOO - LACETTI Hatchback (KLAN)</b>										<b>02/04→</b>
1.4	70 kW	1.4 l	02/04→		-> 12/04					KH10226 ProKIT
1.6	80 kW	1.6 l	02/04→							KH30187 ProKIT
1.8	90 kW	1.8 l	02/04→							
<b>DAEWOO - LANOS / LANOS Saloon (KLAT)</b>										<b>02/97→</b>
1.3	55 kW	1.3 l	05/97→							KH10141 ProKIT
1.5	63 kW	1.5 l	05/97→							
1.6 16V	78 kW	1.6 l	02/97→							KH10353 ProKIT
1.6 16V	78 kW	1.6 l	05/97→							
<b>DAEWOO - LEGANZA Sedan (KLAV)</b>										<b>06/97→04/04</b>
2.0 16V	93 kW	2 l	07/00→04/04		-> 01/03					KH10226 ProKIT
2.0 16V	98 kW	2 l	06/97→12/02		09/97 →					KH10226 ProKIT
2.2 16V	100 kW	2.2 l	04/99→12/02							KH10226 ProKIT
<b>DAEWOO - MATIZ (M100, M150)</b>										<b>09/98→</b>
0.8	38 kW	0.8 l	09/98→		-> 12/08					KH00014 ProKIT
1.0	47 kW	1 l	01/03→		-> 12/08					KH00028 ProKIT
<b>DAEWOO - NUBIRA / NUBIRA Estate / NUBIRA Saloon (J100, J150)</b>										<b>04/97→</b>
1.6	76 kW	1.6 l	08/02→07/03							KH10353 ProKIT
1.6 16V	78 kW	1.6 l	05/97→05/99							
1.6 16V	78 kW	1.6 l	06/99→07/02							
1.6 16V	78 kW	1.6 l	06/99→12/02							
1.8 16V	100 kW	1.8 l	04/97→05/99							
2.0	81 kW	2 l	06/99→07/03							
2.0 16V	93 kW	2 l	12/00→							
2.0 16V	98 kW	2 l	05/97→							
2.0 16V	98 kW	2 l	06/99→07/02							
2.0 CDX	93 kW	2 l	08/02→07/03							
1.6 16V	76 kW	1.6 l	07/00→		07/03 → 07/05					KH10226 ProKIT
										KH10353 ProKIT
<b>DAEWOO - NUBIRA Saloon (J200)</b>										<b>07/03→12/04</b>
1.4	69 kW	1.4 l	10/03→12/04							KH30187 ProKIT
1.6	80 kW	1.6 l	07/03→		-> 07/05					KH10226 ProKIT
1.8	90 kW	1.8 l	07/03→							KH30187 ProKIT
<b>DAEWOO - NUBIRA Wagon (J100)</b>										<b>05/97→</b>
1.6 16V	66 kW	1.6 l	06/97→							KH10353 ProKIT
1.6 16V	78 kW	1.6 l	05/97→05/99							
2.0 16V	93 kW	2 l	12/00→							
2.0 16V	98 kW	2 l	05/97→							
1.6 16V	76 kW	1.6 l	12/00→		10/04 → 07/05					KH10226 ProKIT
										KH10353 ProKIT
<b>DAEWOO - NUBIRA Wagon (J200)</b>										<b>07/03→</b>
1.6	80 kW	1.6 l	07/03→		10/04 → 07/05					KH10226 ProKIT

















     13 					
<b>DAEWOO - NUBIRA Wagon (J200)</b>				<b>07/03→</b>	
1.8	90 kW	1.8 l	07/03→	 ; 10/04 → 07/05	<b>KH10226</b> ProKIT
					<b>KH30187</b> ProKIT
<b>DAEWOO - TACUMA (U100)</b>				<b>09/00→12/04</b>	
1.8	72 kW	1.8 l	09/00→	 ; → 07/05	<b>KH10226</b> ProKIT
1.8	74 kW	1.8 l	09/00→	 ; → 07/05; 	<b>KH20128</b> ProKIT
2.0	94 kW	2 l	09/00→		
2.0	89 kW	2 l	09/01→12/04		<b>KH10226</b> ProKIT
				 	<b>KH20128</b> ProKIT



									
<b>DAIHATSU - APPLAUSE I Hatchback (A101, A111)</b>									
<b>06/89→07/97</b>									
1.6 16V (A101)	66 kW	1.6 l	06/89→07/97	 ; -> 02/97	KH10406 ProKIT				
					KH10225 ProKIT				
1.6 16V (A101)	77 kW	1.6 l	06/89→07/97		KH10406 ProKIT				
					KH10225 ProKIT				
1.6 16V 4WD (A111)	77 kW	1.6 l	06/89→07/97	 ; -> 04/94	KH10406 ProKIT				
					KH10225 ProKIT				
<b>DAIHATSU - APPLAUSE II Hatchback (A101)</b>									
<b>07/97→05/00</b>									
1.6 16V (A101)	73 kW	1.6 l	07/97→05/00	 ; 09/97 ->	KH10406 ProKIT				
					KH10225 ProKIT				
<b>DAIHATSU - CHARADE I (G10)</b>									
<b>10/77→02/83</b>									
1.0	37 kW	1 l	10/77→02/81	 ; 01/78 ->	KH00101 ProKIT				
1.0	38 kW	1 l	02/81→02/83		KH00101 ProKIT				
<b>DAIHATSU - CHARADE III (G100, G101, G102)</b>									
<b>03/87→01/93</b>									
1.0 (G100)	38 kW	1 l	03/87→12/92	 ; 01/89 ->	KH10406 ProKIT				
1.0 D (G101)	27 kW	1 l	03/87→12/92	 ; -> 01/89	KH10225 ProKIT				
1.0 GTi (G100)	74 kW	1 l	03/87→12/92						
1.0 TD (G101)	35 kW	1 l	03/87→12/92						
1.3 i (G102)	66 kW	1.3 l	06/88→12/92						
1.0 (G100)	40 kW	1 l	11/90→12/92		KH10406 ProKIT				
1.0 (G100)	41 kW	1 l	04/89→12/92						
1.0 Turbo (G100)	50 kW	1 l	03/87→10/90	 ; -> 01/89	KH10225 ProKIT				
1.3 i 4WD (G102)	66 kW	1.3 l	06/88→01/93	 ; 01/89 ->	KH10406 ProKIT				
				 ; -> 12/92	KH10225 ProKIT				
<b>DAIHATSU - CHARADE III Saloon (G102)</b>									
<b>11/90→02/93</b>									
1.3	66 kW	1.3 l	11/90→02/93	 ; -> 01/93	KH10406 ProKIT				
<b>DAIHATSU - CHARADE IV / CHARADE IV Saloon (G200, G202, G200, G203)</b>									
<b>01/93→09/00</b>									
1.3	44 kW	1.3 l	09/96→11/99	 ; 09/97 ->	KH10406 ProKIT				
1.3 16V	55 kW	1.3 l	05/96→11/99						
1.3 i 16V	62 kW	1.3 l	01/93→09/00	 ; 03/93 ->	KH10406 ProKIT				
1.5 i 16V	66 kW	1.5 l	06/94→11/99		KH10406 ProKIT				
1.5 i 16V	66 kW	1.5 l	01/97→11/99						
1.6 GTi	77 kW	1.6 l	03/93→11/99	 ; -> 05/96	KH10406 ProKIT				
<b>DAIHATSU - CHARADE CENTRO IV (L501)</b>									
<b>01/95→10/98</b>									
0.8	31 kW	0.8 l	11/96→10/98	 ; -> 02/98	KH00101 ProKIT				
0.8	32 kW	0.8 l	01/95→08/98		KH00101 ProKIT				
<b>DAIHATSU - COPEN (L880_, L881_)</b>									
<b>09/03→09/12</b>									
0.7 (L880)	50 kW	0.7 l	09/03→12/07		KH10225 ProKIT				
					KH00101 ProKIT				
1.3	64 kW	1.3 l	03/06→09/12	 ; -> 01/08	KH10225 ProKIT				
				 ; -> 01/08	KH00101 ProKIT				
<b>DAIHATSU - CUORE II (L80, L81)</b>									
<b>09/85→12/90</b>									
0.8 (L80)	29 kW	0.8 l	11/89→12/90	 ; -> 02/90	KH00101 ProKIT				
0.8 (L80)	32 kW	0.8 l	09/85→06/90						
<b>DAIHATSU - CUORE VII (L275_, L285_, L276_)</b>									
<b>04/07→</b>									
1.0	51 kW	1 l	04/07→	 ; -> 12/08	KH10225 ProKIT				
<b>DAIHATSU - EXTOL Bus (S22_, S23_)</b>									
<b>07/00→11/11</b>									
1.3	63 kW	1.3 l	07/00→11/11	 ; -> 11/04	KH10225 ProKIT				
<b>DAIHATSU - MIRA III (L200, L201)</b>									
<b>10/90→12/94</b>									
0.8	30 kW	0.8 l	10/90→12/94		KH00101 ProKIT				
<b>DAIHATSU - MIRA VI (L251, L250_, L260_)</b>									
<b>05/03→</b>									
1.0	43 kW	1 l	05/03→	 ; -> 11/06	KH10225 ProKIT				
<b>DAIHATSU - MOVE (L6_)</b>									
<b>01/97→11/99</b>									
0.8 (L601)	31 kW	0.8 l	01/97→11/99	 ; -> 09/98	KH00101 ProKIT				

											
<b>DAIHATSU - MOVE (L9_)</b>										<b>10/98→09/02</b>	
1.0 i	41 kW	1 l	10/98→09/02			KH10225 ProKIT					
						KH00101 ProKIT					
<b>DAIHATSU - PYZAR (G3)</b>										<b>10/96→07/98</b>	
1.5 16V (G303)	66 kW	1.5 l	10/96→07/98		-> 06/98	KH10406 ProKIT					
1.6 16V (G301)	67 kW	1.6 l	05/98→		06/98 ->	KH10406 ProKIT					
<b>DAIHATSU - SIRION (M1)</b>										<b>04/98→03/05</b>	
1.0 i (M100)	41 kW	1 l	04/98→09/00			KH10225 ProKIT					
						KH00101 ProKIT					
1.0 i (M100)	43 kW	1 l	09/00→01/05		-> 08/04	KH10225 ProKIT					
1.3 Sport	75 kW	1.3 l	08/00→01/05		-> 08/04	KH00101 ProKIT					
1.0 i 4WD	41 kW	1 l	04/99→09/00			KH10225 ProKIT					
1.0 i 4WD	43 kW	1 l	09/00→01/05		-> 08/04	KH10225 ProKIT					
1.3 Sport 4WD	75 kW	1.3 l	08/00→03/05			KH10225 ProKIT					
<b>DAIHATSU - SIRION (M3_)</b>										<b>01/05→</b>	
1.0	51 kW	1 l	01/05→06/13		-> 07/07	KH10225 ProKIT					
1.3 (M301)	64 kW	1.3 l	01/05→								
1.3 4WD	64 kW	1.3 l	04/05→								
1.3	67 kW	1.3 l	03/08→		-> 06/08	KH10225 ProKIT					
1.3 4WD	67 kW	1.3 l	03/08→								
1.5	76 kW	1.5 l	03/08→								
<b>DAIHATSU - TERIOS (J1_)</b>										<b>10/97→10/06</b>	
1.3	63 kW	1.3 l	07/00→10/06			KH10406 ProKIT					
1.3 4WD (J102)	63 kW	1.3 l	10/00→10/05								
1.3 4WD (J100)	61 kW	1.3 l	10/97→10/00		-> 05/00	KH10406 ProKIT					
<b>DAIHATSU - TERIOS (J2_)</b>										<b>11/05→</b>	
1.3 VVT-i 4x4	63 kW	1.3 l	11/05→		ABS	KH10232 ProKIT					
1.5 4x4	77 kW	1.5 l	05/06→		ABS	KH10390 ProKIT					
1.5 VVT-i 4x4	75 kW	1.5 l	09/10→								
1.5 VVT-i RWD	75 kW	1.5 l	09/10→			KH00108 ProKIT					
1.5 VVT-i RWD	77 kW	1.5 l	11/05→								
<b>DAIHATSU - TREVIS</b>										<b>06/06→</b>	
1.0	43 kW	1 l	06/06→		-> 03/09	KH10225 ProKIT					
<b>DAIHATSU - YRV (M2)</b>										<b>02/01→</b>	
1.0	43 kW	1 l	02/01→		-> 12/02	KH10225 ProKIT					
1.3 (M201)	64 kW	1.3 l	02/01→		-> 12/02	KH00101 ProKIT					
1.3 GTi	95 kW	1.3 l	07/02→								
1.3 4WD	64 kW	1.3 l	02/01→		-> 12/02	KH10225 ProKIT					

    						
<b>DAIMLER - 2.8 - 5.3</b>						<b>10/69→10/86</b>
Double Six / Vanden 5.3	198 kW	5.3 l	07/72→09/73			<b>KH00127</b> ProKIT
Sovereign 4.2	124 kW	4.2 l	06/76→03/79			
Sovereign 4.2	127 kW	4.2 l	09/73→03/79			
Sovereign 4.2	137 kW	4.2 l	10/69→09/73			
Sovereign 2.8	110 kW	2.8 l	10/69→05/75	 ; -> 09/73		<b>KH00127</b> ProKIT
Sovereign 3.4	120 kW	3.4 l	05/75→12/78	 ; 06/75 -> 11/77		<b>KH00127</b> ProKIT
Sovereign 4.2	151 kW	4.2 l	03/79→10/86	 ; -> 11/83		<b>KH00127</b> ProKIT
<b>DAIMLER - COUPE</b>						<b>09/73→12/77</b>
Sovereign 4.2	127 kW	4.2 l	09/73→12/77			<b>KH00127</b> ProKIT
<b>DAIMLER - DAIMLER XJ (X30_)</b>						<b>07/97→06/03</b>
4.0 Long	216 kW	4 l	10/97→06/03	 VIN -> 853935		<b>KH10169</b> ProKIT
V8 Super 4.0	267 kW	4 l	07/97→06/03	 VIN 853936 ->		<b>KH10172</b> ProKIT
<b>DAIMLER - LANDAULETTE</b>						<b>03/74→12/91</b>
4.2	123 kW	4.2 l	03/74→12/91			<b>KH00127</b> ProKIT
<b>DAIMLER - LIMOUSINE Saloon</b>						<b>06/68→12/91</b>
4.2	123 kW	4.2 l	06/68→12/91			<b>KH00127</b> ProKIT





**DODGE - CALIBER**

**06/06→**

1.8	110 kW	1.8 l	06/06→12/09		KH30164 ProKIT
2.0	115 kW	2 l	06/06→		
2.4	125 kW	2.4 l	10/06→		

**DODGE - NEON II Sedan**

**08/99→**

2.0	110 kW	2 l	10/99→09/05		KH10396 ProKIT
2.0 16V	98 kW	2 l	08/99→		
2.0 16V	112 kW	2 l	08/99→12/02		



































**DODGE - NITRO**

**09/06→12/12**







2.8 CRD	130 kW	2.8 l	06/07→12/12		KH30152 ProKIT
2.8 CRD 4WD	130 kW	2.8 l	06/07→12/12		
3.7 V6 4WD	151 kW	3.7 l	06/07→12/12		
4.0 4WD	191 kW	4 l	09/06→12/07		









				13		i	
<b>DS - DS 3 / DS 3 Convertible (SA_, SB_)</b>							<b>04/15→07/19</b>
1.2 THP 110	81 kW	1.2 l	07/15→07/19		Outer diameter 1 [mm]: 82	<b>KH10047</b> ProKIT	
1.2 THP 110 / PureTech 110 (SAHNPS)	81 kW	1.2 l	04/15→07/19		Outer diameter 1 [mm]: 72	<b>KH10054</b> ProKIT	
1.2 THP 130	96 kW	1.2 l	09/15→07/19			<b>KH10086</b> ProKIT	
1.2 VTI 82	60 kW	1.2 l	04/15→07/19				
1.2 VTI 82	60 kW	1.2 l	07/15→07/19				
1.6 BlueHDi 100	73 kW	1.6 l	04/15→07/19				
1.6 BlueHDi 100	73 kW	1.6 l	07/15→07/19				
1.6 BlueHDi 120	88 kW	1.6 l	07/15→07/19				
1.6 BlueHDi 75	55 kW	1.6 l	07/15→07/19				
1.6 Vti	88 kW	1.6 l	07/15→07/19				
1.6 BlueHDi 116	85 kW	1.6 l	07/15→07/19		Outer diameter 1 [mm]: 82	<b>KH10047</b> ProKIT	
1.6 e-HDi 92	68 kW	1.6 l	04/15→07/19		Outer diameter 1 [mm]: 72	<b>KH10054</b> ProKIT	
1.6 THP	110 kW	1.6 l	07/15→07/19				
1.6 THP	120 kW	1.6 l	07/15→07/19				
1.6 THP 156	115 kW	1.6 l	07/16→07/19				
1.6 THP 165	121 kW	1.6 l	07/15→07/19				
1.6 THP 208	153 kW	1.6 l	09/15→07/19				
<b>DS - DS 4 / DS 4 CROSSBACK (NX_)</b>							<b>07/15→12/18</b>
1.2 THP 130 (NXHNYM)	96 kW	1.2 l	07/15→12/18		Outer diameter 1 [mm]: 83;  19 Inch	<b>KH10006</b> ProKIT	
1.6 BlueHDi 100	73 kW	1.6 l	04/16→12/18		Outer diameter 1 [mm]: 82;  19 Inch	<b>KH10047</b> ProKIT	
1.6 BlueHDi 120	88 kW	1.6 l	07/15→12/18				
1.6 THP 165	121 kW	1.6 l	07/15→12/18			<b>KH10040</b> ProKIT	
1.6 THP 210	155 kW	1.6 l	07/15→12/18				
2.0 BlueHDi 150	110 kW	2 l	07/15→12/18				
2.0 BlueHDi 180	133 kW	2 l	07/15→12/18				
1.6 BlueHDi 115	85 kW	1.6 l	07/15→12/18		Outer diameter 1 [mm]: 83;  19 Inch	<b>KH10006</b> ProKIT	
1.6 e-HDi 115	84 kW	1.6 l	07/15→12/18		Outer diameter 1 [mm]: 82;  19 Inch	<b>KH10047</b> ProKIT	
1.6 THP 150	110 kW	1.6 l	10/16→12/18				
1.6 THP 160	120 kW	1.6 l	07/15→12/18				
1.6 THP 208	153 kW	1.6 l	03/17→12/18				
1.6 VTI	88 kW	1.6 l	07/15→12/18				
<b>DS - DS 5 (KF_)</b>							<b>04/15→12/18</b>
1.6 BlueHDi 115	85 kW	1.6 l	06/15→12/18		Outer diameter 1 [mm]: 83	<b>KH10006</b> ProKIT	
1.6 THP 160	120 kW	1.6 l	07/15→12/18		Outer diameter 1 [mm]: 82	<b>KH10047</b> ProKIT	
2.0 BlueHDi 135	100 kW	2 l	06/15→12/18				
1.6 BlueHDi 120	88 kW	1.6 l	06/15→12/18		Outer diameter 1 [mm]: 83	<b>KH10006</b> ProKIT	
1.6 THP 165 (KF5GZT)	121 kW	1.6 l	07/15→12/18		Outer diameter 1 [mm]: 82	<b>KH10047</b> ProKIT	
1.6 THP 210	155 kW	1.6 l	04/15→12/18				
2.0 BlueHDi 150	110 kW	2 l	04/15→12/18			<b>KH10040</b> ProKIT	
2.0 BlueHDi 180	133 kW	2 l	04/15→12/18				
2.0 Hybrid4	147 kW	2 l	04/15→12/18		Outer diameter 1 [mm]: 83	<b>KH10006</b> ProKIT	

     				
<b>FIAT - 126 (126_)</b>				<b>09/72→09/00</b>
600	17 kW	0.6 l	09/72→06/77	 KH00109 ProKIT  KH00075 ProKIT
650	17 kW	0.6 l	07/77→09/87	 KH00075 ProKIT
650	18 kW	0.65 l	07/81→09/00	
700	19 kW	0.7 l	09/87→06/96	
<b>FIAT - 127 / 127 Panorama (127_)</b>				<b>06/71→12/86</b>
0.9	29 kW	0.9 l	06/71→05/83	 ; 05/73 -> 12/76; VIN 1573629 -> VIN 1573628 KH10369 ProKIT
0.9 (127A)	33 kW	0.9 l	09/71→12/84	 ; 09/76 -> VIN 1537630 ->  KH20091 ProKIT
1.0	37 kW	1 l	01/77→12/86	 ; VIN 1573629 -> KH10369 ProKIT
1.0	37 kW	1 l	04/77→12/86	 KH20091 ProKIT
1.0 Sport	51 kW	1 l	07/78→02/82	 KH20091 ProKIT
1.3 D	33 kW	1.3 l	06/81→12/86	
1.3 Diesel	33 kW	1.3 l	04/81→12/86	
1.3 Sport	55 kW	1.3 l	12/81→05/83	
<b>FIAT - 128 Coupe / 128 Familiare / 128 Sedan (128_)</b>				<b>03/69→12/84</b>
1.1	33 kW	1.1 l	02/75→09/81	 ; 10/76 -> 03/79; VIN 1289826 -> VIN Z9997 KH10369 ProKIT
1.1 (AC 5)	48 kW	1.1 l	08/75→02/81	 ; 10/76 -> KH20091 ProKIT
1.1 (AF)	33 kW	1.1 l	02/75→02/81	
1.3 (AF1)	44 kW	1.3 l	12/74→10/82	
1.1 (128A)	40 kW	1.1 l	03/69→12/84	 ; 01/71 -> 03/79; VIN 1289826, 531082 -> VIN 1289825, Z9997 KH10369 ProKIT
1.1 (AF)	40 kW	1.1 l	10/69→10/82	 ; 10/76 -> KH20091 ProKIT
1.1 (AC 5)	47 kW	1.1 l	03/72→02/81	 ; 01/73 -> 03/79; VIN 1289826, 531082 -> VIN 1289825, Z9997 KH10369 ProKIT
				 ; 10/76 -> KH20091 ProKIT
1.3 (AC)	55 kW	1.3 l	03/72→12/79	 ; 01/73 -> 09/76; VIN 1289826, 531082 -> VIN 1289825, Z9997 KH10369 ProKIT
				 ; 10/76 -> KH20091 ProKIT
1.3 Berlinetta (AC)	54 kW	1.3 l	06/75→12/79	 ; 10/76 -> KH20091 ProKIT
1.3 Sport (128A)	44 kW	1.3 l	08/74→12/84	
1.3 Rally (128A)	49 kW	1.3 l	07/71→02/76	 ; 01/73 -> 12/75; VIN 1220153 -> VIN 1220152 KH10369 ProKIT
<b>FIAT - 500 (111_, 101_, 110_)</b>				<b>06/57→01/76</b>
0.5 (110F)	13 kW	0.5 l	01/65→12/75	 KH00109 ProKIT
0.5 (111A)	11 kW	0.5 l	06/57→05/61	 KH00075 ProKIT
0.6	13 kW	0.6 l	08/68→01/76	
<b>FIAT - 500 / 500 C (312_)</b>				<b>07/07→</b>
0.9 (312AG1A)	63 kW	0.9 l	09/09→	 KH10065 ProKIT
0.9 (312AXG1A, 312.AXG11)	63 kW	0.9 l	07/10→	 KH20022 ProKIT
0.9 (312AXH1A)	48 kW	0.9 l	09/12→	
0.9 (312AXM1B)	77 kW	0.9 l	12/13→	
1.2 (312CXA1A, 312AXA1A)	51 kW	1.2 l	09/09→	
1.3 D Multijet (312AXB1A)	55 kW	1.3 l	10/07→	
1.3 D Multijet (312AXE1A)	70 kW	1.3 l	12/09→	
1.3 D Multijet (312CXB1A)	55 kW	1.3 l	09/09→	
1.3 D Multijet (312CXE1A, 312AXE1A)	70 kW	1.3 l	09/09→	
1.4 (312AXC1B, 312CXC1B)	74 kW	1.4 l	10/07→	
1.4 (312CXC1B, 312AXC1B)	74 kW	1.4 l	09/09→	
0.9 (312AXM1B)	77 kW	0.9 l	10/13→	 KH20022 ProKIT
0.9 (312AXN1A, 312AXN11)	59 kW	0.9 l	12/13→	
0.9 (312AXN1A)	59 kW	0.9 l	12/13→	
0.9 (312AXP1A)	44 kW	0.9 l	12/13→	
1.2 (312AXA1A)	51 kW	1.2 l	07/07→	 KH10111 ProKIT
1.2 LPG (312AXA1A)	51 kW	1.2 l	12/10→	 KH20022 ProKIT
<b>FIAT - 500 Estate (101_)</b>				<b>01/60→12/66</b>
0.5	11 kW	0.5 l	01/60→12/66	 KH00109 ProKIT
				 KH00075 ProKIT





























































     				
<b>FIAT - 500L (351_, 352_)</b>				<b>09/12→</b>
0.9 (199LYC1B)	77 kW	0.9 l	09/12→	; <b>ABS</b> ; Payload: not for increased payload <b>KH20109 ProKIT</b>
0.9 Natural Power (199LYC1B)	63 kW	0.9 l	03/13→	
1.3 D Multijet (199.LYM11, 199.LYM1A)	70 kW	1.3 l	06/14→	
1.3 D Multijet (199LXY1A, 199LXY11)	62 kW	1.3 l	09/12→	
1.4 (199LYB1B)	70 kW	1.4 l	09/12→	
1.4 (199LYF1B)	88 kW	1.4 l	10/13→	
1.6 D Multijet (199LYD1B)	77 kW	1.6 l	09/12→05/18	
1.6 D Multijet (199LYE1B)	88 kW	1.6 l	09/13→	
<b>FIAT - 500X (334_)</b>				<b>09/14→09/18</b>
1.3 D Multijet (334AXH1A)	70 kW	1.3 l	11/14→	<b>KH30190 ProKIT</b>
1.4 (334AXC1B, 334AXC11)	103 kW	1.4 l	09/14→09/18	
1.4 (334AXC1B)	100 kW	1.4 l	09/14→09/18	<b>KH30184 ProKIT</b>
1.6 (334AXE1A)	81 kW	1.6 l	11/14→	
1.6 D Multijet (334AXA1B, 334AXA11)	88 kW	1.6 l	09/14→	; <b>KH30190 ProKIT</b>
1.6 D Multijet (334AXA1B)	84 kW	1.6 l	09/14→	
1.4 4x4 (334AXF22)	120 kW	1.4 l	02/15→09/18	
1.4 4x4 (334AXF22)	125 kW	1.4 l	02/15→09/18	
2.0 D Multijet 4x4 (334AXB22, 334AXD2B)	100 kW	2 l	09/14→09/18	<b>KH30190 ProKIT</b>
2.0 D Multijet 4x4 (334AXB22, 334AXD2B)	103 kW	2 l	09/14→09/18	
<b>FIAT - 600 (113_)</b>				<b>03/55→02/71</b>
0.6	15 kW	0.6 l	03/55→05/61	<b>KH00075 ProKIT</b>
0.8 (D)	17 kW	0.8 l	10/60→02/71	
<b>FIAT - BARCHETTA (183_)</b>				<b>04/95→05/05</b>
1.8 16V	96 kW	1.8 l	04/95→05/05	; 05/95 -> 05/99 ; 09/00 -> <b>ABS</b> ; 05/99 -> VIN 43319 -> <b>ABS</b> ; 05/99 -> VIN 0043319 -> -> 05/99; <b>ABS</b>
<b>FIAT - BRAVA (182_)</b>				<b>10/95→12/02</b>
1.2 16V 80	59 kW	1.2 l	10/00→10/01	; Code: 1M; <b>ABS</b> ; <b>ABS</b> ; <b>ABS</b> ; <b>ABS</b>
1.2 16V 80	60 kW	1.2 l	12/98→12/02	
1.4 (182.BG)	55 kW	1.4 l	10/95→10/01	; <b>ABS</b> ; 08/98 -> <b>ABS</b> -> 09/98; <b>ABS</b> ; <b>ABS</b>
1.4 12 V (182.BA)	59 kW	1.4 l	10/95→08/98	; <b>ABS</b> ; <b>ABS</b> ; <b>ABS</b>
1.6 16V (182.BB)	76 kW	1.6 l	02/96→10/01	; <b>TR</b> ; <b>ABS</b> ; <b>MT</b> ; <b>TR</b> ; <b>ABS</b> ; <b>MT</b> ; <b>AT</b> ; <b>TR</b> ; <b>ABS</b> ; <b>TR</b> ; <b>ABS</b> ; 08/98 -> <b>ABS</b> -> 09/98; <b>ABS</b> ; <b>ABS</b>
1.6 16V (182.BH)	66 kW	1.6 l	10/95→10/01	
1.6 16V (182.BU)	76 kW	1.6 l	01/99→12/02	; <b>TR</b> ; <b>ABS</b> ; <b>MT</b> ; <b>TR</b> ; <b>ABS</b> ; <b>MT</b> ; <b>AT</b> ; <b>TR</b> ; <b>ABS</b> ; <b>TR</b> ; <b>ABS</b>
1.8 GT 16V (182.BC)	83 kW	1.8 l	10/95→08/01	; 09/98 -> <b>ABS</b> ; <b>ABS</b> ; 08/98 -> <b>ABS</b> -> 06/98; <b>ABS</b> ; <b>ABS</b>








				     	
<b>FIAT - BRAVA (182_)</b>				<b>10/95→12/02</b>	
1.9 D	48 kW	1.9 l	10/95→10/01	;	KH10044 ProKIT
				; <b>-&gt; 12/98;</b>	KH20047 ProKIT
				;	KH20034 ProKIT
1.9 JTD	74 kW	1.9 l	09/00→10/01	;	KH10065 ProKIT
1.9 JTD 105	77 kW	1.9 l	12/98→10/01	;	KH10181 ProKIT
				;	KH20022 ProKIT
				;	KH20034 ProKIT
1.9 TD 100 S (182.BF)	74 kW	1.9 l	03/96→10/01	; <b>09/98 -&gt;</b> ;	KH10065 ProKIT
1.9 TD 75 S (182.BF)	55 kW	1.9 l	03/96→10/01	;	KH10181 ProKIT
				; <b>08/98 -&gt;</b> ;	KH20022 ProKIT
				; <b>-&gt; 07/98;</b>	KH20047 ProKIT
				;	KH20034 ProKIT
<b>FIAT - BRAVO I (182_)</b>				<b>10/95→10/01</b>	
1.2 16V 80	59 kW	1.2 l	10/00→10/01	; <b>Code: 1M;</b>	KH10043 ProKIT
1.2 16V 80	60 kW	1.2 l	12/98→10/00	;	KH10044 ProKIT
				;	KH20022 ProKIT
1.4 (182.AA)	59 kW	1.4 l	10/95→10/01	;	KH10044 ProKIT
1.4 (182.AG)	55 kW	1.4 l	10/95→10/01	; <b>08/98 -&gt;</b> ;	KH20022 ProKIT
				; <b>-&gt; 09/98;</b>	KH20047 ProKIT
1.6	76 kW	1.6 l	09/00→10/01	; ; ; <b>MT</b>	KH10043 ProKIT
				; ; ; <b>MT, AT</b>	KH10044 ProKIT
				; ;	KH10065 ProKIT
				; ;	KH10181 ProKIT
1.6 16V (182.AB)	76 kW	1.6 l	03/96→10/01	; ; ; <b>MT</b>	KH10043 ProKIT
1.6 16V (182.AH)	66 kW	1.6 l	10/95→10/01	; ; ; <b>MT, AT</b>	KH10044 ProKIT
				; ;	KH10065 ProKIT
				; ;	KH10181 ProKIT
				; <b>08/98 -&gt;</b> ;	KH20022 ProKIT
				; <b>-&gt; 09/98;</b>	KH20047 ProKIT
1.8 GT (182.AC)	83 kW	1.8 l	10/95→10/01	; <b>09/98 -&gt;</b> ;	KH10065 ProKIT
1.9 TD 100 S (182.AF)	74 kW	1.9 l	03/96→10/01	;	KH10181 ProKIT
1.9 TD 75 S (182.AF)	55 kW	1.9 l	03/96→10/01	; <b>08/98 -&gt;</b> ;	KH20022 ProKIT
				; <b>-&gt; 07/98;</b>	KH20047 ProKIT
1.9 D	48 kW	1.9 l	10/95→10/01	;	KH10044 ProKIT
				; <b>-&gt; 12/98;</b>	KH20047 ProKIT
1.9 JTD	74 kW	1.9 l	09/00→10/01	;	KH10065 ProKIT
1.9 JTD 105	77 kW	1.9 l	12/98→10/01	;	KH10181 ProKIT
				;	KH20022 ProKIT
2.0 HGT 20V (182.AD)	108 kW	2 l	10/95→07/98		KH10190 ProKIT
				;	KH20047 ProKIT
2.0 HGT 20V (182AQ)	113 kW	2 l	07/98→10/01		KH10385 ProKIT
				; <b>08/98 -&gt;</b> ;	KH20022 ProKIT
<b>FIAT - CINQUECENTO (170_)</b>				<b>07/91→07/99</b>	
0.7 (170AA)	23 kW	0.7 l	12/91→01/96		KH10217 ProKIT
0.7 i (170AD)	22 kW	0.7 l	07/94→01/98		KH20091 ProKIT
0.9 (170AB)	30 kW	0.9 l	07/91→12/93		
0.9 i.e. (170AC)	30 kW	0.9 l	07/91→09/94		
0.9 i.e. S (170AF, 170CF)	29 kW	0.9 l	07/91→07/99		
1.1 Sporting (170AH)	40 kW	1.1 l	10/94→01/98		
<b>FIAT - COUPE (175_)</b>				<b>11/93→08/00</b>	
1.8 16V	96 kW	1.8 l	03/96→08/00		KH10181 ProKIT
				;	KH20034 ProKIT
				;	KH20161 ProKIT
2.0 16V	102 kW	2 l	11/93→08/96		KH10181 ProKIT
2.0 20V (175AXC1A)	108 kW	2 l	08/96→09/98		KH20161 ProKIT
2.0 16V Turbo	140 kW	2 l	11/93→08/96		KH10190 ProKIT
2.0 20V Turbo	162 kW	2 l	08/96→08/00		KH20161 ProKIT
2.0 20V	113 kW	2 l	04/98→08/00	; <b>07/98 -&gt;</b>	KH10181 ProKIT
					KH20161 ProKIT




































				13	i			
<b>FIAT - CROMA (154_)</b>							<b>12/85→12/96</b>	
1600	61 kW	1.6 l	12/85→12/90				<b>KH10371</b> ProKIT	
1900 Turbo D i.d.	69 kW	1.9 l	11/92→12/96		VIN 2025079 ->		<b>KH10190</b> ProKIT	
1900 Turbo D i.d. (154.LL, 154.PL)	66 kW	1.9 l	08/87→10/92		VIN -> 2025078		<b>KH10371</b> ProKIT	
2000 CHT	74 kW	2 l	01/91→09/92					
2000 CHT (154.AC)	66 kW	2 l	12/85→02/89					
2000 i.e. (154.AD)	88 kW	2 l	03/87→09/92					
2000 i.e. (154.AM)	83 kW	2 l	03/86→09/90					
2000 i.e. Turbo	111 kW	2 l	11/86→11/88					
2000 i.e. Turbo (154.AM)	114 kW	2 l	12/85→06/90					
2500 D	55 kW	2.5 l	12/85→12/89					
2500 TD (154.AE)	74 kW	2.4 l	12/85→08/89					
2000 16V	101 kW	2 l	08/92→08/96				<b>KH10190</b> ProKIT	
2500 V6	119 kW	2.5 l	06/93→08/96					
2000 i.e. (154.AM, 154.LM)	85 kW	2 l	10/87→08/96		11/92 ->; VIN 2025079 ->		<b>KH10190</b> ProKIT	
2000 i.e. Turbo (154.AM, 154.LM)	110 kW	2 l	06/87→08/96		-> 11/92; VIN -> 2025078		<b>KH10371</b> ProKIT	
2500 TD (154.LL, 154.PL)	85 kW	2.5 l	05/89→08/96					
2500 TDE	77 kW	2.5 l	12/91→08/96					
<b>FIAT - CROMA (194_)</b>							<b>06/05→</b>	
1.8 16V	103 kW	1.8 l	12/05→				<b>KH30061</b> ProKIT	
1.9 D Multijet (194AXB1B)	88 kW	1.9 l	06/05→12/11				<b>KH30071</b> ProKIT	
1.9 D Multijet (194AXC1B, 194AXC12)	110 kW	1.9 l	06/05→12/11					
2.2 16V	108 kW	2.2 l	06/05→					
2.4 D Multijet	147 kW	2.4 l	06/05→					
1.9 D Multijet	85 kW	1.9 l	06/05→				<b>KH30061</b> ProKIT	
					-> 10/07		<b>KH30071</b> ProKIT	
<b>FIAT - DOBLO Box Body/MPV (223_)</b>							<b>03/01→01/10</b>	
1.2 (223ZX1A)	48 kW	1.2 l	03/01→01/04		ABS		<b>KH10065</b> ProKIT	
					ABS		<b>KH10163</b> ProKIT	
					ABS		<b>KH10181</b> ProKIT	
					ABS		<b>KH10227</b> ProKIT	
							<b>KH20082</b> ProKIT	
1.3 D Multijet	55 kW	1.3 l	10/05→01/10		01/06 ->; ABS		<b>KH10181</b> ProKIT	
					ABS		<b>KH10065</b> ProKIT	
					01/06 ->		<b>KH20082</b> ProKIT	
1.3 JTD 16V	51 kW	1.3 l	05/04→12/06		-> 12/05; ABS		<b>KH10181</b> ProKIT	
					ABS		<b>KH10065</b> ProKIT	
					-> 12/05		<b>KH20082</b> ProKIT	
1.3 JTD 16V Multijet	62 kW	1.3 l	08/06→		ABS		<b>KH10065</b> ProKIT	
1.9 JTD Multijet	88 kW	1.9 l	12/06→					
1.4	57 kW	1.4 l	10/05→		01/06 ->; ABS		<b>KH10181</b> ProKIT	
					-> 05/10; ABS		<b>KH10163</b> ProKIT	
					ABS		<b>KH10065</b> ProKIT	
					ABS		<b>KH10227</b> ProKIT	
					01/06 ->		<b>KH20082</b> ProKIT	
1.6 16V (223ZXD1A)	76 kW	1.6 l	10/01→		-> 12/03; ABS		<b>KH10181</b> ProKIT	
					-> 05/10; ABS		<b>KH10163</b> ProKIT	
					ABS		<b>KH10065</b> ProKIT	
					ABS		<b>KH10227</b> ProKIT	
					-> 12/03		<b>KH20082</b> ProKIT	
1.6 Natural Power	76 kW	1.6 l	09/02→		01/04 ->; ABS		<b>KH10181</b> ProKIT	
1.9 JTD	77 kW	1.9 l	07/03→		ABS		<b>KH10065</b> ProKIT	
					01/04 ->		<b>KH20082</b> ProKIT	
1.9 D (223ZXB1A)	46 kW	1.9 l	03/01→		-> 12/05; ABS		<b>KH10181</b> ProKIT	
					-> 05/10; ABS		<b>KH10163</b> ProKIT	
					ABS		<b>KH10065</b> ProKIT	
					ABS		<b>KH10227</b> ProKIT	
					-> 12/05		<b>KH20082</b> ProKIT	
1.9 JTD (223ZXE1A)	74 kW	1.9 l	10/01→		ABS		<b>KH10065</b> ProKIT	
					ABS		<b>KH10181</b> ProKIT	
					01/06 ->		<b>KH20082</b> ProKIT	









				    	
<b>FIAT - DOBLO Bus / DOBLO Cargo (263_)</b>				<b>01/10→</b>	
1.3 D Multijet	66 kW	1.3 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20093</b> ProKIT
1.4	70 kW	1.4 l	02/10→	 ; <b>Payload: not for increased payload</b>	<b>KH20109</b> ProKIT
1.4	88 kW	1.4 l	10/11→		
1.4 Natural Power	88 kW	1.4 l	06/10→		
1.3 D Multijet (263AXC1A)	66 kW	1.3 l	02/10→	 ; <b>Payload: not for increased payload</b>	<b>KH20109</b> ProKIT
2.0 D Multijet (263AXF1B)	99 kW	2 l	01/10→		
1.4 (263AXA1A)	70 kW	1.4 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH10198</b> ProKIT
1.6 D Multijet (263AXD1B)	77 kW	1.6 l	01/10→	 ; <b>Payload: not for increased payload</b>	<b>KH20109</b> ProKIT
1.6 D Multijet (263AXH1A, 263AXL11, 263AXH1B)	66 kW	1.6 l	02/10→		
1.4 (263AXG1B, 263AXG1A)	88 kW	1.4 l	10/11→	 ; <b>Payload: for increased payload</b>	<b>KH10198</b> ProKIT
1.6 D Multijet	66 kW	1.6 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20093</b> ProKIT
1.6 D Multijet	74 kW	1.6 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20109</b> ProKIT
1.6 D Multijet	77 kW	1.6 l	02/10→	 ; <b>Payload: not for increased payload</b>	<b>KH20109</b> ProKIT
2.0 D Multijet	99 kW	2 l	02/10→		
1.4 Natural Power (263AXG1B)	88 kW	1.4 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20093</b> ProKIT
1.6 D Multijet (263.WXN1B, 263.ZXN1B)	88 kW	1.6 l	02/16→	 ; <b>Payload: for increased payload</b>	<b>KH10198</b> ProKIT
<b>FIAT - DOBLO MPV (119_, 223_)</b>				<b>03/01→05/05</b>	
1.2 (223AXA1A)	48 kW	1.2 l	03/01→	 ; <b>-&gt; 12/05;</b> 	<b>KH10181</b> ProKIT
1.6 16V (223AXD1A)	76 kW	1.6 l	10/01→	 ; <b>-&gt; 05/10;</b> 	<b>KH10163</b> ProKIT
1.9 D (223AXB1A)	46 kW	1.9 l	03/01→		<b>KH10065</b> ProKIT
					<b>KH10227</b> ProKIT
				 ; <b>-&gt; 12/05</b>	<b>KH20082</b> ProKIT
1.3 D Multijet	62 kW	1.3 l	10/05→		<b>KH10065</b> ProKIT
1.9 D Multijet	88 kW	1.9 l	10/05→	 ; <b>01/06 -&gt;</b>	<b>KH20082</b> ProKIT
1.3 JTD	55 kW	1.3 l	05/05→		<b>KH10065</b> ProKIT
1.3 JTD 16V	51 kW	1.3 l	12/04→05/05	 ; 	<b>KH10065</b> ProKIT
					<b>KH10227</b> ProKIT
1.4	57 kW	1.4 l	10/05→	 ; <b>-&gt; 05/10;</b> 	<b>KH10163</b> ProKIT
					<b>KH10065</b> ProKIT
					<b>KH10227</b> ProKIT
				 ; <b>01/06 -&gt;</b>	<b>KH20082</b> ProKIT
1.6 Natural Power	76 kW	1.6 l	09/02→	 ; <b>01/04 -&gt; 12/05;</b> 	<b>KH10181</b> ProKIT
				 ; <b>-&gt; 05/10;</b> 	<b>KH10163</b> ProKIT
					<b>KH10065</b> ProKIT
				 ; <b>01/04 -&gt;</b>	<b>KH20082</b> ProKIT
1.9 JTD	77 kW	1.9 l	07/03→	 ; <b>09/05 -&gt; 12/05;</b> 	<b>KH10181</b> ProKIT
					<b>KH10065</b> ProKIT
				 ; <b>09/05 -&gt;</b>	<b>KH20082</b> ProKIT
1.9 JTD (223AXE1A)	74 kW	1.9 l	10/01→	 ; <b>-&gt; 12/03;</b> 	<b>KH10181</b> ProKIT
					<b>KH10065</b> ProKIT
				 ; <b>01/06 -&gt;</b>	<b>KH20082</b> ProKIT
<b>FIAT - DOBLO Platform/Chassis (263_)</b>				<b>02/10→</b>	
1.3 D Multijet	66 kW	1.3 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20093</b> ProKIT
1.4	70 kW	1.4 l	04/10→		
1.6 D Multijet	66 kW	1.6 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH10198</b> ProKIT
1.6 D Multijet	74 kW	1.6 l	02/11→	 ; <b>Payload: for increased payload</b>	<b>KH10198</b> ProKIT
1.6 D Multijet	77 kW	1.6 l	02/10→	 ; <b>Payload: for increased payload</b>	<b>KH20093</b> ProKIT
2.0 D Multijet	99 kW	2 l	02/10→		
<b>FIAT - DUCATO Bus (230_)</b>				<b>03/94→04/02</b>	
1.9 D	50 kW	1.9 l	04/98→04/02	 ; <b>11/01 -&gt;</b> ; <b>VIN 6194400 -&gt;</b>	<b>KH10078</b> ProKIT
1.9 D Combinato	51 kW	1.9 l	06/95→04/02	<b>Payload [kg]: 1,000, 1,400</b>	
1.9 TD	66 kW	1.9 l	04/98→04/02	 ; <b>-&gt; 11/01;</b> <b>VIN -&gt; 6194399;</b> <b>Payload [kg]: 1,800</b>	<b>KH00080</b> ProKIT
1.9 TD Combinato	59 kW	1.9 l	08/94→04/02		
1.9 TD Panorama/Combinato	60 kW	1.9 l	03/94→04/02	 ; <b>-&gt; 11/01;</b> <b>VIN -&gt; 6194400;</b> <b>Payload from [kg]: 1,000 -&gt; Payload to [kg]: 1,400</b>	<b>KH00035</b> ProKIT
2.0 JTD	62 kW	2 l	10/01→04/02		
2.0 Panorama/Combinato	80 kW	2 l	03/94→04/02	 ; <b>11/01 -&gt;</b> ; <b>VIN 16194400 -&gt;</b>	<b>KH10091</b> ProKIT
2.5 D Combinato	62 kW	2.5 l	08/94→04/02	 ; <b>-&gt; 11/01;</b> <b>VIN -&gt; 6194399;</b> <b>Payload [kg]: 1,800</b>	<b>KH00019</b> ProKIT
2.5 TDI Panorama/Combinato	80 kW	2.5 l	07/94→04/02		
2.5 TDI Panorama/Combinato	85 kW	2.5 l	03/94→04/02	 ; <b>-&gt; 11/01;</b> <b>VIN -&gt; 6194399;</b> <b>Payload [kg]: 1,000, 1,400</b>	<b>KH00043</b> ProKIT
2.8 D	64 kW	2.8 l	02/98→04/02		
2.8 JTD	94 kW	2.8 l	11/00→04/02		
2.8 TDI	90 kW	2.8 l	10/97→04/02		







    				03/94→04/02	
<b>FIAT - DUCATO Bus (230_)</b>					
1.9 D	59 kW	1.9 l	05/98→11/01	VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
				VIN -> 6194400; Payload [kg]: 1,800	KH00080 ProKIT
2.0 4x4	80 kW	2 l	11/94→11/01	VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
2.5 TD 4x4	80 kW	2.5 l	11/94→04/98	VIN -> 6194400	
2.5 TD 4x4	85 kW	2.5 l	06/94→09/01	VIN -> 6194399; Payload [kg]: 1,800	KH00080 ProKIT
2.5 D	55 kW	2.5 l	03/94→04/02	11/01 -> VIN 6194400 -> Payload [kg]: 1,000, 1,400	KH10078 ProKIT
				-> 11/01; VIN -> 6194399; Payload [kg]: 1,800	KH00080 ProKIT
				-> 11/01; VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
				11/01 -> VIN 16194400 ->	KH10091 ProKIT
2.5 TDI 4x4	85 kW	2.5 l	04/97→04/02	-> 11/01; VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH00035 ProKIT
2.8 JTD 4x4	94 kW	2.8 l	11/00→04/02	-> 11/01; VIN -> 6194400	
2.8 TDI 4x4	90 kW	2.8 l	07/99→04/02	11/01 -> VIN 6194400 -> Payload [kg]: 1,000, 1,400	KH10078 ProKIT
				-> 11/01; VIN -> 6194399; Payload [kg]: 1,800	KH00080 ProKIT
				11/01 -> VIN 6194400 ->	KH10391 ProKIT
<b>FIAT - DUCATO Bus (244_)</b>				12/01→07/06	
2.0	81 kW	2 l	12/01→07/06	09/04 -> Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
				-> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10078 ProKIT
					KH10091 ProKIT
2.0 4x4	81 kW	2 l	05/02→07/06	09/04 -> Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
				-> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10078 ProKIT
2.0 Bipower	81 kW	2 l	11/02→07/06		KH10091 ProKIT
2.0 JTD	62 kW	2 l	12/01→07/06	09/04 ->	KH10155 ProKIT
				-> 09/04	KH10078 ProKIT
					KH10091 ProKIT
2.3 JTD	81 kW	2.3 l	12/01→07/06	09/04 -> Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
2.8 JTD	94 kW	2.8 l	12/01→		
2.8 JTD	107 kW	2.8 l	04/04→07/06	09/04 -> Payload [kg]: 1,800;	
2.8 TD	90 kW	2.8 l	11/03→07/06	-> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10078 ProKIT
				-> 09/04; Payload [kg]: 1,800;	
				09/04 -> Payload [kg]: 1,800;	KH10234 ProKIT
				-> 09/04; Payload [kg]: 1,800;	KH10101 ProKIT
					KH10091 ProKIT
2.3 JTD	93 kW	2.3 l	12/09→	Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
				Payload [kg]: 1,800;	
				Payload [kg]: 1,800;	KH10234 ProKIT
2.8 JTD 4x4	94 kW	2.8 l	12/01→07/06	09/04 -> Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
				09/04 -> Payload [kg]: 1,800;	
				-> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10078 ProKIT
				-> 09/04; Payload [kg]: 1,800;	
				09/04 -> Payload [kg]: 1,800;	KH10234 ProKIT
				-> 09/04; Payload [kg]: 1,800;	KH10101 ProKIT
				-> 06/06	KH10391 ProKIT
2.8 TD 4x4	90 kW	2.8 l	11/03→07/06	09/04 -> Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10155 ProKIT
				09/04 -> Payload [kg]: 1,800;	
				-> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500	KH10078 ProKIT
				-> 09/04; Payload [kg]: 1,800;	
				09/04 -> Payload [kg]: 1,800;	KH10234 ProKIT
				-> 09/04; Payload [kg]: 1,800;	KH10101 ProKIT



								
<b>FIAT - DUCATO Bus (250_)</b>								<b>07/06→</b>
100 Multijet 2,2 D	74 kW	2.2 l	07/06→05/11					KH10120 ProKIT
110 Multijet 2,3 D	83 kW	2.3 l	10/11→		Payload [kg]: 1,700; $f_{max}$ ; Payload [kg]: 2,000			KH20059 ProKIT
115 Multijet 2,0 D	85 kW	2 l	06/11→					KH20086 ProKIT
120 Multijet 2,3 D	88 kW	2.3 l	07/06→		Payload [kg]: 1,100, 1,500, 1,700; $f_{max}$			
130 Multijet 2,3 D	96 kW	2.3 l	06/11→					
140 Natural Power	100 kW	3 l	04/09→					
150 Multijet 2,3 D	109 kW	2.3 l	06/11→					
150 Multijet 2,3 D	110 kW	2.3 l	04/15→					
150 Multijet 3,0 D	107 kW	3 l	04/10→					
160 Multijet 3,0 D	115 kW	3 l	10/06→					
160 Multijet 3,0 D	116 kW	3 l	07/06→					
180 Multijet 3,0 D	130 kW	3 l	06/11→					
110 Multijet 2,3 D	82 kW	2.3 l	05/14→					KH10120 ProKIT
130 Multijet 2,3 D 4x4	96 kW	2.3 l	06/11→					
140 Multijet 2,3 D	103 kW	2.3 l	05/19→					
150 Multijet 2,3 D 4x4	110 kW	2.3 l	04/15→					
160 Multijet 2,3 D	118 kW	2.3 l	05/19→					
160 Multijet 3,0 D 4x4	116 kW	3 l	07/06→					
180 Multijet 2,3 D	130 kW	2.3 l	05/19→					
<b>FIAT - DUCATO Panorama (280_)</b>								<b>07/82→08/90</b>
1.8	51 kW	1.8 l	07/82→12/88		VIN -> 604496			KH00061 ProKIT
					06/85 ->			KH00107 ProKIT
1.9 D	52 kW	1.9 l	02/87→08/90		01/89 ->; VIN 604497 ->			KH00035 ProKIT
2.0	62 kW	2 l	09/88→08/90		-> 12/89; VIN -> 604496			KH00061 ProKIT
2.5 D	55 kW	2.5 l	01/86→08/90					
2.5 D	68 kW	2.5 l	09/86→05/90					
2.5 D 4x4	55 kW	2.5 l	01/87→08/90					
2.5 D 4x4	68 kW	2.5 l	09/86→05/90					
2.5 TD	68 kW	2.5 l	01/87→08/90					
2.5 TD 4x4	68 kW	2.5 l	01/86→08/90					
1.9 TD	60 kW	1.9 l	03/89→08/90		-> 12/89; VIN -> 604496			KH00061 ProKIT
					VIN 604497 ->			KH00035 ProKIT
					07/90 ->			KH00107 ProKIT
2.0	55 kW	2 l	01/86→08/90		01/89 ->; VIN 604497 ->			KH00035 ProKIT
					-> 12/89; VIN -> 604496			KH00061 ProKIT
					-> 06/90			KH00107 ProKIT
2.0	58 kW	2 l	07/82→05/85		VIN -> 604496			KH00061 ProKIT
2.4 D	53 kW	2.4 l	07/82→12/85					
<b>FIAT - DUCATO Panorama (290_)</b>								<b>06/90→05/94</b>
1.9 D	52 kW	1.9 l	07/90→03/94					KH00035 ProKIT
2.0	62 kW	2 l	07/90→03/94		-> 01/94			KH00107 ProKIT
2.5 D	55 kW	2.5 l	07/90→03/94					
2.5 TD	70 kW	2.5 l	06/90→05/94					
1.9 TD	60 kW	1.9 l	07/90→03/94					KH00035 ProKIT
2.0 4x4	63 kW	2 l	06/90→05/94					
2.5 D 4x4	55 kW	2.5 l	07/90→03/94					
2.5 TD 4x4	70 kW	2.5 l	06/90→05/94					
2.5 TD 4x4	70 kW	2.5 l	01/91→03/94					
<b>FIAT - DUCATO Platform/Chassis (230_)</b>								<b>03/94→04/02</b>
1.9 D	50 kW	1.9 l	04/98→04/02		11/01 ->; VIN 6194400 ->; Payload [kg]: 1,000, 1,400			KH10078 ProKIT
1.9 D	51 kW	1.9 l	03/94→04/02					
1.9 TD	60 kW	1.9 l	03/94→04/02		-> 11/01; VIN -> 6194399; Payload [kg]: 1,800			KH00080 ProKIT
1.9 TD	66 kW	1.9 l	04/98→04/02		-> 11/01; VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400			KH00035 ProKIT
1.9 TD CAT	59 kW	1.9 l	08/94→04/02					
2.0	80 kW	2 l	03/94→04/02					
2.5 D	62 kW	2.5 l	03/94→04/02		11/01 ->; VIN 16194400 ->			KH10091 ProKIT
2.5 TDI	80 kW	2.5 l	03/94→04/02		-> 11/01; VIN -> 6194399; Payload [kg]: 1,800			KH00019 ProKIT
2.8 D	64 kW	2.8 l	02/98→04/02		-> 11/01; VIN -> 6194399; Payload [kg]: 1,800			KH00043 ProKIT
2.8 JTD	94 kW	2.8 l	11/00→04/02					
2.8 TDI	90 kW	2.8 l	12/98→04/02					
1.9 TD	59 kW	1.9 l	05/98→11/01		VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400			KH00035 ProKIT
2.5 TD	80 kW	2.5 l	06/94→08/98					
2.5 TD	85 kW	2.5 l	06/94→04/98		VIN -> 6194400; Payload [kg]: 1,800			KH00080 ProKIT
2.0 4x4	80 kW	2 l	11/94→09/01		VIN -> 6194400; Payload from [kg]: 1,000 → Payload to [kg]: 1,400			KH00035 ProKIT
2.5 TD 4x4	80 kW	2.5 l	11/94→04/98					
2.5 TD 4x4	85 kW	2.5 l	11/94→04/98		VIN -> 6194400			
2.8 iDTD 4x4	90 kW	2.8 l	05/98→09/01		VIN -> 6194399; Payload [kg]: 1,800			KH00080 ProKIT
2.8 TD 4x4	64 kW	2.8 l	05/98→11/01					

     					
<b>FIAT - DUCATO Platform/Chassis (230_)</b>				<b>03/94→04/02</b>	
2.0 JTD	62 kW	2 l	07/01→04/02	; 11/01 ->; VIN 6194400 ->; Payload [kg]: 1,000, 1,400	KH10078 ProKIT
				; -> 11/01; VIN -> 6194399; Payload [kg]: 1,800	KH00080 ProKIT
				; -> 11/01; VIN -> 6194400; Payload from [kg]: 1,000 -> Payload to [kg]: 1,400	KH00035 ProKIT
				; 11/01 ->; VIN 16194400 ->	KH10091 ProKIT
2.5 D 4x4	62 kW	2.5 l	03/94→04/02	; -> 11/01; VIN -> 6194400; Payload from [kg]: 1,000 -> Payload to [kg]: 1,400	KH00035 ProKIT
2.5 TDI 4x4	85 kW	2.5 l	06/98→04/02		
2.8 JTD 4x4	94 kW	2.8 l	10/01→04/02	; -> 11/01; VIN -> 6194400	
				; 11/01 ->; VIN 6194400 ->; Payload [kg]: 1,000, 1,400	KH10078 ProKIT
				; -> 11/01; VIN -> 6194399; Payload [kg]: 1,800	KH00080 ProKIT
				; 11/01 ->; VIN 6194400 ->	KH10391 ProKIT
<b>FIAT - DUCATO Platform/Chassis (244_)</b>				<b>12/01→07/14</b>	
2.0	81 kW	2 l	04/02→07/06	; 09/04 ->; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10155 ProKIT
				; -> 09/04; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10078 ProKIT
					KH10091 ProKIT
2.0 JTD	62 kW	2 l	12/01→07/06	; 09/04 ->	KH10155 ProKIT
				; -> 09/04	KH10078 ProKIT
					KH10091 ProKIT
2.3 JTD	81 kW	2.3 l	12/01→07/06	; 09/04 ->; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10155 ProKIT
2.8 JTD	90 kW	2.8 l	11/03→07/06		
2.8 JTD	94 kW	2.8 l	12/01→07/06	; 09/04 ->; Payload [kg]: 1,800;	
2.8 JTD Power	107 kW	2.8 l	04/04→07/06	; -> 09/04; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10078 ProKIT
				; -> 09/04; Payload [kg]: 1,800;	
				; 09/04 ->; Payload [kg]: 1,800;	KH10234 ProKIT
				; -> 09/04; Payload [kg]: 1,800;	KH10101 ProKIT
					KH10091 ProKIT
2.3 JTD	93 kW	2.3 l	12/09→07/14	; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10155 ProKIT
				; Payload [kg]: 1,800;	
				; Payload [kg]: 1,800;	KH10234 ProKIT
2.8 JTD 4x4	90 kW	2.8 l	11/03→07/06	; 09/04 ->; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10155 ProKIT
2.8 JTD 4x4	94 kW	2.8 l	12/01→07/06	; 09/04 ->; Payload [kg]: 1,800;	
				; -> 09/04; Payload from [kg]: 1,100 -> Payload to [kg]: 1,500	KH10078 ProKIT
				; -> 09/04; Payload [kg]: 1,800;	
				; 09/04 ->; Payload [kg]: 1,800;	KH10234 ProKIT
				; -> 09/04; Payload [kg]: 1,800;	KH10101 ProKIT
<b>FIAT - DUCATO Platform/Chassis (250_)</b>				<b>07/06→</b>	
100 Multijet 2,2 D	74 kW	2.2 l	07/06→		KH10120 ProKIT
110 Multijet 2,3 D	83 kW	2.3 l	10/11→	; Payload [kg]: 1,700; ; Payload [kg]: 2,000	KH20059 ProKIT
115 Multijet 2,0 D	85 kW	2 l	06/11→		
120 Multijet 2,3 D	88 kW	2.3 l	07/06→	; Payload [kg]: 1,100, 1,500, 1,700;	KH20086 ProKIT
130 Multijet 2,3 D	96 kW	2.3 l	07/06→		
140 Natural Power	100 kW	3 l	04/09→		
150 Multijet 2,3 D	109 kW	2.3 l	06/11→		
150 Multijet 2,3 D	110 kW	2.3 l	12/15→		
150 Multijet 3,0 D	107 kW	3 l	04/10→		
160 Multijet 3,0 D	115 kW	3 l	07/06→12/11		
160 Multijet 3,0 D	116 kW	3 l	07/06→		
180 Multijet 2,3 D	130 kW	2.3 l	12/15→		
180 Multijet 3,0 D	130 kW	3 l	06/11→		
110 Multijet 2,3 D	82 kW	2.3 l	08/06→		KH10120 ProKIT
120 Multijet 2,3 D 4x4	88 kW	2.3 l	03/10→		
140 Multijet 2,3 D	103 kW	2.3 l	05/19→		
160 Multijet 2,3 D	118 kW	2.3 l	05/19→		
<b>FIAT - DUCATO Platform/Chassis (280_)</b>				<b>07/82→08/90</b>	
1.9 D	52 kW	1.9 l	01/88→08/90	; 01/89 ->; VIN 604497 ->	KH00035 ProKIT
2.0	55 kW	2 l	07/85→08/90	; -> 12/89; VIN -> 604496	KH00061 ProKIT
2.0	62 kW	2 l	08/88→08/90		
2.5 D	55 kW	2.5 l	07/82→08/90		
2.5 TD	68 kW	2.5 l	01/86→08/90		
2.5 TD	68 kW	2.5 l	09/86→05/90		
2.5 TD 4x4	68 kW	2.5 l	01/86→08/90		
2.5 TD 4x4	68 kW	2.5 l	09/86→05/90		



     					
<b>FIAT - DUCATO Platform/Chassis (280_)</b>				<b>07/82→08/90</b>	
1.9 TD	60 kW	1.9 l	03/89→08/90	; -> 12/89; VIN -> 604496	KH00061 ProKIT
2.5 D 4x4	55 kW	2.5 l	03/89→08/90	; VIN 604497 ->	KH00035 ProKIT
<b>FIAT - DUCATO Platform/Chassis (290_)</b>				<b>03/89→05/94</b>	
1.9 D	51 kW	1.9 l	06/90→05/94		KH00035 ProKIT
2.0 4x4	63 kW	2 l	06/90→05/94		
2.5 D 4x4	55 kW	2.5 l	07/90→03/94		
2.5 TD 4x4	70 kW	2.5 l	07/90→03/94		
1.9 TD	60 kW	1.9 l	03/89→03/94		KH00035 ProKIT
				; 07/90 -> 01/94	KH00107 ProKIT
2.0	62 kW	2 l	07/90→03/94		KH00035 ProKIT
2.5 D	55 kW	2.5 l	03/89→03/94		KH00107 ProKIT
2.5 TD	70 kW	2.5 l	07/90→03/94	; -> 01/94	KH00107 ProKIT
<b>FIAT - DUCATO Van (230_)</b>				<b>03/94→04/02</b>	
1.9 D	50 kW	1.9 l	04/98→04/02	; 11/01 ->; VIN 6194400 ->;	KH10078 ProKIT
1.9 D	51 kW	1.9 l	03/94→04/02	<b>Payload [kg]: 1,000, 1,400</b>	
1.9 TD	60 kW	1.9 l	03/94→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00080 ProKIT
1.9 TD	66 kW	1.9 l	04/98→04/02	; -> 11/01; VIN -> 6194400; <b>Payload from [kg]: 1,000 → Payload to [kg]: 1,400</b>	KH00035 ProKIT
1.9 TD CAT	59 kW	1.9 l	08/94→04/02	; 11/01 ->; VIN 16194400 ->	KH10091 ProKIT
2.0	80 kW	2 l	03/94→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00019 ProKIT
2.0 JTD	62 kW	2 l	10/01→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00043 ProKIT
2.5 D	62 kW	2.5 l	03/94→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00043 ProKIT
2.5 TDI	80 kW	2.5 l	03/94→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,000, 1,400</b>	KH00043 ProKIT
2.5 TDI	85 kW	2.5 l	03/94→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,000, 1,400</b>	KH00043 ProKIT
2.8 D	64 kW	2.8 l	05/98→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,000, 1,400</b>	KH00043 ProKIT
2.8 JTD	94 kW	2.8 l	11/00→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,000, 1,400</b>	KH00043 ProKIT
2.8 TDI	90 kW	2.8 l	10/97→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00080 ProKIT
1.9 TD	59 kW	1.9 l	05/98→11/01	; VIN -> 6194400; <b>Payload from [kg]: 1,000 → Payload to [kg]: 1,400</b>	KH00035 ProKIT
2.5 TD	80 kW	2.5 l	06/94→08/98	; VIN -> 6194400; <b>Payload [kg]: 1,800</b>	KH00080 ProKIT
2.0 4x4	80 kW	2 l	11/94→04/02	; -> 11/01; VIN -> 6194400; <b>Payload from [kg]: 1,000 → Payload to [kg]: 1,400</b>	KH00035 ProKIT
2.5 D 4x4	62 kW	2.5 l	03/94→04/02	; -> 11/01; VIN -> 6194400	
2.5 TDI 4x4	85 kW	2.5 l	05/98→04/02	; -> 11/01; VIN -> 6194400	
2.8 D 4x4	64 kW	2.8 l	08/98→04/02	; 11/01 ->; VIN 6194400 ->;	KH10078 ProKIT
2.8 JTD 4x4	94 kW	2.8 l	11/00→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00080 ProKIT
2.8 TDI 4x4	90 kW	2.8 l	06/99→04/02	; -> 11/01; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH10391 ProKIT
2.5 TD 4x4	80 kW	2.5 l	11/94→04/98	; VIN -> 6194400; <b>Payload from [kg]: 1,000 → Payload to [kg]: 1,400</b>	KH00035 ProKIT
2.5 TD 4x4	85 kW	2.5 l	11/94→04/98	; VIN -> 6194400	
2.8 TD 4x4	90 kW	2.8 l	05/98→09/01	; VIN -> 6194400	
				; VIN -> 6194399; <b>Payload [kg]: 1,800</b>	KH00080 ProKIT
<b>FIAT - DUCATO Van (244_)</b>				<b>12/01→12/18</b>	
2.0	81 kW	2 l	12/01→07/06	; 09/04 ->; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10155 ProKIT
				; -> 09/04; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10078 ProKIT
					KH10091 ProKIT
2.0 4x4	81 kW	2 l	05/02→07/06	; 09/04 ->; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10155 ProKIT
2.0 Bipower	81 kW	2 l	11/02→07/06		KH10091 ProKIT
2.0 JTD	62 kW	2 l	12/01→07/06	; 09/04 ->	KH10155 ProKIT
				; -> 09/04	KH10078 ProKIT
					KH10091 ProKIT
2.3 JTD	81 kW	2.3 l	12/01→07/06	; 09/04 ->; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10155 ProKIT
2.8 JTD	94 kW	2.8 l	12/01→12/11		
2.8 JTD Power	107 kW	2.8 l	04/04→07/06	; 09/04 ->; <b>Payload [kg]: 1,800;</b>	
2.8 TD	90 kW	2.8 l	12/01→07/06	; -> 09/04; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10078 ProKIT
				; -> 09/04; <b>Payload [kg]: 1,800;</b>	
				; 09/04 ->; <b>Payload [kg]: 1,800;</b>	KH10234 ProKIT
				; -> 09/04; <b>Payload [kg]: 1,800;</b>	KH10101 ProKIT
					KH10091 ProKIT
2.3 JTD	93 kW	2.3 l	09/09→12/18	; <b>Payload from [kg]: 1,100 → Payload to [kg]: 1,500</b>	KH10155 ProKIT
2.8 JTD	93 kW	2.8 l	06/05→11/10	; <b>Payload [kg]: 1,800;</b>	
				; <b>Payload [kg]: 1,800;</b>	KH10234 ProKIT









































FIAT - DUCATO Van (244_)				12/01→12/18
2.8 JTD 4x4	94 kW	2.8 l	12/01→07/06	; 09/04 ->; Payload from [kg]: 1,100 → Payload to [kg]: 1,500 ; 09/04 ->; Payload [kg]: 1,800; ; -> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500 ; -> 09/04; Payload [kg]: 1,800; 09/04 ->; Payload [kg]: 1,800;  KH10155 ProKIT -> 09/04; Payload [kg]: 1,800;  KH10078 ProKIT 09/04 ->; Payload [kg]: 1,800;  KH10234 ProKIT -> 09/04; Payload [kg]: 1,800;  KH10101 ProKIT -> 06/06 KH10391 ProKIT
2.8 TD 4x4	90 kW	2.8 l	11/03→07/06	; 09/04 ->; Payload from [kg]: 1,100 → Payload to [kg]: 1,500 ; 09/04 ->; Payload [kg]: 1,800; ; -> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500 ; -> 09/04; Payload [kg]: 1,800; 09/04 ->; Payload [kg]: 1,800;  KH10155 ProKIT -> 09/04; Payload from [kg]: 1,100 → Payload to [kg]: 1,500 KH10078 ProKIT ; -> 09/04; Payload [kg]: 1,800; 09/04 ->; Payload [kg]: 1,800;  KH10234 ProKIT -> 09/04; Payload [kg]: 1,800;  KH10101 ProKIT

FIAT - DUCATO Van (250_)				07/06→	
100 Multijet 2,2 D	74 kW	2.2 l	07/06→	KH10120 ProKIT	
110 Multijet 2,3 D	83 kW	2.3 l	10/11→	; Payload [kg]: 1,700; ; Payload [kg]: 2,000 KH20059 ProKIT ; Payload [kg]: 1,100, 1,500, 1,700;  KH20086 ProKIT	
115 Multijet 2,0 D	85 kW	2 l	06/11→		
120 Multijet 2,3 D	88 kW	2.3 l	07/06→		
130 Multijet 2,3 D	96 kW	2.3 l	06/11→		
140 Natural Power	100 kW	3 l	04/09→		
150 Multijet 2,3 D	109 kW	2.3 l	06/11→		
150 Multijet 2,3 D	110 kW	2.3 l	12/15→		
150 Multijet 3,0 D	107 kW	3 l	04/10→		
160 Multijet 3,0 D	115 kW	3 l	07/06→12/11		
160 Multijet 3,0 D	116 kW	3 l	07/06→		
180 Multijet 2,3 D	130 kW	2.3 l	12/15→		
180 Multijet 3,0 D	130 kW	3 l	06/11→		
110 Multijet 2,3 D	82 kW	2.3 l	05/14→		KH10120 ProKIT
120 Multijet 2,3 D 4x4	88 kW	2.3 l	03/10→		
130 Multijet 2,3 D 4x4	96 kW	2.3 l	06/11→		
140 Multijet 2,3 D	103 kW	2.3 l	05/19→		
150 Multijet 2,3 D 4x4	110 kW	2.3 l	04/15→		
160 Multijet 2,3 D	118 kW	2.3 l	05/19→		
160 Multijet 3,0 D 4x4	116 kW	3 l	07/06→		

FIAT - DUCATO Van (280_)				01/82→09/90
1.8	49 kW	1.8 l	01/82→10/88	; VIN -> 604496 KH00061 ProKIT KH00107 ProKIT
1.8	51 kW	1.8 l	07/82→12/88	; VIN -> 604496 KH00061 ProKIT
2.5 D 4x4	53 kW	2.5 l	09/86→10/87	
1.9 D	52 kW	1.9 l	01/88→08/90	; 01/89 ->; VIN 604497 -> KH00035 ProKIT
2.0	55 kW	2 l	07/85→08/90	; -> 12/89; VIN -> 604496 KH00061 ProKIT
2.4 D	53 kW	2.4 l	01/82→08/90	; -> 06/90 KH00107 ProKIT
2.5 D	55 kW	2.5 l	01/82→08/90	; -> 06/90 KH00107 ProKIT
1.9 TD	60 kW	1.9 l	03/89→08/90	; -> 12/89; VIN -> 604496 KH00061 ProKIT ; VIN 604497 -> KH00035 ProKIT ; -> 06/90 KH00107 ProKIT
2.0	58 kW	2 l	01/82→08/90	; 01/89 ->; VIN 604497 -> KH00035 ProKIT ; -> 12/89; VIN -> 604496 KH00061 ProKIT ; -> 05/85 KH00107 ProKIT
2.0	62 kW	2 l	03/89→08/90	; -> 12/89; VIN -> 604496 KH00061 ProKIT
2.5 D 4x4	55 kW	2.5 l	03/89→08/90	; VIN 604497 -> KH00035 ProKIT
2.5 D	55 kW	2.5 l	09/86→05/90	; 01/89 ->; VIN 604497 -> KH00035 ProKIT
2.5 D 4x4	55 kW	2.5 l	09/86→05/90	; -> 12/89; VIN -> 604496 KH00061 ProKIT
2.5 TD	68 kW	2.5 l	09/86→05/90	
2.5 TD 4x4	68 kW	2.5 l	09/86→09/90	
2.5 TD 4x4	70 kW	2.5 l	09/86→05/90	

FIAT - DUCATO Van (290_)				03/89→05/94
1.9 D	52 kW	1.9 l	07/90→03/94	KH00035 ProKIT ; -> 01/94 KH00107 ProKIT
1.9 TD	60 kW	1.9 l	03/89→03/94	KH00035 ProKIT ; 07/90 -> 01/94 KH00107 ProKIT

												
<b>FIAT - DUCATO Van (290_)</b>											<b>03/89→05/94</b>	
2.0	63 kW	2 l	06/90→05/94								KH00035 ProKIT	
2.5 D	55 kW	2.5 l	06/90→05/94									
2.5 D 4x4	55 kW	2.5 l	07/90→03/94									
2.5 TD	70 kW	2.5 l	07/90→03/94									
2.5 TD 4x4	70 kW	2.5 l	07/90→03/94									
<b>FIAT - DUNA (146_)</b>											<b>01/87→12/91</b>	
1.7 DS	44 kW	1.7 l	01/87→12/91								KH20091 ProKIT	
60 1.1	43 kW	1.1 l	01/87→12/91									
70 1.3	49 kW	1.3 l	01/87→12/91									
<b>FIAT - FIORINO (127_, 147_)</b>											<b>10/77→12/87</b>	
1.0	37 kW	1 l	01/80→12/87								KH20091 ProKIT	
1050	37 kW	1 l	01/80→12/87									
900	33 kW	0.9 l	10/77→10/86		01/78 -> 12/79; VIN -> 8817481						KH10369 ProKIT	
<b>FIAT - FIORINO Box Body/MPV (146_)</b>											<b>01/88→05/01</b>	
60 1.1	40 kW	1.1 l	05/88→12/93		07/93 ->						KH10163 ProKIT	
60 1.7 D	42 kW	1.7 l	05/88→10/96									
60 1.7 D	44 kW	1.7 l	05/88→05/00									
75 i.e. 1.5	55 kW	1.5 l	05/88→12/93									
65 1.7 TD	46 kW	1.7 l	01/97→05/01								KH10163 ProKIT	
70 1.3	49 kW	1.3 l	01/88→12/94									
70 i.e. 1.4	49 kW	1.4 l	05/94→05/01									
75 i.e. 1.6	55 kW	1.6 l	10/93→05/01									
<b>FIAT - FIORINO Box Body/MPV (225_)</b>											<b>11/07→</b>	
1.3 D Multijet (225BXD1A, 225BXB1A, 225BXC1A)	55 kW	1.3 l	11/07→								KH10065 ProKIT	
					OE 51754193, 46519901						KH20022 ProKIT	
					OE 519652295						KH20082 ProKIT	
1.3 D Multijet (225BXE1A)	70 kW	1.3 l	07/09→								KH10065 ProKIT	
					OE 51754193, 46519901						KH20022 ProKIT	
1.4 (225BXA1A, 225BXC1A)	54 kW	1.4 l	11/07→		OE 51754193, 46519901						KH20022 ProKIT	
1.4 Natural Power (225BXC1A, 225AXC1A)	57 kW	1.4 l	06/08→		OE 519652295						KH20082 ProKIT	
<b>FIAT - FIORINO Pick up (146_)</b>											<b>01/88→05/01</b>	
1.3	49 kW	1.3 l	01/88→12/94		07/93 ->						KH10163 ProKIT	
1.7 D	44 kW	1.7 l	05/88→10/99									
1.4	49 kW	1.4 l	05/94→05/01								KH10163 ProKIT	
1.6	55 kW	1.6 l	01/94→05/01									
1.7 D	42 kW	1.7 l	10/93→10/99									
1.7 TD	46 kW	1.7 l	01/97→05/01									
<b>FIAT - FULLBACK Pickup (502_, 503_)</b>											<b>04/16→</b>	
2.4 D (KT0T)	113 kW	2.4 l	04/16→								KH20044 ProKIT	
2.4 D 4x4 (KT0T)	113 kW	2.4 l	04/16→									
2.4 D 4x4 (KT0T)	133 kW	2.4 l	04/16→									
<b>FIAT - GRANDE PUNTO Van (199_)</b>											<b>02/06→06/13</b>	
1.3 JTD Multijet (199CXC1A)	55 kW	1.3 l	02/06→06/13								KH20037 ProKIT	
1.3 JTD Multijet (199CXD1B)	66 kW	1.3 l	02/06→08/10									
1.4 (199CXB1A, 199DXB1A)	57 kW	1.4 l	02/06→06/13									
1.4 LPG (199CXB1A, 199DXB1A)	57 kW	1.4 l	03/09→12/12									
1.4 Natural Power (199BXC1A)	57 kW	1.4 l	03/09→12/12									
<b>FIAT - IDEA (350_)</b>											<b>12/03→</b>	
1.2 16V	59 kW	1.2 l	01/04→		ABS						KH10043 ProKIT	
1.4	57 kW	1.4 l	10/05→								KH20022 ProKIT	
1.4	66 kW	1.4 l	12/03→									
1.4 16V	70 kW	1.4 l	01/04→									
1.4 LPG	57 kW	1.4 l	03/09→									
1.3 D Multijet	51 kW	1.3 l	01/04→								KH10065 ProKIT	
1.3 D Multijet	66 kW	1.3 l	10/05→								KH20022 ProKIT	
1.3 D Multijet	70 kW	1.3 l	05/08→12/12									
1.6 D Multijet	88 kW	1.6 l	05/08→									
1.9 JTD	74 kW	1.9 l	01/04→									
<b>FIAT - LINEA (323_, 110_)</b>											<b>05/07→</b>	
1.3 D Multijet (323AXB11, 323AXB1A)	66 kW	1.3 l	06/07→		07/07 ->; ABS						KH10181 ProKIT	
					ABS						KH10065 ProKIT	
					ABS						KH20022 ProKIT	
					ABS						KH20034 ProKIT	

     						
FIAT - LINEA (323_, 110_)					05/07→	
1.3 D Multijet (323AXB1A)	70 kW	1.3 l	09/09→	;	KH10065 ProKIT	
1.6 D Multijet	77 kW	1.6 l	06/09→	;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.4	57 kW	1.4 l	06/07→	;	KH10043 ProKIT	
				;	KH10373 ProKIT	
				;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.4	66 kW	1.4 l	12/08→	;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.4 T-Jet (323AXC1A)	88 kW	1.4 l	05/07→	;	KH10065 ProKIT	
				;	KH10373 ProKIT	
				;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.6 (323.AXF1A)	81 kW	1.6 l	10/11→	;	KH20034 ProKIT	
FIAT - MAREA / MAREA Weekend (185_)					05/96→12/07	
1.2 16V	60 kW	1.2 l	10/98→05/02	; Code: 1M;	KH10043 ProKIT	
				;	KH10044 ProKIT	
				;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.2 16V	60 kW	1.2 l	10/98→05/02	;	KH10043 ProKIT	
				;	KH10044 ProKIT	
				;	KH20022 ProKIT	
				;	KH20034 ProKIT	
1.4 80 12V	59 kW	1.4 l	09/96→05/02	; -> 06/98; VIN -> 176271;	KH20047 ProKIT	
				; -> 06/98; VIN -> 5054833;		
				; -> 06/98; VIN -> 180746;		
				;	KH10044 ProKIT	
				; VIN 0176272 ->;	KH10043 ProKIT	
				;	KH20034 ProKIT	
				; VIN 0176272, 5054834 ->;	KH20022 ProKIT	
1.4 80 12V	59 kW	1.4 l	09/96→05/02	; -> 06/98; VIN -> 176271;	KH20047 ProKIT	
				; -> 06/98; VIN -> 5054833;		
				; -> 06/98; VIN -> 180746;		
				;	KH10044 ProKIT	
				; VIN 3336902 ->; ; AT	KH10043 ProKIT	
				;	KH20034 ProKIT	
				; VIN 0176272, 5054834 ->;	KH20022 ProKIT	
1.6	68 kW	1.6 l	03/99→08/00	;	KH10065 ProKIT	
1.6	76 kW	1.6 l	09/00→08/02	;	KH20022 ProKIT	
1.6 16V	75 kW	1.6 l	04/97→02/99	;	KH20034 ProKIT	
1.6 SX	72 kW	1.6 l	09/00→08/02	;		
1.9 JTD 110 (185BXT1A)	81 kW	1.9 l	09/00→08/02	;	KH10065 ProKIT	
1.9 JTD 105 (185AXN1A)	77 kW	1.9 l	12/98→12/02	;	KH10181 ProKIT	
1.9 JTD 105 (185BXN1A)	77 kW	1.9 l	12/98→12/02	;	KH20022 ProKIT	
1.9 JTD 110 (185AXT1A)	81 kW	1.9 l	09/00→08/02	;	KH20034 ProKIT	
1.6 100 16V	76 kW	1.6 l	09/96→05/02	; -> 06/98; VIN -> 176271;	KH20047 ProKIT	
1.8 115 16V	83 kW	1.8 l	09/96→05/02	; -> 06/98; VIN -> 5054833;		
				; -> 06/98; VIN -> 180746;		
				;	KH10181 ProKIT	
				; -> 12/98; VIN -> 0176271, 5054833 - 0180746;		
				; 01/98 ->; VIN 0176272, 5054834 - 0180747 ->;	KH10065 ProKIT	
				;	KH20022 ProKIT	
				;	KH20034 ProKIT	





**FIAT - MAREA / MAREA Weekend (185\_)**


































































**05/96→12/07**

1.6 100 16V	76 kW	1.6 l	09/96→05/02	-> 06/98; VIN -> 176271;	KH20047 ProKIT
1.9 TD 100 (185AX_)	74 kW	1.9 l	05/96→12/02	-> 06/98; VIN -> 5054833;	
1.9 TD 100 (185BX_)	74 kW	1.9 l	09/96→06/03	-> 06/98; VIN -> 180746;	
1.9 TD 75	55 kW	1.9 l	09/96→05/02		KH10181 ProKIT
				-> 12/98; VIN -> 0176271, 5054833 - 0180746;	
				; 01/98 ->; VIN 0176272, 5054834 - 0180747 ->;	KH10065 ProKIT
					KH20034 ProKIT
				VIN 0176272, 5054834 ->;	KH20022 ProKIT
1.6 100 16V Bipower	76 kW	1.6 l	04/99→05/02		KH10181 ProKIT
				VIN 0176272, 5054834 - 0180747 ->;	KH10065 ProKIT
					KH20022 ProKIT
					KH20034 ProKIT
1.8 115 16V	83 kW	1.8 l	09/96→05/02	-> 01/99	KH10181 ProKIT
1.9 TD 75	55 kW	1.9 l	09/96→05/02	; 02/99 ->;	
				-> 06/98; VIN -> 176271;	KH20047 ProKIT
				-> 06/98; VIN -> 5054833;	
				-> 06/98; VIN -> 180746;	
					KH10065 ProKIT
					KH20034 ProKIT
				VIN 0176272, 5054834 ->;	KH20022 ProKIT
1.9 JTD	79 kW	1.9 l	01/01→12/07		KH20034 ProKIT
2.0 150 20V	108 kW	2 l	09/96→04/99	-> 06/98; VIN -> 176271;	KH20047 ProKIT
2.4 TD 125	91 kW	2.4 l	09/96→04/99	-> 06/98; VIN -> 5054833;	
				-> 06/98; VIN -> 180746;	
				-> 12/98; VIN -> 0176271, 0180746, 5054833;	KH10190 ProKIT
				; 01/98 ->;	KH10385 ProKIT
					KH20034 ProKIT
				VIN 0176272, 5054834 ->;	KH20022 ProKIT
2.0 150 20V	110 kW	2 l	01/01→05/02		KH10190 ProKIT
2.0 155 20V	113 kW	2 l	04/99→01/01		KH10385 ProKIT
2.0 155 20V	113 kW	2 l	04/99→02/03		KH20022 ProKIT
2.4 JTD 130	96 kW	2.4 l	04/99→05/02		KH20034 ProKIT
2.0 150 20V	110 kW	2 l	01/01→05/02		KH10190 ProKIT
					KH10385 ProKIT
					KH20022 ProKIT
					KH20034 ProKIT












































**FIAT - MULTIPLA (186\_)**

**04/99→06/10**

1.6	68 kW	1.6 l	05/04→08/05		KH20034 ProKIT
1.6 (186AXC1A, 186BMC1A, 186BXC1A)	76 kW	1.6 l	09/00→06/10		KH10065 ProKIT
1.6 16V (186AGB1A)	70 kW	1.6 l	04/02→06/10		KH20022 ProKIT
1.6 16V GPL	76 kW	1.6 l	10/01→06/10		KH20034 ProKIT
1.6 100 16V (186AXA1A)	76 kW	1.6 l	04/99→06/10	-> 06/04;	KH10181 ProKIT
1.9 JTD 105 (186AXB1A)	77 kW	1.9 l	04/99→06/10		KH10065 ProKIT
					KH20022 ProKIT
					KH20034 ProKIT
1.6 16V Bipower (186AMB1A)	76 kW	1.6 l	04/99→06/10	-> 06/03;	KH10181 ProKIT
1.6 16V Blupower (186AMA1A)	70 kW	1.6 l	04/99→06/10		KH10065 ProKIT
					KH20022 ProKIT
					KH20034 ProKIT
1.6 16V Bipower (186AXC1A)	76 kW	1.6 l	10/01→06/10		KH10065 ProKIT
1.9 JTD 110	81 kW	1.9 l	03/01→07/02		KH10181 ProKIT
1.9 JTD 115	85 kW	1.9 l	07/02→06/10		KH20022 ProKIT
					KH20034 ProKIT
1.9 JTD (186AXE1A)	88 kW	1.9 l	04/02→06/10	; 01/06 ->;	KH10181 ProKIT
					KH10065 ProKIT
					KH20022 ProKIT
					KH20034 ProKIT


























											
<b>FIAT - PALIO / PALIO Weekend (178_, 171_, 178_, 173_, 373_, 374_, 171_) 04/96→10/04</b>											
1.0	45 kW	1 l	04/96→10/03								KH10378 ProKIT
											KH20022 ProKIT
											KH20047 ProKIT
											KH20034 ProKIT
1.0	56 kW	1 l	04/96→10/03								KH20022 ProKIT
1.1	40 kW	1.1 l	07/97→10/03								KH20034 ProKIT
1.2	59 kW	1.2 l	03/00→01/12								
1.3 JTD Multijet (178BYE1AAT)	51 kW	1.3 l	06/03→01/12								
1.4	57 kW	1.4 l	10/05→								
1.5	62 kW	1.5 l	06/04→								
1.7 TD	53 kW	1.7 l	09/01→								
1.9 JTD	59 kW	1.9 l	09/01→								
1.2	44 kW	1.2 l	07/97→08/02								KH20022 ProKIT
1.6 16V	68 kW	1.6 l	07/97→10/03								KH20034 ProKIT
1.2	50 kW	1.2 l	06/99→10/00								KH20034 ProKIT
1.2	53 kW	1.2 l	07/01→06/05								
1.2 (178BXZ1A)	50 kW	1.2 l	06/99→10/02								
1.2 (178DYE1A, 178DYE1AAP, 178DYE1AAT)	59 kW	1.2 l	09/01→10/04								
1.4	51 kW	1.4 l	07/97→08/01								
1.4	70 kW	1.4 l	06/03→								
1.5	62 kW	1.5 l	02/02→								
1.6	70 kW	1.6 l	06/99→								
1.6	73 kW	1.6 l	01/02→12/07								
1.6	74 kW	1.6 l	06/06→								
1.6 (1788381, 1730980, 1788581, 1788681, 1730780)	78 kW	1.6 l	07/97→02/03								
1.6 16V	68 kW	1.6 l	07/97→10/00								
1.7 D	42 kW	1.7 l	04/96→09/02								
1.7 TD	51 kW	1.7 l	10/02→01/12								
1.7 TD	52 kW	1.7 l	07/97→08/01								
1.2	54 kW	1.2 l	04/96→02/04								KH10378 ProKIT
1.4 Cat	51 kW	1.4 l	04/96→08/01								KH20034 ProKIT
1.6 16V (178DXD1A)	74 kW	1.6 l	06/96→02/01								KH20047 ProKIT
1.7 TD	51 kW	1.7 l	04/96→03/01								
1.2	54 kW	1.2 l	06/98→								KH10387 ProKIT
1.6 16V	76 kW	1.6 l	02/01→01/12								KH10378 ProKIT
1.9 D	46 kW	1.9 l	03/01→								KH20022 ProKIT
											KH20047 ProKIT
											KH20034 ProKIT
1.2 (178DYA1A, 178DXS1A)	44 kW	1.2 l	07/97→10/04								KH10378 ProKIT
1.4	51 kW	1.4 l	04/96→10/02								KH10387 ProKIT
1.6 16V	74 kW	1.6 l	04/96→10/02								KH20022 ProKIT
											KH20047 ProKIT
											KH20034 ProKIT
<b>FIAT - PANDA (141_) 10/80→07/04</b>											
1000	32 kW	1 l	01/86→04/92								KH30113 ProKIT
1000 i.e. Cat	33 kW	1 l	10/87→08/98								KH20091 ProKIT
1100	37 kW	1.1 l	05/91→12/99								
1100	40 kW	1.1 l	02/95→09/03								
1300 D	27 kW	1.3 l	04/86→12/92								
750	25 kW	0.8 l	01/86→10/03								
900	29 kW	0.9 l	04/92→12/96								
1000	37 kW	1 l	01/85→12/92								KH20091 ProKIT
650	22 kW	0.65 l	01/82→07/04								
950	35 kW	0.9 l	09/82→08/83								
1000 4x4	32 kW	1 l	01/86→07/89								KH30113 ProKIT
1000 4x4	33 kW	1 l	05/86→12/94								
1000 4x4	37 kW	1 l	01/86→12/92								
1100 4x4	40 kW	1.1 l	02/95→07/04								
1100 Trekking 4x4	37 kW	1.1 l	10/91→07/04								
950 4x4	35 kW	1 l	09/83→12/86								
800	25 kW	0.8 l	02/81→12/85								KH30113 ProKIT
900	33 kW	0.9 l	10/80→06/94								
<b>FIAT - PANDA (169_) 09/03→08/13</b>											
1.1 (169.AXA1A)	40 kW	1.1 l	09/03→								KH10111 ProKIT
1.2 (169.AXB11, 169.AXB1A)	44 kW	1.2 l	09/03→								KH10217 ProKIT
											KH20034 ProKIT
											KH20022 ProKIT

































				    	
<b>FIAT - PANDA (169_)</b>				<b>09/03→08/13</b>	
1.2 (169AXF2A, 169AXF1A)	51 kW	1.2 l	03/10→08/13	 ; ABS	KH10111 ProKIT
				 ; ABS	KH20022 ProKIT
1.2 4x4 (169.AXB2A)	44 kW	1.2 l	10/04→		KH10065 ProKIT
1.2 4x4 (169AXF2A, 169AXF1A)	51 kW	1.2 l	04/10→08/13		KH10111 ProKIT
1.3 D Multijet 4x4 (169.AXC2A)	51 kW	1.3 l	10/04→		
1.3 JTD Multijet 4x4 (169AXG1A, 169AXG2A)	55 kW	1.3 l	09/10→08/13		
1.2 LPG (169.AXB1A)	44 kW	1.2 l	04/09→	 ; ABS	KH10111 ProKIT
				 ; ABS	KH10217 ProKIT
				 ; ABS	KH20022 ProKIT
1.2 LPG (169CXF1A)	51 kW	1.2 l	11/10→08/13	 ; ABS	KH10217 ProKIT
				 ; ABS	KH20022 ProKIT
1.2 Natural Power (169.AXB1A)	44 kW	1.2 l	01/07→12/11		KH10065 ProKIT
1.4 Natural Power (169AXH1A)	57 kW	1.4 l	09/10→08/13	 ; ABS	KH20022 ProKIT
1.3 D Multijet (169.AXC1A)	51 kW	1.3 l	09/03→		KH10065 ProKIT
1.3 D Multijet (169AXG1A, 169AXD1A)	55 kW	1.3 l	06/06→08/13	 ; -> 12/09; ABS	KH20034 ProKIT
1.4 (169AXE1B)	74 kW	1.4 l	10/06→	 ; ABS	KH20022 ProKIT
<b>FIAT - PANDA (312_, 319_)</b>				<b>02/12→</b>	
0.9 (312PXG1A)	63 kW	0.9 l	02/12→		KH10065 ProKIT
0.9 (312PXH1A)	48 kW	0.9 l	02/12→		KH20022 ProKIT
0.9 (312PXN1A, 312PXN11)	59 kW	0.9 l	12/13→		
0.9 (312PXP1A)	44 kW	0.9 l	12/13→		
0.9 Natural Power (312PXG1A, 312PYC1A)	63 kW	0.9 l	07/12→		
0.9 Natural Power (312PXN1A)	59 kW	0.9 l	01/15→		
1.3 D Multijet (312PXL1A)	55 kW	1.3 l	02/12→		
1.3 D Multijet (312PXU1A, 312PXW1A)	70 kW	1.3 l	04/15→		
0.9 (312PXN1A, 312PXN11)	57 kW	0.9 l	02/12→		KH20022 ProKIT
1.2 (312PXA1A)	51 kW	1.2 l	02/12→		
1.2 LPG (312PXA1A)	51 kW	1.2 l	06/12→		
0.9 4x4 (312PXG1A)	63 kW	0.9 l	09/12→		KH10065 ProKIT
0.9 4x4 (312PXR2B)	66 kW	0.9 l	06/14→		
1.3 D Multijet 4x4 (312PXL1A)	55 kW	1.3 l	06/12→		
1.3 D Multijet 4x4 (312PXS2A)	59 kW	1.3 l	06/14→		
1.3 D Multijet 4x4 (312PXU1A)	70 kW	1.3 l	04/15→		
<b>FIAT - PANDA Hatchback Van (141_)</b>				<b>01/86→02/04</b>	
1000	32 kW	1 l	01/86→02/92		KH30113 ProKIT
1000 i.e	33 kW	1 l	08/92→02/04		KH20091 ProKIT
750	25 kW	0.8 l	01/86→07/92		
<b>FIAT - PANDA Hatchback Van / PANDA VAN (169_, 312_, 519_)</b>				<b>03/04→</b>	
0.9 (312CXH1A, 312DXH1A)	48 kW	0.9 l	02/12→		KH10065 ProKIT
0.9 Natural Power (312DXG1A)	63 kW	0.9 l	07/12→		KH20022 ProKIT
1.3 D Multijet (312CXL1A, 312DXL1A)	55 kW	1.3 l	02/12→		
0.9 4x4 (312CXG2B)	63 kW	0.9 l	09/12→		KH10065 ProKIT
1.2 4x4	44 kW	1.2 l	09/04→		
1.3 D Multijet 4x4	51 kW	1.3 l	10/04→12/06		
1.3 D Multijet 4x4	55 kW	1.3 l	01/06→		
1.1 (169CXA1A)	40 kW	1.1 l	09/04→	 ; ABS	KH10217 ProKIT
1.2	44 kW	1.2 l	09/04→	 ; -> 12/09; ABS	KH20034 ProKIT
				 ; ABS	KH20022 ProKIT
1.2 (312CXA1A, 312DXA1A)	51 kW	1.2 l	02/12→		KH20022 ProKIT
1.2 LPG (312CXA1A)	51 kW	1.2 l	06/12→		
1.2 LPG	44 kW	1.2 l	04/09→	 ; ABS	KH10217 ProKIT
				 ; ABS	KH20022 ProKIT
1.2 LPG	51 kW	1.2 l	09/10→	 ; ABS	KH10217 ProKIT
1.2 Natural Power	44 kW	1.2 l	01/07→11/09		KH10065 ProKIT
1.4 Natural Power	57 kW	1.4 l	10/09→	 ; ABS	KH20022 ProKIT
1.3 D Multijet	51 kW	1.3 l	03/04→		KH10065 ProKIT
				 ; -> 12/09; ABS	KH20034 ProKIT
					KH20022 ProKIT
1.3 D Multijet	55 kW	1.3 l	01/06→		KH10065 ProKIT
				 ; -> 12/09; ABS	KH20034 ProKIT
				 ; ABS	KH20022 ProKIT

				13		i		
<b>FIAT - PUNTO (176_)</b>							<b>09/93→09/99</b>	
1.2 16V	63 kW	1.2 l	04/97→09/99		ABS	KH10044 ProKIT		
1.6	65 kW	1.6 l	01/94→04/97		ABS	KH20034 ProKIT		
1.7 D	42 kW	1.7 l	04/94→09/97		ABS	KH20047 ProKIT		
1.7 TD (176AT)	46 kW	1.7 l	09/96→09/99		ABS	KH20047 ProKIT		
60 1.2	43 kW	1.2 l	01/94→09/99					
75 1.2	54 kW	1.2 l	10/93→09/99					
1.4 GT Turbo (176AD_)	98 kW	1.4 l	10/93→03/97		ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
1.4 GT Turbo (176AS_)	96 kW	1.4 l	09/96→07/99			KH10181 ProKIT		
					ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
1.7 TD	51 kW	1.7 l	01/94→09/99		ABS	KH10044 ProKIT		
						KH10181 ProKIT		
					ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
1.7 TD	52 kW	1.7 l	01/94→09/99		> 04/97	KH10181 ProKIT		
					ABS	KH10044 ProKIT		
					ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
55 1.1	40 kW	1.1 l	09/93→09/99			KH10407 ProKIT		
					ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
60 1.2 (176AP, 176AR, 176AQ, 176BB)	44 kW	1.2 l	09/93→09/99		05/94 >	KH10181 ProKIT		
					ABS	KH10044 ProKIT		
					ABS	KH20034 ProKIT		
					ABS	KH20047 ProKIT		
<b>FIAT - PUNTO (188_)</b>							<b>09/99→03/12</b>	
1.2 16V 80 (188.233, .235, .253, .255, .333, .353, .639, ...)	59 kW	1.2 l	09/99→04/06		ABS	KH10043 ProKIT		
					ABS	KH10044 ProKIT		
1.2 60 (188.030, .050, .130, .150, .230, .250)	44 kW	1.2 l	09/99→12/10		ABS	KH20022 ProKIT		
					ABS	KH20034 ProKIT		
1.2 Bifuel	44 kW	1.2 l	08/07→03/12					
1.2 Natural Power	44 kW	1.2 l	09/03→03/12					
1.4	70 kW	1.4 l	09/03→03/12					
1.9 DS 60 (188.031, .051, .231, .251)	44 kW	1.9 l	09/99→03/12					
1.3 JTD 16V	51 kW	1.3 l	06/03→03/12		ABS	KH10065 ProKIT		
1.8 130 HGT (188.738, .718)	96 kW	1.8 l	09/99→03/12		ABS	KH20022 ProKIT		
					ABS	KH20034 ProKIT		
1.4 (188AXM1A, 188BXM1A)	71 kW	1.4 l	11/05→03/12		ABS	KH10043 ProKIT		
					ABS	KH10044 ProKIT		
					ABS	KH20034 ProKIT		
1.9 JTD 1.9 JTD 80 (188.237, .257, .337, .357)	63 kW	1.9 l	10/01→03/12		> 06/03; ABS	KH10181 ProKIT		
					ABS	KH10065 ProKIT		
					ABS	KH20022 ProKIT		
					ABS	KH20034 ProKIT		
1.9 JTD	74 kW	1.9 l	06/03→03/12		07/03 >; ABS	KH10181 ProKIT		
					ABS	KH10065 ProKIT		
					ABS	KH20022 ProKIT		
					ABS	KH20034 ProKIT		
<b>FIAT - PUNTO (199_)</b>							<b>06/05→</b>	
0.9	74 kW	0.9 l	12/13→			KH20037 ProKIT		
0.9	77 kW	0.9 l	07/13→					
0.9 Bifuel	63 kW	0.9 l	03/12→					
0.9 Twinair Turbo	63 kW	0.9 l	03/12→					
1.2	48 kW	1.2 l	10/05→					
1.2	51 kW	1.2 l	09/10→					
1.2 (199AXZ1A, 199BXZ1A)	51 kW	1.2 l	03/12→					
1.2 (199AYL1A, 199BYL1A)	49 kW	1.2 l	02/14→					
1.2 LPG (199BXA1A, 199AXA1A)	51 kW	1.2 l	06/08→12/12					
1.3 D Multijet	56 kW	1.3 l	06/09→07/14					
1.3 D Multijet	62 kW	1.3 l	04/10→					
1.3 JTD Multijet (199.AYR1A, 199.BYR1A)	66 kW	1.3 l	05/18→					





























































































































    					
<b>FIAT - PUNTO (199_)</b>				<b>06/05→</b>	
1.4 (199AXB11, 199AXB1A, 199BxB1A, 199AXL1A)	57 kW	1.4 l	06/05→12/15		<b>KH20037</b> ProKIT
1.4 (199AXB1A, 199BxB1A, 199BxB11, 199AXB11)	57 kW	1.4 l	03/12→		
1.4 (199AXB1A)	55 kW	1.4 l	10/05→07/07		
1.4 (199AXH1A, 199BxH1A)	55 kW	1.4 l	03/12→		
1.4 16V	112 kW	1.4 l	09/07→07/12		
1.4 16V (199BxG1B, 199AXG1B)	70 kW	1.4 l	10/05→08/11		
1.4 Bifuel	57 kW	1.4 l	03/12→		
1.4 LPG	57 kW	1.4 l	12/08→		
1.4 Multi Air	77 kW	1.4 l	03/12→		
1.4 Natural Power	57 kW	1.4 l	07/08→		
1.4 Natural Power	57 kW	1.4 l	03/12→		
1.3 D Multijet	51 kW	1.3 l	07/08→		<b>KH10065</b> ProKIT
1.3 D Multijet	55 kW	1.3 l	10/05→		
1.3 D Multijet	55 kW	1.3 l	03/12→		<b>KH20037</b> ProKIT
1.3 D Multijet	59 kW	1.3 l	12/13→		
1.3 D Multijet	62 kW	1.3 l	03/12→		
1.3 D Multijet	70 kW	1.3 l	03/12→		
1.3 D Multijet (199.AXD11, 199.AXD1A, 199.AXD1B,...)	66 kW	1.3 l	10/05→12/10		
1.4 T-Jet (199AXM1A, 199BXM1A, 199BXN1A)	88 kW	1.4 l	09/07→		
1.4 Turbo Multi Air	99 kW	1.4 l	03/12→		
1.6 D Multijet	88 kW	1.6 l	07/08→		
1.9 D Multijet	85 kW	1.9 l	06/06→12/09		
1.9 D Multijet	88 kW	1.9 l	10/05→		
1.9 D Multijet	96 kW	1.9 l	10/05→		
<b>FIAT - PUNTO Convertible (176_)</b>				<b>04/94→06/00</b>	
60 1.2	43 kW	1.2 l	04/94→06/00		<b>KH10044</b> ProKIT
85 16V 1.2	63 kW	1.2 l	04/97→06/00		<b>KH20034</b> ProKIT
90 1.6	65 kW	1.6 l	04/94→04/97		<b>KH20047</b> ProKIT
60 1.2 (176AR_, 176BR_)	44 kW	1.2 l	05/95→06/00	 : <b>06/95 -&gt; 09/99</b>	<b>KH10181</b> ProKIT
					<b>KH10044</b> ProKIT
					<b>KH20034</b> ProKIT
					<b>KH20047</b> ProKIT
<b>FIAT - PUNTO EVO / PUNTO EVO Hatchback Van (199_)</b>				<b>07/08→02/12</b>	
1.2	48 kW	1.2 l	10/09→02/12		<b>KH20037</b> ProKIT
1.2	51 kW	1.2 l	10/09→02/12		
1.3 D Multijet (199.AXT1A, 199.AXC1A)	55 kW	1.3 l	03/09→02/12		
1.3 D Multijet (199.AXU1A)	70 kW	1.3 l	03/09→02/12		
1.3 D Multijet (199BXC1A)	56 kW	1.3 l	09/10→		
1.3 D Multijet (199CXD1B, 199CXD1A)	66 kW	1.3 l	03/09→02/12		
1.4 (199.AXB1A)	57 kW	1.4 l	03/09→02/12		
1.4 (199AXB1A)	57 kW	1.4 l	10/09→02/12		
1.4 (199AXH1A)	55 kW	1.4 l	07/09→02/12		
1.4 16V	77 kW	1.4 l	10/09→02/12		
1.4 LPG	57 kW	1.4 l	06/09→02/12		
1.4 Natural Power	57 kW	1.4 l	10/09→02/12		
1.3 D Multijet	51 kW	1.3 l	07/08→02/12		<b>KH10065</b> ProKIT
1.3 D Multijet	62 kW	1.3 l	10/09→02/12		
1.3 D Multijet	70 kW	1.3 l	10/09→02/12		<b>KH20037</b> ProKIT
1.3 D Multijet (199AXC1A, 199BXC1A, 199AXT1A, 199BXT1A)	55 kW	1.3 l	10/09→02/12		
1.3 D Multijet (199AXD1B, 199AXD1A, 199BXD1B, 199BXD1A,...)	66 kW	1.3 l	10/09→02/12		
1.4 16V (199AXW1A)	99 kW	1.4 l	10/09→02/12		
1.6 D Multijet	88 kW	1.6 l	10/09→02/12		
<b>FIAT - PUNTO Hatchback Van (188_)</b>				<b>02/00→10/09</b>	
1.2 60	44 kW	1.2 l	02/00→10/09		<b>KH10043</b> ProKIT
1.9 D 60	44 kW	1.9 l	02/00→10/09		<b>KH10044</b> ProKIT
					<b>KH20022</b> ProKIT
					<b>KH20034</b> ProKIT
1.3 JTD	51 kW	1.3 l	06/03→10/05		<b>KH10065</b> ProKIT
					<b>KH20022</b> ProKIT
					<b>KH20034</b> ProKIT



												
<b>FIAT - PUNTO Hatchback Van (188_)</b>											<b>02/00→10/09</b>	
1.9 JTD	63 kW	1.9 l	02/00→10/09		10/01 → 06/03;	ABS						KH10181 ProKIT
					ABS						KH10065 ProKIT	
					ABS						KH20022 ProKIT	
					ABS						KH20034 ProKIT	
<b>FIAT - PUNTO Hatchback Van (199_)</b>											<b>04/08→</b>	
0.9 Twinair Turbo	63 kW	0.9 l	03/12→							KH20037 ProKIT		
1.4 (199BxB1A, 199AXL1A, 199AXB1A)	57 kW	1.4 l	03/12→									
1.4 LPG (199AXB1A, 199BxB1A, 199AXL1A)	57 kW	1.4 l	03/12→02/12									
1.4 Natural Power (199AXB1A, 199AXL1A)	57 kW	1.4 l	03/09→									
1.3 D Multijet	55 kW	1.3 l	04/08→							KH10065 ProKIT		
1.3 D Multijet	62 kW	1.3 l	03/12→							KH20037 ProKIT		
1.3 D Multijet	70 kW	1.3 l	03/09→									
<b>FIAT - PUNTO Van (176_)</b>											<b>04/96→02/00</b>	
1.1	40 kW	1.1 l	04/96→02/00							KH10407 ProKIT		
					ABS						KH20034 ProKIT	
					ABS						KH20047 ProKIT	
1.7 D	42 kW	1.7 l	04/96→02/00		ABS						KH20034 ProKIT	
					ABS						KH20047 ProKIT	
1.7 TD	46 kW	1.7 l	09/96→09/99		ABS						KH20034 ProKIT	
1.7 TD	52 kW	1.7 l	04/96→02/00		-> 09/99						KH10181 ProKIT	
					ABS						KH20034 ProKIT	
					ABS						KH20047 ProKIT	
<b>FIAT - QUBO (225_)</b>											<b>02/08→</b>	
1.3 D Multijet (225AXE1A, 225CXE1A, 225AXH1A, 225AXL1A,...)	70 kW	1.3 l	07/10→							KH10065 ProKIT		
										KH20022 ProKIT		
1.3 D Multijet (225AXG1A, 225CXG1A, 225AXG11, 225CXG11)	59 kW	1.3 l	03/15→									
1.3 D Multijet (225CXB1A, 225AXB1A, 225CXB11, 225AXB11,...)	55 kW	1.3 l	02/08→									
1.4 (225AXA1A, 225CXA1A)	57 kW	1.4 l	10/09→							KH20022 ProKIT		
1.4 (225AXA1A)	54 kW	1.4 l	02/08→									
1.4 Natural Power (225AXC1A)	57 kW	1.4 l	10/09→									
<b>FIAT - REGATA Sedan (138_)</b>											<b>09/83→12/90</b>	
100 Super 1.6	70 kW	1.6 l	10/83→07/89							KH20091 ProKIT		
100 Super 1.6	74 kW	1.6 l	10/83→12/90									
60 Diesel 1.7	43 kW	1.7 l	09/83→12/86									
60 Diesel 1.7	44 kW	1.7 l	05/85→03/89									
65 Diesel 1.9	48 kW	1.9 l	04/84→07/89									
70 1.3	48 kW	1.3 l	09/83→07/89									
70 1.3	50 kW	1.3 l	09/83→07/86									
75 1.5	55 kW	1.5 l	12/83→07/89									
80 Turbo Diesel 1.9	59 kW	1.9 l	05/86→07/89									
85 1.5	58 kW	1.5 l	05/85→12/87									
85 1.6	60 kW	1.6 l	10/83→06/90									
85 Super 1.5	60 kW	1.5 l	09/83→04/85									
90 i.e. 1.6	66 kW	1.6 l	01/87→07/89									
<b>FIAT - RITMO (138_)</b>											<b>01/78→12/87</b>	
1.0	44 kW	1 l	09/78→09/82							KH20091 ProKIT		
1.1	40 kW	1.1 l	10/82→12/87									
1.1	43 kW	1.1 l	04/85→12/87									
1.3	48 kW	1.3 l	01/78→08/85									
1.3	55 kW	1.3 l	01/81→09/82									
1.5	58 kW	1.5 l	08/85→05/87									
1.5	60 kW	1.5 l	01/83→12/87									
1.5	63 kW	1.5 l	01/81→05/87									
1.6	66 kW	1.6 l	12/85→12/87									
1.6	77 kW	1.6 l	05/81→12/87									
1.7 Diesel	40 kW	1.7 l	10/79→09/82									
1.7 Diesel	44 kW	1.7 l	05/85→12/87									
1.9 TD	59 kW	1.9 l	12/85→12/87									
1.3	50 kW	1.3 l	01/83→04/85		-> 12/83						KH20091 ProKIT	
1.6	74 kW	1.6 l	01/83→12/87		-> 05/84						KH20091 ProKIT	



										
<b>FIAT - RITMO III (198_)</b>										<b>11/06→12/14</b>
1.4 (198AXA1B)	66 kW	1.4 l	04/07→12/14							<b>KH10151</b> ProKIT
1.4 16V (198AXS1B)	103 kW	1.4 l	04/10→12/14							<b>KH20022</b> ProKIT
1.4 T-Jet (198AXF1B)	110 kW	1.4 l	09/07→12/14							
1.4 T-Jet (198AXG1B)	88 kW	1.4 l	10/07→12/14							
1.6 D Multijet (198AXH1B)	77 kW	1.6 l	09/07→12/14							
1.6 D Multijet (198AXL1B)	88 kW	1.6 l	03/08→12/14							
1.9 D Multijet (198AXB1A)	88 kW	1.9 l	04/07→12/14							
1.4 LPG (198AXA1B)	66 kW	1.4 l	12/08→12/14							<b>KH20022</b> ProKIT
1.6 D Multijet (198AXM1B)	66 kW	1.6 l	03/08→12/14							
1.9 D Multijet (198AXD1A)	85 kW	1.9 l	11/06→12/09							
1.9 D Multijet (198AXE1A)	66 kW	1.9 l	04/07→12/08							
1.9 D Multijet (198AXC1B)	110 kW	1.9 l	04/07→12/14							<b>KH10198</b> ProKIT
2.0 D Multijet (198AXN1B)	121 kW	2 l	09/08→12/14							<b>KH20022</b> ProKIT
2.0 D Multijet (198AXPIB)	120 kW	2 l	09/08→12/14							
<b>FIAT - RITMO Convertible (138_)</b>										<b>01/80→07/89</b>
100 1.6	74 kW	1.6 l	10/85→12/87							<b>KH20091</b> ProKIT
100 1.6	77 kW	1.6 l	10/85→12/87							
50 1.3	50 kW	1.3 l	10/85→12/87							
85 1.5	60 kW	1.5 l	03/83→12/86							
85 1.5	63 kW	1.5 l	01/80→07/89							
<b>FIAT - SCUDO Bus (220_)</b>										<b>02/96→12/06</b>
1.6	58 kW	1.6 l	02/96→12/06							<b>KH10089</b> ProKIT
1.9 TD	68 kW	1.9 l	02/96→12/06							<b>KH20095</b> ProKIT
1.9 TD Eco	66 kW	1.9 l	02/96→12/06							
1.9 D	51 kW	1.9 l	02/96→04/98							<b>KH10089</b> ProKIT
2.0 JTD	69 kW	2 l	01/04→12/06							<b>KH20095</b> ProKIT
1.9 D	51 kW	1.9 l	04/98→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
2.0 16V	100 kW	2 l	06/00→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
2.0 JTD	80 kW	2 l	12/99→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
2.0 JTD 16V	80 kW	2 l	05/99→12/06							<b>KH10089</b> ProKIT
<b>FIAT - SCUDO Bus / SCUDO Platform/Chassis (270_, 272_)</b>										<b>01/07→03/16</b>
1.6 D Multijet	66 kW	1.6 l	01/07→03/16							<b>KH10119</b> ProKIT
1.6 D Multijet	66 kW	1.6 l	02/11→03/16							<b>KH30015</b> ProKIT
2.0 D Multijet	88 kW	2 l	01/07→03/16							<b>KH30016</b> ProKIT
2.0 D Multijet	94 kW	2 l	04/11→03/16							
2.0 D Multijet	94 kW	2 l	05/11→03/16							
2.0 D Multijet	100 kW	2 l	01/07→03/16							
2.0 D Multijet	120 kW	2 l	07/10→03/16							
<b>FIAT - SCUDO Van (220_)</b>										<b>02/96→12/06</b>
1.6	58 kW	1.6 l	02/96→12/06							<b>KH10089</b> ProKIT
1.9 TD	66 kW	1.9 l	02/96→12/06							<b>KH20095</b> ProKIT
1.9 D	51 kW	1.9 l	02/96→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
1.9 D	51 kW	1.9 l	04/98→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
1.9 TD	68 kW	1.9 l	02/98→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
										
2.0	100 kW	2 l	05/00→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
2.0 JTD	69 kW	2 l	10/99→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
2.0 JTD	80 kW	2 l	12/02→12/06							<b>KH10089</b> ProKIT
										<b>KH20095</b> ProKIT
2.0 JTD 16V	80 kW	2 l	05/99→12/06							<b>KH10089</b> ProKIT
<b>FIAT - SCUDO Van (270_, 272_)</b>										<b>01/07→03/16</b>
1.6 D Multijet	66 kW	1.6 l	01/07→03/16							<b>KH10119</b> ProKIT
1.6 D Multijet	66 kW	1.6 l	02/11→03/16							<b>KH30015</b> ProKIT
2.0 D Multijet	88 kW	2 l	01/07→03/16							<b>KH30016</b> ProKIT
2.0 D Multijet	94 kW	2 l	05/11→03/16							
2.0 D Multijet	100 kW	2 l	01/07→03/16							
2.0 D Multijet	120 kW	2 l	07/10→03/16							

										
<b>FIAT - SEDICI (189_)</b>										<b>06/06→10/14</b>
1.6 16V	79 kW	1.6 l	06/06→10/14							KH10022 ProKIT
1.6 16V	88 kW	1.6 l	06/06→10/14							KH30108 ProKIT
1.9 D Multijet	88 kW	1.9 l	06/06→10/11							
2.0 D Multijet	99 kW	2 l	06/06→10/14							
1.6 16V 4x4	79 kW	1.6 l	06/06→10/14							KH10022 ProKIT
1.9 D Multijet 4x4	88 kW	1.9 l	06/06→10/11						-> 06/09	KH30075 ProKIT
1.6 16V 4x4	88 kW	1.6 l	06/06→10/14							KH10022 ProKIT
2.0 D Multijet 4x4	99 kW	2 l	06/06→10/14							
<b>FIAT - SEICENTO / 600 (187_)</b>										<b>11/97→01/10</b>
0.9 (187AXA, 187AXA1A)	29 kW	0.9 l	11/97→12/08						ABS	KH10111 ProKIT
1.1 (187AXB, 187AXB1A, 187AXC1A02)	40 kW	1.1 l	01/98→01/10						ABS	KH10217 ProKIT
									-> 12/98	KH20091 ProKIT
Elektra (187AEA1A, 187BEA1A)	30 kW		01/99→01/05						ABS	KH10217 ProKIT
<b>FIAT - SIENA (178_, 172_)</b>										<b>04/96→12/12</b>
1.0 Flex	48 kW	1 l	09/00→12/09						09/01 ->; ABS	KH20022 ProKIT
1.3	59 kW	1.3 l	09/01→12/09						ABS	KH10378 ProKIT
1.3 (178CXS1AAI, 178BYA1AAT, 178CYA1AAT)	44 kW	1.3 l	09/01→12/12						ABS	KH20022 ProKIT
1.4	57 kW	1.4 l	01/07→12/09							
1.3 (178CXG1AAM, 178CXG1AAP, 178CXG1AAT)	54 kW	1.3 l	09/98→12/02						ABS; 09/01 ->	KH10378 ProKIT
									09/01 ->; ABS	KH10387 ProKIT
									09/01 ->; ABS	KH20022 ProKIT
									-> 09/01; ABS	KH20047 ProKIT
1.3 JTD	51 kW	1.3 l	09/03→12/09						ABS	KH10065 ProKIT
									ABS	KH10181 ProKIT
									ABS	KH20022 ProKIT
1.4	51 kW	1.4 l	04/96→12/09						09/01 -> 01/05; ABS	KH10387 ProKIT
1.4 Cat	51 kW	1.4 l	04/96→12/09						ABS; 09/01 ->	KH10378 ProKIT
1.6 16V	74 kW	1.6 l	09/98→12/09						09/01 ->; ABS	KH20022 ProKIT
									-> 09/01; ABS	KH20047 ProKIT
									ABS	KH20022 ProKIT
1.5	62 kW	1.5 l	06/04→12/09						ABS	KH20022 ProKIT
1.5 Bipower	57 kW	1.5 l	09/03→12/05							
1.7 TD	51 kW	1.7 l	02/06→12/09							
1.8 Bipower	81 kW	1.8 l	06/04→12/09							
1.6 (178CYC1AAT)	76 kW	1.6 l	11/00→12/12						ABS; 09/01 ->	KH10378 ProKIT
									-> 09/01; ABS	KH20047 ProKIT
									ABS	KH20022 ProKIT
<b>FIAT - STILO (192_)</b>										<b>10/01→04/07</b>
1.2 16V (192_XA1B)	59 kW	1.2 l	02/02→11/06						ABS	KH10043 ProKIT
										KH20022 ProKIT
1.4 16V	66 kW	1.4 l	03/05→11/06							KH10151 ProKIT
1.6 16V	77 kW	1.6 l	05/05→11/06							KH20022 ProKIT
1.6 16V (192_XB1A)	76 kW	1.6 l	10/01→11/06							
1.8 16V (192AXC1A, 192BXC1A)	98 kW	1.8 l	10/01→04/07							
1.9 D Multijet	74 kW	1.9 l	09/05→11/06							
1.9 D Multijet	88 kW	1.9 l	09/05→11/06							
1.9 JTD (192_XE1A)	85 kW	1.9 l	10/01→11/06							
1.9 JTD (192_XF1A)	59 kW	1.9 l	02/02→11/06							
1.4 16V (192AXH1B, 192BXH1B)	70 kW	1.4 l	10/03→12/06							KH10151 ProKIT
										KH20022 ProKIT
									VIN 594432 ->	KH20082 ProKIT
1.6	100 kW	1.6 l	04/05→11/06							KH20022 ProKIT
1.9 D Multijet	110 kW	1.9 l	09/05→11/06							
1.9 JTD (192AXS1B, 192BXS1B)	66 kW	1.9 l	09/04→11/06							
1.9 JTD	93 kW	1.9 l	09/03→11/06							KH10198 ProKIT
1.9 JTD	100 kW	1.9 l	04/04→11/06							KH20022 ProKIT
1.9 JTD	103 kW	1.9 l	01/04→11/06							
2.4 20V (192_XD1A, 192AXD12)	125 kW	2.4 l	10/01→04/07							
<b>FIAT - STILO Multi Wagon (192_)</b>										<b>01/03→08/08</b>
1.4 16V	66 kW	1.4 l	03/05→08/08						-> 03/08	KH10151 ProKIT
1.9 D	66 kW	1.9 l	09/04→08/08						VIN -> 0594431	KH20130 ProKIT
1.4 16V	70 kW	1.4 l	01/04→08/08						-> 03/08	KH10151 ProKIT
1.9 D Multijet	74 kW	1.9 l	09/05→08/08						VIN -> 0594431	KH20130 ProKIT
									VIN 594432 ->	KH20082 ProKIT



				13	i		
<b>FIAT - STILO Multi Wagon (192_)</b>						<b>01/03→08/08</b>	
1.6 16V	76 kW	1.6 l	01/03→08/08		-> 03/08	KH10151 ProKIT	
1.8 16V	98 kW	1.8 l	01/03→08/08		01/04 ->; VIN 594432 ->	KH20082 ProKIT	
1.9 JTD	85 kW	1.9 l	01/03→08/08		VIN -> 0594431	KH20130 ProKIT	
1.6 16V	77 kW	1.6 l	03/05→12/07		VIN -> 0594431	KH20130 ProKIT	
1.9 D Multijet	88 kW	1.9 l	09/05→08/08		-> 03/08	KH10151 ProKIT	
					03/06 ->; VIN 594432 ->	KH20082 ProKIT	
					VIN -> 0594431	KH20130 ProKIT	
1.9 D Multijet (192DXT1B)	110 kW	1.9 l	09/05→08/08		03/06 ->; VIN 594432 ->	KH20082 ProKIT	
					VIN -> 0594431	KH20130 ProKIT	
1.9 JTD	59 kW	1.9 l	01/03→08/08		-> 03/08	KH10151 ProKIT	
					01/04 -> 08/04; VIN 594432 ->	KH20082 ProKIT	
					VIN -> 0594431	KH20130 ProKIT	
1.9 JTD	93 kW	1.9 l	09/03→08/08			KH10198 ProKIT	
1.9 JTD	100 kW	1.9 l	04/04→08/08		VIN -> 0594431	KH20130 ProKIT	
1.9 JTD	103 kW	1.9 l	01/04→08/08			KH10198 ProKIT	
					VIN -> 0594431	KH20130 ProKIT	
					VIN 594432 ->	KH20082 ProKIT	
<b>FIAT - STRADA Pickup (178_, 278_)</b>						<b>06/99→12/06</b>	
1.2	44 kW	1.2 l	04/03→		-> 12/05; ABS	KH10163 ProKIT	
1.2	54 kW	1.2 l	06/99→12/06		ABS	KH10227 ProKIT	
1.3 D Multijet	62 kW	1.3 l	05/06→		06/06 ->; ABS	KH10181 ProKIT	
					ABS	KH10065 ProKIT	
1.3 D Multijet (278AYR1A)	70 kW	1.3 l	10/10→		ABS	KH10065 ProKIT	
1.7 TD	51 kW	1.7 l	06/99→12/06		11/05 ->; ABS	KH10387 ProKIT	
					-> 10/05; ABS	KH10163 ProKIT	
					-> 10/05; ABS	KH10227 ProKIT	
1.9 D	46 kW	1.9 l	12/00→		-> 12/05; ABS	KH10163 ProKIT	
					-> 12/05; ABS	KH10227 ProKIT	
1.9 JTD	59 kW	1.9 l	04/03→		-> 05/06; ABS	KH10181 ProKIT	
					ABS	KH10065 ProKIT	
<b>FIAT - TALENTO Bus / TALENTO Platform/Chassis / TALENTO Van (290_)</b>						<b>03/89→03/94</b>	
1.9 D (290UAK, 290UTK)	52 kW	1.9 l	03/89→03/94			KH00107 ProKIT	
1.9 D (290UEHK)	52 kW	1.9 l	03/89→03/94				
1.9 D (290UK)	52 kW	1.9 l	03/89→03/94				
2.0 (290U4)	55 kW	2 l	03/89→03/94				
2.0 (290UA4)	55 kW	2 l	03/89→03/94				
2.0 (290UEH4)	55 kW	2 l	03/89→03/94				
<b>FIAT - TEMPRA / TEMPRA S.W. (159_)</b>						<b>03/90→12/98</b>	
1.4 i.e. (159.AA)	57 kW	1.4 l	03/91→08/96		ABS	KH20034 ProKIT	
1.4 i.e. (159.AC)	57 kW	1.4 l	03/91→08/96				
1.6	51 kW	1.6 l	07/93→07/96				
1.6 (159AS, 159AT)	51 kW	1.6 l	04/90→07/96				
1.6 i.e. (159.AJ)	63 kW	1.6 l	06/94→08/96				
1.8 i.e. (159.AM)	81 kW	1.8 l	03/90→08/96				
1.8 i.e. (159.AN)	81 kW	1.8 l	03/90→08/96				
1.9 D (159.AG)	48 kW	1.9 l	07/91→08/96				
2.0	80 kW	2 l	04/90→06/93				
2.0	80 kW	2 l	04/91→06/93				
2.0	81 kW	2 l	05/94→12/98				
1.4 i.e. (159.AC, 159.AX)	51 kW	1.4 l	04/90→08/96			KH10373 ProKIT	
1.4 i.e. (159.AC, 159.AX)	51 kW	1.4 l	10/92→08/96		01/93 ->; ABS	KH20161 ProKIT	
					ABS	KH20034 ProKIT	
1.6	63 kW	1.6 l	12/90→04/93		AT; ABS	KH10373 ProKIT	
1.6 (159.AD)	63 kW	1.6 l	03/90→04/94		MT		
1.6 i.e. (159.AE)	57 kW	1.6 l	10/90→08/96		AT; ABS	KH10163 ProKIT	
1.6 i.e. (159.AS, 159.AT)	55 kW	1.6 l	06/92→08/96		01/93 ->; ABS	KH20161 ProKIT	
1.6 i.e. (159.AS, 159.AT)	55 kW	1.6 l	10/92→08/96		ABS	KH20034 ProKIT	
1.6 i.e. (159.AE)	57 kW	1.6 l	06/90→07/92		AT; ABS	KH10373 ProKIT	
					MT		
					AT; ABS	KH10163 ProKIT	
					ABS	KH20034 ProKIT	

FIAT - TEMPRA / TEMPRA S.W. (159_)				03/90→12/98	
1.6 i.e. (159.AJ)	66 kW	1.6 l	06/94→08/96	; AT; ABS	KH10373 ProKIT
				; MT	
				; AT; ABS	KH10163 ProKIT
				; ABS	KH20034 ProKIT
1.8 i.e. (159.AN)	77 kW	1.8 l	03/92→12/93	; -> 09/93	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
1.8 i.e. (159.AN)	77 kW	1.8 l	03/92→08/96	; 03/93 ->	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
1.8 i.e. (159.AV)	76 kW	1.8 l	09/93→08/96		KH10181 ProKIT
1.8 i.e. (159.AZ)	66 kW	1.8 l	09/93→08/96	; ABS	KH20034 ProKIT
1.9 TD (159.AI, 159.BI, 159.CU, 159.AU)	66 kW	1.9 l	07/91→02/95	; ABS	KH20161 ProKIT
1.9 TD (159.AQ)	59 kW	1.9 l	03/92→06/93		
1.9 TD (159.AQ)	59 kW	1.9 l	07/92→08/96		
1.9 TD (159.CU, 159.AU, 159.AI, 159.BI)	66 kW	1.9 l	05/90→08/96		
2.0 i.e. (159.AP)	83 kW	2 l	10/90→09/96		
1.8 i.e. (159.BY)	74 kW	1.8 l	10/94→08/96	; 01/95 ->	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
2.0 i.e. (159.AP)	83 kW	2 l	01/91→03/95	; -> 02/93	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
2.0 i.e. 4x4 (159.AP)	83 kW	2 l	03/92→03/95		KH10181 ProKIT
					KH10371 ProKIT
FIAT - TIPO (160_)				07/87→10/95	
1.1 (160.AA)	41 kW	1.1 l	01/88→10/91		KH10217 ProKIT
1.4 (160.AC)	52 kW	1.4 l	07/87→12/89	; ABS	KH20034 ProKIT
1.4 i.e.	57 kW	1.4 l	05/89→04/95		KH10217 ProKIT
1.4 i.e. (160.AP, 160.AD, 160.EA)	51 kW	1.4 l	05/89→04/95	; 03/93 ->; ABS	KH20161 ProKIT
				; ABS	KH20034 ProKIT
1.6	56 kW	1.6 l	03/93→10/95	; ABS	KH20034 ProKIT
1.6	58 kW	1.6 l	03/88→10/92		
1.6 SX DGT	66 kW	1.6 l	05/89→10/95		
1.7 D (160.AG)	45 kW	1.7 l	01/88→10/95		
1.9 D	48 kW	1.9 l	07/91→08/95		
2.0	85 kW	2 l	10/90→10/92		
2.0	101 kW	2 l	03/93→10/95		
1.6 (160.AE)	61 kW	1.6 l	01/88→10/91	; ABS	KH20034 ProKIT
1.6 i.e.	66 kW	1.6 l	02/88→05/91	; ABS; AT	KH20161 ProKIT
1.6 i.e. (160.AF)	57 kW	1.6 l	07/90→01/93		
1.6 i.e. (160.A1, 160.EC, 160.EB)	55 kW	1.6 l	10/92→04/95	; 03/93 ->; ABS; MT	KH20161 ProKIT
				; ABS; AT	
				; ABS	KH20034 ProKIT
1.7 D (160.AG)	43 kW	1.7 l	01/88→10/94	; 03/93 ->; ABS	KH20161 ProKIT
				; ABS	KH20034 ProKIT
1.8 i.e.	71 kW	1.8 l	03/93→04/95	; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT
1.8 i.e.	66 kW	1.8 l	09/93→04/95		KH10181 ProKIT
1.8 i.e. (160.ED)	76 kW	1.8 l	04/93→04/95	; ABS	KH20034 ProKIT
1.8 i.e. 16V Sport	100 kW	1.8 l	11/89→06/92		
1.9 TD (160.EL, 160.GL, 160.AQ, 160.EI, 160.AR)	66 kW	1.9 l	09/90→04/95	; ABS	KH20161 ProKIT
2.0 i.e. (160.AJ, 1607571)	80 kW	2 l	06/90→03/92		
2.0 i.e. 16V Sport (160.EF)	102 kW	2 l	03/93→04/95		
1.8 i.e.	81 kW	1.8 l	10/90→06/93	; -> 02/93	KH10181 ProKIT
1.8 i.e. (160.AY)	77 kW	1.8 l	10/90→06/93	; 03/93 ->; ABS	KH20161 ProKIT
				; ABS	KH20034 ProKIT
1.8 i.e. (160.EQ, 160.AM)	74 kW	1.8 l	10/94→10/95	; 01/95 ->	KH10181 ProKIT
				; ABS	KH20034 ProKIT
				; ABS	KH20161 ProKIT



<b>FIAT - TIPO (160_)</b>				<b>07/87→10/95</b>	
1.9 TD (160.AW)	59 kW	1.9 l	03/92→06/93	; -> 02/93	KH10181 ProKIT
2.0 16V (160.AV)	107 kW	2 l	07/91→04/95	;	KH20034 ProKIT
					KH20161 ProKIT
2.0 i.e. (160.AT, 160.AJ)	83 kW	2 l	03/90→04/95	; 06/90 ->	KH10181 ProKIT
					KH20034 ProKIT
					KH20161 ProKIT
<b>FIAT - ULYSSE (179_)</b>				<b>08/02→06/11</b>	
2.0 (179BXA11, 179BXA1A)	100 kW	2 l	08/02→06/11	; -> 12/07; VIN -> 10814	KH10132 ProKIT
2.0 D Multijet	88 kW	2 l	05/06→06/11	; -> 05/10	KH20055 ProKIT
2.0 D Multijet	100 kW	2 l	05/06→06/11		
2.0 JTD	79 kW	2 l	05/03→08/06	; VIN -> 10814	KH10132 ProKIT
2.0 JTD	80 kW	2 l	08/02→08/06		KH20055 ProKIT
2.2 JTD	94 kW	2.2 l	08/02→08/06		
2.2 D Multijet	125 kW	2.2 l	03/08→06/11	; -> 05/10	KH20055 ProKIT
3.0	150 kW	3 l	08/02→06/11		
<b>FIAT - ULYSSE (220_)</b>				<b>06/94→08/02</b>	
1.8 (220.BB5)	73 kW	1.8 l	05/97→08/02		KH10089 ProKIT
1.9 TD (220AH5)	66 kW	1.9 l	02/95→08/02		KH20095 ProKIT
2.0 (220.AC5)	89 kW	2 l	06/94→08/02		
2.0 16V (220AQ5)	100 kW	2 l	09/00→08/02		
2.0 JTD	80 kW	2 l	10/99→08/02		
2.0 Turbo (220.AD5)	108 kW	2 l	06/94→08/02		
2.1 TD	80 kW	2.1 l	03/96→10/99		
1.9 TD	68 kW	1.9 l	05/97→12/99		KH10089 ProKIT
2.0 JTD 16V	80 kW	2 l	05/99→08/02		
2.0 16V	97 kW	2 l	05/98→09/00		KH10089 ProKIT
				; 10/98 ->	KH20095 ProKIT
<b>FIAT - UNO (146_)</b>				<b>01/83→06/06</b>	
1.3 Super Diesel	33 kW	1.3 l	06/83→03/92		KH10369 ProKIT
45 0.9	33 kW	0.9 l	03/83→09/92		KH20091 ProKIT
45 1.0 (146A.ED)	32 kW	1 l	06/86→12/93		
60 1.1	42 kW	1.1 l	04/89→12/92		
70 1.3	48 kW	1.3 l	05/85→08/89		
70 1.3	50 kW	1.3 l	01/83→04/85		
1.3 Turbo i.e.	73 kW	1.3 l	01/87→12/87		KH20091 ProKIT
1.3 Turbo i.e.	74 kW	1.3 l	09/89→03/91		
1.3 Turbo i.e.	77 kW	1.3 l	04/85→08/89		
1.4 Turbo i.e.	82 kW	1.4 l	09/89→09/93		
1.4 Turbo i.e.	87 kW	1.4 l	12/89→12/96		
1.9 D	44 kW	1.9 l	09/89→03/94		
45 i.e. 1.0 (146E, 146A)	33 kW	1 l	10/84→10/95		
50 1.1	37 kW	1.1 l	01/86→12/89		
50 1.1	37 kW	1.1 l	01/90→12/93		
50 i.e. 1.1	36 kW	1.1 l	06/92→12/93		
60 Diesel 1.7	44 kW	1.7 l	07/86→08/89		
60 Diesel 1.7 (146E)	42 kW	1.7 l	09/89→12/93		
70 i.e. 1.4	51 kW	1.4 l	09/89→07/96		
70 i.e. 1.4	53 kW	1.4 l	09/89→12/93		
70 S 1.4	52 kW	1.4 l	10/88→06/06		
70 TD 1.4	52 kW	1.4 l	10/86→10/90		
55 1.1	40 kW	1.1 l	01/83→08/89	; -> 12/85	KH10369 ProKIT
					KH20091 ProKIT
60 1.1 (146A.EG)	43 kW	1.1 l	05/85→08/89	; 01/86 ->	KH10369 ProKIT
					KH20091 ProKIT
75 i.e. 1.5	55 kW	1.5 l	10/85→12/93	; 01/86 -> 12/88; VIN -> 631845	KH10369 ProKIT
					KH20091 ProKIT
<b>FIAT - X 1/9 (128_)</b>				<b>10/75→06/78</b>	
1.3	54 kW	1.3 l	10/75→06/78	; ; VIN 1045 -> VIN 6318	KH10369 ProKIT



**FORD - B-MAX (JK)**

10/12→

1.0 EcoBoost	74 kW	1 l	10/12→		KH10070 ProKIT
1.0 EcoBoost	88 kW	1 l	10/12→		
1.0 EcoBoost	92 kW	1 l	10/12→		
1.0 EcoBoost	103 kW	1 l	02/16→		
1.4	66 kW	1.4 l	10/12→		
1.4 LPG	64 kW	1.4 l	08/13→		
1.4 LPG	66 kW	1.4 l	08/13→		
1.5 TDCi	55 kW	1.5 l	10/12→		
1.5 TDCi	70 kW	1.5 l	04/15→		
1.6 TDCi	70 kW	1.6 l	10/12→		
1.6 Ti	77 kW	1.6 l	10/12→		

**FORD - CAPRI I / CAPRI II / CAPRI III (ECJ, GECP)**

12/68→04/87

1.3	40 kW	1.3 l	02/74→08/77		KH00008 ProKIT
1.3	40 kW	1.3 l	01/78→06/85		
1.3	42 kW	1.3 l	02/74→08/77		
1.6	50 kW	1.6 l	09/74→12/77		
1.6	53 kW	1.6 l	02/74→12/77		
1.6	54 kW	1.6 l	01/78→04/87		
1.6	65 kW	1.6 l	02/74→12/77		
1300	37 kW	1.3 l	12/68→12/72		
1300	39 kW	1.3 l	01/71→12/72		
1300	39 kW	1.3 l	01/71→12/73		
1300	40 kW	1.3 l	10/72→12/73		
1300	43 kW	1.3 l	01/73→12/73		
1500	44 kW	1.5 l	12/68→02/74		
1500	48 kW	1.5 l	12/68→02/74		
1600	53 kW	1.6 l	08/72→02/74		
1600	65 kW	1.6 l	08/72→02/74		
1600 GT	60 kW	1.6 l	01/69→10/72		
1700	55 kW	1.7 l	12/68→08/72		
2.0	64 kW	2 l	01/78→12/85		
2.0	66 kW	2 l	04/76→12/77		
2.0	66 kW	2 l	01/78→12/82		
2.0	74 kW	2 l	01/78→12/85		
2.3	79 kW	2.3 l	02/74→12/77		
2.3 Super	84 kW	2.3 l	06/79→12/85		
2.8 i Turbo	138 kW	2.8 l	01/82→04/87		
2.8 Super Injection	118 kW	2.8 l	01/81→04/87		
2000	63 kW	2 l	02/69→06/71		
2000	66 kW	2 l	02/69→02/74		
2300	79 kW	2.3 l	02/69→02/74		
2300	92 kW	2.3 l	08/69→02/74		
2600	92 kW	2.5 l	08/70→02/74		
2600 RS	110 kW	2.6 l	08/70→02/74		
3.0	101 kW	3 l	02/74→12/77		KH00023 ProKIT
3.0	101 kW	3 l	01/78→12/81		
3000	103 kW	3 l	08/72→02/74		

**FORD - C-MAX (DM2)**

02/07→09/10

1.6	74 kW	1.6 l	02/07→09/10		KH20020 ProKIT
1.6	85 kW	1.6 l	04/07→09/10		
1.6 TDCi	66 kW	1.6 l	02/07→09/10		KH30042 ProKIT
1.6 TDCi	74 kW	1.6 l	02/07→09/10		
1.6 TDCi	80 kW	1.6 l	02/07→09/10		
1.8	90 kW	1.8 l	02/07→09/10		
1.8	92 kW	1.8 l	02/07→09/10		
1.8 Flexifuel	92 kW	1.8 l	02/07→09/10		
1.8 TDCi	85 kW	1.8 l	02/07→09/10		
2.0	107 kW	2 l	02/07→09/10		
2.0 CNG	107 kW	2 l	04/09→09/10		
2.0 LPG	107 kW	2 l	06/08→09/10		
2.0 TDCi	81 kW	2 l	02/08→09/10		
2.0 TDCi	98 kW	2 l	02/07→09/10		
2.0 TDCi	100 kW	2 l	02/07→09/10		

**FORD - C-MAX II (DXA/CB7, DXA/CEU)**

04/10→06/19

1.0 EcoBoost	74 kW	1 l	10/12→06/19		KH10126 ProKIT
1.0 EcoBoost	92 kW	1 l	10/12→06/19		
1.5 EcoBoost	110 kW	1.5 l	03/15→06/19		
1.5 EcoBoost	134 kW	1.5 l	03/15→06/19		
1.5 TDCi	70 kW	1.5 l	03/15→06/19		
1.5 TDCi	88 kW	1.5 l	03/15→06/19		
1.5 TDCi ECOnetic	77 kW	1.5 l	03/15→06/19		
1.6 EcoBoost	110 kW	1.6 l	12/10→06/19		
1.6 EcoBoost	134 kW	1.6 l	12/10→06/19		
1.6 Flexifuel	88 kW	1.6 l	02/11→06/19		
1.6 LPG	86 kW	1.6 l	02/12→06/19		
1.6 LPG	88 kW	1.6 l	02/12→06/19		
1.6 TDCi	70 kW	1.6 l	12/10→06/19		



**FORD - C-MAX II (DXA/CB7, DXA/CEU)**

**04/10→06/19**

1.6 TDCi	85 kW	1.6 l	12/10→06/19		KH10126 ProKIT
1.6 Ti	63 kW	1.6 l	12/10→06/19		
1.6 Ti	77 kW	1.6 l	12/10→06/19		
1.6 Ti	88 kW	1.6 l	02/12→06/19		
1.6 Ti	92 kW	1.6 l	12/10→06/19		
2.0 TDCi	85 kW	2 l	02/11→06/19		
2.0 TDCi	100 kW	2 l	02/11→06/19		
2.0 TDCi	103 kW	2 l	04/10→06/19		
2.0 TDCi	110 kW	2 l	03/15→06/19		
2.0 TDCi	120 kW	2 l	12/10→06/19		
2.0 TDCi	125 kW	2 l	03/15→06/19		

**FORD - CONSUL / CONSUL Coupe / CONSUL Turnier (GGFL, GGCL, GGNL)**

**01/72→12/75**

1700	48 kW	1.7 l	01/72→12/75		KH00023 ProKIT
1700	55 kW	1.7 l	01/72→12/75		
2000	66 kW	2 l	09/74→12/75		
2000	73 kW	2 l	01/72→12/75		
2300	79 kW	2.3 l	01/72→12/75		
3000	101 kW	3 l	01/72→12/74		
3000	101 kW	3 l	01/72→12/75		
3000	101 kW	3 l	01/72→12/75		

**FORD - COUGAR (EC\_)**

**08/98→12/01**

2.0 16V	96 kW	2 l	08/98→12/01		KH10041 ProKIT
2.5 ST 200	151 kW	2.5 l	01/00→12/01		
2.5 V6 24V	125 kW	2.5 l	08/98→12/01		
2.5 V6 24V	125 kW	2.5 l	06/00→12/01		

**FORD - ECONOVAN / ECONOVAN Van (KBA, KCA, KAA)**

**03/86→03/92**

1.4	48 kW	1.4 l	03/86→03/92		KH00119 ProKIT
2.0 D	41 kW	2 l	03/86→03/92		

**FORD - ECOSPORT**

**01/03→**







1.0 EcoBoost	74 kW	1 l	04/18→		KH10070 ProKIT
1.0 EcoBoost	92 kW	1 l	10/13→		
1.0 EcoBoost	103 kW	1 l	03/16→		
1.4 TDCi	50 kW	1.4 l	01/03→05/11		
1.5 EcoBlue TDCi	70 kW	1.5 l	05/15→		
1.5 SE Direct Flex	101 kW	1.5 l	01/17→		
1.5 TDCi	66 kW	1.5 l	10/13→		
1.5 TDCi	67 kW	1.5 l	10/12→		
1.5 TDCi	74 kW	1.5 l	05/15→		
1.5 TDCi EcoBlue	88 kW	1.5 l	11/19→		
1.5 TDCi EcoBlue	92 kW	1.5 l	11/17→		
1.5 Ti	82 kW	1.5 l	10/13→		
1.5 Ti-VCT	81 kW	1.5 l	10/13→		
1.5 Ti-VCT	90 kW	1.5 l	01/18→		
1.6	72 kW	1.6 l	01/03→10/13		
1.6	81 kW	1.6 l	10/12→		
1.6	82 kW	1.6 l	10/07→10/13		
1.6 Flex	79 kW	1.6 l	02/10→07/12		
1.6 Flex	82 kW	1.6 l	06/05→01/10		
1.6 Flex	85 kW	1.6 l	08/12→07/17		
1.6 Flex	96 kW	1.6 l	08/15→07/17		
1.6 Ti-VCT	90 kW	1.6 l	08/12→		
2.0	101 kW	2 l	01/12→		
2.0	105 kW	2 l	01/12→		
2.0	108 kW	2 l	09/12→		
2.0 Flex	108 kW	2 l	08/12→07/17		

**FORD - ESCORT I / ESCORT I Turnier (AFH, ATH, ADH)**




























































**01/68→02/76**








1100	29 kW	1.1 l	06/68→06/71		KH00021 ProKIT
1100	33 kW	1.1 l	06/68→06/71		
1300	35 kW	1.3 l	06/68→06/71		
1300	38 kW	1.3 l	06/68→06/71		
1300 GT	47 kW	1.3 l	06/68→06/71		
950	25 kW	1 l	08/68→08/74		
950	26 kW	1 l	08/68→08/74		
1100	32 kW	1.1 l	01/68→12/74	; 12/74 →	KH00045 ProKIT
1100	32 kW	1.1 l	06/70→02/76	; → 11/74	
1100	35 kW	1.1 l	06/70→02/76		KH00021 ProKIT
1300	40 kW	1.3 l	09/73→02/76		
1300	42 kW	1.3 l	06/70→02/76		
1300	53 kW	1.3 l	06/70→02/76		













































     				03/73→07/81	
<b>FORD - ESCORT II / ESCORT II Turnier (ATH)</b>					
1.1	32 kW	1.1 l	12/74→08/80		KH00045 ProKIT
1.1	32 kW	1.1 l	04/75→08/80		
1.1	34 kW	1.1 l	06/75→08/80		
1.1	35 kW	1.1 l	12/74→08/80		
1.1	35 kW	1.1 l	04/75→08/80		
1.3	40 kW	1.3 l	12/74→08/80		
1.3	42 kW	1.3 l	12/74→08/80		
1.3	42 kW	1.3 l	04/75→08/80		
1.3	44 kW	1.3 l	03/79→08/80		
1.3	51 kW	1.3 l	12/74→08/80		
1.3 (CADR)	40 kW	1.3 l	04/75→01/79		
1.6 RS	62 kW	1.6 l	12/74→08/80		
1.3 (BADR)	40 kW	1.3 l	08/76→07/81	; -> 08/80	KH00045 ProKIT
2.0 RS	80 kW	2 l	08/75→08/80		KH00008 ProKIT
					KH00045 ProKIT
2.0 RS (BATN)	73 kW	2 l	03/73→02/77	; 12/74 ->	KH00045 ProKIT
				; -> 11/74	KH00021 ProKIT
					KH00008 ProKIT
<b>FORD - ESCORT III / ESCORT III Convertible / ESCORT III Express / ESCORT III Turnier / ESCORT IV / ESCORT IV Convertible / ESCORT IV Express / ESCORT IV Turnier (GAA, ALD, AVA, AWA, GAF, AWF, ABFT, ALF, AVF, AWF, AVF)</b>				09/80→10/90	
1.1	37 kW	1.1 l	03/81→02/86		KH00009 ProKIT
1.1	37 kW	1.1 l	05/86→07/90		
1.3	51 kW	1.3 l	03/81→02/86		
1.6	61 kW	1.6 l	03/81→02/86		
1.1	37 kW	1.1 l	08/83→12/85		KH00023 ProKIT
1.1	37 kW	1.1 l	12/85→07/90		
1.1	40 kW	1.1 l	09/80→08/83		
1.1	43 kW	1.1 l	09/80→08/83		
1.3	44 kW	1.3 l	01/86→07/90		
1.3 (GAF)	46 kW	1.3 l	07/88→10/90		
1.1	37 kW	1.1 l	08/83→12/85		KH00009 ProKIT
1.1	37 kW	1.1 l	10/85→09/90		KH00023 ProKIT
1.1	40 kW	1.1 l	09/80→08/83		
1.3	44 kW	1.3 l	01/86→07/90		
1.3	51 kW	1.3 l	09/80→12/85		
1.3	51 kW	1.3 l	03/81→12/85		
1.3	51 kW	1.3 l	09/83→12/85		
1.4	54 kW	1.4 l	01/86→07/90		
1.4	54 kW	1.4 l	02/87→07/90		
1.4	55 kW	1.4 l	01/86→07/90		
1.6	58 kW	1.6 l	09/80→12/85		
1.6	58 kW	1.6 l	09/83→12/85		
1.6	65 kW	1.6 l	04/89→07/90		
1.6	71 kW	1.6 l	09/80→10/82		
1.6 D	40 kW	1.6 l	02/84→12/85		
1.6 D	40 kW	1.6 l	02/84→02/86		
1.6 D	40 kW	1.6 l	01/86→01/89		
1.6 i	66 kW	1.6 l	01/86→05/90		
1.6 i	66 kW	1.6 l	01/86→07/90		
1.6 i	75 kW	1.6 l	08/89→07/90		
1.6 i	77 kW	1.6 l	09/83→12/85		
1.6 i (GAA)	66 kW	1.6 l	07/85→12/85		
1.6 RS Turbo	97 kW	1.6 l	11/84→12/85		
1.6 Turbo RS	97 kW	1.6 l	01/86→07/90		
1.6 XR3i	77 kW	1.6 l	10/82→12/85		
1.6 XR3i	77 kW	1.6 l	01/86→08/89		
1.6 XR3i	77 kW	1.6 l	01/86→07/90		
1.8 D	44 kW	1.8 l	01/89→07/90		
RS 1600i	85 kW	1.6 l	05/82→12/85		
1.3	44 kW	1.3 l	02/86→07/90		KH00009 ProKIT
				; Trim Level: 9.9 CWT	KH00022 ProKIT
1.3	46 kW	1.3 l	07/88→07/90		KH00009 ProKIT
				; Trim Level: 14.5 CWT	KH00022 ProKIT
1.4 i	54 kW	1.4 l	02/86→07/90		KH00009 ProKIT
				; Trim Level: 9.9, 14.5 CWT	KH00022 ProKIT
1.6 D	40 kW	1.6 l	02/86→07/90		KH00009 ProKIT
				; Trim Level: 9.9, 14.5 CWT	KH00022 ProKIT
					KH00023 ProKIT

















































												
<b>FORD - ESCORT III / ESCORT III Convertible / ESCORT III Express / ESCORT III Turnier / ESCORT IV / ESCORT IV Convertible / ESCORT IV Express / ESCORT IV Turnier (GAA, ALD, AVA, AWA, GAF, AWF, ABFT, ALF, AVF, AWF, AVF)</b>											<b>09/80→10/90</b>	
1.8 D	44 kW	1.8 l	07/88→07/90								KH00009 ProKIT	
					Trim Level: 14.5 CWT; 08/88 ->						KH00022 ProKIT	
											KH00023 ProKIT	
<b>FORD - ESCORT V (AAL, ABL)</b>											<b>07/90→01/95</b>	
1.3	44 kW	1.3 l	07/90→01/95		10/91 ->						KH10097 ProKIT	
1.4	52 kW	1.4 l	07/90→01/95		-> 10/91						KH00062 ProKIT	
1.6	66 kW	1.6 l	07/90→08/92								KH00023 ProKIT	
1.6	77 kW	1.6 l	07/90→08/93								KH00034 ProKIT	
1.4	55 kW	1.4 l	09/90→12/94		10/91 ->						KH10097 ProKIT	
											KH00034 ProKIT	
1.6 i 16V	65 kW	1.6 l	01/94→01/95								KH10097 ProKIT	
1.6 i 16V	66 kW	1.6 l	09/92→01/95								KH00034 ProKIT	
1.8 16V XR3i	77 kW	1.8 l	02/92→01/95									
1.8 16V XR3i	96 kW	1.8 l	02/92→01/95									
1.8 TD	66 kW	1.8 l	02/93→01/95									
1.8 D	44 kW	1.8 l	07/90→01/95		10/91 ->						KH10097 ProKIT	
											KH00023 ProKIT	
											KH00034 ProKIT	
1.8 XR3i 16V 4x4	77 kW	1.8 l	08/93→01/95							KH00062 ProKIT		
1.8 XR3i 16V 4x4	96 kW	1.8 l	08/93→01/95									
RS 2000 4x4	110 kW	2 l	05/91→01/95									
RS 2000	110 kW	2 l	05/91→01/95		10/91 ->						KH10097 ProKIT	
					-> 10/91						KH00062 ProKIT	
											KH00034 ProKIT	
RS Cosworth 4x4	162 kW	2 l	10/91→01/95		-> 12/94						KH00057 ProKIT	
											KH00076 ProKIT	
<b>FORD - ESCORT V Convertible (ALL)</b>											<b>07/90→01/95</b>	
1.4	52 kW	1.4 l	07/90→04/94		-> 10/91; ABS						KH00062 ProKIT	
1.6	77 kW	1.6 l	07/90→08/93								KH00023 ProKIT	
											KH00034 ProKIT	
1.4 i	55 kW	1.4 l	07/93→01/95								KH00034 ProKIT	
1.6 16V XR3i	66 kW	1.6 l	12/92→01/95									
1.6 i 16V	65 kW	1.6 l	02/94→01/95									
1.8 16V XR3i	77 kW	1.8 l	02/92→01/95									
1.8 16V XR3i	96 kW	1.8 l	02/92→01/95									
<b>FORD - ESCORT V Express (AVF)</b>											<b>07/90→12/94</b>	
1.3	46 kW	1.3 l	07/90→12/94		-> 10/91						KH00062 ProKIT	
											KH00063 ProKIT	
1.4	52 kW	1.4 l	07/90→12/94								KH00063 ProKIT	
1.8 D	44 kW	1.8 l	07/90→12/94								KH00023 ProKIT	
											KH00063 ProKIT	
<b>FORD - ESCORT V Saloon (AFL)</b>											<b>08/93→01/95</b>	
1.3	44 kW	1.3 l	08/93→01/95								KH10097 ProKIT	
1.4	52 kW	1.4 l	08/93→04/94								KH00034 ProKIT	
1.4	55 kW	1.4 l	08/93→01/95									
1.6 i 16V	65 kW	1.6 l	01/94→01/95									
1.6 i 16V	66 kW	1.6 l	08/93→01/95									
1.8 D	44 kW	1.8 l	08/93→01/95									
1.8 i 16V	77 kW	1.8 l	08/93→01/95									
1.8 TD	66 kW	1.8 l	08/93→01/95									
<b>FORD - ESCORT V Turnier (ANL)</b>											<b>07/90→01/95</b>	
1.3	44 kW	1.3 l	09/91→01/95		10/91 ->						KH10097 ProKIT	
					not for trim level: Body Style VAN						KH00034 ProKIT	
											KH00063 ProKIT	

      				
<b>FORD - ESCORT V Turnier (ANL)</b>				<b>07/90→01/95</b>
1.4	52 kW	1.4 l	07/90→01/95	; 10/91 -> <b>KH10097 ProKIT</b>
1.6	66 kW	1.6 l	07/90→08/92	; > 10/91 <b>KH00062 ProKIT</b>
1.6	77 kW	1.6 l	07/90→09/92	<b>KH00023 ProKIT</b>
				; not for trim level: Body Style VAN <b>KH00034 ProKIT</b>
				<b>KH00063 ProKIT</b>
1.4	55 kW	1.4 l	01/94→01/95	<b>KH10097 ProKIT</b>
1.6 i 16V	65 kW	1.6 l	01/94→01/95	; not for trim level: Body Style VAN <b>KH00034 ProKIT</b>
1.6 i 16V	66 kW	1.6 l	09/92→01/95	<b>KH00063 ProKIT</b>
1.8 16V	77 kW	1.8 l	02/92→01/95	
1.8 i 16V	96 kW	1.8 l	02/93→01/95	
1.8 TD	66 kW	1.8 l	02/93→01/95	
1.8 D	44 kW	1.8 l	07/90→01/95	; 10/91 -> <b>KH10097 ProKIT</b>
				<b>KH00023 ProKIT</b>
				; not for trim level: Body Style VAN <b>KH00034 ProKIT</b>
				<b>KH00063 ProKIT</b>
1.8 TD	55 kW	1.8 l	05/91→12/92	; 10/91 -> <b>KH10097 ProKIT</b>
				; not for trim level: Body Style VAN <b>KH00034 ProKIT</b>
<b>FORD - ESCORT VI (GAL, AAL, ABL)</b>				<b>01/95→12/99</b>
1.3	44 kW	1.3 l	01/95→10/98	<b>KH10097 ProKIT</b>
1.4	54 kW	1.4 l	01/95→12/99	<b>KH00034 ProKIT</b>
1.4	55 kW	1.4 l	01/95→10/98	
1.6 16V	66 kW	1.6 l	01/95→10/98	
1.6 i 16V	65 kW	1.6 l	01/95→08/95	
1.8 16V	77 kW	1.8 l	01/95→08/95	
1.8 16V	85 kW	1.8 l	01/95→10/98	
1.8 D	44 kW	1.8 l	01/95→12/96	
1.8 TD	66 kW	1.8 l	01/95→10/98	
1.8 Turbo D	51 kW	1.8 l	12/95→10/98	
RS 2000	110 kW	2 l	02/95→02/98	
1.6 16V 4x4	66 kW	1.6 l	01/95→10/98	<b>KH00062 ProKIT</b>
RS 2000 4x4	110 kW	2 l	02/95→10/98	
RS Cosworth 4x4	162 kW	2 l	02/95→10/98	; 08/95 -> 12/95 <b>KH00057 ProKIT</b>
				<b>KH00076 ProKIT</b>
<b>FORD - ESCORT VI Convertible (ALL)</b>				<b>02/95→08/00</b>
1.4	55 kW	1.4 l	02/95→08/98	<b>KH00034 ProKIT</b>
1.6 16V XR3i	65 kW	1.6 l	02/95→12/96	
1.6 16V XR3i	66 kW	1.6 l	02/95→09/99	
1.8 16V XR3i	77 kW	1.8 l	02/95→08/98	
1.8 16V XR3i	85 kW	1.8 l	10/95→08/98	
1.8 16V XR3i	96 kW	1.8 l	02/95→08/00	
1.8 TD	66 kW	1.8 l	09/95→08/98	
1.8 Turbo D	51 kW	1.8 l	10/96→08/99	
<b>FORD - ESCORT VI Estate Van (AVL)</b>				<b>01/95→06/01</b>
1.4	54 kW	1.4 l	01/95→08/00	<b>KH00063 ProKIT</b>
1.8 D	44 kW	1.8 l	01/95→08/00	
1.8 Turbo D	51 kW	1.8 l	12/95→06/01	
<b>FORD - ESCORT VI Saloon / ESCORT VI Turnier (GAL, AFL, GAL, ANL)</b>				<b>01/95→02/99</b>
1.3	44 kW	1.3 l	01/95→01/99	<b>KH10097 ProKIT</b>
1.4	55 kW	1.4 l	01/95→02/99	; not for trim level: Body Style VAN <b>KH00034 ProKIT</b>
1.6 16V	66 kW	1.6 l	01/95→02/99	<b>KH00063 ProKIT</b>
1.6 i 16V	65 kW	1.6 l	01/95→08/95	
1.8 16V	77 kW	1.8 l	01/95→08/95	
1.8 16V	85 kW	1.8 l	01/95→02/99	
1.8 D	44 kW	1.8 l	01/95→02/99	
1.8 TD	66 kW	1.8 l	01/95→02/99	
1.8 Turbo D	51 kW	1.8 l	12/95→02/99	
1.3	44 kW	1.3 l	01/95→02/99	<b>KH10097 ProKIT</b>
1.4	54 kW	1.4 l	01/95→12/96	<b>KH00034 ProKIT</b>
1.4	55 kW	1.4 l	01/95→02/99	
1.6 i 16V	65 kW	1.6 l	01/95→08/95	
1.6 i 16V	66 kW	1.6 l	01/95→02/99	
1.8 16V	77 kW	1.8 l	01/95→08/95	
1.8 16V	85 kW	1.8 l	01/95→02/99	
1.8 D	44 kW	1.8 l	01/95→12/96	
1.8 TD	66 kW	1.8 l	01/95→02/99	
1.8 Turbo D	51 kW	1.8 l	12/95→02/99	



				     <b>13</b> 		
<b>FORD - FIESTA I (GFBT)</b>				<b>05/76→08/83</b>		
0.9	29 kW	0.9 l	05/76→08/83		KH00021 ProKIT	
0.9	33 kW	0.9 l	05/76→08/83			
1.1	39 kW	1.1 l	05/76→08/83			
1.1 (WFBT)	40 kW	1.1 l	02/81→08/83			
1.3	49 kW	1.3 l	08/77→08/83		KH00009 ProKIT	
					KH00021 ProKIT	
					KH00009 ProKIT	
					KH00021 ProKIT	
1.6 XR2	62 kW	1.6 l	08/81→08/83		KH00009 ProKIT	
					KH00021 ProKIT	
<b>FORD - FIESTA II (FBD)</b>				<b>09/83→11/89</b>		
1.0 (FBD)	33 kW	1 l	09/83→02/89		KH00021 ProKIT	
1.1 (FBD)	36 kW	1.1 l	05/86→02/89		KH00034 ProKIT	
1.1 (FBD)	37 kW	1.1 l	09/83→02/89			
1.3	51 kW	1.3 l	09/83→09/89		KH00034 ProKIT	
1.6	58 kW	1.6 l	01/85→11/89			
1.3 (FBD)	51 kW	1.3 l	09/83→01/87		KH00009 ProKIT	
1.4	51 kW	1.4 l	09/83→01/87		KH00021 ProKIT	
					KH00034 ProKIT	
1.4 (FBD)	52 kW	1.4 l	10/86→02/89		KH00009 ProKIT	
1.4 (FBD)	54 kW	1.4 l	02/87→02/89		KH00021 ProKIT	
1.4 (FBD)	55 kW	1.4 l	10/85→11/89		KH00034 ProKIT	
1.6 D (FBD)	40 kW	1.6 l	04/84→02/89		KH00034 ProKIT	
1.6 XR2 (FBD)	70 kW	1.6 l	03/84→02/89			
1.6 XR2 (FBD)	71 kW	1.6 l	04/84→02/89			
<b>FORD - FIESTA III (GFJ)</b>				<b>01/89→01/97</b>		
1.0	33 kW	1 l	03/89→12/95		KH10097 ProKIT	
1.1	37 kW	1.1 l	03/89→12/95		KH00062 ProKIT	
1.1	40 kW	1.1 l	03/89→12/95		KH00034 ProKIT	
1.3	44 kW	1.3 l	03/89→12/95			
1.3 Cat	44 kW	1.3 l	05/91→01/97			
1.4	52 kW	1.4 l	03/89→12/95			
1.4	54 kW	1.4 l	03/89→12/95			
1.8 16V	77 kW	1.8 l	02/92→12/95			
1.8 D	44 kW	1.8 l	03/89→12/95			
1.8 TD	55 kW	1.8 l	03/93→12/95			
1.8 XR2i 16V	96 kW	1.8 l	02/92→12/95			
1.3	44 kW	1.3 l	03/89→12/92		KH00062 ProKIT	
1.6	65 kW	1.6 l	01/89→01/94		KH00034 ProKIT	
1.6	66 kW	1.6 l	03/89→12/92			
1.6 Turbo (FBJT)	96 kW	1.6 l	03/90→10/92			
1.6 XR2i	76 kW	1.6 l	03/89→03/93			
1.6 XR2i	81 kW	1.6 l	03/89→01/94			
1.4	55 kW	1.4 l	11/92→12/96		KH10097 ProKIT	
					KH00034 ProKIT	
1.6 i 16V	65 kW	1.6 l	01/94→12/95		KH10097 ProKIT	
					KH00034 ProKIT	
<b>FORD - FIESTA IV (JA_, JB_)</b>				<b>08/95→01/02</b>		
1.0 i	38 kW	1 l	04/96→09/99		KH10097 ProKIT	
1.0 i	48 kW	1 l	09/99→01/02			
1.25 i 16V	55 kW	1.25 l	08/95→01/02		KH10097 ProKIT	
1.3 i	37 kW	1.3 l	08/95→01/02		KH00004 ProKIT	
1.3 i	44 kW	1.3 l	08/95→01/02			
1.4 i 16V	66 kW	1.4 l	04/96→01/02			
1.6 16V Sport	76 kW	1.6 l	02/00→01/02			
1.8 D	44 kW	1.8 l	08/95→04/00			
1.8 DI	55 kW	1.8 l	04/00→01/02			
<b>FORD - FIESTA V / FIESTA V Van / FIESTA VI / FIESTA VI Van / FIESTA VII (JH_, JD_, CB1, CCN, HJ, HF)</b>				<b>11/01→12/12</b>		
1.0	48 kW	1 l	01/13→		KH10070 ProKIT	
1.0	48 kW	1 l	01/13→04/17		KH10070 ProKIT	
1.0	59 kW	1 l	10/12→		KH10070 ProKIT	
1.0	59 kW	1 l	10/12→04/17		KH10070 ProKIT	
1.0 EcoBoost	74 kW	1 l	01/13→			
1.0 EcoBoost	92 kW	1 l	09/12→			
1.5 TDCi	55 kW	1.5 l	09/12→04/17			
1.5 TDCi	55 kW	1.5 l	10/12→			
1.6 Ti	77 kW	1.6 l	09/12→			
1.0 EcoBoost	63 kW	1 l	04/18→		KH10070 ProKIT	
1.0 EcoBoost	70 kW	1 l	12/19→			
1.0 EcoBoost	74 kW	1 l	05/17→			

				  		 13			
FORD - FIESTA V / FIESTA V Van / FIESTA VI / FIESTA VI Van / FIESTA VII								11/01→12/12	
(JH_, JD_, CB1, CCN, HJ, HF)									
1.0 EcoBoost	92 kW	1 l	05/17→		KH10070 ProKIT				
1.0 EcoBoost	103 kW	1 l	06/17→						
1.1 Ti-VCT	52 kW	1.1 l	05/17→						
1.1 Ti-VCT	55 kW	1.1 l	10/19→						
1.1 Ti-VCT	63 kW	1.1 l	05/17→						
1.25	44 kW	1.25 l	08/08→12/12						
1.4	71 kW	1.4 l	10/08→12/12						
1.5 Duratec	82 kW	1.5 l	09/15→						
1.5 Flex	82 kW	1.5 l	05/13→						
1.5 ST EcoBoost	147 kW	1.5 l	04/18→						
1.5 TDCi	63 kW	1.5 l	05/17→						
1.5 TDCi	88 kW	1.5 l	05/17→						
1.6	70 kW	1.6 l	06/08→12/11						
1.6	72 kW	1.6 l	04/10→12/10						
1.6	81 kW	1.6 l	06/10→						
1.6	93 kW	1.6 l	06/16→						
1.6 Flex	85 kW	1.6 l	06/10→						
1.6 Flex	94 kW	1.6 l	05/13→12/19						
1.6 Flex	96 kW	1.6 l	05/13→03/15						
1.6 Ti-VCT	88 kW	1.6 l	10/08→12/12						
1.0 EcoBoost	103 kW	1 l	05/14→		KH10070 ProKIT				
1.0 Sport	103 kW	1 l	05/14→04/17	 					
1.5 TDCi	70 kW	1.5 l	05/15→						
1.5 TDCi	70 kW	1.5 l	05/15→04/17						
1.6	62 kW	1.6 l	03/15→						
1.6 ST	134 kW	1.6 l	03/13→						
1.6 ST	134 kW	1.6 l	03/13→04/17						
1.6 ST200	147 kW	1.6 l	04/16→04/17						
1.25	44 kW	1.25 l	06/08→04/17		KH10070 ProKIT				
1.25	60 kW	1.25 l	06/08→04/17	   ->					
1.25	60 kW	1.25 l	01/09→						
1.4	71 kW	1.4 l	10/08→09/12	   ->	KH30069 ProKIT				
1.4 LPG	68 kW	1.4 l	01/09→04/17						
1.4 LPG	71 kW	1.4 l	01/09→04/17						
1.4 TDCi	50 kW	1.4 l	01/09→						
1.4 TDCi	51 kW	1.4 l	07/10→						
1.6	89 kW	1.6 l	10/10→						
1.6	90 kW	1.6 l	01/11→						
1.6 TDCi	66 kW	1.6 l	01/09→						
1.6 TDCi	70 kW	1.6 l	02/10→						
1.6 TDCi	70 kW	1.6 l	02/10→12/15						
1.6 Ti	88 kW	1.6 l	06/08→09/12						
1.6 Ti	99 kW	1.6 l	12/10→						
1.25 16V	51 kW	1.25 l	03/03→06/08	 	KH10046 ProKIT				
1.25 16V	55 kW	1.25 l	05/02→06/08	 	KH10050 ProKIT				
1.3	44 kW	1.3 l	11/01→06/08	 	KH10037 ProKIT				
1.3	51 kW	1.3 l	11/01→06/08	 	KH10093 ProKIT				
1.3	51 kW	1.3 l	10/03→07/05	 					
1.3 ROCAM	55 kW	1.3 l	01/02→12/04						
1.4 16V	59 kW	1.4 l	11/01→06/08						
1.4 TDCi	50 kW	1.4 l	11/01→06/08						
1.4 TDCi	50 kW	1.4 l	10/03→12/10						
1.6 16V	74 kW	1.6 l	11/01→06/08						
1.6 TDCi	66 kW	1.6 l	11/04→06/08						
1.6 TDCi	66 kW	1.6 l	04/07→09/09						
1.3	44 kW	1.3 l	05/02→08/08	 	KH10093 ProKIT				
1.4	59 kW	1.4 l	05/02→09/05						
1.4 TDCi	50 kW	1.4 l	01/09→09/12		KH10070 ProKIT				
1.4 TDCi	51 kW	1.4 l	07/10→09/12						
1.6 TDCi	55 kW	1.6 l	06/08→12/12	   ->	KH30069 ProKIT				
1.6 TDCi	66 kW	1.6 l	06/08→12/12						
1.6 ROCAM	70 kW	1.6 l	11/01→12/04	 	KH10037 ProKIT				
ST150	110 kW	2 l	03/05→06/08	 	KH10093 ProKIT				
FORD - FIESTA Box Body/MPV (F3L, F5L)								09/91→02/96	
1.3	44 kW	1.3 l	09/91→02/96	   ->	KH00062 ProKIT				
1.8 D	44 kW	1.8 l	09/91→02/96						
FORD - FIESTA Box Body/MPV (JV_)								05/98→08/03	
D 1.8	44 kW	1.8 l	05/98→04/02		KH00004 ProKIT				
TD 1.8	55 kW	1.8 l	03/00→08/03						
FORD - FIESTA Hatchback Van (FVD)								08/83→12/95	
1.0	33 kW	1 l	08/83→11/89	   ->	KH00021 ProKIT				
1.8 D (FVJ)	43 kW	1.8 l	03/89→12/95	   ->	KH00062 ProKIT				





**FORD - FIESTA Hatchback Van (WFVT)**

**10/77→11/86**

1.0 (WFVT)	29 kW	1 l	10/77→11/86		<b>KH00021</b> ProKIT
1.1 (WFVT)	39 kW	1.1 l	10/77→11/86		

**FORD - FOCUS I / FOCUS I Saloon / FOCUS I Turnier (DAW, DBW, DFW, DNW)**

**10/98→03/05**

1.4 16V	55 kW	1.4 l	10/98→09/99		<b>KH10046</b> ProKIT
1.4 16V	55 kW	1.4 l	10/98→11/04		<b>KH10050</b> ProKIT
1.4 16V	55 kW	1.4 l	02/99→11/04		
1.6 16V	74 kW	1.6 l	10/98→11/04		<b>KH10037</b> ProKIT
1.6 16V	74 kW	1.6 l	02/99→11/04		<b>KH10093</b> ProKIT
1.6 16V Flexifuel	75 kW	1.6 l	01/02→11/04		
1.8 16V	85 kW	1.8 l	10/98→11/04		
1.8 16V	85 kW	1.8 l	02/99→11/04		
1.8 BiFuel	82 kW	1.8 l	02/03→01/05		
1.8 DI / TDDi	55 kW	1.8 l	08/99→11/04		
1.8 TDCi	74 kW	1.8 l	08/02→11/04		
1.8 TDCi	85 kW	1.8 l	03/01→11/04		
1.8 Turbo DI / TDDi	66 kW	1.8 l	10/98→11/04		
1.8 Turbo DI / TDDi	66 kW	1.8 l	02/99→11/04		
2.0 16V	96 kW	2 l	10/98→11/04		
2.0 16V	96 kW	2 l	02/99→11/04		
1.4 16V	55 kW	1.4 l	02/99→11/04		<b>KH10037</b> ProKIT
1.6 16V	74 kW	1.6 l	02/99→11/04		<b>KH10093</b> ProKIT
1.8 16V	85 kW	1.8 l	02/99→11/04		
1.8 TDCi	74 kW	1.8 l	08/02→11/04		
1.8 TDCi	85 kW	1.8 l	03/01→11/04		
1.8 Turbo DI / TDDi	55 kW	1.8 l	08/01→03/05		
1.8 Turbo DI / TDDi	66 kW	1.8 l	02/99→11/04		
2.0 16V	96 kW	2 l	02/99→11/04		
ST170	127 kW	2 l	03/02→11/04		
ST170	127 kW	2 l	08/02→11/04		

1.8 16V BiFuel	85 kW	1.8 l	09/02→07/04		<b>KH10093</b> ProKIT
----------------	-------	-------	-------------	--	-----------------------

**FORD - FOCUS II / FOCUS II Convertible / FOCUS II Saloon / FOCUS II Turnier (DA\_, HCP, DP, DB\_, FCH, DH, DA\_, FFS, DS)**

**07/04→09/12**

1.4	59 kW	1.4 l	07/04→09/12		<b>KH20020</b> ProKIT
1.4	59 kW	1.4 l	04/05→09/12		<b>KH30042</b> ProKIT
1.6	74 kW	1.6 l	07/04→07/11		
1.6	74 kW	1.6 l	07/04→09/12		
1.6	74 kW	1.6 l	04/05→09/12		
1.6	74 kW	1.6 l	10/06→09/10		
1.6 LPG	85 kW	1.6 l	10/09→07/11		
1.6 LPG	85 kW	1.6 l	10/09→09/12		
1.6 TDCi	66 kW	1.6 l	07/04→09/12		
1.6 TDCi	66 kW	1.6 l	01/05→09/12		
1.6 TDCi	66 kW	1.6 l	04/05→09/12		
1.6 TDCi	74 kW	1.6 l	07/04→09/12		
1.6 TDCi	74 kW	1.6 l	04/05→09/12		
1.6 TDCi	80 kW	1.6 l	07/04→09/12		
1.6 TDCi	80 kW	1.6 l	04/05→09/12		
1.6 Ti	85 kW	1.6 l	07/04→09/12		
1.6 Ti	85 kW	1.6 l	04/05→09/12		
1.8	92 kW	1.8 l	03/06→09/12		
1.8 Flexifuel	92 kW	1.8 l	01/06→09/12		
1.8 Flexifuel	92 kW	1.8 l	06/06→07/11		
1.8 Flexifuel	96 kW	1.8 l	12/05→01/08		
1.8 TDCi	85 kW	1.8 l	07/04→09/12		
1.8 TDCi	85 kW	1.8 l	01/05→09/12		
1.8 TDCi	85 kW	1.8 l	04/05→09/12		
2.0	104 kW	2 l	06/05→09/08		
2.0	107 kW	2 l	07/04→09/12		
2.0	107 kW	2 l	04/05→07/11		
2.0	107 kW	2 l	10/06→09/10		
2.0 CNG	107 kW	2 l	04/09→07/11		
2.0 Flex	107 kW	2 l	10/08→03/10		
2.0 LPG	107 kW	2 l	06/08→07/11		
2.0 TDCi	81 kW	2 l	02/08→07/11		
2.0 TDCi	98 kW	2 l	07/04→01/08		
2.0 TDCi	100 kW	2 l	07/04→09/12		
2.0 TDCi	100 kW	2 l	04/05→09/12		
2.0 TDCi	100 kW	2 l	10/06→09/10		
2.5 RS 500	257 kW	2.5 l	05/10→07/11		
2.5 ST	166 kW	2.5 l	10/05→09/12		

1.6 TDCi	81 kW	1.6 l	12/07→09/12		<b>KH30042</b> ProKIT
----------	-------	-------	-------------	--	-----------------------

1.8 Flexifuel	97 kW	1.8 l	12/05→01/08		<b>KH20020</b> ProKIT
---------------	-------	-------	-------------	--	-----------------------

2.5 RS	224 kW	2.5 l	01/09→07/11		<b>KH20087</b> ProKIT
--------	--------	-------	-------------	--	-----------------------

					<b>KH30042</b> ProKIT
--	--	--	--	--	-----------------------



**FORD - FOCUS III / FOCUS III Saloon / FOCUS III Turnier**

07/10→

1.0 EcoBoost	74 kW	1 l	02/12→		KH10126 ProKIT
1.0 EcoBoost	74 kW	1 l	02/12→12/17		KH30143 ProKIT
1.0 EcoBoost	92 kW	1 l	02/12→		
1.0 EcoBoost	92 kW	1 l	02/12→12/17		
1.5 EcoBoost	110 kW	1.5 l	09/14→		
1.5 EcoBoost	110 kW	1.5 l	09/14→12/17		
1.5 EcoBoost	110 kW	1.5 l	11/14→		
1.5 EcoBoost	134 kW	1.5 l	09/14→		
1.5 EcoBoost	134 kW	1.5 l	09/14→12/17		
1.5 EcoBoost	134 kW	1.5 l	11/14→		
1.5 TDCi	70 kW	1.5 l	09/14→		
1.5 TDCi	70 kW	1.5 l	09/14→12/17		
1.5 TDCi	70 kW	1.5 l	11/14→		
1.5 TDCi	88 kW	1.5 l	09/14→		
1.5 TDCi	88 kW	1.5 l	09/14→12/17		
1.5 TDCi	88 kW	1.5 l	11/14→		
1.5 TDCi ECOnetic	77 kW	1.5 l	09/14→		
1.5 TDCi ECOnetic	77 kW	1.5 l	09/14→12/17		
1.5 TDCi ECOnetic	77 kW	1.5 l	11/14→		
1.6 EcoBoost	110 kW	1.6 l	07/10→		
1.6 EcoBoost	110 kW	1.6 l	07/10→06/14		
1.6 EcoBoost	134 kW	1.6 l	07/10→		
1.6 EcoBoost	134 kW	1.6 l	07/10→06/14		
1.6 Flexifuel	88 kW	1.6 l	07/10→		
1.6 Flexifuel	110 kW	1.6 l	07/13→		
1.6 LPG	86 kW	1.6 l	02/12→		
1.6 LPG	88 kW	1.6 l	02/12→		
1.6 TDCi	70 kW	1.6 l	07/10→		
1.6 TDCi	70 kW	1.6 l	07/10→12/17		
1.6 TDCi	85 kW	1.6 l	07/10→		
1.6 TDCi	85 kW	1.6 l	07/10→12/17		
1.6 TDCi ECOnetic	77 kW	1.6 l	05/12→		
1.6 Ti	63 kW	1.6 l	08/11→		
1.6 Ti	63 kW	1.6 l	08/11→12/17		
1.6 Ti	77 kW	1.6 l	07/10→		
1.6 Ti	77 kW	1.6 l	07/10→05/18		
1.6 Ti	88 kW	1.6 l	02/12→		
1.6 Ti	88 kW	1.6 l	02/12→12/17		
1.6 Ti	92 kW	1.6 l	07/10→		
1.6 Ti	92 kW	1.6 l	07/10→12/17		
2.0 ST	184 kW	2 l	07/12→		
2.0 ST	184 kW	2 l	07/12→12/17		
2.0 TDCi	85 kW	2 l	07/10→		
2.0 TDCi	85 kW	2 l	07/10→06/14		
2.0 TDCi	100 kW	2 l	07/10→		
2.0 TDCi	100 kW	2 l	07/10→06/14		
2.0 TDCi	103 kW	2 l	07/10→		
2.0 TDCi	103 kW	2 l	07/10→06/14		
2.0 TDCi	110 kW	2 l	11/14→		
2.0 TDCi	110 kW	2 l	11/14→12/17		
2.0 TDCi	120 kW	2 l	07/10→		
2.0 TDCi	120 kW	2 l	07/10→06/14		
2.0 TDCi ST	136 kW	2 l	11/14→		
2.0 TDCi ST	136 kW	2 l	11/14→12/17		
2.3 RS AWD	257 kW	2.3 l	07/15→		
Electric	107 kW		07/13→12/17		
1.6 TDCi	77 kW	1.6 l	05/12→		KH30143 ProKIT
2.0	110 kW	2 l	10/13→		
2.0	110 kW	2 l	10/13→12/17		
2.0 GDi	125 kW	2 l	08/11→		
2.0 TDCi	100 kW	2 l	07/10→		
2.0 Ti-GDi	125 kW	2 l	07/10→		
2.0 Ti-GDi	125 kW	2 l	08/11→		

**FORD - FOCUS C-MAX (DM2)**

10/03→03/07

1.6	74 kW	1.6 l	10/03→03/07		KH20020 ProKIT
1.6 TDCi	66 kW	1.6 l	02/05→03/07		KH30042 ProKIT
1.6 TDCi	80 kW	1.6 l	10/03→03/07		
1.6 Ti	85 kW	1.6 l	08/04→03/07		
1.8	88 kW	1.8 l	10/03→03/07		
1.8	90 kW	1.8 l	09/05→03/07		
1.8	92 kW	1.8 l	04/04→03/07		
1.8 Flexifuel	92 kW	1.8 l	01/06→03/07		
1.8 TDCi	85 kW	1.8 l	01/05→03/07		
2.0	107 kW	2 l	03/04→03/07		
2.0 TDCi	98 kW	2 l	10/03→03/07		
2.0 TDCi	100 kW	2 l	10/03→03/07		



**FORD - FUSION (JU\_)** **08/02→12/12**

1.25	55 kW	1.25 l	08/04→12/12	;	<b>KH10046</b> ProKIT
1.4	59 kW	1.4 l	08/02→12/12	;	<b>KH10050</b> ProKIT
1.4 LPG	59 kW	1.4 l	01/10→12/12	;	<b>KH10037</b> ProKIT
1.4 TDCi	50 kW	1.4 l	08/02→12/12	;	<b>KH10093</b> ProKIT
1.6	74 kW	1.6 l	08/02→11/09	;	<b>KH10093</b> ProKIT
1.6 TDCi	66 kW	1.6 l	11/04→12/12	;	<b>KH10093</b> ProKIT
1.3	44 kW	1.3 l	11/02→07/05	;	<b>KH10093</b> ProKIT

**FORD - GALAXY I (WGR)** **03/95→05/06**

1.9 TDI	66 kW	1.9 l	03/95→05/06		<b>KH10084</b> ProKIT
				; 11/95 -> 03/06	<b>KH10208</b> ProKIT
1.9 TDI	81 kW	1.9 l	08/97→04/00		<b>KH10084</b> ProKIT
				; 11/97 -> 03/00	<b>KH10208</b> ProKIT
1.9 TDI	85 kW	1.9 l	04/00→05/06		<b>KH10084</b> ProKIT
1.9 TDI	96 kW	1.9 l	02/03→05/06		<b>KH10208</b> ProKIT
1.9 TDI	110 kW	1.9 l	05/05→05/06	; -> 04/06	<b>KH10208</b> ProKIT
2.0 i	85 kW	2 l	11/95→05/06		
2.3 16V	103 kW	2.3 l	09/01→05/06		
2.8 V6	150 kW	2.8 l	04/00→05/06		
2.3 16V	107 kW	2.3 l	01/97→05/06		<b>KH10084</b> ProKIT
				; -> 08/01	<b>KH10208</b> ProKIT
2.8 i V6	128 kW	2.8 l	11/95→04/00		<b>KH10084</b> ProKIT
				; -> 03/00	<b>KH10208</b> ProKIT
2.8 i V6 4x4	128 kW	2.8 l	04/96→04/00	; 07/96 -> 03/00	<b>KH10208</b> ProKIT







**FORD - GALAXY II (WA6)** **05/06→06/15**

1.6 EcoBoost	118 kW	1.6 l	11/10→06/15		<b>KH20045</b> ProKIT
1.6 TDCi	85 kW	1.6 l	02/11→06/15		
1.8 TDCi	74 kW	1.8 l	05/06→06/15		
1.8 TDCi	92 kW	1.8 l	05/06→06/15		
2.0	107 kW	2 l	05/06→06/15		
2.0 EcoBoost	146 kW	2 l	07/10→06/15		
2.0 EcoBoost	149 kW	2 l	03/10→06/15		
2.0 Flexifuel	107 kW	2 l	05/06→06/15		
2.0 TDCi	85 kW	2 l	11/07→06/15		
2.0 TDCi	96 kW	2 l	05/06→06/15		
2.0 TDCi	100 kW	2 l	05/06→06/15		
2.0 TDCi	103 kW	2 l	05/06→06/15		
2.0 TDCi	120 kW	2 l	03/10→06/15		
2.2 TDCi	129 kW	2.2 l	03/08→12/12		
2.2 TDCi	147 kW	2.2 l	11/10→06/15		
2.3	118 kW	2.3 l	09/07→06/15		

**FORD - GRANADA / GRANADA I Coupe / GRANADA II / GRANADA Turnier 01/72→08/85 (GGTL, GGFL, GGCL, GU, GGNL, GNU)**

1.6	55 kW	1.6 l	07/81→08/85		<b>KH00023</b> ProKIT
1.7	48 kW	1.7 l	03/72→02/75		<b>KH00128</b> ProKIT
1.7	51 kW	1.7 l	12/74→08/77		
1.7	54 kW	1.7 l	08/77→07/81		
1.7	55 kW	1.7 l	03/72→02/75		
1.7 (GT, GF, GU)	51 kW	1.7 l	08/77→05/82		
2.0	66 kW	2 l	01/75→08/77		
2.0	66 kW	2 l	08/77→06/85		
2.0	66 kW	2 l	08/77→08/85		
2.0	73 kW	2 l	03/72→02/75		
2.0	74 kW	2 l	08/79→08/85		
2.0	77 kW	2 l	08/81→08/85		
2.3	79 kW	2.3 l	01/72→02/76		
2.3	79 kW	2.3 l	01/75→08/77		
2.3	79 kW	2.3 l	08/77→06/79		
2.3	82 kW	2.3 l	06/81→06/85		
2.3	82 kW	2.3 l	06/81→08/85		
2.3	84 kW	2.3 l	06/79→08/85		
2.6	92 kW	2.6 l	01/72→02/76		
2.8	97 kW	2.8 l	06/81→08/85		
2.8	99 kW	2.8 l	08/77→08/85		
3.0	101 kW	3 l	01/72→02/76		
1.9 D	40 kW	1.9 l	08/77→08/82		<b>KH00023</b> ProKIT
2.1 D	46 kW	2.1 l	08/77→08/82		
2.5 D	51 kW	2.5 l	08/82→08/85		
2.8 i	108 kW	2.8 l	08/77→08/85		
2.8 i	110 kW	2.8 l	10/82→08/85		
2.8 i	118 kW	2.8 l	08/77→08/81		



     					
<b>FORD - GRAND C-MAX (DXA/CB7, DXA/CEU)</b>				<b>12/10→06/19</b>	
1.0 EcoBoost	74 kW	1 l	10/12→06/19		KH10126 ProKIT
1.0 EcoBoost	92 kW	1 l	10/12→06/19		
1.5 EcoBoost	110 kW	1.5 l	03/15→06/19		
1.5 EcoBoost	134 kW	1.5 l	03/15→06/19		
1.5 TDCi	70 kW	1.5 l	03/15→06/19		
1.5 TDCi	88 kW	1.5 l	03/15→06/19		
1.6 EcoBoost	110 kW	1.6 l	12/10→06/19		
1.6 EcoBoost	134 kW	1.6 l	12/10→06/19		
1.6 TDCi	70 kW	1.6 l	12/10→06/19		
1.6 TDCi	85 kW	1.6 l	12/10→06/19		
1.6 Ti	77 kW	1.6 l	12/10→06/19		
1.6 Ti	92 kW	1.6 l	12/10→06/19		
2.0 TDCi	85 kW	2 l	02/11→06/19		
2.0 TDCi	100 kW	2 l	02/11→06/19		
2.0 TDCi	103 kW	2 l	02/11→06/19		
2.0 TDCi	110 kW	2 l	03/15→06/19		
2.0 TDCi	120 kW	2 l	12/10→06/19		
2.0 TDCi	125 kW	2 l	03/15→06/19		
<b>FORD - KA (RB_)</b>				<b>09/96→11/08</b>	
1.0 i	48 kW	1 l	09/99→11/08	; 10/02 ->	KH10210 ProKIT
				-> 10/02	KH10097 ProKIT
1.3 i	36 kW	1.3 l	06/98→11/08	; 10/02 ->	KH10210 ProKIT
1.3 i	44 kW	1.3 l	09/96→11/08	; -> 10/02	KH10097 ProKIT
1.3 i ROCAM	51 kW	1.3 l	08/02→11/08		KH00004 ProKIT
1.3 i	37 kW	1.3 l	09/96→10/02	; 10/02 ->	KH10210 ProKIT
					KH10097 ProKIT
					KH00004 ProKIT
1.6 i	70 kW	1.6 l	02/01→11/08		KH10210 ProKIT
					KH00004 ProKIT
<b>FORD - KA (RU8)</b>				<b>10/08→05/16</b>	
1.2	51 kW	1.2 l	10/08→05/16		KH10111 ProKIT
					KH20022 ProKIT
1.3 TDCi	55 kW	1.3 l	10/08→05/16		KH10065 ProKIT
					KH20022 ProKIT
<b>FORD - KA Van (RB)</b>				<b>05/02→05/05</b>	
1.3 i	44 kW	1.3 l	05/02→05/05		KH00004 ProKIT
<b>FORD - KUGA I</b>				<b>02/08→11/12</b>	
2.0 TDCi	100 kW	2 l	03/08→11/12		KH10125 ProKIT
2.0 TDCi	103 kW	2 l	03/10→11/12		KH30081 ProKIT
2.0 TDCi 4x4	100 kW	2 l	03/08→11/12		KH10125 ProKIT
2.0 TDCi 4x4	103 kW	2 l	03/10→11/12		KH30091 ProKIT
2.0 TDCi 4x4	120 kW	2 l	03/10→11/12		
2.5 4x4	147 kW	2.5 l	02/08→11/12		
<b>FORD - KUGA II (DM2)</b>				<b>03/13→</b>	
1.5 EcoBoost	88 kW	1.5 l	01/16→06/19		KH10126 ProKIT
1.5 EcoBoost	110 kW	1.5 l	09/14→06/19		
1.5 EcoBoost 4x4	134 kW	1.5 l	09/14→06/18		
1.6 EcoBoost	110 kW	1.6 l	03/13→09/14		
1.6 EcoBoost 4x4	134 kW	1.6 l	03/13→09/14		
2.0 TDCi	88 kW	2 l	09/14→06/19		
2.0 TDCi	100 kW	2 l	03/13→		
2.0 TDCi	103 kW	2 l	03/13→09/14		
2.0 TDCi	110 kW	2 l	09/14→06/19		
2.0 TDCi 4x4	100 kW	2 l	03/13→		
2.0 TDCi 4x4	103 kW	2 l	03/13→09/14		
2.0 TDCi 4x4	110 kW	2 l	09/14→06/19		
2.0 TDCi 4x4	120 kW	2 l	03/13→09/14		
2.0 TDCi 4x4	132 kW	2 l	09/14→06/19		
<b>FORD - MAVERICK (UDS, UNS)</b>				<b>02/93→04/98</b>	
2.4 i	87 kW	2.4 l	09/96→04/98		KH00024 ProKIT
2.7 TD	92 kW	2.7 l	09/96→04/98	; ;	KH10384 ProKIT
2.4 i	91 kW	2.4 l	02/93→08/96		KH00024 ProKIT
2.4 i (UDS)	85 kW	2.4 l	09/96→04/98		
2.7 TD	74 kW	2.7 l	02/93→08/96	; 07/93 -> 06/96;	KH10383 ProKIT
				; 07/93 -> 07/96;	
					KH00024 ProKIT





**FORD - MONDEO I / MONDEO I Saloon / MONDEO I Turnier / MONDEO II / 01/93→09/00**  
**MONDEO II Saloon (GBP, BNP, BAP, BFP)**

1.6 i	66 kW	1.6 l	08/96→09/00		KH10041 ProKIT
1.6 i 16V	65 kW	1.6 l	07/94→08/96		
1.6 i 16V	66 kW	1.6 l	02/93→08/96		
1.6 i 16V	66 kW	1.6 l	04/93→08/96		
1.6 i 16V	70 kW	1.6 l	05/98→09/00		
1.8 4x4	85 kW	1.8 l	02/93→08/96		
1.8 i	85 kW	1.8 l	08/96→09/00		
1.8 i 16V	82 kW	1.8 l	01/94→08/96		
1.8 i 16V	82 kW	1.8 l	07/94→08/96		
1.8 i 16V	85 kW	1.8 l	02/93→08/96		
1.8 i 16V	85 kW	1.8 l	04/93→08/96		
1.8 i 16V 4x4	85 kW	1.8 l	02/93→08/96		
1.8 i 16V 4x4	85 kW	1.8 l	04/93→08/96		
1.8 TD	65 kW	1.8 l	06/93→08/96		
1.8 TD	66 kW	1.8 l	10/95→08/96		
1.8 TD	66 kW	1.8 l	11/95→08/96		
1.8 TD	66 kW	1.8 l	08/96→09/00		
2.0 i	96 kW	2 l	08/96→09/00		
2.0 i 16V	97 kW	2 l	01/93→08/96		
2.0 i 16V	97 kW	2 l	12/94→08/96		
2.0 i 16V	100 kW	2 l	02/93→08/96		
2.0 i 16V	100 kW	2 l	04/93→08/96		
2.0 i 16V 4x4	97 kW	2 l	12/94→08/96		
2.0 i 16V 4x4	100 kW	2 l	02/93→08/96		
2.0 i 16V 4x4	100 kW	2 l	04/93→08/96		
2.5 24V	125 kW	2.5 l	08/96→09/00		
2.5 24V	125 kW	2.5 l	06/00→09/00		
2.5 i 24V	125 kW	2.5 l	07/94→08/96		
2.5 ST 200	151 kW	2.5 l	05/99→09/00		

**FORD - MONDEO II Turnier (BNP) 08/96→09/00**

































1.6 i	66 kW	1.6 l	08/96→09/00		KH10041 ProKIT
1.8 i	85 kW	1.8 l	08/96→09/00		
1.8 TD	66 kW	1.8 l	08/96→09/00	; 12/97 -> 08/00; ;	KH30191 ProKIT
2.0 i	96 kW	2 l	08/96→09/00		
1.6 i 16V	70 kW	1.6 l	05/98→09/00		KH10041 ProKIT
				; -> 08/00; ;	KH30191 ProKIT
2.5 24V	125 kW	2.5 l	08/96→09/00		KH10041 ProKIT
				; 12/97 -> 08/00	KH30191 ProKIT
2.5 24V	125 kW	2.5 l	10/99→09/00		KH10041 ProKIT
				; 06/00 ->	KH30191 ProKIT
2.5 ST 200	151 kW	2.5 l	05/99→09/00		KH10041 ProKIT
				; -> 08/00	KH30191 ProKIT

**FORD - MONDEO III / MONDEO III Saloon / MONDEO III Turnier (B5Y, B4Y, BWY) 10/00→03/07**








































1.8 16V	81 kW	1.8 l	10/00→03/07		KH10038 ProKIT
1.8 16V	92 kW	1.8 l	10/00→03/07		KH30043 ProKIT
1.8 Sci	96 kW	1.8 l	06/03→03/07		
2.0 16V	107 kW	2 l	10/00→03/07		
2.0 16V DI / TDDi / TDCi	66 kW	2 l	10/00→03/07		
2.0 DI	92 kW	2 l	10/00→03/07		
2.2 TDCi	110 kW	2.2 l	09/04→03/07		
2.2 TDCi	114 kW	2.2 l	09/04→03/07		
3.0 V6 24V	150 kW	3 l	09/04→03/07		
ST220	166 kW	3 l	04/02→03/07		
2.0 16V TDDi / TDCi	85 kW	2 l	10/00→03/07	;	KH10038 ProKIT
2.0 TDCi	96 kW	2 l	10/01→03/07	;	KH10411 ProKIT
					KH30043 ProKIT
2.0 DI	92 kW	2 l	10/00→03/07		KH10038 ProKIT
2.5 V6	125 kW	2.5 l	10/00→03/07	; ; ;	KH10038 ProKIT
2.5 V6 24V	125 kW	2.5 l	10/00→03/07	; ; ;	KH10411 ProKIT
					KH30043 ProKIT







**FORD - MONDEO IV / MONDEO IV Saloon / MONDEO IV Turnier (BA7) 03/07→01/15**

1.6 EcoBoost	118 kW	1.6 l	11/10→01/15		KH20087 ProKIT
1.6 EcoBoost	118 kW	1.6 l	02/11→01/15		KH30081 ProKIT
1.6 TDCi	85 kW	1.6 l	12/10→01/15		
1.6 TDCi	85 kW	1.6 l	02/11→01/15		
1.6 Ti	81 kW	1.6 l	03/07→12/12		
1.6 Ti	81 kW	1.6 l	03/07→01/15		
1.6 Ti	88 kW	1.6 l	03/10→01/15		






				   	 13		
<b>FORD - MONDEO IV / MONDEO IV Saloon / MONDEO IV Turnier (BA7)</b>							<b>03/07→01/15</b>
1.6 Ti	88 kW	1.6 l	07/10→01/15				KH20087 ProKIT
1.6 Ti	92 kW	1.6 l	03/07→12/10				KH30081 ProKIT
1.6 Ti	92 kW	1.6 l	03/07→01/15				
1.8 TDCi	74 kW	1.8 l	03/07→12/12				
1.8 TDCi	74 kW	1.8 l	03/07→01/15				
1.8 TDCi	92 kW	1.8 l	06/07→12/12				
1.8 TDCi	92 kW	1.8 l	06/07→01/15				
2.0	107 kW	2 l	03/07→01/15				
2.0 EcoBoost	176 kW	2 l	03/10→09/14				
2.0 EcoBoost	176 kW	2 l	07/10→01/15				
2.0 Flexifuel	107 kW	2 l	03/09→01/15				
2.0 LPG	107 kW	2 l	07/09→01/15				
2.0 SCTi	149 kW	2 l	03/10→01/15				
2.0 SCTi	149 kW	2 l	03/10→01/15				
2.0 TDCi	85 kW	2 l	11/07→01/15				
2.0 TDCi	96 kW	2 l	03/07→12/12				
2.0 TDCi	96 kW	2 l	03/07→01/15				
2.0 TDCi	100 kW	2 l	03/07→12/14				
2.0 TDCi	100 kW	2 l	08/08→12/14				
2.0 TDCi	103 kW	2 l	03/07→01/15				
2.0 TDCi	120 kW	2 l	03/10→01/15				
2.2 TDCi	129 kW	2.2 l	03/08→10/10				
2.2 TDCi	147 kW	2.2 l	07/10→01/15				
2.2 TDCi	147 kW	2.2 l	10/10→01/15				
2.3	118 kW	2.3 l	07/07→01/15				
2.5	162 kW	2.5 l	03/07→12/12				
2.5	162 kW	2.5 l	03/07→01/15				
<b>FORD - ORION I / ORION II (AFD, AFF)</b>							<b>07/83→07/90</b>
1.3	44 kW	1.3 l	12/85→07/90	 ; -> 12/85			KH00009 ProKIT
1.3	51 kW	1.3 l	07/83→03/86				KH00023 ProKIT
1.4	52 kW	1.4 l	03/86→07/90				KH00009 ProKIT
1.4	54 kW	1.4 l	01/86→07/90				KH00023 ProKIT
1.4	55 kW	1.4 l	12/85→07/90				
1.4 Cat	54 kW	1.4 l	02/87→07/90				
1.6	58 kW	1.6 l	07/83→03/86				
1.6	66 kW	1.6 l	12/85→07/90				
1.6 D	40 kW	1.6 l	02/84→03/86				
1.6 D	40 kW	1.6 l	12/85→01/89				
1.6 i	75 kW	1.6 l	02/86→07/90				
1.6 i	77 kW	1.6 l	07/83→03/86				
1.6 i	77 kW	1.6 l	03/86→07/90				
1.6 i Cat	66 kW	1.6 l	03/86→07/90				
1.8 D	44 kW	1.8 l	01/89→07/90				
<b>FORD - ORION III (GAL)</b>							<b>07/90→12/93</b>
1.3	44 kW	1.3 l	07/90→12/93	 ; 10/91 ->			KH10097 ProKIT
1.4	52 kW	1.4 l	07/90→12/93	 ; -> 10/91; MT			KH00062 ProKIT
1.4	54 kW	1.4 l	07/90→12/93				
1.6	66 kW	1.6 l	07/90→12/92				KH00023 ProKIT
1.6 i	77 kW	1.6 l	07/90→09/92				KH00034 ProKIT
1.6 i 16V	66 kW	1.6 l	07/92→12/93				KH10097 ProKIT
1.8 i 16V	77 kW	1.8 l	02/92→12/93				KH00034 ProKIT
1.8 TD	66 kW	1.8 l	03/92→12/93				
1.8 D	44 kW	1.8 l	11/90→12/93	 ; 10/91 ->			KH10097 ProKIT
							KH00034 ProKIT
1.8 i 16V	96 kW	1.8 l	01/92→12/93				KH10097 ProKIT
							KH00023 ProKIT
							KH00034 ProKIT
<b>FORD - P 100 I</b>							<b>04/82→09/87</b>
1.6	54 kW	1.6 l	04/82→09/87				KH00023 ProKIT
<b>FORD - P 100 II</b>							<b>10/87→12/92</b>
1.8 TD	55 kW	1.8 l	10/87→12/92	 ; 02/89 ->			KH00078 ProKIT
							KH00023 ProKIT
2.0	57 kW	2 l	10/87→12/92	 ; 01/88 ->			KH00078 ProKIT
							KH00023 ProKIT
<b>FORD - PUMA (EC_)</b>							<b>03/97→06/02</b>
1.4 16V	66 kW	1.4 l	11/97→10/00				KH10097 ProKIT
							KH00004 ProKIT
1.6 16V	76 kW	1.6 l	08/00→06/02	 ; -> 12/01			KH10097 ProKIT
1.7 16V	92 kW	1.7 l	03/97→06/02				KH00004 ProKIT
Racing ST 160	114 kW	1.7 l	06/99→06/02				































				     13 		
<b>FORD - RANGER (ET, TU_, ER, EQ, R_)</b>				<b>06/99→07/12</b>		
1.8	85 kW	1.8 l	06/99→02/02		KH00119 ProKIT	
2.5 D	57 kW	2.5 l	10/99→04/02			
2.5 TD	62 kW	2.5 l	04/02→06/06			
3.0 TDCi	115 kW	3 l	05/06→07/12			
2.5 D 4x4	57 kW	2.5 l	10/99→04/02		KH00112 ProKIT	
2.5 TD 4x4	62 kW	2.5 l	04/02→06/06		KH10011 ProKIT	
2.5 TD 4x4	80 kW	2.5 l	10/99→06/06		KH00112 ProKIT	
					KH10011 ProKIT	
<b>FORD - SCORPIO I / SCORPIO I Saloon / SCORPIO I Turnier (GAE, GGE, GGE)</b>				<b>04/85→12/94</b>		
1.8	66 kW	1.8 l	04/85→02/92		KH00128 ProKIT	
2.0	77 kW	2 l	04/85→08/89		KH00076 ProKIT	
2.0 i	74 kW	2 l	10/85→12/90		KH00076 ProKIT	
2.0 i	85 kW	2 l	04/85→02/92			
2.0 i	85 kW	2 l	09/91→09/94			
2.0 i	85 kW	2 l	02/92→09/94			
2.0 i	88 kW	2 l	05/89→09/94			
2.0 i	88 kW	2 l	09/91→09/94			
2.4 i	92 kW	2.4 l	10/88→02/92			
2.4 i	92 kW	2.4 l	10/88→10/94			
2.4 i	92 kW	2.4 l	09/91→09/94			
2.4 i	96 kW	2.4 l	09/86→09/88			
2.4 i Cat	92 kW	2.4 l	10/88→09/94			
2.5 D	51 kW	2.5 l	12/85→02/92			
2.5 D	51 kW	2.5 l	12/89→12/94			
2.5 TD	68 kW	2.5 l	06/88→07/93			
2.5 TD	68 kW	2.5 l	09/91→07/93			
2.5 TD	85 kW	2.5 l	08/93→09/94			
2.8 i	110 kW	2.8 l	04/85→11/86			
2.9 24V	143 kW	2.9 l	08/93→09/94			
2.9 i	107 kW	2.9 l	09/86→09/94			
2.9 i	107 kW	2.9 l	09/86→12/94			
2.9 i	107 kW	2.9 l	09/91→09/94			
2.9 i	110 kW	2.9 l	09/86→09/94			
2.9 i 24V	143 kW	2.9 l	04/91→09/94			
2.9 i Cat	107 kW	2.9 l	10/87→09/94			
2.8 i 4x4	110 kW	2.8 l	10/85→11/86		KH00057 ProKIT	
2.9 i 4x4	110 kW	2.9 l	09/86→09/94		KH00076 ProKIT	
2.9 i 4x4	107 kW	2.9 l	05/88→02/93	 ; 02/92 ->	KH00057 ProKIT	
					KH00076 ProKIT	
2.9 i 4x4	107 kW	2.9 l	05/88→02/93	 ; 11/89 -> 01/92	KH00057 ProKIT	
					KH00076 ProKIT	
2.9 i 4x4	107 kW	2.9 l	12/89→10/94	 ; 01/90 -> 01/92	KH00057 ProKIT	
					KH00076 ProKIT	
<b>FORD - SCORPIO II / SCORPIO II Turnier (GFR, GGR, GNR, GGR)</b>				<b>10/94→08/98</b>		
2.0 i	85 kW	2 l	10/94→08/98	 ; 01/95 -> 10/97	KH00113 ProKIT	
				 ; -> 05/96	KH00076 ProKIT	
2.0 i 16V	100 kW	2 l	10/94→08/98	 ; 01/95 -> 08/96	KH00113 ProKIT	
				 ; -> 05/96	KH00076 ProKIT	
2.3 i 16V	108 kW	2.3 l	06/96→08/98	 ; -> 07/98	KH00113 ProKIT	
2.5 TD	85 kW	2.5 l	10/94→08/98	 ; 01/95 -> 07/98	KH00113 ProKIT	
2.9 i 24V	152 kW	2.9 l	10/94→08/98	 ; -> 05/96	KH00076 ProKIT	
2.9 i	110 kW	2.9 l	02/95→08/98	 ; -> 05/96	KH00076 ProKIT	
				 ; -> 08/96	KH00113 ProKIT	
<b>FORD - SIERRA I Hatchback (GBC)</b>				<b>08/82→12/86</b>		
1.3	44 kW	1.3 l	08/82→12/86	 ; 01/83 -> 12/85	KH00078 ProKIT	
				 ; 01/86 ->	KH00128 ProKIT	
				 ; 09/83 -> 12/85	KH00132 ProKIT	
1.6	55 kW	1.6 l	08/82→12/86	 ; 01/83 ->	KH00078 ProKIT	
2.0	77 kW	2 l	08/82→12/86	 ; 01/86 ->	KH00128 ProKIT	
				 ; 09/83 ->; 	KH00076 ProKIT	
				 ; 09/83 ->	KH00132 ProKIT	






     				13		i		
FORD - SIERRA I Hatchback (GBC)							08/82→12/86	
1.8	66 kW	1.8 l	10/84→12/86	; 01/86 ->		KH00128 ProKIT		
2.0	74 kW	2 l	10/85→12/86			KH00078 ProKIT		
				(ABS)		KH00076 ProKIT		
						KH00132 ProKIT		
2.0	66 kW	2 l	08/82→10/84	; 01/83 ->		KH00078 ProKIT		
						KH00128 ProKIT		
				; 09/83 ->; (ABS)		KH00076 ProKIT		
				; 09/83 ->		KH00132 ProKIT		
2.0 i	85 kW	2 l	03/85→12/86			KH00078 ProKIT		
				(ABS)		KH00076 ProKIT		
						KH00132 ProKIT		
2.3	84 kW	2.3 l	08/82→12/86	; 01/83 ->		KH00078 ProKIT		
				; 01/86 ->		KH00128 ProKIT		
				; 09/82 ->		KH00132 ProKIT		
				; 09/83 ->; (ABS)		KH00076 ProKIT		
2.3 D	49 kW	2.3 l	08/82→12/86	; 10/82 ->		KH00078 ProKIT		
				; 09/83 ->; (ABS)		KH00076 ProKIT		
				; 09/83 ->		KH00132 ProKIT		
2.8 i XR 4x4	107 kW	2.8 l	09/83→12/86			KH00057 ProKIT		
2.8 XR 4x4	110 kW	2.8 l	02/85→12/86	; 06/85 ->		KH00076 ProKIT		
2.8 XR4i	105 kW	2.8 l	08/82→12/86	; 10/83 ->; (ABS)		KH00076 ProKIT		
2.8 XR4i	110 kW	2.8 l	08/82→12/86					
2.8 XR4i	107 kW	2.8 l	08/82→12/86	; 01/83 ->		KH00078 ProKIT		
				; 09/83 ->		KH00132 ProKIT		
				; 10/83 ->; (ABS)		KH00076 ProKIT		
FORD - SIERRA II / SIERRA II Hatchback / SIERRA II Turnier (GBG, GB4, GBC, GBG, BNG)							01/87→02/93	
1.6	53 kW	1.6 l	01/88→02/93	; -> 01/90		KH00128 ProKIT		
1.6	55 kW	1.6 l	01/87→02/93	; -> 01/93		KH00078 ProKIT		
				; -> 01/93; (ABS)		KH00132 ProKIT		
				(ABS)		KH00076 ProKIT		
1.6 i	59 kW	1.6 l	10/89→02/93	; -> 01/93		KH00078 ProKIT		
2.0 i	74 kW	2 l	01/87→02/93			KH00132 ProKIT		
2.0 i	88 kW	2 l	05/89→02/93	; -> 01/93; (ABS)		KH00132 ProKIT		
2.0 i	88 kW	2 l	01/90→02/93	(ABS)		KH00076 ProKIT		
2.0 i	92 kW	2 l	05/89→02/93					
2.0 i	92 kW	2 l	06/89→02/93					
2.0 i	92 kW	2 l	01/90→02/93					
2.0 i Cat	74 kW	2 l	01/87→02/93					
2.0 i DOHC	85 kW	2 l	12/91→02/93					
1.6 i	59 kW	1.6 l	10/89→02/93	; -> 12/92		KH00078 ProKIT		
				; -> 12/92; (ABS)		KH00132 ProKIT		
				(ABS)		KH00076 ProKIT		
1.8	59 kW	1.8 l	10/87→05/88			KH00078 ProKIT		
						KH00128 ProKIT		
				(ABS)		KH00076 ProKIT		
1.8	59 kW	1.8 l	10/87→09/89			KH00128 ProKIT		
				(ABS)		KH00076 ProKIT		
1.8	64 kW	1.8 l	05/88→02/93	; 07/88 -> 01/93		KH00078 ProKIT		
				; -> 01/90		KH00128 ProKIT		
				; 07/88 -> 01/93; (ABS)		KH00132 ProKIT		
				(ABS)		KH00076 ProKIT		
1.8	66 kW	1.8 l	01/87→05/88			KH00078 ProKIT		
						KH00128 ProKIT		
				(ABS)		KH00076 ProKIT		
				(ABS)		KH00132 ProKIT		
1.8 TD	55 kW	1.8 l	08/88→02/93	; 01/90 -> 01/93		KH00078 ProKIT		
2.0 i	88 kW	2 l	06/89→02/93	; 01/90 -> 01/93; (ABS)		KH00132 ProKIT		
				(ABS)		KH00076 ProKIT		
1.8 TD	55 kW	1.8 l	08/88→02/93	; 01/90 -> 01/93		KH00078 ProKIT		
				(ABS)		KH00076 ProKIT		





































































										
<b>FORD - SIERRA II / SIERRA II Hatchback / SIERRA II Turnier (GBG, GB4, GBC, GBG, BNG)</b>										<b>01/87→02/93</b>
2.0	77 kW	2 l	01/87→02/93		-> 01/90				KH00128 ProKIT	
					-> 12/90				KH00078 ProKIT	
					-> 12/90;	ABS			KH00132 ProKIT	
					ABS				KH00076 ProKIT	
2.0 16V Cosworth 4x4	162 kW	2 l	01/90→02/93						KH00076 ProKIT	
2.0 16V Cosworth Cat 4x4	162 kW	2 l	01/90→02/93							
2.0 4x4	88 kW	2 l	01/90→02/93		-> 01/93				KH00057 ProKIT	
2.0 4x4	92 kW	2 l	01/90→02/93		ABS				KH00076 ProKIT	
2.9 4x4	107 kW	2.9 l	08/88→02/93							
2.9 4x4	110 kW	2.9 l	08/88→02/93							
2.0 4x4	88 kW	2 l	02/90→02/93		ABS				KH00076 ProKIT	
2.0 4x4	92 kW	2 l	05/89→02/93							
2.8 4x4	110 kW	2.8 l	01/87→08/88							
2.0 i	74 kW	2 l	01/87→12/89						KH00078 ProKIT	
2.3 D	49 kW	2.3 l	01/87→09/89		ABS				KH00076 ProKIT	
					ABS				KH00132 ProKIT	
2.0 i	85 kW	2 l	01/87→02/93		-> 12/90				KH00078 ProKIT	
					-> 12/90;	ABS			KH00132 ProKIT	
					ABS				KH00076 ProKIT	
2.0 RS Cosworth	150 kW	2 l	11/87→01/90		-> 12/87				KH00132 ProKIT	
									KH00076 ProKIT	
2.3 D	49 kW	2.3 l	01/87→02/93		-> 12/90				KH00078 ProKIT	
					ABS				KH00076 ProKIT	
2.8 i XR 4x4	110 kW	2.8 l	01/87→08/88		-> 03/88				KH00057 ProKIT	
									KH00076 ProKIT	
2.9	107 kW	2.9 l	08/88→02/93		-> 01/90				KH00128 ProKIT	
					-> 01/93				KH00078 ProKIT	
					ABS				KH00076 ProKIT	
2.9 i	107 kW	2.9 l	08/88→02/93		-> 01/93				KH00078 ProKIT	
2.9 i	110 kW	2.9 l	08/88→02/93		ABS				KH00076 ProKIT	
2.9 i XR 4x4	107 kW	2.9 l	08/88→02/93		-> 01/93				KH00057 ProKIT	
2.9 i XR 4x4	110 kW	2.9 l	08/88→02/93						KH00076 ProKIT	
<b>FORD - SIERRA Turnier (BNC)</b>										<b>08/82→12/86</b>
1.6	55 kW	1.6 l	08/82→12/86		01/86 ->				KH00128 ProKIT	
					-> 12/85				KH00078 ProKIT	
					09/83 ->	ABS			KH00076 ProKIT	
									KH00132 ProKIT	
1.8	66 kW	1.8 l	10/84→12/86		01/86 ->				KH00128 ProKIT	
2.0	74 kW	2 l	10/85→12/86						KH00078 ProKIT	
2.0	85 kW	2 l	03/85→12/86							
					ABS				KH00076 ProKIT	
									KH00132 ProKIT	
2.0	66 kW	2 l	08/82→10/84		-> 01/83				KH00078 ProKIT	
									KH00128 ProKIT	
					09/83 ->	ABS			KH00076 ProKIT	
					09/83 ->				KH00132 ProKIT	
2.0	77 kW	2 l	08/82→12/86		01/83 ->				KH00078 ProKIT	
					01/86 ->				KH00128 ProKIT	
					09/83 ->	ABS			KH00076 ProKIT	
									KH00132 ProKIT	
2.3	84 kW	2.3 l	08/82→12/86		01/83 -> 12/85				KH00078 ProKIT	
					01/86 ->				KH00128 ProKIT	
					09/83 -> 12/85				KH00132 ProKIT	
					09/83 ->	ABS			KH00076 ProKIT	
2.3 D	49 kW	2.3 l	08/82→12/86		01/83 ->				KH00078 ProKIT	
					09/83 ->	ABS			KH00076 ProKIT	
					09/83 ->	ABS			KH00132 ProKIT	
2.8 i 4x4	105 kW	2.8 l	08/82→12/86		01/83 ->				KH00057 ProKIT	
					06/85 ->				KH00076 ProKIT	

     						
<b>FORD - SIERRA Turnier (BNC)</b>					<b>08/82→12/86</b>	
2.8 i 4x4	107 kW	2.8 l	08/82→12/86	 ; 01/83 ->  ; 01/83 ->  ; 09/83 ->  ; 06/85 ->	KH00057 ProKIT KH00078 ProKIT KH00132 ProKIT KH00076 ProKIT	
2.8 XR4i	105 kW	2.8 l	08/82→12/86	 ; 10/83 ->; 	KH00076 ProKIT	
2.8 XR4i	107 kW	2.8 l	08/82→12/86	 ; 01/83 ->  ; 09/83 ->  ; 10/83 ->; 	KH00078 ProKIT KH00132 ProKIT KH00076 ProKIT	
<b>FORD - S-MAX (WA6)</b>					<b>05/06→12/14</b>	
1.6 EcoBoost	118 kW	1.6 l	02/11→12/14		KH20045 ProKIT	
1.6 TDCi	85 kW	1.6 l	02/11→12/14			
1.8 TDCi	74 kW	1.8 l	01/07→12/10			
1.8 TDCi	92 kW	1.8 l	05/06→12/14			
2.0	107 kW	2 l	05/06→12/14			
2.0 EcoBoost	146 kW	2 l	07/10→12/14			
2.0 EcoBoost	149 kW	2 l	03/10→12/14			
2.0 EcoBoost	176 kW	2 l	07/10→12/14			
2.0 Flexifuel	107 kW	2 l	05/06→12/14			
2.0 TDCi	85 kW	2 l	11/07→12/14			
2.0 TDCi	96 kW	2 l	05/06→12/14			
2.0 TDCi	100 kW	2 l	05/06→12/14			
2.0 TDCi	103 kW	2 l	05/06→12/14			
2.0 TDCi	120 kW	2 l	03/10→12/14			
2.2 TDCi	129 kW	2.2 l	03/08→12/12			
2.2 TDCi	147 kW	2.2 l	07/10→12/14			
2.3	118 kW	2.3 l	07/07→12/14			
2.5 ST	162 kW	2.5 l	05/06→12/14			
<b>FORD - STREET KA (RL2)</b>					<b>05/03→07/05</b>	
1.6	70 kW	1.6 l	05/03→07/05		KH10210 ProKIT	
<b>FORD - TAUNUS / TAUNUS III Turnier / TAUNUS V / TAUNUS Coupe / TAUNUS Turnier (GBFK, GBTK, GBTS, GBFS, CBTS, GBNS, GBS, GBNS, GBCK, GBNK)</b>					<b>01/70→07/82</b>	
1.3	40 kW	1.3 l	05/75→07/79		KH00045 ProKIT	
1.3	40 kW	1.3 l	12/75→07/79			
1.3	43 kW	1.3 l	05/75→07/79			
1.3	43 kW	1.3 l	07/79→07/82			
1.3 (CBTS)	40 kW	1.3 l	09/76→07/79			
1.6	50 kW	1.6 l	05/75→07/79			
1.6	51 kW	1.6 l	07/79→07/82			
1.6	53 kW	1.6 l	05/75→07/79			
1.6	54 kW	1.6 l	07/79→07/82			
1.6	65 kW	1.6 l	08/76→07/79			
1.6	65 kW	1.6 l	07/79→07/82			
1300	40 kW	1.3 l	01/70→05/75			
1300	40 kW	1.3 l	08/70→02/76			
1600	50 kW	1.6 l	01/74→05/75			
1600	53 kW	1.6 l	01/70→05/75			
1600	53 kW	1.6 l	08/70→02/76			
1600	65 kW	1.6 l	08/70→02/76			
2.0	66 kW	2 l	05/75→07/79			
2.0	66 kW	2 l	07/79→07/82			
2.0	74 kW	2 l	07/79→07/82			
2.3	79 kW	2.3 l	05/75→07/79			
2.3	84 kW	2.3 l	07/79→07/82			
2000 V6	66 kW	2 l	08/70→02/76			
2300 V6	79 kW	2.3 l	08/71→02/76			
<b>FORD - TOURNEO CONNECT</b>					<b>06/02→12/13</b>	
1.8 16V	85 kW	1.8 l	06/02→12/13	 ; -> 05/11; 	KH10116 ProKIT	
1.8 TDCi	66 kW	1.8 l	06/02→12/13	 ; 	KH10105 ProKIT	
1.8 TDCi	81 kW	1.8 l	08/06→12/13	 ; 	KH20084 ProKIT	
1.8 TDCi / TDDi / DI	55 kW	1.8 l	06/02→12/13	 ; 		
<b>FORD - TOURNEO CONNECT / GRAND TOURNEO CONNECT V408 MPV</b>					<b>09/13→</b>	
1.0 EcoBoost	74 kW	1 l	11/13→		KH10126 ProKIT	
1.5 TDCi	55 kW	1.5 l	05/15→			
1.5 TDCi	74 kW	1.5 l	05/15→			
1.5 TDCi	88 kW	1.5 l	05/15→			
1.6 EcoBoost	110 kW	1.6 l	11/13→			
1.6 TDCi	55 kW	1.6 l	09/13→			
1.6 TDCi	70 kW	1.6 l	09/13→			
1.6 TDCi	85 kW	1.6 l	09/13→			



    					
<b>FORD - TOURNEO COURIER B460 MPV</b>				<b>02/14→</b>	
1.0 EcoBoost	74 kW	1 l	02/14→		KH10070 ProKIT
1.5 TDCi	55 kW	1.5 l	02/14→		
1.5 TDCi	70 kW	1.5 l	05/15→		
1.6 TDCi	70 kW	1.6 l	02/14→		
<b>FORD - TRANSIT Bus (E_ _)</b>				<b>01/91→06/00</b>	
2.0	66 kW	2 l	09/91→09/94		KH00013 ProKIT
				; Trim Level: 15 SEAT; 10/91 -> 08/94; Axle Version: 53;	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.0 (EBL, EBS, ECL, EDS, EDL, EGL, ESS, ESL, EUS)	84 kW	2 l	08/94→03/00		KH00013 ProKIT
2.5 TD (EBL, EDL, EDS, EGL, ESL, ESS, EUS)	63 kW	2.5 l	01/95→03/00	; Trim Level: 15 SEAT; Axle Version: 53;	KH00025 ProKIT
2.5 TD (EBS, EBL, ECL, EDS, EDL, ESS, EUS)	63 kW	2.5 l	10/92→07/94	; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.0 CNG	84 kW	2 l	06/94→03/00		KH00013 ProKIT
2.5 DI (EBL, EDL, EDS, ESL, ESS)	85 kW	2.5 l	08/97→03/00	; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EBL, EDS, ESL, ESS, EUS)	51 kW	2.5 l	08/94→03/00		
2.5 TD (EB_ , ED_ , ES_ )	55 kW	2.5 l	08/94→06/00		
2.5 TD (ECL, EDL, EDS, ESL, ESS, EUS)	74 kW	2.5 l	07/94→03/00		
2.0 i (EBL, EDL, EGL, ESS, EUS)	72 kW	2 l	09/91→07/94		KH00013 ProKIT
				; Trim Level: 15/17 SEAT; 10/91 ->; Axle Version: 53;	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EBL, ECL, EDS, EDL)	56 kW	2.5 l	07/94→03/00		KH00013 ProKIT
				; Axle Version: 53;	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EBS, EDS, EDL, ESS, EUS)	51 kW	2.5 l	08/91→07/94	; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 TD (ECL, EDS, EDL, EGL, ESS, EUS)	74 kW	2.5 l	09/91→07/94		
2.9 i	107 kW	2.9 l	01/91→09/94		
2.5 DI (EBS, EDS, EGL, ESS, EUS)	59 kW	2.5 l	09/91→07/94	; -> 09/91; Axle Version: 34,51,52, 53 REAR	KH00022 ProKIT
				; -> 09/91;	
				; -> 09/91;	KH00025 ProKIT
				; -> 09/91; Axle Version: 51, 52 & 53	
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
<b>FORD - TRANSIT Bus (FD_ _ , FB_ _ , FS_ _ , FZ_ _ , FC_ _ )</b>				<b>04/06→12/14</b>	
2.2 TDCi	63 kW	2.2 l	04/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi	74 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi	81 kW	2.2 l	04/06→08/14	; Payload: for increased payload	
2.2 TDCi	85 kW	2.2 l	10/08→08/14		KH20039 ProKIT
2.2 TDCi	92 kW	2.2 l	10/11→08/14		KH20023 ProKIT
2.2 TDCi	96 kW	2.2 l	04/06→08/14	; -> 06/14;	KH20023 ProKIT
2.2 TDCi	103 kW	2.2 l	10/07→08/14	;	KH20029 ProKIT
2.2 TDCi RWD	74 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi RWD	92 kW	2.2 l	09/11→12/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi RWD	100 kW	2.2 l	09/11→08/14	; Payload: for increased payload	
2.4 TDCi	74 kW	2.4 l	04/06→08/14		KH20039 ProKIT
2.4 TDCi	85 kW	2.4 l	04/06→08/14		KH20039 ProKIT
2.4 TDCi	103 kW	2.4 l	04/06→08/14	; Axle Version: Dana	KH00066 ProKIT
3.2 TDCi	147 kW	3.2 l	02/08→08/14		
2.4 TDCi 4x4	103 kW	2.4 l	11/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
				; Axle Load [kg]: 1,850; Payload: for increased payload	KH20018 ProKIT
<b>FORDi - TRANSIT Bus (FD_ _ , FB_ _ , FS_ _ , FZ_ _ , FC_ _ )</b>				<b>01/00→05/06</b>	
2.0	84 kW	2 l	09/00→03/06	; 07/03 ->; Code: 330 / 350;	KH20120 ProKIT
				; Code: 260 / 280 / 300;;	KH20074 ProKIT
				; Code: 260 / 280 / 300;;	KH20127 ProKIT
2.0 DI (F_E_ , F_F_ , F_G_ )	55 kW	2 l	08/00→05/06		KH20039 ProKIT
2.0 DI (F_E_ , F_F_ , F_G_ )	63 kW	2 l	08/00→05/06	; 07/03 ->; Code: 330 / 350;	KH20120 ProKIT
2.0 DI (F_E_ , F_F_ , F_G_ )	74 kW	2 l	08/00→05/06		
2.0 TDCi (F_F_ , F_E_ , F_G_ )	92 kW	2 l	08/02→05/06	; Code: 260 / 280 / 300;;	KH20074 ProKIT
				; Code: 260 / 280 / 300;;	KH20127 ProKIT
2.3 16V RWD (F_B_ , F_C_ , F_A_ )	107 kW	2.3 l	08/00→05/06		KH20039 ProKIT
2.4 DI RWD (F_B_ , F_C_ )	55 kW	2.4 l	01/00→05/06	; Axle Version: Dana	KH00029 ProKIT
2.4 TDCi	101 kW	2.4 l	03/04→05/06	; Axle Version: Dana	KH00066 ProKIT
2.4 TDE	85 kW	2.4 l	03/04→05/06	; Axle Version: Dana	KH00066 ProKIT
2.4 TDE (F_C_ , F_B_ , F_A_ )	92 kW	2.4 l	07/01→05/06	;	KH00070 ProKIT

























    					
<b>FORD - TRANSIT Bus (FD_ , FB_ , FS_ , FZ_ , FC_ )</b>				<b>01/00→05/06</b>	
2.4 DI (F_B_ , F_C_ , F_A_ )	66 kW	2.4 l	01/00→05/06	 ; 03/00 -> 03/06;  ;  ;  ;  ; Payload	KH00025 ProKIT
2.4 DI RWD (F_B_ , F_C_ , F_A_ )	88 kW	2.4 l	01/00→05/06	 ; 08/01 -> 03/06;  ;  ;  ; Payload from [kg]: 1,349 → Payload to [kg]: 1,843	
				 ; 08/01 -> 03/06;  ;  ;  ; Payload from [kg]: 1,935 → Payload to [kg]: 2,382	
				 ; 	KH20039 ProKIT
				 ; Axle Version: Dana	KH00029 ProKIT
				 ; Axle Version: Dana	KH00066 ProKIT
				 ; 	KH00070 ProKIT
<b>FORD - TRANSIT Bus (V_ )</b>				<b>12/77→10/86</b>	
1.6 (VAS, VLS, VZS)	48 kW	1.6 l	12/77→10/86	 ; -> 01/78; Axle Version: 32, 34 REAR	KH00022 ProKIT
2.4 D (VAS, VBL, VIL, VUL, VZS)	46 kW	2.4 l	12/77→10/86	 ; -> 01/78	KH00022 ProKIT
<b>FORD - TRANSIT CONNECT (P65_ , P70_ , P80_ )</b>				<b>06/02→12/13</b>	
1.8 16V	85 kW	1.8 l	06/02→12/13	 ; -> 05/11; 	KH10116 ProKIT
1.8 16V LPG	85 kW	1.8 l	06/02→12/13	 ; 	KH10105 ProKIT
1.8 Di	55 kW	1.8 l	06/02→12/13	 ; 	KH20084 ProKIT
1.8 TDCi	66 kW	1.8 l	06/02→12/13	 ; 	
1.8 TDCi	81 kW	1.8 l	08/06→12/13		
<b>FORD - TRANSIT CONNECT MPV / TRANSIT CONNECT V408 Box Body/MPV</b>				<b>02/13→</b>	
1.0 EcoBoost	74 kW	1 l	02/13→		KH10126 ProKIT
1.5 TDCi	55 kW	1.5 l	08/15→		
1.5 TDCi	74 kW	1.5 l	05/15→		
1.5 TDCi	88 kW	1.5 l	05/15→		
1.6 EcoBoost	110 kW	1.6 l	11/13→		
1.6 TDCi	55 kW	1.6 l	02/13→		
1.6 TDCi	70 kW	1.6 l	02/13→		
1.6 TDCi	85 kW	1.6 l	02/13→		
<b>FORD - TRANSIT COURIER B460 Box Body/MPV / TRANSIT COURIER B460 MPV</b>				<b>02/14→</b>	
1.0 EcoBoost	74 kW	1 l	02/14→		KH10070 ProKIT
1.5 TDCi	55 kW	1.5 l	02/14→		
1.5 TDCi	70 kW	1.5 l	05/15→		
1.6 TDCi	70 kW	1.6 l	02/14→		
<b>FORD - TRANSIT Platform/Chassis (E_ )</b>				<b>09/91→03/00</b>	
2.0 (EME/L/S, ENE/L/S)	72 kW	2 l	09/91→08/94		KH00013 ProKIT
				 ; 10/91 ->	KH00025 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.0 (EME/L/S, ENE/L/S)	84 kW	2 l	08/94→03/00		KH00013 ProKIT
				 ; 09/94 ->; Axle Version: 53; 	KH00025 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EME/L/S, ENE/L/S)	56 kW	2.5 l	08/94→03/00		KH00013 ProKIT
2.5 TD (EME/L/S, ENE/L/S)	63 kW	2.5 l	11/92→08/94		KH00025 ProKIT
2.5 TD (EME/L/S, ENE/L/S)	63 kW	2.5 l	08/94→03/00		KH10127 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	
2.5 DI (EME/L/S, ENE/L/S)	59 kW	2.5 l	09/91→08/94	-> 09/91;  ; Axle Version: 51,52 & 53	KH00025 ProKIT
				 ; 	
				 ; -> 09/91; Axle Version: 34,51,52,53 REAR; 	KH00022 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EML, ENE/L)	85 kW	2.5 l	05/99→03/00		KH00013 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EML/S, ENL/S)	51 kW	2.5 l	09/91→08/94		KH10127 ProKIT
2.5 TD (EME/L/S, ENE/L)	74 kW	2.5 l	09/91→08/94		
2.5 DI (EML/S, ENL/S)	51 kW	2.5 l	08/94→03/00		KH00013 ProKIT
				 ; 	KH00025 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 TD	55 kW	2.5 l	08/94→03/00		KH00013 ProKIT
2.5 TD (EME/L/S, ENE/L/S)	74 kW	2.5 l	08/94→03/00		KH00013 ProKIT
				 ; Axle Version: 53	KH00025 ProKIT
				 ; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT



<b>FORD - TRANSIT Platform/Chassis (FM_, FN_, FF_)</b>				<b>04/06→08/14</b>	
2.2 TDCi	63 kW	2.2 l	04/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi	74 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi	81 kW	2.2 l	04/06→08/14	; Payload: for increased payload	
2.2 TDCi	85 kW	2.2 l	10/08→08/14		KH20039 ProKIT
2.2 TDCi	92 kW	2.2 l	10/11→08/14		KH20023 ProKIT
2.2 TDCi	96 kW	2.2 l	04/06→08/14	; > 06/14;	KH20029 ProKIT
				;	KH20029 ProKIT
2.2 TDCi	103 kW	2.2 l	10/07→09/11	; Axle Load [kg]: 1,750	KH20011 ProKIT
				; Axle Load [kg]: 1,850;	KH20018 ProKIT
				; Payload: for increased payload	
					KH20039 ProKIT
				;	KH20023 ProKIT
				;	KH20029 ProKIT
2.2 TDCi 4x4	92 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.4 TDCi 4x4	103 kW	2.4 l	11/06→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
				; Payload: for increased payload	
2.2 TDCi RWD	74 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi RWD	92 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi RWD	114 kW	2.2 l	10/11→08/14	; Payload: for increased payload	
2.3 16V RWD	107 kW	2.3 l	04/06→08/14		KH20039 ProKIT
2.4 TDCi RWD	74 kW	2.4 l	04/06→08/14		
2.4 TDCi RWD	85 kW	2.4 l	04/06→08/14	; Axle Version: Dana	KH00066 ProKIT
2.4 TDCi RWD	103 kW	2.4 l	04/06→08/14		
3.2 TDCi RWD	147 kW	3.2 l	09/07→08/14		
2.3 16V CNG RWD	100 kW	2.3 l	04/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.3 16V LPG RWD	107 kW	2.3 l	04/06→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
				; Payload: for increased payload	
					KH20039 ProKIT
<b>FORD - TRANSIT Platform/Chassis (FM_, FN_)</b>				<b>01/00→05/06</b>	
2.0 DI (F_E_, F_F_)	55 kW	2 l	08/00→05/06		KH20039 ProKIT
2.0 DI (F_E_, F_F_)	63 kW	2 l	08/00→05/06	; 07/03 ->; Code: 330 / 350;	KH20120 ProKIT
2.0 DI (F_E_, F_F_)	74 kW	2 l	08/00→05/06	; Code: 260 / 280 / 300;;	KH20074 ProKIT
2.0 TDCi (F_E_, F_F_)	92 kW	2 l	08/02→05/06	; Code: 260 / 280 / 300;;	KH20127 ProKIT
2.3 16V (F_A_, F_B_, F_C_, F_D_)	107 kW	2.3 l	04/01→05/06		KH20039 ProKIT
				; > 03/06; ; ; ; ; ; Payload from	KH00025 ProKIT
				; [kg]: 1,349 → Payload to [kg]: 1,843	
				; Axle Version: Dana	KH00029 ProKIT
				; Axle Version: Dana	KH00066 ProKIT
				;	KH00070 ProKIT
2.3 BiFuel	105 kW	2.3 l	03/01→03/06		KH20039 ProKIT
2.4 DI (F_A_, F_B_, F_C_, F_D_)	55 kW	2.4 l	01/00→05/06		KH20039 ProKIT
				; 03/00 -> 03/01; ; ; ; ; ; Payload	KH00025 ProKIT
				; from [kg]: 1,349 → Payload to [kg]: 1,602	
				; Axle Version: Dana	KH00029 ProKIT
				; Axle Version: Dana	KH00066 ProKIT
				;	KH00070 ProKIT
2.4 DI (F_A_, F_B_, F_C_, F_D_)	66 kW	2.4 l	01/00→05/06	; 03/00 -> 03/06; ; ; ; ; ; Payload	KH00025 ProKIT
2.4 DI (F_A_, F_B_, F_C_, F_D_)	88 kW	2.4 l	01/00→05/06	; from [kg]: 1,349 → Payload to [kg]: 1,843	
				; 08/01 -> 03/06; ; ; ; ; ; Payload from	
				; [kg]: 1,935 → Payload to [kg]: 2,382	
					KH20039 ProKIT
				; Axle Version: Dana	KH00029 ProKIT
				; Axle Version: Dana	KH00066 ProKIT
				;	KH00070 ProKIT
2.4 TDCi	101 kW	2.4 l	03/04→05/06		KH20039 ProKIT
2.4 TDE	85 kW	2.4 l	03/04→05/06	; Axle Version: Dana	KH00029 ProKIT
2.4 TDE	92 kW	2.4 l	07/01→05/06	; Axle Version: Dana	KH00066 ProKIT
				;	KH00070 ProKIT
<b>FORD - TRANSIT Platform/Chassis (T_)</b>				<b>11/85→09/92</b>	
2.0 (TTE, TTL, TTS)	57 kW	2 l	01/86→09/92	; 02/86 -> 09/91; Axle Version: 51,52 & 53 REAR	KH00022 ProKIT
				; 02/86 -> 09/91; Axle Version: 51,52 & 53	KH00025 ProKIT
2.0 Cat (TUL)	57 kW	2 l	11/85→09/92	; 02/86 -> 09/91; Axle Version: 51,52,53 REAR	KH00022 ProKIT
				; 02/86 -> 09/91; Axle Version: 51,52 & 53	KH00025 ProKIT
2.5 D (TTL, TTS, TUL, TUS, TTE)	50 kW	2.5 l	01/86→01/89	; 02/86 ->; Axle Version: 51,52,53 REAR	KH00022 ProKIT
				; 02/86 ->; Axle Version: 51,52 & 53	KH00025 ProKIT

<b>FORD - TRANSIT Platform/Chassis (V_ _)</b>				<b>11/77→10/86</b>	
1.6 (VCS, VDS)	48 kW	1.6 l	11/77→10/86	; -> 01/78; Axle Version: 34 REAR	KH00022 ProKIT
2.4 D (VGL, VSL, VTL, VCS, VDS)	46 kW	2.4 l	11/77→09/85	; -> 01/78	KH00022 ProKIT
<b>FORD - TRANSIT TOURNEO Bus</b>				<b>08/94→12/00</b>	
2.0	84 kW	2 l	11/94→12/00		KH00013 ProKIT
2.4 D	55 kW	2.4 l	08/94→06/00		
2.5 DI	51 kW	2.5 l	11/94→12/00		
2.5 DI	56 kW	2.5 l	11/94→12/00		
2.5 TD	63 kW	2.5 l	11/94→12/00		
2.5 TD	74 kW	2.5 l	04/98→12/00		
<b>FORD - TRANSIT TOURNEO Bus</b>				<b>07/06→08/14</b>	
2.2 TDCi	81 kW	2.2 l	07/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi	85 kW	2.2 l	10/08→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi	96 kW	2.2 l	07/06→08/14	Payload: for increased payload	
2.2 TDCi	103 kW	2.2 l	10/07→08/14		
<b>FORD - TRANSIT V363 Bus / TRANSIT V363 Platform/Chassis / TRANSIT V363 Van (FAD, FBD, VQ, FED, FFD, FCD, FDD)</b>				<b>08/13→12/18</b>	
2.2 TDCi	74 kW	2.2 l	08/13→12/18	; -> 12/14; (ABS)	KH20029 ProKIT
2.2 TDCi	92 kW	2.2 l	08/13→12/18		
2.2 TDCi	114 kW	2.2 l	08/13→12/18		
<b>FORD - TRANSIT Van (72E, 71E)</b>				<b>04/71→03/78</b>	
1.7 FT 100	48 kW	1.7 l	04/71→03/78	; -> 12/73	KH00022 ProKIT
<b>FORD - TRANSIT Van (E_ _)</b>				<b>05/91→06/94</b>	
2.0	66 kW	2 l	09/91→06/94		KH00013 ProKIT
2.0 i (EAL, EAS)	72 kW	2 l	09/91→06/94	; 10/91 ->	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EAL, EAS)	51 kW	2.5 l	05/91→06/94	; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 TD (EAS, EAL)	74 kW	2.5 l	05/91→06/94		
2.5 DI (EAL, EAS)	63 kW	2.5 l	10/92→06/94		KH00013 ProKIT
				; 11/92 ->	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EAS, EAL)	59 kW	2.5 l	05/91→06/94	; -> 09/91; Axle Version: 51,52 & 53	KH00025 ProKIT
				; -> 09/91; (ABS)	
				; -> 09/91; Axle Version: 34,51,52,53 REAR; (ABS)	KH00022 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
<b>FORD - TRANSIT Van (E_ _)</b>				<b>06/94→03/00</b>	
2.0 (EAL, EAS)	84 kW	2 l	06/94→03/00		KH00013 ProKIT
				; 09/94 ->	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EAL, EAS)	51 kW	2.5 l	06/94→03/00		KH00013 ProKIT
				; (ABS)	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EAL, EAS)	56 kW	2.5 l	06/94→03/00		KH00013 ProKIT
				; Axle Version: 52; (ABS)	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 DI (EAL, EAS)	85 kW	2.5 l	05/99→03/00		KH00013 ProKIT
2.5 TD (EAS)	55 kW	2.5 l	10/98→03/00	; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 TD (EAL, EAS)	63 kW	2.5 l	06/94→03/00	; Axle Version: 53	KH00025 ProKIT
				; (ABS)	
					KH00013 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
2.5 TDI (EAL, EAS)	74 kW	2.5 l	06/94→03/00	; Axle Version: 53	KH00013 ProKIT
				; Axle Version: 53	KH00025 ProKIT
				; Axle Version: TYP 34; Code: 80-120	KH10127 ProKIT
<b>FORD - TRANSIT Van (FA_ _)</b>				<b>04/06→12/14</b>	
2.2 TDCi	63 kW	2.2 l	04/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT
2.2 TDCi	74 kW	2.2 l	10/11→08/14		
2.2 TDCi	81 kW	2.2 l	04/06→08/14	; Axle Load [kg]: 1,850;	KH20018 ProKIT
2.2 TDCi	85 kW	2.2 l	10/08→08/14	Payload: for increased payload	
2.2 TDCi	92 kW	2.2 l	10/11→08/14		KH20039 ProKIT
2.2 TDCi	96 kW	2.2 l	04/06→08/14	; -> 06/14; (ABS)	KH20023 ProKIT
2.2 TDCi	103 kW	2.2 l	10/07→08/14	; (ABS)	KH20029 ProKIT

    									
FORD - TRANSIT Van (FA_ _)				04/06→12/14					
2.2 TDCi 4x4	92 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT				
				; Axle Load [kg]: 1,850; Payload: for increased payload	KH20018 ProKIT				
				; Axle Version: Dana	KH00066 ProKIT				
2.2 TDCi RWD	74 kW	2.2 l	10/11→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT				
				; Axle Load [kg]: 1,850; Payload: for increased payload	KH20018 ProKIT				
						KH20039 ProKIT			
				2.4 TDCi RWD	85 kW	2.4 l	04/06→08/14	; Axle Version: Dana	KH00066 ProKIT
				2.3 16V RWD	107 kW	2.3 l	04/06→08/14		
2.3 16V CNG RWD	100 kW	2.3 l	04/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT				
				; Axle Load [kg]: 1,850; Payload: for increased payload	KH20018 ProKIT				
2.3 16V LPG RWD	107 kW	2.3 l	04/06→08/14		KH20039 ProKIT				
2.4 TDCi 4x4	103 kW	2.4 l	11/06→08/14	; Axle Load [kg]: 1,750	KH20011 ProKIT				
				; Axle Load [kg]: 1,850; Payload: for increased payload	KH20018 ProKIT				
FORD - TRANSIT Van (FA_ _)				01/00→05/06					
2.0 DI (FAE_ , FAF_ , FAG_ )	55 kW	2 l	08/00→05/06		KH20039 ProKIT				
				; 07/03 ->; Code: 330 / 350;	KH20120 ProKIT				
				; Code: 260 / 280 / 300; ;	KH20074 ProKIT				
				; Code: 260 / 280 / 300; ;	KH20127 ProKIT				
2.3	105 kW	2.3 l	03/01→03/06		KH20039 ProKIT				
				; Axle Version: Dana	KH00029 ProKIT				
						KH00070 ProKIT			
2.4 TDE	85 kW	2.4 l	03/04→05/06	; Axle Version: Dana	KH00066 ProKIT				
2.3 16V RWD (FAA_ , FAB_ , FAC_ )	107 kW	2.3 l	04/01→05/06		KH20039 ProKIT				
				; > 01/05; ; ; ; ; Payload from [kg]: 1,349 → Payload to [kg]: 1,843	KH00025 ProKIT				
				; Axle Version: Dana	KH00029 ProKIT				
				; Axle Version: Dana	KH00066 ProKIT				
					KH00070 ProKIT				
2.3 BiFuel	105 kW	2.3 l	03/01→03/06		KH20039 ProKIT				
				; 03/00 -> 03/06; ; ; ; ; Payload from [kg]: 1,349 → Payload to [kg]: 1,843	KH00025 ProKIT				
2.4 DI RWD (FAA_ , FAB_ , FAC_ , FAD_ )	88 kW	2.4 l	01/00→05/06	; 08/01 -> 03/06; ; ; ; ; Payload from [kg]: 1,935 → Payload to [kg]: 2,382					
					KH20039 ProKIT				
2.4 DI RWD (FAA_ , FAB_ , FAC_ , FAD_ )	55 kW	2.4 l	01/00→05/06	; Axle Version: Dana	KH00029 ProKIT				
				; Axle Version: Dana	KH00066 ProKIT				
					KH00070 ProKIT				
				; 03/00 -> 03/01; ; ; ; ; Payload from [kg]: 1,349 → Payload to [kg]: 1,602	KH00025 ProKIT				
2.4 TD	55 kW	2.4 l	08/00→08/03		KH20039 ProKIT				
					KH00070 ProKIT				
				; Code: 260 / 280 / 300; ;	KH20074 ProKIT				
				; Code: 260 / 280 / 300; ;	KH20127 ProKIT				
2.4 TDCi	101 kW	2.4 l	03/04→05/06		KH20039 ProKIT				
				; 09/04 -> 01/05; Payload [kg]: 1,953; ; ;	KH00025 ProKIT				
				; Axle Version: Dana	KH00029 ProKIT				
				; Axle Version: Dana	KH00066 ProKIT				
2.4 TDCi	101 kW	2.4 l	03/04→05/06		KH00070 ProKIT				
FORD - TRANSIT Van (T_ _)				09/85→09/92					
1.6 (TAS)	46 kW	1.6 l	09/85→09/92	02/86 -> 10/88; Axle Version: 32 REAR	KH00022 ProKIT				
				; 02/86 -> 10/91; Axle Version: 34 REAR					

    					
<b>FORD - TRANSIT Van (T_ _)</b>				<b>09/85→09/92</b>	
2.0 (TAL, TAS, TGL, TWS)	57 kW	2 l	09/85→09/92	02/86 -> 10/88; Axle Version: 32 REAR  02/86 -> 09/91; Axle Version: 34,51,52,53 REAR;  02/86 -> 09/91; Axle Version: 51,52 & 53  02/86 -> 09/91; 	KH00022 ProKIT
2.5 D (TAL, TAS, TGL, TWS)	50 kW	2.5 l	01/86→09/91	02/86 -> 10/88; Axle Version: 32 REAR  02/86 ->; Axle Version: 34,51,52,53 REAR;   02/86 ->; Axle Version: 51,52 & 53 02/86 ->; 	KH00022 ProKIT
<b>FORD - TRANSIT Van (V_ _)</b>				<b>11/77→10/86</b>	
1.6 (WS)	48 kW	1.6 l	11/77→10/86	 -> 01/86; Axle Version: 32 REAR	KH00022 ProKIT
2.0 (VHL, VVS)	57 kW	2 l	11/77→10/86	 ; 01/78 -> 01/86	KH00022 ProKIT
2.4 D (VVS)	46 kW	2.4 l	11/77→10/86	 -> 02/85	KH00022 ProKIT
2.5 D (VVL)	50 kW	2.5 l	10/83→10/86	 ; 02/85 -> 01/86	KH00022 ProKIT





**F50 - 126P**

**09/72→09/00**

0.6	17 kW	0.6 l	09/72→07/77		<b>KH00109</b> ProKIT
0.6	22 kW	0.6 l	07/77→12/91		<b>KH00075</b> ProKIT
650	18 kW	0.65 l	07/81→09/00		

**F50 - 127P**

**10/69→10/76**

0.9	33 kW	0.9 l	10/69→10/76		<b>KH20091</b> ProKIT
-----	-------	-------	-------------	--	-----------------------





**HINDUSTAN - AMBASSADOR**

**01/91→12/03**

1.5 D

40 kW

1.5 l

01/91→12/03


















































**KH00121** ProKIT











































<b>HONDA - ACCORD V Aerodeck (CE)</b>					<b>09/93→02/98</b>
2.0 i LS 16V (CE2)	100 kW	2 l	09/93→02/98	-> 12/97;	KH20200 ProKIT
2.2 i ES (CE1)	110 kW	2.2 l	09/93→02/98		
<b>HONDA - ACCORD V Coupe (CD)</b>					<b>09/93→02/98</b>
2.0 (CD9)	100 kW	2 l	09/93→12/97	-> 09/97	KH20200 ProKIT
2.2 i ES (CD7)	110 kW	2.2 l	09/93→02/98		
<b>HONDA - ACCORD VI Coupe (CG)</b>					<b>02/98→06/03</b>
3.0 V6 24V (CG2)	147 kW	3 l	02/98→06/03	-> 12/02; ;	KH20190 ProKIT
<b>HONDA - ACCORD VI Hatchback / ACCORD VI Sedan (CH, CL, CK, CG, CH, CF)</b>					<b>10/98→06/03</b>
1.6 i (CG7)	85 kW	1.6 l	10/98→12/02	;	KH10028 ProKIT
1.6 LS (CG7)	79 kW	1.6 l	10/98→12/02		
1.8 i (CG8)	100 kW	1.8 l	10/98→12/02	;	KH10029 ProKIT
2.0 i (CG9)	108 kW	2 l	10/98→01/01	; ;  -> 06/99 ->;	KH20149 ProKIT
1.8 i (CH6)	100 kW	1.8 l	12/99→12/02	;	KH10029 ProKIT
2.0 (CH7)	108 kW	2 l	12/99→12/02	;	KH20149 ProKIT
2.0 TDi (CH8)	77 kW	2 l	12/99→10/00	;	KH10029 ProKIT
2.0 Turbo Di (CH2)	77 kW	2 l	02/99→12/02		
2.2 Type-R (CH1)	156 kW	2.2 l	02/99→12/02		
2.3 (CL3, S86)	113 kW	2.3 l	01/01→06/03		
2.3 (CL4)	113 kW	2.3 l	11/00→12/02		
<b>HONDA - ACCORD VII Tourer (CM, CN)</b>					<b>04/03→05/08</b>
2.0 (CM1)	114 kW	2 l	04/03→05/08		KH10388 ProKIT
2.2 i-CTDi (CN2)	103 kW	2.2 l	01/04→05/08		KH20137 ProKIT
2.4 (CM2)	140 kW	2.4 l	04/03→05/08		
<b>HONDA - ACCORD VIII Estate (CW)</b>					<b>07/08→</b>
2.0 i (CW1)	115 kW	2 l	07/08→06/15	; ; OE 42200-TA0A-51	KH30005 ProKIT
2.2 i-DTEC (CW3)	110 kW	2.2 l	07/08→06/15	; ; OE 42200-TL0-G51	KH30012 ProKIT
2.2 i-DTEC (CW3)	132 kW	2.2 l	07/08→		
2.4 i (CW2)	148 kW	2.4 l	07/08→		
<b>HONDA - ACCORD IX Saloon (CU, CR)</b>					<b>01/13→04/16</b>
2.0 Hybrid	146 kW	2 l	01/13→04/16		KH30003 ProKIT
<b>HONDA - ACCORD EURO VII (CL, CN)</b>					<b>02/03→05/08</b>
2.0 (CL7)	114 kW	2 l	02/03→05/08		KH10388 ProKIT
2.0 All-wheel Drive (CL8)	114 kW	2 l	02/03→05/08		KH10388 ProKIT
2.2 i-CTDi (CN1)	103 kW	2.2 l	01/04→05/08		
2.4 (CL9)	140 kW	2.4 l	02/03→05/08		
<b>HONDA - ACCORD EURO VIII Saloon (CU)</b>					<b>06/08→</b>
2.0 i (CU1)	115 kW	2 l	06/08→06/15	; ; OE 42200-TA0A-51	KH30005 ProKIT
2.2 i-DTEC (CU3)	110 kW	2.2 l	07/08→06/15	; ; OE 42200-TL0-G51	KH30012 ProKIT
2.2 i-DTEC (CU3)	132 kW	2.2 l	07/08→06/15		
2.4 i	133 kW	2.4 l	07/08→		
2.4 i (CU2)	148 kW	2.4 l	07/08→06/15		
3.5 i	202 kW	3.5 l	07/08→		
<b>HONDA - CITY V Saloon (GM2, GM3)</b>					<b>09/08→</b>
1.4 i-V TEC	73 kW	1.4 l	09/08→		KH10031 ProKIT
<b>HONDA - CIVIC IV Hatchback (EG)</b>					<b>10/91→11/95</b>
1.3 16V (EG3)	55 kW	1.3 l	10/91→11/95		KH10360 ProKIT
1.5 i 16V (EG4)	66 kW	1.5 l	10/91→11/95	; ;	KH20169 ProKIT
1.5 i 16V (EG4)	69 kW	1.5 l	10/91→11/95		
1.6 16V Vtec (EG5)	92 kW	1.6 l	10/91→11/95		
1.6 VTi 16V (EG6)	118 kW	1.6 l	10/91→11/95	; ;	KH20169 ProKIT
<b>HONDA - CIVIC V Coupe (EJ)</b>					<b>08/93→03/96</b>
1.5 i LSi (EJ2)	74 kW	1.5 l	08/93→11/95	; ; Code: DX	KH10360 ProKIT
1.6 i Vtec (EJ1)	92 kW	1.6 l	01/94→03/96	; ;	KH20169 ProKIT
<b>HONDA - CIVIC V Saloon (EG, EH)</b>					<b>10/91→11/95</b>
1.5 i 16V (EG8)	69 kW	1.5 l	10/91→11/95		KH10360 ProKIT
1.6 16V Vtec (EH9)	92 kW	1.6 l	10/91→11/95	; ;	KH20169 ProKIT
1.6 VTi (EG9)	118 kW	1.6 l	10/91→11/95	; ;	KH20169 ProKIT

























































































				     13 	
<b>HONDA - CIVIC VI Aerodeck / CIVIC VI Coupe / CIVIC VI Fastback / CIVIC VI Hatchback / CIVIC VI Saloon (MB, MC, EJ, EM1, MA, MB, EJ, EK)</b>					
1.4 (EJ9)	55 kW	1.4 l	11/95→10/98		KH10024 ProKIT
1.4 LPG	66 kW	1.4 l	01/97→02/01		
1.5 i	66 kW	1.5 l	10/95→03/01		
1.6 (MB1)	93 kW	1.6 l	10/95→03/01		
1.6 (MB4)	92 kW	1.6 l	11/98→02/01		
1.6 (MB4)	92 kW	1.6 l	11/98→03/01		
1.6 16V (MC1)	92 kW	1.6 l	04/98→02/01		
2.0 TDiC	77 kW	2 l	11/98→10/00		
2.0 TDiC (MB7)	74 kW	2 l	11/98→10/00		
2.0 TDiC (MB7)	77 kW	2 l	11/98→10/00		
1.4 16V (MB8)	55 kW	1.4 l	04/98→02/01		KH10024 ProKIT
1.4 16V (MB8)	66 kW	1.4 l	04/98→02/01		
1.5 i Vtec-E (MA9)	66 kW	1.5 l	09/94→01/97		KH20169 ProKIT
1.6 16V (MB4)	85 kW	1.6 l	01/97→02/01		
1.6 i Vtec (EM1)	92 kW	1.6 l	03/96→03/00		
1.6 i Vtec (EM1)	118 kW	1.6 l	04/99→12/00		
1.6 VTi (EK4)	118 kW	1.6 l	11/95→02/01		
2.0 i D (MC3)	77 kW	2 l	04/98→02/01		
2.0 i TD (MB7)	63 kW	2 l	01/97→02/01		
1.4 i (EJ9)	55 kW	1.4 l	11/95→02/01		KH10360 ProKIT
1.4 i (EJ9)	66 kW	1.4 l	11/95→02/01		KH20199 ProKIT
1.4 i S (EJ9)	66 kW	1.4 l	11/95→02/01		KH20169 ProKIT
1.4 i (MA8, MB2)	55 kW	1.4 l	09/95→02/01		KH20169 ProKIT
1.4 i (MA8, MB2)	66 kW	1.4 l	06/95→02/01		
1.5 16V (MB3)	84 kW	1.5 l	01/97→02/01		
1.6 i (MB1)	83 kW	1.6 l	09/94→01/97		
1.6 i Vtec (MB1)	93 kW	1.6 l	09/94→01/97		
1.6 VTi (MB4)	118 kW	1.6 l	01/97→02/01		
1.5 16V (MB9)	84 kW	1.5 l	04/98→02/01		KH10024 ProKIT
					KH20178 ProKIT
					KH20169 ProKIT
1.5 i (EK3)	84 kW	1.5 l	11/95→02/01		KH10024 ProKIT
1.6 i (EK1)	84 kW	1.6 l	11/95→02/01		KH20199 ProKIT
1.6 i Vtec (EK1)	92 kW	1.6 l	11/95→02/01		KH20169 ProKIT
1.5 i (EK3)	84 kW	1.5 l	11/95→02/01		KH20199 ProKIT
					KH20169 ProKIT
1.6 (EJ6)	79 kW	1.6 l	05/96→04/99		KH10360 ProKIT
					KH10024 ProKIT
1.6 16V (MC1)	85 kW	1.6 l	04/98→02/01		KH10024 ProKIT
					KH20178 ProKIT
					KH20169 ProKIT
1.6 i (EJ6)	77 kW	1.6 l	03/96→03/00		KH10360 ProKIT
					KH10024 ProKIT
					KH20169 ProKIT
1.8 16V (MB6)	124 kW	1.8 l	01/97→02/01		KH10024 ProKIT
					KH20178 ProKIT
					KH20169 ProKIT
1.8 16V (MC2)	124 kW	1.8 l	04/98→02/01		KH10024 ProKIT
					KH20169 ProKIT
					KH20178 ProKIT
<b>HONDA - CIVIC VII Coupe (EM2)</b>				<b>02/01→12/05</b>	
1.6 i (EM1)	81 kW	1.6 l	02/01→12/05		KH10024 ProKIT
1.7 i (EM2)	88 kW	1.7 l	05/01→12/05		KH20069 ProKIT
1.7 i VTEC (EM2)	92 kW	1.7 l	05/01→12/05		
<b>HONDA - CIVIC VII Hatchback / CIVIC VII Saloon (EU, EP, EV, ES, ET)</b>				<b>12/00→09/05</b>	
1.3 IMA (ED9, ES9)	61 kW	1.3 l	10/03→09/05		KH10024 ProKIT
1.6 (ES5)	81 kW	1.6 l	02/01→09/05		KH20069 ProKIT
1.6 i (EP2)	81 kW	1.6 l	02/01→09/05		KH20103 ProKIT
1.7 CTDi (EP4)	74 kW	1.7 l	01/02→09/05		KH20103 ProKIT
1.4 (ES4)	66 kW	1.4 l	12/00→09/05		KH10024 ProKIT
					KH20103 ProKIT
1.4 i (EP1)	55 kW	1.4 l	02/01→09/05		KH20069 ProKIT
1.4 iS (EP1)	66 kW	1.4 l	02/01→09/05		KH20103 ProKIT
1.5 (ES8)	82 kW	1.5 l	02/03→09/05		KH10024 ProKIT
1.7 (EU3)	85 kW	1.7 l	02/01→09/05		KH20069 ProKIT








































































     					
<b>HONDA - CIVIC VII Hatchback / CIVIC VII Saloon (EU, EP, EV, ES, ET)</b>					<b>12/00→09/05</b>
2.0 i Sport (EV1)	118 kW	2 l	09/01→09/05	;	KH10024 ProKIT
				;	KH10028 ProKIT
				;	KH20070 ProKIT
2.0 Type-R (EP3)	147 kW	2 l	09/01→09/05	;	KH10029 ProKIT
				;	KH20070 ProKIT
<b>HONDA - CIVIC VIII Hatchback (FN, FK)</b>					<b>09/05→</b>
1.4 (FK1, FN4)	73 kW	1.4 l	10/08→		KH20160 ProKIT
1.4 (FK1)	61 kW	1.4 l	09/05→		
1.8 (FN1, FK2)	103 kW	1.8 l	09/05→		
2.2 CTDi (FK3)	103 kW	2.2 l	09/05→		KH10035 ProKIT
					KH20160 ProKIT
Type R (FN2)	148 kW	2 l	09/06→		KH10388 ProKIT
					KH20160 ProKIT
<b>HONDA - CIVIC VIII Saloon (FD, FA)</b>					<b>09/05→</b>
1.3 IMA (FA3, FD3)	70 kW	1.3 l	01/06→		KH10397 ProKIT
1.8 (FD1, FD7)	103 kW	1.8 l	09/05→02/12		
<b>HONDA - CIVIC IX / CIVIC IX Tourer (FK)</b>					<b>02/12→</b>
1.4 i-VTEC (FK1)	73 kW	1.4 l	02/12→		KH20160 ProKIT
1.6 i-DTEC (FK3)	88 kW	1.6 l	02/13→		
1.6 i-DTEC (FK3)	88 kW	1.6 l	01/14→		
1.8 i-VTEC (FK2)	104 kW	1.8 l	02/12→		
1.8 i-VTEC (FK2)	104 kW	1.8 l	01/14→		
2.2 i-DTEC (FK3)	110 kW	2.2 l	02/12→		
<b>HONDA - CR-V I Wagon (RD)</b>					<b>10/95→02/02</b>
2.0 16V 4WD (RD1, RD3)	94 kW	2 l	10/95→12/01	; <b>06/97 -&gt;</b>	KH20173 ProKIT
				; <b>06/97 -&gt;</b>	KH20148 ProKIT
2.0 16V 4WD (RD1, RD3)	108 kW	2 l	01/99→02/02	; <b>03/99 -&gt;</b>	KH20173 ProKIT
				; <b>03/99 -&gt;</b>	KH20148 ProKIT
<b>HONDA - CR-V II (RD_)</b>					<b>09/01→03/07</b>
2.0 (RD5)	110 kW	2 l	09/01→03/07	;	KH10018 ProKIT
				;	KH10360 ProKIT
2.2 CTDi (RD9)	103 kW	2.2 l	02/05→09/06		KH10018 ProKIT
<b>HONDA - CR-V III Wagon (RE_)</b>					<b>10/06→</b>
2.0 i-VTEC 4WD (RE5, RE2)	110 kW	2 l	10/06→06/12		KH10229 ProKIT
2.2 i-CTDi 4WD (RE6)	103 kW	2.2 l	01/07→		KH30088 ProKIT
2.2 i-DTEC 4WD (RE6)	110 kW	2.2 l	01/07→		KH30088 ProKIT
2.4 i-VTEC 4WD (RE7)	122 kW	2.4 l	09/09→		
<b>HONDA - CR-V IV Wagon (RM_)</b>					<b>10/12→</b>
1.6 i-DTEC (RE6)	88 kW	1.6 l	10/13→		KH30188 ProKIT
2.0 Flex (RE5)	114 kW	2 l	01/13→		
2.0 iVtec (RE5, RM1)	114 kW	2 l	10/12→		
2.4 i-VTEC	136 kW	2.4 l	01/15→		
<b>HONDA - CRX III (EH, EG)</b>					<b>03/92→12/98</b>
1.6 ESi (EH6)	92 kW	1.6 l	03/92→12/98	;	KH20169 ProKIT
1.6 i VTi (EG2)	118 kW	1.6 l	03/92→12/98		
<b>HONDA - FR-V (BE)</b>					<b>08/04→</b>
1.7 (BE1)	92 kW	1.7 l	08/04→	; <b>-&gt; 01/07</b>	KH20186 ProKIT
1.8 (BE1)	103 kW	1.8 l	01/07→	; <b>02/07 -&gt; 04/10</b>	KH20186 ProKIT
2.0 (BE3)	110 kW	2 l	02/05→		KH10035 ProKIT
				; <b>-&gt; 01/07</b>	KH20186 ProKIT
2.2 i CTDi (BE5)	103 kW	2.2 l	07/05→		KH10388 ProKIT
				; <b>-&gt; 04/10</b>	KH20186 ProKIT
<b>HONDA - HR-V (GH)</b>					<b>03/99→</b>
1.6 16V (GH1, GH3)	77 kW	1.6 l	03/99→		KH10410 ProKIT
1.6 16V 4WD (GH2, GH4)	77 kW	1.6 l	03/99→		
1.6 16V 4WD (GH2, GH4)	91 kW	1.6 l	10/99→09/05		

				  	 	 13			
<b>HONDA - HR-V Wagon (RU)</b>								<b>08/15→</b>	
1.5 (RU1)	96 kW	1.5 l	08/15→				KH10229 ProKIT		
1.6 i-DTEC (RU8)	88 kW	1.6 l	08/15→						
<b>HONDA - INSIGHT (ZE_)</b>								<b>04/09→</b>	
1.3 IMA (ZE2)	73 kW	1.3 l	04/09→				KH10031 ProKIT		
1.3 IMA (ZE28, ZE2)	65 kW	1.3 l	04/09→						
<b>HONDA - JAZZ II (GD_, GE3, GE2)</b>								<b>03/02→07/08</b>	
1.2 i-DSi (GD5, GE2)	57 kW	1.2 l	03/02→07/08				KH10018 ProKIT		
				 ABS, 			KH20006 ProKIT		
				 			KH20007 ProKIT		
				  ABS			KH20153 ProKIT		
1.3 iDSi (GD1)	61 kW	1.3 l	03/02→07/08				KH10018 ProKIT		
				 ABS, 			KH20006 ProKIT		
				  ABS			KH20153 ProKIT		
<b>HONDA - JAZZ III (GE_, GG_, GP_, ZA_)</b>								<b>07/08→06/14</b>	
1.2 (GG1)	66 kW	1.2 l	07/08→				KH10031 ProKIT		
1.3 HYBRID (GP1)	65 kW	1.3 l	04/11→				KH20065 ProKIT		
1.3 i (GE6, GG3, GG6)	73 kW	1.3 l	07/08→				KH20065 ProKIT		
1.4	74 kW	1.4 l	11/08→				KH20065 ProKIT		
1.5 i-VTEC (GE8)	88 kW	1.5 l	07/08→06/14				KH10031 ProKIT		
<b>HONDA - LEGEND I Coupe / LEGEND I Sedan (KA_, HS, KA)</b>								<b>02/87→12/90</b>	
2.5 i (HS)	127 kW	2.5 l	02/87→06/88		-> 09/87		KH10202 ProKIT		
2.7 i 24V (KA3)	124 kW	2.7 l	10/87→12/90				KH10202 ProKIT		
2.7 i 24V (KA4)	124 kW	2.7 l	01/88→12/90						
<b>HONDA - LOGO (GA)</b>								<b>03/99→03/02</b>	
1.3 (GA3)	48 kW	1.3 l	03/99→03/02				KH10360 ProKIT		
<b>HONDA - ODYSSEY (RA)</b>								<b>10/94→06/04</b>	
2.2 16V (RA1)	110 kW	2.2 l	10/94→02/98		07/95 ->		KH20176 ProKIT		
2.3 16V (RA3, RA5)	110 kW	2.3 l	10/97→06/04		02/98 -> 10/00		KH20176 ProKIT		
<b>HONDA - PRELUDE V (BB_)</b>								<b>10/96→12/01</b>	
2.0 16V (BB9)	98 kW	2 l	10/96→10/00		01/97 ->		KH20178 ProKIT		
2.2 16V (BB6, BB8)	136 kW	2.2 l	10/96→10/00		01/97 ->		KH20175 ProKIT		
2.2 16V (BB6, BB8)	147 kW	2.2 l	10/96→12/01						
<b>HONDA - STREAM (RN)</b>								<b>05/01→09/06</b>	
1.7 16V (RN1)	92 kW	1.7 l	05/01→09/06				KH20070 ProKIT		
2.0 16V (RN3)	115 kW	2 l	05/01→09/06						







				      <b>13</b> 	
<b>HYUNDAI - ACCENT II / ACCENT II Saloon (LC)</b>					<b>01/00→11/05</b>
1.3	55 kW	1.3 l	01/00→11/05	 ; 03/02 ->	KH10110 ProKIT
1.3	63 kW	1.3 l	01/00→11/05	 ; -> 01/03; 	KH20196 ProKIT
1.5	66 kW	1.5 l	01/00→11/05		
1.5	75 kW	1.5 l	09/00→11/05		
1.3	62 kW	1.3 l	08/02→11/05	 ; 02/03 ->	KH10110 ProKIT
				 ; 02/03 ->; 	KH20196 ProKIT
1.3	63 kW	1.3 l	01/00→11/05	 ; 03/02 ->	KH10110 ProKIT
				 ; 	KH20196 ProKIT
1.5	66 kW	1.5 l	01/00→11/05	 ; 03/02 -> 01/03	KH10110 ProKIT
				 ; -> 01/03; 	KH20196 ProKIT
1.5 CRDi	60 kW	1.5 l	01/02→11/05	 ; 04/02 -> 01/03; 	KH20196 ProKIT
				 ; 02/03 ->	
1.5 CRDi	60 kW	1.5 l	04/02→11/05	 ; 04/02 ->	KH10110 ProKIT
				 ; -> 01/03; 	KH20196 ProKIT
1.6	77 kW	1.6 l	12/02→11/05	 ; 02/03 ->	KH10110 ProKIT
				 ; 02/03 ->	KH20196 ProKIT
<b>HYUNDAI - ACCENT IV / ACCENT IV Saloon (MC)</b>					<b>11/05→11/10</b>
1.4 GL	71 kW	1.4 l	11/05→11/10	 ; 03/06 ->	KH10110 ProKIT
				 ; 03/06 ->; 	KH30062 ProKIT
				 ; 03/06 ->; 	KH30168 ProKIT
1.5 CRDi GLS	81 kW	1.5 l	11/05→11/10	 ; 12/05 ->	KH10110 ProKIT
1.6 GLS	82 kW	1.6 l	11/05→11/10	 ; 12/05 ->; 	KH30062 ProKIT
				 ; 12/05 ->; 	KH30168 ProKIT
<b>HYUNDAI - ATOS (MX, IL44)</b>					<b>02/98→12/10</b>
1.0 i	40 kW	1 l	02/98→12/00		KH00077 ProKIT
				 ; Drive Shaft: without ABS ring	KH00017 ProKIT
1.0 i	43 kW	1 l	03/01→07/03	 ; 07/01 ->	KH10110 ProKIT
				 ; 07/01 ->; 	KH20195 ProKIT
1.1	43 kW	1.1 l	08/03→12/08	 ; 	KH20195 ProKIT
1.1	45 kW	1.1 l	06/03→12/10		
1.1	46 kW	1.1 l	08/03→12/08	 ; 07/04 ->	KH10110 ProKIT
				 ; 	KH20195 ProKIT
<b>HYUNDAI - COUPE I (RD)</b>					<b>08/96→04/02</b>
1.6 16V	85 kW	1.6 l	03/98→04/02	 ; -> 01/00	KH20170 ProKIT
				 ; 	KH20184 ProKIT
1.6 i 16V	84 kW	1.6 l	12/96→04/02	 ; -> 12/01	KH10110 ProKIT
2.0 16V	102 kW	2 l	08/96→04/02	 ; -> 12/01; 	KH20197 ProKIT
				 ; 	KH20184 ProKIT
2.0 16V	99 kW	2 l	03/01→04/02	 ; 	KH20184 ProKIT
<b>HYUNDAI - ELANTRA III / ELANTRA III Saloon (XD)</b>					<b>06/00→07/06</b>
1.6	66 kW	1.6 l	06/00→07/06	 ; 10/02 ->; 	KH20185 ProKIT
1.8	79 kW	1.8 l	06/00→07/03		
1.6	66 kW	1.6 l	06/00→07/06	 ; Charge Type: Turbocharger/Compressor	KH10133 ProKIT
				 ; 10/02 -> 01/05; 	KH20168 ProKIT
				 ; 10/02 ->; 	KH20185 ProKIT
1.6	77 kW	1.6 l	05/03→05/06	 ; 06/03 ->	KH10197 ProKIT
1.6	77 kW	1.6 l	05/03→07/06	 ; Charge Type: Turbocharger/Compressor	KH10133 ProKIT
				 ; -> 01/05; 	KH20168 ProKIT
				 ; 	KH20185 ProKIT
1.6	79 kW	1.6 l	06/00→07/06	 ; -> 05/03	KH10197 ProKIT
2.0	102 kW	2 l	06/00→07/06	 ; Charge Type: Turbocharger/Compressor	KH10133 ProKIT
2.0	104 kW	2 l	06/00→07/06	 ; 10/02 -> 01/05; 	KH20168 ProKIT
				 ; 10/02 ->; 	KH20185 ProKIT
				 ; -> 07/01; 	KH20180 ProKIT
1.6	79 kW	1.6 l	06/00→07/06	 ; Charge Type: Turbocharger/Compressor	KH10133 ProKIT
1.8	97 kW	1.8 l	06/00→07/06		KH10197 ProKIT
2.0	102 kW	2 l	06/00→07/06	 ; 10/02 -> 01/05; 	KH20168 ProKIT
2.0	104 kW	2 l	06/00→07/06	 ; 10/02 ->; 	KH20185 ProKIT
				 ; -> 07/01; 	KH20180 ProKIT

				13	i		
<b>HYUNDAI - ELANTRA III / ELANTRA III Saloon (XD)</b>						<b>06/00→07/06</b>	
2.0	105 kW	2 l	10/03→07/06		Charge Type: Turbocharger/Compressor	KH10133 ProKIT	
						KH10197 ProKIT	
					-> 01/05;	KH20168 ProKIT	
						KH20185 ProKIT	
2.0 CRDi	83 kW	2 l	04/01→07/06		-> 05/03	KH10197 ProKIT	
					Charge Type: Turbocharger/Compressor	KH10133 ProKIT	
					10/02 -> 01/05;	KH20168 ProKIT	
					-> 07/01;	KH20180 ProKIT	
2.0 CRDi	83 kW	2 l	04/01→07/06		Charge Type: Turbocharger/Compressor	KH10133 ProKIT	
						KH10197 ProKIT	
					10/02 -> 01/05;	KH20168 ProKIT	
					-> 07/01;	KH20180 ProKIT	
<b>HYUNDAI - ELANTRA LAVITA (FC)</b>						<b>06/01→08/10</b>	
1.5 CRDi	60 kW	1.5 l	10/01→08/10		-> 03/05	KH10197 ProKIT	
					-> 03/05;	KH20180 ProKIT	
1.5 CRDi	75 kW	1.5 l	12/04→08/10		02/05 -> 08/05	KH10197 ProKIT	
					02/05 -> 08/05;	KH20180 ProKIT	
1.5 CRDi VGT	81 kW	1.5 l	08/05→08/10			KH10197 ProKIT	
1.6	76 kW	1.6 l	06/01→08/10			KH20180 ProKIT	
1.8	90 kW	1.8 l	06/01→08/10			KH20180 ProKIT	
<b>HYUNDAI - EXCEL (X-2)</b>						<b>10/89→01/95</b>	
1.3	43 kW	1.3 l	10/89→01/95		01/90 -> 07/94	KH00077 ProKIT	
1.5	53 kW	1.5 l	10/89→01/95				
1.5 i	61 kW	1.5 l	10/89→01/95				
1.5 i	62 kW	1.5 l	10/89→01/95				
<b>HYUNDAI - EXCEL I (X-3)</b>						<b>10/94→01/00</b>	
1.3	44 kW	1.3 l	10/94→01/00		10/99 ->	KH10110 ProKIT	
					-> 12/99	KH00077 ProKIT	
					05/96 -> 09/99;	KH20197 ProKIT	
					10/99 ->;	KH20196 ProKIT	
1.3	55 kW	1.3 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
1.5 i 16V	73 kW	1.5 l	12/95→01/00		05/96 -> 09/99;	KH20197 ProKIT	
1.3 i 12V	62 kW	1.3 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
					05/96 -> 12/99;	KH20197 ProKIT	
					-> 12/99	KH20170 ProKIT	
1.5 i 12V	65 kW	1.5 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
					05/96 -> 12/99;	KH20197 ProKIT	
					-> 05/99	KH20170 ProKIT	
<b>HYUNDAI - EXCEL Saloon (X-1)</b>						<b>10/85→09/89</b>	
1.3	50 kW	1.3 l	10/85→09/89		07/87 ->	KH00017 ProKIT	
1.5	53 kW	1.5 l	10/85→09/89				
<b>HYUNDAI - EXCEL Saloon (X-2)</b>						<b>01/90→01/95</b>	
1.5	53 kW	1.5 l	01/90→01/95		-> 07/94	KH00077 ProKIT	
1.5 i	61 kW	1.5 l	01/90→01/95				
1.5 i	62 kW	1.5 l	01/90→01/95				
<b>HYUNDAI - EXCEL Saloon (X-3)</b>						<b>10/94→01/00</b>	
1.3	44 kW	1.3 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
1.3	55 kW	1.3 l	10/94→01/00		05/96 -> 09/99;	KH20197 ProKIT	
1.5 i 16V	73 kW	1.5 l	10/95→01/00				
1.3 i 12V	62 kW	1.3 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
					05/96 -> 12/99;	KH20197 ProKIT	
					-> 12/99	KH20170 ProKIT	
1.5 i 12V	65 kW	1.5 l	10/94→01/00		-> 12/99	KH00077 ProKIT	
					05/96 -> 09/99;	KH20197 ProKIT	
					-> 05/99	KH20170 ProKIT	
<b>HYUNDAI - GALLOPER I</b>						<b>08/91→07/98</b>	
2.5 TD	62 kW	2.5 l	08/91→07/98		01/92 -> 12/97	KH00011 ProKIT	
2.5 TD intercooler	70 kW	2.5 l	08/91→07/98				
3.0 V6	104 kW	3 l	08/91→07/98				








































									
<b>HYUNDAI - GETZ (TB)</b>									<b>09/02→12/10</b>
1.1	46 kW	1.1 l	09/02→09/05		-> 08/05				KH10110 ProKIT
					11/04 -> 08/05; ABS				KH30168 ProKIT
					-> 08/05; ABS				KH30062 ProKIT
1.1	49 kW	1.1 l	09/05→06/09		-> 12/06				KH10110 ProKIT
					-> 12/06; ABS				KH30062 ProKIT
					-> 12/06; ABS				KH30168 ProKIT
1.3	63 kW	1.3 l	09/03→09/05		-> 03/04				KH10110 ProKIT
					-> 03/04; ABS				KH30062 ProKIT
					-> 03/04; ABS				KH30168 ProKIT
1.3 i	60 kW	1.3 l	09/02→03/04						KH10110 ProKIT
1.6	77 kW	1.6 l	09/02→09/05		ABS				KH30062 ProKIT
					ABS				KH30168 ProKIT
1.4 i	71 kW	1.4 l	08/05→12/10		09/05 -> 12/06				KH10110 ProKIT
1.5 CRDi	65 kW	1.5 l	08/05→06/09		09/05 -> 12/06; ABS				KH30062 ProKIT
1.5 CRDi GLS	81 kW	1.5 l	08/05→06/09		09/05 -> 12/06; ABS				KH30168 ProKIT
1.5 CRDi	60 kW	1.5 l	03/03→09/05		-> 08/05				KH10110 ProKIT
					-> 01/04; ABS				KH30168 ProKIT
					-> 08/05; ABS				KH30062 ProKIT
<b>HYUNDAI - GRANDEUR (HG)</b>									<b>01/11→10/16</b>
2.4 16V	148 kW	2.4 l	01/11→10/16		-> 10/13				KH10123 ProKIT
<b>HYUNDAI - GRANDEUR Sedan (TG)</b>									<b>04/05→12/11</b>
2.2 CRDi	110 kW	2.2 l	06/06→12/11		10/06 -> 03/08				KH30161 ProKIT
2.2 CRDi	114 kW	2.2 l	06/06→10/10						
2.7	141 kW	2.7 l	05/06→10/10						
3.3	173 kW	3.3 l	04/05→12/10						
2.4	121 kW	2.4 l	09/06→12/08		-> 03/08				KH30161 ProKIT
<b>HYUNDAI - GRANDEUR Sedan (XG)</b>									<b>12/98→12/05</b>
250	120 kW	2.5 l	12/98→12/05		01/02 ->; ABS				KH10123 ProKIT
30	138 kW	3 l	12/98→12/05		-> 12/01; ABS				KH10133 ProKIT
350	145 kW	3.5 l	10/02→12/05		ABS				KH10123 ProKIT
<b>HYUNDAI - GRAND SANTA FÉ</b>									<b>06/13→</b>
2.2 CRDi All-wheel Drive	145 kW	2.2 l	06/13→						KH30086 ProKIT
<b>HYUNDAI - i10 I (PA)</b>									<b>01/08→12/13</b>
1.1	49 kW	1.1 l	01/08→12/13						KH10346 ProKIT
1.1 CRDi	55 kW	1.1 l	01/08→12/11						KH30062 ProKIT
1.2	57 kW	1.2 l	11/08→12/11						KH10346 ProKIT
<b>HYUNDAI - i20 I (PB, PBT)</b>									<b>08/08→12/15</b>
1.2	57 kW	1.2 l	09/08→12/12		10/08 ->				KH10346 ProKIT
1.4	74 kW	1.4 l	09/08→12/15		10/08 ->				KH30062 ProKIT
1.4 CRDi	66 kW	1.4 l	08/08→12/15						
1.6	93 kW	1.6 l	09/08→12/12						
1.4 CRDi	55 kW	1.4 l	09/08→12/12						KH10346 ProKIT
									KH30062 ProKIT
<b>HYUNDAI - i30 (FD)</b>									<b>10/07→11/11</b>
1.4	77 kW	1.4 l	10/07→11/11						KH10157 ProKIT
1.4	80 kW	1.4 l	10/07→11/11						
1.6	85 kW	1.6 l	10/07→11/11		-> 09/10; ABS				KH30067 ProKIT
1.6	90 kW	1.6 l	10/07→11/11						
1.6	93 kW	1.6 l	02/08→11/11						
1.6 CRDi	66 kW	1.6 l	10/07→11/11						
1.6 CRDi	85 kW	1.6 l	10/07→11/11						
2.0	105 kW	2 l	10/07→11/11						
2.0 CRDi	103 kW	2 l	10/07→11/11						
<b>HYUNDAI - i30 / i30 Coupe / i30 Estate (GD, FD)</b>									<b>10/07→06/12</b>
1.4	73 kW	1.4 l	12/11→12/15						KH30067 ProKIT
1.4	73 kW	1.4 l	06/12→12/15						
1.4	74 kW	1.4 l	01/15→						
1.4	77 kW	1.4 l	10/07→06/12						
1.4 CRDi	66 kW	1.4 l	12/11→12/16						
1.4 CRDi	66 kW	1.4 l	06/12→						
1.4 CRDi	66 kW	1.4 l	05/13→						

											
<b>HYUNDAI - i30 / i30 Coupe / i30 Estate (GD, FD)</b>											<b>10/07→06/12</b>
1.6	88 kW	1.6 l	01/12→12/16								KH30067 ProKIT
1.6	88 kW	1.6 l	06/12→								
1.6	95 kW	1.6 l	12/11→12/15								
1.6	95 kW	1.6 l	06/12→12/15								
1.6 CRDi	81 kW	1.6 l	12/11→12/16								
1.6 CRDi	81 kW	1.6 l	06/12→								
1.6 CRDi	94 kW	1.6 l	12/11→12/15								
1.6 CRDi	94 kW	1.6 l	06/12→12/15								
1.6 CRDi	100 kW	1.6 l	01/15→								
1.6 GDI	99 kW	1.6 l	12/11→12/16								
1.6 GDI	99 kW	1.6 l	06/12→								
1.6 GDI	99 kW	1.6 l	05/13→								
1.6 T-GDI	137 kW	1.6 l	01/15→								
1.4	80 kW	1.4 l	11/09→06/12								KH10157 ProKIT
											KH30067 ProKIT
1.6	90 kW	1.6 l	02/08→06/12								KH10157 ProKIT
1.6	93 kW	1.6 l	02/08→06/12								KH30067 ProKIT
1.6 CRDi	66 kW	1.6 l	02/08→06/12		-> 09/10;	ABS					
1.6 CRDi	85 kW	1.6 l	02/08→06/12								
2.0	105 kW	2 l	02/08→06/12								
2.0 CRDi	103 kW	2 l	02/08→06/12								
<b>HYUNDAI - i40 I / i40 I CW (VF)</b>											<b>07/11→05/19</b>
1.6 GDI	99 kW	1.6 l	07/11→05/19								KH10123 ProKIT
1.6 GDI	99 kW	1.6 l	03/12→05/19								
1.7 CRDi	85 kW	1.7 l	07/11→05/19								KH30147 ProKIT
1.7 CRDi	85 kW	1.7 l	03/12→05/19								
1.7 CRDi	100 kW	1.7 l	07/11→05/19								
1.7 CRDi	100 kW	1.7 l	03/12→05/19								
2.0 GDI	130 kW	2 l	07/11→05/19								
2.0 GDI	131 kW	2 l	03/12→05/19								
1.7 CRDi	104 kW	1.7 l	01/15→05/19								KH30147 ProKIT
1.7 CRDi	104 kW	1.7 l	01/15→05/19								
2.0 CVVT	110 kW	2 l	10/12→05/19								
2.0 GDi	121 kW	2 l	12/14→05/19								
<b>HYUNDAI - i45 VI Saloon (YF)</b>											<b>06/09→12/15</b>
2.0	110 kW	2 l	06/09→06/14								KH30147 ProKIT
2.0	115 kW	2 l	09/10→12/15								
2.4	130 kW	2.4 l	01/10→12/15								
2.4	142 kW	2.4 l	09/11→12/14								
2.0 i	121 kW	2 l	01/11→06/14		-> 10/13						KH10123 ProKIT
											KH30147 ProKIT
2.4	128 kW	2.4 l	06/09→11/10								KH10123 ProKIT
											KH30147 ProKIT
<b>HYUNDAI - iLOAD Cargo (TQ)</b>											<b>02/08→</b>
2.5 CRDi	81 kW	2.5 l	02/08→		ABS						KH20157 ProKIT
2.5 CRDi	85 kW	2.5 l	01/09→								
2.5 CRDi	100 kW	2.5 l	08/09→								
2.5 CRDi	120 kW	2.5 l	02/08→								
2.5 CRDi	125 kW	2.5 l	02/08→								
<b>HYUNDAI - iMAX Travel (TQ)</b>											<b>05/08→</b>
2.5 CRDi	85 kW	2.5 l	08/11→		ABS						KH20157 ProKIT
2.5 CRDi	125 kW	2.5 l	05/08→								
2.5 CRDi	100 kW	2.5 l	07/08→								
<b>HYUNDAI - ix20 (JC)</b>											<b>11/10→07/19</b>
1.4	66 kW	1.4 l	11/10→07/19		ABS						KH30162 ProKIT
1.4 CRDi	57 kW	1.4 l	06/11→07/19								
1.4 CRDi	66 kW	1.4 l	11/10→07/19								
1.6	92 kW	1.6 l	11/10→07/19								
1.6 CRDi	85 kW	1.6 l	06/11→07/19								
1.6 CRDi	94 kW	1.6 l	06/11→07/19								
<b>HYUNDAI - ix35 (LM, EL, ELH)</b>											<b>08/09→07/13</b>
1.6	99 kW	1.6 l	11/10→		-> 08/13						KH10123 ProKIT
1.7 CRDi	85 kW	1.7 l	11/10→								KH30147 ProKIT
2.0 CRDi	100 kW	2 l	01/10→								
2.0 CRDi	135 kW	2 l	01/12→								
2.0	120 kW	2 l	01/10→07/13								KH10123 ProKIT
											KH30147 ProKIT




















































     					
<b>HYUNDAI - ix35 (LM, EL, ELH)</b>				<b>08/09→07/13</b>	
2.0	122 kW	2 l	01/10→		KH30147 ProKIT
2.0 CRDi	130 kW	2 l	01/12→		
2.0 CVVT	110 kW	2 l	08/09→07/13		
2.0 GDi	122 kW	2 l	08/13→		
2.0 4WD	116 kW	2 l	09/14→06/15		KH10201 ProKIT
2.0 AWD	114 kW	2 l	11/13→		
2.0 CVVT 4WD	122 kW	2 l	08/09→		
2.0 CVVT AWD	110 kW	2 l	08/09→07/13		
2.0 GDi 4WD	122 kW	2 l	08/13→12/15		
2.4 4WD	129 kW	2.4 l	09/12→12/13		
2.4 DCVVT-I 4WD	128 kW	2.4 l	07/10→12/13		
2.0 4WD	120 kW	2 l	01/10→	-> 08/13	KH10123 ProKIT
2.0 CRDi 4WD	100 kW	2 l	01/10→		KH10201 ProKIT
2.0 CRDi 4WD	135 kW	2 l	01/10→		
<b>HYUNDAI - ix55</b>				<b>01/07→</b>	
3.0 V6 CRDi 4WD	176 kW	3 l	09/08→12/11		KH30086 ProKIT
3.0 V6 CRDi 4WD	184 kW	3 l	09/11→12/12		
3.8 V6	194 kW	3.8 l	01/11→		
3.8 V6 4WD	191 kW	3.8 l	01/07→		
3.8 V6 4WD	194 kW	3.8 l	01/11→		
<b>HYUNDAI - LANTRA I Sedan (J-1)</b>				<b>10/90→11/95</b>	
1.5 i.e.	63 kW	1.5 l	10/90→11/95		KH00077 ProKIT
1.6 i.e. 16V	78 kW	1.6 l	10/90→11/95		
1.6 i.e. 16V	84 kW	1.6 l	10/90→11/95		
1.8 i.e. 16V	93 kW	1.8 l	10/90→11/95		
<b>HYUNDAI - LANTRA II Estate (J-2)</b>				<b>11/95→10/00</b>	
1.5 12V	65 kW	1.5 l	04/97→10/00	-> 07/00	KH10110 ProKIT
1.9 D	50 kW	1.9 l	03/98→10/00	-> 04/98; ABS	KH20184 ProKIT
				-> 07/00; ABS	KH20197 ProKIT
1.6 16V	84 kW	1.6 l	02/96→10/00	-> 07/00	KH10110 ProKIT
				-> 04/98; ABS	KH20184 ProKIT
				-> 07/00; ABS	KH20197 ProKIT
					KH20170 ProKIT
1.6 i	66 kW	1.6 l	02/96→10/00	-> 04/98; ABS	KH20184 ProKIT
1.8 16V	94 kW	1.8 l	02/96→10/00	-> 07/00	KH10110 ProKIT
				-> 02/97	KH20170 ProKIT
				-> 04/98; ABS	KH20184 ProKIT
				-> 07/00; ABS	KH20197 ProKIT
2.0 16V	102 kW	2 l	11/95→10/00	; 06/97 -> 07/00	KH10110 ProKIT
				; 02/97 ->	KH20170 ProKIT
				; 06/97 -> 07/00; ABS	KH20197 ProKIT
				-> 04/98; ABS	KH20184 ProKIT
<b>HYUNDAI - LANTRA II Sedan (J-2)</b>				<b>11/95→09/00</b>	
1.5 12V	65 kW	1.5 l	12/96→09/00	-> 07/00	KH10110 ProKIT
1.9 D	50 kW	1.9 l	03/98→09/00	-> 07/00; ABS	KH20197 ProKIT
				; ABS	KH20184 ProKIT
1.6 16V	84 kW	1.6 l	11/95→09/00	-> 07/00	KH10110 ProKIT
				; 01/96 ->; ABS	KH20184 ProKIT
				-> 07/00; ABS	KH20197 ProKIT
					KH20170 ProKIT
1.6 i	66 kW	1.6 l	11/95→09/00	; 01/96 ->; ABS	KH20184 ProKIT
1.8 16V	94 kW	1.8 l	11/95→09/00	-> 07/00	KH10110 ProKIT
				; 01/96 ->; ABS	KH20184 ProKIT
				-> 02/97	KH20170 ProKIT
				-> 07/00; ABS	KH20197 ProKIT
2.0 16V	102 kW	2 l	08/96→09/00	; 06/97 -> 07/00	KH10110 ProKIT
				; 02/97 ->	KH20170 ProKIT
				; 06/97 -> 07/00; ABS	KH20197 ProKIT
				; ABS	KH20184 ProKIT














				    	
<b>HYUNDAI - PONY / PONY Wagon</b>				<b>06/74→06/86</b>	
1.2	40 kW	1.2 l	06/74→12/82	  ; 01/82 ->	KH00017 ProKIT
1.2	40 kW	1.2 l	02/78→06/86		
1.4	50 kW	1.4 l	08/77→12/85		
1.4	50 kW	1.4 l	02/78→06/86		
<b>HYUNDAI - SANTA FÉ I (SM)</b>				<b>11/00→03/06</b>	
2.0	99 kW	2 l	08/01→03/06		KH10123 ProKIT
2.0 CRDi	83 kW	2 l	08/01→03/06	 	KH20150 ProKIT
2.4 16V	100 kW	2.4 l	02/01→03/06		
2.4 16V	107 kW	2.4 l	02/01→03/06		
2.0 CRDi 4x4	83 kW	2 l	04/01→03/06		KH10123 ProKIT
2.0 CRDi 4x4	92 kW	2 l	08/03→03/06		KH10201 ProKIT
2.0 CRDi All-wheel Drive	107 kW	2 l	11/03→02/06		
2.4 16V 4x4	100 kW	2.4 l	02/01→03/06		
2.4 16V 4x4	107 kW	2.4 l	02/01→03/06		
2.7 4x4	132 kW	2.7 l	11/00→03/06		
2.7 V6 4x4	127 kW	2.7 l	02/01→03/06		
2.7 4x4	129 kW	2.7 l	09/02→12/04		KH10201 ProKIT
<b>HYUNDAI - SANTA FÉ II / SANTA FÉ III (CM, DM, DMA)</b>				<b>03/06→12/12</b>	
2.0 CRDi	110 kW	2 l	12/10→12/12		KH30086 ProKIT
2.0 CRDi	110 kW	2 l	09/12→		
2.2 CRDi	102 kW	2.2 l	03/06→12/12		KH30195 ProKIT
2.2 CRDi	114 kW	2.2 l	03/06→12/09		
2.2 CRDi	145 kW	2.2 l	01/09→12/12		
2.2 CRDi	145 kW	2.2 l	09/12→12/15		
2.2 CRDi GLS	110 kW	2.2 l	03/06→12/09		
2.4	128 kW	2.4 l	11/10→12/12		
2.4	141 kW	2.4 l	09/12→12/15		
2.7	125 kW	2.7 l	03/06→12/12		
2.7 V6 GLS	139 kW	2.7 l	03/06→12/09		
2.0 CRDi 4WD	110 kW	2 l	09/12→	 	KH30086 ProKIT
2.0 CRDi 4x4	110 kW	2 l	12/10→12/12		
2.0 CRDi 4x4	135 kW	2 l	03/06→12/12		
2.2 CRDi 4WD	145 kW	2.2 l	09/12→12/15		
2.2 CRDi 4x4	102 kW	2.2 l	03/06→12/12		
2.2 CRDi 4x4	114 kW	2.2 l	03/06→12/09		
2.2 CRDi 4x4	145 kW	2.2 l	01/09→12/12		
2.2 CRDi GLS 4x4	110 kW	2.2 l	03/06→12/09		
2.4 4WD	141 kW	2.4 l	09/12→		
2.4 4x4	128 kW	2.4 l	07/10→12/12		
2.4 CCVT AWD	129 kW	2.4 l	09/12→		
2.7 4x4	125 kW	2.7 l	03/06→12/12		
2.7 4x4	147 kW	2.7 l	01/07→12/12		
2.7 V6 GLS 4x4	139 kW	2.7 l	03/06→12/09		
3.5 4x4	204 kW	3.5 l	08/11→12/12		
2.0 CRDi 4x4	85 kW	2 l	03/06→12/12		KH30086 ProKIT
2.4 CCVT	129 kW	2.4 l	09/12→		KH30086 ProKIT
<b>HYUNDAI - S COUPE (SLC)</b>				<b>02/90→05/96</b>	
1.5 i	62 kW	1.5 l	02/90→05/96	 ; 03/90 -> 04/94	KH00077 ProKIT
1.5 i	65 kW	1.5 l	04/92→05/96	 ; -> 04/94	KH00077 ProKIT
1.5 i Turbo	85 kW	1.5 l	04/91→05/96		
<b>HYUNDAI - SONATA IV Sedan (EF)</b>				<b>03/98→11/04</b>	
2.0 16V	96 kW	2 l	10/01→11/04	 ; 01/02 ->	KH10123 ProKIT
2.7 V6	127 kW	2.7 l	10/01→11/04	  ; 	KH30192 ProKIT
2.0 16V	100 kW	2 l	06/98→10/01		KH10133 ProKIT
				 ; 08/98 -> 06/00; 	KH30185 ProKIT
				 ; 08/98 -> 06/01; 	KH30192 ProKIT
2.4 16V	105 kW	2.4 l	03/98→10/01	 ; -> 04/01	KH10133 ProKIT
				 ; 10/98 -> 06/00; 	KH30185 ProKIT
				 ; 10/98 -> 06/01; 	KH30192 ProKIT
2.5 V6 24V	118 kW	2.5 l	06/98→10/01	 ; -> 04/01	KH10133 ProKIT
				 ; 08/98 -> 06/00; 	KH30185 ProKIT
				 ; 08/98 -> 06/01	KH30192 ProKIT
















				      <b>13</b> 	
<b>HYUNDAI - SONATA V Sedan (NF)</b>				<b>01/05→12/10</b>	
2.0 CRDi	100 kW	2 l	02/06→12/10		<b>KH10123</b> ProKIT
2.0 CRDi	103 kW	2 l	02/06→12/10	 ; without ABS sensor ring	<b>KH30171</b> ProKIT
2.0 CRDi	110 kW	2 l	03/09→12/10		<b>KH30176</b> ProKIT
2.0 VVTi GLS	106 kW	2 l	05/05→12/10		
2.0 VVTi GLS	121 kW	2 l	01/08→12/10		
2.4	119 kW	2.4 l	01/05→12/10		
2.4	128 kW	2.4 l	06/08→12/10		
3.3	171 kW	3.3 l	01/05→12/10		
3.3	173 kW	3.3 l	06/05→12/10		
3.3	184 kW	3.3 l	01/08→12/10		
<b>HYUNDAI - TIBURON II (GK)</b>				<b>03/02→08/09</b>	
1.6 16V	77 kW	1.6 l	03/02→08/09		<b>KH10197</b> ProKIT
				 ; 10/02 -> 12/03; 	<b>KH20110</b> ProKIT
1.6 16V	79 kW	1.6 l	03/02→08/09	 ; 01/04 -> 12/06	<b>KH10197</b> ProKIT
				 ; 01/04 -> 12/06; 	<b>KH20110</b> ProKIT
2.0	102 kW	2 l	03/02→08/09	 ; -> 02/03	<b>KH10197</b> ProKIT
				 ; 10/02 -> 02/03; 	<b>KH20110</b> ProKIT
2.0 GLS	105 kW	2 l	02/03→08/09	 ; 04/03 -> 09/08	<b>KH10197</b> ProKIT
				 ; 04/03 -> 12/06; 	<b>KH20110</b> ProKIT
2.7 V6	123 kW	2.7 l	03/02→08/09	 ; -> 01/03	<b>KH10133</b> ProKIT
				 ; 10/02 -> 12/06; 	<b>KH20110</b> ProKIT
<b>HYUNDAI - TRAJET (FO)</b>				<b>03/00→07/08</b>	
2.0	100 kW	2 l	03/00→07/08	 ; -> 10/00	<b>KH10123</b> ProKIT
2.7 V6	127 kW	2.7 l	09/00→07/08	 ; 	<b>KH20151</b> ProKIT
2.0	103 kW	2 l	03/01→10/03	 ; 	<b>KH20151</b> ProKIT
2.0	103 kW	2 l	01/04→07/08		
2.0	104 kW	2 l	11/03→07/08		
2.0 CRDi	83 kW	2 l	04/01→07/08		
2.0 CRDi	92 kW	2 l	08/05→07/08		
<b>HYUNDAI - TUCSON (JM)</b>				<b>08/04→11/10</b>	
2.0	104 kW	2 l	08/04→		<b>KH10123</b> ProKIT
2.0 CRDi	83 kW	2 l	08/04→03/10		
2.0 CRDi	100 kW	2 l	01/06→03/10		
2.0 CRDi	103 kW	2 l	01/06→03/10		
2.0 CRDi	110 kW	2 l	01/09→03/10		
2.0 All-wheel Drive	104 kW	2 l	08/04→03/10		<b>KH10123</b> ProKIT
2.0 CRDi All-wheel Drive	83 kW	2 l	08/04→03/10		<b>KH10201</b> ProKIT
2.0 CRDi All-wheel Drive	100 kW	2 l	01/06→03/10		
2.0 CRDi All-wheel Drive	103 kW	2 l	01/06→03/10		
2.0 CRDi All-wheel Drive	110 kW	2 l	01/09→03/10		
2.7 All-wheel Drive	129 kW	2.7 l	08/04→11/10		
2.0 All-wheel Drive	105 kW	2 l	07/05→11/10		<b>KH10201</b> ProKIT
2.0 CRDi All-wheel Drive	88 kW	2 l	01/07→03/10		



























										
<b>INFINITI - FX</b>										<b>09/02→</b>
30d AWD	175 kW	3 l	04/10→							KH30026 ProKIT
35 All-wheel Drive	206 kW	3.5 l	01/03→12/08							
35 All-wheel Drive	244 kW	3.5 l	04/10→12/12							
35 AWD	205 kW	3.5 l	07/08→05/09							
35 AWD	223 kW	3.5 l	01/12→07/13							
35 AWD	226 kW	3.5 l	02/09→12/10							
37 All-wheel Drive	258 kW	3.7 l	07/12→12/13							
37 AWD	235 kW	3.7 l	10/08→							
37 AWD	242 kW	3.7 l	09/12→							
37 AWD	245 kW	3.7 l	07/08→07/13							
45 All-wheel Drive	232 kW	4.5 l	01/03→12/08							
45 All-wheel Drive	235 kW	4.5 l	09/02→12/05							
45 All-wheel Drive	239 kW	4.5 l	09/05→12/08							
45 AWD	241 kW	4.5 l	10/08→							
50 AWD	287 kW	5 l	10/08→							
50 AWD	291 kW	5 l	10/08→							
50 AWD	309 kW	5 l	06/13→07/13							
<b>INFINITI - G Convertible / G Saloon</b>										<b>08/02→</b>
25	163 kW	2.5 l	01/11→							KH30025 ProKIT
25	173 kW	2.5 l	01/10→12/13							
3.5	209 kW	3.5 l	09/04→06/07							
35	191 kW	3.5 l	10/02→							
35	228 kW	3.5 l	09/07→12/08							
37	235 kW	3.7 l	10/08→							
37	235 kW	3.7 l	09/10→							
37	240 kW	3.7 l	01/12→							
37	242 kW	3.7 l	09/10→							
37	243 kW	3.7 l	10/08→							
37	245 kW	3.7 l	09/08→							
37	245 kW	3.7 l	09/10→							
37	256 kW	3.7 l	09/12→							
37	258 kW	3.7 l	01/09→							
37	258 kW	3.7 l	09/10→12/13							
37	260 kW	3.7 l	09/12→							
25 X	163 kW	2.5 l	09/10→12/12							KH30026 ProKIT
3.5 X	209 kW	3.5 l	09/04→12/06							
35 X	191 kW	3.5 l	08/02→08/04							
35 X	228 kW	3.5 l	01/07→12/08							
37 X	235 kW	3.7 l	10/08→							
37 X	245 kW	3.7 l	09/08→12/13							
<b>INFINITI - M (Y51)</b>										<b>03/10→</b>
25	160 kW	2.5 l	03/10→							KH30025 ProKIT
25	163 kW	2.5 l	07/10→							
25	173 kW	2.5 l	09/10→12/12							
25L	173 kW	2.5 l	06/12→12/13							
30d	175 kW	3 l	03/10→							
35h	225 kW	3.5 l	04/11→							
37	235 kW	3.7 l	03/10→							
37	246 kW	3.7 l	09/10→12/13							
56	300 kW	5.6 l	03/10→							
56	309 kW	5.6 l	01/12→							
56	313 kW	5.6 l	03/10→							
37 X	246 kW	3.7 l	09/10→							KH30026 ProKIT
56 X	300 kW	5.6 l	03/10→							
56 X	313 kW	5.6 l	09/10→							
<b>INFINITI - M35</b>										<b>01/05→</b>
3.5	206 kW	3.5 l	01/05→							KH30025 ProKIT
3.5	209 kW	3.5 l	09/05→12/08							
3.5	226 kW	3.5 l	09/08→12/10							
3.5 X	206 kW	3.5 l	01/05→							KH30026 ProKIT
3.5 X	209 kW	3.5 l	09/05→12/08							
3.5 X	226 kW	3.5 l	09/08→12/10							
<b>INFINITI - Q50</b>										<b>04/13→</b>
2.0 T	153 kW	2 l	04/14→							KH30025 ProKIT
2.0 T	155 kW	2 l	04/14→							
3.0 t	224 kW	3 l	10/16→							
3.7	258 kW	3.7 l	04/14→							
50	275 kW	3 l	09/15→							
50	241 kW	3.7 l	06/13→							
50	245 kW	3.7 l	04/13→							
50 D	125 kW	2.2 l	04/13→							
50 Hybrid	216 kW	3.5 l	12/14→							
50 Hybrid	219 kW	3.5 l	06/13→							
50 Hybrid	268 kW	3.5 l	04/13→							
50 Red	298 kW	3 l	09/15→							



























     				
<b>INFINITI - Q50</b>				<b>04/13→</b>
Hybrid	264 kW	3.5 l	04/13→	 <b>KH30025 ProKIT</b>
<b>INFINITI - Q70 (Y51)</b>				<b>03/13→</b>
2.0	155 kW	2 l	11/18→	 <b>KH30025 ProKIT</b>
2.2 D	125 kW	2.2 l	10/14→	
2.5	163 kW	2.5 l	05/15→	
2.5	173 kW	2.5 l	08/13→05/15	
3.0	175 kW	3 l	03/13→	
3.5 Hybrid	219 kW	3.5 l	05/15→	
3.5 Hybrid	268 kW	3.5 l	03/13→	
3.7	235 kW	3.7 l	03/13→	
3.7	241 kW	3.7 l	06/13→	
3.7	243 kW	3.7 l	01/17→	
3.7	245 kW	3.7 l	06/13→	
3.7	246 kW	3.7 l	10/13→	
5.6	296 kW	5.6 l	01/15→	
5.6	310 kW	5.6 l	07/14→	
5.6	313 kW	5.6 l	09/13→	
<b>INFINITI - QX50 I</b>				<b>08/13→</b>
2.5	173 kW	2.5 l	08/13→	 <b>KH30025 ProKIT</b>
37	242 kW	3.7 l	08/13→	
2.5 AWD	163 kW	2.5 l	02/14→	 <b>KH30026 ProKIT</b>
2.5 AWD	173 kW	2.5 l	08/13→	
3.7 AWD	258 kW	3.7 l	08/13→	
30d AWD	175 kW	3 l	08/13→	
37 AWD	235 kW	3.7 l	08/13→	
37 AWD	240 kW	3.7 l	05/15→	
37 AWD	242 kW	3.7 l	08/13→	
<b>INFINITI - QX70 Wagon</b>				<b>08/13→</b>
3.5 AWD	224 kW	3.5 l	08/13→	 <b>KH30026 ProKIT</b>
3.7 AWD	235 kW	3.7 l	08/13→	
30d AWD	175 kW	3 l	08/13→	
37 AWD	240 kW	3.7 l	08/13→	
37 AWD	242 kW	3.7 l	08/13→	
37 AWD	245 kW	3.7 l	02/14→	
37 AWD	258 kW	3.7 l	08/13→	
50 AWD	287 kW	5 l	08/13→	
50 AWD	291 kW	5 l	08/13→	
50 AWD	294 kW	5 l	08/13→	
50 AWD	317 kW	5 l	02/14→	

     13 		
<b>ISUZU - D-MAX I (TFR, TFS)</b>		<b>10/02→06/12</b>
2.5 DiTD (TFR86_, TFR54_)	74 kW 2.5 l	10/02→06/12  ; 05/06 -> KH00087 ProKIT
2.5 DiTD (TFR86_)	100 kW 2.5 l	10/06→06/12  KH00087 ProKIT
<b>ISUZU - TROOPER I (UBS)</b>		<b>10/87→12/91</b>
2.8 TD (UBS55)	71 kW 2.8 l	10/87→12/91  ; 01/88 -> KH00026 ProKIT
<b>ISUZU - TROOPER I Open Off-Road Vehicle (UBS)</b>		<b>03/84→12/91</b>
2.2 TD (UBS52)	53 kW 2.2 l	03/84→12/91  ; 02/87 -> 09/88 KH00026 ProKIT
2.6 i (UBS17)	85 kW 2.6 l	10/87→12/91  ; 10/88 -> KH00026 ProKIT
<b>ISUZU - TROOPER II / TROOPER II Open Off-Road Vehicle (UB)</b>		<b>08/91→07/98</b>
3.2	130 kW 3.2 l	08/91→07/98  ; 03/92 -> 04/98 KH00026 ProKIT
<b>ISUZU - TROOPER III / TROOPER III Open Off-Road Vehicle</b>		<b>05/98→08/04</b>
3.0 DTI	117 kW 3 l	05/98→08/04  KH00026 ProKIT
3.0 DTI	118 kW 3 l	04/00→08/04
3.5 V6 24V	158 kW 3.5 l	04/00→08/04



										
<b>IVECO - DAILY I Platform/Chassis / DAILY I Van</b>									<b>01/78→12/89</b>	
30-8 (10011131, 10011132, 10011231, 10011232, 10011237,...	53 kW	2.4 l	01/78→12/89		Axle: Iveco Axle				KH00102 ProKIT	
30-8 (10014131, 10014132, 10014137, 10014231, 10014232,...	53 kW	2.4 l	01/78→12/89							
35-8 (10031131, 10031132, 10031137, 10031224, 10031231,...	53 kW	2.4 l	01/78→12/89							
35-8 (10034131, 10034132, 10034137, 10034224, 10034231,...	53 kW	2.4 l	01/78→12/89							
40-8	53 kW	2.4 l	01/83→06/89							
40-8 V	53 kW	2.4 l	01/83→06/89							
35-10 (10310311, 10311111, 10311112, 10311117, 10311211,...	68 kW	2.4 l	01/85→12/89						KH00102 ProKIT	
35-10 (10314204, 10314211, 10314212, 10314217, 10314411,...	68 kW	2.4 l	01/85→12/89							
45-10 (10331211, 10331212, 10331217, 10331304, 10331311,...	68 kW	2.4 l	01/85→12/89		11/85 -> 10/89; for vehicles with gross vehicle weight [t]: 4.5				KH00103 ProKIT	
45-10 V (10334204, 10334211, 10334212, 10334217,...	68 kW	2.4 l	01/85→12/89							
49-10 (10350211, 10350304, 10350311, 10350404, 10350411,...	68 kW	2.4 l	01/85→12/89		11/85 -> 10/89; for vehicles with gross vehicle weight [t]: 4.9				KH00103 ProKIT	
49-10 V (10354204, 10354211, 10354212, 10354217,...	68 kW	2.4 l	01/85→12/89							
<b>IVECO - DAILY II Bus</b>									<b>05/96→05/99</b>	
A 40-12 (95819311, 95819315, 95819317, 95819331)	90 kW	2.8 l	05/96→05/99		for vehicles with gross vehicle weight [t]: 4.05				KH10170 ProKIT	
					for vehicles with gross vehicle weight [t]: 4.05				KH10171 ProKIT	
A 45-10 (95739111, 95739131, 95739311, 95739317,...	76 kW	2.8 l	05/96→05/99		for vehicles with gross vehicle weight [t]: 4.5				KH10170 ProKIT	
					for vehicles with gross vehicle weight [t]: 4.5				KH10171 ProKIT	
<b>IVECO - DAILY II Dump Truck / DAILY II Platform/Chassis / DAILY II Van</b>									<b>01/89→05/99</b>	
30-8 (10011131, 10011132, 10011231, 10011232, 10011237,...	60 kW	2.5 l	01/92→08/98		Axle: Iveco Axle; -> 01/97				KH00102 ProKIT	
30-8 (12910211, 12911111, 12911112, 12911117, 12911131,...	55 kW	2.5 l	01/92→08/98							
30-8 (12910211, 12911111, 12911112, 12911117, 12911131,...	60 kW	2.5 l	01/92→08/98							
30-8 (12914111, 12914112, 12914117, 12914131, 12914137,...	55 kW	2.5 l	01/89→08/98							
30-8 (12914111, 12914112, 12914117, 12914131, 12914137,...	60 kW	2.5 l	01/89→08/98							
30-8 (14914111, 14914117, 14914211, 14914217, 14915111,...	60 kW	2.5 l	01/89→08/98							
35-10 (12971112, 12971212, 12971312, 12971317, 12976112,...	76 kW	2.5 l	01/89→12/96						KH00102 ProKIT	
35-10 (12974212, 12974217, 13014111, 13014131, 13014204,...	76 kW	2.5 l	01/89→08/98		-> 01/97				KH00102 ProKIT	
35-10 (12974212, 12974217, 13014111, 13014131, 13014204,...	80 kW	2.5 l	01/89→08/98							
35-10 (15030111, 15030211, 15030311, 15031111, 15031117,...	76 kW	2.8 l	01/96→05/99		05/96 ->; for vehicles with gross vehicle weight [t]: 3.5				KH10170 ProKIT	
35-10 (15034111, 15034204, 15034211, 15034215, 15034217,...	76 kW	2.8 l	01/96→05/99		-> 01/97				KH00102 ProKIT	
					05/96 ->; for vehicles with gross vehicle weight [t]: 3.5				KH10171 ProKIT	
35-12 (15130311, 15130411, 15131111, 15131204, 15131211,...	90 kW	2.8 l	05/96→05/99		for vehicles with gross vehicle weight [t]: 3.5				KH10170 ProKIT	
35-12 K (15130311, 15130411, 15131111, 15131204,...	90 kW	2.8 l	09/96→08/98		for vehicles with gross vehicle weight [t]: 3.5				KH10171 ProKIT	
35-8 (12931102, 12931104, 12931111, 12931112, 12931117,...	55 kW	2.5 l	01/89→08/98		Axle: Iveco Axle				KH00102 ProKIT	
35-8 (12931102, 12931104, 12931111, 12931112, 12931117,...	60 kW	2.5 l	01/89→08/98		Manufacturer Restriction: SALISBURY-2; 03/96 ->					
35-8 (12934104, 12934111, 12934112, 12934117, 12934124,...	55 kW	2.5 l	01/91→08/98							
35-8 (12934104, 12934111, 12934112, 12934117, 12934124,...	60 kW	2.5 l	01/91→08/98							
35-8 (14930304, 14931104, 14931111, 14931115, 14931204,...	62 kW	2.8 l	09/98→05/99		Axle: Iveco Axle				KH00102 ProKIT	
35-8 (14934104, 14934111, 14934204, 14934205, 14934211,...	62 kW	2.8 l	09/98→05/99		Manufacturer Restriction: SALISBURY-2					
40-10 4x4 (15214104, 15214111, 15214117, 15215111)	76 kW	2.8 l	01/97→05/99		for vehicles with gross vehicle weight [t]: 4.05				KH10170 ProKIT	
40-10 W 4x4 (15211104, 15211105, 15211111, 15211115,...	76 kW	2.8 l	01/97→05/99		for vehicles with gross vehicle weight [t]: 4.05				KH10171 ProKIT	

										
<b>IVECO - DAILY II Dump Truck / DAILY II Platform/Chassis / DAILY II Van</b>									<b>01/89→05/99</b>	
49-10 (13050211, 13050231, 13050304, 13050311, 13050331,...)	76 kW	2.5 l	01/89→04/96		11/89 ->	for vehicles with gross vehicle weight [t]: 5			KH00103 ProKIT	
49-10 V (13054204, 13054211, 13054212, 13054215,...)	76 kW	2.5 l	01/89→04/96							
49-10 (15050304, 15050404, 15050411, 15051204, 15051211,...)	76 kW	2.8 l	05/96→05/99		-> 08/97;	for vehicles with gross vehicle weight [t]: 5			KH10170 ProKIT	
49-12 (15150211, 15150311, 15150404, 15150411, 15151204,...)	90 kW	2.8 l	05/96→05/99		-> 08/97;	for vehicles with gross vehicle weight [t]: 5			KH10171 ProKIT	
49-12 V (15154204, 15154211, 15154215, 15154217,...)	90 kW	2.8 l	05/96→05/99							
59-12 (13150204, 13150211, 13150231, 13150311, 13150312,...)	85 kW	2.5 l	05/91→04/96						KH20179 ProKIT	
59-12 (15170211, 15170304, 15170311, 15170504, 15170511,...)	90 kW	2.8 l	05/96→05/99							
59-12 V (13154404, 13154411, 13154412, 13154417,...)	85 kW	2.5 l	05/91→04/96							
59-12 V (15174404, 15174411, 15174415, 15174417)	90 kW	2.8 l	05/96→05/99							
<b>IVECO - DAILY III Platform/Chassis / DAILY III Van</b>									<b>05/99→07/07</b>	
29 L 9	62 kW	2.8 l	05/99→04/06		07/99 ->	for vehicles with gross vehicle weight [t]: 3.2, 3.3			KH10223 ProKIT	
29 L 9 V	62 kW	2.8 l	05/99→07/07		07/99 ->	for vehicles with gross vehicle weight [t]: 3.2, 3.3			KH10224 ProKIT	
35 C 12 , 35 S 12 (AEKA14A1, AEKA14AA, AEKA64A1,...)	85 kW	2.3 l	09/02→04/06		01/03 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10170 ProKIT	
35 C 12 V, 35 S 12 V (AGKA43A2, AGKB43A2, AGKB46A2,...)	85 kW	2.3 l	09/02→07/07		01/03 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10171 ProKIT	
35 S 11,35 C 11 (A2FC13AA, A6FBU4AB, A2NB14A1, A2ND13A1,...)	78 kW	2.8 l	05/99→04/06		01/01 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10223 ProKIT	
					01/01 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10224 ProKIT	
35 S 13,35 C 13	92 kW	2.8 l	05/99→04/06		07/99 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10170 ProKIT	
35 S 13 V,35 C 13 V	92 kW	2.8 l	05/99→07/07		07/99 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10171 ProKIT	
35 S 9,35 C 9	62 kW	2.8 l	05/99→04/06		07/99 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10223 ProKIT	
35 S 9 V,35 C 9 V	62 kW	2.8 l	05/99→07/07		07/99 ->	for vehicles with gross vehicle weight [t]: 3.5			KH10224 ProKIT	
40 C 13	92 kW	2.8 l	05/99→04/06		07/99 ->	for vehicles with gross vehicle weight [t]: 4.2			KH10170 ProKIT	
					07/99 ->	for vehicles with gross vehicle weight [t]: 4.2			KH10171 ProKIT	
50 C 13	92 kW	2.8 l	05/99→04/06		07/99 ->	for vehicles with gross vehicle weight [t]: 5.2			KH10170 ProKIT	
50 C 13	92 kW	2.8 l	05/99→07/07		07/99 ->	for vehicles with gross vehicle weight [t]: 5.2			KH10171 ProKIT	
<b>IVECO - DAILY IV Bus / DAILY IV Platform/Chassis / DAILY IV Van</b>									<b>05/06→08/11</b>	
29L10	70 kW	2.3 l	05/06→08/11						KH10392 ProKIT	
29L10 V	70 kW	2.3 l	05/06→08/11							
29L12	85 kW	2.3 l	05/06→08/11							
29L12 V, 29L12 V/P	85 kW	2.3 l	05/06→08/11							
29L14	100 kW	2.3 l	05/06→08/11							
29L14 C, 29L14 C/P, 29L14 V, 29L14 V/P	100 kW	2.3 l	05/06→08/11							
35C10, 35S10	70 kW	2.3 l	05/06→08/11							
35C12, 35S12	85 kW	2.3 l	05/06→08/11							
35C12 V, 35C12 V/P, 35S12 V, 35S12 V/P	85 kW	2.3 l	05/06→08/11							
35C14, 35C14 /P, 35S14, 35S14 /P, 35S14 D, 35S14 D/P	103 kW	3 l	09/09→08/11							
35C14, 35S14, 35S14 /P	100 kW	2.3 l	05/06→08/11							
35C14 G, 35C14 G/P, 35S14 G, 35S14 G/P, 35C14 GD,...	100 kW	3 l	07/07→08/11							
35C14 GV, 35C14 GV/P, 35S14 GV, 35S14 GV/P	100 kW	3 l	07/07→08/11							
35C14 V, 35C14 V/P, 35S14 V, 35S14 V/P	103 kW	3 l	09/09→08/11							
35C18, 35S18	130 kW	3 l	05/06→08/11							
35C18 V, 35C18 V/P, 35S18 V, 35S18 V/P	130 kW	3 l	05/06→08/11							
35S14, 35S14 /P	100 kW	2.3 l	05/06→08/11							
35S14 C, 35S14 C/P, 35S14 V, 35S14 V/P, 35C14 V,...	100 kW	2.3 l	05/06→08/11							



**JAGUAR - E-TYPE / E-TYPE 2+2 / E-TYPE Convertible** **04/61→04/75**

3.8 (Series1)	195 kW	3.8 l	04/61→07/64	; 10/61 ->	KH00127 ProKIT
4.2 (Series 1)	195 kW	4.2 l	05/64→09/68	; 08/66 ->	KH00127 ProKIT
4.2 (Series 1)	195 kW	4.2 l	05/64→09/70	; 01/66 ->	KH00127 ProKIT
4.2 (Series 1)	195 kW	4.2 l	06/66→09/68		KH00127 ProKIT
4.2 (Series2)	127 kW	4.2 l	05/68→05/71	; -> 03/71	KH00127 ProKIT
4.2 (Series2)	198 kW	4.2 l	07/68→05/71		
4.2 (Series3)	127 kW	4.2 l	03/71→04/75		
4.2 (Series2)	198 kW	4.2 l	07/68→05/71	; -> 09/70	KH00127 ProKIT
V12 5.3 (Series3)	203 kW	5.3 l	03/71→04/75	; -> 12/74	KH00127 ProKIT

**JAGUAR - S-TYPE II (X200)** **01/99→12/08**

2.5 V6	147 kW	2.5 l	04/02→10/07		KH30096 ProKIT
2.7 D	152 kW	2.7 l	06/04→10/07		KH10168 ProKIT
3.0 V6	175 kW	3 l	01/99→10/07		
4.0 V8	203 kW	4 l	01/99→04/02		
4.2 V8	219 kW	4.2 l	04/02→10/07		
R 4.2 V8	291 kW	4.2 l	04/02→10/07		
4.0 V8	209 kW	4 l	09/99→12/02		KH30096 ProKIT
4.2 Supercharged	298 kW	4.2 l	11/01→12/08		

**JAGUAR - XF I Sedan / XF SPORTBRAKE (X250)** **03/08→04/15**

2.0	177 kW	2 l	06/12→04/15	; 09/12 ->	KH10233 ProKIT
2.2 D	147 kW	2.2 l	03/12→04/15		
2.2 D	120 kW	2.2 l	04/11→04/15		KH10233 ProKIT
2.2 D	140 kW	2.2 l	05/11→04/15		
5.0 XFR-S	405 kW	5 l	10/12→04/15		
2.2 D	120 kW	2.2 l	09/12→04/14		KH30096 ProKIT
3.0 D	155 kW	3 l	03/09→04/15		
5.0 Kompressor	346 kW	5 l	01/09→04/15		
2.2 D	147 kW	2.2 l	09/12→04/14		KH30096 ProKIT
2.7 D	152 kW	2.7 l	03/08→04/15		KH10233 ProKIT
3.0	175 kW	3 l	03/08→04/15		
3.0 D	177 kW	3 l	03/09→04/15		
3.0 D	177 kW	3 l	09/12→04/14		
3.0 D	202 kW	3 l	03/09→04/15		
3.0 D	202 kW	3 l	09/12→04/14		
4.2	219 kW	4.2 l	03/08→04/15		
4.2 Kompressor	306 kW	4.2 l	03/08→04/15		
5.0	283 kW	5 l	03/09→04/15		
5.0 Kompressor	375 kW	5 l	03/09→04/15		
3.0	250 kW	3 l	03/12→04/15	; 09/12 ->	KH10233 ProKIT

**JAGUAR - XJ (X308)** **07/97→05/03**

3.2	174 kW	3.2 l	07/97→05/03	; VIN -> 853935	KH10169 ProKIT
4.0	209 kW	4 l	07/97→05/03	; VIN 853936 ->	KH10172 ProKIT
4.0	267 kW	4 l	07/97→05/03		

**JAGUAR - XJ (X351)** **10/09→**

2.0 Ti4	177 kW	2 l	05/12→	; 09/12 ->	KH10233 ProKIT
3.0 SCV6	250 kW	3 l	03/12→		
3.0 SDV6	202 kW	3 l	10/09→04/16		KH10233 ProKIT
3.0 V6	175 kW	3 l	01/11→		
5.0 SCV8	346 kW	5 l	10/09→		
5.0 SCV8	375 kW	5 l	10/09→		
5.0 V8	283 kW	5 l	10/09→		









































**JAGUAR - XJ (XJ40, XJ81)** **10/86→11/94**

3.6	136 kW	3.6 l	10/86→08/89	; 01/87 ->	KH00097 ProKIT
6 2.9	108 kW	2.9 l	10/86→08/90		KH00131 ProKIT
6 2.9	117 kW	2.9 l	10/86→08/90		
6 2.9	123 kW	2.9 l	10/86→08/90		
6 3.6	145 kW	3.6 l	10/86→08/89		
6 3.6	156 kW	3.6 l	10/86→08/89		
4.0	166 kW	4 l	10/89→08/94		KH00131 ProKIT
4.0	187 kW	4 l	10/89→08/94		
6 3.2 24V	146 kW	3.2 l	09/90→11/94		KH00097 ProKIT
6 4.0	163 kW	4 l	09/89→11/94		KH00131 ProKIT
V12 6.0	229 kW	6 l	03/93→11/94		KH00097 ProKIT






















**JAGUAR - XJSC Convertible (X27)** **09/85→03/96**

3.6	162 kW	3.6 l	10/86→12/88	; -> 09/87	KH00127 ProKIT
4.0	163 kW	4 l	05/91→09/94	; 05/92 -> 01/94	KH00127 ProKIT
5.3	211 kW	5.3 l	01/88→05/92	; 09/89 ->	KH00127 ProKIT












































































































				      13 		
<b>JAGUAR - XJSC Convertible (X27)</b>				<b>09/85→03/96</b>		
5.3 H.E.	217 kW	5.3 l	09/85→12/90	 04/88 ->	KH00127 ProKIT	
				 08/88 -> 08/89; AT		
6.0	222 kW	6 l	05/93→03/96	 -> 05/95	KH00127 ProKIT	
<b>JAGUAR - XJS Coupe</b>				<b>09/73→03/96</b>		
4.0	163 kW	4 l	05/91→09/94		KH00127 ProKIT	
4.0	171 kW	4 l	07/94→03/96			
5.3	211 kW	5.3 l	09/73→05/92	 09/89 ->	KH00127 ProKIT	
5.3	213 kW	5.3 l	09/75→07/81	 -> 12/76;	KH00127 ProKIT	
				VIN -> 2W 2573 (RHD), CH 2W 53169 (LHD)		
				 01/76 ->;		
				VIN 2W 2574 (RHD), CH 2W 53170 (LHD) ->		
5.3 H.E.	217 kW	5.3 l	07/81→12/87	 VIN 2W 2574 (RHD), CH 2W 53170 (LHD) ->	KH00127 ProKIT	
<b>JAGUAR - XJ Sedan</b>				<b>10/69→12/92</b>		
12 5.3	187 kW	5.3 l	08/86→09/89	 01/87 ->	KH00097 ProKIT	
Sovereign V12	194 kW	5.3 l	10/86→12/92		KH00131 ProKIT	
Sovereign V12	197 kW	5.3 l	07/85→12/92			
12 5.3	198 kW	5.3 l	06/72→09/73	 07/72 ->	KH00127 ProKIT	
12 H.E.	217 kW	5.3 l	05/81→12/92	 01/87 ->	KH00097 ProKIT	
				 01/87 ->	KH00131 ProKIT	
				 -> 10/83	KH00127 ProKIT	
6 3.4	119 kW	3.4 l	05/75→10/86		KH00127 ProKIT	
6 4.2	137 kW	4.2 l	10/69→05/75	 -> 09/70	KH00127 ProKIT	
6 4.2	151 kW	4.2 l	09/79→12/87	 01/87 ->	KH00097 ProKIT	
				 -> 10/86	KH00127 ProKIT	
<b>JAGUAR - XJ Sedan (X300, X330)</b>				<b>09/94→09/97</b>		
12 6.0	229 kW	6 l	09/94→09/97	 -> 12/96	KH00097 ProKIT	
6 3.2	155 kW	3.2 l	11/94→07/97		KH00131 ProKIT	
6 Sovereign 4.0	177 kW	4 l	09/94→07/97			
R Super Charged 4.0	235 kW	4 l	11/94→07/97			
<b>JAGUAR - XJ Sedan (X350, X358)</b>				<b>03/03→03/09</b>		
3.0	175 kW	3 l	05/03→03/09		KH30096 ProKIT	
3.6	190 kW	3.6 l	05/03→03/09		KH10168 ProKIT	
4.2	219 kW	4.2 l	05/03→03/09			
R 4.2	291 kW	4.2 l	03/03→03/09			
D 2.7	152 kW	2.7 l	10/05→03/09		KH30096 ProKIT	
<b>JAGUAR - XK 8 Convertible / XK 8 Coupe (X100)</b>				<b>03/96→12/06</b>		
4.0	209 kW	4 l	03/96→12/02	 VIN -> 853935	KH10169 ProKIT	
4.0	209 kW	4 l	03/96→07/05		KH10172 ProKIT	
4.0	216 kW	4 l	05/96→07/99	 VIN 853936 ->	KH00131 ProKIT	
4.0	216 kW	4 l	05/96→07/05			
4.0	267 kW	4 l	02/98→07/05			
4.0 XKR	276 kW	4 l	05/98→07/05		KH00131 ProKIT	
4.2	219 kW	4.2 l	08/02→07/05			
4.2	219 kW	4.2 l	08/02→12/06			
R 4.2	291 kW	4.2 l	08/02→07/05			
R 4.2	291 kW	4.2 l	08/02→12/06			
<b>JAGUAR - X-TYPE I / X-TYPE I Estate (X400)</b>				<b>06/01→12/09</b>		
2.0 D	96 kW	2 l	07/03→11/09		KH10038 ProKIT	
2.1 V6	115 kW	2.1 l	03/02→11/09			
2.2 D	110 kW	2.2 l	10/05→11/09			
2.2 D	110 kW	2.2 l	10/05→12/09			
2.0 D	96 kW	2 l	02/04→12/09		KH10038 ProKIT	
2.1 V6	115 kW	2.1 l	11/03→03/09		KH30043 ProKIT	
2.2 D	107 kW	2.2 l	01/07→11/09			
2.2 D	107 kW	2.2 l	01/07→12/09			
2.2 D	114 kW	2.2 l	10/05→11/09			
2.2 D	114 kW	2.2 l	10/05→12/09			
2.5	144 kW	2.5 l	02/04→12/09		KH10038 ProKIT	
2.5 V6 All-wheel Drive	144 kW	2.5 l	06/01→11/09			
3.0	169 kW	3 l	02/04→12/09	 -> 02/04	KH30107 ProKIT	
3.0 V6 All-wheel Drive	169 kW	3 l	06/01→12/08			

					13	i	
<b>JEEP - CHEROKEE (KJ)</b>							<b>09/01→01/08</b>
2.4 4x4	108 kW	2.4 l	09/01→01/08		-> 09/03;	ABS	KH30076 ProKIT
					-> 09/03;	ABS	KH30093 ProKIT
							KH00120 ProKIT
2.4 Laredo	108 kW	2.4 l	10/01→09/04				KH00120 ProKIT
3.7 Laredo	150 kW	3.7 l	10/01→09/04				
2.5 CRD 4x4	105 kW	2.5 l	09/01→01/08		-> 10/04;	ABS	KH30076 ProKIT
2.8 CRD 4x4	110 kW	2.8 l	11/02→01/08		-> 10/04;	ABS	KH30093 ProKIT
3.7 4x4	155 kW	3.7 l	09/01→01/08				KH00120 ProKIT
2.8 CRD 4x4	120 kW	2.8 l	11/04→01/08		ABS		KH30076 ProKIT
					ABS		KH30093 ProKIT
							KH00120 ProKIT
3.7 4x4	150 kW	3.7 l	08/03→01/08		-> 04/06;	ABS	KH30076 ProKIT
					-> 04/06;	ABS	KH30093 ProKIT
							KH00120 ProKIT
3.7 4x4	157 kW	3.7 l	09/01→10/07		ABS		KH30076 ProKIT
					ABS		KH30093 ProKIT
<b>JEEP - CHEROKEE (KK)</b>							<b>01/08→</b>
2.8 CRD 4x4	130 kW	2.8 l	05/08→				KH30152 ProKIT
3.7 V6 4x4	151 kW	3.7 l	01/08→				
<b>JEEP - CHEROKEE (XJ)</b>							<b>10/84→09/01</b>
2.1 D 4x4	59 kW	2.1 l	10/86→09/92				KH30159 ProKIT
2.1 TD	59 kW	2.1 l	06/89→03/92		Axle Code: Dana 35		KH00081 ProKIT
2.5	89 kW	2.5 l	10/90→09/96				
2.1 TD	64 kW	2.1 l	10/84→09/01		-> 08/99		KH30159 ProKIT
2.5	89 kW	2.5 l	10/95→09/01				KH00081 ProKIT
2.5 i 4x4	87 kW	2.5 l	10/84→09/01		Axle Code: Dana 35		
2.5 i 4x4	90 kW	2.5 l	12/91→09/01				
2.5 TD 4x4	85 kW	2.5 l	01/88→09/01				
2.5 Tdi 4x4	85 kW	2.5 l	10/96→09/01				
4.0 i	127 kW	4 l	07/98→09/01				
4.0 i	136 kW	4 l	01/88→09/01				
4.0 i 4x4	131 kW	4 l	01/95→09/01				
2.5	90 kW	2.5 l	10/86→09/90				KH30159 ProKIT
2.5 4x4	90 kW	2.5 l	10/86→09/90				
4.0	131 kW	4 l	10/86→09/90				
4.0 4x4	131 kW	4 l	10/86→09/90				
2.5 SE	87 kW	2.5 l	10/96→09/99		-> 08/99		KH30159 ProKIT
4.0 i	135 kW	4 l	12/91→09/01				
4.0 i	135 kW	4 l	02/99→09/01		Axle Code: Dana 35		KH00081 ProKIT
<b>JEEP - COMMANDER (XK, XH)</b>							<b>09/05→12/10</b>
3.0 CRD 4x4	160 kW	3 l	04/06→12/10		-> 04/10		KH30142 ProKIT
3.7 V6 4x4	157 kW	3.7 l	09/05→12/10				KH30142 ProKIT
4.7 V8 4x4	170 kW	4.7 l	09/05→12/10				
5.7 V8 4x4	240 kW	5.7 l	09/05→12/10				
<b>JEEP - COMPASS (MK49)</b>							<b>12/10→</b>
2.2 CRD	100 kW	2.2 l	05/11→				KH30164 ProKIT
2.2 CRD 4x4	120 kW	2.1 l	12/10→				
2.2 CRD 4x4	100 kW	2.2 l	05/11→				
<b>JEEP - GRAND CHEROKEE I (ZJ, ZG)</b>							<b>09/91→04/99</b>
2.5 TD 4x4 (Z)	85 kW	2.5 l	10/95→04/99				KH30159 ProKIT
2.5 TD Laredo	85 kW	2.5 l	10/96→09/98		Axle Code: Dana 35		KH00081 ProKIT
4.0 i 4x4 (Z)	130 kW	4 l	10/95→04/99				
4.0 i 4x4 (ZJ)	132 kW	4 l	06/92→04/99				
4.0 i 4x4 (ZJ)	135 kW	4 l	09/91→04/99				
4.0 Laredo	131 kW	4 l	10/96→09/98				
5.2	164 kW	5.2 l	10/96→09/98				
5.2 4x4	164 kW	5.2 l	10/96→09/98				
5.2 4x4 (Z)	156 kW	5.2 l	10/95→04/99				
5.2 i 4x4 (ZJ)	155 kW	5.2 l	01/92→04/99				
5.2 i 4x4 (ZJ)	158 kW	5.2 l	09/92→09/98				
5.2 Limited 4x4	136 kW	5.2 l	10/96→09/98				
5.9 i 4x4	177 kW	5.9 l	08/97→04/99				

											
<b>JEEP - GRAND CHEROKEE II (WJ, WG)</b>											<b>04/99→09/05</b>
2.7 CRD 4x4	120 kW	2.7 l	10/01→09/05							KH30116 ProKIT	
2.7 CRD 4x4	120 kW	2.7 l	10/04→09/05								
3.1 TD 4x4	103 kW	3.1 l	04/99→12/01								
4.0 4x4	140 kW	4 l	04/99→09/05								
4.7 V8 4x4	162 kW	4.7 l	04/99→08/00								
4.7 V8 4x4	164 kW	4.7 l	04/99→09/05								
4.7 V8 4x4	167 kW	4.7 l	06/03→09/05								
4.7 V8 4x4	190 kW	4.7 l	10/01→09/05								
<b>JEEP - GRAND CHEROKEE III (WH, WK)</b>											<b>06/05→12/10</b>
3.0 CRD 4x4	155 kW	3 l	05/06→12/10							KH30142 ProKIT	
4.7 V8 4x4	223 kW	4.7 l	09/07→02/10								
3.0 CRD 4x4	160 kW	3 l	06/05→12/10		-> 05/07					KH30142 ProKIT	
4.7 V8 4x4	170 kW	4.7 l	06/05→12/10								
5.7 V8 4x4	240 kW	5.7 l	06/05→12/10								
6.1 SRT8 4x4	313 kW	6.1 l	03/06→12/10		06/06 -> 03/08					KH30142 ProKIT	
<b>JEEP - PATRIOT (MK74)</b>											<b>02/07→12/17</b>
2.0 CRD 4x4	103 kW	2 l	02/07→12/17							KH30164 ProKIT	
2.2 CRD 4x4	120 kW	2.2 l	01/11→12/17								
2.4 4x4	125 kW	2.4 l	01/08→12/17								
2.4 Eco + 4x4	125 kW	2.4 l	07/08→12/17								
<b>JEEP - RENEGADE SUV (BU, B1, BV)</b>											<b>07/14→</b>
1.4	103 kW	1.4 l	07/14→							KH30190 ProKIT	
1.6	81 kW	1.6 l	07/14→								
1.6 CRD	88 kW	1.6 l	07/14→							KH30184 ProKIT	
1.4 4x4	125 kW	1.4 l	07/14→							KH30190 ProKIT	
2.0 CRD 4x4	88 kW	2 l	07/14→								
2.0 CRD 4x4	103 kW	2 l	07/14→								
2.0 CRD 4x4	125 kW	2 l	07/14→								
<b>JEEP - WRANGLER I (YJ, SJ_)</b>											<b>08/86→08/96</b>
2.5	76 kW	2.5 l	01/88→12/91							KH30159 ProKIT	
2.5	89 kW	2.5 l	12/91→08/96								
4.0	131 kW	4 l	12/91→08/96		Axle Code: Dana 35					KH00081 ProKIT	
4.2	84 kW	4.2 l	08/86→08/89								
4.2 2WD	82 kW	4.2 l	10/86→09/90								
<b>JEEP - WRANGLER II / WRANGLER III (TJ, JK)</b>											<b>08/96→04/07</b>
2.4	105 kW	2.4 l	11/02→04/07		Axle Code: Dana 35					KH00081 ProKIT	
2.8 CRD	130 kW	2.8 l	04/07→								
2.8 CRD	147 kW	2.8 l	11/10→								
3.6 V6	209 kW	3.6 l	10/11→								
3.8	146 kW	3.8 l	04/07→								
3.8	153 kW	3.8 l	04/07→12/11								
4.0 Rubicon	128 kW	4 l	08/03→04/07								
2.5	87 kW	2.5 l	08/96→04/07		-> 08/99					KH30159 ProKIT	
4.0	124 kW	4 l	06/98→04/07								
4.0	130 kW	4 l	08/96→04/07		Axle Code: Dana 35					KH00081 ProKIT	



										
<b>KIA - CARENS I (FC)</b>										<b>03/00→07/02</b>
1.8 i	81 kW	1.8 l	11/00→07/02							KH10016 ProKIT
					ABS, 					KH20198 ProKIT
1.8 i 16V	81 kW	1.8 l	03/00→05/02							KH10016 ProKIT
<b>KIA - CARENS II MPV (FJ)</b>										<b>07/02→</b>
1.6	77 kW	1.6 l	07/02→							KH10016 ProKIT
1.8	93 kW	1.8 l	07/02→		-> 05/06; ABS, 					KH20198 ProKIT
2.0 CRDi	83 kW	2 l	07/02→							KH10016 ProKIT
2.0 CRDi	103 kW	2 l	11/05→							KH10016 ProKIT
					10/06 -> 11/07					KH30161 ProKIT
					09/09 -> 12/12					KH30147 ProKIT
2.0 CVVT	102 kW	2 l	08/04→							KH10016 ProKIT
					09/04 -> 05/06; ABS, 					KH20198 ProKIT
<b>KIA - CARNIVAL / GRAND CARNIVAL III (VQ)</b>										<b>04/06→</b>
2.2 CRDi	110 kW	2.2 l	01/10→							KH30103 ProKIT
2.2 CRDi	143 kW	2.2 l	01/10→							
2.7 V6	139 kW	2.7 l	06/06→							
2.9 CRDi	136 kW	2.9 l	04/06→							
<b>KIA - CARNIVAL I / CARNIVAL II (UP, GQ)</b>										<b>08/99→09/07</b>
2.5 V6	110 kW	2.5 l	10/01→06/06							KH10114 ProKIT
2.5 V6	121 kW	2.5 l	08/99→10/01							KH00084 ProKIT
2.9 CRDi	106 kW	2.9 l	10/01→06/06							
2.9 TDi	93 kW	2.9 l	08/99→10/01							
2.9 TDi	93 kW	2.9 l	08/99→09/07							
3.5	143 kW	3.5 l	07/02→04/06							
<b>KIA - CEE'D (JD)</b>										<b>05/12→07/18</b>
1.4 CRDi 90	66 kW	1.4 l	05/12→07/18							KH30067 ProKIT
1.4 CVVT	73 kW	1.4 l	05/12→07/18							
1.6 CRDi 110	81 kW	1.6 l	05/12→07/18							
1.6 CRDi 128	94 kW	1.6 l	05/12→07/18							
1.6 GDI	99 kW	1.6 l	05/12→07/18							
<b>KIA - CEE'D Hatchback (ED)</b>										<b>12/06→12/12</b>
1.4	80 kW	1.4 l	12/06→12/12							KH10157 ProKIT
1.6	90 kW	1.6 l	12/06→12/12		-> 09/08					KH30067 ProKIT
1.6	93 kW	1.6 l	02/08→12/12							
1.6 CRDi 115	85 kW	1.6 l	12/06→12/12							
1.6 CRDi 90	66 kW	1.6 l	12/06→12/12							
2.0	105 kW	2 l	12/06→12/12							KH10157 ProKIT
2.0 CRDi 140	103 kW	2 l	09/07→12/12							
<b>KIA - CEE'D Sportswagon (JD)</b>										<b>09/12→07/18</b>
1.4 CRDi 90	66 kW	1.4 l	09/12→07/18							KH30067 ProKIT
1.4 CVVT	73 kW	1.4 l	09/12→07/15							
1.6 CRDi 128	94 kW	1.6 l	09/12→07/15							
1.6 GDI	99 kW	1.6 l	09/12→07/18							
<b>KIA - CEE'D SW (ED)</b>										<b>07/07→12/12</b>
1.4	80 kW	1.4 l	09/07→12/12							KH10157 ProKIT
1.6	90 kW	1.6 l	09/07→12/12		-> 09/08					KH30067 ProKIT
1.6	93 kW	1.6 l	09/07→12/12							
1.6 CRDi 115	85 kW	1.6 l	09/07→12/12							
1.6 CRDi 90	66 kW	1.6 l	09/07→12/12							
1.6	85 kW	1.6 l	09/07→11/12							KH10157 ProKIT
2.0	105 kW	2 l	09/07→12/12							
2.0 CRDi 140	103 kW	2 l	07/07→12/12							
<b>KIA - CERATO I Hatchback / CERATO I Saloon (LD)</b>										<b>03/04→12/09</b>
1.6	77 kW	1.6 l	04/04→12/09							KH10197 ProKIT
1.6	77 kW	1.6 l	07/04→01/07							
2.0	105 kW	2 l	03/04→05/07							
2.0	105 kW	2 l	04/04→01/07							
1.6	90 kW	1.6 l	05/06→12/09		08/06 ->					KH10197 ProKIT
<b>KIA - CLARUS Estate (GC)</b>										<b>05/98→</b>
1.8 i 16V	85 kW	1.8 l	05/98→							KH10016 ProKIT
2.0 i 16V	98 kW	2 l	05/98→		-> 07/01; ABS					KH20198 ProKIT

													
<b>KIA - CREDOS Sedan (K9A)</b>												<b>07/96→11/01</b>	
1.8 i 16V	85 kW	1.8 l	07/96→08/01									KH10016 ProKIT	
2.0 i 16V	98 kW	2 l	07/96→11/01		-> 07/01; 							KH20198 ProKIT	
<b>KIA - MAGENTIS II Sedan (MG)</b>												<b>11/05→12/10</b>	
2.0	106 kW	2 l	11/05→12/10									KH10123 ProKIT	
2.0	121 kW	2 l	09/09→12/10		without ABS sensor ring							KH30171 ProKIT	
2.0 CRDi	100 kW	2 l	11/05→12/08									KH30176 ProKIT	
2.0 CRDi	103 kW	2 l	04/06→12/10									KH30176 ProKIT	
2.0 CRDi	110 kW	2 l	04/06→12/10									KH30176 ProKIT	
2.7	138 kW	2.7 l	11/05→12/10									KH30176 ProKIT	
2.7 V6	142 kW	2.7 l	07/09→12/10									KH30176 ProKIT	
2.4	119 kW	2.4 l	08/06→12/09		without ABS sensor ring							KH30171 ProKIT	
												KH30176 ProKIT	
<b>KIA - OPIRUS (GH)</b>												<b>09/03→</b>	
3.0 GH300	138 kW	3 l	09/03→		11/06 -> 09/07							KH30161 ProKIT	
3.5	149 kW	3.5 l	09/03→									KH30161 ProKIT	
3.8 V6	196 kW	3.8 l	10/06→									KH30161 ProKIT	
<b>KIA - OPTIMA (TF, FSGDS6B)</b>												<b>06/10→</b>	
1.7 CRDi	100 kW	1.7 l	03/12→		-> 07/13							KH10123 ProKIT	
2.0	125 kW	2 l	03/12→									KH30147 ProKIT	
2.0 CVVT Hybrid	140 kW	2 l	12/12→									KH30147 ProKIT	
2.0	204 kW	2 l	09/10→									KH30147 ProKIT	
2.0 CVVL	121 kW	2 l	03/12→									KH30147 ProKIT	
2.4	129 kW	2.4 l	06/10→12/15									KH30147 ProKIT	
2.4	132 kW	2.4 l	03/12→									KH30147 ProKIT	
2.4	149 kW	2.4 l	09/10→									KH30147 ProKIT	
2.4 Hybrid	154 kW	2.4 l	09/11→									KH30147 ProKIT	
<b>KIA - OPTIMA I Sedan (GD, MS)</b>												<b>05/01→09/05</b>	
2.0	100 kW	2 l	05/01→09/05		01/02 ->							KH10123 ProKIT	
					-> 08/05							KH10133 ProKIT	
					04/05 -> 							KH30192 ProKIT	
												KH30185 ProKIT	
2.5 V6	124 kW	2.5 l	05/01→09/05		01/02 -> 09/05							KH10123 ProKIT	
					04/05 -> 12/05; 							KH30192 ProKIT	
					-> 12/05; 							KH30185 ProKIT	
<b>KIA - PICANTO I (SA)</b>												<b>04/04→09/11</b>	
1.0	45 kW	1 l	04/04→04/11		-> 12/07							KH10346 ProKIT	
					-> 12/07; 							KH30062 ProKIT	
					-> 12/07; 							KH30168 ProKIT	
1.0	46 kW	1 l	09/07→04/11									KH10346 ProKIT	
1.1	48 kW	1.1 l	04/04→09/11									KH30062 ProKIT	
1.1 CRDi	55 kW	1.1 l	10/05→04/11									KH30168 ProKIT	
<b>KIA - PRIDE (DA)</b>												<b>01/90→09/01</b>	
1.1 i	38 kW	1.1 l	01/91→10/00									KH00079 ProKIT	
												KH00082 ProKIT	
					-> 09/94							KH00100 ProKIT	
1.3	44 kW	1.3 l	01/90→10/00									KH00079 ProKIT	
												KH00082 ProKIT	
					10/94 -> 07/00							KH00100 ProKIT	
1.3	47 kW	1.3 l	10/96→05/01									KH00079 ProKIT	
												KH00082 ProKIT	
					-> 07/00							KH00100 ProKIT	
1.3	53 kW	1.3 l	01/90→09/01									KH00079 ProKIT	
												KH00082 ProKIT	
1.3 i	51 kW	1.3 l	01/90→05/97									KH00079 ProKIT	
												KH00082 ProKIT	
					10/94 ->							KH00100 ProKIT	
<b>KIA - PRIDE Estate</b>												<b>08/99→05/01</b>	
1.3	47 kW	1.3 l	08/99→05/01		-> 07/00							KH00082 ProKIT	
												KH00079 ProKIT	
					-> 07/00							KH00100 ProKIT	



**KIA - PRO CEE'D (ED) 02/08→09/12**

1.4	80 kW	1.4 l	02/08→09/12		KH10157 ProKIT
1.6	90 kW	1.6 l	02/08→09/12		
1.6	93 kW	1.6 l	02/08→09/12		
1.6 CRDi 115	85 kW	1.6 l	02/08→09/12		
1.6 CRDi 90	66 kW	1.6 l	02/08→09/12		
2.0	105 kW	2 l	02/08→09/12		
2.0 CRDi 140	103 kW	2 l	02/08→09/12		

**KIA - PRO CEE'D (JD) 03/13→07/18**

1.4 CRDi 90	66 kW	1.4 l	03/13→07/18		KH30067 ProKIT
1.4 CVVT	73 kW	1.4 l	03/13→07/15		
1.6 CRDi 128	94 kW	1.6 l	03/13→07/15		
1.6 GDI	99 kW	1.6 l	03/13→07/18		

**KIA - RIO I Hatchback / RIO I Saloon (DC, DC\_) 08/00→02/05**

1.3	55 kW	1.3 l	08/00→02/05		KH00082 ProKIT
1.3	55 kW	1.3 l	09/00→02/05		KH00073 ProKIT
1.3	60 kW	1.3 l	08/00→02/05		
1.3	60 kW	1.3 l	08/02→02/05		
1.5 16V	71 kW	1.5 l	09/02→02/05		
1.5 16V	72 kW	1.5 l	08/00→02/05		
1.5 16V	72 kW	1.5 l	09/00→02/05		

**KIA - RIO II / RIO II Saloon (JB) 03/05→12/11**

1.4 16V	71 kW	1.4 l	03/05→12/11	; 06/05 -> 12/06	KH10110 ProKIT
1.5 CRDi	81 kW	1.5 l	03/05→12/11	; 06/05 -> 12/06; ABS, ESP	KH30062 ProKIT
1.6 16V	82 kW	1.6 l	03/05→12/11	; 06/05 -> 12/06; ABS, ESP	KH30168 ProKIT
1.6 CVVT	82 kW	1.6 l	03/05→12/11	; 06/05 -> 12/06; ABS, ESP	KH30168 ProKIT

**KIA - RONDO III MPV (UN) 09/06→**

1.6 CRDi 110	85 kW	1.6 l	10/10→		KH10123 ProKIT
1.6 CRDi 128	94 kW	1.6 l	10/10→	; -> 12/12	KH30147 ProKIT
1.6 CVVT	93 kW	1.6 l	10/10→		
1.6 CVVT	97 kW	1.6 l	08/09→		KH10123 ProKIT
2.0 CRDi 115	85 kW	2 l	05/07→	; 09/09 -> 12/12	KH30147 ProKIT
2.0 CRDi 135	100 kW	2 l	08/09→		
2.0 CRDi 140	103 kW	2 l	09/06→		KH10123 ProKIT
2.0 CVVT	106 kW	2 l	09/06→	; 10/06 -> 11/07	KH30161 ProKIT
				; 09/09 -> 12/12	KH30147 ProKIT

**KIA - RONDO IV (RP) 03/13→**

1.6 GDi	99 kW	1.6 l	03/13→	; -> 02/14	KH10123 ProKIT
1.7 CRDi	85 kW	1.7 l	03/13→		
1.7 CRDi	100 kW	1.7 l	03/13→		
2.0 GDi	122 kW	2 l	03/13→		
2.0 GDi	130 kW	2 l	03/13→		

**KIA - SHUMA II Saloon (FB) 05/01→05/04**




































1.6	75 kW	1.6 l	05/01→05/04		KH10016 ProKIT
-----	-------	-------	-------------	--	----------------

**KIA - SORENTO I (JC) 08/02→12/11**

2.4	102 kW	2.4 l	08/02→06/09		KH10154 ProKIT
2.5 CRDi	103 kW	2.5 l	08/02→03/11		KH10211 ProKIT
2.5 CRDi	125 kW	2.5 l	12/06→12/11		
3.3 V6 4WD	182 kW	3.3 l	02/07→12/11		
3.5 V6 4WD	143 kW	3.5 l	08/02→12/11		
2.5 CRDi	120 kW	2.5 l	05/06→12/11		KH10154 ProKIT

**KIA - SORENTO II (XM) 11/09→12/15**

2.0 CRDi	110 kW	2 l	11/10→12/15	; -> 08/14	KH30086 ProKIT
2.0 CRDi	135 kW	2 l	11/09→12/15		
2.2 CRDi	145 kW	2.2 l	11/09→12/15	; -> 08/14	KH30195 ProKIT
2.2 CRDi	147 kW	2.2 l	11/09→12/15		
2.4 CVVT	128 kW	2.4 l	11/09→12/15		
2.4 CVVT	141 kW	2.4 l	10/12→12/15		
2.4 GDI	141 kW	2.4 l	10/12→12/15		
3.5	204 kW	3.5 l	05/13→12/15		
2.0 CRDi 4WD	110 kW	2 l	11/10→12/15	; ; -> 08/14	KH30086 ProKIT
2.2 CRDi 4WD	145 kW	2.2 l	11/09→12/15		
2.4 CVVT 4WD	128 kW	2.4 l	11/09→12/15		
2.4 CVVT 4WD	141 kW	2.4 l	10/12→12/15		
2.4 GDI 4WD	141 kW	2.4 l	10/12→12/15		
3.5 4WD	204 kW	3.5 l	05/13→12/15		

      					
<b>KIA - SOUL I (AM)</b>				<b>02/09→12/14</b>	
1.6 CRDi 115	85 kW	1.6 l	02/09→12/14	 	KH10157 ProKIT
					KH30162 ProKIT
1.6 CRDi 128	94 kW	1.6 l	02/09→12/14		KH10352 ProKIT
1.6 CVVT	93 kW	1.6 l	02/09→12/11	 	KH30162 ProKIT
1.6 CVVT	77 kW	1.6 l	02/09→12/11	 	KH30162 ProKIT
1.6 GDI	103 kW	1.6 l	06/11→12/14		
<b>KIA - SOUL II (PS)</b>				<b>02/14→</b>	
1.6 CRDi 128	94 kW	1.6 l	02/14→		KH10157 ProKIT
1.6 GDI	97 kW	1.6 l	02/14→		
<b>KIA - SPECTRA II (FB)</b>				<b>05/01→08/04</b>	
1.6	75 kW	1.6 l	05/01→08/04		KH10016 ProKIT
1.8	81 kW	1.8 l	05/01→06/04		
1.8	84 kW	1.8 l	04/03→08/04		
<b>KIA - SPORTAGE II (JE_, KM)</b>				<b>09/04→</b>	
2.0 16V 4WD	104 kW	2 l	09/04→		KH10123 ProKIT
2.0 CRDi 4WD	83 kW	2 l	09/04→		KH10201 ProKIT
2.0 CRDi 4WD	100 kW	2 l	01/06→05/10		
2.0 CRDi 4WD	103 kW	2 l	01/06→		
2.0 CRDi 4WD	110 kW	2 l	09/08→05/10		
2.7 V6 4WD	129 kW	2.7 l	09/04→		
2.0 CRDi	83 kW	2 l	02/05→		KH10123 ProKIT
2.0 CRDi	100 kW	2 l	01/06→05/10		
2.0 CRDi	103 kW	2 l	01/06→		
2.0 CRDi	110 kW	2 l	09/07→		
2.0 i 16V	104 kW	2 l	09/04→		
<b>KIA - SPORTAGE III (SL)</b>				<b>06/10→</b>	
1.6 GDI	99 kW	1.6 l	02/11→	  	KH10123 ProKIT
1.7 CRDi	85 kW	1.7 l	12/10→		KH30147 ProKIT
2.0 CRDi	100 kW	2 l	07/10→		
2.0 CVVT	120 kW	2 l	07/10→		
2.0 CRDi	135 kW	2 l	08/10→		KH30147 ProKIT
2.0 CVVT	110 kW	2 l	06/10→12/13		
2.0 CVVT	122 kW	2 l	07/10→		
2.0 GDI	122 kW	2 l	02/14→		
2.0 CRDi AWD	100 kW	2 l	07/10→	  	KH10123 ProKIT
2.0 CRDi AWD	135 kW	2 l	08/10→		KH10201 ProKIT
2.0 CVVT AWD	120 kW	2 l	07/10→		
2.0 CVVT AWD	122 kW	2 l	07/10→		KH10201 ProKIT
2.0 GDI AWD	122 kW	2 l	02/14→		
<b>KIA - SPORTAGE SUV (K00)</b>				<b>04/94→08/04</b>	
2.0	87 kW	2 l	10/00→08/03		KH00044 ProKIT
2.0 4WD	87 kW	2 l	10/00→08/03		
2.0 i 16V	94 kW	2 l	10/99→08/03		
2.0 i 16V 4WD	94 kW	2 l	04/94→08/03		
2.0 i 16V 4WD	95 kW	2 l	11/98→08/04		
2.0 i 4WD	70 kW	2 l	04/94→08/99		
2.0 TD 4WD	61 kW	2 l	10/97→08/03		
<b>KIA - VENGA (YN)</b>				<b>02/10→</b>	
1.4 CRDi 75	55 kW	1.4 l	02/10→	 	KH10157 ProKIT
					KH30162 ProKIT
1.4 CRDi 75	57 kW	1.4 l	02/10→	 	KH30162 ProKIT
1.4 CRDi 90	66 kW	1.4 l	02/10→		KH10157 ProKIT
1.4 CVVT	66 kW	1.4 l	02/10→		
1.6 CRDi 115	85 kW	1.6 l	02/10→	 	KH30162 ProKIT
1.6 CRDi 128	94 kW	1.6 l	02/10→		
1.6 CVVT	92 kW	1.6 l	02/10→		




















































**LADA - NIVA Closed Off-Road Vehicle (2121, 2131)**

**12/76→12/15**














































1600	56 kW	1.6 l	12/76→12/93		<b>KH00098 ProKIT</b>
1600 4x4	54 kW	1.6 l	01/87→03/95		
1700 i	59 kW	1.7 l	06/96→12/06		
1700 i 4x4	60 kW	1.7 l	10/00→12/15		
1900 Diesel (21215)	48 kW	1.9 l	01/93→08/99		
1900 Diesel (21215)	55 kW	1.9 l	01/99→12/06		





























































     					
<b>LANCIA - A 112</b>				<b>03/78→12/86</b>	
0.9 Junior (A112B/2)	29 kW	0.9 l	03/81→06/86		KH20091 ProKIT
1.0 LX (A112)	35 kW	1 l	03/84→12/86		
1.0 Abarth (A112B2/5)	51 kW	1 l	03/78→02/84		KH10369 ProKIT
					KH20091 ProKIT
<b>LANCIA - BETA / BETA Coupe / BETA H.P.E. / BETA Saloon / BETA Spider (828_)</b>				<b>08/73→10/86</b>	
1300 (828BC3)	62 kW	1.4 l	12/81→12/84		KH10404 ProKIT
1300 (828CB3)	61 kW	1.3 l	04/76→07/82		
1400 (828AB2)	66 kW	1.4 l	08/73→07/76		
1600 (828BC0)	74 kW	1.6 l	04/76→12/84		
1600 (828BF0)	74 kW	1.6 l	08/80→09/84		
1600 (828BS0)	74 kW	1.6 l	05/76→10/86		
1600 (828CB0, 828AB0)	74 kW	1.6 l	08/73→07/82		
1800 (828AB1)	81 kW	1.8 l	08/73→07/76		
2000 (828.BC)	88 kW	2 l	04/76→12/84		
2000 (828.BF)	85 kW	2 l	04/79→09/84		
2000 (828.BF)	88 kW	2 l	05/76→05/78		
2000 (828BC_)	85 kW	2 l	01/81→12/84		
2000 (828BS1)	85 kW	2 l	04/79→10/86		
2000 (828BS1)	88 kW	2 l	05/76→11/79		
2000 (828CB1)	85 kW	2 l	07/78→07/82		
2000 (828CB1)	88 kW	2 l	04/76→07/78		
2000 i.e. (828.BC)	90 kW	2 l	12/81→12/84		
2000 i.e. (828BF)	90 kW	2 l	05/81→09/84		
2000 Volumex (828.BF)	99 kW	2 l	07/83→09/84		
2000 VX (828.BC)	99 kW	2 l	07/83→12/84		
<b>LANCIA - DEDRA / DEDRA SW (835_)</b>				<b>04/89→07/99</b>	
1.6 (835EB)	66 kW	1.6 l	10/94→07/99	 ABS	KH20034 ProKIT
1.6 i.e. (835AN)	55 kW	1.6 l	04/93→07/99	 ABS	KH20161 ProKIT
1.6 LE Cat (835EB)	66 kW	1.6 l	07/94→07/99		
1.8 i.e. (835AT)	66 kW	1.8 l	08/93→07/99		
1.6 16V (835EI)	76 kW	1.6 l	01/96→07/99	 ; 12/97 ->	KH10181 ProKIT
				 ABS	KH20034 ProKIT
				 ABS	KH20161 ProKIT
1.6 i.e. (835AA)	66 kW	1.6 l	08/89→06/94	 ; 02/93 ->; ABS	KH20161 ProKIT
1.6 i.e. (835AB)	57 kW	1.6 l	08/89→03/93	 ; ABS	KH20034 ProKIT
1.8 16V LE (835FG)	83 kW	1.8 l	03/96→07/99		KH10181 ProKIT
1.8 GT 16V (835EH)	96 kW	1.8 l	03/96→07/99	 ; ABS	KH20034 ProKIT
1.8 i.e. (835FA)	74 kW	1.8 l	07/94→07/99	 ; ABS	KH20161 ProKIT
2.0 16V (835ED)	102 kW	2 l	07/94→07/99	 ; ABS	KH20161 ProKIT
1.8 16V LE (835FG)	83 kW	1.8 l	03/96→07/99	 ; -> 11/97	KH10181 ProKIT
				 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT
1.8 i.e. (835AC, 835BC)	80 kW	1.8 l	09/89→06/94	 ; VIN 27912 ->	KH10181 ProKIT
				 ; 02/93 ->; ABS	KH20161 ProKIT
				 ; ABS	KH20034 ProKIT
1.8 i.e. (835BD, 835AD)	77 kW	1.8 l	09/89→07/99	 ; -> 06/94; VIN 27912 ->	KH10181 ProKIT
				 ; 02/93 ->; ABS	KH20161 ProKIT
				 ; ABS	KH20034 ProKIT
1.8 i.e. (835FA)	74 kW	1.8 l	07/94→07/99	 ; 09/94 ->	KH10181 ProKIT
1.9 TDS (835EE, 835EF)	66 kW	1.9 l	07/94→07/99	 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT
1.9 TDS (835EE, 835EF)	66 kW	1.9 l	04/89→07/99	 ; VIN 27911 ->; 06/89 ->	KH10181 ProKIT
				 ; -> 05/89; VIN -> 27910	KH10371 ProKIT
				 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT
2.0 16V (835ED)	102 kW	2 l	07/94→07/99	 ; 09/94 -> 12/96	KH10181 ProKIT
				 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT
2.0 HF Integrale (835AP)	124 kW	2 l	11/90→07/94	 ;  ; 10/92 -> 06/94	KH10181 ProKIT
2.0 i.e. (835AI)	86 kW	2 l	09/89→07/92	 ; VIN 27912 ->	KH10181 ProKIT
2.0 i.e. (835AL)	83 kW	2 l	09/89→07/99	 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT
2.0 i.e. Turbo (835AR)	119 kW	2 l	04/91→07/99	 ; -> 06/94	KH10181 ProKIT
				 ; ABS	KH20034 ProKIT
				 ; ABS	KH20161 ProKIT






























     				
<b>LANCIA - DEDRA / DEDRA SW (835_)</b>				<b>04/89→07/99</b>
2.0 i.e. Turbo Integrale (835AO)	121 kW	2 l	04/90→08/91	 KH10181 ProKIT  KH10371 ProKIT
2.0 Integrale (835ED)	102 kW	2 l	07/94→07/99	 ; 09/94 -> 12/96 KH10181 ProKIT  KH10371 ProKIT
2.0 Turbo (835AQ)	130 kW	2 l	11/90→06/94	 ; 12/90 -> KH10181 ProKIT  ; ABS KH20034 ProKIT  ; ABS KH20161 ProKIT
<b>LANCIA - DELTA I (831_)</b>				<b>09/79→01/94</b>
1.1 (831AB.015)	47 kW	1.1 l	01/86→12/90	 KH20091 ProKIT
1.3 (831AB.011)	55 kW	1.3 l	09/79→08/92	
1.5 (831AB.025)	63 kW	1.5 l	09/79→12/92	
1.6 GT (831AB.06)	77 kW	1.6 l	11/82→04/86	
1.6 GT i.e. (831AB.010)	66 kW	1.6 l	05/87→08/92	
1.6 GT i.e. (831AB.016)	80 kW	1.6 l	08/86→08/88	
1.6 HF Turbo (831AB.0)	96 kW	1.6 l	10/83→12/86	
1.6 HF Turbo (831AB.020)	103 kW	1.6 l	08/86→08/88	
1.6 HF Turbo (831AB.020S)	97 kW	1.6 l	04/87→03/89	
1.9 Turbo DS (831AB.021)	59 kW	1.9 l	10/86→12/89	
2.0 16V HF Evo Integrale (831AB.027)	155 kW	2 l	06/93→01/94	 ; VIN 412353 -> KH10371 ProKIT 
2.0 16V HF Integrale (831AB.026)	144 kW	2 l	03/89→09/91	 ; 04/89 -> KH10181 ProKIT  ; VIN 412353 -> KH10371 ProKIT
2.0 HF Integrale (831AB.019)	122 kW	2 l	11/86→08/88	 ; 01/88 ->; VIN 412353 -> KH10371 ProKIT
2.0 HF Integrale (831AB.024)	133 kW	2 l	10/87→12/91	 ; 01/88 ->; VIN 412353 -> KH10371 ProKIT  ; VIN -> 4122353 KH10181 ProKIT
2.0 HF Integrale (831AB.024S, 831AB.028)	130 kW	2 l	12/86→12/92	 ; 01/88 ->; VIN 412353 -> KH10371 ProKIT  ; 08/88 -> 12/89 KH10181 ProKIT
<b>LANCIA - DELTA II (836_)</b>				<b>06/93→08/99</b>
1.4 i.e. (836AF, 836AH)	51 kW	1.4 l	10/94→08/99	 ; ABS KH10044 ProKIT
1.6 i.e. (836AD)	55 kW	1.6 l	06/93→08/99	 ; ABS KH20034 ProKIT
1.6 i.e. (836AP)	66 kW	1.6 l	03/96→08/99	 ; ABS KH20161 ProKIT
1.6 i.e. 16V (836AO)	76 kW	1.6 l	01/96→08/99	 ; ABS KH20161 ProKIT
1.8 i.e. (836AE)	76 kW	1.8 l	06/93→08/99	 ; -> 12/94 KH10181 ProKIT  ; ABS KH20034 ProKIT  ; ABS KH20161 ProKIT
1.8 i.e. (836AG, 836AL)	66 kW	1.8 l	07/94→08/99	 KH10181 ProKIT
1.8 i.e. 16V (836AQ)	83 kW	1.8 l	03/96→08/99	 ; ABS KH20034 ProKIT
1.9 TD (836AM, 836AN)	66 kW	1.9 l	10/94→08/99	 ; ABS KH20161 ProKIT
2.0 16V (836AA, 836CA)	102 kW	2 l	06/93→08/99	 ; ABS KH20161 ProKIT
1.8 i.e. 16V GT (836AR)	96 kW	1.8 l	03/96→08/99	 ; 05/96 -> KH10181 ProKIT  ; ABS KH20034 ProKIT  ; ABS KH20161 ProKIT
2.0 16V Turbo (836AB)	137 kW	2 l	06/93→08/99	 KH10190 ProKIT
2.0 16V Turbo (836AS)	142 kW	2 l	07/96→08/99	 ; ABS KH20034 ProKIT  ; ABS KH20161 ProKIT
<b>LANCIA - DELTA III (844_)</b>				<b>08/08→08/14</b>
1.4 (844.AXA1A)	88 kW	1.4 l	09/08→08/14	 ; -> 11/10 KH10151 ProKIT
1.4 (844.AXB1A)	110 kW	1.4 l	09/08→08/14	 KH20022 ProKIT
1.4 16V (844.AXL1A)	103 kW	1.4 l	07/10→08/14	
1.6 D Multijet (844.AXC11, 844.AXC1A)	88 kW	1.6 l	09/08→08/14	
1.4 Bifuel (844.AXA1A)	88 kW	1.4 l	07/11→08/14	 KH20022 ProKIT
1.6 D Multijet (844.AXF11, 844.AXF1A)	85 kW	1.6 l	08/08→08/14	
1.6 D Multijet (844.AXP1A)	77 kW	1.6 l	04/11→08/14	
1.8 (844.AXH12)	147 kW	1.8 l	01/09→08/14	 KH10198 ProKIT
1.9 D Multijet (844.AXE1A)	140 kW	1.9 l	01/09→08/14	 KH20022 ProKIT
2.0 D Multijet (844.AXD1A, 844.AXM1A)	121 kW	2 l	09/08→08/14	
2.0 D Multijet (844.AXG1A, 844.AXN1A)	120 kW	2 l	09/08→08/14	






					LANCIA - KAPPA / KAPPA Coupe / KAPPA SW (838_) 08/94→10/01	
2.0 16V Turbo (838AB1AA)	151 kW	2 l	02/95→10/01		04/98 →; VIN 2084919 →	KH10385 ProKIT
2.0 16V Turbo (838BB1AA)	151 kW	2 l	07/96→10/01		→ 04/98; VIN → 2084918	KH10190 ProKIT
2.0 20V (838AA1AA)	107 kW	2 l	10/94→10/01			
2.0 20V (838AG1AA, 838AG11A)	114 kW	2 l	07/96→10/01			
2.0 20V (838BG1AA)	114 kW	2 l	07/96→10/01			
2.4 20V (838AC1AA, 838AC11A)	129 kW	2.4 l	08/94→10/01			
2.4 20V (838BC1AA, 838BC11A)	129 kW	2.4 l	07/96→10/01			
2.4 T.DS (838AE1AA, 838AH1AA)	91 kW	2.4 l	08/94→10/01			
2.4 T.DS (838BH1AA)	91 kW	2.4 l	07/96→10/01			
2.0 16V Turbo (838CB)	151 kW	2 l	11/96→03/01		05/98 →; VIN 1002101 →	KH10385 ProKIT
2.4 20V (838CC)	129 kW	2.4 l	11/96→03/01		→ 05/98; VIN → 1002100	KH10190 ProKIT
3.0 24V (838CD, 838CD11A)	150 kW	3 l	09/96→03/01			
2.0 20V Turbo (838AM1AA)	162 kW	2 l	06/98→10/01			KH10385 ProKIT
2.0 20V Turbo (838BM1AA)	162 kW	2 l	06/98→10/01			
2.0 20V Turbo (838CM)	162 kW	2 l	06/98→03/01			
2.4 JTD (838AL1AA)	100 kW	2.4 l	06/98→10/01			
2.4 JTD (838BL1AA)	100 kW	2.4 l	06/98→10/01			
3.0 24V (838AD1AA, 838AD11A, 838XD1AA, 838ZD1AA)	150 kW	3 l	10/94→10/01		04/98 →; VIN 2084919 →;	KH10385 ProKIT
3.0 24V (838BD11A)	150 kW	3 l	07/96→10/01		→ 04/98; VIN → 2084918;	KH10190 ProKIT
LANCIA - LYBRA / LYBRA SW (839_) 07/99→10/05						
1.6	76 kW	1.6 l	10/00→10/05			KH10065 ProKIT
1.6 (839.BXF1A)	76 kW	1.6 l	10/00→10/05			KH20022 ProKIT
1.6 16V (839AXA1A)	76 kW	1.6 l	07/99→10/05		not for trim level: armored	KH20022 ProKIT
1.6 16V (839BXA1A)	76 kW	1.6 l	07/99→10/05			
1.8 16V (839AXB1A, 839AXG1A)	96 kW	1.8 l	07/99→10/05			
1.8 16V (839BXB1A, 839BXG1A)	96 kW	1.8 l	07/99→10/05			
1.9 JTD (839.AXI1A, 839.AXN1A, 839.CXL1A)	85 kW	1.9 l	05/01→10/05			KH10385 ProKIT
1.9 JTD (839.BXI1A, 839.BXN1A, 839.CXL1A)	85 kW	1.9 l	05/01→10/05		not for trim level: armored	KH20022 ProKIT
1.9 JTD (839AXD1A)	77 kW	1.9 l	07/99→09/00			
1.9 JTD (839AXI1A)	81 kW	1.9 l	09/00→05/01			
1.9 JTD (839BXD1A)	77 kW	1.9 l	07/99→09/01			
1.9 JTD (839BXI1A)	81 kW	1.9 l	09/00→05/01			
2.0 20V (839AXC11, 839AXC1A)	113 kW	2 l	07/99→09/00			
2.0 20V (839AXH1A)	110 kW	2 l	09/00→10/05			
2.0 20V (839BXC11, 839BXC1A)	113 kW	2 l	07/99→09/00			
2.0 20V (839BXH1A)	110 kW	2 l	09/00→10/05			
2.4 JTD (839.AXE1A)	110 kW	2.4 l	05/02→10/05			
2.4 JTD (839.BXE1A)	110 kW	2.4 l	05/02→10/05			
2.4 JTD (839AXE1A)	99 kW	2.4 l	07/99→02/01			
2.4 JTD (839AXL1A)	103 kW	2.4 l	09/00→05/02			
2.4 JTD (839BXE1A)	99 kW	2.4 l	10/99→09/00			
2.4 JTD (839BXL1A)	103 kW	2.4 l	09/00→10/05			
2.4 20V (839.CXM1A)	125 kW	2.4 l	10/01→10/05		not for trim level: armored	KH20022 ProKIT
LANCIA - MUSA (350_) 10/04→09/12						
1.3 D Multijet (350.AXB11, 350.AXB1A)	51 kW	1.3 l	10/04→09/12			KH10065 ProKIT
1.3 D Multijet (350.AXG11, 350.AXG1A)	66 kW	1.3 l	09/06→09/12			KH20022 ProKIT
1.3 D Multijet (350.AXM11, 350.AXM1A, 350.AXI1A)	70 kW	1.3 l	03/09→09/12			
1.6 D Multijet (350.AXH1A)	88 kW	1.6 l	07/08→09/12			
1.6 D Multijet (350.AXL1A, 350.AXH1A)	85 kW	1.6 l	07/08→09/12			
1.4 (350.AXA11, 350.AXA1A)	70 kW	1.4 l	10/04→09/12		ABS	KH10043 ProKIT
1.4 (350.AXE1A)	66 kW	1.4 l	10/07→09/12			KH20022 ProKIT
1.4 (350.AXF1A)	57 kW	1.4 l	09/05→09/12			
1.4 LPG (350.AXF1A)	57 kW	1.4 l	11/10→09/12			
1.9 D Multijet (350.AXC1A)	74 kW	1.9 l	10/04→09/12			KH20022 ProKIT
LANCIA - PHEDRA (179_) 09/02→11/10						
2.0 (179AXA11, 179AXA1A)	100 kW	2 l	09/02→11/10		→ 12/07; VIN → 10814	KH10132 ProKIT
2.0 D Multijet (179.AXL1B, 179.BXL1B)	100 kW	2 l	07/06→11/10		→ 05/10	KH20055 ProKIT
2.0 JTD (179.AXE1A)	79 kW	2 l	07/03→11/10			
2.0 JTD (179.AXH1B, 179.BXH1B)	88 kW	2 l	06/06→11/10			
2.0 JTD (179AXB1A)	80 kW	2 l	09/02→11/10			
2.2 JTD (179AXC1A)	94 kW	2.2 l	09/02→11/10			
2.2 D Multijet (179.AXM1B, 179.AXP11, 179.BXM1B,...)	125 kW	2.2 l	03/08→11/10		→ 05/10	KH20055 ProKIT
3.0 V6 (179.BXD11)	150 kW	3 l	09/02→11/10			



				     	
<b>LANCIA - PRISMA (831_)</b>				<b>01/83→02/92</b>	
1.5 (831AB)	55 kW	1.5 l	09/85→02/92		KH20091 ProKIT
1.5 (831AB)	59 kW	1.5 l	05/86→07/89		
1.5 (831AB)	63 kW	1.5 l	01/83→04/86		
1.6 (831AB)	73 kW	1.6 l	08/86→02/92		
1.6 (831AB)	77 kW	1.6 l	01/83→04/86		
1.6 i.e. (831AB)	80 kW	1.6 l	05/86→12/89		
1.6 i.e. Super (831AB)	66 kW	1.6 l	05/87→12/89		
1.9 Diesel (831AB)	48 kW	1.9 l	01/83→02/92		
1.9 Turbo Diesel (831AB)	59 kW	1.9 l	05/85→12/89		
2.0 i.e. All-wheel Drive (831AB)	85 kW	2 l	04/86→12/89	 ; 01/88 ->; VIN 412353 ->	KH10371 ProKIT
<b>LANCIA - SCORPION (137_)</b>				<b>09/75→05/81</b>	
2.0 (137AS_)	88 kW	2 l	09/75→05/81	 	KH10404 ProKIT
<b>LANCIA - THEMA / THEMA SW (834_)</b>				<b>11/84→07/94</b>	
2000 16V (834FA)	112 kW	2 l	05/92→07/94	 ; -> 12/92; VIN -> 300636	KH10371 ProKIT
2000 16V (834FA)	112 kW	2 l	08/92→12/93	 ; VIN 300637 ->	KH10190 ProKIT
2000 16V Turbo (834AC)	133 kW	2 l	12/88→06/90		KH10371 ProKIT
2000 i.e. (834AB)	83 kW	2 l	03/86→09/88		
2000 i.e. (834B)	88 kW	2 l	11/84→09/88		
2000 i.e. 16V Turbo (834AC)	133 kW	2 l	12/88→06/90		
2000 i.e. Turbo (834C)	122 kW	2 l	11/84→12/89		
2000 i.e. Turbo (834CV)	110 kW	2 l	07/86→05/90		
2500 Turbo D (834D)	74 kW	2.4 l	11/84→09/88		
2500 Turbo DS (834AE)	85 kW	2.5 l	06/88→05/92		
2500 Turbo DS (834AM)	77 kW	2.5 l	05/88→07/92		
2500 Turbo DS (834D)	74 kW	2.4 l	03/87→09/90		
2850 V6 i.e. (834AD, 834CD, 834BD)	108 kW	2.8 l	06/88→05/92		
2850 V6 i.e. (834F)	110 kW	2.8 l	11/84→09/88		
2000 16V Turbo (834GC, 834FC)	148 kW	2 l	10/92→07/94	 ; -> 12/92; VIN -> 303313	KH10371 ProKIT
2000 Turbo 16V (834GC, 834FC)	148 kW	2 l	11/92→07/94	 ; VIN 303314 ->	KH10190 ProKIT
2000 i.e. (834BV)	85 kW	2 l	09/87→05/92	 ; 01/92 ->; VIN 303504 ->	KH10190 ProKIT
2000 i.e. (834AB)	86 kW	2 l	09/88→05/92	 ; VIN -> 303503	KH10371 ProKIT
2000 i.e. 16V (834AA)	108 kW	2 l	05/88→08/92	 ; 01/92 ->; VIN 300637 ->	KH10190 ProKIT
2000 i.e. 16V (834AA)	108 kW	2 l	05/89→08/92	 ; VIN -> 300636	KH10371 ProKIT
2000 i.e. 16V (834AI)	104 kW	2 l	02/89→05/92		
2000 i.e. 16V Turbo (834AL)	130 kW	2 l	04/89→05/92	 ; 01/92 ->; VIN 303314 ->	KH10190 ProKIT
2000 Turbo (834.FA, 834.BV, 834.CV)	110 kW	2 l	12/88→03/92	 ; VIN -> 303313	KH10371 ProKIT
2000 i.e. 16V Turbo (834AL)	130 kW	2 l	04/89→03/93	 ; 01/92 ->; VIN 303314 ->	KH10190 ProKIT
				 ; -> 12/92; VIN -> 303313	KH10371 ProKIT
2500 Turbo DS (834FE, 834LE)	85 kW	2.5 l	05/92→07/94	 ; -> 08/92	KH10371 ProKIT
3000 V6 (834GD, 834FD)	126 kW	3 l	08/92→07/94		KH10190 ProKIT
3000 V6 (834GD, 834FD)	126 kW	3 l	09/92→07/94		
<b>LANCIA - THESIS (841_)</b>				<b>07/02→07/09</b>	
2.0 Turbo (841AXA1B03)	136 kW	2 l	07/02→07/09	 ; 09/02 ->; 	KH20068 ProKIT
2.4 (841AXB1B00)	125 kW	2.4 l	07/02→07/09		
2.4 JTD (841AXD1B02)	110 kW	2.4 l	07/02→07/09		
2.4 D Multijet (841.AXN111, 841.AXH110)	136 kW	2.4 l	04/06→07/09	 ; 	KH20068 ProKIT
2.4 JTD (841.AXE1B0, 841.AXH110)	129 kW	2.4 l	05/03→07/09	 ; 09/03 ->; 	KH20068 ProKIT
3.0 V6 (841AXC1101)	158 kW	3 l	07/02→07/09	 ; 09/02 -> 03/05; 	KH20068 ProKIT
<b>LANCIA - Y (840_)</b>				<b>11/95→09/03</b>	
1.1 (840AE)	40 kW	1.1 l	11/95→09/03	 ; Code: SU; VIN -> 3336901; AT; 	KH10044 ProKIT
				 ; Code: TA; 	KH10043 ProKIT
				 ; 	KH20034 ProKIT
				 ; VIN -> 3336901; 	KH20047 ProKIT
				 ; VIN 3336903 ->; 	KH20022 ProKIT
1.2 (840AA, 840AF1A)	44 kW	1.2 l	03/96→09/03	 ; Code: SU; VIN -> 3336901; AT; 	KH10044 ProKIT
1.2 16V (840AD)	63 kW	1.2 l	04/97→09/03	 ; Code: TA; 	
1.2 16V (840AG1A)	59 kW	1.2 l	10/00→09/03	 ; VIN 3336902 ->;  ; AT	KH10043 ProKIT
1.4 12V (840AB)	59 kW	1.4 l	10/96→09/03	 ; 	KH20034 ProKIT
1.4 12V (840AC)	55 kW	1.4 l	03/96→09/03	 ; VIN -> 3336901; 	KH20047 ProKIT
				 ; VIN 3336903 ->; 	KH20022 ProKIT

									
<b>LANCIA - Y10 (156_)</b>				<b>03/85→12/95</b>					
1.0 (156C)	41 kW	1 l	03/85→07/89		KH30113 ProKIT				
1.0 Fire (156AA)	33 kW	1 l	03/85→06/89		KH20091 ProKIT				
1.0 Fire (156B, 156AD)	32 kW	1 l	06/85→06/91						
1.0 Fire Catalytic-Conv (156AE)	33 kW	1 l	10/87→02/92						
1.0 Turbo (156D)	62 kW	1 l	03/85→02/89						
1.1 Fire (156AG)	40 kW	1.1 l	01/95→12/95						
1.1 i.e. Fire (156AG)	37 kW	1.1 l	07/89→09/95						
1.1 i.e. Fire (156AC)	42 kW	1.1 l	08/89→06/92						
1.3 i.e. (156AF)	53 kW	1.3 l	02/89→12/95						
1.0 Fire All-wheel Drive (156.AD)	32 kW	1 l	12/86→02/89		KH30113 ProKIT				
1.1 Fire All-wheel Drive (156AG)	40 kW	1.1 l	01/95→12/95						
1.1 i.e. Fire All-wheel Drive (156AG)	37 kW	1.1 l	09/92→12/95						
1.1 i.e. Fire All-wheel Drive (156AC)	42 kW	1.1 l	08/89→06/92						
1.3 i.e. (156AB)	56 kW	1.3 l	11/87→05/93						
<b>LANCIA - YPSILON (312_)</b>				<b>05/11→</b>					
0.9 CNG (312.YXG1A)	63 kW	0.9 l	05/11→		KH10065 ProKIT				
0.9 TwinAir (312.PXG11, 312.PXG1A, 312.YXG11, 312.YXG1A)	63 kW	0.9 l	05/11→						
0.9 TwinAir (312.YXN11, 312.YXN1A)	59 kW	0.9 l	12/13→						
1.3 D Multijet (312.YXE1A, 312.YXU1A)	70 kW	1.3 l	05/11→						
<b>LANCIA - YPSILON (843_)</b>				<b>10/03→12/11</b>					
1.2 (843.AXA1A)	44 kW	1.2 l	10/03→12/11			KH10043 ProKIT			
1.2 (843.AXB1A)	59 kW	1.2 l	10/03→12/11		KH20022 ProKIT				
1.2 (843.AXL1A)	51 kW	1.2 l	08/10→12/11						
1.4 (843.AXG1A)	57 kW	1.4 l	02/06→12/11						
1.4 16V (843.AXC11, 843.AXC1B, 843.AXC1A)	70 kW	1.4 l	10/03→12/11						
1.3 D Multijet (843.AXE11, 843.AXE1A)	66 kW	1.3 l	09/06→12/11		KH10065 ProKIT				
1.3 D Multijet (843.AXF11, 843.AXF1A, 843.AXM11,...)	55 kW	1.3 l	09/06→12/11		KH20022 ProKIT				
1.3 D Multijet (843.AXH1A, 843.AXE1A)	77 kW	1.3 l	05/07→12/11						
1.3 JTD (843.AXD11, 843.AXD1A)	51 kW	1.3 l	10/03→12/11						
1.4 LPG (843.AXG1A)	57 kW	1.4 l	11/10→12/11		Code: 1M;		KH10043 ProKIT		
					KH20022 ProKIT				
<b>LANCIA - ZETA (22_)</b>				<b>05/95→09/02</b>					
2.0 16V (220AL5)	97 kW	2 l	05/98→07/00		KH10089 ProKIT				
					07/98 ->	KH20095 ProKIT			
2.0 16V (220AQ5, 220AQ4)	100 kW	2 l	07/00→09/02		KH10089 ProKIT				
					01/01 -> 08/02	KH20095 ProKIT			
2.0 JTD (220.AR5, 220.AN5)	80 kW	2 l	09/99→09/02		KH10089 ProKIT				
2.0 Turbo (220AD5, 220CD5)	108 kW	2 l	05/95→09/02		KH10089 ProKIT				
					-> 05/00	KH20095 ProKIT			
2.1 TD (220AJ5)	80 kW	2.1 l	05/96→09/99		KH10089 ProKIT				
					KH20095 ProKIT				



				    	
LAND ROVER - 90 I (LDV)				09/85→08/90	
2.5 4x4	62 kW	2.5 l	09/85→08/90	; -> 12/85; Code: 110; Left-/right-hand drive vehicles: LHD; Axle number from: 21L10632B → ; -> 12/85; Code: 110; Left-/right-hand drive vehicles: RHD; Axle number from: 20L13359B → ; 01/86 ->; Code: 110 ; 01/88 -> 12/88; Code: 90; Left-/right-hand drive vehicles: RHD; Axle number from: 22L06072B → ; 01/89 ->; Code: 90	KH00037 ProKIT
				; Code: 110; -> 12/85; Axle number from: 21S22955B → ; Code: 110; 01/86 -> ; Code: 90; 01/88 -> 12/88; Axle number from: 22S08284B → ; Code: 90; 01/89 ->	KH00136 ProKIT
				; ; Axle number from: 20L13359B → ; ; Axle number from: 21L10632B → ; ; Axle number from: 21S22955B →	KH00106 ProKIT
LAND ROVER - 110/127 (LDH)				09/83→07/90	
2.5 TD 4x4	63 kW	2.5 l	09/86→07/90	; Code: 110 ; Code: 90; 01/88 -> 12/88; Axle number from: 22S08284B → ; Code: 90; 01/89 ->	KH00136 ProKIT
				; ; Axle number from: 20L13359B → ; ; Axle number from: 21L10632B → ; ; Axle number from: 21S22955B →	KH00106 ProKIT
				; Code: 110	KH00037 ProKIT
3.5 4x4	98 kW	3.5 l	09/83→07/90	; 01/85 -> 12/85; Code: 110; Left-/right-hand drive vehicles: RHD; Axle number from: 22L13359B → ; 01/85 -> 12/85; Code: 110; Left-/right-hand drive vehicles: LHD; Axle number from: 21L10632B → ; 01/86 ->; Code: 110 ; 01/88 -> 12/88; Code: 90; Left-/right-hand drive vehicles: RHD; Axle number from: 22L06072B → ; 01/88 -> 12/88; Code: 90; Left-/right-hand drive vehicles: LHD; Axle number from: 23L03667B → ; 01/89 ->; Code: 90	KH00037 ProKIT
				; Code: 110; 01/85 -> 12/85; Axle number from: 21S22955B → ; Code: 110; 01/86 -> ; Code: 90; 01/88 -> 12/88; Axle number from: 22S08284B → ; Code: 90; 01/89 ->	KH00136 ProKIT
				; ; Axle number from: 20L13359B → ; ; Axle number from: 21L10632B → ; ; Axle number from: 21S22955B →	KH00106 ProKIT
LAND ROVER - DEFENDER Cabrio / DEFENDER Pick Up / DEFENDER Station Wagon (L316)				08/90→02/16	
2.4 Td4 4x4 (L316)	90 kW	2.4 l	10/06→02/16	;	KH00106 ProKIT
2.4 Td4 4x4 (L317)	90 kW	2.4 l	05/07→02/16		
2.5 D 4x4 (L316)	51 kW	2.5 l	09/90→07/94		
2.5 Td5 4x4 (L316)	90 kW	2.5 l	06/98→02/16	; ; -> 12/06	KH00037 ProKIT
3.9 V8 4x4 (L316)	136 kW	3.9 l	11/98→02/16	;	KH00106 ProKIT
2.5 TDI 4x4 (L316)	83 kW	2.5 l	08/90→11/98	; -> 12/92 ; 01/93 -> 12/93; VIN -> KA 930455 ; 01/93 -> 12/93; VIN LA930456 -> 01/94 ->	KH00136 ProKIT
				;	KH00037 ProKIT
				;	KH00106 ProKIT
2.5 TDI 4x4 (L316)	83 kW	2.5 l	08/90→12/98	; -> 12/92 ; 01/93 -> 12/93; VIN -> KA 930455 ; 01/93 -> 12/93; VIN LA930456 -> 01/94 ->	KH00136 ProKIT
				;	KH00037 ProKIT
				;	KH00106 ProKIT

<b>LAND ROVER - DISCOVERY I (LJ)</b>								<b>06/89→10/98</b>			
2.0 16 V 4x4	99 kW	2 l	06/89→10/98							KH00037 ProKIT	
4.0 4x4	134 kW	4 l	09/93→10/98					VIN JA032851 ->		KH00106 ProKIT	
2.5 TDI 4x4	83 kW	2.5 l	10/89→10/98					01/92 -> 12/92; VIN JA032851 ->		KH00037 ProKIT	
3.5 4x4 (SALLJG)	113 kW	3.5 l	06/89→06/94					01/93 ->			
								-> 12/92; VIN -> JA032850		KH00136 ProKIT	
								VIN JA032851 ->		KH00106 ProKIT	
<b>LAND ROVER - DISCOVERY III / DISCOVERY IV (L319)</b>								<b>07/04→12/18</b>			
2.7 TD 4x4	140 kW	2.7 l	07/04→09/09							KH30085 ProKIT	
2.7 TD 4x4	140 kW	2.7 l	09/09→12/18							KH10159 ProKIT	
3.0 SDV6 4x4	188 kW	3 l	11/09→12/18								
3.0 TD 4x4	155 kW	3 l	05/10→12/18								
3.0 TD 4x4	180 kW	3 l	09/09→12/18								
3.0 TD 4x4	183 kW	3 l	07/12→12/18								
3.0 TD 4x4	200 kW	3 l	09/09→12/18								
4.0 4x4	160 kW	4 l	02/05→09/09								
4.0 4x4	160 kW	4 l	09/09→12/18								
4.0 V6 4x4	160 kW	4 l	10/04→09/09								
4.4 4x4	220 kW	4.4 l	07/04→09/09								
5.0 V8 4x4	276 kW	5 l	09/09→12/18								
<b>LAND ROVER - FREELANDER I / FREELANDER I Soft Top (L314)</b>								<b>02/98→10/06</b>			
1.8 16V 4x4	86 kW	1.8 l	04/98→10/06					VIN -> 1A999999		KH10130 ProKIT	
1.8 i 16V 4x4	88 kW	1.8 l	02/98→11/00					VIN 2A000001 ->		KH10148 ProKIT	
1.8 i 16V 4x4	88 kW	1.8 l	02/98→10/06								
2.0 DI 4x4	72 kW	2 l	02/98→11/00								
2.0 DI 4x4	72 kW	2 l	02/98→10/06								
2.0 Td4 4x4	80 kW	2 l	03/01→10/06								
2.0 Td4 4x4	82 kW	2 l	11/00→10/06								
2.5 V6 4x4	130 kW	2.5 l	11/00→10/06								
<b>LAND ROVER - FREELANDER 2 (L359)</b>								<b>10/06→10/14</b>			
2.0 Si4 4x4	177 kW	2 l	10/11→10/14							KH20045 ProKIT	
2.2 eD4	110 kW	2.2 l	08/10→10/14							KH10148 ProKIT	
2.2 SD4 4x4	140 kW	2.2 l	08/10→10/14								
2.2 TD4 4x4	110 kW	2.2 l	10/06→10/14								
2.2 TD4 4x4	112 kW	2.2 l	01/07→10/14								
2.2 TD4 4x4	115 kW	2.2 l	10/06→10/14								
2.2 TD4 4x4	118 kW	2.2 l	10/06→10/14								
3.2 4x4	171 kW	3.2 l	10/06→10/14								
<b>LAND ROVER - RANGE ROVER I</b>								<b>08/81→07/94</b>			
2.4 TD 4x4	78 kW	2.4 l	04/86→12/90					01/90 ->; ABS		KH00106 ProKIT	
3.9 Vogue SEI 4x4	134 kW	3.9 l	11/88→07/94					ABS		KH00037 ProKIT	
								ABS		KH00136 ProKIT	
2.4 TD 4x4	83 kW	2.4 l	04/86→07/94					01/90 ->; ABS		KH00106 ProKIT	
2.5 TD 4x4	89 kW	2.5 l	10/89→11/92					-> 12/91; ABS		KH00136 ProKIT	
								01/92 ->; VIN -> JA624516; ABS			
								01/90 ->; ABS		KH00106 ProKIT	
								ABS		KH00037 ProKIT	
3.5 4x4	107 kW	3.5 l	01/87→09/90					01/90 ->; ABS		KH00106 ProKIT	
3.5 Vogue 4x4	93 kW	3.5 l	08/81→09/90					ABS		KH00037 ProKIT	
3.5 Vogue 4x4	120 kW	3.5 l	10/85→09/90								
3.9 Cat 4x4	127 kW	3.9 l	11/88→07/94					01/90 ->; ABS		KH00106 ProKIT	
								01/92 -> 12/92; VIN -> JA624516; ABS		KH00136 ProKIT	
								ABS		KH00037 ProKIT	
4.3 Vogue LSE 4x4	149 kW	4.3 l	09/92→07/94					-> 12/92; VIN -> JA624516; ABS		KH00136 ProKIT	
								ABS		KH00037 ProKIT	
								ABS		KH00106 ProKIT	
<b>LAND ROVER - RANGE ROVER II (P38A)</b>								<b>07/94→03/02</b>			
2.5 D 4x4	100 kW	2.5 l	07/94→03/02							KH00106 ProKIT	
3.9 4x4	140 kW	3.9 l	07/94→03/02							KH10231 ProKIT	
4.0 4x4	136 kW	4 l	01/95→03/02								
4.6 4x4	160 kW	4.6 l	06/98→03/02							KH10351 ProKIT	
4.6 4x4	165 kW	4.6 l	07/94→03/02								
<b>LAND ROVER - RANGE ROVER III (L322)</b>								<b>03/02→08/12</b>			
3.0 D 4x4	130 kW	3 l	03/02→08/12							KH10160 ProKIT	
3.6 D 4x4	200 kW	3.6 l	04/06→08/12					01/07 ->		KH10160 ProKIT	
4.2 4x4	291 kW	4.2 l	05/05→08/12					06/05 ->		KH10160 ProKIT	
4.4 4x4	225 kW	4.4 l	05/05→08/12								



**LAND ROVER - RANGE ROVER III (L322)**

03/02→08/12

4.4 4x4	210 kW	4.4 l	03/02→08/05	-> 05/05	KH10160 ProKIT
---------	--------	-------	-------------	----------	----------------

**LAND ROVER - RANGE ROVER IV (L405)**

08/12→

3.0 SCV6 4x4	250 kW	3 l	10/13→		KH10355 ProKIT
3.0 SCV6 4x4	280 kW	3 l	06/15→		
3.0 SDV6 4x4	183 kW	3 l	08/12→		
3.0 SDV6 Hybrid 4x4	225 kW	3 l	06/15→		
3.0 SDV6 Hybrid 4x4	250 kW	3 l	10/13→		
3.0 TDV6 4x4	155 kW	3 l	10/13→		
3.0 TDV6 4x4	190 kW	3 l	08/12→		
4.4 SDV8 4x4	250 kW	4.4 l	08/12→		
5.0 SCV8 4x4	375 kW	5 l	08/12→		
5.0 SCV8 4x4	405 kW	5 l	06/15→		
5.0 V8 4x4	276 kW	5 l	12/13→		

**LAND ROVER - RANGE ROVER EVOQUE (L538)**

06/11→12/19

2.0 4x4	177 kW	2 l	06/11→12/19		KH10355 ProKIT
2.2 D	110 kW	2.2 l	06/11→12/19		KH10233 ProKIT
2.2 D 4x4	110 kW	2.2 l	06/11→12/19		
2.2 D 4x4	140 kW	2.2 l	06/11→12/19		

**LAND ROVER - RANGE ROVER SPORT I (L320)**

02/05→03/13











2.7 D 4x4	140 kW	2.7 l	02/05→03/13		KH30085 ProKIT
3.0 D 4x4	155 kW	3 l	05/10→03/13		KH10159 ProKIT
3.0 D 4x4	180 kW	3 l	09/09→03/13		
3.0 D 4x4	188 kW	3 l	06/11→03/13		
3.6 D 4x4	200 kW	3.6 l	04/06→03/13		
4.2 4x4	287 kW	4.2 l	02/05→03/13		
4.4 4x4	220 kW	4.4 l	02/05→03/13		
5.0 4x4	276 kW	5 l	07/09→03/13		
5.0 4x4	372 kW	5 l	04/09→03/13		
5.0 4x4	375 kW	5 l	09/09→03/13		

**LAND ROVER - RANGE ROVER SPORT II (L494)**










































04/13→
















3.0 SCV6 4x4	250 kW	3 l	04/13→12/19		KH10355 ProKIT
3.0 SCV6 4x4	280 kW	3 l	06/15→12/18		
3.0 SDV6 4x4	183 kW	3 l	04/13→		
3.0 SDV6 4x4	215 kW	3 l	04/13→12/16		
3.0 SDV6 4x4	225 kW	3 l	09/14→		
3.0 SDV6 Hybrid 4x4	225 kW	3 l	06/15→12/17		
3.0 SDV6 Hybrid 4x4	250 kW	3 l	10/13→		
3.0 TDV6 4x4	155 kW	3 l	04/13→12/18		
3.0 TDV6 4x4	190 kW	3 l	04/13→		
4.4 SDV8 4x4	250 kW	4.4 l	10/13→		
5.0 SCV8 4x4	375 kW	5 l	04/13→12/18		
5.0 SCV8 4x4	405 kW	5 l	01/14→12/18		

















     					
<b>LDV - 400 Bus / 400 Platform/Chassis</b>					<b>11/95→10/98</b>
2.5 TD	71 kW	2.5 l	11/95→10/96	 ; -> 04/96	<b>KH00060</b> ProKIT
2.5 TD	71 kW	2.5 l	11/95→10/98	 ; -> 04/96	<b>KH00130</b> ProKIT
<b>LDV - CUB</b>					<b>08/98→09/01</b>
2.3 D	53 kW	2.3 l	08/98→09/01	 ; 09/98 ->	<b>KH10383</b> ProKIT
				 ; 09/98 ->	<b>KH10384</b> ProKIT












































    				
<b>LEXUS - CT (ZWA10_)</b>				<b>09/11→</b>
200h (ZWA10_)	100 kW	1.8 l	09/11→	 KH30121 ProKIT
<b>LEXUS - GS Sedan (_S16_)</b>				<b>08/97→12/04</b>
300 (JZS160_)	161 kW	3 l	10/00→12/04	 AT KH10381 ProKIT  KH10347 ProKIT
300 (JZS160_)	163 kW	3 l	08/97→10/00	 10/97 -> AT KH10381 ProKIT  KH10347 ProKIT
300 (JZS160_)	164 kW	3 l	11/01→12/04	 KH10347 ProKIT
300 (JZS160_)	168 kW	3 l	08/97→12/99	
400 (UZS160_)	216 kW	4 l	12/97→11/00	
400 (UZS160_)	224 kW	4 l	09/98→12/00	
430 (UZS161_)	208 kW	4.3 l	11/00→12/04	
430 (UZS161_)	224 kW	4.3 l	09/00→12/04	
<b>LEXUS - GS Sedan (_S19_)</b>				<b>04/05→11/11</b>
300 (GRS190_)	183 kW	3 l	04/05→11/11	 -> 03/09 KH30138 ProKIT
460 (UZS190_, URS190_)	255 kW	4.6 l	09/07→11/11	 -> 03/09 KH30177 ProKIT  KH30151 ProKIT
350 AWD (GRS196_)	226 kW	3.5 l	09/06→11/11	 KH30033 ProKIT  KH30034 ProKIT
430 (UZS190_)	208 kW	4.3 l	04/05→11/11	 -> 09/08 KH30138 ProKIT  -> 09/08 KH30177 ProKIT  KH30151 ProKIT
450h (GRS191_, GWS191_)	254 kW	3.5 l	02/06→11/11	 KH30151 ProKIT
<b>LEXUS - GS Sedan (JZS147_)</b>				<b>01/93→08/97</b>
300 (JZS147_)	156 kW	3 l	01/93→08/97	 10/93 -> AT KH10381 ProKIT  08/93 -> KH10207 ProKIT
<b>LEXUS - IS I (_E1_)</b>				<b>04/99→07/05</b>
200 (GXE10)	114 kW	2 l	04/99→07/05	 KH10128 ProKIT
300 (JCE10)	157 kW	3 l	09/01→07/05	 KH10347 ProKIT
300 (JCE10)	161 kW	3 l	09/00→07/05	 KH10347 ProKIT
<b>LEXUS - IS II Sedan (_E2_)</b>				<b>08/05→03/13</b>
200d (ALE20_)	110 kW	2.2 l	07/10→07/12	 KH30151 ProKIT
IS F (USE20)	311 kW	5 l	11/07→03/13	
220d (ALE20)	130 kW	2.2 l	08/05→07/12	 -> 08/09 KH30138 ProKIT
250 (GSE20)	153 kW	2.5 l	08/05→03/13	 -> 08/09 KH30177 ProKIT  KH30151 ProKIT
250 AWD (GSE25_)	153 kW	2.5 l	10/05→03/13	 KH30033 ProKIT
250 AWD (GSE25_)	158 kW	2.5 l	11/10→03/13	 KH30034 ProKIT
350 AWD (GSE26)	228 kW	3.5 l	09/10→03/13	
<b>LEXUS - IS C (GSE2_)</b>				<b>04/09→06/15</b>
250 (GSE20)	153 kW	2.5 l	04/09→06/15	 -> 12/09 KH30138 ProKIT  -> 12/09 KH30177 ProKIT  KH30151 ProKIT
<b>LEXUS - IS SportCross (_E1_)</b>				<b>10/01→10/05</b>
200 (GXE10_)	114 kW	2 l	10/02→10/05	 KH10128 ProKIT
300 (JCE10_)	157 kW	3 l	10/01→10/05	 KH10347 ProKIT
300 (JCE10_)	161 kW	3 l	10/01→07/05	 KH10347 ProKIT
<b>LEXUS - LS Sedan (_F1_)</b>				<b>12/89→12/95</b>
400 (UCF10)	180 kW	4 l	12/89→12/95	 -> 10/94 KH10207 ProKIT
<b>LEXUS - LS Sedan (_F2_)</b>				<b>12/94→10/00</b>
400 (UCF20_)	194 kW	4 l	12/94→08/97	 -> 07/97 KH10207 ProKIT
400 (UCF20_)	209 kW	4 l	09/97→10/00	 -> 08/00 KH10207 ProKIT
<b>LEXUS - NX (_Z1_)</b>				<b>07/14→</b>
200t AWD (AGZ15_)	173 kW	2 l	07/14→09/17	 KH30013 ProKIT
200t AWD (AGZ15_)	175 kW	2 l	07/14→	
300 AWD (AGZ15_)	175 kW	2 l	09/17→	
300h AWD (AYZ15_)	112 kW	2.5 l	07/14→	
300h AWD (AYZ15)	145 kW	2.5 l	07/14→	
300h AWD (AYZ15)	147 kW	2.5 l	11/18→	



































     					
<b>LEXUS - RX (_L1_)</b>				<b>12/08→10/15</b>	
270 (AGL10_)	138 kW	2.7 l	12/08→10/15		<b>KH10025</b> ProKIT
350 AWD (GGL15_)	204 kW	3.5 l	12/08→08/15		
350 AWD (GGL15_)	206 kW	3.5 l	03/09→02/12		
<b>LEXUS - RX (_U3_)</b>				<b>05/03→12/08</b>	
300 (MCU35_)	150 kW	3 l	05/03→12/08	 ; -> 01/06	<b>KH30118</b> ProKIT
350 AWD (GSU35_)	203 kW	3.5 l	02/06→12/08		<b>KH30118</b> ProKIT
<b>LEXUS - RX (MCU15)</b>				<b>01/98→05/03</b>	
300 AWD (MCU15_)	164 kW	3 l	01/98→02/03	 ; ABS	<b>KH10023</b> ProKIT
300 AWD (MCU15)	148 kW	3 l	10/00→05/03	 ; -> 02/03	<b>KH10182</b> ProKIT
				 ; ABS	<b>KH10023</b> ProKIT
<b>LEXUS - SC Convertible (UZZ40_)</b>				<b>01/01→07/10</b>	
430 (UZZ40_)	210 kW	4.3 l	05/01→07/10	 ; AT	<b>KH10381</b> ProKIT
					<b>KH10347</b> ProKIT
430 (UZZ40_)	215 kW	4.3 l	01/01→07/10		<b>KH10347</b> ProKIT
430 (UZZ40_)	223 kW	4.3 l	01/01→07/05		
430 (UZZ40_)	233 kW	4.3 l	05/01→12/05		
430 (UZZ40_)	244 kW	4.3 l	05/01→07/10		
































































    					
<b>LOTUS - ECLAT</b>					<b>10/75→08/86</b>
2.0	119 kW	2 l	10/75→05/80		<b>KH00124</b> ProKIT
2.2	119 kW	2.2 l	05/80→08/86		
<b>LOTUS - ELISE</b>					<b>08/95→11/00</b>
1.8	88 kW	1.8 l	08/95→11/00	  ; 07/96 -> 01/00; MT	<b>KH10189</b> ProKIT
111 S	107 kW	1.8 l	03/99→11/00	  ; MT	<b>KH10189</b> ProKIT
<b>LOTUS - ELITE</b>					<b>05/74→12/82</b>
2.0	119 kW	2 l	05/74→05/80		<b>KH00124</b> ProKIT
2.2	119 kW	2.2 l	05/80→12/82		
<b>LOTUS - ESPRIT S4 (082)</b>					<b>02/96→06/03</b>
3.5 V8 32V Turbo	260 kW	3.5 l	02/96→06/03	 	<b>KH10370</b> ProKIT
<b>LOTUS - EUROPA</b>					<b>10/66→04/76</b>
1.5	57 kW	1.5 l	10/66→10/70		<b>KH00124</b> ProKIT
1.6	78 kW	1.6 l	05/70→04/76		











































































				  			 13		
<b>MAZDA - 2 (DE_, DH_) 07/07→06/15</b>									
1.3 (DE3FS)	55 kW	1.3 l	10/07→06/15	 ; 					KH10070 ProKIT
1.3 (DE3FS)	63 kW	1.3 l	10/07→06/15						KH30120 ProKIT
1.3 BiFuel	55 kW	1.3 l	05/11→11/14						
1.3 BiFuel	62 kW	1.3 l	05/11→11/14						
1.3 MZR (DE3FS)	62 kW	1.3 l	01/10→06/15						
1.4 MZR-CD	50 kW	1.4 l	01/08→06/15						
1.5 (DE5FS)	76 kW	1.5 l	07/07→06/15						
1.5 MZR (DE5FS)	75 kW	1.5 l	06/11→06/15						
1.6 MZ-CD	66 kW	1.6 l	10/08→06/15						
1.6 MZ-CD	70 kW	1.6 l	06/11→06/15						
<b>MAZDA - 2 (DY) 02/03→06/07</b>									
1.2 (DY3W)	55 kW	1.2 l	02/03→06/07	 ; 					KH10093 ProKIT
1.25 (DY3W)	55 kW	1.25 l	04/03→06/07						
1.3 L (DY3W)	67 kW	1.3 l	04/03→06/07						
1.4	59 kW	1.4 l	02/03→06/07						
1.4	59 kW	1.4 l	04/03→06/07						
1.4 CD	50 kW	1.4 l	04/03→06/07						
1.6	74 kW	1.6 l	02/03→06/07						
1.6	74 kW	1.6 l	04/03→06/07						
<b>MAZDA - 2 Saloon (DE_) 05/10→06/15</b>									
1.3	63 kW	1.3 l	05/10→06/15	 ; 					KH10070 ProKIT
1.5 i	76 kW	1.5 l	05/10→06/15						
<b>MAZDA - 3 / 3 Saloon (BK, BL) 10/03→09/14</b>									
1.3 (BK14)	62 kW	1.3 l	10/03→06/09	 ; 01/05 -> 12/08					KH10156 ProKIT
1.6 (BK12)	77 kW	1.6 l	02/04→06/09	 ; -> 12/04					KH20106 ProKIT
1.6 (BK14)	77 kW	1.6 l	10/03→06/09						
1.6 Di Turbo	80 kW	1.6 l	06/04→06/09	 ; 					KH30153 ProKIT
1.6 Di Turbo (BK12Y)	80 kW	1.6 l	06/04→06/09						
1.6 MZ-CD (BL14)	80 kW	1.6 l	12/08→05/13						KH10156 ProKIT
1.6 MZR (BL12)	77 kW	1.6 l	12/08→09/14						
1.6 MZR (BL14)	77 kW	1.6 l	12/08→09/14	 ; 					KH30153 ProKIT
2.0 MZR (BL12)	110 kW	2 l	03/09→09/14						
2.0 MZR (BLEFW)	110 kW	2 l	01/09→09/14						
2.2 MZR CD (BL10)	110 kW	2.2 l	01/09→10/13						
2.2 MZR CD (BL10)	110 kW	2.2 l	01/09→09/14						
2.2 MZR CD (BL10)	136 kW	2.2 l	01/09→05/13						
2.2 MZR CD (BL10)	136 kW	2.2 l	06/09→05/13						
2.3 MPS Turbo (BK14)	191 kW	2.3 l	12/06→06/09						
2.0 (BKEP)	110 kW	2 l	10/03→12/09	 ; 03/06 -> 12/08					KH10156 ProKIT
				 ; -> 12/04					KH20106 ProKIT
				 ; 					KH30153 ProKIT
2.0 (BKEP)	110 kW	2 l	10/03→12/09	 ; 03/06 -> 12/08					KH10156 ProKIT
				 ; -> 12/04					KH20106 ProKIT
2.0 MZR-CD (BK12)	105 kW	2 l	12/06→06/09	 ; -> 12/08					KH10156 ProKIT
2.0 MZR-CD (BK14)	105 kW	2 l	07/06→06/09	 ; 					KH30153 ProKIT
2.0 MZR DISI (BL12)	111 kW	2 l	02/09→05/13						KH10156 ProKIT
2.0 MZR DISI (BLEFW)	111 kW	2 l	12/08→05/13						
2.3 DiSi Turbo MPS (BK3P)	184 kW	2.3 l	06/06→06/09	 ; 					KH30153 ProKIT
2.3 MPS Turbo (BL14)	191 kW	2.3 l	12/08→09/14						
<b>MAZDA - 5 (CR19) 02/05→05/10</b>									
1.8 (CR19)	85 kW	1.8 l	02/05→05/10	 ; 06/05 ->					KH10156 ProKIT
2.0 (CREW)	107 kW	2 l	02/05→05/10	 ; 					KH30153 ProKIT
2.0 CD (CR19)	81 kW	2 l	02/05→05/10						
2.0 CD (CR19)	105 kW	2 l	02/05→05/10						KH10156 ProKIT
				 ; 					KH30153 ProKIT
<b>MAZDA - 6 Estate (GH) 12/07→07/13</b>									
2.0 MZR-CD (GH14)	103 kW	2 l	12/07→12/10						KH10161 ProKIT
2.2 D (GH10)	95 kW	2.2 l	01/10→07/13						
2.2 MZR-CD (GH10)	92 kW	2.2 l	01/09→12/10						
2.2 MZR-CD (GH10)	120 kW	2.2 l	08/08→07/13						
2.2 MZR-CD (GH10)	132 kW	2.2 l	01/10→07/13						
2.2 MZR-CD (GH10)	136 kW	2.2 l	08/08→12/11						





























































											
<b>MAZDA - 6 Hatchback (GG)</b>										<b>08/02→08/07</b>	
1.8	88 kW	1.8 l	08/02→08/07						KH10016 ProKIT		
2.0 (GGES)	104 kW	2 l	08/02→08/07		-> 07/07; ABS				KH20129 ProKIT		
2.0 (GGES)	108 kW	2 l	03/05→08/07								
2.0 DI (GG14)	89 kW	2 l	08/02→08/07								
2.0 DI (GG14)	100 kW	2 l	08/02→08/07								
2.0 DI (GG14)	105 kW	2 l	06/05→08/07								
2.3 (GG3S)	122 kW	2.3 l	08/02→08/07								
<b>MAZDA - 6 Hatchback (GH)</b>										<b>08/07→12/12</b>	
2.0 MZR-CD (GH14)	103 kW	2 l	08/07→10/09						KH10161 ProKIT		
2.2 D (GH10)	95 kW	2.2 l	01/10→12/12								
2.2 MZR-CD (GH10)	92 kW	2.2 l	01/09→12/12								
2.2 MZR-CD (GH10)	120 kW	2.2 l	01/09→12/12								
2.2 MZR-CD (GH10)	132 kW	2.2 l	01/10→12/12								
2.2 MZR-CD (GH10)	136 kW	2.2 l	01/09→12/12								
<b>MAZDA - 6 Saloon (GG)</b>										<b>06/02→08/07</b>	
1.8	88 kW	1.8 l	08/02→08/07						KH10016 ProKIT		
2.0 (GGEP)	104 kW	2 l	06/02→08/07		-> 07/07; ABS				KH20129 ProKIT		
2.0 (GGEP)	108 kW	2 l	03/05→08/07								
2.0 DI (GG14)	89 kW	2 l	08/02→08/07								
2.0 DI (GG14)	100 kW	2 l	06/02→08/07								
2.0 DI (GG14)	105 kW	2 l	06/05→08/07								
2.3 (GG3P)	122 kW	2.3 l	06/02→08/07								
2.3	120 kW	2.3 l	03/05→07/07						KH10016 ProKIT		
2.3 MPS Turbo (GG3P)	191 kW	2.3 l	12/05→08/07		-> 07/07; ABS				KH20129 ProKIT		
<b>MAZDA - 6 Saloon (GH)</b>										<b>08/07→07/13</b>	
2.0 MZR-CD (GH14)	103 kW	2 l	08/07→10/10						KH10161 ProKIT		
2.2 D (GH10)	95 kW	2.2 l	01/10→12/12								
2.2 D (GH10)	132 kW	2.2 l	01/10→07/13								
2.2 MZR-CD (GH10)	92 kW	2.2 l	01/09→12/12								
2.2 MZR-CD (GH10)	120 kW	2.2 l	01/09→12/12								
2.2 MZR-CD (GH10)	136 kW	2.2 l	01/09→12/12								
<b>MAZDA - 6 Station Wagon (GY)</b>										<b>01/02→02/08</b>	
1.8	88 kW	1.8 l	08/02→08/07						KH10016 ProKIT		
2.0 (GYEW)	104 kW	2 l	08/02→08/07		-> 07/07; ABS				KH20129 ProKIT		
2.0 (GYEW)	108 kW	2 l	03/05→08/07								
2.0 DI (GY19)	89 kW	2 l	08/02→08/07								
2.0 DI (GY19)	105 kW	2 l	06/05→08/07								
2.3 (GY3W)	122 kW	2.3 l	01/02→02/08								
2.0 DI (GY19)	100 kW	2 l	08/02→02/05						KH10016 ProKIT		
					ABS				KH20129 ProKIT		
2.3 AWD (GY3W)	119 kW	2.3 l	11/02→08/07						KH10016 ProKIT		
<b>MAZDA - 121 I (DA)</b>										<b>10/87→06/91</b>	
1.1 (DA101)	42 kW	1.1 l	10/87→10/90						KH00079 ProKIT		
					01/88 ->				KH00100 ProKIT		
1.3 (DA103)	40 kW	1.3 l	04/89→10/90						KH00079 ProKIT		
									KH00100 ProKIT		
1.3 (DA103)	44 kW	1.3 l	10/87→06/91						KH00079 ProKIT		
					01/88 -> 10/90				KH00100 ProKIT		
<b>MAZDA - 121 II Sedan (DB)</b>										<b>11/90→03/96</b>	
1.3 16V (DB3PA)	39 kW	1.3 l	11/90→03/96						KH00079 ProKIT		
1.3 i 16V (DB3PA)	53 kW	1.3 l	11/90→03/96						KH00082 ProKIT		
					-> 02/96; ABS				KH20163 ProKIT		
<b>MAZDA - 121 METRO Hatchback (DW)</b>										<b>08/98→07/03</b>	
1.3 16V (DW3W)	46 kW	1.3 l	08/98→07/03						KH00082 ProKIT		
1.5 16V (DW5W)	55 kW	1.5 l	04/00→07/03		-> 03/03; ABS				KH20163 ProKIT		
1.3 i 16V (DW3W)	53 kW	1.3 l	08/98→04/00						KH00082 ProKIT		
					ABS				KH20163 ProKIT		
<b>MAZDA - 323 III Hatchback / 323 III Sedan / 323 III Station Wagon (BF, BW)</b>										<b>08/85→10/95</b>	
1.1	40 kW	1.1 l	08/85→04/90						KH00079 ProKIT		
1.1	40 kW	1.1 l	09/85→10/89								
1.3 (BF103)	44 kW	1.3 l	08/85→05/89								
1.3 (BF103)	44 kW	1.3 l	09/85→12/87								
1.3 (BW103)	44 kW	1.3 l	07/86→04/90								
1.4 (BF103)	44 kW	1.4 l	04/87→07/89								
1.4 (BF103)	44 kW	1.4 l	09/87→10/89								

												
<b>MAZDA - 323 III Hatchback / 323 III Sedan / 323 III Station Wagon (BF, BW) 08/85→10/95</b>												
1.5 (BF105)	54 kW	1.5 l	09/87→10/89									KH00079 ProKIT
1.5 (BF5S)	55 kW	1.5 l	08/85→05/89									
1.5 (BW105)	54 kW	1.5 l	01/87→05/89									
1.5 (BW5W, BW105)	55 kW	1.5 l	05/86→05/89									
1.5 i (BF5S)	70 kW	1.5 l	08/85→05/89									
1.6 (BF106)	54 kW	1.6 l	09/87→10/89									
1.6 (BW106)	54 kW	1.6 l	09/87→10/89									
1.6 (BW106)	63 kW	1.6 l	09/86→10/95									
1.6 GT (BF106)	63 kW	1.6 l	09/87→10/89									
1.6 GT (BF106)	77 kW	1.6 l	08/85→08/93									
1.6 GT (BFMP)	63 kW	1.6 l	11/86→10/89									
1.6 GT (BFMP)	77 kW	1.6 l	01/86→12/88									
1.7 D (BF7P)	40 kW	1.7 l	09/86→05/89									
1.7 D (BF7P)	42 kW	1.7 l	01/87→05/89									
1.7 D (BF7S)	40 kW	1.7 l	04/86→05/89									
1.7 D (BF7S)	42 kW	1.7 l	01/87→05/89									
1.7 D (BW7W)	40 kW	1.7 l	11/86→08/87									
1.7 D (BW7W)	41 kW	1.7 l	10/89→03/93									
1.7 D (BW7W)	42 kW	1.7 l	11/86→10/89									
<b>MAZDA - 323 IV Saloon / 323 ASTINA IV (BG) 06/89→10/96</b>												
1.3 (BG3P)	49 kW	1.3 l	09/89→06/91									KH20094 ProKIT
1.6 (BG6S, BG6P)	62 kW	1.6 l	09/89→06/91									
1.6 (BG6S)	62 kW	1.6 l	09/89→06/91									
1.8 16V (BG8P)	76 kW	1.8 l	08/89→07/94									
1.8 16V (BG8S, BG8P)	76 kW	1.8 l	08/89→07/94									
1.8 16V GT (BG8P)	94 kW	1.8 l	06/89→07/94									
1.8 16V GT (BG8S, BG8P)	94 kW	1.8 l	08/89→07/94									
1.3 16V (BG3P)	54 kW	1.3 l	04/91→07/94	 ; 07/93 -> 05/94; 							KH20166 ProKIT	
1.6 16V (BG6S, BG6P)	65 kW	1.6 l	03/91→10/94									
1.6 16V (BG6S)	65 kW	1.6 l	08/89→10/96									KH20094 ProKIT
1.7 D (BG7P)	41 kW	1.7 l	08/89→07/94									
1.8 16V Turbo 4WD (BG8R)	120 kW	1.8 l	01/91→07/94	 ; 							KH10016 ProKIT	
1.8 Turbo 4WD (BG8R)	122 kW	1.8 l	04/91→04/94									
<b>MAZDA - 323 ASTINA V (BA) 08/94→09/98</b>												
1.3 16V	54 kW	1.3 l	08/94→09/98	 ; -> 09/96;  ; 							KH20166 ProKIT	
1.5 16V (BA11)	65 kW	1.5 l	08/94→09/98									
1.8 16V (BA8P)	84 kW	1.8 l	08/94→09/98									KH20094 ProKIT
<b>MAZDA - 323 ASTINA V (BA) 07/94→09/98</b>												
1.5 16V (BA11)	65 kW	1.5 l	07/94→09/98	 ; 10/94 -> 06/98;  ; 							KH20166 ProKIT	
1.8 16V (BA8P)	84 kW	1.8 l	08/94→09/98									KH20094 ProKIT
2.0 24V (BAEP)	106 kW	2 l	08/94→09/98	 ; 10/94 -> 09/96;  ; 							KH20166 ProKIT	
<b>MAZDA - 323 ASTINA VI (BJ) 09/98→05/04</b>												
1.4	50 kW	1.4 l	09/98→05/04									KH10017 ProKIT
1.6	77 kW	1.6 l	09/98→05/04									
2.0 (BJ10, BJFW)	98 kW	2 l	02/00→05/04									
1.4 (BJ3P)	53 kW	1.4 l	01/01→05/04									
1.6 (BJ10M)	70 kW	1.6 l	01/01→05/04									
1.6 (BJ10M)	72 kW	1.6 l	01/01→05/04									
2.0 TD	74 kW	2 l	01/01→05/04									KH20094 ProKIT
				 ;  ; 							KH20129 ProKIT	
1.4 16V (BJ3P)	54 kW	1.4 l	09/98→01/01	 ; -> 09/00;  ; 							KH20166 ProKIT	
				 ; -> 09/00; 								
												KH10017 ProKIT
				 ; 10/00 ->  ; 							KH20129 ProKIT	
												KH20094 ProKIT
1.5 16V (BJ5W)	65 kW	1.5 l	09/98→01/01	 ; -> 09/00;  ; 							KH20166 ProKIT	
2.0 TD	66 kW	2 l	09/98→12/01	 ; -> 09/00; 								
												KH10017 ProKIT
												KH20094 ProKIT
1.9 16V (BJ14)	84 kW	1.9 l	09/98→01/01									KH10017 ProKIT
				 ; 10/00 ->  ; 							KH20129 ProKIT	
				 ; -> 09/00;  ; 							KH20166 ProKIT	
												KH20094 ProKIT
2.0 (BJFW)	96 kW	2 l	01/01→05/04									KH10017 ProKIT
				 ; -> 10/03;  ; for vehicles without track widening							KH20166 ProKIT	
												KH20094 ProKIT
												KH20129 ProKIT











































				    	
<b>MAZDA - 323 ASTINA VI (BJ)</b>				<b>09/98→05/04</b>	
2.0 D	52 kW	2 l	09/98→05/04		KH10017 ProKIT
				 ; -> 09/00;  ; 	KH20166 ProKIT
				 ; 	KH20094 ProKIT
<b>MAZDA - 323 P V / 323 PROTEGÉ V Saloon (BA)</b>				<b>05/94→09/98</b>	
1.3 16V	54 kW	1.3 l	08/94→09/98	 ; -> 06/98;  ; 	KH20166 ProKIT
1.3 16V	54 kW	1.3 l	10/96→09/98	 ; 	KH20094 ProKIT
1.5 16V	65 kW	1.5 l	10/96→09/98		
1.5 16V (BA11)	65 kW	1.5 l	08/94→09/98		
1.8 16V (BA11)	84 kW	1.8 l	08/94→09/98		
1.7 TD	60 kW	1.7 l	05/94→09/98	 ; 11/94 -> 09/96;  ; 	KH20166 ProKIT
				 ; 	KH20094 ProKIT
2.0 D	52 kW	2 l	10/96→09/98	 ; 03/97 -> 06/98;  ; 	KH20166 ProKIT
				 ; 	KH20094 ProKIT
<b>MAZDA - 323 PROTEGÉ VI (BJ)</b>				<b>09/98→05/04</b>	
1.3 (BJ3P)	53 kW	1.3 l	01/01→05/04		KH10017 ProKIT
1.6 (BJ10M)	72 kW	1.6 l	01/01→05/04	 ; -> 10/03;  ; for vehicles without track widening	KH20166 ProKIT
				 ; 	KH20094 ProKIT
				 ; 	KH20129 ProKIT
1.3 16V (BJ3P)	54 kW	1.3 l	09/98→01/01	 ; -> 09/00;  ; 	KH20166 ProKIT
				 ; -> 09/00; 	
				 ; 10/00 ->;  ; 	KH20129 ProKIT
				 ; 	KH20094 ProKIT
1.5 16V (BJ5P)	65 kW	1.5 l	09/98→01/01		KH10017 ProKIT
2.0 D (BJ1_)	52 kW	2 l	09/98→05/04	 ; 	KH20094 ProKIT
2.0 TD (BJEP)	66 kW	2 l	09/98→05/04		
1.6 (BJ10M)	70 kW	1.6 l	01/01→05/04		KH10017 ProKIT
				 ; 	KH20094 ProKIT
				 ;  ; 	KH20129 ProKIT
1.9 16V (BJ10M)	84 kW	1.9 l	09/98→05/04		KH10017 ProKIT
				 ; 10/00 ->;  ; 	KH20129 ProKIT
				 ; 	KH20094 ProKIT
2.0 (BJFP)	96 kW	2 l	01/01→05/04		KH10017 ProKIT
				 ; -> 10/03;  ; for vehicles without track widening	KH20166 ProKIT
				 ; 	KH20129 ProKIT
2.0 (SP20)	98 kW	2 l	02/00→05/04		KH10017 ProKIT
2.0 DiTD (BJEP)	74 kW	2 l	10/00→10/02		
<b>MAZDA - 626 II Hatchback / 626 II Sedan (GC)</b>				<b>11/82→01/90</b>	
1.6 (GC1061)	55 kW	1.6 l	03/83→09/87	 ; 06/83 ->	KH00073 ProKIT
1.6 (GC1061)	59 kW	1.6 l	11/82→06/87		
1.6 (GC1061)	59 kW	1.6 l	03/83→09/87		
2.0 (GC10E1)	74 kW	2 l	03/83→09/87		
2.0 D (GC10F1)	46 kW	2 l	01/83→06/87		
2.0 (GC1)	68 kW	2 l	10/86→01/90		KH00073 ProKIT
2.0 (GC10E1)	68 kW	2 l	01/85→09/87		
2.0 (GC10E1)	88 kW	2 l	01/86→09/87		
2.0 D (GC10F1)	46 kW	2 l	03/84→06/87		
<b>MAZDA - 626 III Coupe / 626 III Hatchback / 626 III Sedan (GD)</b>				<b>06/87→05/92</b>	
1.8 (GD8P)	65 kW	1.8 l	09/87→08/91	 ;  ; 	KH20094 ProKIT
1.8 (GD8P)	65 kW	1.8 l	11/87→05/92		
2.0 (GDEP)	66 kW	2 l	09/87→10/90	 ; 02/89 ->;  ; 	KH20094 ProKIT
2.0 12V (GDEP)	79 kW	2 l	09/87→05/92		
2.0 12V (GDEP)	79 kW	2 l	11/87→05/92		
2.0 16V (GDEP)	103 kW	2 l	11/87→10/90		
2.0 16V (GDEP)	103 kW	2 l	11/87→05/92		
2.0 16V (GDEP)	103 kW	2 l	12/87→10/90		
2.0 16V (GDEP)	109 kW	2 l	06/87→08/89		
2.0 16V (GDEP)	109 kW	2 l	06/87→09/89		
2.0 16V (GDEP)	109 kW	2 l	07/87→09/89		
2.0 D (GDFFP)	44 kW	2 l	07/87→07/91	 ; 02/89 ->; 	KH20094 ProKIT



     				
<b>MAZDA - 626 IV Hatchback / 626 IV Sedan / 626 V Hatchback / 626 V Sedan 08/91→10/02 (GE, GF)</b>				
1.8 (GE8P)	66 kW	1.8 l	08/94→04/97	 KH10016 ProKIT
1.8 (GE8P)	77 kW	1.8 l	08/91→04/97	 KH20135 ProKIT
1.8 (GF8P)	66 kW	1.8 l	05/97→12/99	
1.8 (GF8P)	74 kW	1.8 l	12/99→10/02	
1.8 i (GE8P)	66 kW	1.8 l	08/94→04/97	
1.8 i (GE8P)	77 kW	1.8 l	08/91→04/97	
2.0 (GFER)	85 kW	2 l	05/97→10/02	
2.0 (GFER)	100 kW	2 l	04/98→10/02	
2.0 D GLX Complex (GEFP)	55 kW	2 l	10/92→04/97	
2.0 D GLX Complex (GEFP)	55 kW	2 l	01/93→04/97	
2.0 DITD (GFFP)	66 kW	2 l	04/98→10/02	
2.0 DI TD (GFFP)	66 kW	2 l	04/98→10/02	
2.0 H.P. (GFER)	100 kW	2 l	02/98→10/02	
2.0 i (GE10S1)	85 kW	2 l	08/91→04/97	
2.0 i (GE10S1)	85 kW	2 l	01/92→04/97	
2.0 TD (GFFP)	81 kW	2 l	10/00→10/02	
2.0 Turbo DI (GFFP)	74 kW	2 l	04/98→10/02	
2.5 24V (GE5P)	120 kW	2.5 l	08/94→04/97	
2.5 24V (GE5P)	121 kW	2.5 l	01/92→04/97	
1.8 i	78 kW	1.8 l	05/94→06/97	 KH10016 ProKIT
2.0 i 4WD (GE10S1)	85 kW	2 l	04/92→04/97	  KH10016 ProKIT
				 KH20135 ProKIT
<b>MAZDA - 626 V Station Wagon (GW) 02/98→10/02</b>				
1.8 (GW8W)	66 kW	1.8 l	02/98→01/00	 KH10016 ProKIT
				  KH20129 ProKIT
				 KH20135 ProKIT
1.8 (GW8W)	74 kW	1.8 l	01/00→10/02	 KH10016 ProKIT
2.0 (GWEW)	85 kW	2 l	02/98→10/02	
2.0 DITD (GFWF)	66 kW	2 l	09/99→10/02	   KH20129 ProKIT
2.0 H.P. (GWEW)	100 kW	2 l	02/98→10/02	 KH20135 ProKIT
2.0 TD (GFWF)	81 kW	2 l	10/00→10/02	
2.0 Turbo DI (GFWF)	74 kW	2 l	04/98→10/02	
<b>MAZDA - B-SERIES (UF) 09/98→06/99</b>				
2.5 D 4WD (UFY0)	57 kW	2.5 l	09/98→06/99	    KH00137 ProKIT
<b>MAZDA - B-SERIES (UN) 06/99→11/06</b>				
2.2 8V 4WD	68 kW	2.2 l	06/99→11/06	 KH00112 ProKIT
2.5 D	57 kW	2.5 l	06/99→11/06	    KH00033 ProKIT
				 KH00119 ProKIT
2.5 D	62 kW	2.5 l	12/02→11/06	 KH00119 ProKIT
2.5 D 4WD	57 kW	2.5 l	06/99→11/06	 KH00112 ProKIT
				 KH10011 ProKIT
2.5 D 4WD	61 kW	2.5 l	11/99→12/01	 KH10011 ProKIT
2.5 D 4WD	62 kW	2.5 l	12/02→11/06	
2.5 TD 4WD	80 kW	2.5 l	06/99→07/06	
<b>MAZDA - BT-50 Pickup (CD, UN) 12/06→12/15</b>				
2.5 MRZ-CD 4x4 (UNY0W3)	105 kW	2.5 l	12/06→12/15	 KH10011 ProKIT
<b>MAZDA - CX-3 (DK) 02/15→</b>				
1.5 SKYACTIV-D AWD (DK4WS)	77 kW	1.5 l	02/15→01/18	 KH30051 ProKIT
2.0 SKYACTIV-G AWD (DK4W7)	110 kW	2 l	05/15→	
<b>MAZDA - CX-7 (ER) 10/07→03/13</b>				
2.2 MZR-CD AWD (ER10A)	120 kW	2.2 l	01/12→03/13	 KH30182 ProKIT
2.3 MZR DISI Turbo AWD (ER3P)	190 kW	2.3 l	10/07→08/09	
2.3 MZR DISI Turbo AWD (ER3P)	191 kW	2.3 l	06/09→03/13	
<b>MAZDA - E-SERIES Bus (SR1) 01/84→05/94</b>				
E2000	63 kW	2 l	11/84→05/94	     KH00033 ProKIT
				 KH00119 ProKIT
				   KH00137 ProKIT
E2200 D	46 kW	2.2 l	01/84→02/88	    KH00033 ProKIT
				    KH00137 ProKIT
				  KH00137 ProKIT
				 KH00119 ProKIT



				13	i		
<b>MAZDA - E-SERIES Van (SR2)</b>						<b>05/85→12/03</b>	
2200 D 4WD	47 kW	2.2 l	03/91→05/03			KH00033 ProKIT	
E2200 D 4WD	52 kW	2.2 l	02/97→05/03			KH00112 ProKIT	
						KH00137 ProKIT	
E2000	60 kW	2 l	03/91→05/94	; Code: SR1		KH00033 ProKIT	
				; Code: SRY;		KH00119 ProKIT	
				; Code: SR1, SRY		KH00137 ProKIT	
E2000	63 kW	2 l	05/85→04/89	; 12/87 ->; Code: SR1		KH00033 ProKIT	
				; 01/88 ->; Code: SRY;		KH00137 ProKIT	
				; 12/87 ->; Code: SR1		KH00119 ProKIT	
				; 02/88 ->; Code: SRY		KH00033 ProKIT	
E2000	70 kW	2 l	06/94→05/03	; -> 12/96; Code: SRY;		KH00137 ProKIT	
				; 12/01 ->		KH00119 ProKIT	
				; -> 12/96; Code: SRY		KH00033 ProKIT	
				; -> 09/99; Code: SR1		KH00119 ProKIT	
E2200 D	46 kW	2.2 l	05/85→02/88	; 01/88 ->; Code: SDX		KH00033 ProKIT	
				; 01/88 ->; Code: SDY,SRY;		KH00137 ProKIT	
				; 01/88 ->; Code: SDY, SRY		KH00119 ProKIT	
				; 02/88 ->; Code: SDX		KH00033 ProKIT	
E2200 D	47 kW	2.2 l	11/88→12/03	; -> 12/96; Code: SDX		KH00119 ProKIT	
				; -> 12/96; Code: SDY,SRY;		KH00033 ProKIT	
				; -> 12/96; Code: SDY, SDX, SRY		KH00137 ProKIT	
<b>MAZDA - EUNOS 30X (EC)</b>						<b>05/91→09/98</b>	
1.6	66 kW	1.6 l	05/91→10/93	; 07/93 ->;		KH20166 ProKIT	
1.8 i V6 (ECPSA)	98 kW	1.8 l	01/92→01/94			KH20166 ProKIT	
1.6 i	79 kW	1.6 l	11/93→09/98			KH20166 ProKIT	
1.8 i V6 (ECPSA)	95 kW	1.8 l	01/94→10/97			KH20166 ProKIT	
<b>MAZDA - FAMILIA IV (BG)</b>						<b>08/89→10/94</b>	
1.3 (BG3S)	49 kW	1.3 l	09/89→07/94	; 07/93 -> 05/94;		KH20166 ProKIT	
1.3 16V (BG3S)	54 kW	1.3 l	09/89→07/94	;		KH20094 ProKIT	
1.6 16V (BG6Z)	65 kW	1.6 l	03/91→10/94			KH20094 ProKIT	
1.7 D (BG7S)	41 kW	1.7 l	08/89→07/94			KH20094 ProKIT	
1.6 (BG6Z)	62 kW	1.6 l	09/89→06/91			KH20094 ProKIT	
1.8 16V GT (BG8S)	94 kW	1.8 l	09/89→03/93			KH20094 ProKIT	
1.8 16V 4WD (BG8S)	76 kW	1.8 l	11/91→12/93			KH10016 ProKIT	
1.8 16V Turbo 4WD (BG8S)	120 kW	1.8 l	09/90→12/92			KH10016 ProKIT	
1.8 16V Turbo 4WD (BG8S)	136 kW	1.8 l	01/93→07/94			KH10016 ProKIT	
<b>MAZDA - MILLENIA Sedan (TA)</b>						<b>07/93→09/02</b>	
2.0 24V	105 kW	2 l	08/93→01/00			KH10016 ProKIT	
2.3 24V (TA3P)	155 kW	2.3 l	02/95→01/00			KH10016 ProKIT	
2.5 24V (TA5P)	123 kW	2.5 l	07/93→07/00			KH10016 ProKIT	
2.5 V6 (TA5P)	120 kW	2.5 l	07/00→09/02			KH20129 ProKIT	
				; 09/00 ->		KH20129 ProKIT	
<b>MAZDA - MPV II (LW)</b>						<b>09/99→12/06</b>	
2.0 (LWEW)	88 kW	2 l	08/00→07/02			KH10016 ProKIT	
2.0 (LWEW)	90 kW	2 l	09/99→08/00			KH20129 ProKIT	
2.0 DI	100 kW	2 l	07/02→02/06	; -> 01/05		KH20129 ProKIT	
2.3 (LW3W)	104 kW	2.3 l	07/02→02/06			KH20129 ProKIT	
3.0 i V6 (LWFW)	147 kW	3 l	01/02→12/06			KH20129 ProKIT	
<b>MAZDA - MX-5 I (NA)</b>						<b>05/90→04/98</b>	
1.6 (NA6C)	66 kW	1.6 l	01/95→04/98	; 04/95 ->; MT; ; ABS Ring Ø [mm]: 83		KH20114 ProKIT	
				; -> 02/98;		KH20163 ProKIT	
1.6 (NA6C)	85 kW	1.6 l	05/90→01/94	; -> 08/93;		KH20163 ProKIT	
				; MT; ; ABS Ring Ø [mm]: 83		KH20114 ProKIT	
1.8 (NA8C)	96 kW	1.8 l	01/93→04/98	; 05/94 -> 03/98; MT; ; ABS Ring Ø [mm]: 83		KH20114 ProKIT	
				; -> 02/98;		KH20163 ProKIT	
1.8 (NA8C)	96 kW	1.8 l	09/93→12/97	; ; ABS Ring Ø [mm]: 83		KH20114 ProKIT	

										
<b>MAZDA - MX-5 II (NB)</b>										<b>01/98→10/05</b>
1.6 16V (NB6C)	81 kW	1.6 l	05/98→10/05		-> 08/04; MT; ABS; ABS Ring Ø [mm]: 83					KH20114 ProKIT
1.8 16V (NB8C)	102 kW	1.8 l	11/00→10/05		-> 03/05; ABS					KH20163 ProKIT
					ABS; ABS Ring Ø [mm]: 85					KH20136 ProKIT
										KH10017 ProKIT
1.8 (NB8C)	103 kW	1.8 l	01/98→07/02		ABS; ABS Ring Ø [mm]: 83					KH20114 ProKIT
					ABS; ABS Ring Ø [mm]: 85					KH20136 ProKIT
										KH10017 ProKIT
1.8 16V (NB8C)	103 kW	1.8 l	05/98→10/05		-> 08/00; ABS					KH20163 ProKIT
					-> 08/04; MT; ABS; ABS Ring Ø [mm]: 83					KH20114 ProKIT
					ABS; ABS Ring Ø [mm]: 85					KH20136 ProKIT
										KH10017 ProKIT
1.8 16V (NB8C)	107 kW	1.8 l	11/00→10/05		-> 08/04; ABS; ABS Ring Ø [mm]: 83					KH20114 ProKIT
					-> 03/05; ABS					KH20163 ProKIT
					ABS; ABS Ring Ø [mm]: 85					KH20136 ProKIT
										KH10017 ProKIT
<b>MAZDA - MX-5 III (NC)</b>										<b>03/05→12/14</b>
1.8 (NC18)	93 kW	1.8 l	03/05→12/14							KH10016 ProKIT
2.0	127 kW	2 l	03/05→12/07							
2.0 (NC18)	118 kW	2 l	07/05→12/14							
<b>MAZDA - MX-5 IV (ND)</b>										<b>06/15→</b>
1.5 (ND2E)	96 kW	1.5 l	06/15→							KH30050 ProKIT
2.0 (ND2E)	118 kW	2 l	06/15→							
<b>MAZDA - MX-6 (GE)</b>										<b>02/92→09/97</b>
2.0	85 kW	2 l	02/92→02/97							KH10016 ProKIT
2.5 24V	123 kW	2.5 l	02/93→11/95							
2.5 24V (GE10L)	121 kW	2.5 l	02/92→09/97							
2.5 i 24V (GE20L)	120 kW	2.5 l	08/94→02/97							
<b>MAZDA - PREMACY (CP)</b>										<b>07/99→03/05</b>
1.9 (CP10P)	84 kW	1.9 l	07/99→03/05							KH10017 ProKIT
					-> 01/02; ABS					KH20129 ProKIT
					ABS					KH20094 ProKIT
1.9 (CP8W)	74 kW	1.9 l	07/99→03/05							KH10017 ProKIT
					-> 12/04; ABS					KH20129 ProKIT
					ABS					KH20094 ProKIT
2.0 (CP10S)	96 kW	2 l	11/01→03/05							KH10017 ProKIT
					-> 01/05; ABS					KH20129 ProKIT
					ABS					KH20094 ProKIT
2.0 TD	66 kW	2 l	10/99→07/00							KH10017 ProKIT
					ABS					KH20094 ProKIT
					ABS					KH20129 ProKIT
2.0 TD	74 kW	2 l	07/00→03/05							KH10017 ProKIT
					-> 01/05; ABS					KH20129 ProKIT
<b>MAZDA - XEDOS 6 (CA)</b>										<b>01/92→10/99</b>
1.6 16V	79 kW	1.6 l	04/94→10/99							KH10016 ProKIT
1.6 16V	83 kW	1.6 l	01/92→03/94							KH20135 ProKIT
2.0 V6 (CAEP)	103 kW	2 l	06/94→10/99							
2.0 V6 (CAEP)	106 kW	2 l	01/92→05/94							



**MERCEDES-BENZ - /8 Coupe (W114) 04/69→01/77**

250 CE (114.022)	110 kW	2.5 l	04/69→04/72		KH00040 ProKIT
280 CE (114.072)	136 kW	2.7 l	06/72→01/77	; -> 04/76	KH00040 ProKIT

**MERCEDES-BENZ - /8 Sedan (W114) 01/68→11/76**

230.6 (114.015)	88 kW	2.3 l	01/68→11/76	; 05/72 -> 08/76	KH00040 ProKIT
250 2.8 (114.011)	96 kW	2.7 l	06/72→11/76	; 09/72 -> 06/76	KH00040 ProKIT
280 (114.060)	118 kW	2.7 l	06/72→11/76		KH00031 ProKIT
280 E (114.062)	136 kW	2.7 l	06/72→11/76	; -> 03/76	KH00040 ProKIT

**MERCEDES-BENZ - /8 Sedan (W115) 01/68→01/77**

200	70 kW	2 l	01/68→01/77	; 02/75 -> 09/76	KH00040 ProKIT
200 (115.015)	63 kW	2 l	01/68→01/77		
220 (115.010)	77 kW	2.2 l	01/68→07/73		KH00040 ProKIT
220 D (115.110)	44 kW	2.2 l	01/68→01/77	; 03/68 -> 01/73; -	KH00040 ProKIT
				; 03/70 -> 11/73; -	
240 D (115.117)	48 kW	2.4 l	08/73→01/77	; 09/73 -> 09/76	KH00040 ProKIT

**MERCEDES-BENZ - 123 Coupe / 123 Saloon / 123 T-Model (C123, W123, S123) 01/76→12/85**

200	62 kW	2 l	02/76→08/80	(ABS)	KH00055 ProKIT
200	74 kW	2 l	06/80→11/85		
200 (123.020)	69 kW	2 l	02/76→08/80		
200 (123.220)	80 kW	2 l	06/80→11/85		
200 D	44 kW	2 l	03/79→11/85		
200 D (123.120)	40 kW	2 l	07/76→02/79		
200 T	80 kW	2 l	11/80→11/85		
200 T (123.280)	74 kW	2 l	11/80→11/85		
220 D	49 kW	2.2 l	01/77→03/79		
220 D (123.126)	44 kW	2.2 l	01/76→02/79		
230 (123.023)	80 kW	2.3 l	02/76→03/81		
230 C (123.043)	80 kW	2.3 l	05/77→04/80		
230 CE (123.243)	100 kW	2.3 l	04/80→12/85		
230 E (123.223)	100 kW	2.3 l	04/80→12/85		
230 T (123.083)	80 kW	2.3 l	09/77→03/80		
230 TE (123.283)	100 kW	2.3 l	04/80→11/85		
240 D (123.123)	48 kW	2.4 l	02/76→02/79		
240 D (123.123)	53 kW	2.4 l	03/79→11/85		
240 T D	48 kW	2.4 l	09/77→02/79		
240 T D (123.183)	53 kW	2.4 l	03/79→12/85		
250 (123.026)	95 kW	2.5 l	02/76→10/79		
250 (123.026)	103 kW	2.5 l	10/79→07/85		
250 T (123.086)	95 kW	2.5 l	05/78→10/79		
250 T (123.086)	103 kW	2.5 l	05/78→08/82		
280 (123.030)	115 kW	2.7 l	02/76→08/81		
280 C (123.050)	115 kW	2.7 l	03/77→03/80		
280 CE	130 kW	2.7 l	09/77→08/79		
280 CE	136 kW	2.7 l	03/77→11/85		
280 E	130 kW	2.7 l	08/76→08/81		
280 E (123.033)	136 kW	2.7 l	02/76→11/85		
280 TE (123.093)	136 kW	2.7 l	09/77→11/85		
300 C Turbo-D (123.153)	92 kW	2.9 l	09/81→07/85		
300 D (123.130)	59 kW	2.9 l	02/76→07/80		
300 D (123.130)	65 kW	2.9 l	03/79→11/85		
300 T D (123.190)	59 kW	2.9 l	09/77→10/85		
300 T D (123.190)	65 kW	2.9 l	03/79→11/85		
300 T Turbo-D (123.193)	92 kW	2.9 l	10/80→11/85		
300 Turbo-D (123.133)	92 kW	3 l	08/81→07/85		

**MERCEDES-BENZ - 124 Convertible / 124 Coupe / 124 Saloon (A124, C124, W124) 12/84→08/93**

200 (124.020)	75 kW	2 l	01/86→05/90	(ABS)	KH10039 ProKIT
200 (124.020)	80 kW	2 l	12/85→05/90		
200 E (124.019)	100 kW	2 l	10/92→06/93		
200 E (124.021)	87 kW	2 l	09/88→08/93		
200 E (124.021)	90 kW	2 l	09/88→12/89		
220 CE (124.042)	110 kW	2.2 l	10/92→05/93		
220 E (124.022)	110 kW	2.2 l	10/92→06/93		
230 CE (124.043)	97 kW	2.3 l	03/87→12/92		
230 CE (124.043)	100 kW	2.3 l	03/87→12/92		
230 CE Cat (124.043)	97 kW	2.3 l	06/89→12/92		
230 E (124.023)	97 kW	2.3 l	12/84→03/92		
230 E (124.023)	100 kW	2.3 l	01/85→06/93		
230 E Cat (124.023)	97 kW	2.3 l	06/89→06/93		
260 E (124.026)	118 kW	2.6 l	09/85→08/92		
260 E (124.026)	122 kW	2.6 l	09/85→12/89		



**MERCEDES-BENZ - 124 Convertible / 124 Coupe / 124 Saloon (A124, C124, 12/84→08/93 W124)**














































































280 E (124.028)	145 kW	2.8 l	10/92→06/93		KH10039 ProKIT
300 CE (124.050)	132 kW	3 l	03/87→05/93		
300 CE-24 (124.051)	162 kW	3 l	09/89→12/92		
300 CE-24 (124.051)	170 kW	3 l	09/89→12/92		
300 CE-24 (124.061)	162 kW	3 l	04/92→06/93		
300 CE-24 (124.061)	170 kW	3 l	04/92→06/93		
300 E (124.030)	132 kW	3 l	08/85→08/92		
300 E-24 (124.031)	162 kW	3 l	09/88→08/92		
300 E-24 (124.031)	170 kW	3 l	09/88→08/92		
320 CE (124.052)	162 kW	3.2 l	10/92→05/93		
320 E (124.032)	162 kW	3.2 l	10/92→06/93		

















**MERCEDES-BENZ - 124 T-Model (S124) 09/85→07/93**

200 T (124.080)	77 kW	2 l	01/86→05/90		KH10191 ProKIT
200 T (124.080)	80 kW	2 l	09/85→08/89		
200 T D (124.180)	53 kW	2 l	09/85→08/91		
200 T D (124.180)	55 kW	2 l	09/88→08/91		
200 TE	90 kW	2 l	09/88→12/89		
200 TE (124.079)	100 kW	2 l	05/86→06/93		
200 TE (124.081)	87 kW	2 l	09/88→08/92		
220 TE (124.082)	110 kW	2.2 l	10/92→05/93		
230 TE (124.083)	97 kW	2.3 l	09/85→08/92		
230 TE (124.083)	100 kW	2.3 l	09/85→08/92		
230 TE Cat (124.083)	97 kW	2.3 l	06/89→08/92		
250 T D (124.185)	66 kW	2.5 l	09/85→06/93		
250 T D (124.185)	69 kW	2.5 l	01/89→06/93		
250 TD Turbo (124.188)	93 kW	2.5 l	03/88→07/93		
260 TE FGST.	118 kW	2.6 l	09/89→08/92		
260 TE FGST.	122 kW	2.6 l	09/85→12/89		
280 TE (124.088)	145 kW	2.8 l	10/92→06/93		
300 T D (124.190)	80 kW	3 l	09/86→06/93		
300 T D (124.190)	81 kW	3 l	01/89→06/93		
300 T D (124.190)	83 kW	3 l	01/89→06/93		
300 TE (124.090)	132 kW	3 l	01/86→08/92		
300 TE (124.090)	138 kW	3 l	01/86→12/89		
300 TE-24 (124.091)	162 kW	3 l	09/89→08/92		
300 TE-24 (124.091)	170 kW	3 l	09/89→08/92		
300 TE 4-matic (124.290)	132 kW	3 l	09/86→06/93		
300 TE 4-matic (124.290)	138 kW	3 l	09/86→12/89		
300 T Turbo-D	105 kW	3 l	09/86→01/89		
300 T Turbo-D (124.193)	108 kW	3 l	01/89→06/93		
300 T Turbo-D 4-matic (124.393)	105 kW	3 l	09/86→01/89		
300 T Turbo-D 4-matic (124.393)	108 kW	3 l	01/89→06/93		
320 TE (124.092)	162 kW	3.2 l	10/92→06/93		

**MERCEDES-BENZ - 190 Sedan (W201) 10/82→08/93**

2.0 (201.022)	66 kW	2 l	10/82→10/84	VIN 003513 ->	KH00059 ProKIT
2.0 (201.023)	75 kW	2 l	01/86→05/90		
2.0 (201.023)	77 kW	2 l	08/83→05/90		KH10039 ProKIT
2.3	97 kW	2.3 l	09/87→09/88		KH10039 ProKIT
2.3 E	100 kW	2.3 l	10/82→09/88		
2.6	118 kW	2.6 l	10/82→09/88		
E 2.0	93 kW	2 l	10/82→06/93		
E 2.3-16	125 kW	2.3 l	09/85→12/87		
E 2.3-16	130 kW	2.3 l	09/85→08/88		
E 2.3-16 (201.034)	136 kW	2.3 l	04/84→01/87		
E 2.5-16 (201.035)	150 kW	2.5 l	09/88→08/93		
E 2.5-16 Evolution (201.036)	143 kW	2.5 l	03/89→08/93		
D 2.0 (201.122)	53 kW	2 l	08/83→08/89	VIN 000044 ->	KH00059 ProKIT
D 2.0 (201.122)	55 kW	2 l	08/89→08/93		KH10039 ProKIT
D 2.5 (201.126)	69 kW	2.5 l	08/89→08/93		
Turbo-D 2.5 (201.128)	90 kW	2.5 l	02/88→08/93		
Turbo-D 2.5 (201.128)	93 kW	2.5 l	02/88→08/93		
D 2.5 (201.126)	66 kW	2.5 l	04/85→08/93		KH00059 ProKIT
					KH10039 ProKIT
E 1.8 (201.018)	80 kW	1.8 l	04/90→08/93	VIN 006893 ->	KH00059 ProKIT
E 2.0	87 kW	2 l	01/85→08/93		
E 2.0 (201.024)	83 kW	2 l	02/85→12/86		KH10039 ProKIT
E 2.0 (201.024)	85 kW	2 l	02/85→12/86		
E 2.0 (201.024)	90 kW	2 l	10/82→06/93		
E 2.3	97 kW	2.3 l	09/86→08/91		
E 2.3 (201.028)	100 kW	2.3 l	10/86→08/93		
E 2.5-16 Evolution II	173 kW	2.5 l	05/90→08/93		
E 2.6	122 kW	2.6 l	09/86→12/89		
E 2.6 (201.029)	118 kW	2.6 l	09/86→08/93		

MOTION & CONTROL				MERCEDES-BENZ			
							
<b>MERCEDES-BENZ - A-CLASS (W168)</b>				<b>07/97→08/04</b>			
A 140 (168.031, 168.131)	60 kW	1.4 l	07/97→08/04	 ; 09/98 ->; 		KH10147 ProKIT	
				 ; 04/01 ->			
				 ; 03/01 ->; Code: C168.031; VIN J568590 ->		KH10183 ProKIT	
				 ; Code: C168.131			
A 140 (168.031, 168.131)	60 kW	1.6 l	01/01→08/04	 ; 03/01 ->; Code: C168.131; VIN J568590 ->		KH10183 ProKIT	
				 ; Code: C168.131			
A 160 (168.033, 168.133)	75 kW	1.6 l	07/97→08/04	 ; 09/98 ->; 		KH10147 ProKIT	
				 ; 04/01 ->			
				 ; 03/01 ->; VIN J568590 ->; Code: C168.033; 		KH10183 ProKIT	
				 ; Code: C168.133			
A 160 CDI (168.006)	55 kW	1.7 l	02/01→08/04	 ; 03/01 ->; VIN J568590 ->		KH10183 ProKIT	
A 170 CDI (168.008)	66 kW	1.7 l	07/98→02/01	 ; 09/98 ->; 		KH10147 ProKIT	
A 170 CDI (168.009, 168.109)	70 kW	1.7 l	02/01→08/04	 ; 03/01 ->; VIN J568590 ->; Code: C168.009		KH10183 ProKIT	
				 ; Code: C168.109			
				 ; 04/01 ->; 		KH10147 ProKIT	
A 190 (168.032, 168.132)	92 kW	1.9 l	03/99→08/04	 ; 06/99 -> 04/01; 		KH10147 ProKIT	
				04/01 ->			
				 ; 03/01 ->; VIN J568590 ->; Code: C168.032		KH10183 ProKIT	
				 ; Code: C168.132			
A 210 (168.035, 168.135)	103 kW	2.1 l	12/01→08/04	 ; 		KH10147 ProKIT	
				 ; 		KH10183 ProKIT	
<b>MERCEDES-BENZ - A-CLASS (W169)</b>				<b>09/04→06/12</b>			
A 150 (169.031, 169.331)	70 kW	1.5 l	09/04→06/12	 ; 03/05 ->; VIN J116410 ->; 		KH10049 ProKIT	
A 160 CDI (169.006, 169.306)	60 kW	2 l	09/04→06/12	 ; -> 03/05		KH10228 ProKIT	
A 170 (169.032, 169.332)	85 kW	1.7 l	09/04→06/12			KH30144 ProKIT	
A 180 CDI (169.007, 169.307)	80 kW	2 l	09/04→06/12				
A 200 (169.033, 169.333)	100 kW	2 l	09/04→06/12				
A 200 CDI (169.008, 169.308)	103 kW	2 l	09/04→06/12				
A 160 (169.031, 169.331)	70 kW	1.5 l	04/09→06/12	 ; 		KH10049 ProKIT	
A 180 (169.032, 169.332)	85 kW	1.7 l	04/09→06/12			KH30144 ProKIT	
E-CELL (169.090)	50 kW		12/10→06/12				
A 200 CDI (169.308, 169.008)	100 kW	2 l	09/04→06/12	 ; 03/05 ->; VIN J116410 ->; 		KH10049 ProKIT	
						KH30144 ProKIT	
A 200 TURBO (169.034, 169.334)	142 kW	2 l	09/05→06/12	 ; VIN J116410 ->; 		KH10049 ProKIT	
						KH30144 ProKIT	
<b>MERCEDES-BENZ - A-CLASS (W176)</b>				<b>06/12→05/18</b>			
A 160 CDI / d (176.011)	66 kW	1.5 l	06/13→05/18			KH10368 ProKIT	
A 200 CDI / d (176.008)	100 kW	2.2 l	02/14→05/18				
A 200 CDI / d 4-matic (176.002)	100 kW	2.2 l	02/14→05/18				
A 200 CDI (176.001)	100 kW	1.8 l	06/12→10/14				
A 220 CDI (176.003)	125 kW	2.2 l	09/12→05/18				
A 220 CDI 4-matic (176.005)	125 kW	2.2 l	02/14→05/18				
A 250 4-matic (176.046)	155 kW	2 l	06/13→05/18				
A 45 AMG 4-matic (176.052)	265 kW	2 l	06/13→05/18				
A 180 (176.042)	90 kW	1.6 l	09/12→05/18			KH10368 ProKIT	
A 180 CDI / d (176.012)	80 kW	1.5 l	06/12→05/18			KH30189 ProKIT	
A 180 CDI (176.000)	80 kW	1.8 l	06/12→10/14				
A 200 (176.043)	115 kW	1.6 l	06/12→05/18				
A 250 (176.044)	155 kW	2 l	06/12→05/18				
<b>MERCEDES-BENZ - B-CLASS Sports Tourer (W245)</b>				<b>03/05→11/11</b>			
B 150 (245.231)	70 kW	1.5 l	03/05→11/11	 ; VIN J1000184 ->; 		KH10049 ProKIT	
B 170 (245.232)	85 kW	1.7 l	03/05→11/11			KH30144 ProKIT	
B 180 CDI (245.207)	80 kW	2 l	03/05→11/11				
B 200 (245.233)	100 kW	2 l	03/05→11/11				
B 200 CDI (245.208)	100 kW	2 l	03/05→11/11				
B 200 CDI (245.208)	103 kW	2 l	03/05→11/11				
B 200 TURBO (245.234)	142 kW	2 l	03/05→11/11				
B 160 (245.231)	70 kW	1.5 l	04/09→11/11	 ; 		KH10049 ProKIT	
B 170 NGT (245.233)	85 kW	2 l	04/08→11/11			KH30144 ProKIT	
B 180 (245.232)	85 kW	1.7 l	04/09→11/11				
B 180 NGT (245.233)	85 kW	2 l	04/08→11/11				
F-CELL (242.890)	100 kW	0.1 l	01/10→11/11				

     					
<b>MERCEDES-BENZ - B-CLASS Sports Tourer (W246, W242)</b>				<b>11/11→12/18</b>	
B 160 CDI / d (246.211)	66 kW	1.5 l	05/13→12/18	 <b>KH10368 ProKIT</b>	
B 180 CDI / d (246.212)	80 kW	1.5 l	02/13→12/18		
B 200 CDI / d (246.208)	100 kW	2.2 l	08/14→12/18		
B 200 CDI / d 4-matic (246.202)	100 kW	2.2 l	08/14→12/18		
B 200 Natural Gas Drive / B 200 c (242.848)	115 kW	2 l	11/12→12/17		
B 220 4-matic (246.247)	135 kW	2 l	05/13→12/18		
B 220 CDI / d (246.203)	130 kW	2.2 l	08/14→12/18		
B 220 CDI / d 4-matic (246.205)	130 kW	2.2 l	08/14→12/18		
B 250 4-matic (246.246)	155 kW	2 l	08/14→12/18		
Electric Drive / B 250 e (242.890)	65 kW		11/14→10/17		
Electric Drive / B 250 e (242.890)	132 kW		11/14→10/17		
B 180 (246.242)	90 kW	1.6 l	11/11→12/18		 <b>KH10368 ProKIT</b>
B 180 CDI (246.200)	80 kW	1.8 l	11/11→08/14		
B 200 (246.243)	115 kW	1.6 l	11/11→12/18	 <b>KH30189 ProKIT</b>	
B 200 CDI (246.201)	100 kW	1.8 l	11/11→08/14		
B 220 CDI / d (246.203)	125 kW	2.2 l	11/11→12/18		
B 250 (246.244)	155 kW	2 l	05/12→12/18		
<b>MERCEDES-BENZ - CABRIOLET (W111, W112)</b>				<b>04/68→12/71</b>	
280 SE 3.5 (111.025)	147 kW	3.5 l	04/68→12/71	 <b>KH00031 ProKIT</b>	
<b>MERCEDES-BENZ - C-CLASS Coupe / C-CLASS Sedan (CL203, W202, W203)</b>				<b>03/93→05/08</b>	
C 160 Kompressor (203.730)	90 kW	1.8 l	05/02→05/08	 <b>KH00007 ProKIT</b>	
C 180 (203.035)	95 kW	2 l	10/00→05/02		
C 180 (203.735)	95 kW	2 l	03/01→05/02	 <b>KH10039 ProKIT</b>	
C 180 Kompressor (203.046)	105 kW	1.8 l	05/02→02/07		
C 180 Kompressor (203.746)	105 kW	1.8 l	05/02→05/08		
C 200 CDI (203.004)	75 kW	2.2 l	02/01→06/03		
C 200 CDI (203.004)	85 kW	2.2 l	09/00→06/03	 <b>KH00007 ProKIT</b>  <b>KH10039 ProKIT</b> 	
C 200 CDI (203.007)	90 kW	2.2 l	04/03→02/07		
C 200 CDI (203.707)	90 kW	2.2 l	03/03→05/08		
C 200 CGI Kompressor (203.043)	125 kW	1.8 l	07/03→02/07		
C 200 CGI Kompressor (203.743)	125 kW	1.8 l	03/03→05/08		
C 200 Kompressor (203.042)	120 kW	1.8 l	05/02→02/07		
C 200 Kompressor (203.045)	120 kW	2 l	05/00→06/02		
C 200 Kompressor (203.742)	120 kW	1.8 l	05/02→05/08		
C 200 Kompressor (203.745)	120 kW	2 l	03/01→05/02		
C 220 CDI (203.006)	105 kW	2.2 l	05/00→02/07		
C 220 CDI (203.008)	110 kW	2.2 l	02/03→02/07		
C 220 CDI (203.706)	105 kW	2.2 l	03/01→01/04		
C 220 CDI (203.708)	110 kW	2.2 l	02/04→05/08		
C 230 (203.052)	150 kW	2.5 l	01/05→02/07		
C 230 (203.752)	150 kW	2.5 l	01/05→05/08		
C 230 Kompressor (203.040)	141 kW	1.8 l	02/04→02/07		
C 230 Kompressor (203.740)	141 kW	1.8 l	05/02→05/08		
C 230 Kompressor (203.747)	145 kW	2.3 l	03/01→05/02		
C 240 (203.061)	125 kW	2.6 l	05/00→02/07		
C 270 CDI (203.016)	125 kW	2.7 l	12/00→02/07		
C 280 (203.054)	170 kW	3 l	01/05→02/07		
C 320 (203.064)	160 kW	3.2 l	05/00→02/07		
C 320 (203.764)	160 kW	3.2 l	09/02→05/08		
C 320 CDI (203.020)	165 kW	3 l	01/05→02/07		
C 350 (203.056)	200 kW	3.5 l	01/05→02/07		
C 350 (203.756)	200 kW	3.5 l	01/05→05/08		
C 180 (202.018)	89 kW	1.8 l	11/94→05/00		 <b>KH10039 ProKIT</b>
C 180 (202.018)	90 kW	1.8 l	03/93→05/00		
C 200 (202.020)	100 kW	2 l	01/94→05/00		
C 200 CDI (202.134)	75 kW	2.2 l	03/98→05/00		
C 200 D (202.120)	55 kW	2 l	03/93→05/00		
C 200 D (202.122)	65 kW	2 l	10/96→05/00		
C 200 Kompressor (202.025)	132 kW	2 l	10/95→05/00		
C 200 Kompressor (202.025)	141 kW	2 l	11/96→05/00		
C 220	120 kW	1.8 l	05/02→05/08		
C 220 (202.022)	110 kW	2.2 l	03/93→05/00		
C 220 CDI	100 kW	2.2 l	03/01→01/04		
C 220 CDI (202.133)	92 kW	2.2 l	09/97→05/00		
C 220 CDI (203.006)	100 kW	2.2 l	05/00→02/07		
C 220 D (202.021)	55 kW	2.2 l	07/96→05/00		
C 220 D (202.121)	70 kW	2.2 l	08/93→05/00		
C 230 (202.023)	110 kW	2.3 l	06/96→06/97		
C 230 Kompressor (202.024)	142 kW	2.3 l	10/95→05/00		
C 240 (202.026)	125 kW	2.4 l	06/97→05/00		
C 250 D (202.125)	83 kW	2.5 l	05/93→05/00		
C 250 Turbo-D (202.128)	110 kW	2.5 l	10/95→05/00		
C 270 CDI (203.016)	120 kW	2.7 l	12/00→02/07		
C 280 (202.028)	142 kW	2.8 l	05/93→05/00		
C 280 (202.029)	145 kW	2.8 l	06/97→05/00		





**MERCEDES-BENZ - C-CLASS Coupe / C-CLASS Sedan (CL203, W202, W203) 03/93→05/08**

C 36 AMG (202.028)	206 kW	3.6 l	05/94→05/00		KH10039 ProKIT
C 43 AMG (202.033)	225 kW	4.3 l	08/97→05/00		
C 240 4-matic (203.081)	125 kW	2.6 l	07/02→02/07	; 09/02 -> 12/06	KH10415 ProKIT
					KH10039 ProKIT
					KH10145 ProKIT
C 280 4-matic (203.092)	170 kW	3 l	01/05→02/07	; 06/05 -> 12/06	KH10415 ProKIT
					KH10039 ProKIT
					KH10145 ProKIT
C 30 CDI AMG (203.018)	170 kW	3 l	01/03→02/07		KH00007 ProKIT
C 30 CDI AMG (203.718)	170 kW	3 l	09/02→05/08		
C 32 AMG Kompressor (203.065)	260 kW	3.2 l	02/01→02/07		
C 32 AMG Kompressor (203.765)	260 kW	3.2 l	05/02→05/08		
C 55 AMG (203.076)	270 kW	5.4 l	02/04→02/07		
C 320 4-matic (203.084)	160 kW	3.2 l	07/02→02/07	; 09/02 -> 12/03	KH10415 ProKIT
					KH10039 ProKIT
					KH10145 ProKIT
C 350 4-matic (203.087)	200 kW	3.5 l	01/05→02/07	; 07/05 -> 12/06	KH10415 ProKIT
					KH10145 ProKIT







**MERCEDES-BENZ - C-CLASS Sedan (W204) 01/07→01/14**

C 180 CGI (204.049)	115 kW	1.8 l	01/07→01/14	; -> 03/11	KH00007 ProKIT
C 180 Kompressor (204.044, 204.045)	115 kW	1.6 l	01/08→01/14	; -> 03/11	KH20062 ProKIT
C 180 Kompressor (204.046)	115 kW	1.8 l	01/07→01/14		
C 200 CGI (204.048)	135 kW	1.8 l	01/07→01/14		
C 200 Kompressor (204.041)	135 kW	1.8 l	01/07→01/14		
C 220 CDI (204.002)	125 kW	2.2 l	12/08→01/14		
C 230 (204.052)	150 kW	2.5 l	01/07→01/14		
C 250 CDI (204.003)	150 kW	2.2 l	08/08→01/14		
C 250 CGI (204.047)	150 kW	1.8 l	07/09→01/14		
C 280 (204.054)	170 kW	3 l	01/07→01/14		
C 300 (204.054)	170 kW	3 l	07/09→01/14		
C 320 CDI (204.022)	165 kW	3 l	01/07→01/14		
C 350 (204.056)	200 kW	3.5 l	01/07→01/14		
C 350 CDI (204.022)	165 kW	3 l	07/09→01/14		
C 350 CDI (204.025)	170 kW	3 l	10/09→01/14		
C 350 CGI (204.065)	215 kW	3.5 l	09/08→01/14		
C 200 CDI (204.007, 204.006)	100 kW	2.1 l	01/07→12/09		KH00007 ProKIT
C 220 CDI (204.008)	125 kW	2.1 l	01/07→11/08		KH20062 ProKIT
C 230 4-matic (204.085)	150 kW	2.5 l	07/07→01/14	; -> 03/11	KH20062 ProKIT
C 280 4-matic (204.081)	170 kW	3 l	07/07→01/14		
C 300 4-matic (204.081)	170 kW	3 l	07/07→01/14		
C 320 CDI 4-matic (204.089)	165 kW	3 l	07/07→01/14		
C 350 4-matic (204.087)	200 kW	3.5 l	07/07→01/14		
C 350 CDI 4-matic (204.092)	170 kW	3 l	10/09→01/14		
C 63 AMG (204.077)	336 kW	6.2 l	02/08→01/14		
C 350 CDI 4-matic (204.089)	165 kW	3 l	07/09→01/14	; -> 03/10	KH20062 ProKIT















**MERCEDES-BENZ - C-CLASS T-Model (S202, S203) 06/96→08/07**






























C 180 (203.235)	95 kW	2 l	03/01→05/02		KH00007 ProKIT
C 180 Kompressor (203.246)	105 kW	1.8 l	05/02→08/07		
C 200 CDI (203.204)	75 kW	2.2 l	03/01→08/07		KH10039 ProKIT
C 200 CDI (203.204)	85 kW	2.2 l	03/01→08/07		
C 200 CDI (203.207)	90 kW	2.2 l	04/03→08/07		
C 200 CGI Kompressor (203.243)	125 kW	1.8 l	07/03→08/07		
C 200 Kompressor (203.242)	120 kW	1.8 l	05/02→08/07		
C 200 Kompressor (203.245)	120 kW	2 l	03/01→05/02		
C 220 CDI (203.206)	105 kW	2.2 l	03/01→08/07		
C 220 CDI (203.208)	100 kW	2.1 l	08/06→08/07		
C 220 CDI (203.208)	110 kW	2.2 l	02/04→08/07		
C 230 (203.252)	150 kW	2.5 l	01/05→08/07		
C 230 Kompressor (203.240)	141 kW	1.8 l	02/04→08/07		
C 240 (203.261)	125 kW	2.6 l	03/01→08/07		
C 270 CDI (203.216)	125 kW	2.7 l	03/01→08/07		
C 280 (203.254)	170 kW	3 l	01/05→08/07		
C 320 (203.264)	160 kW	3.2 l	03/01→08/07		
C 320 CDI (203.220)	165 kW	3 l	06/05→08/07		
C 350 (203.256)	200 kW	3.5 l	01/05→08/07		
C 180 T (202.078)	90 kW	1.8 l	06/96→09/00		KH10039 ProKIT
C 180 T (202.081)	95 kW	2 l	09/00→03/01		
C 200 T (202.080)	100 kW	2 l	06/96→03/01		
C 200 T CDI (202.194)	75 kW	2.2 l	03/98→03/01		
C 200 T D (202.180)	65 kW	2 l	10/96→03/01		



     						
<b>MERCEDES-BENZ - C-CLASS T-Model (S202, S203)</b>					<b>06/96→08/07</b>	
C 200 T Kompressor (202.082)	141 kW	2 l	11/96→03/01	ABS	KH10039 ProKIT	
C 200 T Kompressor (202.087)	120 kW	2 l	09/00→03/01			
C 220 T CDI (202.193)	92 kW	2.2 l	09/97→03/01			
C 220 T D (202.182)	55 kW	2.2 l	06/96→03/01			
C 220 T D (202.182)	70 kW	2.2 l	06/96→09/98			
C 230 T (202.083)	110 kW	2.3 l	06/96→06/98			
C 230 T Kompressor (202.085)	142 kW	2.3 l	06/97→09/00			
C 240 T (202.086)	125 kW	2.4 l	06/97→09/00			
C 240 T (202.088)	125 kW	2.6 l	09/00→03/01			
C 250 T Turbo-D (202.188)	110 kW	2.5 l	06/96→03/01			
C 270 CDI (203.216)	120 kW	2.7 l	03/01→08/07			
C 280 T (202.089)	145 kW	2.8 l	06/97→03/01			
C 240 4-matic (203.281)	125 kW	2.6 l	07/02→08/07	09/02 ->	KH10415 ProKIT	
				ABS	KH10039 ProKIT	
					KH10145 ProKIT	
C 280 4-matic (203.292)	170 kW	3 l	01/05→08/07	06/05 ->	KH10415 ProKIT	
				ABS	KH10039 ProKIT	
					KH10145 ProKIT	
C 30 CDI AMG (203.218)	170 kW	3 l	01/03→08/07		KH00007 ProKIT	
C 32 AMG Kompressor (203.265)	260 kW	3.2 l	03/01→08/07			
C 55 AMG (203.276)	270 kW	5.4 l	02/04→08/07			
C 320 4-matic (203.284)	160 kW	3.2 l	07/02→08/07	09/02 -> 12/03	KH10415 ProKIT	
				ABS	KH10039 ProKIT	
					KH10145 ProKIT	
C 350 4-matic (203.287)	200 kW	3.5 l	01/05→08/07	07/05 ->	KH10415 ProKIT	
					KH10145 ProKIT	
<b>MERCEDES-BENZ - C-CLASS T-Model (S204)</b>					<b>08/07→08/14</b>	
C 180 Kompressor (204.245)	115 kW	1.6 l	01/08→08/14	-> 03/11	KH00007 ProKIT	
C 180 Kompressor (204.246)	115 kW	1.8 l	08/07→08/14	-> 03/11	KH20062 ProKIT	
C 200 Kompressor (204.241)	135 kW	1.8 l	08/07→08/14			
C 220 CDI (204.202)	125 kW	2.2 l	12/08→08/14			
C 230 (204.252)	150 kW	2.5 l	08/07→08/14			
C 250 CDI (204.203)	150 kW	2.2 l	01/09→08/14			
C 250 CGI (204.247)	150 kW	1.8 l	07/09→08/14			
C 280 (204.254)	170 kW	3 l	08/07→08/14			
C 320 CDI (204.222)	165 kW	3 l	08/07→08/14			
C 350 (204.256)	200 kW	3.5 l	08/07→08/14			
C 350 CDI (204.225)	170 kW	3 l	10/09→08/14			
C 200 CDI (204.207)	100 kW	2.1 l	08/07→12/09		KH00007 ProKIT	
C 220 CDI (204.208)	125 kW	2.1 l	08/07→11/08		KH20062 ProKIT	
C 320 CDI 4-matic (204.289)	165 kW	3 l	08/07→12/11	-> 03/11	KH20062 ProKIT	
C 350 CDI 4-matic (204.292)	170 kW	3 l	10/09→08/14			
C 63 AMG (204.277)	336 kW	6.2 l	02/08→08/14			
<b>MERCEDES-BENZ - CITAN Box Body/MPV / CITAN Mixto / CITAN MPV (W415, Double Cabin)</b>					<b>11/12→08/21</b>	
108 CDI (415.601, 415.603)	55 kW	1.5 l	11/12→08/21	15, 16 Inch	KH10112 ProKIT	
108 CDI (415.703)	55 kW	1.5 l	11/12→08/21	14 Inch	KH10380 ProKIT	
109 CDI (415.601, 415.603, 415.605)	66 kW	1.5 l	11/12→08/21			
109 CDI (415.603, 415.605)	66 kW	1.5 l	11/12→08/21			
109 CDI (415.703)	66 kW	1.5 l	11/12→08/21			
111 CDI (415.603, 415.605)	81 kW	1.5 l	06/13→08/21			
111 CDI (415.703, 415.705)	81 kW	1.5 l	06/13→08/21			
112 (415.603)	84 kW	1.2 l	06/13→08/21			
112 (415.703)	84 kW	1.2 l	06/13→08/21			
<b>MERCEDES-BENZ - CLA Coupe / CLA Shooting Brake (C117, X117)</b>					<b>01/13→03/19</b>	
CLA 180 (117.342)	90 kW	1.6 l	01/13→03/19		KH10368 ProKIT	
CLA 180 CDI / d (117.312)	80 kW	1.5 l	10/13→05/18		KH30189 ProKIT	
CLA 200 (117.343)	115 kW	1.6 l	01/13→03/19			
CLA 220 CDI / d (117.303)	125 kW	2.2 l	01/13→03/19			
CLA 250 (117.344)	155 kW	2 l	01/13→03/19			
CLA 180 (117.942)	90 kW	1.6 l	01/15→03/19		KH10368 ProKIT	
CLA 200 (117.943)	115 kW	1.6 l	01/15→03/19			
CLA 200 CDI / d (117.908)	100 kW	2.2 l	01/15→03/19			
CLA 200 CDI / d 4-matic (117.902)	100 kW	2.2 l	01/15→03/19			
CLA 200 CDI (117.301)	100 kW	1.8 l	06/13→08/14			
CLA 220 CDI / d (117.303)	120 kW	2.2 l	01/13→03/19			
CLA 220 CDI / d (117.303)	130 kW	2.2 l	09/14→03/19			
CLA 220 CDI / d (117.903)	130 kW	2.2 l	01/15→03/19			
CLA 220 CDI / d 4-matic (117.305)	120 kW	2.2 l	08/14→03/19			
CLA 220 CDI / d 4-matic (117.305)	130 kW	2.2 l	09/14→03/19			



				     13 		
<b>MERCEDES-BENZ - CLA Coupe / CLA Shooting Brake (C117, X117)</b>						<b>01/13→03/19</b>
CLA 220 CDI / d 4-matic (117.905)	130 kW	2.2 l	01/15→03/19			<b>KH10368</b> ProKIT
CLA 220 CDI 4-matic (117.305)	125 kW	2.2 l	07/14→03/19			
CLA 250 (117.944)	155 kW	2 l	01/15→03/19			
CLA 250 4-matic (117.346)	155 kW	2 l	07/13→03/19			
CLA 250 4-matic (117.946)	155 kW	2 l	01/15→03/19			
CLA 45 AMG 4-matic (117.352)	265 kW	2 l	07/13→03/19			
CLA 45 AMG 4-matic (117.952)	265 kW	2 l	01/15→07/15			
<b>MERCEDES-BENZ - CLC-CLASS (CL203)</b>						<b>05/08→06/11</b>
CLC 160 (203.731)	95 kW	1.6 l	02/09→06/11	 ; → 03/11		<b>KH00007</b> ProKIT
CLC 180 Kompressor (203.746)	105 kW	1.8 l	05/08→06/11			<b>KH10039</b> ProKIT
CLC 200 CDI (203.707)	90 kW	2.1 l	05/08→06/11			
CLC 200 Kompressor (203.741)	135 kW	1.8 l	05/08→06/11			
CLC 220 CDI (203.708)	110 kW	2.1 l	05/08→06/11			
CLC 230 (203.752)	150 kW	2.5 l	05/08→06/11			
CLC 350 (203.756)	200 kW	3.5 l	05/08→06/11			
<b>MERCEDES-BENZ - CLK / CLK Convertible (C208, C209, A208, A209)</b>						<b>06/97→03/10</b>
200 (208.335)	100 kW	2 l	06/97→06/02			<b>KH10039</b> ProKIT
200 (208.435)	100 kW	2 l	03/98→03/02			
200 Kompressor (208.344)	120 kW	2 l	06/00→06/02			
200 Kompressor (208.345)	141 kW	2 l	06/97→06/00			
200 Kompressor (208.444)	120 kW	2 l	06/00→03/02			
200 Kompressor (208.445)	141 kW	2 l	03/98→06/00			
220 CDI (209.308)	100 kW	2.2 l	01/05→05/09			
230 Kompressor (208.347)	142 kW	2.3 l	06/97→06/00			
230 Kompressor (208.348)	145 kW	2.3 l	06/00→06/02			
230 Kompressor (208.447)	142 kW	2.3 l	03/98→06/00			
230 Kompressor (208.448)	145 kW	2.3 l	06/00→03/02			
240 (209.361)	120 kW	2.6 l	06/02→05/09			
270 CDI (209.316)	120 kW	2.7 l	02/03→06/05			
320 (208.365)	160 kW	3.2 l	06/97→06/02			
320 (208.465)	160 kW	3.2 l	03/98→03/02			
430 (208.370)	205 kW	4.3 l	07/98→06/02			
430 (208.470)	205 kW	4.3 l	09/98→03/02			
55 AMG (208.374)	255 kW	5.4 l	08/99→06/02			
55 AMG (208.474)	255 kW	5.4 l	01/00→03/02			
200 CGI (209.343)	125 kW	1.8 l	07/03→05/09			<b>KH00007</b> ProKIT
200 Kompressor (209.341)	135 kW	1.8 l	10/06→05/09			<b>KH10039</b> ProKIT
200 Kompressor (209.342)	120 kW	1.8 l	09/02→05/09			
220 CDI (209.308)	110 kW	2.2 l	01/05→05/09			
240 (209.361)	125 kW	2.6 l	06/02→05/09			
270 CDI (209.316)	125 kW	2.7 l	10/02→05/09			
280 (209.354)	170 kW	3 l	01/05→05/09			
320 (209.365)	160 kW	3.2 l	06/02→05/09			
320 CDI (209.320)	165 kW	3 l	01/05→05/09			
350 (209.356)	200 kW	3.5 l	01/05→05/09			
500 (209.372)	285 kW	5.5 l	06/06→05/09			
500 (209.375)	225 kW	5 l	06/02→05/09			
CLK 200 CGI (209.343)	125 kW	1.8 l	07/03→03/10			
CLK 200 Kompressor (209.441)	135 kW	1.8 l	10/06→03/10			
CLK 200 Kompressor (209.442)	120 kW	1.8 l	02/03→03/10			
CLK 240 (209.461)	125 kW	2.6 l	02/03→03/10			
CLK 280 (209.454)	170 kW	3 l	01/05→03/10			
CLK 320 (209.465)	160 kW	3.2 l	02/03→03/10			
CLK 320 CDI (209.420)	165 kW	3 l	03/05→03/10			
CLK 350 (209.456)	200 kW	3.5 l	01/05→03/10			
CLK 500 (209.472)	285 kW	5.5 l	06/06→03/10			
CLK 500 (209.475)	225 kW	5 l	02/03→03/10			
55 AMG (209.376)	270 kW	5.4 l	09/02→05/09			<b>KH00007</b> ProKIT
63 AMG (209.377)	354 kW	6.2 l	04/06→05/09			
63 AMG (209.377)	373 kW	6.2 l	05/07→05/09			
CLK 55 AMG (209.476)	270 kW	5.5 l	06/02→03/10			
CLK 63 AMG (209.477)	354 kW	6.2 l	04/06→03/10			
DTM AMG (209.3_)	428 kW	5.4 l	06/04→10/05			
<b>MERCEDES-BENZ - CLS (C218, C219)</b>						<b>10/04→12/17</b>
CLS 220 BlueTEC / d (218.301)	120 kW	2.2 l	05/14→12/17			<b>KH20104</b> ProKIT
CLS 220 BlueTEC / d (218.301)	125 kW	2.2 l	05/14→12/17			
CLS 220 BlueTEC / d (218.301)	130 kW	2.2 l	05/14→12/17			
CLS 250 BlueTEC / d 4-matic (218.397)	150 kW	2.2 l	05/14→12/17			
CLS 250 CDI / BlueTEC / d (218.303, 218.304)	150 kW	2.2 l	04/11→12/17			
CLS 300 (219.354)	170 kW	3 l	04/09→12/10			
CLS 320 CDI	155 kW	3 l	01/05→12/10			
CLS 350 (218.359)	225 kW	3.5 l	01/11→08/14			
CLS 350 BlueTEC / d (218.326)	185 kW	3 l	02/13→12/17			
CLS 350 BlueTEC / d (218.326)	190 kW	3 l	06/14→12/17			

				  	 	 13			
<b>MERCEDES-BENZ - CLS (C218, C219)</b>								<b>10/04→12/17</b>	
CLS 350 BlueTEC / d 4-matic (218.394)	185 kW	3 l	02/13→12/17				KH20104 ProKIT		
CLS 350 CDI	200 kW	3 l	04/09→12/10						
CLS 350 CDI / d (218.323)	195 kW	3 l	01/11→08/14						
CLS 350 CDI / d 4-matic (218.393)	195 kW	3 l	09/11→08/14						
CLS 350 CDI (219.322)	165 kW	3 l	04/09→12/10						
CLS 350 d 4-matic (218.394)	190 kW	3 l	04/15→12/17						
CLS 400 (218.361)	245 kW	3.5 l	07/14→12/17						
CLS 400 (218.365)	245 kW	3 l	05/14→12/17						
CLS 400 4-matic (218.367)	245 kW	3 l	05/14→12/17						
CLS 400 4-matic (218.368)	245 kW	3.5 l	07/14→12/17						
CLS 500 (218.373)	300 kW	4.7 l	02/11→12/17						
CLS 500 4-matic (218.391)	300 kW	4.7 l	09/11→12/17						
CLS 63 AMG (218.374)	386 kW	5.5 l	01/11→12/17						
CLS 63 AMG (218.374)	410 kW	5.5 l	01/11→12/17						
CLS 63 AMG (218.375)	430 kW	5.5 l	02/13→12/17						
CLS 63 AMG 4-matic (218.376)	430 kW	5.5 l	02/13→12/17						
CLS 63 AMG 4-matic (218.392)	410 kW	5.5 l	05/13→12/17						
CLS 280 (219.354)	170 kW	3 l	07/08→12/10		-> 03/10		KH00015 ProKIT		
CLS 320 CDI (219.322)	165 kW	3 l	01/05→12/10				KH20104 ProKIT		
CLS 350 (219.356)	200 kW	3.5 l	10/04→12/10						
CLS 350 (219.357)	215 kW	3.5 l	04/06→12/10						
CLS 500 (219.372)	285 kW	5.5 l	04/06→12/10						
CLS 500 (219.375)	225 kW	5 l	10/04→12/10						
CLS 55 AMG (219.376)	350 kW	5.4 l	01/05→12/10						
CLS 63 AMG (219.377)	378 kW	6.2 l	04/06→12/10						
<b>MERCEDES-BENZ - COUPE (W111, W112)</b>								<b>01/61→12/71</b>	
220 SEB (111.021)	88 kW	2.2 l	01/61→12/65				KH00031 ProKIT		
250 SE (111.021)	110 kW	2.5 l	01/65→12/67						
280 SE (111.024)	118 kW	2.7 l	01/67→12/71						
280 SE 3.5 (111.026)	147 kW	3.5 l	01/69→12/71						
<b>MERCEDES-BENZ - E-CLASS Convertible (A124)</b>								<b>06/93→03/98</b>	
E 200 (124.060)	100 kW	2 l	06/93→03/98				KH10039 ProKIT		
E 220 (124.062)	110 kW	2.2 l	06/93→03/98						
E 320 (124.066)	162 kW	3.2 l	06/93→03/98				KH00085 ProKIT		
E 36 AMG (124.066)	200 kW	3.6 l	05/94→03/98				KH10039 ProKIT		
<b>MERCEDES-BENZ - E-CLASS Convertible (A207)</b>								<b>01/10→12/16</b>	
E 200 CGI (207.448)	135 kW	1.8 l	01/10→12/16		-> 03/10		KH00007 ProKIT		
E 220 CDI / BlueTEC / d (207.402, 207.401)	125 kW	2.2 l	01/10→12/16		-> 03/10		KH20062 ProKIT		
E 250 CDI / BlueTEC / d (207.403, 207.404)	150 kW	2.2 l	01/10→12/16						
E 250 CGI (207.447)	150 kW	1.8 l	01/10→12/16						
E 350 CDI (207.422)	170 kW	3 l	01/10→12/11						
E 350 CGI (207.457)	215 kW	3.5 l	01/10→12/14						
E 500 (207.472)	285 kW	5.5 l	01/10→12/11						
<b>MERCEDES-BENZ - E-CLASS Coupe (C124)</b>								<b>06/93→06/97</b>	
E 200 (124.040)	100 kW	2 l	06/93→06/97				KH10039 ProKIT		
E 220 (124.042)	110 kW	2.2 l	06/93→06/97						
E 320 (124.052)	162 kW	3.2 l	06/93→06/97						
E 36 AMG (124.052)	200 kW	3.6 l	05/94→06/97						
<b>MERCEDES-BENZ - E-CLASS Coupe (C207)</b>								<b>01/09→12/16</b>	
E 200 CGI (207.348)	135 kW	1.8 l	01/10→12/16		-> 03/10		KH00007 ProKIT		
E 220 CDI / d (207.302, 207.301)	125 kW	2.2 l	01/10→12/16		-> 03/10		KH20062 ProKIT		
E 250 CDI / BlueTEC / d (207.303, 207.304)	150 kW	2.2 l	01/09→12/16						
E 250 CGI (207.347)	150 kW	1.8 l	01/09→12/16						
E 350 CDI (207.322)	170 kW	3 l	01/09→06/11						
E 350 CGI (207.357)	215 kW	3.5 l	01/09→12/11						
E 500 (207.372)	285 kW	5.5 l	01/09→12/16						
<b>MERCEDES-BENZ - E-CLASS Sedan (W124)</b>								<b>06/93→06/95</b>	
E 200 (124.019)	100 kW	2 l	06/93→06/95				KH10039 ProKIT		
E 220 (124.022)	110 kW	2.2 l	06/93→06/95						
E 280 (124.028)	145 kW	2.8 l	06/93→06/95						
E 320 (124.032)	162 kW	3.2 l	06/93→06/95						
<b>MERCEDES-BENZ - E-CLASS Sedan (W210)</b>								<b>12/96→03/02</b>	
E 280 4-matic (210.081)	150 kW	2.8 l	12/96→03/02		02/97 -> 06/99		KH10394 ProKIT		
E 320 4-matic (210.082)	165 kW	3.2 l	06/97→03/02		-> 06/99		KH10394 ProKIT		
E 430 (210.070)	205 kW	4.3 l	06/97→03/02		09/97 ->		KH10166 ProKIT		
							KH10377 ProKIT		





**MERCEDES-BENZ - E-CLASS Sedan (W210)**
















**12/96→03/02**

E 55 AMG (210.074)	260 kW	5.4 l	08/97→03/02		<b>KH10377 ProKIT</b>
--------------------	--------	-------	-------------	--	-----------------------

**MERCEDES-BENZ - E-CLASS Sedan (W211, W212)**

**03/02→12/16**

E 180 (212.040)	115 kW	1.6 l	08/13→12/15		<b>KH20104 ProKIT</b>
E 200 (212.034)	135 kW	2 l	01/13→12/16		
E 200 NGT (211.042)	120 kW	1.8 l	03/04→12/08		
E 200 NGT (212.035)	115 kW	2 l	07/13→12/15		
E 200 NGT (212.041)	120 kW	1.8 l	03/11→12/15		
E 220 BlueTEC (212.001)	130 kW	2.2 l	05/14→12/15		
E 220 BlueTEC 4-matic (212.011)	125 kW	2.2 l	01/15→12/15		
E 220 CDI	120 kW	2.1 l	03/03→12/08		
E 220 CDI	120 kW	2.2 l	01/09→12/15		
E 240 4-matic (211.080)	130 kW	2.6 l	03/03→12/08		
E 250 (212.036)	155 kW	2 l	01/13→12/16		
E 250 CDI / BlueTEC 4-matic (212.082, 212.097)	150 kW	2.2 l	01/11→12/15		
E 250 CGI (212.047, 212.147)	150 kW	1.8 l	01/09→12/15		
E 270 CDI (211.016)	120 kW	2.7 l	03/02→12/08		
E 280 4-matic (211.092)	170 kW	3 l	01/06→12/08		
E 280 CDI 4-matic (211.084)	140 kW	3 l	03/05→12/08		
E 300 (212.054)	170 kW	3 l	01/09→12/13		
E 300 (212.055)	185 kW	3.5 l	07/11→12/15		
E 300 4-matic (212.080)	185 kW	3.5 l	07/11→12/15		
E 300 CDI / BlueTEC (212.020, 212.021, 212.027)	170 kW	3 l	03/11→12/15		
E 300 CDI (212.020)	150 kW	3 l	12/09→12/10		
E 300 Hybrid / BlueTEC Hybrid (212.098)	150 kW	2.2 l	12/11→12/16		
E 320 4-matic (211.082)	165 kW	3.2 l	03/03→12/08		
E 320 CDI 4-matic (211.089)	165 kW	3 l	03/05→12/08		
E 350 (212.056)	200 kW	3.5 l	01/09→12/13		
E 350 (212.059)	225 kW	3.5 l	09/11→12/15		
E 350 4-matic (211.087)	200 kW	3.5 l	03/05→12/08		
E 350 4-matic (212.087)	200 kW	3.5 l	01/09→08/11		
E 350 4-matic (212.088)	225 kW	3.5 l	09/11→12/15		
E 350 BlueTEC	185 kW	3 l	01/13→12/15		
E 350 BlueTEC (212.026)	190 kW	3 l	05/14→12/15		
E 350 BlueTEC 4-matic (212.094)	185 kW	3 l	01/13→12/15		
E 350 BlueTEC 4-matic (212.094)	190 kW	3 l	05/14→12/15		
E 350 CDI (212.023)	195 kW	3 l	03/11→12/15		
E 350 CDI 4-matic (212.089)	170 kW	3 l	09/09→08/11		
E 350 CDI 4-matic (212.093)	195 kW	3 l	03/11→12/15		
E 400 (212.061)	245 kW	3.5 l	07/14→12/15		
E 400 (212.065)	245 kW	3 l	01/13→12/16		
E 400 4-matic (212.067)	245 kW	3 l	01/13→12/16		
E 400 4-matic (212.099)	245 kW	3.5 l	07/14→12/15		
E 500 (212.073)	300 kW	4.7 l	09/11→12/15		
E 500 4-matic (211.083)	225 kW	5 l	10/03→12/08		
E 500 4-matic (211.090)	285 kW	5.5 l	04/06→12/08		
E 500 4-matic (212.090)	285 kW	5.5 l	01/09→12/11		
E 500 4-matic (212.091)	300 kW	4.7 l	09/11→12/15		
E 63 AMG (212.074)	386 kW	5.5 l	02/11→12/16		
E 63 AMG (212.074)	410 kW	5.5 l	02/11→12/16		
E 63 AMG (212.075)	430 kW	5.5 l	02/13→12/16		
E 63 AMG 4-matic (212.076)	430 kW	5.5 l	02/13→12/16		
E 63 AMG 4-matic (212.092)	410 kW	5.5 l	01/13→12/16		
E 200 CDI / BlueTEC (212.005, 212.006)	100 kW	2.2 l	01/09→12/15		<b>KH00015 ProKIT</b>
E 200 CGI (212.048, 212.148)	135 kW	1.8 l	08/09→12/15		<b>KH20104 ProKIT</b>
E 220 CDI / BlueTEC (212.001, 212.002)	125 kW	2.2 l	01/09→12/16		
E 250 CDI / BlueTEC (212.003, 212.004)	150 kW	2.2 l	01/09→12/16		
E 350 BlueTEC (212.024)	155 kW	3 l	01/09→12/15		
E 350 CDI (212.025)	170 kW	3 l	01/09→12/15		
E 350 CGI (212.057)	215 kW	3.5 l	01/09→08/11		
E 500 (212.072)	285 kW	5.5 l	01/09→12/11		
E 63 AMG (212.077)	386 kW	6.2 l	12/09→12/15		
E 200 CDI (211.004)	75 kW	2.2 l	07/02→12/08		<b>KH00015 ProKIT</b>
E 200 CDI (211.004)	90 kW	2.2 l	07/02→12/08		<b>KH20104 ProKIT</b>
E 200 CDI (211.007)	100 kW	2.1 l	04/06→12/08		
E 200 Kompressor (211.041)	135 kW	1.8 l	04/06→12/08		
E 200 Kompressor (211.042)	120 kW	1.8 l	11/02→12/08		
E 220 CDI (211.006)	100 kW	2.1 l	03/02→12/08		
E 220 CDI (211.006)	110 kW	2.1 l	03/02→12/08		
E 220 CDI (211.008)	125 kW	2.1 l	04/06→12/08		
E 230 (211.052)	150 kW	2.5 l	09/07→12/08		
E 240 (211.061)	130 kW	2.6 l	03/02→12/08		
E 270 CDI (211.016)	130 kW	2.7 l	03/02→12/08		
E 280 (211.054)	170 kW	3 l	03/05→12/08		

     					
<b>MERCEDES-BENZ - E-CLASS Sedan (W211, W212)</b>				<b>03/02→12/16</b>	
E 280 CDI (211.020)	140 kW	3 l	03/05→12/08		<b>KH00015</b> ProKIT
E 280 CDI (211.023)	130 kW	3.2 l	05/04→12/08		
E 300 BlueTEC (211.024)	155 kW	3 l	09/07→12/08		<b>KH20104</b> ProKIT
E 320 (211.065)	165 kW	3.2 l	03/02→12/08		
E 320 CDI (211.022)	165 kW	3 l	03/05→12/08		
E 320 CDI (211.026)	150 kW	3.2 l	11/02→12/08		
E 350 (211.056)	200 kW	3.5 l	03/05→12/08		
E 350 CGI (211.057)	215 kW	3.5 l	09/07→12/08		
E 400 CDI (211.028)	191 kW	4 l	02/03→12/08		
E 420 CDI (211.029)	231 kW	4 l	01/06→12/08		
E 500 (211.070)	225 kW	5 l	03/02→12/08		
E 500 (211.072)	285 kW	5.5 l	04/06→12/08		
E 55 AMG Kompressor (211.076)	350 kW	5.5 l	10/02→12/08		
E 63 AMG (211.077)	378 kW	6.2 l	03/06→12/08		
<b>MERCEDES-BENZ - E-CLASS T-Model (S124)</b>				<b>06/93→06/96</b>	
E 200 T (124.079)	100 kW	2 l	06/93→06/96		<b>KH10191</b> ProKIT
E 220 T (124.082)	110 kW	2.2 l	06/93→06/96		
E 250 TD (124.186)	83 kW	2.5 l	06/93→06/96		
E 250 Turbo D	93 kW	2.5 l	06/93→06/96		
E 280 T (124.088)	142 kW	2.8 l	06/93→06/96		
E 280 T (124.088)	145 kW	2.8 l	06/93→06/96		
E 300 T 4-matic (124.290)	132 kW	3 l	06/93→06/96		
E 300 TD (124.191)	100 kW	3 l	06/93→06/96		
E 300 T Turbo-D (124.193)	108 kW	3 l	06/93→06/96		
E 300 T Turbo-D 4-matic (124.393)	108 kW	3 l	06/93→06/96		
E 320 T (124.092)	162 kW	3.2 l	06/93→06/96		
E 36 T AMG (124.092)	200 kW	3.6 l	05/94→06/96		
<b>MERCEDES-BENZ - E-CLASS T-Model (S210)</b>				<b>06/96→03/03</b>	
E 200 T (210.235)	100 kW	2 l	06/96→08/00		<b>KH10377</b> ProKIT
E 200 T Kompressor (210.245)	137 kW	2 l	06/97→03/03		
E 200 T Kompressor (210.248)	120 kW	2 l	08/00→03/03		
E 220 T CDI (210.206)	92 kW	2.2 l	06/98→07/99		
E 220 T CDI (210.206)	105 kW	2.2 l	07/99→03/03		
E 230 T (210.237)	110 kW	2.3 l	06/96→06/97		
E 240 T (210.261)	125 kW	2.4 l	06/97→03/03		
E 240 T (210.262)	125 kW	2.6 l	08/00→03/03		
E 250 T D (210.210)	83 kW	2.5 l	06/96→07/99		
E 250 T Turbo-D (210.215)	110 kW	2.5 l	06/97→07/99		
E 270 T CDI (210.216)	125 kW	2.7 l	07/99→03/03		
E 280 T (210.263)	150 kW	2.8 l	12/96→03/03		
E 290 T Turbo-D (210.217)	95 kW	2.9 l	06/96→07/99		
E 300 T Turbo-D (210.225)	130 kW	3 l	12/96→07/99		
E 320 T (210.265)	165 kW	3.2 l	12/96→03/03		
E 320 T CDI (210.226)	145 kW	3.2 l	07/99→03/03		
E 420 T (210.272)	205 kW	4.2 l	06/96→06/97		
E 430 T 4-matic (210.283)	205 kW	4.3 l	05/99→03/03		
E 55 T AMG (210.274)	260 kW	5.4 l	08/97→03/03		
E 280 T 4-matic (210.281)	150 kW	2.8 l	12/96→03/03	 ; -> 06/99	<b>KH10394</b> ProKIT
E 320 T 4-matic (210.282)	165 kW	3.2 l	12/96→03/03		<b>KH10377</b> ProKIT
E 430 T (210.270)	205 kW	4.3 l	06/97→03/03	 ; 09/97 -> 06/02	<b>KH10166</b> ProKIT
					<b>KH10377</b> ProKIT
<b>MERCEDES-BENZ - E-CLASS T-Model (S211)</b>				<b>03/03→07/09</b>	
350 CGI (211.257)	215 kW	3.5 l	05/06→07/09		<b>KH00015</b> ProKIT
E 200 CDI (211.207)	100 kW	2.1 l	04/06→07/09		
E 200 Kompressor (211.241)	135 kW	1.8 l	04/06→07/09		
E 200 T Kompressor (211.242)	120 kW	1.8 l	03/03→07/09		
E 220 CDI (211.206)	100 kW	2.1 l	03/03→07/09		
E 220 T CDI (211.206)	110 kW	2.1 l	03/03→07/09		
E 220 T CDI (211.208)	125 kW	2.1 l	04/06→07/09		
E 230 T (211.252)	150 kW	2.5 l	05/07→07/09		
E 240 T (211.261)	130 kW	2.6 l	03/03→07/09		
E 270 T CDI (211.216)	130 kW	2.7 l	03/03→07/09		
E 280 T (211.254)	170 kW	3 l	03/05→07/09		
E 280 T CDI (211.220)	140 kW	3 l	03/05→07/09		
E 280 T CDI (211.223)	130 kW	3.2 l	05/04→07/09		
E 320 T (211.265)	165 kW	3.2 l	03/03→07/09		
E 320 T CDI (211.222)	165 kW	3 l	03/05→07/09		
E 320 T CDI (211.226)	150 kW	3.2 l	03/03→07/09		
E 350 T (211.256)	200 kW	3.5 l	03/05→07/09		
E 500 T (211.270)	225 kW	5 l	10/03→07/09		
E 500 T (211.272)	285 kW	5.5 l	04/06→07/09		
E 55 T AMG Kompressor (211.276)	350 kW	5.4 l	07/03→07/09		
E 63 AMG (211.277)	378 kW	6.2 l	03/06→07/09		





**MERCEDES-BENZ - E-CLASS T-Model (S212) 08/09→12/16**

E 200 CDI / BlueTEC (212.205, 212.206)	100 kW	2.2 l	11/09→12/16	; -> 11/10	<b>KH00015 ProKIT</b>
E 220 CDI / BlueTEC (212.202, 212.201)	125 kW	2.2 l	11/09→12/16		
E 250 CDI / BlueTEC (212.203, 212.204)	150 kW	2.2 l	11/09→12/16		
E 350 BlueTEC (212.224)	155 kW	3 l	11/09→12/13		
E 350 CDI (212.225)	170 kW	3 l	11/09→12/11		
E 350 CGI (212.257)	215 kW	3.5 l	11/09→12/11		
E 500 (212.272)	285 kW	5.5 l	11/09→12/11		
E 63 AMG (212.277)	386 kW	6.2 l	08/09→12/11		

**MERCEDES-BENZ - GLA-CLASS (X156) 12/13→**

GLA 180 (156.942)	90 kW	1.6 l	02/15→		<b>KH10368 ProKIT</b>
GLA 180 CDI / d (156.912)	80 kW	1.5 l	07/14→		
GLA 200 (156.943)	115 kW	1.6 l	12/13→		
GLA 200 CDI / d (156.908)	100 kW	2.2 l	12/13→		
GLA 200 CDI 4-matic (156.902)	100 kW	2.2 l	12/13→		
GLA 220 CDI (156.903)	125 kW	2.2 l	12/13→		
GLA 220 CDI 4-matic (156.905)	125 kW	2.2 l	12/13→		
GLA 250 (156.944)	155 kW	2 l	12/13→		
GLA 250 4-matic (156.946)	155 kW	2 l	12/13→		
GLA 45 AMG 4-matic (156.952)	265 kW	2 l	05/14→		

**MERCEDES-BENZ - GL-CLASS (X164) 09/06→12/12**

GL 320 CDI / 350 BlueTEC 4-matic (164.824, 164.825)	155 kW	3 l	12/09→08/12		<b>KH10140 ProKIT</b>
GL 320 CDI 4-matic (164.822)	165 kW	3 l	09/06→05/09		
GL 350 CDI 4-matic (164.822)	165 kW	3 l	05/09→08/12		
GL 350 CDI 4-matic (164.823)	195 kW	3 l	10/10→08/12		
GL 420 CDI 4-matic (164.828)	225 kW	4 l	09/06→05/09		
GL 450 4-matic (164.871)	250 kW	4.7 l	09/06→08/12		
GL 450 CDI 4-matic (164.828)	225 kW	4 l	05/09→08/12		
GL 500 4-matic (164.886)	285 kW	5.5 l	09/06→12/12		

**MERCEDES-BENZ - GLK-CLASS (X204) 06/08→12/15**

200 (204.934)	135 kW	2 l	08/13→06/15		<b>KH20104 ProKIT</b>
200 CDI (204.901)	100 kW	2.2 l	12/13→06/15		
200 CDI (204.901)	105 kW	2.2 l	07/10→06/15		
220 CDI (204.902)	120 kW	2.2 l	12/08→06/15		
220 CDI (204.902)	125 kW	2.2 l	12/08→06/15		
220 CDI 4-matic (204.984, 204.997)	125 kW	2.2 l	12/08→06/15		
220 CDI 4-matic (204.984)	120 kW	2.2 l	12/08→06/15		
250 (204.936)	155 kW	2 l	08/13→06/15		
250 4-matic (204.937)	155 kW	2 l	08/13→06/15		
250 CDI 4-matic (204.982, 204.904)	150 kW	2.2 l	09/09→06/15		
280 4-matic (204.981)	170 kW	3 l	06/08→06/09		
300 4-matic (204.981)	170 kW	3 l	07/09→12/15		
300 4-matic (204.990)	185 kW	3.5 l	09/09→06/15		
320 CDI 4-matic (204.983)	165 kW	3 l	06/08→06/15		
350 (204.956)	200 kW	3.5 l	04/09→06/15		
350 4-matic (204.987)	200 kW	3.5 l	06/08→04/11		
350 4-matic (204.988)	225 kW	3.5 l	06/08→06/15		
350 CDI 4-matic (204.992)	165 kW	3 l	07/09→01/10		
350 CDI 4-matic (204.992)	170 kW	3 l	02/10→06/15		
350 CDI 4-matic (204.993)	195 kW	3 l	07/12→06/15		

**MERCEDES-BENZ - HECKFLOSSE (W110, W111, W112) 08/59→02/68**































190 C (110.010)	59 kW	1.9 l	04/61→08/65		<b>KH00031 ProKIT</b>
190 DC (110.110)	40 kW	2 l	06/61→08/65		
200	70 kW	2 l	07/65→02/68		
200 (110.010)	61 kW	2 l	07/65→02/68		
200 D (110.110)	40 kW	2 l	07/65→02/68		
230	88 kW	2.3 l	06/66→12/67		
230 (110.011)	77 kW	2.3 l	07/65→02/68		
230 S (111.010)	88 kW	2.3 l	07/65→01/68		
220 B (111.010)	70 kW	2.2 l	08/59→08/65	; 01/64 ->	<b>KH00031 ProKIT</b>
220 SB (111.012)	81 kW	2.2 l	08/59→08/65		
220 SEB (111.014)	88 kW	2.2 l	08/59→08/65		

**MERCEDES-BENZ - HENSCHEL 2-t 02/73→12/77**































207 1.8	51 kW	1.8 l	02/73→12/77		<b>KH00055 ProKIT</b>
---------	-------	-------	-------------	--	-----------------------

**MERCEDES-BENZ - M-CLASS (W163) 02/98→06/05**










































ML 270 CDI (163.113)	120 kW	2.7 l	12/99→06/05	;	<b>KH10166 ProKIT</b>
ML 500 (163.175)	215 kW	5 l	09/01→06/05		
ML 320 (163.154)	160 kW	3.2 l	02/98→08/02	; ; 04/98 ->; AT	<b>KH10166 ProKIT</b>
ML 350	173 kW	3.7 l	02/03→06/05	; ; AT	<b>KH10166 ProKIT</b>

											
<b>MERCEDES-BENZ - M-CLASS (W163)</b>										<b>02/98→06/05</b>	
ML 350 (163.157)	180 kW	3.7 l	08/02→06/05							09/02 -> AT	KH10166 ProKIT
ML 430 (163.172)	200 kW	4.3 l	02/98→06/05							10/98 -> 08/01; AT	KH10166 ProKIT
ML 55 AMG (163.174)	255 kW	5.4 l	02/00→06/05							06/00 -> AT	KH10166 ProKIT
<b>MERCEDES-BENZ - M-CLASS (W164)</b>										<b>02/05→12/11</b>	
ML 280 CDI 4-matic (164.120)	140 kW	3 l	07/05→07/09								KH10140 ProKIT
ML 300 CDI 4-matic (164.120)	140 kW	3 l	07/09→12/11								
ML 300 CDI 4-matic (164.121)	150 kW	3 l	02/10→12/11								
ML 320 CDI 4-matic (164.122)	165 kW	3 l	07/05→07/09								
ML 350 4-matic (164.186)	200 kW	3.5 l	02/05→12/11								
ML 350 CDI 4-matic (164.122)	165 kW	3 l	07/09→12/11								
ML 350 CDI 4-matic (164.125, 164.124)	155 kW	3 l	09/09→12/11								
ML 350 CDI 4-matic (164.125, 164.124)	170 kW	3 l	02/10→12/11								
ML 500 4-matic (164.172)	285 kW	5.5 l	12/07→12/11								
ML 500 4-matic (164.175)	225 kW	5 l	07/05→12/11								
ML 420 CDI 4-matic (164.128)	225 kW	4 l	02/06→09/09								KH10140 ProKIT
ML 450 CDI 4-matic (164.128)	225 kW	4 l	09/09→12/11								
ML 63 AMG 4-matic (164.177)	375 kW	6.2 l	01/06→12/11								
<b>MERCEDES-BENZ - PAGODE (W113)</b>										<b>01/63→03/71</b>	
230 SL (113.042)	110 kW	2.3 l	01/63→01/67							01/65 ->	KH00031 ProKIT
250 SL (113.043)	110 kW	2.5 l	01/66→01/68								KH00031 ProKIT
280 SL (113.044)	125 kW	2.7 l	01/68→03/71								
<b>MERCEDES-BENZ - R-CLASS (W251, V251)</b>										<b>08/05→12/14</b>	
R 280 (251.054, 251.154)	170 kW	3 l	01/07→12/14								KH10140 ProKIT
R 280 CDI (251.121, 251.026, 251.126)	140 kW	3 l	05/06→12/12								
R 280 CDI 4-matic (251.020)	140 kW	3 l	05/06→12/12								
R 300 (251.054, 251.154)	170 kW	3 l	07/09→12/14								
R 300 CDI (251.021, 251.121, 251.026, 251.126)	140 kW	3 l	07/09→12/12								
R 300 CDI 4-matic (251.020)	140 kW	3 l	07/09→12/12								
R 320 CDI 4-matic (251.022, 251.122)	165 kW	3 l	01/06→07/10								
R 320 CDI 4-matic (251.125)	155 kW	3 l	01/06→12/12								
R 350 (251.056, 251.156)	200 kW	3.5 l	01/07→12/12								
R 350 4-matic (251.065, 251.165)	200 kW	3.5 l	08/05→12/12								
R 350 CDI 4-matic (251.022, 251.122)	165 kW	3 l	07/09→12/12								
R 350 CDI 4-matic (251.023, 251.123)	195 kW	3 l	08/10→12/14								
R 350 CDI 4-matic (251.124, 251.125)	155 kW	3 l	01/06→12/14								
R 350 CGI 4-matic (251.057, 251.157)	225 kW	3.5 l	10/11→12/14								
R 500 4-matic (251.072, 251.172)	285 kW	5.5 l	05/07→12/14								
R 500 4-matic (251.075, 251.175)	225 kW	5 l	08/05→12/14								
R 63 AMG 4-matic (251.077, 251.177)	375 kW	6.2 l	02/06→12/10								KH10140 ProKIT
<b>MERCEDES-BENZ - S-CLASS Coupe (C126)</b>										<b>10/81→08/85</b>	
380 SEC (126.043)	150 kW	3.8 l	10/81→07/85								KH00055 ProKIT
500 SEC (126.044)	170 kW	4.9 l	10/81→08/85								
<b>MERCEDES-BENZ - S-CLASS Coupe (C140, C215)</b>										<b>09/92→03/06</b>	
500 SEC / CL 500 (140.070)	235 kW	5 l	10/92→12/99							VIN A 212245 ->	KH10377 ProKIT
SEC/CL 600 (140.076)	290 kW	6 l	09/92→02/99								
CL 500 (215.375)	225 kW	5 l	03/99→03/06							01/00 -> AT	KH00020 ProKIT
											KH10377 ProKIT
CL 55 AMG (215.373)	265 kW	5.4 l	10/99→03/06							06/00 -> 09/02; AT	KH00020 ProKIT
											KH10377 ProKIT
CL 55 AMG Kompressor (215.374)	368 kW	5.5 l	06/02→03/06								KH10377 ProKIT
CL 600 (215.378)	270 kW	5.8 l	03/99→03/06								
CL 63 AMG	326 kW	6.3 l	09/01→03/06								
SEC/CL 420 (140.063)	205 kW	4.2 l	10/94→02/99								
CL 600 (215.376)	368 kW	5.5 l	09/02→03/06							10/02 -> AT	KH00020 ProKIT
											KH10377 ProKIT
CL 65 AMG (215.379)	450 kW	6 l	09/03→03/06							04/04 -> AT	KH00020 ProKIT






























									
<b>MERCEDES-BENZ - S-CLASS Coupe (C216)</b>									<b>05/06→12/13</b>
CL 500 (216.371)	285 kW	5.5 l	06/06→12/13		-> 06/09				<b>KH00072 ProKIT</b>
CL 65 AMG (216.379)	450 kW	6 l	10/06→12/10						
CL 500 (216.373)	320 kW	4.7 l	02/11→12/13						<b>KH20104 ProKIT</b>
CL 500 4-matic (216.386)	285 kW	5.5 l	02/08→12/13						
CL 500 4-matic (216.394)	320 kW	4.7 l	02/11→12/13						
CL 63 AMG (216.374)	400 kW	5.5 l	02/11→12/13						
CL 63 AMG (216.374)	420 kW	5.5 l	01/10→12/13						
CL 600 (216.376)	380 kW	5.5 l	05/06→12/13		-> 06/09				<b>KH00072 ProKIT</b>
CL 63 AMG (216.377)	386 kW	6.2 l	10/06→12/13						<b>KH20104 ProKIT</b>
<b>MERCEDES-BENZ - S-CLASS Saloon (W108, W109)</b>									<b>01/66→08/72</b>
250 S (108.012)	96 kW	2.5 l	01/66→12/69						<b>KH00031 ProKIT</b>
250 SE (108.014)	110 kW	2.5 l	01/66→12/67						
280 S (108.016)	103 kW	2.7 l	10/67→07/72						
280 SE, SEL (108.018, 108.019)	118 kW	2.7 l	01/68→08/72						
280 SE, SEL 3.5 (108.057, 108.058)	147 kW	3.5 l	03/71→08/72						
300 SEL (109.016)	118 kW	2.7 l	01/68→08/72						
300 SEL 3.5 (109.056)	147 kW	3.5 l	01/70→07/72						
300 SEL 6.3 (109.018)	184 kW	6.3 l	03/68→08/72						
<b>MERCEDES-BENZ - S-CLASS Sedan (W116, W126)</b>									<b>08/72→06/91</b>
260 SE (126.020)	118 kW	2.5 l	09/85→06/91						<b>KH00055 ProKIT</b>
260 SE (126.020)	122 kW	2.5 l	09/85→06/91						
280 S (126.021)	115 kW	2.7 l	12/79→07/85						
280 SE, SEL (126.022, 126.023)	136 kW	2.7 l	10/79→07/85						
300 SE, SEL (126.024, 126.025)	132 kW	3 l	01/86→06/91						
300 SE, SEL (126.024, 126.025)	138 kW	3 l	09/85→12/89						
350 SE, SEL (116.028, 116.029)	143 kW	3.5 l	03/76→03/80						
350 SE, SEL (116.028, 116.029)	147 kW	3.5 l	08/72→02/76						
350 SE, SEL (116.028, 116.029)	151 kW	3.5 l	03/76→03/80						
380 SE, SEL (126.032, 126.033)	160 kW	3.8 l	09/80→10/81						
380 SE, SEL (126.032)	150 kW	3.8 l	10/81→08/85						
280 S (116.020)	115 kW	2.7 l	08/72→07/80						<b>KH00055 ProKIT</b>
280 S (116.020)	118 kW	2.7 l	08/72→07/80						
280 SE, SEL (116.024)	130 kW	2.7 l	08/72→07/80						
280 SE, SEL (116.024)	136 kW	2.7 l	08/72→07/80						
450 SE, SEL (116.032)	165 kW	4.5 l	01/73→04/80						
450 SE, SEL (116.033)	160 kW	4.5 l	12/75→04/80						
450 SEL 6.9 (116.036)	210 kW	6.8 l	07/75→03/80						
500 SE, SEL (126.036)	170 kW	4.9 l	12/79→08/85						
500 SE, SEL (126.036)	177 kW	4.9 l	12/79→08/85						
<b>MERCEDES-BENZ - S-CLASS Sedan (W140)</b>									<b>02/91→10/98</b>
300 SE, SEL/S320 (140.032, 140.033)	170 kW	3.2 l	03/91→10/98						<b>KH00105 ProKIT</b>
300 SE 2.8 (140.028)	145 kW	2.8 l	01/93→10/98		VIN A 212245 ->				<b>KH10377 ProKIT</b>
400 SE, SEL/S420 (140.042, 140.043)	210 kW	4.2 l	02/91→10/98						
S 280 (140.028)	142 kW	2.8 l	02/93→10/98						
S 350 Turbo-D (140.134)	110 kW	3.4 l	01/93→10/98						
S 420 (140.042, 140.043)	205 kW	4.2 l	01/93→10/98						
500 SE, SEL (140.050, 140.051)	240 kW	5 l	02/91→10/98						<b>KH00105 ProKIT</b>
600 SE, SEL (140.056, 140.057)	300 kW	6 l	04/91→12/92		VIN A 212245 ->				<b>KH10377 ProKIT</b>
S 500 (140.050, 140.051)	235 kW	5 l	01/93→10/98						
S 600 (140.056, 140.057)	290 kW	6 l	01/93→10/98						
S 300 Turbo-D (140.135)	130 kW	3 l	05/96→10/98						<b>KH00105 ProKIT</b>
									<b>KH10377 ProKIT</b>
<b>MERCEDES-BENZ - S-CLASS Sedan (W220)</b>									<b>10/98→08/05</b>
S 280 (220.063, 220.163)	150 kW	2.8 l	10/98→08/05		12/98 -> 06/02				<b>KH00020 ProKIT</b>
									<b>KH10377 ProKIT</b>
S 320 (220.065, 220.165)	165 kW	3.2 l	10/98→08/05		12/98 -> 10/02				<b>KH00020 ProKIT</b>
									<b>KH10377 ProKIT</b>
S 320 CDI (220.025, 220.125)	150 kW	3.2 l	09/02→08/05						<b>KH10377 ProKIT</b>
S 350 4-matic (220.087, 220.187)	180 kW	3.7 l	06/03→08/05						
S 400 CDI (220.028, 220.128)	184 kW	4 l	06/00→08/05						
S 400 CDI (220.028, 220.128)	191 kW	4 l	06/03→08/05						
S 430 4-matic (220.083, 220.183)	205 kW	4.3 l	09/02→08/05						
S 500 4-matic (220.084, 220.184)	225 kW	5 l	09/02→08/05						
S 320 CDI (220.026, 220.126)	145 kW	3.2 l	08/99→09/02		10/99 ->				<b>KH00020 ProKIT</b>
									<b>KH10377 ProKIT</b>
S 350 (220.067, 220.167)	180 kW	3.7 l	09/02→08/05						<b>KH00020 ProKIT</b>
									<b>KH10377 ProKIT</b>



											
<b>MERCEDES-BENZ - S-CLASS Sedan (W220)</b>										<b>10/98→08/05</b>	
S 430 (220.070, 220.170)	205 kW	4.3 l	10/98→08/05		12/98 -> 09/02; AT					KH00020 ProKIT	
										KH10377 ProKIT	
S 500 (220.075, 220.175, 220.875)	225 kW	5 l	10/98→08/05		12/98 -> 01/02					KH00020 ProKIT	
					not for code: 220875					KH10377 ProKIT	
S 55 AMG (220.073, 220.173)	265 kW	5.5 l	04/99→08/05		06/00 -> 09/02					KH00020 ProKIT	
										KH10377 ProKIT	
S 55 AMG Kompressor (220.074, 220.174)	368 kW	5.5 l	06/02→08/05		Code: 220074					KH10377 ProKIT	
					Code: 220174; 						
S 600 (220.176)	368 kW	5.5 l	09/02→08/05							KH10377 ProKIT	
S 600 (220.878, 220.178)	270 kW	5.8 l	01/00→08/05		09/02 ->					KH00020 ProKIT	
					Code: 220178; 					KH10377 ProKIT	
S 65 AMG (220.179)	450 kW	6 l	03/04→08/05		04/04 ->; AT					KH00020 ProKIT	
<b>MERCEDES-BENZ - S-CLASS Sedan (W221)</b>										<b>10/05→12/13</b>	
S 250 CDI (221.003, 221.103)	150 kW	2.2 l	01/11→12/13							KH00072 ProKIT	
S 320 CDI (221.022, 221.122)	173 kW	3 l	12/05→06/09							KH20104 ProKIT	
S 350 BlueTec (221.026, 221.126)	190 kW	3 l	04/11→12/13								
S 350 BlueTEC 4-matic (221.083, 221.183)	190 kW	3 l	04/11→12/13								
S 350 CGI (221.057, 221.157)	225 kW	3.5 l	04/11→12/13								
S 420 CDI (221.028, 221.128)	235 kW	4 l	10/06→12/09								
S 63 AMG (221.074, 221.174)	400 kW	5.5 l	03/11→12/13								
S 280 (221.054)	170 kW	3 l	08/06→12/13							KH20104 ProKIT	
S 300 (221.054, 221.154)	170 kW	3 l	08/06→12/13								
S 300 (221.154)	180 kW	3 l	04/12→12/13								
S 320 CDI	155 kW	3 l	10/05→12/13								
S 320 CDI 4-matic (221.080, 221.180)	155 kW	3 l	10/05→12/13								
S 320 CDI 4-matic (221.080, 221.180)	173 kW	3 l	10/06→12/13								
S 350 4-matic (221.087, 221.187)	200 kW	3.5 l	02/08→12/13								
S 350 CDI	155 kW	3 l	06/09→12/13								
S 350 CDI	173 kW	3 l	06/09→12/13								
S 350 CDI 4-matic (221.080, 221.081)	155 kW	3 l	01/09→12/10								
S 350 CDI 4-matic (221.080, 221.180)	173 kW	3 l	06/09→07/13								
S 350 CGI 4-matic (221.082, 221.182)	225 kW	3.5 l	04/11→12/13								
S 450 4-matic (221.084, 221.184)	250 kW	4.7 l	12/05→12/13								
S 450 CDI (221.028, 221.128)	235 kW	4 l	01/09→12/13								
S 500 4-matic (221.086, 221.186)	285 kW	5.5 l	10/05→12/13								
S 500 CGI (221.073, 221.173)	320 kW	4.7 l	04/11→12/13								
S 500 CGI 4-matic (221.094, 221.194)	320 kW	4.7 l	03/11→12/13								
S 63 AMG (221.074, 221.174)	420 kW	5.5 l	02/12→12/13								
S 350 (221.056, 221.156)	200 kW	3.5 l	10/05→12/13		-> 06/09					KH00072 ProKIT	
S 400 Hybrid (221.095, 221.195)	205 kW	3.5 l	01/09→12/13							KH20104 ProKIT	
S 450 (221.070, 221.170)	250 kW	4.7 l	12/05→12/13								
S 500 (221.071, 221.171)	285 kW	5.5 l	10/05→12/13								
S 600 (221.176)	380 kW	5.5 l	12/05→12/13								
S 63 AMG (221.077, 221.177)	386 kW	6.2 l	10/06→12/13								
S 65 AMG (221.179)	450 kW	6 l	12/05→12/13							KH00072 ProKIT	
S 65 AMG (221.179)	463 kW	6 l	10/10→12/13								
<b>MERCEDES-BENZ - SL (R107)</b>										<b>05/71→12/85</b>	
280 SL (107.042)	130 kW	2.7 l	06/76→09/81		10/80 ->					KH00040 ProKIT	
280 SL (107.042)	136 kW	2.7 l	08/74→07/85								
380 SL (107.045)	160 kW	3.8 l	09/80→08/81								
350 SL (107.043)	143 kW	3.5 l	05/71→02/80		06/71 ->					KH00040 ProKIT	
450 SL (107.044)	160 kW	4.5 l	09/75→10/80		-> 08/80					KH00040 ProKIT	
450 SL (107.044)	165 kW	4.5 l	10/72→10/80		05/73 -> 08/80					KH00040 ProKIT	
500 SL (107.046)	170 kW	4.9 l	05/80→12/85		10/80 -> 10/85; AT					KH00040 ProKIT	
500 SL (107.046)	177 kW	4.9 l	05/80→12/81		10/80 ->; AT					KH00040 ProKIT	
<b>MERCEDES-BENZ - SL (R129)</b>										<b>03/89→12/01</b>	
280 (129.058)	142 kW	2.8 l	08/93→10/01							KH00085 ProKIT	
280 (129.059)	150 kW	2.8 l	05/98→10/01							KH10039 ProKIT	
300 SL (129.060)	140 kW	3 l	03/89→08/93								
300 SL-24 (129.061)	170 kW	3 l	03/89→07/93								
320 (129.063)	170 kW	3.2 l	09/93→10/01								
320 (129.064)	165 kW	3.2 l	05/98→10/01								
600 (129.076)	290 kW	6 l	07/92→10/01								



									
<b>MERCEDES-BENZ - SL (R129)</b>									
									<b>03/89→12/01</b>
500 (129.067)	235 kW	5 l	09/92→10/01						<b>KH00085 ProKIT</b>
500 (129.068)	225 kW	5 l	05/98→10/01						
500 SL (129.066)	240 kW	5 l	09/89→08/92						
55 AMG	260 kW	5.5 l	03/00→10/01						
60 AMG (129.067)	280 kW	6 l	05/97→10/01						
SL 73 AMG (129.076)	386 kW	7.3 l	01/99→12/01						
600 SL (129.076)	300 kW	6 l	02/92→08/94						<b>KH10039 ProKIT</b>
<b>MERCEDES-BENZ - SL (R230)</b>									
									<b>10/01→01/12</b>
280 (230.454)	170 kW	3 l	03/08→01/12		-> 03/11				<b>KH00015 ProKIT</b>
300 (230.454)	170 kW	3 l	04/09→01/12		-> 03/11				<b>KH20062 ProKIT</b>
350 (230.456)	200 kW	3.5 l	03/06→01/12						
350 (230.458)	232 kW	3.5 l	04/08→01/12						
350 (230.467)	180 kW	3.7 l	03/03→01/12						
500 (230.471)	285 kW	5.5 l	03/06→01/12						
500 (230.475)	225 kW	5 l	10/01→01/12						
55 AMG (230.472)	380 kW	5.4 l	03/06→01/12						
55 AMG Kompressor (230.474)	368 kW	5.5 l	06/02→01/12						
600 (230.476)	368 kW	5.5 l	04/03→01/12						
600 (230.477)	380 kW	5.5 l	03/06→01/12						
63 AMG (230.470)	386 kW	6.2 l	03/08→01/12						
55 AMG (230.474)	350 kW	5.4 l	10/01→06/02						<b>KH00015 ProKIT</b>
									<b>KH20062 ProKIT</b>
65 AMG (230.479)	450 kW	6 l	03/04→01/12		-> 03/11				<b>KH00015 ProKIT</b>
<b>MERCEDES-BENZ - SL (R231)</b>									
									<b>01/12→</b>
350 (231.457)	225 kW	3.5 l	02/12→						<b>KH20104 ProKIT</b>
400 (231.465)	245 kW	3 l	04/14→						
400 (231.466)	270 kW	3 l	01/16→						
500 (231.473)	320 kW	4.7 l	01/12→						
500 (231.473)	335 kW	4.7 l	04/15→						
63 AMG (231.474)	395 kW	5.5 l	01/12→						
63 AMG (231.474)	415 kW	5.5 l	01/12→						
63 AMG (231.474)	420 kW	5.5 l	07/18→						
63 AMG (231.474)	430 kW	5.5 l	04/14→						
<b>MERCEDES-BENZ - SL Coupe (C107)</b>									
									<b>01/72→09/81</b>
280 SLC (107.022)	130 kW	2.7 l	06/76→09/81		10/80 ->				<b>KH00040 ProKIT</b>
280 SLC (107.022)	136 kW	2.7 l	08/74→09/81						
380 SLC (107.025)	160 kW	3.8 l	07/80→08/81						
350 SLC (107.023)	143 kW	3.5 l	03/76→02/80						<b>KH00040 ProKIT</b>
350 SLC (107.023)	147 kW	3.5 l	01/72→02/76						
450 SLC (107.024)	160 kW	4.5 l	09/75→08/79						
450 SLC (107.024)	165 kW	4.5 l	01/73→11/75		05/73 ->				<b>KH00040 ProKIT</b>
<b>MERCEDES-BENZ - SLK (R170, R171)</b>									
									<b>09/96→02/11</b>
200 (170.435)	100 kW	2 l	09/96→03/00						<b>KH10039 ProKIT</b>
200 Kompressor (170.444)	120 kW	2 l	03/00→04/04						
200 Kompressor (170.445)	141 kW	2 l	10/96→03/00						
230 Kompressor (170.447)	142 kW	2.3 l	09/96→03/00						
230 Kompressor (170.449)	145 kW	2.3 l	03/00→04/04						
300 (171.454)	170 kW	3 l	04/09→02/11						
320 (170.465)	160 kW	3.2 l	03/00→04/04						
32 AMG Kompressor (170.466)	260 kW	3.2 l	03/01→04/04						
55 AMG (171.473)	294 kW	5.5 l	06/06→02/11						
200 Kompressor (171.442)	120 kW	1.8 l	03/04→02/11		-> 03/10				<b>KH00007 ProKIT</b>
200 Kompressor (171.445)	135 kW	1.8 l	01/08→02/11						<b>KH10039 ProKIT</b>
280 (171.454)	170 kW	3 l	01/05→02/11						
350 (171.456)	200 kW	3.5 l	06/04→02/11						
350 (171.458)	224 kW	3.5 l	01/08→02/11						
55 AMG (171.473)	265 kW	5.5 l	06/04→02/11						
<b>MERCEDES-BENZ - SPRINTER 2-t Bus / SPRINTER 2-t Platform/Chassis / SPRINTER 2-t Van (B901, B902)</b>									
									<b>01/95→05/06</b>
208 CDI	60 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: S231915				<b>KH00010 ProKIT</b>
211 CDI	80 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: Y245976				
213 CDI	95 kW	2.1 l	04/00→05/06						
214	105 kW	2.3 l	02/95→05/06						<b>KH10129 ProKIT</b>
214 (902.011, 902.012, 902.611, 902.612)	105 kW	2.3 l	02/95→05/06						
214 (902.071, 902.072, 902.671, 902.672)	105 kW	2.3 l	02/95→05/06						
216 CDI	115 kW	2.7 l	04/00→05/06						































**MERCEDES-BENZ - SPRINTER 2-t Bus / SPRINTER 2-t Platform/Chassis / 01/95→05/06**  
**SPRINTER 2-t Van (B901, B902)**



























208 D	58 kW	2.3 l	01/95→04/00	; 02/95 ->; → Axle number to: S231915 ; 02/95 ->; → Axle number to: Y245976	KH00010 ProKIT
				;	KH10129 ProKIT
208 D	58 kW	2.3 l	02/95→04/00	; → Axle number to: S231915	KH00010 ProKIT
212 D	90 kW	2.9 l	02/95→04/00	; → Axle number to: Y245976	
				;	KH10129 ProKIT
208 D	60 kW	2.3 l	09/96→04/00	;	KH10129 ProKIT
208 D	60 kW	2.3 l	10/96→04/00		
210 D	75 kW	2.9 l	01/97→04/00		
210 D	75 kW	2.9 l	03/97→04/00		
214 NGT	95 kW	2.3 l	02/95→05/06		

**MERCEDES-BENZ - SPRINTER 3,5-t Bus / SPRINTER 3,5-t Platform/Chassis / 06/06→**  
**SPRINTER 3,5-t Van (B906)**















309 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	65 kW	2.1 l	06/06→12/09		KH30094 ProKIT
309 CDI (906.631, 906.633, 906.635, 906.637)	65 kW	2.1 l	06/06→12/09	;	KH30140 ProKIT
310 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	70 kW	2.2 l	03/09→05/16		
310 CDI (906.631, 906.633, 906.635, 906.637)	70 kW	2.2 l	03/09→		
311 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	80 kW	2.1 l	06/06→12/09		
311 CDI (906.631, 906.633, 906.635, 906.637)	80 kW	2.1 l	06/06→12/09		
311 CDI (906.731, 906.733, 906.735)	80 kW	2.1 l	06/06→12/09		
311 CDI 4x4 (906.131, 906.133, 906.135, 906.231, 906.233,...	80 kW	2.1 l	02/08→12/09		
311 CDI 4x4 (906.631, 906.633, 906.635, 906.637)	80 kW	2.1 l	02/08→12/09		
311 CDI 4x4 (906.731, 906.733, 906.735)	80 kW	2.1 l	02/08→12/09		
313 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	95 kW	2.1 l	06/06→05/16		
313 CDI (906.631, 906.633, 906.635, 906.637)	95 kW	2.1 l	06/06→		
313 CDI 4x4 (906.131, 906.133, 906.135, 906.231, 906.233,...	95 kW	2.2 l	06/06→05/16		
313 CDI 4x4 (906.631, 906.633, 906.635, 906.637)	95 kW	2.2 l	05/09→		
315 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	110 kW	2.1 l	06/06→12/09		
315 CDI (906.631, 906.633, 906.635, 906.637)	110 kW	2.1 l	06/06→12/09		
315 CDI (906.731, 906.733, 906.735)	110 kW	2.1 l	06/06→12/09		
315 CDI 4x4 (906.131, 906.133, 906.135, 906.231, 906.233,...	110 kW	2.1 l	02/08→12/09		
315 CDI 4x4 (906.631, 906.633, 906.635, 906.637)	110 kW	2.1 l	02/08→12/09		
315 CDI 4x4 (906.731, 906.733, 906.735)	110 kW	2.1 l	02/08→12/09		
316 (906.133, 906.135, 906.233, 906.235)	115 kW	1.8 l	09/08→		
316 (906.635, 906.633)	115 kW	1.8 l	09/08→		
316 (906.733, 906.735)	115 kW	1.8 l	09/08→		
316 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	120 kW	2.2 l	03/09→		
316 CDI (906.631, 906.633, 906.635, 906.637)	120 kW	2.2 l	03/09→		
316 CDI (906.731, 906.733, 906.735)	120 kW	2.2 l	08/11→		
316 CDI 4x4 (906.131, 906.133, 906.135, 906.231, 906.233,...	120 kW	2.2 l	03/09→		
316 CDI 4x4 (906.631, 906.633, 906.635, 906.637)	120 kW	2.2 l	03/09→		
316 LGT (906.133, 906.135, 906.233, 906.235)	115 kW	1.8 l	09/08→		
316 NGT (906.133, 906.135, 906.233, 906.235)	115 kW	1.8 l	09/08→		
318 CDI (906.131, 906.133, 906.135, 906.231, 906.233,...	135 kW	3 l	06/06→12/09		
318 CDI (906.631, 906.633, 906.635, 906.637)	135 kW	3 l	06/06→12/09		

























									
<b>MERCEDES-BENZ - SPRINTER 3,5-t Bus / SPRINTER 3,5-t Platform/Chassis /</b>									
<b>SPRINTER 3,5-t Van (B906)</b>									
318 CDI 4x4 (906.131, 906.133, 906.135, 906.231, 906.233...)	135 kW	3 l	02/08→12/09						<b>KH30094</b> ProKIT
318 CDI 4x4 (906.631, 906.633, 906.635, 906.637)	135 kW	3 l	02/08→12/09						<b>KH30140</b> ProKIT
319 CDI / BlueTEC (906.131, 906.133, 906.135, 906.231,...	140 kW	3 l	03/09→						
319 CDI / BlueTEC (906.631, 906.633, 906.635, 906.637)	140 kW	3 l	03/09→						
319 CDI / BlueTEC (906.731, 906.733, 906.735)	140 kW	3 l	03/09→						
324 (906.133, 906.135, 906.233, 906.235, 906.132,...	190 kW	3.5 l	06/06→12/13						
324 (906.633, 906.635, 906.637)	190 kW	3.5 l	06/06→12/13						
324 (906.733, 906.735)	190 kW	3.5 l	06/06→12/13						
<b>MERCEDES-BENZ - SPRINTER 3-t Bus (B903)</b>									
<b>02/95→05/06</b>									
308 CDI	60 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: S231915				<b>KH00010</b> ProKIT
314 (903.071, 903.072, 903.073, 903.671, 903.672,...	105 kW	2.3 l	02/95→05/06		-> 02/06; → Axle number to: Y245976				
									<b>KH10129</b> ProKIT
308 D	58 kW	2.3 l	02/95→04/00		-> Axle number to: S231915				<b>KH00010</b> ProKIT
312 D 2.9	90 kW	2.9 l	02/95→04/00		-> Axle number to: Y245976				
									<b>KH10129</b> ProKIT
308 E (903.372)	40 kW		01/96→05/06						<b>KH10129</b> ProKIT
310 D 4x4	75 kW	2.9 l	05/97→08/02						
311 CDI	80 kW	2.1 l	04/00→05/06						
311 CDI 4x4	80 kW	2.1 l	08/02→05/06						
312 D 2.9 4x4	90 kW	2.9 l	05/97→08/02						
313 CDI	95 kW	2.1 l	04/00→05/06						
313 CDI 4x4	95 kW	2.1 l	08/02→05/06						
314 4x4 (903.672, 903.673)	105 kW	2.3 l	08/02→05/06						
314 NGT (903.072, 903.671, 903.672)	95 kW	2.3 l	02/95→05/06						
316 CDI	115 kW	2.7 l	04/00→05/06						
316 CDI 4x4	115 kW	2.7 l	08/02→05/06						
<b>MERCEDES-BENZ - SPRINTER 3-t Bus (B906)</b>									
<b>06/06→</b>									
210 CDI (906.711, 906.713)	70 kW	2.2 l	03/09→12/13						<b>KH30094</b> ProKIT
211 CDI (906.711, 906.713)	80 kW	2.1 l	06/06→12/09						<b>KH30140</b> ProKIT
215 CDI (906.711, 906.713)	110 kW	2.1 l	06/06→12/09						
216 (906.713)	115 kW	1.8 l	09/08→						
224 (906.713)	190 kW	3.5 l	06/06→12/13						
<b>MERCEDES-BENZ - SPRINTER 3-t Platform/Chassis (B903)</b>									
<b>02/95→05/06</b>									
308 CDI	60 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: S231915				<b>KH00010</b> ProKIT
311 CDI	80 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: Y245976				
314 (903.011, 903.012, 903.013, 903.022, 903.611,...	105 kW	2.3 l	02/95→05/06						<b>KH10129</b> ProKIT
316 CDI	115 kW	2.7 l	04/00→05/06						
308 D 2.3	58 kW	2.3 l	02/95→04/00		-> Axle number to: S231915				<b>KH00010</b> ProKIT
312 D 2.9	90 kW	2.9 l	02/95→04/00		-> Axle number to: Y245976				
									<b>KH10129</b> ProKIT
308 D 2.3	60 kW	2.3 l	11/96→04/00						<b>KH10129</b> ProKIT
310 D 2.9	75 kW	2.9 l	01/97→04/00						
311 CDI 4x4	80 kW	2.1 l	04/00→05/06						
313 CDI 4x4	95 kW	2.1 l	04/00→05/06						
314 4x4	105 kW	2.3 l	08/02→05/06						
314 NGT (903.611, 903.612)	95 kW	2.3 l	02/95→05/06						
316 CDI 4x4	115 kW	2.7 l	08/02→05/06						
313 CDI	95 kW	2.1 l	04/00→05/06		-> 02/06; → Axle number to: S231915				<b>KH00010</b> ProKIT
					-> 02/06; → Axle number to: Y245976				
									<b>KH10129</b> ProKIT

												
<b>MERCEDES-BENZ - SPRINTER 3-t Platform/Chassis (B906)</b>												<b>06/06→</b>
209 CDI (906.111, 906.113, 906.211, 906.213)	65 kW	2.1 l	06/06→12/09									<b>KH30094</b> ProKIT
210 CDI (906.111, 906.113, 906.211, 906.213)	70 kW	2.2 l	03/09→05/16									<b>KH30140</b> ProKIT
211 CDI (906.111, 906.113, 906.211, 906.213)	80 kW	2.1 l	06/06→12/09									
213 CDI (906.111, 906.113, 906.211, 906.213)	95 kW	2.1 l	06/06→12/09									
215 CDI (906.111, 906.113, 906.211, 906.213)	110 kW	2.1 l	06/06→12/09									
216 (906.113, 906.213)	115 kW	1.8 l	09/08→05/16									
216 CDI (906.111, 906.113, 906.211, 906.213)	120 kW	2.2 l	03/09→									
218 CDI (906.111, 906.113, 906.211, 906.213)	135 kW	3 l	06/06→12/09									
219 CDI / BlueTEC (906.111, 906.113, 906.211, 906.213)	140 kW	3 l	03/09→05/16									
224 (906.113, 906.213)	190 kW	3.5 l	06/06→12/13									
<b>MERCEDES-BENZ - SPRINTER 3-t Van (B903)</b>												<b>02/95→05/06</b>
308 CDI	60 kW	2.1 l	04/00→05/06									<b>KH00010</b> ProKIT
311 CDI	80 kW	2.1 l	04/00→05/06									
313 CDI (903.663, 903.662, 903.661)	95 kW	2.1 l	04/00→05/06									<b>KH10129</b> ProKIT
314	105 kW	2.3 l	02/95→05/06									
316 CDI	115 kW	2.7 l	04/00→05/06									
308 D 2.3	58 kW	2.3 l	02/95→04/00									<b>KH00010</b> ProKIT
312 D 2.9	90 kW	2.9 l	02/95→04/00									<b>KH10129</b> ProKIT
308 D 2.3	60 kW	2.3 l	02/95→04/00									<b>KH10129</b> ProKIT
310 D 2.9	75 kW	2.9 l	02/95→04/00									
311 CDI 4x4	80 kW	2.1 l	08/02→05/06									
312 D 2.9 4x4	90 kW	2.9 l	05/97→08/02									
313 CDI 4x4	95 kW	2.1 l	08/02→05/06									
314 4x4	105 kW	2.3 l	08/02→05/06									
314 NGT (903.661)	95 kW	2.3 l	02/95→05/06									
316 CDI 4x4	115 kW	2.7 l	02/01→05/06									
<b>MERCEDES-BENZ - SPRINTER 3-t Van (B906)</b>												<b>06/06→</b>
209 CDI (906.611, 906.613)	65 kW	2.1 l	06/06→12/09									<b>KH30094</b> ProKIT
210 CDI (906.611, 906.613)	70 kW	2.2 l	03/09→									<b>KH30140</b> ProKIT
211 CDI (906.611, 906.613)	80 kW	2.1 l	06/06→12/09									
213 CDI (906.611, 906.613)	95 kW	2.1 l	06/06→12/09									
215 CDI (906.611, 906.613)	110 kW	2.1 l	06/06→12/09									
216 (906.613)	115 kW	1.8 l	09/08→									
216 CDI (906.611, 906.613)	120 kW	2.2 l	03/09→									
218 CDI (906.611, 906.613)	135 kW	3 l	06/06→12/09									
219 CDI / BlueTEC (906.611, 906.613)	140 kW	3 l	03/09→									
224 (906.613)	190 kW	3.5 l	06/06→									
<b>MERCEDES-BENZ - SPRINTER 4-t Bus / SPRINTER 4-t Platform/Chassis / SPRINTER 4-t Van (B904)</b>												<b>02/95→05/06</b>
408 CDI	60 kW	2.1 l	04/00→05/06									<b>KH00010</b> ProKIT
408 D	58 kW	2.3 l	02/96→05/06									
410 D	75 kW	2.9 l	02/96→05/06									
410 D 4x4	75 kW	2.9 l	05/97→05/06									<b>KH00118</b> ProKIT
411 CDI	80 kW	2.1 l	04/00→05/06									<b>KH10129</b> ProKIT
412 D	85 kW	2.9 l	02/96→05/06									
412 D	90 kW	2.9 l	02/96→05/06									
413 CDI	95 kW	2.1 l	04/00→05/06									
414 (904.012, 904.013, 904.612, 904.613)	105 kW	2.3 l	02/95→05/06									
414 (904.062, 904.063, 904.662, 904.663)	105 kW	2.3 l	02/96→05/06									
416 CDI	115 kW	2.7 l	04/00→05/06									
408 CDI (904.662, 904.663)	60 kW	2.1 l	04/00→05/06									<b>KH10129</b> ProKIT
411 CDI (904.662, 904.663)	80 kW	2.1 l	04/00→05/06									
411 CDI 4x4	80 kW	2.1 l	04/00→05/06									
412 D	85 kW	2.9 l	02/96→05/06									
412 D 4x4	85 kW	2.9 l	05/97→05/06									
412 D 4x4	90 kW	2.9 l	05/97→05/06									
413 CDI (904.663, 904.662)	95 kW	2.1 l	04/00→05/06									
413 CDI 4x4	95 kW	2.1 l	04/00→05/06									
414 (904.662, 904.663)	105 kW	2.3 l	02/96→05/06									
414 4x4 (904.012, 904.013, 904.612, 904.613)	105 kW	2.3 l	05/97→05/06									



											
<b>MERCEDES-BENZ - SPRINTER 4-t Bus / SPRINTER 4-t Platform/Chassis / SPRINTER 4-t Van (B904)</b>										<b>02/95→05/06</b>	
414 4x4 (904.062, 904.063, 904.662, 904.663)	105 kW	2.3 l	05/97→05/06							<b>KH10129 ProKIT</b>	
416 CDI (904.662, 904.663)	115 kW	2.7 l	04/00→05/06								
416 CDI 4x4	115 kW	2.7 l	04/00→05/06								
410 D 4x4	75 kW	2.9 l	05/97→05/06							<b>KH00118 ProKIT</b>	
										<b>KH10129 ProKIT</b>	
<b>MERCEDES-BENZ - SPRINTER 5-t Platform/Chassis / SPRINTER 5-t Van (B906)</b>										<b>06/06→12/13</b>	
509 CDI (906.153, 906.155, 906.253, 906.255)	65 kW	2.1 l	06/06→12/09							<b>KH30094 ProKIT</b>	
509 CDI (906.653, 906.655, 906.657)	65 kW	2.1 l	06/06→12/09							<b>KH30140 ProKIT</b>	
511 CDI (906.153, 906.155, 906.253, 906.255)	80 kW	2.1 l	06/06→12/09								
511 CDI (906.653, 906.655, 906.657)	80 kW	2.1 l	06/06→12/09								
515 CDI (906.153, 906.155, 906.253, 906.255)	110 kW	2.1 l	06/06→12/09								
515 CDI (906.653, 906.655, 906.657)	110 kW	2.1 l	06/06→12/09								
518 CDI (906.153, 906.155, 906.253, 906.255)	135 kW	3 l	06/06→12/09								
518 CDI (906.653, 906.655, 906.657)	135 kW	3 l	06/06→12/09								
524 (906.653, 906.655, 906.657)	190 kW	3.5 l	06/06→12/13								
<b>MERCEDES-BENZ - T1 Bus (602)</b>										<b>06/89→02/96</b>	
308 D 2.3	58 kW	2.3 l	05/90→02/96						<b>Axle Number: 730.403-404-445-446</b>	<b>KH00055 ProKIT</b>	
308 D 2.3	60 kW	2.3 l	06/89→02/96								
310 D 2.9	70 kW	2.9 l	06/89→02/96								
310 D 2.9	72 kW	2.9 l	06/90→02/96								
<b>MERCEDES-BENZ - T1 Bus / T1 Platform/Chassis (B601, 601)</b>										<b>04/77→02/96</b>	
207 D 2.4	48 kW	2.4 l	04/77→12/82							<b>KH00055 ProKIT</b>	
207 D 2.4	53 kW	2.4 l	12/77→10/89								
207 D 2.4 (601.371, 601.372, 601.376, 601.377)	48 kW	2.4 l	05/77→12/82								
207 D 2.4 (601.371, 601.376, 601.377)	53 kW	2.4 l	07/82→01/90								
208 2.3	63 kW	2.3 l	05/77→12/82								
208 D 2.3	58 kW	2.3 l	11/88→02/96								
208 D 2.3	60 kW	2.3 l	10/88→02/96								
208 D 2.3	60 kW	2.3 l	06/89→02/96								
208 D 2.3 (601.371, 601.372, 601.376, 601.377)	58 kW	2.3 l	10/88→02/96								
209 D 2.9	65 kW	2.9 l	12/82→01/90								
210 2.3	63 kW	2.3 l	04/77→10/89								
210 2.3	70 kW	2.3 l	04/77→10/89								
210 2.3	70 kW	2.3 l	07/82→01/90								
210 2.3	77 kW	2.3 l	05/89→02/96								
210 D 2.8	70 kW	2.8 l	11/88→02/96								
210 D 2.8	72 kW	2.8 l	11/88→02/96								
210 D 2.9	70 kW	2.9 l	11/88→02/96								
<b>MERCEDES-BENZ - T1 Platform/Chassis (B602)</b>										<b>04/77→02/96</b>	
307 D 2.4	48 kW	2.4 l	04/77→01/83						<b>Axle Number: 730.403-404-445-446</b>	<b>KH00055 ProKIT</b>	
307 D 2.4	53 kW	2.4 l	06/82→01/90								
308 D 2.3	58 kW	2.3 l	06/89→02/96								
308 D 2.3	60 kW	2.3 l	06/89→02/96								
309 D 3.0	65 kW	3 l	10/82→01/90								
310 D 2.9	70 kW	2.9 l	06/89→02/96								
310 D 2.9	72 kW	2.9 l	06/89→02/96								
<b>MERCEDES-BENZ - T1 Van (601, 611)</b>										<b>06/82→02/96</b>	
207 D 2.4	53 kW	2.4 l	06/82→01/90							<b>KH00055 ProKIT</b>	
208 D 2.3	58 kW	2.3 l	11/88→02/96								
208 D 2.3	60 kW	2.3 l	10/88→02/96								
209 D 2.9	65 kW	2.9 l	12/82→01/90								
210 2.3	70 kW	2.3 l	07/82→02/96								
210 2.3	77 kW	2.3 l	05/89→02/96								
210 D 2.8	70 kW	2.8 l	10/88→02/96								
210 D 2.8	72 kW	2.8 l	10/88→02/96								



       					
<b>MERCEDES-BENZ - T1 Van (B602)</b>				<b>10/82→02/96</b>	
307 D 2.4	53 kW	2.4 l	10/82→01/90	 ; Axle Number: 730.403-404-445-446 <b>KH00055 ProKIT</b>	
308 D 2.3	58 kW	2.3 l	11/88→02/96		
308 D 2.3	60 kW	2.3 l	06/89→02/96		
309 D 3.0	65 kW	3 l	10/82→01/90		
310 D 2.9	70 kW	2.9 l	06/89→02/96		
310 D 2.9	72 kW	2.9 l	06/89→02/96		
<b>MERCEDES-BENZ - VALENTE Bus (W639)</b>				<b>09/03→08/14</b>	
109 CDI (639.701, 639.703)	70 kW	2.2 l	09/06→	 <b>KH10364 ProKIT</b>	
109 CDI (639.701)	65 kW	2.2 l	09/03→		
111 CDI (639.701, 639.703, 639.705)	80 kW	2.2 l	09/03→		
111 CDI (639.701, 639.703, 639.705)	85 kW	2.2 l	09/07→		
115 CDI (639.701, 639.703, 639.705)	110 kW	2.2 l	09/03→		
119 (639.701, 639.703, 639.705)	140 kW	3.2 l	09/03→		
120 CDI (639.701, 639.703, 639.705)	150 kW	3 l	07/06→		
122 (639.701, 639.703, 639.705)	160 kW	3.2 l	09/03→		
123 (639.701)	170 kW	3.7 l	06/04→07/08		
126 (639.701, 639.703, 639.705)	190 kW	3.5 l	09/07→		
109 CDI 4x4 (639.701)	70 kW	2.2 l	09/07→08/14	  <b>KH10364 ProKIT</b>	
111 CDI 4x4 (639.701, 639.703, 639.705)	80 kW	2.2 l	09/07→08/14		
115 CDI 4x4 (639.701, 639.705)	110 kW	2.2 l	09/07→08/14		
<b>MERCEDES-BENZ - Vaneo (414)</b>				<b>02/02→07/05</b>	
1.6 (414.700)	60 kW	1.6 l	02/02→07/05	 ; 06/02 -> <b>KH10147 ProKIT</b>	
1.6 (414.700)	75 kW	1.6 l	02/02→07/05		
1.7 CDI (414.700)	55 kW	1.7 l	02/02→07/05	 <b>KH10366 ProKIT</b>	
1.7 CDI (414.700)	67 kW	1.7 l	02/02→07/05		
1.9 (414.700)	92 kW	1.9 l	02/02→07/05		
<b>MERCEDES-BENZ - V-CLASS (638/2)</b>				<b>09/96→07/03</b>	
V 200 (638.214, 638.294)	95 kW	2 l	02/97→07/03	  <b>KH10145 ProKIT</b>	
V 200 CDI (638.294)	75 kW	2.2 l	03/99→07/03		
V 220 CDI (638.294)	90 kW	2.2 l	03/99→07/03		
V 230 (638.234, 638.294)	105 kW	2.3 l	10/96→07/03		
V 230 TD (638.274)	72 kW	2.3 l	09/96→07/03		
V 280 (638.244, 638.294)	128 kW	2.8 l	08/97→07/03		
<b>MERCEDES-BENZ - VIANO (W639)</b>					<b>09/03→</b>
3.2 (639.711, 639.811)	140 kW	3.2 l	09/03→	 <b>KH10364 ProKIT</b>	
3.2 (639.713, 639.813, 639.815)	160 kW	3.2 l	09/03→		
3.5 (639.811, 639.813, 639.815)	190 kW	3.5 l	09/07→		
3.7 (639.815)	170 kW	3.7 l	06/04→		
CDI 2.0 (639.711, 639.713, 639.811, 639.813, 639.815)	80 kW	2 l	09/03→		
CDI 2.0 (639.711, 639.713, 639.811, 639.813, 639.815)	85 kW	2 l	08/05→		
CDI 2.2 (639.711, 639.713, 639.811, 639.813, 639.815)	110 kW	2.2 l	09/03→		
CDI 3.0 (639.811, 639.813, 639.815)	150 kW	3 l	03/06→		
CDI 2.0 4-matic (639.713)	80 kW	2 l	07/05→		  <b>KH10364 ProKIT</b>
CDI 2.2 4-matic (639.711, 639.713, 639.811, 639.813,...)	110 kW	2.2 l	07/05→		
<b>MERCEDES-BENZ - VITO / MIXTO Van (W639)</b>				<b>09/03→</b>	
109 CDI (639.601, 639.603, 639.605)	65 kW	2.2 l	09/03→	 <b>KH10364 ProKIT</b>	
109 CDI (639.601, 639.603, 639.605)	70 kW	2.2 l	08/06→		
111 CDI (639.601, 639.603, 639.605)	80 kW	2.2 l	09/03→		
111 CDI (639.601, 639.603)	85 kW	2.2 l	09/07→		
115 CDI (639.601, 639.603, 639.605)	110 kW	2.2 l	09/03→		
119 (639.601, 639.603, 639.605)	140 kW	3.2 l	09/03→		
120 CDI (639.601, 639.603, 639.605)	150 kW	3 l	07/06→		
122 (639.601, 639.603, 639.605)	160 kW	3.2 l	09/03→		
123 (639.601)	170 kW	3.7 l	06/04→07/08		
126 (639.601, 639.603, 639.605)	190 kW	3.5 l	09/07→		
111 CDI 4x4 (639.601, 639.603, 639.605)	80 kW	2.2 l	09/07→		  <b>KH10364 ProKIT</b>
115 CDI 4x4 (639.601, 639.603, 639.605)	110 kW	2.2 l	07/06→		

































































**MERCEDES-BENZ - VITO Bus / VITO Van (W638)**

**02/96→07/03**

108 CDI 2.2 (638.094)	60 kW	2.2 l	03/99→07/03	 	<b>KH10145 ProKIT</b>
108 CDI 2.2 (638.194)	60 kW	2.2 l	03/99→07/03		
108 D 2.3 (638.064, 638.068)	58 kW	2.3 l	03/97→07/03		
108 D 2.3 (638.164)	58 kW	2.3 l	02/96→07/03		
110 CDI 2.2 (638.094)	75 kW	2.2 l	03/99→07/03		
110 CDI 2.2 (638.194)	75 kW	2.2 l	03/99→07/03		
110 D 2.3 (638.074, 638.078)	72 kW	2.3 l	03/97→07/03		
110 TD 2.3 (638.174)	72 kW	2.3 l	02/96→07/03		
112 CDI 2.2 (638.094)	90 kW	2.2 l	03/99→07/03		
112 CDI 2.2 (638.194)	90 kW	2.2 l	03/99→07/03		
113 2.0 (638.014, 638.094)	95 kW	2 l	03/97→07/03		
113 2.0 (638.114, 638.194)	95 kW	2 l	02/96→07/03		
114 2.3 (638.034, 638.094)	105 kW	2.3 l	03/97→07/03		
114 2.3 (638.134, 638.194)	105 kW	2.3 l	12/96→07/03		



     				
<b>MG - MAESTRO</b>				<b>10/84→09/90</b>
2.0 EFi	86 kW	2 l	10/84→09/90	 ; 11/88 -> KH10189 ProKIT
2.0 Turbo	112 kW	2 l	10/88→09/90	 ; 01/89 -> KH10189 ProKIT
<b>MG - MAGNETTE Sedan</b>				<b>03/61→09/68</b>
1.6	51 kW	1.6 l	03/61→09/68	 KH00121 ProKIT
<b>MG - METRO</b>				<b>10/82→09/90</b>
Turbo	69 kW	1.3 l	10/82→09/90	 ; 07/83 -> 09/84 KH00046 ProKIT
<b>MG - MGB GT</b>				<b>10/72→12/77</b>
3.5 (D1)	101 kW	3.5 l	10/72→12/77	 ; 08/73 -> 01/76 KH00126 ProKIT
<b>MG - MGC / MGC GT</b>				<b>01/67→09/69</b>
3.0	108 kW	3 l	01/67→09/69	 ; 10/67 -> 08/69 KH00126 ProKIT
<b>MG - MGF (RD)</b>				<b>03/95→03/02</b>
1.8 i VVC	118 kW	1.8 l	10/01→03/02	 ;  KH10189 ProKIT
1.6	82 kW	1.6 l	02/00→03/02	 ;  ; 02/01 -> KH10189 ProKIT
1.8 i 16V	88 kW	1.8 l	03/95→03/02	 ;  ; 09/95 -> KH10189 ProKIT
1.8 i VVC	107 kW	1.8 l	03/95→03/02	 ;  ; 11/95 -> KH10189 ProKIT
<b>MG - MG TF</b>				<b>03/02→12/09</b>
115	85 kW	1.6 l	03/02→12/09	 ;  KH10189 ProKIT
120	88 kW	1.8 l	03/02→12/09	 KH10189 ProKIT
160	118 kW	1.8 l	03/02→12/09	 ;  ; -> 12/05 KH10189 ProKIT
<b>MG - MG ZR</b>				<b>06/01→04/05</b>
105	76 kW	1.4 l	06/01→04/05	 ; -> 06/04;  ; ABS KH20144 ProKIT
120	86 kW	1.8 l	06/01→04/05	 ; ABS;  KH20145 ProKIT
160	118 kW	1.8 l	06/01→04/05	 ; ABS;  KH20145 ProKIT
2.0 TD	74 kW	2 l	06/01→04/05	 KH20145 ProKIT
<b>MG - MG ZS Hatchback / MG ZS Sedan</b>				<b>07/01→10/05</b>
120	86 kW	1.8 l	07/01→04/05	 ; VIN -> YD471063; MT;  ; ABS KH20145 ProKIT
120	86 kW	1.8 l	07/01→10/05	 ; VIN YD471064 ->;  ; ABS KH20145 ProKIT
180	130 kW	2.5 l	07/01→04/05	 ;  ; ABS KH20144 ProKIT
180	130 kW	2.5 l	07/01→10/05	 ; -> 06/04;  ; ABS KH20144 ProKIT
2.0 TD	74 kW	2 l	01/04→04/05	 KH20144 ProKIT
2.0 TD	74 kW	2 l	01/04→10/05	 KH20144 ProKIT
2.0 TD	83 kW	2 l	01/04→04/05	 KH20144 ProKIT
2.0 TD	83 kW	2 l	01/04→10/05	 KH20144 ProKIT
<b>MG - MG ZT Saloon / MG ZT-T T</b>				<b>06/01→10/05</b>
1.8 16V	88 kW	1.8 l	01/03→07/05	 KH10148 ProKIT
1.8 T 16V	118 kW	1.8 l	01/03→07/05	 KH20098 ProKIT
160	118 kW	2.5 l	06/01→07/05	 KH20098 ProKIT
160	118 kW	2.5 l	10/01→07/05	 KH20098 ProKIT
180	130 kW	2.5 l	02/02→10/05	 KH20098 ProKIT
190	140 kW	2.5 l	06/01→07/05	 KH20098 ProKIT
190	140 kW	2.5 l	10/01→07/05	 KH20098 ProKIT
2.0 CDTi	85 kW	2 l	06/02→09/03	 KH20098 ProKIT
2.0 CDTi	85 kW	2 l	06/02→07/05	 KH20098 ProKIT
2.0 CDTi	96 kW	2 l	11/02→07/05	 KH20098 ProKIT
260	191 kW	4.6 l	10/03→07/05	 KH20098 ProKIT
<b>MG - MIDGET</b>				<b>01/64→12/79</b>
1.1	41 kW	1.1 l	01/64→12/66	 ; -> 10/66 KH00122 ProKIT
1.3	48 kW	1.3 l	01/67→09/74	 KH00122 ProKIT
1.5	49 kW	1.5 l	09/74→12/79	 ; 10/74 -> KH00122 ProKIT
<b>MG - MONTEGO</b>				<b>04/84→09/90</b>
2.0 EFi	86 kW	2 l	04/84→09/90	 ; 11/88 ->; VIN 464731, 462777 -> KH10189 ProKIT
2.0 Turbo	110 kW	2 l	10/84→09/90	 ; 11/88 -> KH10189 ProKIT





**MINI - MINI (R50, R53)**

**06/01→09/06**

Cooper	85 kW	1.6 l	06/01→09/06	; 05/03 -> 07/06; Thread Size: M12	KH30006 ProKIT
Cooper S	120 kW	1.6 l	03/02→09/06	; 07/06 ->; Thread Size: M14	KH30032 ProKIT
One	55 kW	1.4 l	04/03→09/06	; -> 07/06; Thread Size: M12	KH30008 ProKIT
One	66 kW	1.6 l	06/01→09/06	; -> 07/06; Thread Size: M12	KH30008 ProKIT
Cooper S	125 kW	1.6 l	07/04→09/06	; -> 07/06; Thread Size: M12	KH30006 ProKIT
John Cooper Works	160 kW	1.6 l	03/06→09/06	; 07/06 ->; Thread Size: M14	KH30032 ProKIT
One D	55 kW	1.4 l	06/03→09/06	; -> 07/06; Thread Size: M12	KH30008 ProKIT
One D	65 kW	1.4 l	06/03→09/06	; -> 07/06; Thread Size: M12	KH30008 ProKIT
Works	155 kW	1.6 l	11/03→09/06	; Thread Size: M12	KH30006 ProKIT
S Works	149 kW	1.6 l	11/03→06/05	; Thread Size: M12	KH30008 ProKIT

**MINI - MINI / MINI CLUBMAN Wagon / MINI CLUBVAN (R56, R55)**

**09/06→06/14**

Cooper	85 kW	1.6 l	09/06→11/13	; Thread Size: M14	KH30007 ProKIT
Cooper	85 kW	1.6 l	03/10→06/14	; Thread Size: M14	KH30010 ProKIT
Cooper	88 kW	1.6 l	10/06→02/12	; Thread Size: M14	KH30010 ProKIT
Cooper	88 kW	1.6 l	10/07→12/13		
Cooper	90 kW	1.6 l	09/09→11/13		
Cooper	90 kW	1.6 l	03/10→06/14		
Cooper	90 kW	1.6 l	12/12→06/14		
Cooper D	80 kW	1.6 l	11/06→09/10		
Cooper D	80 kW	1.6 l	10/07→02/10		
Cooper D	82 kW	1.6 l	03/10→06/14		
Cooper D	82 kW	1.6 l	06/10→11/13		
Cooper D	82 kW	1.6 l	12/12→06/14		
Cooper D	82 kW	2 l	02/11→11/13		
Cooper D	82 kW	2 l	02/11→06/14		
Cooper S	120 kW	1.6 l	10/07→06/14		
Cooper S	120 kW	1.6 l	03/10→11/13		
Cooper S	128 kW	1.6 l	10/06→02/10		
Cooper S	128 kW	1.6 l	08/07→07/10		
Cooper S	135 kW	1.6 l	03/10→11/13		
Cooper S	135 kW	1.6 l	03/10→06/14		
Cooper S	147 kW	1.6 l	03/10→06/14		
Cooper SD	100 kW	2 l	02/11→11/13		
Cooper SD	100 kW	2 l	02/11→06/14		
Cooper SD	105 kW	2 l	02/11→11/13		
Cooper SD	105 kW	2 l	02/11→06/14		
Cooper S John Cooper Works	141 kW	1.6 l	11/06→02/10		
Cooper S John Cooper Works	141 kW	1.6 l	10/08→02/10		
Cooper S John Cooper Works	147 kW	1.6 l	01/12→11/13		
John Cooper Works	155 kW	1.6 l	11/07→11/13		
John Cooper Works	155 kW	1.6 l	11/07→06/14		
John Cooper Works GP	160 kW	1.6 l	09/12→11/13		
One	55 kW	1.4 l	03/09→03/10		
One	70 kW	1.4 l	11/06→03/10		
One	70 kW	1.4 l	03/09→02/10		
One	55 kW	1.6 l	03/10→11/13		
One	72 kW	1.6 l	03/10→11/13		
One	72 kW	1.6 l	03/10→06/14		
One	72 kW	1.6 l	12/12→06/14		
One D	66 kW	1.6 l	06/09→07/10		
One D	66 kW	1.6 l	03/10→06/14		
One D	66 kW	1.6 l	07/10→11/13		

**MINI - MINI Convertible (R52)**

**04/04→07/08**

Cooper	85 kW	1.6 l	04/04→07/08	; 07/06 ->; Thread Size: M14	KH30007 ProKIT
Cooper S	120 kW	1.6 l	07/04→11/07	; -> 07/06; Thread Size: M12	KH30006 ProKIT
Cooper S	125 kW	1.6 l	07/04→11/07	; 06/06 ->; Thread Size: M14	KH30032 ProKIT
John Cooper Works	155 kW	1.6 l	07/04→11/07	; -> 07/06; Thread Size: M12	KH30008 ProKIT
One	66 kW	1.6 l	07/04→11/07	; -> 07/06; Thread Size: M12	KH30008 ProKIT

**MINI - MINI Convertible / MINI Coupe / MINI Roadster (R57, R58, R59)**

**10/07→06/15**

Cooper	85 kW	1.6 l	12/08→06/15	; Thread Size: M14	KH30007 ProKIT
Cooper	85 kW	1.6 l	12/10→04/15	; Thread Size: M14	KH30010 ProKIT
Cooper	85 kW	1.6 l	11/11→04/15	; Thread Size: M14	KH30010 ProKIT
Cooper	88 kW	1.6 l	12/08→07/10		
Cooper	90 kW	1.6 l	03/10→06/15		
Cooper	90 kW	1.6 l	12/10→04/15		
Cooper	90 kW	1.6 l	11/11→04/15		
Cooper D	82 kW	1.6 l	05/09→11/13		
Cooper D	82 kW	2 l	02/11→05/15		
Cooper S	120 kW	1.6 l	10/07→06/15		
Cooper S	120 kW	1.6 l	12/10→04/15		
Cooper S	120 kW	1.6 l	11/11→04/15		
Cooper S	128 kW	1.6 l	04/08→07/10		
Cooper S	135 kW	1.6 l	02/10→06/15		
Cooper S	135 kW	1.6 l	12/10→04/15		
Cooper S	135 kW	1.6 l	11/11→04/15		








































































































**MINI - MINI Convertible / MINI Coupe / MINI Roadster (R57, R58, R59)**

**10/07→06/15**




















































Cooper S	147 kW	1.6 l	02/10→06/15	; Thread Size: M14	<b>KH30007</b> ProKIT
Cooper SD	100 kW	2 l	12/10→05/15	; Thread Size: M14	<b>KH30010</b> ProKIT
Cooper SD	100 kW	2 l	11/11→04/15		
Cooper SD	105 kW	2 l	06/09→05/15		
Cooper SD	105 kW	2 l	12/10→05/15		
Cooper SD	105 kW	2 l	11/11→04/15		
Cooper S JCW	147 kW	1.6 l	12/10→04/15		
Cooper S JCW	147 kW	1.6 l	11/11→04/15		
John Cooper Works	155 kW	1.6 l	08/08→05/15		
John Cooper Works	155 kW	1.6 l	12/10→05/15		
John Cooper Works	155 kW	1.6 l	11/11→04/15		
One	72 kW	1.6 l	09/09→06/15		














































									
<b>MITSUBISHI - ASX (GA_W_, XA, XB, XC, XD)</b>									<b>06/10→</b>
1.6 MIVEC (GA1W)	86 kW	1.6 l	06/10→		-> 11/10; Code: GA1W				KH10164 ProKIT
1.8 DI-D (GA6W)	85 kW	1.8 l	06/10→		-> 11/10; Code: GA6W				KH10164 ProKIT
1.8 DI-D (GA6W)	110 kW	1.8 l	06/10→						
1.8 DI-D 4WD (GA6W)	85 kW	1.8 l	06/10→		-> 11/10; Code: GA6W				KH10164 ProKIT
1.8 DI-D 4WD (GA6W)	110 kW	1.8 l	06/10→						KH30127 ProKIT
<b>MITSUBISHI - ASX Van (GA_W_)</b>									<b>06/10→</b>
1.8 DI-D 4WD	110 kW	1.8 l	06/10→						KH30127 ProKIT
<b>MITSUBISHI - CARISMA / CARISMA Saloon (DA_)</b>									<b>07/95→06/06</b>
1.6 (DA1A)	66 kW	1.6 l	07/95→06/06		03/99 -> 12/03				KH10398 ProKIT
					05/96 -> 12/97; (ABS)				KH20202 ProKIT
					(ABS)				KH20194 ProKIT
1.6 (DA1A)	66 kW	1.6 l	09/96→06/06		03/99 -> 12/03				KH10398 ProKIT
					-> 12/97; (ABS)				KH20202 ProKIT
					(ABS)				KH20194 ProKIT
1.6 (DA1A)	70 kW	1.6 l	12/98→06/06		03/99 -> 12/03				KH10398 ProKIT
					(ABS)				KH20194 ProKIT
1.6 (DA1A)	73 kW	1.6 l	05/97→06/06		03/99 -> 12/03				KH10398 ProKIT
					-> 03/99				KH10221 ProKIT
					-> 12/97; (ABS)				KH20202 ProKIT
					(ABS)				KH20194 ProKIT
1.6 (DA1A)	76 kW	1.6 l	09/00→06/06		-> 12/03				KH10398 ProKIT
1.8 GDI (DA2A)	90 kW	1.8 l	10/00→06/06		(ABS)				KH20194 ProKIT
1.9 DI-D (DA5A)	75 kW	1.9 l	09/00→06/06						
1.9 DI-D (DA5A)	85 kW	1.9 l	09/00→06/06						
1.8 (DA2A)	85 kW	1.8 l	07/95→07/97						KH10398 ProKIT
1.8 (DA2A)	85 kW	1.8 l	09/96→09/97						
1.8 MSX - 16V (DA2A)	103 kW	1.8 l	07/95→07/97						
1.8 16V GDI (DA2A)	92 kW	1.8 l	09/97→06/06		-> 12/03				KH10398 ProKIT
					11/97 ->; (ABS)				KH20194 ProKIT
1.9 DI-D (DA5A)	85 kW	1.9 l	09/00→06/06		-> 12/03; Code: DA5A				KH10398 ProKIT
					(ABS)				KH20194 ProKIT
1.9 TD (DA4A)	66 kW	1.9 l	10/96→09/00		03/99 -> 06/00				KH10398 ProKIT
					-> 12/97; (ABS)				KH20202 ProKIT
2.0 16V GT EVO VI/VII	206 kW	2 l	11/99→06/06		(ABS)				KH20194 ProKIT
<b>MITSUBISHI - CHALLENGER I (K7_, K9_, PA)</b>									<b>11/97→</b>
1.8 4WD (K90W)	84 kW	1.8 l	03/01→02/05						KH20041 ProKIT
2.5 TD (K94W)	98 kW	2.5 l	08/03→						
2.5 TD 4WD (K94W)	83 kW	2.5 l	11/97→10/98						
3.0 V6 (K96W)	125 kW	3 l	06/00→						
3.0 V6 4WD (K96W)	123 kW	3 l	03/03→						
2.5 TD (K94W, K74T)	85 kW	2.5 l	07/02→		-> 12/02				KH00011 ProKIT
2.5 TD (K94W)	73 kW	2.5 l	11/98→						KH20041 ProKIT
3.0 V6 (K96W)	130 kW	3 l	11/98→10/00						
<b>MITSUBISHI - COLT I (A15_A, RA)</b>									<b>09/81→01/84</b>
1.4 Turbo (A152A)	77 kW	1.4 l	09/81→01/84		01/82 ->				KH00077 ProKIT
					01/82 ->				KH00017 ProKIT
<b>MITSUBISHI - COLT II / COLT III / COLT III Saloon (C1_A, RB, RC, C5_A, RD, 11/83→05/92 RE, C1_A, C6_A, RD, RE)</b>									
1.2 (C65A)	44 kW	1.2 l	08/86→04/88						KH00077 ProKIT
1.2 EL, GL (C15A)	40 kW	1.2 l	02/84→09/86						
1.2 EL, GL (C15A)	44 kW	1.2 l	09/86→04/88						
1.2 GL (C15AS)	40 kW	1.2 l	01/84→10/86						
1.3 EL, GL (C11A)	49 kW	1.3 l	06/86→04/88						
1.3 GL (C61A)	44 kW	1.3 l	04/88→12/90						
1.5 GLX (C12A)	51 kW	1.5 l	09/85→04/88						
1.5 GLX (C12A)	55 kW	1.5 l	09/84→04/88						
1.5 GLX (C12AS)	51 kW	1.5 l	06/85→04/88						
1.5 GLX (C12AS)	55 kW	1.5 l	11/83→04/88						
1.6 GTi 16V (C53A)	91 kW	1.6 l	04/88→05/90						
1.6 Turbo ECi (C13A)	77 kW	1.6 l	07/86→04/88						
1.6 Turbo ECi (C13A)	92 kW	1.6 l	02/84→04/88						
1.8 Diesel (C14AS)	43 kW	1.8 l	01/84→09/86						
1.8 Diesel (C14AS)	44 kW	1.8 l	09/86→04/88						
1.8 GL Diesel (C14A)	43 kW	1.8 l	02/84→09/86						
1.8 GL Diesel (C14A)	44 kW	1.8 l	09/86→04/88						































































										
<b>MITSUBISHI - COLT II / COLT III / COLT III Saloon (C1_A, RB, RC, C5_A, RD, 11/83→05/92 RE, C1_A, C6_A, RD, RE)</b>										
1.3 (C51A)	51 kW	1.3 l	04/88→05/92		-> 12/91	KH00077 ProKIT				
1.3 12V (C51A)	55 kW	1.3 l	04/88→05/92							
1.5 Cat (C52A)	66 kW	1.5 l	07/90→05/92							
1.5 GLXi (C52A)	62 kW	1.5 l	04/88→05/92							
1.8 Diesel GLX (C54A)	44 kW	1.8 l	04/88→05/92							
1.8 GTi 16V Cat (C58A)	100 kW	1.8 l	06/90→05/92							
<b>MITSUBISHI - COLT IV (CA_A) 04/92→04/96</b>										
1.3 GLi 12V (CA1A)	55 kW	1.3 l	04/92→04/96			KH20194 ProKIT				
1.6 GLXi 16V (CA4A)	83 kW	1.6 l	04/92→04/96							
					-> 03/96	KH10221 ProKIT				
1.6 (CA4A)	66 kW	1.6 l	02/94→04/96			KH20194 ProKIT				
										
1.6 4WD (CC4A)	84 kW	1.6 l	08/93→08/95		KH10221 ProKIT					
1.8 GTi 16V (CA5A)	103 kW	1.8 l	04/92→04/96			KH20194 ProKIT				
										
					-> 07/95	KH10221 ProKIT				
<b>MITSUBISHI - COLT VI (Z3_A, Z2_A, RG) 06/04→06/12</b>										
1.1 (Z31A, Z32A)	55 kW	1.1 l	10/04→06/12		-> 06/07; Code: Z32A; 	KH20072 ProKIT				
					-> 09/08	KH10399 ProKIT				
						KH30186 ProKIT				
1.1 LPG	55 kW	1.1 l	10/04→06/12			KH30186 ProKIT				
1.3 (Z21A)	68 kW	1.3 l	10/04→06/12							
1.3 Flexfuel (Z35A)	70 kW	1.3 l	10/08→06/12							
1.3 LPG (Z33A)	70 kW	1.3 l	06/04→06/12							
1.5 Ralliart R	132 kW	1.5 l	02/10→06/12							
1.5 Ralliart R (Z27A)	120 kW	1.5 l	02/10→06/12							
1.3 (Z21A)	70 kW	1.3 l	06/04→06/12		-> 06/07; Code: Z34A; 	KH20072 ProKIT				
					-> 09/08	KH10399 ProKIT				
						KH30186 ProKIT				
1.5 (Z23A)	80 kW	1.5 l	06/04→06/12		-> 06/07; Code: Z36A; 	KH20072 ProKIT				
					-> 09/08	KH10399 ProKIT				
						KH30186 ProKIT				
1.5 CZT (Z37A)	110 kW	1.5 l	03/05→06/12		06/05 -> 09/08	KH10399 ProKIT				
						KH30186 ProKIT				
1.5 DI-D (Z38A)	50 kW	1.5 l	08/04→06/12		01/05 -> 09/08	KH10399 ProKIT				
					-> 06/07; Code: Z38A; 	KH20072 ProKIT				
						KH30186 ProKIT				
1.5 DI-D (Z39A)	70 kW	1.5 l	08/04→06/12		-> 06/07; Code: Z39A, Z39V; 	KH20072 ProKIT				
					-> 09/08	KH10399 ProKIT				
						KH30186 ProKIT				
<b>MITSUBISHI - COLT VI Convertible (RG) 05/06→07/09</b>										
1.5 (Z23)	80 kW	1.5 l	05/06→07/09		-> 07/08	KH10399 ProKIT				
1.5 Turbo (Z23)	110 kW	1.5 l	05/06→07/09			KH30186 ProKIT				
<b>MITSUBISHI - COLT Sedan (A15_, RC) 03/83→01/84</b>										
1.2 GLX (A171)	40 kW	1.2 l	03/83→01/84		KH00017 ProKIT					
1.4 GLX (A172)	51 kW	1.4 l	03/83→01/84							
1.4 Turbo (A156)	77 kW	1.4 l	03/83→01/84		Charge Type: Turbocharger/Compressor	KH00077 ProKIT				
					KH00017 ProKIT					
<b>MITSUBISHI - CORDIA (A21_A, AA, AB, AC) 10/82→12/86</b>										
1.6 GSL (A212A)	55 kW	1.6 l	10/82→12/86		-> 12/85	KH00077 ProKIT				
					-> 12/85	KH00017 ProKIT				
1.6 Turbo (A212A)	84 kW	1.6 l	10/82→05/85		KH00077 ProKIT					
1.6 Turbo (A212A)	85 kW	1.6 l	07/83→05/85		KH00017 ProKIT					
<b>MITSUBISHI - ECLIPSE II (D3_A) 12/95→04/99</b>										
2000 GT 16V	157 kW	2 l	12/95→04/99		KH20096 ProKIT					
<b>MITSUBISHI - EXPRESS II Bus (LO3_P/G, L0_2P, SA, SB, SC, SD, SE) 08/84→02/87</b>										
1.8 4WD (L035G)	60 kW	1.8 l	08/84→02/87		KH00011 ProKIT					
2.0 4WD (L037G)	65 kW	2 l	11/86→02/87							









       				
<b>MITSUBISHI - GALANT III Sedan / GALANT III Station Wagon / GALANT IV Station Wagon (A12_, A12_V, A16_V)</b> 01/77→05/84				
1.6 (A121)	55 kW	1.6 l	01/77→08/80	 KH00017 ProKIT
1.6 GL (A121V)	55 kW	1.6 l	01/79→08/80	
2.0 GLX	63 kW	2 l	01/77→08/80	
2.0 GLX (A123V)	72 kW	2 l	01/79→08/80	
1.6 GLX (A161V)	55 kW	1.6 l	09/80→05/84	 ; -> 12/83; Left-/right-hand drive vehicles: RHD KH00017 ProKIT
2.0 (A123)	72 kW	2 l	01/79→08/80	 ; Left-/right-hand drive vehicles: RHD KH00017 ProKIT
2.0 GLX (A163V)	75 kW	2 l	09/80→06/83	
<b>MITSUBISHI - GALANT V Sedan (E1_A)</b> 06/84→04/90				
2.0 GLS (E15A)	66 kW	2 l	06/86→04/90	 KH00017 ProKIT
2.0 GLS (E15A)	75 kW	2 l	06/84→04/90	 ; 01/85 -> KH00017 ProKIT
<b>MITSUBISHI - GALANT VI / GALANT VI Saloon (E3_A, HG, HH)</b> 11/87→10/92				
1.8 (E32A)	63 kW	1.8 l	11/87→08/90	 KH00017 ProKIT
1.8 (E32A)	66 kW	1.8 l	11/87→10/92	 ; -> 12/91; 
1.8 (E32A)	66 kW	1.8 l	11/88→10/92	
1.8 Turbo-D (E34A)	55 kW	1.8 l	12/87→10/92	 ; -> 12/90; 
1.8 Turbo-D (E34A)	55 kW	1.8 l	11/88→10/92	
<b>MITSUBISHI - GALANT VII / GALANT VII Saloon (E5_A, E7_A, E8_A, HJ, E5_A, E7_A, E8_A)</b> 11/92→08/96				
1.8 (E52A)	85 kW	1.8 l	02/94→08/96	 ; -> 05/96 KH20096 ProKIT
1.8 GLSI (E52A)	93 kW	1.8 l	11/92→08/96	 ; -> 05/96;  ; 
2.0 GLSI (E55A)	101 kW	2 l	11/92→08/96	
2.0 GLSTD (E57A)	66 kW	2 l	11/92→08/96	
2.0 V6-24 (E64A, E54A)	110 kW	2 l	11/92→08/96	
2.0 GLSI 4WD (E75A)	101 kW	2 l	11/92→08/96	 ; -> 05/96 KH20096 ProKIT
2.5 V6-24 4WD (E88A)	125 kW	2.5 l	11/92→08/96	
2.0 GLSTD (E57A)	66 kW	2 l	11/92→08/96	 KH20096 ProKIT
				 ; 
<b>MITSUBISHI - GALANT VIII Estate / GALANT VIII Sedan (EA_)</b> 09/96→10/04				
2.0 (EA2A)	98 kW	2 l	09/00→10/04	 ; -> 05/03 KH20096 ProKIT
2.4 GDI (EA3A)	106 kW	2.4 l	09/00→10/04	 ; -> 05/03;  ; 
2.0 (EA2A)	100 kW	2 l	09/96→09/00	 ; 10/96 -> 02/00 KH20096 ProKIT
2.0 (EA2W)	100 kW	2 l	09/96→09/00	
2.0 TDI (EA6A)	66 kW	2 l	09/96→10/04	 ; 10/96 -> 02/00;  ; 
2.0 TDI (EA6W)	66 kW	2 l	09/96→10/03	
2.0 (EA2W)	98 kW	2 l	09/00→10/03	 ; -> 09/02 KH20096 ProKIT
2.4 GDI (EA3W)	106 kW	2.4 l	09/00→10/03	 ; -> 09/02;  ; 
2.4 GDI (EA3A)	110 kW	2.4 l	02/99→09/00	 ; -> 02/00 KH20096 ProKIT
2.4 GDI (EA3W)	110 kW	2.4 l	02/99→10/03	 ; -> 02/00;  ; 
2.5 V6 24V (EA5A)	118 kW	2.5 l	09/00→10/04	 ; -> 05/03 KH20096 ProKIT
				 ; -> 05/03 KH20193 ProKIT
2.5 V6 24V (EA5A)	120 kW	2.5 l	09/96→09/00	 ; 10/96 -> 02/00 KH20096 ProKIT
2.5 V6 24V (EA5W)	120 kW	2.5 l	09/96→09/00	 ; 10/96 -> 02/00 KH20193 ProKIT
2.5 V6 24V (EA5W)	118 kW	2.5 l	09/00→10/03	 ; -> 09/02 KH20096 ProKIT
				 ; -> 09/02 KH20193 ProKIT
<b>MITSUBISHI - GRANDIS (NA_W, BA)</b> 04/04→12/11				
2.0 DI-D (NA8W)	100 kW	2 l	09/05→03/10	 KH30021 ProKIT
2.0 DI-D (NA8W)	103 kW	2 l	02/07→03/10	
2.4 MIVEC (NA4W)	121 kW	2.4 l	04/04→12/11	
2.4 MIVEC (NA4W)	130 kW	2.4 l	04/04→12/11	
<b>MITSUBISHI - i-MIEV (HA_)</b> 01/06→				
0.7 (HA1W)	38 kW	0.7 l	02/07→	 KH20005 ProKIT
0.7 (HA1W)	42 kW	0.7 l	01/06→	
MiEV (HA4W)	35 kW		07/09→	
MiEV (HA4W)	47 kW		07/09→	
MiEV (HA4W)	49 kW		02/11→	
<b>MITSUBISHI - LANCER I Sedan / LANCER II Sedan (A7_, A17_)</b> 01/78→02/83				
1.2 (A171)	40 kW	1.2 l	01/80→12/81	 KH00017 ProKIT
1.2 (A75A)	40 kW	1.2 l	01/78→09/79	
1.4 (A72A)	50 kW	1.4 l	01/78→09/79	
1.6 (A73A)	60 kW	1.6 l	01/78→09/79	

												
<b>MITSUBISHI - LANCER I Sedan / LANCER II Sedan (A7_, A17_)</b>											<b>01/78→02/83</b>	
1.4 GLX (A172)	50 kW	1.4 l	09/79→02/83		-> 12/82						KH00017 ProKIT	
1.6 (A174)	60 kW	1.6 l	09/79→02/83									
1.6 (A174)	62 kW	1.6 l	01/81→02/83									
<b>MITSUBISHI - LANCER III Station Wagon / LANCER IV / LANCER IV Hatchback (C1_V, C3_V, C6_A, C7_A, CA, CB)</b>											<b>09/85→05/94</b>	
1.3 (C61A)	44 kW	1.3 l	04/88→05/92							KH00077 ProKIT		
1.3 (C61A)	51 kW	1.3 l	08/88→05/92									
1.3 12V (C61A)	55 kW	1.3 l	07/90→06/92									
1.5 (C62A)	62 kW	1.5 l	04/88→05/92									
1.5 12V (C62A)	66 kW	1.5 l	05/89→05/92									
1.5 12V (C62A)	66 kW	1.5 l	06/90→05/92									
1.8 4WD (C37V)	61 kW	1.8 l	01/87→08/89									
1.8 4WD (C37V)	66 kW	1.8 l	01/87→12/87									
1.8 D (C64A)	44 kW	1.8 l	04/88→05/92									
1.8 GLX Diesel (C64A)	44 kW	1.8 l	04/88→05/92									
1.8 GTi 16V (C68A)	100 kW	1.8 l	11/89→05/92									
1.3 12V (C61A)	55 kW	1.3 l	06/92→05/94							KH00077 ProKIT		
1.6 16V (C76A, C66A)	83 kW	1.6 l	06/92→05/94		ABS						KH20194 ProKIT	
1.5 (C12V)	51 kW	1.5 l	09/85→08/89							KH00077 ProKIT		
1.5 (C12V)	55 kW	1.5 l	09/85→12/87							KH00017 ProKIT		
1.5 (C12V)	61 kW	1.5 l	09/88→12/90									
1.5 12V (C12V)	66 kW	1.5 l	09/90→12/91									
1.8 4WD (C37V)	63 kW	1.8 l	03/89→12/90									
1.8 4WD (C37V)	69 kW	1.8 l	08/90→06/92		-> 12/90						KH00077 ProKIT	
										KH00017 ProKIT		
1.8 D (C14V)	43 kW	1.8 l	09/85→09/86		01/86 ->						KH00077 ProKIT	
1.8 D (C14V)	44 kW	1.8 l	08/86→06/92		-> 11/88						KH00077 ProKIT	
<b>MITSUBISHI - LANCER V Sedan / LANCER V Station Wagon / LANCER VI Sedan (CB_A, CD_A, CE_A, CB_W, CD_W, CC, CE, CJ_, CP_)</b>											<b>06/92→10/03</b>	
1.3 (CB1A)	55 kW	1.3 l	06/92→12/96		ABS						KH20194 ProKIT	
1.6 (CB4A)	66 kW	1.6 l	02/94→12/96									
1.6 16V (CB4A)	83 kW	1.6 l	06/92→12/96									
1.6 16V 4WD (CD4W)	83 kW	1.6 l	12/92→10/03									
2.0 Diesel (CB8A)	50 kW	2 l	06/92→12/96									
1.3 12V (CK1A)	55 kW	1.3 l	12/95→08/03		12/98 ->						KH10158 ProKIT	
1.6 16V (CB4W)	83 kW	1.6 l	12/92→10/03									
1.6 16V (CK4A)	66 kW	1.6 l	12/95→08/03									
1.6 16V 4WD (CD4A)	83 kW	1.6 l	06/92→12/96							KH10221 ProKIT		
EVO V (CP9A, CT9A)	206 kW	2 l	01/98→12/98							KH20096 ProKIT		
<b>MITSUBISHI - LANCER VII (CS_A, CG, CH, CJ, CT_A)</b>											<b>09/03→12/13</b>	
1.3	60 kW	1.3 l	09/03→12/13		-> 06/07; Code: CS1A						KH10365 ProKIT	
										KH20132 ProKIT		
										KH20140 ProKIT		
1.6 (CS3A)	72 kW	1.6 l	09/03→12/13		-> 06/07						KH10365 ProKIT	
										KH20132 ProKIT		
										KH20140 ProKIT		
2.0 (CS9A)	99 kW	2 l	12/03→12/13		-> 11/10						KH10365 ProKIT	
										KH20132 ProKIT		
										KH20140 ProKIT		
<b>MITSUBISHI - LANCER VII Estate (CS_W, CT_W, CH)</b>											<b>09/03→10/08</b>	
1.6	72 kW	1.6 l	09/03→10/08		-> 06/07; Code: CS3W						KH10365 ProKIT	
										KH20132 ProKIT		
										KH20140 ProKIT		
2.0 (CS9W)	99 kW	2 l	09/03→12/07		Code: CS9W						KH10365 ProKIT	
										KH20132 ProKIT		
										KH20140 ProKIT		
<b>MITSUBISHI - LANCER VIII (CY_A, CZ_A, CJ)</b>											<b>01/08→12/15</b>	
1.5	80 kW	1.5 l	06/08→		-> 11/10; Code: CY2A						KH10164 ProKIT	
1.8 (CY3A, CY6A)	103 kW	1.8 l	05/10→		-> 11/10; Code: CY3A						KH10164 ProKIT	
1.8 (CY3A, CY6A)	105 kW	1.8 l	02/08→									
1.8 DI-D	85 kW	1.8 l	05/10→		-> 11/10; Code: CY9A						KH10164 ProKIT	
1.8 DI-D (CY9A)	110 kW	1.8 l	06/10→		-> 11/10						KH10164 ProKIT	
2.0 DI-D (CY8A)	103 kW	2 l	01/08→		-> 11/10; Code: CY8A						KH10164 ProKIT	

































     				
<b>MITSUBISHI - LANCER VIII (CY_A, CZ_A, CJ)</b>				<b>01/08→12/15</b>
EVO X (CZ4A)	217 kW	2 l	06/08→12/15	 KH30163 ProKIT
EVO X - FQ330 (CZ4A)	242 kW	2 l	03/08→06/15	 KH30127 ProKIT
<b>MITSUBISHI - LANCER VIII Sportback (CX_A, CJ)</b>				<b>06/08→</b>
1.5	80 kW	1.5 l	06/08→	 ; -> 09/11; Code: CX2A KH10164 ProKIT
1.8 (CX3A)	105 kW	1.8 l	06/08→	 ; -> 09/11 KH10164 ProKIT
<b>MITSUBISHI - LANCER CELESTE Coupe (A7_)</b>				<b>10/75→06/81</b>
1.6 ST (A73A)	54 kW	1.6 l	01/77→06/81	 ; -> 12/80 KH00017 ProKIT
2.0 GSR (A78A)	71 kW	2 l	01/77→06/81	
2.0 GSR (A78A)	77 kW	2 l	01/79→06/81	
2.0 GSR (A78A)	66 kW	2 l	10/75→06/81	 ; 01/76 -> 12/80 KH00017 ProKIT
<b>MITSUBISHI - MIRAGE V (CJ_, CP_)</b>				<b>05/96→09/03</b>
1300 (CJ1A)	60 kW	1.3 l	06/00→09/03	 ;  ;  KH20194 ProKIT
				 ;  KH10158 ProKIT
				 ; -> 06/03;  KH20202 ProKIT
1300 GL, GLX (CJ1A)	55 kW	1.3 l	05/96→06/00	 ;  ;  KH20194 ProKIT
1600 GLX (CJ4A)	66 kW	1.6 l	05/96→09/00	 ;  KH10158 ProKIT
				 ; 12/98 -> KH10221 ProKIT
				 ; -> 11/98 KH20202 ProKIT
				 ;  KH20194 ProKIT
1600 (CJ4A)	76 kW	1.6 l	09/00→09/03	 ;  ;  KH10158 ProKIT
				 ;  KH20202 ProKIT
				 ; -> 06/03;  ; Code: CJ4A KH20202 ProKIT
<b>MITSUBISHI - MIRAGE VI Hatchback / MIRAGE VI Saloon (A0_A, A1_A, LA)</b>				<b>01/12→</b>
1.0 (A05A)	52 kW	1 l	05/12→	 ;  KH10032 ProKIT
1.2	57 kW	1.2 l	07/14→	
1.2 (A03A)	57 kW	1.2 l	01/12→	
1.2 (A03A)	59 kW	1.2 l	10/12→	
1.2 (A13A)	59 kW	1.2 l	10/13→	
<b>MITSUBISHI - NIMBUS (D0_V/W, UA, UB, UC)</b>				<b>01/84→04/91</b>
1.8 4WD (D05V, D05W)	66 kW	1.8 l	10/87→08/88	 KH00077 ProKIT
2.0 GLXi (D04W)	74 kW	2 l	06/88→04/91	
1.8 GLX (D05V, D05W)	66 kW	1.8 l	01/84→12/88	 KH00077 ProKIT
2.0 GLX (D04W)	62 kW	2 l	06/86→05/88	 KH00017 ProKIT
1.8 TD (D09V, D09W)	55 kW	1.8 l	06/86→04/91	 ; -> 01/90 KH00077 ProKIT
				 ; -> 01/90 KH00017 ProKIT
<b>MITSUBISHI - NIMBUS (N9_W, N8_W, UG)</b>				<b>10/98→12/04</b>
2.0	98 kW	2 l	10/98→12/04	 ; -> 01/04 KH20096 ProKIT
2.4 GDI 4WD (N94W)	110 kW	2.4 l	10/98→12/04	
2.4 GDI (N84W)	108 kW	2.4 l	09/00→12/04	 ; -> 01/04 KH20096 ProKIT
				 ;  ; Code: N84W; -> 01/04 KH20187 ProKIT
				 ;  KH20188 ProKIT
2.4 GDI (N84W)	110 kW	2.4 l	10/98→12/04	 ; -> 01/04 KH20096 ProKIT
				 ; -> 01/04;  KH20187 ProKIT
				 ;  KH20188 ProKIT
2.4 GDI 4WD (N94W)	108 kW	2.4 l	09/00→12/04	 ; -> 04/02 KH20096 ProKIT
<b>MITSUBISHI - OUTLANDER I Wagon (CU_W, ZE, ZF)</b>				<b>01/02→09/07</b>
2.0 (CU2W)	100 kW	2 l	05/03→10/06	 KH10365 ProKIT
				 KH20140 ProKIT
2.0 4WD (CU2W)	100 kW	2 l	05/03→10/06	 KH10365 ProKIT
2.0 Turbo 4WD (CU2W)	148 kW	2 l	04/04→10/06	
2.4 4WD (CU5W)	118 kW	2.4 l	11/03→09/07	
2.0 Turbo-R 4WD (CU2W)	177 kW	2 l	01/02→10/06	 ; Code: CU2W KH10365 ProKIT
2.4 4WD (CU4W)	102 kW	2.4 l	05/03→10/06	 ; 09/03 ->; Code: CU5W KH10365 ProKIT
2.4 4WD (CU5W)	119 kW	2.4 l	05/03→09/07	 ; 09/03 -> KH10365 ProKIT
<b>MITSUBISHI - OUTLANDER II Wagon (CW_W, ZG, ZH)</b>				<b>11/06→11/12</b>
2.0 DI-D (CW8W)	103 kW	2 l	02/07→11/12	 ; -> 02/10; Code: CW8W KH10164 ProKIT
				 KH30127 ProKIT



































     					
<b>MITSUBISHI - OUTLANDER II Wagon (CW_W, ZG, ZH)</b>					<b>11/06→11/12</b>
2.2 DI-D	130 kW	2.2 l	11/06→11/12	; -> 02/10; Code: CW8W	KH10164 ProKIT
2.2 DI-D 4WD	115 kW	2.2 l	08/07→11/12	; -> 02/10; Code: CW7W	KH10164 ProKIT
2.2 DI-D 4WD	130 kW	2.2 l	11/06→11/12		
2.4 4WD (CW5W)	125 kW	2.4 l	09/07→11/12	; -> 02/10	KH10164 ProKIT
					KH30127 ProKIT
<b>MITSUBISHI - PAJERO I Canvas Top / PAJERO I Wagon / PAJERO II Canvas Top / PAJERO II Wagon (L04_G, L04_G, L14_G, NA, NB, NC, ND, NE, NF, NG, V2_W, V4_W, V3_W, V2_W, V4_W, NH, NJ, NK, NL)</b>					<b>12/82→04/00</b>
2.3 TD (L043G, L048G)	62 kW	2.3 l	12/82→04/86		KH00011 ProKIT
2.5 TD (L044G, L049G)	62 kW	2.5 l	05/86→10/89		
2.5 TD (L044G, L049G)	64 kW	2.5 l	04/87→12/91		
2.5 TD (L044G, L049G)	70 kW	2.5 l	11/89→11/90		
2.5 TD 4WD (V24C, V24W)	73 kW	2.5 l	12/90→10/99		
2.5 TD 4WD (V24C, V24W)	73 kW	2.5 l	12/90→04/00		
2.6 (L042G, L047G)	76 kW	2.6 l	01/83→11/90		
3.0 V6 (L141G, L146G)	104 kW	3 l	11/88→11/90		
3.0 V6 (V23W, v43W, V23C)	110 kW	3 l	12/90→12/95		
3.0 V6 24V (V23W, V23C)	133 kW	3 l	06/94→04/00		
2.8 TD (V46W, V26W)	92 kW	2.8 l	06/94→10/99	; 11/97 -> 08/99	KH00011 ProKIT
<b>MITSUBISHI - PAJERO III Wagen, Hardtop / PAJERO IV Wagon Hardtop (V6_W, V7_W, NM, NP, V8_W, V9_W, NS, NT, NW, NX)</b>					<b>04/00→12/06</b>
2.5 TDi (V64W, V74W)	73 kW	2.5 l	04/00→12/06		KH20041 ProKIT
3.2 DI-D	123 kW	3.2 l	02/07→		
3.2 DI-D 4WD	121 kW	3.2 l	11/08→		
3.2 DI-D 4WD (V98W, V88W)	140 kW	3.2 l	02/07→		
3.5 V6 GDI (V65W, V75W)	149 kW	3.5 l	04/00→12/06		
2.5 TDi (V64W, V74W)	85 kW	2.5 l	09/01→12/06		KH20041 ProKIT
3.2 DI-D (V68W, V78W)	118 kW	3.2 l	10/01→12/06	; -> 08/06; Code: V75W, V65W	KH20133 ProKIT
3.2 DI-D (V68W, V78W)	121 kW	3.2 l	04/00→12/06		
3.2 DI-D (V88W, V98W)	118 kW	3.2 l	02/07→		KH20041 ProKIT
3.2 DI-D (V88W, V98W)	125 kW	3.2 l	02/07→	; Code: V98W	KH20156 ProKIT
				; Code: V98W	KH20134 ProKIT
3.2 DI-D 4WD (V98W, V88W)	147 kW	3.2 l	01/09→		KH20041 ProKIT
				; Code: V98W	KH20134 ProKIT
3.8 V6 (V87W, V97W)	184 kW	3.8 l	02/07→		KH20041 ProKIT
3.8 V6 (V87W)	182 kW	3.8 l	10/06→	; Code: V97W	KH20156 ProKIT
				; Code: V97W	KH20134 ProKIT
<b>MITSUBISHI - PAJERO CLASSIC (V2_W, V6_W, V7_W)</b>					<b>07/01→</b>
2.5 TD (V24W)	85 kW	2.5 l	07/01→	; -> 04/07; Code: V24W	KH00011 ProKIT
3.2 DiD (V68W, V78W)	125 kW	3.2 l	09/06→	; Code: V98W	KH20156 ProKIT
<b>MITSUBISHI - PAJERO IO I (H6_W, H7_W, QA)</b>					<b>10/99→06/07</b>
1.8 (H76W, H66W)	84 kW	1.8 l	11/01→06/07	; -> 07/06	KH10221 ProKIT
					KH10158 ProKIT
1.8 GDI (H66W, H76W)	88 kW	1.8 l	10/99→10/01	; 01/00 ->	KH10221 ProKIT
2.0 GDI (H67W, H77W)	95 kW	2 l	10/00→06/07	; 12/00 -> 07/06	KH10221 ProKIT
					KH10158 ProKIT
<b>MITSUBISHI - SAPPORO I (A12_)</b>					<b>04/78→07/80</b>
1.6 SL, GL (A121)	55 kW	1.6 l	04/78→07/80		KH00017 ProKIT
<b>MITSUBISHI - SPACE RUNNER (N6_W)</b>					<b>08/99→01/03</b>
2.0 (N63W)	100 kW	2 l	08/99→08/02	; -> 04/00	KH20096 ProKIT
2.4 GDI (N64W)	110 kW	2.4 l	08/99→01/03		
<b>MITSUBISHI - SPACE STAR MPV (DG_A)</b>					<b>06/98→12/04</b>
1.3 16V (DG1A)	60 kW	1.3 l	09/00→12/04	; 04/01 ->	KH10398 ProKIT
1.3 16V (DG1A)	61 kW	1.3 l	12/98→12/04		KH10221 ProKIT
1.3 16V (DG1A)	63 kW	1.3 l	06/98→12/04	; 04/01 ->	KH10398 ProKIT
1.6 16V (DG3A)	72 kW	1.6 l	01/01→12/04	; 04/01 ->	KH10221 ProKIT
				; 04/01 ->	KH10398 ProKIT
1.8 GDI (DG5A)	87 kW	1.8 l	06/98→12/04	; 12/98 ->	KH10221 ProKIT
1.8 GDI (DG5A)	90 kW	1.8 l	06/98→12/04	; 06/00 ->	KH10398 ProKIT
1.8 MPI (DG5A)	82 kW	1.8 l	10/02→12/04	; Code: DG5A	KH10398 ProKIT






































     					
<b>MITSUBISHI - SPACE STAR MPV (DG_A)</b>					<b>06/98→12/04</b>
1.9 DI-D (DG4A)	75 kW	1.9 l	02/01→12/04	; 07/02 ->	<b>KH10221</b> ProKIT
					<b>KH10398</b> ProKIT
1.9 DI-D (DG4A)	85 kW	1.9 l	10/02→12/04	; 04/03 ->	<b>KH10221</b> ProKIT
				; Code: DG4A	<b>KH10398</b> ProKIT
<b>MITSUBISHI - STARWAGON III Bus (P0_W, P1_W, P2_W, SD, SE, SF, SG, SH, SJ,</b>					<b>08/86→05/04</b>
2.0 4WD (P23W, P03W, P13W)	65 kW	2 l	12/86→05/04	; -> 05/03	<b>KH00011</b> ProKIT
2.0 4WD (P23W, P03W, P13W)	66 kW	2 l	11/86→05/04		
2.4 4WD (P24W)	80 kW	2.4 l	11/86→12/90		<b>KH00011</b> ProKIT
2.4 4WD (P24W)	82 kW	2.4 l	08/86→05/04	; -> 06/95	<b>KH00011</b> ProKIT
2.5 TD 4WD (P25W, P35W)	64 kW	2.5 l	12/87→05/04	; -> 08/97	<b>KH00011</b> ProKIT
<b>MITSUBISHI - TREDIA (A21_)</b>					<b>09/82→10/87</b>
1.6 GLS (A212)	55 kW	1.6 l	09/82→10/87	; 01/83 -> 12/84	<b>KH00077</b> ProKIT
1.6 Turbo (A212)	84 kW	1.6 l	09/82→05/85	; 01/83 -> 12/84	<b>KH00017</b> ProKIT
1.6 Turbo (A212)	85 kW	1.6 l	09/82→07/84	; 01/83 ->	<b>KH00077</b> ProKIT
				; 01/83 ->	<b>KH00017</b> ProKIT
<b>MITSUBISHI - TRITON (KA_T, ML, MN, KB_T, KJ_, MQ, KK_, KL_, MR)</b>					<b>11/05→12/15</b>
2.4 DI-D (KJ0T)	113 kW	2.4 l	09/15→		<b>KH20044</b> ProKIT
2.4 DI-D 4WD (KJ0T)	113 kW	2.4 l	09/15→		
2.4 DI-D 4WD (KL1T)	133 kW	2.4 l	11/14→		
2.5 DiD (KA4T)	100 kW	2.5 l	11/05→12/15		
2.5 DI-D (KA4T)	94 kW	2.5 l	04/10→12/15		
2.5 DI-D 4WD (KB4T)	100 kW	2.5 l	11/05→12/15		
2.5 DI-D 4WD (KB4T)	123 kW	2.5 l	10/07→12/15		
2.5 DI-D 4WD (KB4T)	131 kW	2.5 l	04/10→12/15		
2.5 DI-D (KA4T)	123 kW	2.5 l	08/07→12/15	; Code: KK1T	<b>KH20044</b> ProKIT
<b>MITSUBISHI - TRITON Pickup (K3_T, K2_T, K1_T, K0_T, ME, MF, MG, MH, MJ)</b>					<b>11/86→10/96</b>
2.5 D (K14T)	51 kW	2.5 l	11/86→10/96	; Code: K24T	<b>KH00011</b> ProKIT
2.5 D 4WD (K24T)	51 kW	2.5 l	12/87→05/93		<b>KH00011</b> ProKIT
<b>MITSUBISHI - TRITON Pickup (K7_T, K6_T, MK, K5_T)</b>					<b>06/96→12/07</b>
2.4 4WD (K75T)	97 kW	2.4 l	06/96→12/07	; 11/96 -> 07/01;	<b>KH00011</b> ProKIT
2.5 TD 4WD (K74T)	73 kW	2.5 l	06/96→12/07	; -> 05/05	<b>KH00011</b> ProKIT
2.5 TD 4WD (K74T)	85 kW	2.5 l	09/01→12/07		
2.5 TD 4WD (K74T)	98 kW	2.5 l	08/01→12/07		


















































													
<b>NISSAN - 350Z Coupe / 350Z Roadster (Z33)</b>											<b>09/02→12/09</b>		
3.5	206 kW	3.5 l	10/03→12/06		-> 03/06						KH30149 ProKIT		
3.5	206 kW	3.5 l	03/05→12/07								KH20201 ProKIT		
3.5	221 kW	3.5 l	09/02→12/08								KH30149 ProKIT		
3.5	221 kW	3.5 l	11/04→01/07								KH20201 ProKIT		
3.5	230 kW	3.5 l	09/05→12/08								KH20201 ProKIT		
3.5	230 kW	3.5 l	09/05→12/09										
<b>NISSAN - 370Z Coupe / 370Z Roadster (Z34)</b>											<b>04/09→</b>		
3.7	241 kW	3.7 l	06/09→								KH30025 ProKIT		
3.7	241 kW	3.7 l	01/10→										
3.7	243 kW	3.7 l	06/09→										
3.7	243 kW	3.7 l	12/09→										
3.7	245 kW	3.7 l	01/13→										
3.7	248 kW	3.7 l	04/09→										
NISMO 3.7	253 kW	3.7 l	06/13→										
<b>NISSAN - ALMERA TINO (V10)</b>											<b>12/98→02/06</b>		
1.8	84 kW	1.8 l	08/00→02/06								KH10034 ProKIT		
1.8	85 kW	1.8 l	12/02→02/06		ABS						KH20183 ProKIT		
1.8	88 kW	1.8 l	12/98→02/03										
2.0	100 kW	2 l	08/00→01/03										
2.2 dCi	82 kW	2.2 l	09/03→02/06										
2.2 dCi	84 kW	2.2 l	08/00→02/06										
2.2 dCi	100 kW	2.2 l	09/03→02/06										
<b>NISSAN - CABSTAR (F24M, F24W)</b>											<b>09/06→12/13</b>		
28.11 DCI, 32.11 DCI, 35.11 DCI 2.5 (F24M)	81 kW	2.5 l	09/06→12/13								KH00050 ProKIT		
28.12 DCI, 32.12 DCI, 34.12 DCI, 35.12 DCI 2.5 (F24M)	90 kW	2.5 l	09/06→12/13										
35.13 DCI, 45.13 DCI 2.5 (F24M)	96 kW	2.5 l	09/06→12/12										
35.14 DCI, 45.14 DCI 2.5 (F24M)	100 kW	2.5 l	09/06→12/13										
35.14 DCI 3.0 (F24M)	101 kW	3 l	09/06→12/13										
35.15 DCI, 45.15 DCI 3.0 (F24M)	110 kW	3 l	09/06→12/13										
<b>NISSAN - CEFIRO III Saloon (A33)</b>											<b>01/00→09/03</b>		
2.0	103 kW	2 l	01/00→09/03								KH10034 ProKIT		
3.0	147 kW	3 l	01/00→09/03										
<b>NISSAN - DUALIS I (J10, NJ10, JJ10E)</b>											<b>02/07→04/14</b>		
1.5 dCi	76 kW	1.5 l	07/08→12/13								KH30024 ProKIT		
1.5 dCi	78 kW	1.5 l	02/07→12/13										
1.5 dCi	81 kW	1.5 l	01/10→12/13										
1.6	81 kW	1.6 l	02/07→12/13										
1.6	84 kW	1.6 l	02/07→12/13										
1.6	86 kW	1.6 l	11/10→12/13										
1.6 dCi	96 kW	1.6 l	10/11→12/13										
1.6 dCi All-wheel Drive	96 kW	1.6 l	10/11→12/13										
1.6 LPG	86 kW	1.6 l	11/10→12/13										
2.0	101 kW	2 l	01/10→04/14										
2.0	102 kW	2 l	02/07→12/13										
2.0	103 kW	2 l	01/10→04/14										
2.0	104 kW	2 l	02/07→12/13										
2.0 All-wheel Drive	101 kW	2 l	02/07→11/13										
2.0 All-wheel Drive	102 kW	2 l	02/07→12/13										
2.0 All-wheel Drive	103 kW	2 l	01/10→04/14										
2.0 All-wheel Drive	104 kW	2 l	02/07→12/13										
2.0 dCi	110 kW	2 l	02/07→12/13										
2.0 dCi All-wheel Drive	110 kW	2 l	02/07→12/13								KH30024 ProKIT		
											KH30131 ProKIT		
<b>NISSAN - INTERSTAR Bus / INTERSTAR Platform/Chassis / INTERSTAR Van (X70)</b>											<b>04/02→</b>		
dCi 100	73 kW	2.5 l	11/03→03/06								KH10100 ProKIT		
dCi 100	73 kW	2.5 l	02/04→									KH10064 ProKIT	
dCi 100	74 kW	2.5 l	04/06→		16 Inch								
dCi 100	74 kW	2.5 l	04/06→03/11		15 Inch						KH10092 ProKIT		
dCi 115	84 kW	2.5 l	04/02→										
dCi 115	84 kW	2.5 l	04/02→08/06										
dCi 115	84 kW	2.5 l	08/03→										
dCi 120	88 kW	2.5 l	08/06→										
dCi 120	88 kW	2.5 l	09/06→										
dCi 120	88 kW	2.5 l	09/06→03/11										
dCi 140	100 kW	3 l	11/03→										
dCi 150	107 kW	2.5 l	08/06→										
dCi 150	107 kW	2.5 l	09/06→										









































									
<b>NISSAN - INTERSTAR Bus / INTERSTAR Platform/Chassis / INTERSTAR Van (X70)</b>									<b>04/02→</b>
dCi 150	107 kW	2.5 l	09/06→03/11						<b>KH10100</b> ProKIT
dCi 80	60 kW	1.9 l	04/02→08/06			16 Inch		<b>KH10064</b> ProKIT	
dCi 90	66 kW	2.2 l	07/02→			15 Inch		<b>KH10092</b> ProKIT	
dCi 90	66 kW	2.2 l	07/02→08/06			15 Inch		<b>KH10092</b> ProKIT	
<b>NISSAN - JUKE (F15)</b>									<b>06/10→</b>
1.2 DIG-T	85 kW	1.2 l	05/14→						<b>KH30024</b> ProKIT
1.5 dCi	81 kW	1.5 l	06/10→						<b>KH30023</b> ProKIT
1.6	69 kW	1.6 l	01/13→						
1.6	86 kW	1.6 l	06/10→						
1.6 DIG-T	140 kW	1.6 l	06/10→						
1.6 DIG-T NISMO	147 kW	1.6 l	03/13→07/14						
1.6 DIG-T NISMO RS	160 kW	1.6 l	08/14→						
1.5	84 kW	1.5 l	10/13→						<b>KH30024</b> ProKIT
1.6	85 kW	1.6 l	03/16→						
1.6 CVTC	72 kW	1.6 l	08/14→						
1.6 DIG-T NISMO RS	157 kW	1.6 l	11/15→						
1.6 LPG	85 kW	1.6 l	01/12→						
1.6 DIG-T 4x4	140 kW	1.6 l	06/10→						<b>KH30024</b> ProKIT
1.6 DIG-T NISMO 4x4	147 kW	1.6 l	02/13→07/14						<b>KH30131</b> ProKIT
1.6 DIG-T NISMO RS 4x4	157 kW	1.6 l	08/14→						
1.6 DIG-T NISMO RS 4x4	160 kW	1.6 l	11/15→						
<b>NISSAN - KUBISTAR Van (X76)</b>									<b>08/03→</b>
1.2	44 kW	1.2 l	08/03→						<b>KH10057</b> ProKIT
1.2 16V	55 kW	1.2 l	04/06→						
1.4	55 kW	1.4 l	08/03→10/09		Payload: not for increased payload			<b>KH10082</b> ProKIT	
1.5 dCi	42 kW	1.5 l	08/03→10/09		Payload: for increased payload			<b>KH20101</b> ProKIT	
1.5 dCi	45 kW	1.5 l	08/05→10/09						
1.5 dCi	48 kW	1.5 l	08/03→						
1.5 dCi	60 kW	1.5 l	08/03→10/09						
1.5 dCi 70	50 kW	1.5 l	09/05→10/09						
1.6 16V	70 kW	1.6 l	08/03→10/09						
dCi 85	62 kW	1.5 l	04/06→10/09						
<b>NISSAN - LEAF (ZE0)</b>									<b>11/10→</b>
Electric	80 kW		11/10→						<b>KH30024</b> ProKIT
									<b>KH30023</b> ProKIT
<b>NISSAN - MARCH I (K10)</b>									<b>12/82→07/92</b>
1.0	37 kW	1 l	12/82→12/89		12/88 ->			<b>KH20143</b> ProKIT	
1.0	40 kW	1 l	12/82→05/89						
1.2	40 kW	1.2 l	07/86→07/92						
1.2	44 kW	1.2 l	07/86→07/92						
<b>NISSAN - MAXIMA / MAXIMA QX V Saloon (A33)</b>									<b>03/00→11/03</b>
2.0 V6 24V	103 kW	2 l	03/00→11/03						<b>KH10034</b> ProKIT
3.0 V6 24V	147 kW	3 l	03/00→11/03						
<b>NISSAN - MAXIMA II Saloon / MAXIMA IV Saloon (J30, A32)</b>									<b>10/88→08/00</b>
2.0	103 kW	2 l	02/95→08/00						<b>KH10009</b> ProKIT
2.5 V6 24V	140 kW	2.5 l	02/95→08/00						
3.0	128 kW	3 l	10/88→06/94						
3.0	142 kW	3 l	03/94→03/99						
3.0	142 kW	3 l	01/95→08/00						
3.0	157 kW	3 l	01/95→08/00						
3.0 i	125 kW	3 l	10/88→06/94						
<b>NISSAN - MICRA II (K11)</b>									<b>08/92→02/03</b>
1.0 i 16V	40 kW	1 l	08/92→07/00						<b>KH10180</b> ProKIT
1.0 i 16V	44 kW	1 l	07/00→02/03						
1.3 i 16V	55 kW	1.3 l	08/92→09/00						<b>KH20143</b> ProKIT
1.4 i 16V	60 kW	1.4 l	09/00→02/03						
<b>NISSAN - MICRA III (K12)</b>									<b>10/02→06/10</b>
1.0 16V	48 kW	1 l	01/03→06/10						<b>KH10380</b> ProKIT
1.2 16V	48 kW	1.2 l	01/03→06/10						<b>KH10073</b> ProKIT
1.2 16V	59 kW	1.2 l	01/03→06/10						
1.4 16V	65 kW	1.4 l	01/03→06/10						
1.5 dCi	48 kW	1.5 l	01/03→06/10						
1.5 dCi	50 kW	1.5 l	06/05→06/10						
1.5 dCi	60 kW	1.5 l	09/03→06/10						
1.5 dCi	63 kW	1.5 l	06/05→06/10						
160 SR	81 kW	1.6 l	05/05→06/10						
1.2 LPG	59 kW	1.2 l	10/02→06/10						<b>KH10073</b> ProKIT

























										
<b>NISSAN - MICRA IV (K13K)</b>										<b>05/10→09/15</b>
1.2	56 kW	1.2 l	05/10→09/15							KH10176 ProKIT
1.2	59 kW	1.2 l	05/10→09/15							KH10175 ProKIT
1.2 DIG-S	72 kW	1.2 l	03/11→09/15							
<b>NISSAN - MICRA C+C III (K12)</b>										<b>08/05→</b>
1.4 16V	65 kW	1.4 l	08/05→							KH10380 ProKIT
1.6 160 SR	81 kW	1.6 l	08/05→							KH10073 ProKIT
<b>NISSAN - MURANO I (Z50)</b>										<b>08/03→09/08</b>
3.5 4x4	170 kW	3.5 l	01/06→09/08							KH30027 ProKIT
3.5 4x4	172 kW	3.5 l	08/03→09/08							KH30027 ProKIT
										KH30146 ProKIT
										-> 06/08
<b>NISSAN - NAVARA (D21)</b>										<b>03/86→02/98</b>
2.4 4WD	74 kW	2.4 l	03/86→04/92							KH00024 ProKIT
2.4 i 12V	91 kW	2.4 l	04/92→02/98							KH00117 ProKIT
2.5 D	61 kW	2.5 l	08/92→02/98							
2.4 i 12V 4WD	93 kW	2.4 l	04/92→02/98							KH00024 ProKIT
										08/92 -> 12/94
<b>NISSAN - NOTE (E11, NE11)</b>										<b>03/06→06/12</b>
1.4	65 kW	1.4 l	03/06→06/12							KH10380 ProKIT
1.5 dCi	50 kW	1.5 l	03/06→06/12							KH10073 ProKIT
1.5 dCi	63 kW	1.5 l	03/06→06/12							
1.5 dCi	66 kW	1.5 l	09/10→06/12							
1.5 dCi	76 kW	1.5 l	07/08→06/12							
1.6	81 kW	1.6 l	03/06→06/12							
<b>NISSAN - NOTE (E12)</b>										<b>06/13→</b>
1.2	58 kW	1.2 l	06/13→							KH10175 ProKIT
1.2	59 kW	1.2 l	06/13→							
1.2 DIG-S	72 kW	1.2 l	06/13→							
1.2 LPG	56 kW	1.2 l	03/15→							KH10175 ProKIT
<b>NISSAN - NV200 / EVALIA Bus / NV200 Van</b>										<b>02/10→</b>
1.5 dCi 110 (M20, M20M)	81 kW	1.5 l	04/11→							KH30165 ProKIT
1.5 dCi 85 (M20, M20M, M20K, M20KK)	63 kW	1.5 l	07/10→							KH30178 ProKIT
1.5 dCi 85 (M20, M20M)	63 kW	1.5 l	02/10→							
1.5 dCi 90 (M20, M20M)	66 kW	1.5 l	04/11→							
1.6 16V (M20, M20M)	81 kW	1.6 l	02/10→							
1.6 16V (M20, M20M)	81 kW	1.6 l	07/10→							
2.0 (M20, M20M)	98 kW	2 l	09/13→							KH30024 ProKIT
e-NV (MEOM)	80 kW		07/14→							
e-NV (MEON)	80 kW		05/14→							
<b>NISSAN - NV400 Bus / NV400 Platform/Chassis / NV400 Van (X62, X62B)</b>										<b>11/11→</b>
dCi 100	74 kW	2.3 l	11/11→09/16							KH10139 ProKIT
dCi 110	81 kW	2.3 l	06/14→							
dCi 110	81 kW	2.3 l	06/14→06/16							KH10138 ProKIT
dCi 110	81 kW	2.3 l	06/14→09/16							
dCi 125	92 kW	2.3 l	11/11→09/16							
dCi 130	96 kW	2.3 l	06/16→							
dCi 130	96 kW	2.3 l	09/16→							
dCi 135	100 kW	2.3 l	06/14→06/16							
dCi 135	100 kW	2.3 l	06/14→09/16							
dCi 145	107 kW	2.3 l	11/11→							
dCi 145	107 kW	2.3 l	11/11→02/14							
dCi 145	107 kW	2.3 l	11/11→06/16							
dCi 150	110 kW	2.3 l	02/14→09/16							
dCi 150	110 kW	2.3 l	08/14→06/16							
dCi 160	120 kW	2.3 l	06/14→09/16							
dCi 165	120 kW	2.3 l	06/14→06/16							
dCi 165	120 kW	2.3 l	06/14→09/16							
dCi 170	125 kW	2.3 l	07/15→							
dCi 170	125 kW	2.3 l	06/16→							
dCi 170	125 kW	2.3 l	09/16→							








































												
<b>NISSAN - NV400 Bus / NV400 Platform/Chassis / NV400 Van (X62, X62B)</b>											<b>11/11→</b>	
dCi 125 RWD	92 kW	2.3 l	11/11→09/16								KH10174 ProKIT	
dCi 130 RWD	96 kW	2.3 l	06/16→									KH00086 ProKIT
dCi 130 RWD	96 kW	2.3 l	09/16→									KH10143 ProKIT
dCi 135 RWD	100 kW	2.3 l	06/14→06/16									KH10143 ProKIT
dCi 135 RWD	100 kW	2.3 l	06/14→09/16									
dCi 145 RWD	107 kW	2.3 l	11/11→									
dCi 145 RWD	107 kW	2.3 l	11/11→02/14									
dCi 150 RWD	110 kW	2.3 l	02/14→09/16									
dCi 150 RWD	110 kW	2.3 l	08/14→06/16									
dCi 165 RWD	120 kW	2.3 l	06/14→									
dCi 165 RWD	120 kW	2.3 l	06/14→09/16									
<b>NISSAN - PATHFINDER I (WD21)</b>											<b>10/87→02/96</b>	
2.4 i 4WD	76 kW	2.4 l	10/87→02/93								KH00024 ProKIT	
2.7 TD 4WD	73 kW	2.7 l	02/89→02/96			-> 01/94						KH00024 ProKIT
3.0 i 4WD	109 kW	3 l	01/90→12/95									
<b>NISSAN - PATHFINDER III (R51)</b>											<b>01/05→</b>	
2.5 dCi 4WD	120 kW	2.5 l	01/05→								KH30137 ProKIT	
2.5 dCi 4WD	126 kW	2.5 l	10/06→									
2.5 dCi 4WD	128 kW	2.5 l	03/05→									
2.5 dCi 4WD	140 kW	2.5 l	08/10→									
3.0 dCi	170 kW	3 l	08/10→									
4.0 4WD	198 kW	4 l	09/05→									
<b>NISSAN - PATROL IV (Y60, GR, GQ)</b>											<b>09/88→02/98</b>	
2.8 TD (Y60A)	85 kW	2.8 l	09/88→06/97								KH00036 ProKIT	
4.2 Cat	121 kW	4.2 l	11/88→02/98			10/91 ->						KH00036 ProKIT
<b>NISSAN - PATROL IV Station Wagon (Y61, GR_, GU)</b>											<b>06/97→05/00</b>	
2.8 TD	95 kW	2.8 l	06/97→05/00			10/97 ->						KH00036 ProKIT
3.0 DTi	116 kW	3 l	05/00→			-> 07/04						KH00036 ProKIT
3.0 DTi	118 kW	3 l	05/00→			08/04 ->						KH00036 ProKIT
<b>NISSAN - PATROL III/1 Hardtop / PATROL III/1 Station Wagon (K160, MK, MQ, W160, MK, MQ)</b>											<b>11/79→08/88</b>	
2.8 (K160)	89 kW	2.8 l	07/80→08/88			11/84 ->						KH00036 ProKIT
2.8 (W160)	88 kW	2.8 l	07/80→08/88									
3.2 D (K160)	70 kW	3.2 l	11/79→08/88									
3.2 D (W160)	70 kW	3.2 l	11/79→08/88									
3.2 TD (K160)	81 kW	3.2 l	07/83→08/88									
3.2 TD (W160)	81 kW	3.2 l	07/83→08/88									
<b>NISSAN - PATROL III/2 Hardtop / PATROL III/2 Station Wagon (K260, W260)</b>											<b>05/86→11/95</b>	
2.8	88 kW	2.8 l	05/86→06/90			-> 02/89						KH00036 ProKIT
3.2 D	81 kW	3.2 l	08/88→06/90									
2.8 TD	85 kW	2.8 l	05/86→06/90			03/89 ->						KH00036 ProKIT
2.8 TD	85 kW	2.8 l	06/89→11/95								KH00036 ProKIT	
<b>NISSAN - PIXO (UA0)</b>											<b>03/09→</b>	
1.0	50 kW	1 l	03/09→								KH10215 ProKIT	
						ABS						KH10033 ProKIT
<b>NISSAN - PRAIRIE (M11)</b>											<b>10/88→07/94</b>	
2.0	77 kW	2 l	09/90→03/92								KH10009 ProKIT	
2.0 4x4	77 kW	2 l	09/90→03/92									KH10009 ProKIT
2.0 i 4x4	72 kW	2 l	10/88→12/92									
2.4 i 4x4	98 kW	2.4 l	04/92→07/94									
2.0 i	72 kW	2 l	10/88→04/92								KH10009 ProKIT	
						-> 03/92						KH20192 ProKIT
2.4 i	98 kW	2.4 l	01/90→07/94								KH10009 ProKIT	
											KH20192 ProKIT	
<b>NISSAN - PRIMASTAR Bus / PRIMASTAR Platform/Chassis / PRIMASTAR Van (X83)</b>											<b>03/01→08/06</b>	
1.9 dCi 100	74 kW	1.9 l	07/02→08/06			12/02 ->					KH10115 ProKIT	
1.9 dCi 80	60 kW	1.9 l	07/02→08/06								KH10090 ProKIT	
2.0	88 kW	2 l	07/02→08/06									
2.5 dCi 140	99 kW	2.5 l	07/02→08/06									

											
NISSAN - PRIMASTAR Bus / PRIMASTAR Platform/Chassis / PRIMASTAR Van (X83)										03/01→08/06	
1.9 dCi 100	74 kW	1.9 l	09/02→								KH10115 ProKIT
1.9 dCi 80	60 kW	1.9 l	09/02→								KH10149 ProKIT
2.0	88 kW	2 l	03/01→08/06								KH10196 ProKIT
dCi 100	74 kW	1.9 l	03/01→								KH10090 ProKIT
dCi 80	60 kW	1.9 l	03/01→								KH10115 ProKIT
2.0	86 kW	2 l	04/06→								KH10090 ProKIT
2.0	88 kW	2 l	02/03→								KH10115 ProKIT
2.0 dCi 115	84 kW	2 l	09/06→								KH10115 ProKIT
2.0 dCi 90	66 kW	2 l	09/06→								
2.5 dCi 115	84 kW	2.5 l	09/08→								
2.5 dCi 140	99 kW	2.5 l	07/03→								
2.5 dCi 150	107 kW	2.5 l	04/06→								
2.5 dCi 150	107 kW	2.5 l	09/06→								
dCi 115	84 kW	2.5 l	09/08→								
dCi 120	84 kW	2 l	09/06→								
dCi 140	99 kW	2.5 l	07/03→								
dCi 150	107 kW	2.5 l	09/06→								
dCi 90	66 kW	2 l	09/06→								
NISSAN - PRIMERA (P10)										06/90→06/96	
1.6	66 kW	1.6 l	06/90→01/96								KH10009 ProKIT
1.6	71 kW	1.6 l	06/90→01/96								
1.6	75 kW	1.6 l	06/93→01/96								
2.0	96 kW	2 l	06/90→05/96								
2.0 16V	85 kW	2 l	06/90→01/96								
2.0 D	55 kW	2 l	01/91→01/96								
2.0 GT	110 kW	2 l	06/90→01/96								
2.0 GT 4x4	105 kW	2 l	03/91→04/93								
2.0 i	92 kW	2 l	01/95→06/96								
2.0 16V 4x4	85 kW	2 l	04/91→06/96								KH10009 ProKIT
2.0 4x4	110 kW	2 l	03/91→04/93								
NISSAN - PRIMERA (P11)										06/96→12/01	
1.6 16V	66 kW	1.6 l	09/96→12/01								KH10009 ProKIT
1.6 16V	73 kW	1.6 l	09/96→10/00								KH20152 ProKIT
2.0 16V	85 kW	2 l	09/96→12/01								
2.0 16V	96 kW	2 l	09/96→12/01								
2.0 16V	110 kW	2 l	09/96→12/01								
2.0 TD	66 kW	2 l	09/96→12/01								
1.6 16V	78 kW	1.6 l	06/96→12/01								KH10009 ProKIT
1.8 16V	84 kW	1.8 l	08/99→12/01								KH20152 ProKIT
2.0 16V	103 kW	2 l	08/99→12/01								
NISSAN - PRIMERA / PRIMERA Estate (P12, WP12)										01/02→08/08	
1.6	78 kW	1.6 l	03/02→08/08								KH10034 ProKIT
1.9 dCi	85 kW	1.9 l	08/02→10/07								
1.6	80 kW	1.6 l	01/02→04/06								KH10034 ProKIT
1.6 Visia	80 kW	1.6 l	01/02→04/06								
1.8	85 kW	1.8 l	03/02→05/07								KH20142 ProKIT
1.8	85 kW	1.8 l	03/02→10/08								
1.9 dCi	88 kW	1.9 l	04/03→								
1.9 dCi	88 kW	1.9 l	04/03→10/07								
2.0	103 kW	2 l	03/02→								
2.0	103 kW	2 l	03/02→10/08								
2.2 dCi	102 kW	2.2 l	04/03→								
2.2 dCi	102 kW	2.2 l	04/03→04/06								
2.2 Di	93 kW	2.2 l	03/02→04/03								
2.2 Di	93 kW	2.2 l	03/02→05/07								
NISSAN - PRIMERA Hatchback (P10)										06/90→06/96	
1.6	66 kW	1.6 l	06/90→01/96								KH10009 ProKIT
1.6	71 kW	1.6 l	06/90→06/93								
1.6	75 kW	1.6 l	06/93→01/96								
2.0	105 kW	2 l	06/90→04/93								
2.0	110 kW	2 l	06/90→01/96								
2.0	112 kW	2 l	09/90→01/96								
2.0 16V	85 kW	2 l	06/90→01/96								
2.0 D	55 kW	2 l	01/91→01/96								
2.0 i	92 kW	2 l	01/95→06/96								
2.0 16V 4x4	85 kW	2 l	04/91→06/96								KH10009 ProKIT


























											
<b>NISSAN - PRIMERA Hatchback (P11)</b>										<b>09/96→07/02</b>	
1.6 16V	66 kW	1.6 l	09/96→07/02						KH10009 ProKIT		
1.6 16V	73 kW	1.6 l	09/96→07/02		ABS; 06/99 →				KH20152 ProKIT		
2.0 16V	85 kW	2 l	09/96→07/02								
2.0 16V	96 kW	2 l	09/96→07/02								
2.0 16V	110 kW	2 l	09/96→07/02								
2.0 TD	66 kW	2 l	09/96→07/02								
1.6 16V	78 kW	1.6 l	09/00→07/02						KH10009 ProKIT		
1.8 16V	84 kW	1.8 l	08/99→07/02		ABS				KH20152 ProKIT		
2.0 16V	103 kW	2 l	08/99→07/02								
<b>NISSAN - PRIMERA Hatchback (P12)</b>										<b>07/02→10/07</b>	
1.6	78 kW	1.6 l	07/02→08/08						KH10034 ProKIT		
1.8	85 kW	1.8 l	07/02→10/08								
1.9 dCi	88 kW	1.9 l	04/03→10/07		ABS				KH20142 ProKIT		
2.0	103 kW	2 l	07/02→10/08								
2.2 dCi	102 kW	2.2 l	04/03→								
2.2 Di	93 kW	2.2 l	07/02→05/07								
1.6	80 kW	1.6 l	07/02→04/06						KH10034 ProKIT		
1.9 dCi	85 kW	1.9 l	08/02→10/07								
<b>NISSAN - PRIMERA Traveller (W10)</b>										<b>07/90→03/98</b>	
1.6 i	66 kW	1.6 l	07/90→03/98		-> 04/93				KH20192 ProKIT		
1.6 i	75 kW	1.6 l	02/91→03/98		-> 01/98; ABS				KH20192 ProKIT		
2.0 i	85 kW	2 l	07/90→03/98								
2.0 D	55 kW	2 l	07/90→12/95		ABS				KH20192 ProKIT		
<b>NISSAN - PRIMERA Traveller (WP11)</b>										<b>06/96→12/01</b>	
1.6 16V	66 kW	1.6 l	04/98→12/01						KH10009 ProKIT		
1.6 16V	73 kW	1.6 l	04/98→12/01								
1.8 16V	84 kW	1.8 l	08/99→12/01								
2.0 16V	85 kW	2 l	06/96→12/01								
2.0 16V	96 kW	2 l	04/98→12/01								
2.0 16V	103 kW	2 l	08/99→12/01								
2.0 TD	66 kW	2 l	04/98→12/01								
<b>NISSAN - PULSAR I Sedan / PULSAR VI Hatchback (N15)</b>										<b>09/95→07/00</b>	
1.4	64 kW	1.4 l	09/95→03/00		-> 01/00; ABS				KH20158 ProKIT		
1.4	64 kW	1.4 l	09/95→07/00								
1.4 GX,LX	55 kW	1.4 l	09/95→07/00								
1.4 S, GX, LX	55 kW	1.4 l	09/95→03/00								
1.6	73 kW	1.6 l	09/95→03/00								
1.6	73 kW	1.6 l	09/95→07/00								
2.0 D	55 kW	2 l	11/95→03/00								
2.0 D	55 kW	2 l	11/95→07/00								
2.0 GTi	105 kW	2 l	07/96→03/00								
<b>NISSAN - PULSAR VII (B17)</b>										<b>08/12→</b>	
1.6	83 kW	1.6 l	05/13→						KH30024 ProKIT		
1.6	85 kW	1.6 l	05/13→								
1.6	86 kW	1.6 l	08/14→								
1.6 DIG-T	140 kW	1.6 l	06/14→								
1.8	91 kW	1.8 l	10/17→								
1.8	95 kW	1.8 l	01/15→								
1.8	96 kW	1.8 l	08/12→								
2.0 16V	103 kW	2 l	11/14→								
2.0 CVTCS Flex	103 kW	2 l	10/13→12/20								
<b>NISSAN - PULSAR VII Hatchback / PULSAR VII Saloon (N16)</b>										<b>01/00→11/06</b>	
1.5	66 kW	1.5 l	03/00→11/06						KH10003 ProKIT		
1.5	66 kW	1.5 l	07/00→11/06								
1.5	72 kW	1.5 l	10/02→09/06		ABS, ESP				KH20139 ProKIT		
1.8	84 kW	1.8 l	01/00→11/02		ABS				KH20152 ProKIT		
1.8	84 kW	1.8 l	07/00→11/02								
1.8	85 kW	1.8 l	10/02→09/06								
2.2 dCi	82 kW	2.2 l	09/03→09/06								
2.2 dCi	100 kW	2.2 l	09/03→09/06								
2.2 Di	81 kW	2.2 l	03/00→04/03								
2.2 Di	81 kW	2.2 l	07/00→04/03								
1.5 dCi	60 kW	1.5 l	01/03→09/06						KH10003 ProKIT		
1.8	88 kW	1.8 l	06/00→								
<b>NISSAN - PULSAR Hatchback (C13)</b>										<b>10/14→</b>	
1.2 DIG-T	85 kW	1.2 l	10/14→						KH30024 ProKIT		
1.5 dCi	81 kW	1.5 l	10/14→								
1.6 DIG-T	140 kW	1.6 l	02/15→								





















      				
<b>NISSAN - QASHQAI II Wagon (J11, J11_)</b>				<b>11/13→</b>
1.2 DIG-T	85 kW	1.2 l	11/13→	 KH30166 ProKIT
1.5 dCi	81 kW	1.5 l	11/13→	
1.6 dCi	96 kW	1.6 l	11/13→	
1.6 dCi ALL MODE 4x4-i	96 kW	1.6 l	11/13→	
1.6 DIG-T	120 kW	1.6 l	10/14→	
<b>NISSAN - ROGUE</b>				<b>01/07→12/13</b>
2.5	124 kW	2.5 l	01/10→11/13	 KH30024 ProKIT
2.5	125 kW	2.5 l	01/10→11/13	
2.5	127 kW	2.5 l	01/07→12/13	
2.5 AWD	124 kW	2.5 l	01/10→11/13	
2.5 AWD	125 kW	2.5 l	01/10→11/13	
2.5 AWD	127 kW	2.5 l	01/07→12/13	
<b>NISSAN - SENTRA VI (B16)</b>				<b>09/06→12/12</b>
2.5	132 kW	2.5 l	09/06→12/12	 KH30024 ProKIT
2.5	149 kW	2.5 l	09/06→12/12	
<b>NISSAN - TERRANO II (R20)</b>				<b>02/93→09/07</b>
2.4 4WD	85 kW	2.4 l	05/96→01/02	 KH00024 ProKIT
				 -> 05/96 KH10383 ProKIT
				 ; Trim Level: 3-5 SEAT, 5-7 SEAT; -> 10/01 KH10384 ProKIT
2.4 4WD	87 kW	2.4 l	05/96→09/07	 ; -> 12/06 KH00024 ProKIT
				 ; -> 05/96 KH10383 ProKIT
				 ; Trim Level: 3-5 SEAT, 5-7 SEAT; -> 10/01 KH10384 ProKIT
2.4 i 12V 4WD	91 kW	2.4 l	02/93→12/97	 ; 05/96 -> KH00024 ProKIT
2.7 TD 4WD	74 kW	2.7 l	02/93→01/02	 ; 05/96 -> KH00024 ProKIT
				 ; 06/93 -> 05/96 KH10383 ProKIT
				 ; Trim Level: 3-5 SEAT, 5-7 SEAT; 05/96 -> 10/96 KH10384 ProKIT
2.7 TDi 4WD	92 kW	2.7 l	05/96→09/07	 ; Trim Level: 5, 7 SEAT; 07/96 -> KH10384 ProKIT
				 ; 09/98 -> KH00024 ProKIT
				 ; -> 12/06 KH00024 ProKIT
3.0 Di 4WD	113 kW	3 l	05/02→09/07	 KH00024 ProKIT
				 KH10384 ProKIT
<b>NISSAN - TERRANO II Van (R20)</b>				<b>04/03→09/07</b>
3.0 Di 4WD	113 kW	3 l	04/03→09/07	 KH00024 ProKIT
<b>NISSAN - TIIDA Hatchback / TIIDA Saloon (C11, SC11)</b>				<b>05/04→06/13</b>
1.5	80 kW	1.5 l	05/04→08/12	 ; ABS; J KH30011 ProKIT
1.5 4x4	80 kW	1.5 l	05/04→02/07	
1.8 4x4	95 kW	1.8 l	08/06→06/11	
1.5 dCi	76 kW	1.5 l	01/07→12/12	 ; ABS; J KH30011 ProKIT
1.6	80 kW	1.6 l	05/06→06/13	
1.6	87 kW	1.6 l	08/05→06/13	 ; OE 43202-1J60A; ABS KH30004 ProKIT
1.8	78 kW	1.8 l	01/07→06/11	
1.8	95 kW	1.8 l	08/06→12/12	
1.5 dCi	78 kW	1.5 l	09/07→12/11	 ; ABS; J KH30011 ProKIT
1.5 dCi	78 kW	1.5 l	09/07→12/12	
1.6	81 kW	1.6 l	09/07→12/11	 ; OE 43202-1J60A; ABS KH30004 ProKIT
1.6 (C11L)	81 kW	1.6 l	09/07→12/12	
1.8	93 kW	1.8 l	09/07→12/11	
1.8	93 kW	1.8 l	09/07→12/12	 KH30145 ProKIT
<b>NISSAN - URVAN Bus (E23)</b>				<b>04/85→11/88</b>
2.3 D (E23B)	51 kW	2.3 l	04/85→11/88	 ; 02/87 -> KH00117 ProKIT
<b>NISSAN - URVAN Bus / URVAN Van (E24)</b>				<b>05/87→05/97</b>
2.0	64 kW	2 l	05/87→05/97	 ; -> 07/94 KH00117 ProKIT
2.3 D	51 kW	2.3 l	01/88→05/97	 ; -> 12/88 KH00117 ProKIT
2.4 i	74 kW	2.4 l	05/89→09/93	 KH00117 ProKIT
2.5 D	59 kW	2.5 l	12/88→05/97	
2.5 D	59 kW	2.5 l	05/89→10/96	
<b>NISSAN - UTE (720)</b>				<b>04/83→03/86</b>
2.2 4WD	71 kW	2.2 l	04/83→03/86	 ; 05/83 -> 02/86 KH00024 ProKIT

















      					
<b>NISSAN - VANETTE CARGO Van (HC 23)</b>				<b>09/94→05/02</b>	
2.3 D	55 kW	2.3 l	09/94→05/02	 05/98 -> 06/00; Axle Version: C200B; Payload [kg]: 845  06/95 -> 06/00; Axle Version: C200B; Payload from [kg]: 980 → Payload to [kg]: 1,060  06/00 ->; Axle Version: C200B; Payload [kg]: 845  06/00 ->; Axle Version: C200B; Payload from [kg]: 980 → Payload to [kg]: 1,060	KH10383 ProKIT
<b>NISSAN - X-TRAIL I (T30)</b>				<b>06/01→01/13</b>	
2.0	103 kW	2 l	07/01→01/13		KH10034 ProKIT
2.0	110 kW	2 l	09/01→01/13	 -> 07/10	KH10400 ProKIT
2.0 4x4	206 kW	2 l	06/01→01/13		KH10034 ProKIT
2.0 4x4	103 kW	2 l	07/01→01/13		KH10034 ProKIT
2.0 4x4	110 kW	2 l	09/01→01/13		KH10026 ProKIT
2.2 dCi 4x4	100 kW	2.2 l	06/01→12/08		
2.2 Di 4x4	84 kW	2.2 l	07/01→10/05		
2.5 4x4	121 kW	2.5 l	09/02→01/13		
2.5 4x4	132 kW	2.5 l	11/02→01/13		
2.2 dCi	100 kW	2.2 l	12/03→01/13		KH10034 ProKIT
				 -> 02/07	KH10400 ProKIT
<b>NISSAN - X-TRAIL II (T31)</b>				<b>03/07→07/14</b>	
2.0	101 kW	2 l	09/12→02/14		KH30024 ProKIT
2.0	102 kW	2 l	06/08→02/14		
2.0 dCi	110 kW	2 l	06/07→11/13		
2.0 FWD	103 kW	2 l	06/08→11/13		
2.0 FWD	104 kW	2 l	03/07→11/13		
2.5	124 kW	2.5 l	09/07→11/13		
2.5	125 kW	2.5 l	09/07→07/14		
2.0 4x4	101 kW	2 l	06/07→11/13		KH30024 ProKIT
2.0 4x4	103 kW	2 l	06/08→11/13		KH30131 ProKIT
2.0 4x4	104 kW	2 l	06/07→11/13		
2.0 dCi 4x4	110 kW	2 l	06/07→11/13		
2.0 dCi 4x4	127 kW	2 l	06/07→11/13		
2.0 dCi 4x4	130 kW	2 l	10/09→11/13		
2.5 4x4	122 kW	2.5 l	01/08→11/13		
2.5 4x4	124 kW	2.5 l	06/07→11/13		
2.5 4x4	125 kW	2.5 l	06/07→07/14		
2.5 4x4	132 kW	2.5 l	09/07→07/14		
<b>NISSAN - X-TRAIL III (T32_, T32R, T32RR)</b>				<b>10/13→</b>	
1.7 dCi ALL MODE 4x4-i	96 kW	1.7 l	04/19→		KH30131 ProKIT
1.7 dCi ALL MODE 4x4-i	110 kW	1.7 l	04/19→		
1.7 dCi ALL MODE 4x4-i	120 kW	1.7 l	04/19→		
2.0 Hybrid 4WD	104 kW	2 l	10/17→		
2.5 ALL MODE 4x4-i	127 kW	2.5 l	10/13→		







<b>OPEL - ADAM (M13)</b>				<b>10/12→02/19</b>	
1.0	66 kW	1 l	07/14→11/18	15 Inch;	KH20017 ProKIT
1.0	85 kW	1 l	07/14→11/18		
				VIN -> F6058502;  14, 15 Inch	KH10042 ProKIT
				VIN F6058503 ->;  14, 15 Inch	KH10065 ProKIT
				16 Inch;	KH20030 ProKIT
1.2	51 kW	1.2 l	10/12→02/19	15 Inch;	KH20017 ProKIT
1.4	64 kW	1.4 l	10/12→02/19		
1.4	74 kW	1.4 l	10/12→02/19		
1.4 LPG	64 kW	1.4 l	07/13→11/18	14, 15 Inch	KH10042 ProKIT
1.4 S	110 kW	1.4 l	11/14→01/19	16 Inch	KH10065 ProKIT
				16 Inch;	KH20030 ProKIT
<b>OPEL - ADMIRAL A</b>				<b>04/65→03/69</b>	
4.6	140 kW	4.6 l	04/65→03/69	01/69 ->	KH00093 ProKIT
<b>OPEL - ADMIRAL B</b>				<b>03/69→07/76</b>	
2.8	103 kW	2.8 l	03/75→07/76		KH00093 ProKIT
2.8	107 kW	2.8 l	03/69→02/75		
<b>OPEL - AGILA (A) (H00)</b>				<b>09/00→12/07</b>	
1.0 (F68)	44 kW	1 l	08/03→12/07		KH10215 ProKIT
1.0 12V (F68)	43 kW	1 l	09/00→12/07	VIN -> 3G999999	KH10173 ProKIT
1.2 16V (F68)	55 kW	1.2 l	09/00→12/07	VIN 4G000001 ->	KH10122 ProKIT
1.2 16V Twinport (F68)	59 kW	1.2 l	07/04→12/07		KH10121 ProKIT
1.3 CDTI (F68)	51 kW	1.3 l	08/03→12/07	VIN -> 3G999999	KH10173 ProKIT
				VIN 4G000001 ->	KH10122 ProKIT
<b>OPEL - AGILA (B) (H08)</b>				<b>04/08→10/14</b>	
1.0 (F68)	48 kW	1 l	04/08→06/11		KH10137 ProKIT
1.0 (F68)	50 kW	1 l	07/11→07/14		KH10030 ProKIT
1.0 LPG (F68)	48 kW	1 l	01/10→06/11		
1.2 (F68)	63 kW	1.2 l	04/08→10/12		
1.2 (F68)	69 kW	1.2 l	04/10→10/14		
1.2 LPG (F68)	63 kW	1.2 l	04/08→10/10		
1.3 CDTI (F68)	55 kW	1.3 l	04/08→04/10		
<b>OPEL - ANTARA A (L07)</b>				<b>07/06→12/11</b>	
2.0 CDTI	93 kW	2 l	03/07→12/11	-> 12/10	KH30068 ProKIT
2.0 CDTI	93 kW	2 l	09/08→12/11		KH30087 ProKIT
2.0 CDTI	110 kW	2 l	08/06→12/11		
2.0 CDTI 4x4	110 kW	2 l	07/06→12/11		
2.4	104 kW	2.4 l	07/06→12/11		
2.4 4x4	103 kW	2.4 l	08/06→12/11		
2.4 LPG	103 kW	2.4 l	10/08→		
3.2 V6	167 kW	3.2 l	07/06→12/11		
2.0 CDTI	125 kW	2 l	01/16→		KH30087 ProKIT
2.0 CDTI 4x4	125 kW	2 l	01/16→		
2.2 CDTI	120 kW	2.2 l	12/10→12/15		
2.2 CDTI 4x4	120 kW	2.2 l	12/10→12/15		
2.2 CDTI 4x4	135 kW	2.2 l	12/10→12/15		
2.4	123 kW	2.4 l	12/10→		
2.4 4x4	123 kW	2.4 l	12/10→		
3.0	190 kW	3 l	11/10→12/15		
2.4	103 kW	2.4 l	09/08→12/11	-> 10/10	KH30068 ProKIT
					KH30087 ProKIT
2.4 LPG 4x4	103 kW	2.4 l	08/06→12/10		KH30068 ProKIT
					KH30087 ProKIT
<b>OPEL - ARENA Combi / ARENA Van (A97, TB, TF)</b>				<b>03/98→08/01</b>	
1.9 D	44 kW	1.9 l	03/98→08/01	(ABS)	KH00096 ProKIT
				(ABS)	KH00104 ProKIT
2.5 D	55 kW	2.5 l	03/98→08/01		KH00096 ProKIT
<b>OPEL - ASCONA A / ASCONA A Voyage (81_, 86_, 87_, 88_, 84_, 89_)</b>				<b>10/70→08/75</b>	
1.2 S	44 kW	1.2 l	04/72→08/75		KH00088 ProKIT
1.6 N	44 kW	1.6 l	03/75→08/75		
1.6 N	50 kW	1.6 l	10/70→02/75		
1.6 S	55 kW	1.6 l	03/75→08/75		
1.6 S	59 kW	1.6 l	10/70→02/75		
1.9 SR	65 kW	1.9 l	03/75→08/75		
1.9 SR	66 kW	1.9 l	10/70→02/75		
1.9 SR	66 kW	1.9 l	03/71→02/75		



























































     					
<b>OPEL - ASCONA C / ASCONA C Hatchback (J82)</b>				<b>09/81→08/88</b>	
1.3 N (F11, M11, F69)	44 kW	1.3 l	09/81→08/86	 ; -> 07/83	<b>KH10107</b> ProKIT
1.3 N (F68, M68)	44 kW	1.3 l	09/81→08/86		<b>KH00005</b> ProKIT
1.3 S (F11, M11, F68, M68)	55 kW	1.3 l	09/81→08/88	 ; 08/83 ->	<b>KH10107</b> ProKIT
1.3 S (F68, M68)	55 kW	1.3 l	09/81→08/88		<b>KH00005</b> ProKIT
1.6 (F11, F68, M11, M68)	60 kW	1.6 l	09/86→08/88		<b>KH10107</b> ProKIT
1.6 (F68, M68)	60 kW	1.6 l	09/86→08/88		<b>KH00005</b> ProKIT
1.6 i (F11, M11, F68, M68)	55 kW	1.6 l	09/87→08/88		
1.6 i (F68, M68)	55 kW	1.6 l	09/87→08/88		
1.6 i Cat (F11, M11, F68, M68)	55 kW	1.6 l	09/86→08/88		
1.6 i Cat (F68, M68)	55 kW	1.6 l	09/86→08/88		
1.6 (F11, M11, F68, M68)	55 kW	1.6 l	09/81→09/87	 ; -> 08/83	<b>KH10108</b> ProKIT
1.6 (F68, M68)	55 kW	1.6 l	09/81→08/88		<b>KH00005</b> ProKIT
1.6 D (F11, M11, F68, M68)	40 kW	1.6 l	03/82→08/88		<b>KH10108</b> ProKIT
1.6 D (F68, M68)	40 kW	1.6 l	03/82→08/88		<b>KH00005</b> ProKIT
1.6 S (F11, M11, F68, M68)	66 kW	1.6 l	09/81→08/86		
1.6 S (F68, M68)	66 kW	1.6 l	09/81→08/86		
1.8 (F11, M11, F68, M68)	62 kW	1.8 l	09/87→08/88		
1.8 (F68, M68)	62 kW	1.8 l	09/87→08/88		
1.8 i (F11, M11, F68, M68)	85 kW	1.8 l	09/82→08/86		
1.8 i (F68, M68)	85 kW	1.8 l	09/82→08/86		
2.0 i (F11, M11, F68, M68)	74 kW	2 l	08/87→08/88		
2.0 i (F11, M11, F68, M68)	85 kW	2 l	09/86→08/88		
2.0 i (F68, M68)	85 kW	2 l	09/86→08/88		
2.0 i Cat (F11, M11, F68, M68)	85 kW	2 l	09/86→08/88		
2.0 i Cat (F68, M68)	85 kW	2 l	09/86→08/88		
2.0 i GT (F11, M11, F68, M68)	95 kW	2 l	03/87→08/88		
2.0 i GT (F68, M68)	95 kW	2 l	03/87→08/88		
1.8 E (F11, M11, F68, M68)	74 kW	1.8 l	01/85→08/86	 ; 08/85 ->	<b>KH10108</b> ProKIT
1.8 E (F68, M68)	74 kW	1.8 l	01/85→08/86		<b>KH00005</b> ProKIT

<b>OPEL - ASTRA F / ASTRA F CLASSIC Estate / ASTRA F CLASSIC Hatchback / ASTRA F CLASSIC Saloon / ASTRA F Convertible / ASTRA F Estate / ASTRA F Estate Van / ASTRA F Hatchback / ASTRA G CLASSIC / ASTRA G CLASSIC Saloon (T92, T98)</b>				<b>09/91→07/09</b>	
1.4 (F08, M08, F68, M68)	55 kW	1.4 l	09/91→09/93	 ; VIN -> P_999999	<b>KH10107</b> ProKIT
1.4 (F19, M19)	55 kW	1.4 l	09/91→09/93	 ; (ABS); Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.4 (F35, M35)	55 kW	1.4 l	09/91→09/93	 ; (ABS); Rim Hole Number: 4	<b>KH30055</b> ProKIT
1.4 (F08, M08, F68, M68)	60 kW	1.4 l	09/92→01/98	 ; VIN -> NE299999, P5077914, P_999999	<b>KH10107</b> ProKIT
1.4 (F19, M19)	60 kW	1.4 l	09/92→09/98	 ; VIN P5077915 -> VIN P2999999, P3999999, P4999999, P5999999, P6999999, P8999999	<b>KH10108</b> ProKIT
1.4 (F35, M35)	60 kW	1.4 l	09/92→01/98	 ; (ABS); Rim Hole Number: 4	<b>KH30054</b> ProKIT
				 ; (ABS); Rim Hole Number: 4	<b>KH30055</b> ProKIT
1.4 16V (F08, F48)	66 kW	1.4 l	05/04→07/09	 ; (ABS); Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.4 16V (F69)	66 kW	1.4 l	05/04→07/09	 ; (ABS); Rim Hole Number: 4	<b>KH30055</b> ProKIT
1.4 i (F19, M19)	44 kW	1.4 l	01/98→08/02		
1.4 i (F35, M35)	44 kW	1.4 l	01/98→01/05		
1.4 i (M08, M68, F08, F68)	44 kW	1.4 l	01/98→08/02		
1.6 (F08, F48)	76 kW	1.6 l	03/06→06/08		
1.6 16V (F08, F48)	74 kW	1.6 l	05/04→02/06		
1.6 16V (F69)	74 kW	1.6 l	03/04→01/08		
1.6 i (F08, M08, F68, M68)	55 kW	1.6 l	01/98→08/02		
1.6 i (F19, M19)	55 kW	1.6 l	01/98→08/02		
1.6 i (F35, M35)	55 kW	1.6 l	01/98→01/05		
1.6 i (F70)	74 kW	1.6 l	03/92→12/94		
1.6 i 16V (F08, M08, F68, M68)	74 kW	1.6 l	01/98→08/02		
1.6 i 16V (F19, M19)	74 kW	1.6 l	01/98→08/02		
1.6 i 16V (F35, M35)	74 kW	1.6 l	01/98→01/05		
1.7 CDTI (F08, F48)	59 kW	1.7 l	06/04→07/09		
1.7 TD (F70)	60 kW	1.7 l	03/95→02/98		
1.8 (F08, M08, F68, M68)	85 kW	1.8 l	11/91→07/93		
1.8 (F35, M35)	85 kW	1.8 l	11/91→07/93		
1.8 i (F70)	66 kW	1.8 l	06/93→08/94		
1.8 i 16V (F19, M19)	82 kW	1.8 l	09/95→09/96		
1.4 i (F08, M08, F68, M68)	44 kW	1.4 l	09/91→01/98		<b>KH10376</b> ProKIT
1.4 i (F19, M19)	44 kW	1.4 l	09/91→09/98	 ; VIN -> P_999999	<b>KH10107</b> ProKIT
1.4 i (F35, M35)	44 kW	1.4 l	09/91→01/98	 ; (ABS); Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.4 i (F70)	44 kW	1.4 l	10/91→01/99	 ; (ABS); Rim Hole Number: 4	<b>KH30055</b> ProKIT
1.6 i (F70)	55 kW	1.6 l	10/91→02/98	 ; (ABS); Rim Hole Number: 4	<b>KH30055</b> ProKIT
1.6 Si (F19, M19)	74 kW	1.6 l	05/92→12/94		

     					
<b>OPEL - ASTRA F / ASTRA F CLASSIC Estate / ASTRA F CLASSIC Hatchback / ASTRA F CLASSIC Saloon / ASTRA F Convertible / ASTRA F Estate / ASTRA F Estate Van / ASTRA F Hatchback / ASTRA G CLASSIC / ASTRA G CLASSIC Saloon (T92, T98)</b>					
1.4 i 16V	66 kW	1.4 l	01/96→03/01		KH10376 ProKIT
1.4 i 16V (F08, M08, F68, M68)	66 kW	1.4 l	09/96→02/98	; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
1.4 i 16V (F19, M19)	66 kW	1.4 l	02/96→09/98	; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.4 i 16V (F35, M35)	66 kW	1.4 l	02/96→01/98	; (ABS)	Rim Hole Number: 4
1.6 i (F70)	52 kW	1.6 l	02/93→07/96		
1.6 i 16V (F70)	74 kW	1.6 l	08/94→03/98		
1.4 Si	60 kW	1.4 l	05/93→03/01	; 06/93 ->; VIN -> NE299999, P5077914	KH10107 ProKIT
				; 06/93 ->; VIN P5077915 -> VIN P2999999, P3999999, P4999999, P5999999, P6999999, P8999999	KH10108 ProKIT
					KH10376 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.4 Si (F08, M08, F68, M68)	60 kW	1.4 l	03/92→01/98		KH10376 ProKIT
1.4 Si (F19, M19)	60 kW	1.4 l	03/92→09/98	; VIN -> NE299999, P5077914, P_999999	KH10107 ProKIT
1.4 Si (F35, M35)	60 kW	1.4 l	03/92→01/98	; VIN P5077915 -> VIN P2999999, P3999999, P4999999, P5999999, P6999999, P8999999	KH10108 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 (F08, M08, F68, M68)	55 kW	1.6 l	09/95→01/98		KH10108 ProKIT
1.6 (F35, M35)	55 kW	1.6 l	09/95→01/98		KH10206 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 (F19, M19)	55 kW	1.6 l	09/95→09/98	; -> 01/98	KH10108 ProKIT
				; -> 01/98	KH10206 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i	52 kW	1.6 l	03/93→08/96		KH10376 ProKIT
				; VIN P8100001 -> VIN RB000000	KH10108 ProKIT
				; VIN W5013209 ->; (ABS)	KH10206 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i	55 kW	1.6 l	01/96→03/01		KH10376 ProKIT
				; VIN -> P5077914, NE299999	KH10107 ProKIT
				; VIN P5077915 -> VIN RB000000	KH10108 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i (F08, M08, F68, M68)	52 kW	1.6 l	05/93→07/96	; -> 06/95; VIN P5077915 ->	KH10108 ProKIT
					KH10376 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i (F08, M08, F68, M68)	55 kW	1.6 l	09/91→01/98		KH10376 ProKIT
1.6 Si (F08, M08, F68, M68)	74 kW	1.6 l	03/92→12/94	; VIN -> NE299999, P5077914, P_999999	KH10107 ProKIT
1.6 Si (F35, M35)	74 kW	1.6 l	03/92→12/94	; VIN P5077915 ->	KH10108 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i (F19, M19)	52 kW	1.6 l	05/93→07/96		KH10376 ProKIT
				; VIN P5077915 ->	KH10108 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i (F19, M19)	55 kW	1.6 l	03/92→09/98	; -> 08/94; VIN -> NE299999, P5077914, P_999999	KH10107 ProKIT
				; -> 08/94; VIN -> P3999999	KH10108 ProKIT
					KH10376 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT
1.6 i (F35, M35)	52 kW	1.6 l	05/93→07/96		KH10376 ProKIT
				; VIN P8100001 ->	KH10108 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30054 ProKIT
				; (ABS)	Rim Hole Number: 4 KH30055 ProKIT



										
<b>OPEL - ASTRA F / ASTRA F CLASSIC Estate / ASTRA F CLASSIC Hatchback / ASTRA F CLASSIC Saloon / ASTRA F Convertible / ASTRA F Estate / ASTRA F Estate Van / ASTRA F Hatchback / ASTRA G CLASSIC / ASTRA G CLASSIC Saloon (T92, T98)</b>										
1.6 i (F35, M35)	55 kW	1.6 l	09/91→01/98		07/95 ->					KH10206 ProKIT
										KH10376 ProKIT
					VIN -> NE299999, P5077914, P_999999					KH10107 ProKIT
					VIN P5077915 ->					KH10108 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.6 i 16V (F08, M08, F68, M68)	74 kW	1.6 l	08/94→01/98							KH10376 ProKIT
1.6 i 16V (F35, M35)	74 kW	1.6 l	08/94→01/98		VIN W5013209 ->; ABS					KH10206 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.6 i 16V (F19, M19)	74 kW	1.6 l	08/94→09/98		-> 01/98; VIN P8100001 ->					KH10108 ProKIT
					-> 01/98; VIN W5013209 ->; ABS					KH10206 ProKIT
										KH10376 ProKIT
					VIN -> NE299999, P5077914					KH10107 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.7 D (F08, M08, F68, M68)	42 kW	1.7 l	12/91→09/92		VIN -> S_999999					KH10108 ProKIT
1.7 D (F19, M19)	42 kW	1.7 l	03/92→09/92		VIN T_000001 ->					KH10206 ProKIT
1.7 D (F35, M35)	42 kW	1.7 l	12/91→09/92		ABS, Rim Hole Number: 4					KH30054 ProKIT
1.7 D (F35, M35)	44 kW	1.7 l	07/92→01/98		ABS, Rim Hole Number: 4					KH30055 ProKIT
1.7 D (F70)	42 kW	1.7 l	12/91→09/92		ABS, Rim Hole Number: 4					KH30055 ProKIT
1.7 TD (F08, M08, F68, M68)	50 kW	1.7 l	11/94→01/98							
1.7 TD (F35, M35)	50 kW	1.7 l	11/94→01/98							
1.7 TDS (F08, M08, F68, M68)	60 kW	1.7 l	12/91→01/98							
1.7 TDS (F35, M35)	60 kW	1.7 l	12/91→01/98							
1.8 i 16V (F08, M08, F68, M68)	85 kW	1.8 l	09/94→01/98							
2.0 i (F08, M08, F68, M68)	85 kW	2 l	09/91→01/98							
2.0 i (F35, M35)	85 kW	2 l	09/91→07/94							
2.0 i 16V (F08, M08, F68, M68)	100 kW	2 l	02/95→01/98							
2.0 i 16V (F35, M35)	100 kW	2 l	02/95→01/98							
1.7 D (F08, M08, F68, M68)	44 kW	1.7 l	07/92→01/98		09/92 ->; VIN -> S_999999					KH10108 ProKIT
					09/92 ->; VIN T_000001 ->					KH10206 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.7 D (F19, M19)	44 kW	1.7 l	07/92→09/98		09/92 -> 01/98; VIN -> S_999999					KH10108 ProKIT
					09/92 -> 01/98; VIN T_000001 ->					KH10206 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.7 D (F70)	44 kW	1.7 l	07/92→01/99		-> 01/98; VIN -> S_999999					KH10108 ProKIT
1.7 TD (F19, M19)	50 kW	1.7 l	11/94→09/98		-> 01/98; VIN T_000001 ->					KH10206 ProKIT
1.7 TD (F70)	50 kW	1.7 l	08/94→01/99		ABS, Rim Hole Number: 4					KH30054 ProKIT
1.7 TDS (F19, M19)	60 kW	1.7 l	03/92→09/98		ABS, Rim Hole Number: 4					KH30055 ProKIT
1.8 i 16V (F19, M19)	85 kW	1.8 l	11/94→09/98		ABS, Rim Hole Number: 4					KH30055 ProKIT
2.0 i (F19, M19)	85 kW	2 l	03/92→09/98							
2.0 i 16V (F19, M19)	100 kW	2 l	02/95→09/98							
1.8 i (F08, M08, F68, M68)	66 kW	1.8 l	09/91→01/98		-> 08/94; VIN -> S_999999					KH10108 ProKIT
1.8 i (F19, M19)	66 kW	1.8 l	03/92→09/98		-> 08/94; VIN T_000001 ->					KH10206 ProKIT
1.8 i (F35, M35)	66 kW	1.8 l	09/91→01/98		ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.8 i 16V	85 kW	1.8 l	11/94→03/01		-> 02/01; VIN -> S_999999					KH10108 ProKIT
					-> 02/01; VIN T_000001 ->					KH10206 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.8 i 16V (F08, M08, F68, M68)	92 kW	1.8 l	06/93→08/94		07/93 ->; VIN -> S_999999					KH10108 ProKIT
1.8 i 16V (F19, M19)	92 kW	1.8 l	06/93→10/94		07/93 ->; VIN T_000001 ->					KH10206 ProKIT
1.8 i 16V (F35, M35)	92 kW	1.8 l	06/93→01/98		ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT
1.8 i 16V (F35, M35)	85 kW	1.8 l	07/94→01/98		08/94 ->; VIN -> S_999999					KH10108 ProKIT
					08/94 ->; VIN T_000001 ->					KH10206 ProKIT
					ABS, Rim Hole Number: 4					KH30054 ProKIT
					ABS, Rim Hole Number: 4					KH30055 ProKIT



**OPEL - ASTRA F / ASTRA F CLASSIC Estate / ASTRA F CLASSIC Hatchback / ASTRA F CLASSIC Saloon / ASTRA F Convertible / ASTRA F Estate / ASTRA F Estate Van / ASTRA F Hatchback / ASTRA G CLASSIC / ASTRA G CLASSIC Saloon (T92, T98) 09/91→07/09**

2.0 GSI 16V (F08, M08, F68, M68)	110 kW	2 l	09/91→01/98	; 07/94 ->; VIN -> S_999999	KH10108 ProKIT
2.0 i 16V (F35, M35)	110 kW	2 l	03/93→01/98	; 07/94 ->; VIN T_000001 ->	KH10206 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT
2.0 i	85 kW	2 l	03/93→10/94	; 06/93 ->; VIN -> S_999999	KH10108 ProKIT
				; 06/93 ->; VIN T_000001 ->	KH10206 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT

**OPEL - ASTRA G Convertible / ASTRA G Coupe / ASTRA G Estate (T98) 02/98→10/05**

1.2 16V (F35)	48 kW	1.2 l	02/98→09/00	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
1.2 16V (F35)	55 kW	1.2 l	09/00→07/04	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
1.4 16V (F35)	66 kW	1.4 l	06/98→07/04	; Rim Hole Number: 5; (ABS)	KH30059 ProKIT
1.6 (F35)	55 kW	1.6 l	02/98→09/00	; Rim Hole Number: 4	KH30054 ProKIT
1.6 (F35)	62 kW	1.6 l	09/00→07/04	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.6 (F35)	76 kW	1.6 l	12/02→05/04	; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6 (F67)	76 kW	1.6 l	01/03→10/05		
1.6 16V (F07)	74 kW	1.6 l	03/00→05/05		
1.6 16V (F07)	76 kW	1.6 l	03/00→05/05		
1.6 16V (F35)	74 kW	1.6 l	02/98→07/04		
1.6 16V (F67)	74 kW	1.6 l	03/01→10/05		
1.6 CNG (F35)	71 kW	1.6 l	03/03→07/04		
1.7 CDTi (F35)	59 kW	1.7 l	04/03→05/04		
1.7 DTI 16V (F35)	55 kW	1.7 l	02/00→07/04		
1.7 TD (F35)	50 kW	1.7 l	02/98→08/00		
1.4 LPG (F35)	66 kW	1.4 l	03/98→07/04	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.6 LPG (F35)	74 kW	1.6 l	03/98→07/04		
1.6 LPG (F35)	76 kW	1.6 l	06/02→07/04		
1.8 16V (F07)	85 kW	1.8 l	03/00→10/00	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
1.8 16V (F07)	92 kW	1.8 l	09/00→05/05	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
1.8 16V (F67)	92 kW	1.8 l	03/01→10/05	; Rim Hole Number: 5; (ABS)	KH30059 ProKIT
2.0 16V (F35)	100 kW	2 l	02/98→07/04	; (ABS)	KH30114 ProKIT
2.0 DTI 16V (F35)	74 kW	2 l	08/99→07/04	; (ABS)	KH30114 ProKIT
2.2 16V (F07)	108 kW	2.2 l	09/00→05/05	; (ABS)	KH30130 ProKIT
2.2 16V (F35)	108 kW	2.2 l	03/01→07/04		
1.8 16V (F35)	85 kW	1.8 l	02/98→09/00	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
1.8 16V (F35)	92 kW	1.8 l	09/00→07/04	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
2.0 DI (F35)	60 kW	2 l	02/98→07/04	; Rim Hole Number: 5; (ABS)	KH30059 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; (ABS)	KH30114 ProKIT
2.0 16V Turbo (F07)	140 kW	2 l	09/00→08/01	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
2.0 16V Turbo (F07)	141 kW	2 l	08/01→05/05	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
2.0 16V Turbo (F07)	147 kW	2 l	11/02→05/05	; Rim Hole Number: 5; (ABS)	KH30059 ProKIT
2.0 16V Turbo (F67)	147 kW	2 l	11/02→10/05	; (ABS)	KH30114 ProKIT
2.0 OPC (F67)	141 kW	2 l	03/02→10/05	; (ABS)	KH30114 ProKIT
2.2 16V (F67)	108 kW	2.2 l	03/01→10/05		
2.2 DTI (F07)	92 kW	2.2 l	09/02→05/05		
2.2 DTI (F35)	86 kW	2.2 l	09/02→07/04		
2.2 DTI (F35)	92 kW	2.2 l	09/02→07/04		
2.2 DTI (F67)	92 kW	2.2 l	09/02→10/05		
2.0 OPC (F35)	141 kW	2 l	09/02→07/04	; (ABS)	KH30114 ProKIT
2.0 OPC (F35)	147 kW	2 l	11/02→07/04		

**OPEL - ASTRA G Estate Van (F70) 01/99→04/05**

1.6 (F70)	55 kW	1.6 l	01/99→09/00	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
1.6 (F70)	62 kW	1.6 l	09/00→04/05	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
1.7 DTI 16V (F70)	55 kW	1.7 l	02/00→04/05	; Rim Hole Number: 5; (ABS)	KH30059 ProKIT
1.7 TD (F70)	50 kW	1.7 l	01/99→04/05	; (ABS)	KH30055 ProKIT
1.6 (F70)	76 kW	1.6 l	02/04→11/04	; (ABS)	KH30055 ProKIT
1.7 CDTi (F70)	59 kW	1.7 l	07/03→11/04		
2.0 DI (F70)	60 kW	2 l	01/99→04/05	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
				; Rim Hole Number: 4; (ABS)	KH30058 ProKIT
				; Rim Hole Number: 5; (ABS)	KH30059 ProKIT

**OPEL - ASTRA G Hatchback / ASTRA G Saloon (T98) 02/98→12/09**

1.2 16V (F08, F48)	48 kW	1.2 l	02/98→09/00	; (ABS); Rim Hole Number: 4	KH30057 ProKIT
1.2 16V (F08, F48)	55 kW	1.2 l	09/00→01/05	; Rim Hole Number: 4; (ABS)	KH30058 ProKIT



**OPEL - ASTRA G Hatchback / ASTRA G Saloon (T98)**










































**02/98→12/09**

1.2 16V (F69)	48 kW	1.2 l	09/98→09/00	; Rim Hole Number: 5;	KH30059 ProKIT
1.2 16V (F69)	55 kW	1.2 l	09/00→01/05	; ; Rim Hole Number: 4	KH30054 ProKIT
1.4 16V (F08, F48)	66 kW	1.4 l	02/98→01/05	; ; Rim Hole Number: 4	KH30055 ProKIT
1.4 16V (F69)	66 kW	1.4 l	09/98→01/05	; ; Rim Hole Number: 4	
1.6 (F08, F48)	55 kW	1.6 l	02/98→09/00		
1.6 (F08, F48)	62 kW	1.6 l	09/00→01/05		
1.6 (F08, F48)	76 kW	1.6 l	11/02→01/05		
1.6 (F69)	55 kW	1.6 l	09/98→09/00		
1.6 (F69)	62 kW	1.6 l	09/00→01/05		
1.6 (F69)	76 kW	1.6 l	12/02→12/09		
1.6 16V (F08, F48)	74 kW	1.6 l	02/98→01/05		
1.6 16V (F69)	74 kW	1.6 l	09/98→01/05		
1.6 LPG (F08, F48)	74 kW	1.6 l	03/98→01/05		
1.6 LPG (F69)	74 kW	1.6 l	06/02→01/05		
1.7 CDTI (F08, F48)	59 kW	1.7 l	04/03→01/05		
1.7 CDTI (F69)	59 kW	1.7 l	04/03→12/09		
1.7 DTI 16V (F08, F48)	55 kW	1.7 l	02/00→01/05		
1.7 DTI 16V (F69)	55 kW	1.7 l	02/00→01/05		
1.7 TD (F08, F48)	50 kW	1.7 l	02/98→08/00		
1.7 TD (F69)	50 kW	1.7 l	09/98→08/00		
1.4 (F08, F48)	66 kW	1.4 l	09/07→12/09	; ; Rim Hole Number: 4	KH30054 ProKIT
1.4 (F69)	66 kW	1.4 l	09/07→12/09	; ; Rim Hole Number: 4	KH30055 ProKIT
1.4 LPG (F08, F48)	66 kW	1.4 l	02/98→01/05	; ; Rim Hole Number: 4	KH30054 ProKIT
1.4 LPG (F69)	66 kW	1.4 l	03/98→01/05		
1.6 LPG (F08, F48)	76 kW	1.6 l	11/02→06/07		
1.8 16V (F08, F48)	85 kW	1.8 l	02/98→09/00	; ; Rim Hole Number: 4	KH30057 ProKIT
1.8 16V (F08, F48)	92 kW	1.8 l	09/00→01/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V (F69)	85 kW	1.8 l	09/98→09/00	; Rim Hole Number: 5;	KH30059 ProKIT
1.8 16V (F69)	92 kW	1.8 l	06/00→01/05	; ; Rim Hole Number: 4	KH30055 ProKIT
2.0 DI (F08, F48)	60 kW	2 l	02/98→01/05	; ; Rim Hole Number: 4	KH30055 ProKIT
2.0 DI (F69)	60 kW	2 l	09/98→01/05	;	KH30114 ProKIT
2.0 16V (F08, F48)	100 kW	2 l	02/98→01/05	; ; Rim Hole Number: 4	KH30057 ProKIT
2.0 16V (F69)	100 kW	2 l	09/98→01/05	; Rim Hole Number: 4;	KH30058 ProKIT
2.0 16V OPC (F08, F48)	118 kW	2 l	11/99→09/02	; Rim Hole Number: 5;	KH30059 ProKIT
2.0 DTI 16V (F08, F48)	74 kW	2 l	08/99→01/05	;	KH30114 ProKIT
2.0 DTI 16V (F69)	74 kW	2 l	08/99→01/05	;	KH30130 ProKIT
2.0 OPC (F08, F48)	141 kW	2 l	09/02→01/05	; ; Rim Hole Number: 4	KH30057 ProKIT
2.0 OPC (F08, F48)	147 kW	2 l	11/02→01/05	; Rim Hole Number: 4;	KH30058 ProKIT
2.2 16V (F08, F48)	108 kW	2.2 l	06/00→01/05	; Rim Hole Number: 5;	KH30059 ProKIT
2.2 DTI (F08, F48)	86 kW	2.2 l	09/02→01/05	;	KH30114 ProKIT
2.2 DTI (F08, F48)	92 kW	2.2 l	09/02→01/05	;	
2.2 DTI (F69)	86 kW	2.2 l	09/02→01/05		
2.2 DTI (F69)	92 kW	2.2 l	09/02→01/05		
2.2 16V (F69)	108 kW	2.2 l	03/01→01/05	;	KH30114 ProKIT
				;	KH30130 ProKIT





















**OPEL - ASTRA H / ASTRA H Estate / ASTRA H Estate Van / ASTRA H GTC / 01/04→05/14  
ASTRA H Saloon / ASTRA H TwinTop (A04, L70)**







1.2 (L48)	59 kW	1.2 l	08/05→10/10	; Rim Hole Number: 5	KH30046 ProKIT
1.3 CDTI (L08)	66 kW	1.3 l	04/05→10/10	; Rim Hole Number: 4	KH30072 ProKIT
1.3 CDTI (L35)	66 kW	1.3 l	08/05→10/10		
1.3 CDTI (L48)	66 kW	1.3 l	08/05→10/10	; Rim Hole Number: 4	KH30041 ProKIT
1.3 CDTI (L69)	66 kW	1.3 l	02/07→10/10	; Rim Hole Number: 5	KH30044 ProKIT
1.3 CDTI (L70)	66 kW	1.3 l	08/05→10/10		
1.4 (L35)	55 kW	1.4 l	08/04→10/10		
1.4 (L35)	66 kW	1.4 l	08/04→10/10		
1.4 (L48)	55 kW	1.4 l	04/04→10/04		
1.4 (L48)	66 kW	1.4 l	03/04→10/10		
1.4 LPG (L35)	66 kW	1.4 l	08/09→10/10		
1.4 LPG (L48)	66 kW	1.4 l	08/09→10/10		
1.6 (L35)	77 kW	1.6 l	08/04→10/10		
1.6 (L35)	85 kW	1.6 l	12/06→05/14		
1.6 (L48)	77 kW	1.6 l	03/04→10/10		
1.6 (L48)	85 kW	1.6 l	12/06→05/14		
1.6 (L67)	77 kW	1.6 l	09/05→10/10		
1.6 (L67)	85 kW	1.6 l	12/06→10/10		
1.6 (L69)	85 kW	1.6 l	02/07→05/14		
1.6 EcoTec (L70)	76 kW	1.6 l	02/04→11/04		
1.6 LPG (L35)	85 kW	1.6 l	08/09→10/10		
1.6 Turbo (L35)	132 kW	1.6 l	02/07→10/10		
1.6 Turbo (L48)	132 kW	1.6 l	02/07→10/10		
1.6 Turbo (L67)	132 kW	1.6 l	02/07→10/10		
1.7 CDTI (L35)	59 kW	1.7 l	08/04→10/10		
1.7 CDTI (L35)	74 kW	1.7 l	08/04→10/10		
1.7 CDTI (L48)	59 kW	1.7 l	03/04→10/10		
1.7 CDTI (L48)	74 kW	1.7 l	03/04→10/10		





























      					
<b>OPEL - ASTRA H / ASTRA H Estate / ASTRA H Estate Van / ASTRA H GTC / 01/04→05/14</b> <b>ASTRA H Saloon / ASTRA H TwinTop (A04, L70)</b>					
1.7 CDTi (L48)	81 kW	1.7 l	02/07→05/14	 ; Rim Hole Number: 5	KH30046 ProKIT
1.7 CDTi (L69)	74 kW	1.7 l	02/07→10/10	 ; Rim Hole Number: 4	KH30072 ProKIT
1.7 CDTi (L69)	81 kW	1.7 l	02/07→05/14	 ; Rim Hole Number: 4	KH30041 ProKIT
1.7 CDTi (L70)	74 kW	1.7 l	03/04→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.8 (L08)	92 kW	1.8 l	03/05→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.8 (L08)	103 kW	1.8 l	01/06→10/10		
1.8 (L35)	92 kW	1.8 l	08/04→10/10		
1.8 (L35)	103 kW	1.8 l	08/05→05/14		
1.8 (L48)	92 kW	1.8 l	01/04→10/10		
1.8 (L48)	103 kW	1.8 l	01/06→10/10		
1.8 (L67)	92 kW	1.8 l	09/05→10/10		
1.8 (L67)	103 kW	1.8 l	09/05→10/10		
1.8 (L69)	103 kW	1.8 l	02/07→09/12		
1.4 (L08)	55 kW	1.4 l	03/05→10/10	 ; Rim Hole Number: 5	KH30046 ProKIT
1.4 (L08)	66 kW	1.4 l	03/05→10/10	 ; Rim Hole Number: 4	KH30072 ProKIT
1.4 (L69)	66 kW	1.4 l	02/07→06/10		
1.4 EcoTec (L70)	66 kW	1.4 l	12/04→12/12		
1.6 (L08)	77 kW	1.6 l	03/05→10/10		
1.6 (L08)	85 kW	1.6 l	12/06→10/10		
1.6 (L69)	77 kW	1.6 l	02/07→06/10		
1.6 EcoTec (L70)	85 kW	1.6 l	10/06→12/10		
1.6 Turbo (L08)	132 kW	1.6 l	02/07→10/10		
1.7 CDTi (L08)	74 kW	1.7 l	03/05→10/10		
1.7 CDTi (L08)	59 kW	1.7 l	03/05→10/10		
1.7 CDTi (L08)	81 kW	1.7 l	02/07→10/10		
1.7 CDTi (L70)	59 kW	1.7 l	12/04→07/07		
1.4 (L48)	59 kW	1.4 l	04/04→10/04	 ; Rim Hole Number: 5	KH30046 ProKIT
1.4 (L67)	66 kW	1.4 l	10/05→10/10	 ; Rim Hole Number: 5	KH30046 ProKIT
				 ; Rim Hole Number: 4	KH30072 ProKIT
				 ; Rim Hole Number: 4	KH30041 ProKIT
1.7 CDTi (L08)	92 kW	1.7 l	02/07→10/10	 ; Rim Hole Number: 4	KH30072 ProKIT
1.9 CDTi (L70)	74 kW	1.9 l	08/05→12/12	 ; Rim Hole Number: 5	KH30084 ProKIT
1.7 CDTi (L35)	81 kW	1.7 l	02/07→05/14	 ; Rim Hole Number: 4	KH30072 ProKIT
1.7 CDTi (L70)	81 kW	1.7 l	02/07→10/10	 ; Rim Hole Number: 5;	KH30084 ProKIT
				VIN -> 62079978, 65076709, 68027072	
				 ; Rim Hole Number: 5;	KH30046 ProKIT
				VIN 62079979, 65076710, 68027073, 8B000001 ->	
				 ; Rim Hole Number: 4	KH30041 ProKIT
				 ; Rim Hole Number: 5	KH30044 ProKIT
1.7 CDTi (L35)	92 kW	1.7 l	02/07→05/14	 ; Rim Hole Number: 4	KH30072 ProKIT
1.7 CDTi (L48)	92 kW	1.7 l	02/07→05/14	 ; Rim Hole Number: 5	KH30084 ProKIT
1.7 CDTi (L70)	92 kW	1.7 l	02/07→10/10	 ; Rim Hole Number: 4	KH30041 ProKIT
1.9 CDTi (L70)	88 kW	1.9 l	09/05→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTi 16V (L70)	88 kW	1.9 l	08/04→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTi (L08)	110 kW	1.9 l	03/05→10/10	 ; Rim Hole Number: 4	KH30072 ProKIT
1.9 CDTi (L35)	110 kW	1.9 l	09/04→10/10	 ; Rim Hole Number: 5	KH30074 ProKIT
1.9 CDTi (L48)	110 kW	1.9 l	09/04→10/10	 ; Rim Hole Number: 4	KH30041 ProKIT
1.9 CDTi (L67)	110 kW	1.9 l	09/05→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTi (L70)	110 kW	1.9 l	09/04→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
2.0 Turbo (L08)	177 kW	2 l	08/05→10/10		
2.0 Turbo (L48)	177 kW	2 l	03/05→10/10		
1.9 CDTi (L08)	74 kW	1.9 l	01/06→10/10	 ; Rim Hole Number: 4	KH30072 ProKIT
1.9 CDTi (L08)	88 kW	1.9 l	09/05→10/10	 ; Rim Hole Number: 5;	KH30046 ProKIT
1.9 CDTi (L35)	88 kW	1.9 l	09/05→10/10	VIN -> 62083449, 65076709, 68027072	
1.9 CDTi (L48)	74 kW	1.9 l	09/05→10/10	 ; Rim Hole Number: 5;	KH30084 ProKIT
1.9 CDTi (L48)	88 kW	1.9 l	06/04→10/10	VIN 62083450, 65076710, 68027073, 8B000001 ->	
1.9 CDTi 16V (L08)	88 kW	1.9 l	03/05→10/10	 ; Rim Hole Number: 4	KH30041 ProKIT
1.9 CDTi 16V (L35)	88 kW	1.9 l	08/04→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTi 16V (L48)	88 kW	1.9 l	04/04→10/10		
2.0 Turbo (L08)	125 kW	2 l	03/05→10/10	 ; Rim Hole Number: 5	KH30044 ProKIT
2.0 Turbo (L08)	147 kW	2 l	03/05→10/10		
2.0 Turbo (L35)	125 kW	2 l	08/04→10/10		
2.0 Turbo (L35)	147 kW	2 l	09/04→10/10		
2.0 Turbo (L48)	125 kW	2 l	03/04→10/10		
2.0 Turbo (L48)	147 kW	2 l	09/04→10/10		
2.0 Turbo (L67)	125 kW	2 l	09/05→10/10		
2.0 Turbo (L67)	147 kW	2 l	09/05→10/10		



    				
<b>OPEL - ASTRA H / ASTRA H Estate / ASTRA H Estate Van / ASTRA H GTC / 01/04→05/14</b>				
<b>ASTRA H Saloon / ASTRA H TwinTop (A04, L70)</b>				
1.9 CDTi (L35)	74 kW	1.9 l	09/05→10/10	 Rim Hole Number: 5; KH30046 ProKIT  VIN -> 62083449, 65076709, 68027072
				 Rim Hole Number: 5; KH30084 ProKIT  VIN 62083450, 65076710, 68027073, 8B000001 ->
				 Rim Hole Number: 4 KH30041 ProKIT  Rim Hole Number: 5 KH30044 ProKIT  Rim Hole Number: 4 KH30072 ProKIT
<b>OPEL - ASTRA J / ASTRA J GTC / ASTRA J Saloon / ASTRA J Sports Tourer 09/09→</b>				
<b>(P10)</b>				
1.3 CDTi (35)	70 kW	1.3 l	10/10→10/14	  15 Inch KH30119 ProKIT
1.3 CDTi (68)	70 kW	1.3 l	12/09→10/15	
1.3 CDTi (69)	70 kW	1.3 l	06/12→10/15	
1.4 (08)	74 kW	1.4 l	10/11→10/15	
1.4 (08)	88 kW	1.4 l	10/11→	
1.4 (08)	103 kW	1.4 l	10/11→	
1.4 (35)	74 kW	1.4 l	10/10→10/15	
1.4 (68)	64 kW	1.4 l	12/09→10/15	
1.4 (68)	74 kW	1.4 l	12/09→10/15	
1.4 (69)	74 kW	1.4 l	06/12→10/15	
1.4 LPG (35)	103 kW	1.4 l	12/11→10/15	
1.4 LPG (68)	103 kW	1.4 l	01/12→10/15	
1.4 LPG (69)	103 kW	1.4 l	07/14→	
1.4 Turbo (35)	88 kW	1.4 l	10/10→10/15	
1.4 Turbo (35)	103 kW	1.4 l	10/10→10/15	
1.4 Turbo (68)	88 kW	1.4 l	10/10→10/15	
1.4 Turbo (68)	103 kW	1.4 l	12/09→10/15	
1.4 Turbo (69)	88 kW	1.4 l	06/12→10/15	
1.4 Turbo (69)	103 kW	1.4 l	06/12→	
1.6 (08)	132 kW	1.6 l	10/11→	
1.6 (35)	85 kW	1.6 l	10/10→10/15	
1.6 (68)	85 kW	1.6 l	12/09→10/15	
1.6 (69)	85 kW	1.6 l	06/12→	
1.6 CDTi (08)	81 kW	1.6 l	07/14→	
1.6 CDTi (08)	100 kW	1.6 l	07/14→	
1.6 CDTi (68)	81 kW	1.6 l	02/14→10/15	
1.6 CDTi (68)	100 kW	1.6 l	11/13→10/15	
1.6 CDTi (69)	81 kW	1.6 l	04/14→	
1.6 CDTi (69)	100 kW	1.6 l	01/14→	
1.6 SIDI (35)	125 kW	1.6 l	12/12→10/15	
1.6 SIDI (69)	125 kW	1.6 l	06/12→10/15	
1.6 CDTi (35)	81 kW	1.6 l	02/14→10/15	 KH30089 ProKIT
1.6 CDTi (35)	100 kW	1.6 l	11/13→10/15	  15 Inch KH30119 ProKIT
1.6 SIDI (08)	125 kW	1.6 l	12/12→	
1.6 SIDI (08)	147 kW	1.6 l	07/13→	
1.6 SIDI (68)	125 kW	1.6 l	12/12→10/15	
1.6 Turbo (35)	132 kW	1.6 l	10/10→10/15	
1.6 Turbo (68)	132 kW	1.6 l	12/09→10/15	
1.6 Turbo (69)	132 kW	1.6 l	06/12→	
1.7 CDTi (08)	81 kW	1.7 l	10/11→10/15	
1.7 CDTi (08)	96 kW	1.7 l	10/11→10/15	
1.7 CDTi (35)	74 kW	1.7 l	10/10→10/15	
1.7 CDTi (35)	81 kW	1.7 l	10/10→10/15	
1.7 CDTi (35)	92 kW	1.7 l	10/10→10/15	
1.7 CDTi (35)	96 kW	1.7 l	10/10→10/15	
1.7 CDTi (68)	81 kW	1.7 l	09/09→10/15	
1.7 CDTi (68)	92 kW	1.7 l	12/09→10/15	
1.7 CDTi (68)	96 kW	1.7 l	07/11→10/15	
1.7 CDTi (69)	81 kW	1.7 l	06/12→10/15	
1.7 CDTi (69)	96 kW	1.7 l	06/12→10/15	
1.8 (08)	103 kW	1.8 l	10/11→10/15	
2.0 (08)	206 kW	2 l	04/12→	
2.0 BiTurbo CDTi (08)	143 kW	2 l	10/12→10/15	
2.0 BiTurbo CDTi (35)	143 kW	2 l	09/12→10/15	
2.0 BiTurbo CDTi (68)	143 kW	2 l	09/12→10/15	
2.0 CDTi (08)	121 kW	2 l	10/11→10/15	
2.0 CDTi (35)	118 kW	2 l	10/10→10/15	
2.0 CDTi (35)	121 kW	2 l	08/11→10/15	
2.0 CDTi (68)	118 kW	2 l	09/09→10/15	
2.0 CDTi (68)	121 kW	2 l	06/11→10/15	
<b>OPEL - CALIBRA A (C89) 08/89→07/97</b>				
2.0 i (M07)	85 kW	2 l	08/89→12/96	 VIN -> S1999999, S9999999 KH10108 ProKIT
2.0 i 4x4 (M07)	85 kW	2 l	06/90→07/97	 VIN T1000001 -> KH10206 ProKIT
				 KH10219 ProKIT

     					
<b>OPEL - CALIBRA A (C89)</b>				<b>08/89→07/97</b>	
2.0 i 16V (M07)	100 kW	2 l	02/94→07/97	; 06/94 ->; VIN -> S1999999, S9999999	KH10108 ProKIT
2.0 i 16V 4x4 (M07)	100 kW	2 l	02/94→07/97	; VIN T1000001 ->	KH10206 ProKIT
				; 06/94 ->	KH10219 ProKIT
2.0 i 16V (M07)	110 kW	2 l	06/90→02/94	; VIN -> S1999999, S9999999	KH10108 ProKIT
2.0 i 16V 4x4 (M07)	110 kW	2 l	06/90→02/94	; VIN T9000001 ->	KH10206 ProKIT
					KH10219 ProKIT
2.0 i Turbo 4x4 (M07)	150 kW	2 l	08/91→07/97	; VIN -> N1299999, N9299999	KH10108 ProKIT
				; VIN P9000001 ->	KH10206 ProKIT
					KH10219 ProKIT
2.5 i V6 (M07)	125 kW	2.5 l	04/93→07/97	; 05/93 ->	KH10206 ProKIT
				; 05/93 ->	KH10219 ProKIT
<b>OPEL - CAMPO (TF0, TF1)</b>				<b>08/91→06/01</b>	
2.3 4x4 (TFS16)	69 kW	2.3 l	08/91→08/94		KH00026 ProKIT
2.3 4x4 (TFS16)	72 kW	2.3 l	08/94→09/96		
2.5 D 4x4 (TFS54)	56 kW	2.5 l	08/91→06/94		
2.5 TD 4x4 (TFS54)	56 kW	2.5 l	07/94→06/01		
3.1 TD 4x4 (TFS69)	80 kW	3.1 l	12/92→06/01		
<b>OPEL - CASCADA (W13)</b>				<b>03/13→04/19</b>	
1.4 (67)	88 kW	1.4 l	04/13→04/18		KH30089 ProKIT
1.4 Turbo (67)	103 kW	1.4 l	03/13→04/18		
1.6 SIDI (67)	125 kW	1.6 l	04/13→04/19		
2.0 CDTI (67)	121 kW	2 l	04/13→06/15		
2.0 CDTI (67)	143 kW	2 l	04/13→06/15		
<b>OPEL - COMBO Box Body/MPV</b>				<b>10/01→</b>	
1.3 CDTI 16V	51 kW	1.3 l	08/05→		KH10063 ProKIT
1.3 CDTI 16V	55 kW	1.3 l	10/05→12/12	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.4 16V	66 kW	1.4 l	08/05→	; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6	64 kW	1.6 l	10/01→		
1.6 CNG 16V	69 kW	1.6 l	06/06→		
1.6 CNG 16V	71 kW	1.6 l	04/05→		
1.7 DI 16V	48 kW	1.7 l	10/01→		
1.7 DTI 16V	55 kW	1.7 l	10/01→		
1.7 CDTI 16V	74 kW	1.7 l	12/04→		KH10108 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT
<b>OPEL - COMBO Box Body/MPV (X12)</b>				<b>02/12→</b>	
1.3 CDTI (B05)	66 kW	1.3 l	02/12→	; (ABS); Payload: for increased payload	KH20093 ProKIT
1.4 (B05)	70 kW	1.4 l	02/12→	; (ABS); Payload: not for increased payload	KH20109 ProKIT
1.4 (B05)	88 kW	1.4 l	02/12→	; (ABS)	KH10198 ProKIT
				; (ABS); Payload: for increased payload	KH20093 ProKIT
1.4 CNG (B05)	88 kW	1.4 l	02/12→	; (ABS)	KH10198 ProKIT
1.6 CDTI (B05)	66 kW	1.6 l	02/12→	; (ABS); Payload: for increased payload;	KH10198 ProKIT
1.6 CDTI (B05)	77 kW	1.6 l	02/12→	; (ABS); Payload: for increased payload	KH20093 ProKIT
				; (ABS); Payload: not for increased payload	KH20109 ProKIT
1.6 CDTI (B05)	74 kW	1.6 l	02/12→	; (ABS); Payload: for increased payload;	KH10198 ProKIT
1.6 CDTI (B05)	88 kW	1.6 l	04/15→		
2.0 CDTI (B05)	99 kW	2 l	02/12→	; (ABS)	KH10198 ProKIT
				; (ABS); Payload: for increased payload	KH20093 ProKIT
				; (ABS); Payload: not for increased payload	KH20109 ProKIT
<b>OPEL - COMBO Tour</b>				<b>10/01→12/11</b>	
1.3 CDTI 16V	51 kW	1.3 l	06/04→01/11		KH10063 ProKIT
1.3 CDTI 16V	55 kW	1.3 l	10/05→12/11		
1.4	66 kW	1.4 l	10/04→12/11	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.6	64 kW	1.6 l	10/01→09/06	; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6 CNG	69 kW	1.6 l	06/06→12/11		
1.6 CNG	71 kW	1.6 l	04/05→01/11		
1.7 DI 16V	48 kW	1.7 l	10/01→06/04		
1.7 DTI 16V	55 kW	1.7 l	10/01→06/04		
1.6	62 kW	1.6 l	10/01→09/06		KH10063 ProKIT
1.7 CDTI 16V	74 kW	1.7 l	07/04→12/11		KH10108 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT



										
<b>OPEL - COMBO Tour (X12)</b>									<b>02/12→</b>	
1.3 CDTI (C26, D26, E26, C05)	66 kW	1.3 l	02/12→		ABS	Payload: for increased payload		KH20093 ProKIT		
1.4 (C26, D26, E26, C06)	70 kW	1.4 l	02/12→		ABS	Payload: not for increased payload		KH20109 ProKIT		
1.4 (C26, D26, E26, C06)	88 kW	1.4 l	02/12→		ABS			KH10198 ProKIT		
					ABS	Payload: for increased payload		KH20093 ProKIT		
1.4 CNG (C26, D26, E26, C05)	88 kW	1.4 l	02/12→		ABS			KH10198 ProKIT		
1.6 CDTI (C26, D26, E26, C05)	66 kW	1.6 l	02/12→		ABS	Payload: for increased payload; 		KH10198 ProKIT		
1.6 CDTI (C26, D26, E26, C05)	77 kW	1.6 l	02/12→		ABS	Payload: for increased payload		KH20093 ProKIT		
					ABS	Payload: not for increased payload		KH20109 ProKIT		
1.6 CDTI (C26, D26, E26, C05)	70 kW	1.6 l	03/15→		ABS	Payload: for increased payload; 		KH10198 ProKIT		
2.0 CDTI (C26, D26, E26, C05)	99 kW	2 l	02/12→		ABS			KH10198 ProKIT		
					ABS	Payload: for increased payload		KH20093 ProKIT		
					ABS	Payload: not for increased payload		KH20109 ProKIT		
<b>OPEL - COMMODORE A / COMMODORE A Coupe / COMMODORE B / COMMODORE B Coupe</b>									<b>08/67→07/78</b>	
2.5	85 kW	2.5 l	08/67→08/69				KH00093 ProKIT			
2.5	85 kW	2.5 l	01/72→07/78							
2.5	88 kW	2.5 l	08/69→01/72							
<b>OPEL - CORSA A Hatchback / CORSA A Hatchback Van / CORSA A TR / CORSA B / CORSA B Estate / CORSA B Hatchback Van (S83, S93)</b>									<b>09/82→12/02</b>	
1.0 (F08, M08, F68, M68)	33 kW	1 l	09/82→03/93				KH10107 ProKIT			
1.0 (F08, W5L)	33 kW	1 l	02/86→04/89				KH10376 ProKIT			
1.0 (F11, M11, F19, M19)	33 kW	1 l	09/82→09/92				KH00005 ProKIT			
1.2 (F08, M08, F68, M68)	33 kW	1.2 l	09/82→08/90							
1.2 (F08, M08, F68, M68)	44 kW	1.2 l	09/82→08/90							
1.2 (F08, W5L)	33 kW	1.2 l	02/86→04/89							
1.2 (F08, W5L)	40 kW	1.2 l	02/86→04/89							
1.2 (F08, W5L)	44 kW	1.2 l	02/86→07/90							
1.2 i (F08, M08, F68, M68)	33 kW	1.2 l	09/89→03/93							
1.2 i (F11, M11, F19, M19)	33 kW	1.2 l	09/89→03/93							
1.2 N (F08, M08, F68, M68)	38 kW	1.2 l	01/90→03/93							
1.2 N (F11, M11, F19, M19)	33 kW	1.2 l	01/85→10/87							
1.2 S (F08, M08, F68, M68)	40 kW	1.2 l	09/82→02/90							
1.2 S (F11, M11, M19, F19)	40 kW	1.2 l	09/82→03/93							
1.3 (F08, M08, F68, M68)	44 kW	1.3 l	09/85→10/89							
1.3 (F08, W5L)	44 kW	1.3 l	02/86→04/89							
1.3 (F08, W5L)	51 kW	1.3 l	02/86→04/89							
1.3 (F11, F19, M11, M19)	44 kW	1.3 l	09/85→10/87							
1.3 i (F08, M08, F68, M68)	44 kW	1.3 l	09/86→09/90							
1.3 S (F08, M08, F68, M68)	51 kW	1.3 l	09/82→10/89							
1.3 S (F11, M11, F19, M19)	51 kW	1.3 l	09/82→10/87							
1.4 i (F08, M08, F68, M68)	44 kW	1.4 l	01/90→03/93							
1.4 i (F11, M11, F19, M19)	44 kW	1.4 l	10/89→03/93							
1.4 S (F08, M08, F68, M68)	53 kW	1.4 l	01/90→03/93							
1.4 S (F11, M11, F19, M19)	53 kW	1.4 l	09/89→03/93							
1.4 Si (F08, M08, F68, M68)	60 kW	1.4 l	09/91→03/93							
1.5 D (F08, M08, F68, M68)	37 kW	1.5 l	09/87→03/93							
1.5 D (F08, W5L)	37 kW	1.5 l	06/87→04/89							
1.5 D (F11, M11, F19, M19)	37 kW	1.5 l	10/87→11/92							
1.5 TD (F08, M08, F68, M68)	49 kW	1.5 l	03/88→03/93							
1.5 TD (F11, M11, F19, M19)	49 kW	1.5 l	10/87→03/93							
1.6 GSI (F08, M08, F68, M68)	72 kW	1.6 l	09/89→03/93							
1.6 GSI (F08, M08, F68, M68)	74 kW	1.6 l	05/88→03/92							
1.6 GSI (F08, M08, M68, F68)	55 kW	1.6 l	08/88→09/92							
1.6 GSI Cat (F08, M08, F68, M68)	74 kW	1.6 l	02/92→03/93							
1.0 i 12V (F08, F68, M68)	40 kW	1 l	11/96→09/00				KH10376 ProKIT			
1.2 (F08, W5L)	33 kW	1.2 l	08/90→07/94				KH00005 ProKIT			
1.2 (F08, W5L)	37 kW	1.2 l	08/90→07/94							
1.2 i (F08, F68, M68)	33 kW	1.2 l	03/93→09/00							
1.2 i 16V (F08, F68, M68)	48 kW	1.2 l	03/98→09/00							
1.2 S (F11, M11, F19, M19)	43 kW	1.2 l	09/82→10/87							
1.4 (F08, F68, M68)	54 kW	1.4 l	04/93→08/94							
1.4 i (F08, F68, M68)	40 kW	1.4 l	03/93→09/00							
1.4 i (F08, F68, M68)	44 kW	1.4 l	03/93→09/00							
1.4 i (F08, M08, F68, M68)	40 kW	1.4 l	01/85→03/93							
1.4 i (F08, W5L)	44 kW	1.4 l	08/99→09/00							
1.4 i 16V (F08, F68, M68)	63 kW	1.4 l	08/97→09/00							
1.4 i 16V (F08, F68, M68)	66 kW	1.4 l	09/94→09/00							
1.4 i 16V (F35)	66 kW	1.4 l	01/99→12/02							
1.4 Si (F08, F68, M68)	60 kW	1.4 l	03/93→09/00							
1.5 D (F08, F68, M68)	37 kW	1.5 l	03/93→09/00							
1.5 TD (F08, F68, M68)	49 kW	1.5 l	03/93→09/00							
1.6 GSI 16V (F08, F68, M68)	80 kW	1.6 l	03/93→09/00							
1.6 i 16V (F08, F68, M68)	74 kW	1.6 l	08/97→09/00							



**OPEL - CORSA A Hatchback / CORSA A Hatchback Van / CORSA A TR / CORSA B / CORSA B Estate / CORSA B Hatchback Van (S83, S93)** **09/82→12/02**

1.6 i 16V (F08, F68, M68)	78 kW	1.6 l	09/94→09/00		KH10376 ProKIT
1.7 D (F08, F68, M68)	44 kW	1.7 l	02/96→09/00		KH00005 ProKIT
1.7 D (F08, W5L)	44 kW	1.7 l	08/99→09/00		
1.7 D (F35)	44 kW	1.7 l	01/99→12/02		
1.2 (F08, W5L)	33 kW	1.2 l	08/94→12/01		KH10376 ProKIT
1.3 (F08, W5L)	44 kW	1.3 l	01/98→12/01		
1.5 D (F08, W5L)	37 kW	1.5 l	09/94→05/97		
1.6 GSI (F08, M08, F68, M68)	60 kW	1.6 l	09/88→08/90		KH00005 ProKIT

**OPEL - CORSA C / CORSA C Hatchback Van (X01)** **09/00→12/12**

1.0 (F08, F68)	43 kW	1 l	09/00→06/03		KH10063 ProKIT
1.2 (F08, W5L)	59 kW	1.2 l	07/05→06/06		KH10113 ProKIT
1.2 16V (F08, W5L)	55 kW	1.2 l	09/00→07/03		KH20118 ProKIT
1.3 CDTi 16V (F08, W5L)	51 kW	1.3 l	07/05→06/06		
1.7 DI 16V (F08, W5L)	48 kW	1.7 l	09/00→07/03		
1.7 DTi 16V (F08, W5L)	55 kW	1.7 l	09/00→07/03		
1.0 (F08, F68)	44 kW	1 l	06/03→12/09		KH10063 ProKIT
1.3 CDTi (F08, F68)	51 kW	1.3 l	06/03→12/09		KH20118 ProKIT
1.4 Twinport (F08, F68)	66 kW	1.4 l	06/03→12/09		KH10113 ProKIT
1.8 (F08, F68)	92 kW	1.8 l	09/00→12/09		
1.2 (F08, F68)	55 kW	1.2 l	09/00→12/09		KH10063 ProKIT
					KH20118 ProKIT
					KH10113 ProKIT
1.2 Twinport (F08, F68)	59 kW	1.2 l	07/04→12/09		KH10063 ProKIT
					KH20118 ProKIT
					KH10113 ProKIT
1.3 CDTi 16V (F08, W5L)	59 kW	1.3 l	07/05→06/06		KH10063 ProKIT
1.4 (F08, F68)	60 kW	1.4 l	01/02→12/09		
1.6 (F08, F68)	62 kW	1.6 l	09/00→12/09		
1.6 (F08, F68)	69 kW	1.6 l	01/03→12/07		
1.8 (F08, F68)	79 kW	1.8 l	01/02→12/09		
1.4 (F08, F68)	66 kW	1.4 l	09/00→12/09		KH10063 ProKIT
1.7 DTi (F08, F68)	55 kW	1.7 l	09/00→12/09		KH20118 ProKIT
					KH10113 ProKIT
1.4 (W5L, F08)	66 kW	1.4 l	08/03→06/12		KH10063 ProKIT
					KH10113 ProKIT
1.7 CDTi (F08, F68)	74 kW	1.7 l	06/03→12/09		KH10108 ProKIT
					KH20118 ProKIT
					KH10113 ProKIT
1.7 CDTi (F08, W5L)	74 kW	1.7 l	08/03→12/12		KH10108 ProKIT
					KH20118 ProKIT
					KH10113 ProKIT
1.7 DI (F08, F68)	48 kW	1.7 l	09/00→12/09		KH10063 ProKIT
					KH20118 ProKIT
					KH10113 ProKIT

**OPEL - CORSA CLASSIC Saloon** **08/94→12/05**































































1.3	44 kW	1.3 l	01/97→12/02		KH00005 ProKIT
1.4	44 kW	1.4 l	08/94→07/02		
1.4	66 kW	1.4 l	07/00→05/01		
1.4	66 kW	1.4 l	07/00→12/03		
1.6	74 kW	1.6 l	01/00→12/03		
1.8	79 kW	1.8 l	01/02→12/05		





















**OPEL - CORSA C Saloon (X01)** **01/03→12/07**

1.6	69 kW	1.6 l	01/03→12/07		KH10063 ProKIT
-----	-------	-------	-------------	--	----------------

**OPEL - CORSA D (S07)** **07/06→08/14**

1.0 (L08, L68)	44 kW	1 l	07/06→12/10		KH10042 ProKIT
1.0 (L08, L68)	48 kW	1 l	12/09→08/14		KH20017 ProKIT
1.2 (L08, L68)	51 kW	1.2 l	12/09→08/14		KH20030 ProKIT
1.2 (L08, L68)	59 kW	1.2 l	07/06→08/14		
1.2 (L08, L68)	63 kW	1.2 l	12/09→08/14		
1.2 LPG (L08, L68)	55 kW	1.2 l	09/09→12/11		
1.2 LPG (L08, L68)	59 kW	1.2 l	08/06→08/14		
1.2 LPG (L08, L68)	61 kW	1.2 l	06/11→08/14		
1.2 LPG (L08, L68)	63 kW	1.2 l	06/11→08/14		
1.4 (L08, L68)	64 kW	1.4 l	09/09→08/14		
1.4 (L08, L68)	66 kW	1.4 l	07/06→08/14		
1.4 (L08, L68)	74 kW	1.4 l	12/09→08/14		







































												
<b>OPEL - CORSA D (S07)</b>											<b>07/06→08/14</b>	
1.4 LPG (L08, L68)	64 kW	1.4 l	09/09→08/14								<b>KH10042</b> ProKIT	
1.4 LPG (L08, L68)	66 kW	1.4 l	08/06→12/11								<b>KH20017</b> ProKIT	
											<b>KH20030</b> ProKIT	
1.3 CDTI (L08, L68)	55 kW	1.3 l	07/06→08/14								<b>KH10065</b> ProKIT	
1.3 CDTI (L08, L68)	66 kW	1.3 l	07/06→06/11								<b>KH20017</b> ProKIT	
1.3 CDTI (L08, L68)	70 kW	1.3 l	06/09→08/14								<b>KH20030</b> ProKIT	
1.4 (L08, L68)	88 kW	1.4 l	07/12→08/14									
1.6 Turbo (L08, L68)	110 kW	1.6 l	05/07→08/14									
1.6 Turbo (L08, L68)	141 kW	1.6 l	11/06→08/14									
1.6 Turbo (L08, L68)	155 kW	1.6 l	06/11→08/14									
1.7 CDTI (L08, L68)	92 kW	1.7 l	08/06→12/11									
1.7 CDTI (L08, L68)	96 kW	1.7 l	12/09→08/14									
1.6 T (L08, L68)	132 kW	1.6 l	02/07→08/14								<b>KH20017</b> ProKIT	
<b>OPEL - CORSA D Hatchback Van (S07)</b>											<b>07/06→08/14</b>	
1.0 (L08)	44 kW	1 l	08/06→08/14								<b>KH10042</b> ProKIT	
1.0 (L08)	48 kW	1 l	01/10→08/14									
1.2 (L08)	51 kW	1.2 l	01/10→08/14									
1.2 (L08)	59 kW	1.2 l	08/06→08/14									
1.2 (L08)	63 kW	1.2 l	06/10→08/14									
1.3 CDTI (L08)	55 kW	1.3 l	07/06→08/14								<b>KH10065</b> ProKIT	
1.3 CDTI (L08)	66 kW	1.3 l	07/06→06/10									
1.3 CDTI (L08)	70 kW	1.3 l	11/09→08/14									
<b>OPEL - CORSA E (X15)</b>											<b>09/14→</b>	
1.0 (08, 68)	66 kW	1 l	09/14→		VIN -> F4168927;							<b>KH10042</b> ProKIT
1.0 (08, 68)	85 kW	1 l	09/14→		VIN -> F6D58386;							
					VIN F4168928, F6058387 ->						<b>KH10065</b> ProKIT	
					Rim Hole Number: 4						<b>KH20017</b> ProKIT	
					Rim Hole Number: 5						<b>KH20030</b> ProKIT	
1.2 (08, 68)	51 kW	1.2 l	09/14→								<b>KH10042</b> ProKIT	
1.4 (08, 68)	55 kW	1.4 l	09/14→									
1.4 (08, 68)	66 kW	1.4 l	09/14→		Rim Hole Number: 4						<b>KH20017</b> ProKIT	
1.4 LPG (08, 68)	64 kW	1.4 l	11/15→		Rim Hole Number: 5						<b>KH20030</b> ProKIT	
1.4 LPG (08, 68)	66 kW	1.4 l	03/15→									
1.3 CDTI (08, 68)	55 kW	1.3 l	09/14→								<b>KH10065</b> ProKIT	
1.3 CDTI (08, 68)	70 kW	1.3 l	09/14→		Rim Hole Number: 4						<b>KH20017</b> ProKIT	
1.6 Turbo (08, 68)	152 kW	1.6 l	03/15→		Rim Hole Number: 5						<b>KH20030</b> ProKIT	
1.4 Turbo (08, 68)	74 kW	1.4 l	09/14→06/19								<b>KH10042</b> ProKIT	
1.4 Turbo (08, 68)	110 kW	1.4 l	03/15→								<b>KH10065</b> ProKIT	
					Rim Hole Number: 4						<b>KH20017</b> ProKIT	
					Rim Hole Number: 5						<b>KH20030</b> ProKIT	
<b>OPEL - CORSA E Hatchback Van (X15)</b>											<b>09/14→</b>	
1.2 (08)	51 kW	1.2 l	01/15→								<b>KH10042</b> ProKIT	
1.4 (08)	55 kW	1.4 l	09/14→									
1.4 (08)	66 kW	1.4 l	09/14→									
1.3 CDTI (08)	55 kW	1.3 l	01/15→								<b>KH10065</b> ProKIT	
1.3 CDTI (08)	70 kW	1.3 l	09/14→									
<b>OPEL - DIPLOMAT A / DIPLOMAT A Coupe</b>											<b>10/64→03/69</b>	
4.6	140 kW	4.6 l	10/64→03/69								<b>KH00093</b> ProKIT	
5.4	169 kW	5.4 l	03/65→10/67									
5.4	169 kW	5.4 l	09/66→03/69									
<b>OPEL - DIPLOMAT B</b>											<b>03/69→01/78</b>	
5.4	169 kW	5.4 l	03/69→01/78		-> 12/77						<b>KH00093</b> ProKIT	
<b>OPEL - FRONTERA A / FRONTERA A Sport (U92)</b>											<b>03/92→10/98</b>	
2.0 i (52SUD2, 55SUD2)	85 kW	2 l	03/92→10/98								<b>KH00026</b> ProKIT	
2.2 i (54MWL4)	100 kW	2.2 l	03/95→10/98		04/95 -> 09/98						<b>KH00065</b> ProKIT	
2.3 TD (5JMWL4)	74 kW	2.3 l	03/92→10/98		-> 03/95						<b>KH00026</b> ProKIT	
2.4 i (53MWL4)	92 kW	2.4 l	03/92→10/98									
2.5 TDS	85 kW	2.5 l	09/96→10/98								<b>KH00026</b> ProKIT	
2.5 TDS	85 kW	2.5 l	09/96→10/98								<b>KH00026</b> ProKIT	
					-> 09/98						<b>KH00065</b> ProKIT	
2.8 TD (5BMWL4, 5BSUD2)	83 kW	2.8 l	03/95→08/98		-> 01/96						<b>KH00026</b> ProKIT	
2.8 TD (5BSUD2)	83 kW	2.8 l	03/95→08/96		05/95 -> 07/96						<b>KH00065</b> ProKIT	

												
<b>OPPEL - FRONTERA B (U99)</b>											<b>09/98→07/04</b>	
2.2 DTI (6B_66, 6B_76)	88 kW	2.2 l	09/02→07/04								KH00065 ProKIT	
2.2 DTI (6B_ZC, 6B_VF, 6B_66, 6B_76)	85 kW	2.2 l	09/98→12/03								KH00026 ProKIT	
2.2 i (6B_ZC, 6B_VF, 6B_66, 6B_76)	100 kW	2.2 l	10/98→07/04								KH00065 ProKIT	
3.2 i (6B1VF, 6B1_6)	151 kW	3.2 l	10/98→07/04									
<b>OPPEL - GT</b>											<b>09/68→08/73</b>	
1.1	44 kW	1.1 l	09/68→12/70								KH00088 ProKIT	
1.9	66 kW	1.9 l	09/68→08/73									
<b>OPPEL - INSIGNIA A (G09)</b>											<b>07/08→03/17</b>	
1.4 (68)	103 kW	1.4 l	04/11→03/17								KH30070 ProKIT	
1.4 LPG (68)	103 kW	1.4 l	07/12→03/17		VIN -> C1000000						KH30105 ProKIT	
1.6 (68)	85 kW	1.6 l	07/08→03/17									
1.6 CDTi (68)	88 kW	1.6 l	07/15→03/17									
1.6 CDTi (68)	100 kW	1.6 l	07/15→03/17									
1.6 SIDI (68)	125 kW	1.6 l	03/13→03/17									
1.6 Turbo (68)	132 kW	1.6 l	07/08→03/17									
1.8 (68)	103 kW	1.8 l	07/08→03/17									
2.0 Biturbo CDTI (68)	140 kW	2 l	07/08→12/11									
2.0 Biturbo CDTI (68)	143 kW	2 l	01/12→03/17									
2.0 CDTI (68)	81 kW	2 l	07/08→03/17									
2.0 CDTI (68)	88 kW	2 l	03/12→03/17									
2.0 CDTI (68)	96 kW	2 l	07/08→03/17									
2.0 CDTI (68)	103 kW	2 l	06/13→03/17									
2.0 CDTI (68)	118 kW	2 l	07/08→03/17									
2.0 CDTI (68)	120 kW	2 l	07/13→03/17									
2.0 CDTI (68)	125 kW	2 l	11/14→03/17									
2.0 E85 Turbo (68)	162 kW	2 l	10/10→03/17									
2.0 Turbo (68)	162 kW	2 l	07/08→03/17									
2.0 Turbo (68)	184 kW	2 l	04/14→03/17									
2.0 Biturbo CDTI 4x4 (68)	140 kW	2 l	05/09→12/11								KH30070 ProKIT	
2.0 Biturbo CDTI 4x4 (68)	143 kW	2 l	01/12→03/17		VIN -> C1000000						KH30196 ProKIT	
2.0 CDTI 4x4 (68)	118 kW	2 l	06/10→03/17		VIN C1000001 ->						KH30183 ProKIT	
2.0 CDTI 4x4 (68)	120 kW	2 l	07/13→03/17									
2.0 CDTI 4x4 (68)	125 kW	2 l	11/14→03/17									
2.0 Turbo 4x4 (68)	162 kW	2 l	07/08→03/17									
2.0 Turbo 4x4 (68)	184 kW	2 l	07/11→03/17									
2.8 V6 Turbo 4x4 (68)	191 kW	2.8 l	07/08→03/17									
2.8 V6 Turbo OPC 4x4 (68)	239 kW	2.8 l	07/09→03/17									
<b>OPPEL - INSIGNIA A Country Tourer (G09)</b>											<b>07/08→03/17</b>	
1.6 CDTi (47)	88 kW	1.6 l	07/15→03/17								KH30070 ProKIT	
1.6 CDTi (47)	100 kW	1.6 l	07/15→03/17									
1.6 SIDI (47)	125 kW	1.6 l	07/14→03/17									
2.0 CDTi (47)	88 kW	2 l	03/12→03/17									
2.0 CDTi (47)	96 kW	2 l	07/08→03/17									
2.0 CDTi (47)	120 kW	2 l	07/14→03/17									
2.0 CDTi (47)	125 kW	2 l	11/14→03/17									
2.0 CDTi 4x4 (47)	120 kW	2 l	09/13→03/17									
2.0 CDTi 4x4 (47)	125 kW	2 l	11/14→03/17									
2.0 CDTi 4x4 (47)	143 kW	2 l	09/13→03/17									
2.0 Turbo 4x4 (47)	184 kW	2 l	09/13→03/17									
<b>OPPEL - INSIGNIA A Saloon / INSIGNIA A Sports Tourer (G09)</b>											<b>07/08→03/17</b>	
1.4 (35)	103 kW	1.4 l	09/11→06/13								KH30070 ProKIT	
1.4 (69)	103 kW	1.4 l	04/11→03/17		VIN -> C1000000						KH30105 ProKIT	
1.4 LPG (35)	103 kW	1.4 l	07/12→06/13									
1.4 LPG (69)	103 kW	1.4 l	07/12→03/17									
1.6 (35)	85 kW	1.6 l	07/08→06/12									
1.6 (69)	85 kW	1.6 l	07/08→03/17									
1.6 CDTi (35)	88 kW	1.6 l	07/15→01/17									
1.6 CDTi (35)	100 kW	1.6 l	07/15→12/16									
1.6 CDTi (69)	88 kW	1.6 l	07/15→03/17									
1.6 CDTi (69)	100 kW	1.6 l	07/15→03/17									
1.6 SIDI (35)	125 kW	1.6 l	03/13→11/14									
1.6 SIDI (69)	125 kW	1.6 l	03/13→03/17									
1.6 Turbo (35)	132 kW	1.6 l	01/09→06/13									
1.6 Turbo (69)	132 kW	1.6 l	07/08→03/17									
1.8 (35)	103 kW	1.8 l	07/08→06/13									
1.8 (69)	103 kW	1.8 l	07/08→03/17									
2.0 Biturbo CDTI (35)	140 kW	2 l	07/08→03/17									
2.0 Biturbo CDTI (35)	143 kW	2 l	01/12→06/15									
2.0 Biturbo CDTI (69)	140 kW	2 l	07/08→12/11									
2.0 Biturbo CDTI (69)	143 kW	2 l	01/12→03/17									
2.0 CDTI (35)	81 kW	2 l	07/08→06/13									
2.0 CDTI (35)	88 kW	2 l	03/12→06/15									
2.0 CDTI (35)	96 kW	2 l	07/08→06/15									
2.0 CDTI (35)	103 kW	2 l	07/13→06/15									



				13	i		
<b>OPEL - INSIGNIA A Saloon / INSIGNIA A Sports Tourer (G09)</b>						<b>07/08→03/17</b>	
2.0 CDTI (35)	118 kW	2 l	07/08→06/15			KH30070 ProKIT	
2.0 CDTI (35)	120 kW	2 l	07/13→06/15			KH30105 ProKIT	
2.0 CDTI (35)	125 kW	2 l	11/14→12/16		VIN -> C1000000	KH30105 ProKIT	
2.0 CDTI (69)	81 kW	2 l	07/08→03/17				
2.0 CDTI (69)	88 kW	2 l	03/12→03/17				
2.0 CDTI (69)	103 kW	2 l	06/13→03/17				
2.0 CDTI (69)	118 kW	2 l	07/08→03/17				
2.0 CDTI (69)	120 kW	2 l	07/13→03/17				
2.0 CDTI (69)	125 kW	2 l	11/14→03/17				
2.0 E85 Turbo (35)	162 kW	2 l	09/10→11/11				
2.0 Turbo (35)	162 kW	2 l	07/08→06/13				
2.0 Turbo (35)	184 kW	2 l	04/14→11/14				
2.0 Turbo (69)	162 kW	2 l	07/08→03/17				
2.0 Turbo (69)	184 kW	2 l	04/14→03/17				
2.0 Turbo E85 (69)	162 kW	2 l	07/08→03/17				
2.0 Biturbo CDTI 4x4 (35)	140 kW	2 l	07/08→03/17			KH30070 ProKIT	
2.0 Biturbo CDTI 4x4 (35)	143 kW	2 l	01/12→06/15		VIN -> C1000000	KH30196 ProKIT	
2.0 Biturbo CDTI 4x4 (69)	140 kW	2 l	07/08→12/11				
2.0 Biturbo CDTI 4x4 (69)	143 kW	2 l	01/12→03/17		VIN C1000001 ->	KH30183 ProKIT	
2.0 CDTI 4x4 (35)	118 kW	2 l	06/10→06/15				
2.0 CDTI 4x4 (35)	120 kW	2 l	07/13→06/15				
2.0 CDTI 4x4 (35)	125 kW	2 l	11/14→12/16				
2.0 CDTI 4x4 (69)	118 kW	2 l	06/10→03/17				
2.0 CDTI 4x4 (69)	120 kW	2 l	07/13→03/17				
2.0 CDTI 4x4 (69)	125 kW	2 l	11/14→03/17				
2.0 Turbo 4x4 (35)	162 kW	2 l	07/08→06/11				
2.0 Turbo 4x4 (35)	184 kW	2 l	09/11→06/13				
2.0 Turbo 4x4 (69)	162 kW	2 l	07/08→03/17				
2.0 Turbo 4x4 (69)	184 kW	2 l	07/11→03/17				
2.8 V6 Turbo 4x4 (35)	191 kW	2.8 l	10/08→06/13				
2.8 V6 Turbo 4x4 (69)	191 kW	2.8 l	07/08→03/17				
2.8 V6 Turbo OPC 4x4 (35)	239 kW	2.8 l	07/09→06/15				
2.8 V6 Turbo OPC 4x4 (69)	239 kW	2.8 l	07/09→03/17				
2.0 CDTI (69)	96 kW	2 l	07/08→03/17			KH30070 ProKIT	
						KH30105 ProKIT	
<b>OPEL - KADETT A</b>						<b>09/62→08/65</b>	
1.0	29 kW	1 l	09/62→08/65			KH00093 ProKIT	
<b>OPEL - KADETT B / KADETT B Coupe / KADETT B Estate</b>						<b>09/65→08/73</b>	
1.1	33 kW	1.1 l	09/65→07/71			KH00088 ProKIT	
1.1	37 kW	1.1 l	08/71→08/73			KH00093 ProKIT	
1.1	40 kW	1.1 l	09/65→07/71				
1.1	44 kW	1.1 l	11/66→07/71				
1.2	44 kW	1.2 l	08/71→08/73				
1.7	55 kW	1.7 l	08/67→08/71				
1.9	66 kW	1.9 l	08/67→08/73				
1.1 S	40 kW	1.1 l	09/65→07/71			KH00088 ProKIT	
1.1 SR	44 kW	1.1 l	11/66→07/71				
1.2 S	44 kW	1.2 l	08/71→08/73				
<b>OPEL - KADETT C / KADETT C City / KADETT C Coupe / KADETT C Estate</b>						<b>08/73→07/79</b>	
1.0	29 kW	1 l	01/74→07/79		-> 12/76; VIN -> 52696299	KH00088 ProKIT	
1.0	29 kW	1 l	05/75→07/79		-> 12/76; VIN -> 55151638	KH00093 ProKIT	
1.2	38 kW	1.2 l	08/73→04/77				
1.2	38 kW	1.2 l	05/75→04/77				
1.2	40 kW	1.2 l	08/73→07/79				
1.2	40 kW	1.2 l	07/76→07/79				
1.2 S	44 kW	1.2 l	08/73→07/79		-> 12/76; VIN -> 52696299	KH00088 ProKIT	
					-> 12/76; VIN -> 55151638		
<b>OPEL - KADETT D / KADETT D Estate (31_-34_, 41_-44_, 32_,37_,39_,_42_, 35_, 36_, 45_, 46_)</b>						<b>08/79→08/84</b>	
1.0	30 kW	1 l	09/79→08/82			KH00005 ProKIT	
1.0	33 kW	1 l	09/79→08/84				
1.0	37 kW	1 l	08/79→12/83				
1.2	40 kW	1.2 l	08/82→08/84				
1.2 S	44 kW	1.2 l	08/79→08/84				
1.3 N	44 kW	1.3 l	08/79→08/84				
1.3 S	55 kW	1.3 l	08/79→08/84				
1.2	39 kW	1.2 l	08/79→07/82			KH10107 ProKIT	
1.3 N	44 kW	1.3 l	08/79→08/84			KH00005 ProKIT	
1.3 S	55 kW	1.3 l	08/79→08/84				
1.2 S	44 kW	1.2 l	08/79→08/84		-> 07/84	KH10107 ProKIT	
						KH00005 ProKIT	



											
<b>OPEL - KADETT D / KADETT D Estate (31_34_, 41_44_, 32_37_,39_, 42, 35_, 36_, 45_, 46_)</b>										<b>08/79→08/84</b>	
1.6 D	40 kW	1.6 l	03/82→08/84							<b>04/82 -&gt;</b>	<b>KH10108</b> ProKIT
											<b>KH00005</b> ProKIT
1.6 S	66 kW	1.6 l	09/81→08/84								<b>KH10108</b> ProKIT
											<b>KH00005</b> ProKIT
1.8 GT/E	85 kW	1.8 l	02/83→08/84							<b>05/83 -&gt;</b>	<b>KH10108</b> ProKIT
											<b>KH00005</b> ProKIT
<b>OPEL - KADETT E / KADETT E Combo / KADETT E Convertible / KADETT E Estate / KADETT E Estate Van / KADETT E Hatchback (T85)</b>										<b>08/84→07/94</b>	
1.2 (C08, C48, D08, D48)	40 kW	1.2 l	09/84→07/86								<b>KH10107</b> ProKIT
1.2 (C15, C35, D15, D35)	40 kW	1.2 l	09/84→07/86								<b>KH10376</b> ProKIT
										<b>01/86 -&gt;</b>	<b>KH00093</b> ProKIT
1.2 (C19, D19)	40 kW	1.2 l	09/84→07/86							<b>08/85 -&gt;</b>	<b>KH10107</b> ProKIT
											<b>KH10376</b> ProKIT
										<b>01/86 -&gt;</b>	<b>KH00093</b> ProKIT
1.2 (C70, D70)	40 kW	1.2 l	09/84→07/86								<b>KH10376</b> ProKIT
										<b>01/86 -&gt;</b>	<b>KH00093</b> ProKIT
1.3 (C08, C48, D08, D48)	50 kW	1.3 l	01/85→12/87								<b>KH10376</b> ProKIT
1.3 (C15, C35, D15, D35)	50 kW	1.3 l	01/85→12/87								
1.3 i Cat (C15, C35, D15, D35)	44 kW	1.3 l	09/85→08/91								
1.3 N (C70, D70)	44 kW	1.3 l	09/84→07/89								
1.4 S (C08, C48, D08, D48)	60 kW	1.4 l	09/89→08/91								
1.6 (C19, D19)	75 kW	1.6 l	09/87→08/91								
1.3 i Cat (C08, C48, D08, D48)	44 kW	1.3 l	09/85→08/91								<b>KH10107</b> ProKIT
1.3 N (C08, C48, D08, D48)	44 kW	1.3 l	09/84→08/91								<b>KH10376</b> ProKIT
1.3 N (C15, C35, D15, D35)	44 kW	1.3 l	09/84→08/91								
1.3 N (C25, D25)	44 kW	1.3 l	01/86→12/89								
1.3 S (C08, C48, D08, D48)	55 kW	1.3 l	09/84→08/87								
1.3 S (C15, C35, D15, D35)	55 kW	1.3 l	09/84→08/87								
1.3 S (C25, D25)	55 kW	1.3 l	01/86→12/89								
1.4 i	44 kW	1.4 l	01/90→08/91								
1.4 i (C08, C48, D08, D48)	44 kW	1.4 l	01/90→08/91								
1.4 i (C15, C35, D15, D35)	44 kW	1.4 l	01/90→08/91								
1.4 i (C19, D19)	44 kW	1.4 l	01/90→08/91								
1.4 i (C70, D70)	44 kW	1.4 l	01/90→08/91								
1.4 S (C08, C48, D08, D48)	55 kW	1.4 l	01/90→08/91								
1.4 S (C15, C35, D15, D35)	55 kW	1.4 l	01/90→08/91								
1.4 S (C19, D19)	55 kW	1.4 l	01/90→08/91								
1.6 i (C08, C48, D08, D48)	55 kW	1.6 l	09/86→08/91								
1.6 i (C15, C35, D15, D35)	55 kW	1.6 l	09/86→08/91								
1.6 i (C19, D19)	55 kW	1.6 l	09/86→08/91								
1.6 i Cat (C15, C35, D15, D35)	55 kW	1.6 l	09/86→08/91								
1.6 i Cat (C19, D19)	55 kW	1.6 l	09/86→08/91								
1.6 S (C08, C48, D08, D48)	60 kW	1.6 l	09/86→08/91								
1.6 S (C19, D19)	60 kW	1.6 l	09/86→08/91								
1.3 i Cat (C19, D19)	44 kW	1.3 l	09/85→08/91							<b>09/86 -&gt;</b>	<b>KH10107</b> ProKIT
1.3 N (C19, D19)	44 kW	1.3 l	09/84→08/89								<b>KH10376</b> ProKIT
1.3 S	55 kW	1.3 l	03/87→02/93							<b>-&gt; 12/89</b>	<b>KH10107</b> ProKIT
											<b>KH10376</b> ProKIT
1.3 S (C19, D19)	55 kW	1.3 l	09/84→08/87							<b>08/85 -&gt;</b>	<b>KH10107</b> ProKIT
											<b>KH10376</b> ProKIT
1.4 i (C25, D25)	44 kW	1.4 l	08/91→07/94							<b>-&gt; 03/93</b>	<b>KH10107</b> ProKIT
1.6 i (C25, D25)	55 kW	1.6 l	08/91→07/94								<b>KH10376</b> ProKIT
1.4 S	55 kW	1.4 l	08/90→02/93							<b>-&gt; 12/91</b>	<b>KH10107</b> ProKIT
1.6 i	55 kW	1.6 l	10/86→02/93								<b>KH10376</b> ProKIT
1.6 i	60 kW	1.6 l	07/89→02/93								
1.6 i (C70, D70)	55 kW	1.6 l	08/89→09/93								
1.4 S (C25, D25)	55 kW	1.4 l	07/89→08/91							<b>09/89 -&gt; 06/91</b>	<b>KH10107</b> ProKIT
											<b>KH10376</b> ProKIT
1.5 TD (C08, C48, D08, D48)	53 kW	1.5 l	07/88→08/91								<b>KH10107</b> ProKIT
1.5 TD (C19, D19)	53 kW	1.5 l	07/88→08/91								
1.6 D (C25, D25)	40 kW	1.6 l	01/86→12/89								
1.5 TD (C15, C35, D15, D35)	53 kW	1.5 l	07/88→08/91								<b>KH10108</b> ProKIT
1.6 D (C08, C48, D08, D48)	40 kW	1.6 l	09/84→01/89								
1.6 D (C15, C35, D15, D35)	40 kW	1.6 l	09/84→01/89								
1.6 D (C19, D19)	40 kW	1.6 l	09/84→01/89								
1.7 D (C08, C48, D08, D48)	42 kW	1.7 l	02/89→08/91								
1.7 D (C15, C35, D15, D35)	42 kW	1.7 l	02/89→08/91								
1.7 D (C19, D19)	42 kW	1.7 l	02/89→08/91								





**OPEL - KADETT E / KADETT E Combo / KADETT E Convertible / KADETT E Estate / KADETT E Estate Van / KADETT E Hatchback (T85)** 08/84→07/94



























1.8 GSI (C08, C48, D08, D48)	85 kW	1.8 l	09/84→08/86		KH10108 ProKIT
1.8 i (C15, C35, D15, D35)	85 kW	1.8 l	09/84→08/86		
1.8 i (C19, D19)	66 kW	1.8 l	08/89→05/92		
1.8 i (C19, D19)	85 kW	1.8 l	09/84→08/86		
1.8 S (C08, C48, D08, D48)	62 kW	1.8 l	09/87→08/91		
1.8 S (C19, D19)	62 kW	1.8 l	09/87→08/91		
2.0 GSI (C08, C48, D08, D48)	85 kW	2 l	09/86→08/91		
2.0 GSI (C08, C48, D08, D48)	95 kW	2 l	09/86→08/91		
2.0 GSI 16V (C08, C48, D08, D48)	110 kW	2 l	03/88→08/91		
2.0 GSI 16V Cat (C08, C48, D08, D48)	110 kW	2 l	03/88→08/91		
2.0 GSI Cat (C08, C48, D08, D48)	85 kW	2 l	09/86→08/91		
2.0 i (C15, C35, D15, D35)	85 kW	2 l	09/87→08/91		
2.0 i (C19, D19)	85 kW	2 l	09/87→05/92		
2.0 i Cat (C15, C35, D15, D35)	85 kW	2 l	09/87→08/91		
2.0 i Cat (C19, D19)	85 kW	2 l	03/87→05/92		
1.6 (C15, C35, D15, D35)	60 kW	1.6 l	09/86→08/91		KH10107 ProKIT
					KH10376 ProKIT
					KH00093 ProKIT
1.6 (C25, D25)	60 kW	1.6 l	09/86→12/91		KH10376 ProKIT
					KH00093 ProKIT
					KH10107 ProKIT
1.6 D (C70, D70)	40 kW	1.6 l	08/84→08/88	; 09/86 ->	KH10108 ProKIT
1.8 i (C08, C48, D08, D48)	66 kW	1.8 l	06/85→08/91		
1.8 i (C15, C35, D15, D35)	66 kW	1.8 l	06/85→08/91		
1.6 i Cat	55 kW	1.6 l	10/87→02/93	; -> 02/91	KH10107 ProKIT
					KH10376 ProKIT
1.6 i Cat (C08, C48, D08, D48)	55 kW	1.6 l	09/86→08/91	; 01/89 ->	KH10107 ProKIT
					KH10376 ProKIT
1.6 S (C08, D08, C48, D48)	66 kW	1.6 l	09/84→08/86		KH10108 ProKIT
1.6 S (C15, C35, D35, D15)	66 kW	1.6 l	09/84→08/86		KH10376 ProKIT
1.6 S (C19, D19)	66 kW	1.6 l	09/84→08/86		
1.7 D (C25, D25)	42 kW	1.7 l	01/89→07/94	; 08/90 -> 03/93	KH10107 ProKIT
1.7 D (C25, D25)	44 kW	1.7 l	07/92→07/94	; -> 03/93	KH10107 ProKIT
1.7 D (C70, D70)	42 kW	1.7 l	08/88→09/92	; 01/89 -> 12/91	KH10108 ProKIT
1.8 (C19, D19)	84 kW	1.8 l	09/87→08/90		KH10108 ProKIT
					KH00093 ProKIT
1.8 i (C70, D70)	66 kW	1.8 l	08/84→09/92	; 09/86 -> 12/91	KH10108 ProKIT
2.0 GSI 16V (C08, C48, D08, D48)	115 kW	2 l	12/87→08/91	; 04/88 ->	KH10108 ProKIT
2.0 i	85 kW	2 l	10/86→02/93	; -> 12/91	KH10108 ProKIT
2.0 i Cat	85 kW	2 l	10/86→02/93		

**OPEL - MANTA A (58\_, 59\_) 09/70→08/75**



































1.2	44 kW	1.2 l	04/72→08/75		KH00088 ProKIT
1.6	44 kW	1.6 l	02/75→08/75		
1.6	50 kW	1.6 l	09/70→08/75		
1.6	55 kW	1.6 l	02/75→08/75		
1.6 S	59 kW	1.6 l	09/70→08/75		
1.9 GT/E	77 kW	1.9 l	02/74→08/75		
1.9 S	65 kW	1.9 l	09/70→08/75		
1.9 S	66 kW	1.9 l	09/70→08/75		







































**OPEL - MERIVA A MPV (X03) 05/03→05/10**

1.3 CDTI (E75)	51 kW	1.3 l	04/05→05/10		KH10063 ProKIT
1.3 CDTI (E75)	55 kW	1.3 l	09/03→05/10	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.4 16V Twinport (E75)	66 kW	1.4 l	07/04→05/10		KH30114 ProKIT
1.4 16V Twinport LPG (E75)	66 kW	1.4 l	07/04→05/10		
1.6 (E75)	64 kW	1.6 l	05/03→05/10		
1.6 (E75)	77 kW	1.6 l	01/06→05/10		
1.6 16V (E75)	74 kW	1.6 l	05/03→01/06		
1.7 DTI (E75)	55 kW	1.7 l	09/03→05/10		
1.8 (E75)	92 kW	1.8 l	05/03→05/10		
1.6 Turbo (E75)	132 kW	1.6 l	09/05→05/10	; 03/06 ->	KH10108 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
					KH30114 ProKIT
1.7 CDTI (E75)	74 kW	1.7 l	09/03→05/10		KH10108 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
					KH30114 ProKIT




















































































     					
<b>OPEL - MERIVA A MPV (X03)</b>				<b>05/03→05/10</b>	
1.7 CDTI (E75)	92 kW	1.7 l	09/06→05/10	 ;  ; Rim Hole Number: 4	KH30054 ProKIT
					KH30114 ProKIT
<b>OPEL - MERIVA B MPV (S10)</b>				<b>06/10→03/17</b>	
1.3 CDTI (75)	55 kW	1.3 l	06/10→10/13		KH10348 ProKIT
1.3 CDTI (75)	70 kW	1.3 l	06/10→11/14	 ; Rim Hole Number: 5	KH30044 ProKIT
1.4 (75)	74 kW	1.4 l	06/10→03/17		
1.4 (75)	88 kW	1.4 l	06/10→03/17		
1.4 (75)	103 kW	1.4 l	06/10→03/17		
1.4 LPG (75)	88 kW	1.4 l	06/11→03/17		
1.6 CDTi (75)	100 kW	1.6 l	08/13→01/17		
1.6 CDTI (75)	70 kW	1.6 l	01/14→01/17		
1.6 CDTI (75)	81 kW	1.6 l	03/14→03/17		
1.7 CDTI (75)	74 kW	1.7 l	06/10→01/17		
1.7 CDTI (75)	81 kW	1.7 l	06/10→06/15		
1.7 CDTI (75)	96 kW	1.7 l	06/10→10/13		
<b>OPEL - MONTEREY A / MONTEREY B (M92, M98)</b>				<b>08/91→08/99</b>	
3.0 DTI (UBS73D, UBS73G)	117 kW	3 l	07/98→08/99		KH00026 ProKIT
3.1 TD (UBS69D, UBS69G)	84 kW	3.1 l	09/91→07/98		
3.2 (UBS25D, UBS25G)	130 kW	3.2 l	08/91→03/94		
3.5 V6 24V (UBS26D, UBS26G)	158 kW	3.5 l	07/98→08/99	 ; 	KH00026 ProKIT
<b>OPEL - MONZA A (22_)</b>				<b>02/78→07/82</b>	
2.8	103 kW	2.8 l	02/78→04/81		KH00093 ProKIT
3.0	110 kW	3 l	04/78→07/82		
<b>OPEL - MOVANO A Bus / MOVANO A Platform/Chassis / MOVANO A Van (X70)</b>				<b>07/98→</b>	
1.9 DTI (FD)	59 kW	1.9 l	09/00→10/01	 ;  16 Inch	KH10100 ProKIT
1.9 DTI (FD)	60 kW	1.9 l	10/01→	 ;  15 Inch;	
1.9 DTI (JD)	59 kW	1.9 l	09/00→10/01		
1.9 DTI (JD)	60 kW	1.9 l	10/01→	VIN B000184, B000207, B000486, B000807, B001462 ->	
2.2 DTI (ED, HD, UD0, UD4)	66 kW	2.2 l	09/00→		KH10195 ProKIT
2.2 DTI (FD)	66 kW	2.2 l	09/00→	VIN -> B000183, B000206, B000485, B000806, B001461;	
2.2 DTI (JD)	66 kW	2.2 l	09/00→		
2.5 CDTI (ED, HD, UD0, UD4)	74 kW	2.5 l	08/06→	 ;  16 Inch	KH10064 ProKIT
2.5 CDTI (ED, HD, UD0, UD4)	88 kW	2.5 l	08/06→	 ;  15 Inch	KH10092 ProKIT
2.5 CDTI (ED, HD, UD0, UD4)	107 kW	2.5 l	08/06→		
2.5 CDTI (FD)	74 kW	2.5 l	10/03→		
2.5 CDTI (FD)	88 kW	2.5 l	10/03→		
2.5 CDTI (FD)	107 kW	2.5 l	10/03→		
2.5 CDTI (JD)	74 kW	2.5 l	09/07→		
2.5 CDTI (JD)	88 kW	2.5 l	08/06→		
2.5 CDTI (JD)	107 kW	2.5 l	08/06→		
2.5 D (ED, HD, UD0, UD4)	59 kW	2.5 l	07/98→09/00		
2.5 D (FD)	59 kW	2.5 l	01/99→09/00		
2.5 D (JD)	59 kW	2.5 l	07/98→09/00		
2.5 DTi (ED, HD, UD0, UD4)	73 kW	2.5 l	10/03→		
2.5 DTI (ED, HD, UD0, UD4)	84 kW	2.5 l	10/01→		
2.5 DTi (FD)	73 kW	2.5 l	10/03→		
2.5 DTI (FD)	84 kW	2.5 l	10/01→		
2.5 DTI (JD)	84 kW	2.5 l	10/01→		
2.8 DTI (ED, HD, UD0, UD4)	84 kW	2.8 l	07/98→10/01		
2.8 DTI (FD)	84 kW	2.8 l	01/99→10/01		
2.8 DTI (JD)	84 kW	2.8 l	07/98→10/01		
3.0 DTI (ED, HD, UD0, UD4)	100 kW	3 l	10/03→		
3.0 DTI (FD)	100 kW	3 l	10/03→		
3.0 DTi (JD)	100 kW	3 l	10/03→		
<b>OPEL - MOVANO B Bus / MOVANO B Platform/Chassis / MOVANO B Van (X62)</b>				<b>05/10→</b>	
2.3 CDTI FWD (EV, HV, UV)	74 kW	2.3 l	05/10→		KH10139 ProKIT
2.3 CDTI FWD (EV, HV, UV)	81 kW	2.3 l	05/14→		KH10138 ProKIT
2.3 CDTI FWD (EV, HV, UV)	92 kW	2.3 l	05/10→		
2.3 CDTI FWD (EV, HV, UV)	96 kW	2.3 l	11/16→		
2.3 CDTI FWD (EV, HV, UV)	100 kW	2.3 l	05/14→		
2.3 CDTI FWD (EV, HV, UV)	107 kW	2.3 l	05/10→		
2.3 CDTI FWD (EV, HV, UV)	110 kW	2.3 l	01/13→		
2.3 CDTI FWD (EV, HV, UV)	120 kW	2.3 l	05/14→		
2.3 CDTI FWD (EV, HV, UV)	125 kW	2.3 l	11/16→		
2.3 CDTI FWD (FV)	74 kW	2.3 l	05/10→		
2.3 CDTI FWD (FV)	81 kW	2.3 l	02/12→		
2.3 CDTI FWD (FV)	92 kW	2.3 l	05/10→		
2.3 CDTI FWD (FV)	96 kW	2.3 l	11/16→		
2.3 CDTI FWD (FV)	100 kW	2.3 l	05/14→		
2.3 CDTI FWD (FV)	107 kW	2.3 l	05/10→		
2.3 CDTI FWD (FV)	110 kW	2.3 l	01/13→		
2.3 CDTI FWD (FV)	120 kW	2.3 l	05/14→		
2.3 CDTI FWD (FV)	125 kW	2.3 l	11/16→		
2.3 CDTI FWD (JV)	74 kW	2.3 l	12/10→		


































































      				
<b>OPEL - MOVANO B Bus / MOVANO B Platform/Chassis / MOVANO B Van (X62) 05/10→</b>				
2.3 CDTI FWD (JV)	81 kW	2.3 l	05/14→	 KH10139 ProKIT
2.3 CDTI FWD (JV)	92 kW	2.3 l	12/10→	 KH10138 ProKIT
2.3 CDTI FWD (JV)	100 kW	2.3 l	05/14→	
2.3 CDTI FWD (JV)	107 kW	2.3 l	12/10→	
2.3 CDTI FWD (JV)	110 kW	2.3 l	01/13→	
2.3 CDTI FWD (JV)	120 kW	2.3 l	05/14→	
2.3 CDTI FWD (JV)	125 kW	2.3 l	07/15→	
2.3 CDTI RWD (EV, HV, UV)	74 kW	2.3 l	05/10→	 KH10174 ProKIT
2.3 CDTI RWD (EV, HV, UV)	92 kW	2.3 l	05/10→	 KH00086 ProKIT
2.3 CDTI RWD (EV, HV, UV)	96 kW	2.3 l	11/16→	 KH10143 ProKIT
2.3 CDTI RWD (EV, HV, UV)	100 kW	2.3 l	05/14→	
2.3 CDTI RWD (EV, HV, UV)	110 kW	2.3 l	01/13→	
2.3 CDTI RWD (EV, HV, UV)	120 kW	2.3 l	05/14→	
2.3 CDTI RWD (FV)	74 kW	2.3 l	05/10→	
2.3 CDTI RWD (FV)	92 kW	2.3 l	05/10→	
2.3 CDTI RWD (FV)	96 kW	2.3 l	11/16→	
2.3 CDTI RWD (FV)	100 kW	2.3 l	05/14→	
2.3 CDTI RWD (FV)	110 kW	2.3 l	01/13→	
2.3 CDTI RWD (FV)	120 kW	2.3 l	05/14→	
2.3 CDTI RWD (EV, HV, UV)	107 kW	2.3 l	05/10→	 KH10174 ProKIT
2.3 CDTI RWD (FV)	107 kW	2.3 l	05/10→	 KH00086 ProKIT
<b>OPEL - OLYMPIA A / OLYMPIA A Coupe 08/67→08/71</b>				
1.0	44 kW	1 l	08/67→08/71	 KH00088 ProKIT
<b>OPEL - OMEGA A / OMEGA A Estate (V87) 09/86→04/94</b>				
1.8 (F19, M19, N19)	65 kW	1.8 l	09/87→03/94	 KH10218 ProKIT
1.8 (F19, M19, N19)	85 kW	1.8 l	09/86→03/94	
1.8 N (F19, M19, N19)	60 kW	1.8 l	09/86→08/87	
1.8 S (F19, M19, N19)	66 kW	1.8 l	09/86→03/94	
2.0 (F19, M19, N19)	73 kW	2 l	09/90→03/94	
2.0 (F19, M19, N19)	74 kW	2 l	09/90→03/94	
2.0 (F19, M19, N19)	90 kW	2 l	09/86→03/94	
2.0 i (F19, M19, N19)	85 kW	2 l	09/86→03/94	
2.3 D (F19, M19, N19)	54 kW	2.3 l	10/86→03/94	
1.8 (F35, M35)	65 kW	1.8 l	09/87→03/94	 KH10219 ProKIT
1.8 (F35, M35)	85 kW	1.8 l	09/86→03/94	 KH10219 ProKIT
2.0 i (F35, M35)	85 kW	2 l	09/86→04/94	 10/86 -> 02/94
2.3 D (F35, M35)	54 kW	2.3 l	09/86→03/94	
1.8 N (F35, M35)	60 kW	1.8 l	09/86→08/87	 10/86 ->
2.3 TD (F35, M35)	66 kW	2.3 l	09/86→08/88	
1.8 S (F35, M35)	66 kW	1.8 l	09/86→03/94	 10/86 -> 07/90
2.0 (F35, M35)	74 kW	2 l	09/90→03/94	 10/86 -> 02/94
2.6 i (F19, M19, N19)	110 kW	2.6 l	09/90→03/94	
2.6 i (F35, M35)	110 kW	2.6 l	09/90→03/94	
3.0 (3000) Cat (F19, M19, N19)	130 kW	3 l	03/88→03/94	
3.0 (F35, M35)	115 kW	3 l	03/87→03/94	
3.0 24V (3000) (F19, M19, N19)	147 kW	3 l	09/89→03/94	
3.0 Cat (F35, M35)	130 kW	3 l	03/87→03/94	
2.0 (F35, M35)	90 kW	2 l	09/86→03/94	 10/86 -> 07/93
2.3 TD (F19, M19, N19)	66 kW	2.3 l	10/86→08/88	 KH10218 ProKIT
				 KH10219 ProKIT
2.3 TD Interc. (F19, M19, N19)	74 kW	2.3 l	08/88→03/94	 10/88 -> 02/94
				 KH10218 ProKIT
2.3 TD Interc. (F35, M35)	74 kW	2.3 l	09/88→03/94	 10/88 -> 02/94
2.4 i (F19, M19, N19)	92 kW	2.4 l	09/88→03/94	 10/88 -> 07/91
2.4 i (F35, M35)	92 kW	2.4 l	09/88→03/94	
3.0 (3000) (F19, M19, N19)	115 kW	3 l	03/87→12/87	 KH10219 ProKIT
3.0 (3000) (F19, M19, N19)	130 kW	3 l	03/87→09/90	
3.0 (F35, M35)	130 kW	3 l	03/87→09/90	
3.6 24V Lotus (F19, M19, N19)	277 kW	3.6 l	08/90→09/92	
3.0 24V (3000) (F19, M19, N19)	150 kW	3 l	09/89→03/94	 10/89 -> 02/94
3.0 24V (F35, M35)	147 kW	3 l	09/89→03/94	
<b>OPEL - OMEGA B (V94) 03/94→07/03</b>				
2.0 (F69, M69, P69)	85 kW	2 l	03/94→09/99	 KH10206 ProKIT
2.0 (F69, M69, P69)	85 kW	2 l	03/94→12/00	
2.5 TD (F69, M69, P69)	96 kW	2.5 l	04/94→07/03	
2.5 V6 (F69, M69, P69)	125 kW	2.5 l	03/94→09/00	
2.0 16V (F69, M69, P69)	100 kW	2 l	03/94→09/99	 -> 08/99
				 KH10206 ProKIT

















































										
<b>OPEL - OMEGA B (V94)</b>										<b>03/94→07/03</b>
2.0 DTI 16V (F69, M69, P69)	74 kW	2 l	09/97→09/00							KH10206 ProKIT
2.2 16V (F69, M69, P69)	106 kW	2.2 l	09/99→07/03							
2.2 DTI 16V (F69, M69, P69)	88 kW	2.2 l	09/00→07/03							
2.5 DTI (F69, M69, P69)	110 kW	2.5 l	09/01→07/03							
2.6 V6 (F69, M69, P69)	132 kW	2.6 l	09/00→07/03							
3.2 V6 (F69, M69, P69)	160 kW	3.2 l	02/01→07/03							
3.0 V6 (F69, M69, P69)	155 kW	3 l	04/94→02/01							KH10206 ProKIT
										KH10219 ProKIT
<b>OPEL - OMEGA B Estate (V94)</b>										<b>03/94→07/03</b>
2.0 (F35, M35, P35)	85 kW	2 l	03/94→09/99							KH10219 ProKIT
2.0 16V (F35, M35, P35)	100 kW	2 l	03/94→09/99							
2.0 DTI 16V (F35, M35, P35)	74 kW	2 l	09/97→09/00							
2.5 DTI (F35, M35, P35)	110 kW	2.5 l	09/01→07/03							
2.5 TD (F35, M35, P35)	96 kW	2.5 l	04/94→07/01							
2.5 V6 (F35, M35, P35)	125 kW	2.5 l	03/94→09/00							
3.0 V6 (F35, M35, P35)	155 kW	3 l	04/94→02/01							
2.2 16V (F35, M35, P35)	106 kW	2.2 l	09/99→07/03							KH10219 ProKIT
2.2 DTI 16V (F35, M35, P35)	88 kW	2.2 l	09/00→07/03							
2.6 V6 (F35, M35, P35)	132 kW	2.6 l	09/00→07/03							
3.2 V6 (F35, M35, P35)	160 kW	3.2 l	02/01→07/03							
<b>OPEL - REKORD B / REKORD B Coupe / REKORD B Estate / REKORD C / REKORD C Coupe / REKORD C Estate</b>										<b>08/65→12/71</b>
1.5	43 kW	1.5 l	08/66→12/71							KH00088 ProKIT
1.5	44 kW	1.5 l	08/65→08/66							KH00093 ProKIT
1.5	44 kW	1.5 l	02/68→12/71							
1.7	44 kW	1.7 l	08/66→12/71							
1.7	49 kW	1.7 l	02/68→12/71							
1.7	55 kW	1.7 l	08/65→12/66							
1.9	66 kW	1.9 l	08/65→12/66							
1.9	66 kW	1.9 l	08/65→02/67							
1.9	66 kW	1.9 l	08/66→12/71							
2.2	70 kW	2.2 l	08/66→09/69							
1.7 S	55 kW	1.7 l	08/66→12/71							KH00088 ProKIT
<b>OPEL - REKORD E / REKORD E Estate / REKORD P2 / REKORD P2 Coupe / REKORD P2 Estate (17_, 11_, 14_, 16_, 18_, 19_, 61_, 66_, 67_)</b>										<b>08/60→08/86</b>
1.5	37 kW	1.5 l	08/60→01/63							KH00093 ProKIT
1.7	44 kW	1.7 l	08/60→01/63							
1.7	48 kW	1.7 l	08/61→01/63							
2.3 D	52 kW	2.3 l	11/82→08/86							
1.7	44 kW	1.7 l	09/77→10/82			01/78 ->	MT, AT, AC, ☉			KH00093 ProKIT
1.9	55 kW	1.9 l	09/77→10/82							
2.0	66 kW	2 l	09/77→10/82			01/78 ->	12/81; VIN -> 11028762; MT			KH00093 ProKIT
2.0 D	43 kW	2 l	09/77→10/82			01/78 ->				KH00093 ProKIT
2.1 D	44 kW	2.1 l	09/77→07/78							
<b>OPEL - SENATOR A (29_)</b>										<b>02/78→08/87</b>
2.5	85 kW	2.5 l	05/78→12/80			VIN 91362918 ->				KH00093 ProKIT
2.8	103 kW	2.8 l	02/78→04/81							
3.0	110 kW	3 l	04/78→07/82							
3.0	115 kW	3 l	09/85→08/87							
<b>OPEL - SENATOR B (V88)</b>										<b>09/87→09/93</b>
2.6 i (P19)	110 kW	2.6 l	09/90→09/93			-> 06/93				KH10219 ProKIT
3.0 (P19)	115 kW	3 l	09/87→09/93							
3.0 i Cat (P19)	130 kW	3 l	01/88→09/93							
3.0 (P19)	130 kW	3 l	01/88→09/90							KH10219 ProKIT
3.0 24V (P19)	150 kW	3 l	09/89→09/93			10/89 ->	06/93			KH10219 ProKIT
<b>OPEL - SIGNUM Hatchback (Z03)</b>										<b>05/03→12/08</b>
1.8 (F48)	90 kW	1.8 l	05/03→07/05			06/03 ->				KH30065 ProKIT
3.0 V6 CDTI (F48)	130 kW	3 l	05/03→07/05			-> 12/04;				KH30061 ProKIT
3.2 V6 (F48)	155 kW	3.2 l	05/03→07/05			06/03 ->				KH30071 ProKIT
1.8 (F48)	103 kW	1.8 l	09/05→12/08			10/05 ->	11/08			KH30065 ProKIT
3.0 V6 CDTI (F48)	135 kW	3 l	09/05→12/08							KH30061 ProKIT
						10/05 ->	11/08			KH30071 ProKIT
1.9 CDTI (F48)	74 kW	1.9 l	08/05→02/08			10/05 ->				KH30065 ProKIT
										KH30061 ProKIT
						10/05 ->				KH30071 ProKIT



											
<b>OPEL - SIGNUM Hatchback (Z03)</b>										<b>05/03→12/08</b>	
1.9 CDTI (F48)	88 kW	1.9 l	04/04→02/08		-> 09/05;						KH30065 ProKIT
1.9 CDTI (F48)	110 kW	1.9 l	04/04→02/08		10/05 ->						
					-> 12/04;						KH30061 ProKIT
											KH30071 ProKIT
2.0 DTI (F48)	74 kW	2 l	05/03→04/04		06/03 ->						KH30065 ProKIT
2.2 DTI (F48)	92 kW	2.2 l	05/03→04/04								KH30061 ProKIT
					06/03 ->						KH30071 ProKIT
2.0 Turbo (F48)	129 kW	2 l	05/03→12/08		06/03 -> 09/05;						KH30065 ProKIT
					10/05 -> 11/08						
					-> 12/04;						KH30061 ProKIT
					06/03 -> 11/08						KH30071 ProKIT
2.2 direct (F48)	114 kW	2.2 l	05/03→09/08		06/03 -> 09/05;						KH30065 ProKIT
					10/05 ->						
					-> 12/04;						KH30061 ProKIT
					06/03 ->						KH30071 ProKIT
2.8 V6 Turbo (F48)	169 kW	2.8 l	09/05→12/08		10/05 -> 12/06						KH30065 ProKIT
											KH30061 ProKIT
					10/05 -> 12/06						KH30071 ProKIT
2.8 V6 Turbo (F48)	184 kW	2.8 l	01/06→12/08		12/06 -> 11/08						KH30065 ProKIT
											KH30061 ProKIT
					12/06 -> 11/08						KH30071 ProKIT
<b>OPEL - TIGRA (S93)</b>										<b>07/94→12/00</b>	
1.4 16V (F07)	63 kW	1.4 l	08/97→12/00								KH10376 ProKIT
1.4 16V (F07)	66 kW	1.4 l	07/94→12/00								KH00005 ProKIT
1.6 16V (F07)	74 kW	1.6 l	08/97→08/98								
1.6 16V (F07)	78 kW	1.6 l	07/94→08/98								
<b>OPEL - TIGRA TwinTop (X04)</b>										<b>06/04→12/10</b>	
1.3 CDTI (R97)	51 kW	1.3 l	06/04→12/10								KH10063 ProKIT
1.4 (R97)	66 kW	1.4 l	06/04→12/10		07/08 -> 08/09;						KH20118 ProKIT
											KH10113 ProKIT
1.8 (R97)	92 kW	1.8 l	06/04→12/10								KH10063 ProKIT
					07/04 -> 08/09;						KH20118 ProKIT
											KH10113 ProKIT
<b>OPEL - VECTRA A / VECTRA A Hatchback (J89)</b>										<b>04/88→11/95</b>	
1.4 S (F19, M19)	55 kW	1.4 l	09/88→06/92								KH10107 ProKIT
											KH00005 ProKIT
1.4 S (F68, M68)	55 kW	1.4 l	04/88→06/92		09/88 ->						KH10107 ProKIT
											KH00005 ProKIT
1.6 (F19, M19)	51 kW	1.6 l	08/92→07/93								KH10376 ProKIT
1.6 (F68, M68)	51 kW	1.6 l	08/92→07/93		01/93 ->		Rim Hole Number: 4				KH30054 ProKIT
					01/93 ->		Rim Hole Number: 4				KH30055 ProKIT
					-> 12/92						KH00005 ProKIT
1.6 (F19, M19)	60 kW	1.6 l	09/88→05/93		-> 07/92						KH10107 ProKIT
1.6 S	60 kW	1.6 l	09/88→05/93		-> 07/92						KH10108 ProKIT
											KH10376 ProKIT
					01/93 ->		Rim Hole Number: 4				KH30054 ProKIT
					01/93 ->		Rim Hole Number: 4				KH30055 ProKIT
					-> 12/92						KH00005 ProKIT
1.6 (F68, M68)	65 kW	1.6 l	08/88→06/94		01/93 ->		Rim Hole Number: 4				KH30054 ProKIT
1.7 D (F68, M68)	44 kW	1.7 l	07/92→11/95		01/93 ->		Rim Hole Number: 4				KH30055 ProKIT
					-> 12/92						KH00005 ProKIT
1.6 i (F19, M19)	52 kW	1.6 l	09/93→11/95		-> 12/93;	VIN -> P1999999, P5999999, P7999999					KH10107 ProKIT
							Rim Hole Number: 4				KH10376 ProKIT
							Rim Hole Number: 4				KH30054 ProKIT
							Rim Hole Number: 4				KH30055 ProKIT
1.6 i (F19, M19)	55 kW	1.6 l	09/88→11/95								KH10376 ProKIT
					VIN -> P1999999, P5999999, P7999999						KH10107 ProKIT
					01/93 ->		Rim Hole Number: 4				KH30054 ProKIT
					01/93 ->		Rim Hole Number: 4				KH30055 ProKIT
					-> 12/92						KH00005 ProKIT

     				<b>13</b>		<b>i</b>		
<b>OPEL - VECTRA A / VECTRA A Hatchback (J89)</b>							<b>04/88→11/95</b>	
1.6 i (F19, M19)	55 kW	1.6 l	09/93→11/95	 ; -> 12/93; VIN -> P1999999, P5999999, P7999999	KH10108 ProKIT			
					KH10376 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
1.6 i (F68, M68)	52 kW	1.6 l	09/93→11/95	 ; -> 12/93; VIN -> P7999999, P5999999, P1999999	KH10107 ProKIT			
					KH10376 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
1.6 i (F68, M68)	55 kW	1.6 l	09/93→11/95		KH10376 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
					KH10376 ProKIT			
1.6 i Cat (F68, M68)	55 kW	1.6 l	09/88→11/95	 ; -> 12/93; VIN -> P1999999, P5999999, P7999999	KH10107 ProKIT			
				 ; -> 12/93; VIN -> P1999999, P5999999, P7999999	KH10108 ProKIT			
					KH10376 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
				 ; -> 12/92	KH00005 ProKIT			
1.7 D (F19, M19)	42 kW	1.7 l	10/88→09/92	 ; -> 06/92	KH10108 ProKIT			
1.7 D (F68, M68)	42 kW	1.7 l	09/88→09/92		KH00005 ProKIT			
1.7 D (F19, M19)	44 kW	1.7 l	07/92→11/95	 ; -> 09/95	KH10108 ProKIT			
1.8 i Cat (F19, M19)	66 kW	1.8 l	03/90→11/95	 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
1.8 i Cat (F68, M68)	66 kW	1.8 l	03/90→11/95	 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
2.0 i Cat (F19, M19)	85 kW	2 l	09/88→11/95	 ; -> 12/92	KH00005 ProKIT			
2.0 i Cat (F68, M68)	85 kW	2 l	09/88→11/95		KH10108 ProKIT			
1.7 TD (F19, M19)	60 kW	1.7 l	03/90→11/95	 ; 07/91 -> 09/95	KH10108 ProKIT			
1.7 TD (F68, M68)	60 kW	1.7 l	03/90→11/95	 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
				 ; -> 12/92	KH00005 ProKIT			
1.8 i (F68, M68)	66 kW	1.8 l	09/88→10/90		KH10108 ProKIT			
1.8 S (F19, M19)	65 kW	1.8 l	09/88→07/89		KH00005 ProKIT			
1.8 S (F19, M19)	66 kW	1.8 l	09/89→10/90					
2.0 (F19, M19)	74 kW	2 l	09/88→09/89					
2.0 i (F19, M19)	85 kW	2 l	09/88→10/90					
2.0 i (F68, M68)	85 kW	2 l	09/88→10/90					
1.8 S (F68, M68)	65 kW	1.8 l	09/88→07/89		KH00005 ProKIT			
2.0 i 16V (F68, M68)	110 kW	2 l	02/89→10/90					
1.8 S 4x4 (F19, M19)	65 kW	1.8 l	01/89→07/89		KH10108 ProKIT			
2.0 i 4x4 (F19, M19)	85 kW	2 l	01/89→10/90		KH10219 ProKIT			
2.0 i 4x4 (F19, M19)	95 kW	2 l	08/89→07/92					
2.0 (F68, M68)	74 kW	2 l	04/88→09/89	 ; 09/88 ->	KH10108 ProKIT			
					KH00005 ProKIT			
2.0 i (F19, M19)	95 kW	2 l	09/88→09/92	 ; -> 07/92	KH10108 ProKIT			
					KH00005 ProKIT			
2.0 i 16V (F19, M19)	100 kW	2 l	08/92→08/95		KH10108 ProKIT			
2.0 i 16V (F68, M68)	100 kW	2 l	08/92→08/95	 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
				 ; -> 12/92	KH00005 ProKIT			
2.0 i 16V 4x4 (F19, M19)	100 kW	2 l	06/94→11/95		KH10219 ProKIT			
2.5 CD 4x4 (F19, M19)	125 kW	2.5 l	08/92→08/95					
2.0 i 16V Cat (F68, M68)	110 kW	2 l	02/90→11/95	 ; 03/90 -> 09/93	KH10108 ProKIT			
2000/GT 16V Cat (F19, M19)	110 kW	2 l	02/90→11/95	 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
				 ; -> 12/92	KH00005 ProKIT			
2.0 i Cat 4x4 (F19, M19)	85 kW	2 l	01/89→11/95	 ; 07/92 -> 09/95	KH10108 ProKIT			
					KH10219 ProKIT			
2.0 i GT (F68, M68)	95 kW	2 l	09/88→11/95	 ; -> 07/92	KH10108 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30054 ProKIT			
				 (ABS); Rim Hole Number: 4	KH30055 ProKIT			
				 ; -> 12/92	KH00005 ProKIT			
2.0 i Turbo 4x4 (F19, M19)	150 kW	2 l	06/94→11/95	 ; -> 09/95; VIN P1000001 ->	KH10206 ProKIT			
					KH10219 ProKIT			
2.5 V6 (F19, M19)	125 kW	2.5 l	02/93→11/95	 ; 05/93 -> 09/95	KH10206 ProKIT			
2.5 V6 (F68, M68)	125 kW	2.5 l	02/93→11/95	 (ABS)	KH30114 ProKIT			












































































     					
<b>OPEL - VECTRA A / VECTRA A Hatchback (J89)</b>					<b>04/88→11/95</b>
2000/GT 16V (F19, M19)	110 kW	2 l	01/89→06/94	 ; <b>03/90</b> →	<b>KH10108</b> ProKIT
				 ; <b>01/93</b> →; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
				 ; <b>01/93</b> →; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30055</b> ProKIT
				 ; → <b>12/92</b>	<b>KH00005</b> ProKIT
2000/GT 16V Cat 4x4 (F19, M19)	110 kW	2 l	02/90→11/95	 ; → <b>09/95</b>	<b>KH10108</b> ProKIT
					<b>KH10219</b> ProKIT
2000 16V 4x4 (F19, M19)	110 kW	2 l	01/89→10/90	 ; <b>03/90</b> →	<b>KH10108</b> ProKIT
					<b>KH10219</b> ProKIT
<b>OPEL - VECTRA B / VECTRA B Estate / VECTRA B Hatchback (J96)</b>					<b>09/95→07/03</b>
1.6 GL (F19)	60 kW	1.6 l	09/95→08/96	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
2.0 i (F19)	82 kW	2 l	10/95→04/02		<b>KH30114</b> ProKIT
2.0 i (F19)	85 kW	2 l	09/95→04/02		
2.0 i (F35)	82 kW	2 l	11/96→02/02		
2.0 i (F68)	82 kW	2 l	10/95→02/02		
2.0 i 16V (F35)	85 kW	2 l	07/00→07/03		
2.0 i 16V (F68)	85 kW	2 l	07/00→07/03		
1.6 i (F19)	55 kW	1.6 l	10/95→04/02	 ; → <b>01/99</b>	<b>KH10206</b> ProKIT
1.6 i (F35)	55 kW	1.6 l	11/96→06/00		
1.6 i (F68)	55 kW	1.6 l	10/95→07/03	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.8 i 16V (F19)	85 kW	1.8 l	10/95→09/00		<b>KH30114</b> ProKIT
1.8 i 16V (F68)	85 kW	1.8 l	10/95→09/00		
2.0 DI 16V (F19)	60 kW	2 l	11/96→04/02		
2.0 DI 16V (F35)	60 kW	2 l	11/96→06/00		
2.0 DI 16V (F68)	60 kW	2 l	11/96→06/00		
2.0 i 16V (F19)	100 kW	2 l	09/95→06/00		
2.0 i 16V (F35)	100 kW	2 l	11/96→06/00		
2.0 i 16V (F68)	100 kW	2 l	09/95→06/00		
1.6 i 16V (F19)	74 kW	1.6 l	10/95→04/02	 ; → <b>03/02</b>	<b>KH10206</b> ProKIT
1.6 i 16V (F68)	74 kW	1.6 l	10/95→07/02		
1.8 i 16V (F19)	92 kW	1.8 l	09/00→04/02	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.8 i 16V (F68)	92 kW	1.8 l	09/00→07/03		<b>KH30114</b> ProKIT
1.6 i 16V (F35)	74 kW	1.6 l	11/96→07/02		<b>KH10206</b> ProKIT
1.8 i 16V (F35)	85 kW	1.8 l	11/96→09/00	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
					<b>KH30114</b> ProKIT
1.7 TD (F19)	60 kW	1.7 l	10/95→12/98		<b>KH10206</b> ProKIT
1.7 TD (F68)	60 kW	1.7 l	10/95→12/98	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.7 TD (F35)	60 kW	1.7 l	11/96→12/97	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
1.8 FlexFuel (F68)	85 kW	1.8 l	01/99→09/00		<b>KH30114</b> ProKIT
2.2 DTI 16V (F19)	88 kW	2.2 l	09/00→04/02		
2.2 DTI 16V (F35)	88 kW	2.2 l	09/00→04/02		
2.2 DTI 16V (F68)	88 kW	2.2 l	09/00→04/02		
2.2 i 16V (F19)	102 kW	2.2 l	07/00→07/02		
2.2 i 16V (F35)	102 kW	2.2 l	07/00→07/02		
2.2 i 16V (F68)	102 kW	2.2 l	07/00→07/02		
2.5 (F68)	144 kW	2.5 l	10/99→06/00		
1.8 i 16V (F35)	92 kW	1.8 l	09/00→07/03	 ; → <b>06/03</b>	<b>KH10206</b> ProKIT
				 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
					<b>KH30114</b> ProKIT
2.0 DTI 16V (F19)	74 kW	2 l	06/97→04/02	 ; <b>09/97</b> → <b>03/02</b>	<b>KH10206</b> ProKIT
2.0 DTI 16V (F68)	74 kW	2 l	06/97→07/03	 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
					<b>KH30114</b> ProKIT
2.0 DTI 16V (F35)	74 kW	2 l	06/97→07/03	 ; <b>09/97</b> → <b>06/03</b>	<b>KH10206</b> ProKIT
				 ; <b>ABS</b> ; Rim Hole Number: 4	<b>KH30054</b> ProKIT
					<b>KH30114</b> ProKIT
2.2 DTI 16V (F19)	92 kW	2.2 l	09/00→04/02	 ; → <b>03/02</b>	<b>KH10206</b> ProKIT
2.2 DTI 16V (F68)	92 kW	2.2 l	09/00→07/03		<b>KH30114</b> ProKIT
2.2 i 16V (F19)	108 kW	2.2 l	09/00→04/02		
2.2 i 16V (F68)	108 kW	2.2 l	09/00→07/03		
2.6 i V6 (F19)	125 kW	2.6 l	09/00→04/02		
2.6 i V6 (F68)	125 kW	2.6 l	09/00→07/03		
2.2 DTI 16V (F35)	92 kW	2.2 l	09/00→07/03	 ; → <b>06/03</b>	<b>KH10206</b> ProKIT
2.2 i 16V (F35)	108 kW	2.2 l	09/00→07/03		<b>KH30114</b> ProKIT
2.6 i V6 (F35)	125 kW	2.6 l	09/00→07/03		
2.5 i V6 (F19)	125 kW	2.5 l	10/95→09/00	 ; → <b>01/99</b>	<b>KH10206</b> ProKIT
2.5 i V6 (F35)	125 kW	2.5 l	11/96→09/00		<b>KH30114</b> ProKIT
2.5 i V6 (F68)	125 kW	2.5 l	10/95→09/00		
i 500 2.5 (F19)	143 kW	2.5 l	05/98→09/00		
i 500 2.5 (F35)	143 kW	2.5 l	05/98→09/00		









				OPEL - VECTRA C / VECTRA C Estate / VECTRA C GTS (Z02)		04/02→01/09	
1.6 (F35)	77 kW	1.6 l	12/05→08/08	VIN -> 41999999;			KH30061 ProKIT
1.9 CDTi (F35)	74 kW	1.9 l	06/05→08/08	VIN -> 48999999;			
1.9 CDTi (F68)	74 kW	1.9 l	06/05→08/08				KH30065 ProKIT
1.9 CDTi (F69)	74 kW	1.9 l	10/05→08/08				
2.8 V6 Turbo (F35)	184 kW	2.8 l	08/05→08/08				KH30071 ProKIT
2.8 V6 Turbo (F35)	206 kW	2.8 l	07/06→08/08				
1.6 (F68)	74 kW	1.6 l	08/05→08/08	VIN -> 41999999;			KH30061 ProKIT
2.8 V6 Turbo (F69)	188 kW	2.8 l	08/05→09/06	VIN -> 48999999;			
3.0 CDTi (F68)	135 kW	3 l	08/05→08/08				KH30065 ProKIT
3.0 CDTi (F69)	135 kW	3 l	08/05→08/08	10/05 ->			
3.0 V6 CDTi (F35)	135 kW	3 l	08/05→08/08	10/05 ->			KH30071 ProKIT
1.6 (F68)	77 kW	1.6 l	01/06→08/08	VIN -> 41999999;			KH30061 ProKIT
1.6 (F69)	77 kW	1.6 l	08/05→08/08	VIN -> 48999999;			
1.8 (F35)	103 kW	1.8 l	08/05→08/08				KH30065 ProKIT
1.8 (F68)	103 kW	1.8 l	08/05→08/08	VIN -> 41999999, 48999999;			
1.8 (F69)	103 kW	1.8 l	08/05→08/08				KH30071 ProKIT
1.6 16V (F35)	74 kW	1.6 l	06/04→09/05	VIN -> 41999999, 48999999;			KH30065 ProKIT
				01/05 ->; VIN 51000001 ->			
				VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
1.6 16V (F69)	74 kW	1.6 l	07/04→10/05	VIN -> 41999999, 48999999;			KH30065 ProKIT
1.8 (F35)	90 kW	1.8 l	10/03→09/06	01/05 ->; VIN 58000001 ->			
1.8 16V	90 kW	1.8 l	04/02→09/08				KH30061 ProKIT
1.9 CDTi (F35)	110 kW	1.9 l	04/04→08/08	VIN -> 41999999;			
1.9 CDTi (F68)	88 kW	1.9 l	04/04→01/09	VIN -> 48999999;			
1.9 CDTi (F68)	110 kW	1.9 l	04/04→08/08				KH30071 ProKIT
1.9 CDTi (F69)	88 kW	1.9 l	04/04→01/09				
2.0 16V Turbo (F68)	129 kW	2 l	03/03→08/08				
2.0 Turbo (F35)	129 kW	2 l	10/03→08/08				
2.2 DGi (F68)	114 kW	2.2 l	10/03→08/08				
2.2 DGi (F69)	114 kW	2.2 l	10/03→08/08				
2.2 direct (F35)	114 kW	2.2 l	10/03→08/08				
3.0 CDTi (F68)	130 kW	3 l	06/03→07/05				
3.0 CDTi (F69)	130 kW	3 l	02/03→07/05				
3.0 V6 CDTi (F35)	130 kW	3 l	10/03→07/05				
3.2 V6 (F35)	155 kW	3.2 l	10/03→07/05				
1.8 (F69)	81 kW	1.8 l	04/02→07/08	VIN -> 41999999, 48999999;			KH30065 ProKIT
2.2 16V (F68)	108 kW	2.2 l	08/02→08/08	01/05 -> 09/05; VIN 58000001 ->			
2.2 16V (F69)	108 kW	2.2 l	04/02→12/08	VIN -> 41999999;			KH30061 ProKIT
2.2 DTi (F35)	92 kW	2.2 l	10/03→12/05				
2.2 DTi 16V (F68)	92 kW	2.2 l	08/02→07/06	VIN -> 48999999;			
3.2 V6 (F68)	155 kW	3.2 l	08/02→07/06	-> 09/05			KH30071 ProKIT
1.8 16V (F68)	90 kW	1.8 l	08/02→09/08	VIN -> 41999999, 48999999;			KH30065 ProKIT
				01/05 -> 09/05; VIN 51000001 ->			
				01/05 ->; VIN 58000001 ->			
				VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
1.9 CDTi (F35)	88 kW	1.9 l	04/04→01/09	VIN -> 41999999, 48999999;			KH30065 ProKIT
				01/05 ->; VIN 510000001 ->			
				01/05 -> 09/05; VIN 58000001 ->			
				VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
1.9 CDTi (F69)	110 kW	1.9 l	04/04→08/08	VIN -> 41999999, 48999999;  (ESP)			KH30065 ProKIT
				01/05 ->; VIN 58000001 ->			
				VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
2.0 16V Turbo (F69)	129 kW	2 l	03/03→08/08	07/03 ->; VIN -> 41999999, 48999999;			KH30065 ProKIT
				01/05 ->; VIN 58000001 ->			
				VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
				07/03 ->			KH30065 ProKIT
2.0 DTi (F35)	74 kW	2 l	10/03→08/05	VIN -> 41999999, 48999999;			KH30065 ProKIT
2.0 DTi 16V (F68)	74 kW	2 l	08/02→08/05	01/05 -> 03/05; VIN 58000001 ->			
2.0 DTi 16V (F69)	74 kW	2 l	04/02→08/06	VIN -> 41999999;			KH30061 ProKIT
				VIN -> 48999999;			KH30071 ProKIT
				-> 03/05			KH30071 ProKIT




















































				     	
<b>OPEL - VECTRA C / VECTRA C Estate / VECTRA C GTS (Z02)</b>				<b>04/02→01/09</b>	
2.2 DTI 16V (F69)	92 kW	2.2 l	04/02→07/04	 VIN -> 41999999;   VIN -> 48999999;   VIN -> 41999999, 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F35)	169 kW	2.8 l	08/05→10/08	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F68)	169 kW	2.8 l	08/05→08/08	 VIN -> 48999999; 	KH30071 ProKIT
2.8 V6 Turbo (F69)	169 kW	2.8 l	08/05→10/06	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F35)	188 kW	2.8 l	08/05→09/08	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F68)	188 kW	2.8 l	08/05→09/08	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F69)	184 kW	2.8 l	08/05→08/08	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
2.8 V6 Turbo (F68)	206 kW	2.8 l	08/06→08/08	 VIN -> 48999999; 	KH30065 ProKIT
2.8 V6 Turbo (F69)	184 kW	2.8 l	08/05→08/08	 VIN -> 41999999;   VIN -> 48999999; 	KH30065 ProKIT
3.2 V6 (F69)	155 kW	3.2 l	08/02→07/06	 VIN -> 41999999;   VIN -> 48999999; 	KH30061 ProKIT
<b>OPEL - VIVARO A Bus / VIVARO A Platform/Chassis / VIVARO A Van (X83)</b>				<b>02/01→07/14</b>	
1.9 Di	60 kW	1.9 l	08/01→07/14	 VIN 3V613234 ->; 	KH10115 ProKIT
1.9 DTI	74 kW	1.9 l	02/01→12/10		KH10090 ProKIT
2.0 16V	88 kW	2 l	01/02→07/06		
2.0 CDTI	66 kW	2 l	01/06→07/14		
2.0 CDTI	84 kW	2 l	08/06→07/14		
2.0 CDTI (F7, J7, A07)	66 kW	2 l	08/06→07/14		
2.0 CDTI (F7, J7, A07)	84 kW	2 l	08/06→07/14		
2.0 CDTI (F7)	66 kW	2 l	08/06→07/14		
2.0 CDTI (F7)	84 kW	2 l	08/06→07/14		
2.0 ECOTEC	86 kW	2 l	08/06→07/14		
2.0 ECOTEC (F7, A07, J7)	86 kW	2 l	08/06→07/14		
2.0 ECOTEC (F7)	86 kW	2 l	08/06→07/14		
2.5 CDTI	84 kW	2.5 l	08/06→03/10		
2.5 CDTI	107 kW	2.5 l	08/06→07/14		
2.5 CDTI (F7, J7, A07)	84 kW	2.5 l	08/06→03/10		
2.5 CDTI (F7, J7, A07)	107 kW	2.5 l	08/06→07/14		
2.5 CDTI (F7)	84 kW	2.5 l	08/06→03/10		
2.5 CDTI (F7)	107 kW	2.5 l	08/06→07/14		
2.5 DTI	99 kW	2.5 l	04/03→03/10		
1.9 DI (F7, J7, A07)	60 kW	1.9 l	08/01→07/06	 ABS;  VIN -> 3V613233	KH10149 ProKIT
1.9 DI (F7)	60 kW	1.9 l	08/01→07/06	 ABS;  VIN -> 3V613233	KH10196 ProKIT
1.9 DTI (F7, J7, A07)	74 kW	1.9 l	08/01→07/14	 VIN 3V613234 ->; 	KH10115 ProKIT
1.9 DTI (F7)	74 kW	1.9 l	08/01→07/14		KH10090 ProKIT
2.0 16V (F7, J7, A07)	88 kW	2 l	08/01→07/06		
2.0 16V (F7)	88 kW	2 l	08/01→07/06		
2.5 DTI (F7, J7, A07)	99 kW	2.5 l	04/03→03/10		
2.5 DTI (F7)	99 kW	2.5 l	04/03→03/10		
<b>OPEL - ZAFIRA / ZAFIRA FAMILY B (A05)</b>				<b>07/05→04/15</b>	
1.6 (M75)	77 kW	1.6 l	07/05→09/12	 Rim Hole Number: 5	KH30044 ProKIT
1.6 (M75)	85 kW	1.6 l	01/08→04/15		
1.8 (M75)	103 kW	1.8 l	07/05→04/15		
1.6 CNG (M75)	69 kW	1.6 l	07/05→04/15	 VIN 62034066, 6G019310 ->	KH30084 ProKIT
1.6 CNG Turbo (M75)	110 kW	1.6 l	04/10→04/15		
1.7 CDTI (M75)	81 kW	1.7 l	01/08→04/15	 VIN 62034066, 6G019310 ->	KH30084 ProKIT
1.9 CDTI (M75)	74 kW	1.9 l	07/05→12/10	 Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTI (M75)	88 kW	1.9 l	07/05→04/15		
2.0 (M75)	147 kW	2 l	07/05→12/10		
2.2 (M75)	110 kW	2.2 l	07/05→12/12		
1.7 CDTI (M75)	92 kW	1.7 l	03/07→04/15	 OE 16 03 841, 93188477	KH30084 ProKIT
1.8 (M75)	88 kW	1.8 l	06/13→04/15	 FR;  Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTI (M75)	110 kW	1.9 l	07/05→04/15	 Rim Hole Number: 5	KH30074 ProKIT
2.0 (M75)	177 kW	2 l	01/06→12/10	 Rim Hole Number: 5	KH30044 ProKIT
<b>OPEL - ZAFIRA A MPV (T98)</b>				<b>04/99→06/05</b>	
1.6 (F75)	76 kW	1.6 l	10/03→06/05	 ABS  ABS	KH30114 ProKIT
				 ABS	KH30130 ProKIT

     					
OPEL - ZAFIRA A MPV (T98)				04/99→06/05	
1.6 16V (F75)	74 kW	1.6 l	04/99→06/05	; ; Rim Hole Number: 4	KH30057 ProKIT
1.6 CNG (F75)	71 kW	1.6 l	09/01→06/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V (F75)	85 kW	1.8 l	04/99→09/00	; Rim Hole Number: 4;	KH30059 ProKIT
1.8 16V (F75)	92 kW	1.8 l	09/00→06/05	; Rim Hole Number: 5;	KH30114 ProKIT
2.0 DI 16V (F75)	60 kW	2 l	07/99→06/05	;	KH30130 ProKIT
2.0 DTI 16V (F75)	74 kW	2 l	09/00→06/05	;	
2.0 OPC (F75)	141 kW	2 l	09/01→06/05	;	
2.0 OPC (F75)	147 kW	2 l	11/02→06/05		
2.2 16V (F75)	108 kW	2.2 l	09/00→06/05		
2.2 DTI 16V (F75)	86 kW	2.2 l	01/02→06/05		
2.2 DTI 16V (F75)	92 kW	2.2 l	01/02→06/05		
1.6 LPG (F75)	74 kW	1.6 l	04/99→06/05	;	KH30114 ProKIT
1.6 LPG (F75)	76 kW	1.6 l	10/03→06/05		
OPEL - ZAFIRA B Box Body/MPV (A05)				07/05→04/15	
1.6 CNG Turbo VAN (M75)	110 kW	1.6 l	02/09→04/15	; VIN 62034066, 6G019310 ->	KH30084 ProKIT
1.6 CNG VAN (M75)	69 kW	1.6 l	07/05→04/15	; VIN -> 62034065, 6G019309	KH30046 ProKIT
1.9 CDTI VAN (M75)	88 kW	1.9 l	07/05→04/15	; VIN 62034066, 6G019310 ->	KH30084 ProKIT
2.0 VAN (M75)	147 kW	2 l	07/05→12/10		
2.2 DGi VAN (M75)	110 kW	2.2 l	07/05→12/11		
1.7 CDTI VAN (M75)	81 kW	1.7 l	01/08→04/15	; VIN 62034066, 6G019310 ->	KH30084 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
1.7 CDTI VAN (M75)	92 kW	1.7 l	01/08→04/15	; OE 16 03 254, 93178652	KH30046 ProKIT
				; OE 16 03 841, 93188477	KH30084 ProKIT
1.8 VAN (M75)	103 kW	1.8 l	07/05→04/15		KH30046 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTI VAN (M75)	110 kW	1.9 l	07/05→04/15		KH30074 ProKIT
OPEL - ZAFIRA C (P12)				10/11→	
1.4 (75)	88 kW	1.4 l	10/11→		KH30089 ProKIT
1.4 (75)	103 kW	1.4 l	10/11→		
1.4 LPG (75)	103 kW	1.4 l	10/11→	; -> 12/12; VIN -> C29999999	KH30134 ProKIT
1.6 CNG (75)	110 kW	1.6 l	10/11→		
1.8 (75)	85 kW	1.8 l	10/11→		
1.8 (75)	103 kW	1.8 l	10/11→		
2.0 CDTi (75)	81 kW	2 l	10/11→		
2.0 CDTi (75)	96 kW	2 l	10/11→		
2.0 CDTi (75)	121 kW	2 l	10/11→		
1.6 (75)	125 kW	1.6 l	12/12→		KH30089 ProKIT
1.6 CDTI (75)	88 kW	1.6 l	07/14→		
1.6 CDTI (75)	100 kW	1.6 l	02/13→		
2.0 BiTurbo CDTI (75)	143 kW	2 l	01/13→		



				     	
<b>PEUGEOT - 104 / 104 Coupe</b>				<b>10/72→06/88</b>	
0.9	33 kW	0.9 l	09/73→10/83	; 07/80 ->; VIN 5496582 ->	KH00094 ProKIT
0.9	33 kW	0.9 l	10/79→10/83	; 07/80 ->; VIN 7029645 ->	
1.1	42 kW	1.1 l	07/76→08/82		
1.1	42 kW	1.1 l	08/79→06/83	; VIN 5656287 ->	KH00091 ProKIT
1.2	42 kW	1.2 l	08/79→06/83	; VIN 7159482 ->	
1.4	53 kW	1.4 l	08/79→06/83		
1.4	53 kW	1.4 l	08/79→06/84		
0.9	34 kW	0.9 l	10/72→10/79	; VIN 5656287 ->	KH00091 ProKIT
				; VIN 7159482 ->	
1.0	32 kW	1 l	09/83→06/88	; VIN 5496582 ->	KH00094 ProKIT
1.1	37 kW	1.1 l	08/79→06/88	; VIN 7029645 ->	
1.1	37 kW	1.1 l	08/80→06/88	; VIN 5656287 ->	KH00091 ProKIT
				; VIN 7159482 ->	
1.1	48 kW	1.1 l	09/73→09/79	; VIN 5656287 ->	KH00091 ProKIT
1.1	48 kW	1.1 l	09/78→09/79	; VIN 7159482 ->	
1.1	49 kW	1.1 l	08/75→06/80	; VIN 7029645 ->	KH00094 ProKIT
				; VIN 5496582 ->	
<b>PEUGEOT - 106 I (1A, 1C)</b>				<b>08/91→04/96</b>	
1.0	33 kW	1 l	09/91→04/96		KH10051 ProKIT
				; Rim Hole Number: 3	KH10062 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT
1.0	37 kW	1 l	09/91→04/96		KH10051 ProKIT
1.3	72 kW	1.3 l	10/93→04/96		
1.4	51 kW	1.4 l	08/91→03/96	; Rim Hole Number: 4	KH10083 ProKIT
1.4	55 kW	1.4 l	09/91→04/96		
1.4	72 kW	1.4 l	08/91→03/96		
1.4 D	37 kW	1.4 l	09/92→04/96		
1.4 Le Mans	69 kW	1.4 l	09/91→11/94		
1.5 D	40 kW	1.5 l	06/94→04/96		
1.5 D	43 kW	1.5 l	06/94→04/96		
1.6	65 kW	1.6 l	06/93→04/96		
1.6	76 kW	1.6 l	11/94→04/96		
1.1	44 kW	1.1 l	09/91→04/96		KH10051 ProKIT
				; Rim Hole Number: 3	KH10062 ProKIT
				; Rim Hole Number: 3; ABS	KH10081 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT
Electric	20 kW		08/91→03/96		KH10051 ProKIT
<b>PEUGEOT - 106 II / 106 Van II Hatchback Van (1A_, 1C_, 1S_)</b>				<b>04/96→07/04</b>	
1.0	33 kW	1 l	04/96→03/01		KH10051 ProKIT
				; -> 01/99; Rim Hole Number: 3	KH10081 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT
1.0 i	33 kW	1 l	05/96→10/99	; 01/99 ->; Rim Hole Number: 4; ABS	KH10053 ProKIT
				; -> 01/99	KH10051 ProKIT
				; Rim Hole Number: 3	KH10062 ProKIT
				; 01/99 ->; Rim Hole Number: 4	KH10056 ProKIT
				; -> 01/99; Rim Hole Number: 3	KH10081 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT
1.0 i	37 kW	1 l	04/96→03/01	; 01/99 ->; Rim Hole Number: 4; ABS	KH10053 ProKIT
				; -> 01/99	KH10051 ProKIT
				; -> 12/00; Rim Hole Number: 3	KH10062 ProKIT
				; 01/99 ->; Rim Hole Number: 4	KH10056 ProKIT
				; -> 01/99; Rim Hole Number: 3	KH10081 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT
1.1 i	40 kW	1.1 l	01/97→03/01	; 01/99 ->; Rim Hole Number: 4; ABS	KH10053 ProKIT
				; -> 01/99	KH10051 ProKIT
				; -> 12/00; Rim Hole Number: 3; ABS	KH10062 ProKIT
				; 01/99 ->; Rim Hole Number: 4	KH10056 ProKIT
				; -> 01/99; Rim Hole Number: 3	KH10081 ProKIT
				; Rim Hole Number: 4	KH10083 ProKIT

				  	 	 13			
<b>PEUGEOT - 106 II / 106 Van II Hatchback Van (1A_, 1C_, 1S_)</b>								<b>04/96→07/04</b>	
1.1 i	44 kW	1.1 l	05/96→07/04		01/99 ->; Rim Hole Number: 4; ABS			KH10053 ProKIT	
					-> 01/99			KH10051 ProKIT	
					-> 12/00; Rim Hole Number: 3; 			KH10062 ProKIT	
					01/99 ->; Rim Hole Number: 4			KH10056 ProKIT	
					-> 01/99; Rim Hole Number: 3			KH10081 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.4 i	55 kW	1.4 l	05/96→07/04		01/99 ->; not for trim level: Level2S; ABS			KH10053 ProKIT	
					-> 01/99			KH10051 ProKIT	
					01/99 ->			KH10056 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.5 D	40 kW	1.5 l	05/96→03/01		01/99 ->; ABS			KH10053 ProKIT	
1.6 i	65 kW	1.6 l	05/96→10/99		-> 01/99			KH10051 ProKIT	
					01/99 ->			KH10056 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.5 D	42 kW	1.5 l	06/96→03/01					KH10056 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.5 D	42 kW	1.5 l	04/98→07/04		-> 01/99			KH10051 ProKIT	
								KH10056 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.6 i	74 kW	1.6 l	05/96→01/01		-> 01/99			KH10051 ProKIT	
					10/97 -> 04/98; ABS			KH20171 ProKIT	
					01/99 ->			KH10056 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.6 S16	87 kW	1.6 l	05/96→07/04		-> 01/99			KH10051 ProKIT	
					Rim Hole Number: 4			KH10083 ProKIT	
1.6 S16	88 kW	1.6 l	04/98→09/01		Rim Hole Number: 4			KH10083 ProKIT	
Electric	20 kW		04/96→03/01		ABS			KH10053 ProKIT	
Electric	20 kW		04/96→07/04		01/99 ->; Rim Hole Number: 4			KH10056 ProKIT	
<b>PEUGEOT - 107 (PM_, PN_)</b>								<b>06/05→05/14</b>	
1.0	50 kW	1 l	06/05→05/14					KH10106 ProKIT	
1.4 HDi	40 kW	1.4 l	06/05→05/14					KH30064 ProKIT	
<b>PEUGEOT - 108</b>								<b>05/14→</b>	
1.0 VTi	51 kW	1 l	05/14→					KH10106 ProKIT	
1.2	60 kW	1.2 l	05/14→					KH30064 ProKIT	
<b>PEUGEOT - 205 I / 205 I Convertible / 205 II / 205 Hatchback Van (741A/C, 741B, 20D, 20A/C)</b>								<b>02/83→09/98</b>	
1.0	32 kW	1 l	08/87→07/90		ABS			KH10052 ProKIT	
1.0	37 kW	1 l	08/92→05/97					KH10083 ProKIT	
1.1	40 kW	1.1 l	08/87→12/94						
1.1 XA	40 kW	1.1 l	07/87→10/88						
1.2	47 kW	1.2 l	01/87→12/90						
1.3	47 kW	1.3 l	02/84→10/87						
1.3	47 kW	1.3 l	08/90→07/92						
1.3 Rallye	74 kW	1.3 l	10/87→10/90						
1.4	41 kW	1.4 l	02/83→07/87						
1.4	50 kW	1.4 l	08/87→07/90						
1.4	50 kW	1.4 l	08/90→07/92						
1.4	53 kW	1.4 l	02/83→10/87						
1.4	53 kW	1.4 l	01/87→07/88						
1.4	63 kW	1.4 l	06/87→12/89						
1.5	63 kW	1.5 l	02/84→10/87						
1.6	85 kW	1.6 l	08/87→07/92						
1.6 Aut.	58 kW	1.6 l	10/87→09/98						
1.6 GTX	69 kW	1.6 l	01/87→10/91						
1.7 Diesel	44 kW	1.7 l	08/83→10/87						
1.7 Diesel	44 kW	1.7 l	07/87→09/98						
1.8 TD	57 kW	1.8 l	01/90→09/98						
1.9 Diesel	51 kW	1.9 l	08/87→06/94						
1.0	33 kW	1 l	02/83→10/87					KH10051 ProKIT	
1.0	33 kW	1 l	10/87→09/98		ABS			KH10052 ProKIT	
1.1	36 kW	1.1 l	02/83→07/87						
1.1	36 kW	1.1 l	02/83→10/87					KH10083 ProKIT	
1.1	36 kW	1.1 l	10/87→10/90						
1.1	37 kW	1.1 l	02/83→10/87						
1.1	40 kW	1.1 l	08/87→07/90						
1.1	40 kW	1.1 l	10/87→07/92						




















































































**PEUGEOT - 205 I / 205 I Convertible / 205 II / 205 Hatchback Van (741A/C, 741B, 20D, 20A/C) 02/83→09/98**

1.1	44 kW	1.1 l	07/89→09/98		KH10051 ProKIT
1.1 CJ	44 kW	1.1 l	10/89→12/94		KH10052 ProKIT
1.4	44 kW	1.4 l	02/83→07/87	ABS	KH10083 ProKIT
1.4	44 kW	1.4 l	02/83→10/87		KH10083 ProKIT
1.4	44 kW	1.4 l	10/87→05/89		
1.4	49 kW	1.4 l	10/87→10/90		
1.4	55 kW	1.4 l	07/88→09/98		
1.4	58 kW	1.4 l	10/85→10/87		
1.4	58 kW	1.4 l	07/88→05/89		
1.4	59 kW	1.4 l	02/83→10/87		
1.4	62 kW	1.4 l	06/87→12/89		
1.4 Cat	44 kW	1.4 l	08/87→09/93		
1.4 CJ	44 kW	1.4 l	03/88→05/89		
1.4 CJ	49 kW	1.4 l	03/89→12/94		
1.4 CJ	55 kW	1.4 l	05/91→12/94		
1.4 CJ Cat	44 kW	1.4 l	01/89→09/93		
1.4 CT	58 kW	1.4 l	04/86→12/88		
1.6	53 kW	1.6 l	03/87→10/87		
1.6	53 kW	1.6 l	10/87→09/98		
1.6	55 kW	1.6 l	08/86→10/87		
1.6	55 kW	1.6 l	10/87→09/98		
1.6	66 kW	1.6 l	08/90→07/92		
1.6 Aut.	65 kW	1.6 l	05/90→09/98		
1.6 CJ	65 kW	1.6 l	08/92→12/94		
1.6 CTI	76 kW	1.6 l	03/86→10/90		
1.7 Diesel	44 kW	1.7 l	03/94→05/97		
1.8 D	44 kW	1.8 l	02/83→07/90		
1.8 XDT	58 kW	1.8 l	08/90→05/97		
1.9 Diesel	47 kW	1.9 l	10/87→09/98		
1.1	44 kW	1.1 l	08/90→05/97		KH10083 ProKIT
1.4	62 kW	1.4 l	08/87→06/94		
1.6 GTI	76 kW	1.6 l	12/84→10/87		KH10051 ProKIT
1.6 GTI	76 kW	1.6 l	10/87→12/89	ABS	KH10052 ProKIT
1.6 GTI	85 kW	1.6 l	02/83→07/87	ABS	KH10083 ProKIT
1.6 GTI	77 kW	1.6 l	06/85→06/87	ABS	KH10083 ProKIT
1.6 GTI	85 kW	1.6 l	10/87→12/89	ABS	KH10052 ProKIT
				ABS	KH10083 ProKIT
1.8 Turbo 16	147 kW	1.8 l	10/84→02/86	ABS	KH10052 ProKIT
1.9 GTI	75 kW	1.9 l	03/87→10/87		
1.9 GTI	75 kW	1.9 l	10/87→05/89		
1.9 GTI Cat	75 kW	1.9 l	10/87→07/94		
1.9 CTi	74 kW	1.9 l	08/87→07/90		KH10051 ProKIT
1.9 CTI	75 kW	1.9 l	10/87→12/94	ABS	KH10052 ProKIT
1.9 GTI	88 kW	1.9 l	10/87→10/94		KH10052 ProKIT
1.9 GTI	94 kW	1.9 l	10/86→10/87		
1.9 GTI	94 kW	1.9 l	10/87→09/98		

**PEUGEOT - 206 CC / 206 Hatchback / 206 Saloon / 206 SW / 206 Van (2D, 2A/C, 2E/K) 08/98→12/12**

1.1	40 kW	1.1 l	08/98→07/00	ABS	KH10053 ProKIT
1.6 i	65 kW	1.6 l	09/98→12/00		KH10056 ProKIT
1.9 D	51 kW	1.9 l	09/98→11/01		
1.1	44 kW	1.1 l	07/02→02/07	ABS	KH10053 ProKIT
1.4	55 kW	1.4 l	07/02→02/07	11/02 ->	KH20100 ProKIT
				-> 09/02	KH20056 ProKIT
					KH10056 ProKIT
1.1 i	44 kW	1.1 l	09/98→02/07	ABS	KH10053 ProKIT
1.4 HDi	50 kW	1.4 l	09/01→03/09	11/02 ->	KH20100 ProKIT
1.4 HDi	50 kW	1.4 l	07/02→02/07		KH10056 ProKIT
1.4 HDi	51 kW	1.4 l	09/02→02/07		
1.4 HDi eco 70	50 kW	1.4 l	09/01→04/09		
1.4 i	55 kW	1.4 l	09/98→12/12		
1.9 D	51 kW	1.9 l	04/99→05/07		
1.4	55 kW	1.4 l	03/07→	ABS	KH10053 ProKIT
1.4 HDi eco 70	50 kW	1.4 l	09/08→		KH10056 ProKIT
1.4 LPG	55 kW	1.4 l	05/06→09/07		KH20100 ProKIT
1.4 16V	65 kW	1.4 l	10/03→	ABS	KH10053 ProKIT
1.4 16V	65 kW	1.4 l	10/03→02/08		KH10056 ProKIT
					KH20100 ProKIT

											
<b>PEUGEOT - 206 CC / 206 Hatchback / 206 Saloon / 206 SW / 206 Van (2D, 2A/C, 2E/K)</b>										<b>08/98→12/12</b>	
1.4 CNG	55 kW	1.4 l	05/06→09/07								KH10052 ProKIT
											KH10056 ProKIT
											KH20100 ProKIT
1.6	81 kW	1.6 l	09/01→12/08								KH20100 ProKIT
1.6	81 kW	1.6 l	05/05→07/08								KH20100 ProKIT
1.6 16V	79 kW	1.6 l	06/01→04/09								KH10052 ProKIT
1.6 LPG	80 kW	1.6 l	07/02→02/07								KH20100 ProKIT
1.6 16V	80 kW	1.6 l	07/00→04/09								KH10052 ProKIT
1.6 16V	80 kW	1.6 l	07/02→								KH20100 ProKIT
1.6 16V (2DNFUF, 2DNFUR)	80 kW	1.6 l	09/00→12/07								KH20056 ProKIT
2.0 16V	100 kW	2 l	07/02→02/07								KH20056 ProKIT
2.0 S16	100 kW	2 l	06/99→12/07								
2.0 S16	100 kW	2 l	09/00→12/07								
1.6 16V	80 kW	1.6 l	03/07→								KH10052 ProKIT
1.6 HDi 110	80 kW	1.6 l	05/04→								KH20100 ProKIT
1.6 HDi 110	80 kW	1.6 l	05/04→02/07								
1.6 HDi 110	80 kW	1.6 l	04/05→02/07								
2.0 RC	130 kW	2 l	07/03→12/07								
2.0 HDi	66 kW	2 l	07/02→02/07								KH10052 ProKIT
											KH20100 ProKIT
											KH20056 ProKIT
											KH10056 ProKIT
2.0 HDi 90	66 kW	2 l	12/99→09/09								KH10052 ProKIT
											KH20100 ProKIT
											KH10056 ProKIT
2.0 S16	99 kW	2 l	04/99→10/00								KH10052 ProKIT
											KH20056 ProKIT
<b>PEUGEOT - 206+ (2L_, 2M_)</b>										<b>01/09→08/13</b>	
1.4 HDi eco 70	50 kW	1.4 l	01/09→06/13								KH10053 ProKIT
1.4 i (2LKFWA, 2MKFWA)	55 kW	1.4 l	01/09→08/13								KH10056 ProKIT
1.4 i	54 kW	1.4 l	09/10→06/13								KH10056 ProKIT
<b>PEUGEOT - 207 / 207 CC / 207 Hatchback Van / 207 Saloon / 207 SW Estate Van / 207 SW Wagon (WA_, WC_, WD_, WK_)</b>										<b>02/06→12/15</b>	
1.4	53 kW	1.4 l	02/06→10/13								KH10054 ProKIT
1.4	54 kW	1.4 l	04/06→10/13								KH10048 ProKIT
1.4	54 kW	1.4 l	06/07→10/08								
1.4	54 kW	1.4 l	06/07→12/12								
1.4	54 kW	1.4 l	12/07→12/12								
1.4	55 kW	1.4 l	08/08→12/15								
1.4 16V	65 kW	1.4 l	02/06→10/13								
1.4	55 kW	1.4 l	01/11→12/12								KH10054 ProKIT
1.4 BiFuel	54 kW	1.4 l	08/07→12/13								
1.4 LPG	54 kW	1.4 l	08/07→12/12								
1.4 16V	70 kW	1.4 l	06/07→10/13								KH10047 ProKIT
1.4 16V	72 kW	1.4 l	10/09→12/12								KH10054 ProKIT
1.4 16V	72 kW	1.4 l	11/09→12/12								KH10054 ProKIT
1.4 HDi	50 kW	1.4 l	02/06→12/15								KH10048 ProKIT
1.4 HDi	50 kW	1.4 l	04/07→								
1.4 Bioflex	60 kW	1.4 l	08/08→12/14								KH10048 ProKIT
1.4 Flex	60 kW	1.4 l	11/08→12/14								
1.4 HDi	52 kW	1.4 l	02/11→12/15								KH10047 ProKIT
											KH10054 ProKIT
1.6	81 kW	1.6 l	08/08→12/12								KH10047 ProKIT
1.6	81 kW	1.6 l	08/08→12/13								
1.6	81 kW	1.6 l	09/09→10/13								
1.6 16V	79 kW	1.6 l	08/08→12/13								
1.6 16V	80 kW	1.6 l	11/08→10/13								
1.6 16V VTI	81 kW	1.6 l	09/08→12/12								
1.6 Flex	83 kW	1.6 l	08/08→12/13								
1.6 HDi	66 kW	1.6 l	08/07→12/12								
1.6 HDi	68 kW	1.6 l	11/09→03/13								
1.6 HDi	80 kW	1.6 l	04/06→12/12								
1.6 HDi	80 kW	1.6 l	08/07→12/12								
1.6 VTI	88 kW	1.6 l	03/07→12/12								
1.6 16V	80 kW	1.6 l	02/06→10/13								KH10047 ProKIT
1.6 16V	88 kW	1.6 l	02/07→10/13								KH10048 ProKIT
1.6 16V	88 kW	1.6 l	06/07→10/13								



**PEUGEOT - 207 / 207 CC / 207 Hatchback Van / 207 Saloon / 207 SW Estate 02/06→12/15**  
**Van / 207 SW Wagon (WA\_, WC\_, WD\_, WK\_)**

1.6 16V RC	128 kW	1.6 l	02/07→12/12	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 16V Turbo	110 kW	1.6 l	02/06→10/13		
1.6 16V Turbo	110 kW	1.6 l	02/07→12/12		KH10048 ProKIT
1.6 16V Turbo	115 kW	1.6 l	10/09→12/12		
1.6 16V Turbo	115 kW	1.6 l	10/09→12/13		
1.6 16V VTi	88 kW	1.6 l	02/07→12/12		
1.6 Bioflex	83 kW	1.6 l	01/08→12/13		
1.6 HDi	66 kW	1.6 l	02/06→10/13		
1.6 HDi	66 kW	1.6 l	04/07→10/12		
1.6 HDi	66 kW	1.6 l	06/07→12/12		
1.6 HDi	68 kW	1.6 l	11/09→12/12		
1.6 HDi	68 kW	1.6 l	11/09→12/13		
1.6 HDi	80 kW	1.6 l	02/06→10/13		
1.6 HDi	80 kW	1.6 l	02/07→01/15		
1.6 HDi	80 kW	1.6 l	06/07→12/12		
1.6 HDi	82 kW	1.6 l	08/09→10/13		
1.6 HDi 110	82 kW	1.6 l	08/09→12/12		

**PEUGEOT - 208 I / 208 Hatchback Van (CA\_, CC\_, CR\_) 03/12→**

1.0	50 kW	1 l	03/12→	; -> 06/15;	KH10086 ProKIT
1.2 THP 110	81 kW	1.2 l	01/13→	; 06/15 ->; ; Brake diameter, outer [mm]: 203	
1.2 VTi 82	60 kW	1.2 l	03/12→		KH10048 ProKIT
1.4 GPL	70 kW	1.4 l	10/13→		
1.4 HDi	50 kW	1.4 l	03/12→	; ; $\varnothing$ 9 Inch;	
1.4 HDi 68 (CR8HR0)	50 kW	1.4 l	10/12→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.4 VTi	70 kW	1.4 l	03/12→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.6	88 kW	1.6 l	03/12→		
1.6	115 kW	1.6 l	03/12→		
1.6 BlueHdi 100	73 kW	1.6 l	01/15→		
1.6 BlueHdi 120	88 kW	1.6 l	11/13→		
1.6 BlueHdi 75	55 kW	1.6 l	04/15→		
1.6 GTi	147 kW	1.6 l	08/12→		
1.6 GTi	153 kW	1.6 l	10/14→		
1.6 HDi	68 kW	1.6 l	03/12→		
1.6 HDi	84 kW	1.6 l	03/12→		
1.6 HDi	85 kW	1.6 l	04/14→		
1.6 HDi / BlueHdi 75	55 kW	1.6 l	01/13→		
1.6 HDi 92	68 kW	1.6 l	03/14→		
1.6 THP 165	121 kW	1.6 l	03/15→		
1.2 Flex	66 kW	1.2 l	02/16→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.2 PureTech 82	61 kW	1.2 l	03/18→		
1.2 VTi 68 / PureTech 68 (CRHMP6, CRHMM6)	50 kW	1.2 l	06/15→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.2 VTi 82 / PureTech 82 (CRHMZ6, CRHMRP)	60 kW	1.2 l	06/15→		
1.5	66 kW	1.5 l	06/13→		
1.5 BlueHdi 100	75 kW	1.5 l	05/18→		
1.5 BlueHdi 100	75 kW	1.5 l	05/18→		
1.5 Flex	68 kW	1.5 l	01/13→12/16		
1.6	85 kW	1.6 l	06/13→		
1.6 Blue HDi 100	73 kW	1.6 l	06/15→		
1.6 e-HDi	82 kW	1.6 l	07/15→		
1.6 Flex	87 kW	1.6 l	10/17→		
1.6 Flex	90 kW	1.6 l	07/13→10/17		
1.6 GT Turbo Flex	127 kW	1.6 l	02/16→		
1.2 GPL	60 kW	1.2 l	06/15→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.2 VTi 68 / PureTech 68	50 kW	1.2 l	08/16→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
				; ; Brake diameter, outer [mm]: 203	KH10086 ProKIT









































































































**PEUGEOT - 301 11/12→**

1.2 PureTech 82	61 kW	1.2 l	02/18→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.5 BlueHdi 100	75 kW	1.5 l	05/18→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.6 LPG	85 kW	1.6 l	07/14→		
1.2 VTi 72	53 kW	1.2 l	11/12→	; -> 02/17;	KH10086 ProKIT
1.2 VTi 82	60 kW	1.2 l	12/14→	; 02/17 ->; ; Brake diameter, outer [mm]: 203	
1.6 BlueHdi 100	73 kW	1.6 l	04/14→	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 HDi 90	68 kW	1.6 l	11/12→		
1.6 VTi 115	85 kW	1.6 l	11/12→10/17	; Outer diameter 1 [mm]: 72	KH10054 ProKIT






































































































**PEUGEOT - 305 II / 305 II Break (581M, 581E) 10/82→12/88**

1.3	44 kW	1.3 l	10/82→08/85		KH20046 ProKIT
1.3	44 kW	1.3 l	10/82→08/86		
1.5	50 kW	1.5 l	09/85→10/86		
1.5	54 kW	1.5 l	10/82→08/85		
1.5	54 kW	1.5 l	10/82→08/86		
1.6	54 kW	1.6 l	11/86→12/88		
1.6	55 kW	1.6 l	02/86→12/88		



     					
<b>PEUGEOT - 305 II / 305 II Break (581M, 581E)</b>				<b>10/82→12/88</b>	
1.6	66 kW	1.6 l	07/84→08/87		KH20046 ProKIT
1.6	66 kW	1.6 l	07/84→12/87		
1.6	71 kW	1.6 l	09/83→06/84		
1.9	72 kW	1.9 l	11/86→12/88		
1.9	75 kW	1.9 l	10/82→08/85		
1.9	75 kW	1.9 l	09/84→10/87		
1.9 D	48 kW	1.9 l	10/82→07/88		
1.9 Diesel	47 kW	1.9 l	10/82→12/88		
1.9 Diesel	48 kW	1.9 l	10/82→12/88		
1.6	54 kW	1.6 l	11/86→12/88	 ; -> 02/88	KH20046 ProKIT
1.6	55 kW	1.6 l	10/82→07/88		
1.6	69 kW	1.6 l	10/82→06/88		
1.9	72 kW	1.9 l	11/86→12/88		
<b>PEUGEOT - 306 Break (7E, N3, N5)</b>				<b>07/95→04/02</b>	
1.4	55 kW	1.4 l	03/97→04/02	 ; 10/97 -> 01/99	KH20171 ProKIT
				 ; 04/98 ->; 	KH20035 ProKIT
				 ; -> 09/98; Code: N5; 	KH20048 ProKIT
1.6	65 kW	1.6 l	03/97→10/00	 ; 10/97 ->	KH20171 ProKIT
1.8 16V	81 kW	1.8 l	03/97→04/02	 ; 04/98 ->; 	KH20035 ProKIT
				 ; -> 09/98; Code: N5; 	KH20048 ProKIT
1.6	72 kW	1.6 l	10/00→04/02	 ; not for code: N5; Number of Doors: 3; 	KH10052 ProKIT
				 ; Code: N5; Number of Doors: 3;  ; 	KH10053 ProKIT
				 ; 	KH20035 ProKIT
1.8	74 kW	1.8 l	03/97→04/02	 ; 04/98 ->; 	KH20035 ProKIT
1.9 D	50 kW	1.9 l	03/97→04/02	 ; -> 09/98; Code: N5; 	KH20048 ProKIT
1.9 D	55 kW	1.9 l	03/98→04/02		
2.0	97 kW	2 l	03/97→04/02		
1.8 16V	82 kW	1.8 l	03/97→07/01	 ; 04/98 ->; 	KH20035 ProKIT
1.9 D	51 kW	1.9 l	05/97→05/99		
1.9 Td	52 kW	1.9 l	07/95→08/00		
2.0 16V	99 kW	2 l	03/97→04/02		
1.9 D	51 kW	1.9 l	09/98→04/02		KH10052 ProKIT
				 ; 07/99 ->	KH20171 ProKIT
				 ; 	KH20035 ProKIT
1.9 TD	66 kW	1.9 l	02/97→04/02	 ; 10/97 -> 05/99	KH20171 ProKIT
				 ; 04/98 ->; 	KH20035 ProKIT
				 ; -> 09/98; Code: N5; 	KH20048 ProKIT
2.0 HDI 90	66 kW	2 l	06/99→04/02		KH10052 ProKIT
				 ; 	KH20035 ProKIT
<b>PEUGEOT - 306 Convertible (7D, N3, N5)</b>				<b>01/94→04/02</b>	
1.6	65 kW	1.6 l	04/96→10/00	 ; -> 05/97;  ; 	KH10083 ProKIT
2.0 16V	97 kW	2 l	03/97→04/02	 ; 05/97 -> 09/98;  ;  ; 	
2.0 16V	99 kW	2 l	03/97→04/02	 ; 04/98 ->; 	KH20035 ProKIT
1.6	72 kW	1.6 l	10/00→04/02	 ; not for code: N5; Number of Doors: 3; 	KH10052 ProKIT
				 ; Code: N5; Number of Doors: 3;  ; 	KH10053 ProKIT
					KH10056 ProKIT
				 ; 	KH20035 ProKIT
1.8	74 kW	1.8 l	03/94→04/02	 ; -> 05/97;  ; 	KH10083 ProKIT
				 ; 05/97 -> 09/98;  ;  ; 	
				 ; 04/98 ->; 	KH20035 ProKIT
				 ; -> 06/95; Code: N3;	KH20048 ProKIT
				Manufacturer Restriction: BOSCH;  ;  ; 	
1.8	74 kW	1.8 l	05/97→04/99	 ; 04/98 ->; 	KH20035 ProKIT
				 ;  ;  ; 	KH10083 ProKIT
1.8 16V	81 kW	1.8 l	05/97→04/02		KH10052 ProKIT
					KH10056 ProKIT
				 ; 	KH20035 ProKIT
2.0	89 kW	2 l	03/94→04/02	 ; -> 05/97;  ; 	KH10083 ProKIT
				 ; 05/97 -> 09/98;  ;  ; 	
				 ; 05/94 -> 06/97	KH20171 ProKIT
				 ; 04/98 ->; 	KH20035 ProKIT
				 ; -> 06/95; Code: N3;	KH20048 ProKIT
				Manufacturer Restriction: BOSCH;  ;  ; 	
2.0	90 kW	2 l	02/95→11/97	 ; -> 05/97;  ; 	KH10083 ProKIT
2.0	92 kW	2 l	01/94→06/97	 ; 05/97 ->;  ;  ; 	



											
<b>PEUGEOT - 306 Estate Van (N_, 7_)</b>										<b>02/94→08/02</b>	
1.4	55 kW	1.4 l	03/96→07/01		04/98 ->					KH20035 ProKIT	
1.9 D	68 kW	1.9 l	02/94→04/99								
1.9 STD	51 kW	1.9 l	02/94→05/99								
1.9 D	51 kW	1.9 l	02/99→08/02							KH20035 ProKIT	
<b>PEUGEOT - 306 Hatchback / 306 Hatchback Van / 306 Sedan (7A, 7C, N3, N5, 7B, N3, N5)</b>										<b>01/93→10/03</b>	
1.1	44 kW	1.1 l	05/93→05/01		-> 06/95; Code: N3;					KH20048 ProKIT	
1.4	55 kW	1.4 l	04/93→07/01	<b>Manufacturer Restriction: BOSCH; ; ; *</b>							
1.4 SL	55 kW	1.4 l	06/94→05/01		-> 09/98; Code: N3, ENTERPRISE						
1.6	65 kW	1.6 l	05/93→10/00		01/97 -> 09/98; Code: N5, ENTERPRISE						
1.8	74 kW	1.8 l	05/93→05/01		-> 05/97;  ; 					KH10083 ProKIT	
1.8 ST	74 kW	1.8 l	06/94→05/01		05/97 -> 09/98;  ;  ; 					KH20035 ProKIT	
2.0 S16	110 kW	2 l	06/94→05/01		04/98 ->						
2.0 S16	112 kW	2 l	05/93→05/01								
2.0 S16	112 kW	2 l	06/94→05/01								
2.0 ST	89 kW	2 l	07/94→05/01								
2.0 XSi	89 kW	2 l	05/93→05/01								
1.1	44 kW	1.1 l	07/93→12/94		 ; 					KH10083 ProKIT	
1.4	48 kW	1.4 l	04/93→10/94								
1.9 STD	51 kW	1.9 l	02/94→10/95								
1.1	44 kW	1.1 l	06/94→05/01		-> 06/95; Code: N3;					KH20048 ProKIT	
<b>Manufacturer Restriction: BOSCH; ; ; *</b>											
<b>-&gt; 09/98; Code: N3, ENTERPRISE</b>											
<b>01/97 -&gt; 09/98; Code: N5, ENTERPRISE</b>											
<b>-&gt; 05/97; ; </b>											
<b>05/97 -&gt; 09/98; ; ; </b>											
<b>01/99 -&gt; </b>											
<b>-&gt; 01/99</b>											
<b></b>											
<b>04/98 -&gt;</b> 											
<b></b>											
1.4	55 kW	1.4 l	03/96→07/01		-> 05/97;  ; 					KH10083 ProKIT	
1.8 16V	82 kW	1.8 l	03/97→07/01		05/97 -> 09/98;  ;  ; 						
1.8 16V	82 kW	1.8 l	03/97→10/03		04/98 ->					KH20035 ProKIT	
2.0 16V	99 kW	2 l	03/97→06/00								
1.6	66 kW	1.6 l	07/00→05/01							KH10056 ProKIT	
1.9 D	52 kW	1.9 l	01/99→08/03							KH20035 ProKIT	
1.6	66 kW	1.6 l	07/00→05/01							KH10056 ProKIT	
<b>; ; ; </b>											
<b></b>											
<b>; ; </b>											
1.6	72 kW	1.6 l	10/00→05/01		not for code: N5; Number of Doors: 3; 					KH10052 ProKIT	
<b>; Code: N5; Number of Doors: 3; ; </b>											
<b></b>											
<b></b>											
1.6 SR	65 kW	1.6 l	06/94→10/00		-> 05/97;  ; 					KH10083 ProKIT	
2.0 S16	110 kW	2 l	06/94→05/01		05/97 -> 09/98;  ;  ; 						
<b>-&gt; 06/95; Code: N3;</b>											
<b>Manufacturer Restriction: BOSCH; ; ; *</b>											
<b>-&gt; 09/98; Code: N3, ENTERPRISE</b>											
<b>04/98 -&gt;</b> 											
1.8	74 kW	1.8 l	06/94→05/01		-> 05/97;  ; 					KH10083 ProKIT	
<b>05/97 -&gt; 09/98; ; ; </b>											
1.8 16V	81 kW	1.8 l	03/97→05/01		-> 05/97;  ; 					KH10083 ProKIT	
2.0	97 kW	2 l	03/97→05/01		05/97 -> 09/98;  ;  ; 						
2.0 16V	97 kW	2 l	03/97→05/01		04/98 ->					KH20035 ProKIT	
<b>-&gt; 09/98; Code: N5, ENTERPRISE</b>											
1.8 D	43 kW	1.8 l	05/93→05/01		04/98 ->					KH20035 ProKIT	
<b>-&gt; 05/97; ; </b>											
<b>-&gt; 09/98; Code: N5, ENTERPRISE</b>											
1.8 D	44 kW	1.8 l	04/93→05/99		04/98 ->					KH20035 ProKIT	
1.9 D	51 kW	1.9 l	04/93→05/99		-> 05/97;  ; 					KH10083 ProKIT	
1.9 Td	52 kW	1.9 l	07/95→08/00								



**PEUGEOT - 306 Hatchback / 306 Hatchback Van / 306 Sedan (7A, 7C, N3, N5, 7B, N3, N5)** 01/93→10/03

1.9 D	47 kW	1.9 l	05/93→05/01	-> 06/95; Code: N3;	KH20048 ProKIT
1.9 D	50 kW	1.9 l	06/94→05/01	<b>Manufacturer Restriction: BOSCH;</b> ; ;	
1.9 DT	66 kW	1.9 l	05/93→05/01	-> 09/98; Code: N3, ENTERPRISE	
1.9 SLD	47 kW	1.9 l	06/94→05/01	; 01/97 -> 09/98; Code: N5, ENTERPRISE	
1.9 SLD	50 kW	1.9 l	06/94→05/01	; 04/98 ->;	KH20035 ProKIT
1.9 SRDT	66 kW	1.9 l	06/94→05/01	-> 05/97; ;	KH10083 ProKIT
1.9 D	50 kW	1.9 l	05/97→05/99	; 04/98 ->;	KH20035 ProKIT
1.9 D	51 kW	1.9 l	09/98→05/01		KH10052 ProKIT
2.0 HDI 90	66 kW	2 l	06/99→12/01		KH10056 ProKIT
2.0 HDI 90	66 kW	2 l	06/99→12/02	;	KH20035 ProKIT
1.9 D	51 kW	1.9 l	09/98→05/01		KH10052 ProKIT
				-> 09/98; Code: N5, ENTERPRISE	KH20048 ProKIT
					KH10056 ProKIT
				;	KH20035 ProKIT
1.9 D	51 kW	1.9 l	02/99→08/01	;	KH20035 ProKIT
1.9 D	55 kW	1.9 l	03/98→05/01	; 04/98 ->;	KH20035 ProKIT
				-> 09/98; Code: N5, ENTERPRISE	KH20048 ProKIT
1.9 D	68 kW	1.9 l	01/93→12/97	-> 05/97; ;	KH10083 ProKIT
1.9 D	68 kW	1.9 l	02/94→12/97		
2.0	92 kW	2 l	11/95→06/97	-> 05/97; ;	KH10083 ProKIT
				; 05/97 ->; ; ;	
2.0 S16	120 kW	2 l	06/96→05/01	-> 09/98; Code: N3, ENTERPRISE	KH20048 ProKIT
				; 01/97 -> 09/98; Code: N5, ENTERPRISE	
				-> 05/97; ;	KH10083 ProKIT
				; 05/97 -> 09/98; ; ;	
				; 04/98 ->;	KH20035 ProKIT

**PEUGEOT - 307 / 307 Break / 307 CC / 307 SW (3A/C, 3E, 3B, 3H)** 08/00→04/12

1.4	55 kW	1.4 l	08/00→09/03	-> Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.4	55 kW	1.4 l	04/02→09/03		
1.4 HDi	50 kW	1.4 l	10/01→06/05		KH10079 ProKIT
1.4 HDi	50 kW	1.4 l	03/02→06/05		
2.0	100 kW	2 l	03/02→06/05		
2.0 16V	100 kW	2 l	08/00→06/05		
2.0 16V	100 kW	2 l	03/02→06/05		
2.0 16V	100 kW	2 l	10/03→06/05		
1.4 16V	65 kW	1.4 l	11/03→07/07	-> Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6	81 kW	1.6 l	07/06→04/12	; 09/06 ->;	KH10048 ProKIT
1.4 16V	65 kW	1.4 l	11/03→07/07	-> Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 16V	80 kW	1.6 l	08/00→11/07		
1.6 16V	80 kW	1.6 l	03/02→04/08	; 09/06 ->;	KH10048 ProKIT
1.6 16V	80 kW	1.6 l	03/03→04/09	-> 09/06	KH10079 ProKIT
1.6 HDi	66 kW	1.6 l	04/05→04/08		
1.6 HDi	66 kW	1.6 l	04/05→03/09		
1.6 HDi 110	80 kW	1.6 l	02/04→04/08		
1.6 HDi 110	80 kW	1.6 l	02/04→03/09		
1.6 HDi 110	80 kW	1.6 l	11/03→12/07		
2.0 16V	103 kW	2 l	12/04→04/09		
2.0 16V	103 kW	2 l	03/05→11/07		
2.0 16V	103 kW	2 l	03/05→04/08		
2.0 16V	130 kW	2 l	10/03→04/09		
2.0 16V	130 kW	2 l	06/05→04/08		
2.0 HDi 110	79 kW	2 l	08/00→03/07		
2.0 HDi 110	79 kW	2 l	03/02→12/09		
2.0 HDi 135	100 kW	2 l	10/03→11/07		
2.0 HDi 135	100 kW	2 l	02/04→04/08		
2.0 HDi 135	100 kW	2 l	06/05→04/09		
2.0 HDi 90	66 kW	2 l	08/00→03/07		
2.0 HDi 90	66 kW	2 l	03/02→04/08		
1.6 BioFlex	80 kW	1.6 l	09/07→04/08	-> Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 BioFlex	80 kW	1.6 l	09/07→04/09	;	KH10048 ProKIT
1.6 HDi 90	66 kW	1.6 l	04/05→04/08		
2.0	105 kW	2 l	08/08→12/11		
2.0 16V	130 kW	2 l	06/05→11/07	-> Outer diameter 1 [mm]: 82	KH10047 ProKIT
				-> 09/06	KH10079 ProKIT
				;	KH10048 ProKIT

**PEUGEOT - 308 I (4A\_, 4C\_)** 09/07→12/15

1.4 16V	70 kW	1.4 l	09/07→10/14	;	KH10047 ProKIT
---------	-------	-------	-------------	---	----------------



**PEUGEOT - 308 I (4A\_, 4C\_)**

**09/07→12/15**

1.4 16V	72 kW	1.4 l	12/09→10/14		KH10040 ProKIT
1.6	120 kW	1.6 l	01/12→12/15		
1.6 16V	88 kW	1.6 l	09/07→10/14		
1.6 16V	103 kW	1.6 l	09/07→10/14		
1.6 16V	110 kW	1.6 l	09/07→10/14		
1.6 16V	128 kW	1.6 l	03/08→10/14		
1.6 BioFlex	80 kW	1.6 l	04/08→10/14		
1.6 HDi	66 kW	1.6 l	09/07→10/14		
1.6 HDi	68 kW	1.6 l	11/09→10/14		
1.6 HDi	80 kW	1.6 l	09/07→10/14		
1.6 HDi	82 kW	1.6 l	12/09→10/14		
1.6 HDi	84 kW	1.6 l	03/13→10/14		
1.6 THP 16V	115 kW	1.6 l	10/09→10/14		
2.0 Bioflex	103 kW	2 l	01/08→12/12		
2.0 HDi	100 kW	2 l	09/07→10/14		
2.0 HDi	103 kW	2 l	07/10→12/12		
2.0 HDi	110 kW	2 l	10/11→10/14		
2.0 HDi	120 kW	2 l	04/12→10/14		
1.6 GTi	147 kW	1.6 l	07/10→10/14		KH10006 ProKIT
					KH20138 ProKIT

**PEUGEOT - 308 II (LB\_, LP\_, LW\_, LH\_, L3\_)**

**09/13→06/21**

1.2 THP 110	81 kW	1.2 l	11/13→06/21		KH10027 ProKIT
1.2 THP 130	96 kW	1.2 l	11/13→06/21		
1.2 VTI 72	60 kW	1.2 l	09/13→06/21		KH30112 ProKIT
1.6 BlueHDi 120	88 kW	1.6 l	11/13→06/21		
1.6 GT 205	151 kW	1.6 l	06/14→06/21		
1.6 GTi	184 kW	1.6 l	08/15→06/21		
1.6 GTi (L35GNH)	200 kW	1.6 l	06/15→06/21		
1.6 HDi	68 kW	1.6 l	09/13→06/21		
1.6 HDi / BlueHDi 115	85 kW	1.6 l	09/13→06/21		
1.6 HDi 100	73 kW	1.6 l	04/14→06/21		
1.6 THP	115 kW	1.6 l	09/13→06/21		
1.6 THP 125	92 kW	1.6 l	09/13→06/21		
2.0 BlueHDi 150	110 kW	2 l	11/13→06/21		
2.0 GT BlueHDi 180	133 kW	2 l	06/14→06/21		
1.6 THP	112 kW	1.6 l	09/13→06/21		KH10027 ProKIT
1.6 THP 150	110 kW	1.6 l	03/14→06/21		
1.6 THP 163	120 kW	1.6 l	06/14→06/21		

**PEUGEOT - 308 CC (4B\_)**



































**02/09→12/15**

1.6	121 kW	1.6 l	10/12→12/15		KH10047 ProKIT
1.6	129 kW	1.6 l	07/09→12/14		
1.6 HDi	82 kW	1.6 l	02/09→05/12		
1.6 THP	120 kW	1.6 l	08/12→12/14		
1.6 16V	88 kW	1.6 l	06/09→12/14		KH10047 ProKIT
1.6 16V	103 kW	1.6 l	06/09→12/14		KH10040 ProKIT
1.6 16V	110 kW	1.6 l	06/09→12/14		
1.6 16V	115 kW	1.6 l	06/09→12/14		
1.6 HDi	82 kW	1.6 l	06/09→12/14		
1.6 HDi	84 kW	1.6 l	03/13→12/14		
2.0 CVVT	103 kW	2 l	07/09→12/14		
2.0 HDi	100 kW	2 l	04/09→12/14		
2.0 HDi	103 kW	2 l	04/09→12/12		
2.0 HDi	120 kW	2 l	06/09→12/14		
1.6 THP	147 kW	1.6 l	10/10→12/14		KH10006 ProKIT
					KH10047 ProKIT

**PEUGEOT - 308 SW I Wagon (4E\_, 4H\_)**

**09/07→10/14**

1.4 16V	70 kW	1.4 l	09/07→10/14		KH10047 ProKIT
1.4 16V	72 kW	1.4 l	12/09→10/14		KH10040 ProKIT
1.6 16V	88 kW	1.6 l	09/07→10/14		
1.6 16V	103 kW	1.6 l	09/07→10/14		
1.6 16V	110 kW	1.6 l	09/07→10/14		
1.6 16V	128 kW	1.6 l	03/08→10/14		
1.6 Bioflex	82 kW	1.6 l	03/09→10/14		
1.6 HDi	66 kW	1.6 l	09/07→10/14		
1.6 HDi	68 kW	1.6 l	11/09→10/14		
1.6 HDi	80 kW	1.6 l	09/07→10/14		
1.6 HDi	82 kW	1.6 l	12/09→10/14		
1.6 HDi	84 kW	1.6 l	03/13→10/14		
1.6 THP 16V	115 kW	1.6 l	10/09→10/14		
2.0 Bioflex	103 kW	2 l	01/08→12/11		
2.0 HDi	100 kW	2 l	09/07→12/12		
2.0 HDi	103 kW	2 l	09/07→10/14		
2.0 HDi	110 kW	2 l	04/11→10/14		
2.0 HDi	120 kW	2 l	06/09→10/14		





























































											
<b>PEUGEOT - 308 SW II (LC_, LJ_, LR_, LX_, L4_)</b>										<b>03/14→06/21</b>	
1.2 THP 110	81 kW	1.2 l	03/14→06/21								<b>KH10027 ProKIT</b>
1.2 THP 130	96 kW	1.2 l	03/14→06/21								<b>KH30112 ProKIT</b>
1.6 BlueHdI 100	73 kW	1.6 l	04/14→06/21								
1.6 BlueHdI 120	88 kW	1.6 l	03/14→06/21								
1.6 GT 205	151 kW	1.6 l	02/15→06/21								
1.6 HDi / BlueHdI 115 (LCBHXM, LCBHXT)	85 kW	1.6 l	03/14→06/21								
1.6 HDi 92	68 kW	1.6 l	03/14→06/21								
1.6 THP 155	115 kW	1.6 l	03/14→06/21								
2.0 BlueHdI 150	110 kW	2 l	03/14→06/21								
2.0 GT HDi 180 / BlueHdI 180	133 kW	2 l	06/14→06/21								
<b>PEUGEOT - 309 I / 309 II (10C, 10A, 3C, 3A)</b>										<b>10/85→12/93</b>	
1.1	40 kW	1.1 l	10/85→07/89								<b>KH10083 ProKIT</b>
1.1	40 kW	1.1 l	09/89→10/93								
1.3	47 kW	1.3 l	10/85→07/89								
1.4	48 kW	1.4 l	10/85→08/88								
1.4	61 kW	1.4 l	10/85→08/89								
1.5	63 kW	1.5 l	06/87→12/89								
1.6	59 kW	1.6 l	10/85→07/89								
1.6	74 kW	1.6 l	09/89→10/93								
1.6 Cat	55 kW	1.6 l	09/86→12/89								
1.6 GTi	85 kW	1.6 l	09/89→10/93								
1.8 TD	57 kW	1.8 l	08/89→12/93								
1.9 D	50 kW	1.9 l	09/89→10/93								
1.9 GTI	96 kW	1.9 l	10/85→08/89								
1.9 GTI	96 kW	1.9 l	09/89→10/93								
1.1	44 kW	1.1 l	08/90→12/93								<b>KH10051 ProKIT</b>
1.4	49 kW	1.4 l	07/90→12/93								<b>KH10083 ProKIT</b>
1.4	49 kW	1.4 l	03/89→07/89								<b>KH10052 ProKIT</b>
1.4	55 kW	1.4 l	03/89→07/89								<b>KH10083 ProKIT</b>
1.4	62 kW	1.4 l	08/88→08/89								
1.6	53 kW	1.6 l	08/87→07/89								
1.6	55 kW	1.6 l	10/85→07/89								
1.6	65 kW	1.6 l	07/89→12/93								
1.6	68 kW	1.6 l	07/89→12/93								
1.6	69 kW	1.6 l	01/86→07/89								
1.6	69 kW	1.6 l	07/89→12/93								
1.6	76 kW	1.6 l	11/85→09/88								
1.6	83 kW	1.6 l	07/86→06/89								
1.8 Diesel	44 kW	1.8 l	07/89→12/93								
1.9	72 kW	1.9 l	03/86→07/89								
1.9	72 kW	1.9 l	08/89→12/93								
1.9	75 kW	1.9 l	10/85→07/89								
1.9	80 kW	1.9 l	07/88→07/89								
1.9	80 kW	1.9 l	10/90→12/93								
1.9 D	47 kW	1.9 l	06/86→07/89								
1.9 Diesel	47 kW	1.9 l	07/89→12/93								
1.9 GTI	88 kW	1.9 l	07/88→07/89								
1.9 GTI	88 kW	1.9 l	07/89→12/93								
1.9 GTI	94 kW	1.9 l	10/86→07/89								
1.9 GTI 16V	108 kW	1.9 l	10/90→12/93								
1.9 GTI 16V	116 kW	1.9 l	08/89→07/90								
1.4	55 kW	1.4 l	07/89→12/93		<b>01/90 -&gt;</b>						<b>KH10051 ProKIT</b>
											<b>KH10083 ProKIT</b>
<b>PEUGEOT - 405 I Break / 405 I Sedan / 405 II Break / 405 II Sedan (15E, 15B, 01/87→11/99 4E, 4B)</b>											
1.4	47 kW	1.4 l	01/87→07/92								<b>KH10052 ProKIT</b>
					<b>06/87 -&gt; 06/92;</b>						<b>KH20046 ProKIT</b>
					<b>Manufacturer Restriction: BOSCH;</b>						<b>KH20191 ProKIT</b>
1.4	47 kW	1.4 l	05/88→07/92								<b>KH10052 ProKIT</b>
1.6	53 kW	1.6 l	10/88→08/92		<b>Manufacturer Restriction: BOSCH;</b>						<b>KH20191 ProKIT</b>
1.9	72 kW	1.9 l	05/88→07/92								
2.0 16V	110 kW	2 l	06/94→10/95								
2.0 MI-16	112 kW	2 l	08/92→10/95								
1.4	50 kW	1.4 l	06/87→07/92								<b>KH10052 ProKIT</b>
1.4	58 kW	1.4 l	08/92→06/94								
1.6	66 kW	1.6 l	08/92→05/97								
1.6	68 kW	1.6 l	08/92→08/94								
1.6	69 kW	1.6 l	10/88→08/92								
1.6	80 kW	1.6 l	08/92→10/96								
1.6	80 kW	1.6 l	08/92→05/97								



























**PEUGEOT - 405 I Break / 405 I Sedan / 405 II Break / 405 II Sedan (15E, 15B, 01/87→11/99 4E, 4B)**






1.6 4x4	65 kW	1.6 l	04/88→07/92		KH10052 ProKIT
1.6 SRi 4x4	65 kW	1.6 l	04/88→07/92		
1.8	76 kW	1.8 l	08/96→11/99		
1.8 D	44 kW	1.8 l	04/90→07/92		
1.8 D 4x4	66 kW	1.8 l	10/87→07/92		
1.8 DT 4x4	66 kW	1.8 l	05/90→07/92		
1.8 GLD	44 kW	1.8 l	04/90→07/92		
1.9	72 kW	1.9 l	06/87→07/92		
1.9	93 kW	1.9 l	07/87→12/93		
1.9	116 kW	1.9 l	06/87→07/92		
1.9 4x4	80 kW	1.9 l	07/88→12/92		
1.9 4x4	80 kW	1.9 l	10/88→08/92		
1.9 4x4	116 kW	1.9 l	06/87→07/92		
1.9 All-wheel Drive	77 kW	1.9 l	09/88→07/92		
1.9 All-wheel Drive	116 kW	1.9 l	06/87→07/92		
1.9 D	51 kW	1.9 l	08/92→08/94		
1.9 D	52 kW	1.9 l	08/97→11/99		
1.9 Injection 4x4	77 kW	1.9 l	06/87→07/92		
1.9 SPort MI-16 4x4	108 kW	1.9 l	06/87→07/92		
1.9 TD	69 kW	1.9 l	08/92→10/96		
1.9 TD	69 kW	1.9 l	08/92→05/97		
2.0 4x4	89 kW	2 l	08/92→10/96		
2.0 4x4	144 kW	2 l	08/92→12/95		
2.0 T 16 X4	144 kW	2 l	08/92→10/95		
2.0 X4	89 kW	2 l	08/92→10/95		
1.4	55 kW	1.4 l	08/92→10/95		KH10052 ProKIT
1.4	55 kW	1.4 l	08/92→10/96		KH20046 ProKIT
1.4	58 kW	1.4 l	07/93→06/94		KH20191 ProKIT
1.6	65 kW	1.6 l	08/92→10/95	; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.6	65 kW	1.6 l	08/92→10/96		
1.8	74 kW	1.8 l	08/92→10/95		
1.8	74 kW	1.8 l	08/92→10/96		
1.9	70 kW	1.9 l	07/87→12/92		
1.9	70 kW	1.9 l	10/88→08/92		
1.9 D	47 kW	1.9 l	08/92→10/95		
1.9 D	47 kW	1.9 l	08/92→10/96		
1.9 D	50 kW	1.9 l	06/94→10/95		
1.9 D	50 kW	1.9 l	06/94→10/96		
1.9 D	51 kW	1.9 l	09/93→12/95		
1.9 Injection	77 kW	1.9 l	07/87→12/92		
1.9 Sport MI-16	116 kW	1.9 l	07/87→11/92		
1.9 TD	66 kW	1.9 l	08/92→10/95		
1.9 TD	66 kW	1.9 l	08/92→10/96		
2.0	89 kW	2 l	08/92→10/95		
2.0	89 kW	2 l	08/92→10/96		
1.6	53 kW	1.6 l	07/87→12/92		KH10052 ProKIT
				; -> 06/91;	KH20046 ProKIT
				; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.6	55 kW	1.6 l	07/87→06/88		KH10052 ProKIT
				; -> 05/88;	KH20046 ProKIT
				; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.6	55 kW	1.6 l	10/88→08/92		KH10052 ProKIT
1.6	66 kW	1.6 l	10/88→08/92	; -> 06/92;	KH20046 ProKIT
1.8 TD	66 kW	1.8 l	10/88→08/92	; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.8 Turbo Diesel	66 kW	1.8 l	03/88→12/92		
1.9	77 kW	1.9 l	10/88→08/92		
1.9	80 kW	1.9 l	06/87→07/92		
1.9	80 kW	1.9 l	10/88→08/92		
1.9	88 kW	1.9 l	06/87→07/92		
1.9	88 kW	1.9 l	10/88→08/92		
1.9	90 kW	1.9 l	01/89→12/92		
1.9 D	47 kW	1.9 l	10/88→08/92		
1.9 Diesel	51 kW	1.9 l	10/88→08/92		
1.9 Diesel	51 kW	1.9 l	03/88→12/92		
1.6	65 kW	1.6 l	07/87→12/92		KH10052 ProKIT
				; 06/89 -> 06/92;	KH20046 ProKIT
				; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.6	65 kW	1.6 l	10/88→08/92		KH10052 ProKIT
1.6	66 kW	1.6 l	10/89→12/92	; 06/90 -> 06/92;	KH20046 ProKIT
1.9 Sport MI-16	108 kW	1.9 l	06/87→07/92	; Manufacturer Restriction: BOSCH;	KH20191 ProKIT
1.6	68 kW	1.6 l	05/88→07/92		KH10052 ProKIT
				; 06/88 ->;	KH20046 ProKIT
				; Manufacturer Restriction: BOSCH;	KH20191 ProKIT

									
<b>PEUGEOT - 405 I Break / 405 I Sedan / 405 II Break / 405 II Sedan (15E, 15B, 01/87→11/99 4E, 4B)</b>									
1.6	69 kW	1.6 l	01/87→12/92						KH10052 ProKIT
					06/87 ->	ABS			KH20046 ProKIT
					Manufacturer Restriction: BOSCH;		ABS		KH20191 ProKIT
1.9 Diesel	47 kW	1.9 l	07/88→09/92						KH10052 ProKIT
					-> 05/90;	ABS			KH20046 ProKIT
					Manufacturer Restriction: BOSCH;		ABS		KH20191 ProKIT
<b>PEUGEOT - 406 Break (8E/F)</b>								<b>10/96→10/04</b>	
1.8	66 kW	1.8 l	05/97→10/04						KH10052 ProKIT
1.8 16V	81 kW	1.8 l	10/96→10/00		04/99 ->	ABS			KH20012 ProKIT
2.0 16V	97 kW	2 l	10/96→10/04		ABS;	-> 02/99			KH20079 ProKIT
2.0 16V	99 kW	2 l	01/99→10/00		ABS				KH20015 ProKIT
2.0 HDi 90	66 kW	2 l	02/99→10/04		ABS				KH20015 ProKIT
3.0 24V	140 kW	3 l	10/96→10/04						
1.8 16V	85 kW	1.8 l	10/00→10/04						KH10052 ProKIT
2.0 16V HPI	103 kW	2 l	05/01→10/04		ABS				KH20015 ProKIT
2.2	116 kW	2.2 l	07/00→10/04		ABS				KH20079 ProKIT
2.2 HDi	98 kW	2.2 l	03/00→10/04		ABS				
1.9 D	55 kW	1.9 l	10/96→10/04						KH10052 ProKIT
1.9 TD	66 kW	1.9 l	10/96→10/04		ABS;	-> 02/99			KH20079 ProKIT
2.0 HDi 110	80 kW	2 l	02/99→04/04		ABS				KH20015 ProKIT
2.0 Turbo	108 kW	2 l	10/96→10/04		ABS				
2.1 TD 12V	80 kW	2.1 l	10/96→10/04						
2.0	104 kW	2 l	11/96→03/99		ABS				KH20015 ProKIT
2.0 16V	100 kW	2 l	10/00→10/04						KH10052 ProKIT
2.0 HDi 110	79 kW	2 l	08/01→10/04		ABS				KH20012 ProKIT
3.0 V6	152 kW	3 l	03/00→10/04		ABS				KH20015 ProKIT
					ABS				KH20079 ProKIT
<b>PEUGEOT - 406 Coupe / 406 Sedan (8C, 8B)</b>								<b>10/95→12/04</b>	
1.6	65 kW	1.6 l	11/95→05/04						KH10052 ProKIT
1.8	66 kW	1.8 l	05/97→05/04		04/99 ->	ABS			KH20012 ProKIT
1.8 16V	81 kW	1.8 l	11/95→10/00		ABS;	-> 02/99			KH20079 ProKIT
2.0 16V	97 kW	2 l	11/95→05/04		ABS				KH20015 ProKIT
2.0 16V	99 kW	2 l	01/99→08/00		ABS				
2.0 HDi 110	80 kW	2 l	06/98→08/01						
2.0 HDi 90	66 kW	2 l	02/99→05/04						
3.0 24V	140 kW	3 l	10/96→05/04						
1.8	74 kW	1.8 l	10/96→03/99						KH10052 ProKIT
2.0 16V	99 kW	2 l	04/99→09/04						
1.8 16V	85 kW	1.8 l	10/00→05/04						KH10052 ProKIT
2.0 16V HPI	103 kW	2 l	05/01→05/04		ABS				KH20015 ProKIT
2.2	116 kW	2.2 l	07/00→05/04		ABS				KH20079 ProKIT
2.2 HDi	98 kW	2.2 l	03/00→05/04		ABS				
1.8 Bifuel	81 kW	1.8 l	04/99→05/03						KH10052 ProKIT
					ABS				KH20012 ProKIT
					ABS				KH20015 ProKIT
1.9 D	55 kW	1.9 l	10/96→05/04						KH10052 ProKIT
1.9 TD	66 kW	1.9 l	01/96→05/04		ABS;	-> 02/99			KH20079 ProKIT
1.9 TD	68 kW	1.9 l	01/96→05/04		ABS				KH20015 ProKIT
2.0 Turbo	108 kW	2 l	04/96→05/04		ABS				
2.1 TD 12V	80 kW	2.1 l	01/96→05/04						
1.9 TD	69 kW	1.9 l	10/95→10/97						KH10052 ProKIT
					ABS				KH20015 ProKIT
2.0	104 kW	2 l	11/96→03/99		ABS				KH20015 ProKIT
3.0 24V	143 kW	3 l	01/98→06/99						
2.0 16V	97 kW	2 l	03/97→12/04						KH10052 ProKIT
2.0 16V	99 kW	2 l	01/99→10/00		ABS;	-> 02/99			KH20079 ProKIT
3.0 V6 24V	140 kW	3 l	03/97→12/04						
2.0 16V	100 kW	2 l	08/00→06/04						KH10052 ProKIT
2.0 HDi 110	79 kW	2 l	08/01→05/04		ABS				KH20012 ProKIT
3.0 V6	152 kW	3 l	03/00→05/04		ABS				KH20015 ProKIT
					ABS				KH20079 ProKIT
2.0 16V	100 kW	2 l	10/00→12/04						KH10052 ProKIT
2.2	116 kW	2.2 l	03/02→12/04		ABS				KH20079 ProKIT
2.2 HDi	98 kW	2.2 l	03/00→12/04						
3.0 V6	152 kW	3 l	03/00→12/04						




























										
<b>PEUGEOT - 407 Coupe (6C_)</b>										<b>10/05→</b>
2.0 HDi	100 kW	2 l	10/05→							<b>KH10006</b> ProKIT
2.0 HDi	120 kW	2 l	06/09→							<b>KH20061</b> ProKIT
2.2 16V	120 kW	2.2 l	10/05→							
2.7 HDi	150 kW	2.7 l	10/05→							
3.0 HDi	177 kW	3 l	06/09→							
3.0 V6	155 kW	3 l	10/05→							
<b>PEUGEOT - 407 Sedan / 407 SW (6D_, 6E_)</b>										<b>03/04→02/11</b>
1.6 HDi 110	80 kW	1.6 l	05/04→12/10							<b>KH10006</b> ProKIT
1.6 HDi 110 (6D9HZC, 6D9HYC)	80 kW	1.6 l	05/04→12/10							<b>KH20001</b> ProKIT
1.8	85 kW	1.8 l	05/04→07/05							
1.8 (6D6FZB)	85 kW	1.8 l	03/04→07/05							
1.8 16V	92 kW	1.8 l	08/05→12/10							
1.8 16V (6D6FYC)	92 kW	1.8 l	08/05→12/10							
2.0	100 kW	2 l	05/04→07/05							
2.0 (6DRFNB, 6DRFNE)	100 kW	2 l	03/04→07/05							
2.0 16V	103 kW	2 l	08/05→12/10							
2.0 16V (6DRFJC, 6DRFJE, 6DRFJF)	103 kW	2 l	09/05→12/10							
2.0 Bioflex	103 kW	2 l	01/08→12/10							
2.0 Bioflex (6DRFJB)	103 kW	2 l	09/07→02/11							
2.0 HDi	93 kW	2 l	11/04→10/07							
2.0 HDi	103 kW	2 l	08/08→12/10							
2.0 HDi	120 kW	2 l	06/09→12/10							
2.0 HDi (6DRHHA)	120 kW	2 l	06/09→12/10							
2.0 HDi (6DRHRH)	103 kW	2 l	06/09→12/10							
2.0 HDi 135	100 kW	2 l	07/04→12/10							
2.0 HDi 135 (6DRHRH, 6DRHRE, 6DRHRG, 6DRHRJ)	100 kW	2 l	05/04→10/10							
2.2	116 kW	2.2 l	05/04→07/05							
2.2 (6D3FZE, 6D3FZH)	116 kW	2.2 l	03/04→10/06							
2.2 16V	120 kW	2.2 l	08/05→12/10							
2.2 16V (6D3FYH, 6D3FYE)	120 kW	2.2 l	08/05→12/10							
2.2 HDi	120 kW	2.2 l	06/08→12/10							
2.2 HDi (6D4HPH)	120 kW	2.2 l	03/06→12/10							
2.2 HDi 170	125 kW	2.2 l	03/06→12/10							
2.2 HDi 170 (6D4HTH)	125 kW	2.2 l	03/06→12/10							
2.7 HDi	150 kW	2.7 l	10/05→12/10							
2.7 HDi (6DUHZJ, 6DUHZF)	150 kW	2.7 l	10/05→12/10							
3.0	155 kW	3 l	05/04→12/10							
3.0 (6DXFVJ)	155 kW	3 l	03/04→12/10							
2.0 16V (6DRFJC, 6DRFJF)	105 kW	2 l	08/08→12/09							<b>KH10006</b> ProKIT
<b>PEUGEOT - 508 I / 508 SW I (8D_, 8E_)</b>										<b>11/10→12/18</b>
1.6	121 kW	1.6 l	02/12→12/18							<b>KH10006</b> ProKIT
1.6 HDi	82 kW	1.6 l	11/10→12/18							<b>KH20002</b> ProKIT
1.6 HDi	84 kW	1.6 l	02/12→12/18							
1.6 THP	110 kW	1.6 l	11/10→12/18							
1.6 THP	115 kW	1.6 l	11/10→12/18							
1.6 VTi	85 kW	1.6 l	11/10→12/18							
1.6 VTi	88 kW	1.6 l	11/10→12/18							
2.0 BlueHDi 150	110 kW	2 l	04/14→12/18							
2.0 BlueHDi 180	133 kW	2 l	04/14→12/18							
2.0 HDi	100 kW	2 l	11/10→12/18							
2.0 HDi	103 kW	2 l	11/10→12/18							
2.0 HDi	120 kW	2 l	11/10→12/18							
2.0 HDi 180 RXH	133 kW	2 l	10/14→12/18							
1.6 BlueHDi 120	88 kW	1.6 l	03/14→12/18							<b>KH10006</b> ProKIT
1.6 HDi	85 kW	1.6 l	09/14→12/18							
1.6 THP	120 kW	1.6 l	01/12→12/18							<b>KH20002</b> ProKIT
1.6 THP	121 kW	1.6 l	09/11→12/18							
2.0 HDi Hybrid4 AWC	147 kW	2 l	11/10→12/18							<b>KH10006</b> ProKIT
2.0 HDi RXH Hybrid4	120 kW	2 l	11/10→12/18							
2.2 HDi	150 kW	2.2 l	11/10→12/18							<b>KH10006</b> ProKIT
										<b>KH20001</b> ProKIT
<b>PEUGEOT - 605 Sedan (6B)</b>										<b>06/89→09/99</b>
2.0	79 kW	2 l	02/90→09/99		<b>05/97 -&gt;</b>	<b>VIN 7469 -&gt;</b>				<b>KH10165</b> ProKIT
2.0	89 kW	2 l	06/89→09/99		<b>-&gt; 04/97;</b>	<b>VIN -&gt; 7468</b>				<b>KH10192</b> ProKIT
2.0 16V	97 kW	2 l	07/94→09/99							
2.0 Turbo	104 kW	2 l	07/92→09/99							
2.0 Turbo	108 kW	2 l	07/91→09/99							
2.1 TD 12V	80 kW	2.1 l	08/94→09/99							
2.1 Turbo Diesel	80 kW	2.1 l	06/89→09/99							
2.5 Turbo Diesel	95 kW	2.5 l	07/94→09/99							
3.0	123 kW	3 l	10/89→09/99							
3.0 SV 24	147 kW	3 l	08/89→09/99							
2.1 D	60 kW	2.1 l	06/89→07/95							<b>KH10192</b> ProKIT

































































				    	
<b>PEUGEOT - 605 Sedan (6B)</b>				<b>06/89→09/99</b>	
3.0 V6	140 kW	3 l	04/97→09/99		KH10165 ProKIT
<b>PEUGEOT - 607 Sedan (9D, 9U)</b>				<b>02/00→07/11</b>	
2.0	100 kW	2 l	02/00→08/05	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
2.0 HDi	80 kW	2 l	05/00→09/05	; Outer diameter 1 [mm]: 84	KH10165 ProKIT
2.2 16V	116 kW	2.2 l	02/00→08/05	; 01/05 ->	KH20001 ProKIT
2.2 HDi	98 kW	2.2 l	02/00→02/06	; -> 12/04	KH20038 ProKIT
2.0 HDi	79 kW	2 l	03/01→09/04	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
3.0 V6 24V	152 kW	3 l	02/00→07/04	; Outer diameter 1 [mm]: 84	KH10165 ProKIT
					KH20038 ProKIT
2.0 HDi	100 kW	2 l	09/05→07/11		KH10006 ProKIT
2.2 16V	120 kW	2.2 l	09/05→06/10		KH20001 ProKIT
2.2 HDi	125 kW	2.2 l	05/06→06/10		
2.7 HDi 24V	150 kW	2.7 l	12/04→07/11	; Outer diameter 1 [mm]: 83	KH10006 ProKIT
3.0 V6 24V	155 kW	3 l	03/04→07/11	; Outer diameter 1 [mm]: 84	KH10165 ProKIT
				; 01/05 ->	KH20001 ProKIT
<b>PEUGEOT - 806 (221)</b>				<b>06/94→08/02</b>	
1.8	73 kW	1.8 l	07/95→08/02		KH10089 ProKIT
1.9 TD	66 kW	1.9 l	07/95→08/02	; -> 05/02	KH20095 ProKIT
2.0 16V	100 kW	2 l	09/00→08/02		
2.0 HDi	80 kW	2 l	08/99→08/02		
1.9 TD	68 kW	1.9 l	05/97→08/02		KH10089 ProKIT
				; -> 09/98	KH20095 ProKIT
2.0	89 kW	2 l	06/94→08/02		KH10089 ProKIT
2.0 Turbo	108 kW	2 l	06/94→08/02	; 07/94 -> 05/02	KH20095 ProKIT
2.0 16V	97 kW	2 l	05/98→09/00		KH10089 ProKIT
				; 10/98 ->	KH20095 ProKIT
2.0 HDi 16V	80 kW	2 l	08/99→08/02		KH10089 ProKIT
				; 01/01 -> 05/02	KH20095 ProKIT
2.1 td 12V	80 kW	2.1 l	06/96→08/99		KH10089 ProKIT
					KH20095 ProKIT
<b>PEUGEOT - 807 (EB_)</b>				<b>06/02→06/10</b>	
2.0	100 kW	2 l	06/02→	; -> 03/11	KH10132 ProKIT
2.0 16V	103 kW	2 l	09/05→	; -> 03/11	KH20055 ProKIT
2.0 HDi	88 kW	2 l	02/06→		
2.0 HDi	100 kW	2 l	06/06→		
2.2	116 kW	2.2 l	06/02→		
2.2 HDi	94 kW	2.2 l	06/02→		
2.0 HDi	79 kW	2 l	06/02→05/06		KH10132 ProKIT
2.0 HDi	80 kW	2 l	04/04→		KH20055 ProKIT
2.0 HDi	120 kW	2 l	06/09→	; -> 03/11	KH20055 ProKIT
3.0 V6	150 kW	3 l	06/02→		
2.2 HDi	125 kW	2.2 l	06/06→06/10		KH20055 ProKIT
<b>PEUGEOT - 1007 (KM_)</b>				<b>04/05→</b>	
1.4	54 kW	1.4 l	04/05→	(ABS)	KH10054 ProKIT
					KH10056 ProKIT
					KH20100 ProKIT
1.4 16V	65 kW	1.4 l	10/05→		KH10054 ProKIT
1.4 HDi	50 kW	1.4 l	04/05→		KH10056 ProKIT
1.6 16V	80 kW	1.6 l	04/05→		KH20100 ProKIT
1.6 HDi	80 kW	1.6 l	06/07→		KH20100 ProKIT
<b>PEUGEOT - 2008 I (CU_)</b>				<b>03/13→</b>	
1.2 PureTech 82	61 kW	1.2 l	01/18→12/19	; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.5 BlueHDI 100	75 kW	1.5 l	05/18→	; Outer diameter 1 [mm]: 72	KH10054 ProKIT
1.5 BlueHDI 120	88 kW	1.5 l	05/18→		
1.6 Flex	87 kW	1.6 l	01/19→		
1.6 Flex	90 kW	1.6 l	04/15→		
1.6 Griffe Flex	127 kW	1.6 l	04/15→		
1.6 THP 165	121 kW	1.6 l	02/16→		
1.6 VTi	85 kW	1.6 l	02/16→		








											
<b>PEUGEOT - 2008 I (CU_)</b>										<b>03/13→</b>	
1.2 THP 110 / PureTech 110	81 kW	1.2 l	01/15→		Outer diameter 1 [mm]: 82				KH10047 ProKIT		
1.2 THP 130 / PureTech 130	96 kW	1.2 l	01/15→		Outer diameter 1 [mm]: 72				KH10054 ProKIT		
1.2 VTi	60 kW	1.2 l	03/13→12/18		ABS				KH10048 ProKIT		
1.4 HDi	50 kW	1.4 l	06/13→								
1.6 BlueHDi	85 kW	1.6 l	07/14→								
1.6 BlueHDi 100	73 kW	1.6 l	01/15→								
1.6 BlueHDi 120	88 kW	1.6 l	07/14→								
1.6 BlueHDi 75	55 kW	1.6 l	01/15→								
1.6 HDi	68 kW	1.6 l	03/13→								
1.6 HDi	84 kW	1.6 l	03/13→								
1.6 VTi	88 kW	1.6 l	03/13→								
<b>PEUGEOT - 3008 MPV (0U_)</b>										<b>06/09→08/16</b>	
1.2	96 kW	1.2 l	01/15→08/16						KH10047 ProKIT		
1.6 BlueHDi 120	88 kW	1.6 l	05/14→08/16		ABS				KH10040 ProKIT		
1.6 HDi	80 kW	1.6 l	06/09→08/16								
1.6 HDi	82 kW	1.6 l	12/09→08/16								
1.6 HDi	84 kW	1.6 l	03/13→08/16								
1.6 HDi 115 / BlueHDi 115	85 kW	1.6 l	02/13→08/16								
1.6 THP	110 kW	1.6 l	06/09→08/16								
1.6 THP	115 kW	1.6 l	06/09→08/16								
1.6 Turbo	121 kW	1.6 l	05/14→08/16								
1.6 VTi	88 kW	1.6 l	06/09→08/16								
2.0 HDi	100 kW	2 l	09/11→08/16								
2.0 HDi	120 kW	2 l	06/09→08/16								
2.0 HDi 150 / BlueHDi 150	110 kW	2 l	06/09→08/16								
1.6 THP	120 kW	1.6 l	09/10→08/16						KH10047 ProKIT		
<b>PEUGEOT - 4007 (VU_, VV_)</b>										<b>02/07→03/13</b>	
2.2 HDi	115 kW	2.2 l	02/07→03/13		-> 03/10				KH10164 ProKIT		
2.4 16V	125 kW	2.4 l	02/07→03/13								
<b>PEUGEOT - 4008 Wagon</b>										<b>05/12→</b>	
1.6 HDi AWC	84 kW	1.6 l	05/12→						KH30127 ProKIT		
1.8 HDi AWC	110 kW	1.8 l	05/12→								
<b>PEUGEOT - 5008 (0U_, 0E_)</b>										<b>06/09→03/17</b>	
1.2	96 kW	1.2 l	01/15→03/17						KH10047 ProKIT		
1.6 16V	88 kW	1.6 l	09/09→03/17		ABS				KH10040 ProKIT		
1.6 16V	115 kW	1.6 l	09/09→03/17								
1.6 BlueHDi 120	88 kW	1.6 l	05/14→03/17								
1.6 HDi	80 kW	1.6 l	09/09→03/17								
1.6 HDi	82 kW	1.6 l	08/10→03/17								
1.6 HDi	84 kW	1.6 l	03/13→03/17								
1.6 THP 150	110 kW	1.6 l	02/12→03/17								
1.6 THP 163	120 kW	1.6 l	02/12→03/17								
1.6 THP 165	121 kW	1.6 l	02/12→03/17								
2.0 HDi	120 kW	2 l	09/09→03/17								
2.0 HDi 136 / BlueHDi 136	100 kW	2 l	02/12→03/17								
2.0 HDi 150 / BlueHDi 150	110 kW	2 l	06/09→03/17								
<b>PEUGEOT - BIPPER / BIPPER TEPEE (AA_)</b>										<b>02/08→</b>	
1.3 HDi 75	55 kW	1.3 l	10/10→						KH20022 ProKIT		
1.3 HDi 80	59 kW	1.3 l	12/15→								
1.3 HDi 75	55 kW	1.3 l	10/10→						KH10065 ProKIT		
1.4 HDi	50 kW	1.4 l	02/08→						KH20022 ProKIT		
1.4 HDi	50 kW	1.4 l	04/08→								
1.4	54 kW	1.4 l	02/08→		ABS				KH10043 ProKIT		
1.4	54 kW	1.4 l	04/08→						KH20022 ProKIT		
<b>PEUGEOT - BOXER Bus</b>										<b>09/05→</b>	
2.0 BlueHDi 110	81 kW	2 l	07/15→09/19						KH10120 ProKIT		
2.0 BlueHDi 130	96 kW	2 l	07/15→09/19		Payload [kg]: 1,600; $F_{HD}$ : 1; Payload [kg]: 2,000				KH20059 ProKIT		
2.0 BlueHDi 160	120 kW	2 l	07/15→09/19		Payload [kg]: 1,200, 1,400, 1,600; $F_{HD}$ : 1				KH20086 ProKIT		
2.2 HDi 100	74 kW	2.2 l	04/06→								
2.2 HDi 110	81 kW	2.2 l	03/11→								
2.2 HDi 120	88 kW	2.2 l	04/06→								
2.2 HDi 130	96 kW	2.2 l	03/11→								
2.2 HDi 150	110 kW	2.2 l	03/11→								
3.0 HDi 145	107 kW	3 l	04/10→								
3.0 HDi 160	116 kW	3 l	04/06→								
3.0 HDi 175	130 kW	3 l	03/11→								
2.2 BlueHDi 120	88 kW	2.2 l	07/19→						KH10120 ProKIT		
2.2 BlueHDi 140	103 kW	2.2 l	07/19→								
2.2 BlueHDi 165	121 kW	2.2 l	08/19→								
2.8 HDi	93 kW	2.8 l	09/05→09/09								
3.0 HDi	115 kW	3 l	01/15→12/15								





































PEUGEOT - BOXER Bus (230P)				03/94→04/02	
1.9 D	51 kW	1.9 l	03/94→04/02	; VIN -> 16205754; ; ; Payload from [kg]:	KH00035 ProKIT
1.9 TD	66 kW	1.9 l	08/94→04/02	1,000 → Payload to [kg]: 1,400	
1.9 TD	68 kW	1.9 l	03/94→04/02	; VIN -> 1620653; ; ; Payload from [kg]:	
2.0 i	80 kW	2 l	03/94→04/02	1,000 → Payload to [kg]: 1,400	
2.5 D	63 kW	2.5 l	08/94→04/02	; VIN 16205754 ->; ; ; Payload from [kg]:	KH10078 ProKIT
2.5 TD	76 kW	2.5 l	07/94→04/02	1,000 → Payload to [kg]: 1,400	
2.5 TDI	79 kW	2.5 l	01/97→04/02	; VIN 16205755 ->; ; ; Payload from [kg]:	
2.8 HDi	93 kW	2.8 l	10/00→11/01	1,000 → Payload to [kg]: 1,400	
2.8 HDi	94 kW	2.8 l	11/00→04/02	; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,800	KH00019 ProKIT
				; VIN -> 16194399; Payload [kg]: 1,000, 1,400	KH00043 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT
1.9 TD 4x4	68 kW	1.9 l	07/96→04/02	; VIN -> 16205754; ; ; Payload from [kg]:	KH00035 ProKIT
2.0 i 4x4	80 kW	2 l	08/96→04/02	1,000 → Payload to [kg]: 1,400	
2.5 D 4x4	63 kW	2.5 l	07/96→04/02	; VIN -> 1620653; ; ; Payload from [kg]:	
2.5 TD 4x4	76 kW	2.5 l	07/96→04/02	1,000 → Payload to [kg]: 1,400	
2.5 TDI 4x4	79 kW	2.5 l	01/97→04/02	;	
2.8 HDi 4x4	94 kW	2.8 l	10/00→04/02	; VIN 16205754 ->; ; ; Payload from [kg]:	KH10078 ProKIT
2.8 HDi All-wheel Drive	93 kW	2.8 l	10/00→11/01	1,000 → Payload to [kg]: 1,400	
				; VIN 16205755 ->; ; ; Payload from [kg]:	
				1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				;	KH10391 ProKIT
2.5 DT	62 kW	2.5 l	10/97→11/01	; VIN -> 16205754; ; ; Payload from [kg]:	KH00035 ProKIT
2.8 D	64 kW	2.8 l	01/99→02/02	1,000 → Payload to [kg]: 1,400	
				; VIN -> 1620653; ; ; Payload from [kg]:	
				1,000 → Payload to [kg]: 1,400	
				; VIN 16205754 ->; ; ; Payload from [kg]:	KH10078 ProKIT
				1,000 → Payload to [kg]: 1,400	
				; VIN 16205755 ->; ; ; Payload from [kg]:	
				1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT
2.8 DTiC	90 kW	2.8 l	10/97→09/00	; VIN -> 16205754; ; ; Payload from [kg]:	KH00035 ProKIT
				1,000 → Payload to [kg]: 1,400	
				; VIN -> 1620653; ; ; Payload from [kg]:	
				1,000 → Payload to [kg]: 1,400	
				; VIN 16205754 ->; ; ; Payload from [kg]:	KH10078 ProKIT
				1,000 → Payload to [kg]: 1,400	
				; VIN 16205755 ->; ; ; Payload from [kg]:	
				1,000 → Payload to [kg]: 1,400	
				; ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	
				; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
				; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN 16194400 ->	KH10091 ProKIT
PEUGEOT - BOXER Bus / BOXER Platform/Chassis (244, Z_, 244)				12/01→06/06	
2.0	81 kW	2 l	12/01→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
2.0 BiFuel	81 kW	2 l	12/01→06/06	; not for vehicle identification number: 936...;	KH10101 ProKIT
2.0 HDi	62 kW	2 l	12/01→06/06	Payload [kg]: 1,800	
2.2 HDi	74 kW	2.2 l	12/01→06/06	; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
2.8 HDi	94 kW	2.8 l	12/01→06/06		KH10091 ProKIT
2.8 HDi	107 kW	2.8 l	04/04→06/06		KH10120 ProKIT
2.0 BlueHDi 110	81 kW	2 l	07/15→09/19		KH10120 ProKIT
2.0 BlueHDi 130	96 kW	2 l	07/15→09/19	; Payload [kg]: 1,600; ; Payload [kg]: 2,000	KH20059 ProKIT
2.0 BlueHDi 160	120 kW	2 l	07/15→09/19	; Payload [kg]: 1,200, 1,400, 1,600;	KH20086 ProKIT
2.2 HDi 100	74 kW	2.2 l	04/06→		
2.2 HDi 110	81 kW	2.2 l	03/11→		
2.2 HDi 120	88 kW	2.2 l	04/06→		
2.2 HDi 130	96 kW	2.2 l	03/11→		
2.2 HDi 150	110 kW	2.2 l	03/11→		
3.0 HDi	115 kW	3 l	04/06→		
3.0 HDi 145	107 kW	3 l	04/10→		
3.0 HDi 160	116 kW	3 l	04/06→		
3.0 HDi 175	130 kW	3 l	03/11→		
















































































											
<b>PEUGEOT - BOXER Bus / BOXER Platform/Chassis (244, Z_, 244)</b>										<b>12/01→06/06</b>	
2.2 BlueHDi 120	88 kW	2.2 l	08/19→								KH10120 ProKIT
2.2 BlueHDi 140	103 kW	2.2 l	08/19→								
2.2 BlueHDi 165	121 kW	2.2 l	08/19→								
2.3 HDi	93 kW	2.3 l	04/06→								
2.8 HDi	90 kW	2.8 l	03/02→08/05								KH10078 ProKIT
2.8 HDi 4x4	94 kW	2.8 l	12/01→06/06								KH10101 ProKIT
2.8 TD	90 kW	2.8 l	12/01→03/05								
										 ; Payload [kg]: 800, 1,000, 1,400	KH10234 ProKIT
										 ; not for vehicle identification number: 936...;	KH10101 ProKIT
										 ; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
2.8 HDi 4x4	94 kW	2.8 l	12/01→06/06								KH10078 ProKIT
										 ; Payload [kg]: 800, 1,000, 1,400	KH10101 ProKIT
										 ; not for vehicle identification number: 936...;	KH10101 ProKIT
										 ; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
										 ; 04/04 -> 08/05	KH10391 ProKIT
<b>PEUGEOT - BOXER Platform/Chassis (ZCT_)</b>										<b>03/94→04/02</b>	
1.9 D	51 kW	1.9 l	03/94→04/02								KH00035 ProKIT
2.0	81 kW	2 l	12/01→04/02								
2.8 D	64 kW	2.8 l	01/99→02/02								
										 ; VIN -> 16205754;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN -> 1620653;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN 16205754 ->;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN 16205755 ->;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
										 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
1.9 TD	66 kW	1.9 l	06/94→04/02								KH00035 ProKIT
1.9 TD	68 kW	1.9 l	07/94→04/02								
2.0 i	80 kW	2 l	06/94→04/02								
2.5 D	63 kW	2.5 l	03/94→04/02								
2.5 TD	76 kW	2.5 l	03/94→04/02								KH10078 ProKIT
2.5 TDI	79 kW	2.5 l	01/97→04/02								
2.8 HDi	93 kW	2.8 l	10/00→11/01								
2.8 HDi	94 kW	2.8 l	11/00→04/02								
										 ; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
										 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
										 ; VIN -> 16194399; Payload [kg]: 1,800	KH00019 ProKIT
										 ; VIN -> 16194399; Payload [kg]: 1,000, 1,400	KH00043 ProKIT
2.5 D 4x4	63 kW	2.5 l	07/99→04/02								KH00035 ProKIT
2.5 TDI 4x4	79 kW	2.5 l	07/99→04/02								
2.8 HDi All-wheel Drive	93 kW	2.8 l	10/00→11/01								
										 ; VIN -> 16205754;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN 16205755 ->;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ;  ; Payload from [kg]: 1,000 → Payload to [kg]: 1,400	KH10078 ProKIT
										 ; VIN -> 16194399; Payload [kg]: 1,800	KH00080 ProKIT
										 ; VIN 16194400 ->; Payload [kg]: 1,800	KH10101 ProKIT
										 ; 	KH10391 ProKIT
<b>PEUGEOT - BOXER Van</b>										<b>09/05→</b>	
2.0 BlueHDi 110	81 kW	2 l	07/15→09/19								KH10120 ProKIT
2.0 BlueHDi 130	96 kW	2 l	07/15→09/19								
2.0 BlueHDi 160	120 kW	2 l	07/15→09/19								
2.2 HDi 100	74 kW	2.2 l	04/06→								KH20086 ProKIT
2.2 HDi 110	81 kW	2.2 l	03/11→								
2.2 HDi 120	88 kW	2.2 l	04/06→								
2.2 HDi 130	96 kW	2.2 l	03/11→								
2.2 HDi 150	110 kW	2.2 l	03/11→								
3.0 HDi	115 kW	3 l	07/06→								
3.0 HDi 145	107 kW	3 l	04/10→								
3.0 HDi 160	116 kW	3 l	04/06→								
3.0 HDi 175	130 kW	3 l	03/11→								

				13	i			
<b>PEUGEOT - BOXER Van</b>							<b>09/05→</b>	
2.0 BlueHdi 130 4x4	96 kW	2 l	07/15→09/19					KH10120 ProKIT
2.0 BlueHdi 160 4x4	120 kW	2 l	07/15→09/19					
2.2 BlueHdi 120	88 kW	2.2 l	07/19→					
2.2 BlueHdi 140	103 kW	2.2 l	07/19→					
2.2 BlueHdi 165	121 kW	2.2 l	07/19→					
2.2 HDi 130 4x4	96 kW	2.2 l	03/11→					
2.2 HDi 150 4x4	110 kW	2.2 l	03/11→					
2.8 HDi	93 kW	2.8 l	09/05→09/09					
3.0 HDi 175	129 kW	3 l	01/15→12/15					
<b>PEUGEOT - BOXER Van (230L)</b>							<b>03/94→08/05</b>	
1.9 D	50 kW	1.9 l	07/99→04/02		VIN -> 16205754; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH00035 ProKIT
1.9 D	51 kW	1.9 l	03/94→04/02					
1.9 TD	66 kW	1.9 l	07/99→04/02		VIN -> 1620653; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
1.9 TD	68 kW	1.9 l	03/94→04/02					
2.0 HDi	62 kW	2 l	08/01→04/02		VIN 16205754 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH10078 ProKIT
2.0 i	80 kW	2 l	06/94→04/02					
2.5 D	63 kW	2.5 l	03/94→04/02		VIN 16205755 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
2.5 DT	62 kW	2.5 l	10/97→11/01					
2.5 TD	76 kW	2.5 l	03/94→04/02					
2.5 TDI	79 kW	2.5 l	01/97→04/02					
2.8 HDi	93 kW	2.8 l	10/00→11/01					
2.8 HDi	94 kW	2.8 l	11/00→04/02		VIN -> 16194399; Payload [kg]: 1,800			KH00080 ProKIT
					VIN 16194400 ->; Payload [kg]: 1,800			KH10101 ProKIT
					VIN -> 16194399; Payload [kg]: 1,800			KH00019 ProKIT
					VIN -> 16194399; Payload [kg]: 1,000, 1,400			KH00043 ProKIT
					VIN 16194400 ->			KH10091 ProKIT
1.9 DT 4x4	66 kW	1.9 l	03/96→09/98		VIN -> 16205754; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH00035 ProKIT
2.0 4x4	80 kW	2 l	03/96→09/98					
2.5 D 4x4	63 kW	2.5 l	07/99→04/02		VIN -> 1620653; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
2.5 TDI 4x4	79 kW	2.5 l	07/99→04/02					
2.8 DTiC 4x4	90 kW	2.8 l	10/97→08/05					
2.8 HDi 4x4	93 kW	2.8 l	10/00→11/01		VIN 16205754 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH10078 ProKIT
2.8 HDi 4x4	94 kW	2.8 l	10/00→04/02		VIN 16205755 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
					VIN -> 16194399; Payload [kg]: 1,800			KH00080 ProKIT
					VIN 16194400 ->; Payload [kg]: 1,800			KH10101 ProKIT
					VIN 16194400 ->			KH10091 ProKIT
2.8 D	64 kW	2.8 l	01/99→02/02		VIN -> 16205754; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH00035 ProKIT
					VIN -> 1620653; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
					VIN 16205754 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH10078 ProKIT
					VIN 16205755 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
					VIN -> 16194399; Payload [kg]: 1,800			KH00080 ProKIT
					VIN 16194400 ->; Payload [kg]: 1,800			KH10101 ProKIT
					VIN 16194400 ->			KH10091 ProKIT
2.8 DTiC	90 kW	2.8 l	10/97→09/00		VIN -> 16205754; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH00035 ProKIT
					VIN -> 1620653; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
					VIN 16205754 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		KH10078 ProKIT
					VIN 16205755 ->; ○; ABS; Payload from [kg]:	1,000 → Payload to [kg]: 1,400		
					VIN -> 16194399; Payload [kg]: 1,800			KH00080 ProKIT
					VIN 16194400 ->; Payload [kg]: 1,800			KH10101 ProKIT
<b>PEUGEOT - BOXER Van (244)</b>							<b>12/01→09/09</b>	
2.0	81 kW	2 l	12/01→06/06					KH10078 ProKIT
2.0 BiFuel	81 kW	2 l	12/01→06/06					
2.0 HDi	62 kW	2 l	04/02→06/06		not for vehicle identification number: 936...;			KH10101 ProKIT
2.2 HDi	74 kW	2.2 l	12/01→06/06					
2.8 HDi	93 kW	2.8 l	09/05→09/09		VIN 936...; Payload [kg]: 1,800			KH10234 ProKIT
2.8 HDi	94 kW	2.8 l	12/01→06/06					KH10091 ProKIT
2.8 HDi	107 kW	2.8 l	04/04→06/06					





































				    	
<b>PEUGEOT - BOXER Van (244)</b>				<b>12/01→09/09</b>	
2.3 HDi	93 kW	2.3 l	02/07→		KH10120 ProKIT
2.8 HDi	90 kW	2.8 l	03/02→08/05	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
				; not for vehicle identification number: 936...; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
2.8 HDi 4x4	94 kW	2.8 l	12/01→06/06	; Payload [kg]: 800, 1,000, 1,400	KH10078 ProKIT
				; not for vehicle identification number: 936...; Payload [kg]: 1,800	KH10101 ProKIT
				; VIN 936...; Payload [kg]: 1,800	KH10234 ProKIT
				; 04/04 -> 08/05	KH10391 ProKIT
<b>PEUGEOT - EXPERT (224_)</b>				<b>02/96→12/06</b>	
1.6	58 kW	1.6 l	02/96→09/00		KH10089 ProKIT
1.8	74 kW	1.8 l	10/96→09/00		KH20095 ProKIT
1.9 D	51 kW	1.9 l	02/96→12/98		
1.9 TD	68 kW	1.9 l	02/96→05/98		
2.0 HDi	69 kW	2 l	10/00→10/06		
1.9 D	51 kW	1.9 l	12/03→12/06		KH10089 ProKIT
1.9 TD	66 kW	1.9 l	02/96→09/00		KH10089 ProKIT
				; 07/97 ->	KH20095 ProKIT
2.0	100 kW	2 l	07/00→12/06		KH10089 ProKIT
2.0 HDI	80 kW	2 l	07/00→12/06	; 09/00 ->	KH20095 ProKIT
2.0 HDI 16V	80 kW	2 l	07/00→12/06		KH10089 ProKIT
				; 09/01 -> 12/03	KH20095 ProKIT
<b>PEUGEOT - EXPERT Platform/Chassis</b>				<b>01/07→</b>	
1.6 HDi 90 16V	66 kW	1.6 l	01/07→		KH10119 ProKIT
1.6 HDi 90 8V	66 kW	1.6 l	01/07→		KH30015 ProKIT
2.0 HDi 120	88 kW	2 l	01/07→	;	KH30016 ProKIT
2.0 HDi 130	94 kW	2 l	03/11→	;	KH30016 ProKIT
2.0 HDi 140	100 kW	2 l	01/07→		
2.0 HDi 165	120 kW	2 l	09/09→		
<b>PEUGEOT - EXPERT Platform/Chassis (223)</b>				<b>02/96→10/06</b>	
1.6	58 kW	1.6 l	02/96→09/00		KH10089 ProKIT
1.9 D	51 kW	1.9 l	02/96→12/98		KH20095 ProKIT
1.9 TD	68 kW	1.9 l	02/96→05/98		
1.9 D	51 kW	1.9 l	06/98→09/01		KH10089 ProKIT
2.0 HDi	69 kW	2 l	10/00→10/06		
2.0 HDi	80 kW	2 l	10/00→10/06		
2.0 HDi	80 kW	2 l	10/00→10/06		
1.9 TD	66 kW	1.9 l	02/96→09/00		KH10089 ProKIT
				; 07/97 ->	KH20095 ProKIT
<b>PEUGEOT - EXPERT TEPEE (VF3X_)</b>				<b>01/07→03/16</b>	
1.6 HDi 90 16V	66 kW	1.6 l	01/07→03/16		KH10119 ProKIT
1.6 HDi 90 8V	66 kW	1.6 l	01/07→03/16		KH30015 ProKIT
2.0 16V	103 kW	2 l	01/07→03/16		KH30016 ProKIT
2.0 HDi 100	72 kW	2 l	03/11→03/16	;	KH30016 ProKIT
2.0 HDi 120	88 kW	2 l	01/07→03/16		
2.0 HDi 130	94 kW	2 l	03/11→		
2.0 HDi 140	100 kW	2 l	01/07→		
2.0 HDi 165	120 kW	2 l	09/09→		
2.0 HDi 120 4x4	88 kW	2 l	01/07→03/16		KH30016 ProKIT
2.0 HDi 130 4x4	94 kW	2 l	03/11→03/16		
<b>PEUGEOT - EXPERT Van (222)</b>				<b>02/96→12/06</b>	
1.6	58 kW	1.6 l	02/96→09/00		KH10089 ProKIT
1.8	74 kW	1.8 l	10/96→09/00		KH20095 ProKIT
1.9 D	51 kW	1.9 l	02/96→12/98		
1.9 TD	68 kW	1.9 l	02/96→05/98		
2.0	100 kW	2 l	09/02→12/06		
1.9 D 70	51 kW	1.9 l	12/98→12/06		KH10089 ProKIT
2.0 HDI	69 kW	2 l	07/00→12/06	; 09/00 ->	KH20095 ProKIT
					KH10089 ProKIT
1.9 TD	66 kW	1.9 l	02/96→09/00		KH10089 ProKIT
				; 05/98 ->	KH20095 ProKIT
2.0 HDI	80 kW	2 l	07/00→12/06		KH10089 ProKIT
				; 09/00 ->	KH20095 ProKIT
				; 01/01 ->	KH20095 ProKIT

     					
<b>PEUGEOT - EXPERT Van (V_)</b>				<b>04/16→</b>	
1.6 BlueHDi 115	85 kW	1.6 l	04/16→	    	KH10119 ProKIT
1.6 BlueHDi 95	70 kW	1.6 l	04/16→		
2.0 BlueHDi 120	90 kW	2 l	04/16→		
2.0 BlueHDi 150	110 kW	2 l	04/16→		
2.0 BlueHDi 180	130 kW	2 l	04/16→		
<b>PEUGEOT - EXPERT Van (VF3A_, VF3U_, VF3X_)</b>				<b>01/07→</b>	
1.6 HDi 90 16V	66 kW	1.6 l	01/07→	      	KH10119 ProKIT
1.6 HDi 90 8V	66 kW	1.6 l	01/07→		
2.0 16V	103 kW	2 l	01/07→		
2.0 HDi 100	72 kW	2 l	03/11→		
2.0 HDi 120	88 kW	2 l	01/07→		
2.0 HDi 130	94 kW	2 l	03/11→		
2.0 HDi 140	100 kW	2 l	01/07→		
2.0 HDi 165	120 kW	2 l	09/09→		
<b>PEUGEOT - ION</b>				<b>11/10→</b>	
Electric	35 kW		11/10→		KH20005 ProKIT
Electric	47 kW		11/10→		
Electric	49 kW		01/11→		
<b>PEUGEOT - J5 Bus (280P)</b>				<b>09/81→09/90</b>	
2.0	55 kW	2 l	09/81→09/90	 ; 01/89 ->; VIN 604497 ->  ; -> 12/89; VIN -> 604496  ; 01/89 ->; VIN 604497 ->  ; -> 12/89; VIN -> 604496  ; -> 08/90; VIN 0244301 ->	KH00035 ProKIT
2.0	58 kW	2 l	01/83→09/90		
2.0 Super 4x4	58 kW	2 l	09/81→08/90		
2.5 DT	70 kW	2.5 l	01/86→08/90		
2.5 D	54 kW	2.5 l	09/81→09/90		
2.5 D	54 kW	2.5 l	09/81→09/90		
<b>PEUGEOT - J5 Bus (290P)</b>				<b>10/90→02/94</b>	
1.9 D	51 kW	1.9 l	10/90→02/94		KH00035 ProKIT
2.0	62 kW	2 l	10/90→02/94		
2.5 D	54 kW	2.5 l	10/90→02/94		
2.5 D 4x4	54 kW	2.5 l	10/90→02/94		
2.5 TD	70 kW	2.5 l	10/90→02/94		
2.5 TD 4x4	70 kW	2.5 l	10/90→02/94		
<b>PEUGEOT - J5 Platform/Chassis (280L)</b>				<b>09/81→09/90</b>	
1.8	51 kW	1.8 l	09/81→08/90	 ; 01/89 ->; VIN 604497 ->  ; -> 12/89; VIN -> 604496  ; VIN -> 604496  ; 01/89 ->; VIN 604497 ->  ; -> 12/89; VIN -> 604496  ; -> 08/90; VIN 0244301 ->	KH00035 ProKIT
2.5 D 4x4	54 kW	2.5 l	09/81→08/90		
2.5 DT	70 kW	2.5 l	09/81→08/90		
2.0	55 kW	2 l	01/86→11/88		
2.0	58 kW	2 l	01/83→11/88		
2.5 D	54 kW	2.5 l	09/81→09/90		
<b>PEUGEOT - J5 Platform/Chassis (290L)</b>				<b>10/90→02/94</b>	
1.9 D	51 kW	1.9 l	10/90→02/94		KH00035 ProKIT
2.0	62 kW	2 l	10/90→02/94		
2.5 D	54 kW	2.5 l	10/90→02/94		
2.5 D 4x4	54 kW	2.5 l	10/90→02/94		
2.5 TD	70 kW	2.5 l	10/90→02/94		
2.5 TD 4x4	70 kW	2.5 l	10/90→02/94		
<b>PEUGEOT - J5 Van (280L)</b>				<b>09/81→08/90</b>	
1.8	51 kW	1.8 l	01/83→11/88	 ; VIN -> 604496  ; 01/89 ->; VIN 604497 ->  ; -> 12/89; VIN -> 604496	KH00061 ProKIT
1.9 D	51 kW	1.9 l	09/87→08/90		
2.0	55 kW	2 l	09/87→08/90		
2.0	58 kW	2 l	09/81→08/90		
2.5 D	54 kW	2.5 l	09/81→08/90		
2.5 DT	70 kW	2.5 l	09/81→08/90		
2.5 DT All-wheel Drive	70 kW	2.5 l	09/81→08/90		
<b>PEUGEOT - J5 Van (290L)</b>					
1.8	51 kW	1.8 l	09/90→01/94		KH00035 ProKIT
1.9 D	51 kW	1.9 l	10/90→03/94		
2.0	62 kW	2 l	09/90→01/94		
2.5 D	54 kW	2.5 l	09/90→01/94		
2.5 D 4x4	54 kW	2.5 l	10/90→03/94		
2.5 DT	70 kW	2.5 l	09/90→01/94		
2.5 TD 4x4	70 kW	2.5 l	10/90→03/94		



				  	 	 13			
<b>PEUGEOT - J7 Bus / J7 Platform/Chassis / J7 Van</b>								<b>08/68→03/80</b>	
1.6	44 kW	1.6 l	08/68→03/80				KH10216 ProKIT		
1.6	44 kW	1.6 l	07/70→03/80						
1.6	50 kW	1.6 l	08/68→03/80						
1.8	48 kW	1.8 l	07/70→03/80						
1.9 D	40 kW	1.9 l	08/68→07/78						
2.1 D	42 kW	2.1 l	08/68→07/77						
2.3 D	49 kW	2.3 l	07/77→03/80						
<b>PEUGEOT - J9 Bus / J9 Platform/Chassis / J9 Van</b>								<b>03/80→06/87</b>	
1.6	44 kW	1.6 l	03/80→06/87				KH10216 ProKIT		
2.0	57 kW	2 l	03/80→06/87						
2.1 D	41 kW	2.1 l	03/80→06/87						
2.3 D	49 kW	2.3 l	03/80→07/82						
2.5 D	53 kW	2.5 l	07/82→06/87						
2.5 D	53 kW	2.5 l	08/82→06/87						
<b>PEUGEOT - PARTNER Box Body/MPV</b>								<b>04/08→</b>	
1.6	66 kW	1.6 l	04/08→				KH10047 ProKIT		
1.6	72 kW	1.6 l	11/10→	 			KH10040 ProKIT		
1.6	80 kW	1.6 l	04/08→						
1.6	88 kW	1.6 l	04/10→						
1.6 BlueHDi 100	73 kW	1.6 l	04/15→						
1.6 BlueHDi 120	88 kW	1.6 l	04/15→						
1.6 HDi	55 kW	1.6 l	04/08→						
1.6 HDi	66 kW	1.6 l	12/11→						
1.6 HDi	80 kW	1.6 l	04/08→						
1.6 HDi	84 kW	1.6 l	03/13→						
1.6 HDi / BlueHDi 75	55 kW	1.6 l	07/11→						
1.6 HDi 16V	66 kW	1.6 l	04/08→						
1.6 HDi 16V 4x4	66 kW	1.6 l	04/12→						
1.6 HDi 90	68 kW	1.6 l	04/10→						
Électrique	49 kW		06/13→						
1.6 HDi	82 kW	1.6 l	08/10→				KH10047 ProKIT		
1.6 HDi 16V	68 kW	1.6 l	04/10→						
<b>PEUGEOT - PARTNER Box Body/MPV / PARTNER MPV (5_, G_)</b>								<b>05/96→12/15</b>	
1.1	44 kW	1.1 l	06/96→10/02				KH10052 ProKIT		
1.8	66 kW	1.8 l	05/97→12/02	 			KH20014 ProKIT		
1.8 D	43 kW	1.8 l	06/96→12/02	 			KH20108 ProKIT		
1.9 D	50 kW	1.9 l	06/96→12/02	  			KH20013 ProKIT		
1.9 D	51 kW	1.9 l	06/96→12/02	  			KH20013 ProKIT		
				 			KH20126 ProKIT		
1.1	44 kW	1.1 l	06/96→09/05				KH10052 ProKIT		
1.4	55 kW	1.4 l	06/96→12/15	  			KH20108 ProKIT		
1.9 D	51 kW	1.9 l	06/96→12/15	 			KH20014 ProKIT		
				 			KH20016 ProKIT		
				 			KH20013 ProKIT		
				 			KH20126 ProKIT		
1.4	54 kW	1.4 l	11/02→10/06	 			KH10052 ProKIT		
1.4 BiFuel	55 kW	1.4 l	04/03→10/06	 			KH20016 ProKIT		
1.6 16V	80 kW	1.6 l	07/01→03/08						
1.9 D 4x4	51 kW	1.9 l	04/04→08/05	  			KH20108 ProKIT		
1.9 D 4x4	51 kW	1.9 l	04/04→07/11	  			KH20013 ProKIT		
2.0 HDi	66 kW	2 l	04/00→07/08	 			KH20014 ProKIT		
2.0 HDi	66 kW	2 l	02/00→07/08						
2.0 HDi 4x4	66 kW	2 l	04/04→08/05						
1.4	54 kW	1.4 l	11/02→10/06	 			KH20016 ProKIT		
				  			KH20108 ProKIT		
				 			KH20013 ProKIT		
1.6	80 kW	1.6 l	09/00→10/02				KH10052 ProKIT		
				  			KH20013 ProKIT		
				 			KH20014 ProKIT		
				  			KH20108 ProKIT		
1.6 Bioflex	80 kW	1.6 l	09/00→10/02				KH10052 ProKIT		
				  			KH20013 ProKIT		
				 			KH20014 ProKIT		
1.6 HDi 75	55 kW	1.6 l	08/05→07/08				KH10052 ProKIT		
1.6 HDi 90	66 kW	1.6 l	08/05→12/15	 			KH20014 ProKIT		
				 			KH20016 ProKIT		



     					
<b>PEUGEOT - PARTNER Box Body/MPV / PARTNER MPV (5_, G_) 05/96→12/15</b>					
1.8 Electric	66 kW 28 kW	1.8 l	03/97→08/00 01/98→12/01	  ; 01/99 ->; ABS  ; ESP, ABS	KH10052 ProKIT KH20014 ProKIT KH20013 ProKIT
1.8 D	44 kW	1.8 l	11/96→02/98	  ; ESP, ABS	KH10052 ProKIT
1.9 D	51 kW	1.9 l	05/96→12/98	 ; ABS  ; ABS, 29  ; ABS	KH20013 ProKIT KH20108 ProKIT KH20126 ProKIT
1.9 D	50 kW	1.9 l	06/96→12/98	  ; ESP, ABS  ; ABS, 29	KH10052 ProKIT KH20013 ProKIT KH20108 ProKIT
1.9 D	51 kW	1.9 l	01/99→07/08	  ; 11/04 ->; ABS  ; -> 10/04; ABS, 29  ; -> 11/04; ESP, ABS  ; ABS  ; ABS	KH10052 ProKIT KH20016 ProKIT KH20108 ProKIT KH20013 ProKIT KH20014 ProKIT KH20126 ProKIT
Electric	25 kW		06/96→12/02	  ; 01/99 ->; ABS  ; 01/99 ->; ABS, 29  ; ESP, ABS	KH10052 ProKIT KH20014 ProKIT KH20108 ProKIT KH20013 ProKIT
<b>PEUGEOT - PARTNER Platform/Chassis / PARTNER TEPEE 04/08→</b>					
1.6 BlueHDi 100	73 kW	1.6 l	12/14→		KH10047 ProKIT
1.6 BlueHDi 120	88 kW	1.6 l	12/14→	 ; ABS	KH10040 ProKIT
1.6 HDi	66 kW	1.6 l	03/13→		
1.6 HDi	80 kW	1.6 l	04/08→		
1.6 HDi	82 kW	1.6 l	08/10→		
1.6 HDi	84 kW	1.6 l	03/13→		
1.6 HDi / BlueHDi 75	55 kW	1.6 l	06/08→12/18		
1.6 HDi 16V	66 kW	1.6 l	04/08→		
1.6 HDi 16V	66 kW	1.6 l	01/09→		
1.6 HDi 90	68 kW	1.6 l	04/10→		
1.6 VTi	66 kW	1.6 l	04/08→		
1.6 VTi	72 kW	1.6 l	08/10→		
1.6 VTi	80 kW	1.6 l	04/08→		
1.6 VTi	88 kW	1.6 l	09/09→04/16		
1.6 HDi	55 kW	1.6 l	01/09→	 ; ABS	KH10040 ProKIT
1.6 VTi	78 kW	1.6 l	04/08→		
1.6 VTi	81 kW	1.6 l	09/08→		
<b>PEUGEOT - RCZ 03/10→12/15</b>					
1.6 16V	115 kW	1.6 l	03/10→12/15	 ; Outer diameter 1 [mm]: 83	KH10006 ProKIT
1.6 16V	147 kW	1.6 l	06/10→12/15	 ; Outer diameter 1 [mm]: 82	KH10047 ProKIT
1.6 THP 150	110 kW	1.6 l	03/11→12/15		
1.6 THP 270	199 kW	1.6 l	06/13→12/15		KH20061 ProKIT
2.0 HDi	120 kW	2 l	03/10→12/15		
1.6 16V	121 kW	1.6 l	01/11→12/15	 ; Outer diameter 1 [mm]: 83	KH10006 ProKIT
1.6 16V	150 kW	1.6 l	06/10→12/15	 ; Outer diameter 1 [mm]: 82	KH10047 ProKIT
<b>PEUGEOT - TRAVELLER Bus (V_) 04/16→</b>					
1.6 BlueHDi 115	85 kW	1.6 l	04/16→		KH10119 ProKIT
1.6 BlueHDi 95	70 kW	1.6 l	04/16→		
2.0 BlueHDi 150	110 kW	2 l	04/16→		
2.0 BlueHDi 180	130 kW	2 l	04/16→		





**PORSCHE - 911**

**08/67→06/87**

2.0 L	96 kW	2 l	08/67→12/68		KH00031 ProKIT
2.0 T	81 kW	2 l	08/68→02/72		
2.2 T	92 kW	2.2 l	01/70→12/72		
2.3 E	121 kW	2.3 l	08/71→12/73		
2.3 S	140 kW	2.3 l	08/71→08/73		
2.3 T	96 kW	2.3 l	01/72→12/73		
2.3 T	103 kW	2.3 l	08/71→12/73		
2.7	110 kW	2.7 l	09/73→08/75		
2.7	121 kW	2.7 l	09/75→06/77		
2.7 S Carrera	129 kW	2.7 l	08/73→01/76		
2.7 SC Carrera RS	154 kW	2.7 l	08/72→01/79		
3.0 SC Carrera	147 kW	3 l	09/75→06/77		
3.0 Turbo	191 kW	3 l	01/75→12/77		
3.0 SC Carrera	132 kW	3 l	07/77→06/80	; -> 12/79	
3.0 SC Carrera	138 kW	3 l	09/79→06/80		
3.0 SC Carrera	154 kW	3 l	03/74→10/83		
3.3 SC Turbo	221 kW	3.3 l	09/77→06/87		

**PORSCHE - 911 (993)**

**10/93→09/97**

3.6 Carrera	200 kW	3.6 l	10/93→08/95		KH10409 ProKIT
3.6 Carrera	210 kW	3.6 l	08/95→09/97		
3.6 Carrera 4	200 kW	3.6 l	07/94→08/95		
3.6 Carrera 4	210 kW	3.6 l	08/95→09/97		
3.6 Turbo 4	300 kW	3.6 l	03/95→09/97		
3.6 Turbo GT2	316 kW	3.6 l	03/95→09/97		
3.6 Turbo GT2 4	316 kW	3.6 l	08/95→09/97		
3.6 Turbo GT2 4	331 kW	3.6 l	06/97→09/97		
3.8 Carrera	210 kW	3.8 l	06/95→09/97		KH10409 ProKIT
3.8 Carrera 4	210 kW	3.8 l	06/95→09/97		
3.8 Carrera 4	221 kW	3.8 l	08/95→09/97		
3.8 Carrera RS	221 kW	3.8 l	06/95→09/97		

**PORSCHE - 911 (996)**

**08/97→09/05**

3.4 Carrera	221 kW	3.4 l	08/97→09/01		KH10349 ProKIT
3.4 Carrera	235 kW	3.4 l	05/01→08/04		
3.4 Carrera 4	221 kW	3.4 l	08/97→09/01		
3.4 Carrera 4	235 kW	3.4 l	05/01→08/04		
3.6 Carrera	235 kW	3.6 l	10/01→08/04		
3.6 Carrera 4	235 kW	3.6 l	10/01→08/04		
3.6 Carrera 4S	254 kW	3.6 l	02/03→07/04		
3.6 Carrera S	254 kW	3.6 l	02/03→08/05		
3.6 GT2	340 kW	3.6 l	04/01→08/05		
3.6 GT2	355 kW	3.6 l	10/03→08/05		
3.6 GT3	265 kW	3.6 l	03/99→07/02		
3.6 GT3	280 kW	3.6 l	03/03→09/05		
3.6 S	331 kW	3.6 l	08/04→08/05		
3.6 Turbo 4	309 kW	3.6 l	06/00→08/05		
3.6 Turbo 4S	331 kW	3.6 l	02/03→08/05		

**PORSCHE - 911 (997)**

**07/04→12/12**

3.6 Carrera	239 kW	3.6 l	07/04→12/08		KH10350 ProKIT
3.6 Carrera	254 kW	3.6 l	06/08→12/11		
3.6 Carrera 4	239 kW	3.6 l	07/04→12/08		
3.6 Carrera 4	254 kW	3.6 l	06/08→12/12		
3.6 GT 2	390 kW	3.6 l	09/07→12/12		
3.6 GT2 RS	456 kW	3.6 l	05/10→12/12		
3.6 GT3	305 kW	3.6 l	03/06→12/09		
3.6 Turbo	353 kW	3.6 l	03/06→12/09		
3.8 Carrera 4S	261 kW	3.8 l	07/04→12/08		
3.8 Carrera 4S	264 kW	3.8 l	09/05→12/08		
3.8 Carrera 4S	280 kW	3.8 l	08/05→12/08		
3.8 Carrera 4S	283 kW	3.8 l	06/08→12/12		
3.8 Carrera 4S / 4 GTS	300 kW	3.8 l	06/09→12/12		
3.8 Carrera S	261 kW	3.8 l	07/04→12/08		
3.8 Carrera S	280 kW	3.8 l	08/05→12/08		
3.8 Carrera S	283 kW	3.8 l	06/08→12/11		
3.8 Carrera S / GTS	300 kW	3.8 l	06/09→12/11		
3.8 GT3	320 kW	3.8 l	05/09→12/11		
3.8 GT3 RS	331 kW	3.8 l	08/09→12/11		
3.8 Turbo	368 kW	3.8 l	09/09→12/12		
3.8 Turbo S	390 kW	3.8 l	02/10→12/12		
4.0 GT3 RS	368 kW	4 l	07/11→12/12		

**PORSCHE - 911 Convertible (993)**

**07/94→09/97**

3.6 Carrera	200 kW	3.6 l	07/94→08/95		KH10409 ProKIT
3.6 Carrera	210 kW	3.6 l	08/95→09/97		
3.6 Carrera 4	200 kW	3.6 l	07/94→08/95		
3.6 Carrera 4	210 kW	3.6 l	08/95→09/97		



**PORSCHE - 911 Convertible (993)**

**07/94→09/97**

3.8 Carrera	210 kW	3.8 l	06/95→09/97
3.8 Carrera	221 kW	3.8 l	08/95→09/97
3.8 Carrera 4	210 kW	3.8 l	06/95→09/97
3.8 Carrera 4	221 kW	3.8 l	08/95→09/97

	<b>KH10409 ProKIT</b>
--	-----------------------

**PORSCHE - 911 Convertible (996)**

**02/98→08/05**

3.4 Carrera	221 kW	3.4 l	02/98→09/01
3.4 Carrera	235 kW	3.4 l	05/01→08/05
3.4 Carrera 4	221 kW	3.4 l	02/98→09/01
3.4 Carrera 4	235 kW	3.4 l	05/01→08/05
3.6 Carrera	235 kW	3.6 l	10/01→08/05
3.6 Carrera 4	235 kW	3.6 l	10/01→08/05
3.6 Carrera 4S	254 kW	3.6 l	06/02→08/05
3.6 Carrera S	254 kW	3.6 l	06/02→08/05
3.6 Turbo 4	309 kW	3.6 l	10/03→08/05
3.6 Turbo 4S	331 kW	3.6 l	10/03→08/05

	<b>KH10349 ProKIT</b>
--	-----------------------

**PORSCHE - 911 Convertible (997)**

**04/05→12/12**

3.6 Carrera	239 kW	3.6 l	04/05→12/08
3.6 Carrera	254 kW	3.6 l	06/08→12/11
3.6 Carrera 4	239 kW	3.6 l	04/05→12/08
3.6 Carrera 4	254 kW	3.6 l	06/08→12/12
3.6 Turbo	353 kW	3.6 l	09/07→12/09
3.8 Carrera 4S	261 kW	3.8 l	04/05→12/08
3.8 Carrera 4S	264 kW	3.8 l	04/05→12/10
3.8 Carrera 4S	280 kW	3.8 l	08/05→12/08
3.8 Carrera 4S	283 kW	3.8 l	06/08→12/12
3.8 Carrera 4S / 4 GTS	300 kW	3.8 l	06/09→12/12
3.8 Carrera S	261 kW	3.8 l	04/05→12/08
3.8 Carrera S	280 kW	3.8 l	08/05→12/08
3.8 Carrera S	283 kW	3.8 l	06/08→12/11
3.8 Carrera S / GTS	300 kW	3.8 l	06/09→12/11
3.8 Turbo	368 kW	3.8 l	09/09→12/12
3.8 Turbo S	390 kW	3.8 l	02/10→12/12

	<b>KH10350 ProKIT</b>
--	-----------------------

**PORSCHE - 911 Targa**

**07/66→06/80**

2.0 E	103 kW	2 l	09/68→02/72
2.0 L	96 kW	2 l	01/67→11/68
2.0 S	118 kW	2 l	07/66→11/68
2.0 S	125 kW	2 l	07/66→02/72
2.0 T	81 kW	2 l	06/67→02/72
2.2 E	114 kW	2.2 l	09/69→02/72
2.2 S	132 kW	2.2 l	09/69→02/72
2.2 T	92 kW	2.2 l	01/70→12/72
2.3 E	121 kW	2.3 l	08/71→12/73
2.3 T	96 kW	2.3 l	01/72→12/73
2.7	110 kW	2.7 l	09/73→08/75
2.7	121 kW	2.7 l	09/75→06/77
2.7 S	129 kW	2.7 l	08/73→01/76
2.7 SC Carrera RS	154 kW	2.7 l	08/72→01/79
3.0 SC Carrera	147 kW	3 l	09/75→06/77

	<b>KH00031 ProKIT</b>
--	-----------------------

3.0 SC Carrera	132 kW	3 l	07/77→06/80
3.0 SC Carrera	138 kW	3 l	09/79→06/80

	<b>KH00031 ProKIT</b>
--	-----------------------

**PORSCHE - 911 Targa (993)**

**08/95→09/97**

3.6 Carrera	210 kW	3.6 l	08/95→09/97
3.8 Carrera	221 kW	3.8 l	05/96→09/97

	<b>KH10409 ProKIT</b>
--	-----------------------

**PORSCHE - 911 Targa (997)**

**07/06→12/12**

3.6 Carrera 4	239 kW	3.6 l	07/06→12/08
3.6 Carrera 4	254 kW	3.6 l	10/08→12/12
3.8 Carrera 4S	261 kW	3.8 l	07/06→12/08
3.8 Carrera 4S	283 kW	3.8 l	10/08→12/12

	<b>KH10350 ProKIT</b>
--	-----------------------

**PORSCHE - 912 / 912 Targa**

**01/65→02/70**

1.6	66 kW	1.6 l	01/65→12/69
1.6	66 kW	1.6 l	03/65→02/70
































	<b>KH00031 ProKIT</b>
--	-----------------------

**PORSCHE - 914**

**01/69→02/76**

/6 2.0	81 kW	2 l	11/69→12/73
1.8	63 kW	1.8 l	08/73→02/76
1.7	59 kW	1.7 l	01/69→12/73
2.0	74 kW	2 l	01/72→12/75

	<b>KH00031 ProKIT</b>
	<b>KH00031 ProKIT</b>
	<b>KH00067 ProKIT</b>

												
<b>PORSCHE - 924</b>										<b>11/75→08/89</b>		
2.0	92 kW	2 l	11/75→08/89						KH00068 ProKIT			
2.0 Turbo	125 kW	2 l	11/78→06/80									
2.0 Turbo	130 kW	2 l	06/80→10/86									
<b>PORSCHE - 928</b>										<b>08/86→11/95</b>		
5.0 GT	243 kW	5 l	01/89→07/91						KH00133 ProKIT			
5.0 S, S4	235 kW	5 l	08/86→07/91		09/86 ->				KH00133 ProKIT			
5.0 S4 Cat	235 kW	5 l	08/86→07/91									
5.4 GTS	257 kW	5.4 l	08/91→11/95		05/92 -> 01/95				KH00133 ProKIT			
<b>PORSCHE - 944</b>										<b>06/81→07/91</b>		
2.5	110 kW	2.5 l	01/85→07/87		-> 01/85				KH00068 ProKIT			
2.5	120 kW	2.5 l	06/81→07/87		01/87 ->				KH00133 ProKIT			
					-> 01/85				KH00068 ProKIT			
2.5 S	140 kW	2.5 l	08/86→07/88		01/87 -> 06/88				KH00133 ProKIT			
2.5 Turbo	162 kW	2.5 l	08/85→07/88		01/87 ->				KH00133 ProKIT			
2.5 Turbo	184 kW	2.5 l	09/87→07/91									
2.7	121 kW	2.7 l	11/88→08/89		-> 06/89				KH00133 ProKIT			
3.0 S2	155 kW	3 l	12/88→07/91		01/89 ->				KH00133 ProKIT			
<b>PORSCHE - 944 Convertible</b>										<b>12/88→07/91</b>		
3.0 S2	155 kW	3 l	12/88→07/91		03/89 ->				KH00133 ProKIT			
<b>PORSCHE - BOXSTER (986)</b>										<b>09/96→12/04</b>		
2.5	150 kW	2.5 l	09/96→08/99									
2.7	162 kW	2.7 l	08/99→07/02									
2.7	168 kW	2.7 l	07/02→12/04									
S 3.2	185 kW	3.2 l	08/99→07/02									
S 3.2	191 kW	3.2 l	07/02→12/04									
S 3.2	196 kW	3.2 l	01/04→12/04									
<b>PORSCHE - BOXSTER / BOXSTER Spyder (987)</b>										<b>11/04→03/12</b>		
2.7	176 kW	2.7 l	11/04→12/06									
S 3.2	206 kW	3.2 l	11/04→12/06									
												
												
2.7	180 kW	2.7 l	07/06→12/09									
2.9	188 kW	2.9 l	06/09→03/12									
3.4	235 kW	3.4 l	02/10→12/11									
S 3.4	217 kW	3.4 l	07/06→12/09									
S 3.4	223 kW	3.4 l	08/08→12/09									
S 3.4	228 kW	3.4 l	06/09→12/11									
<b>PORSCHE - CAYENNE (9PA)</b>										<b>09/02→09/10</b>		
3.0 TDI	176 kW	3 l	02/09→09/10									
3.2	184 kW	3.2 l	10/03→09/07									
3.6	213 kW	3.6 l	02/07→09/10									
GTS 4.8	298 kW	4.8 l	10/07→09/10									
S 4.5	250 kW	4.5 l	09/02→09/07									
S 4.8	283 kW	4.8 l	02/07→09/10									
Turbo 4.5	331 kW	4.5 l	09/02→09/07									
Turbo S 4.5	368 kW	4.5 l	01/04→09/07									
Turbo S 4.5	383 kW	4.5 l	03/06→09/07									
Turbo S 4.8	368 kW	4.8 l	02/07→09/10									
Turbo S 4.8	397 kW	4.8 l	02/07→09/10									
Turbo S 4.8	404 kW	4.8 l	08/08→09/10									
<b>PORSCHE - CAYMAN (987)</b>										<b>11/05→06/13</b>		
2.7	180 kW	2.7 l	07/06→12/09									
2.9	195 kW	2.9 l	02/09→12/12									
R 3.4	243 kW	3.4 l	11/10→12/12									
S 3.4 Sport	223 kW	3.4 l	08/08→12/12									
S 3.4	217 kW	3.4 l	11/05→12/09									
S 3.4	235 kW	3.4 l	02/09→06/13									



















































**PORSCHE - MACAN (95B)**

**02/14→**




















































2.0	174 kW	2 l	07/14→09/18		KH20008 ProKIT
2.0	185 kW	2 l	05/15→		
3.0 GTS	265 kW	3 l	10/15→09/18		
3.0 S	250 kW	3 l	02/14→09/18		
3.0 S Diesel	155 kW	3 l	02/14→09/18		
3.0 S Diesel	184 kW	3 l	02/14→09/18		
3.0 S Diesel	190 kW	3 l	02/14→09/18		
3.6 Turbo	294 kW	3.6 l	02/14→09/18		
3.6 Turbo	324 kW	3.6 l	09/16→		
































				  	 	 13			
<b>PROTON - PERSONA / PERSONA Saloon (C9_M, C9_S)</b>								<b>01/94→07/04</b>	
313i	55 kW	1.3 l	03/96→01/00					KH20194 ProKIT	
315 GLi/GLSi	66 kW	1.5 l	03/96→07/00					KH20194 ProKIT	
315 GLSi	64 kW	1.5 l	09/96→07/00					KH20194 ProKIT	
413	55 kW	1.3 l	01/94→06/03					KH20194 ProKIT	
316	70 kW	1.6 l	03/96→07/04					KH20194 ProKIT	
316 GLXi	83 kW	1.6 l	03/96→07/00					KH20194 ProKIT	
415 GLi/GLSi	66 kW	1.5 l	01/94→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
416 GLXi	83 kW	1.6 l	01/94→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
418	85 kW	1.8 l	05/96→07/00					KH10221 ProKIT	
420 GLS D	48 kW	2 l	05/96→04/99					KH10221 ProKIT	
								KH20194 ProKIT	
420 TD	60 kW	2 l	09/96→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
<b>PROTON - SATRIA (C9_M)</b>								<b>07/00→05/06</b>	
1.5 (C97M)	64 kW	1.5 l	07/00→05/06					KH10221 ProKIT	
								-> 10/04	
<b>PROTON - WIRA Hatchback (C9_C, C9_S)</b>								<b>01/94→07/00</b>	
413 GLSi	55 kW	1.3 l	01/94→01/00					KH10221 ProKIT	
								KH20194 ProKIT	
415 GLi/GLSi	66 kW	1.5 l	01/94→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
416 GLXi	83 kW	1.6 l	01/94→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
416 i	70 kW	1.6 l	12/95→07/00					KH20194 ProKIT	
418 GLXi	85 kW	1.8 l	05/96→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
420 D	60 kW	2 l	09/96→07/00					KH10221 ProKIT	
								KH20194 ProKIT	
420 GLS D	48 kW	2 l	05/96→04/99					KH10221 ProKIT	
								KH20194 ProKIT	
<b>PROTON - WIRA Hatchback / WIRA Sedan (C9_L)</b>								<b>08/00→</b>	
1.3	55 kW	1.3 l	08/00→					KH10221 ProKIT	
1.3	55 kW	1.3 l	08/00→06/07					-> 10/04	
1.5	64 kW	1.5 l	08/00→						

					
<b>RELIANT - REBEL</b>					<b>01/68→08/71</b>
700	23 kW	0.7 l	01/68→08/71		<b>KH00124</b> ProKIT
<b>RELIANT - SCIMITAR Cabriolet / SCIMITAR Station Wagon</b>					<b>01/68→12/86</b>
2.8 GTC	99 kW	2.8 l	01/80→12/85		<b>KH00124</b> ProKIT
2.8 GTE	99 kW	2.8 l	01/80→12/86		
3.0 GTE	99 kW	3 l	01/68→12/79		



















































											
<b>RENAULT - 4 (112_)</b>										<b>10/62→06/90</b>	
0.8 (1123)	19 kW	0.8 l	10/62→09/83		-> 12/82; VIN 1785388, 239821, 32708, 501246 ->					KH00092 ProKIT	
					VIN 1785387, 32707, 501245					KH00092 ProKIT	
0.8 (1123)	21 kW	0.8 l	10/83→10/88		VIN 1785388, 32708 ->					KH00032 ProKIT	
0.8 (1123)	25 kW	0.8 l	09/71→12/88		01/75 -> 12/86; VIN 1785388, 239821, 32708, 501246 ->					KH00092 ProKIT	
					VIN 1785387, 32707, 501245					KH00032 ProKIT	
1.1	32 kW	1.1 l	06/86→06/90		01/87 -> 12/88					KH00092 ProKIT	
1.1 (1128, S128)	25 kW	1.1 l	06/78→06/90		01/82 -> 12/88; VIN 1785388, 239821, 32708, 501246 ->					KH00092 ProKIT	
										KH00032 ProKIT	
<b>RENAULT - 4 Box Body/MPV (R21_, R23_)</b>										<b>09/66→07/89</b>	
0.8 (2106)	25 kW	0.8 l	09/66→12/88		01/75 -> 12/86; VIN 1785388, 239821, 32708, 501246 ->					KH00092 ProKIT	
					VIN 1785387, 32707, 501245					KH00032 ProKIT	
					12/77 ->					KH00032 ProKIT	
0.8 (2391)	21 kW	0.8 l	04/83→07/89		01/87 -> 12/88; VIN 1785388, 32708 ->					KH00092 ProKIT	
1.1 (2370, 210B)	25 kW	1.1 l	10/76→07/89		01/77 -> 12/88; VIN 1785388, 239821, 32708, 501246 ->					KH00092 ProKIT	
					VIN 1785387, 32707, 501245					KH00032 ProKIT	
					12/77 ->					KH00032 ProKIT	
1.1 (239B)	26 kW	1.1 l	07/82→05/89		01/87 -> 12/88; VIN 1785388, 32708 ->					KH00092 ProKIT	
										KH00032 ProKIT	
<b>RENAULT - 5 (122_)</b>										<b>01/72→12/85</b>	
0.8 (1221, 1391)	27 kW	0.8 l	01/82→12/84		VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					VIN 69657 ->					KH00032 ProKIT	
1.0 (1222, 1392)	32 kW	1 l	01/72→12/85		01/77 -> 12/84; VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					01/78 -> 12/81; VIN 1771 ->					KH00090 ProKIT	
					12/77 ->; VIN 800359 ->					KH00032 ProKIT	
1.1 (1227, 1397)	33 kW	1.1 l	09/80→12/85		01/81 -> 12/84; VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					-> 12/81; VIN 1771 ->					KH00090 ProKIT	
										KH00032 ProKIT	
1.3 (1224, 1394)	47 kW	1.3 l	09/75→09/84		01/77 ->; VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					01/78 -> 12/81; VIN 1771 ->					KH00090 ProKIT	
					12/77 ->; VIN 143615 ->					KH00032 ProKIT	
1.3 (1225, 1395)	33 kW	1.3 l	06/79→09/84		01/80 ->; VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					-> 12/81; VIN 1771 ->					KH00090 ProKIT	
										KH00032 ProKIT	
1.3 (1225)	31 kW	1.3 l	09/76→09/79		VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
					VIN 1771 ->					KH00090 ProKIT	
					12/77 ->; VIN 45781 ->					KH00032 ProKIT	
1.3 Automatik (1225, 1395)	40 kW	1.3 l	06/79→09/84							KH00032 ProKIT	
1.4 Alpine A5 (1223)	68 kW	1.4 l	09/77→09/81								
1.4 Automatik (1229, 1399)	43 kW	1.4 l	06/82→09/84								
1.4 (1229, 1399)	46 kW	1.4 l	01/82→12/85		-> 12/84; VIN 115055, 143615, 45781, 69658, 800359 ->					KH00092 ProKIT	
										KH00032 ProKIT	
1.4 Alpine Turbo (122B)	79 kW	1.4 l	10/81→01/85		01/82 -> 12/84					KH00090 ProKIT	
										KH00032 ProKIT	
<b>RENAULT - 6 (118_)</b>										<b>07/71→04/80</b>	
1.1	35 kW	1.1 l	07/71→04/80		10/75 -> 12/79; VIN 565498, 586728 ->					KH00092 ProKIT	
					12/77 ->					KH00032 ProKIT	
<b>RENAULT - 9 Sedan (L42_)</b>										<b>09/81→12/89</b>	
1.1 (L421)	35 kW	1.1 l	09/81→05/87							KH10075 ProKIT	
1.2 (L42S)	40 kW	1.2 l	09/85→12/88							KH10073 ProKIT	
1.4	43 kW	1.4 l	07/86→10/87								
1.4	44 kW	1.4 l	06/87→04/89								
1.4 (L422, L42C)	44 kW	1.4 l	12/81→12/88								
1.4 (L423, L42R)	49 kW	1.4 l	09/85→12/88								
1.4 (L423)	53 kW	1.4 l	09/81→12/85								



												
<b>RENAULT - 9 Sedan (L42_)</b>											<b>09/81→12/89</b>	
1.4 Automatik (L423)	50 kW	1.4 l	09/81→12/85									KH10075 ProKIT
1.4 Turbo	85 kW	1.4 l	12/86→12/89									KH10073 ProKIT
1.4 Turbo	87 kW	1.4 l	07/86→12/89									
1.4 Turbo (L425)	77 kW	1.4 l	04/84→12/86									
1.6 D (L424)	40 kW	1.6 l	10/82→12/88									
1.7 (L426)	59 kW	1.7 l	09/84→12/89									
1.7 (L42E)	69 kW	1.7 l	06/87→12/88									
1.7 (L42F)	54 kW	1.7 l	10/86→12/88									
1.7 (L42L)	55 kW	1.7 l	10/86→12/88									
1.7 (L42N)	65 kW	1.7 l	10/86→12/88									
<b>RENAULT - 11 (B/C37_)</b>											<b>03/83→12/88</b>	
1.1 (B/C371)	35 kW	1.1 l	03/83→06/86									KH10075 ProKIT
1.2 (B37S, C375)	40 kW	1.2 l	10/84→12/88									KH10073 ProKIT
1.4	43 kW	1.4 l	07/86→10/87									
1.4 (B/C372, B/C37C)	44 kW	1.4 l	03/83→12/88									
1.4 (B/C373, B/C37R)	49 kW	1.4 l	03/83→12/88									
1.4 (B/C373)	50 kW	1.4 l	03/83→12/85									
1.4 (B/C373)	53 kW	1.4 l	05/83→12/85									
1.4 Turbo	87 kW	1.4 l	02/84→06/86									
1.4 Turbo (B/C375)	77 kW	1.4 l	04/84→12/86									
1.4 Turbo (B/C375)	85 kW	1.4 l	10/86→12/88									
1.6 D (B/C374)	40 kW	1.6 l	08/83→12/88									
1.7 (B/C376)	59 kW	1.7 l	10/83→12/87									
1.7 (B/C37D)	64 kW	1.7 l	06/87→12/88									
1.7 (B/C37E)	69 kW	1.7 l	06/87→12/88									
1.7 (B/C37F)	55 kW	1.7 l	10/84→12/88									
1.7 (B/C37L)	54 kW	1.7 l	10/86→12/88									
1.7 (B37N, C73N)	65 kW	1.7 l	10/86→12/88									
<b>RENAULT - 11 Hatchback Van (S37_)</b>											<b>03/83→12/88</b>	
1.1 (S371)	35 kW	1.1 l	03/83→06/86									KH10073 ProKIT
1.2 (S37S)	40 kW	1.2 l	10/84→12/88									
1.4 (S372)	44 kW	1.4 l	03/83→09/86									
1.4 (S373)	50 kW	1.4 l	03/83→12/86									
1.6 D (S374)	40 kW	1.6 l	08/83→12/88									
<b>RENAULT - 14 (121_)</b>											<b>05/76→12/83</b>	
1.2 (1210)	42 kW	1.2 l	05/76→01/80									KH00032 ProKIT
1.2 (1210)	43 kW	1.2 l	01/80→12/83									
1.4 (1212)	52 kW	1.4 l	09/79→06/83									
1.4 (1213)	44 kW	1.4 l	12/81→12/83									
<b>RENAULT - 15 (130_)</b>											<b>03/72→10/80</b>	
1.3 (1300)	44 kW	1.3 l	03/72→10/80									KH00032 ProKIT
1.6 (1302)	66 kW	1.6 l	03/72→10/80									KH00032 ProKIT
												-> 12/76; AT
<b>RENAULT - 16 (115_)</b>											<b>09/68→08/80</b>	
1.6 TA	52 kW	1.6 l	01/69→08/80									KH00032 ProKIT
1.6 TL	40 kW	1.6 l	07/75→08/80									
1.6 TL (1152, 1153, 1157)	48 kW	1.6 l	01/71→08/80									
1.6 TS (1151, 1154)	61 kW	1.6 l	09/68→08/80									
1.6 TX (1156)	68 kW	1.6 l	06/74→08/80									KH00032 ProKIT
<b>RENAULT - 17</b>											<b>03/72→10/80</b>	
1.6	66 kW	1.6 l	03/72→10/80									KH00090 ProKIT
<b>RENAULT - 18 Estate Van / 18 Sedan / 18 Variable (134_, 135_)</b>											<b>04/78→11/93</b>	
1.4	47 kW	1.4 l	05/79→07/86									KH20036 ProKIT
1.6	52 kW	1.6 l	08/86→11/93									
1.6	82 kW	1.6 l	10/83→09/86									
1.6 Turbo (1355)	80 kW	1.6 l	09/82→07/86									
1.6 Turbo Inj.	82 kW	1.6 l	09/82→07/86									
2.1 Diesel	49 kW	2.1 l	11/81→07/86									
2.1 Diesel	53 kW	2.1 l	05/79→07/86									
1.4 (1340)	47 kW	1.4 l	04/78→07/86									KH00090 ProKIT
												KH20075 ProKIT
												KH10370 ProKIT
												KH00032 ProKIT



										
<b>RENAULT - 18 Estate Van / 18 Sedan / 18 Variable (134_, 135_)</b>								<b>04/78→11/93</b>		
1.4 (1350)	47 kW	1.4 l	05/79→07/86	 ; 01/81 -> 12/83; VIN -> 504400, 534400	KH00090 ProKIT					
				 ; 01/81 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 ; 01/82 ->	KH10370 ProKIT					
1.6 (1341)	54 kW	1.6 l	04/82→07/86	 (ABS)	KH20036 ProKIT					
				 ; 10/82 ->	KH10370 ProKIT					
				 ; 01/83 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
1.6 (1341)	58 kW	1.6 l	04/78→09/82	 ; -> 12/83; VIN -> 504400, 534400	KH00090 ProKIT					
				 ; VIN -> 504400, 534400	KH00032 ProKIT					
				 ; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
1.6 (1341)	58 kW	1.6 l	04/78→09/82	 ; VIN -> 504400, 534400	KH00090 ProKIT					
				 ; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 ; 10/82 ->	KH10370 ProKIT					
1.6 (1351)	54 kW	1.6 l	01/82→07/86	 ; 01/83 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 ; -> 12/83; VIN -> 504400, 534400	KH00090 ProKIT					
				 (ABS)	KH20036 ProKIT					
1.6 (1351)	58 kW	1.6 l	05/79→09/82	 ; VIN -> 504400, 534400	KH00090 ProKIT					
				 ; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 (ABS)	KH20036 ProKIT					
1.6 4x4	54 kW	1.6 l	01/83→07/86		KH10370 ProKIT					
1.6 TS	71 kW	1.6 l	05/82→07/86		KH20075 ProKIT					
1.6 TS (1342)	71 kW	1.6 l	05/82→07/86	 ; 10/82 ->	KH10370 ProKIT					
1.6 Turbo	92 kW	1.6 l	10/82→07/86		KH10370 ProKIT					
				 (ABS)	KH20036 ProKIT					
2.1 Diesel (1354)	49 kW	2.1 l	11/80→07/86		KH20036 ProKIT					
2.1 TD	65 kW	2.1 l	11/81→07/86		KH20036 ProKIT					
1.6 Turbo (1345)	80 kW	1.6 l	10/80→09/82		KH10370 ProKIT					
1.6 Turbo (1345)	92 kW	1.6 l	10/82→07/86	 (ABS)	KH20036 ProKIT					
				 ; VIN -> 495669	KH00032 ProKIT					
				 ; VIN -> 49569	KH10370 ProKIT					
2.0 (1343)	77 kW	2 l	05/82→07/86	 ; 01/83 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 ; -> 12/83; VIN -> 504400, 534400	KH00090 ProKIT					
					KH10370 ProKIT					
2.0 (1353)	77 kW	2 l	10/81→07/86	 (ABS)	KH20036 ProKIT					
				 ; 01/82 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 1010, 11001, 118200, 122600, 4600, 49569, 5000, 50000, 9000	KH20075 ProKIT					
				 ; -> 12/83; VIN -> 504400, 534400	KH00090 ProKIT					
2.0 4x4	76 kW	2 l	05/83→12/86		KH10370 ProKIT					
				 (ABS)	KH20036 ProKIT					
				 ; 01/84 -> 12/85; VIN 1011, 11002, 118201, 122601, 4601, 49570, 50001, 5001, 504401, 534401, 9001 -> VIN 11001, 118200, 122600, 5000, 9000	KH20075 ProKIT					
2.1 Diesel	53 kW	2.1 l	11/81→07/86		KH10370 ProKIT					
2.1 Diesel (1344)	49 kW	2.1 l	11/81→07/86		KH00032 ProKIT					
<b>RENAULT - 19 I (B/C53_)</b>								<b>01/88→09/94</b>		
1.2	40 kW	1.2 l	01/88→12/92	 ;  ; (ABS)	KH10073 ProKIT					
1.4	59 kW	1.4 l	01/88→12/92							



**RENAULT - 19 I (B/C53\_) 01/88→09/94**

1.4 (B/C53P)	43 kW	1.4 l	01/89→05/93		KH10074 ProKIT
1.4 Cat (B/C532)	43 kW	1.4 l	01/89→04/92		
1.7	68 kW	1.7 l	09/88→04/92		
1.7	69 kW	1.7 l	07/88→04/92		
1.7	79 kW	1.7 l	06/89→04/92		
1.7 (B/C53B)	54 kW	1.7 l	09/88→04/92		
1.7 (B/C53C)	66 kW	1.7 l	09/88→04/92		
1.8	67 kW	1.8 l	05/92→09/94		
1.8 16V	101 kW	1.8 l	06/89→04/92		
1.8 16V (B/C53D)	99 kW	1.8 l	06/89→04/92		
1.9 D (B/C534, B/C53J)	47 kW	1.9 l	09/88→04/92		
1.9 DT	66 kW	1.9 l	09/90→04/92		
1.9 DT	68 kW	1.9 l	09/90→04/92		

**RENAULT - 19 I Cabriolet / 19 I Chamade / 19 I Hatchback Van / 19 II / 19 II Cabriolet / 19 II Chamade / 19 II Hatchback Van (D53\_, L53\_, S53\_, B/C53\_, D53\_, 853\_) 01/88→06/01**

1.2	40 kW	1.2 l	01/88→12/92		KH10073 ProKIT
1.2	40 kW	1.2 l	03/92→12/95		KH10074 ProKIT
1.2	40 kW	1.2 l	04/92→12/95		
1.2	44 kW	1.2 l	05/92→09/94		
1.4	44 kW	1.4 l	05/92→09/94		
1.4	55 kW	1.4 l	09/90→04/92		
1.4	57 kW	1.4 l	07/88→08/90		
1.4	57 kW	1.4 l	05/93→12/98		
1.4	57 kW	1.4 l	10/94→11/95		
1.4	58 kW	1.4 l	06/89→08/90		
1.4	59 kW	1.4 l	01/92→12/95		
1.4	59 kW	1.4 l	10/94→11/95		
1.4	60 kW	1.4 l	10/96→06/01		
1.4 (B/C532)	43 kW	1.4 l	04/92→12/95		
1.4 (B/C535)	55 kW	1.4 l	01/92→12/95		
1.4 (L535)	55 kW	1.4 l	11/93→12/95		
1.7	69 kW	1.7 l	10/96→06/01		
1.7	79 kW	1.7 l	05/92→09/94		
1.7 (B/C53B)	54 kW	1.7 l	04/92→12/95		
1.7 (B/C53C)	66 kW	1.7 l	04/92→12/95		
1.8 (5/353A)	66 kW	1.8 l	04/92→12/95		
1.8 (5/353F, B/C538)	79 kW	1.8 l	05/94→12/95		
1.8 (B/C538)	81 kW	1.8 l	04/92→05/94		
1.8 (B/C53Y)	65 kW	1.8 l	04/92→12/95		
1.8 16V (B/C53D)	99 kW	1.8 l	04/92→12/95		
1.9 D	48 kW	1.9 l	01/88→12/92		
1.9 D	48 kW	1.9 l	03/92→12/95		
1.9 D (B/C53J)	47 kW	1.9 l	04/92→12/95		
1.9 dT	68 kW	1.9 l	03/92→12/95		
1.9 dT (B/C53T)	66 kW	1.9 l	04/92→12/95		
1.2	40 kW	1.2 l	01/88→12/92		KH10057 ProKIT
1.4	59 kW	1.4 l	01/88→12/92		KH10073 ProKIT
1.4	59 kW	1.4 l	03/92→12/95		KH10074 ProKIT
1.4 (532)	43 kW	1.4 l	04/92→12/95		KH10074 ProKIT
1.4 (L532, L53P)	43 kW	1.4 l	07/88→04/92		
1.7	55 kW	1.7 l	07/91→04/92		
1.7	55 kW	1.7 l	05/92→11/95		
1.7	66 kW	1.7 l	07/91→04/92		
1.7	69 kW	1.7 l	09/90→04/92		
1.7	70 kW	1.7 l	07/91→04/92		
1.7 (D53C)	66 kW	1.7 l	04/92→09/93		
1.7 (L533)	68 kW	1.7 l	09/88→12/92		
1.7 (L533)	68 kW	1.7 l	01/93→08/95		
1.7 (L53B)	54 kW	1.7 l	10/89→04/92		
1.7 (L53B)	54 kW	1.7 l	04/92→12/95		
1.7 (L53C)	66 kW	1.7 l	07/88→04/92		
1.7 (L53C)	66 kW	1.7 l	04/92→12/95		
1.7 (L53F)	79 kW	1.7 l	08/88→12/92		
1.8	67 kW	1.8 l	05/92→09/94		
1.8	79 kW	1.8 l	05/92→11/95		
1.8	86 kW	1.8 l	01/95→06/01		
1.8 (453A/F)	66 kW	1.8 l	04/92→12/95		
1.8 (853A)	66 kW	1.8 l	09/93→06/96		
1.8 (D53V, 853F, D53C)	79 kW	1.8 l	07/94→06/96		
1.8 (D53Y)	65 kW	1.8 l	04/92→06/96		
1.8 (L538)	81 kW	1.8 l	04/92→05/94		
1.8 (L53V, L538)	79 kW	1.8 l	05/94→12/95		
1.8 (L53Y)	65 kW	1.8 l	04/92→12/95		
1.8 16V	101 kW	1.8 l	06/89→08/90		
1.8 16V (D53D)	99 kW	1.8 l	04/92→06/96		
1.8 16V (D53D)	101 kW	1.8 l	07/91→04/92		
1.8 16V (D53D)	101 kW	1.8 l	05/92→04/94		
1.8 16V (L53D)	99 kW	1.8 l	10/89→04/92		



**RENAULT - 19 I Cabriolet / 19 I Chamade / 19 I Hatchback Van / 19 II / 19 II 01/88→06/01**  
**Cabriolet / 19 II Chamade / 19 II Hatchback Van (D53\_, L53\_, S53\_, B/C53\_, D53\_, 853\_)**








1.8 16V (L53D)	99 kW	1.8 l	04/92→12/95		KH10057 ProKIT
1.9 D	68 kW	1.9 l	05/92→11/95		KH10073 ProKIT
1.9 D (L534, L53J)	47 kW	1.9 l	10/89→04/92		KH10074 ProKIT
1.9 D (L53J)	47 kW	1.9 l	04/92→12/95		KH10074 ProKIT
1.9 DT	66 kW	1.9 l	09/90→04/92		
1.9 dT (L53T)	66 kW	1.9 l	04/92→12/95		
1.9 TD (L53K)	68 kW	1.9 l	09/90→04/92		

**RENAULT - 20 (127\_) 10/75→12/83**

1.6 (1271)	66 kW	1.6 l	10/75→05/77		KH00090 ProKIT
1.6 (1271)	71 kW	1.6 l	05/77→12/83		KH10405 ProKIT
2.0 (1272)	80 kW	2 l	10/77→10/80		KH20075 ProKIT
2.2 (1279)	85 kW	2.2 l	10/80→12/83		KH20075 ProKIT
2.0 (1277)	76 kW	2 l	10/80→12/83		KH00090 ProKIT
					KH10370 ProKIT
					KH10405 ProKIT
					KH20075 ProKIT
2.1 Diesel (1276)	47 kW	2.1 l	10/80→12/83		KH10370 ProKIT
2.1 TD	63 kW	2.1 l	01/82→12/83		KH10370 ProKIT
					KH20075 ProKIT











**RENAULT - 21 / 21 Estate / 21 Saloon (B48\_, K48\_, L48\_) 03/86→09/95**

1.7 (B48E)	66 kW	1.7 l	09/89→06/94		KH20075 ProKIT
1.7 (L48E)	66 kW	1.7 l	09/89→02/94		KH20075 ProKIT
1.7 (B48F)	54 kW	1.7 l	09/89→10/92		KH20075 ProKIT
1.7 (L481)	55 kW	1.7 l	03/86→12/87		
1.7 (K/S481)	55 kW	1.7 l	06/86→03/93		KH20075 ProKIT
1.7 (K48E)	69 kW	1.7 l	06/86→12/89		KH20036 ProKIT
1.7 (K48M)	54 kW	1.7 l	06/86→12/89		KH20036 ProKIT
1.7 (K/S482)	65 kW	1.7 l	10/86→12/88		KH20075 ProKIT
1.7 (K48E)	66 kW	1.7 l	10/89→12/93		KH20036 ProKIT
1.7 (K48N)	64 kW	1.7 l	06/87→04/89		KH20075 ProKIT
1.7 Cat (K48F)	54 kW	1.7 l	05/88→06/93		KH20036 ProKIT
1.7 (L482)	65 kW	1.7 l	03/86→03/93		KH20075 ProKIT
1.7 (L48E)	69 kW	1.7 l	03/86→02/94		KH20075 ProKIT
1.7 (L48M, L48F)	54 kW	1.7 l	07/86→02/94		KH20075 ProKIT
1.7 (L48N)	64 kW	1.7 l	06/87→04/89		KH20075 ProKIT
1.9 D	47 kW	1.9 l	03/86→08/94		KH10370 ProKIT
2.1 D (K/S486)	48 kW	2.1 l	10/86→09/90		KH20036 ProKIT
2.1 D (K/S48V, K/S48O)	53 kW	2.1 l	08/89→12/92		KH20036 ProKIT
2.1 D (K480)	51 kW	2.1 l	02/92→09/95		
1.9 D (L48H, L48I)	47 kW	1.9 l	08/89→10/93		KH10370 ProKIT
2.0 Turbo (L485)	129 kW	2 l	04/87→03/90		
2.0 Turbo (L48L)	119 kW	2 l	02/90→10/92		
2.0 Turbo 4x4	129 kW	2 l	08/89→10/93		
2.0 Turbo 4x4 (L48L)	119 kW	2 l	02/90→10/92		
2.1 D (B480)	51 kW	2.1 l	04/92→06/94		
2.1 D (B48V/B48O)	53 kW	2.1 l	09/89→12/92		
2.1 D (L480)	51 kW	2.1 l	10/92→06/94		
2.1 D (L486)	48 kW	2.1 l	03/86→12/89		
2.1 D (L48V, L48O)	53 kW	2.1 l	05/89→06/94		
2.1 D 4x4 (K486)	48 kW	2.1 l	10/88→05/92		
2.0	75 kW	2 l	06/91→05/93		KH20036 ProKIT
2.0	86 kW	2 l	07/89→06/92		
2.0 (K48C)	88 kW	2 l	03/86→12/93		
2.0	78 kW	2 l	05/91→10/93		KH10370 ProKIT
2.0 (B48R/Y)	99 kW	2 l	02/90→10/92		KH20075 ProKIT
2.0 (L483)	85 kW	2 l	03/86→12/88		
2.0 4x4 (B48R/Y)	99 kW	2 l	09/90→10/92		
2.0 (K483)	85 kW	2 l	06/86→12/88		KH10370 ProKIT
					KH20075 ProKIT
					KH20036 ProKIT
2.0 (K48R)	99 kW	2 l	06/90→02/94		KH20075 ProKIT
					KH10370 ProKIT
					KH20036 ProKIT
2.0 (L48C)	88 kW	2 l	03/86→12/93		KH20075 ProKIT
					KH10370 ProKIT















































      					
RENAULT - 21 / 21 Estate / 21 Saloon (B48_, K48_, L48_)				03/86→09/95	
2.0 (L48R)	99 kW	2 l	02/90→06/94		KH20075 ProKIT
2.0 4x4 (L48R)	99 kW	2 l	12/89→02/94		KH10370 ProKIT
2.1 Turbo-D (B486, B488, B48V)	65 kW	2.1 l	09/89→06/94		
2.2 (B48K)	79 kW	2.2 l	09/89→06/94		
2.2 4x4 (B48K)	79 kW	2.2 l	07/90→06/94		
2.2 4x4 (L48K)	79 kW	2.2 l	07/90→02/94		
2.1 Turbo-D (K48A, K48W, K487, K488)	65 kW	2.1 l	10/86→11/93	; 01/89 ->	KH20075 ProKIT
					KH10370 ProKIT
				(ABS)	KH20036 ProKIT
2.1 Turbo-D (L48A, L48W, L487, L488)	65 kW	2.1 l	03/86→06/94	; 01/89 -> 12/93	KH20075 ProKIT
					KH10370 ProKIT
2.2 (K48K)	79 kW	2.2 l	06/86→11/93	; 01/87 ->	KH20075 ProKIT
					KH10370 ProKIT
				(ABS)	KH20036 ProKIT
2.2 (L48K)	79 kW	2.2 l	07/86→02/94	; 01/87 -> 12/93	KH20075 ProKIT
					KH10370 ProKIT
2.2 4x4 (K48K)	79 kW	2.2 l	06/86→12/93	; 01/89 ->	KH20075 ProKIT
					KH10370 ProKIT
RENAULT - 25 (B29_)				04/84→12/93	
2.0	88 kW	2 l	03/87→12/93		KH20036 ProKIT
2.0 (B297)	74 kW	2 l	04/84→12/92	; 01/89 -> 12/90; (ABS), (ABS)	KH20075 ProKIT
					KH10370 ProKIT
				(ABS)	KH20036 ProKIT
2.0 12V	103 kW	2 l	06/88→12/93		KH10370 ProKIT
2.0 12V (B294)	99 kW	2 l	06/89→12/92		
2.1 Turbo-D FWD (B290, B29W)	63 kW	2.1 l	04/84→12/92	(ABS)	KH20036 ProKIT
2.1 Diesel (B296)	46 kW	2.1 l	04/84→05/89		KH10370 ProKIT
				(ABS), (ABS)	KH20075 ProKIT
				(ABS)	KH20036 ProKIT
2.1 Diesel (B296)	51 kW	2.1 l	06/89→12/92	; -> 12/90; (ABS), (ABS)	KH20075 ProKIT
					KH10370 ProKIT
				(ABS)	KH20036 ProKIT
2.2 (B29)	76 kW	2.2 l	11/85→03/89		KH10370 ProKIT
2.2 (B29E)	89 kW	2.2 l	04/84→12/89		KH20075 ProKIT
2.2 (B29E)	91 kW	2.2 l	04/84→12/89	(ABS)	KH20036 ProKIT
2.2 (B29B)	79 kW	2.2 l	09/86→12/92	; 06/87 -> 12/90; (ABS), (ABS)	KH20075 ProKIT
					KH10370 ProKIT
				(ABS)	KH20036 ProKIT
2.4 V6 Turbo (B295)	133 kW	2.4 l	10/84→05/90		KH10370 ProKIT
2.5 V6 Turbo (B29G)	151 kW	2.5 l	01/90→12/92		
2.7 V6 Injection (B298)	104 kW	2.7 l	04/84→08/89		
2.8 V6 Injection (B29A)	100 kW	2.8 l	06/86→02/88		
2.8 V6 Injection (B29F)	110 kW	2.8 l	06/87→12/92		
2.8 V6 (B293)	115 kW	2.8 l	06/87→02/90		KH10370 ProKIT
				(ABS), (ABS)	KH20075 ProKIT
RENAULT - 30 (127_)				02/82→03/86	
2.1 Turbo-D (1270)	63 kW	2.1 l	02/82→03/86		KH10370 ProKIT
RENAULT - AVANTIME (DE0_)				09/01→05/03	
2.0 16V Turbo (DE0U, DE0V)	120 kW	2 l	11/01→05/03	; Code: DE0U, DE0V, JE0A, JE0L, JE0N	KH10393 ProKIT
				; Code: DE0U, DE0V, JE0A, JE0L, JE0N	KH20116 ProKIT
2.2 dCi (DE01)	110 kW	2.2 l	05/02→05/03	; Code: DE01, JE0E, JE0H, JE0K, JE0P, JE0S	KH10393 ProKIT
				; Code: DE01, JE0E, JE0H, JE0K, JE0S	KH20116 ProKIT
3.0 V6 (DE04, DE0T)	152 kW	3 l	09/01→05/03	; Code: DE04, DE0T, JE0D, JE0G	KH10393 ProKIT
				; Code: JE0D, JE0G, JE0P, DE04, DE0T	KH20116 ProKIT
RENAULT - CAPTUR I (J5_, H5_)				06/13→	
0.9 TCe 90	66 kW	0.9 l	06/13→		KH10013 ProKIT
					KH10142 ProKIT
1.2 TCe 120	88 kW	1.2 l	06/13→		KH10184 ProKIT
1.5 dCi 90	66 kW	1.5 l	06/13→		KH10142 ProKIT
1.5 dCi 110	81 kW	1.5 l	01/15→		KH10184 ProKIT





























				13		i	
RENAULT - CLIO I / CLIO I Hatchback Van (B/C57_, 5/357_, S57_) 05/90→09/98							
1.1	34 kW	1.1 l	01/91→09/98		ABS; Outer diameter 1 [mm]: 65	KH10075 ProKIT	
1.1	36 kW	1.1 l	04/92→08/92		ABS	KH10073 ProKIT	
1.2	40 kW	1.2 l	01/91→09/98		ABS	KH10074 ProKIT	
1.2	40 kW	1.2 l	06/94→02/98		not for code: MCV; ABS	KH10074 ProKIT	
1.2	44 kW	1.2 l	01/91→09/98				
1.9 D	40 kW	1.9 l	01/97→09/98				
Electric	21 kW		05/96→02/98				
Williams (B/C57M)	108 kW	2 l	01/94→09/98				
1.2 (5/357Y, 5/357K)	40 kW	1.2 l	01/96→09/98		ABS; Outer diameter 1 [mm]: 72	KH10057 ProKIT	
1.2 (5/357Y, 5/357K)	43 kW	1.2 l	01/96→09/98		ABS; Outer diameter 1 [mm]: 65	KH10075 ProKIT	
1.2 (B/C/S572)	44 kW	1.2 l	05/90→03/96		ABS	KH10073 ProKIT	
1.2 (B/C/S577)	40 kW	1.2 l	01/96→12/96		ABS	KH10074 ProKIT	
1.2 (B/C/S57A, B/C57S, 5/357F, 5/357J, 5/357L, 5/357R)	43 kW	1.2 l	05/90→09/98		not for code: MCV; ABS	KH10074 ProKIT	
1.2 (B/C57R, B575, B57A)	40 kW	1.2 l	01/91→06/96				
1.4	57 kW	1.4 l	05/90→02/98				
1.4	59 kW	1.4 l	01/91→09/98				
1.4 (B/C57T, B/C57Y)	58 kW	1.4 l	01/91→09/98				
1.4 (B57J, C57J, B57P)	55 kW	1.4 l	01/91→09/98				
1.7 (B/C574)	68 kW	1.7 l	01/91→12/93				
1.8	70 kW	1.8 l	01/91→09/98				
1.8 (B/C57C, B/C57U)	65 kW	1.8 l	01/91→09/98				
1.8 (B/C57C, C579, B/C57U)	66 kW	1.8 l	08/94→04/96				
1.8 16V (C57D)	99 kW	1.8 l	01/91→03/96				
1.8 Rsi (B/C579)	80 kW	1.8 l	01/93→08/95				
1.8 Rsi (B/C57H)	79 kW	1.8 l	08/95→09/98				
1.9 D	48 kW	1.9 l	01/91→09/98				
1.9 D	48 kW	1.9 l	05/96→02/98				
1.9 D (B/C/S576, B/C/S57L)	47 kW	1.9 l	01/91→09/98				
1.9 RND	40 kW	1.9 l	04/96→02/98				
RENAULT - CLIO II / CLIO II Hatchback Van (BB_, CB_, SB0/1/2_) 09/98→08/16							
1.0	40 kW	1 l	02/00→05/01		ABS	KH10075 ProKIT	
1.2 (BB0A, BB0F, BB10, BB1K, BB28, BB2D, BB2H, CB0A,...)	43 kW	1.2 l	09/98→02/10		ABS	KH10073 ProKIT	
1.2 LPG	43 kW	1.2 l	09/98→06/09		ABS	KH10074 ProKIT	
1.2 LPG (BB0A, CB0A)	44 kW	1.2 l	03/99→05/01				
1.0 Flex (CB32, CB3B, CB3V, CB3W, BB32, BB3B, BB3V,...)	57 kW	1 l	11/05→10/12			KH10075 ProKIT	
1.2 (SB0A, SB0F, SB10)	44 kW	1.2 l	03/99→10/03			KH10057 ProKIT	
1.2 (SB0A, SB0F, SB1K, SB2D)	43 kW	1.2 l	09/98→		ABS	KH10075 ProKIT	
					ABS	KH10073 ProKIT	
					ABS	KH10074 ProKIT	
1.2 16V (BB05, BB0W, BB11, BB27, BB2T, BB2U, BB2V, CB05,...)	55 kW	1.2 l	06/01→08/16		Outer diameter 1 [mm]: 72	KH10057 ProKIT	
1.6 (BB01, BB1J)	81 kW	1.6 l	11/04→02/09		Outer diameter 1 [mm]: 65	KH10075 ProKIT	
1.6 16V (BB01, BB0H, BB0T, BB14, BB1D, BB1R, BB2KL, BB3G...)	79 kW	1.6 l	09/98→04/05		ABS	KH10073 ProKIT	
1.6 Flex	81 kW	1.6 l	05/00→12/06		ABS	KH10074 ProKIT	
1.6 Hi-Flex (CB0H)	86 kW	1.6 l	01/05→02/10				
1.4 (B/CB0C, B/CB0S)	55 kW	1.4 l	09/98→05/05			KH10057 ProKIT	
1.4 16V (B/CB0L)	70 kW	1.4 l	10/99→09/04		ABS	KH10073 ProKIT	
1.4 16V (B/CB0P, BB13)	72 kW	1.4 l	02/00→07/08		ABS	KH10074 ProKIT	
1.5 dCi	42 kW	1.5 l	06/01→12/06		ABS	KH10074 ProKIT	
1.5 dCi	74 kW	1.5 l	10/03→04/05				
1.5 dCi (B/C2J)	50 kW	1.5 l	08/04→12/12				
1.5 dCi (B/CB03)	59 kW	1.5 l	06/01→10/03				
1.5 dCi (B/CB07)	48 kW	1.5 l	06/01→07/09				
1.5 dCi (B/CB08)	60 kW	1.5 l	06/01→04/05				
1.5 dCi (B/CB3M)	47 kW	1.5 l	06/05→12/10				
1.5 dCi (BB3N, CB3N)	62 kW	1.5 l	02/07→06/09				
1.6 (B/CB0D, BB00)	66 kW	1.6 l	09/98→05/05				
1.9 D (B/CB0E, BB0J)	47 kW	1.9 l	09/98→05/05				
1.9 D (B/CB0J)	48 kW	1.9 l	02/00→05/01				
1.9 D (SB0E)	47 kW	1.9 l	09/98→				
1.9 D (SB0J)	48 kW	1.9 l	02/00→05/01				
1.9 D (SB0R)	40 kW	1.9 l	03/99→01/00				
1.9 dTi (B/CB0U)	59 kW	1.9 l	12/99→05/05				
1.9 DTi (SB0U)	59 kW	1.9 l	02/00→05/01				
1.5 dCi	50 kW	1.5 l	04/04→		ABS	KH10073 ProKIT	
1.5 dCi	59 kW	1.5 l	06/01→10/04		ABS	KH10074 ProKIT	
1.5 dCi	60 kW	1.5 l	11/03→		ABS	KH10074 ProKIT	
1.5 dCi (SB07)	48 kW	1.5 l	06/01→				
1.6 (SB0H)	79 kW	1.6 l	11/03→				
3.0 V6 Sport (CB1A)	166 kW	3 l	11/00→12/02				
3.0 V6 Sport (CB1H, CB1U, CB2S)	187 kW	3 l	12/02→04/05				

												
<b>RENAULT - CLIO II / CLIO II Hatchback Van (BB_, CB_, SB0/1/2_)</b>											<b>09/98→08/16</b>	
2.0 16V Sport	132 kW	2 l	01/04→04/05		Outer diameter 1 [mm]: 72							KH10057 ProKIT
2.0 16V Sport (CB0M)	124 kW	2 l	02/00→06/09		Outer diameter 1 [mm]: 84; 							KH10150 ProKIT
					ABS							KH10073 ProKIT
					ABS							KH10074 ProKIT
<b>RENAULT - CLIO III (BR0/1, CR0/1)</b>											<b>05/05→12/14</b>	
1.2 (BR01, BR03, BR0E, CR0E)	57 kW	1.2 l	10/05→12/12									KH10380 ProKIT
1.2 16V	43 kW	1.2 l	06/06→08/10									KH10073 ProKIT
1.2 16V	58 kW	1.2 l	06/05→12/14									KH10073 ProKIT
1.2 16V	76 kW	1.2 l	09/10→12/14									KH10076 ProKIT
1.2 16V (BR02, BR0J, BR11, CR02, CR0J, CR11)	55 kW	1.2 l	06/05→12/14									
1.2 16V (BR0P, CR0P)	74 kW	1.2 l	05/07→12/14									
1.2 16V (BR0R, BR1D, BR1L, CR0R)	48 kW	1.2 l	06/05→12/14									
1.2 16V Hi-Flex (BR1U, CR1U)	55 kW	1.2 l	07/08→12/14									
1.2 Ethanol (CR1U, BR1U)	55 kW	1.2 l	07/08→12/12									
1.4 16V	72 kW	1.4 l	06/05→12/12									
1.5 dCi	47 kW	1.5 l	06/05→12/12		MTF							KH10380 ProKIT
1.5 dCi	48 kW	1.5 l	05/05→07/10									
1.5 dCi	55 kW	1.5 l	08/10→12/14									KH10073 ProKIT
1.5 dCi	60 kW	1.5 l	11/07→12/12									KH10076 ProKIT
1.5 dCi	65 kW	1.5 l	08/10→12/14									
1.5 dCi (BR0H, CR0H, CR1S, BR1S)	78 kW	1.5 l	06/05→12/14									
1.5 dCi (BR17, CR17)	63 kW	1.5 l	06/05→12/12									
1.5 dCi (BR1C, CR1C)	76 kW	1.5 l	06/05→12/12									
1.5 dCi (C/BR0G, C/BR1G)	50 kW	1.5 l	06/05→12/12									
1.6 16V (BR05, BR0B, BR0Y, BR15, BR1J, BR1M, BR1Y, CR0B, ...)	82 kW	1.6 l	06/05→12/14									
1.6 16V (BR09, BR0T, CR09, CR0T)	65 kW	1.6 l	06/05→10/07									
1.6 16V GT (BR10, CR10)	94 kW	1.6 l	06/09→12/14									
2.0 16V (BR0C, BR0K, CR0C, CR0K)	102 kW	2 l	09/06→12/14									KH10073 ProKIT
												KH10076 ProKIT
2.0 16V Sport	148 kW	2 l	09/08→12/14									KH10380 ProKIT
2.0 16V Sport (CR0N, CR1P)	145 kW	2 l	02/06→12/12									KH20066 ProKIT
												KH10073 ProKIT
<b>RENAULT - CLIO III Grandtour (KR0/1_)</b>											<b>11/07→12/14</b>	
1.2 16V	76 kW	1.2 l	03/10→12/12									KH10380 ProKIT
1.2 16V (KR02, KR0J)	55 kW	1.2 l	02/08→12/14									KH10077 ProKIT
1.2 16V (KR0E)	58 kW	1.2 l	11/07→12/14									KH10077 ProKIT
1.2 16V (KR0P)	74 kW	1.2 l	11/07→12/12									
1.2 16V Hi-Flex (KR0S)	55 kW	1.2 l	07/08→12/14									
1.4 16V	72 kW	1.4 l	11/07→12/12									
1.2 16V Hi-Flex (KR1U)	58 kW	1.2 l	11/07→12/12									KH10380 ProKIT
1.5 dCi	48 kW	1.5 l	11/07→12/12		MTF							KH10380 ProKIT
1.5 dCi	55 kW	1.5 l	08/10→12/12									KH10077 ProKIT
1.5 dCi	65 kW	1.5 l	08/10→12/12									KH10077 ProKIT
1.5 dCi (KR0F)	63 kW	1.5 l	11/07→12/12									
1.5 dCi (KR0G)	50 kW	1.5 l	11/07→12/12									
1.5 dCi (KR0H, KR1S)	78 kW	1.5 l	02/08→12/12									
1.5 dCi (KR1C, KR1N)	76 kW	1.5 l	11/07→12/12									
1.6 16V	80 kW	1.6 l	11/07→12/12									
1.6 16V (KR0B)	82 kW	1.6 l	11/07→12/12									
1.6 16V (KR10)	94 kW	1.6 l	11/07→12/12									
<b>RENAULT - CLIO III Hatchback Van (SB_, SR_)</b>											<b>06/05→12/14</b>	
1.2 (SR0J)	55 kW	1.2 l	11/05→12/14									KH10073 ProKIT
1.2 (SR0P)	74 kW	1.2 l	11/07→12/11									KH10076 ProKIT
1.5 dCi	50 kW	1.5 l	10/05→07/10									KH10076 ProKIT
1.5 dCi	55 kW	1.5 l	08/10→12/14									
1.5 dCi	63 kW	1.5 l	06/05→07/10									
1.5 dCi	78 kW	1.5 l	10/05→10/07									
1.5 dCi (SR1H)	65 kW	1.5 l	08/10→12/14									
<b>RENAULT - CLIO IV (BH_)</b>											<b>11/12→</b>	
0.9 TCe 90	66 kW	0.9 l	11/12→									KH10013 ProKIT
1.2 16V	54 kW	1.2 l	11/12→									
1.2 TCe 120 (BHAU)	87 kW	1.2 l	01/16→		OE 77 01 210 004; 							KH10077 ProKIT
1.2 TCe 120 (BHM0)	88 kW	1.2 l	03/13→									
1.5 dCi 110	81 kW	1.5 l	06/16→									
0.9 TCe 90 LPG	66 kW	0.9 l	06/16→		OE 77 01 210 004; 							KH10077 ProKIT
1.2 16V (BHA1, BHAK, BHMG, BHMK)	55 kW	1.2 l	06/15→									
1.2 LPG 16V	54 kW	1.2 l	11/12→06/15									



				    	
<b>RENAULT - CLIO IV (BH_)</b>				<b>11/12→</b>	
1.5 dCi 75	55 kW	1.5 l	11/12→		<b>KH10013</b> ProKIT
1.5 dCi 90	66 kW	1.5 l	11/12→	 ; OE 77 01 210 004; 	<b>KH10077</b> ProKIT
				 ; 	<b>KH10144</b> ProKIT
<b>RENAULT - CLIO IV Grandtour (KH_)</b>				<b>11/12→</b>	
0.9 TCe 90	66 kW	0.9 l	01/13→		<b>KH10013</b> ProKIT
1.2 16V	54 kW	1.2 l	01/13→	 ;  15, 16, 17 Inch	<b>KH10144</b> ProKIT
1.2 TCe 120 (KHAU)	87 kW	1.2 l	01/16→		<b>KH10013</b> ProKIT
1.5 dCi 110	81 kW	1.5 l	06/16→		
1.2 TCe 120 (KHM0)	88 kW	1.2 l	03/13→		<b>KH10013</b> ProKIT
1.5 dCi 75	55 kW	1.5 l	01/13→		<b>KH10144</b> ProKIT
1.5 dCi 90 (KHN3, KHN4)	66 kW	1.5 l	11/12→		
<b>RENAULT - DUSTER (HS_)</b>				<b>06/11→</b>	
1.5 dCi (HSAE, HSAD, HSAF, HSJ7, HSMC, HSMD)	80 kW	1.5 l	09/13→01/18		<b>KH10080</b> ProKIT
1.5 dCi 4x4	66 kW	1.5 l	06/11→		
1.5 dCi 4x4 (HSMD)	80 kW	1.5 l	09/13→01/18		
1.6 16V	84 kW	1.6 l	06/15→		
1.6 16V (HSAT)	75 kW	1.6 l	02/12→		
1.6 16V (HSAT)	77 kW	1.6 l	06/11→01/18		
1.6 16V 4x4	75 kW	1.6 l	06/11→05/15		
1.6 16V 4x4	84 kW	1.6 l	06/15→		
2.0	98 kW	2 l	02/12→		
2.0 4x4	99 kW	2 l	02/12→		
<b>RENAULT - ESPACE I / ESPACE II (J11_, J/S63_)</b>				<b>07/84→12/96</b>	
2.0 (J/S112)	74 kW	2 l	01/88→12/90		<b>KH10370</b> ProKIT
2.0 (J/S112)	80 kW	2 l	07/84→12/90	 ;  ; 	<b>KH20075</b> ProKIT
2.0 (J636)	76 kW	2 l	01/91→10/96	 ; 	<b>KH20036</b> ProKIT
2.2 (J/S637, J63G)	79 kW	2.2 l	01/91→10/96	 ; 	<b>KH20036</b> ProKIT
2.2 (J117)	79 kW	2.2 l	07/86→12/90		
2.0 i (J116)	87 kW	2 l	01/89→12/90		<b>KH10370</b> ProKIT
2.1 TD (J/S115)	65 kW	2.1 l	10/84→12/90	 ; 	<b>KH20036</b> ProKIT
2.1 TD (J633, J634, J/S635, J/S63D)	65 kW	2.1 l	01/91→10/96		
2.1 TD (J63E)	66 kW	2.1 l	11/94→10/96		
2.0 i Quadra (J116)	87 kW	2 l	03/88→12/92		<b>KH10370</b> ProKIT
2.2 Quadra (J117)	79 kW	2.2 l	01/88→12/90		
2.2 4x4 (J/S637, J63G)	79 kW	2.2 l	03/91→12/96		<b>KH10370</b> ProKIT
					<b>KH20075</b> ProKIT
2.8 V6 (J638, J63J)	110 kW	2.8 l	01/91→10/96	 ; 	<b>KH10370</b> ProKIT
					<b>KH20116</b> ProKIT
<b>RENAULT - ESPACE III (JE0_)</b>				<b>11/96→10/02</b>	
1.9 dTi (JE0M)	72 kW	1.9 l	02/99→10/02		<b>KH10393</b> ProKIT
2.0 (JE0A)	84 kW	2 l	11/96→10/00		<b>KH20116</b> ProKIT
2.2 12V TD (JE0E, JE0H, JE0P)	83 kW	2.2 l	11/96→10/00		
3.0 (JE0D)	123 kW	3 l	11/96→10/98		
2.0	102 kW	2 l	09/01→10/02	 ; Code: JE0A	<b>KH10393</b> ProKIT
				 ; Code: JE0A	<b>KH20116</b> ProKIT
2.0 16V (JE0N, JE0L, JE02)	103 kW	2 l	10/98→10/02	 ; Code: DE0U, DE0V, JE0L, JE0N	<b>KH10393</b> ProKIT
				 ; Code: DE0U, DE0V, JE0L, JE0N	<b>KH20116</b> ProKIT
2.2 dCi (JE0K)	95 kW	2.2 l	10/00→10/02	 ; Code: DE01, JE0K, JE0S	<b>KH10393</b> ProKIT
2.2 dCi (JE0S)	85 kW	2.2 l	07/00→10/02	 ; Code: DE01, JE0K, JE0S	<b>KH20116</b> ProKIT
3.0 V6 24V (JE0G, JE0R)	140 kW	3 l	10/98→10/02	 ; Code: DE04, DE0T, JE0G	<b>KH10393</b> ProKIT
				 ; Code: DE04, DE0T, JE0G	<b>KH20116</b> ProKIT
<b>RENAULT - ESPACE IV (JK0/1_)</b>				<b>11/02→</b>	
1.9 dCi (JK0U, JK0G)	88 kW	1.9 l	11/02→		<b>KH10115</b> ProKIT
1.9 dCi (JK0U)	85 kW	1.9 l	04/03→02/05		
2.0 (JK09)	100 kW	2 l	11/02→01/15		
2.0 (JK0A, JK1D, JK0N)	125 kW	2 l	04/05→		
2.0 (JK0K)	98 kW	2 l	11/02→12/15		
2.0 dCi (JK01, JK02, JK1J, JK1K, JK1H)	110 kW	2 l	01/06→		
2.0 dCi (JK02, JK03)	96 kW	2 l	01/06→		
2.0 dCi (JK03, JK04, JK1C, JK1G, JK1J, JK1K)	127 kW	2 l	01/06→		
2.0 Turbo (JK0A, JK0B, JK0N)	120 kW	2 l	11/02→		
2.2 dCi (JK07)	102 kW	2.2 l	02/06→		
2.2 dCi (JK0H)	110 kW	2.2 l	11/02→08/06		
3.0 dCi	120 kW	3 l	09/05→		
3.0 dCi (JK0E, JK0Y)	133 kW	3 l	01/06→01/15		



											
<b>RENAULT - ESPACE IV (JK0/1_)</b>										<b>11/02→</b>	
3.0 dCi (JK0J, JK0V)	130 kW	3 l	11/02→08/06								KH10115 ProKIT
3.5 V6 (JK00, JK0F, JK0P, JK0S, JK0W)	177 kW	3.5 l	11/02→								
<b>RENAULT - ESTAFETTE (213_)</b>										<b>08/69→12/81</b>	
1.3	29 kW	1.3 l	08/69→12/81		-> 12/77; VIN -> 96645, 155527				KH00129 ProKIT		
<b>RENAULT - EXPRESS Box Body/MPV</b>										<b>07/95→03/98</b>	
1.9 D	47 kW	1.9 l	07/95→03/98		ABS				KH10075 ProKIT		
<b>RENAULT - FLUENCE (L3_)</b>										<b>02/10→</b>	
1.5 dCi	70 kW	1.5 l	07/14→								KH10080 ProKIT
1.5 dCi (L30A)	63 kW	1.5 l	02/10→								
1.5 dCi (L30B)	78 kW	1.5 l	02/10→								
1.5 dCi (L30D, L30L, L306, L33F, L33L, L33M, L33V, L33W)	81 kW	1.5 l	02/10→								
1.5 dCi (L30S)	66 kW	1.5 l	02/10→								
1.6 (L33T, L33J, L304, L305, L30H)	86 kW	1.6 l	01/13→								
1.6 16V	78 kW	1.6 l	02/10→								
1.6 16V (L301, L30F, L30P, L30R)	81 kW	1.6 l	02/10→								
1.6 16V (L301, L30P, L30R)	82 kW	1.6 l	02/10→								
1.6 dCi	96 kW	1.6 l	07/14→								
1.6 LPG 16V	81 kW	1.6 l	01/12→								
2.0 16V (L30C, L30G, L30T, L30V)	103 kW	2 l	02/10→								
Z.E.	70 kW		02/12→								
<b>RENAULT - FUEGO (136_)</b>										<b>02/80→10/85</b>	
1.4 TL/GTL	47 kW	1.4 l	02/80→10/85								KH10370 ProKIT
											KH00032 ProKIT
1.6	52 kW	1.6 l	04/83→10/85								KH10370 ProKIT
					VIN 61220 -> VIN 61221				KH20075 ProKIT		
1.6 TS/GTS (1362)	71 kW	1.6 l	10/80→10/85								KH10370 ProKIT
1.6 Turbo (1365)	97 kW	1.6 l	08/83→10/85								
2.0 TX/GTX (1363)	81 kW	2 l	10/80→10/85		ABS				KH20036 ProKIT		
2.1 TD	65 kW	2.1 l	08/82→10/85								
<b>RENAULT - GRAND SCÉNIC II (JM0/1_)</b>										<b>04/04→06/09</b>	
1.5 dCi	76 kW	1.5 l	06/06→11/08						KH10104 ProKIT		
1.5 dCi (JM02, JM13)	74 kW	1.5 l	04/04→11/08								
1.5 dCi (JM1E)	78 kW	1.5 l	05/05→01/09								
1.6	77 kW	1.6 l	06/06→11/08								
1.6	82 kW	1.6 l	06/06→11/08								
1.6	83 kW	1.6 l	04/04→08/06								
1.6 Flex	82 kW	1.6 l	06/06→06/09								
1.9 dCi	85 kW	1.9 l	05/05→01/09								
1.9 dCi (JM0G, JM12, JM1G, JM2C)	88 kW	1.9 l	04/04→05/06								
1.9 dCi (JM14)	96 kW	1.9 l	04/04→02/08								
1.9 dCi (JM15)	81 kW	1.9 l	05/05→11/08								
2.0	99 kW	2 l	04/04→06/09								
2.0	120 kW	2 l	04/04→06/09								
2.0 dCi (JM1K)	110 kW	2 l	09/05→11/08						KH10112 ProKIT		
					15, 16 Inch				KH10104 ProKIT		
<b>RENAULT - GRAND SCÉNIC III (JZ0/1_)</b>										<b>02/09→</b>	
1.2 TCe	85 kW	1.2 l	04/12→								KH10080 ProKIT
1.2 TCe	96 kW	1.2 l	07/14→								
1.2 TCe (JZ16)	97 kW	1.2 l	01/13→								
1.4 16V (JZ0F)	96 kW	1.4 l	02/09→								
1.5 dCi	63 kW	1.5 l	04/09→								
1.5 dCi	70 kW	1.5 l	11/10→								
1.5 dCi	78 kW	1.5 l	02/09→								
1.5 dCi	81 kW	1.5 l	04/09→								
1.6 16V (JZ0U)	81 kW	1.6 l	02/09→								
1.6 16V Bifuel	79 kW	1.6 l	04/12→								
1.6 16V Bifuel	81 kW	1.6 l	02/09→								
1.6 E85	81 kW	1.6 l	02/09→								
2.0 16V (JZ0G)	103 kW	2 l	02/09→								
1.6 dCi (JZ00, JZ12)	96 kW	1.6 l	04/11→		OE 40 21 070 49R				KH10080 ProKIT		
					OE 40 21 018 77R				KH10200 ProKIT		
<b>RENAULT - KADJAR (HA_, HL_)</b>										<b>06/15→</b>	
1.2 TCe 130	96 kW	1.2 l	06/15→								KH30166 ProKIT
1.5 dCi 110 (HLA3)	81 kW	1.5 l	06/15→								
1.6 dCi 130	96 kW	1.6 l	06/15→								
1.6 dCi 130 4x4	96 kW	1.6 l	06/15→								





**RENAULT - KANGOO / GRAND KANGOO II (KW0/1\_) 02/08→**

1.2 TCe 115 (KW02, KW14)	84 kW	1.2 l	07/13→	;  15, 16 Inch	<b>KH10112</b> ProKIT	
1.5 dCi 110 (KW06, KW12)	81 kW	1.5 l	03/13→	;  14 Inch	<b>KH10380</b> ProKIT	
1.5 dCi 110 (KW0C, KW0H)	80 kW	1.5 l	09/10→			
1.5 dCi 115 (KW17)	85 kW	1.5 l	03/19→			
1.5 dCi 75 (KW07, KW10, KW04)	55 kW	1.5 l	11/12→			
1.5 dCi 80 (KW15)	59 kW	1.5 l	03/19→			
1.5 dCi 90 (KW05, KW08, KW0G, KW11)	66 kW	1.5 l	06/08→			
1.5 dCi 90 (KW18)	67 kW	1.5 l	08/17→			
1.5 dCi 95 (KW16)	70 kW	1.5 l	03/19→			
1.6 16V FLEX (KW01)	78 kW	1.6 l	02/08→			
1.6 16V LPG (KW0U)	78 kW	1.6 l	12/08→			
1.5 dCi 105 (KW0F)	76 kW	1.5 l	02/08→		;  15, 16 Inch	<b>KH10112</b> ProKIT
1.5 dCi 70 (KW0V, KW0A)	50 kW	1.5 l	02/08→		;  14 Inch	<b>KH10380</b> ProKIT
1.5 dCi 85 (KW0K, KW0L, KW0B)	63 kW	1.5 l	02/08→			<b>KH10177</b> ProKIT
1.6 (KW00, KW0Y, KW0E, KW0N, KW0P)	64 kW	1.6 l	02/08→			
1.6 16V (KW03, KW09, KW0D, KW0U, KW0W, KW13)	78 kW	1.6 l	02/08→			

**RENAULT - KANGOO (KC0/1\_) 08/97→**

1.2 (KC0A, KC0K, KC0F, KC01)	43 kW	1.2 l	08/97→		<b>KH10057</b> ProKIT	
1.2 16V (KC05, KC06, KC03, KC0T, KC0W, KC1D)	55 kW	1.2 l	06/01→	; ;	<b>KH10082</b> ProKIT	
1.4 (KC0C, KC0H, KC0B, KC0M)	55 kW	1.4 l	08/97→	; ;  26;	<b>KH20050</b> ProKIT	
1.5 dCi	42 kW	1.5 l	07/03→	; ;  44;	<b>KH20101</b> ProKIT	
1.5 dCi	45 kW	1.5 l	04/05→06/10			
1.5 dCi	50 kW	1.5 l	06/05→			
1.5 dCi	62 kW	1.5 l	06/05→			
1.5 dCi (KC07)	48 kW	1.5 l	12/01→			
1.5 dCi (KC08, KC09)	60 kW	1.5 l	07/02→			
1.6 16V	70 kW	1.6 l	06/01→			
1.6 16V bivalent	60 kW	1.6 l	06/05→			
1.6 (KC00)	66 kW	1.6 l	09/99→06/01			<b>KH10057</b> ProKIT
1.9 dTi (KC0U)	59 kW	1.9 l	02/00→		; ;  26;	<b>KH20050</b> ProKIT
1.9 RXED	48 kW	1.9 l	09/99→06/01	; ;  44;	<b>KH20101</b> ProKIT	
D 55 1.9 (KC0D)	40 kW	1.9 l	08/97→	; ;	<b>KH10150</b> ProKIT	
D 65 1.9 (KC0E, KC02, KC0J, KC0N)	47 kW	1.9 l	08/97→06/01			
1.6 16V 4x4 (KC0P, KC0S, KC0L)	70 kW	1.6 l	10/01→	; ;	<b>KH10082</b> ProKIT	
1.9 dCi 4x4	62 kW	1.9 l	10/03→	;	<b>KH10150</b> ProKIT	
1.9 dCi 4x4 (KC0V)	59 kW	1.9 l	10/01→	;	<b>KH10150</b> ProKIT	

**RENAULT - KANGOO BE BOP (KW0/1\_) 02/09→12/12**







1.5 dCi	47 kW	1.5 l	11/13→	;  15, 16 Inch	<b>KH10112</b> ProKIT	
1.5 dCi	80 kW	1.5 l	06/09→	;  14 Inch	<b>KH10380</b> ProKIT	
1.5 dCi 75	55 kW	1.5 l	09/10→			
1.6 16V	80 kW	1.6 l	11/13→		<b>KH10177</b> ProKIT	
1.5 dCi (KW0F)	76 kW	1.5 l	02/09→12/12		;  15, 16 Inch	<b>KH10112</b> ProKIT
1.5 dCi (KW0G)	66 kW	1.5 l	06/09→12/12		;  14 Inch	<b>KH10380</b> ProKIT
1.6 (KW0D)	78 kW	1.6 l	02/09→12/12			




































**RENAULT - KANGOO Express (FC0/1\_) 08/97→06/01**

1.2 (FC01, FC0A, FC0F)	43 kW	1.2 l	08/97→		<b>KH10057</b> ProKIT	
1.2 (FC1A)	44 kW	1.2 l	07/98→07/01	; ;	<b>KH10082</b> ProKIT	
1.2 16V (FC05, FC0W, FC1D, FC1P, FC1K, FC0T)	55 kW	1.2 l	10/01→			
1.2 BiFuel	43 kW	1.2 l	07/98→07/01		; ;  26;	<b>KH20050</b> ProKIT
1.4 (FC0C, FC0B, FC0H, FC0M)	55 kW	1.4 l	08/97→06/08		; ;  44;	<b>KH20101</b> ProKIT
1.5 dCi	45 kW	1.5 l	10/05→			
1.5 dCi (FC07, FC1R)	48 kW	1.5 l	12/01→			
1.5 dCi (FC08, FC09)	60 kW	1.5 l	04/03→			
1.5 dCi (FC1E)	50 kW	1.5 l	06/05→			
1.5 dCi (FC1G)	62 kW	1.5 l	06/05→			
1.5 dCi (FC1R)	42 kW	1.5 l	12/02→			
1.6 16V	70 kW	1.6 l	10/01→	;	<b>KH10057</b> ProKIT	
1.6 16V bivalent	60 kW	1.6 l	06/05→			
1.9 D (FC0J)	48 kW	1.9 l	09/99→06/03			
1.9 dCi (FC0V)	62 kW	1.9 l	07/03→			
1.6	66 kW	1.6 l	09/99→06/01			<b>KH10150</b> ProKIT
1.6 16V 4x4 (FC0L, FC0P, FC0S)	70 kW	1.6 l	10/01→		;	<b>KH10150</b> ProKIT
1.9 dCi 4x4 (FC0V)	59 kW	1.9 l	10/01→			
1.9 dCi 4x4 (FC0V)	62 kW	1.9 l	07/03→			








				13		i		
<b>RENAULT - KANGOO Express (FC0/1_)</b>							<b>08/97→06/01</b>	
1.9 dTi (FC0U)	59 kW	1.9 l	02/00→				KH10057 ProKIT	
D 55 1.9 (FC0D)	40 kW	1.9 l	08/97→		26;		KH20050 ProKIT	
D 65 1.9 (FC0E, FC02, FC0J, FC0N)	47 kW	1.9 l	08/97→		44;		KH20101 ProKIT	
<b>RENAULT - KANGOO Express (FW0/1_)</b>							<b>02/08→</b>	
1.2 TCe 115 (FW02, FW14)	84 kW	1.2 l	07/13→		14 Inch		KH10380 ProKIT	
1.5 dCi 110 (FW06, FW12)	81 kW	1.5 l	09/13→					
1.5 dCi 110 (FW0C, FW0H)	80 kW	1.5 l	09/10→					
1.5 dCi 75 (FW07, FW10, FW04)	55 kW	1.5 l	09/10→					
1.5 dCi 90 (FW18)	67 kW	1.5 l	08/17→					
1.5 dCi 105 (FW0F)	76 kW	1.5 l	02/08→		15, 16 Inch		KH10112 ProKIT	
1.5 dCi 70 (FW0A, KW0V)	50 kW	1.5 l	02/08→		14 Inch		KH10380 ProKIT	
1.5 dCi 85 (FW0K, FW0L, FW0B)	63 kW	1.5 l	02/08→				KH10177 ProKIT	
1.5 dCi 90 (FW0G, FW05, FW08, FW11)	66 kW	1.5 l	06/09→					
1.6 (FW00, FW0E, FW0N, FW0P, FW0Y)	64 kW	1.6 l	02/08→					
1.6 16V (FW03, FW09, FW0D, FW0U, FW0W, FW13)	78 kW	1.6 l	02/08→					
Z.E. (FW0Z, FW1Z)	44 kW		10/11→		15, 16 Inch		KH10112 ProKIT	
					14 Inch		KH10380 ProKIT	
<b>RENAULT - KOLEOS I (HY_)</b>							<b>09/08→</b>	
2.0	103 kW	2 l	08/13→				KH30024 ProKIT	
2.0 dCi	127 kW	2 l	07/13→					
2.0 dCi (HY0K)	110 kW	2 l	09/08→					
2.5 (HY0C, HY0N)	126 kW	2.5 l	09/08→					
2.0 dCi 4x4	130 kW	2 l	09/08→03/13				KH30024 ProKIT	
2.0 dCi 4x4 (HY0B)	127 kW	2 l	09/08→				KH30131 ProKIT	
2.0 dCi 4x4 (HY0K)	110 kW	2 l	09/08→					
2.5 4x4 (HY0C, HY0N)	126 kW	2.5 l	09/08→					
<b>RENAULT - LAGUNA I (B56_, 556_)</b>							<b>11/93→03/01</b>	
1.6 16V (B568, B561)	79 kW	1.6 l	11/97→03/01				KH10167 ProKIT	
							KH10082 ProKIT	
							KH20081 ProKIT	
1.8	69 kW	1.8 l	06/95→02/01		Outer diameter 1 [mm]: 72		KH10057 ProKIT	
1.8	70 kW	1.8 l	06/95→06/98		Outer diameter 1 [mm]: 84; Width 1 [mm]: 38		KH10085 ProKIT	
1.8 (B56A/B)	66 kW	1.8 l	11/93→03/01		Outer diameter 1 [mm]: 84; Width 1 [mm]: 39.7		KH10167 ProKIT	
1.8 (B56S/T/O)	66 kW	1.8 l	08/95→03/01				KH10082 ProKIT	
1.8 (B56Z)	69 kW	1.8 l	08/95→03/01				KH20077 ProKIT	
1.8 16V (B563, B564)	88 kW	1.8 l	04/98→03/01				KH10167 ProKIT	
1.9 dCi (B56W)	79 kW	1.9 l	09/99→03/01				KH10082 ProKIT	
1.9 dTi (B56J)	72 kW	1.9 l	10/97→03/01				KH10167 ProKIT	
							KH10082 ProKIT	
							KH20080 ProKIT	
							KH20081 ProKIT	
2.0	80 kW	2 l	03/99→03/01		Outer diameter 1 [mm]: 72		KH10057 ProKIT	
					Outer diameter 1 [mm]: 84; Width 1 [mm]: 38		KH10085 ProKIT	
					Outer diameter 1 [mm]: 84; Width 1 [mm]: 39.7		KH10167 ProKIT	
							KH10082 ProKIT	
					OE 77 01 204 689, 77 00 820 849		KH20077 ProKIT	
					OE 77 01 205 471		KH20080 ProKIT	
					OE 77 01 206 353		KH20081 ProKIT	
2.0	84 kW	2 l	06/95→02/01		Outer diameter 1 [mm]: 72		KH10057 ProKIT	
2.0 (B56C/H/N)	83 kW	2 l	11/93→03/01		Outer diameter 1 [mm]: 84; Width 1 [mm]: 38		KH10085 ProKIT	
					Outer diameter 1 [mm]: 84; Width 1 [mm]: 39.7		KH10167 ProKIT	
							KH10082 ProKIT	
2.0	103 kW	2 l	06/95→02/01		Width 1 [mm]: 38		KH10085 ProKIT	
					Width 1 [mm]: 39.7		KH10167 ProKIT	
					OE 77 01 205 471		KH20080 ProKIT	
2.0 (556A)	102 kW	2 l	09/99→02/01				KH10167 ProKIT	
2.0 16V (556A/B)	103 kW	2 l	09/99→03/01				KH20081 ProKIT	



											
<b>RENAULT - LAGUNA I (B56_, 556_)</b>										<b>11/93→03/01</b>	
2.0 16V (B56D, B56M)	102 kW	2 l	06/95→03/01		Width 1 [mm]: 38					KH10085 ProKIT	
					Width 1 [mm]: 39.7					KH10167 ProKIT	
										KH10082 ProKIT	
					OE 77 01 205 471					KH20080 ProKIT	
2.2 D (B56F/2)	61 kW	2.2 l	11/93→03/01		Width 1 [mm]: 38					KH10085 ProKIT	
					Width 1 [mm]: 39.7					KH10167 ProKIT	
										KH10082 ProKIT	
										KH20077 ProKIT	
2.2 dT (B569)	83 kW	2.2 l	03/96→03/01		Width 1 [mm]: 38					KH10085 ProKIT	
					Width 1 [mm]: 39.7					KH10167 ProKIT	
					01/97 -> 12/97;					KH20080 ProKIT	
					09/99 ->					KH20081 ProKIT	
										KH10082 ProKIT	
3.0 (B56E, B565, B56R)	123 kW	3 l	11/93→03/01		Width 1 [mm]: 38					KH10085 ProKIT	
					Width 1 [mm]: 39.7					KH10167 ProKIT	
3.0 24V (B56V)	140 kW	3 l	03/97→03/01							KH10167 ProKIT	
					09/99 ->					KH20081 ProKIT	
					-> 09/99					KH20080 ProKIT	
										KH10082 ProKIT	
<b>RENAULT - LAGUNA I Grandtour (K56_)</b>										<b>09/95→03/01</b>	
1.6 16V (K568)	79 kW	1.6 l	11/97→03/01							KH10167 ProKIT	
1.8 16V (K563, K564)	88 kW	1.8 l	04/98→03/01							KH20078 ProKIT	
1.9 dTi (K56J)	72 kW	1.9 l	10/97→03/01								
1.8 (K56S/T/0)	66 kW	1.8 l	09/95→03/01		01/97 ->; Width 1 [mm]: 39.7					KH10167 ProKIT	
1.8 (K56Z)	69 kW	1.8 l	09/95→03/01		-> 01/97; Width 1 [mm]: 38					KH10085 ProKIT	
2.0 (K56C/H)	83 kW	2 l	09/95→03/01							KH10057 ProKIT	
					02/97 -> 09/99;					KH20099 ProKIT	
					-> 02/97;					KH20077 ProKIT	
										KH20078 ProKIT	
1.9 dCi (K56W)	79 kW	1.9 l	09/99→03/01							KH10167 ProKIT	
2.0 16V (A56A/B)	103 kW	2 l	09/99→03/01								
3.0 24V (K56V)	140 kW	3 l	03/97→03/01								
2.0	84 kW	2 l	10/98→01/01							KH10057 ProKIT	
					Width 1 [mm]: 39.7					KH10167 ProKIT	
2.0 16V (K56D, K56M)	102 kW	2 l	09/95→03/01		01/97 ->; Width 1 [mm]: 39.7					KH10167 ProKIT	
					-> 01/97; Width 1 [mm]: 38					KH10085 ProKIT	
2.2 D (K56F/2, S56F)	61 kW	2.2 l	09/95→03/01		01/97 ->; Width 1 [mm]: 39.7					KH10167 ProKIT	
2.2 dT (K569)	83 kW	2.2 l	03/96→03/01		-> 01/97; Width 1 [mm]: 38					KH10085 ProKIT	
										KH20078 ProKIT	
3.0 (K56R, K565)	123 kW	3 l	02/96→03/01		01/97 ->; Width 1 [mm]: 39.7					KH10167 ProKIT	
					-> 01/97; Width 1 [mm]: 38					KH10085 ProKIT	
					02/97 -> 09/99;					KH20099 ProKIT	
					-> 02/97;					KH20077 ProKIT	
<b>RENAULT - LAGUNA III / LAGUNA III Grandtour / LAGUNA Coupe (BT0/1, KT0/1, DT0/1)</b>										<b>10/07→12/15</b>	
2.0 16V (BT05, BT0F, BT0W)	103 kW	2 l	10/07→12/15							KH30101 ProKIT	
2.0 16V (KT0F, KT0W)	103 kW	2 l	10/07→12/15								
2.0 16V Hi-Flex (BT1H, BT1G, BT1K)	103 kW	2 l	10/07→12/15								
2.0 16V Hi-Flex (KT1H, KT1G, KT1K)	103 kW	2 l	10/07→12/15								
2.0 16V Turbo	125 kW	2 l	10/07→12/15								
2.0 16V Turbo	125 kW	2 l	09/08→12/15								
2.0 dCi (BT01, BT08, BT09, BT0E, BT0K, BT12, BT1C, BT1D,...)	110 kW	2 l	10/07→12/15								
2.0 dCi (BT07, BT0J, BT14, BT1A, BT1S)	96 kW	2 l	10/07→12/15								
2.0 dCi (BT0M, BT0N, BT0S, BT19, BT1F)	127 kW	2 l	01/08→12/15								
2.0 dCi (DT01, DT08, DT09, DT0K, DT12, DT1C, DT1D, DT1M,...)	110 kW	2 l	09/08→12/15								
2.0 dCi (DT0M, DT0N, DT0S, DT19, DT1F)	127 kW	2 l	09/08→12/15								
2.0 dCi (KT01, KT08, KT09, KT0K, KT12, KT1D, KT1W)	110 kW	2 l	10/07→12/15								

												
<b>RENAULT - LAGUNA III / LAGUNA III Grandtour / LAGUNA Coupe (BT0/1, 10/07→12/15</b>												
<b>KT0/1, DT0/1)</b>												
2.0 dCi (KT07, KT0J, KT14, KT1A, KT1S)	96 kW	2 l	10/07→12/15									KH30101 ProKIT
2.0 dCi (KT0M, KT0N, KT0S, KT19, KT1F)	127 kW	2 l	01/08→12/15									
2.0 dCi GT (BT11, BT1E, BT1N)	131 kW	2 l	03/08→12/15									
2.0 dCi GT (DT11, DT1E, DT1N)	131 kW	2 l	09/08→12/15									
2.0 dCi GT (KT11, KT1E, KT1N)	131 kW	2 l	03/08→12/15									
2.0 GT	150 kW	2 l	03/08→12/15									
2.0 GT	150 kW	2 l	09/08→12/15									
3.0 dCi	177 kW	3 l	01/12→12/15									
3.0 dCi (BT03, BT13)	173 kW	3 l	09/08→12/15									
3.0 dCi (DT03)	173 kW	3 l	09/08→12/15									
3.0 dCi (KT03, KT13)	173 kW	3 l	09/08→12/15									
3.5 V6 (DT0P, DT0C)	177 kW	3.5 l	09/08→12/11									
3.5 V6 (DT0P)	175 kW	3.5 l	09/08→12/15									
<b>RENAULT - LATITUDE (L70_) 07/10→</b>												
1.5 dCi (L70R, L731)	81 kW	1.5 l	07/10→									KH30101 ProKIT
2.0 16V	102 kW	2 l	02/11→									
2.0 16V	105 kW	2 l	01/11→									
2.0 16V (L70B)	103 kW	2 l	02/11→									
2.0 16V eco2 Flexfuel (L70B)	103 kW	2 l	02/11→									
2.0 dCi 130	96 kW	2 l	12/13→									
2.0 dCi 150 (L70H)	110 kW	2 l	02/11→									
2.0 dCi 175 (L70Y)	127 kW	2 l	05/11→									
2.5 (L702)	133 kW	2.5 l	05/11→									
2.5 V6 (L702, L703, L704, L707)	130 kW	2.5 l	05/11→									
3.0 dCi 240 (L70G)	177 kW	3 l	02/11→									
3.5 V6	174 kW	3.5 l	08/13→									
3.5 V6	176 kW	3.5 l	01/11→									
3.5 V6 (L700, L701, L706, L708)	169 kW	3.5 l	01/11→									
<b>RENAULT - LOGAN/STEPWAY II (L8_) 11/13→</b>												
1.2	55 kW	1.2 l	11/13→									KH10380 ProKIT
1.6	60 kW	1.6 l	04/14→									KH10058 ProKIT
1.6	66 kW	1.6 l	11/13→									KH10077 ProKIT
1.6	81 kW	1.6 l	11/13→									
1.6	83 kW	1.6 l	09/16→									
1.6 (L8A9, L8J0)	75 kW	1.6 l	04/14→									
1.2 16V LPG	53 kW	1.2 l	11/13→									KH10058 ProKIT
1.5 dCi	62 kW	1.5 l	12/13→									KH10077 ProKIT
1.5 dCi	66 kW	1.5 l	12/13→									
1.6	59 kW	1.6 l	11/13→									KH10380 ProKIT
<b>RENAULT - LOGAN I (LS_) 09/04→06/15</b>												
1.4	55 kW	1.4 l	09/04→									KH10199 ProKIT
												KH10058 ProKIT
												KH10077 ProKIT
1.5 dCi	48 kW	1.5 l	04/06→10/13									KH10058 ProKIT
1.5 dCi	63 kW	1.5 l	02/08→06/15									KH10077 ProKIT
1.5 dCi	50 kW	1.5 l	04/07→									KH10199 ProKIT
												KH10058 ProKIT
												KH10077 ProKIT
1.6	64 kW	1.6 l	09/04→									KH10199 ProKIT
1.6 (LS0L, LS09, LS0V, LS0P, LS18, LS1S, LS1V, LS1Y,...)	77 kW	1.6 l	04/07→10/13									KH10058 ProKIT
												KH10077 ProKIT
<b>RENAULT - LOGAN I Estate (KS_) 04/07→</b>												
1.4	55 kW	1.4 l	10/07→									KH10199 ProKIT
												KH10058 ProKIT
1.5 dCi	50 kW	1.5 l	04/07→									KH10199 ProKIT
												KH10058 ProKIT
1.5 dCi	63 kW	1.5 l	02/08→06/15									KH10058 ProKIT
1.5 dCi	66 kW	1.5 l	06/11→									
1.6	64 kW	1.6 l	04/07→									KH10199 ProKIT
1.6 (KS0L, KS0M, KS0P, KS1S)	77 kW	1.6 l	04/07→									KH10058 ProKIT



      						
<b>RENAULT - LOGAN II Estate (K8_)</b>						<b>12/13→</b>
1.2 16V	54 kW	1.2 l	12/13→	; → 04/17	<b>KH10380</b> ProKIT	
1.2 16V LPG	53 kW	1.2 l	12/13→	;	<b>KH10058</b> ProKIT	
1.5 dCi	62 kW	1.5 l	12/13→		<b>KH10077</b> ProKIT	
1.5 dCi	66 kW	1.5 l	12/13→			
1.6	59 kW	1.6 l	12/13→			
<b>RENAULT - LOGAN EXPRESS (US_)</b>						<b>04/07→</b>
1.5 dCi	50 kW	1.5 l	04/07→	;	<b>KH10058</b> ProKIT	
1.6	64 kW	1.6 l	04/07→			
<b>RENAULT - MASTER I Bus / MASTER I Platform/Chassis / MASTER I Van (T_, P_)</b>						<b>08/80→07/98</b>
2.5 DT	69 kW	2.5 l	11/89→10/93		<b>KH00095</b> ProKIT	
28-35 2.0	59 kW	2 l	08/80→09/86		<b>KH00096</b> ProKIT	
28-35 2.0	59 kW	2 l	08/80→10/86			
28-35 2,5 D	55 kW	2.5 l	08/89→07/98	; → 09/97	<b>KH00095</b> ProKIT	
28-35 2,5 D	55 kW	2.5 l	08/89→07/98	; → 09/97	<b>KH00096</b> ProKIT	
28-35 2,5 TD	72 kW	2.5 l	08/89→07/98	; 10/94 → 09/97	<b>KH00095</b> ProKIT	
30 2.2	67 kW	2.2 l	08/80→07/98	; 10/94 → 09/97	<b>KH00096</b> ProKIT	
35 2,5 TD	69 kW	2.5 l	08/89→07/98			
28-35 2.0	58 kW	2 l	10/86→07/98	; → 09/94	<b>KH00095</b> ProKIT	
				; → 09/94	<b>KH00096</b> ProKIT	
28-35 2.0	58 kW	2 l	10/86→07/98	; 03/89 → 09/94	<b>KH00095</b> ProKIT	
				; 03/89 → 09/94	<b>KH00096</b> ProKIT	
28-35 2.1 D	44 kW	2 l	08/80→07/98	; → 02/89	<b>KH00095</b> ProKIT	
28-35 2.4 D	52 kW	2.4 l	08/80→08/89	; → 02/89	<b>KH00096</b> ProKIT	
<b>RENAULT - MASTER II Bus / MASTER II Platform/Chassis / MASTER II Van (JD, ED/HD/UD, FD)</b>						<b>07/98→10/01</b>
1.9 dCi 80	60 kW	1.9 l	11/01→		<b>KH10100</b> ProKIT	
1.9 dTi	59 kW	1.9 l	09/00→	;	<b>KH10064</b> ProKIT	
2.2 dCi 90	66 kW	2.2 l	09/00→	;	<b>KH10092</b> ProKIT	
2.5 dCi	74 kW	2.5 l	08/06→	;		
2.5 dCi	74 kW	2.5 l	08/06→01/10			
2.5 dCi	88 kW	2.5 l	08/06→			
2.5 dCi	107 kW	2.5 l	08/06→			
2.5 dCi 100 (ED4V, ED8V)	73 kW	2.5 l	10/03→			
2.5 dCi 100 (FD0U, FDOV)	73 kW	2.5 l	10/03→			
2.5 dCi 100 (JDCV)	73 kW	2.5 l	10/03→			
2.5 dCi 120	84 kW	2.5 l	10/01→			
3.0 dCi 140 (ED0S, UD0S)	100 kW	3 l	10/03→			
3.0 dCi 140 (HD0S, FD0S, HD1S)	100 kW	3 l	10/03→10/06			
3.0 dCi 140 (JD0T)	100 kW	3 l	10/03→			
2.5 D	59 kW	2.5 l	07/98→01/01	; 03/00 →	<b>KH10100</b> ProKIT	
2.8 dTi	84 kW	2.8 l	07/98→10/01	; → 03/00	<b>KH10195</b> ProKIT	
				;	<b>KH10064</b> ProKIT	
				;	<b>KH10092</b> ProKIT	
<b>RENAULT - MASTER III Bus / MASTER III Platform/Chassis / MASTER III Van (JV, EV, HV, UV, FV)</b>						<b>02/10→</b>
2.3 dCi 100 FWD (EV0A, EV0B, HV0A, HV0B, UV0A, UV0B,...	74 kW	2.3 l	02/10→		<b>KH10139</b> ProKIT	
2.3 dCi 100 FWD (FV0A, FV0B, FV0G, FV0K, FV0H)	74 kW	2.3 l	02/10→		<b>KH10138</b> ProKIT	
2.3 dCi 100 FWD (JV0A, JV0B, JV0G, JV0H)	74 kW	2.3 l	02/11→			
2.3 dCi 110 FWD (EV0R, EV0W, HV0R, HV0W, UV0R, UV0W)	81 kW	2.3 l	09/14→			
2.3 dCi 110 FWD (FV0R, FV0W)	81 kW	2.3 l	09/14→			
2.3 dCi 110 FWD (JV0R, JV0W)	81 kW	2.3 l	09/14→			
2.3 dCi 125 FWD (EV0C, EV0D, EV0J, HV0C, HV0D, HV0H,...	92 kW	2.3 l	02/10→			
2.3 dCi 125 FWD (FV0C, FV0D, FV0G, FV0H, FV0J, FV0K)	92 kW	2.3 l	02/10→			
2.3 dCi 125 FWD (JV0C, JV0D, JV0H, JV0G, JV0J)	92 kW	2.3 l	02/11→			
2.3 dCi 130 FWD (EV0Y, HV0Y, UV0M, UV0Y)	96 kW	2.3 l	03/12→			
2.3 dCi 130 FWD (FV0M, FV0Y)	96 kW	2.3 l	06/16→			
2.3 dCi 135 FWD (EV0N, HV0N, UV0N, EV08, HV08, UV08)	100 kW	2.3 l	07/14→			
2.3 dCi 135 FWD (FV0N, FV08)	100 kW	2.3 l	07/14→			
2.3 dCi 135 FWD (JV0N, JV08)	100 kW	2.3 l	07/14→			











































**RENAULT - MASTER III Bus / MASTER III Platform/Chassis / MASTER III Van (JV, 02/10→  
EV, HV, UV, FV)**

2.3 dCi 145 FWD (EV0E, EV0F, HV0E, HV0F, UV0E, UV0F,...)	107 kW	2.3 l	02/10→		<b>KH10139</b> ProKIT
2.3 dCi 145 FWD (FV0E, FV0F, FV0H, FV02, FV0M, FV0S,...)	107 kW	2.3 l	02/10→		<b>KH10138</b> ProKIT
2.3 dCi 145 FWD (JV0F, JV0S, JV0T)	107 kW	2.3 l	02/11→		
2.3 dCi 150 FWD (EV0F, HV0F, UV0F, EV03, HV03, UV03)	110 kW	2.3 l	03/13→		
2.3 dCi 150 FWD (FV0F, FV03)	110 kW	2.3 l	03/13→		
2.3 dCi 150 FWD (JV0F, JV03)	110 kW	2.3 l	10/12→		
2.3 dCi 165 FWD (EV0P, EV0U, EV11, EV12, HV0P, HV0U,...)	120 kW	2.3 l	07/14→		
2.3 dCi 165 FWD (FV0P, FV0U, FV11, FV12)	120 kW	2.3 l	07/14→		
2.3 dCi 165 FWD (JV0P, JV0U)	120 kW	2.3 l	07/14→		
2.3 dCi 170 FWD (EV0L, HV0L, UV0L)	125 kW	2.3 l	06/16→		
2.3 dCi 170 FWD (FV0L)	125 kW	2.3 l	07/15→		
2.3 dCi 170 FWD (JV0L)	125 kW	2.3 l	07/15→		
2.3 dCi 100 RWD (FV0B)	74 kW	2.3 l	02/10→		<b>KH10174</b> ProKIT
2.3 dCi 100 RWD (HV0B, UV0B)	74 kW	2.3 l	02/10→		<b>KH00086</b> ProKIT
2.3 dCi 125 RWD (FV0C, FV0D, FV0H, FV0J, FV0A, FV0K)	92 kW	2.3 l	02/10→		<b>KH10143</b> ProKIT
2.3 dCi 125 RWD (HV0C, HV0D, UV0C, UV0D, UV0H, UV0J,...)	92 kW	2.3 l	02/10→		
2.3 dCi 130 RWD (FV01, FV10, FV11, FV12)	96 kW	2.3 l	03/12→		
2.3 dCi 130 RWD (HV01, HV10, HV11, HV12, UV01, UV10,...)	96 kW	2.3 l	07/16→		
2.3 dCi 135 RWD (FV0N)	100 kW	2.3 l	07/14→		
2.3 dCi 135 RWD (HV0N, UV0N)	100 kW	2.3 l	07/14→		
2.3 dCi 145 RWD (FV0E, FV0F, FV0T, FV10, FV12)	107 kW	2.3 l	02/10→		
2.3 dCi 145 RWD (UV0F, UV0E, HV0E, HV0F, HV0T, HV10,...)	107 kW	2.3 l	02/10→		
2.3 dCi 150 RWD (FV0F)	110 kW	2.3 l	03/13→		
2.3 dCi 150 RWD (HV0F, UV0F)	110 kW	2.3 l	03/13→		
2.3 dCi 165 RWD (FV0P, FV0U, FV10, FV12)	120 kW	2.3 l	07/14→		
2.3 dCi 165 RWD (HV0P, HV0U, HV10, HV12, UV0P, UV0U,...)	120 kW	2.3 l	07/14→		

**RENAULT - MEGANE I / MEGANE I Cabriolet / MEGANE I Classic / MEG- 08/95→12/04  
ANE I Coach (BA0/1\_, EA0/1\_, LA0/1\_, DA0/1\_)**

1.4 (LA0E, LA0V)	55 kW	1.4 l	09/96→08/03		<b>KH10057</b> ProKIT
1.4 16V (BA0D, BA1H, BA0W, BA10)	70 kW	1.4 l	03/99→08/03		<b>KH10073</b> ProKIT
1.4 16V (DA0D, DA1H, DA0W, DA10)	70 kW	1.4 l	03/99→07/03		
1.4 16V (EA0D, EA1H, EA0W, EA10)	70 kW	1.4 l	03/99→08/03		
1.4 16V (LA0D, LA1H, IA0W, LA10)	70 kW	1.4 l	03/99→08/03		
1.4 e (BA0E, BA0V)	55 kW	1.4 l	01/96→08/03		
1.4 Eco (BA0T)	52 kW	1.4 l	01/96→03/99		
1.6	64 kW	1.6 l	02/00→09/00		
1.6 16V (BA04, BA0B, BA11, BA1J, BA16, BA19, BA1K, BA1V,...)	79 kW	1.6 l	03/99→08/02		
1.6 16V (DA0B, DA04, DA11)	79 kW	1.6 l	03/99→07/03		
1.6 16V (EA04, EA0B, EA11, EA1J)	79 kW	1.6 l	03/99→07/03		
1.6 16V (LA00, LA04, LA0B, LA11, LA16, LA19, LA1J, LA1K,...)	79 kW	1.6 l	03/99→07/03		
1.6 e (BA0F, BA0S)	66 kW	1.6 l	01/96→03/99		
1.6 e (DA0F)	66 kW	1.6 l	03/96→03/99		
1.6 e (EA0F)	66 kW	1.6 l	10/96→03/99		
1.6 e (LA0F, LA0S)	66 kW	1.6 l	09/96→03/99		
1.6 i (BA0L)	55 kW	1.6 l	01/96→03/99		
1.6 i (LA0L)	55 kW	1.6 l	09/96→03/99		
1.6 LPG	66 kW	1.6 l	08/95→03/99		
1.6 LPG	80 kW	1.6 l	10/00→08/02		
1.8 16V (BA06, BA12, BA1A, BA1M, BA1R)	85 kW	1.8 l	01/01→08/03		
1.8 16V (LA06, LA12, LA1A, LA1M, LA1R)	85 kW	1.8 l	01/01→08/03		
1.9 D	69 kW	1.9 l	04/96→02/01		
1.9 D (LA0A, LA0U, LA0R)	47 kW	1.9 l	09/96→08/03		
1.9 DCi	77 kW	1.9 l	03/99→09/00		
1.9 dCi (BA05, BA1F)	75 kW	1.9 l	02/01→08/03		
1.9 dCi (DA05, DA1F)	75 kW	1.9 l	02/01→08/03		
1.9 dCi (LA05, LA1F)	75 kW	1.9 l	02/01→08/03		



											
<b>RENAULT - MEGANE I / MEGANE I Cabriolet / MEGANE I Classic / MEG-</b>									<b>08/95→12/04</b>		
<b>ANE I Coach (BA0/1_, EA0/1_, LA0/1_, DA0/1_)</b>											
1.9 dCi (LA05)	77 kW	1.9 l	03/99→07/03						<b>KH10057 ProKIT</b>		
1.9 D Eco (BA0A, BA0U, BA0R)	47 kW	1.9 l	01/96→08/03						<b>KH10073 ProKIT</b>		
1.9 dT	76 kW	1.9 l	08/98→10/99								
1.9 dT (B/SA0K, B/SA0Y)	66 kW	1.9 l	01/96→08/03								
1.9 dT (LA0K, LA0Y)	66 kW	1.9 l	09/96→08/03								
1.9 dTi (BA08, BA0N)	72 kW	1.9 l	03/97→02/01								
1.9 dTi (BA1U)	59 kW	1.9 l	02/01→08/03								
1.9 dTi (DA0N)	72 kW	1.9 l	03/97→02/01								
1.9 dTi (LA08, LA0N)	72 kW	1.9 l	03/97→02/01								
1.9 dTi (LA1U)	59 kW	1.9 l	02/01→08/03								
1.9 TDI	69 kW	1.9 l	09/96→08/03								
2.0	85 kW	2 l	05/98→05/01								
2.0 (EA0G)	84 kW	2 l	04/97→08/03								
2.0 16V	102 kW	2 l	01/02→08/03								
2.0 16V IDE (DA03, DA0P, DA14)	103 kW	2 l	11/99→08/03								
2.0 16V IDE (EA03, EA0P, EA14)	103 kW	2 l	11/99→08/03								
2.0 i	80 kW	2 l	03/99→08/03								
2.0 i (BA0G)	84 kW	2 l	01/96→08/03								
2.0 i (DA0G)	84 kW	2 l	03/96→08/03								
2.0 i (EA0G)	80 kW	2 l	03/99→08/03								
2.0 i (LA07, LA0G)	84 kW	2 l	09/96→08/03								
2.0 i (LA0G)	80 kW	2 l	03/99→08/03								
2.0 RT	103 kW	2 l	03/01→08/03								
2.0 RT	112 kW	2 l	10/96→02/99								
1.6 16V	81 kW	1.6 l	09/99→12/01							<b>KH10073 ProKIT</b>	
1.6 16V	81 kW	1.6 l	11/01→12/04								
1.9 DCi	77 kW	1.9 l	03/99→08/03								
1.9 dT	76 kW	1.9 l	08/98→10/99								
1.9 TDI	69 kW	1.9 l	09/96→08/03								
2.0 16V (BA0H)	108 kW	2 l	07/96→08/03		-> 09/98; Outer diameter 1 [mm]: 84				<b>KH10085 ProKIT</b>		
2.0 16V (DA0H)	108 kW	2 l	03/96→11/99		Outer diameter 1 [mm]: 72				<b>KH10057 ProKIT</b>		
2.0 16V (EA0H)	108 kW	2 l	10/96→11/99							<b>KH10073 ProKIT</b>	
<b>RENAULT - MEGANE I Grandtour (KA0/1_)</b>									<b>03/99→08/03</b>		
1.4 16V (KA0D, KA1H, KA0W, KA10)	70 kW	1.4 l	03/99→08/03						<b>KH10057 ProKIT</b>		
1.4 e (KA0V)	55 kW	1.4 l	03/99→08/03							<b>KH10073 ProKIT</b>	
1.6 16V (KA0B, KA04, KA11)	79 kW	1.6 l	03/99→08/03						<b>KH20036 ProKIT</b>		
1.6 e (KA0F)	66 kW	1.6 l	03/99→08/03						<b>KH20147 ProKIT</b>		
1.8 16V (KA0S, KA12, KA1A, KA1M, KA1R)	85 kW	1.8 l	01/01→08/03								
1.9 D (KA0J, KA0R)	47 kW	1.9 l	04/99→08/03								
1.9 dCi (KA05, KA1F)	75 kW	1.9 l	02/01→08/03								
1.9 dTi (KA0N)	72 kW	1.9 l	03/99→02/01								
1.9 dTi (KA1U)	59 kW	1.9 l	02/01→08/03								
1.6 Bifuel	80 kW	1.6 l	03/99→09/00							<b>KH10073 ProKIT</b>	
1.9 dCi	77 kW	1.9 l	03/99→09/00						<b>KH20036 ProKIT</b>		
<b>RENAULT - MEGANE II (BM0/1_, CM0/1_)</b>									<b>09/02→12/09</b>		
1.4 16V	60 kW	1.4 l	10/03→02/08						<b>KH10380 ProKIT</b>		
1.4 16V (BM0B, CM0B)	72 kW	1.4 l	11/02→02/08						<b>KH10076 ProKIT</b>		
1.6	77 kW	1.6 l	06/05→02/08								
1.6 16V	82 kW	1.6 l	01/06→06/08								
1.6 16V (BM0C, CM0C)	83 kW	1.6 l	11/02→02/08								
1.6 Bifuel	77 kW	1.6 l	06/05→02/08								
1.6 Flex-Fuel	77 kW	1.6 l	01/07→02/08								
1.5 dCi (BM02, BM13, BM2A, CM02, CM13)	74 kW	1.5 l	10/03→02/08		 				<b>KH10380 ProKIT</b>		
1.5 dCi (BM0F, BM0T, BM2B, CM0F, CM0T)	60 kW	1.5 l	09/02→02/08						<b>KH10076 ProKIT</b>		
1.5 dCi (BM16, CM16)	76 kW	1.5 l	01/07→03/09								
1.5 dCi (BM1E, CM1E)	78 kW	1.5 l	05/05→06/08								
1.5 dCi (BM1F, CM1F)	63 kW	1.5 l	05/05→02/08								
1.9 dCi	66 kW	1.9 l	11/02→12/05						<b>KH10076 ProKIT</b>		
1.9 dCi	68 kW	1.9 l	03/04→08/06								
1.9 dCi	81 kW	1.9 l	05/05→02/08								
1.9 dCi	85 kW	1.9 l	11/02→02/08								
1.9 dCi	96 kW	1.9 l	05/05→12/09								
1.9 dCi (BM0G, CM0G)	88 kW	1.9 l	11/02→02/08								
2.0	169 kW	2 l	08/06→02/08						<b>KH10380 ProKIT</b>		
2.0 16V (BM0U, CM0U)	99 kW	2 l	11/02→02/08						<b>KH10076 ProKIT</b>		
2.0 16V Turbo	120 kW	2 l	05/04→02/08								
2.0 Renault Sport	165 kW	2 l	05/04→10/09								





**RENAULT - MEGANE II (BM0/1\_, CM0/1\_) 09/02→12/09**










































2.0 dCi	127 kW	2 l	01/07→02/08	; <b>Outer diameter 1 [mm]: 83</b>	<b>KH10112</b> ProKIT
2.0 dCi (BM1K, CM1K)	110 kW	2 l	09/05→02/08	; <b>Outer diameter 1 [mm]: 88</b>	<b>KH10115</b> ProKIT
					<b>KH10104</b> ProKIT







**RENAULT - MEGANE II Coupé-Cabriolet / MEGANE II Estate / MEGANE II Saloon (EM0/1\_, KM0/1\_, LM0/1\_) 08/03→10/11**

1.4	60 kW	1.4 l	09/03→		<b>KH10380</b> ProKIT
1.4	72 kW	1.4 l	09/03→		<b>KH10076</b> ProKIT
1.6	77 kW	1.6 l	05/05→		
1.6	83 kW	1.6 l	09/03→		
1.6 16V (LM1R, LM0C)	82 kW	1.6 l	01/06→		
1.6 Hi-Flex (LM2E, LM2M, LM24)	85 kW	1.6 l	03/06→		
1.4	72 kW	1.4 l	08/03→07/09		<b>KH10380</b> ProKIT
1.6	83 kW	1.6 l	08/03→07/09		<b>KH10104</b> ProKIT
1.6 16V	75 kW	1.6 l	05/05→07/09		
1.6 16V	77 kW	1.6 l	05/05→07/09		
1.6 16V	81 kW	1.6 l	05/06→10/11		
1.6 16V	82 kW	1.6 l	01/06→08/09		
1.6 16V Hi-Flex	77 kW	1.6 l	02/08→07/09		
1.5 dCi (KM02, KM13)	74 kW	1.5 l	02/04→03/06	; <b>AT, MTs</b>	<b>KH10380</b> ProKIT
1.5 dCi (KM0F, KM0T, KM2B)	60 kW	1.5 l	08/03→05/06		<b>KH10104</b> ProKIT
1.5 dCi (KM16, KM1E)	78 kW	1.5 l	05/05→06/08		
1.5 dCi (KM16)	76 kW	1.5 l	01/07→07/09		
1.5 dCi (KM1F)	63 kW	1.5 l	05/05→07/09		
1.5 dCi (LM02, LM13, LM2A)	74 kW	1.5 l	02/04→12/10	; <b>AT, MTs</b>	<b>KH10380</b> ProKIT
1.5 dCi (LM0F, LM0T, LM2B)	60 kW	1.5 l	08/03→12/10		<b>KH10076</b> ProKIT
1.5 dCi (LM16)	76 kW	1.5 l	10/03→12/10		
1.5 dCi (LM1E)	78 kW	1.5 l	05/05→12/10		
1.5 dCi (LM1F)	63 kW	1.5 l	05/05→12/10		
1.6	81 kW	1.6 l	09/03→11/08		
1.6	77 kW	1.6 l	06/05→03/09		<b>KH10380</b> ProKIT
1.6	83 kW	1.6 l	09/03→03/09		
1.6 16V	82 kW	1.6 l	01/06→06/08		
1.6 LPG 16V	82 kW	1.6 l	01/06→08/09		<b>KH10104</b> ProKIT
1.9 dCi	66 kW	1.9 l	04/04→12/05		
1.9 dCi	68 kW	1.9 l	03/04→02/07		
1.9 dCi	81 kW	1.9 l	05/05→07/09		
1.9 dCi	85 kW	1.9 l	05/05→07/09		
1.9 dCi	96 kW	1.9 l	05/05→07/09		
1.9 dCi (KMRG, KM1G, KM0G, KM2C)	88 kW	1.9 l	08/03→07/09		
1.9 dCi	66 kW	1.9 l	09/03→12/05		<b>KH10076</b> ProKIT
1.9 dCi	68 kW	1.9 l	03/04→		
1.9 dCi	96 kW	1.9 l	05/05→		
1.9 dCi (LM0G, LM1G, LM2C)	88 kW	1.9 l	09/03→		
1.9 dCi (LM14, LM1D)	81 kW	1.9 l	05/05→		
2.0	99 kW	2 l	08/03→07/09	; <b>AT</b>	<b>KH10380</b> ProKIT
2.0 (KM0S, KM2N, KM23)	102 kW	2 l	12/06→01/11		<b>KH10104</b> ProKIT
2.0	99 kW	2 l	09/03→	; <b>AT</b>	<b>KH10380</b> ProKIT
2.0	101 kW	2 l	04/06→11/10		<b>KH10076</b> ProKIT
2.0	99 kW	2 l	09/03→12/09	; <b>AT</b>	<b>KH10380</b> ProKIT
2.0 (EM0S)	102 kW	2 l	09/03→02/07		
2.0 16V Turbo	120 kW	2 l	05/04→03/09		
2.0 dCi	110 kW	2 l	09/05→	; <b>15, 16 Inch</b>	<b>KH10112</b> ProKIT
2.0 dCi	110 kW	2 l	09/05→03/09	; <b>AT</b>	<b>KH10380</b> ProKIT
2.0 dCi	110 kW	2 l	09/05→07/09		<b>KH10104</b> ProKIT






**RENAULT - MEGANE III Coupe / MEGANE III Grandtour / MEGANE III Hatchback / MEGANE IV Hatchback (DZ0/1\_, KZ0/1, BZ0/1\_, B3\_, B9A/M/N\_) 11/08→**



































1.2 TCe (BZ16, BZ28)	97 kW	1.2 l	01/13→		<b>KH10080</b> ProKIT
1.2 TCe (BZ2B, BZ11)	85 kW	1.2 l	03/12→08/15		
1.2 TCe (DZ16, DZ28)	97 kW	1.2 l	01/13→08/15		
1.2 TCe (DZ2B, DZ11)	85 kW	1.2 l	03/12→08/15		
1.2 TCe (KZ16, KZ28)	97 kW	1.2 l	01/13→		
1.2 TCe (KZ2B, KZ11)	85 kW	1.2 l	03/12→		
1.2 TCe 100 (B9MS)	74 kW	1.2 l	11/15→		
1.2 TCe 130 (B9MR)	97 kW	1.2 l	11/15→		
1.4 TCe (BZ0F, BZ1V)	96 kW	1.4 l	04/09→		
1.4 TCe (DZ0F, DZ1V)	96 kW	1.4 l	04/09→		
1.4 TCe (KZ0F, KZ1V)	96 kW	1.4 l	05/09→		
1.5 dCi	63 kW	1.5 l	11/08→		
1.5 dCi	63 kW	1.5 l	03/09→		
1.5 dCi	70 kW	1.5 l	11/13→		
1.5 dCi	70 kW	1.5 l	07/14→		

     							
<b>RENAULT - MEGANE III Coupe / MEGANE III Grandtour / MEGANE III Hatchback / MEGANE IV Hatchback (DZ0/1_, KZ0/1, BZ0/1_, B3_, B9A/M/N_) 11/08→</b>							
1.5 dCi	78 kW	1.5 l	02/09→		KH10080 ProKIT		
1.5 dCi (BZ09, BZ0D, BZ1W, BZ29, BZ14)	81 kW	1.5 l	02/09→				
1.5 dCi (BZ0C)	66 kW	1.5 l	11/08→08/15				
1.5 dCi (BZ1G, BZ1W, BZ0R)	70 kW	1.5 l	11/13→08/15				
1.5 dCi (DZ09, DZ0D, DZ1F, DZ1G, DZ14, DZ29)	81 kW	1.5 l	02/09→08/15				
1.5 dCi (DZ0A)	63 kW	1.5 l	11/08→08/15				
1.5 dCi (DZ0B)	78 kW	1.5 l	02/09→				
1.5 dCi (DZ0C, DZ1A)	66 kW	1.5 l	11/08→08/15				
1.5 dCi (KZ09, KZ0D, KZ1G, KZ29, KZ14, KZ1W, KZ10, KZ1F,...)	81 kW	1.5 l	02/09→				
1.5 dCi (KZ0C, KZ1A)	66 kW	1.5 l	05/09→				
1.5 dCi (KZ1M, KZ1W)	78 kW	1.5 l	02/09→				
1.5 dCi 110 (B9A3)	81 kW	1.5 l	11/15→				
1.5 dCi 90 (B9A1)	66 kW	1.5 l	11/15→				
1.6 16V	82 kW	1.6 l	11/08→				
1.6 16V	84 kW	1.6 l	11/15→				
1.6 16V	85 kW	1.6 l	01/13→				
1.6 16V (BZ0H)	74 kW	1.6 l	11/08→08/15				
1.6 16V (BZ1B, BZ1H)	81 kW	1.6 l	11/08→				
1.6 16V (DZ0H)	74 kW	1.6 l	11/08→				
1.6 16V (DZ0U, DZ1B, DZ1H)	81 kW	1.6 l	11/08→08/15				
1.6 16V (KZ0H)	74 kW	1.6 l	05/09→				
1.6 16V (KZ0U, KZ1B, KZ1U)	81 kW	1.6 l	05/09→				
1.6 16V Bifuel (DZ03, DZ1Y)	81 kW	1.6 l	11/08→				
1.6 16V Hi-Flex (BZ03)	81 kW	1.6 l	11/08→08/15				
1.6 BiFuel (KZ03)	81 kW	1.6 l	11/08→				
1.6 dCi (BZ00, BZ12, BZ13)	96 kW	1.6 l	04/11→08/15				
1.6 dCi (DZ00, DZ12, DZ2A, DZ13)	96 kW	1.6 l	04/11→08/15				
1.6 dCi (KZ00, KZ12, KZ13)	96 kW	1.6 l	04/11→				
1.9 dCi (BZ0N, BZ0J)	96 kW	1.9 l	11/08→				
1.9 dCi (DZ0N, DZ0J, DZ1J, DZ1K)	96 kW	1.9 l	11/08→08/15				
1.9 dCi (KZ0J, KZ0N, KZ1S)	96 kW	1.9 l	05/09→				
2.0 dCi	120 kW	2 l	07/12→			 ; -> 01/14	KH10200 ProKIT
2.0 dCi (BZ0L)	118 kW	2 l	04/09→08/15				
2.0 dCi (BZ0Y)	110 kW	2 l	10/10→				
2.0 dCi (DZ0L)	118 kW	2 l	04/09→08/15				
2.0 dCi (DZ0Y)	110 kW	2 l	04/09→				
2.0 dCi (KZ0L)	118 kW	2 l	04/09→				
2.0 dCi (KZ0Y)	110 kW	2 l	10/10→				
2.0 R.S.	195 kW	2 l	11/08→				
2.0 TCe	140 kW	2 l	06/12→				
2.0 TCe	140 kW	2 l	09/12→				
2.0 TCe	162 kW	2 l	09/12→				
2.0 TCe (BZ0K)	132 kW	2 l	11/08→08/15				
2.0 TCe (DZ0K)	132 kW	2 l	11/08→08/15				
2.0 TCe (KZ0K, KZ1T)	132 kW	2 l	11/08→				
2.0 TCe 220	162 kW	2 l	11/13→				
2.0 TCe (DZ1N)	184 kW	2 l	05/09→	KH20066 ProKIT			
<b>RENAULT - MEGANE CC (EZ0/1_) 06/10→</b>							
2.0 dCi (EZ0L)	118 kW	2 l	06/10→	 ; -> 07/12	KH10200 ProKIT		
2.0 TCe (EZ1T)	132 kW	2 l	06/10→				
<b>RENAULT - MEGANE Scenic (JA0/1_) 10/96→10/99</b>							
1.4 i (JA0E)	55 kW	1.4 l	01/97→09/99		KH10057 ProKIT		
						KH10085 ProKIT	
					 ; 	KH20036 ProKIT	
					 ;  ; 	KH20147 ProKIT	
1.6 16V (JA0B, JA04, JA11, JA00)	79 kW	1.6 l	04/98→10/99	 ; 06/98 ->	KH10057 ProKIT		
					 ; -> 06/98	KH10085 ProKIT	
						KH10080 ProKIT	
					 ; 	KH20036 ProKIT	
					 ;  ; 	KH20147 ProKIT	
					 ; 	KH20147 ProKIT	
1.6 e (JA0F)	66 kW	1.6 l	10/96→10/99	 ; <b>Outer diameter 1 [mm]: 72</b>	KH10057 ProKIT		
1.6 i (JA0L)	55 kW	1.6 l	01/97→09/99		 ; <b>Outer diameter 1 [mm]: 84</b>	KH10085 ProKIT	
1.9 D (JA0J)	47 kW	1.9 l	03/97→09/99	 ; 06/98 ->	KH10057 ProKIT		
					 ; -> 06/98	KH10085 ProKIT	
					 ; 	KH20036 ProKIT	
					 ;  ; 	KH20147 ProKIT	
1.9 dT (JA0K, JA0Y)	66 kW	1.9 l	01/97→09/99	 ; -> 06/98	KH10085 ProKIT		
2.0 i (JA0G)	84 kW	2 l	01/97→09/99				
					 ; 	KH20036 ProKIT	
					 ;  ; 	KH20147 ProKIT	







     					
<b>RENAULT - MEGANE Scenic (JA0/1_)</b>					<b>10/96→10/99</b>
1.9 dT (JA0Y)	69 kW	1.9 l	03/97→08/99	; 06/98 -> ; -> 06/98 ;	KH10057 ProKIT KH10085 ProKIT KH20036 ProKIT
1.9 dTi (JA0N)	72 kW	1.9 l	04/97→09/99	; 06/98 -> ; -> 06/98 ; Code: JA05, JA1F; ; ; ;	KH10057 ProKIT KH10085 ProKIT KH10150 ProKIT KH20036 ProKIT KH20147 ProKIT
2.0 i (JA02, JA0G)	80 kW	2 l	01/99→09/99	 ; ; ;	KH10057 ProKIT KH20036 ProKIT KH20147 ProKIT
<b>RENAULT - MODUS / GRAND MODUS (F/JP0_)</b>					<b>09/04→</b>
1.2	76 kW	1.2 l	04/11→		KH10380 ProKIT
1.2 (FP0C, FP0K, FP0P)	48 kW	1.2 l	05/05→	; ;	KH10073 ProKIT
1.2 (JP0C, JP0K, FP0C, FP0K, FP0P, JP0P, JP0T)	55 kW	1.2 l	12/04→	;	KH10076 ProKIT
1.2 (JP0S)	58 kW	1.2 l	12/04→	; ;	KH10077 ProKIT
1.2 16V (JP0W)	74 kW	1.2 l	05/07→		
1.2 16V Hi-Flex	55 kW	1.2 l	10/08→		
1.4 (JP01, JP0J)	72 kW	1.4 l	12/04→		
1.5 dCi (FP0D, JP0D)	60 kW	1.5 l	09/04→		
1.5 dCi (FP0E, JP0E)	48 kW	1.5 l	12/04→		
1.5 dCi (FP0F, JP0F)	63 kW	1.5 l	12/04→		
1.5 dCi (FP0G, JP0G)	50 kW	1.5 l	12/04→		
1.5 dCi (JP02)	76 kW	1.5 l	05/07→		
1.5 dCi (JP0G, JP0H)	78 kW	1.5 l	05/05→		
1.5 dCi 75	55 kW	1.5 l	10/10→		
1.5 dCi 90	65 kW	1.5 l	10/10→		
1.6 (JP03, JP0B, JP0U, JP0Y, JP1G)	82 kW	1.6 l	12/04→		
1.6 (JP0L, JP0V)	65 kW	1.6 l	12/04→		
<b>RENAULT - RAPID Box Body/MPV (F40_, G40_)</b>					<b>07/85→08/98</b>
1.0	27 kW	1 l	02/86→05/92		KH10075 ProKIT
1.0	31 kW	1 l	09/85→08/91		
1.1	34 kW	1.1 l	09/85→08/91		
1.1	35 kW	1.1 l	09/93→04/95		
1.1 (F401)	33 kW	1.1 l	07/85→04/95		
1.1 (F40H)	33 kW	1.1 l	06/87→09/91		
1.2	40 kW	1.2 l	09/91→08/93		
1.4 (F402)	43 kW	1.4 l	07/85→08/91		
1.4 (F40M)	44 kW	1.4 l	03/86→08/91		
1.4 Cat (F407)	43 kW	1.4 l	08/88→03/98		
1.2 (F406, G40A)	40 kW	1.2 l	09/91→03/98	; Outer diameter 1 [mm]: 72	KH10057 ProKIT
1.4	54 kW	1.4 l	09/91→08/93	; Outer diameter 1 [mm]: 65	KH10075 ProKIT
1.4	59 kW	1.4 l	05/95→08/97		
1.4 (F40D)	58 kW	1.4 l	01/94→03/98		
1.4 (F40U, F40V)	55 kW	1.4 l	09/91→03/98		
1.4 (F40Y, F40A, F40V)	43 kW	1.4 l	09/91→08/97		
1.4 RN	44 kW	1.4 l	09/91→08/93		
1.6 D	40 kW	1.6 l	09/93→04/95		
1.6 D (F404)	40 kW	1.6 l	03/86→08/98		
1.9 D (F40P, F40N, F40E)	47 kW	1.9 l	09/91→03/98		
1.9 D (F40R)	40 kW	1.9 l	09/94→03/98		
<b>RENAULT - RODEO 4 (ACL_)</b>					<b>08/71→11/81</b>
0.8	25 kW	0.8 l	08/71→11/81	; 02/77 ->	KH00032 ProKIT
<b>RENAULT - RODEO 6 (ACL_)</b>					<b>08/73→11/81</b>
1.1	35 kW	1.1 l	08/73→11/81	; VIN 32708 ->	KH00032 ProKIT
<b>RENAULT - SAFRANE I / SAFRANE II (B54_)</b>					<b>04/92→12/00</b>
2.0 (B540)	77 kW	2 l	11/92→07/96	 ;	KH10085 ProKIT KH20036 ProKIT
2.0 12V (B542, B54E)	97 kW	2 l	04/92→07/96	 ;	KH10085 ProKIT KH20036 ProKIT KH20113 ProKIT
2.0 16V (B54L)	100 kW	2 l	07/96→12/00		KH10085 ProKIT
2.2 dT (B54G)	83 kW	2.2 l	07/96→12/00		
2.5 dT (B548)	83 kW	2.5 l	12/92→07/96		KH20113 ProKIT
3.0 V6 (B54B, B544)	123 kW	3 l	12/92→07/96		
3.0 V6 (B54M)	123 kW	3 l	07/96→12/00		









    				
<b>RENAULT - SAFRANE I / SAFRANE II (B54_)</b>				<b>04/92→12/00</b>
2.1 dT (B546)	65 kW	2.1 l	11/93→07/96	KH10085 ProKIT
3.0	125 kW	3 l	02/93→06/96	
3.0	125 kW	3 l	03/93→10/96	
3.0 Biturbo 4x4 (B545)	193 kW	3 l	02/93→07/96	
3.0 V6 4x4 (B54B, B544)	123 kW	3 l	12/92→07/96	
2.2 (B541)	79 kW	2.2 l	04/92→07/96	KH10085 ProKIT
2.2 (B543)	101 kW	2.2 l	04/92→07/96	; 02/95 -> ; ;
2.5 20V (B54F)	121 kW	2.5 l	07/96→12/00	KH20036 ProKIT
2.9 24V (B54N)	140 kW	2.9 l	03/99→12/00	; Outer diameter 1 [mm]: 84 
<b>RENAULT - SANDERO/STEPWAY I (BS_)</b>				<b>12/07→07/13</b>
1.4	55 kW	1.4 l	02/09→	; -> 04/17;
1.6	62 kW	1.6 l	11/10→	;
1.6	75 kW	1.6 l	12/07→	
1.6	77 kW	1.6 l	12/12→	
1.6 (BS0H, BS0F)	64 kW	1.6 l	02/09→	
1.6	76 kW	1.6 l	12/07→07/13	;
				;
1.6 Flex	77 kW	1.6 l	12/12→	;
<b>RENAULT - SANDERO/STEPWAY II (B8_)</b>				<b>11/13→</b>
1.2 16V	54 kW	1.2 l	12/13→	; -> 04/17;
1.2 16V LPG	53 kW	1.2 l	12/13→	;
1.5 dCi	62 kW	1.5 l	12/13→	
1.6	59 kW	1.6 l	11/13→	
1.6	60 kW	1.6 l	11/13→	
1.6	61 kW	1.6 l	11/13→	
1.2 16V	55 kW	1.2 l	04/15→	; -> 04/17;
1.6 (B8JA)	83 kW	1.6 l	09/16→	;
1.6 16V	75 kW	1.6 l	04/14→	
1.6 16V	81 kW	1.6 l	04/14→	
TCe 90 (B8MA, B8M1, B8JR)	66 kW	0.9 l	09/15→	
<b>RENAULT - SCÉNIC I MPV (JA0/1_, FA0_)</b>				<b>09/99→09/03</b>
1.4 16V (JA0D, JA1H, Ja0W, JA10)	70 kW	1.4 l	09/99→08/03	
1.8 16V (JA12, JA1R, JA1M, JA1A)	85 kW	1.8 l	01/01→08/03	; ;
1.9 dCi (JA05, JA1F)	75 kW	1.9 l	09/99→08/03	
1.9 dTi (JA0N)	72 kW	1.9 l	09/99→08/03	
1.9 dTi (JA1U)	59 kW	1.9 l	02/01→08/03	
2.0 16V (JA1B, JA1D, JA0C)	102 kW	2 l	07/00→08/03	
2.0 16V (JA1D, JA17)	103 kW	2 l	09/99→08/03	
1.6	75 kW	1.6 l	03/01→08/03	
1.6 (JA00, JA16, JA15, JA19, JA1V, JA2B, JA2C, JA0B,...)	79 kW	1.6 l	09/99→09/03	
1.6 BiFuel	75 kW	1.6 l	03/01→08/03	
1.6 BiFuel (JA04)	79 kW	1.6 l	09/99→04/01	
1.9 D (JA0J, FA0J)	47 kW	1.9 l	09/99→03/01	
1.9 dCi RX4	75 kW	1.9 l	11/00→08/03	; ; Code: JA05, JA1F
2.0 16V RX4	102 kW	2 l	06/00→08/03	; ; Code: JA0C, JA13, JA1S
<b>RENAULT - SCÉNIC II (JM0/1_)</b>				<b>06/03→07/10</b>
1.4 (JM0B, JM0H, JM1A)	72 kW	1.4 l	06/03→11/08	;
1.5 dCi (JM02, JM13)	74 kW	1.5 l	11/03→08/05	
1.5 dCi (JM0F)	60 kW	1.5 l	06/03→05/06	
1.5 dCi (JM16)	76 kW	1.5 l	01/07→11/08	
1.5 dCi (JM1E, JM16)	78 kW	1.5 l	05/05→11/08	
1.5 dCi (JM1F)	63 kW	1.5 l	05/05→11/08	
1.6	77 kW	1.6 l	06/06→11/08	
1.6 (JM0C, JM0J, JM1B)	83 kW	1.6 l	06/03→10/06	
1.6 16V (JM1R)	82 kW	1.6 l	10/05→11/08	
1.6 BiFuel	83 kW	1.6 l	08/03→05/06	
1.6 Hi-Flex	81 kW	1.6 l	03/05→07/10	
1.9 D	85 kW	1.9 l	06/06→11/08	
1.9 dCi	92 kW	1.9 l	06/03→11/08	
1.9 dCi (JM0G, JM12, JM1G, JM2C)	88 kW	1.9 l	06/03→05/06	
1.9 dCi (JM14)	96 kW	1.9 l	05/05→11/08	
1.9 dCi (JM15)	81 kW	1.9 l	05/05→11/08	
1.9 dCi 130	97 kW	1.9 l	10/05→12/09	
2.0 (JM05, JM0U, JM1N, JM1U, JM2V)	99 kW	2 l	06/03→06/09	






     				
<b>RENAULT - SCÉNIC II (JM0/1_)</b>				<b>06/03→07/10</b>
2.0 (JM0S, JM2N)	101 kW	2 l	02/08→04/09	  <b>KH10104 ProKIT</b>
2.0 16V Turbo (JM0W)	120 kW	2 l	05/04→11/08	  <b>KH10112 ProKIT</b>
2.0 dCi (JM1K)	110 kW	2 l	09/05→11/08	  <b>KH10104 ProKIT</b>
<b>RENAULT - SCÉNIC III (JZ0/1_)</b>				<b>12/08→</b>
1.2 TCe	85 kW	1.2 l	04/12→	 <b>KH10080 ProKIT</b>
1.2 TCe	96 kW	1.2 l	07/14→	
1.2 TCe (JZ16)	97 kW	1.2 l	01/13→	
1.4 16V (JZ0F, JZ1V)	96 kW	1.4 l	02/09→	
1.5 dCi	63 kW	1.5 l	04/09→	
1.5 dCi	78 kW	1.5 l	02/09→	
1.5 dCi	81 kW	1.5 l	04/09→	
1.5 dCi (JZ02, JZ0R)	70 kW	1.5 l	11/10→	
1.6 16V (JZ0U, JZ1B)	81 kW	1.6 l	02/09→	
1.6 16V Bifuel	79 kW	1.6 l	04/12→12/13	
1.6 16V Bifuel	81 kW	1.6 l	02/09→	
1.6 E85 (JZ03, JZ1Y)	81 kW	1.6 l	02/09→	
2.0 16V	101 kW	2 l	12/08→	
2.0 16V (JZ0G, JZ0P, JZ1E, JZ1P)	103 kW	2 l	02/09→	
<b>RENAULT - SPORT SPIDER (EF0_)</b>				<b>03/95→10/99</b>
2.0 16V	110 kW	2 l	03/95→10/99	  <b>KH10370 ProKIT</b>
<b>RENAULT - SUPER 5 / SUPER 5 Hatchback Van (B/C40_, S40_)</b>				<b>10/84→12/96</b>
1.0 (B/C/400)	30 kW	1 l	10/84→10/88	  <b>KH10075 ProKIT</b>
				  <b>KH10073 ProKIT</b>
1.0 (S400)	30 kW	1 l	10/84→10/88	 <b>KH10073 ProKIT</b>
1.1 (S401)	34 kW	1.1 l	10/84→12/96	
1.2 (S40F, S407)	44 kW	1.2 l	01/87→12/96	
1.4	44 kW	1.4 l	09/85→07/86	
1.4	85 kW	1.4 l	04/85→10/87	
1.4 Turbo GT (C405)	88 kW	1.4 l	01/85→05/91	
1.6 D (S404)	40 kW	1.6 l	10/84→12/96	
1.1	35 kW	1.1 l	10/89→12/90	  <b>KH10075 ProKIT</b>
1.1 (B/C/401, B/C40H)	33 kW	1.1 l	01/86→03/95	 <b>KH10073 ProKIT</b>
1.1 (B/C/401)	34 kW	1.1 l	10/84→10/88	
1.2 (B/C40F)	40 kW	1.2 l	01/87→08/90	
1.4	43 kW	1.4 l	08/86→12/96	
1.4 (B/C402)	43 kW	1.4 l	10/84→06/88	
1.4 (B/C403)	52 kW	1.4 l	10/84→07/89	
1.4 (B/C40J)	49 kW	1.4 l	06/87→07/89	
1.4 (B/C40M)	44 kW	1.4 l	06/87→08/90	
1.4 Cat (B/C/407)	43 kW	1.4 l	10/85→12/96	
1.4 Turbo (C405)	88 kW	1.4 l	04/85→08/90	
1.6 D	40 kW	1.6 l	04/85→12/90	
1.6 D (B/C/404)	40 kW	1.6 l	08/85→12/96	
1.7	66 kW	1.7 l	09/88→09/90	
1.7 (B/C408)	54 kW	1.7 l	10/86→03/95	
1.7 (B/C40K, B/C40G)	64 kW	1.7 l	06/87→03/95	
1.7 i (C409)	69 kW	1.7 l	10/86→08/91	
<b>RENAULT - THALIA I / THALIA II / THALIA III (LB_, LU_, L8_)</b>				<b>02/98→</b>
0.9 TCe	66 kW	0.9 l	06/14→06/14	  <b>KH10073 ProKIT</b>
1.0 (LB06, LB2R)	52 kW	1 l	06/00→01/05	
1.2 16V (LU2V)	55 kW	1.2 l	09/08→06/14	
1.2 LPG	55 kW	1.2 l	01/10→12/13	
1.4	55 kW	1.4 l	09/08→06/14	
1.4 16V	72 kW	1.4 l	08/00→	
1.5 dCi	47 kW	1.5 l	06/05→	
1.5 dCi	48 kW	1.5 l	04/02→	
1.5 dCi	50 kW	1.5 l	02/03→	
1.5 dCi	58 kW	1.5 l	04/04→11/09	
1.5 dCi	60 kW	1.5 l	06/01→02/09	
1.6	66 kW	1.6 l	03/98→	
1.6 16V	79 kW	1.6 l	07/00→02/09	
1.9 D	48 kW	1.9 l	02/98→05/01	
1.2 16V	55 kW	1.2 l	04/02→	  <b>KH10075 ProKIT</b>
1.4	55 kW	1.4 l	08/00→	  <b>KH10073 ProKIT</b>
1.4 (LB17)	72 kW	1.4 l	05/00→02/09	  <b>KH10057 ProKIT</b>
1.5 dCi	47 kW	1.5 l	09/08→	 <b>KH10073 ProKIT</b>
1.5 dCi	48 kW	1.5 l	01/09→	  <b>KH10073 ProKIT</b>
1.5 dCi	55 kW	1.5 l	07/14→06/14	
1.5 dCi	62 kW	1.5 l	09/08→	
1.5 dCi	66 kW	1.5 l	01/09→	












     					
<b>RENAULT - THALIA I / THALIA II / THALIA III (LB_, LU_, L8_)</b>					<b>02/98→</b>
1.5 dCi	60 kW	1.5 l	12/13→		KH10057 ProKIT
1.5 dCi (L8AJ)	66 kW	1.5 l	12/13→		
1.6 16V	77 kW	1.6 l	09/08→		KH10057 ProKIT
					KH10073 ProKIT
<b>RENAULT - TRAFIC II Bus / TRAFIC II Platform/Chassis (JL, EL)</b>					<b>03/01→10/06</b>
1.9 dCi	59 kW	1.9 l	04/01→07/03	; 12/02 →	KH10115 ProKIT
1.9 dCi	59 kW	1.9 l	09/01→07/03		KH10090 ProKIT
1.9 dCi 100 (EL0C)	74 kW	1.9 l	03/01→10/06	; 12/02 →	KH10115 ProKIT
1.9 dCi 100 (JL0C)	74 kW	1.9 l	03/01→10/06		
1.9 dCi 80 (EL0B)	60 kW	1.9 l	03/01→10/06	(ABS); → 11/02	KH10149 ProKIT
1.9 dCi 80 (JL0B)	60 kW	1.9 l	03/01→10/06	; → 11/02; (ABS)	KH10196 ProKIT
2.0 (ELOA)	88 kW	2 l	03/01→10/06		KH10090 ProKIT
2.5 dCi 135 (EL0D)	99 kW	2.5 l	03/01→10/06		
2.0 (JL0A)	88 kW	2 l	03/01→	; 12/02 →	KH10115 ProKIT
				(ABS); → 11/02	KH10149 ProKIT
				; → 11/02; (ABS)	KH10196 ProKIT
				; VIN C00001701 →	KH10405 ProKIT
					KH10090 ProKIT
2.0 16V	86 kW	2 l	08/06→		KH10115 ProKIT
2.0 dCi 115	84 kW	2 l	08/06→		
2.0 dCi 115 (EL0H)	84 kW	2 l	08/06→		KH10090 ProKIT
2.0 dCi 90	66 kW	2 l	08/06→		
2.0 dCi 90 (EL0H)	66 kW	2 l	08/06→		
2.5 dCi	84 kW	2.5 l	08/07→		
2.5 dCi 115	84 kW	2.5 l	02/08→		
2.5 dCi 145 (EL0J)	107 kW	2.5 l	08/06→		
2.5 dCi 145 (JL0J)	107 kW	2.5 l	08/06→		
2.5 dCi 135 (JL0D)	99 kW	2.5 l	05/03→10/06		KH10115 ProKIT
				; VIN C00001701 →	KH10405 ProKIT
					KH10090 ProKIT
<b>RENAULT - TRAFIC Bus (T5, T6, T7)</b>					<b>03/80→04/89</b>
1.4	35 kW	1.4 l	03/80→04/89	; → 12/88;	KH10405 ProKIT
				VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 →	
				; Manufacturer Restriction: T900,T900D; 03/89 →	KH00104 ProKIT
1.6	48 kW	1.6 l	01/84→06/86		KH10405 ProKIT
				VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 →	
1.6 4x4	48 kW	1.6 l	03/80→08/86		KH10405 ProKIT
1.7	50 kW	1.7 l	06/86→04/89	; → 12/88;	KH10405 ProKIT
				VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801 →	
				; Trim Level: T1000, T1000D; 03/89 →	KH00104 ProKIT
2.0	59 kW	2 l	06/86→04/89	; → 12/88;	KH10405 ProKIT
				VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801 →	
2.0 4x4	59 kW	2 l	06/86→04/89	; 03/89 →	KH10405 ProKIT
2.1 D	43 kW	2.1 l	03/80→04/89	; Trim Level: T1000, T1000D; 03/89 →	KH00104 ProKIT
<b>RENAULT - TRAFIC Bus (TXW)</b>					<b>05/89→03/01</b>
1.7	50 kW	1.7 l	08/92→08/94	; VIN C00001701 →	KH10405 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
1.9 D	44 kW	1.9 l	06/97→03/01	; 09/97 →; (ABS)	KH00096 ProKIT
2.0	59 kW	2 l	05/89→08/90	; VIN C00001701 →	KH10405 ProKIT
				; Type Mines No.: TYPE MIN T7 T8	KH00096 ProKIT
				; Trim Level: T1400, T3000	KH00104 ProKIT
2.1 D	43 kW	2.1 l	05/89→06/94	; Type Mines No.: TYPE MIN T7 T8	KH00096 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
2.1 D	47 kW	2.1 l	06/94→10/97	; 10/94 → 08/97; (ABS)	KH00096 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
2.2	70 kW	2.2 l	05/89→06/94	; VIN C00001701 →	KH10405 ProKIT
					KH00096 ProKIT
2.2	74 kW	2.2 l	06/94→10/97	; VIN C00001701 →	KH10405 ProKIT
				; 10/94 → 08/97	KH00096 ProKIT

     					
<b>RENAULT - TRAFIC Bus (TXW)</b>					<b>05/89→03/01</b>
2.5 D	55 kW	2.5 l	05/89→03/01	-> 12/98	KH00096 ProKIT
<b>RENAULT - TRAFIC Platform/Chassis (P6)</b>					<b>03/80→04/89</b>
1.4	35 kW	1.4 l	03/80→04/89	-> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 ->	KH10405 ProKIT
1.6	48 kW	1.6 l	03/80→06/86		KH10405 ProKIT
2.0	63 kW	2 l	03/80→12/86	VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 ->	KH10405 ProKIT
1.7	50 kW	1.7 l	06/86→04/89	-> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801 ->	KH10405 ProKIT
2.0	59 kW	2 l	03/80→04/89	-> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 ->	KH10405 ProKIT
				; 07/86 -> 02/89	KH00096 ProKIT
<b>RENAULT - TRAFIC Platform/Chassis (PXX)</b>					<b>05/89→03/01</b>
1.7	50 kW	1.7 l	05/89→08/94	; VIN C00001701 ->	KH10405 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
2.0 RWD	59 kW	2 l	05/89→10/97	; VIN C00001701 ->	KH10405 ProKIT
2.2	70 kW	2.2 l	05/89→06/94		KH00096 ProKIT
2.5 D	51 kW	2.5 l	05/89→03/01		KH00096 ProKIT
<b>RENAULT - TRAFIC Van (FL)</b>					<b>03/01→10/06</b>
1.9 dCi	59 kW	1.9 l	04/01→07/03	; 12/02 ->	KH10115 ProKIT
1.9 dCi	75 kW	1.9 l	03/01→		KH10090 ProKIT
1.9 dCi 100 (FL0C)	74 kW	1.9 l	03/01→10/06	; 12/02 ->	KH10115 ProKIT
1.9 dCi 80 (FL0B)	60 kW	1.9 l	03/01→10/06	; (ABS); -> 11/02	KH10149 ProKIT
				-> 11/02; (ABS)	KH10196 ProKIT
					KH10090 ProKIT
2.0 (FL0A)	88 kW	2 l	03/01→	; 12/02 ->	KH10115 ProKIT
				; (ABS); -> 11/02	KH10149 ProKIT
				-> 11/02; (ABS)	KH10196 ProKIT
				; VIN C00001701 ->	KH10405 ProKIT
					KH10090 ProKIT
2.0 16V	86 kW	2 l	08/06→		KH10115 ProKIT
2.0 dCi 115 (FL01, FL0U)	84 kW	2 l	08/06→		KH10090 ProKIT
2.0 dCi 90 (FL0H)	66 kW	2 l	08/06→		KH10090 ProKIT
2.5 dCi	84 kW	2.5 l	08/07→		KH10090 ProKIT
2.5 dCi 145 (FL0J)	107 kW	2.5 l	08/06→		KH10090 ProKIT
2.5 dCi 135 (FL0D)	99 kW	2.5 l	05/03→10/06		KH10115 ProKIT
				; VIN C00001701 ->	KH10405 ProKIT
					KH10090 ProKIT
<b>RENAULT - TRAFIC Van (T1, T3, T4, T2, TXX)</b>					<b>03/80→03/01</b>
1.4	35 kW	1.4 l	03/80→04/89	-> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 ->	KH10405 ProKIT
				; Manufacturer Restriction: T900,T900D; 03/89 ->	KH00104 ProKIT
1.4	35 kW	1.4 l	05/89→06/91	; VIN C00001701 ->	KH10405 ProKIT
1.6	48 kW	1.6 l	01/83→06/86		KH10405 ProKIT
				VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801, C00011201 ->	KH10405 ProKIT
1.6 4x4	48 kW	1.6 l	08/85→06/86		KH10405 ProKIT
2.2 4x4	70 kW	2.2 l	05/89→06/94		KH10405 ProKIT
2.2 4x4	74 kW	2.2 l	06/94→10/97		KH10405 ProKIT
1.7	50 kW	1.7 l	06/86→04/89	-> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801 ->	KH10405 ProKIT
				; Trim Level: T1000, T1000D; 03/89 ->	KH00104 ProKIT
1.7	50 kW	1.7 l	08/92→08/94	; VIN C00001701 ->	KH10405 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
1.9 D	44 kW	1.9 l	06/97→03/01	; 09/97 ->; (ABS)	KH00096 ProKIT



































































				    	
<b>RENAULT - TRAFIC Van (T1, T3, T4, T2, TXX)</b>				<b>03/80→03/01</b>	
2.0	59 kW	2 l	06/86→04/89	; -> 12/88; VIN B00002001,C00012401, B0003401,C00002351, C00000101, C00001701, C00002201, C00005801 ->	KH10405 ProKIT
				; 07/86 -> 02/89	KH00096 ProKIT
2.0	59 kW	2 l	05/89→08/90	; VIN C00001701 ->	KH10405 ProKIT
					KH00096 ProKIT
				; Trim Level: T1400, T3000	KH00104 ProKIT
2.0 4x4	59 kW	2 l	06/86→04/89	; 03/89 ->	KH10405 ProKIT
2.1 D	43 kW	2.1 l	09/80→04/89	; Trim Level: T1000, T1000D; 03/89 ->	KH00104 ProKIT
2.1 D 4x4	43 kW	2.1 l	11/86→04/89		
2.1 D	43 kW	2.1 l	05/89→06/94	; Type Mines No.: TYPE MIN T7 T8	KH00096 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
2.1 D	47 kW	2.1 l	06/94→10/97	; 10/94 -> 08/97; ABS	KH00096 ProKIT
				; Trim Level: T1400	KH00104 ProKIT
2.2	70 kW	2.2 l	05/89→06/94	; VIN C00001701 ->	KH10405 ProKIT
					KH00096 ProKIT
2.2	74 kW	2.2 l	06/94→10/97	; VIN C00001701 ->	KH10405 ProKIT
				; 10/94 -> 08/97	KH00096 ProKIT
2.5 D	55 kW	2.5 l	05/89→03/01		KH00096 ProKIT
<b>RENAULT - TWINGO I / TWINGO I Hatchback Van (C06_, S06_)</b>				<b>03/93→06/12</b>	
1.2	55 kW	1.2 l	01/01→06/12	; ABS	KH10075 ProKIT
1.2 (C063, C064)	40 kW	1.2 l	03/93→10/96		KH10073 ProKIT
1.2 (C066, C068)	43 kW	1.2 l	05/96→06/07		
1.2 (C067)	40 kW	1.2 l	05/96→03/07		
1.2 (S063, S064)	40 kW	1.2 l	03/93→05/96		
1.2 (S066, S068)	43 kW	1.2 l	05/96→08/04		
1.2 16V (C060)	44 kW	1.2 l	08/04→06/07		
1.2 16V (C06C, C06D, C06K)	55 kW	1.2 l	01/01→06/07		
1.2 LPG	43 kW	1.2 l	09/00→06/07		
1.2 LPG	44 kW	1.2 l	10/03→06/07		
<b>RENAULT - TWINGO II (CN0_)</b>				<b>03/07→09/14</b>	
1.2 (CN0D)	43 kW	1.2 l	03/07→09/14		KH10380 ProKIT
1.2 16V	55 kW	1.2 l	03/08→		KH10073 ProKIT
1.2 16V (CN04, CN0A, CN0B)	55 kW	1.2 l	03/07→09/14		
1.2 16V (CN0K, CN0V)	56 kW	1.2 l	03/07→		
1.2 TCe 100 (CN0P)	75 kW	1.2 l	02/11→		
1.2 Turbo (CN0C, CN0F)	74 kW	1.2 l	03/07→09/14		
1.5 dCi (CN0E)	47 kW	1.5 l	03/07→09/14		
1.5 dCi (CN0U)	62 kW	1.5 l	04/08→09/14		
1.5 dCi 75	55 kW	1.5 l	10/10→		
1.5 dCi 90	63 kW	1.5 l	10/10→		
1.6 RS (CN0N, CN0R, CN0S)	98 kW	1.6 l	05/08→09/14		KH10073 ProKIT
<b>RENAULT - TWINGO III (BCM_, BCA_)</b>				<b>09/14→</b>	
0.9 TCe 110	80 kW	0.9 l	11/16→		KH30029 ProKIT
0.9 TCe 90	66 kW	0.9 l	09/14→		
1.0 SCe 70	52 kW	1 l	09/14→		
1.0 SCe 70 (BCMB)	51 kW	1 l	09/15→		
<b>RENAULT - VEL SATIS (BJ0_)</b>				<b>06/02→</b>	
2.0 16 V Turbo	125 kW	2 l	04/04→		KH10115 ProKIT
2.0 16V Turbo (BJ0K)	120 kW	2 l	06/02→08/09		
2.0 dCi (BJ03, BJ0B)	127 kW	2 l	01/06→		
2.0 dCi (BJ03)	110 kW	2 l	08/05→		
2.0 Turbo	108 kW	2 l	04/05→		
2.2 dCi (BJ0E, BJ0F, BJ0G, BJ0H)	102 kW	2.2 l	09/04→		
2.2 dCi (BJ0E, BJ0F)	110 kW	2.2 l	06/02→08/09		
2.2 dCi (BJ0H)	85 kW	2.2 l	04/04→		
2.2 dCi (BJ0M)	83 kW	2.2 l	12/04→		
3.0 dCi (BJ0J, BJ0N)	130 kW	3 l	06/02→06/06		
3.0 dCi (BJ0S)	133 kW	3 l	06/06→08/09		
3.5 (BJ01)	170 kW	3.5 l	10/04→		
3.5 V6 (BJ0R, BJ0V, BJ0U)	177 kW	3.5 l	06/02→		
<b>RENAULT - VIRAGE Saloon / VIRAGE Variable (117_)</b>				<b>10/69→08/80</b>	
1.3 (1170)	37 kW	1.3 l	07/75→04/80	; 09/77 -> 12/79;	KH00090 ProKIT
1.3 (1170)	40 kW	1.3 l	10/69→08/80	VIN 13263, 1523070, 336271, 345641, 7545 ->	
1.3 (1170)	40 kW	1.3 l	10/70→08/80		KH00032 ProKIT
1.3 (1177)	44 kW	1.3 l	08/73→08/80	; 10/77 ->	
1.3 TS (1177, 1337)	44 kW	1.3 l	08/72→08/80	; 10/77 ->	KH00032 ProKIT
































     				
<b>RENAULT - WIND (E4M_)</b>				<b>07/10→</b>
1.2 (E4MF)	74 kW	1.2 l	07/10→	 <b>KH10076</b> ProKIT
1.2 TCe 100 (E4MF)	75 kW	1.2 l	02/11→	
1.6 (E4MB, E4MC)	98 kW	1.6 l	07/10→	
<b>RENAULT - ZOE (BFM_)</b>				<b>06/12→</b>
ZOE	65 kW		06/12→	 <b>KH10013</b> ProKIT
				 <b>KH10142</b> ProKIT









<b>ROVER - 25 I Hatchback (RF)</b>				<b>10/99→05/05</b>	
1.1 16V	55 kW	1.1 l	01/04→05/05	; ;	KH20144 ProKIT
1.4 16V	62 kW	1.4 l	10/99→05/05	;	KH20145 ProKIT
1.4 16V	76 kW	1.4 l	10/99→05/05		
1.6 16V	80 kW	1.6 l	10/99→05/05		
1.8 16V	85 kW	1.8 l	10/99→05/05		
1.8 16V	107 kW	1.8 l	02/00→05/05		
2.0 iDT	74 kW	2 l	10/99→05/05		
<b>ROVER - 45 I Hatchback / 45 I Saloon (RT)</b>				<b>02/00→05/05</b>	
1.4	76 kW	1.4 l	02/00→05/05	-> YD471063; ;	KH20145 ProKIT
1.6	80 kW	1.6 l	02/00→05/05	YD471064 ->;	
1.8	86 kW	1.8 l	02/00→05/05		
2.0 iDT	74 kW	2 l	02/00→05/05		KH10357 ProKIT
2.0 V6	110 kW	2 l	02/00→05/05	; ;	KH20144 ProKIT
2.0 iDT	74 kW	2 l	02/00→05/05	-> YD471063; ;	KH20145 ProKIT
				YD471064 ->;	
					KH10357 ProKIT
				;	KH20144 ProKIT
<b>ROVER - 75 I Tourer / 75 Sedan (RJ)</b>				<b>02/99→05/05</b>	
1.8	88 kW	1.8 l	02/99→05/05		KH10148 ProKIT
1.8	88 kW	1.8 l	08/01→05/05		KH20098 ProKIT
1.8 Turbo	110 kW	1.8 l	05/03→05/05		
2.0 CDT	85 kW	2 l	02/99→05/05		
2.0 CDT	85 kW	2 l	08/01→05/05		
2.0 CDTi	96 kW	2 l	02/03→04/05		
2.0 CDTi	96 kW	2 l	02/03→05/05		
2.0 V6	110 kW	2 l	02/99→05/05		
2.0 V6	110 kW	2 l	08/01→05/05		
2.5 V6	129 kW	2.5 l	02/99→10/01		
2.5 V6	130 kW	2.5 l	08/01→05/05		
2.5 V6	130 kW	2.5 l	10/01→05/05		
<b>ROVER - 100 / METRO Hatchback / 100 Convertible (XP)</b>				<b>03/90→12/98</b>	
111	44 kW	1.1 l	04/94→10/97	; 01/95 ->	KH10189 ProKIT
114	55 kW	1.4 l	04/94→10/97		KH00135 ProKIT
111 C/L/S	44 kW	1.1 l	03/90→12/98	; 01/95 ->	KH10189 ProKIT
114 S/L/GTA	55 kW	1.4 l	03/90→12/98	; 05/90 ->	KH00135 ProKIT
114	75 kW	1.4 l	03/97→10/98		KH00135 ProKIT
114 GTI 16V	76 kW	1.4 l	08/91→12/98		
114 GTI/GT 16V Cat	66 kW	1.4 l	03/90→12/98	; 05/90 ->	KH00135 ProKIT
114 GTI 16V	69 kW	1.4 l	03/90→08/91		
115 D	42 kW	1.5 l	12/94→12/98	; 01/95 -> 10/98	KH10189 ProKIT
				; 01/95 ->	KH00135 ProKIT
<b>ROVER - 200 II Convertible (XW)</b>				<b>04/90→11/99</b>	
214 1.4	66 kW	1.4 l	01/92→11/99		KH20144 ProKIT
214 1.4	70 kW	1.4 l	04/90→09/92		
214 1.4i 16V	76 kW	1.4 l	01/93→11/99		
216 1.6i	90 kW	1.6 l	01/92→11/99		
216 1.6i 16V	82 kW	1.6 l	01/96→11/99		
<b>ROVER - 200 II Hatchback (RF)</b>				<b>11/95→03/00</b>	
211	44 kW	1.1 l	01/98→03/00	; ;	KH20144 ProKIT
214 i	55 kW	1.4 l	11/95→03/00		KH20145 ProKIT
214 Si	76 kW	1.4 l	11/95→03/00	;	
216 Si	82 kW	1.6 l	11/95→06/99		
218 K Vi	107 kW	1.8 l	11/95→03/00		
220 D/SD	63 kW	2 l	11/95→03/00		
220 SDi	77 kW	2 l	11/95→03/00		
<b>ROVER - 200 II Hatchback / 200 Coupe (XW)</b>				<b>10/89→06/99</b>	
214	55 kW	1.4 l	09/93→12/95		KH20144 ProKIT
214 GSi/Si	70 kW	1.4 l	01/90→10/95		
214 GSi/Si	76 kW	1.4 l	12/92→10/95		
214 Si/Gsi	66 kW	1.4 l	10/89→10/95		
216	90 kW	1.6 l	10/92→06/99		
216 GSi	82 kW	1.6 l	01/90→12/95		
216 GTi	90 kW	1.6 l	01/90→10/95		
218 TD	65 kW	1.8 l	09/91→10/95		
220 GSi	100 kW	2 l	05/94→06/99		
220 GTi	100 kW	2 l	01/93→10/95		
220 GTi	103 kW	2 l	09/91→10/95		
220 Turbo	147 kW	2 l	10/92→06/99		
220 Turbo	147 kW	2 l	01/93→12/95		

										
<b>ROVER - 400 II (RT)</b>										<b>03/95→03/00</b>
414 Si	76 kW	1.4 l	05/95→03/00		VIN → YD471063;	MT ;				KH20145 ProKIT
416 Si	82 kW	1.6 l	05/95→03/00		VIN YD471064 →;					
420 D	63 kW	2 l	11/95→03/00		04/96 → 12/99					KH10357 ProKIT
420 Di	77 kW	2 l	05/95→03/00							KH20144 ProKIT
420 Si Lux	100 kW	2 l	12/95→03/00							
416 Si	83 kW	1.6 l	03/95→06/99		VIN → YD471063;	MT ;				KH20145 ProKIT
					VIN YD471064 →;					
					04/96 →					KH10357 ProKIT
										KH20144 ProKIT
<b>ROVER - 400 II (XW)</b>										<b>04/90→04/95</b>
414 GSI/SI	66 kW	1.4 l	04/90→04/95							KH20144 ProKIT
414 GSI/SI Cat	76 kW	1.4 l	10/92→04/95							
416 GSI	82 kW	1.6 l	04/90→04/95							
416 GTI	90 kW	1.6 l	04/90→04/95							
418 D	49 kW	1.9 l	09/91→04/95							
418 TD	65 kW	1.8 l	09/91→04/95							
420 GSI/SLI/GTI/Vite	100 kW	2 l	01/93→04/95							
420 GTI/GSI/Vitesse	103 kW	2 l	02/92→04/95							
420 Turbo	147 kW	2 l	01/93→04/95							
<b>ROVER - 400 II Hatchback (RT)</b>										<b>05/95→03/00</b>
414	55 kW	1.4 l	03/96→12/97		VIN → YD471063;	MT ;				KH20145 ProKIT
					VIN YD471064 →;					
414 Si	76 kW	1.4 l	05/95→03/00		VIN → YD471063;	MT ;				KH20145 ProKIT
416 Si	82 kW	1.6 l	05/95→03/00		VIN YD471064 →;					
416 Si	83 kW	1.6 l	06/95→03/00		04/96 → 12/99					KH10357 ProKIT
420 D	63 kW	2 l	11/95→03/00							KH20144 ProKIT
420 Di	77 kW	2 l	05/95→03/00							
420 Si Lux	100 kW	2 l	12/95→03/00							
<b>ROVER - 400 Tourer (XW)</b>										<b>09/93→11/98</b>
1.6 i	82 kW	1.6 l	05/94→11/98		04/96 →					KH10357 ProKIT
1.6 i	90 kW	1.6 l	05/94→11/98							KH20144 ProKIT
1.8 TD	65 kW	1.8 l	09/93→11/98							KH20145 ProKIT
2.0 i	100 kW	2 l	05/94→11/98		VIN 911249 →					
1.8 i	107 kW	1.8 l	06/96→11/98							KH10357 ProKIT
										KH20144 ProKIT
					VIN 911249 →					KH20145 ProKIT
<b>ROVER - 800 / 800 Coupe / 800 Hatchback (XS)</b>										<b>10/86→02/99</b>
2.5	129 kW	2.5 l	02/96→10/98							KH10202 ProKIT
2.5 Si	129 kW	2.5 l	02/96→10/98							
820 16 V I/SI (XS)	103 kW	2 l	10/86→10/88							
820 I/SI (RS)	100 kW	2 l	01/92→02/99							
820 i/Si (XS)	103 kW	2 l	10/88→12/91							
820 I/SI (XS)	100 kW	2 l	01/91→02/99							
820 Si (XS)	98 kW	2 l	10/88→12/91							
820 Sport	145 kW	2 l	04/94→03/96							
825 D/SD (XS)	87 kW	2.5 l	01/92→02/99							
825 Si (RS)	129 kW	2.5 l	04/96→02/99							
820	74 kW	2 l	10/88→10/91		→ 09/90					KH10202 ProKIT
825 D/SD (XS)	87 kW	2.5 l	01/90→02/99		12/91 →					KH10202 ProKIT
825 Si/Sterling (XS)	123 kW	2.5 l	10/86→10/88		→ 02/88					KH10202 ProKIT
825 Si/Sterling (XS)	127 kW	2.5 l	01/87→12/91							
827 24V (RS)	124 kW	2.7 l	08/92→02/99		→ 03/96					KH10202 ProKIT
827 24V I/SI Cat (RS)	124 kW	2.7 l	01/92→02/99							
827 Si/Sterling Catalytic-Conv (XS)	124 kW	2.7 l	02/88→02/99		10/91 → 03/96					KH10202 ProKIT
827 Vitesse/SLI	130 kW	2.7 l	10/88→12/91		→ 08/91					KH10202 ProKIT
827 Vitesse Catalytic-Conv (XS)	124 kW	2.7 l	10/88→12/91		10/91 →					KH10202 ProKIT
<b>ROVER - 2000-3500 Hatchback (SD1)</b>										<b>06/76→10/86</b>
2000	74 kW	2 l	10/82→10/86							KH00126 ProKIT
2600 S	93 kW	2.6 l	10/82→10/86							
3500	115 kW	3.5 l	06/76→10/86							
3500 Vitesse	142 kW	3.5 l	10/82→10/86							
2300	92 kW	2.3 l	09/77→10/86		10/77 →					KH00126 ProKIT
2400 TD	67 kW	2.4 l	05/82→10/86		06/82 → 01/86					KH00126 ProKIT
2600	99 kW	2.6 l	09/77→10/82		10/80 →					KH00126 ProKIT
<b>ROVER - A60 CAMBRIDGE Saloon</b>										<b>01/62→10/69</b>
1.7	46 kW	1.7 l	01/62→10/69							KH00121 ProKIT



     						
<b>ROVER - COUPE</b>					<b>03/96→11/99</b>	
1.6 16 V	82 kW	1.6 l	03/96→11/99		KH20144 ProKIT	
1.8 16 V	107 kW	1.8 l	03/96→11/99			
<b>ROVER - MAESTRO Hatchback</b>					<b>09/90→01/95</b>	
1.3	51 kW	1.3 l	09/90→01/95	 -> 03/93	KH10189 ProKIT	
2.0 D	44 kW	2 l	09/90→10/92	 -> 08/92	KH10189 ProKIT	
2.0 TD	60 kW	2 l	09/90→01/95	 ; 09/92 -> 03/93	KH10189 ProKIT	
<b>ROVER - MINI Convertible / MINI Hatchback (XN)</b>					<b>08/90→11/00</b>	
1000	30 kW	1 l	08/90→06/93		KH00051 ProKIT	
1300	37 kW	1.3 l	10/92→11/00	 -> 06/97	KH00051 ProKIT	
				 -> 12/99	KH00046 ProKIT	
1300	39 kW	1.3 l	01/92→04/95		KH00051 ProKIT	
				 ; 06/92 ->	KH00046 ProKIT	
1300	45 kW	1.3 l	01/91→12/91		KH00051 ProKIT	
1300	46 kW	1.3 l	09/92→04/95		KH00046 ProKIT	
1300	46 kW	1.3 l	01/92→11/00	 -> 06/97	KH00051 ProKIT	
				 ; 06/92 -> 12/99	KH00046 ProKIT	
<b>ROVER - MONTEGO / MONTEGO Estate (XE)</b>					<b>02/85→10/95</b>	
1.6	61 kW	1.6 l	10/90→09/92		KH10189 ProKIT	
2.0 D Turbo	60 kW	2 l	10/88→10/95	 -> 01/95	KH10189 ProKIT	
2.0 GTi	86 kW	2 l	02/85→10/91	 ; 11/88 ->; VIN 462777 ->; MT	KH10189 ProKIT	
				11/88 ->;  ; VIN 464731 ->; AT		
2.0 GTi	86 kW	2 l	10/88→10/91	 ; 11/88 ->; AT; VIN 464731 ->	KH10189 ProKIT	
				 ; MT; VIN 462777 ->		
2.0 GTi/LXi	75 kW	2 l	12/90→12/93	 -> 11/91; MT; VIN 462777 ->	KH10189 ProKIT	
2.0 i Cat	75 kW	2 l	12/90→10/94	 -> 11/91; VIN 462777, 464731 ->	KH10189 ProKIT	
<b>ROVER - STREETWISE Hatchback</b>					<b>08/03→05/05</b>	
1.4	62 kW	1.4 l	08/03→05/05	 (ABS); 	KH20145 ProKIT	
1.4	76 kW	1.4 l	08/03→05/05			
2.0 TD	74 kW	2 l	08/03→05/05			

SAAB - 9-3 (YS3D)				02/98→09/02		
2.0 i	96 kW	2 l	02/98→09/02	VIN X2028829 ->	KH10222 ProKIT	
2.0 SE Turbo	147 kW	2 l	02/98→09/02		KH30114 ProKIT	
2.0 Turbo	110 kW	2 l	03/99→09/02			
2.0 Turbo	113 kW	2 l	10/98→09/02			
2.0 Turbo	136 kW	2 l	02/98→09/02			
2.0 Turbo	151 kW	2 l	10/99→09/02			
2.2 TiD	85 kW	2.2 l	02/98→11/00			
2.2 TiD	92 kW	2.2 l	11/00→09/02			
2.3 i	110 kW	2.3 l	02/98→09/02			
2.3 Turbo	165 kW	2.3 l	10/98→09/02			
2.3	169 kW	2.3 l	09/99→01/02			KH30114 ProKIT
SAAB - 9-3 (YS3F, E79, D79, D75)				09/02→02/15		
1.8t	110 kW	2 l	09/02→02/15		KH10222 ProKIT	
2.0 t	129 kW	2 l	09/02→02/15		KH30061 ProKIT	
2.0 t	154 kW	2 l	09/02→02/15		KH30071 ProKIT	
2.2 TiD	92 kW	2.2 l	09/02→02/15		KH30071 ProKIT	
1.8t BioPower	129 kW	2 l	05/09→02/15		KH30061 ProKIT	
1.8 i	90 kW	1.8 l	01/04→02/15		KH30071 ProKIT	
1.9 TiD	88 kW	1.9 l	09/04→02/15		KH30071 ProKIT	
1.9 TiD	110 kW	1.9 l	09/04→02/15			
2.0 t BioPower	147 kW	2 l	05/09→02/15			
1.9 TTTiD	132 kW	1.9 l	12/07→02/15			
2.0 t	177 kW	2 l	05/09→02/15			
2.0 t BioPower	129 kW	2 l	01/07→02/15			
2.0 t BioPower	154 kW	2 l	09/02→02/15			
2.0 Turbo XWD	154 kW	2 l	01/08→02/15			
2.8 Turbo V6	188 kW	2.8 l	12/07→02/15			
2.8 Turbo V6 XWD	206 kW	2.8 l	05/08→12/11			
2.8 Turbo V6	184 kW	2.8 l	03/05→02/15		KH30061 ProKIT	
				06/05 ->	KH30071 ProKIT	
SAAB - 9-3 Cabriolet (YS3D)				02/98→08/03		
2.0 i	96 kW	2 l	02/98→08/03	VIN X2028829 ->	KH10222 ProKIT	
2.0 SE Turbo	147 kW	2 l	02/98→08/03		KH30114 ProKIT	
2.0 Turbo	110 kW	2 l	01/01→08/03			
2.0 Turbo	113 kW	2 l	10/98→08/03			
2.0 Turbo	136 kW	2 l	02/98→08/03			
2.0 Turbo	151 kW	2 l	10/99→08/03			
2.3 i	110 kW	2.3 l	02/98→08/03			
2.3 Turbo	165 kW	2.3 l	10/99→08/03			
2.3	169 kW	2.3 l	09/99→01/02			KH30114 ProKIT
SAAB - 9-3 Convertible / 9-3 Estate (YS3F, E50)					08/03→02/15	
1.8t	110 kW	2 l	08/03→02/15			KH10222 ProKIT
2.0 t	129 kW	2 l	08/03→02/15		KH30061 ProKIT	
2.0 t	154 kW	2 l	08/03→02/15		KH30071 ProKIT	
1.8 i	90 kW	1.8 l	03/05→02/15		KH30061 ProKIT	
1.8t 2.0	110 kW	2 l	03/05→02/15		KH30071 ProKIT	
1.9 TiD	88 kW	1.9 l	03/05→02/15			
1.9 TiD	110 kW	1.9 l	03/05→02/15			
2.0 t	129 kW	2 l	03/05→02/15			
2.0 t	154 kW	2 l	03/05→02/15			
2.8 Turbo V6	184 kW	2.8 l	03/05→02/15			
1.9 TiD	110 kW	1.9 l	01/06→02/15			
					02/06 ->	KH30061 ProKIT
1.9 TTTiD	132 kW	1.9 l	12/07→02/15			KH30061 ProKIT
2.0 t	110 kW	2 l	03/05→02/15			KH30071 ProKIT
2.0 t	147 kW	2 l	02/09→02/15			
2.0 t BioPower	129 kW	2 l	01/07→02/15			
2.0 t XWD	154 kW	2 l	06/08→02/15			
2.8 Turbo V6	188 kW	2.8 l	12/07→02/15			
2.8 Turbo V6	203 kW	2.8 l	02/09→02/15			
2.8 Turbo V6	206 kW	2.8 l	02/09→02/15			
2.8 Turbo V6 XWD	206 kW	2.8 l	05/08→12/11			
2.0 t BioPower	129 kW	2 l	01/07→02/15			KH30061 ProKIT
2.0 t BioPower	147 kW	2 l	06/07→02/15	07/07 ->		KH30071 ProKIT
2.8 Turbo V6	184 kW	2.8 l	02/06→02/15		KH30061 ProKIT	
					KH30071 ProKIT	

				     13 		
<b>SAAB - 9-5 (YS3G)</b>				<b>05/10→01/12</b>		
1.6 Turbo	132 kW	1.6 l	05/10→01/12		KH30070 ProKIT	
2.0 t BioPower	162 kW	2 l	05/10→01/12		KH30105 ProKIT	
2.0 TiD	118 kW	2 l	05/10→01/12			
2.0 TTiD	140 kW	2 l	05/10→01/12			
2.0 Turbo	162 kW	2 l	05/10→01/12			
2.0 t BioPower XWD	162 kW	2 l	05/10→01/12		KH30070 ProKIT	
2.0 TTiD XWD	140 kW	2 l	05/10→01/12		KH30196 ProKIT	
2.0 Turbo XWD	162 kW	2 l	05/10→01/12			
2.8 Turbo V6 XWD	221 kW	2.8 l	05/10→01/12			
<b>SAAB - 9-5 Estate / 9-5 Sedan (YS3E)</b>				<b>09/97→12/09</b>		
1.9 TiD	110 kW	1.9 l	01/06→12/09	; VIN X3025771 ->	KH30098 ProKIT	
2.3 t BioPower	154 kW	2.3 l	11/06→12/09			
2.3 Turbo	191 kW	2.3 l	11/05→12/09			
2.3 Turbo	191 kW	2.3 l	01/06→12/09			
2.0 t	110 kW	2 l	09/97→12/09	; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
2.0 t	110 kW	2 l	10/98→12/09	; VIN X3025769 ->	KH10222 ProKIT	
3.0 V6t	147 kW	3 l	01/98→12/09	; 01/99 -> 09/05	KH30122 ProKIT	
3.0 V6t	147 kW	3 l	10/98→12/09			
2.0 t	136 kW	2 l	07/00→12/09	; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
2.0 t	141 kW	2 l	10/98→07/00	; VIN X3025769 ->	KH10222 ProKIT	
2.2 TiD	88 kW	2.2 l	03/02→12/09		KH10222 ProKIT	
				; VIN X3025771 ->	KH30098 ProKIT	
				; -> 09/05	KH30122 ProKIT	
2.3 t	125 kW	2.3 l	09/97→12/09	; 01/99 -> 12/01; VIN X3025769 ->	KH30122 ProKIT	
2.3 t	125 kW	2.3 l	10/98→12/09	; 01/02 -> 09/05	KH30122 ProKIT	
				; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
				; VIN X3025769 ->	KH10222 ProKIT	
2.3 t	136 kW	2.3 l	01/01→12/09	; -> 12/01; VIN X3025769 ->	KH30122 ProKIT	
				; 01/02 -> 09/05	KH30122 ProKIT	
				; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
					KH10222 ProKIT	
2.3 Turbo	162 kW	2.3 l	07/03→12/09		KH10222 ProKIT	
				; VIN X3025771 ->	KH30098 ProKIT	
2.3 Turbo	169 kW	2.3 l	10/99→09/01	; VIN X3025769 ->	KH10222 ProKIT	
					KH30122 ProKIT	
2.3 Turbo	184 kW	2.3 l	09/01→12/09	; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
					KH10222 ProKIT	
				; -> 09/05	KH30122 ProKIT	
3.0 TiD	130 kW	3 l	07/01→12/09	; 01/02 ->; VIN X3025771 ->	KH30098 ProKIT	
					KH10222 ProKIT	
				; 09/01 -> 09/05	KH30122 ProKIT	
<b>SAAB - 900 II Convertible / 900 II Coupe</b>				<b>12/93→02/98</b>		
2.0 -16 Turbo	136 kW	2 l	12/93→02/98		KH30114 ProKIT	
2.0 i	96 kW	2 l	12/93→02/98			
2.0 i	96 kW	2 l	08/94→02/98			
2.0 i	98 kW	2 l	12/93→07/94			
2.3 -16	110 kW	2.3 l	12/93→02/98			
2.5 -24 V6	125 kW	2.5 l	12/93→02/98			































**SANTANA - 300/350**



























**09/98→**
























1.6 D 4x4	66 kW	1.6 l	09/98→		<b>KH10072 ProKIT</b>
1.6 HDi 4x4	66 kW	1.6 l	07/06→02/11		



     				
<b>SEAT - 127 (127A)</b>				<b>04/72→12/82</b>
0.9	33 kW	0.9 l	04/72→12/82	 ; 01/76 -> <b>KH10369 ProKIT</b>
1.0	38 kW	1 l	04/72→12/82	 ; 10/76 -> <b>KH20091 ProKIT</b>
<b>SEAT - 128 (128A)</b>				<b>01/76→12/80</b>
1.2	49 kW	1.2 l	01/76→12/80	 <b>KH10369 ProKIT</b>
1.4	57 kW	1.4 l	01/76→12/80	 <b>KH20091 ProKIT</b>
<b>SEAT - 600 (110B)</b>				<b>09/63→04/70</b>
0.8	17 kW	0.8 l	09/63→04/70	 <b>KH00075 ProKIT</b>
<b>SEAT - ALHAMBRA (7V8, 7V9)</b>				<b>04/96→03/10</b>
1.8 T 20V	110 kW	1.8 l	10/97→03/10	 <b>KH10084 ProKIT</b>
				 ; 05/98 -> <b>KH10208 ProKIT</b>
1.9 TDI	66 kW	1.9 l	04/96→03/10	 <b>KH10084 ProKIT</b>
1.9 TDI	85 kW	1.9 l	06/00→03/10	 <b>KH10208 ProKIT</b>
1.9 TDI	96 kW	1.9 l	11/02→11/08	
2.0 i	85 kW	2 l	04/96→03/10	
2.0 TDI	103 kW	2 l	11/05→03/10	
2.8 V6	150 kW	2.8 l	06/00→03/10	
1.9 TDI	81 kW	1.9 l	08/96→06/00	 <b>KH10084 ProKIT</b>
				 ; 09/97 -> 05/00 <b>KH10208 ProKIT</b>
1.9 TDI	110 kW	1.9 l	05/05→05/07	 <b>KH10084 ProKIT</b>
				 ; 06/05 -> <b>KH10208 ProKIT</b>
1.9 TDI 4motion	85 kW	1.9 l	06/00→03/10	 <b>KH10084 ProKIT</b>
2.8 V6 4motion	150 kW	2.8 l	06/00→03/10	
<b>SEAT - ALHAMBRA (710, 711)</b>				<b>06/10→</b>
1.4 TSI	110 kW	1.4 l	06/10→04/15	 <b>KH30002 ProKIT</b>
1.4 TSI	110 kW	1.4 l	05/15→	
1.8 TSI	118 kW	1.8 l	11/12→04/15	 ; Inner diameter 1 [mm]: 32 <b>KH20004 ProKIT</b>
2.0 TDI	85 kW	2 l	05/11→	
2.0 TDI	100 kW	2 l	06/10→05/11	
2.0 TDI	103 kW	2 l	06/10→	
2.0 TDI	110 kW	2 l	05/15→	
2.0 TDI	125 kW	2 l	06/10→02/13	
2.0 TDI	130 kW	2 l	11/12→	
2.0 TDI	135 kW	2 l	05/15→	
2.0 TFSI	147 kW	2 l	11/10→05/12	
2.0 TSI	162 kW	2 l	05/15→	
2.0 TDi 4Drive	130 kW	2 l	11/18→	 <b>KH30002 ProKIT</b>
2.0 TDI 4Drive	103 kW	2 l	05/11→04/15	
2.0 TDI 4Drive	110 kW	2 l	05/15→	
2.0 TDI 4Drive	135 kW	2 l	05/16→	
<b>SEAT - ALHAMBRA VAN (711)</b>				<b>05/15→</b>
TDI	110 kW	2 l	05/15→	 <b>KH30002 ProKIT</b>
TDI	135 kW	2 l	05/15→	
TDI 4Drive	110 kW	2 l	05/15→	
TSi	110 kW	1.4 l	05/15→	
<b>SEAT - ALTEA / ALTEA XL (5P1, 5P5, 5P8)</b>				<b>03/04→</b>
1.2 TSI	77 kW	1.2 l	04/10→	 ; Number of mounting bores: 4 <b>KH30002 ProKIT</b>
1.4 16V	63 kW	1.4 l	05/06→	
1.4 16V	63 kW	1.4 l	10/06→	 ; Number of mounting bores: 3 <b>KH30048 ProKIT</b>
1.4 TSI	92 kW	1.4 l	11/07→	 ; Inner diameter 1 [mm]: 30 <b>KH20003 ProKIT</b>
1.6	75 kW	1.6 l	03/04→	 ; Inner diameter 1 [mm]: 32 <b>KH20004 ProKIT</b>
1.6	75 kW	1.6 l	10/06→	
1.6 LPG	75 kW	1.6 l	09/09→	
1.6 Multifuel	75 kW	1.6 l	10/06→11/10	
1.6 Multifuel	75 kW	1.6 l	11/10→05/11	
1.6 TDI	66 kW	1.6 l	11/10→	
1.6 TDI	77 kW	1.6 l	10/09→	
1.8 TFSI	118 kW	1.8 l	01/07→	
1.9 TDI	66 kW	1.9 l	08/09→	
1.9 TDI	66 kW	1.9 l	08/09→12/10	
1.9 TDI	77 kW	1.9 l	04/04→	
1.9 TDI	77 kW	1.9 l	10/06→12/10	
2.0 FSI	110 kW	2 l	05/04→03/09	
2.0 FSI	110 kW	2 l	10/06→03/09	
2.0 TDI	100 kW	2 l	03/04→05/09	
2.0 TDI	100 kW	2 l	11/06→03/09	
2.0 TDI	103 kW	2 l	11/05→	
2.0 TDI	103 kW	2 l	10/06→	
2.0 TDI	125 kW	2 l	03/06→	
2.0 TDI	125 kW	2 l	06/07→12/13	



     				
<b>SEAT - ALTEA / ALTEA XL (5P1, 5P5, 5P8)</b>				<b>03/04→</b>
2.0 TDI 16V	103 kW	2 l	03/04→	 ; Number of mounting bores: 4 KH30002 ProKIT
2.0 TDI 16V	103 kW	2 l	10/06→	 ; Number of mounting bores: 3 KH30048 ProKIT
2.0 TFSI	147 kW	2 l	04/06→05/09	 ; Inner diameter 1 [mm]: 30 KH20003 ProKIT
2.0 TFSI	147 kW	2 l	10/06→05/09	 ; Inner diameter 1 [mm]: 32 KH20004 ProKIT
2.0 TFSI	155 kW	2 l	05/09→	 ; Number of mounting bores: 4 KH30002 ProKIT
1.9 TDI 4x4	77 kW	1.9 l	06/09→12/10	 ; Number of mounting bores: 3 KH30048 ProKIT
2.0 TDI 16V 4WD	103 kW	2 l	10/10→	
2.0 TDI 16V 4x4	103 kW	2 l	10/10→	
2.0 TDI 4x4	103 kW	2 l	06/07→	
2.0 TDI 4x4	125 kW	2 l	06/07→05/09	
2.0 TFSI 4x4	147 kW	2 l	06/07→05/09	
2.0 TFSI 4x4	155 kW	2 l	05/09→	
<b>SEAT - AROSA (6H1)</b>				<b>05/97→06/04</b>
1.0	37 kW	1 l	05/97→06/04	 KH10358 ProKIT
1.0	37 kW	1 l	10/98→01/01	 ; VIN -> 6H-X-027 500 KH00003 ProKIT
1.4	44 kW	1.4 l	05/97→06/04	 ; VIN 6H-X-027 501 -> KH20117 ProKIT
1.4 16V	74 kW	1.4 l	01/00→06/04	
1.4 TDI	55 kW	1.4 l	01/00→06/04	
1.7 SDI	44 kW	1.7 l	08/97→06/04	
<b>SEAT - ATECA (KH7, KHP)</b>				<b>04/16→</b>
1.0 TSI	81 kW	1 l	09/20→	 KH30014 ProKIT
1.0 TSI	85 kW	1 l	05/16→	 KH20003 ProKIT
1.4 TSI	110 kW	1.4 l	06/16→	
1.5 TSI	110 kW	1.5 l	07/18→	
1.6 TDI	85 kW	1.6 l	04/16→07/18	
2.0 TDI	81 kW	2 l	10/16→	
2.0 TDI	105 kW	2 l	10/16→	
2.0 TDI	110 kW	2 l	04/16→	
1.4 TSI 4Drive	110 kW	1.4 l	06/16→	 KH30014 ProKIT
1.5 TSI 4Drive	110 kW	1.5 l	07/18→	 KH30049 ProKIT
2.0 TDI 4Drive	110 kW	2 l	04/16→	
2.0 TDI 4Drive	140 kW	2 l	06/16→	
2.0 TSI 4Drive	140 kW	2 l	05/17→	
<b>SEAT - CORDOBA Sedan (6K1, 6K2)</b>				<b>02/93→10/02</b>
1.0	51 kW	1 l	06/01→08/02	 ; VIN 6K-X400000 -> KH20117 ProKIT
1.0 i	37 kW	1 l	09/96→10/02	 ; ABS KH10055 ProKIT
1.4	40 kW	1.4 l	12/97→04/99	 ; VIN -> 6K-X-399999 KH00003 ProKIT
1.4 16V	55 kW	1.4 l	05/00→10/02	 ; VIN 6K-X400000 -> KH20117 ProKIT
1.4 i	44 kW	1.4 l	06/94→10/02	
1.4 i 16V	74 kW	1.4 l	09/96→10/02	
1.6 i	55 kW	1.6 l	02/93→10/02	
1.6 i	55 kW	1.6 l	05/94→06/99	
1.6 i	74 kW	1.6 l	07/96→10/02	
1.8 i	66 kW	1.8 l	02/93→09/02	
1.8 i 16V	95 kW	1.8 l	10/93→08/96	
1.8 T 20V Cupra	115 kW	1.8 l	07/00→10/02	
1.9 D	47 kW	1.9 l	01/96→08/96	
1.9 D	50 kW	1.9 l	02/93→08/96	
1.9 SDI	47 kW	1.9 l	08/96→06/99	
1.9 SDI	50 kW	1.9 l	06/99→10/02	
1.9 TD	55 kW	1.9 l	02/93→08/96	
1.9 TDI	66 kW	1.9 l	08/96→10/02	
1.9 TDI	81 kW	1.9 l	03/97→10/02	
2.0 i	85 kW	2 l	02/93→06/99	
2.0 i 16V	110 kW	2 l	08/96→06/99	
<b>SEAT - CORDOBA Sedan (6L2)</b>				<b>09/02→11/09</b>
1.2	47 kW	1.2 l	10/02→06/06	 KH30045 ProKIT
1.2 12V	51 kW	1.2 l	05/06→11/09	 KH20009 ProKIT
1.4 16V	55 kW	1.4 l	09/02→12/07	
1.4 16V	63 kW	1.4 l	05/06→11/09	
1.4 16V	74 kW	1.4 l	10/02→11/09	
1.4 TDI	51 kW	1.4 l	05/05→11/09	
1.4 TDI	55 kW	1.4 l	10/02→12/05	
1.4 TDI	59 kW	1.4 l	06/05→11/09	
1.6	74 kW	1.6 l	04/03→11/09	
1.6 16V	77 kW	1.6 l	11/06→11/09	
1.9 SDI	47 kW	1.9 l	09/02→11/09	
1.9 TDI	74 kW	1.9 l	09/02→11/09	
1.9 TDI	96 kW	1.9 l	10/02→11/09	
2.0	85 kW	2 l	09/02→11/09	
<b>SEAT - CORDOBA Vario / CORDOBA VARIO Estate Van (6K5)</b>				<b>08/96→12/02</b>
1.4	74 kW	1.4 l	02/00→07/00	 ; VIN 6K-X-290001 -> KH20117 ProKIT
1.9 TDI	81 kW	1.9 l	08/00→12/02	

				     13 		
<b>SEAT - CORDOBA Vario / CORDOBA VARIO Estate Van (6K5)</b>						<b>08/96→12/02</b>
1.4 16V	55 kW	1.4 l	06/99→12/02	 ABS		KH10055 ProKIT
1.9 SDI	50 kW	1.9 l	06/99→12/02			
1.4 i	44 kW	1.4 l	09/96→12/02	 ABS		KH10055 ProKIT
1.6 i	55 kW	1.6 l	09/96→12/02	 VIN → 6K-X-290000		KH00003 ProKIT
1.6 i	55 kW	1.6 l	05/97→06/99			
1.6 i	74 kW	1.6 l	09/96→12/02	 VIN 6K-X-290001 →		KH20117 ProKIT
1.9 SDI	47 kW	1.9 l	09/96→06/99			
1.9 TDI	66 kW	1.9 l	08/96→12/02			
1.9 TDI	81 kW	1.9 l	07/97→12/02			
<b>SEAT - EXEO / EXEO ST (3R2, 3R5)</b>						<b>12/08→05/13</b>
1.6	75 kW	1.6 l	03/09→09/10			KH20032 ProKIT
1.6	75 kW	1.6 l	06/09→09/10			
1.8 T	110 kW	1.8 l	12/08→05/10			KH20040 ProKIT
1.8 T	110 kW	1.8 l	06/09→05/10			
1.8 TSI	88 kW	1.8 l	09/10→05/13			KH20032 ProKIT
1.8 TSI	118 kW	1.8 l	05/10→05/13			
2.0 TDI	88 kW	2 l	12/08→05/13	 → 11/10		KH20040 ProKIT
2.0 TDI	88 kW	2 l	07/09→05/13			
2.0 TDI	105 kW	2 l	12/08→05/13			
2.0 TDI	105 kW	2 l	05/09→05/13			
2.0 TDI	125 kW	2 l	02/09→05/13			
2.0 TDI	125 kW	2 l	05/09→05/13			
2.0 TFSI	147 kW	2 l	03/09→05/13			
2.0 TFSI	147 kW	2 l	06/09→05/13			
2.0 TFSI	155 kW	2 l	05/10→05/13			
<b>SEAT - IBIZA I (21A)</b>						<b>06/84→12/93</b>
0.9	29 kW	0.9 l	08/90→05/93			KH20091 ProKIT
0.9	32 kW	0.9 l	08/86→05/93			
1.2	44 kW	1.2 l	11/84→12/93			
1.2 i	52 kW	1.2 l	01/89→05/93			
1.5	63 kW	1.5 l	11/84→05/93			
1.5 i	65 kW	1.5 l	10/86→05/93			
1.5 i	74 kW	1.5 l	10/86→05/93			
1.5 i Cat	66 kW	1.5 l	10/86→05/93			
1.7	72 kW	1.7 l	01/91→05/93			
1.7 D	40 kW	1.7 l	06/84→05/93			
1.7 D	42 kW	1.7 l	08/90→05/93			
<b>SEAT - IBIZA II (6K1)</b>						<b>03/93→02/02</b>
1.0	33 kW	1 l	03/93→09/96	 ABS		KH10055 ProKIT
1.0 16V	51 kW	1 l	10/99→02/02	 VIN → 6K-X-399999		KH00003 ProKIT
1.0 i	37 kW	1 l	09/96→02/02			
1.3 i	40 kW	1.3 l	03/93→08/99	 VIN 6K-X-400000 →		KH20117 ProKIT
1.4	40 kW	1.4 l	12/97→04/99			
1.4 i	44 kW	1.4 l	09/93→02/02			
1.4 i 16V	74 kW	1.4 l	06/97→02/02			
1.6 i	55 kW	1.6 l	03/93→02/02			
1.6 i	55 kW	1.6 l	09/94→06/99			
1.6 i	74 kW	1.6 l	04/96→02/02			
1.8 i	66 kW	1.8 l	03/93→08/99			
1.8 i 16V	95 kW	1.8 l	11/93→08/96			
1.9 D	47 kW	1.9 l	04/93→08/96			
1.9 SDI	47 kW	1.9 l	08/96→08/99			
1.9 SDI	50 kW	1.9 l	08/99→02/02			
1.9 TD	55 kW	1.9 l	03/93→08/96			
1.9 TDI	66 kW	1.9 l	08/96→02/02			
1.9 TDI	81 kW	1.9 l	02/97→02/02			
2.0 i	85 kW	2 l	03/93→08/99			
2.0 i 16V	110 kW	2 l	08/96→08/99			
1.4 16V	55 kW	1.4 l	05/00→02/02	 ABS		KH10055 ProKIT
1.8 T 20V Cupra	115 kW	1.8 l	07/00→02/02	 VIN 6K-X-400000 →		KH20117 ProKIT
1.8 T 20V Cupra R	132 kW	1.8 l	07/00→02/02	 VIN 6K-X-400000 →		KH20117 ProKIT
<b>SEAT - IBIZA III (6L1)</b>						<b>02/02→11/09</b>
1.2	44 kW	1.2 l	06/07→05/08	 Outer diameter 1 [mm]: 72		KH30045 ProKIT
1.2	47 kW	1.2 l	02/02→06/06			KH20009 ProKIT
1.2 12V	51 kW	1.2 l	05/06→11/09			
1.4 16V	55 kW	1.4 l	02/02→12/07			
1.4 16V	63 kW	1.4 l	05/06→11/09			
1.4 16V	74 kW	1.4 l	02/02→11/09			
1.4 TDI	51 kW	1.4 l	05/05→11/09			
1.4 TDI	55 kW	1.4 l	05/02→12/05			
1.4 TDI	59 kW	1.4 l	06/05→11/09			
1.6	74 kW	1.6 l	02/03→11/09			
1.6 16V	77 kW	1.6 l	11/06→11/09			
1.8 T Cupra R	132 kW	1.8 l	01/04→02/08			

SEAT - IBIZA III (6L1)				02/02→11/09	
1.8 T FR	110 kW	1.8 l	12/03→05/08	; Outer diameter 1 [mm]: 72 	KH30045 ProKIT
1.9 SDI	47 kW	1.9 l	02/02→12/05		KH20009 ProKIT
1.9 TDI	74 kW	1.9 l	02/02→11/09		
1.9 TDI	96 kW	1.9 l	02/02→11/09		
1.9 TDI Cupra R	118 kW	1.9 l	03/04→02/08		
2.0	85 kW	2 l	04/02→11/09		
SEAT - IBIZA IV / IBIZA IV SC / IBIZA IV ST (6J5, 6P1, 6P5, 6J8, 6P8)				03/08→06/17	
1.0	55 kW	1 l	05/15→07/16		KH30045 ProKIT
1.0	55 kW	1 l	05/15→12/16		KH20009 ProKIT
1.0	55 kW	1 l	05/15→06/17		
1.0 TSI	70 kW	1 l	05/15→07/16		
1.0 TSI	70 kW	1 l	05/15→12/16		
1.0 TSI	70 kW	1 l	05/15→06/17		
1.0 TSI	81 kW	1 l	05/15→07/16		
1.0 TSI	81 kW	1 l	05/15→12/16		
1.0 TSI	81 kW	1 l	05/15→06/17		
1.2	44 kW	1.2 l	07/09→05/11		
1.2	44 kW	1.2 l	07/09→05/15		
1.2	44 kW	1.2 l	05/10→05/15		
1.2	51 kW	1.2 l	03/08→05/15		
1.2	51 kW	1.2 l	07/08→05/15		
1.2	51 kW	1.2 l	05/10→05/15		
1.2 TDI	55 kW	1.2 l	04/10→05/15		
1.2 TDI	55 kW	1.2 l	05/10→05/15		
1.2 TDI	55 kW	1.2 l	06/10→03/12		
1.2 TSI	63 kW	1.2 l	08/12→05/15		
1.2 TSI	63 kW	1.2 l	09/12→05/15		
1.2 TSI	66 kW	1.2 l	05/15→07/16		
1.2 TSI	66 kW	1.2 l	05/15→12/16		
1.2 TSI	66 kW	1.2 l	05/15→06/17		
1.2 TSI	77 kW	1.2 l	09/10→03/12		
1.2 TSI	77 kW	1.2 l	09/10→05/15		
1.2 TSI	81 kW	1.2 l	09/15→07/16		
1.2 TSI	81 kW	1.2 l	09/15→12/16		
1.2 TSI	81 kW	1.2 l	09/15→06/17		
1.4	63 kW	1.4 l	03/08→05/15		
1.4	63 kW	1.4 l	07/08→05/15		
1.4	63 kW	1.4 l	03/10→05/15		
1.4 TDI	55 kW	1.4 l	05/15→07/16		
1.4 TDI	55 kW	1.4 l	05/15→12/16		
1.4 TDI	55 kW	1.4 l	05/15→06/17		
1.4 TDI	59 kW	1.4 l	07/08→06/10		
1.4 TDI	66 kW	1.4 l	05/15→07/16		
1.4 TDI	66 kW	1.4 l	05/15→12/16		
1.4 TDI	66 kW	1.4 l	05/15→06/17		
1.4 TDI	77 kW	1.4 l	05/15→07/16		
1.4 TDI	77 kW	1.4 l	05/15→12/16		
1.4 TDI	77 kW	1.4 l	05/15→06/17		
1.4 TSI	103 kW	1.4 l	10/13→05/15		
1.4 TSI	110 kW	1.4 l	01/09→05/15		
1.4 TSI	110 kW	1.4 l	06/09→05/15		
1.4 TSI	110 kW	1.4 l	02/12→05/15		
1.4 TSI	110 kW	1.4 l	11/15→07/16		
1.4 TSI	110 kW	1.4 l	11/15→12/16		
1.4 TSI	110 kW	1.4 l	11/15→06/17		
1.4 TSI Cupra	132 kW	1.4 l	06/09→05/15		
1.6	77 kW	1.6 l	05/08→03/12		
1.6	77 kW	1.6 l	07/08→05/15		
1.6	77 kW	1.6 l	02/12→05/15		
1.6 LPG	60 kW	1.6 l	05/11→05/15		
1.6 TDI	66 kW	1.6 l	05/09→05/15		
1.6 TDI	66 kW	1.6 l	03/10→05/15		
1.6 TDI	77 kW	1.6 l	05/09→05/15		
1.6 TDI	77 kW	1.6 l	03/10→05/15		
1.8 TSI Cupra	141 kW	1.8 l	11/15→12/16		
1.9 TDI	66 kW	1.9 l	06/08→06/10		
1.9 TDI	66 kW	1.9 l	07/08→06/10		
1.9 TDI	77 kW	1.9 l	03/08→06/10		
1.9 TDI	77 kW	1.9 l	07/08→06/10		
2.0 TDI	105 kW	2 l	01/10→05/15		
1.2 LPG	51 kW	1.2 l	03/08→05/11		KH30045 ProKIT
1.4 LPG	63 kW	1.4 l	03/08→05/11		
1.4 LPG	63 kW	1.4 l	07/08→05/11		
1.6 TDI	55 kW	1.6 l	05/09→06/10		
1.6 TDI	55 kW	1.6 l	05/10→06/10		
2.0	85 kW	2 l	10/08→05/15		





**SEAT - IBIZA V (KJ1, KJG)**

01/17→

1.0	55 kW	1 l	01/17→	; OE 6C0 407 621	KH30045 ProKIT
1.0 MPI	59 kW	1 l	07/18→		
1.0 TGI	66 kW	1 l	11/17→		
1.0 TSI	70 kW	1 l	01/17→		
1.0 TSI	85 kW	1 l	01/17→		
1.5 TSI	110 kW	1.5 l	07/17→		
1.6	81 kW	1.6 l	05/17→		
1.6 TDI	59 kW	1.6 l	11/17→		
1.6 TDI	70 kW	1.6 l	09/17→		
1.6 TDI	85 kW	1.6 l	12/17→		

**SEAT - INCA (6K9)**

11/95→06/03

1.4 16V	55 kW	1.4 l	04/00→06/03	; ABS	KH10055 ProKIT
1.4 i	44 kW	1.4 l	11/95→06/03	; VIN → 9K-V-015 942	KH00002 ProKIT
1.7 D	42 kW	1.7 l	09/96→06/03	; VIN 9K-V-015943 → VIN 9K-X-023408	KH00038 ProKIT
1.9 D	47 kW	1.9 l	11/95→06/03	; VIN 9K-X-023 409 →	KH20052 ProKIT
1.9 SDI	47 kW	1.9 l	11/95→06/03	; VIN → 9K-V-015 942	KH10055 ProKIT
1.6 i	55 kW	1.6 l	11/95→05/98	; ABS	KH00002 ProKIT
1.6 i	55 kW	1.6 l	06/97→09/00	; VIN 9K-V-015943 → VIN 9K-X-023408	KH00038 ProKIT
1.9 TDI	66 kW	1.9 l	09/96→06/03	; ABS	KH10055 ProKIT
				; VIN 9K-V-015943 → VIN 9K-X-023408	KH00038 ProKIT

**SEAT - LEON (1M1)**

11/99→06/06

1.4 16V	55 kW	1.4 l	11/99→06/06		KH10001 ProKIT
1.6	74 kW	1.6 l	11/99→06/06	; ABS	KH20010 ProKIT
1.6	75 kW	1.6 l	10/05→06/06		
1.6 16 V	77 kW	1.6 l	09/00→06/06		
1.8 20V	92 kW	1.8 l	11/99→06/06		
1.8 20V T	132 kW	1.8 l	11/99→06/06		
1.8 T Cupra R	154 kW	1.8 l	02/02→06/06		
1.9 SDI	50 kW	1.9 l	11/99→06/06		
1.9 TDI	66 kW	1.9 l	11/99→06/06		
1.9 TDI	74 kW	1.9 l	10/05→06/06		
1.9 TDI	81 kW	1.9 l	11/99→06/06		
1.9 TDI	96 kW	1.9 l	05/03→06/06		
1.9 TDI	110 kW	1.9 l	09/00→06/06		
2.8	150 kW	2.8 l	05/02→06/04		
1.8 20V T 4	132 kW	1.8 l	11/99→06/06	;	KH10001 ProKIT
1.9 TDI Syncro	110 kW	1.9 l	05/02→06/06		
2.8 Cupra 4	150 kW	2.8 l	02/01→06/06		
1.8 T Cupra R	165 kW	1.8 l	07/03→06/06		KH10001 ProKIT
					KH10117 ProKIT
				; ABS	KH20010 ProKIT

**SEAT - LEON (1P1)**



















05/05→08/13

1.2 TSI	77 kW	1.2 l	02/10→12/12	; Number of mounting bores: 4	KH30002 ProKIT
1.4 16V	63 kW	1.4 l	06/06→12/12	; Number of mounting bores: 3	KH30048 ProKIT
1.4 TSI	92 kW	1.4 l	11/07→12/12		
1.6	75 kW	1.6 l	07/05→12/12	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.6 LPG	75 kW	1.6 l	12/09→12/12	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.6 MultiFuel	75 kW	1.6 l	07/05→08/13		
1.6 TDI	66 kW	1.6 l	11/10→12/12		
1.6 TDI	77 kW	1.6 l	02/10→12/12		
1.8 TSI	118 kW	1.8 l	06/07→12/12		
1.9 TDI	66 kW	1.9 l	06/07→12/10		
1.9 TDI	77 kW	1.9 l	07/05→12/10		
2.0 Cupra R	195 kW	2 l	09/09→12/12		
2.0 FSI	110 kW	2 l	07/05→05/10		
2.0 TDI	100 kW	2 l	07/05→05/10		
2.0 TDI	103 kW	2 l	10/05→10/10		
2.0 TDI	125 kW	2 l	05/06→12/12		
2.0 TDI 16V	103 kW	2 l	07/05→12/12		
2.0 TFSI	136 kW	2 l	09/05→05/06		
2.0 TFSI	147 kW	2 l	05/05→03/09		
2.0 TFSI	155 kW	2 l	06/09→12/12		
2.0 TFSI	177 kW	2 l	11/06→05/11		

**SEAT - LEON (5F1)**

09/12→08/20

1.0 Tsi	63 kW	1 l	09/18→08/20	; Centering Diameter [mm]: 85	KH30014 ProKIT
1.0 TSI	85 kW	1 l	05/15→08/20	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	63 kW	1.2 l	12/12→08/18		
1.2 TSI	77 kW	1.2 l	01/13→08/20		KH20003 ProKIT
1.2 TSI	81 kW	1.2 l	04/14→08/20		
1.4 TGI	81 kW	1.4 l	02/13→08/18		
1.4 TSI	90 kW	1.4 l	11/12→10/16		
1.4 TSI	92 kW	1.4 l	05/14→08/20		

     					
<b>SEAT - LEON (5F1)</b>				<b>09/12→08/20</b>	
1.4 TSI	103 kW	1.4 l	09/12→08/20	 ; Centering Diameter [mm]: 85	KH30014 ProKIT
1.4 TSI	110 kW	1.4 l	05/14→08/20		
1.5 TGI	96 kW	1.5 l	10/18→08/20	 ; Centering Diameter [mm]: 80	KH30048 ProKIT
1.5 TSI	96 kW	1.5 l	09/18→08/20		
1.5 TSI	110 kW	1.5 l	09/18→08/20		KH20003 ProKIT
1.6 TDI	66 kW	1.6 l	11/12→08/18		
1.6 TDI	77 kW	1.6 l	09/12→08/20		
1.6 TDI	81 kW	1.6 l	09/13→08/20		
1.6 TDI	85 kW	1.6 l	11/16→08/20		
1.8 TSI	132 kW	1.8 l	02/13→08/18		
2.0 Cupra	195 kW	2 l	10/13→08/20		
2.0 Cupra	206 kW	2 l	10/13→08/20		
2.0 Cupra	213 kW	2 l	10/15→08/20		
2.0 Cupra	221 kW	2 l	01/17→08/18		
2.0 Cupra R	228 kW	2 l	11/17→08/18		
2.0 TDI	81 kW	2 l	05/13→08/20		
2.0 TDI	105 kW	2 l	05/13→08/20		
2.0 TDI	110 kW	2 l	10/12→08/20		
2.0 TDI	135 kW	2 l	09/12→08/20		
2.0 TSI	140 kW	2 l	09/18→08/20		
1.6 SRE	81 kW	1.6 l	04/14→08/20		KH20003 ProKIT
<b>SEAT - LEON (KL1)</b>				<b>11/19→</b>	
1.0 TSI	66 kW	1 l	03/20→	 ; Centering Diameter [mm]: 80	KH30048 ProKIT
1.0 TSI	81 kW	1 l	03/20→		
1.4 TSI e-Hybrid	150 kW	1.4 l	05/20→	 ; Centering Diameter [mm]: 85	KH30049 ProKIT
1.5 eTSI	110 kW	1.5 l	11/19→		
1.5 TGI CNG	96 kW	1.5 l	08/20→		
1.5 TSI	96 kW	1.5 l	11/19→		
1.5 TSI	110 kW	1.5 l	11/19→		
2.0 TDI	85 kW	2 l	11/19→		
2.0 TDI	110 kW	2 l	11/19→		
<b>SEAT - LEON Hatchback Van (5F1)</b>				<b>09/12→08/20</b>	
1.0 TSI	85 kW	1 l	05/15→08/20	 ; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	63 kW	1.2 l	01/13→08/18		
1.2 TSI	81 kW	1.2 l	04/14→08/18		KH20003 ProKIT
1.4 TSI	90 kW	1.4 l	09/12→10/16		
1.4 TSI	103 kW	1.4 l	09/12→10/16		
1.4 TSI	110 kW	1.4 l	05/14→08/20		
1.6 TDI	66 kW	1.6 l	11/12→10/16		
1.6 TDI	77 kW	1.6 l	09/12→10/16		
1.6 TDI	81 kW	1.6 l	09/13→10/16		
1.6 TDI	85 kW	1.6 l	11/16→08/20		
1.8 TFSI	132 kW	1.8 l	02/13→08/18		
2.0 Cupra	213 kW	2 l	09/15→10/16		
2.0 Cupra	221 kW	2 l	01/17→08/18		
2.0 TDI	110 kW	2 l	10/12→08/18		
2.0 TDI	135 kW	2 l	02/13→08/18		
<b>SEAT - LEON SC (5F5)</b>				<b>01/13→08/18</b>	
1.0 TSI	85 kW	1 l	05/15→08/18	 ; Centering Diameter [mm]: 85	KH30014 ProKIT
1.2 TSI	63 kW	1.2 l	01/13→08/18		
1.2 TSI	77 kW	1.2 l	02/13→04/14	 ; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	81 kW	1.2 l	05/14→08/18		
1.4 TSI	90 kW	1.4 l	02/13→06/15		KH20003 ProKIT
1.4 TSI	92 kW	1.4 l	05/14→08/18		
1.4 TSI	103 kW	1.4 l	02/13→11/16		
1.4 TSI	110 kW	1.4 l	05/14→08/18		
1.6 TDI	66 kW	1.6 l	02/13→08/18		
1.6 TDI	77 kW	1.6 l	02/13→08/18		
1.6 TDI	81 kW	1.6 l	09/13→11/16		
1.6 TDI	85 kW	1.6 l	11/16→08/18		
1.8 TSI	132 kW	1.8 l	02/13→08/18		
2.0 Cupra	195 kW	2 l	10/13→11/16		
2.0 Cupra	206 kW	2 l	10/13→11/16		
2.0 Cupra	213 kW	2 l	10/15→11/16		
2.0 Cupra	221 kW	2 l	01/17→08/18		
2.0 TDI	105 kW	2 l	05/13→08/18		
2.0 TDI	110 kW	2 l	02/13→08/18		
2.0 TDI	135 kW	2 l	03/13→08/18		
2.0 TDI	81 kW	2 l	02/13→08/18		KH20003 ProKIT





**SEAT - LEON Sportstourer (KL8)**

03/20→

1.0 TSI	66 kW	1 l	03/20→	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.0 TSI	81 kW	1 l	03/20→		
1.4 TSI e-Hybrid	150 kW	1.4 l	05/20→	; Centering Diameter [mm]: 85	KH30049 ProKIT
1.5 eTSI	110 kW	1.5 l	03/20→		
1.5 TSI	96 kW	1.5 l	03/20→		
1.5 TSI	110 kW	1.5 l	03/20→		
2.0 TDI	110 kW	2 l	04/20→		

**SEAT - LEON ST (5F8)**

09/12→08/20

1.0 TSi	63 kW	1 l	09/18→08/20	; Centering Diameter [mm]: 85	KH30014 ProKIT
1.0 TSI	85 kW	1 l	05/15→08/20	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	63 kW	1.2 l	11/13→08/18		
1.2 TSI	77 kW	1.2 l	08/13→08/20		KH20003 ProKIT
1.2 TSI	81 kW	1.2 l	05/14→08/20		
1.4 TGI	81 kW	1.4 l	10/13→08/18		
1.4 TSI	90 kW	1.4 l	09/12→06/15		
1.4 TSI	92 kW	1.4 l	05/14→08/18		
1.4 TSI	103 kW	1.4 l	10/13→08/20		
1.4 TSI	110 kW	1.4 l	05/14→08/20		
1.5 TGI	96 kW	1.5 l	10/18→08/20		
1.5 TSI	96 kW	1.5 l	09/18→08/20		
1.5 TSI	110 kW	1.5 l	09/18→08/20		
1.6 TDI	66 kW	1.6 l	11/13→08/18		
1.6 TDI	77 kW	1.6 l	10/13→08/20		
1.6 TDI	81 kW	1.6 l	09/13→08/20		
1.6 TDI	85 kW	1.6 l	11/16→08/20		
1.8 TSI	132 kW	1.8 l	10/13→08/18		
2.0 Cupra	195 kW	2 l	10/13→08/20		
2.0 Cupra	206 kW	2 l	10/13→08/20		
2.0 Cupra	213 kW	2 l	10/15→08/20		
2.0 Cupra	221 kW	2 l	11/16→08/18		
2.0 TDI	81 kW	2 l	02/13→12/16		
2.0 TDI	105 kW	2 l	10/13→08/18		
2.0 TDI	110 kW	2 l	10/13→08/18		
2.0 TDI	135 kW	2 l	08/13→08/20		
2.0 TSI	140 kW	2 l	07/18→08/20		
1.6 SRE	81 kW	1.6 l	05/15→08/20		KH20003 ProKIT
1.6 TDI 4Drive	77 kW	1.6 l	04/14→08/20	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.6 TDI 4Drive	81 kW	1.6 l	11/14→08/20		
1.6 TDI 4Drive	85 kW	1.6 l	07/18→08/20	; Centering Diameter [mm]: 85	KH30014 ProKIT
1.8 TSI 4Drive	132 kW	1.8 l	11/14→08/18		
2.0 Cupra 4Drive	221 kW	2 l	11/16→08/20		
2.0 TDI 4Drive	110 kW	2 l	04/14→08/18		
2.0 TDI 4Drive	135 kW	2 l	11/14→08/18		
2.0 TSI 4Drive	140 kW	2 l	09/18→08/20		

**SEAT - LEON ST Estate Van (5F8)**

01/13→08/20

1.0 TSI	85 kW	1 l	05/15→08/20	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	63 kW	1.2 l	01/13→08/18		KH20003 ProKIT
1.2 TSI	81 kW	1.2 l	05/14→08/18		
1.4 TSI	110 kW	1.4 l	05/14→08/20		
1.6 TDI	81 kW	1.6 l	09/13→08/20		
1.6 TDI	85 kW	1.6 l	11/16→08/20		
1.8 TFSI	132 kW	1.8 l	10/13→08/18		
2.0 Cupra	206 kW	2 l	10/13→08/20		
2.0 Cupra	221 kW	2 l	11/16→08/18		
2.0 TDI	110 kW	2 l	04/13→08/18		
2.0 TDI	135 kW	2 l	08/13→08/18		
2.0 Cupra 4Drive	221 kW	2 l	11/16→08/18		KH30048 ProKIT
2.0 TDI 4Drive	110 kW	2 l	09/14→08/18		
2.0 TDI 4Drive	135 kW	2 l	10/14→08/18		

**SEAT - MALAGA (23A)**





























05/85→12/93

1.2	44 kW	1.2 l	05/85→12/93		KH20091 ProKIT
1.2 i	52 kW	1.2 l	12/89→12/93		
1.5	63 kW	1.5 l	05/85→12/93		
1.5 i	74 kW	1.5 l	01/87→12/93		
1.5 i Cat	66 kW	1.5 l	10/86→12/93		
1.7 D	40 kW	1.7 l	05/85→12/93		
1.7 D	42 kW	1.7 l	05/90→12/93		

**SEAT - MARBELLA / MARBELLA Hatchback Van (28A, 028A)**

08/86→10/98

0.8	25 kW	0.8 l	08/86→12/93		KH30113 ProKIT
0.8	25 kW	0.8 l	01/87→12/93		
0.9	29 kW	0.9 l	01/87→12/93		
0.9	32 kW	0.9 l	07/97→10/98		
0.9 Cat	29 kW	0.9 l	01/87→12/93		
0.9 Cat	29 kW	0.9 l	01/90→11/96		
0.9 Cat	30 kW	0.9 l	11/96→10/98		

											
<b>SEAT - Mii (KF1, KE1)</b>										<b>10/11→07/19</b>	
1.0	44 kW	1 l	10/11→07/19						KH10010 ProKIT		
1.0	55 kW	1 l	10/11→07/19						KH20021 ProKIT		
1.0 EcoFuel	50 kW	1 l	10/12→07/19								
<b>SEAT - RITMO (138)</b>										<b>07/78→09/83</b>	
1.4	57 kW	1.4 l	07/78→09/83						KH20091 ProKIT		
<b>SEAT - RONDA (22A)</b>										<b>06/82→11/88</b>	
1.2	44 kW	1.2 l	10/84→12/86						KH20091 ProKIT		
1.2	47 kW	1.2 l	08/83→05/85								
1.4	54 kW	1.4 l	06/82→11/88								
1.5	63 kW	1.5 l	09/84→12/86								
1.6	68 kW	1.6 l	08/83→09/85								
1.7 Diesel	40 kW	1.7 l	06/82→12/86								
1.7 Diesel	41 kW	1.7 l	06/82→12/86								
<b>SEAT - TARRACO (KN2)</b>										<b>09/18→</b>	
1.4 TSI	110 kW	1.4 l	09/18→						KH30049 ProKIT		
1.5 TSI ACT	110 kW	1.5 l	09/18→						KH20004 ProKIT		
2.0 TDI	110 kW	2 l	09/18→								
2.0 TDI 4Drive	110 kW	2 l	09/18→							KH30049 ProKIT	
2.0 TDI 4Drive	140 kW	2 l	09/18→								
2.0 TDI 4Drive	147 kW	2 l	07/20→								
2.0 TSI 4Drive	140 kW	2 l	11/18→								
<b>SEAT - TERRA / TERRA Estate Van (24, 024A)</b>										<b>01/87→12/96</b>	
0.9	29 kW	0.9 l	01/87→12/95						KH30113 ProKIT		
0.9	29 kW	0.9 l	02/87→12/96								
0.9 Cat	29 kW	0.9 l	02/92→12/94								
1.3 D	33 kW	1.3 l	03/90→12/94								
1.4 D	35 kW	1.4 l	10/90→12/95								
0.9 Cat	29 kW	0.9 l	01/90→12/95							KH30113 ProKIT	
1.3 D	33 kW	1.3 l	03/90→02/92								
1.4 D	35 kW	1.4 l	10/90→02/92								
<b>SEAT - TOLEDO I (1L2)</b>										<b>05/91→03/99</b>	
1.6 i	52 kW	1.6 l	05/91→12/93							KH10055 ProKIT	
1.6 i	54 kW	1.6 l	05/91→03/99						KH00003 ProKIT		
1.6 i	55 kW	1.6 l	01/93→03/99								
1.6 i	74 kW	1.6 l	11/96→03/99								
1.8 16V	92 kW	1.8 l	05/91→03/99								
1.8 16V	98 kW	1.8 l	05/91→03/99								
1.8 i	65 kW	1.8 l	05/91→12/96								
1.8 i	66 kW	1.8 l	11/93→12/96								
1.9 D	47 kW	1.9 l	12/95→03/99								
1.9 D	50 kW	1.9 l	05/91→03/99								
1.9 TD	55 kW	1.9 l	05/91→03/99								
1.9 TDI	66 kW	1.9 l	08/95→03/99								
1.9 TDI	81 kW	1.9 l	11/96→03/99								
2.0 i	85 kW	2 l	05/91→03/99								
2.0 i 16V	110 kW	2 l	11/93→03/99						KH00003 ProKIT		
<b>SEAT - TOLEDO II Sedan (1M2)</b>										<b>10/98→05/06</b>	
1.4 16V	55 kW	1.4 l	01/00→05/02						KH10001 ProKIT		
1.6	74 kW	1.6 l	10/98→07/04							KH20010 ProKIT	
1.6 16V	77 kW	1.6 l	06/00→05/06								
1.8 20V	92 kW	1.8 l	10/98→07/04								
1.8 20VT	132 kW	1.8 l	09/00→07/04								
1.9 TDI	66 kW	1.9 l	03/99→07/04								
1.9 TDI	81 kW	1.9 l	10/98→07/04								
1.9 TDI	96 kW	1.9 l	05/03→05/06								
1.9 TDI	110 kW	1.9 l	10/00→07/04								
2.3 V5	110 kW	2.3 l	10/98→11/00								
2.3 V5 20V	125 kW	2.3 l	09/00→11/03								
<b>SEAT - TOLEDO III (5P2)</b>										<b>04/04→05/09</b>	
1.4 16V	63 kW	1.4 l	05/06→05/09		Number of mounting bores: 4				KH30002 ProKIT		
1.4 TSI	92 kW	1.4 l	11/07→05/09		Number of mounting bores: 3				KH30048 ProKIT		
1.6	75 kW	1.6 l	10/04→05/09								
1.8 TFSI	118 kW	1.8 l	01/07→05/09		Inner diameter 1 [mm]: 30				KH20003 ProKIT		
1.9 TDI	77 kW	1.9 l	10/04→05/09		Inner diameter 1 [mm]: 32				KH20004 ProKIT		
2.0 FSI	110 kW	2 l	10/04→05/09								
2.0 TDI	100 kW	2 l	09/04→05/09								
2.0 TDI	103 kW	2 l	11/05→05/09								
2.0 TDI	125 kW	2 l	01/06→05/09								
2.0 TDI 16V	103 kW	2 l	04/04→05/09								
2.0 TFSI	147 kW	2 l	11/05→05/09								


























































**SEAT - TOLEDO IV (KG3)**

**07/12→04/19**










































































1.0 TSI	70 kW	1 l	05/17→04/19		KH30045 ProKIT
1.0 TSI	81 kW	1 l	05/17→04/19		
1.2	55 kW	1.2 l	07/12→06/15		
1.2 TSI	63 kW	1.2 l	07/12→06/15		
1.2 TSI	66 kW	1.2 l	05/15→05/17		
1.2 TSI	77 kW	1.2 l	07/12→06/15		
1.2 TSI	81 kW	1.2 l	05/15→05/17		
1.4 TDI	66 kW	1.4 l	05/15→04/19		
1.4 TSI	90 kW	1.4 l	07/12→06/15		
1.4 TSI	92 kW	1.4 l	05/15→04/19		
1.6	77 kW	1.6 l	07/13→06/15		
1.6	81 kW	1.6 l	05/15→04/19		
1.6 TDI	66 kW	1.6 l	06/13→06/15		
1.6 TDI	77 kW	1.6 l	07/12→06/15		
1.6 TDI	85 kW	1.6 l	05/15→04/19		






























				     	
<b>SKODA - CITIGO (NF1)</b>				<b>10/11→08/19</b>	
1.0	44 kW	1 l	10/11→08/19		KH10010 ProKIT
1.0	55 kW	1 l	10/11→08/19		KH20021 ProKIT
1.0 CNG	50 kW	1 l	11/12→08/19		
<b>SKODA - FABIA I / FABIA I Combi / FABIA I Praktik / FABIA I Saloon (6Y2, 6Y5, 6Y3)</b>				<b>08/99→03/08</b>	
1.0	37 kW	1 l	12/99→08/02	 ;  ; Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel	KH20027 ProKIT
1.2	40 kW	1.2 l	07/01→04/07		
1.2	40 kW	1.2 l	07/01→12/07	 ;  ; Bolt Head-/Nut Design: Male Star	KH20028 ProKIT
1.2	47 kW	1.2 l	01/03→12/07		
1.2	47 kW	1.2 l	01/03→03/08	 ; PR 1LB; for brake disc diameter [mm]: 239; 	KH20024 ProKIT
1.4	44 kW	1.4 l	04/00→08/02	 ; PR 1LN, 1LQ, 1LR, 1ZD; 	KH30045 ProKIT
1.4	44 kW	1.4 l	04/00→03/03		KH20009 ProKIT
1.4	44 kW	1.4 l	08/00→08/02		
1.4	50 kW	1.4 l	08/99→05/03		
1.4	50 kW	1.4 l	04/00→05/03		
1.4	50 kW	1.4 l	07/01→05/03		
1.4 16V	55 kW	1.4 l	10/99→12/07		
1.4 16V	55 kW	1.4 l	12/99→03/08		
1.4 16V	55 kW	1.4 l	05/00→12/07		
1.4 16V	59 kW	1.4 l	04/06→12/07		
1.4 16V	74 kW	1.4 l	12/99→12/07		
1.4 16V	74 kW	1.4 l	12/99→03/08		
1.4 16V	74 kW	1.4 l	04/00→12/07		
1.4 TDI	51 kW	1.4 l	10/05→12/07		
1.4 TDI	51 kW	1.4 l	10/05→03/08		
1.4 TDI	55 kW	1.4 l	04/03→12/07		
1.4 TDI	55 kW	1.4 l	04/03→03/08		
1.4 TDI	59 kW	1.4 l	10/05→12/07		
1.4 TDI	59 kW	1.4 l	10/05→03/08		
1.9 SDI	47 kW	1.9 l	11/99→12/07		
1.9 SDI	47 kW	1.9 l	12/99→03/08		
1.9 SDI	47 kW	1.9 l	04/00→12/07		
1.9 TDI	74 kW	1.9 l	01/00→12/07		
1.9 TDI	74 kW	1.9 l	01/00→03/08		
1.9 TDI	74 kW	1.9 l	04/00→12/07		
1.9 TDI RS	96 kW	1.9 l	06/03→03/08		
2.0	85 kW	2 l	12/99→12/07		
2.0	85 kW	2 l	12/99→03/08		
2.0	85 kW	2 l	04/00→12/07		
1.2	40 kW	1.2 l	07/01→12/07	 ; Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel	KH20027 ProKIT
				 ;  ; Bolt Head-/Nut Design: Male Star	KH20028 ProKIT
				 ; PR 1LB; for brake disc diameter [mm]: 239; 	KH20024 ProKIT
				 ; PR 1LN, 1LQ, 1LR, 1ZD; 	KH30045 ProKIT
					KH20009 ProKIT
1.4 16V	59 kW	1.4 l	04/06→12/07	 ;  ; Bolt / Nut Version: Conical-seat Nut; Material: Sheet Steel	KH20027 ProKIT
				 ;  ; Bolt Head-/Nut Design: Male Star	KH20028 ProKIT
				 ; PR 1LB; for brake disc diameter [mm]: 239; 	KH20024 ProKIT
				 ; PR 1LN, 1LQ, 1LR, 1ZD; 	KH30045 ProKIT
					KH20009 ProKIT
1.9 SDI	47 kW	1.9 l	07/01→12/07	 ;  ; Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel	KH20027 ProKIT
				 ;  ; Bolt Head-/Nut Design: Male Star	KH20028 ProKIT
				 ; PR 1LB; for brake disc diameter [mm]: 239; 	KH20024 ProKIT
				 ; PR 1LN, 1LQ, 1LR, 1ZD; 	KH30045 ProKIT
					KH20009 ProKIT
<b>SKODA - FABIA II / FABIA II Combi (5J, 542, 5J, 545)</b>				<b>12/06→12/14</b>	
1.2	44 kW	1.2 l	12/06→12/14	 ; Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 239	KH20024 ProKIT
1.2	44 kW	1.2 l	10/07→11/14		
1.2	51 kW	1.2 l	01/07→12/14	 ;  ; Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel	KH20027 ProKIT
1.2	51 kW	1.2 l	10/07→12/14		
1.4	63 kW	1.4 l	01/07→12/14	 ;  ; Bolt Head-/Nut Design: Male Star, Hexagon	KH20028 ProKIT
1.4	63 kW	1.4 l	10/07→12/14		
1.4 TDI	51 kW	1.4 l	02/07→03/10	 ; Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288	KH30045 ProKIT
1.4 TDI	51 kW	1.4 l	10/07→03/10		
1.4 TDI	59 kW	1.4 l	01/07→03/10		KH20009 ProKIT
1.4 TDI	59 kW	1.4 l	10/07→03/10		
1.6	77 kW	1.6 l	04/07→12/14		
1.6	77 kW	1.6 l	10/07→12/14		
1.9 TDI	77 kW	1.9 l	04/07→03/10		
1.9 TDI	77 kW	1.9 l	10/07→03/10		



												
<b>SKODA - FABIA II / FABIA II Combi (5J, 542, 5J, 545)</b>											<b>12/06→12/14</b>	
1.2 12V	44 kW	1.2 l	11/11→12/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 239							KH20024 ProKIT
1.2 TDI	55 kW	1.2 l	05/10→12/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288							KH30045 ProKIT
1.2 TSI	63 kW	1.2 l	03/10→12/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288							KH30045 ProKIT
1.2 TSI	77 kW	1.2 l	03/10→12/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288							KH20009 ProKIT
1.4 TSI RS	132 kW	1.4 l	05/10→12/14									KH20009 ProKIT
1.6 TDI	55 kW	1.6 l	04/10→12/14									KH20009 ProKIT
1.6 TDI	66 kW	1.6 l	03/10→12/14									KH20009 ProKIT
1.6 TDI	77 kW	1.6 l	03/10→12/14									KH20009 ProKIT
1.2 LPG	44 kW	1.2 l	03/09→11/11		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 239							KH20024 ProKIT
1.2 LPG	51 kW	1.2 l	10/07→11/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 239							KH20024 ProKIT
1.4 LPG	63 kW	1.4 l	01/07→11/14		Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel							KH20027 ProKIT
1.4 LPG	63 kW	1.4 l	10/07→11/14		Bolt Head-/Nut Design: Male Star, Hexagon							KH20028 ProKIT
					Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288							KH30045 ProKIT
1.2 LPG	51 kW	1.2 l	07/07→11/14		Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 239							KH20024 ProKIT
					Bolt Head-/Nut Design: Hexagon; Material: Sheet Steel							KH20027 ProKIT
					Outer diameter 1 [mm]: 72;  ; for brake disc diameter [mm]: 256, 288							KH30045 ProKIT
<b>SKODA - FABIA III / FABIA III Estate (NJ3, NJ5)</b>											<b>08/14→</b>	
1.0	44 kW	1 l	08/14→									KH30045 ProKIT
1.0	44 kW	1 l	10/14→									KH20009 ProKIT
1.0	55 kW	1 l	08/14→									KH20009 ProKIT
1.0	55 kW	1 l	10/14→									KH20009 ProKIT
1.2 TSI	66 kW	1.2 l	08/14→									KH20009 ProKIT
1.2 TSI	66 kW	1.2 l	10/14→									KH20009 ProKIT
1.2 TSI	81 kW	1.2 l	08/14→									KH20009 ProKIT
1.2 TSI	81 kW	1.2 l	10/14→									KH20009 ProKIT
1.4 TDI	55 kW	1.4 l	05/15→									KH20009 ProKIT
1.4 TDI	66 kW	1.4 l	08/14→									KH20009 ProKIT
1.4 TDI	66 kW	1.4 l	10/14→									KH20009 ProKIT
1.4 TDI	77 kW	1.4 l	08/14→									KH20009 ProKIT
1.4 TDI	77 kW	1.4 l	10/14→									KH20009 ProKIT
1.6	81 kW	1.6 l	01/15→									KH20009 ProKIT
1.0 TSI	70 kW	1 l	08/14→									KH30045 ProKIT
1.0 TSI	81 kW	1 l	08/14→									KH30045 ProKIT
1.4 TSI R5	92 kW	1.4 l	02/18→									KH30045 ProKIT
<b>SKODA - FAVORIT / FAVORIT Forman (781, 785)</b>											<b>05/89→06/95</b>	
1.3	50 kW	1.3 l	01/94→06/95									KH10162 ProKIT
1.3 (781)	50 kW	1.3 l	01/94→09/94									KH10162 ProKIT
1.3 (135)	44 kW	1.3 l	12/91→06/95		05/93 ->							KH10162 ProKIT
1.3 (135 E)	40 kW	1.3 l	09/91→06/95									KH10162 ProKIT
1.3 (136)	45 kW	1.3 l	08/91→06/95									KH10162 ProKIT
1.3 135 (781)	42 kW	1.3 l	12/91→09/94									KH10162 ProKIT
1.3 135 (781)	43 kW	1.3 l	12/91→09/94									KH10162 ProKIT
1.3 135 (781)	44 kW	1.3 l	10/90→09/94									KH10162 ProKIT
1.3 135L (781)	43 kW	1.3 l	05/89→09/94									KH10162 ProKIT
1.3 135 X, LX, GLX (781)	40 kW	1.3 l	01/90→09/94									KH10162 ProKIT
1.3 136 (781)	45 kW	1.3 l	10/90→09/94									KH10162 ProKIT
<b>SKODA - FELICIA I / FELICIA I Estate / FELICIA I Pickup (6U1, 6U5, 6UF, 6U7)</b>											<b>10/94→04/02</b>	
1.3	40 kW	1.3 l	10/94→03/98									KH00003 ProKIT
1.3	40 kW	1.3 l	06/97→04/02									KH00003 ProKIT
1.3	43 kW	1.3 l	10/94→03/98									KH00003 ProKIT
1.3	43 kW	1.3 l	08/95→03/98									KH00003 ProKIT
1.3	43 kW	1.3 l	10/95→04/02									KH00003 ProKIT
1.3	50 kW	1.3 l	10/94→03/98									KH00003 ProKIT
1.3 LX	40 kW	1.3 l	08/95→03/98									KH00003 ProKIT
1.3 LXI	50 kW	1.3 l	08/95→03/98									KH00003 ProKIT
1.3	50 kW	1.3 l	06/97→04/02		-> 05/98							KH10162 ProKIT
												KH00003 ProKIT
1.6	55 kW	1.6 l	06/97→04/02		06/98 -> 02/01							KH10162 ProKIT
												KH00003 ProKIT
1.6 GLX	55 kW	1.6 l	08/95→03/98		02/96 ->							KH10162 ProKIT
1.6 LX	55 kW	1.6 l	08/95→03/98									KH00003 ProKIT
1.9 D	47 kW	1.9 l	10/95→03/98		05/97 ->							KH10162 ProKIT
												KH00003 ProKIT
1.9 D	47 kW	1.9 l	06/97→04/02		-> 02/01							KH10162 ProKIT
												KH00003 ProKIT

												
<b>SKODA - FELICIA II / FELICIA II Estate (6U1, 6U5)</b>											<b>01/98→06/01</b>	
1.3	40 kW	1.3 l	01/98→06/01		-> 01/01						KH10162 ProKIT	
1.3	50 kW	1.3 l	01/98→06/01									KH10162 ProKIT
1.9 D	47 kW	1.9 l	01/98→06/01									KH10162 ProKIT
1.6	55 kW	1.6 l	01/98→06/01		-> 01/00						KH10162 ProKIT	
<b>SKODA - KAROQ (NU7, ND7)</b>											<b>07/17→</b>	
1.0 TSI	81 kW	1 l	09/20→								KH30014 ProKIT	
1.0 TSI	85 kW	1 l	07/17→									KH30014 ProKIT
1.4 TSI	110 kW	1.4 l	07/17→		Inner diameter 1 [mm]: 30						KH20003 ProKIT	
1.5 TSI	110 kW	1.5 l	07/17→									KH20003 ProKIT
1.6 SRE	81 kW	1.6 l	07/17→									KH20003 ProKIT
1.6 TDI	85 kW	1.6 l	07/17→									KH20003 ProKIT
2.0 TDI	110 kW	2 l	07/17→									KH20003 ProKIT
1.5 TSI 4x4	110 kW	1.5 l	07/17→								KH30014 ProKIT	
2.0 TDI 4x4	105 kW	2 l	07/18→								KH30049 ProKIT	
2.0 TDI 4x4	110 kW	2 l	07/17→									KH30049 ProKIT
2.0 TDI 4x4	140 kW	2 l	07/17→									KH30049 ProKIT
2.0 TSI 4x4	140 kW	2 l	04/19→									KH30049 ProKIT
<b>SKODA - KODIAQ (NS7, NV7, NS6)</b>											<b>10/16→</b>	
1.4 TSI	92 kW	1.4 l	10/16→								KH30014 ProKIT	
1.4 TSI	110 kW	1.4 l	10/16→									KH30014 ProKIT
1.5 TSI	110 kW	1.5 l	07/18→		Inner diameter 1 [mm]: 32						KH20004 ProKIT	
2.0 TDI	110 kW	2 l	10/16→									KH20004 ProKIT
1.4 TSI 4x4	110 kW	1.4 l	10/16→								KH30014 ProKIT	
1.5 TSI 4x4	110 kW	1.5 l	07/18→									KH30014 ProKIT
2.0 RS Bi-TDI 4x4	176 kW	2 l	11/18→								KH30049 ProKIT	
2.0 TDI 4x4	110 kW	2 l	10/16→									KH30049 ProKIT
2.0 TDI 4x4	130 kW	2 l	04/17→									KH30049 ProKIT
2.0 TDI 4x4	140 kW	2 l	10/16→									KH30049 ProKIT
2.0 TDI 4x4	147 kW	2 l	06/20→									KH30049 ProKIT
2.0 TSI 4x4	132 kW	2 l	10/16→									KH30049 ProKIT
2.0 TSI 4x4	140 kW	2 l	02/19→									KH30049 ProKIT
<b>SKODA - OCTAVIA I / OCTAVIA I Combi (1U2, 1U5)</b>											<b>09/96→12/10</b>	
1.4	44 kW	1.4 l	04/99→03/01								KH10001 ProKIT	
1.4 16V	55 kW	1.4 l	08/00→12/10									KH10001 ProKIT
1.4 16V	55 kW	1.4 l	09/00→12/10		ABS						KH20010 ProKIT	
1.6	55 kW	1.6 l	09/96→09/04									KH20010 ProKIT
1.6	55 kW	1.6 l	07/98→09/04									KH20010 ProKIT
1.6	74 kW	1.6 l	02/97→12/07									KH20010 ProKIT
1.6	74 kW	1.6 l	07/98→12/07									KH20010 ProKIT
1.6	75 kW	1.6 l	09/00→12/10									KH20010 ProKIT
1.6	75 kW	1.6 l	11/00→12/10									KH20010 ProKIT
1.8	92 kW	1.8 l	09/96→07/00									KH20010 ProKIT
1.8 20V	92 kW	1.8 l	07/98→07/00									KH20010 ProKIT
1.8 T	110 kW	1.8 l	08/97→12/10									KH20010 ProKIT
1.8 T	110 kW	1.8 l	07/98→12/10									KH20010 ProKIT
1.9 SDI	50 kW	1.9 l	06/97→12/03									KH20010 ProKIT
1.9 SDI	50 kW	1.9 l	07/98→12/03									KH20010 ProKIT
1.9 TDI	66 kW	1.9 l	09/96→03/10									KH20010 ProKIT
1.9 TDI	66 kW	1.9 l	07/98→03/10									KH20010 ProKIT
1.9 TDI	74 kW	1.9 l	08/00→12/10									KH20010 ProKIT
1.9 TDI	74 kW	1.9 l	10/05→12/10									KH20010 ProKIT
1.9 TDI	81 kW	1.9 l	08/97→01/06									KH20010 ProKIT
1.9 TDI	81 kW	1.9 l	07/98→01/06									KH20010 ProKIT
1.9 TDI	96 kW	1.9 l	09/02→09/04									KH20010 ProKIT
2.0	85 kW	2 l	04/99→05/07									KH20010 ProKIT
RS 1.8 T	132 kW	1.8 l	05/01→01/06									KH20010 ProKIT
RS 1.8 T	132 kW	1.8 l	08/02→01/06									KH20010 ProKIT
1.8 T 4x4	110 kW	1.8 l	05/01→05/06								KH10001 ProKIT	
1.9 TDI 4x4	66 kW	1.9 l	11/99→02/06									KH10001 ProKIT
1.9 TDI 4x4	74 kW	1.9 l	09/00→01/06									KH10001 ProKIT
2.0 4x4	85 kW	2 l	08/00→09/04									KH10001 ProKIT
2.0 4x4	88 kW	2 l	01/00→12/10									KH10001 ProKIT
<b>SKODA - OCTAVIA II / OCTAVIA II Combi (1Z3, 1Z5)</b>											<b>02/04→06/13</b>	
1.2 TSI	77 kW	1.2 l	02/10→04/13		Number of mounting bores: 4						KH30002 ProKIT	
1.2 TSI	77 kW	1.2 l	02/10→06/13									KH30002 ProKIT
1.4	55 kW	1.4 l	05/04→05/06		Number of mounting bores: 3						KH30048 ProKIT	
1.4	59 kW	1.4 l	06/04→04/13		Inner diameter 1 [mm]: 32						KH20004 ProKIT	
1.4	59 kW	1.4 l	05/06→06/13									KH20004 ProKIT
1.4 TSI	90 kW	1.4 l	11/08→06/13									KH20004 ProKIT
1.6	75 kW	1.6 l	06/04→06/13									KH20004 ProKIT
1.6	75 kW	1.6 l	09/04→06/13									KH20004 ProKIT
1.6 FSI	85 kW	1.6 l	02/04→10/08									KH20004 ProKIT
1.6 LPG	75 kW	1.6 l	08/09→11/12									KH20004 ProKIT
1.6 MultiFuel	75 kW	1.6 l	01/08→06/13									KH20004 ProKIT
1.6 TDI	77 kW	1.6 l	06/09→04/13									KH20004 ProKIT



**SKODA - OCTAVIA II / OCTAVIA II Combi (1Z3, 1Z5)**

**02/04→06/13**

1.8 TSI	112 kW	1.8 l	03/09→06/13	; Number of mounting bores: 4	KH30002 ProKIT
1.8 TSI	118 kW	1.8 l	06/07→04/13	; Number of mounting bores: 3	KH30048 ProKIT
1.9 TDI	77 kW	1.9 l	06/04→12/10	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.9 TDI	77 kW	1.9 l	09/04→12/10		
2.0 FSI	110 kW	2 l	11/04→10/08		
2.0 TDI	81 kW	2 l	03/10→06/13		
2.0 TDI	100 kW	2 l	02/04→05/10		
2.0 TDI	103 kW	2 l	11/05→05/10		
2.0 TDI 16V	100 kW	2 l	02/04→05/10		
2.0 TDI 16V	103 kW	2 l	02/04→04/13		
2.0 TDI 16V	103 kW	2 l	02/04→05/13		
2.0 TDI RS	125 kW	2 l	04/06→02/13		
2.0 TFSI	147 kW	2 l	10/05→02/13		
1.6 TDI 4x4	77 kW	1.6 l	06/09→02/13	; ; Number of mounting bores: 4	KH30002 ProKIT
1.8 TSI 4x4	112 kW	1.8 l	03/09→02/13	; ; Number of mounting bores: 3	KH30048 ProKIT
1.8 TSI 4x4	118 kW	1.8 l	11/08→02/13		
1.9 TDI 4x4	77 kW	1.9 l	11/04→12/10		
2.0 FSI 4x4	110 kW	2 l	11/04→04/09		
2.0 TDI 16V 4x4	103 kW	2 l	05/10→02/13		
2.0 TDI 4x4	81 kW	2 l	05/11→02/13		
2.0 TDI 4x4	103 kW	2 l	07/06→05/10		

**SKODA - OCTAVIA III / OCTAVIA III Combi (5E3, NL3, NR3, 5E5, 5E6)**






























**11/12→10/20**

1.0 TSI	85 kW	1 l	05/16→10/20	; Centering Diameter [mm]: 85	KH30014 ProKIT
1.2 TSI	63 kW	1.2 l	11/12→02/17	; Centering Diameter [mm]: 80	KH30048 ProKIT
1.2 TSI	77 kW	1.2 l	11/12→02/17		
1.2 TSI	81 kW	1.2 l	05/15→02/17	; Centering Diameter [mm]: 85	KH20003 ProKIT
1.4 TSI	103 kW	1.4 l	11/12→02/17		
1.4 TSI	110 kW	1.4 l	08/14→10/20		
1.4 TSI G-TEC	81 kW	1.4 l	11/12→02/17		
1.4 TSI G-TEC	81 kW	1.4 l	11/13→02/17		
1.5 TSI	110 kW	1.5 l	02/17→10/20		
1.5 TSI G-TEC	96 kW	1.5 l	01/19→10/20		
1.6	81 kW	1.6 l	01/14→02/17		
1.6	81 kW	1.6 l	01/14→10/20		
1.6 TDI	66 kW	1.6 l	11/12→10/20		
1.6 TDI	77 kW	1.6 l	11/12→05/15		
1.6 TDI	81 kW	1.6 l	05/13→02/17		
1.6 TDI	85 kW	1.6 l	02/17→10/20		
1.8 TSI	132 kW	1.8 l	11/12→10/20		
2.0 TDI	105 kW	2 l	11/12→02/17		
2.0 TDI	110 kW	2 l	11/12→10/20		
2.0 TDI RS	135 kW	2 l	05/13→10/20		
2.0 TSI	140 kW	2 l	02/17→10/20		
2.0 TSI RS	162 kW	2 l	11/12→02/17		
2.0 TSI RS	162 kW	2 l	05/13→02/17		
2.0 TSI RS	169 kW	2 l	05/15→10/20		
2.0 TSI RS	180 kW	2 l	02/17→10/20		
1.6 TDI 4x4	77 kW	1.6 l	11/12→05/15	; Centering Diameter [mm]: 85	KH30014 ProKIT
1.8 TSI 4x4	132 kW	1.8 l	05/14→10/20	; ; Centering Diameter [mm]: 80	KH30048 ProKIT
2.0 TDI 4x4	110 kW	2 l	11/12→10/20		
2.0 TDI 4x4	110 kW	2 l	05/13→10/20		
1.6 TDI 4x4	77 kW	1.6 l	05/13→05/15	; ; Centering Diameter [mm]: 85	KH30014 ProKIT
1.6 TDI 4x4	81 kW	1.6 l	05/15→02/17	; ; Centering Diameter [mm]: 80	KH30048 ProKIT
1.6 TDI 4x4	85 kW	1.6 l	02/17→10/20		
1.8 TSI 4x4	132 kW	1.8 l	11/12→02/17		
2.0 TDI / TDI RS 4x4	135 kW	2 l	05/13→10/20		
2.0 TSI 4x4	140 kW	2 l	02/19→10/20		

**SKODA - OCTAVIA IV / OCTAVIA IV Combi (NX3, NN3, NX5)**

**11/19→**

1.0 TSI	81 kW	1 l	06/20→	; Centering Diameter [mm]: 85	KH30049 ProKIT
1.0 TSI e-TEC	81 kW	1 l	06/20→		
1.4 TSI RS iV	180 kW	1.4 l	06/20→		
1.5 TSI	110 kW	1.5 l	11/19→		
1.5 TSI	110 kW	1.5 l	01/20→		
1.5 TSI e-TEC	110 kW	1.5 l	11/20→		
1.5 TSI G-TEC	96 kW	1.5 l	06/20→		
1.6 SRE	81 kW	1.6 l	07/20→		
2.0 TDI	85 kW	2 l	11/19→		
2.0 TDI	85 kW	2 l	03/20→		
2.0 TDI	105 kW	2 l	06/20→		
2.0 TDI	110 kW	2 l	11/19→		
2.0 TDI	110 kW	2 l	01/20→		
2.0 TDI RS	147 kW	2 l	07/20→		
2.0 TSI	140 kW	2 l	07/20→		
2.0 TSI RS	180 kW	2 l	03/20→		
2.0 TDI RS 4x4	147 kW	2 l	07/20→	; ; Centering Diameter [mm]: 85	KH30049 ProKIT

				     13 	
<b>SKODA - RAPID / RAPID Spaceback (NH3, NK3, NK6, NH1)</b>					<b>07/12→12/19</b>
1.0 TSI	70 kW	1 l	06/17→12/19		KH30045 ProKIT
1.0 TSI	81 kW	1 l	06/17→12/19		
1.2	55 kW	1.2 l	07/12→06/15		
1.2 LPG	55 kW	1.2 l	07/12→06/15		
1.2 LPG	63 kW	1.2 l	07/12→05/15		
1.2 TSI	63 kW	1.2 l	07/12→05/15		
1.2 TSI	66 kW	1.2 l	05/15→12/19		
1.2 TSI	77 kW	1.2 l	07/12→05/15		
1.2 TSI	81 kW	1.2 l	05/15→12/19		
1.4 TDI	66 kW	1.4 l	05/15→12/19		
1.4 TSI	90 kW	1.4 l	07/12→06/15		
1.4 TSI	92 kW	1.4 l	05/15→12/19		
1.6	77 kW	1.6 l	07/12→06/15		
1.6	81 kW	1.6 l	05/15→12/19		
1.6 SRE	66 kW	1.6 l	06/15→12/19		
1.6 SRE	81 kW	1.6 l	05/15→12/19		
1.6 TDI	66 kW	1.6 l	08/13→05/15		
1.6 TDI	77 kW	1.6 l	07/12→12/19		
1.6 TDI	85 kW	1.6 l	05/15→12/19		
<b>SKODA - ROOMSTER (5J7)</b>					<b>03/06→05/15</b>
1.2	47 kW	1.2 l	05/06→01/07	 ; PR 1LB, 1LM;  13 Inch	KH30045 ProKIT
1.2 TDI	55 kW	1.2 l	03/10→05/15	 ; ABS	KH20010 ProKIT
1.2 TSI	63 kW	1.2 l	03/10→05/15		
1.2 TSI	77 kW	1.2 l	03/10→05/15		
1.6 TDI	66 kW	1.6 l	03/10→05/15		
1.6 TDI	77 kW	1.6 l	03/10→05/15		
1.9 TDI	74 kW	1.9 l	03/06→05/06		
1.2	51 kW	1.2 l	01/07→05/15	 ; 03/08 -> 03/10; PR 1LB, 1LM	KH20024 ProKIT
1.4	63 kW	1.4 l	09/06→05/15	 ; PR 1LB, 1LM;  13 Inch	KH30045 ProKIT
1.6	77 kW	1.6 l	09/06→05/15	 ; ABS	KH20010 ProKIT
1.4 TDI	51 kW	1.4 l	07/06→03/10	 ; 03/08 ->; PR 1LB, 1LM	KH20024 ProKIT
1.4 TDI	59 kW	1.4 l	09/06→03/10	 ; PR 1LB, 1LM;  13 Inch	KH30045 ProKIT
1.9 TDI	77 kW	1.9 l	09/06→03/10	 ; ABS	KH20010 ProKIT
<b>SKODA - ROOMSTER Praktik (5J)</b>					<b>03/07→05/15</b>
1.2	51 kW	1.2 l	03/07→05/15	 ; 03/08 -> 03/10; PR 1LB, 1LM	KH20024 ProKIT
1.4	63 kW	1.4 l	03/07→05/15		
1.4 TDI	51 kW	1.4 l	03/07→03/10	 ; 03/08 ->; PR 1LB, 1LM	KH20024 ProKIT
1.4 TDI	59 kW	1.4 l	03/07→03/10		
<b>SKODA - SUPERB I Sedan (3U4)</b>					<b>12/01→03/08</b>
1.8 T	110 kW	1.8 l	12/01→03/08		KH10066 ProKIT
1.9 TDI	96 kW	1.9 l	12/01→03/08	 ; AT	KH10069 ProKIT
					KH30095 ProKIT
1.9 TDI	74 kW	1.9 l	08/02→10/05		KH10066 ProKIT
1.9 TDI	77 kW	1.9 l	10/05→05/07		KH10069 ProKIT
1.9 TDI	85 kW	1.9 l	01/07→03/08		KH10069 ProKIT
2.0	85 kW	2 l	12/01→03/08		KH30095 ProKIT
2.0 TDI	103 kW	2 l	10/05→03/08		
2.5 TDI	114 kW	2.5 l	12/01→08/03		
2.5 TDI	120 kW	2.5 l	06/03→03/08		
2.8 V6	142 kW	2.8 l	12/01→03/08		
2.8 V6	140 kW	2.8 l	06/02→03/08		KH10066 ProKIT
					KH10069 ProKIT
<b>SKODA - SUPERB II / SUPERB II Estate (3T4, 3T5)</b>					<b>03/08→05/15</b>
1.4 TSI	92 kW	1.4 l	07/08→05/15		KH30002 ProKIT
1.4 TSI	92 kW	1.4 l	10/09→05/15		
1.6 TDI	77 kW	1.6 l	09/10→05/15	 ; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.8 TSI	112 kW	1.8 l	03/09→05/15		
1.8 TSI	112 kW	1.8 l	10/09→05/15		
1.8 TSI	118 kW	1.8 l	03/08→05/15		
1.8 TSI	118 kW	1.8 l	10/09→05/15		
1.9 TDI	77 kW	1.9 l	03/08→11/10		
1.9 TDI	77 kW	1.9 l	10/09→11/10		
2.0 TDI	103 kW	2 l	03/08→05/10		
2.0 TDI	103 kW	2 l	10/09→03/10		
2.0 TDI	125 kW	2 l	07/08→05/15		
2.0 TDI	125 kW	2 l	10/09→05/15		
2.0 TDI 16V	103 kW	2 l	01/09→05/15		
2.0 TDI 16V	103 kW	2 l	10/09→05/15		
2.0 TFSI	147 kW	2 l	05/10→05/15		





**SKODA - SUPERB II / SUPERB II Estate (3T4, 3T5)**

**03/08→05/15**

1.8 TSI 4x4	112 kW	1.8 l	03/09→05/15		<b>KH30002 ProKIT</b>
1.8 TSI 4x4	112 kW	1.8 l	10/09→05/15		
1.8 TSI 4x4	118 kW	1.8 l	11/08→05/15		
1.8 TSI 4x4	118 kW	1.8 l	10/09→05/15		
2.0 TDI 16V 4x4	103 kW	2 l	11/10→05/15		
2.0 TDI 4x4	125 kW	2 l	09/08→05/15		
2.0 TDI 4x4	125 kW	2 l	10/09→05/15		
3.6 FSI 4x4	191 kW	3.6 l	11/08→05/15		
3.6 V6 4x4	191 kW	3.6 l	10/09→05/15		

**SKODA - SUPERB III / SUPERB III Estate (3V3, 3V5)**




































**03/15→**

1.4 TSI	92 kW	1.4 l	03/15→		<b>KH30014 ProKIT</b>
1.4 TSI	110 kW	1.4 l	03/15→		
1.4 TSI IV	160 kW	1.4 l	08/19→		<b>KH20004 ProKIT</b>
1.5 TSi	110 kW	1.5 l	02/17→		
1.5 TSI	110 kW	1.5 l	02/17→		
1.6 TDI	88 kW	1.6 l	03/15→		
1.8 TSI	132 kW	1.8 l	03/15→		
2.0 TDI	90 kW	2 l	07/20→		
2.0 TDI	110 kW	2 l	03/15→		
2.0 TDI	130 kW	2 l	03/15→		
2.0 TDI	140 kW	2 l	03/15→		
2.0 TDI	147 kW	2 l	09/20→		
2.0 TSI	140 kW	2 l	07/19→		
2.0 TSI	162 kW	2 l	03/15→		
1.4 TSI 4x4	110 kW	1.4 l	03/15→		<b>KH30014 ProKIT</b>
2.0 TDI 4x4	110 kW	2 l	03/15→		<b>KH30049 ProKIT</b>
2.0 TDI 4x4	140 kW	2 l	03/15→		
2.0 TDI 4x4	147 kW	2 l	09/20→		
2.0 TSI 4x4	200 kW	2 l	03/15→		
2.0 TSI 4x4	206 kW	2 l	03/15→		

**SKODA - YETI (5L)**

**05/09→12/17**

1.2 TSI	77 kW	1.2 l	09/09→05/15	; Number of mounting bores: 4	<b>KH30002 ProKIT</b>
1.2 TSI	81 kW	1.2 l	05/15→12/17	; Number of mounting bores: 3	<b>KH30048 ProKIT</b>
1.4 TSI	90 kW	1.4 l	06/10→05/15	; Number of mounting bores: 3	<b>KH30048 ProKIT</b>
1.4 TSI	92 kW	1.4 l	05/15→12/17	; Inner diameter 1 [mm]: 32	<b>KH20004 ProKIT</b>
1.6	81 kW	1.6 l	04/14→12/17		
1.6 TDI	77 kW	1.6 l	11/10→05/15		
2.0 TDI	81 kW	2 l	11/09→12/17		
2.0 TDI	103 kW	2 l	11/11→12/17		
2.0 TDI	110 kW	2 l	05/15→12/17		
1.4 TSI 4x4	110 kW	1.4 l	05/15→12/17	; Number of mounting bores: 4	<b>KH30002 ProKIT</b>
1.8 TSI 4x4	112 kW	1.8 l	11/09→12/17	; Number of mounting bores: 3	<b>KH30048 ProKIT</b>
1.8 TSI 4x4	118 kW	1.8 l	05/09→12/17	; Number of mounting bores: 3	<b>KH30048 ProKIT</b>
2.0 TDI 4x4	81 kW	2 l	11/09→12/17		
2.0 TDI 4x4	103 kW	2 l	05/09→12/17		
2.0 TDI 4x4	110 kW	2 l	05/15→12/17		
2.0 TDI 4x4	125 kW	2 l	11/09→05/15		

     				
<b>SMART - CABRIO (450)</b>				<b>03/00→01/04</b>
0.6 (S1OLA1, 450.441, 450.442, 450.443)	40 kW	0.6 l	03/00→01/04	 KH20054 ProKIT
0.6 (S1OLD2, 450.452)	45 kW	0.6 l	01/01→01/04	 KH30160 ProKIT
0.8 CDI (S1OLC1, 450.401, 450.402, 450.403, 450.400)	30 kW	0.8 l	03/01→01/04	
0.7 (450.433)	55 kW	0.7 l	01/03→01/04	 KH20054 ProKIT
0.7 (450.452, 450.432)	45 kW	0.7 l	01/03→01/04	 KH30160 ProKIT
<b>SMART - CITY-COUPE (450)</b>				<b>07/98→01/04</b>
0.6 (450.352, 450.353)	45 kW	0.6 l	01/01→01/04	 KH20054 ProKIT
0.8 CDI (S1CLC1, 450.300, 450.301, 450.302, 450.303,...)	30 kW	0.8 l	11/99→01/04	 KH30160 ProKIT
0.6 (S1CLA1, 450.341)	40 kW	0.6 l	07/98→01/04	 KH20054 ProKIT
0.6 (S1CLB1, 450.331, 450.336)	33 kW	0.6 l	07/98→01/04	 KH30160 ProKIT
0.7 (450.330)	37 kW	0.7 l	01/03→01/04	 KH20054 ProKIT
0.7 (450.333)	55 kW	0.7 l	01/03→01/04	 KH30160 ProKIT
0.7 (450.352, 450.353)	45 kW	0.7 l	01/03→01/04	 KH30160 ProKIT
<b>SMART - CROSSBLADE (450)</b>				<b>06/02→12/03</b>
0.6 (450.418)	52 kW	0.6 l	06/02→12/03	 KH20054 ProKIT
				 KH30160 ProKIT
<b>SMART - FORFOUR (454)</b>				<b>01/04→06/06</b>
1.1 (454.030)	55 kW	1.1 l	01/04→06/06	 KH20072 ProKIT
1.3 (454.031)	70 kW	1.3 l	01/04→06/06	 KH20194 ProKIT
				 KH30186 ProKIT
1.1 (454.033)	47 kW	1.1 l	02/05→06/06	 KH20072 ProKIT
1.5 (454.032)	80 kW	1.5 l	01/04→06/06	 KH30186 ProKIT
1.5 (454.032)	90 kW	1.5 l	01/04→06/06	 KH30186 ProKIT
1.5 CDI (454.000)	50 kW	1.5 l	09/04→06/06	
1.5 CDI (454.001)	70 kW	1.5 l	09/04→06/06	
1.5 BRABUS (454.034)	130 kW	1.5 l	05/05→06/06	 KH30186 ProKIT
<b>SMART - FORFOUR Hatchback (453)</b>				<b>07/14→</b>
0.9 (453.044, 453.053)	66 kW	0.9 l	11/14→	 KH30029 ProKIT
1.0 (453.041)	45 kW	1 l	11/14→	
1.0 (453.042, 453.043)	52 kW	1 l	07/14→	
<b>SMART - FORTWO Cabrio (450)</b>				<b>01/04→01/07</b>
0.7 (450.433)	55 kW	0.7 l	01/04→01/07	 KH20054 ProKIT
0.7 (450.452)	45 kW	0.7 l	01/04→01/07	 KH30160 ProKIT
0.8 CDI (450.401, 450.402, 450.403, 450.400)	30 kW	0.8 l	01/04→01/07	 KH30160 ProKIT
<b>SMART - FORTWO Cabrio (451)</b>				<b>01/07→</b>
0.8 CDi (451.400)	33 kW	0.8 l	01/07→	 KH20123 ProKIT
0.8 CDi (451.401)	40 kW	0.8 l	08/09→	 KH30172 ProKIT
1.0 (451.431, 451.480)	52 kW	1 l	01/07→	
1.0 Brabus	88 kW	1 l	04/12→	
1.0 Brabus (451.433)	72 kW	1 l	01/08→	
1.0 Turbo (451.432)	62 kW	1 l	01/07→	
1.0 Turbo Brabus (451.433)	75 kW	1 l	07/10→	
electric drive (451.490, 451.491)	20 kW		12/10→12/12	
electric drive (451.490, 451.491)	55 kW		01/13→	
electric drive (451.490)	35 kW		12/11→12/12	
electric drive (451.491)	30 kW		11/09→12/11	
electric drive Brabus (451.492)	60 kW		01/13→	
<b>SMART - FORTWO Coupe (450)</b>				<b>01/04→01/07</b>
0.7 (450.330)	37 kW	0.7 l	01/04→01/07	 KH20054 ProKIT
0.7 (450.333)	55 kW	0.7 l	01/04→01/07	 KH30160 ProKIT
0.7 (450.352, 450.332)	45 kW	0.7 l	01/04→01/07	 KH30160 ProKIT
0.8 CDI (450.300, 450.301, 450.302, 450.303, 450.306)	30 kW	0.8 l	01/04→01/07	





**SMART - FORTWO Coupe (451)**

**01/07** →

0.8 CDi (451.300)	33 kW	0.8 l	01/07 →		<b>KH20123</b> ProKIT
0.8 CDi (451.301)	40 kW	0.8 l	08/09 →		<b>KH30172</b> ProKIT
1.0 (451.330, 451.334)	45 kW	1 l	01/07 →		
1.0 (451.331, 451.380)	52 kW	1 l	01/07 →		
1.0 Brabus (451.333)	72 kW	1 l	01/08 →		
1.0 Turbo (451.332)	62 kW	1 l	01/07 →		
1.0 Turbo Brabus (451.333)	75 kW	1 l	07/10 →		
electric drive (451.390, 451.391)	55 kW		01/13 →		
electric drive (451.390)	35 kW		12/11 → 12/12		
electric drive (451.391, 451.390)	20 kW		12/10 → 12/12		
electric drive (451.391)	30 kW		11/09 → 12/11		
electric drive Brabus (451.392)	60 kW		01/13 →		

**SMART - FORTWO Coupe (453)**

**07/14** →
















0.9 (453.344, 453.353)	66 kW	0.9 l	09/14 →		<b>KH30029</b> ProKIT
1.0 (453.341)	45 kW	1 l	11/14 →		
1.0 (453.342, 453.343)	52 kW	1 l	07/14 →		

**SMART - ROADSTER / ROADSTER Coupe (452)**

































































**04/03** → **11/05**

























0.7 (452.334)	60 kW	0.7 l	04/03 → 11/05		<b>KH20054</b> ProKIT
0.7 (452.432)	45 kW	0.7 l	04/03 → 11/05		<b>KH30160</b> ProKIT
0.7 (452.434)	60 kW	0.7 l	04/03 → 11/05	; 05/03 ->	<b>KH30160</b> ProKIT
0.7 Brabus (452.337)	74 kW	0.7 l	12/03 → 11/05		<b>KH20054</b> ProKIT
0.7 Brabus (452.437)	74 kW	0.7 l	12/03 → 11/05		<b>KH30160</b> ProKIT



     					
<b>SSANGYONG - KORANDO / KORANDO Cabrio (KJ)</b>					<b>12/96→11/06</b>
2.0	94 kW	2 l	05/97→10/02	 ; -> 03/99	KH00083 ProKIT
2.3	103 kW	2.3 l	05/97→02/00		
2.9 D (KJ)	72 kW	2.9 l	12/96→10/00		
2.3	105 kW	2.3 l	01/99→11/06	 ; 03/99 -> 09/05	KH00083 ProKIT
2.3	105 kW	2.3 l	02/99→11/06		
2.9 TD	88 kW	2.9 l	04/98→02/00	 ; 03/99 ->	KH00083 ProKIT
3.2	156 kW	3.2 l	01/99→02/00		
3.2	156 kW	3.2 l	01/99→11/02		
2.9 TD	88 kW	2.9 l	04/98→11/06		KH00083 ProKIT
<b>SSANGYONG - MUSSO (FJ)</b>					<b>10/95→09/07</b>
2.3	110 kW	2.3 l	04/03→08/06		KH00083 ProKIT
2.9 D	73 kW	2.9 l	03/96→11/98		
2.3 D	59 kW	2.3 l	10/95→04/99	 ; -> 03/99	KH00083 ProKIT
2.9 TD	88 kW	2.9 l	04/98→09/07	 ; 03/99 ->	KH00083 ProKIT
3.2	162 kW	3.2 l	06/96→09/04	 ; 02/97 -> 04/00	KH00083 ProKIT
<b>SSANGYONG - REXTON (GAB_)</b>					<b>04/02→</b>
2.7 Xdi	120 kW	2.7 l	08/04→		KH00083 ProKIT
2.9 TD	88 kW	2.9 l	04/02→08/06		
3.2 RX320 4x4	162 kW	3.2 l	04/02→		



											
<b>SUBARU - FORESTER (SF_)</b>											<b>08/97→09/02</b>
2.0 AWD (SF5)	90 kW	2 l	08/97→09/02								KH10359 ProKIT
2.0 AWD (SF5)	92 kW	2 l	06/98→09/02								KH10345 ProKIT
2.0 S Turbo AWD (SF5)	125 kW	2 l	06/98→04/01								
2.0 S Turbo AWD (SF5)	130 kW	2 l	04/01→09/02								
<b>SUBARU - FORESTER (SG_)</b>											<b>02/02→05/08</b>
2.0 AWD (SG5)	92 kW	2 l	06/02→05/05								KH10359 ProKIT
2.0 S Turbo AWD (SG5)	130 kW	2 l	02/02→05/05								KH10345 ProKIT
2.0 X AWD (SG5)	116 kW	2 l	06/05→05/08								KH10345 ProKIT
2.5 AWD (SG9, S11SG, S12SH)	169 kW	2.5 l	06/05→05/08								
2.5 AWD (SG9)	155 kW	2.5 l	12/03→05/05								
<b>SUBARU - FORESTER (SH_)</b>											<b>01/08→09/13</b>
2.0 AWD (SH5)	110 kW	2 l	01/08→09/13								KH30092 ProKIT
2.0 AWD (SHJ)	110 kW	2 l	01/10→								KH30136 ProKIT
2.5 AWD (SH9)	126 kW	2.5 l	01/09→09/13								
2.5 AWD (SH9)	169 kW	2.5 l	06/08→09/13								
2.0 D AWD (SHH)	108 kW	2 l	09/08→09/13								KH30092 ProKIT
<b>SUBARU - IMPREZA Estate (GF)</b>											<b>08/92→12/00</b>
1.6 i (GF3)	70 kW	1.6 l	06/98→12/00								KH10359 ProKIT
											KH20177 ProKIT
1.6 i AWD (GF4)	66 kW	1.6 l	08/92→12/00								KH10359 ProKIT
1.6 i AWD (GF4)	70 kW	1.6 l	06/98→12/00								KH10345 ProKIT
1.8 i AWD (GF6)	76 kW	1.8 l	08/92→12/00								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 i 16V AWD (GF8)	92 kW	2 l	06/98→12/00								
2.0 i AWD (GF8)	85 kW	2 l	12/95→12/00								
2.0 i Turbo AWD (GF8)	155 kW	2 l	03/94→12/00								
2.0 Turbo GT AWD (GF8)	160 kW	2 l	06/98→12/00								
<b>SUBARU - IMPREZA Hatchback (GG)</b>											<b>12/00→12/08</b>
1.5 AWD (GG3)	77 kW	1.5 l	05/06→03/07								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 i R AWD (GG9)	118 kW	2 l	09/05→06/07								KH10345 ProKIT
2.5 WRX AWD (GGG)	169 kW	2.5 l	09/05→12/08								
1.6 AWD	70 kW	1.6 l	12/00→09/06								KH10359 ProKIT
2.0 AWD (GG9)	92 kW	2 l	12/00→12/07								KH10345 ProKIT
2.0 Turbo AWD (GGA)	160 kW	2 l	12/00→12/05								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 WRX Turbo AWD (GGA)	165 kW	2 l	12/02→09/06								
<b>SUBARU - IMPREZA Hatchback (GR, GH, G3, GE)</b>											<b>01/08→08/13</b>
1.5 AWD (GH3)	79 kW	1.5 l	02/08→03/12								KH30092 ProKIT
2.0 R AWD (GH7)	110 kW	2 l	01/08→03/12								KH30136 ProKIT
2.5 AWD (GHE)	169 kW	2.5 l	01/08→09/11								
1.5 F (GH2)	79 kW	1.5 l	02/08→03/12								KH30092 ProKIT
2.0 D AWD	110 kW	2 l	01/09→03/12								
2.5 STI CS400 AWD (GRF)	294 kW	2.5 l	04/10→08/13								KH30154 ProKIT
2.5 WRX STI 330S AWD	243 kW	2.5 l	05/09→12/10								
2.5 WRX STI AWD (GRF)	221 kW	2.5 l	01/08→08/13								KH30092 ProKIT
											KH30154 ProKIT
<b>SUBARU - IMPREZA Saloon (GC)</b>											<b>08/92→12/00</b>
1.6 i (GC3)	66 kW	1.6 l	08/92→12/00								KH10359 ProKIT
1.6 i (GC3)	70 kW	1.6 l	06/98→12/00								KH20177 ProKIT
1.6 i AWD (GC4)	66 kW	1.6 l	08/92→12/00								KH10359 ProKIT
1.6 i AWD (GC4)	70 kW	1.6 l	06/98→12/00								KH10345 ProKIT
1.8 i AWD (GC6)	76 kW	1.8 l	08/92→12/00								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 AWD (GC8)	206 kW	2 l	09/98→09/00								
2.0 i AWD (GC7)	85 kW	2 l	10/95→12/00								
2.0 i AWD (GC8)	92 kW	2 l	06/98→12/00								
2.0 Turbo GT AWD (GC8)	155 kW	2 l	03/94→12/00								
2.0 Turbo GT AWD (GC8)	160 kW	2 l	06/98→12/00								
<b>SUBARU - IMPREZA Saloon (GD)</b>											<b>12/00→06/09</b>
1.5 AWD (GD3)	77 kW	1.5 l	05/06→03/07								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 i R AWD (GD9)	118 kW	2 l	09/05→03/07								KH10345 ProKIT
2.0 i WRX AWD (GDA)	168 kW	2 l	12/02→09/05								
2.0 WRX Turbo AWD (GDA)	165 kW	2 l	12/02→03/07								
2.5 i WRX AWD (GDG)	169 kW	2.5 l	09/05→12/08								
1.6 AWD (GD5)	70 kW	1.6 l	12/00→06/09								KH10359 ProKIT
2.0 i AWD (GD9)	92 kW	2 l	12/00→06/09								<b>Bearing Type: Tapered Roller Bearing</b>
2.0 WRX Turbo AWD (GDA)	160 kW	2 l	12/00→12/05								KH10345 ProKIT

      					
<b>SUBARU - IMPREZA Saloon (GD)</b>				<b>12/00→06/09</b>	
2.0 WRX STi AWD	235 kW	2 l	02/04→07/05		KH10363 ProKIT
2.0 WRX STi AWD (GDB)	195 kW	2 l	11/01→07/05		
2.5 AWD (GDF)	221 kW	2.5 l	10/05→03/07		
2.5 WRX STi AWD (GDF)	206 kW	2.5 l	09/05→12/07		
<b>SUBARU - IMPREZA Saloon (GE, GV)</b>				<b>01/11→</b>	
2.5 WRX STi AWD (GVF)	221 kW	2.5 l	01/11→		KH30154 ProKIT
<b>SUBARU - LIBERTY I Estate / LIBERTY I Sedan / LIBERTY II / LIBERTY II Estate (BC, BJF, BC, BD, BG)</b>				<b>01/89→03/99</b>	
1800 (BC2)	76 kW	1.8 l	01/89→12/93		KH10359 ProKIT
1800 (BF2)	76 kW	1.8 l	01/89→07/94		
2.0 i (BD4)	85 kW	2 l	09/94→03/99	 ABS	KH20177 ProKIT
2.0 i (BG4)	85 kW	2 l	09/94→11/98		
1800 4WD (BC3)	76 kW	1.8 l	01/89→09/91		KH10359 ProKIT
1800 4WD (BF3)	76 kW	1.8 l	01/89→07/94		
2.0 i 4WD (BD5)	85 kW	2 l	09/94→03/99		KH10345 ProKIT
2.0 i 4WD (BG5)	85 kW	2 l	09/94→11/98		
2.2 i 4WD (BD7)	94 kW	2.2 l	09/94→03/99		
2.2 i 4WD (BD7)	96 kW	2.2 l	06/96→03/99		
2.2 i 4WD (BG7)	94 kW	2.2 l	02/94→12/98		
2.2 i 4WD (BG7)	96 kW	2.2 l	06/96→11/98		
2.5 i 4WD (BD9)	110 kW	2.5 l	06/96→03/99		
2.5 i 4WD (BG9)	110 kW	2.5 l	06/96→11/98		
2000 4WD (BC5)	85 kW	2 l	08/91→07/94		
2000 4WD (BF5)	85 kW	2 l	09/91→07/94		
2000 Turbo 4WD (BC5)	147 kW	2 l	05/92→07/94		
2000 Turbo Super 4WD (BF5)	147 kW	2 l	05/92→07/94		
2200 4WD (BC7)	100 kW	2.2 l	01/89→07/94		
2200 Super 4WD (BF7)	100 kW	2.2 l	01/89→07/94		
<b>SUBARU - LIBERTY III Estate / LIBERTY III Sedan (BH, BE)</b>				<b>10/98→08/03</b>	
2.0 AWD	206 kW	2 l	06/02→08/03		KH10359 ProKIT
3.0 H6 AWD (BHE)	154 kW	3 l	08/00→08/03		
2.0 AWD (BE5)	92 kW	2 l	04/99→08/03		KH10359 ProKIT
2.0 AWD (BH5)	92 kW	2 l	12/98→08/03	 -> 06/03	KH20154 ProKIT
2.5 AWD (BE9)	115 kW	2.5 l	10/98→08/03		
2.5 AWD (BH9)	115 kW	2.5 l	12/98→08/03		
<b>SUBARU - LIBERTY IV Estate / LIBERTY IV Sedan (BP, BL)</b>				<b>09/03→12/09</b>	
2.0 AWD (BL5)	101 kW	2 l	09/03→10/05		KH30092 ProKIT
2.0 AWD (BL5)	121 kW	2 l	06/05→04/09		
2.0 AWD (BP5)	101 kW	2 l	09/03→10/05		KH30036 ProKIT
2.0 AWD (BP5)	121 kW	2 l	06/05→04/09		
2.0 D AWD (BLD)	110 kW	2 l	02/08→12/09		
2.0 D AWD (BPD)	110 kW	2 l	02/08→12/09		
2.0 R AWD (BL5)	110 kW	2 l	09/07→12/09		
2.0 R AWD (BP5)	110 kW	2 l	09/07→12/09		
2.5 AWD (BL9)	121 kW	2.5 l	09/03→04/09		
2.5 AWD (BP9)	121 kW	2.5 l	09/03→04/09		
2.5 i AWD (BL9)	127 kW	2.5 l	09/07→12/09		
2.5 i AWD (BP9)	127 kW	2.5 l	01/08→12/09		
3.0 R AWD (BLE)	180 kW	3 l	09/03→08/09		
3.0 R AWD (BPE)	180 kW	3 l	09/03→08/09		
<b>SUBARU - LIBERTY V Estate / LIBERTY V Sedan (BR, BM)</b>				<b>09/09→12/14</b>	
2.0 D AWD	108 kW	2 l	01/13→12/14		KH30136 ProKIT
2.0 i AWD	110 kW	2 l	06/12→12/14		
2.5 i AWD (BRM)	127 kW	2.5 l	07/12→12/14		
2.0 D AWD	110 kW	2 l	09/09→12/14		KH30092 ProKIT
2.0 D AWD (BMD)	110 kW	2 l	09/09→12/14		
2.0 i AWD	110 kW	2 l	09/09→12/14		KH30136 ProKIT
2.0 i AWD (BM5)	110 kW	2 l	09/09→12/14		
2.5 i AWD (BM9)	123 kW	2.5 l	09/09→12/14		
2.5 i AWD (BR9)	123 kW	2.5 l	09/09→12/14		
2.5 GT AWD (BM9)	195 kW	2.5 l	07/10→12/14		KH30092 ProKIT
2.5 GT AWD (BR9)	195 kW	2.5 l	07/10→12/14		
<b>SUBARU - OUTBACK Estate (BR)</b>				<b>09/09→</b>	
2.0 D AWD (BRD)	110 kW	2 l	09/09→		KH30136 ProKIT
2.5 i AWD (BR9)	123 kW	2.5 l	09/09→		
3.6 R AWD (BRF)	191 kW	3.6 l	09/09→		
<b>SUBARU - OUTBACK Wagon (BE, BH)</b>				<b>10/00→08/03</b>	
2.5 AWD (BH9)	115 kW	2.5 l	10/00→08/03	 -> 06/03	KH20154 ProKIT
3.0 H6 AWD (BHE)	154 kW	3 l	10/00→08/03		





**SUBARU - OUTBACK Wagon (BL, BP)**

**11/03→09/09**

























































2.0 D AWD (BPD)	110 kW	2 l	09/08→09/09		<b>KH30092</b> ProKIT
2.5 AWD (BP9)	121 kW	2.5 l	11/03→09/09		<b>KH30036</b> ProKIT
2.5 AWD (BP9)	127 kW	2.5 l	09/08→09/09		
3.0 AWD (BPE)	180 kW	3 l	11/03→09/09		

**SUBARU - SVX (CX)**



























































**09/92→12/97**






























































3.3 i 24V 4WD (CXW)	162 kW	3.3 l	09/94→12/97		<b>KH10363</b> ProKIT
3.3 i 24V 4WD (CXW)	169 kW	3.3 l	09/92→09/94		






















































												
<b>SUZUKI - ALTO I / ALTO II Van (0S)</b>											<b>06/82→12/88</b>	
0.8 (SB308/CA)	29 kW	0.8 l	01/86→12/88								KH00048 ProKIT	
0.8 (SS80)	29 kW	0.8 l	06/82→08/84									
<b>SUZUKI - ALTO IV (EF)</b>											<b>09/94→06/02</b>	
1.0 (SH410)	39 kW	1 l	09/94→06/02								KH10375 ProKIT	
											KH00048 ProKIT	
<b>SUZUKI - ALTO VI (FF)</b>											<b>09/04→12/08</b>	
1.1 (RF410)	46 kW	1.1 l	09/04→12/08								KH10215 ProKIT	
					-> 03/06						KH10124 ProKIT	
											KH00048 ProKIT	
<b>SUZUKI - ALTO VII (GF)</b>											<b>01/09→</b>	
1.0 (AMF310)	50 kW	1 l	01/09→								KH10215 ProKIT	
					ABS						KH10033 ProKIT	
<b>SUZUKI - BALENO Estate / BALENO Hatchback / BALENO Sedan (EG)</b>											<b>07/95→05/02</b>	
1.3 (SY413)	52 kW	1.3 l	09/96→05/02								KH10413 ProKIT	
1.3 16V (SY413)	63 kW	1.3 l	03/97→05/02		ABS						KH20122 ProKIT	
1.3 i 16V (SY413)	63 kW	1.3 l	07/95→05/02									
1.6 i 16V (SY416)	72 kW	1.6 l	07/95→05/02									
1.6 i 16V (SY416)	72 kW	1.6 l	08/96→05/02									
1.6 i 16V (SY416)	73 kW	1.6 l	08/96→05/02									
1.8 GTX (SY418)	89 kW	1.8 l	03/96→05/02									
1.8 i 16V (SY418)	89 kW	1.8 l	08/96→05/02									
1.9 TD (SY419)	55 kW	1.9 l	04/98→05/02									
1.6 i 16V 4x4 (SY416)	72 kW	1.6 l	07/95→05/02								KH10413 ProKIT	
1.6 i 16V 4x4 (SY416)	72 kW	1.6 l	08/96→05/02								KH10401 ProKIT	
1.6 i 16V 4x4 (SY416)	73 kW	1.6 l	08/96→05/02									
<b>SUZUKI - CAPPUCCINO (EE)</b>											<b>02/92→08/95</b>	
0.7 (SX306)	47 kW	0.7 l	02/92→08/95		ABS						KH10401 ProKIT	
<b>SUZUKI - CARRY Van (0S)</b>											<b>11/80→10/85</b>	
0.8 (ST90)	27 kW	0.8 l	11/80→10/85								KH00048 ProKIT	
<b>SUZUKI - CULTUS Convertible (SF413)</b>											<b>09/91→10/96</b>	
1.3 i (SF413, AK35, SY415, E35)	50 kW	1.3 l	09/91→10/96		04/92 -> 08/96						KH10375 ProKIT	
											KH00048 ProKIT	
<b>SUZUKI - GRAND VITARA / GRAND VITARA I Open Off-Road Vehicle (INC XL-7) I, GT)</b>											<b>03/98→09/05</b>	
1.6 4x4 (SQ 416)	69 kW	1.6 l	03/98→07/03		OE 09269-41001						KH10072 ProKIT	
2.0 4x4 (TA52, TL52, SQ 420)	94 kW	2 l	03/98→07/03		ABS						KH20107 ProKIT	
2.0 HDI 110 16V 4x4 (SQ 420D)	80 kW	2 l	07/01→09/05		ABS						KH00049 ProKIT	
2.0 TD 4x4 (SQ 420D)	64 kW	2 l	03/98→07/03		ABS							
2.5 V6 24V 4x4 (SQ 625)	116 kW	2.5 l	04/01→07/03									
2.5 V6 24V 4x4 (TD62, SQ 625)	106 kW	2.5 l	04/98→07/03									
1.6 4x4 (SQ 416)	69 kW	1.6 l	03/98→07/03		OE 09269-41001						KH10072 ProKIT	
1.6 4x4 (SQ 416)	71 kW	1.6 l	09/03→09/05									
1.6 4x4 (SQ 416)	73 kW	1.6 l	02/00→09/02									
2.0 4x4 (SQ 420)	97 kW	2 l	08/98→12/00									
2.0 4x4 (SQ 420)	103 kW	2 l	04/98→08/05									
2.0 TD 4x4 (SQ 420D)	63 kW	2 l	04/00→09/05									
2.0 HDI 110 4x4 (SQ 420D)	80 kW	2 l	02/01→12/03		ABS						KH20107 ProKIT	
					ABS						KH00049 ProKIT	
2.7 4x4 (JA 627)	127 kW	2.7 l	09/01→07/03		ABS						KH20107 ProKIT	
2.7 4x4 (TX92, JA 627)	135 kW	2.7 l	04/03→07/03									
<b>SUZUKI - GRAND VITARA II Wagon Hardtop (JT, TE, TD)</b>											<b>04/05→</b>	
1.6 All-wheel Drive (JB416)	78 kW	1.6 l	04/05→02/15								KH30090 ProKIT	
1.9 DDiS All-wheel Drive (JT419, TD44, JB419WD, JB419XD)	95 kW	1.9 l	10/05→02/15									
2.0 All-wheel Drive (TD54, JB420)	103 kW	2 l	10/05→02/15									
2.4 All-wheel Drive (JB424)	124 kW	2.4 l	01/09→									
2.4 All-wheel Drive (JT424, JB424)	122 kW	2.4 l	01/09→									
3.2 All-wheel Drive (TDB4, JT632, JB632)	171 kW	3.2 l	01/09→02/15									
<b>SUZUKI - IGNIS I (FH)</b>											<b>10/00→12/05</b>	
1.3 (HV51, HX51, RG413)	61 kW	1.3 l	10/00→09/03								KH10215 ProKIT	



											
<b>SUZUKI - IGNIS I (FH)</b>										<b>10/00→12/05</b>	
1.3 4WD (RG413)	61 kW	1.3 l	10/00→09/03								KH10215 ProKIT
					Code: RG413-2, RG413-3;						KH00115 ProKIT
1.5 Sport (RG415)	80 kW	1.5 l	12/03→12/05								KH10121 ProKIT
											KH30153 ProKIT
<b>SUZUKI - IGNIS II (MH)</b>										<b>09/03→</b>	
1.3 (RM413)	69 kW	1.3 l	09/03→								KH10121 ProKIT
1.3 DDiS (RM413D)	51 kW	1.3 l	09/03→								
1.5 (RM415)	73 kW	1.5 l	09/03→								
1.3 4x4 (RM413)	69 kW	1.3 l	09/03→								KH10121 ProKIT
					-> 04/09; Code: RG413-2, RG413-3, RG413-4;						KH00115 ProKIT
											
1.5 4x4 (RM415)	73 kW	1.5 l	09/03→								KH10121 ProKIT
					-> 04/09; Code: RG415;						KH00115 ProKIT
<b>SUZUKI - JIMNY Hardtop (SN)</b>										<b>09/98→</b>	
1.3 16V (SN413)	59 kW	1.3 l	09/98→		-> 04/09						KH10118 ProKIT
1.3 16V 4WD (SN413)	59 kW	1.3 l	09/98→								KH00138 ProKIT
1.3 16V (SN413)	60 kW	1.3 l	02/01→		-> 04/09						KH10118 ProKIT
1.3 16V 4WD (SN413)	60 kW	1.3 l	02/01→		04/02 ->						KH00138 ProKIT
							not for code: SN413V-1;				KH00074 ProKIT
1.3 16V 4x4 (SN413)	63 kW	1.3 l	08/05→		-> 04/09						KH10118 ProKIT
1.5 DDiS 4WD (SN415D)	48 kW	1.5 l	12/03→								KH00074 ProKIT
											KH00138 ProKIT
1.5 DDiS 4x4	63 kW	1.5 l	08/05→		-> 04/09						KH10118 ProKIT
					10/05 ->						KH00138 ProKIT
											KH00074 ProKIT
<b>SUZUKI - LIANA Hatchback / LIANA Sedan (ER, RH_)</b>										<b>07/01→12/07</b>	
1.3	66 kW	1.3 l	07/01→12/07								KH10121 ProKIT
1.3 (RH 413)	66 kW	1.3 l	03/02→								KH20122 ProKIT
1.4 DDiS	66 kW	1.4 l	04/04→12/07								
1.4 DDiS (RH 414D)	66 kW	1.4 l	04/04→								
1.6	76 kW	1.6 l	07/01→12/07								
1.6	79 kW	1.6 l	01/05→08/07								
1.6 (RH 416)	76 kW	1.6 l	03/02→								
1.6 (RH 416)	79 kW	1.6 l	01/05→								
1.6 i (RH416)	78 kW	1.6 l	04/02→								
1.6 i (RH416)	78 kW	1.6 l	04/02→12/07								
1.6 4WD	76 kW	1.6 l	07/01→12/07								KH10121 ProKIT
1.6 4WD	78 kW	1.6 l	04/02→12/07								KH10401 ProKIT
1.6 4WD	79 kW	1.6 l	01/05→12/07								
1.6 4WD (RH 416)	79 kW	1.6 l	01/05→12/07								
1.6 4WD (RH 416)	76 kW	1.6 l	03/02→								KH10121 ProKIT
1.6 4WD (RH 416)	78 kW	1.6 l	04/02→		-> 04/09						KH10401 ProKIT
<b>SUZUKI - LJ80 (OL)</b>										<b>01/80→01/84</b>	
0.8 (LJ 80)	29 kW	0.8 l	01/80→01/84								KH00047 ProKIT
<b>SUZUKI - S-CROSS (JY)</b>										<b>08/13→</b>	
1.0 (AKK 310)	82 kW	1 l	08/16→								KH30108 ProKIT
1.4 T (AKK 414)	103 kW	1.4 l	08/16→								
1.6 (AKK416)	85 kW	1.6 l	12/13→								
1.6 (AKK 416)	86 kW	1.6 l	12/13→								
1.6 (AKK 416)	88 kW	1.6 l	08/13→								
1.6 DDiS (AKK 416D)	88 kW	1.6 l	08/13→								
<b>SUZUKI - SIERRA (OS)</b>										<b>09/84→08/90</b>	
1.3 (SJ413)	47 kW	1.3 l	09/84→08/90								KH00018 ProKIT
					01/86 ->						KH00138 ProKIT
											KH00047 ProKIT
1.3 (SJ 413)	44 kW	1.3 l	08/86→08/90								KH00018 ProKIT
											KH00047 ProKIT
											KH00138 ProKIT
<b>SUZUKI - SIERRA Cabrio (OS)</b>										<b>09/81→07/91</b>	
1.0 (SJ410)	33 kW	1 l	09/81→07/91								KH00018 ProKIT
					-> 06/85						KH00138 ProKIT
											KH00047 ProKIT

										
<b>SUZUKI - SIERRA Closed Off-Road Vehicle (SJ_)</b>										<b>11/88→12/04</b>
1.0 All-wheel Drive (SJ 410)	33 kW	1 l	11/88→12/04							KH00018 ProKIT
1.3 All-wheel Drive (SJ 413)	44 kW	1.3 l	11/88→12/04							KH00138 ProKIT
1.3 All-wheel Drive (SJ 413)	47 kW	1.3 l	11/88→12/04							
1.3 All-wheel Drive (SJ 413)	51 kW	1.3 l	11/88→12/04							KH00018 ProKIT
1.3 All-wheel Drive (SJ 413)	59 kW	1.3 l	01/00→12/04							
1.9 D All-wheel Drive	47 kW	1.9 l	11/98→12/04							
1.9 TD All-wheel Drive (SJ 419TD)	46 kW	1.9 l	11/98→12/04							KH00018 ProKIT
										KH00138 ProKIT
<b>SUZUKI - SJ410</b>										<b>09/81→12/88</b>
1.0 (SJ410)	33 kW	1 l	09/81→12/88							KH00018 ProKIT
										KH00138 ProKIT
										KH00047 ProKIT
<b>SUZUKI - SPLASH (EX)</b>										<b>01/08→</b>
1.0 (A5B 310)	48 kW	1 l	01/08→							KH10137 ProKIT
1.2 (A5B 412)	63 kW	1.2 l	01/08→							KH10030 ProKIT
1.3 CDTI (A5B 413D)	55 kW	1.3 l	01/08→							
1.0 (A5B 310)	50 kW	1 l	06/11→							KH10030 ProKIT
1.2 VVT (A5B 412)	66 kW	1.2 l	06/11→							
<b>SUZUKI - SUPER CARRY Bus (ED)</b>										<b>10/85→03/99</b>
1.0 (SK410)	30 kW	1 l	09/94→03/99							KH00047 ProKIT
1.0 (SK410)	31 kW	1 l	10/92→03/99							
1.0 (SK410)	33 kW	1 l	10/85→03/99							
<b>SUZUKI - SWIFT I (AA)</b>										<b>10/83→12/89</b>
1.0 (SA310, AA41/43)	37 kW	1 l	10/83→03/89							KH10375 ProKIT
										KH00048 ProKIT
										
1.0 Turbo (SA310)	52 kW	1 l	02/85→12/89							KH10375 ProKIT
1.3 (SA413, AA51/53)	54 kW	1.3 l	10/84→03/89							KH10375 ProKIT
1.3 (SA413, AA51)	50 kW	1.3 l	10/84→03/89							
1.3 (SA413, AA53)	47 kW	1.3 l	08/86→03/89							KH00048 ProKIT
										
1.3 GTi/GXi (SA413, AA33)	74 kW	1.3 l	08/85→03/89							KH10375 ProKIT
<b>SUZUKI - SWIFT II Hatchback / SWIFT II Saloon (EA, MA, AH, AJ)</b>										<b>03/89→12/05</b>
1.0 (SF310, AA44)	37 kW	1 l	03/89→05/01							KH10375 ProKIT
1.3 (SF413, AB35)	50 kW	1.3 l	03/89→05/01							KH00048 ProKIT
1.0 i (SF310, AA44)	39 kW	1 l	01/95→12/05							KH10375 ProKIT
1.0 i (SF310, AA44)	40 kW	1 l	03/89→12/91							KH10375 ProKIT
1.3 (SF413, AB35)	52 kW	1.3 l	03/89→12/91							KH00048 ProKIT
1.6 (SF416, AH14)	70 kW	1.6 l	11/89→12/91							
1.3 (SF413, AH35, MA)	50 kW	1.3 l	01/91→12/95							KH10375 ProKIT
										KH00048 ProKIT
1.3 (SF413, AH35)	52 kW	1.3 l	03/89→12/91							KH10375 ProKIT
										KH00048 ProKIT
1.3 4WD (SF413, AA35)	50 kW	1.3 l	03/89→05/01							KH10401 ProKIT
1.3 4WD (SF413, AF35)	52 kW	1.3 l	10/89→12/91							KH10375 ProKIT
										KH10401 ProKIT
1.6 i 4WD (SF416, AJ14)	68 kW	1.6 l	01/90→05/01							KH10401 ProKIT
<b>SUZUKI - SWIFT III / SWIFT IV (MZ, EZ, FZ, NZ)</b>										<b>02/05→</b>
1.2 (AZG 412)	66 kW	1.2 l	10/10→							KH10137 ProKIT
1.2 (AZH 412, AZG 412)	67 kW	1.2 l	08/12→							
1.2 (AZH 412)	69 kW	1.2 l	10/10→							
1.3 DDiS (AZG 413D)	55 kW	1.3 l	10/10→							
1.3 DDiS (RS 413D)	55 kW	1.3 l	08/05→							
1.3 (RS 413)	68 kW	1.3 l	02/05→							KH10137 ProKIT
1.3 DDiS (RS 413D)	51 kW	1.3 l	08/05→							KH10030 ProKIT
1.5 (RS 415)	75 kW	1.5 l	02/05→							
1.3 4x4 (RS 413)	66 kW	1.3 l	01/06→							KH10030 ProKIT
1.3 4x4 (RS 413)	68 kW	1.3 l	02/05→							
1.6 (AZG 416, AZH 416, RS416)	100 kW	1.6 l	01/12→							KH10022 ProKIT
										KH30108 ProKIT
										KH10022 ProKIT

										
<b>SUZUKI - SX4 / SX4 Saloon (EY, GY, GY, RW)</b>										<b>06/06→12/15</b>
1.5 (RW 415)	73 kW	1.5 l	06/06→07/10							<b>KH10022</b> ProKIT
1.5 VVT (RW 415)	82 kW	1.5 l	07/10→							<b>KH30108</b> ProKIT
1.6 DDiS (RW 416D)	66 kW	1.6 l	04/07→							
1.6 VVT (RW 416)	79 kW	1.6 l	06/06→							
1.6 VVT (RW 416)	88 kW	1.6 l	07/09→							
1.9 DDiS (RW 419D)	88 kW	1.9 l	06/06→							
2.0 DDiS (RW 420D)	99 kW	2 l	07/09→							
1.5 VVT 4x4 (RW 415)	82 kW	1.5 l	07/10→							<b>KH10022</b> ProKIT
1.6 (RW 416)	79 kW	1.6 l	10/07→							
1.6 (RW 416)	88 kW	1.6 l	10/07→							
1.5 VVTi	81 kW	1.5 l	07/07→12/15							<b>KH30108</b> ProKIT
1.6 VVT	82 kW	1.6 l	11/10→12/15							
1.6 VVT 4x4 (RW 416)	79 kW	1.6 l	06/06→							<b>KH10022</b> ProKIT
1.9 DDiS 4x4 (RW 419D)	88 kW	1.9 l	06/06→							<b>KH30075</b> ProKIT
										<b>KH30197</b> ProKIT
1.6 VVT 4x4 (RW 416)	82 kW	1.6 l	07/09→							<b>KH10022</b> ProKIT
										<b>KH30197</b> ProKIT
1.6 VVT 4x4 (RW 416)	88 kW	1.6 l	07/09→							<b>KH10022</b> ProKIT
2.0 DDiS 4x4 (RW 420D)	99 kW	2 l	07/09→							<b>KH30075</b> ProKIT
										<b>KH30197</b> ProKIT
<b>SUZUKI - VITARA / VITARA Cabrio (ET, TA, TD, ET, ET, TA)</b>										<b>07/88→12/05</b>
1.6 (SE 416)	55 kW	1.6 l	01/90→12/93							<b>KH10072</b> ProKIT
1.6 All-wheel Drive (SE 416)	55 kW	1.6 l	10/88→12/98							
2.0 16V (TA51, SV420)	97 kW	2 l	12/96→03/99							
2.0 HDI (SE 420HDI)	64 kW	2 l	01/02→12/05							
2.0 V6 24V All-wheel Drive (SV620)	100 kW	2 l	12/94→03/98							
HDI (SE 420HDI)	64 kW	2 l	12/03→12/05							
1.6 (TA01, SE416)	59 kW	1.6 l	07/88→01/95							<b>KH10072</b> ProKIT
1.6 All-wheel Drive (SE 416)	60 kW	1.6 l	07/88→12/95							<b>KH00064</b> ProKIT
1.6 All-wheel Drive (TA, TA01, SE416)	59 kW	1.6 l	07/88→03/98							<b>KH10072</b> ProKIT
										<b>KH00064</b> ProKIT
1.6 i 16V (TA02, SE416)	71 kW	1.6 l	07/90→03/99							<b>KH10072</b> ProKIT
1.6 i 16V All-wheel Drive (ET, TA02, SE416)	71 kW	1.6 l	07/90→03/98							<b>KH00064</b> ProKIT
1.9 D All-wheel Drive (SE 419TD)	55 kW	1.9 l	08/96→03/98							
2.0 16V All-wheel Drive (SV420)	97 kW	2 l	12/96→03/98							
1.9 D (SE 419TD)	50 kW	1.9 l	01/95→03/98							<b>KH10072</b> ProKIT
1.9 D All-wheel Drive (SE 419TD)	50 kW	1.9 l	01/95→03/98							<b>KH00064</b> ProKIT
2.0 TD All-wheel Drive (SV 420D)	52 kW	2 l	12/94→03/98							
2.0 TD Intercooler All-wheel Drive (SV 420D)	64 kW	2 l	12/95→03/98							
1.9 D (SE 419TD)	55 kW	1.9 l	08/96→03/99							<b>KH10072</b> ProKIT
										<b>KH00064</b> ProKIT
<b>SUZUKI - WAGON R+ Hatchback (EM, MM)</b>										<b>02/98→</b>
1.0 (RC410, SR410, SR412)	48 kW	1 l	02/98→05/00							<b>KH10215</b> ProKIT
1.2 (SR412)	51 kW	1.2 l	02/98→05/00							
1.2 4WD (SR412)	51 kW	1.2 l	02/98→05/00							
1.3 (RB 413)	56 kW	1.3 l	05/00→12/04							
1.3 (RB 413)	69 kW	1.3 l	09/03→							
1.3 4WD (RB 413)	56 kW	1.3 l	10/01→							<b>KH10215</b> ProKIT
1.3 4WD (RB 413)	69 kW	1.3 l	09/03→							<b>KH00115</b> ProKIT
										<b>KH10121</b> ProKIT
1.3 DDiS (RB 413D)	51 kW	1.3 l	09/03→							
<b>SUZUKI - X-90 (EL)</b>										<b>09/95→12/97</b>
1.6 i 16V 4x4 (SZ416)	71 kW	1.6 l	09/95→12/97							<b>KH10072</b> ProKIT
										<b>KH00064</b> ProKIT









































































**TALBOT - SAMBA / SAMBA Convertible**

**01/81→10/86**




















0.9 (51A601, 51A591)	31 kW	0.9 l	01/81→12/85		<b>KH00091</b> ProKIT
1.1 (51A611, 51A702)	37 kW	1.1 l	01/81→06/86		<b>KH00094</b> ProKIT
1.2 Rallye (51A692)	65 kW	1.2 l	01/83→10/86		
1.4 (51A632)	53 kW	1.4 l	01/81→06/86		
1.4 (51A642)	44 kW	1.4 l	06/83→10/86		
1.4 (51E642)	58 kW	1.4 l	01/81→06/86		
1.4 Rallye (51A642)	58 kW	1.4 l	01/83→10/86		

































































											
<b>TOYOTA - 4 RUNNER I (_N5_, _N6_, _N7_) 08/87→07/89</b>											
2.4 4WD (RN50, RN55, RN60)	82 kW	2.4 l	08/87→07/89								KH00134 ProKIT
<b>TOYOTA - 1000 / 1000 Estate (KP3_, KP36V_) 04/69→08/88</b>											
1.0 (KP30)	33 kW	1 l	04/69→02/78							KH00056 ProKIT	
1.0 (KP36V)	33 kW	1 l	04/69→08/88	; 01/74 ->							
<b>TOYOTA - ALLION I / ALLION II (_T24_, _T26_) 06/01→</b>											
1.5 (NZT240)	80 kW	1.5 l	06/01→04/05						KH10002 ProKIT		
1.5 (NZT260_)	80 kW	1.5 l	07/07→								
1.8 (ZRT260)	100 kW	1.8 l	07/07→								
1.8 (ZRT260)	105 kW	1.8 l	12/12→								
1.8 (ZRT260)	106 kW	1.8 l	07/07→02/13								
1.8 (ZZT240)	92 kW	1.8 l	06/01→09/04								
1.8 (ZZT240)	97 kW	1.8 l	06/01→04/05								
1.8 4WD (ZRT265)	92 kW	1.8 l	07/07→								
1.8 4WD (ZRT265)	96 kW	1.8 l	03/13→								
1.8 4WD (ZRT265)	98 kW	1.8 l	07/07→02/13								
1.8 4WD (ZZT245)	92 kW	1.8 l	06/01→09/04								
1.8 4WD (ZZT245)	97 kW	1.8 l	06/01→06/07								
2.0 (AZT240)	92 kW	2 l	06/01→09/04								
2.0 (AZT240)	114 kW	2 l	06/01→04/05								
2.0 (ZRT261)	112 kW	2 l	12/12→								
2.0 (ZRT261)	116 kW	2 l	07/07→02/13								
2.0 4WD (AZT240)	114 kW	2 l	06/01→04/07								
<b>TOYOTA - AURIS Estate (_E18_) 07/13→12/18</b>											
1.3 (NRE180_)	73 kW	1.3 l	07/13→12/18							KH30017 ProKIT	
1.4 D-4D (NDE180_)	66 kW	1.4 l	07/13→12/18								
1.6 (ZRE185_)	97 kW	1.6 l	07/13→12/18						KH30017 ProKIT		
1.8 Hybrid (ZWE186_)	73 kW	1.8 l	07/13→12/18								
1.6 D-4D (WWE185_)	82 kW	1.6 l	04/15→12/18						KH30018 ProKIT		
2.0 D-4D (ADE186_)	91 kW	2 l	07/13→04/15								
<b>TOYOTA - AURIS VAN Hatchback Van (_E18_) 03/13→12/18</b>											
1.4 D-4D (NDE180_)	66 kW	1.4 l	03/13→12/18						KH30035 ProKIT		
<b>TOYOTA - AVENTIS (_T22_) 09/97→02/03</b>											
1.6 (AT220_)	74 kW	1.6 l	09/97→10/00						KH10402 ProKIT		
1.6 (AT220_)	81 kW	1.6 l	10/97→06/00								
1.6 VVT-i (ZZT220_)	81 kW	1.6 l	10/00→02/03						KH20162 ProKIT		
1.8 (AT221_)	81 kW	1.8 l	09/97→10/00								
1.8 VVT-i (ZZT221_)	95 kW	1.8 l	10/00→02/03								
2.0 (ST220_)	94 kW	2 l	09/97→10/00								
2.0 D-4D (CDT220_)	81 kW	2 l	10/99→02/03								
2.0 TD (CT220_)	66 kW	2 l	09/97→02/03								
2.0 VVT-i (AZT220_)	110 kW	2 l	10/00→02/03								
<b>TOYOTA - AVENTIS (_T25_) 03/03→11/08</b>											
1.6 VVT-i (ZZT250_)	81 kW	1.6 l	04/03→11/08						KH10002 ProKIT		
1.8 (ZZT251_)	95 kW	1.8 l	03/03→10/08								
2.0 (AZT250_)	108 kW	2 l	03/03→11/08						KH30117 ProKIT		
2.0 D-4D (ADT250_)	93 kW	2 l	03/06→11/08								
2.4 (AZT251_)	120 kW	2.4 l	10/03→10/08								
2.4 (AZT251_)	125 kW	2.4 l	09/03→11/08								
2.0 D-4D (CDT250_)	85 kW	2 l	04/03→11/08						KH10002 ProKIT		
					ABS						
											
2.0 VVTi (AZT250_)	114 kW	2 l	03/03→10/08						KH10002 ProKIT		
2.2 D-4D (ADT251_)	110 kW	2.2 l	10/05→11/08		ABS				KH10021 ProKIT		
2.2 D-CAT (ADT251_)	130 kW	2.2 l	07/05→11/08								
<b>TOYOTA - AVENTIS Estate (_T22_) 09/97→02/03</b>											
1.6 (AT220_, ZZT220_)	81 kW	1.6 l	09/97→10/00						KH10402 ProKIT		
1.6 (AT220_)	74 kW	1.6 l	09/97→10/00								
1.6 (ZZT220_)	81 kW	1.6 l	07/00→02/03						KH20162 ProKIT		
1.8 (AT221_)	81 kW	1.8 l	09/97→10/00								
1.8 (ZZT221_)	95 kW	1.8 l	10/00→02/03								
2.0 (AZT220_)	110 kW	2 l	10/00→02/03								
2.0 (ST220_)	94 kW	2 l	09/97→10/00								
2.0 D (CDT220_)	85 kW	2 l	09/02→02/03								
2.0 D (CT220_)	61 kW	2 l	10/97→05/98								
2.0 D-4D (CDT220_)	81 kW	2 l	10/99→02/03								
2.0 TD (CT220_)	66 kW	2 l	09/97→02/03								



















































										
<b>TOYOTA - AVENSIS Estate (_T25_)</b>										<b>04/03→11/08</b>
1.6 VVT-i (ZZT250_)	81 kW	1.6 l	04/03→11/08							<b>KH10002</b> ProKIT
1.8 (ZZT251_)	95 kW	1.8 l	04/03→11/08							<b>KH30117</b> ProKIT
2.0 (AZT250_)	108 kW	2 l	04/03→11/08							
2.0 D-4D (ADT250_)	93 kW	2 l	03/06→11/08							
2.0 D-4D (CDT250_)	85 kW	2 l	04/03→11/08							
2.4 (AZT251_)	120 kW	2.4 l	10/03→10/08							
2.4 (AZT251_)	125 kW	2.4 l	09/03→11/08							
2.0 VVTi (AZT250_)	114 kW	2 l	04/03→11/08							<b>KH10002</b> ProKIT
2.2 D-4D (ADT251_)	110 kW	2.2 l	10/05→11/08							<b>KH10021</b> ProKIT
2.2 D-CAT (ADT251_)	130 kW	2.2 l	07/05→11/08							
<b>TOYOTA - AVENSIS Estate (_T27_)</b>										<b>11/08→10/18</b>
1.6 (ZRT270_)	97 kW	1.6 l	11/08→10/18							<b>KH30017</b> ProKIT
1.8 (ZRT271_)	108 kW	1.8 l	11/08→10/18							<b>KH30150</b> ProKIT
2.0 (ZRT272_)	112 kW	2 l	11/08→10/18							
1.6 D4-D (WWT270_)	82 kW	1.6 l	04/15→10/18							<b>KH30018</b> ProKIT
2.0 D-4D (ADT270_)	91 kW	2 l	11/11→10/18							
2.0 D-4D (WWT271_)	105 kW	2 l	04/15→10/18							
2.0 D-4D (ADT270_)	93 kW	2 l	11/08→10/18							<b>KH30018</b> ProKIT
2.2 D-4D (ADT271_)	110 kW	2.2 l	11/08→10/18							<b>KH30150</b> ProKIT
2.2 D-4D (ADT271_)	130 kW	2.2 l	11/08→10/18							
<b>TOYOTA - AVENSIS Liftback (_T22_)</b>										<b>09/97→02/03</b>
1.6 (AT220_)	74 kW	1.6 l	09/97→10/00							<b>KH10402</b> ProKIT
1.6 (AT220_)	81 kW	1.6 l	09/97→10/00							<b>KH20162</b> ProKIT
1.6 (ZZT220_)	81 kW	1.6 l	10/00→02/03							
1.8 (AT221_)	81 kW	1.8 l	09/97→10/00							
1.8 (ZZT221_)	95 kW	1.8 l	10/00→02/03							
2.0 (AZT220_)	110 kW	2 l	10/00→02/03							
2.0 (ST220_)	94 kW	2 l	09/97→10/00							
2.0 D (CDT220_)	85 kW	2 l	09/02→02/03							
2.0 D-4D (CDT220_)	81 kW	2 l	10/99→02/03							
2.0 TD (CT220_)	66 kW	2 l	09/97→02/03							
<b>TOYOTA - AVENSIS Saloon (_T25_)</b>										<b>01/03→11/08</b>
1.6 VVT-i (ZZT250_)	81 kW	1.6 l	04/03→11/08							<b>KH10002</b> ProKIT
1.8 (ZZT251_)	95 kW	1.8 l	04/03→11/08							<b>KH30117</b> ProKIT
2.0 (AZT250_)	108 kW	2 l	04/03→11/08							
2.0 D-4D (ADT250_)	93 kW	2 l	03/06→10/08							
2.0 D-4D (CDT250_)	85 kW	2 l	04/03→11/08							
2.0 VVTi (AZT250_)	114 kW	2 l	01/03→11/08							
2.4 (AZT251_)	120 kW	2.4 l	10/03→10/08							
2.4 (AZT251_)	125 kW	2.4 l	09/03→11/08							
2.0 VVTi 4WD (AZT255)	114 kW	2 l	10/03→10/08							<b>KH10002</b> ProKIT
2.2 D-4D (ADT251_)	110 kW	2.2 l	10/05→11/08							<b>KH10021</b> ProKIT
2.2 D-CAT (ADT251_)	130 kW	2.2 l	07/05→11/08							
<b>TOYOTA - AVENSIS Saloon (_T27_)</b>										<b>11/08→10/18</b>
1.6 (ZRT270_)	97 kW	1.6 l	11/08→10/18							<b>KH30017</b> ProKIT
1.8 (ZRT271_)	108 kW	1.8 l	11/08→10/18							<b>KH30150</b> ProKIT
2.0 (ZRT272_)	112 kW	2 l	11/08→10/18							
1.6 D4-D (WWT270_)	82 kW	1.6 l	04/15→10/18							<b>KH30018</b> ProKIT
2.0 D-4D (ADT270_)	91 kW	2 l	11/11→10/18							
2.0 D-4D (WWT271_)	105 kW	2 l	04/15→10/18							
2.0 (ZRT272)	102 kW	2 l	12/12→10/18							<b>KH30017</b> ProKIT
2.0 D-4D (ADT270_)	93 kW	2 l	11/08→10/18							<b>KH30018</b> ProKIT
2.2 D-4D (ADT271_)	110 kW	2.2 l	11/08→10/18							<b>KH30150</b> ProKIT
2.2 D-4D (ADT271_)	130 kW	2.2 l	11/08→10/18							
<b>TOYOTA - AVENSIS VERSO (_M2_)</b>										<b>08/01→11/09</b>
2.0 (ACM20_)	110 kW	2 l	08/01→11/09		-> 10/09					<b>KH10182</b> ProKIT
					-> 07/05					<b>KH30194</b> ProKIT
2.0 D (CLM20_)	85 kW	2 l	08/01→08/05							<b>KH10182</b> ProKIT
					-> 07/05					<b>KH30194</b> ProKIT
<b>TOYOTA - AYGO (_B1_, _B4_)</b>										<b>07/05→</b>
1.0 (KGB10_)	50 kW	1 l	07/05→05/14							<b>KH10106</b> ProKIT
1.0 (KGB40)	51 kW	1 l	05/14→							
1.0 GPL (KGB10_)	50 kW	1 l	07/05→05/14							<b>KH30064</b> ProKIT
1.2 (PAB40)	60 kW	1.2 l	05/14→							
1.4 HDi (WNB10_)	40 kW	1.4 l	07/05→08/10							














































































     				
<b>TOYOTA - CALDINA Estate (_T24_)</b>				<b>09/02→06/07</b>
1.8 (ZZT241_)	97 kW	1.8 l	09/02→06/07	 KH10002 ProKIT
2.0 (AZT241W_)	112 kW	2 l	09/02→06/07	
2.0 (AZT241W)	114 kW	2 l	09/02→06/07	
2.0 4WD (AZT246W)	110 kW	2 l	09/02→06/07	
2.0 4WD (AZT246W)	114 kW	2 l	09/02→06/07	
2.0 4WD (ST246W)	191 kW	2 l	09/02→06/07	
<b>TOYOTA - CAMRY Saloon (_V3_)</b>				<b>08/01→11/06</b>
2.4 (ACV30, ACV36)	112 kW	2.4 l	11/01→11/06	 ; -> 07/03 KH10182 ProKIT
3.0 (MCV30_)	137 kW	3 l	08/01→11/06	
<b>TOYOTA - CAMRY Sedan (_V2_)</b>				<b>08/96→09/02</b>
2.2 (SXV20_)	96 kW	2.2 l	08/96→11/01	 ; -> 08/01 KH10005 ProKIT
2.2 (SXV20)	93 kW	2.2 l	08/97→09/02	
3.0 24V (MCV20_, MCV20)	140 kW	3 l	08/96→11/01	
3.0 V6 (MCV20_)	135 kW	3 l	08/96→11/01	
<b>TOYOTA - CARINA I Sedan (TA1_)</b>				<b>12/70→03/78</b>
1.6 (TA12_, TA14_)	58 kW	1.6 l	12/70→03/78	 ; -> 04/74 KH00056 ProKIT
<b>TOYOTA - CARINA II Sedan (TA4_, TA6_)</b>				<b>01/78→09/83</b>
1.6 (TA40, TA60)	55 kW	1.6 l	01/78→09/83	 ; -> 07/81 KH00054 ProKIT
<b>TOYOTA - CARINA E VI Liftback / CARINA E VI Saloon / CARINA E VI Sportswagon (_T19_)</b>				<b>04/92→09/97</b>
1.6 (AT190)	73 kW	1.6 l	12/93→09/97	 (ABS) KH10204 ProKIT
1.6 (AT190)	73 kW	1.6 l	01/95→09/97	
1.6 (AT190)	78 kW	1.6 l	10/95→09/97	 KH20162 ProKIT
1.6 (AT190)	79 kW	1.6 l	01/93→09/97	
1.6 (AT190)	85 kW	1.6 l	04/92→09/97	
1.6 (AT190)	85 kW	1.6 l	12/93→09/97	
1.6 16V (AT190_)	78 kW	1.6 l	10/95→09/97	
1.6 16V (AT190_)	85 kW	1.6 l	12/94→09/97	
1.6 GLI (AT190_)	79 kW	1.6 l	01/93→09/97	
1.6 GLI (AT190)	79 kW	1.6 l	04/92→09/97	
1.6 i (AT190_)	73 kW	1.6 l	02/95→09/97	
1.8 (AT191)	79 kW	1.8 l	01/95→09/97	
1.8 i (AT191_)	79 kW	1.8 l	02/95→09/97	
1.8 i 16V (AT191)	79 kW	1.8 l	01/95→09/97	
2.0 (ST191)	98 kW	2 l	01/93→09/97	
2.0 D (CT190_)	54 kW	2 l	01/93→01/96	
2.0 D (CT190)	54 kW	2 l	04/92→01/96	
2.0 D (CT190)	54 kW	2 l	08/92→01/96	
2.0 GLI (ST191_)	98 kW	2 l	01/93→09/97	
2.0 GLI (ST191)	98 kW	2 l	04/92→09/97	
2.0 GTi (ST191_)	116 kW	2 l	04/92→12/95	
2.0 GTi (ST191)	116 kW	2 l	04/92→02/94	
2.0 GTi 16V (ST191_)	129 kW	2 l	03/94→09/97	
2.0 i (ST191_)	93 kW	2 l	05/95→09/97	
2.0 i (ST191)	93 kW	2 l	12/92→09/97	
2.0 i (ST191)	93 kW	2 l	12/93→09/97	
2.0 TD (CT190_)	61 kW	2 l	01/96→09/97	
2.0 TD (CT190)	61 kW	2 l	01/96→09/97	
<b>TOYOTA - CELICA Coupe (_A2_)</b>				<b>05/73→03/78</b>
1.6 GT (TA2, TA22)	79 kW	1.6 l	12/74→03/78	 ; -> 10/77; Code: TA23, TA28 KH00054 ProKIT
1.6 LT (TA2)	55 kW	1.6 l	02/76→03/78	
1.6 LT (TA22)	58 kW	1.6 l	05/73→03/78	 ; -> 04/74 KH00056 ProKIT
1.6 ST (TA2, TA22)	63 kW	1.6 l	05/73→03/78	
<b>TOYOTA - CELICA Coupe (_T18_)</b>				<b>09/89→01/94</b>
1.6 (AT180)	77 kW	1.6 l	09/89→12/93	 (ABS) KH10204 ProKIT
2.0 (ST182_)	118 kW	2 l	09/89→10/93	
2.0 (ST182, ST183)	115 kW	2 l	10/89→01/94	
2.0 4WD (ST185)	150 kW	2 l	10/89→11/93	
2.0 4WD (ST185)	153 kW	2 l	10/89→01/94	
<b>TOYOTA - CELICA Coupe (_T20_)</b>				<b>11/93→11/99</b>
1.8 i 16V (AT200/ST)	85 kW	1.8 l	11/93→11/99	 (ABS) KH10204 ProKIT
2.0 i 16V (ST202_)	125 kW	2 l	04/96→11/99	
2.0 i 16V (ST202/GT)	129 kW	2 l	11/93→11/99	 KH20162 ProKIT
<b>TOYOTA - CELICA Coupe (_T23_)</b>				<b>08/99→09/05</b>
1.8	104 kW	1.8 l	09/99→09/05	 KH10002 ProKIT
1.8 16V	134 kW	1.8 l	08/99→09/05	


















































      					
<b>TOYOTA - CELICA Coupe (_T23_)</b>				<b>08/99→09/05</b>	
1.8 16V TS (ZZT231_)	141 kW	1.8 l	08/99→09/05		KH10002 ProKIT
1.8 16V VT-i (ZZT230_)	105 kW	1.8 l	08/99→07/05		KH30117 ProKIT
<b>TOYOTA - CELICA Liftback (_A4_)</b>				<b>02/79→07/81</b>	
2.0 XT (RA40)	65 kW	2 l	01/80→07/81	 ; -> 06/81; Axle: Rigid Axle	KH00054 ProKIT
2.0 XT (RA40)	66 kW	2 l	02/79→07/81		
<b>TOYOTA - COROLLA (_E12_)</b>				<b>01/01→12/07</b>	
1.4 D (NDE120_)	66 kW	1.4 l	07/04→02/07		KH10002 ProKIT
1.4 VVT-i (ZZE120_)	71 kW	1.4 l	11/01→02/07		KH30169 ProKIT
1.6 VVT-i (ZZE121_)	81 kW	1.6 l	01/02→12/06		
1.8 VVTi (ZZE122_)	100 kW	1.8 l	01/01→12/07		
1.8 VVTL-i TS (ZZE123_)	160 kW	1.8 l	10/05→12/06		
1.8 VVTL-i TS (ZZE123_)	165 kW	1.8 l	02/05→02/07		
1.8 VVTL-i TS (ZZE123)	140 kW	1.8 l	01/01→09/06		
1.8 VVTL-i TS (ZZE123)	141 kW	1.8 l	11/01→02/07		
2.0 D-4D (CDE120_)	66 kW	2 l	01/02→12/06		
2.0 D-4D (CDE120R_, CDE120L_)	81 kW	2 l	01/02→12/06		
2.0 D-4D (CDE120R_, CDE120L_)	85 kW	2 l	05/03→02/07		
1.5 RUNX VVT-i (NZE121_)	81 kW	1.5 l	01/01→08/06		KH10002 ProKIT
1.8 (ZZE122_)	93 kW	1.8 l	10/05→12/07		
1.8 4WD (ZZE124)	100 kW	1.8 l	01/01→02/07		
<b>TOYOTA - COROLLA (_E15_, _E18_)</b>				<b>10/06→12/18</b>	
1.3 (NRE180_)	73 kW	1.3 l	10/12→12/18		KH30017 ProKIT
1.4 D-4D (NDE180_)	66 kW	1.4 l	10/12→12/18		KH30035 ProKIT
1.33 Dual-VVTi (NRE150_)	73 kW	1.33 l	01/10→09/12		KH30017 ProKIT
1.33 Dual-VVTi (NRE150_)	74 kW	1.33 l	05/09→09/12		KH30028 ProKIT
1.4 (ZZE150_)	71 kW	1.4 l	03/07→09/12		KH30150 ProKIT
1.6 (ZRE151_)	91 kW	1.6 l	03/07→09/12	 ; Code: ADE157	KH30150 ProKIT
1.6 (ZRE151_)	97 kW	1.6 l	05/09→09/12		
1.8 (ZRE152_)	108 kW	1.8 l	02/09→09/12		
1.4 D-4D (NDE150_)	66 kW	1.4 l	03/07→09/12		KH30017 ProKIT
1.8 Hybrid (ZWE150_)	73 kW	1.8 l	09/10→09/12	 ; Code: ADE157	KH30150 ProKIT
1.5 (NZE151_)	81 kW	1.5 l	10/06→08/12	 ; Code: ADE157	KH30150 ProKIT
1.5 4WD (NZE154_)	77 kW	1.5 l	10/06→09/12		KH30013 ProKIT
1.5 4WD (NZE184_)	77 kW	1.5 l	10/12→12/18		
1.8 4WD (ZRE152)	94 kW	1.8 l	01/08→10/09		
2.4 4WD (AZE154H)	123 kW	2.4 l	11/06→04/12		
1.6 (ZRE181_, ZRE185_)	97 kW	1.6 l	10/12→12/18		KH30017 ProKIT
1.8 (ZRE152_, ZZE122)	100 kW	1.8 l	10/06→09/12		
1.8 (ZRE182)	103 kW	1.8 l	10/12→12/18		
1.6 D4-D (WWE185_)	82 kW	1.6 l	04/15→12/18		KH30018 ProKIT
2.0 D-4D (ADE186_)	91 kW	2 l	10/12→04/15		
1.8 (ZRE152_)	106 kW	1.8 l	02/09→09/12		KH30017 ProKIT
					KH30028 ProKIT
1.8 4WD (ZRE154_)	100 kW	1.8 l	10/06→10/09		KH30017 ProKIT
					KH30013 ProKIT
2.0 D-4D (ADE150_)	93 kW	2 l	10/06→09/12		KH30018 ProKIT
2.2 D (ADE157_, ADE151_)	130 kW	2.2 l	11/06→09/12	 ; Code: ADE157	KH30150 ProKIT
<b>TOYOTA - COROLLA Compact (_E11_)</b>				<b>04/97→01/02</b>	
1.4 (EE111_)	63 kW	1.4 l	05/97→09/99	 ; 	KH10402 ProKIT
1.6 (ZZE112_)	81 kW	1.6 l	10/99→10/01	 ;  ;  ; 	KH20174 ProKIT
1.4 (ZZE111_)	71 kW	1.4 l	10/99→01/02	 ; 	KH10402 ProKIT
1.9 D (WZE110_)	51 kW	1.9 l	02/00→01/02	 ; -> 10/01;  ;  ; 	KH20174 ProKIT
1.6 (AE111_)	81 kW	1.6 l	05/97→02/00	 ; 	KH10402 ProKIT
				 ; -> 11/99;  ;  ; 	KH20174 ProKIT
1.6 Aut. (AE111_)	79 kW	1.6 l	05/97→02/00	 ; 	KH10402 ProKIT
2.0 D (CE110_)	53 kW	2 l	04/97→02/00	 ; -> 09/99;  ;  ; 	KH20174 ProKIT
2.0 D-4D (CDE110_)	66 kW	2 l	09/00→01/02	 ; -> 10/01;  ;  ; 	KH20174 ProKIT
<b>TOYOTA - COROLLA Estate (_E7_)</b>				<b>05/83→08/87</b>	
1.8 D (TE72LG_)	44 kW	1.8 l	05/83→08/87		KH00054 ProKIT
<b>TOYOTA - COROLLA Estate (_E10_)</b>				<b>07/92→04/97</b>	
1.3 12V (EE100_)	53 kW	1.3 l	07/92→05/95	 ; 	KH20174 ProKIT
1.3 XLI 16V (EE101_)	65 kW	1.3 l	07/92→09/95		
1.6 Si (AE101_)	84 kW	1.6 l	07/92→04/97		
2.0 D (CE100_)	53 kW	2 l	07/92→04/97		




































												
<b>TOYOTA - COROLLA Estate (_E11_)</b>											<b>04/97→10/01</b>	
1.4 (EE111_)	63 kW	1.4 l	04/97→02/00									KH10402 ProKIT
1.6 (AE111_)	81 kW	1.6 l	04/97→02/00									KH20174 ProKIT
1.6 Aut. (AE111_)	79 kW	1.6 l	04/97→02/00									KH20174 ProKIT
1.4 16V (ZZE111_)	71 kW	1.4 l	02/00→10/01									KH10402 ProKIT
1.6 16V (ZZE112_)	81 kW	1.6 l	02/00→10/01									KH20174 ProKIT
1.9 D (WZE110_)	51 kW	1.9 l	02/00→10/01									KH20174 ProKIT
2.0 D (CE110_)	53 kW	2 l	04/97→02/00									KH20174 ProKIT
2.0 D-4D (CDE110_)	66 kW	2 l	09/00→10/01									KH20174 ProKIT
<b>TOYOTA - COROLLA Estate (_E12_)</b>											<b>03/01→12/08</b>	
1.4 D4-D (NDE120_)	66 kW	1.4 l	06/04→10/07									KH10002 ProKIT
1.4 VVT-i (ZZE120_)	71 kW	1.4 l	01/02→02/07									KH30169 ProKIT
1.6 VVT-i (ZZE121_)	81 kW	1.6 l	01/02→08/07									KH30169 ProKIT
1.8 (ZZE122)	100 kW	1.8 l	12/01→12/07									
2.0 D-4D (CDE120_)	66 kW	2 l	01/02→02/07									
2.0 D-4D (CDE120_)	85 kW	2 l	04/04→02/07									
1.5 (NZE121_)	81 kW	1.5 l	03/01→09/06									KH10002 ProKIT
1.8 (ZZE122_)	93 kW	1.8 l	10/05→12/07									
1.8 (ZZE123_)	140 kW	1.8 l	03/01→09/06									
1.8 4WD (ZZE121)	100 kW	1.8 l	12/01→02/07									
1.8 Flex (ZZE122)	100 kW	1.8 l	05/07→12/08									
<b>TOYOTA - COROLLA Hatchback (KE, TE)</b>											<b>09/76→01/80</b>	
1.6 (TE51_)	54 kW	1.6 l	09/76→01/80									KH00054 ProKIT
1.6 (TE51_)	62 kW	1.6 l	09/76→01/80									
<b>TOYOTA - COROLLA Liftback (_E10_)</b>											<b>07/92→04/97</b>	
1.3 12V (EE100_)	53 kW	1.3 l	07/92→05/95									KH20174 ProKIT
1.3 XLI (EE101_)	65 kW	1.3 l	07/92→04/97									KH20174 ProKIT
1.6 GLI (AE101_)	84 kW	1.6 l	07/92→04/97									KH20174 ProKIT
2.0 D (CE100_)	53 kW	2 l	07/92→04/97									
1.8 GT (AE102_)	86 kW	1.8 l	11/92→05/95									KH20174 ProKIT
<b>TOYOTA - COROLLA Liftback (_E11_)</b>											<b>05/97→01/02</b>	
1.4 (EE111_)	63 kW	1.4 l	05/97→09/99									KH10402 ProKIT
1.4 (ZZE111_)	71 kW	1.4 l	10/99→01/02									
1.6 (AE111_)	81 kW	1.6 l	05/97→02/00									
1.6 (ZZE112_)	81 kW	1.6 l	02/00→01/02									
1.6 Aut. (AE111_)	79 kW	1.6 l	05/97→02/00									
1.9 D (WZE110_)	51 kW	1.9 l	02/00→01/02									KH10402 ProKIT
<b>TOYOTA - COROLLA Saloon (_E12_)</b>											<b>08/00→03/08</b>	
1.3 (NZE120_ ZZE120_)	65 kW	1.3 l	08/00→05/04									KH10002 ProKIT
1.5 (NZE121, NZE120, ZZE123, ZZA120)	78 kW	1.5 l	10/01→10/07									
1.5 (NZE121)	80 kW	1.5 l	11/01→07/07									
1.5 (NZE141)	81 kW	1.5 l	06/07→07/07									
1.5 G 4WD (ZZE128)	80 kW	1.5 l	11/01→05/04									
1.8 (ZZE130)	97 kW	1.8 l	09/02→12/05									
1.8 (ZZE131)	127 kW	1.8 l	09/04→12/06									
1.8 4x4 (ZZE124)	92 kW	1.8 l	08/00→10/06									
1.4 D-4D (NDE120_)	66 kW	1.4 l	06/04→10/06									KH10002 ProKIT
1.4 VVT-i (ZZE120_)	71 kW	1.4 l	10/01→10/06									KH30169 ProKIT
1.6 VVT-i (ZZE121_)	81 kW	1.6 l	10/01→03/08									KH30169 ProKIT
1.8 (ZZE122)	92 kW	1.8 l	05/02→05/04									
1.8 (ZZE122)	96 kW	1.8 l	03/01→07/05									
1.8 (ZZE122)	100 kW	1.8 l	11/01→10/06									
2.0 D-4D (CDE120_)	66 kW	2 l	01/02→12/06									
2.0 D-4D (CDE120_)	85 kW	2 l	06/04→07/07									
<b>TOYOTA - COROLLA Saloon (_E15_, _E18_, ZRE1_)</b>											<b>10/06→08/19</b>	
1.3 (NRE180_)	73 kW	1.3 l	06/13→12/18									KH30017 ProKIT
1.4 D-4D (NDE150)	66 kW	1.4 l	10/06→07/14									
1.4 D-4D (NDE180_, NDE170_)	66 kW	1.4 l	06/13→12/18									
1.6 (ZRE171_, ZRE181_)	90 kW	1.6 l	06/13→12/18									
1.6 (ZRE171)	89 kW	1.6 l	10/13→12/18									
1.6 (ZRE181_)	97 kW	1.6 l	06/13→12/18									
1.6 VVTi (ZRE141_, ZRE151_)	90 kW	1.6 l	07/10→05/14									
1.6 VVTi (ZRE151)	100 kW	1.6 l	03/07→12/10									
1.8 (ZRE142, ZRE152)	100 kW	1.8 l	10/06→07/14									
1.8 VVTi (ZRE142)	97 kW	1.8 l	01/08→07/14									
1.8 VVTi (ZRE172, ZRE182)	103 kW	1.8 l	06/13→08/19									
2.0 VVTi (ZRE153)	102 kW	2 l	08/10→11/13									

									
<b>TOYOTA - COROLLA Saloon (_E15_, _E18_, ZRE1_) 10/06→08/19</b>									
1.33 (NRE150)	74 kW	1.33 l	12/08→07/14						KH30017 ProKIT
1.4 VVT-i (ZZE150_)	71 kW	1.4 l	11/06→11/13						KH30028 ProKIT
1.6 (ZRE151)	97 kW	1.6 l	11/06→11/13						
1.6 Dual VVTi (ZRE141, ZRE151)	91 kW	1.6 l	01/07→07/14						
2.0 D-4D (ADE150)	93 kW	2 l	11/06→07/14						KH30018 ProKIT
<b>TOYOTA - COROLLA SECCA Compact (_E10_, AE102) 07/92→04/97</b>									
1.3 12V (EE100_)	53 kW	1.3 l	07/92→05/95						KH20174 ProKIT
1.3 XLI 16V (EE101)	65 kW	1.3 l	07/92→09/95						
1.6 Si (AE101_)	84 kW	1.6 l	07/92→04/97						
2.0 D (CE100_)	53 kW	2 l	07/92→04/97						
<b>TOYOTA - COROLLA Sedan (_E7_) 10/82→09/83</b>									
1.6 (TE71)	55 kW	1.6 l	10/82→09/83		-> 05/83; Body Type: Hatchback;   				KH00054 ProKIT
1.8 D (CE70)	43 kW	1.8 l	01/83→09/83						KH00054 ProKIT
<b>TOYOTA - COROLLA Sedan (_E10_) 07/92→04/97</b>									
1.3 12V (EE100_)	53 kW	1.3 l	07/92→04/97		-> 05/95; 				KH20174 ProKIT
1.3 XLI 16V (EE101)	65 kW	1.3 l	07/92→09/95						KH20174 ProKIT
1.6 Si (AE101_)	84 kW	1.6 l	09/95→04/97						
2.0 D (CE100_)	53 kW	2 l	07/92→04/97						
<b>TOYOTA - COROLLA Sedan (_E11_) 04/97→12/01</b>									
1.4 (EE111_)	63 kW	1.4 l	05/97→09/99						KH10402 ProKIT
1.4 16V (ZZE111_)	71 kW	1.4 l	02/00→11/01						KH20174 ProKIT
1.9 D (WZE110_)	51 kW	1.9 l	02/00→11/01		-> 10/01; 				KH20174 ProKIT
1.6 16V (ZZE112_)	81 kW	1.6 l	10/99→12/01						KH10402 ProKIT
1.6 16V (ZZE112_)	81 kW	1.6 l	10/99→12/01						KH20174 ProKIT
1.6 Aut. (AE111_)	79 kW	1.6 l	04/97→02/00						KH10402 ProKIT
1.6 Aut. (AE111_)	79 kW	1.6 l	04/97→02/00						KH20174 ProKIT
2.0 D (CE110_)	53 kW	2 l	04/97→02/00		-> 09/99; 				KH20174 ProKIT
2.0 D-4D (CDE110_)	66 kW	2 l	09/00→11/01		-> 10/01; 				KH20174 ProKIT
2.0 D-4D (CDE110_)	66 kW	2 l	09/00→11/01		-> 10/01; 				KH20174 ProKIT
<b>TOYOTA - COROLLA Verso (_E12_) 07/01→05/07</b>									
1.5 (NZE120_)	80 kW	1.5 l	07/01→02/04		-> 01/04				KH10002 ProKIT
1.8 VVTi 4WD (ZZE126_, ZZE124)	99 kW	1.8 l	10/01→05/07						
1.6 VVT-i (ZZE121_)	81 kW	1.6 l	08/01→05/04		-> 01/04				KH10002 ProKIT
1.8 VVT-i (ZZE122_)	99 kW	1.8 l	12/01→05/04						KH30173 ProKIT
2.0 D-4D (CDE120_)	66 kW	2 l	01/02→05/04		02/04 ->; 				KH30169 ProKIT
<b>TOYOTA - COROLLA Verso (ZER_, ZZE12_, R1_) 04/04→03/09</b>									
1.6 (ZNR10_)	81 kW	1.6 l	04/04→03/09						KH10021 ProKIT
1.8 (ZNR11_)	95 kW	1.8 l	04/04→03/09		-> 02/09; 				KH30173 ProKIT
2.0 D-4D (CUR10_)	85 kW	2 l	04/04→03/09						
2.2 D-4D (AUR10_)	100 kW	2.2 l	10/05→03/09						
2.2 D-4D (AUR10_)	130 kW	2.2 l	10/05→03/09						
<b>TOYOTA - CORONA Estate / CORONA Sedan (RT118, RT1_) 09/75→05/79</b>									
2.0 (RT104)	65 kW	2 l	01/76→05/79		-> 12/78				KH00054 ProKIT
2.0 (RT118)	65 kW	2 l	09/75→05/79						
<b>TOYOTA - CRESSIDA Saloon / CRESSIDA Station Wagon (_X3_, MX62, _X6_) 07/77→06/85</b>									
2.0 (RX30)	66 kW	2 l	07/77→07/81						KH00054 ProKIT
2.0 (RX35)	66 kW	2 l	12/77→03/81						
2.0 GLI (GX61_)	80 kW	2 l	08/82→06/85						














































									
<b>TOYOTA - ECHO (_P1_)</b>									<b>04/99→11/05</b>
1.0 (SCP10_)	48 kW	1 l	03/03→09/05						<b>KH10014</b> ProKIT
1.0 (SCP10_)	50 kW	1 l	04/99→09/05						<b>KH30097</b> ProKIT
1.3 (NCP10_, SCP12_)	63 kW	1.3 l	08/99→11/05						
1.3 (SCP12_, SCP13_)	64 kW	1.3 l	04/02→09/05						
1.4 D-4D (NLP10_)	55 kW	1.4 l	10/01→09/05						
1.5 (NCP13_)	77 kW	1.5 l	01/03→11/05						
1.5 (NCP13_)	78 kW	1.5 l	04/01→09/05						
1.5 (NCP13_)	110 kW	1.5 l	03/00→07/05						
<b>TOYOTA - HARRIER (_U6_)</b>									<b>10/13→</b>
2.0 4WD (ZSU65W)	111 kW	2 l	10/13→						<b>KH30013</b> ProKIT
2.5 Hybrid E-Four (AVU65W)	112 kW	2.5 l	01/14→						
<b>TOYOTA - HIACE II Bus / HIACE III Bus / HIACE III Van (_H11, _H2_, _H3_, _H4_, _H5_, _H6_, _H7_, _H8_, _H9_)</b>									<b>02/77→08/89</b>
1.6 (RH20, RH30)	49 kW	1.6 l	02/77→11/82						<b>KH00042</b> ProKIT
1.8 (YH50, YH60)	58 kW	1.8 l	12/82→07/89						
2.0 (YH51, YH61)	65 kW	2 l	12/82→08/89						
2.0 (YH51, YH61)	65 kW	2 l	01/85→08/89						
2.4 D (LH51, LH61, LH66)	55 kW	2.4 l	04/84→08/89						
<b>TOYOTA - HIACE IV Bus (_H1_, _H2_)</b>									<b>08/95→12/06</b>
2.4 (RCH12, RCH22)	85 kW	2.4 l	08/95→04/98						<b>KH00042</b> ProKIT
2.4 D (LXH12, LXH22)	58 kW	2.4 l	08/95→08/01						<b>KH10135</b> ProKIT
2.4 D (LXH12)	55 kW	2.4 l	08/95→08/01						
2.4 TD (LXH12, LXH22)	66 kW	2.4 l	08/95→08/01						
2.7 (RCH13, RCH23)	105 kW	2.7 l	04/98→11/01						
2.4 4WD (RCH18)	85 kW	2.4 l	08/95→04/98						<b>KH10135</b> ProKIT
2.4 TD 4WD (LXH18, LXH28)	66 kW	2.4 l	08/95→08/01						
2.5 D-4D (KLH12, KLH22)	75 kW	2.5 l	08/01→08/06						
2.5 D-4D (KLH12)	65 kW	2.5 l	08/01→08/06						
2.7 (RCH13, RCH23)	106 kW	2.7 l	07/98→12/06			-> 05/06			<b>KH10135</b> ProKIT
2.7 4WD (RCH19)	105 kW	2.7 l	04/98→08/06						
<b>TOYOTA - HIACE IV Bus / HIACE IV Van (_H1_)</b>									<b>08/89→12/04</b>
2.0 (RZH102, RZH112)	74 kW	2 l	08/89→04/98						<b>KH00042</b> ProKIT
2.0 (RZH102, RZH112)	74 kW	2 l	02/90→08/04						<b>KH00030</b> ProKIT
2.4 (RZH10)	88 kW	2.4 l	08/89→08/95						
2.4 (RZH103, RZH183)	88 kW	2.4 l	08/89→08/03						
2.4 D (LH102)	55 kW	2.4 l	08/89→08/95						
2.4 D (LH112)	55 kW	2.4 l	08/89→08/04						
2.4 D (LH5_, LH6_, LH7_, LH10_, LH11_)	57 kW	2.4 l	08/89→12/04						
2.4 D 4WD (LXH22_, LXH12_, LH114_, LH112_, LH104_...)	55 kW	2.4 l	08/89→07/99						<b>KH00030</b> ProKIT
<b>TOYOTA - HIACE SBV IV Van (_H1_, _H2_)</b>									<b>08/95→08/06</b>
2.4 (RCH12, RCH22)	85 kW	2.4 l	08/95→11/03						<b>KH00042</b> ProKIT
2.4 D (LXH12, LXH22)	58 kW	2.4 l	08/95→08/01						<b>KH10135</b> ProKIT
2.4 TD (LXH12, LXH22)	66 kW	2.4 l	08/95→08/01						
2.4 4WD (RCH18, RCH28)	85 kW	2.4 l	08/95→04/98						<b>KH10135</b> ProKIT
2.4 TD 4WD (LXH18, LXH28)	66 kW	2.4 l	08/95→08/01						
2.7 4WD (RCH19, RCH29)	106 kW	2.7 l	07/98→06/05						
2.5 D-4D (KLH12, KLH22)	65 kW	2.5 l	08/01→08/06			Code: KLH12, KLH22			<b>KH00042</b> ProKIT
2.5 D-4D (KLH12, KLH22)	75 kW	2.5 l	08/01→08/06						<b>KH10135</b> ProKIT
2.5 D-4D 4WD (KLH18, KLH28)	75 kW	2.5 l	08/01→08/06						
2.7 (RCH13, RCH23)	105 kW	2.7 l	04/98→06/05			-> 06/04			<b>KH00042</b> ProKIT
									<b>KH10135</b> ProKIT
<b>TOYOTA - HILUX V Pickup (_N_, KZN1_, VZN1_)</b>									<b>09/88→06/98</b>
1.8 (YN5_, YN8_, YN85)	61 kW	1.8 l	09/88→06/98			-> 01/94			<b>KH00042</b> ProKIT
						-> 05/94			<b>KH00030</b> ProKIT
2.4 D 4WD (LN1_)	61 kW	2.4 l	09/88→08/97			08/97 ->			<b>KH00030</b> ProKIT
2.4 D 4WD (LN110_)	58 kW	2.4 l	01/94→12/97			09/97 ->			<b>KH00042</b> ProKIT
						08/97 ->			<b>KH00030</b> ProKIT
<b>TOYOTA - HILUX VI Pickup (_N1_)</b>									<b>08/97→07/05</b>
2.4 D (LN150, LN145)	55 kW	2.4 l	08/97→04/05			-> 08/01			<b>KH00042</b> ProKIT
						-> 08/01			<b>KH00030</b> ProKIT
2.5 D-4D (KDN145, KDN150)	65 kW	2.5 l	11/01→07/05			08/04 ->; Code: KUN15; 			<b>KH10379</b> ProKIT
						-> 01/05; 			<b>KH20063</b> ProKIT
						Code: KDN145, KDN150			<b>KH00042</b> ProKIT





























































														
<b>TOYOTA - HILUX VI Pickup (_N1_)</b>												<b>08/97→07/05</b>		
2.5 D-4D 4WD (KDN165, KDN170, KDN190)	75 kW	2.5 l	11/01→07/05		08/04 ->	Code: KUN15;	TH					KH10379 ProKIT		
					-> 01/05;	ABS					KH20063 ProKIT			
													KH00116 ProKIT	
<b>TOYOTA - HILUX VII Pickup (_N1_, _N2_, _N3_)</b>												<b>03/05→09/15</b>		
2.0 (TGN10, TGN15, TGN16)	100 kW	2 l	06/05→05/15										KH10379 ProKIT	
					-> 08/08									KH00071 ProKIT
2.5 D-4D (KUN15_, KUN10)	75 kW	2.5 l	03/05→05/15		03/09;	Code: KUN15;	TH					KH10379 ProKIT		
					-> 08/08									KH00071 ProKIT
2.5 D-4D 4WD (KUN25_)	88 kW	2.5 l	06/06→05/15										KH20089 ProKIT	
2.5 D-4D 4WD (KUN25)	106 kW	2.5 l	12/07→05/15											
2.5 D 4WD (KUN25)	75 kW	2.5 l	03/05→05/15		TH;	Code: KUN15					KH10379 ProKIT			
													KH20089 ProKIT	
2.7 (TGN16)	118 kW	2.7 l	08/05→05/15		-> 08/08									KH00071 ProKIT
3.0 D (KUN16)	126 kW	3 l	08/06→05/15											
3.0 D-4D 4WD (KUN26)	126 kW	3 l	08/05→09/15		Code: KUN25									KH20089 ProKIT
<b>TOYOTA - INNOVA / KIJANG INNOVA I (_N4_)</b>												<b>04/04→</b>		
2.7 (TGN41_)	118 kW	2.7 l	04/04→		-> 08/08									KH00071 ProKIT
<b>TOYOTA - IQ (_J1_)</b>												<b>01/09→12/15</b>		
1.0 (KGJ10_)	50 kW	1 l	01/09→12/15										KH10019 ProKIT	
1.33 (NGJ10_)	72 kW	1.33 l	01/09→12/15		ABS									KH30148 ProKIT
1.4 D-4D (NUJ10_)	66 kW	1.4 l	01/09→12/15											
<b>TOYOTA - LAND CRUISER (_J1_)</b>												<b>01/98→08/07</b>		
4.2 TD (HDJ100_, HDJ100)	150 kW	4.2 l	01/98→08/07		01/03 ->	ABS					KH20063 ProKIT			
													KH10395 ProKIT	
4.7 (UZJ100_)	173 kW	4.7 l	01/98→08/07		-> 04/07									KH10389 ProKIT
4.7 (UZJ100)	175 kW	4.7 l	02/02→08/07										KH10395 ProKIT	
<b>TOYOTA - LAND CRUISER (_J4_, _J5_, _J6_)</b>												<b>03/69→12/92</b>		
3.0 D 4WD (BJ42_, FJ4_, FJ5_, BJ40RV)	59 kW	3 l	03/69→10/84										KH00134 ProKIT	
3.4 D (BJ42_V, BJ45_V, BJ46_, BJ42RV)	66 kW	3.4 l	08/80→10/84		Axle: Independent wheel suspension									
3.4 Diesel (BJ60, HJ60, BJ61)	66 kW	3.4 l	10/81→08/87											
3.6 D (HJ45_V)	66 kW	3.6 l	04/79→07/80											
3.9 (FJ40_, FJ43_, FJ45_, FJ55_V)	96 kW	3.9 l	03/69→01/75											
4.0 (FJ62_G, BJ62_)	115 kW	4 l	08/87→12/92											
4.0 (FJ62_V)	101 kW	4 l	11/84→08/87											
4.0 D (HJ47_V)	76 kW	4 l	08/80→10/84											
4.0 D (HJ60_)	77 kW	4 l	10/81→01/88											
4.0 Diesel (HJ60)	74 kW	4 l	01/82→12/85											
4.0 Diesel (HJ60)	76 kW	4 l	10/82→12/89											
4.0 Turbo-D (HJ61_V, HJ61)	100 kW	4 l	10/85→12/89											
4.2 (FJ40, FJ43, FJ45, FJ55)	89 kW	4.2 l	01/75→04/86											
4.2 (FJ60_V, FJ55_)	88 kW	4.2 l	10/81→01/88											
<b>TOYOTA - LAND CRUISER / LAND CRUISER FRP Top (_J7_, _J8_)</b>												<b>11/84→12/96</b>		
2.4 (RJ70_, RJ73_, RJ70RV)	81 kW	2.4 l	11/84→05/93										KH00134 ProKIT	
2.4 (RJ70_, RJ73_)	77 kW	2.4 l	11/84→05/93											
2.4 (RJ70_V, RJ73_V)	84 kW	2.4 l	12/88→12/96											
2.4 D (LJ70_)	53 kW	2.4 l	11/84→10/85											
2.4 TD (LJ70_, LJ73_, LJ70RV)	63 kW	2.4 l	10/85→05/90											
2.4 TD (LJ70_)	66 kW	2.4 l	07/90→05/96											
2.4 TD (LJ70)	66 kW	2.4 l	01/90→05/93											
3.0 TD (KZJ70_, KZJ73_, KZJ77_, KZJ78)	92 kW	3 l	05/93→05/96											
3.0 TD (KZJ70_)	92 kW	3 l	05/93→05/96											
3.4 D (BJ70_V, BJ73_, BJ75)	70 kW	3.4 l	11/84→12/96											
3.4 TD (BJ71_V, BJ74)	91 kW	3.4 l	10/85→08/86											
4.0 (FJ80_)	115 kW	4 l	01/90→10/92											
<b>TOYOTA - LAND CRUISER Pickup (_J4_)</b>												<b>01/75→04/86</b>		
3.4 D (BJ45_P)	66 kW	3.4 l	08/80→10/84										KH00134 ProKIT	
3.6 D (HJ45_P)	66 kW	3.6 l	01/75→07/80		Axle: Independent wheel suspension									
4.0 D (HJ47_P)	76 kW	4 l	08/80→10/84											
4.2 (FJ45_P)	89 kW	4.2 l	01/75→04/86											



































												
<b>TOYOTA - LAND CRUISER PRADO (_J9_)</b>											<b>03/96→12/02</b>	
3.0 D-4D 4WD (KDJ90_, KDJ95_)	120 kW	3 l	08/00→08/02								KH10395 ProKIT	
3.0 TD (KZJ90_, KZJ95_)	92 kW	3 l	04/96→12/02									
3.4 i 24V (VZJ90_, VZJ95_)	131 kW	3.4 l	03/96→08/02									
<b>TOYOTA - LAND CRUISER PRADO (_J12_)</b>											<b>09/02→12/10</b>	
3.0 D (LJ120, LJ125)	70 kW	3 l	09/02→02/10								KH20063 ProKIT	
3.0 D-4D (KDJ120, KDJ125, KDJ121)	127 kW	3 l	09/02→12/10		-> 08/04;							KH20089 ProKIT
					ABS						KH20063 ProKIT	
3.0 D-4D (KDJ120, KDJ125)	120 kW	3 l	09/02→08/09		-> 08/04;							KH20089 ProKIT
3.0 D-4D (KDJ120, KDJ125)	122 kW	3 l	07/04→08/09		ABS						KH20063 ProKIT	
					ABS						KH20125 ProKIT	
					ABS						KH20131 ProKIT	
4.0 (GRJ120, GRJ125, GRJ121)	183 kW	4 l	12/02→12/10		-> 08/04;							KH20089 ProKIT
											KH10395 ProKIT	
					ABS						KH20063 ProKIT	
					ABS						KH20125 ProKIT	
					ABS						KH20131 ProKIT	
4.0 (GRJ120)	179 kW	4 l	09/02→08/10		01/03 ->							KH20089 ProKIT
<b>TOYOTA - LAND CRUISER PRADO (_J15_)</b>											<b>08/09→</b>	
3.0 D-4D (KDJ150_, KDJ150, KDJ155)	127 kW	3 l	08/09→								KH20125 ProKIT	
											KH20131 ProKIT	
3.0 D-4D (KDJ155_, KDJ150_)	140 kW	3 l	08/09→									
4.0 V6 VVTi (GRJ150_)	183 kW	4 l	11/12→									
<b>TOYOTA - LAND CRUISER Softtop (_J4_)</b>											<b>03/69→01/75</b>	
3.9 (FJ45_P, FJ45)	96 kW	3.9 l	03/69→01/75								KH00134 ProKIT	
					Axle: Independent wheel suspension							
<b>TOYOTA - LITEACE Van (_M2_)</b>											<b>10/79→10/86</b>	
1.3 (KM20)	42 kW	1.3 l	10/79→10/86		-> 01/85						KH00054 ProKIT	
<b>TOYOTA - MARK X ZIO I (_A1_)</b>											<b>09/07→</b>	
2.4 4WD (ANA15)	120 kW	2.4 l	09/07→								KH30013 ProKIT	
<b>TOYOTA - MR2 III (ZZW3_)</b>											<b>10/99→06/07</b>	
1.8 16V VT-i (ZZW30)	103 kW	1.8 l	10/99→06/07								KH10002 ProKIT	
<b>TOYOTA - OPA (ZCT1_, ACT1_)</b>											<b>04/00→04/05</b>	
1.8 (ZCT10)	97 kW	1.8 l	04/00→08/03								KH10002 ProKIT	
1.8 (ZTC10)	100 kW	1.8 l	04/00→08/03									
1.8 4WD (ZTC15)	92 kW	1.8 l	04/00→08/03									
2.0 (ACT10)	112 kW	2 l	08/00→04/05									
<b>TOYOTA - PASEO Convertible / PASEO Coupe (_L5_, EL44_)</b>											<b>06/88→06/99</b>	
1.5 (EL44)	74 kW	1.5 l	06/90→08/95								KH00027 ProKIT	
1.5 (EL44)	85 kW	1.5 l	06/88→07/95									
1.5 (EL54_)	66 kW	1.5 l	08/95→06/99									
1.5 (EL54_)	66 kW	1.5 l	10/96→01/98									
1.5 (EL54_)	81 kW	1.5 l	08/95→06/99									
1.5 (EL54_)	81 kW	1.5 l	10/96→01/98									
1.5 (EL54_)	85 kW	1.5 l	08/95→06/99									
<b>TOYOTA - PICNIC (_XM1_)</b>											<b>05/96→12/01</b>	
2.0 (SXM10_)	90 kW	2 l	06/00→12/01		06/01 ->						KH10182 ProKIT	
					-> 09/01						KH10361 ProKIT	
					05/01 ->						KH30194 ProKIT	
2.0 (SXM10_)	100 kW	2 l	05/96→04/01		08/96 ->		05/00				KH10005 ProKIT	
2.0 16V (SXM10_)	94 kW	2 l	08/96→09/00		10/96 ->						KH10361 ProKIT	
					-> 05/00						KH10005 ProKIT	
2.2 D (CMX10_)	66 kW	2.2 l	08/97→12/01		09/97 ->		09/01				KH10361 ProKIT	
					-> 05/00						KH10005 ProKIT	
<b>TOYOTA - PREMIO (_T24_, _T26_)</b>											<b>12/01→</b>	
1.5 (NZT240_)	80 kW	1.5 l	12/01→05/07								KH10002 ProKIT	
1.5 (NZT260)	80 kW	1.5 l	12/12→									
1.5 (NZT260)	81 kW	1.5 l	07/07→11/12									
1.8 (ZRT260)	100 kW	1.8 l	07/07→									
1.8 (ZRT260)	105 kW	1.8 l	12/12→									
1.8 (ZRT260)	106 kW	1.8 l	07/07→02/13									

<b>TOYOTA - PREMIO (_T24_, _T26_) 12/01→</b>									
1.8 (ZZT240)	97 kW	1.8 l	12/01→06/07						KH10002 ProKIT
1.8 4WD (ZRT265)	92 kW	1.8 l	01/08→						
1.8 4WD (ZRT265)	96 kW	1.8 l	03/13→						
1.8 4WD (ZRT265)	98 kW	1.8 l	07/07→02/13						
1.8 4WD (ZZT245_)	97 kW	1.8 l	12/01→04/07						
1.8 4WD (ZZT245)	92 kW	1.8 l	12/01→06/07						
2.0 (AZT240_)	114 kW	2 l	12/01→06/07						
2.0 (AZT240)	112 kW	2 l	12/01→06/07						
2.0 (ZRT261)	112 kW	2 l	12/12→						
2.0 (ZRT261)	116 kW	2 l	07/07→02/13						
2.0 4WD (ZRT261)	116 kW	2 l	07/07→						
<b>TOYOTA - PRIUS V (_W4_) 05/11→</b>									
1.8 Hybrid (ZVW40W, ZVW41W)	73 kW	1.8 l	05/11→						KH30017 ProKIT
<b>TOYOTA - PRIUS Liftback (_W2_) 09/03→12/09</b>									
1.5 Hybrid (NHW20_)	57 kW	1.5 l	09/03→12/09						KH30124 ProKIT
									KH30117 ProKIT
<b>TOYOTA - PRIUS Saloon (_W1_) 09/00→12/03</b>									
1.5 Hybrid (NHW1_)	85 kW	1.5 l	09/00→12/03						KH10002 ProKIT
<b>TOYOTA - PROACE Bus (MDZ_) 02/16→</b>									
1.6 D4d (MDZ2)	85 kW	1.6 l	02/16→						KH10119 ProKIT
1.6 D4d (MDZ9)	70 kW	1.6 l	02/16→						
2.0 D4d (MDZ4)	110 kW	2 l	02/16→						
2.0 D4d (MDZ6, MDZ5)	130 kW	2 l	02/16→						
<b>TOYOTA - PROACE Van (MDX_) 06/13→03/16</b>									
1.6 D (MDX9)	66 kW	1.6 l	06/13→03/16						KH10119 ProKIT
2.0 D (MDX3)	94 kW	2 l	06/13→03/16						KH30015 ProKIT
2.0 D (MDX6)	120 kW	2 l	06/13→03/16						KH30016 ProKIT
<b>TOYOTA - PROACE Van (MDZ_) 02/16→</b>									
1.6 D4d (MDZ2)	85 kW	1.6 l	02/16→						KH10119 ProKIT
1.6 D4d (MDZ9)	70 kW	1.6 l	02/16→						
2.0 D4d (MDZ3)	90 kW	2 l	02/16→						
2.0 D4d (MDZ4)	110 kW	2 l	02/16→						
2.0 D4d (MDZ6, MDZ5)	130 kW	2 l	02/16→						
<b>TOYOTA - RAV 4 I / RAV 4 I Cabrio (_A1_) 06/94→06/00</b>									
2.0 4WD (SXA10)	95 kW	2 l	06/94→06/00						KH10204 ProKIT
2.0 4WD (SXA11)	94 kW	2 l	12/97→06/00						KH20172 ProKIT
<b>TOYOTA - RAV 4 II (_A2_) 05/00→11/05</b>									
1.8 (ZCA25_, ZCA26_)	92 kW	1.8 l	08/00→11/05						KH10182 ProKIT
									KH30194 ProKIT
2.0 4WD (ACA21, ACA20)	110 kW	2 l	05/00→11/05						KH10182 ProKIT
2.0 D 4WD (CLA20_, CLA21_)	85 kW	2 l	05/01→11/05						KH30135 ProKIT
<b>TOYOTA - RAV 4 III / RAV 4 IV (_A3_, _A4_) 11/05→11/18</b>									
2.0 (ZSA35_)	116 kW	2 l	12/08→06/13						KH30017 ProKIT
2.0 (ZSA35)	109 kW	2 l	03/09→06/13						KH30018 ProKIT
2.2 D (ALA35_)	110 kW	2.2 l	12/08→06/13						
2.0 (ZSA42)	105 kW	2 l	12/12→						KH30017 ProKIT
2.0 (ZSA42)	107 kW	2 l	12/12→						KH30018 ProKIT
									CVT Automatic Transmission (stepless)
									not for CVT automatic transmission (stepless)
2.0 4WD (ACA30_)	112 kW	2 l	02/06→06/13						KH30017 ProKIT
2.4 4WD (ACA31, ACA33)	125 kW	2.4 l	11/05→06/13						KH30018 ProKIT
									KH30013 ProKIT
2.0 4WD (ZSA30_)	116 kW	2 l	12/08→06/13						KH30017 ProKIT
2.0 4WD (ZSA30)	109 kW	2 l	03/09→06/13						KH30018 ProKIT
2.2 D 4WD (ALA30_)	100 kW	2.2 l	02/06→12/12						
2.2 D 4WD (ALA30_)	110 kW	2.2 l	12/08→06/13						KH30013 ProKIT
2.2 D 4WD (ALA30_)	130 kW	2.2 l	02/06→06/13						
2.2 D 4WD (ALA30)	98 kW	2.2 l	11/05→12/10						
3.5 4WD (GSA33)	198 kW	3.5 l	11/05→12/12						
3.5 4WD (GSA33)	201 kW	3.5 l	11/05→12/12						
2.0 4WD (ZSA44_)	111 kW	2 l	12/12→						CVT Automatic Transmission (stepless)
2.0 4WD (ZSA44_)	112 kW	2 l	04/15→						not for CVT automatic transmission (stepless)
2.0 4WD (ZSA44)	107 kW	2 l	12/12→						KH30013 ProKIT



											
<b>TOYOTA - RAV 4 III / RAV 4 IV (_A3_, _A4_)</b>											<b>11/05→11/18</b>
2.0 4WD (ZSA44)	105 kW	2 l	12/12→11/18								<b>KH30013</b> ProKIT
2.5 4WD (ASA33)	132 kW	2.5 l	11/08→06/13								
3.5 4WD (GSA33W)	206 kW	3.5 l	11/05→12/12								
2.0 D (ALA40_)	91 kW	2 l	12/12→11/18								<b>KH30018</b> ProKIT
2.0 D (WWA42_)	105 kW	2 l	10/15→11/18								
2.5 (ASA42)	132 kW	2.5 l	12/12→11/18								
2.5 Hybrid (AVA42_)	145 kW	2.5 l	11/15→11/18								
2.0 D 4WD (ALA41_)	91 kW	2 l	01/13→11/18								<b>KH30018</b> ProKIT
2.2 D 4WD (ALA49)	110 kW	2.2 l	12/12→								<b>KH30013</b> ProKIT
2.2 D 4WD (ALA49)	130 kW	2.2 l	12/12→								
2.5 4WD (ASA44)	131 kW	2.5 l	12/12→12/18								
2.5 4WD (ASA44)	132 kW	2.5 l	12/12→								
2.5 Hybrid 4WD (AVA44)	145 kW	2.5 l	11/15→11/18								
2.4 (ACA36, ACA38)	125 kW	2.4 l	11/05→12/13								<b>KH30017</b> ProKIT
											<b>KH30018</b> ProKIT
<b>TOYOTA - RUKUS (_E15_)</b>											<b>09/07→</b>
1.8 4WD (ZRE154)	100 kW	1.8 l	09/07→								<b>KH30013</b> ProKIT
<b>TOYOTA - SIENNA (_L3_)</b>											<b>01/10→</b>
3.5 4WD (GSL35_)	198 kW	3.5 l	01/10→								<b>KH10025</b> ProKIT
<b>TOYOTA - STARLET (_P8_)</b>											<b>12/89→03/96</b>
1.0 (EP80_)	40 kW	1 l	12/89→12/92								<b>KH00027</b> ProKIT
1.3 12V (EP81_)	55 kW	1.3 l	12/89→12/92								
1.3 12V Cat (EP81)	55 kW	1.3 l	12/89→03/96								
<b>TOYOTA - STARLET (_P9_)</b>											<b>01/96→07/99</b>
1.3 (EP91_)	55 kW	1.3 l	01/96→07/99							<b>KH10179</b> ProKIT	
											<b>KH00027</b> ProKIT
<b>TOYOTA - STARLET / STARLET Estate (KP6_)</b>											<b>02/78→09/84</b>
1.0 (KP60)	33 kW	1 l	02/78→09/84								<b>KH00056</b> ProKIT
1.2 (KP61_)	41 kW	1.2 l	02/78→09/82								
1.2 S (KP62)	39 kW	1.2 l	10/78→08/82								
1.3 S (KP61)	48 kW	1.3 l	08/82→09/84								
<b>TOYOTA - SUPRA (_A7_)</b>											<b>01/86→05/93</b>
3.0 24V (MA70_, MA70)	150 kW	3 l	01/86→08/88								<b>KH10207</b> ProKIT
3.0 Turbo (MA70_, MA70)	173 kW	3 l	09/87→04/93							<b>KH10381</b> ProKIT	
											<b>KH10207</b> ProKIT
3.0 Turbo (MA70_, MA70)	175 kW	3 l	08/88→05/93							<b>KH10381</b> ProKIT	
										<b>KH10207</b> ProKIT	
<b>TOYOTA - SUPRA (_A8_)</b>											<b>05/93→07/02</b>
3.0 i Bi-Turbo (JZA80_)	243 kW	3 l	05/93→07/02								<b>KH10381</b> ProKIT
										<b>KH10207</b> ProKIT	
<b>TOYOTA - T-18 Hatchback (_E7_, T18)</b>											<b>09/79→09/83</b>
1.6 (TE71)	54 kW	1.6 l	09/79→05/83								<b>KH00054</b> ProKIT
1.6 (TE71)	55 kW	1.6 l	09/79→05/83								
1.6 (TE71)	63 kW	1.6 l	09/79→05/83								
1.6 GT (TE71)	81 kW	1.6 l	05/80→09/83								<b>KH00054</b> ProKIT
<b>TOYOTA - TARAGO / ESTIMA I (_R1_, _R2_)</b>											<b>01/90→08/00</b>
2.4 4WD (TCR21_, TCR20_)	97 kW	2.4 l	01/90→08/00								<b>KH10412</b> ProKIT
<b>TOYOTA - URBAN CRUISER (_P1_)</b>											<b>01/09→03/16</b>
1.33 (NSP110_)	73 kW	1.33 l	01/09→03/16								<b>KH10019</b> ProKIT
1.33 (NSP110_)	74 kW	1.33 l	04/09→03/16								
1.4 D-4D (NLP110_)	66 kW	1.4 l	01/09→04/14								
1.4 D-4D 4WD (NLP115_)	66 kW	1.4 l	01/09→04/14								
<b>TOYOTA - VERSO (_R2_)</b>											<b>04/09→08/18</b>
1.6 (ZGR20_)	97 kW	1.6 l	04/09→08/18								<b>KH30017</b> ProKIT
											<b>KH30018</b> ProKIT
											<b>KH30141</b> ProKIT
1.6 (ZGR20)	81 kW	1.6 l	04/09→08/18								<b>KH30017</b> ProKIT
1.8 (ZGR21_)	95 kW	1.8 l	04/09→08/18								

													
<b>TOYOTA - VERSO (_R2_)</b>												<b>04/09→08/18</b>	
1.6 D4-D (WAR20_)	82 kW	1.6 l	11/13→08/18									KH30018 ProKIT	
2.0 D-4D (AUR20_)	91 kW	2 l	11/12→08/18										
2.2 D-4D (AUR21)	100 kW	2.2 l	04/09→08/18										
1.8 (ZGR21_)	108 kW	1.8 l	04/09→08/18									KH30017 ProKIT	
												KH30141 ProKIT	
2.0 D-4D (AUR20_)	93 kW	2 l	04/09→08/18									KH30018 ProKIT	
2.2 D-4D (AUR21_)	110 kW	2.2 l	04/09→08/18									KH30141 ProKIT	
2.2 D-CAT (AUR21_)	130 kW	2.2 l	04/09→08/18									KH30141 ProKIT	
<b>TOYOTA - VERSO S (_P12_)</b>												<b>11/10→10/16</b>	
1.33 (NSP120_)	73 kW	1.33 l	11/10→10/16									KH10019 ProKIT	
1.4 D4-D (NLP121_)	66 kW	1.4 l	11/10→10/16										
<b>TOYOTA - VISTA Estate / VISTA Saloon (_V5_)</b>												<b>06/98→08/03</b>	
1.8 (ZZV50)	96 kW	1.8 l	06/98→08/03									KH10002 ProKIT	
1.8 (ZZV50)	100 kW	1.8 l	06/98→06/03										
2.0 (AZV50)	110 kW	2 l	04/02→07/03										
2.0 (AZV50)	112 kW	2 l	06/98→06/03										
2.0 (AZV50)	112 kW	2 l	06/98→08/03										
2.0 (SV50)	107 kW	2 l	06/98→08/03										
2.0 (SV50)	107 kW	2 l	04/00→08/01										
2.0 4WD (AZV55)	110 kW	2 l	04/02→06/03										
2.0 4WD (AZV55)	112 kW	2 l	06/98→08/03										
2.0 4WD (SV55)	99 kW	2 l	06/98→04/02										
2.5 (MCV21)	147 kW	2.5 l	06/98→08/02										
3.0	140 kW	3 l	06/98→08/02										
<b>TOYOTA - WISH MPV (_E1_, _E2_)</b>												<b>04/03→</b>	
1.8 (ZGE20_)	106 kW	1.8 l	04/09→									KH10002 ProKIT	
1.8 4WD (ZGE25_)	98 kW	1.8 l	04/09→03/12										
1.8 4WD (ZGE25)	96 kW	1.8 l	04/12→										
1.8 Hi (ZNE10)	97 kW	1.8 l	04/03→03/09										
1.8 Hi 4WD (ZNE14G)	92 kW	1.8 l	04/03→03/09										
2.0	108 kW	2 l	12/03→12/07										
2.0 (ZGE21_, ZGE22_)	107 kW	2 l	04/09→										
2.0 (ZGE21_, ZGE22_)	116 kW	2 l	04/09→										
2.0 (ZGE21R)	104 kW	2 l	11/09→										
2.0 (ZGE22W)	112 kW	2 l	09/12→										
2.0 VVTi (ANE10G, ANE11W)	114 kW	2 l	04/03→03/09										
<b>TOYOTA - YARIS (_P9_, _P13_)</b>												<b>08/05→12/12</b>	
1.0 (KSP130_)	51 kW	1 l	12/10→									KH10019 ProKIT	
1.3 (NSP130_)	73 kW	1.3 l	09/11→									KH30082 ProKIT	
1.33 VVT-i (NSP90_)	73 kW	1.33 l	07/10→05/11										
1.4 D (NLP130_)	66 kW	1.4 l	09/11→										
1.0 GPL (KSP90_)	51 kW	1 l	01/06→12/11									KH10019 ProKIT	
1.3 (NCP130_)	63 kW	1.3 l	12/11→										
1.5 Hybrid (NHP130_)	55 kW	1.5 l	03/12→										
1.0 VVT-i (KSP90_)	51 kW	1 l	08/05→12/11									KH10019 ProKIT	
1.33 VVT-i (NSP90_)	74 kW	1.33 l	11/08→12/11									KH30082 ProKIT	
1.3 VVT-i (NCP90_)	63 kW	1.3 l	11/05→12/12									KH10019 ProKIT	
												KH30082 ProKIT	
1.3 VVT-i (SCP90_)	64 kW	1.3 l	08/05→11/10									KH10019 ProKIT	
												KH30082 ProKIT	
1.4 D-4D (NLP90_)	66 kW	1.4 l	08/05→12/12									KH10019 ProKIT	
												KH30082 ProKIT	
1.8 VVTi (ZSP90_)	98 kW	1.8 l	01/07→12/11									KH10019 ProKIT	
												KH30082 ProKIT	
<b>TOYOTA - YARIS VERSO (_P2_)</b>												<b>08/99→09/05</b>	
1.3 (NCP20_, NCP22_)	62 kW	1.3 l	11/02→09/05									KH10014 ProKIT	
1.3 (NCP20_, NCP22_)	63 kW	1.3 l	08/99→10/02										
1.4 D-4D (NLP20_, NLP22_)	55 kW	1.4 l	09/00→09/05									KH30097 ProKIT	
1.5 (NCP21_)	77 kW	1.5 l	03/00→09/05										
1.5 (NCP21_)	78 kW	1.5 l	03/00→09/05										





**TOYOTA (FAW) - RAV4 (\_A3\_)**

**04/09→08/13**

2.4 4x4 (ACA33)

125 kW






























2.4 l

04/09→08/13



**KH30013** ProKIT



























































												
<b>TRIUMPH - DOLOMITE Sedan (W, TW)</b>										<b>01/72→12/81</b>		
1300	43 kW	1.3 l	01/77→12/81						KH00124 ProKIT			
1500 HL	53 kW	1.5 l	01/77→12/81									
1850	68 kW	1.9 l	01/72→12/77									
1850 HL	68 kW	1.9 l	01/77→12/81									
Sprint	95 kW	2 l	06/73→12/81									
<b>TRIUMPH - GT6 I</b>										<b>01/66→12/73</b>		
MK I	70 kW	2 l	01/66→12/68		MT					KH00124 ProKIT		
MK II	77 kW	2 l	12/68→12/70								KH00124 ProKIT	
MK III	71 kW	2 l	12/72→12/73									
MK III	77 kW	2 l	12/71→12/72									
<b>TRIUMPH - HERALD (1GET)</b>										<b>01/67→12/71</b>		
1200	35 kW	1.2 l	01/68→12/69								KH00123 ProKIT	
											KH00052 ProKIT	
1200	46 kW	1.3 l	01/67→12/68								KH00123 ProKIT	
					08/67 ->							KH00052 ProKIT
13/60	46 kW	1.3 l	01/67→12/71		08/67 -> 09/71							KH00052 ProKIT
<b>TRIUMPH - HERALD Convertible (1RET)</b>										<b>01/61→10/67</b>		
1200	29 kW	1.2 l	01/61→10/67								KH00123 ProKIT	
					05/61 ->							KH00052 ProKIT
<b>TRIUMPH - HERALD Estate (1EET)</b>										<b>01/61→12/71</b>		
1200	29 kW	1.2 l	01/61→10/67								KH00123 ProKIT	
					05/61 ->							KH00052 ProKIT
13/60	46 kW	1.3 l	01/67→12/71		08/67 -> 09/71							KH00052 ProKIT
<b>TRIUMPH - SPITFIRE 1500 (FM)</b>										<b>01/75→01/80</b>		
1500	51 kW	1.5 l	01/75→01/80								KH00052 ProKIT	
<b>TRIUMPH - SPITFIRE MK I (FC)</b>										<b>10/62→12/65</b>		
1.2 MK I	46 kW	1.2 l	10/62→12/65								KH00053 ProKIT	
											KH00052 ProKIT	
<b>TRIUMPH - SPITFIRE MK II (FD)</b>										<b>12/64→01/67</b>		
1.2	49 kW	1.2 l	12/64→01/67								KH00053 ProKIT	
<b>TRIUMPH - SPITFIRE MK III / SPITFIRE MK IV (FD)</b>										<b>02/67→11/74</b>		
1.3	55 kW	1.3 l	02/67→11/70								KH00053 ProKIT	
1.3	55 kW	1.3 l	01/71→12/72								KH00052 ProKIT	
1.5	51 kW	1.5 l	12/72→11/74								KH00053 ProKIT	
<b>TRIUMPH - TOLEDO Sedan (ADM, ADF)</b>										<b>10/70→12/77</b>		
1300	43 kW	1.3 l	10/70→12/77								KH00124 ProKIT	
<b>TRIUMPH - TR 2 I / TR 3 I / TR 3A I / TR 4 I / TR 4A / TR 5 / TR 6 I (250)</b>										<b>01/53→12/76</b>		
2.0	66 kW	2 l	01/53→12/55								KH00123 ProKIT	
2.0	67 kW	2 l	12/55→12/57									
2.0	70 kW	2 l	12/57→12/61									
2.0	75 kW	2 l	01/61→12/65									
2.2	74 kW	2.2 l	01/59→12/61									
2.2	76 kW	2.2 l	12/65→12/67									
2.5	90 kW	2.5 l	01/72→12/76									
2.5 PI	105 kW	2.5 l	01/67→12/68									
2.5 PI	105 kW	2.5 l	01/69→12/76									
<b>TRIUMPH - VITESSE I / VITESSE Cabriolet (HBC)</b>										<b>01/62→12/71</b>		
1.6	51 kW	1.6 l	01/62→10/66								KH00124 ProKIT	
1.6	51 kW	1.6 l	01/62→12/67									
2.0	70 kW	2 l	12/65→12/71									
2.0	70 kW	2 l	01/67→12/68									
2.0	77 kW	2 l	12/68→12/71									






























































					<b>01/72→12/75</b>
<b>TVR - 1600</b>					
1.6	63 kW	1.6 l	01/72→12/75		<b>KH00123 ProKIT</b>
<b>TVR - 2500</b>					<b>01/72→12/77</b>
2.5	78 kW	2.5 l	01/72→12/77		<b>KH00123 ProKIT</b>
<b>TVR - 3000 Coupe</b>					<b>01/72→12/80</b>
3.0	105 kW	3 l	01/72→12/80		<b>KH00123 ProKIT</b>
3.0 Turbo	169 kW	3 l	01/76→12/80		
<b>TVR - GRIFFITH (TCT)</b>					<b>01/90→12/93</b>
4.3	206 kW	4.3 l	01/90→12/93		<b>KH00076 ProKIT</b>
<b>TVR - TAIMAR</b>					<b>01/76→12/80</b>
3.0	105 kW	3 l	01/76→12/80		<b>KH00123 ProKIT</b>
3.0 Turbo	169 kW	3 l	01/76→12/80		
<b>TVR - TUSCAN I Coupe</b>					<b>01/69→12/71</b>
3.0	107 kW	3 l	01/69→12/71		<b>KH00123 ProKIT</b>
4.7	199 kW	4.7 l	01/69→12/69		
<b>TVR - VIXEN</b>					<b>12/68→12/71</b>
1600 S2	73 kW	1.6 l	12/68→12/70		<b>KH00123 ProKIT</b>
1600 S3	63 kW	1.6 l	12/70→12/71		



     					
<b>VAUXHALL - ADAM (M13)</b>				<b>10/12→04/19</b>	
1.0	85 kW	1 l	07/14→11/18	  	KH20017 ProKIT
				 VIN → F6058502; 	KH10042 ProKIT
				 VIN F6058503 →; 	KH10065 ProKIT
					KH20030 ProKIT
1.2	51 kW	1.2 l	10/12→04/19	  	KH20017 ProKIT
1.4	64 kW	1.4 l	10/12→02/19		
1.4	74 kW	1.4 l	10/12→02/19	 	KH10042 ProKIT
1.4 S	110 kW	1.4 l	11/14→01/19	 	KH10065 ProKIT
				 	KH20030 ProKIT
<b>VAUXHALL - AGILA Mk I (A) (H00)</b>				<b>02/00→03/08</b>	
1.0 12V	43 kW	1 l	09/00→08/05		KH10215 ProKIT
1.0 12V	44 kW	1 l	02/00→11/06	 VIN → 3G999999	KH10173 ProKIT
1.2 16V	55 kW	1.2 l	09/00→03/08		
1.2 16V Twinport	59 kW	1.2 l	07/04→11/06	 VIN 4G000001 →	KH10122 ProKIT
<b>VAUXHALL - AGILA Mk II (B) (H08)</b>				<b>01/08→11/14</b>	
1.0 12V	48 kW	1 l	01/08→11/14		KH10137 ProKIT
1.0 i	50 kW	1 l	08/11→11/14		KH10030 ProKIT
1.2 i 16V	63 kW	1.2 l	01/08→11/14		
1.2 i 16V	69 kW	1.2 l	01/08→11/14		
1.3 CDTi	55 kW	1.3 l	01/08→11/14		
<b>VAUXHALL - ANTARA A (L07)</b>				<b>08/06→04/15</b>	
2.0 CDTi 4x4	110 kW	2 l	08/06→04/15	 ; → 12/10	KH30068 ProKIT
2.4 4x4	103 kW	2.4 l	08/06→04/15		KH30087 ProKIT
2.2 CDTi 4x4	120 kW	2.2 l	12/10→		KH30087 ProKIT
2.2 CDTi 4x4	135 kW	2.2 l	12/10→		
2.2 CDTi FWD	120 kW	2.2 l	12/10→		
2.4	123 kW	2.4 l	12/10→04/15		
2.4 4x4	123 kW	2.4 l	12/10→04/15		
<b>VAUXHALL - ARENA Combi / ARENA Van (A97)</b>				<b>03/98→08/01</b>	
1.9 D	44 kW	1.9 l	03/98→08/01	 (ABS)	KH00096 ProKIT
				 (ABS)	KH00104 ProKIT
2.5 D	55 kW	2.5 l	03/98→08/01		KH00096 ProKIT
<b>VAUXHALL - ASTRA Estate / ASTRA Hatchback</b>				<b>09/79→08/86</b>	
1.2 S	44 kW	1.2 l	02/82→08/84		KH10107 ProKIT
1.3 S	55 kW	1.3 l	09/79→08/84	 ; 02/80 →	KH10107 ProKIT
1.6 D	40 kW	1.6 l	02/82→08/86	 ; 09/82 → 10/84	KH10108 ProKIT
1.6 D	40 kW	1.6 l	03/82→08/86		
1.6 S	66 kW	1.6 l	09/81→08/86	 ; 12/81 → 10/84	KH10108 ProKIT
1.8 GTE	85 kW	1.8 l	03/83→08/86	 ; 04/83 → 10/84	KH10108 ProKIT
<b>VAUXHALL - ASTRA Mk II Belmont (T85)</b>				<b>09/85→12/91</b>	
1.3	55 kW	1.3 l	09/85→08/91	 ; 01/86 → 09/89	KH10107 ProKIT
1.4 i	44 kW	1.4 l	01/90→12/91	 ; 08/90 → 09/91	KH10107 ProKIT
1.6 D	40 kW	1.6 l	09/85→08/91	 ; 01/86 → 01/89	KH10108 ProKIT
1.6 S	60 kW	1.6 l	01/89→12/91	 ; → 09/91	KH10107 ProKIT
1.7 D	42 kW	1.7 l	01/89→12/91	 ; → 09/91	KH10108 ProKIT
1.8	82 kW	1.8 l	01/86→12/90		KH10108 ProKIT
<b>VAUXHALL - ASTRA Mk II Convertible (T85)</b>				<b>01/87→08/93</b>	
1.6 i	60 kW	1.6 l	01/87→12/91	 ; 03/87 → 09/91	KH10107 ProKIT
2.0 i	85 kW	2 l	01/87→12/91	 ; 03/87 → 09/91	KH10108 ProKIT
2.0 i Cat	85 kW	2 l	01/91→08/93	 ; 09/91 →	KH10108 ProKIT
<b>VAUXHALL - ASTRA Mk II Estate / ASTRA Mk II Hatchback (T85)</b>				<b>09/84→08/91</b>	
1.2	44 kW	1.2 l	09/84→12/88	 ; 10/84 →	KH10107 ProKIT
1.2	44 kW	1.2 l	09/84→08/91		
1.3	55 kW	1.3 l	09/84→08/91	 ; 10/84 → 10/89	KH10107 ProKIT
1.3	55 kW	1.3 l	09/84→08/91	 ; 10/84 → 10/89	KH10108 ProKIT
1.4 i	44 kW	1.4 l	01/90→08/91		KH10107 ProKIT
1.4 S	55 kW	1.4 l	01/90→08/91		
1.6	60 kW	1.6 l	09/84→08/91	 ; 10/84 → 08/86	KH10107 ProKIT
1.6 D	40 kW	1.6 l	09/84→12/89	 ; 10/84 → 01/89	KH10108 ProKIT



     			
VAUXHALL - ASTRA Mk II Estate / ASTRA Mk II Hatchback (T85)			
09/84→08/91			
1.6 S	66 kW	1.6 l	09/84→08/86  ; 10/84 ->
1.8 GTE	82 kW	1.8 l	09/84→08/91
1.7 D	42 kW	1.7 l	09/88→08/91 
1.7 D	42 kW	1.7 l	02/89→08/91
1.8 i	83 kW	1.8 l	01/90→08/91
2.0 GTE 16V	115 kW	2 l	05/88→08/91
2.0 GTE	95 kW	2 l	09/86→08/91  ; 03/87 ->
VAUXHALL - ASTRA Mk III (F) Convertible, (F) Estate, (F) Hatchback, (F) Sa- loon)			
03/91→03/01			
1.4 i	44 kW	1.4 l	09/91→02/98 
1.4 i	60 kW	1.4 l	03/92→02/98 
1.6 i	52 kW	1.6 l	02/93→12/96
1.6 i	55 kW	1.6 l	09/91→12/98  ; ABS; Rim Hole Number: 4
1.6 i	55 kW	1.6 l	03/92→09/98  ; ABS; Rim Hole Number: 4
1.6 i	55 kW	1.6 l	01/96→03/01
1.6 i	74 kW	1.6 l	03/92→02/98
1.4 i	44 kW	1.4 l	04/92→09/98  ; -> 03/98
1.6 i 16V	74 kW	1.6 l	08/94→09/98 
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.4 i	60 kW	1.4 l	03/91→02/98  ; 09/91 -> 12/93
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.4 i	60 kW	1.4 l	04/92→09/98  ; -> 12/93
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.4 i 16V	66 kW	1.4 l	02/96→01/98 
1.4 i 16V	66 kW	1.4 l	02/96→02/98  ; ABS; Rim Hole Number: 4
1.4 i 16V	66 kW	1.4 l	02/96→09/98  ; ABS; Rim Hole Number: 4
1.6 i	52 kW	1.6 l	08/94→07/96  ; ABS; Rim Hole Number: 4
1.4 S	55 kW	1.4 l	09/91→02/98  ; 10/91 -> 12/92
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 i	52 kW	1.6 l	03/93→08/96  ; 01/96 ->
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 i	52 kW	1.6 l	07/94→02/98  ; -> 06/95
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 i	55 kW	1.6 l	09/91→02/98  ; 10/91 ->
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 i	74 kW	1.6 l	05/92→12/94  ; -> 03/94
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 i 16V	74 kW	1.6 l	01/94→02/98  ; 08/94 ->
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4
1.6 Si	74 kW	1.6 l	03/91→12/94  ; 09/91 ->
			
			 ; ABS; Rim Hole Number: 4
			 ; ABS; Rim Hole Number: 4



**VAUXHALL - ASTRA Mk III (F) Convertible, (F) Estate, (F) Hatchback, (F) Sa- 03/91→03/01  
loon)**

1.7 D	42 kW	1.7 l	12/91→02/98			KH10108 ProKIT
1.7 D	42 kW	1.7 l	03/92→09/92		ABS, Rim Hole Number: 4	KH30054 ProKIT
1.7 TD	60 kW	1.7 l	12/91→02/98		ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8 i 16V	85 kW	1.8 l	09/94→02/98		ABS, Rim Hole Number: 4	KH30055 ProKIT
2.0 i	85 kW	2 l	09/91→02/98			
2.0 i	85 kW	2 l	03/93→10/94			
1.7 D	42 kW	1.7 l	12/91→02/98		-> 08/94	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.7 D	44 kW	1.7 l	03/91→12/94		09/91 ->	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.7 D	44 kW	1.7 l	09/91→12/94		ABS, Rim Hole Number: 4	KH30054 ProKIT
1.7 TD	50 kW	1.7 l	08/94→09/98		ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8	92 kW	1.8 l	09/94→08/96		ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8 i (F08)	66 kW	1.8 l	09/91→02/98			
1.8 i 16V	82 kW	1.8 l	09/95→02/98			
1.8 i 16V	85 kW	1.8 l	01/94→12/96			
1.8 i 16V	92 kW	1.8 l	06/93→10/94			
1.8 i 16V	92 kW	1.8 l	09/94→02/98			
2.0 i 16V	100 kW	2 l	01/94→02/98			
2.0 i 16V	100 kW	2 l	02/95→09/98			
1.7 D	44 kW	1.7 l	07/92→09/98		-> 03/98	KH10108 ProKIT
1.7 TD	60 kW	1.7 l	12/91→09/98		ABS, Rim Hole Number: 4	KH30054 ProKIT
2.0 i	85 kW	2 l	03/92→09/98		ABS, Rim Hole Number: 4	KH30055 ProKIT
1.7 TD	50 kW	1.7 l	01/94→02/98		08/94 ->	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.7 TD	50 kW	1.7 l	08/94→02/98		11/94 ->	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8 16V	85 kW	1.8 l	11/94→03/01		01/96 ->; VIN -> S_999999	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8 i	66 kW	1.8 l	09/91→02/98		10/91 -> 07/94	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
1.8 i	66 kW	1.8 l	03/92→09/98			KH10107 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
2.0 i	85 kW	2 l	09/91→02/98		10/91 -> 07/93	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
2.0 i 16V	100 kW	2 l	01/94→02/98		04/95 ->	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT
2.0 i 16V	110 kW	2 l	09/91→02/98		10/91 ->	KH10108 ProKIT
					ABS, Rim Hole Number: 4	KH30054 ProKIT
					ABS, Rim Hole Number: 4	KH30055 ProKIT

**VAUXHALL - ASTRA Mk IV (G) Convertible, (G) Coupe, (G) Estate, (G) Hatch- 02/98→10/05  
back, (G) Saloon)**

1.4 16V	66 kW	1.4 l	02/98→05/05		ABS, Rim Hole Number: 4	KH30057 ProKIT
1.4 16V	66 kW	1.4 l	09/98→05/05		Rim Hole Number: 4; ABS	KH30058 ProKIT
1.4 16V (F08, F48)	66 kW	1.4 l	02/98→05/05		Rim Hole Number: 5; ABS	KH30059 ProKIT
1.6	55 kW	1.6 l	03/98→04/04		ABS, Rim Hole Number: 4	KH30054 ProKIT
1.6	55 kW	1.6 l	09/98→09/00		ABS, Rim Hole Number: 4	KH30054 ProKIT
1.6	62 kW	1.6 l	03/98→04/04		ABS, Rim Hole Number: 4	KH30055 ProKIT
1.6	62 kW	1.6 l	09/00→05/05			
1.6	76 kW	1.6 l	12/02→05/05			
1.6 (F08, F48)	55 kW	1.6 l	02/98→09/00			
1.6 (F08, F48)	62 kW	1.6 l	09/00→05/05			
1.6 16V	74 kW	1.6 l	03/98→04/04			
1.6 16V	74 kW	1.6 l	09/98→05/05			
1.6 16V	74 kW	1.6 l	03/01→10/05			
1.6 16V	76 kW	1.6 l	03/00→08/05			
1.6 16V	76 kW	1.6 l	03/03→10/05			









**VAUXHALL - ASTRA Mk IV (G) Convertible, (G) Coupe, (G) Estate, (G) Hatch- 02/98→10/05 back, (G) Saloon)**
















































































1.6 16V (F08, F48)	74 kW	1.6 l	02/98→05/05	; ; Rim Hole Number: 4	KH30057 ProKIT
1.7 CDTi 16V	59 kW	1.7 l	04/03→05/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.7 CDTi 16V (F08, F48)	59 kW	1.7 l	04/03→05/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.7 DTi 16V	55 kW	1.7 l	02/00→05/05	; Rim Hole Number: 5;	KH30059 ProKIT
1.7 DTi 16V (F08, F48)	55 kW	1.7 l	02/00→05/05	; ; Rim Hole Number: 4	KH30054 ProKIT
1.7 TD	50 kW	1.7 l	02/98→08/00	; ; Rim Hole Number: 4	KH30055 ProKIT
1.7 TD	50 kW	1.7 l	09/98→08/00	; ; Rim Hole Number: 4	KH30055 ProKIT
1.7 TD (F08, F48)	50 kW	1.7 l	02/98→08/00	; ; Rim Hole Number: 4	KH30055 ProKIT
1.4 16V Dualfuel	66 kW	1.4 l	09/99→06/03	; ; Rim Hole Number: 4	KH30054 ProKIT
1.4 16V Dualfuel (F08, F48)	66 kW	1.4 l	09/99→06/03	; ; Rim Hole Number: 4	KH30054 ProKIT
1.6 (F08, F48)	76 kW	1.6 l	12/02→05/05		
1.6 Dualfuel	55 kW	1.6 l	02/98→12/00		
1.6 Dualfuel	74 kW	1.6 l	09/99→08/04		
1.6 Dualfuel (F08, F48)	55 kW	1.6 l	02/98→12/00		
1.6 Dualfuel (F08, F48)	74 kW	1.6 l	09/99→08/04		
1.6 Dualfuel	62 kW	1.6 l	07/00→05/05	; ; Rim Hole Number: 4	KH30057 ProKIT
1.6 Dualfuel	63 kW	1.6 l	03/98→04/04	; Rim Hole Number: 4;	KH30058 ProKIT
1.6 Dualfuel	63 kW	1.6 l	09/02→05/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.6 Dualfuel (F08, F48)	63 kW	1.6 l	09/02→05/05	; Rim Hole Number: 5;	KH30059 ProKIT
1.6 Dualfuel (F08)	62 kW	1.6 l	07/00→05/05	; ; Rim Hole Number: 4	KH30054 ProKIT
1.8 16V	85 kW	1.8 l	02/98→08/00	; ; Rim Hole Number: 4	KH30057 ProKIT
1.8 16V	85 kW	1.8 l	02/98→07/04	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V	92 kW	1.8 l	02/98→07/04	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V	92 kW	1.8 l	09/00→05/05	; Rim Hole Number: 5;	KH30059 ProKIT
1.8 16V (F08, F48)	85 kW	1.8 l	02/98→09/00	; ; Rim Hole Number: 4	KH30055 ProKIT
1.8 16V (F08, F48)	92 kW	1.8 l	09/00→05/05	;	KH30114 ProKIT
1.8 16V Dualfuel	87 kW	1.8 l	02/98→07/04	;	KH30114 ProKIT
1.8 16V Dualfuel	87 kW	1.8 l	09/02→05/05		
1.8 16V Dualfuel (F08, F48)	87 kW	1.8 l	09/02→05/05		
2.0 DI	60 kW	2 l	02/98→07/04		
2.0 DI	60 kW	2 l	03/98→04/04		
2.0 DI (F48)	60 kW	2 l	02/98→05/05		
1.8 16V	85 kW	1.8 l	03/00→08/05	; ; Rim Hole Number: 4	KH30057 ProKIT
1.8 16V	92 kW	1.8 l	09/00→08/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V	92 kW	1.8 l	03/01→10/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.8 16V Dualfuel	87 kW	1.8 l	09/02→08/05	; Rim Hole Number: 5;	KH30059 ProKIT
2.0 16V	100 kW	2 l	09/98→05/05	;	KH30114 ProKIT
2.0 16V (F08)	100 kW	2 l	02/98→05/05	;	KH30114 ProKIT
2.0 DTi 16V	74 kW	2 l	02/98→07/04	;	KH30130 ProKIT
2.0 DTi 16V	74 kW	2 l	03/98→04/04		
2.0 DTi 16V (F48)	74 kW	2 l	08/99→05/05		
2.0 SRI Turbo (F08)	141 kW	2 l	11/01→05/05		
2.2 16V	108 kW	2.2 l	03/00→08/05		
2.2 16V	108 kW	2.2 l	03/01→05/05		
2.2 16V (F08, F48)	108 kW	2.2 l	03/01→05/05		
1.8 16V Dualfuel	92 kW	1.8 l	07/02→12/03	;	KH30114 ProKIT
1.8 16V Dualfuel	92 kW	1.8 l	07/02→08/04		
1.8 16V Dualfuel (F08, F48)	92 kW	1.8 l	07/02→12/03		
2.0 (F08)	147 kW	2 l	08/02→05/05		
2.0	147 kW	2 l	09/02→10/05	; ; Rim Hole Number: 4	KH30057 ProKIT
2.0 16V Turbo	140 kW	2 l	09/00→08/05	; Rim Hole Number: 4;	KH30058 ProKIT
2.0 Turbo	141 kW	2 l	03/02→10/05	; Rim Hole Number: 4;	KH30059 ProKIT
2.2 16V	108 kW	2.2 l	03/01→10/05	; Rim Hole Number: 5;	KH30059 ProKIT
				;	KH30114 ProKIT








**VAUXHALL - ASTRA Mk V (H), (H) Estate, (H) Sport Hatch, (H) TwinTop) 01/04→10/12**

1.3 CDTi (L08)	66 kW	1.3 l	04/05→11/10	; Rim Hole Number: 5	KH30046 ProKIT
1.3 CDTi (L35)	66 kW	1.3 l	08/04→03/09	; Rim Hole Number: 4	KH30072 ProKIT
1.3 CDTi (L48)	66 kW	1.3 l	01/04→05/09	; Rim Hole Number: 4	KH30041 ProKIT
1.4 (L35)	66 kW	1.4 l	08/04→03/09	; Rim Hole Number: 4	KH30041 ProKIT
1.4 (L48)	66 kW	1.4 l	01/04→05/09	; Rim Hole Number: 5	KH30044 ProKIT
1.4 i 16V (L08)	66 kW	1.4 l	03/05→11/10		
1.6 (L08)	77 kW	1.6 l	02/05→11/10		
1.6 (L08)	132 kW	1.6 l	10/06→11/10		
1.6 (L35)	77 kW	1.6 l	08/04→03/09		
1.6 (L35)	85 kW	1.6 l	08/04→03/11		
1.6 (L35)	132 kW	1.6 l	08/04→03/09		
1.6 (L48)	77 kW	1.6 l	01/04→05/09		
1.6 (L48)	85 kW	1.6 l	01/04→05/09		
1.6 (L67)	77 kW	1.6 l	09/05→11/10		
1.6 i 16V (L08)	85 kW	1.6 l	12/06→11/10		
1.6 i 16V (L67)	85 kW	1.6 l	10/06→08/11		
1.6 Turbo (L48)	132 kW	1.6 l	09/06→09/09		
1.7 CDTi (L08)	74 kW	1.7 l	02/05→11/10		
1.7 CDTi (L08)	81 kW	1.7 l	02/07→11/09		
1.7 CDTi (L35)	74 kW	1.7 l	08/04→03/09		
1.7 CDTi (L35)	59 kW	1.7 l	08/04→05/09		
1.7 CDTi (L48)	81 kW	1.7 l	01/04→03/11		






     					
VAUXHALL - ASTRA Mk V (H), (H) Estate, (H) Sport Hatch, (H) TwinTop)				01/04→10/12	
1.7 CDTi (L48)	59 kW	1.7 l	01/04→05/09	; Rim Hole Number: 5	KH30046 ProKIT
1.7 CDTi (L48)	74 kW	1.7 l	01/04→05/09	; Rim Hole Number: 4	KH30072 ProKIT
1.8 (L08)	92 kW	1.8 l	02/05→11/10	; Rim Hole Number: 4	KH30041 ProKIT
1.8 (L35)	92 kW	1.8 l	10/04→03/09	; Rim Hole Number: 4	KH30041 ProKIT
1.8 (L35)	103 kW	1.8 l	12/05→10/10	; Rim Hole Number: 5	KH30044 ProKIT
1.8 (L48)	92 kW	1.8 l	01/04→05/09		
1.8 (L48)	103 kW	1.8 l	01/04→05/09		
1.8 (L67)	103 kW	1.8 l	05/08→11/10		
1.8 i 16V (L08)	103 kW	1.8 l	03/07→11/10		
1.7 CDTi (L35)	81 kW	1.7 l	08/04→10/12	; Rim Hole Number: 4	KH30072 ProKIT
				; Rim Hole Number: 5;	KH30084 ProKIT
				VIN -> 62079978, 65076709, 68027072	
				; Rim Hole Number: 5;	KH30046 ProKIT
				VIN 62079979, 65076710, 68027073, 8B000001 ->	
				; Rim Hole Number: 4	KH30041 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTi (L08)	74 kW	1.9 l	08/05→11/10	; Rim Hole Number: 4	KH30072 ProKIT
1.9 CDTi (L08)	88 kW	1.9 l	02/05→11/10	; Rim Hole Number: 5;	KH30046 ProKIT
1.9 CDTi (L35)	88 kW	1.9 l	08/04→03/09		
1.9 CDTi (L48)	88 kW	1.9 l	01/04→05/09		
1.9 CDTi 16V (L48)	88 kW	1.9 l	01/04→05/09	; Rim Hole Number: 5;	KH30084 ProKIT
2.0 Turbo (L08)	125 kW	2 l	02/05→11/10	VIN 62083450, 65076710, 68027073, 8B000001 ->	
2.0 Turbo (L35)	125 kW	2 l	08/04→10/10	; Rim Hole Number: 4	KH30041 ProKIT
2.0 Turbo (L35)	147 kW	2 l	08/04→10/10	; Rim Hole Number: 5	KH30044 ProKIT
2.0 Turbo (L48)	125 kW	2 l	01/04→05/09		
2.0 Turbo (L48)	147 kW	2 l	01/04→05/09		
1.9 CDTi (L08)	110 kW	1.9 l	02/05→11/10	; Rim Hole Number: 4	KH30072 ProKIT
1.9 CDTi (L35)	110 kW	1.9 l	08/04→03/09	; Rim Hole Number: 5	KH30074 ProKIT
1.9 CDTi (L48)	110 kW	1.9 l	01/04→05/09	; Rim Hole Number: 4	KH30041 ProKIT
1.9 CDTi (L67)	110 kW	1.9 l	01/06→11/10	; Rim Hole Number: 5	KH30044 ProKIT
2.0 Turbo (L48)	177 kW	2 l	01/04→05/09		
1.9 CDTi 16V (L35)	88 kW	1.9 l	08/04→03/09	; Rim Hole Number: 5;	KH30046 ProKIT
				VIN -> 62083449, 65076709, 68027072	
				; Rim Hole Number: 5;	KH30084 ProKIT
				VIN 62083450, 65076710, 68027073, 8B000001 ->	
2.0 (L67)	125 kW	2 l	02/06→11/10	; Rim Hole Number: 4	KH30072 ProKIT
				; Rim Hole Number: 5	KH30084 ProKIT
				; Rim Hole Number: 4	KH30041 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
2.0 Turbo (L67)	147 kW	2 l	01/06→11/10	; Rim Hole Number: 4	KH30072 ProKIT
				; Rim Hole Number: 5	KH30084 ProKIT
				; Rim Hole Number: 5;	KH30046 ProKIT
				VIN -> 62083449, 65076709, 68027072	
				; Rim Hole Number: 4	KH30041 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
2.0 VXR (L08)	176 kW	2 l	02/09→11/10	; Rim Hole Number: 4	KH30072 ProKIT
				; Rim Hole Number: 4	KH30041 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
VAUXHALL - ASTRA Mk VI (J), (J) Estate, (J) GTC, (J) Saloon)				12/09→10/15	
1.3 CDTi	70 kW	1.3 l	10/10→10/15	; 15 Inch	KH30119 ProKIT
1.3 CDTi	70 kW	1.3 l	12/09→10/15		
1.3 CDTi	70 kW	1.3 l	06/12→10/15		
1.4	64 kW	1.4 l	12/09→10/15		
1.4	74 kW	1.4 l	12/09→10/15		
1.4	74 kW	1.4 l	10/10→10/15		
1.4	74 kW	1.4 l	10/11→10/15		
1.4	74 kW	1.4 l	06/12→10/15		
1.4	88 kW	1.4 l	10/11→10/15		
1.4	103 kW	1.4 l	10/11→10/15		
1.4 Turbo	88 kW	1.4 l	08/10→10/15		
1.4 Turbo	103 kW	1.4 l	12/09→10/15		
1.4 Turbo	103 kW	1.4 l	10/10→10/15		
1.4 Turbo	103 kW	1.4 l	06/12→10/15		
1.6	85 kW	1.6 l	12/09→10/15		
1.6	85 kW	1.6 l	10/10→10/15		
1.6	85 kW	1.6 l	06/12→10/15		
1.6	132 kW	1.6 l	10/11→10/15		
1.6 CDTi	81 kW	1.6 l	11/13→10/15		
1.6 CDTi	81 kW	1.6 l	01/14→10/15		
1.6 CDTi	81 kW	1.6 l	07/14→10/15		
1.6 CDTi	100 kW	1.6 l	11/13→10/15		
1.6 CDTi	100 kW	1.6 l	01/14→10/15		



				      <b>13</b> 		
<b>VAUXHALL - ASTRA Mk VI (J, J) Estate, J) GTC, J) Saloon)</b>				<b>12/09→10/15</b>		
1.6 CDTi	100 kW	1.6 l	07/14→10/15	  15 Inch	KH30119 ProKIT	
1.6 SIDI	147 kW	1.6 l	09/13→10/15		KH30089 ProKIT	
1.6 Turbo	132 kW	1.6 l	12/09→10/15		KH30089 ProKIT	
1.6 Turbo	132 kW	1.6 l	10/10→10/15	  15 Inch	KH30119 ProKIT	
1.6 Turbo	132 kW	1.6 l	06/12→10/15			
1.7 CDTi	81 kW	1.7 l	12/09→10/15			
1.7 CDTi	81 kW	1.7 l	10/10→10/15			
1.7 CDTi	81 kW	1.7 l	10/11→10/15			
1.7 CDTi	92 kW	1.7 l	12/09→10/15			
1.7 CDTi	92 kW	1.7 l	10/10→10/15			
1.7 CDTi	96 kW	1.7 l	06/11→10/15			
1.7 CDTi	96 kW	1.7 l	10/11→10/15			
1.7 CDTi	81 kW	1.7 l	06/12→10/15			
1.7 CDTi	96 kW	1.7 l	06/12→10/15			
2.0 BiTurbo CDTi	143 kW	2 l	12/12→10/15			
2.0 CDTi	118 kW	2 l	12/09→06/11			
2.0 CDTi	118 kW	2 l	10/10→06/11			
2.0 CDTi	121 kW	2 l	08/11→10/15			
2.0 CDTi	121 kW	2 l	10/11→10/15			
2.0 VXR	206 kW	2 l	04/12→10/15			
<b>VAUXHALL - ASTRAVAN Mk III (F) Estate Van (T92)</b>				<b>09/91→08/98</b>		
1.4 i (F70)	44 kW	1.4 l	09/91→08/95	  10/91 -> VIN -> P_999999	KH10107 ProKIT	
					KH10376 ProKIT	
				  Rim Hole Number: 4	KH30054 ProKIT	
				  Rim Hole Number: 4	KH30055 ProKIT	
1.6 i (F70)	52 kW	1.6 l	09/94→08/96		KH10376 ProKIT	
				 VIN -> P_999999	KH10107 ProKIT	
				  Rim Hole Number: 4	KH30054 ProKIT	
				  Rim Hole Number: 4	KH30055 ProKIT	
1.6 i (F70)	55 kW	1.6 l	10/91→08/98	 -> 03/98	KH10107 ProKIT	
					KH10376 ProKIT	
				  Rim Hole Number: 4	KH30054 ProKIT	
				  Rim Hole Number: 4	KH30055 ProKIT	
1.7 D (F70)	42 kW	1.7 l	09/91→08/93	  Rim Hole Number: 4	KH30054 ProKIT	
1.7 TD (F70)	60 kW	1.7 l	09/95→08/96	  Rim Hole Number: 4	KH30055 ProKIT	
1.7 D (F70)	44 kW	1.7 l	10/91→12/94		KH10108 ProKIT	
				  Rim Hole Number: 4	KH30054 ProKIT	
				  Rim Hole Number: 4	KH30055 ProKIT	
1.7 TD (F70)	50 kW	1.7 l	09/94→08/98	 VIN -> P_999999	KH10107 ProKIT	
				  Rim Hole Number: 4	KH30054 ProKIT	
				  Rim Hole Number: 4	KH30055 ProKIT	
<b>VAUXHALL - ASTRAVAN Mk IV (G) Estate Van (T98)</b>				<b>02/98→08/06</b>		
1.4 16V	66 kW	1.4 l	09/00→05/05	  Rim Hole Number: 4	KH30054 ProKIT	
1.6 Dualfuel	55 kW	1.6 l	02/98→12/00			
1.6 Dualfuel	62 kW	1.6 l	09/00→10/04			
1.6 Dualfuel	74 kW	1.6 l	07/00→08/05			
1.6 Dualfuel 16V	77 kW	1.6 l	10/04→12/05			
1.6 i	55 kW	1.6 l	08/98→09/00	  Rim Hole Number: 4	KH30057 ProKIT	
1.6 i	62 kW	1.6 l	09/00→08/06	 Rim Hole Number: 4; 	KH30058 ProKIT	
1.7 CDTi	59 kW	1.7 l	07/03→08/06	 Rim Hole Number: 5; 	KH30059 ProKIT	
1.7 DTI 16V	55 kW	1.7 l	04/01→08/06	  Rim Hole Number: 4	KH30054 ProKIT	
1.7 TD	50 kW	1.7 l	08/98→08/06	  Rim Hole Number: 4	KH30057 ProKIT	
2.0 DI	60 kW	2 l	08/98→08/06	  Rim Hole Number: 4	KH30058 ProKIT	
				 Rim Hole Number: 4; 	KH30059 ProKIT	
				 Rim Hole Number: 5; 	KH30055 ProKIT	
				  Rim Hole Number: 4	KH30114 ProKIT	
				 	KH30114 ProKIT	
2.0 DTI	74 kW	2 l	04/04→08/06	  Rim Hole Number: 4	KH30057 ProKIT	
				 Rim Hole Number: 4; 	KH30058 ProKIT	
				 Rim Hole Number: 5; 	KH30059 ProKIT	
				 	KH30114 ProKIT	
<b>VAUXHALL - ASTRAVAN Mk V (H) Estate Van (A04)</b>				<b>03/05→12/13</b>		
1.3 CDTi	66 kW	1.3 l	08/05→	 Rim Hole Number: 5	KH30046 ProKIT	
1.4 i	66 kW	1.4 l	03/05→	 Rim Hole Number: 4	KH30072 ProKIT	
1.6	76 kW	1.6 l	03/05→			
1.7 CDTi	59 kW	1.7 l	03/05→07/06	 Rim Hole Number: 4	KH30041 ProKIT	
1.7 CDTi	74 kW	1.7 l	03/05→11/11	 Rim Hole Number: 5	KH30044 ProKIT	

      					
<b>VAUXHALL - ASTRAVAN Mk V (H) Estate Van (A04)</b>				<b>03/05→12/13</b>	
1.7 CDTi	81 kW	1.7 l	06/11→12/13	; Rim Hole Number: 4 ; Rim Hole Number: 5; VIN -> 62079978, 65076709, 68027072 ; Rim Hole Number: 5; VIN 62079979, 65076710, 68027073, 8B000001 -> ; Rim Hole Number: 4 ; Rim Hole Number: 5	KH30072 ProKIT KH30084 ProKIT KH30046 ProKIT KH30041 ProKIT KH30044 ProKIT
1.7 CDTi	92 kW	1.7 l	11/11→	; Rim Hole Number: 4 ; Rim Hole Number: 5 ; Rim Hole Number: 4 ; Rim Hole Number: 5	KH30072 ProKIT KH30084 ProKIT KH30041 ProKIT KH30044 ProKIT
1.9 CDTi	88 kW	1.9 l	03/05→11/11	; Rim Hole Number: 4 ; Rim Hole Number: 5; VIN -> 62083449, 65076709, 68027072 ; Rim Hole Number: 5; VIN 62083450, 65076710, 68027073, 8B000001 -> ; Rim Hole Number: 4 ; Rim Hole Number: 5	KH30072 ProKIT KH30046 ProKIT KH30084 ProKIT KH30041 ProKIT KH30044 ProKIT
1.9 CDTi	110 kW	1.9 l	03/05→11/11	; Rim Hole Number: 4 ; Rim Hole Number: 4 ; Rim Hole Number: 5	KH30072 ProKIT KH30041 ProKIT KH30044 ProKIT
<b>VAUXHALL - BRAVA Pickup (TF0, TF1)</b>				<b>06/90→12/02</b>	
2.3 4x4 (TFS16)	69 kW	2.3 l	06/90→08/94		KH00026 ProKIT
2.5 TD 4x4 (TFS54)	56 kW	2.5 l	06/90→06/94		KH00026 ProKIT
2.5 TD 4x4 (TFS54)	56 kW	2.5 l	07/94→12/02	; -> 07/02	KH00026 ProKIT
<b>VAUXHALL - CALIBRA (C89)</b>				<b>06/90→07/97</b>	
2.0 i	85 kW	2 l	06/90→07/97	; -> 08/96; VIN T1000001 -> ; VIN -> S1999999, S9999999 ; -> 08/96	KH10206 ProKIT KH10108 ProKIT KH10219 ProKIT
2.0 i 16V	100 kW	2 l	06/90→07/97	; -> 06/97; VIN T1000001 -> ; VIN -> S1999999, S9999999 ; -> 06/97	KH10206 ProKIT KH10108 ProKIT KH10219 ProKIT
2.0 i 16V	110 kW	2 l	06/90→02/94	; VIN -> S1999999, S9999999 ; VIN T1000001 -> 	KH10108 ProKIT KH10206 ProKIT KH10219 ProKIT
2.0 i 16V 4x4	110 kW	2 l	06/90→02/94	; 09/90 ->; VIN -> S1999999, S9999999 ; -> 04/92; VIN T1000001 -> ; 09/90 -> 04/92	KH10108 ProKIT KH10206 ProKIT KH10219 ProKIT
2.0 i Turbo 4x4	150 kW	2 l	03/92→07/97	; 04/92 ->; VIN -> N1299999, N9299999 ; VIN P1000001 -> ; 04/92 ->	KH10108 ProKIT KH10206 ProKIT KH10219 ProKIT
2.5 i V6	125 kW	2.5 l	04/93→07/97	; 08/93 -> ; 08/93 ->	KH10206 ProKIT KH10219 ProKIT
<b>VAUXHALL - CARLTON Mk III Estate / CARLTON Mk III Saloon (V87)</b>				<b>09/86→03/94</b>	
1.8 i	85 kW	1.8 l	09/86→03/94	; 11/86 -> 08/92	KH10219 ProKIT
1.8 S	66 kW	1.8 l	09/86→03/94	; 11/86 -> 09/90	KH10219 ProKIT
2.2 TD	66 kW	2.2 l	10/86→08/88	; 11/86 ->	KH10219 ProKIT
2.3 TD Interc.	74 kW	2.3 l	08/88→03/94	; 09/88 ->	KH10219 ProKIT
2.6 i	110 kW	2.6 l	09/90→03/94		KH10219 ProKIT
3000 24V	147 kW	3 l	09/89→03/94		
3000 Cat	130 kW	3 l	03/88→03/94		
3.0	130 kW	3 l	03/87→03/94	; 10/89 -> 09/90	KH10219 ProKIT
3.0 3000	130 kW	3 l	03/87→09/90	; -> 10/89	KH10219 ProKIT
3.0 3000 24V	150 kW	3 l	09/89→03/94	; 10/89 -> 08/93	KH10219 ProKIT
3.6 24V Lotus	277 kW	3.6 l	08/90→09/92	; 09/90 ->	KH10219 ProKIT
<b>VAUXHALL - CASCADA Convertible (W13)</b>				<b>02/13→</b>	
1.4	103 kW	1.4 l	02/13→		KH30089 ProKIT
1.6	125 kW	1.6 l	02/13→		
2.0 CDTI	121 kW	2 l	02/13→		
2.0 CDTI	143 kW	2 l	02/13→		



    					
<b>VAUXHALL - CAVALIER Mk II Convertible (J82)</b> <span style="float:right">03/85→10/88</span>					
1800i	82 kW	1.8 l	03/85→10/88	; 11/85 -> 08/88	KH10108 ProKIT
<b>VAUXHALL - CAVALIER Mk II Estate / CAVALIER Mk II Hatchback / CAVALIER Mk II Saloon (J82)</b> <span style="float:right">09/81→08/88</span>					
1.3 S	55 kW	1.3 l	09/81→08/88		KH10107 ProKIT
1.6 i	55 kW	1.6 l	08/86→08/88		KH00005 ProKIT
1.6 i Cat	55 kW	1.6 l	08/86→08/88		
1.6	66 kW	1.6 l	10/83→08/88		KH10108 ProKIT
1.6 N	55 kW	1.6 l	09/81→08/88		KH00005 ProKIT
1.6 S	66 kW	1.6 l	09/81→08/88		
1.8 i Cat	74 kW	1.8 l	01/85→08/86		
2.0 i Cat	85 kW	2 l	09/86→08/88		
1.6 D	40 kW	1.6 l	03/82→08/88	; 09/82 ->	KH10108 ProKIT
1600D	40 kW	1.6 l	03/82→08/88		KH00005 ProKIT
1.8 i	82 kW	1.8 l	09/81→08/86		KH10108 ProKIT
1.8 i	82 kW	1.8 l	09/81→08/88	; 01/85 -> 07/88	KH10108 ProKIT
					KH00005 ProKIT
1.8 i	85 kW	1.8 l	09/81→08/88	; 10/82 -> 08/87	KH10108 ProKIT
					KH00005 ProKIT
2.0 i	85 kW	2 l	09/86→08/88	; 03/87 ->	KH10108 ProKIT
2.0 i Cat	85 kW	2 l	09/86→08/88		KH00005 ProKIT
2.0 SRi 130	95 kW	2 l	03/87→08/88	; 04/87 ->	KH10108 ProKIT
2000i	90 kW	2 l	09/86→08/88		KH00005 ProKIT
<b>VAUXHALL - CAVALIER Mk III Hatchback / CAVALIER Mk III Saloon (J89)</b> <span style="float:right">08/88→11/95</span>					
1.4 S	55 kW	1.4 l	09/88→11/95	; 11/88 -> 08/92	KH10107 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
1.6	60 kW	1.6 l	09/88→05/93	; 10/88 -> 08/92	KH10107 ProKIT
				; 10/88 -> 08/92	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
1.6 i	52 kW	1.6 l	09/93→11/95	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6 i	52 kW	1.6 l	09/93→11/95	; -> 12/93; VIN -> P1999999, P5999999, P7999999	KH10107 ProKIT
				; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6 i	55 kW	1.6 l	09/88→11/95	; 09/91 -> 12/93; VIN -> P1999999, P5999999, P7999999	KH10107 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
1.7 D	42 kW	1.7 l	09/88→09/92	; 11/88 ->	KH10108 ProKIT
					KH00005 ProKIT
1.7 D	44 kW	1.7 l	07/92→11/95	; 09/92 -> 10/95	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
1.7 TD	60 kW	1.7 l	09/88→11/95	; 09/91 -> 10/95	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
1.8	65 kW	1.8 l	09/89→08/92		KH00005 ProKIT
2.0 GSi	115 kW	2 l	09/89→08/92		
1.8	66 kW	1.8 l	09/88→10/90	; 10/89 ->	KH10108 ProKIT
					KH00005 ProKIT
1.8	66 kW	1.8 l	09/88→08/95	; 10/89 -> 08/92	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT





**VAUXHALL - CAVALIER Mk III Hatchback / CAVALIER Mk III Saloon (J89) 08/88→11/95**

















































1.8 i Cat	66 kW	1.8 l	03/90→11/95	; 09/90 -> 10/95	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.0 GSi 4x4	115 kW	2 l	09/89→08/92		KH10219 ProKIT
2.0 i	85 kW	2 l	09/88→10/90	; 10/88 ->	KH10108 ProKIT
2.0 i	85 kW	2 l	09/88→10/92		KH00005 ProKIT
2.0 i 16V 2.0 SRi 16V	100 kW	2 l	09/92→08/95 09/92→08/95	; 03/94 ->	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.0 i 16V	110 kW	2 l	09/88→11/95	; 10/89 -> 10/94	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.0 i 16V 4x4	110 kW	2 l	09/88→11/95	; 10/89 -> 10/92	KH10108 ProKIT
					KH10219 ProKIT
2.0 i 16V 4x4	110 kW	2 l	01/92→11/93	; -> 10/92	KH10108 ProKIT
					KH10219 ProKIT
2.0 i 4x4 2.0 i 4x4 (89)	85 kW	2 l	01/91→10/92 09/91→10/92	; -> 08/92	KH10108 ProKIT
					KH10219 ProKIT
2.0 i 4x4	95 kW	2 l	09/88→08/92	; 12/88 ->	KH10108 ProKIT
					KH10219 ProKIT
2.0 i Cat	85 kW	2 l	09/88→11/95	; -> 10/95	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.0 i Cat	85 kW	2 l	09/90→11/95	; -> 05/94	KH10108 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.0 i Turbo 4x4	150 kW	2 l	09/92→06/94	; 07/93 ->; VIN P1000001 ->	KH10206 ProKIT
				; -> 07/93; VIN -> N1999999	KH10108 ProKIT
					KH10219 ProKIT
2.0 SRi	95 kW	2 l	09/88→08/92	; 12/88 ->	KH10108 ProKIT
2.0 SRi	95 kW	2 l	09/88→09/92		KH00005 ProKIT
2.5 V6	125 kW	2.5 l	08/88→06/94	; 03/93 ->	KH10206 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
				; -> 12/92	KH00005 ProKIT
2.5 V6	125 kW	2.5 l	09/88→06/94	; (ABS)	KH30114 ProKIT
					KH10206 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30054 ProKIT
				; 01/93 ->; (ABS); Rim Hole Number: 4	KH30055 ProKIT
2.5 V6	125 kW	2.5 l	09/88→06/94	; -> 12/92	KH00005 ProKIT
				; (ABS)	KH30114 ProKIT

**VAUXHALL - CHEVETTE Saloon 09/74→12/85**


















1300	39 kW	1.3 l	03/75→12/85	; -> 04/76; VIN -> 133466	KH00088 ProKIT
1300	42 kW	1.3 l	09/74→12/85		





























**VAUXHALL - COMBO Mk II (C) Box Body/MPV (F25) 09/01→02/12**

1.3 CDTi 16V	51 kW	1.3 l	09/04→02/12		KH10063 ProKIT
1.3 CDTi 16V	55 kW	1.3 l	10/05→11/11	; (ABS); Rim Hole Number: 4	KH30054 ProKIT
1.4 16V	66 kW	1.4 l	10/01→05/07	; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.4 i 16V	66 kW	1.4 l	01/04→11/11	; (ABS); Rim Hole Number: 4	KH30055 ProKIT
1.6	62 kW	1.6 l	09/01→10/04		
1.6	64 kW	1.6 l	10/01→11/11		
1.6 CNG 16V	69 kW	1.6 l	06/06→02/12		
1.6 CNG 16V	71 kW	1.6 l	04/05→02/12		
1.7 DI 16V	48 kW	1.7 l	09/01→11/11		
1.7 DTi 16V	55 kW	1.7 l	10/01→11/11		

										
<b>VAUXHALL - COMBO Mk II (C) Box Body/MPV (F25)</b>									<b>09/01→02/12</b>	
1.7 CDTi 16V	74 kW	1.7 l	12/04→11/11							KH10108 ProKIT
				 ABS	Rim Hole Number: 4					KH30054 ProKIT
				 ABS	Rim Hole Number: 4					KH30055 ProKIT
<b>VAUXHALL - COMBO Mk III (D) Box Body/MPV (X12)</b>									<b>11/11→</b>	
1.6 CDTi	66 kW	1.6 l	11/11→		ABS; Payload: for increased payload; 					KH10198 ProKIT
1.6 CDTi	74 kW	1.6 l	11/11→							
1.6 CDTi	77 kW	1.6 l	11/11→							
2.0 CDTi	99 kW	2 l	11/11→		ABS					KH10198 ProKIT
<b>VAUXHALL - COMBO Mk IV (E) Box Body/MPV (K9)</b>									<b>06/18→</b>	
1.2	81 kW	1.2 l	02/19→							KH10063 ProKIT
1.5 D	56 kW	1.5 l	08/18→							
1.5 D	75 kW	1.5 l	08/18→							
1.5 D	96 kW	1.5 l	08/18→							
1.6 D	55 kW	1.6 l	06/18→							
1.6 D	73 kW	1.6 l	06/18→							
<b>VAUXHALL - COMBO TOUR Mk II (C) (F25)</b>									<b>09/01→02/12</b>	
1.3 CDTi 16V	51 kW	1.3 l	09/04→09/06							KH10063 ProKIT
1.3 CDTi 16V	55 kW	1.3 l	07/06→02/12		ABS; Rim Hole Number: 4					KH30054 ProKIT
1.4	66 kW	1.4 l	10/04→09/10		ABS; Rim Hole Number: 4					KH30055 ProKIT
1.6	64 kW	1.6 l	10/01→06/04							
1.6 CNG	69 kW	1.6 l	06/06→09/10							
1.6 CNG	71 kW	1.6 l	04/05→02/12							
1.7 DI 16V	48 kW	1.7 l	09/01→06/04							
1.7 DTi 16V	55 kW	1.7 l	10/01→02/12							
1.7 CDTi 16V	74 kW	1.7 l	12/04→09/10		ABS; Rim Hole Number: 4					KH30054 ProKIT
					ABS; Rim Hole Number: 4					KH30055 ProKIT
<b>VAUXHALL - CORSA Mk I (B) (S93)</b>									<b>12/92→09/00</b>	
1.0 i 12V	40 kW	1 l	11/96→09/00							KH10376 ProKIT
1.2 i	33 kW	1.2 l	03/93→09/00							KH00005 ProKIT
1.2 i 16V	48 kW	1.2 l	03/98→09/00							
1.4 i 16V	66 kW	1.4 l	09/94→09/00							
1.4 i S	60 kW	1.4 l	03/93→09/00							
1.5 D	37 kW	1.5 l	12/92→12/96							
1.5 TD	49 kW	1.5 l	03/93→10/96							
1.6 GSI 16V	80 kW	1.6 l	03/93→09/00							
1.6 i 16V	78 kW	1.6 l	09/94→09/00							
1.7 D	44 kW	1.7 l	02/96→09/00							
1.4 i	44 kW	1.4 l	03/93→09/00							KH10107 ProKIT
										KH10376 ProKIT
										KH00005 ProKIT
<b>VAUXHALL - CORSA Mk II (C) (X01)</b>									<b>08/00→04/07</b>	
1.0 12V (F08, F68)	43 kW	1 l	09/00→10/03							KH10063 ProKIT
1.2 16V (F08, F68)	55 kW	1.2 l	09/00→10/06		-> 08/03; 					KH20118 ProKIT
1.2 16V Dualfuel (F08)	55 kW	1.2 l	08/01→10/06		ABS; 					KH10113 ProKIT
1.4 16V (F08, F68)	66 kW	1.4 l	09/00→10/06							
1.7 DI 16V (F08, F68)	48 kW	1.7 l	08/00→09/06							
1.7 DTi 16V (F08, F68)	55 kW	1.7 l	08/00→09/06							
1.8 16V (F08, F68)	92 kW	1.8 l	08/00→09/06							
1.0 12V (F08, F68)	44 kW	1 l	11/03→10/06							KH10063 ProKIT
					ABS; 					KH10113 ProKIT
										KH20118 ProKIT
1.2 Twinport (F08, F68)	59 kW	1.2 l	07/04→10/06							KH10063 ProKIT
1.4 Twinport (F08, F68)	66 kW	1.4 l	06/03→10/06							
1.3 CDTi 16V (F08, F68)	51 kW	1.3 l	10/03→04/07							KH10063 ProKIT
					04/04 ->; 					KH20118 ProKIT
										KH10113 ProKIT
1.7 CDTi 16V (F08, F68)	74 kW	1.7 l	08/00→09/06							KH10108 ProKIT
										KH10113 ProKIT
										KH20118 ProKIT
<b>VAUXHALL - CORSA Mk III (D) (S07)</b>									<b>07/06→08/14</b>	
1.0 (L08)	44 kW	1 l	08/06→08/14		ABS					KH10042 ProKIT
1.0 i 12V (L08)	48 kW	1 l	01/10→08/14							KH20017 ProKIT
1.2 (L08)	51 kW	1.2 l	06/10→08/14							
1.2 (L08)	59 kW	1.2 l	08/06→08/14							KH20030 ProKIT
1.2 i 16V (L08)	63 kW	1.2 l	12/09→08/14							
1.2 LPG (L08)	59 kW	1.2 l	09/09→08/14							
1.2 LPG (L08)	63 kW	1.2 l	08/11→08/14							

				13	i			
<b>VAUXHALL - CORSA Mk III (D) (S07)</b>							<b>07/06→08/14</b>	
1.3 CDTI (L08)	55 kW	1.3 l	08/06→08/14		ABS	KH10042 ProKIT		
1.3 CDTI (L08)	66 kW	1.3 l	08/06→08/14			KH20017 ProKIT		
1.3 CDTI (L08)	70 kW	1.3 l	07/10→08/14			KH20030 ProKIT		
1.4 (L08)	66 kW	1.4 l	08/06→08/14					
1.4 (L08)	74 kW	1.4 l	01/10→08/14					
1.4 (L08)	88 kW	1.4 l	08/12→08/14					
1.4 LPG (L08)	66 kW	1.4 l	07/06→08/14					
1.6 SRi (L08)	110 kW	1.6 l	05/07→08/14					
1.6 VXR (L08)	141 kW	1.6 l	11/06→08/14					
1.6 VXR (L08)	150 kW	1.6 l	06/11→08/14					
1.7 CDTI (L08)	92 kW	1.7 l	11/06→08/14					
1.7 CDTI (L08)	96 kW	1.7 l	03/07→08/14					
<b>VAUXHALL - CORSA Mk IV (E) (X15)</b>							<b>08/14→</b>	
1.0	66 kW	1 l	08/14→		VIN -> F4168927; ABS	KH10042 ProKIT		
1.0	85 kW	1 l	08/14→		VIN -> F6D58386; ABS	KH10065 ProKIT		
					VIN F4168928, F6058387 ->	KH20017 ProKIT		
					Rim Hole Number: 4	KH20030 ProKIT		
					Rim Hole Number: 5	KH10042 ProKIT		
					ABS	KH20017 ProKIT		
					Rim Hole Number: 4	KH20030 ProKIT		
					Rim Hole Number: 5	KH10065 ProKIT		
					ABS	KH20017 ProKIT		
					Rim Hole Number: 4	KH20030 ProKIT		
					Rim Hole Number: 5	KH10042 ProKIT		
					ABS	KH10065 ProKIT		
					Rim Hole Number: 4	KH20017 ProKIT		
					Rim Hole Number: 5	KH20030 ProKIT		
					Rim Hole Number: 4	KH20017 ProKIT		
					Rim Hole Number: 5	KH20030 ProKIT		
<b>VAUXHALL - CORSAVAN Mk I (B) Hatchback Van (S93)</b>							<b>01/94→09/00</b>	
1.4 i	44 kW	1.4 l	01/94→09/00			KH10376 ProKIT		
1.5 D	37 kW	1.5 l	08/94→12/95					
1.7 D	44 kW	1.7 l	01/94→09/00					
<b>VAUXHALL - CORSAVAN Mk II (C) Hatchback Van (X01)</b>							<b>09/00→11/06</b>	
1.2 16V (F08)	55 kW	1.2 l	09/00→06/06			KH10063 ProKIT		
1.7 DI 16V (F08)	48 kW	1.7 l	09/00→06/06		-> 08/03; 00	KH20118 ProKIT		
1.7 DTI 16V (F08)	55 kW	1.7 l	09/00→06/06			KH10113 ProKIT		
1.2 16V (F08)	59 kW	1.2 l	07/04→11/06			KH10063 ProKIT		
1.2 16V Dualfuel (F08)	59 kW	1.2 l	07/04→12/05					
1.4 (F08)	66 kW	1.4 l	11/03→06/06					
1.2 16V Dualfuel (F08)	55 kW	1.2 l	08/01→06/06			KH10063 ProKIT		
						KH10113 ProKIT		
1.3 CDTI 16V (F08)	52 kW	1.3 l	04/04→06/06			KH10063 ProKIT		
						KH10113 ProKIT		
						KH20118 ProKIT		
<b>VAUXHALL - CORSAVAN Mk III / CORSAVAN Mk IV (D) Hatchback Van, E) Hatchback Van)</b>							<b>07/09→</b>	
1.2	51 kW	1.2 l	01/10→		ABS	KH10042 ProKIT		
1.2	51 kW	1.2 l	10/14→					
1.2	59 kW	1.2 l	07/09→					
1.3 CDTi	55 kW	1.3 l	10/14→			KH10065 ProKIT		
1.3 CDTi	70 kW	1.3 l	10/14→					
<b>VAUXHALL - FRONTERA Mk I (A) (U92)</b>							<b>09/91→10/98</b>	
2.2 i	100 kW	2.2 l	03/95→10/98		04/95 ->	KH00026 ProKIT		
					04/95 -> 09/98	KH00065 ProKIT		
2.3 TD	74 kW	2.3 l	09/91→06/98		-> 04/95	KH00026 ProKIT		
2.4 i	92 kW	2.4 l	03/92→10/98					
2.5 TDS	85 kW	2.5 l	11/91→06/98			KH00026 ProKIT		
						KH00065 ProKIT		
2.8 TD	83 kW	2.8 l	01/95→12/96		04/95 -> 09/96	KH00026 ProKIT		
					04/95 ->	KH00065 ProKIT		

									
<b>VAUXHALL - FRONTERA Mk I (A) Sport (U92)</b>									
<b>03/92→10/98</b>									
2.0 i	85 kW	2 l	03/92→10/98		04/95 -> 09/98	KH00065 ProKIT			
2.5 TDS	85 kW	2.5 l	09/96→10/98		-> 08/98	KH00065 ProKIT			
2.8 TD	83 kW	2.8 l	01/95→12/96		04/95 ->	KH00065 ProKIT			
<b>VAUXHALL - FRONTERA Mk II (B) (U99)</b>									
<b>10/98→10/04</b>									
2.2 DTI	85 kW	2.2 l	10/98→09/04		KH00026 ProKIT				
2.2 i	100 kW	2.2 l	10/98→10/04		KH00065 ProKIT				
3.2 i	151 kW	3.2 l	10/98→10/04						
<b>VAUXHALL - INSIGNIA Mk I (A) Country Tourer, A) Hatchback, A) Saloon, A) Sports Tourer)</b>									
<b>07/08→05/17</b>									
1.4 (35)	103 kW	1.4 l	04/11→05/17		KH30070 ProKIT				
1.4 (68)	103 kW	1.4 l	04/11→05/17		VIN -> C1000000	KH30105 ProKIT			
1.4 (69)	103 kW	1.4 l	04/11→05/17						
1.4 LPG (35)	103 kW	1.4 l	07/12→05/17						
1.4 LPG (68)	103 kW	1.4 l	07/12→05/17						
1.4 LPG (69)	103 kW	1.4 l	07/12→05/17						
1.6 CDTI (35)	100 kW	1.6 l	07/15→05/17						
1.6 CDTI (68)	100 kW	1.6 l	07/15→05/17						
1.6 Turbo (35)	125 kW	1.6 l	07/13→05/17						
1.6 Turbo (35)	132 kW	1.6 l	01/09→05/17						
1.6 Turbo (68)	125 kW	1.6 l	07/13→05/17						
1.6 Turbo (68)	132 kW	1.6 l	01/09→05/17						
1.6 Turbo (69)	132 kW	1.6 l	01/09→05/17						
1.8 (35)	103 kW	1.8 l	07/08→05/17						
1.8 (68)	103 kW	1.8 l	07/08→05/17						
1.8 (69)	103 kW	1.8 l	07/08→05/17						
2.0 Biturbo CDTI (35)	143 kW	2 l	03/12→05/17						
2.0 Biturbo CDTI (68)	143 kW	2 l	03/12→05/17						
2.0 Biturbo CDTI (69)	143 kW	2 l	03/12→05/17						
2.0 CDTI (35)	81 kW	2 l	07/08→05/17						
2.0 CDTI (35)	88 kW	2 l	03/12→03/16						
2.0 CDTI (35)	96 kW	2 l	07/08→12/14						
2.0 CDTI (35)	103 kW	2 l	07/13→05/17						
2.0 CDTI (35)	118 kW	2 l	07/08→05/17						
2.0 CDTI (35)	120 kW	2 l	07/13→05/17						
2.0 CDTI (35)	125 kW	2 l	11/14→05/17						
2.0 CDTI (35)	140 kW	2 l	11/08→05/17						
2.0 CDTI (68)	81 kW	2 l	07/08→05/17						
2.0 CDTI (68)	88 kW	2 l	03/12→03/16						
2.0 CDTI (68)	96 kW	2 l	07/08→12/14						
2.0 CDTI (68)	103 kW	2 l	07/13→05/17						
2.0 CDTI (68)	118 kW	2 l	07/08→05/17						
2.0 CDTI (68)	120 kW	2 l	07/13→05/17						
2.0 CDTI (68)	125 kW	2 l	11/14→05/17						
2.0 CDTI (68)	140 kW	2 l	10/08→05/17						
2.0 CDTI (69)	96 kW	2 l	07/08→12/14						
2.0 CDTI (69)	103 kW	2 l	07/13→05/17						
2.0 CDTI (69)	118 kW	2 l	07/08→05/17						
2.0 CDTI (69)	120 kW	2 l	07/13→05/17						
2.0 CDTI (69)	125 kW	2 l	11/14→05/17						
2.0 CDTI (69)	140 kW	2 l	11/08→05/17						
2.0 Turbo (35)	162 kW	2 l	07/08→05/17						
2.0 Turbo (35)	184 kW	2 l	07/11→05/17						
2.0 Turbo (68)	184 kW	2 l	07/11→05/17						
2.0 Turbo (69)	162 kW	2 l	07/08→05/17						
2.0 Turbo (69)	184 kW	2 l	09/11→05/17						
1.6	85 kW	1.6 l	07/08→07/12		KH30070 ProKIT				
1.6 CDTI (69)	100 kW	1.6 l	07/15→05/17						
1.6 Turbo (47)	125 kW	1.6 l	07/13→05/17						
2.0 Biturbo CDTI 4x4 (47)	143 kW	2 l	09/13→05/17						
2.0 CDTI (47)	120 kW	2 l	07/13→05/17						
2.0 CDTI (47)	125 kW	2 l	11/14→05/17						
2.0 CDTI 4x4 (47)	125 kW	2 l	11/14→05/17						
2.0 Turbo (68)	162 kW	2 l	07/08→05/17						
2.0 Biturbo CDTI 4x4 (35)	143 kW	2 l	03/12→05/17		KH30070 ProKIT				
2.0 Biturbo CDTI 4x4 (68)	143 kW	2 l	03/12→05/17		VIN -> C1000000	KH30196 ProKIT			
2.0 Biturbo CDTI 4x4 (69)	143 kW	2 l	03/12→05/17		VIN C1000001 ->	KH30183 ProKIT			
2.0 CDTI 4x4 (35)	118 kW	2 l	07/08→05/17						
2.0 CDTI 4x4 (35)	125 kW	2 l	11/14→05/17						
2.0 CDTI 4x4 (35)	140 kW	2 l	05/09→05/17						
2.0 CDTI 4x4 (68)	118 kW	2 l	07/08→05/17						
2.0 CDTI 4x4 (68)	125 kW	2 l	11/14→05/17						
2.0 CDTI 4x4 (68)	140 kW	2 l	05/09→05/17						
2.0 CDTI 4x4 (69)	118 kW	2 l	07/08→05/17						
2.0 CDTI 4x4 (69)	125 kW	2 l	11/14→05/17						
2.0 CDTI 4x4 (69)	140 kW	2 l	05/09→05/17						
2.0 Turbo 4x4 (35)	162 kW	2 l	07/08→05/17						
2.0 Turbo 4x4 (68)	162 kW	2 l	07/08→05/17						

											
<b>VAUXHALL - INSIGNIA Mk I (A) Country Tourer, (A) Hatchback, (A) Saloon, 07/08→05/17</b>											
<b>A) Sports Tourer)</b>											
2.0 Turbo 4x4 (69)	162 kW	2 l	07/08→05/17								KH30070 ProKIT
2.0 Turbo 4x4 (69)	184 kW	2 l	09/11→05/17								
2.8 V6 Turbo (35)	191 kW	2.8 l	08/08→05/17		VIN -> C1000000						KH30196 ProKIT
2.8 V6 Turbo 4x4 (68)	191 kW	2.8 l	07/08→05/17		VIN C1000001 ->						KH30183 ProKIT
2.8 V6 Turbo 4x4 (69)	191 kW	2.8 l	07/08→05/17								
2.8 VXR (35)	239 kW	2.8 l	07/09→05/17								
2.8 VXR (68)	239 kW	2.8 l	07/09→05/17								
2.8 VXR (69)	239 kW	2.8 l	07/09→05/17								
<b>VAUXHALL - MERIVA A (X03) 01/03→06/10</b>											
1.3 CDTI	51 kW	1.3 l	04/05→06/10								KH10063 ProKIT
1.3 CDTI	55 kW	1.3 l	01/03→10/09		ABS	Rim Hole Number: 4					KH30054 ProKIT
1.4 16V Twinport	66 kW	1.4 l	01/03→06/10								
1.6 i	64 kW	1.6 l	01/03→06/10								KH30114 ProKIT
1.6 i 16V	74 kW	1.6 l	01/03→09/05								
1.6 i 16V Twinport	77 kW	1.6 l	05/03→06/10								
1.7 DTI	55 kW	1.7 l	06/03→06/10								
1.8 i 16V	92 kW	1.8 l	05/03→06/10								
1.6 Turbo	132 kW	1.6 l	05/06→06/10								KH10108 ProKIT
1.7 CDTI	74 kW	1.7 l	09/03→08/05		ABS	Rim Hole Number: 4					KH30054 ProKIT
<b>VAUXHALL - MERIVA Mk II (B) (S10) 06/10→</b>											
1.3 CDTI	70 kW	1.3 l	06/10→								KH10348 ProKIT
1.3 CDTI	55 kW	1.3 l	06/10→								
1.4	74 kW	1.4 l	06/10→								
1.4	88 kW	1.4 l	06/10→								
1.4	103 kW	1.4 l	06/10→								
1.4 LPG	88 kW	1.4 l	06/11→								
1.6 CDTI	81 kW	1.6 l	07/14→								
1.6 CDTI	100 kW	1.6 l	08/13→								
1.6 CDTI	70 kW	1.6 l	01/14→								
1.7 CDTI	81 kW	1.7 l	06/10→								
1.7 CDTI	96 kW	1.7 l	06/10→								
1.7 CDTI	74 kW	1.7 l	06/10→								
<b>VAUXHALL - MONTEREY (M92) 09/91→07/98</b>											
3.1 TD	84 kW	3.1 l	09/91→07/98		05/94 ->						KH00026 ProKIT
3.2	130 kW	3.2 l	06/92→07/98								
<b>VAUXHALL - MOVANO Mk I (A) Chassis/Cab, (A) Combi, (A) Van) 10/98→12/10</b>											
1.9 DTI (FD)	60 kW	1.9 l	10/01→05/10		16 Inch						KH10100 ProKIT
1.9 DTI (JD)	60 kW	1.9 l	10/01→05/10		15 Inch;						
2.2 DTI (FD)	66 kW	2.2 l	09/00→05/10	VIN	B000184, B000207, B000486, B000807, B001462 ->						
2.2 DTI (JD)	66 kW	2.2 l	09/00→05/10								KH10195 ProKIT
2.2 DTI (UD0)	66 kW	2.2 l	09/00→05/10								
2.5 CDTI (ED, UD0)	88 kW	2.5 l	08/06→05/10	VIN ->	B000183, B000206, B000485, B000806, B001461;						
2.5 CDTI (ED, UD0)	107 kW	2.5 l	08/06→05/10		15 Inch						
2.5 CDTI (FD)	74 kW	2.5 l	10/06→12/10		16 Inch						KH10064 ProKIT
2.5 CDTI (FD)	88 kW	2.5 l	08/06→05/10		15 Inch						KH10092 ProKIT
2.5 CDTI (FD)	107 kW	2.5 l	08/06→05/10								
2.5 CDTI (JD)	74 kW	2.5 l	10/01→08/09								
2.5 CDTI (JD)	88 kW	2.5 l	02/03→08/09								
2.5 CDTI (JD)	107 kW	2.5 l	08/06→05/10								
2.5 CDTI (UD0, ED)	74 kW	2.5 l	10/06→12/10								
2.5 D (FD)	59 kW	2.5 l	10/98→09/00								
2.5 D (JD)	59 kW	2.5 l	10/98→09/00								
2.5 D (UD0)	59 kW	2.5 l	10/98→08/02								
2.5 DTI (ED, UD0)	84 kW	2.5 l	01/01→12/06								
2.5 DTI (FD)	84 kW	2.5 l	10/01→05/10								
2.5 DTI (JD)	84 kW	2.5 l	10/01→08/09								
2.8 DTI (JD)	84 kW	2.8 l	10/98→10/01								
2.8 DTI (UD0, ED, HD)	84 kW	2.8 l	10/98→10/01								
2.8 TDI (FD)	84 kW	2.8 l	10/98→10/01								
3.0 DTi (ED)	100 kW	3 l	10/03→05/10								
3.0 DTi (FD)	100 kW	3 l	10/03→05/10								
3.0 DTi (JD)	100 kW	3 l	10/03→05/10								
2.5 (FD)	73 kW	2.5 l	11/03→12/06		16 Inch						KH10100 ProKIT
2.5 CDTI (UD0, ED)	73 kW	2.5 l	11/03→12/06		15 Inch;						
VIN B000184, B000207, B000486, B000807, B001462 ->											
 KH10195 ProKIT											
VIN -> B000183, B000206, B000485, B000806, B001461;											
 15 Inch											
 15 Inch KH10092 ProKIT											





**VAUXHALL - MOVANO Mk II (B) Chassis/Cab, (B) Combi, (B) VAN**

**05/10→**

2.3 CDTI FWD (FV)	74 kW	2.3 l	05/10→		<b>KH10139</b> ProKIT
2.3 CDTI FWD (FV)	81 kW	2.3 l	02/12→		<b>KH10138</b> ProKIT
2.3 CDTI FWD (FV)	92 kW	2.3 l	05/10→		
2.3 CDTI FWD (FV)	96 kW	2.3 l	10/16→		
2.3 CDTI FWD (FV)	100 kW	2.3 l	05/14→		
2.3 CDTI FWD (FV)	107 kW	2.3 l	05/10→		
2.3 CDTI FWD (FV)	120 kW	2.3 l	05/14→		
2.3 CDTI FWD (FV)	125 kW	2.3 l	11/16→		
2.3 CDTI FWD (JV)	74 kW	2.3 l	05/10→		
2.3 CDTI FWD (JV)	81 kW	2.3 l	05/14→		
2.3 CDTI FWD (JV)	92 kW	2.3 l	05/10→		
2.3 CDTI FWD (JV)	100 kW	2.3 l	05/14→		
2.3 CDTI FWD (JV)	107 kW	2.3 l	05/10→		
2.3 CDTI FWD (JV)	120 kW	2.3 l	05/14→		
2.3 CDTI FWD (JV)	125 kW	2.3 l	07/15→		
2.3 CDTI FWD (UV, EV)	81 kW	2.3 l	05/14→		
2.3 CDTI FWD (UV, HV, EV)	92 kW	2.3 l	05/10→		
2.3 CDTI FWD (UV, HV, EV)	96 kW	2.3 l	10/16→		
2.3 CDTI FWD (UV, HV, EV)	107 kW	2.3 l	05/10→		
2.3 CDTI FWD (UV, HV)	74 kW	2.3 l	05/10→		
2.3 CDTI FWD (UV, HV)	100 kW	2.3 l	05/14→		
2.3 CDTI FWD (UV, HV)	125 kW	2.3 l	11/16→		
2.3 CDTI RWD (FV)	74 kW	2.3 l	05/10→		<b>KH10174</b> ProKIT
2.3 CDTI RWD (FV)	92 kW	2.3 l	05/10→		<b>KH00086</b> ProKIT
2.3 CDTI RWD (FV)	96 kW	2.3 l	10/16→		
2.3 CDTI RWD (FV)	100 kW	2.3 l	05/14→		<b>KH10143</b> ProKIT
2.3 CDTI RWD (FV)	107 kW	2.3 l	05/10→		
2.3 CDTI RWD (FV)	120 kW	2.3 l	05/14→		
2.3 CDTI RWD (UV, HV, EV)	92 kW	2.3 l	07/10→		
2.3 CDTI RWD (UV, HV, EV)	107 kW	2.3 l	07/10→		
2.3 CDTI RWD (UV, HV)	74 kW	2.3 l	07/10→		
2.3 CDTI RWD (UV, HV)	96 kW	2.3 l	10/16→		
2.3 CDTI RWD (UV, HV)	100 kW	2.3 l	05/14→		
2.3 CDTI RWD (UV, HV)	120 kW	2.3 l	05/14→		

**VAUXHALL - NOVA Hatchback / NOVA Saloon (S83)**

**09/82→12/93**

1.0	33 kW	1 l	09/82→10/87		<b>KH10107</b> ProKIT
1.0	33 kW	1 l	05/83→03/93		<b>KH00005</b> ProKIT
1.2	33 kW	1.2 l	09/89→03/93		
1.2 N	38 kW	1.2 l	01/90→03/93		
1.2 S	40 kW	1.2 l	09/82→10/87		
1.2 S	40 kW	1.2 l	05/83→02/90		
1.3 S	51 kW	1.3 l	09/82→10/87		
1.3 S	51 kW	1.3 l	05/83→10/89		
1.4 i	44 kW	1.4 l	01/90→03/93		
1.4 i S	60 kW	1.4 l	09/91→03/93		
1.4 S	55 kW	1.4 l	01/90→02/93		
1.4 S	55 kW	1.4 l	01/90→03/93		
1.5 D	37 kW	1.5 l	09/87→03/93		
1.5 TD	49 kW	1.5 l	01/90→03/93		
1.6 GSI	74 kW	1.6 l	05/88→03/92		
1.6 GSI Cat	74 kW	1.6 l	02/92→03/93		
1.2	33 kW	1.2 l	02/92→12/93		<b>KH00005</b> ProKIT
1.4	44 kW	1.4 l	10/90→08/92		
1.4	60 kW	1.4 l	09/90→08/92		
1.5 TD	49 kW	1.5 l	01/90→02/93		
1.6 GSI	72 kW	1.6 l	09/89→03/93		

**VAUXHALL - NOVAVAN Hatchback Van (S83)**

**01/90→10/94**

1.0	33 kW	1 l	10/91→12/91		<b>KH00005</b> ProKIT
1.4	55 kW	1.4 l	11/90→03/93		
1.2	38 kW	1.2 l	01/90→10/94		<b>KH10107</b> ProKIT
1.5 D	37 kW	1.5 l	01/91→10/94		<b>KH00005</b> ProKIT

**VAUXHALL - OMEGA (B) Estate (V94)**

**02/94→06/03**

2.0	85 kW	2 l	03/94→09/99	; 04/94 -> 10/95	<b>KH10219</b> ProKIT
2.0 16V	100 kW	2 l	03/94→07/01	; 04/94 -> 09/99	<b>KH10219</b> ProKIT
2.0 DTI 16V	74 kW	2 l	01/98→09/00	; 10/98 ->	<b>KH10219</b> ProKIT
2.2 16V	106 kW	2.2 l	02/94→06/03		<b>KH10219</b> ProKIT
2.5 TD	96 kW	2.5 l	04/94→07/01		
3.0 V6	155 kW	3 l	07/94→07/00		
3.2 V6	160 kW	3.2 l	02/01→06/03		
2.2 DTI 16V	88 kW	2.2 l	08/00→06/03	; 09/00 ->	<b>KH10219</b> ProKIT
2.6 V6	132 kW	2.6 l	08/00→06/03		
2.5 V6	125 kW	2.5 l	03/94→09/00	; 04/94 ->	<b>KH10219</b> ProKIT

				13		i		
<b>VAUXHALL - OMEGA (B) Saloon (V94)</b>								<b>01/94→07/03</b>
2.0	85 kW	2 l	03/94→09/99	; 04/94 -> 10/95;				KH10206 ProKIT
				; 04/94 -> 10/95;				KH10219 ProKIT
2.0	85 kW	2 l	09/95→09/96	; -> 10/95;				KH10206 ProKIT
				; -> 10/95;				KH10219 ProKIT
2.0 16V	100 kW	2 l	03/94→07/01	; 04/94 ->;				KH10206 ProKIT
2.5 V6	125 kW	2.5 l	03/94→09/00	; 04/94 ->;				KH10219 ProKIT
2.0 DTI 16V	74 kW	2 l	01/98→09/00	; 10/98 ->;				KH10206 ProKIT
				; 10/98 ->;				KH10219 ProKIT
2.2 16V	106 kW	2.2 l	01/94→06/03	;				KH10206 ProKIT
2.5 TD	96 kW	2.5 l	04/94→07/01	;				KH10219 ProKIT
3.2 V6	160 kW	3.2 l	02/01→07/03	;				
2.2 DTI 16V	88 kW	2.2 l	08/00→07/03	; 09/00 ->;				KH10206 ProKIT
2.6 V6	132 kW	2.6 l	08/00→07/03	; 09/00 ->;				KH10219 ProKIT
3.0 V6	155 kW	3 l	04/94→07/00	; 06/94 ->;				KH10206 ProKIT
				; 06/94 ->;				KH10219 ProKIT
<b>VAUXHALL - SENATOR Mk II (B) (V88)</b>								<b>09/87→09/93</b>
2.5 i	103 kW	2.5 l	09/87→10/90	; -> 09/90				KH10219 ProKIT
2.6 i	110 kW	2.6 l	09/90→09/93	; -> 08/93				KH10219 ProKIT
3.0	130 kW	3 l	01/88→09/90	; -> 08/90				KH10219 ProKIT
3.0 24V	150 kW	3 l	09/89→09/93	; 10/89 -> 08/93				KH10219 ProKIT
3.0 i Cat	130 kW	3 l	01/88→09/93	; 09/90 -> 10/92				KH10219 ProKIT
<b>VAUXHALL - SIGNUM (Z03)</b>								<b>03/03→10/08</b>
1.9 CDTI	88 kW	1.9 l	04/04→03/08	; -> 12/04; VIN -> 41999999;				KH30065 ProKIT
1.9 CDTI 16V	110 kW	1.9 l	04/04→03/08	; 01/05 ->; VIN 51000001 ->				
				; -> 12/04;				KH30061 ProKIT
								KH30071 ProKIT
2.0 DTI	74 kW	2 l	05/03→04/04	; 06/03 ->; VIN -> 41999999;				KH30065 ProKIT
				;				KH30061 ProKIT
				; 06/03 ->				KH30071 ProKIT
2.0 i Turbo	129 kW	2 l	03/03→10/08	; 06/03 -> 12/04; VIN -> 41999999;				KH30065 ProKIT
2.2 DTI	92 kW	2.2 l	05/03→05/08	; 01/05 -> 09/05; VIN 51000001 ->				
2.2 i	114 kW	2.2 l	05/03→05/08	; -> 12/04;				KH30061 ProKIT
3.0 CDTi	130 kW	3 l	05/03→05/08	; 06/03 -> 09/05				KH30071 ProKIT
3.2 V6	155 kW	3.2 l	05/03→05/08	; 06/03 -> 09/05				KH30065 ProKIT
2.8 V6 Turbo	169 kW	2.8 l	07/05→05/08	; 10/05 -> 12/06				KH30061 ProKIT
				;				KH30071 ProKIT
3.0 V6 CDTI	135 kW	3 l	07/05→06/08	; 10/05 ->				KH30065 ProKIT
				;				KH30061 ProKIT
				; 10/05 ->				KH30071 ProKIT
<b>VAUXHALL - TIGRA Mk I (S93)</b>								<b>07/94→12/00</b>
1.4 16V	66 kW	1.4 l	07/94→12/00					KH10376 ProKIT
1.6 16V	78 kW	1.6 l	07/94→12/00					KH00005 ProKIT
<b>VAUXHALL - TIGRA TwinTop (X04)</b>								<b>06/04→08/09</b>
1.3 CDTI	51 kW	1.3 l	06/04→08/09					KH10063 ProKIT
1.4	66 kW	1.4 l	06/04→08/09	; 07/08 ->;				KH20118 ProKIT
				;				KH10113 ProKIT
1.8	92 kW	1.8 l	06/04→08/09					KH10063 ProKIT
				; 07/04 ->;				KH20118 ProKIT
				;				KH10113 ProKIT
<b>VAUXHALL - VECTRA (B) Estate, B) Hatchback, B) Saloon)</b>								<b>08/95→07/03</b>
1.6 i (F19)	55 kW	1.6 l	08/95→10/01	; -> 01/99				KH10206 ProKIT
1.6 i (F68)	55 kW	1.6 l	08/95→10/01	; (ABS); Rim Hole Number: 4				KH30054 ProKIT
2.0 Di 16V (F35)	60 kW	2 l	08/95→10/01	; (ABS)				KH30114 ProKIT
1.6 i 16V (F19)	74 kW	1.6 l	08/95→10/01					KH10206 ProKIT
1.6 i 16V (F68)	74 kW	1.6 l	08/95→10/01	; (ABS); Rim Hole Number: 4				KH30054 ProKIT
1.8 i 16V (F19)	85 kW	1.8 l	10/95→09/00	; (ABS)				KH30114 ProKIT
1.8 i 16V (F19)	92 kW	1.8 l	09/00→03/02	; (ABS)				KH30114 ProKIT
1.8 i 16V (F35)	85 kW	1.8 l	11/96→09/00					
1.8 i 16V (F35)	92 kW	1.8 l	09/00→03/02					
1.8 i 16V (F68)	85 kW	1.8 l	10/95→09/00					

<b>VAUXHALL - VECTRA (B) Estate, B) Hatchback, B) Saloon</b>				<b>08/95→07/03</b>		
1.7 TD (F19)	60 kW	1.7 l	10/95→11/96		-> 07/96	KH10206 ProKIT
1.7 TD (F68)	60 kW	1.7 l	10/95→11/96	(ABS)	Rim Hole Number: 4	KH30054 ProKIT
1.8 Dualfuel (F19)	92 kW	1.8 l	09/00→03/02	(ABS)		KH30114 ProKIT
1.8 Dualfuel (F35)	92 kW	1.8 l	09/00→03/02			
1.8 Dualfuel (F68)	92 kW	1.8 l	09/00→07/03			
2.0 Dualfuel (F19)	100 kW	2 l	05/98→01/01			
2.0 Dualfuel (F35)	100 kW	2 l	10/98→01/01			
2.0 Dualfuel (F68)	100 kW	2 l	08/98→01/01			
1.8 i 16V (F35)	85 kW	1.8 l	09/96→09/00	(ABS)	Rim Hole Number: 4	KH30054 ProKIT
1.8 i 16V (F68)	85 kW	1.8 l	09/95→09/00	(ABS)		KH30114 ProKIT
1.8 i 16V (F68)	92 kW	1.8 l	09/00→07/03		-> 03/02	KH10206 ProKIT
				(ABS)	Rim Hole Number: 4	KH30054 ProKIT
				(ABS)		KH30114 ProKIT
2.0 DI 16V (F19)	60 kW	2 l	08/95→10/01		11/96 -> 01/99	KH10206 ProKIT
2.0 Di 16V (F68)	60 kW	2 l	08/95→10/01	(ABS)	Rim Hole Number: 4	KH30054 ProKIT
				(ABS)		KH30114 ProKIT
2.0 DTi 16V (F19)	74 kW	2 l	08/95→10/01		09/97 -> 03/99	KH10206 ProKIT
2.0 DTi 16V (F35)	74 kW	2 l	08/95→10/01	(ABS)	Rim Hole Number: 4	KH30054 ProKIT
2.0 DTi 16V (F68)	74 kW	2 l	06/97→10/01	(ABS)		KH30114 ProKIT
2.0 i 16V (F19)	100 kW	2 l	10/95→01/01		-> 08/00	KH10206 ProKIT
2.0 i 16V (F68)	100 kW	2 l	10/95→01/01	(ABS)	Rim Hole Number: 4	KH30054 ProKIT
				(ABS)		KH30114 ProKIT
2.0 i 16V (F35)	100 kW	2 l	10/95→01/01		11/96 -> 08/00	KH10206 ProKIT
				(ABS)	Rim Hole Number: 4	KH30054 ProKIT
				(ABS)		KH30114 ProKIT
2.2 DTi 16V (F19)	92 kW	2.2 l	08/95→10/01			KH10206 ProKIT
2.2 DTi 16V (F35)	92 kW	2.2 l	08/95→10/01	(ABS)		KH30114 ProKIT
2.2 DTi 16V (F68)	92 kW	2.2 l	08/95→10/01			
2.2 i 16V (F19)	108 kW	2.2 l	08/95→10/01			
2.2 i 16V (F35)	108 kW	2.2 l	08/95→10/01			
2.5 i GSi (F35)	143 kW	2.5 l	05/98→09/99			
2.5 i V6 (F35)	125 kW	2.5 l	11/96→08/00			
2.6 i V6 (F19)	125 kW	2.6 l	09/00→03/02			
2.6 i V6 (F35)	125 kW	2.6 l	09/00→03/02			
2.2 i 16V (F68)	108 kW	2.2 l	09/00→07/03		-> 03/02	KH10206 ProKIT
2.6 i V6 (F68)	125 kW	2.6 l	09/00→07/03	(ABS)		KH30114 ProKIT
2.5 i GSi (F19)	143 kW	2.5 l	03/98→07/00		05/98 -> 09/99	KH10206 ProKIT
2.5 i GSi (F68)	143 kW	2.5 l	03/98→07/00	(ABS)		KH30114 ProKIT
2.5 i V6 (F19)	125 kW	2.5 l	09/95→08/00		10/95 ->	KH10206 ProKIT
2.5 i V6 (F68)	125 kW	2.5 l	09/95→08/00	(ABS)		KH30114 ProKIT
<b>VAUXHALL - VECTRA Mk II (C), C) Estate, C) GTS</b>				<b>01/00→05/09</b>		
1.8	103 kW	1.8 l	01/06→07/08		VIN -> 41999999;	KH30061 ProKIT
2.8 V6 Turbo	188 kW	2.8 l	08/05→08/06		VIN -> 48999999;	
1.8 16V	90 kW	1.8 l	04/02→07/08		-> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
1.8 16V	90 kW	1.8 l	10/03→08/05		01/05 ->; VIN 51000001 ->	
1.9 CDTi	88 kW	1.9 l	04/02→09/08		VIN -> 41999999;	KH30061 ProKIT
1.9 CDTi	88 kW	1.9 l	08/02→07/08		VIN -> 48999999;	
1.9 CDTi	88 kW	1.9 l	04/04→07/08			
1.9 CDTi 16V	110 kW	1.9 l	04/04→07/08			KH30071 ProKIT
1.9 CDTi 16V	110 kW	1.9 l	04/04→08/08			
1.9 CDTi 16V	110 kW	1.9 l	04/04→05/09			
2.0 16V Turbo	129 kW	2 l	10/03→07/08			
2.2 direct	114 kW	2.2 l	01/02→10/08			
2.2 direct	114 kW	2.2 l	10/03→08/05			
3.0 V6 CDTi	130 kW	3 l	10/03→08/05			
3.2 V6	155 kW	3.2 l	10/03→08/05			
1.8 16V	90 kW	1.8 l	08/02→07/08		-> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
					01/05 ->; VIN 51000001 ->	
					VIN -> 41999999;	KH30061 ProKIT
					VIN -> 48999999;	
						KH30071 ProKIT



VAUXHALL - VECTRA Mk II (C), (C) Estate, (C) GTS				01/00→05/09		
1.8 16V Dualfuel	90 kW	1.8 l	04/02→07/08		-> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
1.8 16V Dualfuel	90 kW	1.8 l	08/02→07/08		01/05 -> 09/05; VIN 51000001 ->	
2.0 DTI 16V	74 kW	2 l	04/02→10/08		VIN -> 41999999;	KH30061 ProKIT
2.0 DTI 16V	74 kW	2 l	08/02→07/08		VIN -> 48999999;	
2.0 DTI 16V	74 kW	2 l	10/03→07/08			
2.2 16V	108 kW	2.2 l	01/02→10/08		-> 09/05	KH30071 ProKIT
2.2 16V	108 kW	2.2 l	08/02→07/08			
2.2 DTI 16V	92 kW	2.2 l	08/02→07/08			
2.2 DTI 16V	92 kW	2.2 l	10/03→07/08			
3.2 V6	155 kW	3.2 l	08/02→07/08			
3.2 V6	155 kW	3.2 l	06/03→07/08			
2.0 16V Turbo	129 kW	2 l	01/00→10/08		05/03 -> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
2.0 16V Turbo	129 kW	2 l	03/03→07/08		01/05 ->; VIN 51000001 ->	
					VIN -> 41999999;	KH30061 ProKIT
					VIN -> 48999999;	
					05/03 ->	KH30071 ProKIT
2.2 direct	114 kW	2.2 l	10/03→07/08		VIN -> 41999999;	KH30061 ProKIT
3.0 CDTi	135 kW	3 l	08/05→07/08		VIN -> 48999999;	
					10/05 ->	KH30065 ProKIT
					10/05 ->	KH30071 ProKIT
2.2 DTI 16V	92 kW	2.2 l	04/02→10/08		-> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
					-> 03/04; VIN 51000001 ->	
					VIN -> 41999999;	KH30061 ProKIT
					VIN -> 48999999;	
					-> 03/04	KH30071 ProKIT
2.8 V6 Turbo	169 kW	2.8 l	08/05→05/09		VIN -> 41999999;	KH30061 ProKIT
					VIN -> 48999999;	
					10/05 -> 08/06	KH30065 ProKIT
					10/05 -> 08/06	KH30071 ProKIT
2.8 V6 Turbo	184 kW	2.8 l	02/06→05/09		VIN -> 41999999;	KH30061 ProKIT
2.8 V6 Turbo	188 kW	2.8 l	08/06→05/09		VIN -> 48999999;	
					09/06 ->	KH30065 ProKIT
					09/06 ->	KH30071 ProKIT
3.0 V6 CDTi	130 kW	3 l	06/03→08/05		07/03 -> 12/04; VIN -> 41999999, 48999999;	KH30065 ProKIT
					01/05 ->; VIN 51000001 ->	
					VIN -> 41999999;	KH30061 ProKIT
					VIN -> 48999999;	
					07/03 ->	KH30071 ProKIT
VAUXHALL - VICEROY Saloon				01/80→10/82		
2500	85 kW	2.5 l	01/80→10/82			KH00093 ProKIT
VAUXHALL - VIVARO A Bus (X83)				08/01→07/14		
1.9 DI	59 kW	1.9 l	08/01→12/06		(ABS); VIN -> 3V613233	KH10149 ProKIT
1.9 DTI	74 kW	1.9 l	08/01→12/06		(ABS); VIN -> 3V613233	KH10196 ProKIT
2.0 16V	88 kW	2 l	08/01→12/06		(ABS); VIN -> 3V613233	
2.5 DTI	99 kW	2.5 l	07/03→07/14		VIN 3V613234 ->; (ABS)	KH10115 ProKIT
2.0 CDTi	66 kW	2 l	01/06→07/14		VIN 3V613234 ->; (ABS)	KH10115 ProKIT
2.0 CDTi	84 kW	2 l	08/06→07/14			
2.0 ECOTEC	86 kW	2 l	08/06→07/14			
2.5 CDTi	84 kW	2.5 l	08/06→07/14			
2.5 CDTi	107 kW	2.5 l	01/06→07/14			
VAUXHALL - VIVARO A Platform/Chassis (X83)				04/03→07/14		
2.0 16V	88 kW	2 l	04/03→07/14		VIN -> 3V613233; (ABS)	KH10149 ProKIT
2.5 CDTi	99 kW	2.5 l	04/03→07/06		VIN -> 3V613233; (ABS)	KH10196 ProKIT
					VIN 3V613234 ->; (ABS)	KH10115 ProKIT
						KH10090 ProKIT
2.0 CDTi	66 kW	2 l	01/06→07/14		VIN 3V613234 ->; (ABS)	KH10115 ProKIT
2.0 CDTi	84 kW	2 l	08/06→07/14			KH10090 ProKIT
2.0 ECOTEC	86 kW	2 l	08/06→07/14			
2.5 CDTi	84 kW	2.5 l	08/06→07/14			
2.5 CDTi	107 kW	2.5 l	08/06→07/14			
VAUXHALL - VIVARO A Van (X83)				08/01→07/14		
1.9 DI	59 kW	1.9 l	08/01→12/06		(ABS); VIN -> 3V613233	KH10149 ProKIT
1.9 DTI	74 kW	1.9 l	08/01→12/06		(ABS); VIN -> 3V613233	KH10196 ProKIT
2.0 16V	88 kW	2 l	08/01→12/06		(ABS); VIN -> 3V613233	
2.5 DTI	99 kW	2.5 l	07/03→07/14		VIN 3V613234 ->; (ABS)	KH10115 ProKIT



**VAUXHALL - VIVARO A Van (X83)**

**08/01→07/14**

2.0 CDTI	66 kW	2 l	01/06→07/14	; VIN 3V613234 ->;	KH10115 ProKIT
2.0 CDTI	84 kW	2 l	08/06→07/14		
2.0 ECOTEC	86 kW	2 l	08/06→07/14		
2.5 CDTI	84 kW	2.5 l	08/06→08/08		
2.5 CDTI	107 kW	2.5 l	08/06→07/14		

**VAUXHALL - ZAFIRA A (T98)**

**11/98→08/05**

1.6 16V	74 kW	1.6 l	04/99→08/05	; ; Rim Hole Number: 4	KH30057 ProKIT
1.6 CNG	71 kW	1.6 l	09/01→06/05	; Rim Hole Number: 4;	KH30058 ProKIT
1.6 Dualfuel	74 kW	1.6 l	11/98→08/05	; Rim Hole Number: 4;	KH30059 ProKIT
1.8 16V	85 kW	1.8 l	05/99→08/00	; Rim Hole Number: 5;	KH30059 ProKIT
1.8 16V	92 kW	1.8 l	09/00→08/05	;	KH30114 ProKIT
1.8 Dualfuel	92 kW	1.8 l	09/00→08/05	;	KH30130 ProKIT
2.0 DI 16V	60 kW	2 l	10/99→08/05	;	
2.0 DTI 16V	74 kW	2 l	04/99→08/05		
2.0 GSI Turbo	141 kW	2 l	09/01→06/05		
2.2 16V	108 kW	2.2 l	11/98→08/04		
2.0	147 kW	2 l	06/02→06/05	; ; Rim Hole Number: 4	KH30057 ProKIT
				; Rim Hole Number: 4;	KH30058 ProKIT
				; Rim Hole Number: 5;	KH30059 ProKIT
				;	KH30114 ProKIT

**VAUXHALL - ZAFIRA Mk II (B) (A05)**























































**04/05→11/14**

1.6	77 kW	1.6 l	07/05→11/14		KH30046 ProKIT
1.8	88 kW	1.8 l	04/13→11/14	; Rim Hole Number: 5	KH30044 ProKIT
1.8	103 kW	1.8 l	04/05→11/14	; Rim Hole Number: 5	KH30044 ProKIT
1.6	85 kW	1.6 l	12/07→11/14	; Rim Hole Number: 5	KH30044 ProKIT
1.7 CDTI	81 kW	1.7 l	04/09→11/14	; VIN 62034066, 6G019310 ->	KH30084 ProKIT
				; Rim Hole Number: 5	KH30044 ProKIT
1.7 CDTI	92 kW	1.7 l	01/08→11/14	; OE 16 03 254, 93178652	KH30046 ProKIT
				; OE 16 03 841, 93188477	KH30084 ProKIT
1.9 CDTI	88 kW	1.9 l	07/05→11/14	; VIN -> 62034065, 6G019309	KH30046 ProKIT
2.0	147 kW	2 l	07/05→11/14	; VIN 62034066, 6G019310 ->	KH30084 ProKIT
2.2	110 kW	2.2 l	07/05→11/14	; Rim Hole Number: 5	KH30044 ProKIT
1.9 CDTI	110 kW	1.9 l	07/05→11/14		KH30074 ProKIT
2.0	176 kW	2 l	01/06→11/14	; Rim Hole Number: 5	KH30044 ProKIT

**VAUXHALL - ZAFIRA Mk III (P12)**

**10/11→08/18**

1.4 (75)	88 kW	1.4 l	10/11→08/18		KH30089 ProKIT
1.4 (75)	103 kW	1.4 l	10/11→08/18		KH30134 ProKIT
1.6 CNG (75)	110 kW	1.6 l	10/11→08/18	; -> 12/12; VIN -> C29999999	KH30134 ProKIT
1.8 (75)	85 kW	1.8 l	10/11→08/18		
1.8 (75)	103 kW	1.8 l	10/11→08/18		
2.0 CDTi (75)	81 kW	2 l	10/11→08/18		
2.0 CDTi (75)	96 kW	2 l	10/11→08/18		
2.0 CDTi (75)	121 kW	2 l	10/11→08/18		
1.6 CDTi (75)	100 kW	1.6 l	03/13→08/18		KH30089 ProKIT
2.0 BiTurbo CDTI (75)	143 kW	2 l	11/12→08/18		
2.0 CDTi (75)	125 kW	2 l	01/15→08/18		

				   	 13				
<b>VOLVO - 440 (445)</b>						<b>08/88→12/96</b>			
1.6	61 kW	1.6 l	09/88→12/96	 ; 10/91 ->; VIN -> 205699	KH10178 ProKIT				
1.8	66 kW	1.8 l	08/91→07/96	 ; ABS	KH10220 ProKIT				
1.7	64 kW	1.7 l	09/88→12/96	 ; ABS	KH10220 ProKIT				
1.7	70 kW	1.7 l	08/88→07/89						
2.0	80 kW	2 l	08/93→07/96						
1.7	75 kW	1.7 l	08/89→12/96	 ; VIN -> 205699	KH10178 ProKIT				
1.7 Turbo	90 kW	1.7 l	01/91→12/96	 ; ABS	KH10220 ProKIT				
1.8	66 kW	1.8 l	09/95→12/96						
1.9 Turbo-Diesel	66 kW	1.9 l	07/94→12/96						
1.7 Turbo	88 kW	1.7 l	08/88→07/96	 ; 10/88 ->; VIN -> 205699	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
2.0	81 kW	2 l	08/92→07/95	 ; 10/92 ->; VIN -> 205699	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
<b>VOLVO - 460 Sedan (464)</b>						<b>09/88→07/96</b>			
1.6	61 kW	1.6 l	07/92→07/96	 ; VIN -> 205699	KH10178 ProKIT				
1.9 Turbo-Diesel	66 kW	1.9 l	07/94→07/96	 ; ABS	KH10220 ProKIT				
2.0	80 kW	2 l	08/93→07/96						
1.7	64 kW	1.7 l	09/88→07/96	 ; ABS	KH10220 ProKIT				
1.7 Turbo	90 kW	1.7 l	01/91→07/96						
1.7	75 kW	1.7 l	08/89→07/92	 ; 01/90 ->; VIN -> 205699	KH10178 ProKIT				
1.7 Turbo	88 kW	1.7 l	08/89→07/96	 ; ABS	KH10220 ProKIT				
1.8	66 kW	1.8 l	08/91→07/96	 ; 10/91 ->; VIN -> 205699	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
2.0	81 kW	2 l	08/92→07/95	 ; 07/93 ->; VIN -> 205699	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
<b>VOLVO - 480 (482)</b>						<b>04/86→07/96</b>			
1.7	70 kW	1.7 l	08/87→07/89	 ; VIN -> 567102	KH10178 ProKIT				
1.7	80 kW	1.7 l	08/86→07/88	 ; ABS	KH10220 ProKIT				
1.7	75 kW	1.7 l	08/89→07/96	 ; -> 12/91; VIN -> 567102	KH10178 ProKIT				
1.7 Turbo	90 kW	1.7 l	01/91→07/96	 ; ABS	KH10220 ProKIT				
1.7	78 kW	1.7 l	04/86→07/89	 ; 07/86 ->; VIN -> 567102	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
1.7 Turbo	88 kW	1.7 l	08/87→07/96	 ; 04/88 -> 12/91; VIN -> 567102	KH10178 ProKIT				
				 ; ABS	KH10220 ProKIT				
2.0	81 kW	2 l	08/92→09/95	 ; ABS	KH10220 ProKIT				
<b>VOLVO - 850 (854)</b>						<b>06/91→12/96</b>			
2.0	93 kW	2 l	08/94→12/96	 ; VIN -> 219645	KH30128 ProKIT				
2.0	105 kW	2 l	06/91→12/96		KH20164 ProKIT				
2.4	125 kW	2.4 l	08/91→12/96						
2.0 Turbo	155 kW	2 l	08/93→12/96	 ; 01/94 ->; VIN -> 219645	KH30128 ProKIT				
2.3 T5	166 kW	2.3 l	08/93→07/96	 ; 01/94 ->; VIN -> 219645	KH30128 ProKIT				
					KH20164 ProKIT				
2.3 T5-R	184 kW	2.3 l	08/95→12/96	 ; 01/96 ->; VIN -> 219645	KH30128 ProKIT				
2.4	106 kW	2.4 l	08/94→12/96	 ; VIN -> 219645	KH30128 ProKIT				
2.5 TDI	103 kW	2.5 l	08/95→12/96	 ; 02/96 ->; VIN -> 219645	KH30128 ProKIT				
				 ; 10/95 ->	KH20164 ProKIT				
<b>VOLVO - 850 Estate (855)</b>						<b>09/92→12/96</b>			
2.0	93 kW	2 l	08/94→12/96	 ; VIN -> 121429	KH30128 ProKIT				
2.0	105 kW	2 l	02/93→12/96		KH20164 ProKIT				
2.0 Turbo	155 kW	2 l	02/93→12/96	 ; 01/94 ->; VIN -> 121429	KH30128 ProKIT				
2.3 T5	166 kW	2.3 l	02/93→12/96	 ; 01/94 ->; VIN -> 121429	KH30128 ProKIT				
					KH20164 ProKIT				
2.3 T5-R	184 kW	2.3 l	08/95→12/96	 ; 01/96 ->; VIN -> 121429	KH30128 ProKIT				
2.4	106 kW	2.4 l	08/94→12/96	 ; VIN -> 121429	KH30128 ProKIT				
2.4	125 kW	2.4 l	09/92→12/96	 ; 12/92 ->; VIN -> 121429	KH30128 ProKIT				
					KH20164 ProKIT				
2.4 AWD	142 kW	2.4 l	04/96→12/96	 ; 06/96 ->; VIN -> 121429	KH30128 ProKIT				
2.5 TDI	103 kW	2.5 l	08/95→12/96	 ; 02/96 ->; VIN -> 121429	KH30128 ProKIT				
				10/95 ->; 	KH20164 ProKIT				



**VOLVO - C30 (533)**

**10/06→12/12**

1.6	74 kW	1.6 l	10/06→12/12		KH20088 ProKIT
1.6 D	80 kW	1.6 l	10/06→12/12		
1.6 D2	84 kW	1.6 l	10/10→12/12		
1.8	92 kW	1.8 l	10/06→12/12		
1.8 FlexFuel	92 kW	1.8 l	01/07→12/12		
2.0	107 kW	2 l	10/06→12/12		
2.0 D	100 kW	2 l	10/06→12/12		
2.0 FlexFuel	107 kW	2 l	01/10→12/12		
2.4 i	125 kW	2.4 l	10/06→12/12		
D3	110 kW	2 l	10/10→12/12		
D4	130 kW	2 l	10/10→12/12		
D5	120 kW	2.4 l	10/06→12/12		
D5	132 kW	2.4 l	10/06→12/12		
Electric	82 kW		12/10→12/12		
Electric	89 kW		12/10→12/12		
T5	162 kW	2.5 l	10/06→12/12		
T5	169 kW	2.5 l	03/07→12/12		

**VOLVO - C70 I Convertible / C70 I Coupe (873, 872)**

**03/97→10/05**

2.0	132 kW	2 l	03/97→09/02	; -> 09/98	KH30128 ProKIT
2.0	132 kW	2 l	03/98→10/05		
2.0 T	120 kW	2 l	03/00→09/02		KH30106 ProKIT
2.0 T	120 kW	2 l	03/00→10/05		
2.4	121 kW	2.4 l	03/99→09/02		KH20164 ProKIT
2.4	125 kW	2.4 l	05/99→09/02		
2.0 T	166 kW	2 l	03/97→09/02	; -> 12/98	KH30128 ProKIT
2.0 T	166 kW	2 l	03/98→10/05		
2.3 T5	176 kW	2.3 l	03/98→10/05	; 01/04 -> ; -> 12/98	KH30106 ProKIT KH30128 ProKIT
				; 01/04 ->	KH20164 ProKIT
2.3 T-5	176 kW	2.3 l	03/97→09/02	; 07/98 ->	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; 06/97 ->	KH20164 ProKIT
2.4 T	142 kW	2.4 l	03/97→09/02	; 04/98 -> 04/99	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; 04/98 -> 04/99	KH20164 ProKIT
2.4 T	142 kW	2.4 l	03/98→10/05	; 04/99 ->	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; 04/99 ->	KH20164 ProKIT

**VOLVO - C70 II Convertible (542)**







**03/06→06/13**

2.0 D	100 kW	2 l	01/08→10/09		KH20088 ProKIT
2.4	103 kW	2.4 l	03/06→10/09		
2.4 D	120 kW	2.4 l	03/07→06/13		
2.4 i	125 kW	2.4 l	03/06→10/09		
D3	110 kW	2 l	10/10→06/13		
D4	130 kW	2 l	10/10→06/13		
D5	132 kW	2.4 l	03/06→06/13		
T5	162 kW	2.5 l	03/06→02/07		
T5	169 kW	2.5 l	03/07→06/13		

**VOLVO - S40 I Sedan (644)**

**07/95→12/03**

1.6	77 kW	1.6 l	09/95→08/99	; 04/97 ->	KH10146 ProKIT
				; -> 12/97	KH10212 ProKIT
				; 04/97 ->	KH20146 ProKIT
1.6	80 kW	1.6 l	03/99→12/03		KH10146 ProKIT
1.9 DI	85 kW	1.9 l	07/00→12/03		KH20146 ProKIT
1.8	85 kW	1.8 l	07/95→08/99	; 07/97 -> 04/99	KH10146 ProKIT
				; -> 12/97	KH10212 ProKIT
				; 03/96 -> 04/99	KH20146 ProKIT
1.8	90 kW	1.8 l	03/99→12/03	; 04/99 ->	KH10146 ProKIT
				; 04/99 ->	KH20146 ProKIT
1.8 i	92 kW	1.8 l	03/98→12/03	; 04/98 -> 09/00	KH10146 ProKIT
				; 04/98 -> 09/00	KH20146 ProKIT
1.9 DI	70 kW	1.9 l	03/99→07/00	; -> 04/00	KH10146 ProKIT
				; -> 04/00	KH20146 ProKIT
1.9 DI	75 kW	1.9 l	07/00→12/03	; -> 01/03	KH10146 ProKIT
				; -> 01/03	KH20146 ProKIT

											
<b>VOLVO - S40 I Sedan (644)</b>										<b>07/95→12/03</b>	
1.9 T4	147 kW	1.9 l	05/97→07/00		05/00 ->					KH10146 ProKIT	
					-> 12/97					KH10212 ProKIT	
					05/00 ->					KH20146 ProKIT	
1.9 TD	66 kW	1.9 l	07/95→08/99		07/97 -> 02/99					KH10146 ProKIT	
					-> 12/97					KH10212 ProKIT	
					12/96 -> 02/99					KH20146 ProKIT	
2.0	100 kW	2 l	07/95→12/03		07/97 -> 05/00					KH10146 ProKIT	
					03/96 -> 05/00					KH20146 ProKIT	
2.0	103 kW	2 l	07/95→08/99		07/97 ->					KH10146 ProKIT	
					-> 12/97					KH10212 ProKIT	
					03/96 ->					KH20146 ProKIT	
2.0 T	118 kW	2 l	10/97→12/03		-> 12/97					KH10212 ProKIT	
					-> 05/00					KH10146 ProKIT	
					-> 05/00					KH20146 ProKIT	
<b>VOLVO - S40 II Sedan (544)</b>										<b>01/04→12/12</b>	
1.6	74 kW	1.6 l	01/05→12/12							KH20088 ProKIT	
1.6 D	81 kW	1.6 l	01/05→12/12		ABS					KH30066 ProKIT	
1.8	92 kW	1.8 l	04/04→12/10								
1.8 FlexFuel	92 kW	1.8 l	01/06→12/10								
2.0	107 kW	2 l	10/06→12/12								
2.0 D	100 kW	2 l	01/04→12/10								
2.4	103 kW	2.4 l	01/04→12/10								
2.4	125 kW	2.4 l	01/04→12/12								
2.4 D5	132 kW	2.4 l	03/06→12/10								
T5	162 kW	2.5 l	01/04→12/07								
T5	169 kW	2.5 l	03/07→12/12								
1.6 D2	84 kW	1.6 l	10/10→12/12							KH20088 ProKIT	
2.0 CDI	98 kW	2 l	07/05→12/06								
2.0 F	107 kW	2 l	10/09→12/12								
2.4 CDI	120 kW	2.4 l	03/07→12/10								
D3	110 kW	2 l	10/10→12/12								
D4	130 kW	2 l	10/10→12/12								
T5 AWD	162 kW	2.5 l	04/04→12/07								
T5 AWD	169 kW	2.5 l	03/07→12/10								
<b>VOLVO - S60 I Saloon (384)</b>										<b>07/00→04/10</b>	
2.0 T	132 kW	2 l	07/00→04/10		-> 03/09					KH30115 ProKIT	
2.4	103 kW	2.4 l	07/00→04/10							KH30129 ProKIT	
2.4	125 kW	2.4 l	11/00→04/10								
2.4 Bifuel (CNG)	103 kW	2.4 l	07/01→04/10								
2.4 D	93 kW	2.4 l	03/05→04/10								
2.4 D5	120 kW	2.4 l	01/01→04/10								
2.4 D5	136 kW	2.4 l	03/05→04/10								
2.4 T5	191 kW	2.4 l	04/04→04/10								
2.4 D	96 kW	2.4 l	05/01→04/10		-> 03/05					KH30115 ProKIT	
										KH30129 ProKIT	
2.4 T	147 kW	2.4 l	07/00→04/10		-> 01/03					KH30115 ProKIT	
										KH30129 ProKIT	
2.4 T AWD	147 kW	2.4 l	06/01→04/10		-> 01/03					KH30115 ProKIT	
					-> 01/03					KH30099 ProKIT	
										KH30129 ProKIT	
2.5 T	154 kW	2.5 l	01/03→04/10		-> 03/09					KH30115 ProKIT	
2.5 T AWD	154 kW	2.5 l	07/02→04/10		-> 03/09					KH30099 ProKIT	
										KH30129 ProKIT	
R 2,5 T AWD	221 kW	2.5 l	01/03→04/10		-> 04/07					KH30115 ProKIT	
					-> 04/07					KH30099 ProKIT	
										KH30129 ProKIT	
T5	184 kW	2.3 l	07/00→04/10		-> 12/04					KH30115 ProKIT	
										KH30129 ProKIT	
<b>VOLVO - S60 II (134)</b>										<b>04/10→12/18</b>	
1.5 T3	112 kW	1.5 l	03/15→05/18							KH20073 ProKIT	
2.0 D2	88 kW	2 l	03/15→05/18							KH30139 ProKIT	
2.0 D3	110 kW	2 l	03/15→05/18								
2.0 D4	140 kW	2 l	03/15→05/18								
2.0 D5	165 kW	2 l	03/15→05/18								
2.0 T	132 kW	2 l	05/12→12/15								
2.0 T	149 kW	2 l	04/10→12/11								
2.0 T3	112 kW	2 l	03/15→05/18								





**VOLVO - S60 II (134)**

**04/10→12/18**

2.0 T4	140 kW	2 l	03/15→05/18		KH20073 ProKIT
D3	100 kW	2 l	05/12→12/15		KH30139 ProKIT
D3	120 kW	2 l	04/10→12/14		
D4	120 kW	2 l	04/10→12/14		
D4	133 kW	2 l	09/13→12/15		
D5	151 kW	2.4 l	04/10→12/11		
D5	158 kW	2.4 l	04/11→12/15		
D5	169 kW	2.4 l	04/14→12/15		
DRIVe / D2	84 kW	1.6 l	01/11→12/15		
T3	110 kW	1.6 l	04/10→12/15		
T4	132 kW	1.6 l	04/10→12/15		
T4F	132 kW	1.6 l	04/11→12/15		
T5	177 kW	2 l	04/10→12/14		
T5	180 kW	2 l	09/13→12/18		
T6	225 kW	2 l	09/13→12/18		
2.4 D4 AWD	140 kW	2.4 l	03/15→05/18		KH20073 ProKIT
3.0 T AWD	258 kW	3 l	04/14→12/18		KH30126 ProKIT
D5 AWD	151 kW	2.4 l	04/10→12/11		
D5 AWD	158 kW	2.4 l	04/11→12/15		
D5 AWD	169 kW	2.4 l	04/14→12/15		
T5 AWD	187 kW	2.5 l	08/15→12/18		
T6 AWD	224 kW	3 l	04/10→12/15		
T6 AWD	242 kW	3 l	04/14→12/15		

**VOLVO - S70 Sedan (874)**

**11/96→11/00**

2.0	93 kW	2 l	01/97→11/00	; 07/98 -> 04/99	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; -> 04/99	KH20164 ProKIT
					KH30129 ProKIT
2.0	105 kW	2 l	01/97→11/00		KH30129 ProKIT
2.0 Turbo	155 kW	2 l	01/97→11/00		
2.3 T-5	176 kW	2.3 l	01/97→11/00		
2.4 Bifuel	103 kW	2.4 l	07/99→11/00		
2.0	120 kW	2 l	01/97→11/00	; 07/98 -> 12/98	KH30128 ProKIT
2.0	132 kW	2 l	01/97→11/00	; -> 06/98	KH30128 ProKIT
					KH30129 ProKIT
2.0 Turbo	166 kW	2 l	01/97→11/00	; -> 12/98	KH30128 ProKIT
2.4 Bifuel	106 kW	2.4 l	10/98→11/00		KH30129 ProKIT
2.3 Turbo	184 kW	2.3 l	01/97→11/00	; 07/98 -> 12/99	KH30106 ProKIT
2.4	121 kW	2.4 l	06/98→11/00	; -> 12/98	KH30128 ProKIT
2.5 TDI	103 kW	2.5 l	01/97→11/00	; -> 12/99	KH20164 ProKIT
					KH30129 ProKIT
2.4	103 kW	2.4 l	08/99→11/00	; -> 12/99	KH30106 ProKIT
				; -> 12/99	KH20164 ProKIT
					KH30129 ProKIT
2.4	106 kW	2.4 l	01/97→11/00	; 07/98 -> 01/99	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; -> 01/99	KH20164 ProKIT
					KH30129 ProKIT
2.4	125 kW	2.4 l	01/97→11/00	; 07/98 -> 12/99	KH30106 ProKIT
				; -> 12/99	KH20164 ProKIT
					KH30129 ProKIT
2.4 T5 AWD	142 kW	2.4 l	11/96→04/99	; 04/99 ->	KH30106 ProKIT
2.4 Turbo	142 kW	2.4 l	01/97→11/00	; 07/98 -> 03/99	KH30106 ProKIT
				; -> 12/98	KH30128 ProKIT
				; -> 03/99	KH20164 ProKIT
					KH30129 ProKIT

**VOLVO - S80 I Sedan (184)**

**05/98→07/06**

2.0	120 kW	2 l	06/98→07/06	; ; Housing Type: Aluminium Housing	KH30115 ProKIT
2.0 T	132 kW	2 l	12/99→07/06	; ; Housing Type: Metal Housing	KH30193 ProKIT
2.0 T	166 kW	2 l	06/98→07/06	; ; Housing Type: Metal Housing	
2.3 R	195 kW	2.3 l	04/00→08/05		
2.4 Bifuel (LPG)	103 kW	2.4 l	09/01→07/06		
2.4 LTP	132 kW	2.4 l	06/04→07/06		
2.4 T5 AWD	147 kW	2.4 l	04/00→09/03		
2.5 T	154 kW	2.5 l	03/03→07/06		

				13	i		
<b>VOLVO - S80 I Sedan (184)</b>						<b>05/98→07/06</b>	
2.4	103 kW	2.4 l	01/99→07/06			<b>KH30115 ProKIT</b>	
2.4	125 kW	2.4 l	01/99→07/06			<b>KH30193 ProKIT</b>	
2.4 Bifuel (CNG)	103 kW	2.4 l	09/01→07/06			<b>KH30129 ProKIT</b>	
2.4 D	96 kW	2.4 l	10/01→07/06				
2.4 D5	120 kW	2.4 l	08/01→07/06				
2.4 T	147 kW	2.4 l	06/00→07/06				
2.5 TDI	103 kW	2.5 l	01/99→07/06				
2.8 T6	200 kW	2.8 l	05/98→12/01				
2.9	147 kW	2.9 l	03/99→07/06				
2.9	150 kW	2.9 l	05/98→07/06				
3.0	144 kW	3 l	06/01→07/06				
3.0 T6	200 kW	3 l	06/01→07/06				
2.5 T AWD	154 kW	2.5 l	07/03→07/06			<b>KH30115 ProKIT</b>	
						<b>KH30193 ProKIT</b>	
					<b>07/04 -&gt; 02/06</b>	<b>KH30099 ProKIT</b>	
						<b>KH30129 ProKIT</b>	
<b>VOLVO - S80 II Sedan (124)</b>						<b>03/06→12/16</b>	
1.6 D DRIVe	80 kW	1.6 l	01/10→12/11			<b>KH20073 ProKIT</b>	
1.6 DRIVe	84 kW	1.6 l	06/11→01/14			<b>KH30139 ProKIT</b>	
2.0	107 kW	2 l	01/08→09/12				
2.0 Drive- E	180 kW	2 l	12/14→12/16				
2.0 FlexFuel	107 kW	2 l	01/08→12/11				
2.0 T	149 kW	2 l	01/10→05/11				
2.0 T5	162 kW	2 l	01/14→12/16				
2.0 TDi	100 kW	2 l	02/08→03/11				
2.4 D	120 kW	2.4 l	03/06→03/11				
2.4 D	129 kW	2.4 l	01/10→03/11				
2.5 T	147 kW	2.5 l	03/06→12/11				
2.5 T	170 kW	2.5 l	01/10→12/12				
2.5 T	183 kW	2.5 l	09/12→12/16				
2.5 T	187 kW	2.5 l	01/12→04/16				
2.5 T FlexFuel	147 kW	2.5 l	05/08→12/11				
2.5 T FlexFuel	170 kW	2.5 l	01/10→12/11				
3.2	175 kW	3.2 l	03/06→12/10				
3.2	179 kW	3.2 l	01/10→12/14				
D3	100 kW	2 l	05/12→05/14				
D3 / D4	120 kW	2 l	01/10→12/16				
D4	133 kW	2 l	09/13→12/16				
D5	136 kW	2.4 l	03/06→08/09				
D5	151 kW	2.4 l	01/10→12/11				
D5	158 kW	2.4 l	06/11→04/15				
T4	132 kW	1.6 l	10/10→04/14				
T4F	132 kW	1.6 l	05/11→01/14				
T5	177 kW	2 l	10/10→12/16				
T5	180 kW	2 l	09/13→05/14				
3.2 AWD	175 kW	3.2 l	01/07→12/10			<b>KH20073 ProKIT</b>	
3.2 AWD	179 kW	3.2 l	01/10→12/12			<b>KH30126 ProKIT</b>	
4.4 V8 AWD	232 kW	4.4 l	03/06→03/12				
D5 AWD	136 kW	2.4 l	01/07→05/09				
D5 AWD	151 kW	2.4 l	01/10→12/11				
D5 AWD	158 kW	2.4 l	06/11→04/15				
T6 AWD	210 kW	3 l	01/07→12/10				
T6 AWD	224 kW	3 l	10/10→12/16				
<b>VOLVO - V40 Estate (645)</b>						<b>07/95→06/04</b>	
1.6	77 kW	1.6 l	12/95→08/99		<b>09/98 -&gt; 04/99</b>	<b>KH10146 ProKIT</b>	
					<b>-&gt; 12/97</b>	<b>KH10212 ProKIT</b>	
					<b>09/98 -&gt; 04/99</b>	<b>KH20146 ProKIT</b>	
1.6	80 kW	1.6 l	03/99→06/04		<b>-&gt; 04/99</b>	<b>KH10146 ProKIT</b>	
					<b>-&gt; 04/99</b>	<b>KH20146 ProKIT</b>	
1.8	85 kW	1.8 l	07/95→08/99		<b>07/97 -&gt;</b>	<b>KH10146 ProKIT</b>	
2.0	103 kW	2 l	07/95→08/99		<b>-&gt; 12/97</b>	<b>KH10212 ProKIT</b>	
					<b>03/96 -&gt;</b>	<b>KH20146 ProKIT</b>	
1.8	90 kW	1.8 l	03/99→06/04		<b>05/00 -&gt;</b>	<b>KH10146 ProKIT</b>	
					<b>05/00 -&gt;</b>	<b>KH20146 ProKIT</b>	
1.8 i	92 kW	1.8 l	03/98→06/04		<b>04/98 -&gt; 09/00</b>	<b>KH10146 ProKIT</b>	
					<b>04/98 -&gt; 09/00</b>	<b>KH20146 ProKIT</b>	
1.9 DI	70 kW	1.9 l	03/99→07/00		<b>-&gt; 04/00</b>	<b>KH10146 ProKIT</b>	
					<b>-&gt; 04/00</b>	<b>KH20146 ProKIT</b>	
1.9 DI	75 kW	1.9 l	07/00→06/04		<b>-&gt; 01/03</b>	<b>KH10146 ProKIT</b>	
					<b>-&gt; 01/03</b>	<b>KH20146 ProKIT</b>	





**VOLVO - V40 Estate (645)**

**07/95→06/04**

1.9 DI	85 kW	1.9 l	07/00→06/04		KH10146 ProKIT
					KH20146 ProKIT
1.9 T4	147 kW	1.9 l	05/97→07/00	; 06/97 -> 04/00	KH10146 ProKIT
				; -> 12/97	KH10212 ProKIT
				; 06/97 -> 04/00	KH20146 ProKIT
1.9 TD	66 kW	1.9 l	07/95→08/99	; 07/97 -> 02/99	KH10146 ProKIT
				; -> 12/97	KH10212 ProKIT
				; 12/96 -> 02/99	KH20146 ProKIT
2.0	100 kW	2 l	07/95→06/04	; 07/97 -> 05/00	KH10146 ProKIT
				; 03/96 -> 05/00	KH20146 ProKIT
2.0 T	118 kW	2 l	10/97→07/00	; -> 12/97	KH10212 ProKIT
				; -> 05/00	KH10146 ProKIT
				; -> 05/00	KH20146 ProKIT
2.0 T	121 kW	2 l	07/99→06/04	; -> 05/00	KH10146 ProKIT
				; -> 05/00	KH20146 ProKIT
2.0 T4	147 kW	2 l	07/00→06/04	; -> 01/04	KH10146 ProKIT
				; -> 01/04	KH20146 ProKIT

**VOLVO - V50 Wagon (545)**

**12/03→12/12**

1.6	74 kW	1.6 l	01/05→12/12		KH20088 ProKIT
1.6 D	81 kW	1.6 l	01/05→12/11	(ABS)	KH30066 ProKIT
1.8	92 kW	1.8 l	04/04→12/10		
1.8 FlexFuel	92 kW	1.8 l	01/05→12/10		
2.0	107 kW	2 l	10/06→12/12		
2.0 D	100 kW	2 l	04/04→12/10		
2.4	103 kW	2.4 l	04/04→12/10		
2.4	125 kW	2.4 l	04/04→12/10		
2.4 D5	132 kW	2.4 l	03/06→12/10		
2.4 Tdi	120 kW	2.4 l	05/07→12/10		
T5	162 kW	2.5 l	04/04→12/07		
T5	169 kW	2.5 l	03/07→12/12		
1.6 D	80 kW	1.6 l	03/05→12/12		KH20088 ProKIT
1.6 D2	84 kW	1.6 l	01/10→12/12		
1.8 BiFuel	93 kW	1.8 l	01/09→09/10		
2.0 CDI	98 kW	2 l	12/03→12/06		
2.0 D4	96 kW	2 l	07/05→12/06		
2.0 FlexFuel	107 kW	2 l	01/10→12/12		
2.4 AWD	125 kW	2.4 l	08/06→12/09		
D3	110 kW	2 l	10/10→12/12		
D4	130 kW	2 l	10/10→12/12		
T5 AWD	162 kW	2.5 l	04/04→12/07		
T5 AWD	169 kW	2.5 l	03/07→12/10		

**VOLVO - V60 I (155, 157)**































**07/10→12/18**























1.6 DRIVe	84 kW	1.6 l	02/11→12/15		KH20073 ProKIT
2.0 D2	88 kW	2 l	03/15→05/18		KH30139 ProKIT
2.0 D3	110 kW	2 l	03/15→05/18		
2.0 D4	140 kW	2 l	03/15→05/18		
2.0 T	132 kW	2 l	01/14→07/18		
2.0 T	149 kW	2 l	07/10→12/12		
2.0 T4	140 kW	2 l	03/15→05/18		
2.0 T5	162 kW	2 l	01/14→12/17		
2.4 D5	158 kW	2.4 l	04/11→12/15		
D3	100 kW	2 l	05/12→12/15		
D3 / D4	120 kW	2 l	07/10→12/14		
D4	133 kW	2 l	10/13→12/15		
D5	165 kW	2 l	03/15→05/18		
D5	151 kW	2.4 l	07/10→12/11		
D5	169 kW	2.4 l	04/14→12/15		
T3	110 kW	1.6 l	09/10→12/15		
T3	112 kW	2 l	03/15→05/18		
T4	132 kW	1.6 l	09/10→12/15		
T4F	132 kW	1.6 l	04/11→12/15		
T5	157 kW	2 l	10/13→05/18		
T5	176 kW	2 l	08/12→07/14		
T5	177 kW	2 l	09/10→12/14		
T5	180 kW	2 l	10/13→12/18		
T6	225 kW	2 l	10/13→12/18		
2.0 Polestar AWD	270 kW	2 l	06/15→05/18		KH20073 ProKIT
2.4 D5 AWD	158 kW	2.4 l	04/11→12/15		KH30126 ProKIT
2.4 D5 Hybrid AWD	120 kW	2.4 l	03/15→05/18		
2.4 Hybrid D6 AWD	158 kW	2.4 l	06/12→12/15		
3.0 T AWD	258 kW	3 l	04/14→05/18		
D4 AWD	120 kW	2.4 l	05/12→12/15		



















































VOLVO - V60 I (155, 157)				07/10→12/18
D4 AWD	133 kW	2.4 l	10/13→12/15	KH20073 ProKIT
D4 AWD	140 kW	2.4 l	03/15→05/18	KH30126 ProKIT
D5 AWD	151 kW	2.4 l	07/10→12/11	
D5 AWD	169 kW	2.4 l	04/14→12/15	
D6 Hybrid AWD	162 kW	2.4 l	03/15→05/18	
T5 AWD	187 kW	2.5 l	04/15→05/18	
T6 AWD	225 kW	2 l	10/13→12/18	
T6 AWD	224 kW	3 l	07/10→12/15	
T6 AWD	242 kW	3 l	04/14→12/15	
VOLVO - V70 I (875, 876)				12/95→12/00
2.0	93 kW	2 l	12/95→03/00	; 05/97 -> 06/98 KH30128 ProKIT
				; 07/98 -> 04/99 KH30106 ProKIT
				; -> 04/99 KH20164 ProKIT
				KH30129 ProKIT
2.0	105 kW	2 l	12/95→03/00	KH30129 ProKIT
2.0 Turbo	155 kW	2 l	12/95→03/00	
2.0	120 kW	2 l	01/97→12/00	; 05/97 -> 06/98 KH30128 ProKIT
2.0 Turbo AWD	166 kW	2 l	11/96→12/00	
2.0	132 kW	2 l	11/96→03/00	; 05/97 -> 06/98 KH30128 ProKIT
2.0 Turbo	166 kW	2 l	11/96→12/00	KH30129 ProKIT
2.3 AWD	177 kW	2.3 l	04/97→09/98	; 05/97 -> 06/98 KH30128 ProKIT
				; 07/98 -> KH30106 ProKIT
2.3 T-5	176 kW	2.3 l	11/96→12/00	; 05/97 -> 06/98 KH30128 ProKIT
				; 07/98 -> 12/99 KH30106 ProKIT
				; -> 12/99 KH20164 ProKIT
				KH30129 ProKIT
2.3 T-5 AWD	176 kW	2.3 l	01/97→12/00	; 05/97 -> 06/98 KH30128 ProKIT
2.3 T AWD	184 kW	2.3 l	04/97→03/00	; 07/98 -> 04/99 KH30106 ProKIT
2.3 Turbo	184 kW	2.3 l	12/95→03/00	; 05/97 -> 06/98 KH30128 ProKIT
				; 07/98 -> 04/99 KH30106 ProKIT
				KH30129 ProKIT
2.4	103 kW	2.4 l	03/99→12/00	; -> 04/00 KH30106 ProKIT
				; -> 04/00 KH20164 ProKIT
				KH30129 ProKIT
2.4	106 kW	2.4 l	12/95→03/00	; 07/98 -> 04/99 KH30106 ProKIT
				; -> 12/98 KH30128 ProKIT
				; -> 04/99 KH20164 ProKIT
				KH30129 ProKIT
2.4	121 kW	2.4 l	06/98→12/99	; 04/99 -> KH30106 ProKIT
				; -> 12/98 KH30128 ProKIT
				; 04/99 -> KH20164 ProKIT
				KH30129 ProKIT
2.4	125 kW	2.4 l	12/95→05/00	; 07/98 -> 04/00 KH30106 ProKIT
				; -> 12/98 KH30128 ProKIT
				; -> 04/00 KH20164 ProKIT
				KH30129 ProKIT
2.4 Bifuel	103 kW	2.4 l	08/99→12/00	KH30106 ProKIT
				KH20164 ProKIT
				KH30129 ProKIT
2.4 Bifuel	106 kW	2.4 l	05/98→12/99	; -> 04/99 KH30106 ProKIT
				KH30128 ProKIT
				; -> 04/99 KH20164 ProKIT
				KH30129 ProKIT
2.4 Turbo	142 kW	2.4 l	04/96→12/00	; 07/98 -> KH30106 ProKIT
				; -> 12/98 KH30128 ProKIT
				KH20164 ProKIT
				KH30129 ProKIT
2.4 Turbo AWD	142 kW	2.4 l	04/96→12/00	; 07/98 -> 04/00 KH30106 ProKIT
				; -> 12/98 KH30128 ProKIT
				; 04/99 -> 04/00 KH20164 ProKIT
2.4 Turbo AWD	195 kW	2.4 l	03/99→12/00	KH30128 ProKIT













































											
<b>VOLVO - V70 I (875, 876)</b>										<b>12/95→12/00</b>	
2.5 TDI	103 kW	2.5 l	12/95→12/00		05/97 -> 06/98					KH30128 ProKIT	
					07/98 -> 03/00					KH30106 ProKIT	
					-> 03/00					KH20164 ProKIT	
										KH30129 ProKIT	
<b>VOLVO - V70 II (285)</b>										<b>11/99→12/08</b>	
2.0 T	132 kW	2 l	11/99→08/07		-> 04/07					KH30115 ProKIT	
2.4 Bifuel (CNG)	103 kW	2.4 l	09/01→08/07								
2.4 T5	191 kW	2.4 l	04/04→08/07								
2.5 T	154 kW	2.5 l	07/01→08/07								
2.3 T5	184 kW	2.3 l	11/99→12/04							KH30115 ProKIT	
2.4	103 kW	2.4 l	03/00→08/07		01/01 -> 04/07					KH30115 ProKIT	
2.4	125 kW	2.4 l	03/00→08/07							KH30129 ProKIT	
2.4 D	93 kW	2.4 l	04/05→12/08		09/05 -> 03/07					KH30115 ProKIT	
2.4 D	96 kW	2.4 l	07/01→08/07		-> 04/07					KH30115 ProKIT	
2.4 D5	120 kW	2.4 l	01/01→12/08							KH30129 ProKIT	
2.4 D5	136 kW	2.4 l	04/05→12/08								
2.4 D5 AWD	120 kW	2.4 l	07/02→08/07		-> 04/07					KH30115 ProKIT	
2.4 D5 AWD	136 kW	2.4 l	05/05→08/07		-> 04/07					KH30099 ProKIT	
2.5 T AWD	154 kW	2.5 l	07/02→08/07								
R 2,5 T AWD	221 kW	2.5 l	03/03→08/07								
2.4 T	147 kW	2.4 l	11/99→08/03							KH30115 ProKIT	
										KH30129 ProKIT	
2.4 T AWD	147 kW	2.4 l	09/01→08/02							KH30115 ProKIT	
										KH30099 ProKIT	
2.5 TDI	103 kW	2.5 l	11/99→08/07		-> 12/01					KH30115 ProKIT	
										KH30129 ProKIT	
<b>VOLVO - V70 III (135)</b>										<b>04/07→04/16</b>	
1.6 D	80 kW	1.6 l	07/09→12/11							KH20073 ProKIT	
1.6 DRIVE / D2	84 kW	1.6 l	04/11→12/15							KH30139 ProKIT	
1.6 T4F	132 kW	1.6 l	01/11→12/15								
2.0	107 kW	2 l	10/07→12/11								
2.0 D	100 kW	2 l	10/07→12/15								
2.0 FlexiFuel	107 kW	2 l	01/08→12/11								
2.0 GDI	157 kW	2 l	04/12→12/15								
2.0 T	149 kW	2 l	09/09→12/11								
2.4 D	120 kW	2.4 l	04/07→12/10								
2.4 D	129 kW	2.4 l	04/09→12/10								
2.5 T	147 kW	2.5 l	08/07→12/09								
2.5 T	170 kW	2.5 l	04/09→12/12								
2.5 T FlexiFuel	147 kW	2.5 l	05/08→12/09								
2.5 T FlexiFuel	170 kW	2.5 l	04/09→12/11								
3.2	175 kW	3.2 l	08/07→12/10								
3.2	179 kW	3.2 l	04/10→12/14								
D2	88 kW	2 l	03/15→04/16								
D3	100 kW	2 l	10/07→12/15								
D3	110 kW	2 l	03/15→04/16								
D3 / D4	120 kW	2 l	03/10→12/15								
D4	133 kW	2 l	10/13→04/16								
D5	136 kW	2.4 l	04/07→12/09								
D5	151 kW	2.4 l	10/08→12/11								
D5	158 kW	2.4 l	04/11→12/15								
T4	132 kW	1.6 l	10/10→12/15								
T4	140 kW	2 l	03/15→04/16								
T5	177 kW	2 l	01/10→12/14								
T5	180 kW	2 l	10/13→04/16								
3.2 AWD	175 kW	3.2 l	04/07→12/10							KH20073 ProKIT	
3.2 AWD	179 kW	3.2 l	04/10→12/15							KH30126 ProKIT	
D4 AWD	120 kW	2.4 l	10/07→12/15								
D4 AWD	133 kW	2.4 l	10/13→04/16								
D5 AWD	136 kW	2.4 l	04/07→12/09								
D5 AWD	151 kW	2.4 l	12/09→12/11								
D5 AWD	158 kW	2.4 l	04/11→12/15								
T6 AWD	210 kW	3 l	08/07→12/10								
T6 AWD	224 kW	3 l	01/10→12/15								
<b>VOLVO - XC60 I SUV (156)</b>										<b>05/08→12/17</b>	
2.0 T	149 kW	2 l	12/09→12/12							KH20073 ProKIT	
2.4 D	129 kW	2.4 l	04/09→12/10								
2.4 D / D3 / D4 AWD	120 kW	2.4 l	05/08→02/17								
3.2 AWD	175 kW	3.2 l	07/09→12/10								
3.2 AWD	179 kW	3.2 l	03/10→12/15								
D3	100 kW	2 l	04/12→12/15								
D3	110 kW	2 l	03/15→04/17								

													
<b>VOLVO - XC60 I SUV (156)</b>										<b>05/08→12/17</b>			
D3 / D4	120 kW	2 l	03/10→12/14									KH20073 ProKIT	
D4	133 kW	2 l	10/13→12/15										
D4	140 kW	2 l	03/15→02/17										
D4 AWD	133 kW	2.4 l	10/13→12/15										
D4 AWD	140 kW	2.4 l	03/15→02/17										
D5	158 kW	2.4 l	06/11→02/17										
D5 AWD	136 kW	2.4 l	05/08→12/09										
D5 AWD	151 kW	2.4 l	07/09→06/11										
D5 AWD	158 kW	2.4 l	04/11→12/15										
D5 AWD	162 kW	2.4 l	03/15→02/17										
D5 AWD	169 kW	2.4 l	04/14→12/15										
T5	177 kW	2 l	09/10→02/17										
T5	180 kW	2 l	10/13→02/17										
T5 AWD	180 kW	2 l	10/15→02/17										
T6	225 kW	2 l	10/13→02/17										
T6 AWD	225 kW	2 l	10/13→12/17										
T6 AWD	210 kW	3 l	05/08→12/10										
T6 AWD	224 kW	3 l	03/10→02/17										
T6 AWD	242 kW	3 l	04/14→12/15										
<b>VOLVO - XC70 II Estate (136)</b>										<b>04/07→12/16</b>			
2.4 D	129 kW	2.4 l	06/09→12/10									KH20073 ProKIT	
D3	120 kW	2 l	04/10→12/15										
D4	133 kW	2 l	10/13→04/16									KH30139 ProKIT	
T5	180 kW	2 l	10/13→12/16										
2.4 D / D4 AWD	120 kW	2.4 l	08/07→04/16									KH20073 ProKIT	
3.2 AWD	175 kW	3.2 l	08/07→12/11										
3.2 AWD	179 kW	3.2 l	05/10→12/14									KH30126 ProKIT	
D4 AWD	133 kW	2.4 l	10/13→04/16										
D5 AWD	136 kW	2.4 l	04/07→12/09										
D5 AWD	151 kW	2.4 l	04/09→12/11										
D5 AWD	158 kW	2.4 l	04/11→12/15										
D5 AWD	162 kW	2.4 l	03/15→04/16										
T6 AWD	210 kW	3 l	01/08→12/16										
T6 AWD	224 kW	3 l	01/10→04/15										
<b>VOLVO - XC70 CROSS COUNTRY I Wagon (295)</b>										<b>03/00→08/07</b>			
2.4 D5 AWD	136 kW	2.4 l	12/05→08/07		-> 03/07					KH30115 ProKIT			
2.5 T XC AWD	154 kW	2.5 l	09/02→08/07		-> 03/07					KH30099 ProKIT			
2.4 D5 XC AWD	120 kW	2.4 l	09/02→08/07		-> 08/05					KH30115 ProKIT			
					-> 08/05					KH30099 ProKIT			
2.4 T XC AWD	147 kW	2.4 l	03/00→09/02		09/00 ->					KH30115 ProKIT			
					09/00 ->					KH30099 ProKIT			
<b>VOLVO - XC90 I (275)</b>										<b>10/02→12/14</b>			
2.5 T AWD	154 kW	2.5 l	10/02→09/14		VIN -> 367133					KH30123 ProKIT			
2.5 T AWD	154 kW	2.5 l	10/12→09/14		VIN 367134 ->					KH30109 ProKIT			
3.2 AWD	175 kW	3.2 l	03/06→12/10										
3.2 AWD	179 kW	3.2 l	04/10→09/14									KH30060 ProKIT	
D5 AWD	120 kW	2.4 l	10/02→12/06										
D5 AWD	136 kW	2.4 l	04/05→12/10										
D5 AWD	147 kW	2.4 l	01/11→12/14										
T6 AWD	200 kW	2.9 l	10/02→12/06										
V8 AWD	232 kW	4.4 l	01/05→12/10										
D3 / D5	120 kW	2.4 l	04/09→12/14									KH30104 ProKIT	

				      <b>13</b> 	
<b>VW - 181</b>					<b>08/70→02/79</b>
1.6	32 kW	1.6 l	08/70→07/73		KH00067 ProKIT
				 ; 01/73 ->; VIN 1832346525 ->	KH00068 ProKIT
1.6	35 kW	1.6 l	03/73→02/79		KH00067 ProKIT
				 ; VIN 1832346525 ->	KH00068 ProKIT
<b>VW - 1500,1600 / 1500,1600 Hatchback / 1500,1600 Variant (31, 36)</b>					<b>04/61→07/73</b>
1.5	33 kW	1.5 l	04/61→07/73	 ; 03/68 ->; VIN 118857240 ->	KH00067 ProKIT
1.5 L	33 kW	1.5 l	07/68→07/73		KH00067 ProKIT
1.6	40 kW	1.6 l	08/65→07/73	 ; 08/67 ->; AT	KH00068 ProKIT
1.6 TL	40 kW	1.6 l	08/65→07/73	 ; 01/69 ->; MT; Axle: Double Joint RA	
				 ; 03/68 ->; VIN 318189213 ->	KH00067 ProKIT
1.6 L	37 kW	1.6 l	07/64→07/73	 ; 08/67 ->; AT	KH00068 ProKIT
1.6 L	40 kW	1.6 l	08/65→07/73	 ; 01/69 ->; MT; Axle: Double Joint RA	
<b>VW - AMAROK (2HA, 2HB, S1B, S6B, S7A, S7B)</b>					<b>09/10→</b>
2.0 BiTDI	120 kW	2 l	09/10→08/12		KH10004 ProKIT
2.0 BiTDI	132 kW	2 l	11/11→		KH10367 ProKIT
2.0 BiTDI 4motion	120 kW	2 l	09/10→08/12		
2.0 BiTDI 4motion	132 kW	2 l	11/11→		
2.0 TDI	90 kW	2 l	09/10→10/13		
2.0 TDI	103 kW	2 l	07/12→10/16		
2.0 TDI 4motion	90 kW	2 l	09/10→10/13		
2.0 TDI 4motion	103 kW	2 l	06/12→10/16		
2.0 TSI	118 kW	2 l	12/10→10/16		
<b>VW - ARTEON / ARTEON SHOOTING BRAKE (3H7, 3H8, 3H9)</b>					<b>03/17→07/20</b>
1.5 TSi	110 kW	1.5 l	08/20→		KH30014 ProKIT
2.0 TDI	110 kW	2 l	09/20→		
2.0 TDI	140 kW	2 l	09/20→		
2.0 TDI	147 kW	2 l	09/20→		
2.0 TDI 4motion	147 kW	2 l	09/20→		
2.0 TSi 4motion	200 kW	2 l	09/20→		
2.0 TSi 4motion	200 kW	2 l	04/18→		
2.0 TSi 4motion	206 kW	2 l	06/20→		
1.5 TSi	110 kW	1.5 l	11/17→07/19		KH30014 ProKIT
2.0 TDI	110 kW	2 l	03/17→11/19	 ; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TDI	130 kW	2 l	11/17→07/20		
2.0 TDI	140 kW	2 l	05/17→06/20		
2.0 TSi	140 kW	2 l	05/17→		
2.0 TDI 4motion	140 kW	2 l	05/17→06/20		KH30014 ProKIT
2.0 TDI 4motion	176 kW	2 l	03/17→07/20		KH30049 ProKIT
2.0 TSi 4motion	206 kW	2 l	04/17→06/20		
2.0 TDI 4motion	140 kW	2 l	09/20→	 ; 	KH30014 ProKIT
<b>VW - BEETLE</b>					<b>01/60→12/85</b>
1200 1.2 (11)	25 kW	1.2 l	01/60→12/85	 ; 03/68 -> 12/74; VIN 118857240 ->	KH00067 ProKIT
				 ; 01/75 -> 12/78; 	
				 ; 01/75 -> 12/78; AT	KH00068 ProKIT
1300 1.3	27 kW	1.3 l	08/65→07/70	 ; 03/68 ->; VIN 118857240 ->	KH00067 ProKIT
1300 1.3 (11)	29 kW	1.3 l	08/65→07/75	 ; 01/69 ->; AT	KH00068 ProKIT
1300 1.3 (11)	32 kW	1.3 l	01/70→01/73		KH00067 ProKIT
				 ; AT	KH00068 ProKIT
1302 1.2 (11)	25 kW	1.2 l	08/69→08/72		KH00067 ProKIT
1302 1.3 (11)	32 kW	1.3 l	08/70→08/72		KH00068 ProKIT
1302 1.6 (11)	37 kW	1.6 l	01/70→01/73		
1302 1.3	29 kW	1.3 l	08/70→07/75		KH00067 ProKIT
1302 1.6	35 kW	1.6 l	07/71→07/74	 ; -> 12/72	KH00068 ProKIT
1303 1.2 (13)	25 kW	1.2 l	07/72→02/76		KH00068 ProKIT
1303 1.3 (13)	32 kW	1.3 l	08/72→07/75	 ; VIN 118857240->	KH00067 ProKIT
				 ; AT	KH00068 ProKIT
1303 1.6 (13)	35 kW	1.6 l	08/72→12/79		KH00067 ProKIT
1303 LS, S 1.6 (13)	37 kW	1.6 l	08/72→12/79	 ; -> 12/78	KH00068 ProKIT
1500 1.5 (11)	32 kW	1.5 l	08/66→11/73	 ; 03/68 ->; VIN 118857240 ->	KH00067 ProKIT
				 ; 01/68 -> 12/70; AT	KH00068 ProKIT
1500 1.6	37 kW	1.6 l	07/70→01/73		KH00067 ProKIT

<b>VW - BEETLE (5C1, 5C2)</b>				<b>04/11→07/19</b>	
1.2 TSI	77 kW	1.2 l	07/11→07/19		KH30002 ProKIT
1.2 TSI 16V	77 kW	1.2 l	12/14→07/19		KH20004 ProKIT
1.4 TSI	110 kW	1.4 l	12/14→07/19	PR 0N4; Axle: Independent wheel suspension; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	118 kW	1.4 l	10/11→07/16		KH20003 ProKIT
1.6 TDI	77 kW	1.6 l	10/11→07/16	PR 0N9; Axle: Rigid Axle; Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 TDI	81 kW	2 l	06/14→09/18		
2.0 TDI	103 kW	2 l	04/11→07/16		
2.0 TDI	110 kW	2 l	07/14→09/18		
2.0 TFSI	147 kW	2 l	04/11→07/16		
2.0 TSI	155 kW	2 l	12/12→07/19		
2.0 TSI	162 kW	2 l	12/14→09/18		
2.5	125 kW	2.5 l	04/11→07/19		
1.8 TSI	125 kW	1.8 l	12/13→07/17		KH30002 ProKIT
2.0 TSI	130 kW	2 l	07/17→07/19	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
				; Inner diameter 1 [mm]: 32	KH20004 ProKIT
<b>VW - BEETLE Convertible (1Y7)</b>				<b>09/02→10/10</b>	
1.4	55 kW	1.4 l	01/03→09/10		KH10001 ProKIT
1.6	75 kW	1.6 l	01/03→09/10	(ABS)	KH20010 ProKIT
1.8 T	110 kW	1.8 l	01/03→09/10		
1.9 TDI	74 kW	1.9 l	06/03→09/10		
1.9 TDI	77 kW	1.9 l	07/05→09/10		
2.0	85 kW	2 l	09/02→10/10		
2.5	110 kW	2.5 l	07/05→09/10		
<b>VW - BEETLE Convertible (5C7, 5C8)</b>				<b>12/11→07/19</b>	
1.2 TSI	77 kW	1.2 l	12/11→07/19		KH30002 ProKIT
1.2 TSI 16V	77 kW	1.2 l	12/14→07/19		KH20004 ProKIT
1.4 TSI	110 kW	1.4 l	12/14→09/18	PR 0N4; Axle: Independent wheel suspension; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	118 kW	1.4 l	12/11→07/16		KH20003 ProKIT
1.6 TDI	77 kW	1.6 l	12/11→07/16	PR 0N9; Axle: Rigid Axle; Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 TDI	81 kW	2 l	06/14→09/18		
2.0 TDI	103 kW	2 l	04/12→07/16		
2.0 TDI	110 kW	2 l	09/14→09/18		
2.0 TFSI	147 kW	2 l	12/11→07/16		
2.0 TSI	155 kW	2 l	12/12→07/19		
2.0 TSI	162 kW	2 l	12/14→09/18		
2.5	125 kW	2.5 l	12/11→07/16		
1.8 TSI	125 kW	1.8 l	12/13→12/16		KH30002 ProKIT
2.0 TFSI	157 kW	2 l	01/13→07/16	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 TSI	130 kW	2 l	07/17→07/19	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
<b>VW - BEETLE Convertible (15)</b>				<b>07/64→03/81</b>	
1302,1303 1.6	37 kW	1.6 l	07/70→06/79		KH00067 ProKIT
Karmann 1.3	29 kW	1.3 l	07/64→07/70		
1302 1.3	29 kW	1.3 l	08/70→07/74		KH00067 ProKIT
1302 1.6	34 kW	1.6 l	08/70→07/74	; -> 12/72	KH00068 ProKIT
1303 1.2	25 kW	1.2 l	04/75→12/79		KH00067 ProKIT
1303 1.3	32 kW	1.3 l	07/70→03/81	; -> 12/78	KH00068 ProKIT
1303 1.6	35 kW	1.6 l	08/70→07/74		KH00068 ProKIT
1500 1.5	32 kW	1.5 l	01/66→12/70	; 01/68 ->; AT	KH00068 ProKIT
				; MT	KH10187 ProKIT
1500 1.6	35 kW	1.6 l	07/69→07/70	; AT	KH00068 ProKIT
<b>VW - BORA I Sedan / BORA Variant (1J2, 1J6)</b>				<b>10/98→12/13</b>	
1.4 16V	55 kW	1.4 l	03/00→05/05		KH10001 ProKIT
1.4 16V	55 kW	1.4 l	09/01→05/05	(ABS)	KH20010 ProKIT
1.6	74 kW	1.6 l	10/98→05/05		
1.6	74 kW	1.6 l	05/99→05/05		
1.6	75 kW	1.6 l	08/00→05/05		
1.6 16V	77 kW	1.6 l	02/00→05/05		
1.6 16V	77 kW	1.6 l	05/00→05/05		
1.6 FSI	81 kW	1.6 l	01/02→05/05		
1.8	92 kW	1.8 l	10/98→05/05		
1.8 T	110 kW	1.8 l	05/00→05/05		
1.8 T	132 kW	1.8 l	03/02→05/05		
1.8 T	132 kW	1.8 l	05/02→05/05		
1.9 SDI	50 kW	1.9 l	10/98→05/05		
1.9 TDI	66 kW	1.9 l	10/98→05/05		
1.9 TDI	66 kW	1.9 l	07/04→05/05		
1.9 TDI	74 kW	1.9 l	09/00→05/05		
1.9 TDI	81 kW	1.9 l	10/98→06/01		
1.9 TDI	81 kW	1.9 l	05/99→06/01		
1.9 TDI	85 kW	1.9 l	12/98→01/02		
1.9 TDI	85 kW	1.9 l	05/99→06/01		

				      <b>13</b> 	
<b>VW - BORA I Sedan / BORA Variant (1J2, 1J6)</b>				<b>10/98→12/13</b>	
1.9 TDI	96 kW	1.9 l	11/00→05/05		<b>KH10001</b> ProKIT
1.9 TDI	110 kW	1.9 l	05/00→05/05		<b>KH20010</b> ProKIT
1.9 TDI	110 kW	1.9 l	05/01→05/05	 	<b>KH20010</b> ProKIT
2.0	85 kW	2 l	10/98→12/13		
2.0	85 kW	2 l	05/99→05/05		
2.3 V5	110 kW	2.3 l	10/98→10/00		
2.3 V5	110 kW	2.3 l	05/99→10/00		
2.3 V5	125 kW	2.3 l	10/00→05/05		
1.8 4motion	92 kW	1.8 l	02/99→05/05	 	<b>KH10001</b> ProKIT
1.8 4motion	92 kW	1.8 l	05/99→05/05		
1.9 TDI 4motion	66 kW	1.9 l	11/98→04/02		
1.9 TDI 4motion	74 kW	1.9 l	09/00→05/05		
1.9 TDI 4motion	85 kW	1.9 l	02/99→06/01		
1.9 TDI 4motion	85 kW	1.9 l	05/99→06/01		
1.9 TDI 4motion	96 kW	1.9 l	11/00→05/05		
1.9 TDI 4motion	110 kW	1.9 l	05/00→05/05		
1.9 TDI 4motion	110 kW	1.9 l	05/01→05/05		
2.0 4motion	85 kW	2 l	04/00→05/05		
2.0 4motion	88 kW	2 l	12/99→05/03		
2.3 V5 4motion	110 kW	2.3 l	12/98→10/00		
2.3 V5 4motion	110 kW	2.3 l	05/99→10/00		
2.3 V5 4motion	125 kW	2.3 l	10/00→05/05		
2.8 V6 4motion	150 kW	2.8 l	03/99→05/05		
2.8 V6 4motion	150 kW	2.8 l	05/99→05/05		
2.8 VR6	130 kW	2.8 l	11/98→07/05	 	<b>KH20010</b> ProKIT
<b>VW - CADDY I Sedan (14)</b>				<b>08/82→07/92</b>	
1.5	51 kW	1.5 l	08/82→07/83		<b>KH10186</b> ProKIT
1.6	55 kW	1.6 l	01/83→07/92		<b>KH00002</b> ProKIT
1.8	70 kW	1.8 l	08/85→07/92		
1.6	55 kW	1.6 l	10/82→10/83		<b>KH00002</b> ProKIT
1.6 D	40 kW	1.6 l	08/82→07/92		
<b>VW - CADDY II Box Body/MPV / CADDY II MPV (9K9A, 9K9B)</b>				<b>11/95→01/04</b>	
1.4	44 kW	1.4 l	11/95→06/03	 	<b>KH10055</b> ProKIT
1.4	55 kW	1.4 l	08/00→01/04		<b>KH00002</b> ProKIT
1.4 16V	55 kW	1.4 l	08/00→01/04	  VIN -> 9K-W-503 258	<b>KH00002</b> ProKIT
1.6	55 kW	1.6 l	11/95→05/97	  VIN 9K-W503 259 -> VIN 9K-X-541 900	<b>KH00038</b> ProKIT
1.6	55 kW	1.6 l	06/97→09/00	  VIN 9K-X-541 901 ->	<b>KH20052</b> ProKIT
1.7 SDI	42 kW	1.7 l	07/96→09/00		
1.9 D	47 kW	1.9 l	11/95→01/04		
1.9 SDI	47 kW	1.9 l	11/95→01/04		
1.9 TDI	66 kW	1.9 l	09/96→01/04		
1.9 TDI	66 kW	1.9 l	10/96→01/04		
60 1.4	44 kW	1.4 l	11/95→01/04		
75 1.6	55 kW	1.6 l	11/95→05/97		
75 1.6	55 kW	1.6 l	11/95→09/00		
1.6	65 kW	1.6 l	11/98→12/03	  VIN 9K-X-541 901 ->	<b>KH20052</b> ProKIT
1.8	63 kW	1.8 l	11/95→12/01		
<b>VW - CADDY II Pickup (9U7)</b>				<b>06/96→12/00</b>	
1.6	55 kW	1.6 l	06/96→12/00		<b>KH00003</b> ProKIT
1.9 D	47 kW	1.9 l	06/96→12/00	  03/98 ->	<b>KH10162</b> ProKIT
					<b>KH00003</b> ProKIT
<b>VW - CADDY III Box Body/MPV / CADDY III MPV (2KA, 2KH, 2CA, 2CH, 2KB, 2KJ, 2CB, 2CJ)</b>				<b>03/04→05/15</b>	
1.2 TSI	63 kW	1.2 l	09/10→05/15	  Number of mounting bores: 4	<b>KH30002</b> ProKIT
1.2 TSI	77 kW	1.2 l	09/10→05/15	  Number of mounting bores: 3	<b>KH30048</b> ProKIT
1.4	55 kW	1.4 l	03/04→05/06		<b>KH20042</b> ProKIT
1.4	59 kW	1.4 l	05/06→08/10		
1.6	75 kW	1.6 l	04/04→05/15		
1.6 BiFuel	75 kW	1.6 l	05/11→05/15		
1.6 TDI	55 kW	1.6 l	08/10→05/15		
1.6 TDI	75 kW	1.6 l	08/10→05/15		
1.9 TDI	55 kW	1.9 l	09/05→08/10		
1.9 TDI	77 kW	1.9 l	04/04→08/10		
2.0 EcoFuel	80 kW	2 l	04/06→05/15		
2.0 SDI	51 kW	2 l	03/04→08/10		
2.0 TDI	62 kW	2 l	11/10→05/15		
2.0 TDI	81 kW	2 l	08/10→05/15		
2.0 TDI	103 kW	2 l	09/07→08/10		
2.0 TDI	125 kW	2 l	05/12→05/15		
2.0 TDI 16V	103 kW	2 l	11/10→05/15		
1.6	65 kW	1.6 l	01/05→12/09	  Number of mounting bores: 4	<b>KH30002</b> ProKIT
1.9 D	48 kW	1.9 l	10/05→06/09	  Number of mounting bores: 3	<b>KH30048</b> ProKIT



**VW - CADDY III Box Body/MPV / CADDY III MPV (2KA, 2KH, 2CA, 2CH, 2KB, 2KJ, 2CB, 2CJ)**

03/04→05/15

1.9 TDI 4motion	77 kW	1.9 l	05/08→08/10	; Number of mounting bores: 4	KH30002 ProKIT
1.9 TDI 4motion	77 kW	1.9 l	11/08→08/10		
2.0 TDI 16V 4motion	103 kW	2 l	11/10→05/15		
2.0 TDI 4motion	62 kW	2 l	12/10→05/15		
2.0 TDI 4motion	81 kW	2 l	08/10→05/15		

**VW - CADDY IV Box Body/MPV / CADDY IV MPV / CADDY ALLTRACK Box Body/MPV / CADDY ALLTRACK MPV (SAA, SAH, SAB, SAJ, SAA, SAB)**

05/15→09/20

































1.0 TSI	62 kW	1 l	11/18→		KH30002 ProKIT
1.0 TSI	62 kW	1 l	11/18→07/19		
1.0 TSI	75 kW	1 l	11/15→		KH30002 ProKIT
1.2 TSI	62 kW	1.2 l	06/15→		
1.4 TGI CNG	81 kW	1.4 l	06/15→		
1.4 TSI	92 kW	1.4 l	05/15→		
1.4 TSI	96 kW	1.4 l	07/18→		
1.4 TSI	96 kW	1.4 l	07/18→09/20		
1.4 TSI	96 kW	1.4 l	06/19→		
1.4 TSI	96 kW	1.4 l	06/19→09/20		
1.6	81 kW	1.6 l	11/15→09/20		
1.6 TDI	55 kW	1.6 l	05/15→11/17		
1.6 TDI	75 kW	1.6 l	05/15→		
2.0 TDI	55 kW	2 l	05/15→		
2.0 TDI	75 kW	2 l	05/15→		
2.0 TDI	81 kW	2 l	05/15→		
2.0 TDI	81 kW	2 l	09/15→09/20		
2.0 TDI	103 kW	2 l	05/15→		
2.0 TDI	110 kW	2 l	05/15→		
2.0 TDI 4motion	55 kW	2 l	11/15→07/19		
2.0 TDI 4motion	81 kW	2 l	05/15→09/20		
2.0 TDI 4motion	90 kW	2 l	05/15→09/20		
2.0 TDI 4motion	103 kW	2 l	05/15→09/20		
2.0 TDI 4motion	110 kW	2 l	11/15→09/20		
ABT e-Caddy	83 kW		04/20→		
1.0 TSI	75 kW	1 l	11/15→09/20		KH30002 ProKIT
1.2 TSI	62 kW	1.2 l	06/15→09/20		
1.4 TGI CNG	81 kW	1.4 l	06/15→09/20		KH20004 ProKIT
1.4 TSI	92 kW	1.4 l	05/15→09/20		
1.6 TDI	55 kW	1.6 l	05/15→11/17		
1.6 TDI	75 kW	1.6 l	05/15→09/20		
2.0 TDI	55 kW	2 l	05/15→09/20		
2.0 TDI	75 kW	2 l	05/15→09/20		
2.0 TDI	103 kW	2 l	05/15→09/20		
2.0 TDI	110 kW	2 l	05/15→09/20		
2.0 TDI 4motion	81 kW	2 l	05/15→05/16		
2.0 TDI 4motion	90 kW	2 l	05/15→		
2.0 TDI 4motion	103 kW	2 l	05/15→		
2.0 TDI 4motion	110 kW	2 l	11/15→		

**VW - CC B6 / CC B7 (357, 358)**
















































02/08→12/16

1.4 TSI	110 kW	1.4 l	05/15→12/16		KH30002 ProKIT
1.4 TSI	118 kW	1.4 l	11/11→12/16		
1.4 TSI MultiFuel	118 kW	1.4 l	01/11→01/12	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI MultiFuel	118 kW	1.4 l	11/11→12/16		
1.8 TSI	112 kW	1.8 l	11/08→05/10		
1.8 TSI	112 kW	1.8 l	11/11→12/16		
1.8 TSI	118 kW	1.8 l	06/08→01/12		
1.8 TSI	118 kW	1.8 l	11/11→12/16		
2.0 BlueTDI	105 kW	2 l	05/09→11/10		
2.0 TDI	100 kW	2 l	06/08→05/11		
2.0 TDI	100 kW	2 l	11/11→12/16		
2.0 TDI	103 kW	2 l	06/08→01/12		
2.0 TDI	103 kW	2 l	11/11→12/16		
2.0 TDI	110 kW	2 l	05/15→12/16		
2.0 TDI	120 kW	2 l	05/08→05/11		
2.0 TDI	125 kW	2 l	06/08→01/12		
2.0 TDI	125 kW	2 l	11/11→12/16		
2.0 TDI	130 kW	2 l	12/12→12/16		
2.0 TDI	135 kW	2 l	05/15→12/16		
2.0 TFSI	147 kW	2 l	06/08→01/12		
2.0 TFSI	147 kW	2 l	11/11→12/16		
2.0 TSI	155 kW	2 l	11/10→01/12		
2.0 TSI	155 kW	2 l	11/11→12/16		
































































































				  	 	 13			
<b>VW - CC B6 / CC B7 (357, 358)</b>								<b>02/08→12/16</b>	
2.0 TDI 4motion	103 kW	2 l	08/09→01/12	 			KH30002 ProKIT		
2.0 TDI 4motion	103 kW	2 l	11/11→12/16						
2.0 TDI 4motion	125 kW	2 l	11/09→01/12						
2.0 TDI 4motion	125 kW	2 l	11/11→01/13						
2.0 TDI 4motion	130 kW	2 l	12/12→12/16						
3.6 FSI 4motion	206 kW	3.6 l	06/08→01/12						
3.6 FSI 4motion	220 kW	3.6 l	02/08→12/11						
3.6 FSI 4motion	220 kW	3.6 l	11/11→12/16						
3.6 FSI	206 kW	3.6 l	06/08→01/12		Inner diameter 1 [mm]: 32		KH20004 ProKIT		
<b>VW - CORRADO (53I)</b>								<b>09/88→12/95</b>	
1.8 16V	100 kW	1.8 l	04/89→07/92		ABS		KH10055 ProKIT		
1.8 G60	118 kW	1.8 l	09/88→09/93				KH00003 ProKIT		
2.0 i	85 kW	2 l	04/93→12/95						
2.0 i 16V	100 kW	2 l	08/91→12/95		OE 1H0 498 625		KH10193 ProKIT		
2.9 VR6	140 kW	2.9 l	08/91→12/95				KH00003 ProKIT		
<b>VW - CRAFTER 30-35 Bus / CRAFTER 30-50 Platform/Chassis / CRAFTER 30-50 Van (2E_, 2F_)</b>								<b>04/06→12/16</b>	
2.0 TDI	80 kW	2 l	05/11→12/16				KH30094 ProKIT		
2.0 TDI	100 kW	2 l	05/11→12/16						
2.0 TDI	105 kW	2 l	10/11→12/16						
2.0 TDI	120 kW	2 l	07/11→12/16						
2.5 TDI	65 kW	2.5 l	04/06→07/11						
2.5 TDI	80 kW	2.5 l	04/06→05/13						
2.5 TDI	100 kW	2.5 l	04/06→05/13						
2.5 TDI	120 kW	2.5 l	04/06→07/11						
<b>VW - DERBY (86)</b>								<b>02/77→09/81</b>	
0.9	29 kW	0.9 l	02/77→09/81				KH10187 ProKIT		
1.1	37 kW	1.1 l	02/77→09/81						
1.3	44 kW	1.3 l	02/77→09/81						
<b>VW - DERBY (86C, 80)</b>								<b>08/81→12/84</b>	
1.0	29 kW	1 l	10/81→12/84				KH10187 ProKIT		
1.1	37 kW	1.1 l	10/81→07/83				KH00003 ProKIT		
1.3	37 kW	1.3 l	08/83→12/84				KH00003 ProKIT		
1.3	40 kW	1.3 l	08/83→12/84		-> 10/84		KH10187 ProKIT		
							KH00003 ProKIT		
1.3	44 kW	1.3 l	08/81→07/83		10/81 ->		KH10187 ProKIT		
							KH00003 ProKIT		
1.3	55 kW	1.3 l	09/82→12/84		08/83 -> 10/84		KH10187 ProKIT		
							KH00003 ProKIT		
<b>VW - EOS (1F7, 1F8)</b>								<b>03/06→08/15</b>	
1.4 TSI	90 kW	1.4 l	11/07→08/15				KH30002 ProKIT		
1.4 TSI	118 kW	1.4 l	05/08→08/15						
1.6 FSI	85 kW	1.6 l	06/06→05/08		Inner diameter 1 [mm]: 32		KH20004 ProKIT		
2.0 FSI	110 kW	2 l	03/06→05/08						
2.0 TDI	100 kW	2 l	11/10→08/15						
2.0 TDI	103 kW	2 l	06/06→05/08						
2.0 TDI 16V	103 kW	2 l	05/08→08/15						
2.0 TFSI	147 kW	2 l	03/06→08/15						
2.0 TSI	155 kW	2 l	11/09→08/15						
3.2 V6	184 kW	3.2 l	06/06→05/09						
3.6 V6	191 kW	3.6 l	05/09→11/10						
<b>VW - FOX Hatchback (5Z1, 5Z3, 5Z4)</b>								<b>10/03→08/14</b>	
1.2	40 kW	1.2 l	04/05→07/11		ABS		KH20028 ProKIT		
1.2	44 kW	1.2 l	09/10→12/11				KH30045 ProKIT		
1.4	55 kW	1.4 l	04/05→12/09						
1.4 TDI	51 kW	1.4 l	04/05→12/09		EU		KH20009 ProKIT		
1.6	74 kW	1.6 l	10/03→08/14						
1.6 Total Flex	73 kW	1.6 l	09/07→12/09						
1.6 Total Flex	74 kW	1.6 l	10/03→08/14		ABS		KH20028 ProKIT		
							KH30045 ProKIT		



												
<b>VW - GOLF I / GOLF I Cabriolet (17, 155)</b>											<b>04/74→04/93</b>	
1.1		37 kW	1.1 l	04/74→07/83		VIN -> E299999					KH10186 ProKIT	
1.1		38 kW	1.1 l	08/76→07/80							KH00003 ProKIT	
1.3		44 kW	1.3 l	08/79→07/83								
1.5		51 kW	1.5 l	04/74→12/75								
1.5		51 kW	1.5 l	08/77→07/83								
1.5		51 kW	1.5 l	01/79→11/83								
1.6		55 kW	1.6 l	08/75→02/84								
1.6		81 kW	1.6 l	08/79→07/82								
1.3		40 kW	1.3 l	08/83→07/86							KH00003 ProKIT	
1.3		43 kW	1.3 l	08/82→12/83								
1.5 D		37 kW	1.5 l	08/76→07/80								
1.6		51 kW	1.6 l	08/75→07/77								
1.6		55 kW	1.6 l	08/79→07/83								
1.6		55 kW	1.6 l	01/83→02/84								
1.6 D		40 kW	1.6 l	08/80→07/83								
1.6 GTI		81 kW	1.6 l	08/76→07/82								
1.6 TD		51 kW	1.6 l	03/82→07/83								
1.8		82 kW	1.8 l	08/83→12/92								
1.8 GTI		82 kW	1.8 l	08/82→12/83								
1.6		53 kW	1.6 l	04/86→02/90							KH10186 ProKIT	
1.8		72 kW	1.8 l	08/89→03/93							KH00003 ProKIT	
1.6		55 kW	1.6 l	08/83→04/92		-> 12/84; VIN -> E299999					KH10186 ProKIT	
1.8		66 kW	1.8 l	08/83→09/92							KH00003 ProKIT	
1.8		70 kW	1.8 l	08/83→04/93								
1.8		82 kW	1.8 l	08/82→12/89								
<b>VW - GOLF II (19E, 1G1)</b>											<b>08/83→12/92</b>	
1.0		33 kW	1 l	11/83→08/85		01/84 ->; VIN E300001 ->					KH10060 ProKIT	
1.3		40 kW	1.3 l	08/83→06/87		-> 12/84; VIN -> E299999					KH10186 ProKIT	
1.3		43 kW	1.3 l	08/83→10/86							KH00003 ProKIT	
1.0		37 kW	1 l	08/85→10/91		01/88 ->					KH10055 ProKIT	
1.3 Cat		40 kW	1.3 l	06/86→12/92		-> 12/87; VIN E300001 ->					KH10060 ProKIT	
1.6		51 kW	1.6 l	08/86→07/91							KH00003 ProKIT	
1.6		51 kW	1.6 l	10/86→12/92								
1.6		53 kW	1.6 l	02/86→10/91								
1.8		62 kW	1.8 l	08/86→01/90								
1.8 GTI 16V		95 kW	1.8 l	02/86→10/91								
1.8 GTI 16V		102 kW	1.8 l	02/86→06/90								
1.8 GTI Cat		79 kW	1.8 l	01/87→10/91								
1.8 i Cat		66 kW	1.8 l	08/87→10/91								
1.3		37 kW	1.3 l	08/85→12/87		VIN E300001 ->					KH10060 ProKIT	
1.8 GTI		77 kW	1.8 l	01/85→07/85							KH00003 ProKIT	
1.8 GTI		79 kW	1.8 l	08/85→10/87								
1.6		55 kW	1.6 l	08/83→07/92		01/84 -> 12/87; VIN E300001 ->					KH10060 ProKIT	
1.6 D		37 kW	1.6 l	08/83→10/91		01/88 ->					KH10055 ProKIT	
1.8 GTI		82 kW	1.8 l	08/83→10/91		-> 12/84; VIN -> E299999					KH10186 ProKIT	
											KH00003 ProKIT	
1.6 D		40 kW	1.6 l	08/83→10/91		01/88 ->					KH10055 ProKIT	
1.6 TD		51 kW	1.6 l	08/83→10/91		-> 12/84; VIN -> E299999					KH10186 ProKIT	
1.8		66 kW	1.8 l	08/84→10/91		-> 12/87; VIN E300001 ->					KH10060 ProKIT	
											KH00003 ProKIT	
1.6 TD		44 kW	1.6 l	08/89→10/91							KH10055 ProKIT	
1.6 TD		59 kW	1.6 l	04/89→10/91							KH00003 ProKIT	
1.8 GTI G60		118 kW	1.8 l	04/90→07/91								
1.6 TD		55 kW	1.6 l	08/83→07/85		01/84 ->; VIN E300001 ->					KH10060 ProKIT	
						-> 12/84; VIN -> E299999					KH10186 ProKIT	
1.8		51 kW	1.8 l	08/86→12/88		01/88 ->					KH10055 ProKIT	
						-> 12/87; VIN E300001 ->					KH10060 ProKIT	
1.8		75 kW	1.8 l	09/88→12/92							KH10055 ProKIT	
2.0 GTI		100 kW	2 l	09/89→12/92								
1.8 GTI 16V		100 kW	1.8 l	08/86→07/88		-> 12/87; VIN E300001 ->					KH10060 ProKIT	
1.8 GTI G60 Syncro		118 kW	1.8 l	08/88→12/91							KH10194 ProKIT	
1.8 i Cat Syncro		66 kW	1.8 l	08/87→10/91								
1.8 Syncro		62 kW	1.8 l	08/87→07/88								
1.8 Syncro		66 kW	1.8 l	02/86→07/91								
1.8 Syncro		72 kW	1.8 l	08/88→07/91								
<b>VW - GOLF II Van (19E, 1G1)</b>											<b>08/83→07/91</b>	
1.6 D		40 kW	1.6 l	08/83→07/91		01/88 ->					KH10055 ProKIT	
1.8 i		66 kW	1.8 l	08/87→07/91							KH00003 ProKIT	



				  	 	 13		
<b>VW - GOLF III (1H1)</b>								<b>10/91→09/97</b>
1.4	40 kW	1.4 l	11/91→08/97	 ; 				<b>KH10055</b> ProKIT
1.4	44 kW	1.4 l	10/91→08/97					<b>KH00003</b> ProKIT
1.6	55 kW	1.6 l	09/92→08/97					
1.6	74 kW	1.6 l	07/95→08/97					
1.8	55 kW	1.8 l	11/91→08/97					
1.8	66 kW	1.8 l	11/91→08/97					
1.9 D	47 kW	1.9 l	11/91→08/97					
1.9 SDI	47 kW	1.9 l	07/95→08/97					
1.9 TD, GTD	55 kW	1.9 l	11/91→08/97					
1.9 TDI	66 kW	1.9 l	08/93→08/97					
2.0 GL	79 kW	2 l	08/95→09/97					
Citystromer	20 kW		11/94→08/97					
1.8 Syncro (1HX1)	66 kW	1.8 l	01/93→08/97	 ; 				<b>KH10055</b> ProKIT
1.9 TDI Syncro (1HX1)	66 kW	1.9 l	08/95→08/97					<b>KH10194</b> ProKIT
1.9 TDI	81 kW	1.9 l	04/96→08/97	 ; 				<b>KH10055</b> ProKIT
				 ; Code: Anniversary				<b>KH10193</b> ProKIT
								<b>KH00003</b> ProKIT
2.0	85 kW	2 l	11/91→08/97	 ; not for TECDOC engine number: 4,979; 				<b>KH10055</b> ProKIT
								<b>KH00003</b> ProKIT
2.0 GTI 16V	110 kW	2 l	08/92→08/97					<b>KH10193</b> ProKIT
2.8 VR6	128 kW	2.8 l	01/92→08/97					<b>KH00003</b> ProKIT
2.0 Syncro (1HX1)	85 kW	2 l	08/95→08/97					<b>KH10194</b> ProKIT
2.8 VR6	120 kW	2.8 l	08/95→09/97					<b>KH00003</b> ProKIT
2.9 VR6 Syncro (1HX1)	140 kW	2.9 l	10/94→08/97					<b>KH10193</b> ProKIT
<b>VW - GOLF III Cabriolet (1E7)</b>								<b>07/93→05/98</b>
1.6	74 kW	1.6 l	10/94→02/98					<b>KH10055</b> ProKIT
1.8	55 kW	1.8 l	07/93→05/98					<b>KH00003</b> ProKIT
1.8	66 kW	1.8 l	07/93→05/98					
1.9 TDI	66 kW	1.9 l	08/95→05/98					
1.9 TDI	81 kW	1.9 l	07/96→05/98					
2.0	85 kW	2 l	07/93→05/98					
<b>VW - GOLF III Van (1H1)</b>								<b>08/91→12/97</b>
1.8	66 kW	1.8 l	08/91→12/97	 ; 				<b>KH10055</b> ProKIT
								<b>KH00003</b> ProKIT
<b>VW - GOLF III Variant (1H5)</b>								<b>07/93→04/99</b>
1.4	40 kW	1.4 l	07/93→04/99					<b>KH10055</b> ProKIT
1.4	44 kW	1.4 l	07/93→04/99					<b>KH00003</b> ProKIT
1.6	74 kW	1.6 l	07/94→04/99					
1.8	55 kW	1.8 l	07/93→04/99					
1.8	66 kW	1.8 l	07/93→04/99					
1.9 D	47 kW	1.9 l	07/93→04/99					
1.9 SDI	47 kW	1.9 l	07/95→04/99					
1.9 TD	55 kW	1.9 l	07/93→04/99					
1.9 TDI	66 kW	1.9 l	03/94→04/99					
1.9 TDI	81 kW	1.9 l	04/96→04/99					
2.0	85 kW	2 l	07/93→04/99					
1.8 Syncro	66 kW	1.8 l	10/94→04/99					<b>KH10194</b> ProKIT
1.9 TDI Syncro	66 kW	1.9 l	07/95→04/99					
2.0 Syncro	85 kW	2 l	08/95→04/99					
2.0	79 kW	2 l	08/95→04/96					<b>KH00003</b> ProKIT
<b>VW - GOLF IV (1J1)</b>								<b>08/97→06/05</b>
1.4 16V	55 kW	1.4 l	10/97→05/04					<b>KH10001</b> ProKIT
1.6	74 kW	1.6 l	08/97→05/04	 ; 				<b>KH20010</b> ProKIT
1.6	75 kW	1.6 l	08/00→06/05					
1.6 16V	77 kW	1.6 l	02/00→06/05					
1.6 FSI	81 kW	1.6 l	01/02→06/05					
1.8	92 kW	1.8 l	08/97→06/05					
1.8 T	110 kW	1.8 l	08/97→06/05					
1.9 SDI	50 kW	1.9 l	08/97→06/05					
1.9 TDI	66 kW	1.9 l	10/97→05/04					
1.9 TDI	74 kW	1.9 l	09/00→06/05					
1.9 TDI	81 kW	1.9 l	08/97→05/04					
1.9 TDI	85 kW	1.9 l	12/98→06/01					
1.9 TDI	96 kW	1.9 l	11/00→06/05					
1.9 TDI	110 kW	1.9 l	05/00→06/05					
2.0	85 kW	2 l	07/98→05/04					
2.3 V5	110 kW	2.3 l	08/97→10/00					
2.3 V5	125 kW	2.3 l	10/00→06/05					

				     	
<b>VW - GOLF IV (1J1)</b>				<b>08/97→06/05</b>	
1.8 4motion	92 kW	1.8 l	05/98→06/05	 	<b>KH10001</b> ProKIT
1.9 TDI 4motion	66 kW	1.9 l	07/98→04/02		
1.9 TDI 4motion	74 kW	1.9 l	09/00→06/05		
1.9 TDI 4motion	85 kW	1.9 l	09/99→06/01		
1.9 TDI 4motion	96 kW	1.9 l	11/00→06/05		
1.9 TDI 4motion	110 kW	1.9 l	02/00→06/05		
2.0 4motion	85 kW	2 l	10/00→06/05		
2.3 V5 4motion	110 kW	2.3 l	12/98→10/00		
2.3 V5 4motion	125 kW	2.3 l	10/00→06/05		
2.8 VR6 4motion	150 kW	2.8 l	03/99→06/05		
1.8 T GTI	132 kW	1.8 l	08/01→06/05		<b>KH10001</b> ProKIT
					<b>KH10117</b> ProKIT
				 	<b>KH20010</b> ProKIT
3.2 R32 4motion	177 kW	3.2 l	09/02→06/05	 	<b>KH10001</b> ProKIT
				 	<b>KH10117</b> ProKIT
<b>VW - GOLF IV Cabriolet (1E7)</b>				<b>06/98→06/02</b>	
1.6	74 kW	1.6 l	06/98→06/02		<b>KH00003</b> ProKIT
1.8	55 kW	1.8 l	06/98→06/02		
1.8	66 kW	1.8 l	06/98→06/02		
1.9 TDI	66 kW	1.9 l	06/98→06/02		
1.9 TDI	81 kW	1.9 l	06/98→06/02		
2.0	85 kW	2 l	06/98→06/02		
<b>VW - GOLF IV Variant (1J5)</b>				<b>05/99→06/06</b>	
1.4 16V	55 kW	1.4 l	05/99→06/06		<b>KH10001</b> ProKIT
1.6	74 kW	1.6 l	05/99→04/02		
1.6	75 kW	1.6 l	08/00→06/06	 	<b>KH20010</b> ProKIT
1.6 16V	77 kW	1.6 l	02/00→06/06		
1.6 FSI	81 kW	1.6 l	01/02→06/06		
1.8 T	110 kW	1.8 l	05/00→06/06		
1.9 SDI	50 kW	1.9 l	05/99→06/06		
1.9 TDI	66 kW	1.9 l	05/99→05/06		
1.9 TDI	74 kW	1.9 l	09/00→06/06		
1.9 TDI	81 kW	1.9 l	05/99→06/01		
1.9 TDI	85 kW	1.9 l	08/99→06/01		
1.9 TDI	96 kW	1.9 l	11/00→06/06		
1.9 TDI	110 kW	1.9 l	06/01→06/06		
2.0	85 kW	2 l	05/99→06/06		
2.0 Bi-Fuel	85 kW	2 l	02/02→06/06		
2.3 V5	110 kW	2.3 l	05/99→06/06		
2.3 V5	125 kW	2.3 l	10/00→06/06		
1.8 4motion	92 kW	1.8 l	05/99→06/06	 	<b>KH10001</b> ProKIT
1.9 TDI 4motion	66 kW	1.9 l	05/99→04/02		
1.9 TDI 4motion	74 kW	1.9 l	09/00→06/06		
1.9 TDI 4motion	85 kW	1.9 l	05/99→06/01		
1.9 TDI 4motion	96 kW	1.9 l	11/00→06/06		
1.9 TDI 4motion	110 kW	1.9 l	05/02→06/05		
2.0 4motion	85 kW	2 l	10/00→06/06		
2.0 4motion	88 kW	2 l	12/99→06/06		
2.3 V5 4motion	110 kW	2.3 l	05/99→06/06		
2.3 V5 4motion	125 kW	2.3 l	10/00→06/06		
2.8 V6 4motion	150 kW	2.8 l	05/99→06/06		
<b>VW - GOLF V / GOLF V Variant / GOLF VI (1K1, 1K5, 5K1)</b>				<b>10/03→02/14</b>	
1.2 TSI	63 kW	1.2 l	05/10→11/12	 <b>Number of mounting bores: 4</b>	<b>KH30002</b> ProKIT
1.2 TSI	77 kW	1.2 l	11/08→11/12	 <b>Number of mounting bores: 3</b>	<b>KH30048</b> ProKIT
1.4	59 kW	1.4 l	10/08→11/12		
1.4 16V	55 kW	1.4 l	10/03→05/06	 <b>Inner diameter 1 [mm]: 30</b>	<b>KH20003</b> ProKIT
1.4 16V	59 kW	1.4 l	05/06→11/08	 <b>Inner diameter 1 [mm]: 32</b>	<b>KH20004</b> ProKIT
1.4 FSI	66 kW	1.4 l	10/03→07/06		
1.4 TSI	90 kW	1.4 l	05/07→11/08		
1.4 TSI	90 kW	1.4 l	10/08→11/12		
1.4 TSI	103 kW	1.4 l	05/06→11/08		
1.4 TSI	118 kW	1.4 l	10/08→11/12		
1.4 TSI	125 kW	1.4 l	11/05→11/08		
1.6	75 kW	1.6 l	01/04→11/08		
1.6	75 kW	1.6 l	10/08→11/12		
1.6 BiFuel	75 kW	1.6 l	03/09→11/12		
1.6 FSI	85 kW	1.6 l	10/03→07/08		
1.6 MultiFuel	75 kW	1.6 l	10/07→11/08		
1.6 MultiFuel	75 kW	1.6 l	10/08→11/12		
1.6 TDI	66 kW	1.6 l	02/09→11/12		
1.6 TDI	77 kW	1.6 l	02/09→11/12		
1.8 TSI	118 kW	1.8 l	06/09→01/11		
1.9 TDI	66 kW	1.9 l	05/04→11/08		
1.9 TDI	77 kW	1.9 l	10/03→11/08		
2.0	85 kW	2 l	01/05→11/08		





**VW - GOLF V / GOLF V Variant / GOLF VI (1K1, 1K5, 5K1)**

**10/03→02/14**

2.0	86 kW	2 l	09/09→12/10	; Number of mounting bores: 4	KH30002 ProKIT
2.0 FSI	110 kW	2 l	01/04→11/08	; Number of mounting bores: 3	KH30048 ProKIT
2.0 GTI	147 kW	2 l	10/04→02/09	; Number of mounting bores: 3	KH30048 ProKIT
2.0 GTI	149 kW	2 l	01/10→02/14	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 GTI	169 kW	2 l	09/06→12/08	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 SDI	55 kW	2 l	01/04→11/08		
2.0 TDI	81 kW	2 l	10/08→11/12		
2.0 TDI	100 kW	2 l	10/03→11/08		
2.0 TDI	100 kW	2 l	10/08→11/12		
2.0 TDI	103 kW	2 l	12/04→11/08		
2.0 TDI	103 kW	2 l	10/08→05/13		
2.0 TDI	125 kW	2 l	11/05→11/08		
2.0 TDI	125 kW	2 l	04/09→11/12		
2.0 TDI 16V	103 kW	2 l	10/03→11/08		
2.5	125 kW	2.5 l	05/07→11/08		
Blue E-Motion	65 kW		12/10→11/13		
1.4	59 kW	1.4 l	06/07→07/09	; Number of mounting bores: 4	KH30002 ProKIT
1.4 TSI	90 kW	1.4 l	06/07→07/09	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	103 kW	1.4 l	06/07→07/09		
1.4 TSI	118 kW	1.4 l	07/08→07/09		
1.4 TSI	125 kW	1.4 l	06/07→07/09		
1.6	75 kW	1.6 l	06/07→07/09		
1.6 MultiFuel	75 kW	1.6 l	11/07→07/09		
1.9 TDI	77 kW	1.9 l	06/07→07/09		
2.0 TDI	100 kW	2 l	06/07→07/09		
2.0 TDI	103 kW	2 l	06/07→07/09		
2.0 TDI 16V	103 kW	2 l	06/07→07/09		
2.0 TFSI	147 kW	2 l	06/07→07/09		
2.5	110 kW	2.5 l	06/07→07/09		
2.5	125 kW	2.5 l	01/08→07/09		
1.9 TDI 4motion	77 kW	1.9 l	08/04→11/08	; Number of mounting bores: 4	KH30002 ProKIT
1.9 TDI 4motion	77 kW	1.9 l	01/08→07/09		
2.0 FSI 4motion	110 kW	2 l	08/04→11/08		
2.0 R 4motion	188 kW	2 l	11/09→11/13		
2.0 R 4motion	195 kW	2 l	11/09→05/11		
2.0 R 4motion	199 kW	2 l	11/09→11/12		
2.0 TDI 16V 4motion	103 kW	2 l	08/04→11/08		
2.0 TDI 4motion	103 kW	2 l	01/07→11/08		
2.0 TFSI 4motion	191 kW	2 l	09/11→11/13		
3.2 R32 4motion	184 kW	3.2 l	11/05→11/08		
2.0 GTi	147 kW	2 l	06/09→11/13	; Number of mounting bores: 4	KH30002 ProKIT
2.0 GTi	155 kW	2 l	04/09→11/12	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 GTi	173 kW	2 l	05/11→11/12	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TDI 4motion	103 kW	2 l	05/09→11/12	; Number of mounting bores: 4	KH30002 ProKIT
				; Number of mounting bores: 3	KH30048 ProKIT
2.5	112 kW	2.5 l	01/06→12/08	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
				; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.5	125 kW	2.5 l	07/09→05/13	; Number of mounting bores: 4	KH30002 ProKIT
				; Number of mounting bores: 3	KH30048 ProKIT

**VW - GOLF VI Convertible (517)**

**03/11→05/16**

1.2 TSI	77 kW	1.2 l	03/11→05/16	; Number of mounting bores: 4	KH30002 ProKIT
1.2 TSI 16V	77 kW	1.2 l	11/13→05/16	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.4 TSI	90 kW	1.4 l	11/11→05/16		
1.4 TSI	92 kW	1.4 l	11/13→05/16		
1.4 TSI	110 kW	1.4 l	11/13→05/16		
1.4 TSI	118 kW	1.4 l	03/11→05/16		
1.6 TDI	77 kW	1.6 l	03/11→05/16		
2.0 GTI	155 kW	2 l	05/12→05/16		
2.0 R	195 kW	2 l	01/13→05/16		
2.0 TDI	81 kW	2 l	11/13→05/16		
2.0 TDI	103 kW	2 l	11/11→05/16		
2.0 TDI	110 kW	2 l	11/13→05/16		
2.0 TSI	162 kW	2 l	11/13→05/16		

**VW - GOLF VI Van (5K1\_)**

**10/08→11/12**

1.2 TSi	63 kW	1.2 l	05/10→11/12	; Number of mounting bores: 4	KH30002 ProKIT
1.2 TSi BlueMotion	77 kW	1.2 l	05/09→11/12	; Number of mounting bores: 3	KH30048 ProKIT
1.4 TSi	118 kW	1.4 l	10/08→11/12		
1.6 TDi	66 kW	1.6 l	02/09→11/12	; Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.6 TDi BlueMotion	77 kW	1.6 l	05/09→11/12	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 GTi	155 kW	2 l	02/09→11/12		
2.0 TDi	103 kW	2 l	09/09→11/12		
2.0 TDi	125 kW	2 l	05/10→11/12		
TSi	90 kW	1.4 l	10/08→11/12		
2.0 TSi R 4motion	199 kW	2 l	11/09→11/12	; Number of mounting bores: 4	KH30002 ProKIT
























































**VW - GOLF VI Variant (AJ5)** **07/09→07/14**




















1.2 TSI	63 kW	1.2 l	07/10→07/13		KH30002 ProKIT	
1.2 TSI	77 kW	1.2 l	07/09→07/13	; Inner diameter 1 [mm]: 32	KH20004 ProKIT	
1.4	59 kW	1.4 l	07/09→07/13			
1.4 TSI	90 kW	1.4 l	07/09→07/13			
1.4 TSI	118 kW	1.4 l	07/09→07/13			
1.6	75 kW	1.6 l	07/09→07/13			
1.6 MultiFuel	75 kW	1.6 l	07/10→07/13			
1.6 TDI	66 kW	1.6 l	12/09→07/13			
1.6 TDI	77 kW	1.6 l	07/09→07/13			
2.0 TDI	81 kW	2 l	01/10→07/13			
2.0 TDI	100 kW	2 l	07/09→07/13			
2.0 TDI	103 kW	2 l	07/09→07/13			
2.0 TFSI	147 kW	2 l	07/09→07/13			
1.6 BiFuel	75 kW	1.6 l	07/09→12/10			KH30002 ProKIT
2.0	85 kW	2 l	01/11→07/14			
1.6 TDI 4motion	77 kW	1.6 l	07/09→07/13	;	KH30002 ProKIT	

**VW - GOLF VII / GOLF VII Variant (5G1, BQ1, BE1, BE2, BA5, BV5)** **08/12→**





































1.0 TSI	63 kW	1 l	01/17→07/18	; PR 1LV, 1ZA, 1ZB, 1ZD	KH30014 ProKIT	
1.0 TSI	81 kW	1 l	11/16→	; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT	
1.0 TSI	85 kW	1 l	05/15→			
1.0 TSI	85 kW	1 l	05/15→03/17			
1.2 TSI	63 kW	1.2 l	08/12→03/17			
1.2 TSI	63 kW	1.2 l	05/13→03/17			
1.2 TSI	77 kW	1.2 l	11/12→03/17			
1.2 TSI	77 kW	1.2 l	05/13→			
1.2 TSI	81 kW	1.2 l	04/14→			
1.4 TGI CNG	81 kW	1.4 l	06/13→			
1.4 TGI CNG	81 kW	1.4 l	09/13→			
1.4 TSI	90 kW	1.4 l	11/12→			
1.4 TSI	90 kW	1.4 l	05/13→			
1.4 TSI	92 kW	1.4 l	05/14→			
1.4 TSI	92 kW	1.4 l	05/14→03/17			
1.4 TSI	103 kW	1.4 l	08/12→03/17			
1.4 TSI	103 kW	1.4 l	05/13→03/17			
1.4 TSI	110 kW	1.4 l	05/14→			
1.4 TSI MultiFuel	90 kW	1.4 l	04/13→			
1.4 TSI MultiFuel	90 kW	1.4 l	04/13→03/17			
1.4 TSI MultiFuel	92 kW	1.4 l	12/13→			
1.4 TSI MultiFuel	92 kW	1.4 l	05/14→03/17			
1.5 TSI	96 kW	1.5 l	05/17→08/20			
1.5 TSI	96 kW	1.5 l	07/17→			
1.5 TSI	110 kW	1.5 l	04/17→			
1.6	81 kW	1.6 l	05/14→03/17			
1.6	81 kW	1.6 l	05/14→07/17			
1.6 TDI	66 kW	1.6 l	04/13→07/18			
1.6 TDI	66 kW	1.6 l	05/13→03/17			
1.6 TDI	77 kW	1.6 l	08/12→03/17			
1.6 TDI	77 kW	1.6 l	05/13→03/17			
1.6 TDI	81 kW	1.6 l	01/13→			
1.6 TDI	81 kW	1.6 l	05/13→03/17			
1.6 TDI	85 kW	1.6 l	11/16→			
1.6 TDI	85 kW	1.6 l	11/16→08/20			
2.0 TDI	81 kW	2 l	11/12→			
2.0 TDI	81 kW	2 l	05/13→03/17			
2.0 TDI	105 kW	2 l	08/12→			
2.0 TDI	110 kW	2 l	08/12→			
2.0 TDI	110 kW	2 l	04/13→			
e-Golf	85 kW		03/14→02/17			
e-Golf	100 kW		12/16→			
1.4 GTE Hybrid	110 kW	1.4 l	05/14→		KH30014 ProKIT	
2.0 GTD	135 kW	2 l	04/13→	; Inner diameter 1 [mm]: 30	KH20003 ProKIT	
2.0 GTD	135 kW	2 l	01/15→03/17			
2.0 GTI	155 kW	2 l	11/13→			
2.0 GTI	162 kW	2 l	04/13→			
2.0 GTI	169 kW	2 l	04/13→			
2.0 GTI	180 kW	2 l	03/17→			
2.0 GTI Clubsport	195 kW	2 l	02/16→03/17			
2.0 GTI Clubsport S	228 kW	2 l	09/16→			
1.6 TDI 4motion	77 kW	1.6 l	11/12→03/17		; PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.6 TDI 4motion	77 kW	1.6 l	05/13→03/17			
1.6 TDI 4motion	81 kW	1.6 l	01/13→	; ; PR 1LV, 1ZA, 1ZB, 1ZD	KH30014 ProKIT	
1.6 TDI 4motion	81 kW	1.6 l	05/13→03/17			
1.8 TSI 4motion	132 kW	1.8 l	11/16→			
2.0 R 360S 4motion	265 kW	2 l	09/16→			
2.0 R 4motion	206 kW	2 l	11/13→			
2.0 R 4motion	206 kW	2 l	03/15→03/17			
2.0 R 4motion	213 kW	2 l	12/16→07/18			
2.0 R 4motion	221 kW	2 l	11/13→			
2.0 R 4motion	221 kW	2 l	03/15→03/17			





























									
<b>VW - GOLF VII / GOLF VII Variant (5G1, BQ1, BE1, BE2, BA5, BV5)</b>									<b>08/12→</b>
2.0 R 4motion	228 kW	2 l	12/16→					PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
2.0 TDI 4motion	110 kW	2 l	11/12→08/20						
2.0 TDI 4motion	110 kW	2 l	04/13→05/18						
<b>VW - GOLF VIII / GOLF VIII Variant (CD1, CG5)</b>									<b>07/19→</b>
1.0 eTSI	81 kW	1 l	06/20→					Centering Diameter [mm]: 80	KH30048 ProKIT
1.0 eTSI	81 kW	1 l	09/20→					Centering Diameter [mm]: 85	KH30049 ProKIT
1.0 TSI	66 kW	1 l	02/20→						
1.0 TSI	66 kW	1 l	08/20→						
1.0 TSI	81 kW	1 l	02/20→						
1.0 TSI	81 kW	1 l	08/20→						
1.5 eTSI	96 kW	1.5 l	12/20→						
1.5 eTSI	110 kW	1.5 l	12/19→						
1.5 eTSI	110 kW	1.5 l	12/20→						
1.5 TGI	96 kW	1.5 l	09/20→						
1.5 TSI	96 kW	1.5 l	07/19→						
1.5 TSI	96 kW	1.5 l	08/20→						
1.5 TSI	110 kW	1.5 l	07/19→						
1.5 TSI	110 kW	1.5 l	08/20→						
2.0 TDI	85 kW	2 l	08/19→						
2.0 TDI	85 kW	2 l	08/20→						
2.0 TDI	110 kW	2 l	08/19→						
2.0 TDI	110 kW	2 l	08/20→						
2.0 TDI 4motion	147 kW	2 l	09/20→						
2.0 GTI	180 kW	2 l	08/20→						KH30049 ProKIT
2.0 GTI	180 kW	2 l	09/20→						
2.0 GTI Clubsport	221 kW	2 l	10/20→						
2.0 TSI R 4motion	235 kW	2 l	09/20→						
<b>VW - GOLF ALLTRACK VII Variant (BA5, BV5)</b>									<b>12/14→</b>
1.6 TDI 4motion	81 kW	1.6 l	12/14→					PR 1ZE, 1ZF, 1ZP	KH30048 ProKIT
1.8 TSI 4motion	132 kW	1.8 l	12/14→						
2.0 TDI 4motion	110 kW	2 l	12/14→05/18					PR 1LV, 1ZA, 1ZB, 1ZD	KH30014 ProKIT
2.0 TDI 4motion	135 kW	2 l	12/14→						
<b>VW - GOLF PLUS V (5M1, 521)</b>									<b>12/04→12/13</b>
1.2 TSI	63 kW	1.2 l	05/10→12/13					Number of mounting bores: 4	KH30002 ProKIT
1.2 TSI	77 kW	1.2 l	11/09→12/13					Number of mounting bores: 3	KH30048 ProKIT
1.4 16V	55 kW	1.4 l	01/05→11/06						
1.4 16V	59 kW	1.4 l	05/06→12/13					Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.4 FSI	66 kW	1.4 l	07/05→11/06					Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	118 kW	1.4 l	06/08→12/13						
1.6	75 kW	1.6 l	05/05→12/13						
1.6 BiFuel	75 kW	1.6 l	05/09→12/13						
1.6 MultiFuel	75 kW	1.6 l	11/07→12/13						
1.6 TDI	66 kW	1.6 l	02/09→12/13						
1.6 TDI	77 kW	1.6 l	03/09→12/13						
1.9 TDI	66 kW	1.9 l	05/05→12/08						
1.9 TDI	77 kW	1.9 l	01/05→01/09						
1.4 TSI	90 kW	1.4 l	06/07→12/13					OE 1K0 407 621 C; Number of mounting bores: 4	KH30002 ProKIT
1.4 TSI	103 kW	1.4 l	05/06→06/08					OE 1K0 407 621 E; Number of mounting bores: 3	KH30048 ProKIT
1.4 TSI	125 kW	1.4 l	05/06→06/08						
1.6 FSI	85 kW	1.6 l	12/04→05/08					Inner diameter 1 [mm]: 30	KH20003 ProKIT
2.0 FSI	110 kW	2 l	05/05→06/08					Inner diameter 1 [mm]: 32	KH20004 ProKIT
2.0 TDI	81 kW	2 l	01/09→12/13						
2.0 TDI	96 kW	2 l	05/05→05/07						
2.0 TDI	100 kW	2 l	05/05→12/13						
2.0 TDI	103 kW	2 l	12/05→05/11						
2.0 TDI 16V	103 kW	2 l	01/05→12/13						
<b>VW - GOLF PLUS Van (521)</b>									<b>01/09→08/14</b>
1.2 TSi	77 kW	1.2 l	11/09→08/14					Inner diameter 1 [mm]: 30	KH20003 ProKIT
1.4 TSi	90 kW	1.4 l	01/09→08/14					Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSi	118 kW	1.4 l	01/09→09/12						
1.6 TDi	66 kW	1.6 l	02/09→08/14						
1.6 TDi	77 kW	1.6 l	02/09→08/14						
2.0 TDi	103 kW	2 l	11/09→08/14						
<b>VW - GOLF SPORTSVAN VII (AM1, AN1)</b>									<b>02/14→</b>
1.0 TSI	63 kW	1 l	05/17→					PR 1LV, 1ZA, 1ZB, 1ZD	KH30014 ProKIT
1.0 TSI	81 kW	1 l	05/17→						
1.0 TSI	85 kW	1 l	05/15→						

     					
<b>VW - GOLF SPORTSVAN VII (AM1, AN1)</b>				<b>02/14→</b>	
1.2 TSI	63 kW	1.2 l	05/14→	 PR 0N9; Axle: Rigid Axle; Inner diameter 1 [mm]: 30	
1.2 TSI	81 kW	1.2 l	04/14→		
1.4 TSI	92 kW	1.4 l	04/14→		
1.4 TSI	110 kW	1.4 l	02/14→		
1.4 TSI MultiFuel	92 kW	1.4 l	04/14→		
1.5 TSI	96 kW	1.5 l	05/17→		
1.5 TSI	110 kW	1.5 l	05/17→		
1.6	81 kW	1.6 l	05/14→		
1.6 TDI	66 kW	1.6 l	02/14→		
1.6 TDI	81 kW	1.6 l	02/14→		
1.6 TDI	85 kW	1.6 l	11/16→		
2.0 TDI	81 kW	2 l	05/14→11/17		
2.0 TDI	110 kW	2 l	02/14→		
<b>VW - GOLF VAN VI Variant (AJ5)</b>					<b>07/09→05/14</b>
1.2 TSi	77 kW	1.2 l	09/09→05/14		
1.4 TSi	90 kW	1.4 l	07/09→05/14		
1.4 TSi	118 kW	1.4 l	07/09→10/12		
1.6 TDi	66 kW	1.6 l	12/09→10/12		
1.6 TDi BlueMotion	77 kW	1.6 l	07/09→05/14		
2.0 TDi	103 kW	2 l	07/09→05/14		
<b>VW - JETTA I (1K2)</b>				<b>09/04→10/10</b>	
1.4 TSI	90 kW	1.4 l	05/07→10/10		
1.4 TSI	103 kW	1.4 l	07/06→10/10		
1.4 TSI	118 kW	1.4 l	07/08→10/10	 Inner diameter 1 [mm]: 32	
1.4 TSI	125 kW	1.4 l	07/06→10/10		
1.6	75 kW	1.6 l	09/04→10/10		
1.6 FSI	85 kW	1.6 l	09/05→10/10		
1.6 MultiFuel	75 kW	1.6 l	01/08→10/10		
1.6 TDI	66 kW	1.6 l	12/09→10/10		
1.6 TDI	77 kW	1.6 l	06/09→10/10		
1.9 TDI	74 kW	1.9 l	08/05→10/10		
1.9 TDI	77 kW	1.9 l	08/05→10/10		
2.0	85 kW	2 l	05/05→10/10		
2.0 FSI	110 kW	2 l	08/05→10/10		
2.0 TDI	100 kW	2 l	09/05→10/10		
2.0 TDI	103 kW	2 l	10/05→10/10		
2.0 TDI	125 kW	2 l	10/06→10/10		
2.0 TDI 16V	103 kW	2 l	08/05→10/10		
2.0 TFSI	125 kW	2 l	07/08→10/10		
2.0 TFSI	147 kW	2 l	10/05→10/10		
2.5	110 kW	2.5 l	01/06→10/10		
2.5	125 kW	2.5 l	07/08→10/10		
2.8 VR6	128 kW	2.8 l	10/09→10/10	 Inner diameter 1 [mm]: 32	
<b>VW - JETTA I Sedan (16)</b>				<b>08/78→02/84</b>	
1.1	37 kW	1.1 l	08/79→02/84	 VIN -> E299999	
1.3	44 kW	1.3 l	08/79→02/84		
1.5	51 kW	1.5 l	08/78→02/84		
1.6	63 kW	1.6 l	08/78→02/84		
1.8	82 kW	1.8 l	08/82→02/84		
1.3	43 kW	1.3 l	08/82→02/84		
1.5 D	37 kW	1.5 l	08/78→07/80		
1.6	55 kW	1.6 l	08/81→07/83		
1.6	55 kW	1.6 l	08/82→07/83		
1.6 D	40 kW	1.6 l	08/80→02/84		
1.6 GLI	81 kW	1.6 l	08/78→07/82		
1.6 TD	51 kW	1.6 l	03/82→02/84		
<b>VW - JETTA II Sedan (19E, 1G2, 165)</b>					<b>08/83→12/92</b>
1.3	40 kW	1.3 l	01/84→06/87		 Outer diameter 1 [mm]: 66
1.3	43 kW	1.3 l	01/84→10/86		
1.8	79 kW	1.8 l	08/85→10/87		
1.3 Cat	40 kW	1.3 l	06/87→12/91		
1.6	51 kW	1.6 l	10/86→10/91	 01/88 ->; Outer diameter 1 [mm]: 72; 	
1.6	53 kW	1.6 l	03/86→10/91		
1.6	55 kW	1.6 l	01/84→07/92	 -> 12/87; Outer diameter 1 [mm]: 66	
1.6 D	40 kW	1.6 l	01/84→10/91		
1.6 TD	51 kW	1.6 l	01/84→10/91		
1.8	62 kW	1.8 l	08/86→01/90		
1.8	66 kW	1.8 l	08/84→10/91		
1.8	77 kW	1.8 l	01/85→12/92		
1.8	82 kW	1.8 l	01/84→10/91		
1.8 16V	95 kW	1.8 l	08/86→10/91		
1.8 16V	102 kW	1.8 l	06/87→12/89		
1.8 Cat	66 kW	1.8 l	08/87→10/91		
1.8 Cat	79 kW	1.8 l	01/87→10/91		



				     13 	
<b>VW - JETTA II Sedan (19E, 1G2, 165)</b>					<b>08/83→12/92</b>
1.6 TD	44 kW	1.6 l	01/90→10/91	 ; Outer diameter 1 [mm]: 72; 	<b>KH10055</b> ProKIT
1.6 TD	59 kW	1.6 l	04/89→10/91		<b>KH00003</b> ProKIT
2.0	100 kW	2 l	08/89→07/92		
1.7	57 kW	1.7 l	08/83→07/85	 ; Outer diameter 1 [mm]: 66	<b>KH10060</b> ProKIT
1.8	51 kW	1.8 l	08/86→12/88	 ; 01/88 ->; Outer diameter 1 [mm]: 72; 	<b>KH10055</b> ProKIT
1.8	70 kW	1.8 l	08/84→07/88	 ; -> 12/87; Outer diameter 1 [mm]: 66	<b>KH10060</b> ProKIT
1.8 Syncro	62 kW	1.8 l	08/87→07/88	 ; VIN -> H-999 999; Outer diameter 1 [mm]: 66	<b>KH10060</b> ProKIT
1.8 Syncro	66 kW	1.8 l	08/87→12/88	 ; VIN J-000 001 ->; Outer diameter 1 [mm]: 72	<b>KH10055</b> ProKIT
1.8 Syncro	72 kW	1.8 l	08/88→07/91		
<b>VW - JETTA IV (162, 163, AV3, AV2)</b>					<b>04/10→04/18</b>
1.2 TSI	77 kW	1.2 l	10/10→12/17		<b>KH30002</b> ProKIT
1.2 TSI 16V	77 kW	1.2 l	08/14→12/17	 ; PR 0N4; Axle: Independent wheel suspension;	<b>KH20004</b> ProKIT
1.4 TSI	90 kW	1.4 l	05/11→	Inner diameter 1 [mm]: 32	
1.4 TSI	92 kW	1.4 l	08/14→		
1.4 TSI	110 kW	1.4 l	04/11→	 ; PR 0N9; Axle: Rigid Axle;	<b>KH20003</b> ProKIT
1.4 TSI	110 kW	1.4 l	08/14→	Inner diameter 1 [mm]: 30	
1.4 TSI	118 kW	1.4 l	04/11→		
1.4 TSI Hybrid	110 kW	1.4 l	04/11→		
1.6	63 kW	1.6 l	03/13→		
1.6	77 kW	1.6 l	12/11→		
1.6	81 kW	1.6 l	09/15→		
1.6 TDI	77 kW	1.6 l	04/10→07/15		
1.8 TSI	125 kW	1.8 l	07/14→		
2.0	85 kW	2 l	06/10→12/17		
2.0 TDI	81 kW	2 l	10/10→		
2.0 TDI	103 kW	2 l	02/11→		
2.0 TDI	110 kW	2 l	07/14→		
2.0 TFSI	147 kW	2 l	12/10→		
2.0 TSI	155 kW	2 l	12/12→12/17		
2.5	125 kW	2.5 l	04/10→		
1.6 MPI	66 kW	1.6 l	09/15→04/18		<b>KH30002</b> ProKIT
2.0 Flex	88 kW	2 l	10/10→12/16		
<b>VW - LT 28-35 II Bus / LT 28-46 II Platform/Chassis / LT 28-46 II Van (2DB, 2DE, 2DK, 2DC, 2DF, 2DG, 2DL, 2DM, 2DA, 2DD, 2DH)</b>					<b>05/96→07/06</b>
2.3	105 kW	2.3 l	05/96→07/06		<b>KH00010</b> ProKIT
2.3	105 kW	2.3 l	06/96→07/06	 ; -> 11/01	<b>KH00118</b> ProKIT
2.3	105 kW	2.3 l	05/96→07/06		<b>KH00010</b> ProKIT
2.5 SDI	55 kW	2.5 l	07/96→07/06		
2.5 SDI	55 kW	2.5 l	09/96→07/06		
2.5 TDI	61 kW	2.5 l	05/01→07/06		
2.5 TDI	66 kW	2.5 l	05/99→07/06		
2.5 TDI	70 kW	2.5 l	05/01→07/06		
2.5 TDI	75 kW	2.5 l	05/96→08/99		
2.5 TDI	80 kW	2.5 l	05/99→07/06		
2.8 TDI	116 kW	2.8 l	05/01→06/06		
2.5 TDI	61 kW	2.5 l	05/01→07/06		<b>KH00010</b> ProKIT
2.5 TDI	70 kW	2.5 l	05/01→07/06		<b>KH00118</b> ProKIT
2.5 TDI	80 kW	2.5 l	05/99→07/06		
2.8 TDI	92 kW	2.8 l	07/97→01/02		
2.8 TDI	116 kW	2.8 l	04/02→07/06		
2.5 TDI	66 kW	2.5 l	05/99→07/06		<b>KH00010</b> ProKIT
				 ; -> 04/01	<b>KH00118</b> ProKIT
2.5 TDI	70 kW	2.5 l	05/01→07/06		<b>KH00010</b> ProKIT
				 ; 01/04 ->	<b>KH00118</b> ProKIT
2.5 TDI	75 kW	2.5 l	05/96→08/99		<b>KH00010</b> ProKIT
2.5 TDI	75 kW	2.5 l	06/96→08/99	 ; -> 05/99	<b>KH00118</b> ProKIT
2.8 TDI	96 kW	2.8 l	01/99→07/06		<b>KH00010</b> ProKIT
				 ; -> 01/02	<b>KH00118</b> ProKIT
2.8 TDI	116 kW	2.8 l	04/02→07/06		<b>KH00010</b> ProKIT
				 ; -> 05/03	<b>KH00118</b> ProKIT
<b>VW - LUPO I (6X1, 6E1)</b>					<b>09/98→07/05</b>
1.0	37 kW	1 l	09/98→07/05		<b>KH10358</b> ProKIT
1.0	37 kW	1 l	10/98→05/00		<b>KH20117</b> ProKIT
1.4	44 kW	1.4 l	10/00→07/05		
1.4 16V	55 kW	1.4 l	09/98→07/05		
1.4 16V	74 kW	1.4 l	08/99→07/05		
1.4 FSI	77 kW	1.4 l	02/01→07/05		
1.4 TDI	55 kW	1.4 l	01/99→07/05		
1.6 GTI	92 kW	1.6 l	09/00→07/05		
1.7 SDI	44 kW	1.7 l	09/98→07/05		



     					
<b>VW - LUPO I (6X1, 6E1)</b>				<b>09/98→07/05</b>	
1.2 TDI 3L	45 kW	1.2 l	07/99→07/05	 KH20167 ProKIT  KH20119 ProKIT	
<b>VW - NEW BEETLE (9C1, 1C1)</b>				<b>01/98→09/10</b>	
1.4	55 kW	1.4 l	11/01→09/10	 KH10001 ProKIT	
1.6	74 kW	1.6 l	10/99→09/00	  ABS KH20010 ProKIT	
1.6	75 kW	1.6 l	06/00→09/10		
1.8 T	110 kW	1.8 l	10/99→09/10		
1.8 T	132 kW	1.8 l	11/01→06/05		
1.9 TDI	66 kW	1.9 l	01/98→06/04		
1.9 TDI	74 kW	1.9 l	02/01→09/10		
1.9 TDI	77 kW	1.9 l	07/05→09/10		
2.0	85 kW	2 l	01/98→09/10		
2.3 V5	125 kW	2.3 l	10/00→09/10		
2.5	110 kW	2.5 l	07/05→09/10		
3.2 RSI 4motion (1C9)	165 kW	3.2 l	04/00→05/01	  KH10001 ProKIT	
<b>VW - PASSAT ALLTRACK B7 (365)</b>				<b>01/12→12/14</b>	
1.8 TSI	112 kW	1.8 l	01/12→12/14	 KH30002 ProKIT	
1.8 TSI	118 kW	1.8 l	01/12→12/14	  Inner diameter 1 [mm]: 32 KH20004 ProKIT	
2.0 TDI	103 kW	2 l	01/12→12/14		
2.0 TDI 4motion	103 kW	2 l	01/12→12/14	  KH30002 ProKIT	
2.0 TDI 4motion	125 kW	2 l	01/12→12/14		
2.0 TDI 4motion	130 kW	2 l	01/13→12/14		
2.0 TSI 4motion	155 kW	2 l	01/12→12/14		
<b>VW - PASSAT ALLTRACK B8 Variant (3G5, CB5)</b>				<b>05/15→</b>	
1.4 TSI 4motion	110 kW	1.4 l	05/15→	 KH30014 ProKIT	
2.0 TDI 4motion	110 kW	2 l	05/15→11/17	 KH30049 ProKIT	
2.0 TDI 4motion	135 kW	2 l	07/15→		
2.0 TDI 4motion	140 kW	2 l	05/15→		
2.0 TDI 4motion	176 kW	2 l	05/15→		
2.0 TSI 4motion	162 kW	2 l	07/15→		
2.0 TSI 4motion	200 kW	2 l	08/18→		
2.0 TSI 4motion	206 kW	2 l	11/18→		
2.0 TSI 4motion	206 kW	2 l	11/18→		
<b>VW - PASSAT B1 / PASSAT B1 Variant / PASSAT B2 (32, 33, 32B)</b>				<b>05/73→03/88</b>	
1.3	40 kW	1.3 l	05/73→01/78	  01/74 ->; VIN 3242310590 -> KH10194 ProKIT	
1.3	40 kW	1.3 l	05/73→07/80		
1.3	44 kW	1.3 l	05/73→01/78	 KH00003 ProKIT	
1.3	44 kW	1.3 l	10/73→01/78		
1.5	55 kW	1.5 l	07/73→12/75		
1.5	55 kW	1.5 l	10/73→08/75		
1.5	63 kW	1.5 l	05/73→12/75		
1.5	63 kW	1.5 l	10/73→12/75		
1.3	40 kW	1.3 l	08/80→07/83		 KH10194 ProKIT
1.3	44 kW	1.3 l	01/78→07/80		 KH00003 ProKIT
1.3	44 kW	1.3 l	08/80→07/86		
1.5 D	37 kW	1.5 l	02/77→07/80		
1.5 D	37 kW	1.5 l	08/77→07/80		
1.6	51 kW	1.6 l	08/86→03/88		
1.6	53 kW	1.6 l	02/86→03/88		
1.6	55 kW	1.6 l	02/76→07/80		
1.6	55 kW	1.6 l	09/79→03/88		
1.6	55 kW	1.6 l	08/80→03/88		
1.6	63 kW	1.6 l	08/75→07/80		
1.6	63 kW	1.6 l	01/81→02/83		
1.6 D	40 kW	1.6 l	02/79→07/80		
1.6 D	40 kW	1.6 l	08/80→03/88		
1.6 i	81 kW	1.6 l	06/78→07/80		
1.6 TD	51 kW	1.6 l	04/82→03/88		
1.6 TD	59 kW	1.6 l	05/86→03/88		
1.8	64 kW	1.8 l	05/86→03/88		
1.8	66 kW	1.8 l	01/83→03/88		
1.8	82 kW	1.8 l	12/83→03/88		
1.9	85 kW	1.9 l	01/81→07/83		
2.0	85 kW	2 l	08/83→03/88		
2.2	85 kW	2.2 l	08/85→03/88		
2.2	100 kW	2.2 l	01/85→03/88		
1.6	53 kW	1.6 l	08/75→07/80	 KH00003 ProKIT	
1.6	53 kW	1.6 l	02/76→08/79		
1.6	55 kW	1.6 l	08/79→07/80		
1.6	61 kW	1.6 l	08/75→11/80		
1.6 GLi	81 kW	1.6 l	08/77→07/80		
2.1	85 kW	2.1 l	01/81→12/83		





**VW - PASSAT B2 Saloon (32B) 08/84→03/88**

1.6	51 kW	1.6 l	08/86→03/88		KH10194 ProKIT
1.6	53 kW	1.6 l	01/85→03/88		
1.6	55 kW	1.6 l	08/84→03/88		
1.6 D	40 kW	1.6 l	08/84→03/88		
1.6 TD	51 kW	1.6 l	01/85→03/88		
1.8	64 kW	1.8 l	05/86→03/88		
1.8	66 kW	1.8 l	01/85→03/88		
2.0	85 kW	2 l	08/84→07/85		
2.2	85 kW	2.2 l	01/85→03/88		

**VW - PASSAT B2 Variant (33B) 08/80→12/88**

1.3	40 kW	1.3 l	08/80→07/83		KH10194 ProKIT
1.3	44 kW	1.3 l	08/80→07/86		
1.6	51 kW	1.6 l	08/86→03/88		KH00003 ProKIT
1.6	53 kW	1.6 l	02/86→03/88		
1.6	55 kW	1.6 l	08/80→07/83		
1.6	55 kW	1.6 l	08/83→03/88		
1.6	63 kW	1.6 l	01/81→02/83		
1.6 D	40 kW	1.6 l	08/80→03/88		
1.6 TD	51 kW	1.6 l	04/82→03/88		
1.8	64 kW	1.8 l	05/86→03/88		
1.8	66 kW	1.8 l	01/83→03/88		
1.8	82 kW	1.8 l	12/83→03/88		
1.9	85 kW	1.9 l	01/81→07/83		
2.0	85 kW	2 l	08/83→03/88		
2.2	85 kW	2.2 l	08/85→03/88		
2.2	100 kW	2.2 l	01/85→03/88		
1.8 Syncro	66 kW	1.8 l	01/86→03/88	; Outer diameter 1 [mm]: 68	KH10194 ProKIT
2.0 Syncro	85 kW	2 l	05/84→03/88		
2.2 Syncro	88 kW	2.2 l	08/85→03/88		
2.2 Syncro	88 kW	2.2 l	09/85→12/88		
2.2 Syncro	100 kW	2.2 l	08/84→07/88		
2.1	85 kW	2.1 l	01/81→07/83		KH00003 ProKIT

**VW - PASSAT B3/B4 / PASSAT B3/B4 Variant (3A2, 35I, 3A5, 35I) 02/88→05/97**

1.6	53 kW	1.6 l	04/88→07/89	; ABS	KH10055 ProKIT	
1.6	55 kW	1.6 l	04/88→07/92			
1.6	74 kW	1.6 l	10/94→08/96			
1.6 TD	59 kW	1.6 l	08/88→09/93			
1.8	55 kW	1.8 l	08/90→08/96			
1.8	66 kW	1.8 l	02/88→08/96			
1.8	79 kW	1.8 l	04/88→07/93			
1.8	82 kW	1.8 l	04/88→07/92			
1.8 16V	100 kW	1.8 l	04/88→12/89			
1.8 GL	102 kW	1.8 l	08/91→09/93			
1.9 D	50 kW	1.9 l	05/89→10/93			
2.0	79 kW	2 l	03/95→08/96			
2.0 16V	100 kW	2 l	08/88→09/93			
1.6	53 kW	1.6 l	04/88→07/89	; ABS	KH10055 ProKIT	
1.6	55 kW	1.6 l	04/88→07/91			
1.6 TD	59 kW	1.6 l	08/88→10/93		KH00003 ProKIT	
1.8	79 kW	1.8 l	04/88→07/90			
1.8	82 kW	1.8 l	04/88→07/92			
1.8	102 kW	1.8 l	08/91→09/93			
1.8 16V	100 kW	1.8 l	04/88→12/89			
1.9 D	50 kW	1.9 l	05/89→10/93			
2.0 16V	100 kW	2 l	08/88→09/93			
1.6	74 kW	1.6 l	07/94→12/95			KH00003 ProKIT
1.9 TDI	81 kW	1.9 l	03/96→05/97			
2.0	79 kW	2 l	03/95→08/96			
2.0	85 kW	2 l	10/93→10/96			
2.0 16V	110 kW	2 l	01/94→05/97			
1.8	55 kW	1.8 l	08/90→05/97	; -> 12/93; ABS	KH10055 ProKIT	
1.8	66 kW	1.8 l	02/88→05/97			
1.9 TD	55 kW	1.9 l	03/91→05/97		KH00003 ProKIT	
1.9 TDI	66 kW	1.9 l	10/93→05/97			
2.0	85 kW	2 l	02/90→05/97			
1.8 G60 Syncro	118 kW	1.8 l	08/88→08/96	; VIN -> 31-M-367 757		KH10194 ProKIT
1.8 G60 Syncro	118 kW	1.8 l	08/88→05/97			
2.0 Syncro	81 kW	2 l	09/89→07/92			
2.0 Syncro	85 kW	2 l	03/90→12/96			
2.0 Syncro	85 kW	2 l	10/90→08/96			
2.9 VR6 Syncro	135 kW	2.9 l	01/94→05/97			
1.9 TD	55 kW	1.9 l	03/91→08/96	; -> 12/93; ABS		KH10055 ProKIT
1.9 TDI	66 kW	1.9 l	10/93→08/96			
2.0	85 kW	2 l	02/90→08/96			
1.9 TDI	81 kW	1.9 l	03/96→08/96		KH10193 ProKIT	



**VW - PASSAT B3/B4 / PASSAT B3/B4 Variant (3A2, 35I, 3A5, 35I) 02/88→05/97**

2.8 VR6	128 kW	2.8 l	06/91→08/96	; 01/93 ->; VIN -> 31-N-255 988	KH10055 ProKIT
				; 01/94 ->; VIN 31-N-255 990 ->	KH10193 ProKIT
2.8 VR6	128 kW	2.8 l	06/91→05/97	; 01/94 ->; VIN 31-N-255 990 ->	KH10193 ProKIT
				; -> 12/93; VIN -> 31-N-255 989	KH10055 ProKIT
					KH00003 ProKIT

**VW - PASSAT B5.5 Sedan (3B3) 10/00→11/05**

1.6	75 kW	1.6 l	11/00→05/05		KH10066 ProKIT
1.8 T 20V	110 kW	1.8 l	11/00→05/05		KH10069 ProKIT
1.9 TDI	96 kW	1.9 l	11/00→05/05		KH10069 ProKIT
2.0	85 kW	2 l	11/00→05/05		KH30095 ProKIT
2.0	96 kW	2 l	11/01→05/05		
2.0 TDI	100 kW	2 l	12/03→05/05		
2.3 V5	125 kW	2.3 l	11/00→05/05		
2.5 TDI	110 kW	2.5 l	11/00→05/05		
2.5 TDI	120 kW	2.5 l	05/03→05/05		
1.8	85 kW	1.8 l	11/00→03/05		KH10066 ProKIT
1.8 T	125 kW	1.8 l	02/01→11/05		KH10069 ProKIT
1.8 T 4motion	125 kW	1.8 l	11/03→05/05		KH10069 ProKIT
1.9 TDI 4motion	96 kW	1.9 l	11/00→05/05		
2.0 4motion	85 kW	2 l	11/00→05/05		
2.3 V5 4motion	125 kW	2.3 l	11/00→05/05		
2.5 TDI 4motion	110 kW	2.5 l	11/00→05/05		
2.5 TDI 4motion	132 kW	2.5 l	01/03→05/05		
2.8	140 kW	2.8 l	10/00→05/05		
2.8	142 kW	2.8 l	05/02→05/03		
2.8 4motion	140 kW	2.8 l	10/00→05/05		
2.8 4motion	142 kW	2.8 l	11/00→05/05		
1.9 TDI	74 kW	1.9 l	11/00→05/05		KH10066 ProKIT
				; AT	KH10069 ProKIT
					KH30095 ProKIT
4.0 W8 4motion	202 kW	4 l	09/01→09/04		KH10066 ProKIT
				; VIN -> 3B-3-450 000	KH10069 ProKIT
				; VIN 3B-3-450 001 ->	KH20032 ProKIT

**VW - PASSAT B5.5 Variant / PASSAT B5 Sedan / PASSAT B5 Variant (3B6, 3B2, 3B5) 08/96→08/05**

1.6	74 kW	1.6 l	10/96→11/00		KH10069 ProKIT
1.6	74 kW	1.6 l	06/97→11/00		KH30095 ProKIT
1.6	75 kW	1.6 l	11/00→05/05		KH30095 ProKIT
1.8	92 kW	1.8 l	10/96→11/00		
1.8	92 kW	1.8 l	06/97→11/00		
1.8 T	110 kW	1.8 l	10/96→11/00		
1.8 T	110 kW	1.8 l	05/97→11/00		
1.9 TDI	66 kW	1.9 l	06/97→11/00		
1.9 TDI	81 kW	1.9 l	06/97→11/00		
1.9 TDI	96 kW	1.9 l	11/00→05/05		
2.0	85 kW	2 l	11/00→05/05		
2.0	96 kW	2 l	11/01→05/05		
2.0 TDI	100 kW	2 l	12/03→05/05		
2.3 VR5	125 kW	2.3 l	11/00→05/05		
2.5 TDI	110 kW	2.5 l	07/98→11/00		
2.5 TDI	110 kW	2.5 l	11/00→05/05		
2.5 TDI	120 kW	2.5 l	05/03→05/05		
2.8 V6	132 kW	2.8 l	05/97→09/99		
2.8 V6	142 kW	2.8 l	08/96→11/00		
2.8 V6	142 kW	2.8 l	06/97→11/00		
1.8	85 kW	1.8 l	01/97→11/00		KH10069 ProKIT
1.8	85 kW	1.8 l	06/97→11/00		
1.8 4motion	125 kW	1.8 l	11/03→05/05		
1.8 Syncro/4motion	92 kW	1.8 l	12/96→08/00		
1.8 Syncro/4motion	92 kW	1.8 l	06/97→11/00		
1.8 T	125 kW	1.8 l	05/02→08/05		
1.9 TDI 4motion	96 kW	1.9 l	11/00→05/05		
1.9 TDI Syncro/4motion	81 kW	1.9 l	06/97→08/00		
2.0	88 kW	2 l	04/00→11/00		
2.0 4motion	85 kW	2 l	11/00→05/05		
2.0 4motion	88 kW	2 l	04/00→11/00		
2.3 VR5 4motion	125 kW	2.3 l	11/00→05/05		
2.5 TDI 4motion	110 kW	2.5 l	11/00→05/05		
2.5 TDI 4motion	132 kW	2.5 l	01/03→05/05		
2.5 TDI Syncro/4motion	110 kW	2.5 l	12/98→11/00		
2.8	142 kW	2.8 l	10/00→08/05		
2.8 4motion	140 kW	2.8 l	10/00→05/05		
2.8 4motion	142 kW	2.8 l	11/00→05/05		
2.8 V6	132 kW	2.8 l	09/97→09/99		





















**VW - PASSAT B5.5 Variant / PASSAT B5 Sedan / PASSAT B5 Variant (3B6, 3B2, 3B5) 08/96→08/05**































2.8 V6	140 kW	2.8 l	09/99→11/00		KH10069 ProKIT
2.8 V6 4motion	140 kW	2.8 l	09/99→11/00		
2.8 V6 Syncro/4motion	142 kW	2.8 l	10/96→11/00		
2.8 V6 Syncro/4motion	142 kW	2.8 l	06/97→11/00		
1.8 T 20V	110 kW	1.8 l	11/00→05/05	; AT	KH10069 ProKIT
1.9 TDI	74 kW	1.9 l	11/00→05/05		KH30095 ProKIT
1.9 TDI	85 kW	1.9 l	08/98→11/00		
2.3 VR5	110 kW	2.3 l	10/96→11/00		
2.3 VR5	110 kW	2.3 l	06/97→11/00		
1.9 TDI	66 kW	1.9 l	10/96→11/00	; -> 12/97; VIN 31NZ390 ->	KH10193 ProKIT
1.9 TDI	81 kW	1.9 l	10/96→11/00		KH10069 ProKIT
					KH30095 ProKIT
1.9 TDI	74 kW	1.9 l	02/00→11/00	; AT	KH10069 ProKIT
1.9 TDI 4motion	85 kW	1.9 l	08/99→11/00		
2.3 VR5 Syncro/4motion	110 kW	2.3 l	10/97→11/00		
4.0 W8 4motion	202 kW	4 l	09/01→09/04	; VIN -> 3B-3-450 000	KH10069 ProKIT
				; VIN 3B-3-450 001 ->	KH20032 ProKIT






















**VW - PASSAT B6 Sedan / PASSAT B6 Variant / PASSAT B7 / PASSAT B7 Estate Van / PASSAT B7 Variant (3C2, 3C5, 362, A32, A33, 365) 03/05→12/15**

1.4 TSI	90 kW	1.4 l	05/07→07/10		KH30002 ProKIT
1.4 TSI	90 kW	1.4 l	05/07→11/10		
1.4 TSI	90 kW	1.4 l	08/10→12/14	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	118 kW	1.4 l	11/12→12/14		
1.4 TSI EcoFuel	110 kW	1.4 l	01/09→07/10		
1.4 TSI EcoFuel	110 kW	1.4 l	01/09→11/10		
1.4 TSI EcoFuel	110 kW	1.4 l	08/10→12/14		
1.4 TSI MultiFuel	118 kW	1.4 l	11/10→12/14		
1.6	75 kW	1.6 l	05/05→07/10		
1.6	75 kW	1.6 l	08/05→11/10		
1.6 FSI	85 kW	1.6 l	03/05→06/08		
1.6 FSI	85 kW	1.6 l	08/05→06/08		
1.6 TDI	77 kW	1.6 l	08/09→07/10		
1.6 TDI	77 kW	1.6 l	08/09→11/10		
1.6 TDI	77 kW	1.6 l	08/10→12/14		
1.8 TSI	112 kW	1.8 l	11/09→07/10		
1.8 TSI	112 kW	1.8 l	11/09→11/10		
1.8 TSI	112 kW	1.8 l	02/11→12/14		
1.8 TSI	118 kW	1.8 l	05/07→07/10		
1.8 TSI	118 kW	1.8 l	05/07→10/11		
1.8 TSI	118 kW	1.8 l	08/10→12/14		
1.9 TDI	77 kW	1.9 l	03/05→07/10		
1.9 TDI	77 kW	1.9 l	08/05→11/10		
2.0 BlueTDI	105 kW	2 l	01/09→11/10		
2.0 FSI	110 kW	2 l	03/05→07/10		
2.0 FSI	110 kW	2 l	08/05→11/10		
2.0 FSI	125 kW	2 l	08/07→07/10		
2.0 TDI	81 kW	2 l	11/08→07/10		
2.0 TDI	81 kW	2 l	11/08→11/10		
2.0 TDI	88 kW	2 l	11/05→05/07		
2.0 TDI	90 kW	2 l	08/05→02/06		
2.0 TDI	90 kW	2 l	08/05→07/06		
2.0 TDI	100 kW	2 l	03/05→11/10		
2.0 TDI	100 kW	2 l	08/05→11/10		
2.0 TDI	100 kW	2 l	08/10→12/14		
2.0 TDI	103 kW	2 l	03/05→05/09		
2.0 TDI	103 kW	2 l	08/05→05/09		
2.0 TDI	103 kW	2 l	08/10→12/14		
2.0 TDI	120 kW	2 l	08/05→05/09		
2.0 TDI	125 kW	2 l	08/05→07/10		
2.0 TDI	125 kW	2 l	08/05→11/10		
2.0 TDI	125 kW	2 l	08/10→12/14		
2.0 TDI	130 kW	2 l	12/12→12/14		
2.0 TDI 16V	103 kW	2 l	03/05→07/10		
2.0 TDI 16V	103 kW	2 l	08/05→11/10		
2.0 TFSI	147 kW	2 l	07/05→07/10		
2.0 TFSI	147 kW	2 l	08/05→11/10		
2.0 TSI	155 kW	2 l	11/10→12/14		
2.0 TSI	155 kW	2 l	11/10→12/15		
1.4 TSi BlueMotion	90 kW	1.4 l	08/10→12/14		KH30002 ProKIT
1.6 TDi BlueMotion	77 kW	1.6 l	08/10→12/14		
1.8 TFSI	118 kW	1.8 l	08/10→12/14		
1.8 TSI	125 kW	1.8 l	06/13→		
2.0	100 kW	2 l	09/06→12/07		
2.0 TDI	103 kW	2 l	04/11→06/15		
2.0 TDI	110 kW	2 l	06/14→		

     					
<b>VW - PASSAT B6 Sedan / PASSAT B6 Variant / PASSAT B7 / PASSAT B7 Estate Van / PASSAT B7 Variant (3C2, 3C5, 362, A32, A33, 365)</b>				<b>03/05→12/15</b>	
2.0 TDi BlueMotion	103 kW	2 l	08/10→12/14		KH30002 ProKIT
2.0 TDi BlueMotion	125 kW	2 l	08/10→12/14		
2.0 TFSI	155 kW	2 l	11/10→12/14		
2.0 TSI	130 kW	2 l	07/17→		
2.5	125 kW	2.5 l	01/11→		
3.6 FSI	206 kW	3.6 l	06/05→07/10		
3.6 FSI	206 kW	3.6 l	09/05→11/10		
3.6 FSI	206 kW	3.6 l	04/11→		
3.6 FSI	209 kW	3.6 l	04/11→09/15		
3.6 FSi 4motion	220 kW	3.6 l	01/11→12/14		
3.6 FSI 4motion	206 kW	3.6 l	09/05→07/10		
3.6 FSI 4motion	206 kW	3.6 l	09/05→11/10		
2.0 FSI 4motion	110 kW	2 l	09/05→07/10	 	KH30002 ProKIT
2.0 FSI 4motion	110 kW	2 l	09/05→11/10		
2.0 TDI 16V 4motion	103 kW	2 l	03/05→08/10		
2.0 TDI 16V 4motion	103 kW	2 l	08/05→11/10		
2.0 TDI 4motion	103 kW	2 l	03/05→05/09		
2.0 TDI 4motion	103 kW	2 l	08/05→05/09		
2.0 TDI 4motion	103 kW	2 l	08/10→12/14		
2.0 TDI 4motion	125 kW	2 l	05/09→07/10		
2.0 TDI 4motion	125 kW	2 l	05/09→11/10		
2.0 TDI 4motion	125 kW	2 l	08/10→01/13		
2.0 TDI 4motion	130 kW	2 l	01/13→12/14		
3.2 FSI 4motion	184 kW	3.2 l	11/05→07/10		
3.2 FSI 4motion	184 kW	3.2 l	11/05→11/10		
3.6 FSI 4motion	220 kW	3.6 l	01/11→12/14		
3.6 R36 4motion	220 kW	3.6 l	04/07→07/10		
3.6 R36 4motion	220 kW	3.6 l	04/07→11/10		
<b>VW - PASSAT B8 / PASSAT B8 Variant (3G2, CB2, 3G5, CB5)</b>				<b>08/14→</b>	
1.4 GTE Hybrid	115 kW	1.4 l	06/15→		KH30014 ProKIT
1.4 GTE Hybrid	115 kW	1.4 l	06/15→11/18	 ; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.4 TSI	92 kW	1.4 l	11/14→		
1.4 TSI	110 kW	1.4 l	11/14→		
1.6 TDI	88 kW	1.6 l	08/14→		
1.8 TSI	132 kW	1.8 l	02/15→		
2.0 TDI	81 kW	2 l	01/16→05/17		
2.0 TDI	110 kW	2 l	11/14→		
2.0 TDI	130 kW	2 l	05/16→		
2.0 TDI	135 kW	2 l	07/15→		
2.0 TDI	140 kW	2 l	11/14→		
2.0 TSI	162 kW	2 l	08/14→		
2.0 TSI	162 kW	2 l	02/15→		
1.4 TSI 4motion	110 kW	1.4 l	02/15→		KH30014 ProKIT
2.0 TDI 4motion	110 kW	2 l	08/14→11/17		KH30049 ProKIT
2.0 TDI 4motion	140 kW	2 l	11/14→		
2.0 TDI 4motion	147 kW	2 l	08/20→		
2.0 TDI 4motion	176 kW	2 l	08/14→		
2.0 TSI 4motion	200 kW	2 l	09/18→		
2.0 TSI 4motion	206 kW	2 l	05/15→		
1.5 TSI	110 kW	1.5 l	08/18→		KH30014 ProKIT
2.0 TDI	90 kW	2 l	07/20→		
2.0 TDI	147 kW	2 l	09/20→		KH20004 ProKIT
2.0 TSI	140 kW	2 l	11/18→		
2.0 TSI	140 kW	2 l	11/18→		KH30014 ProKIT
<b>VW - PHAETON Sedan (3D1, 3D2, 3D3, 3D4, 3D6, 3D7, 3D8, 3D9)</b>				<b>04/02→03/16</b>	
3.0 V6 TDI 4motion	165 kW	3 l	09/04→05/07	 	KH20031 ProKIT
3.0 V6 TDI 4motion	171 kW	3 l	06/07→11/08		
3.0 V6 TDI 4motion	176 kW	3 l	11/08→03/16		
3.0 V6 TDI 4motion	180 kW	3 l	11/13→03/16		
3.2 V6	177 kW	3.2 l	04/02→05/05		
3.2 V6 4motion	177 kW	3.2 l	02/04→11/08		
3.6 V6 4motion	206 kW	3.6 l	11/08→03/16		
4.2 V8 4motion	246 kW	4.2 l	05/03→03/16		
5.0 V10 TDI 4motion	230 kW	5 l	11/02→10/06		
6.0 W12 4motion	309 kW	6 l	04/02→12/05		
6.0 W12 4motion	331 kW	6 l	05/05→03/16		





























										
<b>VW - POLO (6N2)</b>										<b>10/99→09/01</b>
1.0	37 kW	1 l	10/99→09/01						<b>KH10358</b> ProKIT	
1.4	40 kW	1.4 l	10/99→09/01						<b>KH20117</b> ProKIT	
1.4	44 kW	1.4 l	10/99→09/01							
1.4 16V	55 kW	1.4 l	10/99→09/01							
1.4 16V	74 kW	1.4 l	10/99→09/01							
1.4 TDI	55 kW	1.4 l	10/99→09/01							
1.6 16V GTI	92 kW	1.6 l	10/99→09/01							
1.7 SDI	44 kW	1.7 l	10/99→09/01							
1.9 D	47 kW	1.9 l	10/99→09/01							
1.9 SDI	47 kW	1.9 l	10/99→09/01							
<b>VW - POLO (9N_, 9A_)</b>										<b>10/01→01/12</b>
1.2	40 kW	1.2 l	01/02→05/07						<b>KH20028</b> ProKIT	
1.2	44 kW	1.2 l	05/07→11/09						<b>KH30045</b> ProKIT	
1.2 12V	47 kW	1.2 l	10/01→07/07							
1.2 12V	51 kW	1.2 l	05/07→11/09						<b>KH20009</b> ProKIT	
1.4	61 kW	1.4 l	08/02→11/09							
1.4 16V	55 kW	1.4 l	10/01→05/08							
1.4 16V	59 kW	1.4 l	05/06→11/09							
1.4 16V	74 kW	1.4 l	10/01→05/08							
1.4 FSI	63 kW	1.4 l	02/02→07/06							
1.4 TDI	51 kW	1.4 l	04/05→11/09							
1.4 TDI	55 kW	1.4 l	10/01→06/05							
1.4 TDI	59 kW	1.4 l	04/05→11/09							
1.6	74 kW	1.6 l	08/02→05/05							
1.6 16V	77 kW	1.6 l	05/06→11/09							
1.8 GTI	110 kW	1.8 l	09/05→11/09							
1.8 GTi Cup Edition	132 kW	1.8 l	05/06→11/09							
1.9 SDI	47 kW	1.9 l	10/01→11/09							
1.9 TDI	74 kW	1.9 l	10/01→11/09							
2.0	85 kW	2 l	10/04→01/12							
1.6 Flex	74 kW	1.6 l	06/08→04/09						<b>KH20028</b> ProKIT	
									<b>KH30045</b> ProKIT	
1.9 TDI	96 kW	1.9 l	11/03→11/09						<b>KH20028</b> ProKIT	
									<b>KH30045</b> ProKIT	
									<b>KH20009</b> ProKIT	
<b>VW - POLO / POLO II (86, 86C, 80)</b>										<b>03/75→09/94</b>
0.8	25 kW	0.8 l	09/75→09/81						<b>KH00003</b> ProKIT	
0.9	29 kW	0.9 l	10/81→12/81							
1.1	44 kW	1.1 l	03/75→09/81							
1.3	37 kW	1.3 l	08/83→07/85							
1.3	43 kW	1.3 l	08/82→07/88							
1.3	56 kW	1.3 l	10/90→08/94							
0.9	29 kW	0.9 l	09/75→09/81						<b>KH10187</b> ProKIT	
1.0	33 kW	1 l	08/85→01/92						<b>KH00003</b> ProKIT	
1.0 Cat	33 kW	1 l	08/89→09/94							
1.3	40 kW	1.3 l	08/83→07/88							
1.3	44 kW	1.3 l	10/81→07/83							
1.3	55 kW	1.3 l	09/82→09/89							
1.3 Cat	40 kW	1.3 l	07/87→09/94							
1.3 Cat	55 kW	1.3 l	10/89→03/91							
1.3 D	33 kW	1.3 l	08/86→07/90							
1.4 D	35 kW	1.4 l	10/90→09/94							
1.0	29 kW	1 l	10/81→10/86		-> 07/86				<b>KH10187</b> ProKIT	
									<b>KH00003</b> ProKIT	
1.1	37 kW	1.1 l	03/75→09/81		-> 07/81				<b>KH10187</b> ProKIT	
									<b>KH00003</b> ProKIT	
1.1	37 kW	1.1 l	10/81→09/89		-> 07/83				<b>KH10187</b> ProKIT	
									<b>KH00003</b> ProKIT	
1.3	44 kW	1.3 l	12/76→09/81		01/77 ->				<b>KH10187</b> ProKIT	
									<b>KH00003</b> ProKIT	

     				
<b>VW - POLO III (6N1)</b>				<b>10/94→10/99</b>
1.7 SDI	42 kW	1.7 l	04/97→10/99	 KH10358 ProKIT
100 1.4 16V	74 kW	1.4 l	04/96→10/99	 VIN → 6N-XY379 991 KH00003 ProKIT
120 1.6 16V GTI	88 kW	1.6 l	09/98→10/99	 VIN 6N-XY379 992 → KH20117 ProKIT
45 1.0	33 kW	1 l	10/94→09/96	
50 1.0	37 kW	1 l	09/96→10/99	
55 1.3	40 kW	1.3 l	10/94→04/97	
55 1.4	40 kW	1.4 l	08/95→10/99	
60 1.4	44 kW	1.4 l	07/95→10/99	
60 1.7 SDI	44 kW	1.7 l	08/97→10/99	
64 1.9 D	47 kW	1.9 l	10/94→10/99	
64 1.9 SDI	47 kW	1.9 l	07/96→10/99	
75 1.6	55 kW	1.6 l	10/94→10/99	
75 1.6 4motion	55 kW	1.6 l	08/95→10/99	 VIN 6N-XY379 992 → KH20117 ProKIT
<b>VW - POLO III CLASSIC (6V2)</b>				<b>11/95→07/02</b>
1.8	82 kW	1.8 l	08/00→07/02	 ABS KH10055 ProKIT
1.9 SDI	48 kW	1.9 l	06/96→09/01	
1.9 TDI	67 kW	1.9 l	01/97→08/99	 VIN → 6K-Y-502794 KH00003 ProKIT
100 1.6	74 kW	1.6 l	12/95→09/01	
110 1.9 TDI	81 kW	1.9 l	06/98→01/02	
54 1.4	40 kW	1.4 l	01/98→08/99	
57 1.7 SDI	42 kW	1.7 l	07/97→09/01	
60 1.4	44 kW	1.4 l	12/95→09/01	
64 1.9 D	47 kW	1.9 l	01/96→10/96	
64 1.9 SDI	47 kW	1.9 l	12/95→08/99	
68 1.9 SDI	50 kW	1.9 l	08/99→01/02	
75 1.6	55 kW	1.6 l	11/95→09/97	
75 1.6	55 kW	1.6 l	11/95→09/01	
90 1.8	66 kW	1.8 l	01/97→09/01	
90 1.9 TDI	66 kW	1.9 l	09/96→09/01	
75 1.4 16V	55 kW	1.4 l	10/99→09/01	 ABS KH10055 ProKIT
<b>VW - POLO IV Saloon (9A4, 9A2, 9N2, 9A6)</b>				<b>09/02→</b>
1.4	55 kW	1.4 l	11/02→04/12	 KH30045 ProKIT
1.4	61 kW	1.4 l	12/03→08/10	
1.4	74 kW	1.4 l	11/03→06/05	 EHM KH20009 ProKIT
1.6	74 kW	1.6 l	09/02→	
1.9 SDI	47 kW	1.9 l	09/02→04/12	
1.9 TDi	74 kW	1.9 l	09/02→	
1.4 TDI	55 kW	1.4 l	07/03→06/05	 KH30045 ProKIT
2.0	85 kW	2 l	09/02→	
<b>VW - POLO IV Saloon (9N4)</b>				<b>09/02→12/10</b>
1.6	74 kW	1.6 l	09/02→05/05	 KH20028 ProKIT
1.6	77 kW	1.6 l	01/07→12/10	
1.9 TDI	74 kW	1.9 l	07/03→12/10	 KH30045 ProKIT
<b>VW - POLO V (6R1, 6C1)</b>				<b>03/09→</b>
1.0	44 kW	1 l	01/14→	 KH30045 ProKIT
1.0	55 kW	1 l	01/14→	 KH20009 ProKIT
1.0 TSI	70 kW	1 l	11/14→	
1.0 TSI	81 kW	1 l	11/14→	
1.2	44 kW	1.2 l	06/09→	
1.2	51 kW	1.2 l	06/09→	
1.2 TDI	55 kW	1.2 l	10/09→	
1.2 TSI	66 kW	1.2 l	05/11→05/14	
1.2 TSI	77 kW	1.2 l	11/09→	
1.2 TSI	81 kW	1.2 l	01/14→	
1.2 TSI 16V	66 kW	1.2 l	02/14→10/17	
1.4 (6R1)	63 kW	1.4 l	03/09→05/14	
1.4 BiFuel	60 kW	1.4 l	03/10→01/11	
1.4 GTI	132 kW	1.4 l	05/10→	
1.4 TDI	55 kW	1.4 l	03/14→10/17	
1.4 TDI	66 kW	1.4 l	02/14→	
1.4 TDI	77 kW	1.4 l	05/14→	
1.4 TSI	103 kW	1.4 l	10/12→05/14	
1.4 TSI	110 kW	1.4 l	05/14→10/17	
1.6 BiFuel	60 kW	1.6 l	01/11→05/14	
1.6 TDI	55 kW	1.6 l	06/09→	
1.6 TDI	66 kW	1.6 l	06/09→	
1.6 TDI	77 kW	1.6 l	06/09→	
1.8 GTI	141 kW	1.8 l	11/14→	
2.0 R WRC	162 kW	2 l	08/13→05/14	
1.2	55 kW	1.2 l	08/11→	 KH30045 ProKIT
1.6	66 kW	1.6 l	07/14→10/17	
1.6	77 kW	1.6 l	01/10→	
1.6	81 kW	1.6 l	07/14→10/17	
1.8 GTI 230	169 kW	1.8 l	04/16→	
























<b>VW - POLO CLASSIC / POLO Coupe (86C, 80)</b>				<b>10/81→09/94</b>	
1.0	29 kW	1 l	05/82→10/86	; 08/83 ->	KH10187 ProKIT
					KH00003 ProKIT
1.0	29 kW	1 l	01/85→10/86	; 08/86 ->	KH10187 ProKIT
1.0	33 kW	1 l	01/85→09/94		KH00003 ProKIT
1.3	40 kW	1.3 l	01/85→07/87		
1.0	33 kW	1 l	08/85→01/92		KH10187 ProKIT
1.3	40 kW	1.3 l	08/83→06/87		KH00003 ProKIT
1.3	55 kW	1.3 l	09/82→09/89		
1.3	57 kW	1.3 l	03/91→09/94		
1.3 Cat	40 kW	1.3 l	07/87→08/94		
1.3 Cat	40 kW	1.3 l	07/87→09/94		
1.3 Cat	55 kW	1.3 l	10/89→09/94		
1.3 D	33 kW	1.3 l	08/86→12/88		
1.3 D	33 kW	1.3 l	08/86→08/90		
1.3 G40	85 kW	1.3 l	01/87→08/90		
1.4 D	35 kW	1.4 l	10/90→09/94		
1.0 Cat	33 kW	1 l	08/89→09/94	; 01/90 ->	KH10187 ProKIT
					KH00003 ProKIT
1.1	37 kW	1.1 l	10/81→07/83	; 08/82 ->	KH10187 ProKIT
1.3	44 kW	1.3 l	10/81→07/83		KH00003 ProKIT
1.3	43 kW	1.3 l	08/82→07/88		KH00003 ProKIT
1.3 G40	83 kW	1.3 l	08/90→09/94	; 10/90 ->	KH10187 ProKIT
1.4 D	35 kW	1.4 l	08/90→09/94		KH00003 ProKIT
<b>VW - POLO Van (6R)</b>				<b>01/14→</b>	
1.0	44 kW	1 l	01/14→		KH30045 ProKIT
1.0	55 kW	1 l	01/14→		
1.0 TSI	70 kW	1 l	11/14→		
1.2 TSI	66 kW	1.2 l	02/14→		
1.2 TSI	81 kW	1.2 l	01/14→		
1.4 TDI	55 kW	1.4 l	03/14→		
1.4 TDI	66 kW	1.4 l	02/14→		
1.4 TSI	110 kW	1.4 l	05/14→		
<b>VW - POLO Van Hatchback Van (6N1)</b>				<b>10/94→12/99</b>	
1.0	33 kW	1 l	10/94→12/99		KH10358 ProKIT
				; VIN 6N-XY379 992 ->	KH20117 ProKIT
<b>VW - POLO Variant (6V5)</b>				<b>05/97→09/01</b>	
1.4	40 kW	1.4 l	12/98→09/01	; ABS	KH10055 ProKIT
1.4	44 kW	1.4 l	05/97→09/01		
1.4 16V	55 kW	1.4 l	10/99→09/01	; VIN -> 6K-X-610 000	KH00003 ProKIT
1.6	55 kW	1.6 l	05/97→09/01		
1.6	74 kW	1.6 l	05/97→09/01		
1.7 SDI	42 kW	1.7 l	08/97→09/01		
1.8	66 kW	1.8 l	05/97→09/01		
1.9 SDI	47 kW	1.9 l	06/97→09/01		
1.9 SDI	50 kW	1.9 l	08/99→09/01		
1.9 TDI	66 kW	1.9 l	05/97→09/01		
1.9 TDI	81 kW	1.9 l	06/98→09/01		
<b>VW - SANTANA (32B)</b>				<b>08/81→12/84</b>	
1.3	44 kW	1.3 l	08/81→07/83		KH10194 ProKIT
1.6	55 kW	1.6 l	08/81→12/84		KH00003 ProKIT
1.6	63 kW	1.6 l	08/81→12/82		
1.6 D	40 kW	1.6 l	08/81→12/84		
1.6 TD	51 kW	1.6 l	12/81→12/84		
1.8	66 kW	1.8 l	01/83→12/84		
1.9	85 kW	1.9 l	08/81→07/83		
2.0	85 kW	2 l	08/83→12/84		
2.1	85 kW	2.1 l	08/82→12/83		KH00003 ProKIT
<b>VW - SCIROCCO (53, 53B)</b>				<b>02/74→07/92</b>	
1.1	37 kW	1.1 l	04/74→07/79		KH10186 ProKIT
1.3	44 kW	1.3 l	08/79→07/80		KH00003 ProKIT
1.3	44 kW	1.3 l	08/80→12/83		
1.5	51 kW	1.5 l	02/74→12/75		
1.5	51 kW	1.5 l	08/77→07/80		
1.5	51 kW	1.5 l	08/80→12/83		
1.5	55 kW	1.5 l	02/74→08/75		
1.5	63 kW	1.5 l	02/74→12/77		
1.6	53 kW	1.6 l	04/86→07/90		
1.6	55 kW	1.6 l	08/75→07/79		
1.6	55 kW	1.6 l	01/83→12/89		
1.6	63 kW	1.6 l	08/75→07/80		



     					
<b>VW - SCIROCCO (53, 53B)</b>				<b>02/74→07/92</b>	
1.6	63 kW	1.6 l	08/80→04/84		<b>KH10186</b> ProKIT
1.6	81 kW	1.6 l	06/76→07/80		<b>KH00003</b> ProKIT
1.6	81 kW	1.6 l	08/80→07/82		
1.8	66 kW	1.8 l	08/83→07/92		
1.8	70 kW	1.8 l	11/85→07/92		
1.8	82 kW	1.8 l	08/82→12/89		
1.3	40 kW	1.3 l	08/83→07/84		<b>KH00003</b> ProKIT
1.6	51 kW	1.6 l	08/75→07/77		
1.6	51 kW	1.6 l	08/83→07/84		
1.8 16V	95 kW	1.8 l	03/86→07/92		
1.8 16V	102 kW	1.8 l	10/85→07/89		
<b>VW - SCIROCCO III / SCIROCCO Van (137, 138, 137)</b>				<b>05/08→11/17</b>	
1.4 TSi	90 kW	1.4 l	08/08→05/14	 ; Number of mounting bores: 4	<b>KH30002</b> ProKIT
1.4 TSi	118 kW	1.4 l	06/08→05/14	 ; Inner diameter 1 [mm]: 32	<b>KH20004</b> ProKIT
1.4 TSi	90 kW	1.4 l	08/08→11/17		
1.4 TSi	92 kW	1.4 l	11/13→11/17		
1.4 TSi	96 kW	1.4 l	07/15→11/17		
1.4 TSi	110 kW	1.4 l	07/15→11/17		
1.4 TSi	118 kW	1.4 l	05/08→11/17		
2.0 R	188 kW	2 l	11/09→11/17		
2.0 R	195 kW	2 l	11/09→11/17		
2.0 R	206 kW	2 l	05/14→11/17		
2.0 TDi	103 kW	2 l	08/08→05/14		
2.0 TDi	125 kW	2 l	05/09→05/14		
2.0 TDi	100 kW	2 l	11/10→11/17		
2.0 TDi	103 kW	2 l	08/08→11/17		
2.0 TDi	110 kW	2 l	11/13→11/17		
2.0 TDi	125 kW	2 l	05/09→11/17		
2.0 TDi	130 kW	2 l	01/13→11/17		
2.0 TDi	135 kW	2 l	05/14→11/17		
2.0 TFSi	155 kW	2 l	11/09→05/14		
2.0 TFSi	147 kW	2 l	05/08→11/09		
2.0 TSi	132 kW	2 l	11/13→11/17		
2.0 TSi	155 kW	2 l	11/09→11/17		
2.0 TSi	162 kW	2 l	11/13→11/17		
<b>VW - SHARAN (7M8, 7M9, 7M6)</b>				<b>09/95→03/10</b>	
1.8 T 20V	110 kW	1.8 l	09/97→03/10		<b>KH10084</b> ProKIT
2.0	85 kW	2 l	09/95→03/10	 ; -> 05/06	<b>KH10208</b> ProKIT
1.9 TDi	66 kW	1.9 l	09/95→03/10		<b>KH10084</b> ProKIT
1.9 TDi	85 kW	1.9 l	04/00→03/10		<b>KH10208</b> ProKIT
1.9 TDi	96 kW	1.9 l	11/02→03/10		
2.0 LPG	85 kW	2 l	04/06→03/10		
2.0 TDi	103 kW	2 l	11/05→03/10		
2.8 V6 24V	150 kW	2.8 l	04/00→03/10		
1.9 TDi	81 kW	1.9 l	09/96→04/00		<b>KH10084</b> ProKIT
				 ; 12/96 -> 02/00	<b>KH10208</b> ProKIT
1.9 TDi	110 kW	1.9 l	06/05→03/10		<b>KH10084</b> ProKIT
				 ; -> 05/07	<b>KH10208</b> ProKIT
1.9 TDi 4motion	85 kW	1.9 l	03/00→03/10		<b>KH10084</b> ProKIT
2.0 16V	110 kW	2 l	09/95→02/00		
2.0 TDi	100 kW	2 l	11/05→03/10		
2.8 V6 24V 4motion	150 kW	2.8 l	04/00→03/10		
2.8 VR6	128 kW	2.8 l	09/95→04/00		<b>KH10084</b> ProKIT
2.8 VR6 Syncro	128 kW	2.8 l	11/96→04/00	 ; -> 02/00	<b>KH10208</b> ProKIT
<b>VW - SHARAN / SHARAN VAN (7N1, 7N2)</b>				<b>05/10→</b>	
1.4 TSi	110 kW	1.4 l	05/10→		<b>KH30002</b> ProKIT
1.4 TSi	110 kW	1.4 l	05/15→	 ; Inner diameter 1 [mm]: 32	<b>KH20004</b> ProKIT
2.0 TDi	85 kW	2 l	05/11→07/19		
2.0 TDi	100 kW	2 l	05/10→		
2.0 TDi	103 kW	2 l	05/10→		
2.0 TDi	110 kW	2 l	05/15→10/20		
2.0 TDi	125 kW	2 l	08/10→		
2.0 TDi	130 kW	2 l	01/13→11/15		
2.0 TDi	135 kW	2 l	05/15→		
2.0 TFSi	147 kW	2 l	12/10→11/15		
2.0 TSi	162 kW	2 l	05/15→		
1.4 TSi	110 kW	1.4 l	05/10→11/15		<b>KH30002</b> ProKIT
1.8 TSi	118 kW	1.8 l	11/11→		<b>KH20004</b> ProKIT
2.0 TDi	85 kW	2 l	05/11→11/15		
2.0 TDi	100 kW	2 l	05/10→05/11		
2.0 TDi	103 kW	2 l	05/10→11/15		
2.0 TDi	125 kW	2 l	08/10→01/13		
2.0 TSi	147 kW	2 l	12/10→11/15		



				    	
<b>VW - SHARAN / SHARAN VAN (7N1, 7N2)</b>				<b>05/10→</b>	
2.0 TDI 4motion	103 kW	2 l	05/11→11/15	 , 	<b>KH30002</b> ProKIT
2.0 TDI 4motion	110 kW	2 l	05/15→		
2.0 TDI 4motion	130 kW	2 l	11/18→		
2.0 TDI 4motion	135 kW	2 l	05/16→		
<b>VW - TARO</b>				<b>04/89→03/97</b>	
1.8	61 kW	1.8 l	04/89→09/94		<b>KH00042</b> ProKIT
2.2	69 kW	2.2 l	06/89→07/94		
2.4 D	58 kW	2.4 l	07/94→03/97		
2.4 D	59 kW	2.4 l	09/91→07/94		
2.4 D	61 kW	2.4 l	06/89→03/97		
2.4 D 4x4	58 kW	2.4 l	07/94→03/97		<b>KH00134</b> ProKIT
2.4 i 4x4	84 kW	2.4 l	06/89→03/97		
<b>VW - TIGUAN (5N_)</b>				<b>09/07→07/18</b>	
1.4 TSI	90 kW	1.4 l	08/10→07/18		<b>KH30002</b> ProKIT
1.4 TSI	92 kW	1.4 l	05/15→07/18		
1.4 TSI	110 kW	1.4 l	05/08→07/18	 ; Inner diameter 1 [mm]: 32	<b>KH20004</b> ProKIT
1.4 TSI	110 kW	1.4 l	05/15→07/18		
1.4 TSI	118 kW	1.4 l	05/11→07/18		
2.0 TDI	81 kW	2 l	05/10→07/18		
2.0 TDI	103 kW	2 l	03/08→07/18		
2.0 TDI	110 kW	2 l	05/15→07/18		
2.0 TFSI	147 kW	2 l	11/07→07/18		
1.4 TSI 4motion	110 kW	1.4 l	09/07→07/18	 , 	<b>KH30002</b> ProKIT
1.4 TSI 4motion	118 kW	1.4 l	05/11→07/18		
2.0 TDI 4motion	100 kW	2 l	11/07→07/18		
2.0 TDI 4motion	103 kW	2 l	09/07→07/18		
2.0 TDI 4motion	120 kW	2 l	02/08→08/09		
2.0 TDI 4motion	125 kW	2 l	09/07→07/18		
2.0 TDI 4motion	130 kW	2 l	11/12→07/18		
2.0 TFSI 4motion	125 kW	2 l	09/07→07/18		
2.0 TFSI 4motion	147 kW	2 l	09/07→07/18		
2.0 TSI 4motion	132 kW	2 l	05/11→07/18		
2.0 TSI 4motion	155 kW	2 l	05/11→07/18		
2.0 TDI 4motion	110 kW	2 l	05/15→07/18		<b>KH30002</b> ProKIT
2.0 TDI 4motion	135 kW	2 l	05/15→07/18		
<b>VW - TIGUAN / TIGUAN ALLSPACE (AD1, AX1, BW2, BJ2)</b>				<b>01/16→07/20</b>	
1.4 eHybrid	110 kW	1.4 l	11/20→		<b>KH30014</b> ProKIT
1.5 TSI	96 kW	1.5 l	07/18→		
2.0 TDI	90 kW	2 l	06/20→		<b>KH20004</b> ProKIT
1.4 TSI	92 kW	1.4 l	01/16→07/18		<b>KH30014</b> ProKIT
1.4 TSI	110 kW	1.4 l	05/16→07/18		
1.5 TSI	96 kW	1.5 l	11/18→08/19	 ; Inner diameter 1 [mm]: 32	<b>KH20004</b> ProKIT
1.5 TSI	110 kW	1.5 l	11/18→08/19		
1.6 TDI	85 kW	1.6 l	05/16→06/20		
2.0 TDI	81 kW	2 l	08/16→07/20		
2.0 TDI	85 kW	2 l	05/16→07/19		
2.0 TDI	110 kW	2 l	01/16→07/20		
1.4 TSI	110 kW	1.4 l	06/17→07/21		<b>KH30014</b> ProKIT
1.4 TSI E100 Flex	110 kW	1.4 l	07/17→		
1.5 TSI	110 kW	1.5 l	09/18→		
2.0 TDI	110 kW	2 l	06/17→		
2.0 TSI	137 kW	2 l	04/17→		
1.4 TSI 4motion	110 kW	1.4 l	05/16→07/18		<b>KH30014</b> ProKIT
2.0 TDI 4motion	105 kW	2 l	06/16→07/20		<b>KH30049</b> ProKIT
2.0 TDI 4motion	110 kW	2 l	01/16→07/20		
2.0 TDI 4motion	110 kW	2 l	06/17→		
2.0 TDI 4motion	130 kW	2 l	08/16→07/20		
2.0 TDI 4motion	140 kW	2 l	04/16→07/20		
2.0 TDI 4motion	140 kW	2 l	06/17→07/21		
2.0 TDI 4motion	147 kW	2 l	06/20→		
2.0 TDI 4motion	176 kW	2 l	05/16→07/20		
2.0 TDI 4motion	176 kW	2 l	06/17→09/20		
2.0 TSI 4motion	132 kW	2 l	01/16→		
2.0 TSI 4motion	132 kW	2 l	03/17→		
2.0 TSI 4motion	137 kW	2 l	04/17→		
2.0 TSI 4motion	140 kW	2 l	09/18→		
2.0 TSI 4motion	162 kW	2 l	06/16→		
2.0 TSI 4motion	162 kW	2 l	07/17→		
2.0 TSI 4motion	169 kW	2 l	09/18→07/20		
2.0 TSI 4motion	180 kW	2 l	01/21→		
2.0 TSI R 4motion	235 kW	2 l	11/20→		



**VW - TIGUAN VAN (5N\_)** 11/07→07/18

1.4 TSI (5N1)	90 kW	1.4 l	08/10→05/11		KH30002 ProKIT
1.4 TSI (5N1)	110 kW	1.4 l	05/08→05/10		KH20004 ProKIT
1.4 TSI (5N2)	118 kW	1.4 l	09/12→07/18		
2.0 TDI (5N1, 5N2)	103 kW	2 l	11/09→07/18		
2.0 TDI (5N1)	81 kW	2 l	05/10→07/11		
1.4 TSI 4motion (5N2)	118 kW	1.4 l	09/12→07/18		KH30002 ProKIT
2.0 TDI 4motion (5N1, 5N2)	103 kW	2 l	11/07→07/18		
2.0 TDI 4motion (5N1, 5N2)	125 kW	2 l	05/10→05/13		
2.0 TDI 4motion (5N2)	130 kW	2 l	11/12→07/18		
2.0 TSI 4motion (5N1)	125 kW	2 l	11/09→05/11		
2.0 TSI 4motion (5N1)	147 kW	2 l	11/09→05/11		
2.0 TSI 4motion (5N2)	155 kW	2 l	05/11→07/18		

**VW - TOUAREG (7LA, 7L6, 7L7)** 10/02→05/10

2.5 R5 TDI	120 kW	2.5 l	08/03→05/10	VIN -> 4-035 000; PR 1LB	KH20025 ProKIT
2.5 R5 TDI	128 kW	2.5 l	01/03→05/10	VIN -> 4-035 000; PR 1KE	
				VIN 4-035 001 ->; PR 1LB	KH20026 ProKIT
				VIN 4-035 001 ->; PR 1KE	
3.0 V6 TDI	165 kW	3 l	11/04→05/10		KH10152 ProKIT
3.0 V6 TDI	176 kW	3 l	11/07→05/10		
3.2 V6	162 kW	3.2 l	10/02→11/06		
3.2 V6	177 kW	3.2 l	11/04→11/06		
3.6 V6 FSI	206 kW	3.6 l	10/05→05/10		
4.2 V8	228 kW	4.2 l	12/02→11/06		
4.2 V8 FSI	257 kW	4.2 l	06/06→05/10		
5.0 R50 TDI	257 kW	5 l	08/07→05/10		
5.0 V10 TDI	230 kW	5 l	10/02→05/10		
6.0 W12	331 kW	6 l	08/04→05/10		

**VW - TOUAREG (7P5, 7P6)** 01/10→03/18

3.0 V6 TDI	176 kW	3 l	01/10→03/18	-> 11/10	KH10152 ProKIT
3.6 V6 FSI	206 kW	3.6 l	04/10→03/18		

**VW - TOURAN (1T1, 1T2, 1T3)** 02/03→05/15

1.2 TSI	77 kW	1.2 l	05/10→05/15		KH30002 ProKIT
1.4 TSI	103 kW	1.4 l	02/06→05/10		KH20004 ProKIT
1.4 TSI	103 kW	1.4 l	05/10→05/15	; Inner diameter 1 [mm]: 32	
1.4 TSI	125 kW	1.4 l	11/06→05/10		
1.4 TSI	125 kW	1.4 l	05/10→05/15		
1.4 TSI EcoFuel	110 kW	1.4 l	05/09→05/10		
1.4 TSI EcoFuel	110 kW	1.4 l	05/10→05/15		
1.6	75 kW	1.6 l	07/03→05/10		
1.6 FSI	85 kW	1.6 l	02/03→01/07		
1.6 TDI	66 kW	1.6 l	05/10→05/15		
1.6 TDI	77 kW	1.6 l	05/10→05/15		
1.9 TDI	66 kW	1.9 l	11/04→05/10		
1.9 TDI	74 kW	1.9 l	02/03→05/04		
1.9 TDI	77 kW	1.9 l	08/03→05/10		
2.0 EcoFuel	80 kW	2 l	02/06→05/09		
2.0 FSI	110 kW	2 l	10/03→01/07		
2.0 TDI	81 kW	2 l	11/10→05/15		
2.0 TDI	100 kW	2 l	02/03→05/10		
2.0 TDI	103 kW	2 l	12/05→05/10		
2.0 TDI	103 kW	2 l	05/10→05/15		
2.0 TDI	125 kW	2 l	12/05→05/10		
2.0 TDI	125 kW	2 l	05/10→01/13		
2.0 TDI	130 kW	2 l	01/13→05/15		
2.0 TDI 16V	103 kW	2 l	08/03→05/10		
1.6 BiFuel	75 kW	1.6 l	11/06→05/10	; Number of mounting bores: 4	KH30002 ProKIT
				; Inner diameter 1 [mm]: 32	KH20004 ProKIT

**VW - TOURAN (5T1)** 05/15→

1.0 TSI	85 kW	1 l	12/18→		KH30014 ProKIT
1.5 TSI	110 kW	1.5 l	11/18→		KH20004 ProKIT
2.0 TDI	85 kW	2 l	02/19→		
1.2 TSI	81 kW	1.2 l	05/15→		KH30014 ProKIT
1.4 TSI	110 kW	1.4 l	05/15→		KH20004 ProKIT
1.6 TDI	81 kW	1.6 l	05/15→05/16	; Inner diameter 1 [mm]: 32	
1.6 TDI	85 kW	1.6 l	05/16→		
1.8 TSI	132 kW	1.8 l	11/15→		
2.0 TDI	81 kW	2 l	11/15→07/19		
2.0 TDI	110 kW	2 l	05/15→		
2.0 TDI	140 kW	2 l	11/15→07/19		

**VW - TOURAN VAN (1T1, 1T2, 1T3)** 02/03→05/15

1.2 TSI	77 kW	1.2 l	05/10→05/15	; Number of mounting bores: 4	KH30002 ProKIT
1.4 TSI	103 kW	1.4 l	05/10→05/15	; Inner diameter 1 [mm]: 32	KH20004 ProKIT



**VW - TOURAN VAN (1T1, 1T2, 1T3)**

**02/03→05/15**

1.4 TSI	125 kW	1.4 l	05/10→05/15	; Number of mounting bores: 4	KH30002 ProKIT
1.4 TSi EcoFuel	110 kW	1.4 l	05/10→05/15		
1.6 TDI	66 kW	1.6 l	05/10→05/15	; Inner diameter 1 [mm]: 32	KH20004 ProKIT
1.6 TDI	77 kW	1.6 l	05/10→05/15		
1.9 TDI	66 kW	1.9 l	11/04→05/10		
1.9 TDI	74 kW	1.9 l	10/03→05/05		
1.9 TDI	77 kW	1.9 l	08/03→11/06		
2.0 EcoFuel	80 kW	2 l	02/06→11/06		
2.0 FSI	110 kW	2 l	05/04→01/07		
2.0 TDi	103 kW	2 l	08/03→05/10		
2.0 TDi	103 kW	2 l	12/05→05/10		
2.0 TDi	125 kW	2 l	05/10→01/13		
2.0 TDI	100 kW	2 l	02/03→05/10		
2.0 TDI	103 kW	2 l	05/10→05/15		
FSI	85 kW	1.6 l	02/03→11/06		

**VW - TRANSPORTER / CARAVELLE III Bus**

**05/79→07/92**

1.6	37 kW	1.6 l	05/79→12/82	; VIN 24-E-023828 ->	KH00058 ProKIT
1.9	61 kW	1.9 l	01/83→07/85		
1.9	66 kW	1.9 l	08/83→07/85		
2.0	51 kW	2 l	05/79→12/82		
2.1	64 kW	2.1 l	10/86→07/92		
2.1	70 kW	2.1 l	08/85→07/92		
2.1	82 kW	2.1 l	08/84→07/92		
2.1 Cat	70 kW	2.1 l	06/89→07/92		
1.9	44 kW	1.9 l	08/82→07/92	; 01/84 ->; VIN 24-E-023828 ->	KH00058 ProKIT
1.9	57 kW	1.9 l	08/82→07/92		

**VW - TRANSPORTER / CARAVELLE IV Bus (70B, 70C, 7DB, 7DK, 70J, 70K)**

**09/90→06/03**

1.8	49 kW	1.8 l	12/90→07/92		KH10205 ProKIT
2.0	62 kW	2 l	09/90→04/03		
2.5	81 kW	2.5 l	09/90→06/03	; VIN 24-E-023828 ->	KH00058 ProKIT
1.9 D	44 kW	1.9 l	09/90→12/95		
1.9 TD	50 kW	1.9 l	10/92→04/03		
2.4 D	55 kW	2.4 l	08/97→04/03		
2.4 D	57 kW	2.4 l	09/90→04/98		
2.5	85 kW	2.5 l	08/96→04/03		
2.5 TDI	65 kW	2.5 l	05/98→04/03		
2.5 TDI	75 kW	2.5 l	09/95→04/03		
2.5 TDI	111 kW	2.5 l	05/98→04/03		
2.8 VR6	150 kW	2.8 l	04/00→04/03		
2.8 VR 6	103 kW	2.8 l	11/95→04/00		
2.4 D Syncro	57 kW	2.4 l	10/92→09/98	;	KH10205 ProKIT
2.5 Syncro	81 kW	2.5 l	08/92→04/03		
2.5 Syncro	85 kW	2.5 l	07/96→04/03		
2.5 TDI Syncro	75 kW	2.5 l	01/96→04/03		

**VW - TRANSPORTER / CARAVELLE V Bus (7HB, 7HJ, 7EB, 7EJ)**

**04/03→08/15**

1.9 TDI	62 kW	1.9 l	01/06→11/09	; VIN -> 4-017 500	KH20025 ProKIT
1.9 TDI	63 kW	1.9 l	04/03→11/09		
1.9 TDI	75 kW	1.9 l	06/06→11/09	; VIN 4-017 501 ->	KH20026 ProKIT
1.9 TDI	77 kW	1.9 l	04/03→11/09		
2.0	85 kW	2 l	11/03→08/15		
2.0 BiTDI	132 kW	2 l	09/09→08/15		
2.0 TDI	62 kW	2 l	09/09→08/15		
2.0 TDI	75 kW	2 l	09/09→08/15		
2.0 TDI	84 kW	2 l	05/11→08/15		
2.0 TDI	100 kW	2 l	05/10→08/15		
2.0 TDI	103 kW	2 l	09/09→08/15		
2.0 TSI	110 kW	2 l	07/12→08/15		
2.0 TSI	150 kW	2 l	05/11→08/15		
2.5 TDi	120 kW	2.5 l	11/03→11/09		
2.5 TDI	96 kW	2.5 l	04/03→11/09		
2.5 TDI	128 kW	2.5 l	04/03→11/09		
3.2 V6	170 kW	3.2 l	02/04→06/04		
3.2 V6	173 kW	3.2 l	02/04→11/09		
2.0 BiTDI 4motion	132 kW	2 l	09/09→08/15	; ; VIN -> 4-017 500	KH20025 ProKIT
2.0 TDI 4motion	100 kW	2 l	05/10→08/15		
2.0 TDI 4motion	103 kW	2 l	09/09→08/15	; ; VIN 4-017 501 ->	KH20026 ProKIT
2.0 TSI 4motion	150 kW	2 l	07/11→08/15		
2.5 TDI 4motion	96 kW	2.5 l	07/04→11/09		
2.5 TDI 4motion	128 kW	2.5 l	07/04→11/09		
3.2 V6 4motion	173 kW	3.2 l	11/03→12/09		



**VW - TRANSPORTER I Bus / TRANSPORTER I Platform/Chassis / TRANSPORTER I Van / TRANSPORTER II Bus / TRANSPORTER II Platform/Chassis / TRANSPORTER II Van / TRANSPORTER III Platform/Chassis / TRANSPORTER III Van (22, 24, 25, 28, 26, 21, 23)** 01/50→07/92

























1.1 (44593)	18 kW	1.1 l	01/50→12/62	VIN 24-E-023828 ->	KH00058 ProKIT
1.2	25 kW	1.2 l	01/50→03/62		
1.2	25 kW	1.2 l	02/62→07/67		
1.2	25 kW	1.2 l	11/62→08/66		
1.5	31 kW	1.5 l	11/62→08/66		
1.5	32 kW	1.5 l	02/62→12/68		
1.5	32 kW	1.5 l	06/66→10/70		
1.5	32 kW	1.5 l	07/66→07/67		
1.6	34 kW	1.6 l	08/67→07/70		
1.6	35 kW	1.6 l	08/64→12/68		
1.6	35 kW	1.6 l	06/66→07/67		
1.6	37 kW	1.6 l	08/68→07/79		
1.6	37 kW	1.6 l	08/70→04/79		
1.6	37 kW	1.6 l	08/70→07/79		
1.6	37 kW	1.6 l	05/79→12/82		
1.7	49 kW	1.7 l	08/71→10/73		
1.7	49 kW	1.7 l	08/71→12/73		
1.8	50 kW	1.8 l	11/73→07/75		
1.9	61 kW	1.9 l	10/84→02/89		
1.9	66 kW	1.9 l	08/83→02/89		
2.0	51 kW	2 l	08/75→04/79		
2.0	51 kW	2 l	08/76→07/79		
2.0	51 kW	2 l	05/79→04/86		
2.1	70 kW	2.1 l	08/85→07/92		
2.1	82 kW	2.1 l	03/86→07/92		
1.9	44 kW	1.9 l	09/82→07/92	01/84 ->; VIN 24-E-023828 ->	KH00058 ProKIT
1.9	44 kW	1.9 l	10/82→07/92		
1.9	57 kW	1.9 l	08/82→07/92		
1.9	57 kW	1.9 l	10/82→07/92		















**VW - TRANSPORTER IV Platform/Chassis / TRANSPORTER IV Van (70E, 70L, 70M, 7DE, 7DL, 7, 70A, 70H, 7DA, 7DH)** 07/90→04/03

1.9 D	44 kW	1.9 l	09/90→12/95		KH10205 ProKIT
1.9 D	45 kW	1.9 l	07/90→12/95		
1.9 TD	50 kW	1.9 l	10/92→04/03		
2.4 D	55 kW	2.4 l	08/97→04/03		
2.4 D	57 kW	2.4 l	07/90→04/98		
2.4 D	57 kW	2.4 l	09/90→04/98		
2.5	85 kW	2.5 l	08/96→04/03		
2.5 TDI	65 kW	2.5 l	05/98→04/03		
2.5 TDI	65 kW	2.5 l	12/98→04/03		
2.5 TDI	75 kW	2.5 l	09/95→04/03		
2.5 TDI	111 kW	2.5 l	09/00→04/03		
2.8 VR6	103 kW	2.8 l	05/96→05/00		
2.8 VR6	150 kW	2.8 l	06/00→04/03		
2.0	62 kW	2 l	07/90→04/03		KH10205 ProKIT
2.5	81 kW	2.5 l	11/90→04/03	VIN 24-E-023828 ->	KH00058 ProKIT
2.4 D Syncro	57 kW	2.4 l	10/92→09/98		KH10205 ProKIT
2.5 Syncro	81 kW	2.5 l	11/92→11/01		
2.5 Syncro	81 kW	2.5 l	01/96→11/01		
2.5 Syncro	85 kW	2.5 l	08/96→04/03		
2.5 TDI Syncro	75 kW	2.5 l	09/95→04/03		
2.5 TDI Syncro	75 kW	2.5 l	05/98→04/03		

**VW - TRANSPORTER V Platform/Chassis / TRANSPORTER V Van (7JD, 7JE, 7JL, 7JY, 7JZ, 7F, 7HA, 7HH, 7EA, 7EH)** 04/03→08/15

1.9 TDI	62 kW	1.9 l	01/06→11/09	VIN -> 4-017 500	KH20025 ProKIT
1.9 TDI	63 kW	1.9 l	04/03→11/09	VIN 4-017 501 ->	KH20026 ProKIT
1.9 TDI	75 kW	1.9 l	06/06→11/09		
1.9 TDI	77 kW	1.9 l	04/03→11/09		
2.0	85 kW	2 l	11/03→05/13		
2.0	85 kW	2 l	11/03→08/15		
2.0 BiFuel	85 kW	2 l	05/11→08/15		
2.0 BiTDI	132 kW	2 l	09/09→08/15		
2.0 TDI	62 kW	2 l	09/09→08/15		
2.0 TDI	75 kW	2 l	09/09→08/15		
2.0 TDI	84 kW	2 l	05/11→08/15		
2.0 TDI	100 kW	2 l	05/10→08/15		
2.0 TDI	103 kW	2 l	09/09→08/15		
2.0 TSI	110 kW	2 l	07/12→08/15		
2.0 TSI	150 kW	2 l	05/11→08/15		
2.5 TDI	96 kW	2.5 l	04/03→11/09		
2.5 TDI	128 kW	2.5 l	04/03→11/09		

											
<b>VW - TRANSPORTER V Platform/Chassis / TRANSPORTER V Van (7JD, 7JE, 7JL, 7JY, 7JZ, 7F, 7HA, 7HH, 7EA, 7EH)</b>										<b>04/03→08/15</b>	
3.2 V6	170 kW	3.2 l	04/03→06/05		VIN -> 4-017 500					KH20025 ProKIT	
3.2 V6	170 kW	3.2 l	02/04→11/09		VIN 4-017 501 ->					KH20026 ProKIT	
3.2 V6	173 kW	3.2 l	08/03→05/06		VIN 4-017 501 ->					KH20026 ProKIT	
3.2 V6	173 kW	3.2 l	02/04→11/09		VIN -> 4-017 500					KH20025 ProKIT	
2.0 BiTDI 4motion	132 kW	2 l	09/09→08/15		VIN 4-017 501 ->					KH20026 ProKIT	
2.0 TDI 4motion	100 kW	2 l	05/10→08/15		VIN 4-017 501 ->					KH20026 ProKIT	
2.0 TDI 4motion	103 kW	2 l	09/09→08/15		VIN 4-017 501 ->					KH20026 ProKIT	
2.0 TSI 4motion	150 kW	2 l	07/11→08/15								
2.5 TDI 4motion	96 kW	2.5 l	07/04→11/09								
2.5 TDI 4motion	128 kW	2.5 l	04/04→11/09								
2.5 TDI 4motion	128 kW	2.5 l	07/04→11/09								
3.2 4motion	170 kW	3.2 l	11/03→11/09								
3.2 4motion	173 kW	3.2 l	11/03→11/09								
<b>VW - TRANSPORTER VI / CARAVELLE VI Bus / TRANSPORTER VI Platform/ Chassis / TRANSPORTER VI Van (SGB, SGJ, SHB, SHJ, SFD, SFE, SFL, SFZ, SJD, S, SGA, SGH, SHA, SHH)</b>										<b>04/15→</b>	
2.0 TDI	62 kW	2 l	04/15→07/19								KH20026 ProKIT
2.0 TDI	62 kW	2 l	04/15→11/19								
2.0 TDI	75 kW	2 l	04/15→11/19								
2.0 TDI	75 kW	2 l	04/15→12/19								
2.0 TDI	84 kW	2 l	05/16→08/19								
2.0 TDI	84 kW	2 l	05/16→11/19								
2.0 TDI	103 kW	2 l	04/15→11/19								
2.0 TDI	103 kW	2 l	04/15→12/19								
2.0 TDI	110 kW	2 l	04/15→								
2.0 TDI	110 kW	2 l	08/15→								
2.0 TDI	132 kW	2 l	04/15→11/19								
2.0 TDI	132 kW	2 l	04/15→12/19								
2.0 TDI	150 kW	2 l	06/15→								
2.0 TDI	150 kW	2 l	05/16→11/19								
2.0 TSI	110 kW	2 l	04/15→06/19								
2.0 TSI	110 kW	2 l	04/15→07/19								
2.0 TSI	150 kW	2 l	04/15→07/19								
2.0 TDI 4motion	103 kW	2 l	06/15→11/19							KH20026 ProKIT	
2.0 TDI 4motion	103 kW	2 l	06/15→12/19								
2.0 TDI 4motion	110 kW	2 l	08/15→								
2.0 TDI 4motion	110 kW	2 l	05/16→								
2.0 TDI 4motion	132 kW	2 l	06/15→11/19								
2.0 TDI 4motion	132 kW	2 l	06/15→12/19								
2.0 TDI 4motion	150 kW	2 l	06/15→								
2.0 TDI 4motion	150 kW	2 l	05/16→11/19								
2.0 TSI 4motion	150 kW	2 l	06/15→07/19								
<b>VW - T-ROC (A11, D11)</b>										<b>07/17→</b>	
1.0 TSI	81 kW	1 l	09/20→								KH30014 ProKIT
1.0 TSI	85 kW	1 l	07/17→11/20								KH20003 ProKIT
1.4 TSI	110 kW	1.4 l	08/20→								
1.5 TSI	110 kW	1.5 l	11/17→								
1.6 TDI	85 kW	1.6 l	03/18→06/21								
2.0 TDI	110 kW	2 l	03/18→								
2.0 TDI SCR	85 kW	2 l	11/20→								
1.5 TSI 4motion	110 kW	1.5 l	05/18→11/19								KH30014 ProKIT
2.0 R 4motion	221 kW	2 l	09/19→								KH30049 ProKIT
2.0 TDI 4motion	110 kW	2 l	09/17→								
2.0 TDI 4motion	140 kW	2 l	07/19→06/21								
2.0 TSI 4motion	140 kW	2 l	07/17→								
<b>VW - T-ROC Convertible (AC7, AC8)</b>										<b>12/19→</b>	
1.0 TSI	81 kW	1 l	09/20→								KH30014 ProKIT
1.0 TSI	85 kW	1 l	12/19→10/20								
1.5 TSI	110 kW	1.5 l	12/19→								
<b>VW - UP! (121, 122, BL1, BL2, BL3, 123)</b>										<b>08/11→08/20</b>	
1.0	44 kW	1 l	08/11→08/20								KH10010 ProKIT
1.0	55 kW	1 l	08/11→11/19								KH20021 ProKIT
1.0 EcoFuel	50 kW	1 l	11/12→08/20								
e-Up	60 kW		07/13→								
1.0 GTI	85 kW	1 l	11/17→08/20								KH20021 ProKIT
1.0 TSI	66 kW	1 l	05/16→09/18								

     				<b>11/91→09/98</b>	
<b>VW - VENTO Sedan (1H2)</b>					
1.4	40 kW	1.4 l	11/91→09/98	 ABS	<b>KH10055</b> ProKIT
1.4	44 kW	1.4 l	11/91→09/98		<b>KH00003</b> ProKIT
1.6	55 kW	1.6 l	09/92→09/98		
1.6	74 kW	1.6 l	10/94→09/98		
1.8	55 kW	1.8 l	11/91→09/98		
1.8	66 kW	1.8 l	11/91→09/98		
1.9 D	48 kW	1.9 l	11/91→09/98		
1.9 SDI	47 kW	1.9 l	04/97→09/98		
1.9 TD	55 kW	1.9 l	11/91→09/98		
1.9 TDI	66 kW	1.9 l	09/93→09/98		
1.9 TDI	81 kW	1.9 l	04/96→09/98		
2.0 GL	79 kW	2 l	05/96→12/97		
2.0	85 kW	2 l	11/91→09/98	 01/92 ->	<b>KH10193</b> ProKIT
					<b>KH00003</b> ProKIT
2.8 VR6	120 kW	2.8 l	01/92→09/98		<b>KH00003</b> ProKIT
2.8 VR6	128 kW	2.8 l	01/92→09/98		<b>KH10193</b> ProKIT
					<b>KH00003</b> ProKIT

















**YUGO - FLORIDA (VX65)**

**10/88→11/08**

1.3 (103 A)	50 kW	1.3 l	03/91→11/08		<b>KH20091 ProKIT</b>
1.4	51 kW	1.4 l	10/91→06/95		
1.4 Cat	52 kW	1.4 l	10/88→11/08		





     					
<b>ZASTAVA - 101</b>					<b>06/73→12/93</b>
1.1	37 kW	1.1 l	12/75→01/80	 ; 01/78 ->	<b>KH10369</b> ProKIT
1.1	40 kW	1.1 l	06/73→01/90	 ; 01/78 -> 06/82	<b>KH10369</b> ProKIT
1.1	41 kW	1.1 l	05/75→12/93		
1.3	48 kW	1.3 l	10/81→12/93	 ; -> 06/82	<b>KH10369</b> ProKIT
<b>ZASTAVA - YUGO</b>					<b>04/80→06/95</b>
0.9	33 kW	0.9 l	04/80→06/92	 ; 01/81 -> 12/90	<b>KH10369</b> ProKIT
					<b>KH20091</b> ProKIT
60 EFI (145 A)	44 kW	1.1 l	08/91→06/95		<b>KH20091</b> ProKIT
65 EFI (145 A)	48 kW	1.3 l	07/81→06/95		



**ABARTH**

46512970	KH10065
46512973	KH20022
46519901	KH20022
46773662	KH10065
51753791	KH10065
51754193	KH20022
55703171	KH10065
60815375	KH10065
60815429	KH20022
60815492	KH10065
71745047	KH10065

**ALFA ROMEO**

26800140	KH00102
26800330	KH00102
4330647	KH00061
4400918	KH30113
4470124	KH00107
46421951	KH10190
46423869	KH10371
46423870	KH10407
46425959	KH20161
46474537	KH10371
46512970	KH10065
46512972	KH10385
46512973	KH20022
46519901	KH20022
46529970	KH10181
46529970	KH10371
46739139	KH20083
46773662	KH10065
46783975	KH10385
46836200	KH10198
50700495	KH10198
50702890	KH30170
50706067	KH30170
50707555	KH30073
50707556	KH30100
51753789	KH10407
51753791	KH10065
51754191	KH10371
51754192	KH20034
51754193	KH20022
51754195	KH20051
51757885	KH20058
51813925	KH20068
51832400	KH20090
55703171	KH10065
5890987	KH10181
5890994	KH30113
5963034	KH30113
60523333	KH00111
60523334	KH00111
60535941	KH00056
60547722	KH00110
60613615	KH20097
60652011	KH20068
60652014	KH20049
60652720	KH20051
60671437	KH20068
60809721	KH20161
60811481	KH20161
60811546	KH10371
60812057	KH20047
60813089	KH10371
60814780	KH10371
60815375	KH10065
60815378	KH10385
60815429	KH20022
60815492	KH10065
60815880	KH10181
71714453	KH00107
71714460	KH10181
71714466	KH10407
71714472	KH10190
71714478	KH20068
71737612	KH20034
71737613	KH20034
71745047	KH10065
71747857	KH30113
71753813	KH30170
71753815	KH30073
71753816	KH30100
71753817	KH20083
71753821	KH10198
7613514	KH20161
7769902	KH20047
82374669	KH10371
82390273	KH10371

**AUDI**

171 498 625A	KH10186
171 498 625B	KH10186
171 498 625C	KH10186
171 498 625D	KH10186

**AUDI**

191 498 625 A	KH10055
191 598 625	KH00003
1H0 498 625	KH10193
1J0 498 625	KH10001
1J0 598 477	KH20010
1J0 598 625	KH10001
1K0 407 621 E	KH30048
1K0 498 621	KH30048
1K0 501 611 G	KH20003
1K0 598 611	KH20003
1T0 498 621	KH30002
1T0 598 611	KH20004
1T0 598 611 B	KH20004
211 405 645	KH00002
211 405 645 D	KH00002
211 405 645 D	KH00038
311 405 625 F	KH00002
311 405 625 F	KH00003
311 405 625 F	KH00038
311 405 625 N	KH00003
311 405 645	KH00003
311 405 645 B	KH00003
321 498 625 E	KH10194
331 598 625	KH10194
357 407 625	KH10055
357 407 625 A	KH10193
357 498 625 B	KH10055
357 498 625 C	KH10055
3C0 498 621	KH30002
3D0 498 607	KH20031
3D0 498 607 A	KH20031
3G0 598 611	KH20004
3G0 598 611 A	KH20004
420 598 625	KH20159
420 598 625 A	KH20159
420 598 625 D	KH20159
443 505 509	KH00002
443 505 509	KH00038
4A0 407 625 A	KH10136
4A0 498 625	KH10069
4A0 598 625	KH00002
4A0 598 625 A	KH00002
4B0 498 625	KH10066
4B0 498 625 A	KH10069
4B0 598 625 B	KH10134
4D0 407 625 E	KH10136
4E0 498 625 B	KH20031
4E0 598 625	KH20057
4F0 498 625	KH20071
4F0 498 625 A	KH20031
4F0 498 625 B	KH20071
4F0 598 611 A	KH30125
4F0 598 611 B	KH30125
4F0 598 625 A	KH20031
4G0 598 611	KH20141
4H0 498 625	KH20008
4H0 498 625 A	KH20008
4H0 498 625 B	KH20008
4H0 498 625 C	KH20008
4H0 498 625 D	KH20008
4H0 498 625 E	KH20008
5K0 498 621	KH30002
5K0 498 621 A	KH30048
5Q0 407 621 A	KH30014
5Q0 407 621 A	KH30049
5QF 598 611	KH20004
5WA 407 621	KH30048
5WA 407 621 A	KH30049
6C0 407 621	KH30045
6E0 407 621 C	KH20167
6E0 407 621 D	KH20167
6E0 598 611	KH20119
6G0 501 611	KH20141
6Q0 407 621 AD	KH30045
6Q0 407 621 AH	KH30045
6Q0 407 621 AJ	KH30045
6Q0 407 621 BR	KH30045
6Q0 598 611	KH20009
6Q0 598 611 F	KH20009
6R0 407 621 A	KH30045
6R0 407 621 E	KH30045
7L0498287	KH10152
861 498 625	KH10187
871 498 625 A	KH10187
8D0 598 625	KH00038
8E0 498 625 B	KH20032
8E0 501 611	KH30095
8E0 501 611 J	KH30095
8E0598611	KH20040
8E0 598 625	KH10136
8J0 598 625	KH30002
8J0 598 625A	KH30002
8K0 407 625	KH20008
8K0 407 625 A	KH20008
8K0 407 625 G	KH20008
8K0 407 625 J	KH20008
8K0 598 611 A	KH20064

**AUDI**

8K0 598 625	KH20008
8L0 498 625	KH10117
8L0 498 625 B	KH10117
8S0 498 625	KH30049
8S0 598 611	KH20004
8V0 498 625	KH30048
8V0 498 625 A	KH30014
8V0 498 625 B	KH30048
8V0 598 611 A	KH20003
8V0 598 625	KH30048
8V0 598 625 B	KH30048
8V0 598 625C	KH30049
8X0 498 625	KH30002
8X0 598 611	KH20009

**AUSTIN**

GHB377	KH00046
GHK1140	KH00051

**BMW**

31 20 1 095 616	KH30078
31 20 6 773 207	KH30102
31 20 6 779 735	KH30102
31 20 6 867 087	KH30110
31 20 6 872 888	KH30110
31 21 1 106 032	KH00041
31 21 1 106 033	KH00041
31 21 1 107 456	KH00039
31 21 1 119 571	KH00041
31 21 1 128 157	KH20111
31 21 1 128 569	KH20060
31 21 1 128 569	KH20111
31 21 1 129 576	KH20060
31 21 1 131 297	KH20060
31 21 1 131 297	KH20111
31 21 1 131 298	KH20112
31 21 6 634 103	KH00039
31 21 6 634 106	KH00039
31 21 6 765 157	KH30080
31 22 1 092 519	KH20115
31 22 1 093 427	KH30078
31 22 1 095 702	KH10109
31 22 2 229 501	KH20102
31 22 2 282 670	KH30179
31 22 6 750 217	KH30175
31 22 6 751 978	KH10153
31 22 6 757 024	KH20033
31 22 6 765 601	KH30063
31 22 6 783 913	KH10153
31 22 6 867 808	KH30102
33 40 6 789 970	KH20155
33 40 6 850 156	KH20124
33 40 6 850 159	KH20124
33 41 1 090 505	KH10109
33 41 1 095 238	KH20067
33 41 1 095 238	KH20085
33 41 1 095 652	KH20067
33 41 1 095 654	KH20067
33 41 1 124 358	KH10374
33 41 1 124 358	KH10408
33 41 1 130 617	KH10007
33 41 1 134 549	KH10188
33 41 2 220 987	KH10007
33 41 2 282 675	KH20189
33 41 6 762 317	KH10061
33 41 6 762 317	KH10203
33 41 6 762 317	KH10362
33 41 6 762 317	KH10374
33 41 6 762 321	KH10008
33 41 6 775 021	KH20124
33 41 6 775 842	KH10008
33 41 6 792 356	KH10354
33 41 6 792 361	KH10356
6 750 217	KH30175
6 757 024	KH20033
6762317	KH10061
6 792 361	KH10356
6 867 087	KH30110
6 872 888	KH30110

**BOND**

GHB110	KH00123
GHB111	KH00123

**CATERHAM**

GHB110	KH00053
GHB111	KH00053

**CHEVROLET**

13502785	KH30070
13502785	KH30105
13502828	KH30119
13502829	KH30089
13502872	KH30133



## CHEVROLET

13502873	KH30134
13507374	KH30105
13580135	KH30070
13580135	KH30105
13583478	KH30119
13583479	KH30089
13590795	KH30089
13591999	KH30134
19316545	KH30024
19318302	KH30024
19318306	KH30024
25903295	KH30087
25903358	KH30068
3 028 016	KH30119
3 28 000	KH30119
328292	KH30070
48 09 314	KH30068
48 14 304	KH30068
94535247	KH10141
94535249	KH10141
94535259	KH10226
94535982	KH10226
95459540	KH30181
95951600	KH30181
96264600	KH20128
96280244	KH20128
96285525	KH00014
96316634	KH00028
96316635	KH00028
96471775	KH10213
96471776	KH10213
96626339	KH30068
96626439	KH30087
96636585	KH30167
96639607	KH30187
96995000	KH10226

## CHRYSLER

04779218AB	KH30155
4397498	KH30174
4509766	KH20182
4509767	KH20182
4641196	KH30158
4641517AD	KH30077
4860074AA	KH20181
5105770AC	KH30164
5105770AD	KH30164
5141067	KH30174
5272447AA	KH10396
5272448AA	KH10396
BCA513074	KH30158

## CITROËN

144 008 82 80	KH30016
1606291880	KH30127
16 063 747 80	KH20086
16 066 235 80	KH10047
16 066 353 80	KH20022
160 812 83 80	KH20005
16 101 376 80	KH10027
2358 17	KH00094
3307 67	KH20076
3326.71	KH10120
3326 14	KH10216
3326 27	KH00035
3326 27	KH00061
3326 31	KH10051
3326 40	KH10089
3326 62	KH10078
3326 63	KH10101
3326 66	KH10391
3326 69	KH10234
3326 72	KH10043
3326 74	KH10164
3326 75	KH10065
3326 76	KH10043
3326 77	KH10065
3350.69	KH10047
3350.82	KH10006
3350.84	KH10047
3350.93	KH10119
3350.97	KH10047
3350 11	KH00091
3350 15	KH10192
3350 16	KH10052
3350 17	KH10051
3350 18	KH10062
3350 19	KH10081
3350 25	KH00043
3350 26	KH00019
3350 27	KH10089
3350 28	KH20095
3350 29	KH00035
3350 30	KH00080
3350 31	KH10165

## CITROËN

3350 32	KH10053
3350 33	KH10052
3350 70	KH10132
3350 71	KH20055
3350 72	KH10054
3350 81	KH10132
3350 86	KH10054
3350 87	KH10132
3350 91	KH10089
3350 92	KH10054
3448.A3	KH30016
3701 42	KH20046
3701 58	KH20191
3701 61	KH20095
3701 67	KH20171
3701 82	KH20086
3701 83	KH20059
3701 84	KH20022
3730 15	KH00094
3730 20	KH00107
3730 22	KH00019
3730 32	KH10091
3730 36	KH30163
3735 15	KH00043
3735 15	KH00107
3735 18	KH00019
3748.69	KH20038
3748.82	KH20001
3748.85	KH30064
3748.86	KH20001
3748.87	KH20001
3748.95	KH30016
3748.96	KH30015
3748.A3	KH30016
3748 13	KH00094
3748 17	KH10083
3748 28	KH20015
3748 30	KH20076
3748 31	KH20048
3748 35	KH20079
3748 36	KH20126
3748 39	KH10056
3748 41	KH20056
3748 43	KH20014
3748 44	KH20108
3748 68	KH20012
3748 70	KH20053
3748 72	KH20035
3748 75	KH20171
3748 76	KH20100
3748 77	KH10056
3748 78	KH20121
3748 79	KH20100
3748 80	KH20013
3748 83	KH10079
3748 88	KH20016
3748 89	KH20061
3748 90	KH10048
3748 94	KH10040
3748 99	KH30016
3748 A0	KH30015
3748 A1	KH10086
3748 A5	KH20138
3748 A7	KH20005
5451859	KH10185
6822JL	KH10106
75523458	KH10185
95603182	KH10062
95 619 160	KH10052
95619162	KH20046
95 654 076	KH10051
95 654 077	KH10081
95 666 965	KH20092
96 713 260 80	KH30111
96 743 752 80	KH30112
98 037 361 80	KH30111
98 037 361 80	KH30112

## CITROËN/PEUGEOT

16 066 235 80	KH10047
3326 31	KH10051
3350.69	KH10047
3350.84	KH10047
3350.97	KH10047
3350 16	KH10052
3350 17	KH10051
3350 32	KH10053
3350 33	KH10052
3350 72	KH10054
3350 86	KH10054
3350 92	KH10054
3748 28	KH20015
3748 43	KH20014
3748 68	KH20012
3748 80	KH20013
3748-82	KH20001

## CITROËN/PEUGEOT

3748-86	KH20001
3748-87	KH20001
3748 88	KH20016
3748 90	KH10048
3748 94	KH10040
95 619 160	KH10052
95 654 076	KH10051
96 418 876 80	KH20001

## DACIA

40 21 015 54 R	KH10380
40 21 070 49R	KH10080
40 21 073 14R	KH10184
40 21 080 22R	KH10080
40 21 095 33R	KH10214
43 21 020 69R	KH10142
43 21 031 06R	KH10142
60 01 543 344	KH10075
60 01 547 686	KH10199
60 01 547 696	KH10058
60 01 548 986	KH10177
60 01 550 915	KH10380
77 01 205 778	KH10075
77 01 205 812	KH10073
77 01 207 677	KH10380
77 01 208 058	KH10076
77 01 208 767	KH10073
77 01 210 004	KH10077
77 01 462 469	KH10075
77 01 465 181	KH10075
77 01 465 735	KH10073
77 03 090 266	KH00032
77 03 090 267	KH00032
82 00 381 151	KH10177

## DAEWOO

90279332	KH10108
94535247	KH10141
94535249	KH10141
94535254	KH10353
94535259	KH10226
94535982	KH10226
96264600	KH20128
96280244	KH20128
96285525	KH00014
96316634	KH00028
96316635	KH00028
96471775	KH10213
96471776	KH10213
96636585	KH30167
96639607	KH30187
96995000	KH10226

## DAIHATSU

90043-61387	KH10406
90043-63010	KH00101
90043-63012	KH00101
90043-63248-000	KH00108
90043-63253	KH10225
90043-63314	KH10390
90043-63315	KH10232
90043-63369	KH10232

## DAIMLER

C15230	KH00127
C19066	KH00127

## DODGE

4509766	KH20182
4509767	KH20182
52109947AF	KH30152
5272447AA	KH10396
5272448AA	KH10396

## DS

16 066 235 80	KH10047
3350.69	KH10047
3350.82	KH10006
3350.84	KH10047
3350.97	KH10047
3350 72	KH10054
3350 86	KH10054
3350 92	KH10054
3748 94	KH10040
3748 A1	KH10086

## FIAT

1300535080	KH00080
1326188080	KH10132
1328029080	KH10091
1328046080	KH10078
1328054080	KH10101
1330512080	KH10089



**FIAT**

1346650080	KH10234
1346651080	KH10155
1401393280	KH30016
140 139 34 80	KH30015
1440088280	KH30016
4330647	KH00035
4330647	KH00061
4400918	KH30113
4470124	KH00107
4470127	KH00043
46421951	KH10190
46423869	KH10371
46423870	KH10407
46425959	KH20161
46474537	KH10371
46512970	KH10065
46512972	KH10385
46512973	KH20022
46519901	KH20022
46519901	KH20130
46528566	KH10044
46529970	KH10181
46529970	KH10371
46531160	KH10111
46532573	KH10378
46539970	KH10163
46554135	KH20082
46576148	KH00075
46576155	KH00109
46773659	KH10044
46773659	KH10373
46773660	KH10043
46773662	KH10065
46783975	KH10385
46836196	KH10151
46836198	KH10151
46836200	KH10198
50700495	KH10198
50701247	KH20130
50704683	KH20130
51745702	KH10120
51748680	KH30061
51753789	KH10217
51753789	KH10407
51753790	KH10043
51753791	KH10065
51754191	KH10163
51754191	KH10371
51754192	KH20034
51754193	KH20022
5175492	KH20086
517549410	KH20059
51759727	KH20082
51810086	KH20109
51810087	KH20093
51943307	KH30184
51952935	KH30190
51965295	KH20082
52056182	KH20109
55703171	KH10065
5890987	KH10181
5890990	KH10044
5890991	KH10217
5890994	KH30113
5963034	KH30113
5996248	KH00019
5996253	KH00019
6000609410	KH20044
60055388	KH00109
60809721	KH20161
60811481	KH20161
60811546	KH10371
60812057	KH20047
60813089	KH10371
60814780	KH10371
60815375	KH10065
60815378	KH10385
60815429	KH20022
60815492	KH10065
60815880	KH10181
71714450	KH00035
71714452	KH00019
71714453	KH00107
71714454	KH00043
71714455	KH10369
71714458	KH10111
71714459	KH10043
71714460	KH10181
71714464	KH10378
71714464	KH10387
71714466	KH10217
71714466	KH10407
71714468	KH10044
71714472	KH10190
71714473	KH10089
71714480	KH10163
71728975	KH10391

**FIAT**

71729125	KH10151
71731547	KH10132
71737612	KH20034
71737613	KH20034
71740076	KH10378
71740076	KH10387
71742696	KH30075
71742699	KH10022
7174474	KH20095
71745046	KH10043
71745047	KH10065
71745047	KH10227
71747068	KH30108
71747713	KH20037
71747857	KH30113
71748673	KH10119
71753062	KH10043
71753810	KH20059
71753811	KH20086
71753818	KH10091
71753819	KH20082
71753820	KH10151
71753821	KH10198
71768040	KH30075
71768165	KH30075
71768167	KH30108
71769492	KH20082
7364573	KH10369
7555466	KH10044
7603485	KH20091
7613514	KH20161
7667784	KH00043
7746191	KH20105
7769902	KH20047
82374669	KH10163
82374669	KH10371
82390273	KH10163
82390273	KH10371
92403013	KH10151
9403350718	KH20055
9403350889	KH10119
940 374 89 59	KH30016
940 374 89 69	KH30015
9567217680	KH10089
9567217780	KH20095

**FORD**

0634048	KH00025
0634049	KH00025
1001718	KH10084
1053115	KH00013
1061596	KH10050
1085565	KH10093
1085569	KH10046
109E1200A2	KH00008
1112547	KH10046
1115019	KH30043
1118054	KH30191
1124904	KH30043
1133023	KH10038
1135043	KH10093
1137830	KH00004
1 137 830	KH00034
1141771	KH10097
1146689	KH30043
11-634048	KH00025
11-634049	KH00025
1201300	KH20039
1201302	KH00070
1201303	KH20074
1 201 304	KH20127
1201568	KH10037
1201568	KH10093
1201569	KH10046
1212541	KH10093
1212546	KH10093
1223640	KH20020
1225764	KH10411
1318154	KH20120
1326487	KH20020
1332888	KH30043
1333562	KH10210
1334289	KH20084
1334291	KH20084
1336139	KH20020
1362870	KH20084
1362872	KH20084
1375743	KH00004
1377907	KH20011
1377908	KH20018
1 377 910	KH20127
1377911	KH20023
1377912	KH20029
1383427	KH30043
1 417 338	KH20127
1437643	KH20045

**FORD**

1458701	KH20084
1458702	KH20084
1462160	KH20084
1463833	KH20087
1469186 7	KH20084
1469189	KH20084
1471852	KH30042
1471854	KH20020
1481197	KH30042
1484266	KH10105
1484269	KH10116
1491957	KH30042
1492160	KH00021
1492160	KH00023
1492160	KH00045
1496721	KH20087
1497386	KH10084
1497388	KH10208
1501642	KH10125
1501642	KH10126
1506577	KH30042
1508112	KH30042
1513043	KH10046
1513043	KH10070
1516151	KH00008
1538604	KH30091
1565443	KH00021
1565443	KH00045
1565444	KH00023
1582282	KH10070
1583567	KH00008
1583567	KH00013
1583567	KH00022
1587548	KH10111
1591389	KH00009
1591389	KH00078
1591389	KH00132
1668557	KH10125
1668557	KH10126
1699196	KH30069
1699368	KH10070
1702973	KH30143
1703150	KH30143
1706172	KH30143
1706173	KH30143
1730689	KH20022
1746588	KH10070
1760855	KH30143
1766628	KH30042
1769848	KH30081
1776845	KH30081
1785690	KH30143
1796001	KH10126
1814090	KH30143
1815483	KH30143
1851452	KH30143
1896739	KH30069
1899042	KH30069
1954435	KH00024
1954437	KH00024
1954476	KH10383
1959350	KH10384
1C1J-1A049-AA	KH20127
1C1J-1A049-BA	KH20074
1C1J-1A049-CA	KH00070
1C1J-1K018-AA	KH20039
1S71-2C299-AC	KH30043
1S71-2C299-AD	KH30043
1S71-2C299-AF	KH30043
1S71-2C299-AG	KH30043
1S71-2C299-AH	KH30043
1S71-2C299-AJ	KH30043
1S7-1K018-AA	KH10038
1S7J-1K018-AA	KH10411
2012478	KH00076
2215574	KH10125
2356115	KH10070
2S41-1A154-AA	KH10093
2S41-1A154-BA	KH10093
2S6J-1A049-AA	KH10093
2S6J-1K018-AA	KH10097
2S6J-1K018-BA	KH10046
2SJ-1A049-AA	KH10037
2T14-1K018-AA	KH10105
2T14-1K018-AB	KH10105
2T14-1K018-BA	KH10116
2T14-1K018-BB	KH10116
2T14-2C299-CA	KH20084
2T14-2C299-CB	KH20084
2T14-2C299-CC	KH20084
2T14-2C299-CD	KH20084
2T14-2C299-CE	KH20084
2T14-2C299-DA	KH20084
2T14-2C299-DB	KH20084
2T14-2C299-DD	KH20084
3024E-1200A	KH00045
3666951	KH00033



**FORD**

3666957	KH00112
3666963	KH00112
3897275	KH00070
3C11-1A049-AA	KH00029
3C11-1A049-AA	KH00066
3C1J-1A049BA	KH20120
3M34 1215 AA	KH10011
3M51-2C299-RBC	KH30042
3M51-2C300-CA	KH20020
3M51-2C300-CF	KH20020
3M51-2C300-CG	KH20020
3M51-2C300-CH	KH20020
3S6J-1K018-AA	KH10210
4052783	KH20039
4410218	KH10105
4410219	KH10116
4432022	KH10011
4479002	KH00029
4479002	KH00066
4488728	KH00033
4552765	KH00070
4858822	KH30043
5007028	KH00023
5007029	KH00022
5007040	KH00009
5010762	KH00078
5011392	KH00132
5012346	KH00128
5012347	KH00076
5012477	KH00128
5013161	KH00057
5015650	KH00025
5024195	KH00062
5024251	KH00063
5025899	KH00013
5025900	KH10127
5027620	KH10041
5911391	KH00132
5L3W-1225-AA	KH00070
5U7J-1A049-AA	KH00004
6077541	KH00022
6140418	KH00057
6140418	KH00076
6140418	KH00113
6197791	KH00013
6765406	KH10127
6C11-1A049-BA	KH20023
6C11-1A049-DA	KH20029
6C11-1K018-AA	KH20011
6C11-1K018-BA	KH20018
6C11-2C229-AA	KH20127
6G91-2C300-AAB	KH20045
6G91-2C300-GAB	KH20087
6G91-2C300-GAC	KH20087
6M21-1A047-AA	KH10084
70EB-1200-AA	KH00008
7220658	KH00004
72GB-1200-AA	KH00023
72GB-1215-AA	KH00023
72GB-1215-AA	KH00045
7M51-2C299-AA	KH30042
7M51-2C299-AB	KH30042
7M51-2C299-AC	KH30042
7M51-2C299-AD	KH30042
7M51-2C299-BC	KH30042
7T16-2C99-BB	KH20084
81AB-1215-AB	KH00009
81AB-1215-AB	KH00078
81AB-1215-AB	KH00132
81AB1238AA	KH00008
81AB-1238-AA	KH00022
81AB-1238-BA	KH00022
85GB-1238-AA	KH00057
85GB-1238-AA	KH00076
85GB-1238-AA	KH00113
86VX-1A049-CA	KH00025
89FB-1238-AD	KH00004
8V41-1215-BA	KH10125
8V41-1215-BA	KH10126
8V41-1215-BB	KH10125
8V41-1215-BB	KH10126
8V41-1215-BC	KH10125
8V41-1A049-AA	KH30091
8V41-1K018-AA	KH10126
8V51-1215-AB	KH10046
8V51-1215-AB	KH10070
8V5J-1K018-AA	KH10070
91AX-1A049-AA	KH00063
91AX-1K028-AA	KH00062
92VB-1225-BA	KH10127
92VX-1A049-AA	KH10127
93BX-1K018-AA	KH10041
95VW-1A047-AA	KH10084
96FX-1A049-AB	KH00004
96FX-1A049-AB	KH00034
97VX-1K018-AA	KH00013
98-AB1215-AB	KH10050

**FORD**

98AX-1A049-AA	KH10093
98AX-1A049-AB	KH10093
98AX-1K018-BA	KH10046
98AX-1K018-BB	KH10046
98BG-2C299-DC	KH30191
9S51J-1K018-BA	KH10065
A800X-1K028-BA	KH00023
A800X-1K028-CA	KH00022
A820X-1K018-RA	KH00078
A830X-1A049-FA	KH00132
A830X-1A049-GA	KH00132
A840X-1A049-BA	KH00076
A840X-1A049-DA	KH00076
A840X-1K018-AA	KH00128
A840X-1K018-BA	KH00128
A850X-4K018-AA	KH00057
ACP1-1215-AFA	KH10070
ACP1-1215-AFB	KH10070
AG9C-2B664-FAA	KH30081
AG9C-2B664-FAE	KH30081
BS51-1A034-AA	KH20022
BV61-2C299-AAB	KH30143
BV61-2C299-AAC	KH30143
BV61-2C299-AAD	KH30143
BV61-2C299-AAE	KH30143
BV61-2C299-AAF	KH30143
BV61-2C299-BAA	KH30143
BV61-2C299-BAB	KH30143
BV61-2C299-BAC	KH30143
DCP1-2C299-A1C	KH30069
DCP1-2C299-B6A	KH30069
F75W-1225-BA	KH00070
HPCP-1K018-AA	KH10070
XM34-1215-AA	KH00033
XM34-1215-BA	KH00112
XM34-1216-BA	KH00112
XM34-1216-CA	KH00033

**GENERAL MOTORS**

90510542	KH10206
----------	---------

**HONDA**

42200-S04-951	KH20199
42200-S10-A01	KH20173
42200-S1A-E02	KH20149
42200-S30-951	KH20178
42200-S30-C51	KH20175
42200-S30-J51	KH20175
42200-S5A-J01	KH20069
42200-S7A-008	KH20070
42200-S87-C51	KH20190
42200-S87-C52	KH20190
42200-SAA-003	KH20006
42200-SAA-G01	KH20006
42200-SAA-G02	KH20006
42200-SAA-G51	KH20007
42200-SAH-G51	KH20007
42200-SED-952	KH20137
42200-SEL-T01	KH20153
42200-SJF-951	KH20186
42200-SK7-A01	KH20169
42200-SMG-G51	KH20160
42200-ST3-E51	KH20169
42200-STK-951	KH30088
42200-SV2-N51	KH20200
42200-SV4-N51	KH20200
42200-T3V-A51	KH30003
42200-TA0A-51	KH30005
42200-TA0A-A511-M1	KH30005
42200-TF0-N51	KH20065
42200-TL0-G51	KH30012
42200-TOB-951	KH30188
42201-S10-A01	KH20148
4220-S5A-008	KH20103
42300-S2L-004	KH10410
42300-S2L-008	KH10410
44200-SXO-008	KH20176
44300-S1A-E01	KH10028
44300-S1A-E01	KH10029
44300-S5A-008	KH10024
44300-S6D-E01	KH10024
44300-S6D-E011	KH10024
44300-S6D-E012-M1	KH10024
44300-S9A-003	KH10035
44300-SAA-003	KH10018
44300-SCA-E51	KH10018
44300-SDA-A51	KH10388
44300-SDA-A52	KH10388
44300-SE0-003	KH10372
44300-SE0-018	KH10372
44300-SJK-G01	KH10229
44300-SMG-G01	KH10397
44300-SNA-951	KH10397
44300-SNA-952	KH10397
44300-SR3-004	KH10360

**HONDA**

44300-SR3-008	KH10360
44300-SR3-015	KH10360
44300-SR3-A01	KH10024
44300-ST3-E01	KH10024
44300-SWWW-E01	KH10229
44300-TF0-951	KH10031

**HYUNDAI**

32710-3A100	KH20151
51720-02000	KH10110
51720-02000	KH10346
51720-0Q000	KH10157
51720-11000	KH00017
51720-11100	KH00017
51720-1C000	KH10110
51720-21100	KH00077
51720-25000	KH10110
51720-29100	KH10110
51720-29150	KH10110
51720-29300	KH10110
51720-29400	KH10110
51720-2D000	KH10197
51720-2D100	KH10197
51720-2D200	KH10133
51720-2H000	KH10157
51720-2J001	KH10201
51720-2K000	KH10157
51720-38000	KH10133
51720-38000	KH10414
51720-38110	KH10123
51720-3A101	KH10123
51730-11000	KH00017
51730-11100	KH00017
51750-3J000	KH30086
51750-4H050	KH20157
52701-44120	KH00011
52710-02500	KH20195
52710-17100	KH20180
52710-22400	KH20170
52710-25100	KH20196
52710-25101	KH20196
52710-26500	KH10201
52710-26510	KH10201
52710-26530	KH10201
52710-29100	KH20197
52710-29670	KH20184
52710-29671	KH20184
52710-2C101	KH20110
52710-2C105	KH20110
52710-2D000	KH20197
52710-2D010	KH20168
52710-2D011	KH20168
52710-2D100	KH20180
52710-2D111	KH20185
52710-3A101	KH20151
52730-2G200	KH30176
52730-2H000	KH30067
52730-38000	KH30185
52730-38001	KH30185
52730-38002	KH30185
52730-38003	KH30185
52730-38100	KH30192
52730-38102	KH30192
52730-3K000	KH30176
52730-3K100	KH30171
52730-3K200	KH30161
52730-3S200	KH30147
52750-1C000	KH30168
52750-1C002	KH30168
52750-1G000	KH30168
52750-1G001	KH30168
52750-1G100	KH30062
52750-1G101	KH30062
52750-26100	KH20150
52750-2B100	KH30195
52750-2K000	KH30162

**INFINITI**

40202 1EAOB	KH30025
40202 4GAOA	KH30025
40202 CG010	KH30025
40202 CG01A	KH30025
40202 CG01B	KH30025
40202 EG000	KH30025
40202 EG06C	KH30025
40202 EJ70A	KH30025
40202-EJ70B	KH30026

**ISUZU**

8-84242-683-0	KH00087
8-94227-041-01	KH00026
8-94242-913-0	KH00087
8-94258-819-0	KH00026



**IVECO**

2996026	KH10392
42470834	KH10223
42470839	KH10223
42470840	KH10170
42470845	KH10170
42471033	KH10224
42471216	KH10386
42558516	KH10171
46393024	KH10171
500054867	KH10392
7180066	KH10171
7187566	KH10171
7188164	KH10392
8582739	KH00103
8582740	KH00103
93810034	KH20179
93813627	KH00102

**JAGUAR**

C15230	KH00127
C19066	KH00127
C2C19585	KH30096
C2P12624	KH10233
C2S3301	KH30107
C2S46771	KH30043
C2S46772	KH30107
C2S8276	KH10038
CAC 4306	KH00097
CAC 4999	KH00097
CAC6333	KH00131
JLM1708	KH00131
JLM21053	KH00131
MJA1830AD	KH10169
MJA1830AE	KH10169
MNC1830AA	KH10172
XR81723	KH10168
XR825194	KH30096

**JEEP**

05012825AA	KH00120
5105770AD	KH30164
5105770AE	KH30164
51943307	KH30184
51952935	KH30190
52089434AB	KH30142
52089434AC	KH30142
52098679AD	KH30116
52109947AF	KH30152
52128692AC	KH30076
52128692AD	KH30076
52128692AE	KH30076
52128692AF	KH30076
52128693AA	KH30093
52128693AB	KH30093
52128693AE	KH30093
52128693AF	KH30093
53007449	KH30159
J8134586	KH00081

**KIA**

00317 33075	KH00073
0K01A-33-047	KH00044
0K01A-33-075	KH00044
0K2 JT 33047	KH10016
0K552-33047	KH10114
0K72A-33-047	KH00084
0K72A-33-075	KH00084
0K9 A2 33047	KH10016
0K9A5-26-150	KH20198
50310-3E101	KH10154
50310-3E200	KH10154
50310-3E201	KH10154
51720-02000	KH10110
51720-02000	KH10346
51720-0Q000	KH10157
51720-0Q000	KH10352
51720-2D000	KH10197
51720-2D100	KH10197
51720-2D200	KH10133
51720-2H000	KH10157
51720-2J001	KH10201
51720-2K000	KH10157
51720-2K000	KH10352
51720-38000	KH10133
51720-38110	KH10123
51720-3A101	KH10123
51720-FD000	KH00082
51720-FL047	KH10114
51750-3J000	KH30086
51750-4D000	KH30103
52371-3E000	KH10211
52710-25100	KH20196
52710-25101	KH20196
52710-26500	KH10201
52710-26510	KH10201

**KIA**

52710-26530	KH10201
52710-29100	KH20197
52710-2D000	KH20197
52710-2D111	KH20185
52730-2G200	KH30176
52730-2H000	KH30067
52730-38100	KH30192
52730-38102	KH30192
52730-3K000	KH30176
52730-3K100	KH30171
52730-3K200	KH30161
52730-3S200	KH30147
52750-1C000	KH30168
52750-1C002	KH30168
52750-1G000	KH30168
52750-1G001	KH30168
52750-1G100	KH30062
52750-2B100	KH30195
52750-2K000	KH30162
KGA 2A 33047	KH10016
KK15033047	KH00079
KK150-33-047	KH00082
KKY01-33047	KH00100
KKY01-33075	KH00100
MB002-033-47	KH00100
MB002-33-047	KH00073
MB002-33-075	KH00100

**LADA**

2121-3103020-10	KH00098
-----------------	---------

**LANCIA**

1326188080	KH10132
1330512080	KH10089
4400918	KH30113
46421951	KH10190
46423870	KH10407
46425959	KH20161
46474537	KH10371
46512970	KH10065
46512972	KH10385
46512973	KH20022
46519901	KH20022
46528566	KH10044
46529970	KH10181
46529970	KH10371
46773659	KH10044
46773659	KH10373
46773660	KH10043
46773662	KH10065
46783975	KH10385
46836196	KH10151
46836198	KH10151
46836200	KH10198
50700495	KH10198
51753789	KH10407
51753790	KH10043
51753791	KH10065
51754191	KH10371
51754192	KH20034
51754193	KH20022
51813925	KH20068
55703171	KH10065
5890987	KH10181
5890990	KH10044
5890994	KH30113
5963034	KH30113
60652011	KH20068
60671437	KH20068
60809721	KH20161
60811481	KH20161
60811546	KH10371
60812057	KH20047
60813089	KH10371
60814780	KH10371
60815375	KH10065
60815378	KH10385
60815429	KH20022
60815492	KH10065
60815880	KH10181
71714459	KH10043
71714460	KH10181
71714466	KH10407
71714468	KH10044
71714472	KH10190
71714473	KH10089
71714478	KH20068
71729125	KH10151
71731547	KH10132
71737612	KH20034
71737613	KH20034
7174474	KH20095
71745046	KH10043
71745047	KH10065

**LANCIA**

71747857	KH30113
71753062	KH10043
71753820	KH10151
71753821	KH10198
7555466	KH10044
7603485	KH20091
7613514	KH20161
7769902	KH20047
82289841	KH10404
82374669	KH10371
82390273	KH10371
92403013	KH10151
9403350718	KH20055
9567217680	KH10089
9567217780	KH20095

**LAND ROVER**

ANR5861	KH10130
FTC1507	KH10231
FTC1507	KH10351
LR003157	KH20045
LR014147	KH30085
LR024267	KH10355
LR024508	KH10233
LR041425	KH10148
LR070453	KH10355
RFC 000010	KH10148
RFM500010	KH30085
RFM500020	KH10159
RLB000011	KH10160
RLB100042	KH10159
RTC3416	KH00125
RTC3426	KH00125
RTC 3429	KH00136
STC3482	KH00037
STC 4382	KH00106
STC 4382	KH00136

**LDV**

RTC3412	KH00130
RTC3427	KH00060
RTC3436	KH00130

**LEXUS**

42410-0E050	KH30118
42410-30020	KH30151
42410-30021	KH30151
42450-60050	KH20125
42460-60010	KH20131
435500-30010	KH30138
43550-30030	KH30033
43550-30031	KH30033
43550-47010	KH30121
43550-47011	KH30121
43560-30010	KH30177
43560-30011	KH30177
43560-30030	KH30034
43560-30031	KH30034
90363-32035	KH10128
90369-32003	KH10128
90369-35034	KH10381
90369-38019	KH10023
90369-43005	KH10207
90369-43008	KH10182
90369-43009	KH10182
90369-45006	KH10025
90369-49001	KH10347
90369-49002	KH10347
90369-A0002	KH10025
90903-63006	KH10381

**LOTUS**

A036C6041Z	KH00124
A036C6042Z	KH00124

**MAZDA**

0317-33-075	KH00073
9960-30-208	KH00137
B001-33-047	KH00079
B001-33-047	KH00082
B002-33-047	KH00073
B002-33-047	KH00100
B002-33-075	KH00100
B455-26-15XA	KH20094
B455-26-15XB	KH20094
B 4553 3047 C	KH10017
B 4553 3047 D	KH10017
B603-26-15XA	KH20166
B603-26-15XB	KH20166
B603-26-15XC	KH20166
BB2M-26-15XA	KH30153
BB2M-26-15XB	KH30153
BP4K-26-15XA	KH30153
BP4K-26-15XB	KH30153



**MAZDA**

BP4K-26-15XC	KH30153
BP4K-33-15XB	KH20106
BP4L-33-047	KH10156
BP4L-33-047A	KH10156
BP4L-33-047B	KH10156
D10H-26-15X	KH30051
D350-26-151B	KH10093
D350-26-151C	KH10093
D651-25-15XD	KH30120
D651-26-15XA	KH30120
D651-26-15XB	KH30120
D651-26-15XC	KH30120
D651-26-15XE	KH30120
D651-33-047A	KH10070
D651-33-047B	KH10070
FB01 26 151 A	KH10016
FB01 26 151 B	KH10016
FB01 26 151 C	KH10016
FB01 26 151 D	KH10016
FB01 26 151 E	KH10016
FB01 26 151 F	KH10016
G14V-26-15X	KH20129
G14V-26-15XA	KH20129
G14V-26-15XB	KH20129
G331-26-15X	KH30182
G33S-26-15XA	KH30182
G33S-26-15XB	KH30182
G33S-26-15XC	KH30182
GA2A 33047	KH10016
GAM6-33-047	KH10161
GAM6-33-047A	KH10161
GAM6-33-047B	KH10161
GD1D-33-047	KH10230
GF4K-26-15X	KH20135
GF4K-26-15XA	KH20135
GF4K-26-15XB	KH20135
GP9A33047A	KH10403
GP9A33047B	KH10403
GP9A33047C	KH10403
GP9A33047D	KH10403
GS1D-33-047C	KH10230
N243-26-15X	KH30050
NA01-33-04X	KH20163
NA01-33-04XA	KH20163
NA23-33-04XA	KH20114
NA23-33-04XC	KH20136
S083-33-047	KH00033
S083-33-047	KH00119
S08-333-075	KH00033
S231-33-047	KH00112
S231-33-047	KH00119
S231-33-075	KH00119
S321-3375	KH00112
UH71-33-047	KH00119
UH71-33-061B	KH00033
UM51 33 047	KH10011

**MERCEDES-BENZ**

140 981 03 05	KH00015
203 330 00 51	KH00007
210 980 01 16	KH10377
210 980 05 16	KH10377
212 330 00 25	KH00015
218 330 01 25	KH00015
220 330 00 51	KH10377
220 980 00 16	KH10377
220 980 01 16	KH10377
220 981 00 27	KH10377
230 330 03 25	KH00015
415 334 07 00	KH10380
A 000 980 05 16	KH10377
A 000 981 58 05	KH00031
A 000 981 58 05	KH00040
A 000 981 58 05	KH00059
A 000 981 58 05	KH00099
A 000 981 59 05	KH00031
A 000 981 59 05	KH00040
A 000 981 59 05	KH00099
A 000 981 63 05	KH00055
A 001 980 29 02	KH00055
A 001 981 89 05	KH00118
A 002 980 19 02	KH00085
A 002 980 30 02	KH00007
A 002 980 31 02	KH00007
A 002 980 65 02	KH00015
A 002 980 65 02	KH00020
A 002 980 65 02	KH00085
A 002 981 13 05	KH00118
A 002 981 19 05	KH00118
A 002 981 66 05	KH00118
A 005 981 53 05	KH00118
A 006 981 16 05	KH00059
A 006 981 56 05	KH00118
A 006 981 58 05	KH00010
A 007 981 04 05	KH00118
A 007 981 13 05	KH00010

**MERCEDES-BENZ**

A 007 981 55 05	KH00118
A 011 981 89 05	KH10129
A 017 981 46 05	KH10129
A 107 330 00 51	KH00031
A 115 330 00 51	KH00040
A 116 330 00 51	KH00055
A 124 980 05 16	KH10191
A 129 330 03 51	KH00085
A 129 980 02 16	KH10039
A 129 980 03 16	KH10039
A 140 330 02 51	KH00105
A 140 980 06 16	KH10377
A 140 981 03 05	KH00015
A 140 981 03 05	KH00020
A 140 981 03 05	KH00105
A 140 981 04 27	KH10377
A 140 981 05 05	KH00105
A 163 330 0051	KH10166
A 164 981 01 06	KH10140
A 164 981 04 06	KH10140
A 168 981 03 27	KH10209
A 168 981 06 27	KH10147
A 168 981 07 27	KH10183
A 169 981 00 06	KH10049
A 169 981 00 06	KH10228
A 169 981 00 27	KH30144
A 169 981 01 27	KH10049
A 169 981 01 27	KH10228
A 201 220 01 51	KH00059
A 201 330 01 51	KH00059
A 201 330 02 51	KH00099
A 202 980 00 16	KH10039
A 202 980 01 16	KH10039
A 202 981 01 27	KH10039
A 203 980 00 16	KH10039
A 209 980 00 16	KH10039
A 210 330 01 51	KH10394
A 210 981 02 27	KH10415
A2119810227	KH20104
A 221 330 02 25	KH00072
A 230 981 01 27	KH20062
A 246 334 00 06	KH30189
A 246 981 00 06	KH10368
A 414 981 01 27	KH10147
A 414 981 02 05	KH10366
A 415 334 06 00	KH10112
A 638 981 00 27	KH10145
A 639 330 13 32	KH10364
A 639 981 04 27	KH10364
A 901 330 10 25	KH00010
A 902 350 00 68	KH10129
A 902 350 14 10	KH10129
A 903 350 02 49	KH30140
A 906 350 01 49	KH30094

**MG**

GHB102	KH00126
GHB105	KH00126
GHB127	KH00121
GHB130	KH00122
GHB377	KH00046
GHK 1366	KH10189
GHK1596	KH20144
GHK 1692	KH10148
GHK 1693	KH20098
RFM000050	KH10189
RLB000050	KH20144
RLB000060	KH20145
RLB 100292	KH20098
RUD100150	KH10148

**MINI**

31 22 6 756 889	KH30006
31 22 6 776 162	KH30007
31 22 6 776 671	KH30007
33 41 6 756 830	KH30008
33 41 6 786 552	KH30010
33 41 6 786 552	KH30032

**MITSUBISHI**

3555A015	KH20156
3758A004	KH20134
3785 A002	KH20005
3785A009	KH30127
3785A015	KH30163
3785A019	KH10032
3785-A024	KH20005
3785 A026	KH20005
3885A013	KH20041
3885A014	KH20156
3885A017	KH10164
MA125842	KH00017
MA125843	KH00017
MB101397	KH30127
MB303865	KH10398

**MITSUBISHI**

MB316451	KH20193
MB349416	KH00077
MB808442	KH10221
MB844919	KH20194
MB864967	KH20193
MB864968	KH20193
MB9322726	KH00011
MB992372	KH20044
MN101347	KH10164
MN102067	KH20072
MN102068	KH20072
MR223284	KH20202
MR316631	KH20188
MR369518	KH20096
MR403558	KH20187
MR418068	KH20133
MR418524	KH20133
MR449797	KH10221
MR47533	KH20096
MR491449	KH10365
MR519097	KH10158
MR527452	KH20132
MR527453	KH20140
MR594080	KH10399
MR594142	KH30186
MR 594443	KH30021
MR992374	KH20044

**NISSAN**

039-05923	KH00117
19802902	KH00117
40202 1EA0B	KH30025
40202 1KA0A	KH30024
40202 3DA0A	KH30024
40202 3LH0A	KH30165
40202 3PU0A	KH30024
40202 3RA0A	KH30024
40202 3SH0A	KH30024
40202 3SH1A	KH30024
40202 4AE0A	KH30166
40202 4AFOA	KH30024
40202 4Ea1A	KH30166
40202 4GA0A	KH30025
40202 5SK0A	KH30024
40 20 275 85 R	KH30131
40202-AL510	KH30149
40202-AL56C	KH30149
40202-BA60A	KH30024
40202-CA06C	KH30027
40202-ED000	KH30011
40202-ED00A	KH30011
40202-ED02A	KH30011
40202-ED05A	KH30011
40202 EG000	KH30025
40202 EG06C	KH30025
40202 EJ70A	KH30025
40202-EN010	KH30024
40202-JG000	KH30024
40202-JG01A	KH30024
40202-JG01B	KH30024
40202-JX00A	KH30165
40202-ZM70A	KH30027
40210-00Q0E	KH10115
40210-00Q0H	KH10139
40210-00Q0L	KH10174
40210-00QAA	KH10057
40210-00QAC	KH10100
40210-00QAE	KH10149
40210-00QAF	KH10196
40210-00QAG	KH10115
40210-00QAK	KH10115
40210-1HA1A	KH10176
40210-1HA9D	KH10176
40210-2S600	KH00024
40210-2Y000	KH10034
40210-30R01	KH10009
40210-30R06	KH10009
40210-32R01	KH10009
40210-32R06	KH10009
40210-4M400	KH10003
40210-4Z000	KH10003
40210-50W00	KH00024
40210-90J00	KH10009
40210-99B00	KH10180
40210-9X50A	KH00050
40210-AX000	KH10380
40210-F1700	KH00117
40210-F3900	KH00050
40215-0F000	KH00024
40215-50W00	KH00024
40215-9X50A	KH00050
40215-C6000	KH00036
40215-F1700	KH00117
40215-F3901	KH00050
43200-0M800	KH20158
43200-30R06	KH20192



**NISSAN**

43200-30R07  
43200-AV700  
43200-BM400  
43200-BM500  
4320-OM801  
43202-0L710  
43202-1J60A  
43202 1KA0A  
43202-1YPDA  
43202-34B00  
43202-4X00A  
43202-72B00  
43202 BA60A  
43202-CA000  
43202-EE500  
43202-EN100  
43202-EN11A  
43202-JG200  
43202-JG21B  
43202-JX00A  
43 20 2JY 30A  
43202-ZP80A  
43210-00Q0A  
43210-00Q0B  
43210-00Q0C  
43210-00Q0D  
43210-00Q0M  
43210-00Q1B  
43210-00QAB  
43210-00QAC  
43210-00QAC  
43210-00QAD  
43210-0VV000  
43210-1HA1A  
43210-1HA9D  
43210-1HM0A  
43210-42G10  
43210-4A00A  
43210-4A00D  
43210-8H300  
43210 AG000  
43210-AL500  
43210-AL505  
43210-AX000  
43210-AZ300  
43210-C9300  
43215-00Q0A

KH20192  
KH20142  
KH20152  
KH20139  
KH20158  
KH20183  
KH30004  
KH30023  
KH30145  
KH20143  
KH30137  
KH20143  
KH30023  
KH30146  
KH30145  
KH30131  
KH30131  
KH30131  
KH30131  
KH30178  
KH30131  
KH30137  
KH10138  
KH10143  
KH00086  
KH20101  
KH10090  
KH10138  
KH10064  
KH10090  
KH20101  
KH10082  
KH10384  
KH10175  
KH10175  
KH10175  
KH10175  
KH10383  
KH10033  
KH10033  
KH10400  
KH10026  
KH20201  
KH20201  
KH10073  
KH10073  
KH00036  
KH00086

**OPEL**

16 04 007  
16 04 017  
16 04 018  
1604020  
16 04 287  
16 04 292  
16 04 301  
16 04 302  
16 04 306  
16 04 307  
16 04 314  
16 04 315  
16 04 316  
16 04 358  
1604360  
25903295  
25903358  
3 28 000  
3 28 001  
3 28 002  
3 28 003  
3 28 006  
3 28 006  
3 28 011  
3 28 012  
328013  
328014  
3 28 016  
3 28 018  
3 28 021  
3 28 023  
3 28 037  
3 28 038  
3 28 042  
3 28 042  
3 28 042  
3 28 042  
3 28 103  
3 28 103  
3 28 106  
3 28 109  
3 28 292  
3 28 292  
3 28 292  
3 28 292  
328980  
3 30 012  
3 30 019  
3 30 023  
4 14 301  
4 15 203  
4 20 004  
4 20 240  
4 21 000  
44 03 023  
44 030 44  
44 03 942  
44 08 277  
4408668  
44 08 669  
4412598  
44 19 183  
44 19 184  
44 21 076  
44 21 370  
44 213 78  
44 22 229  
4430305  
45 01 154  
45 01 155  
47 00 322  
47 06 538  
47 06 538  
47 09 078  
47 11 556  
48 04 658  
48 09 314  
48 14 139  
48 14 304  
90005147  
9005147  
90065431  
90235281  
90279332  
90447280  
904486460  
90486461  
90486463  
90486468  
90510542  
90510543  
90510544  
90510629  
90511494  
90540069  
90540262  
9111023

KH10113  
KH20017  
KH20017  
KH20030  
KH10218  
KH10219  
KH30114  
KH30054  
KH30054  
KH30055  
KH30071  
KH30041  
KH30044  
KH20017  
KH20030  
KH30087  
KH30068  
KH30119  
KH30089  
KH30133  
KH30134  
KH30070  
KH30105  
KH10151  
KH10198  
KH20109  
KH20093  
KH30119  
KH00093  
KH30089  
KH30070  
KH30105  
KH30183  
KH30196  
KH10063  
KH00093  
KH00026  
KH00026  
KH00065  
KH10219  
KH20017  
KH20118  
KH30055  
KH10100  
KH10064  
KH00104  
KH10090  
KH10149  
KH10196  
KH10115  
KH10139  
KH10138  
KH10143  
KH00086  
KH00086  
KH10174  
KH10195  
KH10092  
KH10215  
KH10122  
KH10173  
KH10137  
KH10030  
KH30087  
KH30068  
KH30087  
KH30068  
KH00005  
KH00088  
KH10107  
KH10219  
KH10218  
KH10376  
KH10108  
KH10218  
KH00005  
KH10219  
KH10206  
KH30114  
KH10376  
KH30054  
KH30055  
KH30054  
KH30055  
KH10100

**OPEL**

9111044  
9111942  
91149606  
91159917  
91160086  
91160087  
9117619  
9117620  
9117622  
9119931  
9120128  
9120129  
9120273  
9161454  
9161455  
9195608  
9196286  
9196298  
9203934  
9213602  
9213602  
92 14 025  
931168843  
93161059  
93161376  
93168535  
93168760  
93170611  
93171495  
93175327  
93178625  
93178626  
93178651  
93178652  
93178661  
93182913  
93186387  
93186388  
93186389  
93188477  
93188889  
93188890  
93190215  
93190216  
93193920  
93197149  
93197150  
94227041  
94258819  
95507285  
95507796  
95511623  
95511624  
95511659  
95511660  
95512288  
95513921  
95516872  
95517093  
95517150  
96626339  
96626439

KH10064  
KH00104  
KH00065  
KH10090  
KH10149  
KH10196  
KH30057  
KH30058  
KH30059  
KH30114  
KH30054  
KH30055  
KH30130  
KH10195  
KH10092  
KH10063  
KH10113  
KH20118  
KH10215  
KH10122  
KH10173  
KH10121  
KH10143  
KH10115  
KH10115  
KH10348  
KH20017  
KH30071  
KH30061  
KH30061  
KH30041  
KH30044  
KH30072  
KH30046  
KH30065  
KH30074  
KH30061  
KH30065  
KH30074  
KH10065  
KH20017  
KH20030  
KH10137  
KH10139  
KH10138  
KH00026  
KH00026  
KH00086  
KH10030  
KH10151  
KH10198  
KH20109  
KH20093  
KH20017  
KH10151  
KH10174  
KH20030  
KH20017  
KH30068  
KH30087

**PEUGEOT**

140 139 34 80  
144 008 82 80  
1606291880  
16 063 747 80  
16 066 235 80  
16 066 353 80  
160 812 83 80  
16 101 376 80  
2358 17  
3307 67  
3326.71  
3326 14  
3326 27  
3326 27  
3326 31  
3326 40  
3326 62  
3326 63  
3326 66  
3326 69  
3326 72  
3326 74  
3326 75  
3326 76  
3326 77  
3350.69  
3350.82  
3350.84  
3350.93  
3350.97  
3350.98  
3350 11

KH30015  
KH30016  
KH30127  
KH20086  
KH10047  
KH20022  
KH20005  
KH10027  
KH00094  
KH20076  
KH10120  
KH10216  
KH00035  
KH00061  
KH10051  
KH10089  
KH10078  
KH10101  
KH10391  
KH10234  
KH10043  
KH10164  
KH10065  
KH10043  
KH10065  
KH10047  
KH10119  
KH10047  
KH10006  
KH00091





**PEUGEOT**

3350 15	KH10192
3350 16	KH10052
3350 17	KH10051
3350 18	KH10062
3350 19	KH10081
3350 25	KH00043
3350 26	KH00019
3350 27	KH10089
3350 28	KH20095
3350 29	KH00035
3350 30	KH00080
3350 31	KH10165
3350 32	KH10053
3350 33	KH10052
3350 70	KH10132
3350 71	KH20055
3350 72	KH10054
3350 81	KH10132
3350 86	KH10054
3350 87	KH10132
3350 91	KH10089
3350 92	KH10054
3701 42	KH20046
3701 58	KH20191
3701 61	KH20095
3701 67	KH20171
3701 82	KH20086
3701 83	KH20059
3701 84	KH20022
3730 15	KH00094
3730 20	KH00107
3730 22	KH00019
3730 32	KH10091
3730 36	KH30163
3735 15	KH00043
3735 15	KH00107
3735 18	KH00019
3748.69	KH20038
3748.82	KH20001
3748.85	KH30064
3748.86	KH20001
3748.87	KH20001
3748.A3	KH30016
3748.A6	KH20002
3748 13	KH00094
3748 17	KH10083
3748 28	KH20015
3748 30	KH20076
3748 31	KH20048
3748 35	KH20079
3748 36	KH20126
3748 39	KH10056
3748 41	KH20056
3748 43	KH20014
3748 44	KH20108
3748 68	KH20012
3748 70	KH20053
3748 72	KH20035
3748 75	KH20171
3748 76	KH20100
3748 77	KH10056
3748 78	KH20121
3748 79	KH20100
3748 80	KH20013
3748 83	KH10079
3748 88	KH20016
3748 89	KH20061
3748 90	KH10048
3748 94	KH10040
3748 99	KH30016
3748 A0	KH30015
3748 A1	KH10086
3748 A5	KH20138
3748 A7	KH20005
5451859	KH10185
6822JL	KH10106
75523458	KH10185
95603182	KH10062
95 619 160	KH10052
95619162	KH20046
95 654 076	KH10051
95 654 077	KH10081
95 666 965	KH20092
96 713 260 80	KH30111
96 743 752 80	KH30112
96 858 633 80	KH20002
98 037 361 80	KH30111
98 037 361 80	KH30112

**PORSCHE**

113 501 277 A	KH00068
113 501 283	KH00068
311 405 625 F	KH00067
311 405 645	KH00067
7L0498287	KH10152
8K0 704 625 B	KH20008

**PORSCHE**

999 053 041 03	KH10409
999 053 042 10	KH10349
999 053 054 05	KH10349
999 053 054 05	KH10350
999 059 065 00	KH00031
999 059 089 01	KH00133
999 059 090 00	KH00133
999 059 098 00	KH00031

**RENAULT**

3748 A5	KH20138
40030-3865R	KH10013
40202 2560R	KH30024
40 20 24E A0A	KH30166
40202 JY00A	KH30024
40 21 000 06R	KH30101
40 21 015 54 R	KH10380
40 21 018 77R	KH10200
40 21 037 08R	KH10139
40 21 046 30R	KH30101
40 21 046 87R	KH30101
40 21 050 19R	KH30101
40 21 056 62R	KH30101
40210-5733R	KH10013
40 21 065 66R	KH10149
40 21 070 49R	KH10080
40 21 073 14R	KH10184
40 21 074 35R	KH10174
40 21 080 22R	KH10080
40 21 095 33R	KH10214
40 21 096 97R	KH10115
43206 7636R	KH30029
43 21 020 69R	KH10142
43 21 021 03R	KH10144
43 21 031 06R	KH10142
43 21 041 77R	KH10138
43 21 048 99R	KH10143
43 21 051 62R	KH00086
43 21 070 45R	KH10138
43 21 098 18R	KH00086
60 01 543 344	KH10075
60 01 544 851	KH00090
60 01 547 686	KH10199
60 01 547 696	KH10058
60 01 548 986	KH10177
60 01 550 915	KH10380
60 25 370 536	KH10393
60 25 370 612	KH20116
60 25 371 670	KH10393
77 00 803 924	KH20113
77 00 820 849	KH20077
77 01 204 667	KH20036
77 01 204 689	KH20077
77 01 204 693	KH20113
77 01 205 170	KH20147
77 01 205 416	KH10195
77 01 205 417	KH10092
77 01 205 471	KH20080
77 01 205 472	KH20099
77 01 205 477	KH20078
77 01 205 499	KH20050
77 01 205 596	KH10082
7701205692	KH10405
77 01 205 778	KH10075
77 01 205 779	KH10057
77 01 205 780	KH10085
77 01 205 812	KH10073
77 01 205 972	KH10167
77 01 206 353	KH20081
77 01 206 740	KH10100
77 01 206 742	KH10064
77 01 206 771	KH10150
77 01 206 847	KH10149
77 01 206 848	KH10196
77 01 206 849	KH10090
77 01 207 358	KH10115
77 01 207 677	KH10380
77 01 207 966	KH10115
77 01 208 058	KH10076
77 01 208 059	KH10104
77 01 208 075	KH20101
77 01 208 427	KH10115
77 01 208 767	KH10073
77 01 208 950	KH10112
77 01 208 966	KH20066
77 01 209 838	KH10112
77 01 210 004	KH10077
77 01 450 639	KH00090
77 01 460 637	KH00092
77 01 460 639	KH00090
77 01 460 640	KH00089
77 01 462 020	KH20075
77 01 462 469	KH10075
77 01 463 523	KH10074
77 01 463 986	KH10370
77 01 463 987	KH10082

**RENAULT**

77 01 465 181	KH10075
77 01 465 647	KH00096
77 01 465 735	KH10073
77 01 466 803	KH10085
77 01 467 860	KH10085
77 01 468 409	KH00095
77 01 469 682	KH10393
77 01 470 552	KH10167
77 03 090 203	KH00129
77 03 090 266	KH00032
77 03 090 267	KH00032
77 03 090 269	KH00129
77 03 090 270	KH00092
77 03 090 271	KH00092
77 03 090 313	KH10074
77 03 090 325	KH10370
77 03 090 434	KH10370
77 04 002 263	KH20036
82 00 351 777	KH10200
82 00 381 151	KH10177
82 00 416 590	KH20066

**ROVER**

ADU9475EVA	KH10202
GHB102	KH00126
GHB105	KH00126
GHB105	KH00126
GHB127	KH00121
GHB213	KH00135
GHB377	KH00046
GHB377	KH00135
GHK1140	KH00051
GHK1285	KH10202
GHK 1366	KH10189
GHK1548	KH00135
GHK1549	KH00135
GHK1550	KH00135
GHK1559	KH10357
GHK1596	KH20144
GHK 1692	KH10148
GHK 1693	KH20098
RFB000050	KH10189
RLB000050	KH20144
RLB000060	KH20145
RLB 100292	KH20098
RUD100070	KH10357
RUD100150	KH10148

**SAAB**

13502785	KH30070
24 421 906	KH30071
328292	KH30070
43 98 046	KH30114
4689923	KH10222
47 78 494	KH30114
48 39 122	KH30114
5058185	KH30122
5392493	KH30098
93 170 611	KH30071
93175327	KH30061
93186387	KH30061

**SANTANA**

09269-41001	KH10072
43462-85C00	KH10072

**SEAT**

171 498 625A	KH10186
171 498 625B	KH10186
171 498 625C	KH10186
171 498 625D	KH10186
191 498 625 A	KH10055
191 598 625	KH00003
1H0 498 625	KH10193
1J0 498 625	KH10001
1J0 598 477	KH20010
1J0 598 625	KH10001
1K0 407 621 E	KH30048
1K0 498 621	KH30048
1K0 501 611 G	KH20003
1K0 598 611	KH20003
1S0 498 625	KH10010
1S0 498 625A	KH10010
1S0 598 611	KH20021
1T0 498 621	KH30002
1T0 598 611	KH20004
1T0 598 611 B	KH20004
211 405 645	KH00002
211 405 645 D	KH00002
211 405 645 D	KH00038
311 405 625 F	KH00002
311 405 625 F	KH00003
311 405 625 F	KH00038
311 405 625 N	KH00003
311 405 645	KH00003



**SEAT**

311 405 645 B	KH00003
357 407 625	KH10055
357 407 625 A	KH10193
357 498 625 B	KH10055
357 498 625 C	KH10055
3C0 498 621	KH30002
3G0 598 611	KH20004
3G0 598 611 A	KH20004
443 505 509	KH00002
443 505 509	KH00038
4A0 598 625	KH00002
4A0 598 625 A	KH00002
5K0 498 621	KH30002
5K0 498 621 A	KH30048
5Q0 407 621 A	KH30049
5QF 598 611	KH20004
5WA 407 621	KH30048
5WA 407 621 A	KH30049
6C0 407 621	KH30045
6K9 501 477	KH20052
6N0 407 625	KH10358
6N0 498 625	KH10358
6Q0 407 621 AD	KH30045
6Q0 407 621 AH	KH30045
6Q0 407 621 AJ	KH30045
6Q0 407 621 BR	KH30045
6Q0 598 611	KH20009
6Q0 598 611 F	KH20009
6R0 407 621 A	KH30045
6R0 407 621 E	KH30045
6X0 501 477	KH20117
6X0 598 477	KH20117
7M0 598 625 A	KH10208
7M3 498 625	KH10084
7M3 498 625 A	KH10084
7M3 598 625	KH10208
8E0 498 625 B	KH20032
8E0598611	KH20040
8J0 598 625	KH30002
8J0 598 625A	KH30002
8L0 498 625	KH10117
8L0 498 625 B	KH10117
8S0 598 611	KH20004
8V0 498 625	KH30048
8V0 498 625 A	KH30014
8V0 498 625 B	KH30048
8V0 598 611 A	KH20003
8V0 598 625	KH30048
8V0 598 625 B	KH30048
8V0 598 625C	KH30049
8X0 598 611	KH20009

**SKODA**

171 498 625A	KH10186
171 498 625B	KH10186
171 498 625C	KH10186
171 498 625D	KH10186
191 598 625	KH00003
1H0 498 625	KH10193
1J0 498 625	KH10001
1J0 598 477	KH20010
1J0 598 625	KH10001
1K0 407 621 E	KH30048
1K0 498 621	KH30048
1S0 498 625	KH10010
1S0 498 625A	KH10010
1S0 598 611	KH20021
1T0 498 621	KH30002
1T0 598 611	KH20004
1T0 598 611 B	KH20004
311 405 625 F	KH00003
311 405 625 N	KH00003
311 405 645	KH00003
311 405 645 B	KH00003
357 407 625 A	KH10193
3C0 498 621	KH30002
3G0 598 611	KH20004
3G0 598 611 A	KH20004
4A0 498 625	KH10069
4B0 498 625	KH10066
4B0 498 625 A	KH10069
5K0 498 621	KH30002
5K0 498 621 A	KH30048
5Q0 407 621 A	KH30049
5QF 598 611	KH20004
5WA 407 621	KH30048
5WA 407 621 A	KH30049
6C0 407 621	KH30045
6Q0 407 621 AB	KH20027
6Q0 407 621 AB	KH20028
6Q0 407 621 AD	KH30045
6Q0 407 621 AF	KH20027
6Q0 407 621 AF	KH20028
6Q0 407 621 AH	KH30045
6Q0 407 621 AJ	KH30045
6Q0 407 621 AL	KH20027

**SKODA**

6Q0 407 621 AL	KH20028
6Q0 407 621 BG	KH20024
6Q0 407 621 BH	KH20024
6Q0 407 621 BK	KH20027
6Q0 407 621 BK	KH20028
6Q0 407 621 BP	KH20027
6Q0 407 621 BP	KH20028
6Q0 407 621 BR	KH30045
6Q0 407 621 CA	KH20024
6Q0 407 621 CB	KH20024
6Q0 598 611	KH20009
6Q0 598 611 F	KH20009
6R0 407 621 A	KH30045
6R0 407 621 C	KH20027
6R0 407 621 C	KH20028
6R0 407 621 E	KH30045
6R0 407 621 F	KH20024
6R0 407 621 G	KH20024
6U0 407 625 A	KH10162
6U0 498 002	KH10162
6U0 498 003	KH10162
8E0 498 625 B	KH20032
8E0 501 611	KH30095
8E0 501 611 J	KH30095
8J0 598 625	KH30045
8J0 598 625A	KH30002
8S0 598 611	KH20004
8V0 498 625	KH30048
8V0 498 625 A	KH30014
8V0 498 625 B	KH30048
8V0 598 611 A	KH20003
8V0 598 625	KH30048
8V0 598 625 B	KH30048
8V0 598 625C	KH30049
8X0 598 611	KH20009
969106801	KH10162

**SMART**

0001870V023000000	KH20054
0002072V010000000	KH30160
4543300059	KH20072
A 451 330 00 59	KH20123
A 451 330 01 59	KH20123
A 451 350 01 35	KH30172
A 451 350 02 35	KH30172
A 453 356 00 00	KH30029
A 454 350 01 35	KH30186

**SSANGYONG**

4143103210	KH00083
4143103210X	KH00083
4143203210	KH00083
4143203210X	KH00083

**SUBARU**

28016-AA011	KH10359
28016-AA020	KH10345
28016-AA030	KH10345
28016-PA010	KH10363
28063-AA-010	KH20177
28063-AC-000	KH20177
28316-FE000	KH10359
28373-AG000	KH30092
28373-AG001	KH30092
28373-FG000	KH30092
28473-AG000	KH30036
28473-AG001	KH30036
28473-FG000	KH30136
28473-FG010	KH30154
28473-SC000	KH30136
28473-Va000	KH30154
28473-ZR000	KH30154
28474-AE000	KH20154
28474-AG000	KH30036

**SUZUKI**

09262-25061	KH00048
09262-30069	KH00048
09262-30103	KH00115
09262-30103	KH00139
09262-350031	KH00047
09262-35007	KH00047
09265-41001	KH00018
09267-35003	KH10401
09267-36002	KH10375
09267-40001	KH10413
09269-35009	KH00069
09269-35009	KH00074
09269-35009	KH00138
09269-35009	KH00138
09269-35010	KH00064
09269-41001	KH10072
43401-65D10	KH20107
43401-65J01	KH30090
43401-65J02	KH30090

**SUZUKI**

43402-54G22	KH20122
43402-57L50	KH30090
43402-57L51	KH30090
43402-60G20	KH20122
43402-60G21	KH20122
43402-79J00	KH30108
43402-79J01	KH30108
43402-79J02	KH30108
43402-79J50	KH30075
43402-79J51	KH20024
43402-79J52	KH30075
43402-80J50	KH30197
43402-80J51	KH30197
43402-80J52	KH30197
43440-51K00	KH10137
43440-56K00	KH10022
43440-71L00	KH10137
43440-74F00	KH10215
43440-78A00	KH10215
43440-79J00	KH10022
43440-80J00	KH10022
43440-86G00	KH10121
43462-84A00	KH10118
43462-85C00	KH10072
43591-65D00	KH00049
46860 62J00	KH10030
46860 62J01	KH10030
46860 63J00	KH10030
46860 63J01	KH10030
46860-76G01	KH10124
46860-M68K00	KH10033
46860-M68K01	KH10033
46860-M68K10	KH10033

**TOYOTA**

04421-30011	KH00054
04421-30012	KH00054
04421-35010	KH00042
04421-35020	KH00042
42409-05010	KH20162
42409-19015	KH20174
42409-20010	KH20162
42409-42010	KH20172
42410-0E050	KH30118
42410-30020	KH30151
42410-30021	KH30151
42410-42020	KH30135
42410-42040	KH30013
42450-02060	KH30169
42450-02120	KH30035
42450-05030	KH20162
42450-05040	KH30117
42450-05080	KH30150
42450-05081	KH30150
42450-0D010	KH30097
42450-0D050	KH30082
42450-0F010	KH30173
42450-0F020	KH30141
42450-0F021	KH30141
42450-0H010	KH30064
42450-12030	KH20174
42450-12070	KH30169
42450-12090	KH30028
42450-12100	KH30035
42450-12110	KH30150
42450-12140	KH30028
42450-42030	KH30194
42450-47030	KH30117
42450-47040	KH30040
42450-52020	KH30097
42450-52021	KH30097
42450-52060	KH30082
42450-60050	KH20125
42450-63011	KH30117
42450-74010	KH30148
42450-74020	KH30082
42460-60010	KH20131
43350-42020	KH30018
43510-47010	KH30124
43510-47011	KH30124
43550-02010	KH30017
43550-02020	KH30018
43550-02070	KH30017
43550-02080	KH30018
435500-30010	KH30138
43550-12010	KH30017
43550-42010	KH30017
43550-47010	KH30121
43550-47011	KH30121
43560-60010	KH20089
43570-60010	KH20063
43570-60011	KH20063
90080-36043	KH10204
90080-36064	KH00134
90080-36067	KH00134
90080-36067	KH00140

**TOYOTA**

90080-36087	KH10002
90080-36087	KH10402
90080-36098	KH00140
90080-36137	KH10002
90080-37030	KH20089
90363-40020	KH00030
90363-40066	KH10002
90363-40067	KH10002
90363-40068	KH00116
90363-40072	KH00071
90363-40072	KH00116
90363-40079	KH10019
90363-W0001	KH10021
90366-17010	KH00027
90366-27001	KH00027
90366-T0007	KH10379
90368-17017	KH00027
90368-17017	KH00056
90368-21065	KH00042
90368-26027	KH00056
90368-34001	KH00042
90368-45087	KH00134
90368-49084	KH00134
90369-35029	KH10179
90369-35034	KH10381
90369-35060	KH10412
90369-38021	KH10014
90369-38022	KH10014
90369-43005	KH10207
90369-43008	KH10005
90369-43008	KH10182
90369-43008	KH10361
90369-43009	KH10182
90369-47001	KH10135
90369-48001	KH10389
90369-49001	KH10347
90369-49002	KH10347
90369-54001	KH10395
90369-54002	KH10395
90369-A0002	KH10025
90369-T0003	KH20089
90369-T0004	KH10021
90369-T0007	KH10021
90369-W0001	KH10106
90903-63006	KH10381
SU001-A0982	KH10119
SU 001A 1005	KH30015
SU 001A 1006	KH30016

**TOYOTA (FAW)**

42410-42040	KH30013
-------------	---------

**TRIUMPH**

117853	KH00052
GHB110	KH00053
GHB110	KH00123
GHB111	KH00053
GHB111	KH00123
GHB117	KH00052

**TVR**

GHB110	KH00123
GHB111	KH00123

**VAG**

1J0 498 625	KH10001
1J0 598 625	KH10001
8V0 498 625 A	KH30014

**VAUXHALL**

11055109	KH00093
11055119	KH00093
13502785	KH30070
13502785	KH30105
13502785	KH30183
13502785	KH30196
13502828	KH30119
13502829	KH30089
13502872	KH30133
13502873	KH30134
13507374	KH30070
13507374	KH30105
13507374	KH30183
13507374	KH30196
13580135	KH30070
13580135	KH30105
13583478	KH30119
13583479	KH30089
13590795	KH30089
13591999	KH30134
16 03 022	KH10348
16 03 025	KH00088
16 03 049	KH00088
16 03 065	KH00005

**VAUXHALL**

16 03 143	16 03 191	16 03 193	16 03 195	16 03 196	1603208	1603209	1603211	16 03 243	16 03 253	16 03 254	16 03 255	16 03 282	16 03 294	16 03 295	16 03 296	16 03 337	16 03 338	16 03 841	16 04 002	16 04 003	16 04 004	16 04 005	16 04 007	16 04 017	16 04 018	1604020	16 04 287	16 04 292	16 04 301	16 04 302	16 04 306	16 04 307	16 04 314	16 04 315	16 04 316	16 04 358	1604360	25903295	25903358	3 28 000	3 28 001	3 28 002	3 28 003	3 28 0037	3 28 006	3 28 006	3 28 011	3 28 012	328013	328014	3 28 016	3 28 018	3 28 021	3 28 023	3 28 038	3 28 042	3 28 042	3 28 042	3 28 103	3 28 103	3 28 106	3 28 109	3 28 292	3 28 292	3 28 292	3 28 292	3 28 292	328980	3 30 012	3 30 019	3 30 023	4 14 301	4 15 203	4 20 004	4 20 240	4 21 000	44 03 023	44 030 44	44 03 942	44 08 277	4408668	44 08 699	4412598	44 19 183	44 19 184	44 21 076	44 213 78	44 22 229	4430305	45 01 154	45 01 155	47 00 322	47 06 538	47 06 538	47 09 078	47 11 556
-----------	-----------	-----------	-----------	-----------	---------	---------	---------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	---------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	-----------	---------	----------	----------	----------	----------	----------	----------	-----------	----------	----------	----------	----------	--------	--------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	--------	----------	----------	----------	----------	----------	----------	----------	----------	-----------	-----------	-----------	-----------	---------	-----------	---------	-----------	-----------	-----------	-----------	-----------	---------	-----------	-----------	-----------	-----------	-----------	-----------	-----------

KH30061	KH10108	KH00005	KH10376	KH10206	KH30057	KH30058	KH30059	KH30061	KH30072	KH30046	KH30065	KH30074	KH30061	KH30065	KH30074	KH10042	KH10065	KH30084	KH30114	KH30054	KH30055	KH30130	KH10113	KH20017	KH20017	KH20030	KH10218	KH10219	KH30114	KH30054	KH30054	KH30055	KH30071	KH30041	KH30044	KH20017	KH20030	KH30087	KH30068	KH30119	KH30089	KH30133	KH30134	KH30134	KH30070	KH30105	KH10151	KH10198	KH20109	KH20093	KH30119	KH00093	KH30089	KH10151	KH30089	KH30070	KH30183	KH30196	KH10108	KH10218	KH10376	KH00026	KH30070	KH30105	KH30183	KH30196	KH10063	KH00093	KH00026	KH00026	KH00026	KH00065	KH10219	KH20017	KH20118	KH30055	KH10100	KH10064	KH00104	KH30055	KH10014	KH10064	KH10113	KH30055	KH10113	KH20017	KH30071	KH30061	KH30061	KH30041	KH30044	KH30072	KH30046	KH30065	KH30074	KH30061	KH30065	KH30074	KH30084	KH10042	KH10065	KH20017	KH20030	KH10137	KH10139	KH10138	KH00026	KH00026	KH00086	KH00086	KH10030	KH10151	KH10198	KH20109	KH20093	KH20017	KH10151	KH10174	KH20030	KH20017	KH30068	KH30087
---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------

**VAUXHALL**

48 04 658	48 09 314	48 14 139	48 14 304	90005147	9005147	90065431	90235281	90279332	90447280	904486460	90486461	90486463	90486468	90510542	90510543	90510544	90510629	90511494	90540069	90540262	9111023	9111044	9111942	91149607	91159917	91160086	91160087	9117619	9117620	9117622	9119931	9120128	9120129	9120273	9161454	9161455	9195608	9196286	9196298	9203934	9213602	9213602	92 14 025	931168843	93161059	93161376	93168535	93168760	93170611	93171495	93175327	93178625	93178626	93178651	93178652	93178661	93182913	93186387	93186388	93186389	93188477	93188889	93188890	93190215	93190216	93193920	93197149	93197150	94227041	94258819	95507285	95507286	95507796	95511623	95511624	95511659	95511660	95512288	95513921	95516872	95517093	95517150	96626339	96626439
-----------	-----------	-----------	-----------	----------	---------	----------	----------	----------	----------	-----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	---------	---------	---------	----------	----------	----------	----------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	---------	-----------	-----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------	----------

**VOLVO**

271585	271795	272456	274378	30639875	30714730	30736501	30748989	30794650
--------	--------	--------	--------	----------	----------	----------	----------	----------

KH20164	KH20164	KH30106	KH30128	KH30123	KH20088	KH20073	KH30104	KH30109
---------	---------	---------	---------	---------	---------	---------	---------	---------





K ...		K ...		K ...		K ...	
KH00002	12	KH00102	31	KH10066	51	KH10176	72
KH00003	12	KH00103	31	KH10069	51	KH10177	72
KH00004	12	KH00104	32	KH10070	52	KH10178	72
KH00005	12	KH00105	32	KH10072	52	KH10179	72
KH00007	13	KH00106	32	KH10073	52	KH10180	72
KH00008	13	KH00107	32	KH10074	52	KH10181	73
KH00009	13	KH00108	32	KH10075	52	KH10182	73
KH00010	13	KH00109	33	KH10076	53	KH10183	73
KH00011	13	KH00110	33	KH10077	53	KH10184	73
KH00013	14	KH00111	33	KH10078	53	KH10185	73
KH00014	14	KH00112	33	KH10079	53	KH10186	74
KH00015	14	KH00113	33	KH10080	53	KH10187	74
KH00017	14	KH00115	34	KH10081	54	KH10188	74
KH00018	14	KH00116	34	KH10082	54	KH10189	74
KH00019	15	KH00117	34	KH10083	54	KH10190	74
KH00020	15	KH00118	34	KH10084	54	KH10191	75
KH00021	15	KH00119	34	KH10085	54	KH10192	75
KH00022	15	KH00120	35	KH10086	55	KH10193	75
KH00023	15	KH00121	35	KH10089	55	KH10194	75
KH00024	16	KH00122	35	KH10090	55	KH10195	75
KH00025	16	KH00123	35	KH10091	55	KH10196	76
KH00026	16	KH00124	35	KH10092	55	KH10197	76
KH00027	16	KH00125	36	KH10093	56	KH10198	76
KH00028	16	KH00126	36	KH10097	56	KH10199	76
KH00029	17	KH00127	36	KH10100	56	KH10200	77
KH00030	17	KH00128	36	KH10101	56	KH10201	77
KH00031	17	KH00129	36	KH10104	56	KH10202	77
KH00032	17	KH00130	37	KH10105	57	KH10203	77
KH00033	17	KH00131	37	KH10106	57	KH10204	77
KH00034	18	KH00132	37	KH10107	57	KH10205	78
KH00035	18	KH00133	37	KH10108	57	KH10206	78
KH00036	18	KH00134	37	KH10109	57	KH10207	78
KH00037	18	KH00135	38	KH10110	58	KH10208	78
KH00038	18	KH00136	38	KH10111	58	KH10209	78
KH00039	19	KH00137	38	KH10112	58	KH10210	79
KH00040	19	KH00138	38	KH10113	58	KH10211	79
KH00041	19	KH00139	38	KH10114	58	KH10212	79
KH00042	19	KH00140	39	KH10115	59	KH10213	79
KH00043	19	KH10001	39	KH10116	59	KH10214	79
KH00044	20	KH10002	39	KH10117	59	KH10215	80
KH00045	20	KH10003	39	KH10118	59	KH10216	80
KH00046	20	KH10004	39	KH10119	60	KH10217	80
KH00047	20	KH10005	40	KH10120	60	KH10218	80
KH00048	20	KH10006	40	KH10121	60	KH10219	80
KH00049	21	KH10007	40	KH10122	60	KH10220	81
KH00050	21	KH10008	40	KH10123	61	KH10221	81
KH00051	21	KH10009	40	KH10124	61	KH10222	81
KH00052	21	KH10010	41	KH10125	61	KH10223	81
KH00053	21	KH10011	41	KH10126	61	KH10224	81
KH00054	22	KH10013	41	KH10127	61	KH10225	82
KH00055	22	KH10014	41	KH10128	62	KH10226	82
KH00056	22	KH10016	41	KH10129	62	KH10227	82
KH00057	22	KH10017	42	KH10130	62	KH10228	82
KH00058	22	KH10018	42	KH10132	62	KH10229	83
KH00059	23	KH10019	42	KH10133	62	KH10230	83
KH00060	23	KH10021	42	KH10134	63	KH10231	83
KH00061	23	KH10022	43	KH10135	63	KH10232	83
KH00062	23	KH10023	43	KH10136	63	KH10233	84
KH00063	23	KH10024	43	KH10137	63	KH10234	84
KH00064	24	KH10025	43	KH10138	63	KH10345	84
KH00065	24	KH10026	43	KH10139	64	KH10346	84
KH00066	24	KH10027	44	KH10140	64	KH10347	84
KH00067	24	KH10028	44	KH10141	64	KH10348	85
KH00068	24	KH10029	44	KH10142	64	KH10349	85
KH00069	25	KH10030	44	KH10143	65	KH10350	85
KH00070	25	KH10031	44	KH10144	65	KH10351	85
KH00071	25	KH10032	45	KH10145	65	KH10352	86
KH00072	25	KH10033	45	KH10146	65	KH10353	86
KH00073	25	KH10034	45	KH10147	65	KH10354	86
KH00074	26	KH10035	45	KH10148	66	KH10355	86
KH00075	26	KH10037	45	KH10149	66	KH10356	87
KH00076	26	KH10038	46	KH10150	66	KH10357	87
KH00077	26	KH10039	46	KH10151	66	KH10358	87
KH00078	26	KH10040	46	KH10152	67	KH10359	87
KH00079	27	KH10041	46	KH10153	67	KH10360	87
KH00080	27	KH10042	46	KH10154	67	KH10361	88
KH00081	27	KH10043	47	KH10155	67	KH10362	88
KH00082	27	KH10044	47	KH10156	67	KH10363	88
KH00083	27	KH10046	47	KH10157	68	KH10364	88
KH00084	28	KH10047	47	KH10158	68	KH10365	88
KH00085	28	KH10048	48	KH10159	68	KH10366	89
KH00086	28	KH10049	48	KH10160	68	KH10367	89
KH00087	28	KH10050	48	KH10161	68	KH10368	89
KH00088	28	KH10051	48	KH10162	69	KH10369	89
KH00089	29	KH10052	48	KH10163	69	KH10370	89
KH00090	29	KH10053	49	KH10164	69	KH10371	90
KH00091	29	KH10054	49	KH10165	69	KH10372	90
KH00092	29	KH10055	49	KH10166	69	KH10373	90
KH00093	29	KH10056	49	KH10167	70	KH10374	90
KH00094	30	KH10057	49	KH10168	70	KH10375	90
KH00095	30	KH10058	50	KH10169	70	KH10376	91
KH00096	30	KH10060	50	KH10170	70	KH10377	91
KH00097	30	KH10061	50	KH10171	70	KH10378	91
KH00098	30	KH10062	50	KH10172	71	KH10379	91
KH00099	31	KH10063	50	KH10173	71	KH10380	91
KH00100	31	KH10064	51	KH10174	71	KH10381	92
KH00101	31	KH10065	51	KH10175	71	KH10383	92

41279  
30185  
21912

K ...		K ...		K ...		K ...	
KH10384	92	KH20068	112	KH20166	132	KH30075	154
KH10385	92	KH20069	112	KH20167	132	KH30076	154
KH10386	92	KH20070	113	KH20168	133	KH30077	154
KH10387	93	KH20071	113	KH20169	133	KH30078	154
KH10388	93	KH20072	113	KH20170	133	KH30079	155
KH10389	93	KH20073	113	KH20171	133	KH30080	155
KH10390	93	KH20074	113	KH20172	133	KH30081	155
KH10391	93	KH20075	114	KH20173	134	KH30082	155
KH10392	94	KH20076	114	KH20174	134	KH30083	156
KH10393	94	KH20077	114	KH20175	134	KH30084	156
KH10394	94	KH20078	114	KH20176	134	KH30085	156
KH10395	94	KH20079	114	KH20177	134	KH30086	156
KH10396	94	KH20080	115	KH20178	135	KH30087	156
KH10397	95	KH20081	115	KH20179	135	KH30088	157
KH10398	95	KH20082	115	KH20180	135	KH30089	157
KH10399	95	KH20083	115	KH20181	135	KH30090	157
KH10400	95	KH20084	116	KH20182	135	KH30091	157
KH10401	95	KH20085	116	KH20183	136	KH30092	158
KH10402	96	KH20086	116	KH20184	136	KH30093	158
KH10403	96	KH20087	116	KH20185	136	KH30094	158
KH10404	96	KH20088	117	KH20186	136	KH30095	158
KH10405	96	KH20089	117	KH20187	136	KH30096	159
KH10406	96	KH20090	117	KH20188	137	KH30097	159
KH10407	97	KH20091	117	KH20189	137	KH30098	159
KH10408	97	KH20092	117	KH20190	137	KH30099	159
KH10409	97	KH20093	118	KH20191	137	KH30100	159
KH10410	97	KH20094	118	KH20192	137	KH30101	160
KH10411	97	KH20095	118	KH20193	138	KH30102	160
KH10412	98	KH20096	118	KH20194	138	KH30103	160
KH10413	98	KH20097	118	KH20195	138	KH30104	160
KH10414	98	KH20098	119	KH20196	138	KH30105	160
KH10415	98	KH20099	119	KH20197	138	KH30106	160
KH20001	98	KH20100	119	KH20198	139	KH30107	161
KH20002	99	KH20101	119	KH20199	139	KH30108	161
KH20003	99	KH20102	120	KH20200	139	KH30109	161
KH20004	99	KH20103	120	KH20201	139	KH30110	161
KH20005	99	KH20104	120	KH20202	139	KH30111	161
KH20006	99	KH20105	120	KH30002	140	KH30112	162
KH20007	100	KH20106	120	KH30003	140	KH30113	162
KH20008	100	KH20107	121	KH30004	140	KH30114	162
KH20009	100	KH20108	121	KH30005	140	KH30115	162
KH20010	100	KH20109	121	KH30006	140	KH30116	163
KH20011	100	KH20110	121	KH30007	141	KH30117	163
KH20012	101	KH20111	121	KH30008	141	KH30118	163
KH20013	101	KH20112	122	KH30009	141	KH30119	163
KH20014	101	KH20113	122	KH30010	141	KH30120	163
KH20015	101	KH20114	122	KH30011	141	KH30121	164
KH20016	101	KH20115	122	KH30012	141	KH30122	164
KH20017	102	KH20116	122	KH30013	142	KH30123	164
KH20018	102	KH20117	123	KH30014	142	KH30124	164
KH20019	102	KH20118	123	KH30015	142	KH30125	164
KH20020	102	KH20119	123	KH30016	142	KH30126	165
KH20021	102	KH20120	123	KH30017	143	KH30127	165
KH20022	103	KH20121	123	KH30018	143	KH30128	165
KH20023	103	KH20122	124	KH30019	143	KH30129	165
KH20024	103	KH20123	124	KH30020	143	KH30130	166
KH20025	103	KH20124	124	KH30021	144	KH30131	166
KH20026	103	KH20125	124	KH30022	144	KH30132	166
KH20027	104	KH20126	124	KH30023	144	KH30133	166
KH20028	104	KH20127	125	KH30024	144	KH30134	166
KH20029	104	KH20128	125	KH30025	144	KH30135	166
KH20030	104	KH20129	125	KH30026	144	KH30136	166
KH20031	105	KH20130	125	KH30027	145	KH30137	167
KH20032	105	KH20131	125	KH30028	145	KH30138	167
KH20033	105	KH20132	126	KH30029	145	KH30139	167
KH20034	105	KH20133	126	KH30030	145	KH30140	167
KH20035	105	KH20134	126	KH30031	146	KH30141	167
KH20036	106	KH20135	126	KH30032	146	KH30142	168
KH20037	106	KH20136	126	KH30033	146	KH30143	168
KH20038	106	KH20137	127	KH30034	146	KH30144	168
KH20039	106	KH20138	127	KH30035	147	KH30145	168
KH20040	106	KH20139	127	KH30036	147	KH30146	168
KH20041	107	KH20140	127	KH30037	147	KH30147	169
KH20042	107	KH20141	127	KH30038	147	KH30148	169
KH20043	107	KH20142	128	KH30039	147	KH30149	169
KH20044	107	KH20143	128	KH30040	148	KH30150	169
KH20045	107	KH20144	128	KH30041	148	KH30151	169
KH20046	108	KH20145	128	KH30042	148	KH30152	170
KH20047	108	KH20146	128	KH30043	148	KH30153	170
KH20048	108	KH20147	129	KH30044	148	KH30154	170
KH20049	108	KH20148	129	KH30045	149	KH30155	170
KH20050	108	KH20149	129	KH30046	149	KH30156	170
KH20051	109	KH20150	129	KH30047	149	KH30157	171
KH20052	109	KH20151	129	KH30048	149	KH30158	171
KH20053	109	KH20152	130	KH30049	149	KH30159	171
KH20054	109	KH20153	130	KH30050	149	KH30160	171
KH20055	110	KH20154	130	KH30051	150	KH30161	171
KH20056	110	KH20155	130	KH30052	150	KH30162	171
KH20057	110	KH20156	130	KH30053	150	KH30163	171
KH20058	110	KH20157	131	KH30054	150	KH30164	172
KH20059	111	KH20158	131	KH30055	151	KH30165	172
KH20060	111	KH20159	131	KH30056	151	KH30166	172
KH20061	111	KH20160	131	KH30057	151	KH30167	172
KH20062	111	KH20161	131	KH30058	151	KH30168	172
KH20063	111	KH20162	132	KH30059	152	KH30169	173
KH20064	112	KH20163	132	KH30060	152	KH30170	173
KH20065	112	KH20164	132	KH30061	152	KH30171	173
KH20066	112			KH30062	153	KH30172	173
KH20067	112			KH30063	153	KH30173	173
				KH30064	153	KH30174	174
				KH30065	153	KH30175	174
				KH30066	153	KH30176	174

41279  
30185  
21912

---

<b>K ...</b>	
KH30177	174
KH30178	174
KH30179	175
KH30181	175
KH30182	175
KH30183	175
KH30184	175
KH30185	176
KH30186	176
KH30187	176
KH30188	176
KH30189	176
KH30190	177
KH30191	177
KH30192	177
KH30193	177
KH30194	177
KH30195	178
KH30196	178
KH30197	178

**NSK Sales Offices – Europe, Middle East and Africa**

**UK**

NSK UK Ltd.  
Northern Road, Newark  
Nottinghamshire NG24 2JF  
Tel. +44 (0) 1636 605123  
Fax +44 (0) 1636 643276  
info-uk@nsk.com

**France**

NSK France S.A.S.  
Quartier de l'Europe  
2, rue Georges Guynemer  
78283 Guyancourt Cedex  
Tel. +33 (0) 1 30573939  
Fax +33 (0) 1 30570001  
info-fr@nsk.com

**Middle East**

NSK Bearings Gulf Trading Co.  
JAFZA View 19, Floor 24 Office 2/3  
PO Box 262163  
Jebel Ali Downtown, Dubai, UAE  
Tel. +971 (0) 4 804 8205  
Fax +971 (0) 4 884 7227  
info-me@nsk.com

**Spain**

NSK Spain, S.A.  
C/ Tarragona, 161 Cuerdo Bajo  
2ª Planta  
08014 Barcelona  
Tel. +34 93 2892763  
Fax +34 93 4335776  
info-es@nsk.com

**Germany, Austria, Benelux,  
Switzerland, Nordic**

NSK Deutschland GmbH  
Harkortstraße 15  
40880 Ratingen  
Tel. +49 (0) 2102 4810  
Fax +49 (0) 2102 4812290  
info-de@nsk.com

**Poland & CEE**

NSK Polska Sp. z o.o.  
Warsaw Branch  
Ul. Migdałowa 4/73  
02-796 Warszawa  
Tel. +48 22 645 15 25  
Fax +48 22 645 15 29  
info-pl@nsk.com

**Turkey**

NSK Rulmanları Orta Doğu Tic. Ltd. Şti.  
Cevizli Mah. D-100 Güney Yan Yol  
Kuriş Kule İş Merkezi No:2 Kat:4  
Kartal - İstanbul  
Tel. +90 216 5000 675  
Fax +90 216 5000 676  
turkey@nsk.com

**Italy**

NSK Italia S.p.A.  
Via Garibaldi, 215  
20024 Garbagnate  
Milanese (MI)  
Tel. +39 02 995 191  
Fax +39 02 990 25 778  
info-it@nsk.com

**South Africa**

NSK South Africa (Pty) Ltd.  
25 Galaxy Avenue  
Linbro Business Park  
Sandton 2146  
Tel. +27 (011) 458 3600  
Fax +27 (011) 458 3608  
nsk-sa@nsk.com

**Please also visit our website: [www.nskeurope.com](http://www.nskeurope.com)  
Global NSK: [www.nsk.com](http://www.nsk.com)**

