


TECHNICAL INSIGHT

A PUBLICATION OF NSK EUROPE

Bearing tolerances

Standard values

The tolerances for the dimensions and running accuracy of bearings are set out in ISO 492/199/582. This largely corresponds to DIN 620.



Accuracy classes

Apart from the standard accuracies defined by DIN/ISO, higher accuracies are specified by 6x, 6, 5, 4 and 2.

Bearing types and tolerance classes

Bearing types				Applicable tolerance classes			
Deep-groove ball bearings		Normal	Class 6	Class 5	Class 4	Class 2	
Angular-contact ball bearings			Normal	Class 6	Class 5	Class 4	Class 2
Self-aligning ball bearings			Normal	Class 6	Class 5	-	_
Cylindrical roller bearings			Normal	Class 6	Class 5	Class 4	Class 2
Needle roller bearings (solid type)			Normal	Class 6	Class 5	Class 4	_
Spherical roller bearings			Normal	Class 6	Class 5	-	_
Tapered	roller	Metric design	Normal Class 6X	-	Class 5	Class 4	_
bearin	igs	Inch design	ANSI/ABMA Class 4	ANSI/ABMA Class 2	ANSI/ABMA Class 3	ANSI/ABMA Class 0	ANSI/ABMA Class 00
Magneto bearings			Normal	Class 6	Class 5	_	_
Thrust ball bearings			Normal	Class 6	Class 5	Class 4	_
bearings			Normal	_	_	-	_
	JIS ⁽¹⁾		Class 0	Class 6	Class 5	Class 4	Class 2
ards	DIN ⁽²⁾		P0	P6	P5	P4	P2
Equivalent standards (reference)	ANSI/ ABMA ⁽³⁾	Ball bearing	ABEC 1	ABEC 3	ABEC 5 (Class 5P)	ABEC 7 (Class 7P)	ABEC 9 (Class 9P)
quive (r		Roller bearing	RBEC 1	RBEC 3	RBEC 5	_	-
ш		Tapered roller bearing	Class 4	Class 2	Class 3	Class 0	Class 00

Notes

The tolerances of the accuracy class "Normal" (P0) are sufficient for general applications in most cases.

⁽¹⁾ JIS: Japanese Industrial Standards


⁽²⁾ DIN: Deutsche Industrie Norm

⁽³⁾ ANSI/ABMA: The American Bearing Manufacturers Association


Typical tolerance classes for specific applications (reference)

Bearing requirement, operating conditions	Examples of applications	Tolerance classes
High running accuracy is required	VTR drum spindles Magnetic disk spindles for computers Machine tool main spindles Rotary printing presses Rotary tables of vertical presses, etc. Roll necks of cold rolling mill backup rolls Slewing bearings for parabolic antennae	P5 P5, P4, P2 P5, P4, P2 P5 P5, P4 Higher than P4 Higher than P4
Very high speed is required	Dental drills Gyroscopes High-frequency spindles superchargers Compresors Centrifugal separators Main shafts for jet engines	Class 7P, Class 5P Class 7P, P4 Class 7P, P4 P5, P4 P5, P4 Higher than P4
Low torque and low torque variation are required	Gyroscope gimbals Servomechanisms Potentiometric controllers	Class 7P, P4 Class 7P, Class 5P Class 7P

Measuring methods



Running accuracy	Inner ring	Outer ring	Measuring point
	rotating	stationary	Α
Kea	stationary	rotating	Α
Sia	rotating	stationary	B ₁
Sea	stationary	rotating	B ₂
Sd	rotating	stationary	С
SD	-	rotating	D
S _i , S _e	Only the shaft or housing or o	E	



- r: Chamfer dimension of inner/outer ring
- r₁: Chamfer dimension of inner/outer ring (front side) or the centre washer of thrust ball bearings

Remarks: The exact shape of the edge reduction results from the radius that is reduced in the area of the face and rolling surfaces. Make sure that there is no contact between the surrounding structure and the bearing in the area of the edge reduction. The radius here is smaller than the r (min) or r1 (min) value quoted in the bearing table. (According to DIN 616, ISO 15 and ISO 355.)

Tolerances for tapered bores (Class Normal)

